

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333177-927

Luminaire Tested: **S125DIP-S610D590U927-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333177-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S610D590U927-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3661.8 lumens
Efficiency: N/A
Efficacy: 111.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333177-927

CATALOG NUMBER: S125DIP-S610D590U927-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333177-927

CATALOG NUMBER: S125DIP-S610D590U927-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60
1	99	94	90	87	91	88	84	81	75	72	70	63	62	60	53	52	50
2	90	82	76	71	83	76	71	66	66	62	58	56	53	50	46	44	42
3	82	72	65	59	76	67	61	56	58	53	49	49	45	42	41	38	36
4	75	64	56	50	69	60	53	47	51	46	42	44	40	36	37	34	31
5	69	57	49	43	64	53	46	40	46	40	36	39	35	31	33	30	27
6	63	51	43	37	59	48	40	35	41	36	31	36	31	28	30	27	24
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	27	24	21
8	54	42	34	29	50	39	32	27	34	29	25	30	25	22	25	22	19
9	51	38	31	26	47	36	29	24	31	26	22	27	23	20	23	20	17
10	47	35	28	23	44	33	26	22	29	24	20	25	21	18	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4914	4914	4914
5°	4924	4877	4909
10°	4894	4844	4871
15°	4841	4785	4805
20°	4766	4704	4712
25°	4684	4606	4603
30°	4583	4502	4480
35°	4475	4389	4328
40°	4364	4268	4207
45°	4244	4156	4074
50°	4112	4022	3900
55°	3985	3869	3762
60°	3834	3716	3584
65°	3651	3533	3412
70°	3478	3320	3206
75°	3169	3064	2959
80°	2819	2775	2708
85°	2453	2497	2364



TEST NUMBER: P333177-927

CATALOG NUMBER: S125DIP-S610D590U927-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.7	2.0
10°-20°	202.6	5.5
20°-30°	299.2	8.2
30°-40°	349.1	9.5
40°-50°	350.6	9.6
50°-60°	307.8	8.4
60°-70°	229.3	6.3
70°-80°	131.1	3.6
80°-90°	39.4	1.1
90°-100°	162.5	4.4
100°-110°	349.2	9.5
110°-120°	327.8	9.0
120°-130°	265.6	7.3
130°-140°	213.2	5.8
140°-150°	160.9	4.4
150°-160°	113.2	3.1
160°-170°	66.7	1.8
170°-180°	21.7	0.6
0°-30°	573.6	15.7
0°-40°	922.7	25.2
0°-60°	1581.1	43.2
0°-90°	1980.9	54.1
90°-120°	839.5	22.9
90°-150°	1479.1	40.4
90°-180°	1681.0	45.9
0°-180°	3661.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	761	761	761	761	761	
5°	760	758	752	757	757	72
15°	724	722	716	719	719	204
25°	657	654	646	648	646	302
35°	568	565	557	554	549	355
45°	465	462	455	448	446	358
55°	354	352	344	338	334	316
65°	239	237	231	226	223	237
75°	127	126	123	121	119	135
85°	33	34	34	33	32	37
90°	0	4	7	9	10	3
95°	15	44	400	182	106	16
105°	51	71	328	645	599	54
115°	91	110	263	567	667	90
125°	126	148	252	451	526	112
135°	148	178	250	378	436	115
145°	173	198	251	313	344	108
155°	197	212	245	277	289	91
165°	215	221	235	249	253	61
175°	224	224	226	228	227	21
180°	224	224	224	224	224	



TEST NUMBER: P333177-927

CATALOG NUMBER: S125DIP-S610D590U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	760.8	760.8	760.8	760.8	760.8	760.8	760.8	760.8	760.8	760.8	760.8
2.5°	762.7	762.4	762.1	761.8	761.4	760.7	759.7	758.6	757.6	756.5	757.6
5°	759.6	759.3	759.1	758.8	758.5	757.7	756.4	755.0	753.7	752.3	753.6
7.5°	752.6	752.3	752.1	751.8	751.5	750.7	749.2	747.7	746.2	744.8	745.9
10°	746.3	746.1	745.8	745.5	745.3	744.4	742.9	741.5	740.0	738.6	739.6
12.5°	738.6	738.2	737.7	737.2	736.7	735.8	734.4	733.1	731.7	730.3	731.2
15°	724.1	723.7	723.3	722.9	722.5	721.5	720.1	718.6	717.1	715.7	716.3
17.5°	707.3	706.8	706.2	705.6	705.0	703.9	702.4	700.8	699.3	697.8	698.6
20°	693.4	693.1	692.8	692.6	692.3	691.3	689.6	687.9	686.1	684.4	685.3
22.5°	679.4	678.9	678.4	677.9	677.5	676.4	674.8	673.2	671.5	669.9	670.5
25°	657.3	656.6	655.9	655.3	654.6	653.4	651.6	649.9	648.2	646.4	646.7
27.5°	631.4	631.0	630.6	630.2	629.8	628.7	626.9	625.1	623.3	621.5	621.5
30°	614.5	614.1	613.7	613.3	612.9	611.7	609.7	607.7	605.7	603.7	603.4
32.5°	596.2	595.6	595.0	594.4	593.7	592.6	590.8	589.0	587.2	585.4	584.9
35°	567.6	567.0	566.5	566.0	565.5	564.3	562.4	560.5	558.6	556.7	556.1
37.5°	537.8	537.2	536.5	535.8	535.2	533.9	532.2	530.4	528.6	526.9	525.9
40°	517.6	517.0	516.3	515.6	514.9	513.7	511.8	509.9	508.0	506.2	505.0
42.5°	496.0	495.4	494.8	494.2	493.7	492.5	490.6	488.8	486.9	485.0	483.9
45°	464.7	464.1	463.6	463.0	462.6	461.4	459.9	458.3	456.6	455.0	453.4
47.5°	430.9	430.9	431.0	431.0	431.0	430.1	428.2	426.3	424.4	422.4	420.8
50°	409.3	408.8	408.4	408.1	407.7	406.7	405.0	403.5	401.9	400.3	398.5
52.5°	387.1	386.8	386.6	386.3	386.0	384.9	383.3	381.5	379.9	378.1	376.6
55°	353.9	353.5	353.1	352.7	352.3	351.2	349.3	347.5	345.5	343.6	342.5
57.5°	318.9	318.7	318.5	318.2	318.1	317.1	315.5	313.9	312.4	310.9	309.3
60°	296.8	296.2	295.6	295.1	294.6	293.6	292.2	290.7	289.1	287.7	286.4
62.5°	273.6	273.2	272.7	272.4	271.9	271.1	269.8	268.5	267.3	266.0	264.6
65°	238.9	238.7	238.4	238.1	237.9	237.0	235.5	234.1	232.6	231.2	229.9
67.5°	205.3	204.8	204.2	203.7	203.1	202.3	201.2	200.1	199.0	197.9	196.9
70°	184.2	183.5	182.8	182.2	181.5	180.5	179.4	178.2	177.0	175.8	174.9
72.5°	161.1	160.6	160.2	159.7	159.2	158.6	157.9	157.1	156.3	155.5	154.6
75°	127.0	126.7	126.4	126.2	126.0	125.5	124.8	124.1	123.4	122.8	122.4
77.5°	95.6	95.5	95.4	95.2	95.1	94.9	94.5	94.2	93.8	93.4	93.2
80°	75.8	75.8	75.8	75.8	75.8	75.7	75.4	75.2	74.9	74.6	74.5
82.5°	58.5	58.3	58.1	57.8	57.7	57.5	57.4	57.4	57.4	57.3	57.0
85°	33.1	33.3	33.4	33.5	33.7	33.7	33.7	33.7	33.7	33.7	33.6
87.5°	13.1	13.2	13.4	13.5	13.7	13.9	13.9	13.9	13.9	13.9	14.0
90°	0.5	0.9	1.8	2.7	3.6	4.5	5.0	5.9	6.3	7.2	7.7
92.5°	5.5	6.7	10.5	16.1	23.8	37.1	61.7	103.1	148.1	145.7	118.0
95°	14.9	15.4	19.0	23.9	33.9	54.3	102.6	202.0	326.7	400.4	391.8
97.5°	24.8	25.3	27.8	32.8	41.7	56.4	88.4	161.2	291.8	427.5	495.7
100°	31.6	32.6	34.4	39.3	47.9	61.5	87.7	146.4	260.3	408.1	521.0
102.5°	39.2	39.8	41.2	46.6	54.4	67.6	90.9	140.3	236.4	373.7	505.8
105°	51.1	51.1	53.3	57.8	65.0	77.7	97.6	137.8	213.3	327.6	457.3
107.5°	62.7	63.5	65.7	69.4	76.9	88.3	107.6	142.0	203.5	295.9	407.8
110°	71.0	71.9	73.7	77.7	84.5	96.3	114.8	145.9	200.7	281.1	379.6



TEST NUMBER: P333177-927

CATALOG NUMBER: S125DIP-S610D590U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	79.3	80.2	81.6	85.7	92.4	103.9	121.7	151.0	200.7	272.4	358.6
115°	91.3	92.2	93.6	97.6	104.4	115.7	132.4	158.6	202.0	263.0	335.7
117.5°	102.1	103.5	105.0	109.0	116.7	127.6	143.5	167.3	204.9	258.4	322.1
120°	109.3	110.7	112.5	116.6	124.3	135.5	151.4	173.1	207.9	256.2	314.5
122.5°	116.9	118.0	119.4	123.4	131.9	143.1	159.0	179.6	210.4	254.4	308.0
125°	126.5	127.5	129.7	133.7	142.4	154.1	169.0	188.5	214.7	252.2	299.1
127.5°	134.0	135.4	138.3	143.5	152.6	164.3	178.6	196.5	219.4	251.0	291.0
130°	138.7	140.1	143.7	149.6	159.1	170.8	184.8	202.0	222.4	250.3	285.6
132.5°	142.4	144.1	148.4	155.0	164.9	176.6	190.6	206.7	225.6	250.3	281.2
135°	148.2	150.0	155.4	162.7	172.1	184.3	198.4	213.3	230.0	250.3	276.1
137.5°	155.7	157.0	162.1	169.3	178.6	191.2	203.9	218.2	234.1	250.9	271.5
140°	159.9	161.3	166.8	174.0	182.6	194.8	207.9	221.4	235.9	251.3	269.3
142.5°	165.0	166.0	171.1	178.3	186.6	198.0	210.4	223.2	236.9	251.6	267.5
145°	172.6	173.5	178.0	184.3	192.5	202.9	214.7	225.9	238.1	251.3	264.8
147.5°	180.5	181.1	185.0	190.8	197.9	207.1	217.4	227.6	238.6	250.1	262.0
150°	185.3	186.2	189.3	195.2	201.5	209.2	219.2	228.6	238.6	249.0	259.8
152.5°	190.4	190.8	193.7	198.8	204.8	211.8	220.9	229.3	238.2	247.6	257.3
155°	197.0	197.0	199.7	204.2	208.7	215.1	222.8	230.0	237.3	244.9	253.0
157.5°	203.0	202.9	205.1	209.0	212.9	217.7	224.3	230.4	236.1	242.2	249.1
160°	207.0	206.5	208.3	211.5	215.1	219.2	225.1	230.4	235.0	240.4	245.8
162.5°	210.2	209.8	211.6	214.4	217.3	220.6	225.8	230.1	233.9	238.2	243.0
165°	215.1	214.2	215.6	217.8	219.6	222.4	225.9	229.6	232.3	235.0	238.6
167.5°	218.3	217.9	218.7	220.0	221.3	222.9	225.9	228.5	229.7	231.8	234.3
170°	220.5	220.1	220.5	221.4	222.4	223.7	225.9	227.8	228.6	230.0	231.8
172.5°	222.0	221.2	221.6	222.5	223.1	223.7	225.6	227.0	227.2	227.8	229.3
175°	223.7	222.8	223.2	223.7	223.7	223.7	225.1	225.9	225.5	225.5	225.9
177.5°	224.5	223.8	223.8	224.1	223.8	223.8	224.5	224.8	224.1	224.1	224.5
180°	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1



TEST NUMBER: P333177-927

CATALOG NUMBER: S125DIP-S610D590U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	760.8	760.8	760.8	760.8	760.8	760.8	760.8	760.8
2.5°	758.6	759.7	760.7	761.2	761.1	761.0	760.9	760.8
5°	754.8	756.0	757.2	757.7	757.6	757.5	757.3	757.2
7.5°	747.1	748.3	749.5	750.0	749.9	749.7	749.6	749.5
10°	740.7	741.7	742.8	743.3	743.1	743.0	742.8	742.8
12.5°	732.1	732.9	733.7	734.2	734.1	734.1	734.1	734.0
15°	717.0	717.6	718.4	718.7	718.7	718.7	718.7	718.7
17.5°	699.5	700.3	701.2	701.2	700.5	699.9	699.3	698.5
20°	686.2	687.1	688.1	688.2	687.5	686.9	686.2	685.6
22.5°	671.1	671.8	672.4	672.5	672.0	671.5	671.1	670.7
25°	647.0	647.2	647.5	647.5	647.1	646.7	646.3	645.9
27.5°	621.6	621.7	621.7	621.5	621.2	620.8	620.4	620.0
30°	603.2	602.9	602.6	602.3	601.9	601.5	601.1	600.7
32.5°	584.5	583.9	583.4	582.9	582.2	581.5	580.7	580.0
35°	555.4	554.8	554.1	553.2	552.2	551.0	550.0	548.9
37.5°	524.9	523.9	522.9	522.1	521.5	520.9	520.3	519.7
40°	503.7	502.6	501.4	500.6	500.2	499.8	499.4	499.0
42.5°	482.8	481.7	480.6	479.7	479.1	478.6	477.9	477.3
45°	451.8	450.2	448.6	447.6	447.2	446.8	446.4	446.0
47.5°	419.1	417.5	415.9	414.6	413.7	412.7	411.8	410.8
50°	396.8	395.1	393.3	392.0	391.0	390.1	389.1	388.2
52.5°	375.0	373.5	372.0	370.7	369.7	368.6	367.6	366.5
55°	341.3	340.1	338.9	337.8	336.8	335.9	335.0	334.1
57.5°	307.7	306.2	304.6	303.6	303.1	302.5	302.1	301.6
60°	285.0	283.7	282.3	281.2	280.3	279.3	278.4	277.5
62.5°	263.2	261.7	260.2	259.2	258.5	257.7	257.0	256.3
65°	228.7	227.5	226.3	225.5	224.9	224.3	223.9	223.3
67.5°	195.9	194.9	193.8	193.1	192.8	192.5	192.2	191.9
70°	174.1	173.3	172.5	171.9	171.3	170.8	170.2	169.8
72.5°	153.7	152.8	151.9	151.1	150.6	150.1	149.6	149.0
75°	122.0	121.6	121.2	120.7	120.2	119.6	119.1	118.6
77.5°	92.9	92.7	92.4	92.1	91.7	91.4	91.0	90.6
80°	74.4	74.2	74.1	73.9	73.6	73.4	73.1	72.8
82.5°	56.8	56.6	56.3	56.2	56.2	56.1	56.0	56.0
85°	33.4	33.3	33.2	33.0	32.7	32.4	32.2	31.9
87.5°	14.2	14.3	14.3	14.4	14.2	13.9	13.9	13.6
90°	8.2	8.6	9.0	9.9	9.9	9.9	10.4	10.4
92.5°	80.1	58.1	43.7	37.1	31.3	30.2	29.5	28.8
95°	324.9	256.2	200.7	162.7	130.6	117.0	113.4	106.2
97.5°	483.9	435.7	381.6	328.8	300.9	275.5	262.4	256.7
100°	555.8	533.7	487.1	440.1	408.9	376.4	359.7	352.4
102.5°	580.0	593.7	571.3	539.6	506.2	483.1	464.9	459.5
105°	565.8	627.6	647.5	642.5	628.1	613.2	604.2	598.7
107.5°	514.8	597.4	648.5	672.0	679.4	679.3	676.3	672.6
110°	477.2	563.1	626.8	665.2	685.5	694.1	697.3	697.3



TEST NUMBER: P333177-927

CATALOG NUMBER: S125DIP-S610D590U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	447.6	529.1	593.5	638.8	668.5	683.3	691.1	694.3
115°	410.3	480.4	542.2	591.5	626.8	648.5	661.1	667.0
117.5°	386.3	446.6	499.9	545.2	580.4	602.9	615.4	619.0
120°	373.3	427.5	477.2	517.0	550.4	572.1	584.3	587.9
122.5°	363.5	413.8	458.0	495.3	525.1	544.9	557.1	560.4
125°	349.3	395.4	434.7	467.2	492.6	511.1	521.0	525.5
127.5°	334.9	377.9	414.5	445.0	467.9	484.3	493.7	495.7
130°	325.8	365.6	400.8	430.2	452.8	467.7	476.7	479.4
132.5°	316.8	354.0	386.0	414.3	436.9	451.8	460.1	463.2
135°	305.0	336.2	365.1	390.9	410.7	425.6	433.8	436.5
137.5°	295.1	320.3	344.4	366.2	384.0	397.6	405.0	408.1
140°	289.6	310.9	331.7	350.7	367.4	379.1	385.9	388.2
142.5°	284.9	302.9	320.8	337.3	351.5	361.4	367.8	369.7
145°	278.8	292.8	306.8	319.0	329.9	337.5	342.5	344.4
147.5°	273.1	284.4	295.2	304.4	313.0	319.1	322.0	322.8
150°	269.7	279.7	288.3	296.4	303.2	308.6	310.5	310.9
152.5°	266.2	275.0	282.9	289.2	294.9	299.2	301.0	301.5
155°	260.7	268.0	274.3	279.2	283.8	286.9	288.3	288.8
157.5°	255.3	261.3	266.2	270.1	273.5	276.2	277.4	277.3
160°	251.7	256.2	260.7	263.9	267.0	269.3	270.2	269.7
162.5°	247.7	251.9	255.6	258.5	260.9	262.8	263.0	262.9
165°	242.2	245.3	248.1	250.3	252.2	253.0	253.0	253.0
167.5°	236.9	239.1	241.1	242.7	243.7	244.5	244.1	244.0
170°	234.1	235.4	236.8	237.7	238.6	239.1	239.1	238.6
172.5°	230.8	232.2	233.1	233.7	233.9	234.7	234.0	233.5
175°	227.3	227.3	228.2	228.2	228.2	228.6	227.8	227.3
177.5°	224.8	225.2	225.2	225.2	224.8	225.2	224.1	224.1
180°	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1

(END OF REPORT)