

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333185-927

Luminaire Tested: **S125DIP-S610D810U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333185-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S610D810U927-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4202.6 lumens
Efficiency: N/A
Efficacy: 109.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333185-927

CATALOG NUMBER: S125DIP-S610D810U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333185-927

CATALOG NUMBER: S125DIP-S610D810U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	54	54	54	47						47														
1	97	93	89	85	89	85	82	79	72	69	67	59	57	56	47	46	45	40						40														
2	88	81	75	70	81	75	69	65	63	59	55	52	49	46	41	40	38	33						33														
3	81	71	64	58	74	66	59	54	55	50	47	46	42	39	37	34	32	28						28														
4	74	63	55	49	67	58	51	46	49	44	40	41	37	34	33	30	28	24						24														
5	68	56	48	42	62	52	45	39	44	38	34	36	32	29	30	27	24	21						21														
6	62	50	42	36	57	47	39	34	39	34	30	33	29	25	27	24	21	18						18														
7	58	45	37	32	53	42	35	30	36	30	26	30	26	22	24	21	19	16						16														
8	53	41	33	28	49	38	31	26	33	27	23	27	23	20	22	19	17	15						15														
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15	13						13														
10	46	34	27	22	43	32	26	21	28	22	19	23	19	16	19	16	14	12						12														

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4914	4914	4914
5°	4924	4877	4909
10°	4894	4844	4871
15°	4841	4785	4805
20°	4766	4704	4712
25°	4684	4606	4603
30°	4583	4502	4480
35°	4475	4389	4328
40°	4364	4268	4207
45°	4244	4156	4074
50°	4112	4022	3900
55°	3985	3869	3762
60°	3834	3716	3584
65°	3651	3533	3412
70°	3478	3320	3206
75°	3169	3064	2959
80°	2819	2775	2708
85°	2453	2497	2364



TEST NUMBER: P333185-927

CATALOG NUMBER: S125DIP-S610D810U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.7	1.7
10°-20°	202.6	4.8
20°-30°	299.2	7.1
30°-40°	349.1	8.3
40°-50°	350.6	8.3
50°-60°	307.8	7.3
60°-70°	229.3	5.5
70°-80°	131.1	3.1
80°-90°	39.9	0.9
90°-100°	53.3	1.3
100°-110°	157.4	3.7
110°-120°	266.7	6.3
120°-130°	350.9	8.4
130°-140°	393.2	9.4
140°-150°	385.4	9.2
150°-160°	323.7	7.7
160°-170°	215.2	5.1
170°-180°	75.3	1.8
0°-30°	573.6	13.6
0°-40°	922.7	22.0
0°-60°	1581.1	37.6
0°-90°	1981.4	47.1
90°-120°	477.4	11.4
90°-150°	1607.0	38.2
90°-180°	2221.0	52.8
0°-180°	4202.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	761	761	761	761	761	
5°	760	758	752	757	757	72
15°	724	722	716	719	719	204
25°	657	654	646	648	646	302
35°	568	565	557	554	549	355
45°	465	462	455	448	446	358
55°	354	352	344	338	334	316
65°	239	237	231	226	223	237
75°	127	126	123	121	119	135
85°	33	34	34	33	32	37
90°	1	6	10	13	15	4
95°	40	42	48	52	53	43
105°	141	144	148	152	154	151
115°	267	269	271	270	270	264
125°	390	393	394	393	392	349
135°	507	510	511	511	509	390
145°	614	616	618	618	616	384
155°	702	702	703	705	702	323
165°	764	763	763	765	762	215
175°	794	792	792	795	791	75
180°	796	796	796	796	796	



TEST NUMBER: P333185-927

CATALOG NUMBER: S125DIP-S610D810U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	760.8	760.8	760.8	760.8	760.8	760.8	760.8	760.8	760.8	760.8	760.8
2.5°	762.7	762.4	762.1	761.8	761.4	760.7	759.7	758.6	757.6	756.5	757.6
5°	759.6	759.3	759.1	758.8	758.5	757.7	756.4	755.0	753.7	752.3	753.6
7.5°	752.6	752.3	752.1	751.8	751.5	750.7	749.2	747.7	746.2	744.8	745.9
10°	746.3	746.1	745.8	745.5	745.3	744.4	742.9	741.5	740.0	738.6	739.6
12.5°	738.6	738.2	737.7	737.2	736.7	735.8	734.4	733.1	731.7	730.3	731.2
15°	724.1	723.7	723.3	722.9	722.5	721.5	720.1	718.6	717.1	715.7	716.3
17.5°	707.3	706.8	706.2	705.6	705.0	703.9	702.4	700.8	699.3	697.8	698.6
20°	693.4	693.1	692.8	692.6	692.3	691.3	689.6	687.9	686.1	684.4	685.3
22.5°	679.4	678.9	678.4	677.9	677.5	676.4	674.8	673.2	671.5	669.9	670.5
25°	657.3	656.6	655.9	655.3	654.6	653.4	651.6	649.9	648.2	646.4	646.7
27.5°	631.4	631.0	630.6	630.2	629.8	628.7	626.9	625.1	623.3	621.5	621.5
30°	614.5	614.1	613.7	613.3	612.9	611.7	609.7	607.7	605.7	603.7	603.4
32.5°	596.2	595.6	595.0	594.4	593.7	592.6	590.8	589.0	587.2	585.4	584.9
35°	567.6	567.0	566.5	566.0	565.5	564.3	562.4	560.5	558.6	556.7	556.1
37.5°	537.8	537.2	536.5	535.8	535.2	533.9	532.2	530.4	528.6	526.9	525.9
40°	517.6	517.0	516.3	515.6	514.9	513.7	511.8	509.9	508.0	506.2	505.0
42.5°	496.0	495.4	494.8	494.2	493.7	492.5	490.6	488.8	486.9	485.0	483.9
45°	464.7	464.1	463.6	463.0	462.6	461.4	459.9	458.3	456.6	455.0	453.4
47.5°	430.9	430.9	431.0	431.0	431.0	430.1	428.2	426.3	424.4	422.4	420.8
50°	409.3	408.8	408.4	408.1	407.7	406.7	405.0	403.5	401.9	400.3	398.5
52.5°	387.1	386.8	386.6	386.3	386.0	384.9	383.3	381.5	379.9	378.1	376.6
55°	353.9	353.5	353.1	352.7	352.3	351.2	349.3	347.5	345.5	343.6	342.5
57.5°	318.9	318.7	318.5	318.2	318.1	317.1	315.5	313.9	312.4	310.9	309.3
60°	296.8	296.2	295.6	295.1	294.6	293.6	292.2	290.7	289.1	287.7	286.4
62.5°	273.6	273.2	272.7	272.4	271.9	271.1	269.8	268.5	267.3	266.0	264.6
65°	238.9	238.7	238.4	238.1	237.9	237.0	235.5	234.1	232.6	231.2	229.9
67.5°	205.3	204.8	204.2	203.7	203.1	202.3	201.2	200.1	199.0	197.9	196.9
70°	184.2	183.5	182.8	182.2	181.5	180.5	179.4	178.2	177.0	175.8	174.9
72.5°	161.1	160.6	160.2	159.7	159.2	158.6	157.9	157.1	156.3	155.5	154.6
75°	127.0	126.7	126.4	126.2	126.0	125.5	124.8	124.1	123.4	122.8	122.4
77.5°	95.6	95.5	95.4	95.2	95.1	94.9	94.5	94.2	93.8	93.4	93.2
80°	75.8	75.8	75.8	75.8	75.8	75.7	75.4	75.2	74.9	74.6	74.5
82.5°	58.5	58.3	58.1	57.8	57.7	57.5	57.4	57.4	57.4	57.3	57.0
85°	33.1	33.3	33.4	33.5	33.7	33.7	33.7	33.7	33.7	33.7	33.6
87.5°	13.2	13.3	13.5	13.8	14.0	14.2	14.3	14.3	14.4	14.5	14.7
90°	0.6	1.7	2.9	4.0	5.0	6.0	7.1	8.0	9.0	9.9	10.6
92.5°	15.0	15.8	16.6	17.3	18.1	19.0	20.2	21.4	22.6	23.8	24.7
95°	40.2	40.6	40.8	41.1	41.4	42.2	43.6	44.9	46.3	47.7	48.6
97.5°	66.9	67.0	67.1	67.3	67.3	68.4	70.3	72.2	74.1	76.0	76.8
100°	86.7	86.7	86.7	86.7	86.7	87.6	89.4	91.2	93.0	94.7	96.0
102.5°	108.1	108.6	109.2	109.7	110.3	111.0	111.9	112.8	113.7	114.6	116.0
105°	141.2	142.0	142.6	143.3	144.0	144.7	145.6	146.4	147.2	148.1	148.9
107.5°	177.9	178.6	179.3	180.0	180.7	181.3	182.0	182.6	183.2	183.9	184.3
110°	203.2	203.9	204.5	205.3	206.0	206.5	206.9	207.3	207.7	208.1	208.6



TEST NUMBER: P333185-927

CATALOG NUMBER: S125DIP-S610D810U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	228.9	229.3	229.7	230.0	230.4	230.8	231.3	231.9	232.4	232.9	233.1
115°	267.0	267.5	268.1	268.6	269.2	269.6	269.9	270.1	270.5	270.7	270.5
117.5°	305.1	305.4	305.6	305.9	306.1	306.4	306.7	306.9	307.1	307.4	307.4
120°	328.9	329.6	330.3	331.0	331.7	332.1	332.2	332.4	332.5	332.6	332.6
122.5°	354.7	355.0	355.2	355.5	355.7	356.0	356.3	356.7	357.0	357.4	357.3
125°	389.6	390.5	391.3	392.1	392.9	393.4	393.6	393.7	393.8	394.0	393.7
127.5°	426.8	427.3	427.7	428.2	428.6	429.0	429.1	429.3	429.5	429.7	429.5
130°	449.1	449.8	450.5	451.1	451.9	452.3	452.6	452.9	453.1	453.4	453.3
132.5°	471.4	472.5	473.6	474.8	475.9	476.4	476.4	476.3	476.3	476.3	476.1
135°	506.7	507.6	508.3	509.2	510.0	510.5	510.6	510.8	510.9	511.0	511.0
137.5°	540.0	540.7	541.5	542.3	543.1	543.7	544.0	544.2	544.5	544.9	545.0
140°	561.3	561.9	562.6	563.3	564.0	564.5	564.9	565.4	565.8	566.2	566.5
142.5°	582.6	583.1	583.7	584.2	584.9	585.4	585.9	586.5	586.9	587.5	587.6
145°	613.9	614.4	615.0	615.5	616.1	616.6	617.0	617.3	617.8	618.2	618.2
147.5°	642.9	643.2	643.5	643.8	644.0	644.4	644.8	645.1	645.4	645.7	646.0
150°	662.2	662.0	661.9	661.8	661.6	661.9	662.4	663.0	663.5	664.1	664.1
152.5°	678.0	678.3	678.4	678.7	678.8	679.1	679.2	679.5	679.7	679.9	680.2
155°	702.4	702.4	702.4	702.4	702.4	702.5	702.7	702.8	702.9	703.1	703.6
157.5°	724.3	724.0	723.7	723.3	723.0	722.9	723.1	723.3	723.3	723.5	724.1
160°	737.1	736.7	736.3	735.9	735.5	735.4	735.5	735.6	735.8	735.9	736.5
162.5°	748.5	748.2	747.9	747.7	747.3	747.2	747.2	747.3	747.3	747.3	748.0
165°	763.8	763.5	763.3	763.0	762.7	762.6	762.7	762.9	763.0	763.2	763.7
167.5°	776.7	776.1	775.5	775.0	774.4	774.2	774.2	774.2	774.2	774.2	775.0
170°	783.6	783.1	782.5	782.0	781.4	781.1	781.1	781.1	781.1	781.1	782.0
172.5°	788.5	788.0	787.4	786.9	786.3	786.1	786.1	786.1	786.1	786.1	786.9
175°	794.2	793.6	793.1	792.5	791.9	791.6	791.6	791.6	791.6	791.6	792.5
177.5°	797.0	796.5	796.1	795.7	795.2	795.0	794.9	794.7	794.6	794.5	795.2
180°	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0



TEST NUMBER: P333185-927

CATALOG NUMBER: S125DIP-S610D810U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	760.8	760.8	760.8	760.8	760.8	760.8	760.8	760.8
2.5°	758.6	759.7	760.7	761.2	761.1	761.0	760.9	760.8
5°	754.8	756.0	757.2	757.7	757.6	757.5	757.3	757.2
7.5°	747.1	748.3	749.5	750.0	749.9	749.7	749.6	749.5
10°	740.7	741.7	742.8	743.3	743.1	743.0	742.8	742.8
12.5°	732.1	732.9	733.7	734.2	734.1	734.1	734.1	734.0
15°	717.0	717.6	718.4	718.7	718.7	718.7	718.7	718.7
17.5°	699.5	700.3	701.2	701.2	700.5	699.9	699.3	698.5
20°	686.2	687.1	688.1	688.2	687.5	686.9	686.2	685.6
22.5°	671.1	671.8	672.4	672.5	672.0	671.5	671.1	670.7
25°	647.0	647.2	647.5	647.5	647.1	646.7	646.3	645.9
27.5°	621.6	621.7	621.7	621.5	621.2	620.8	620.4	620.0
30°	603.2	602.9	602.6	602.3	601.9	601.5	601.1	600.7
32.5°	584.5	583.9	583.4	582.9	582.2	581.5	580.7	580.0
35°	555.4	554.8	554.1	553.2	552.2	551.0	550.0	548.9
37.5°	524.9	523.9	522.9	522.1	521.5	520.9	520.3	519.7
40°	503.7	502.6	501.4	500.6	500.2	499.8	499.4	499.0
42.5°	482.8	481.7	480.6	479.7	479.1	478.6	477.9	477.3
45°	451.8	450.2	448.6	447.6	447.2	446.8	446.4	446.0
47.5°	419.1	417.5	415.9	414.6	413.7	412.7	411.8	410.8
50°	396.8	395.1	393.3	392.0	391.0	390.1	389.1	388.2
52.5°	375.0	373.5	372.0	370.7	369.7	368.6	367.6	366.5
55°	341.3	340.1	338.9	337.8	336.8	335.9	335.0	334.1
57.5°	307.7	306.2	304.6	303.6	303.1	302.5	302.1	301.6
60°	285.0	283.7	282.3	281.2	280.3	279.3	278.4	277.5
62.5°	263.2	261.7	260.2	259.2	258.5	257.7	257.0	256.3
65°	228.7	227.5	226.3	225.5	224.9	224.3	223.9	223.3
67.5°	195.9	194.9	193.8	193.1	192.8	192.5	192.2	191.9
70°	174.1	173.3	172.5	171.9	171.3	170.8	170.2	169.8
72.5°	153.7	152.8	151.9	151.1	150.6	150.1	149.6	149.0
75°	122.0	121.6	121.2	120.7	120.2	119.6	119.1	118.6
77.5°	92.9	92.7	92.4	92.1	91.7	91.4	91.0	90.6
80°	74.4	74.2	74.1	73.9	73.6	73.4	73.1	72.8
82.5°	56.8	56.6	56.3	56.2	56.2	56.1	56.0	56.0
85°	33.4	33.3	33.2	33.0	32.7	32.4	32.2	31.9
87.5°	14.8	14.9	15.1	15.1	14.9	14.8	14.7	14.5
90°	11.2	12.0	12.7	13.2	13.6	14.0	14.4	14.9
92.5°	25.6	26.5	27.4	28.0	28.4	28.6	28.9	29.2
95°	49.6	50.6	51.6	52.2	52.4	52.8	53.0	53.2
97.5°	77.8	78.7	79.6	80.1	80.2	80.4	80.6	80.8
100°	97.3	98.5	99.7	100.5	100.8	101.0	101.3	101.6
102.5°	117.3	118.7	120.0	120.9	121.3	121.6	122.0	122.4
105°	149.7	150.5	151.4	151.9	152.4	152.8	153.2	153.6
107.5°	184.7	185.1	185.5	185.7	185.7	185.6	185.6	185.6
110°	209.0	209.4	209.8	209.9	209.8	209.6	209.5	209.4



TEST NUMBER: P333185-927

CATALOG NUMBER: S125DIP-S610D810U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	233.3	233.5	233.7	233.7	233.4	233.1	232.9	232.7
115°	270.5	270.3	270.1	270.0	269.9	269.7	269.6	269.5
117.5°	307.6	307.7	307.8	307.6	307.0	306.5	305.9	305.4
120°	332.6	332.6	332.6	332.4	331.8	331.3	330.7	330.2
122.5°	357.2	357.1	357.0	356.7	356.2	355.8	355.4	355.0
125°	393.4	393.2	392.8	392.7	392.5	392.4	392.3	392.1
127.5°	429.4	429.2	429.1	428.9	428.6	428.3	428.1	427.8
130°	453.1	453.0	452.9	452.7	452.4	452.1	451.9	451.5
132.5°	475.9	475.8	475.7	475.4	475.1	474.7	474.3	473.9
135°	511.0	511.0	511.0	510.8	510.2	509.7	509.1	508.6
137.5°	545.2	545.3	545.5	545.3	544.5	543.9	543.2	542.5
140°	566.7	567.0	567.3	567.0	566.4	565.7	565.0	564.4
142.5°	587.8	588.0	588.1	587.9	587.2	586.5	585.8	585.1
145°	618.2	618.2	618.2	618.0	617.6	617.2	616.8	616.3
147.5°	646.3	646.7	647.1	646.7	645.8	644.8	644.0	643.0
150°	664.1	664.1	664.1	663.9	663.6	663.4	663.1	662.8
152.5°	680.6	680.9	681.2	681.1	680.6	680.2	679.7	679.1
155°	704.2	704.7	705.3	705.2	704.5	703.9	703.1	702.4
157.5°	724.6	725.2	725.7	725.6	724.6	723.7	722.8	721.9
160°	737.0	737.5	738.1	738.1	737.4	736.7	735.9	735.3
162.5°	748.6	749.3	750.0	749.9	749.1	748.3	747.5	746.7
165°	764.3	764.9	765.3	765.2	764.4	763.6	762.7	761.9
167.5°	775.9	776.7	777.5	777.4	776.7	775.8	774.9	774.0
170°	782.8	783.6	784.4	784.3	783.4	782.4	781.5	780.5
172.5°	787.7	788.5	789.4	789.4	788.5	787.7	786.8	785.9
175°	793.3	794.2	795.0	794.9	793.9	793.0	792.0	791.1
177.5°	795.8	796.5	797.2	797.1	796.3	795.6	794.8	794.0
180°	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0

(END OF REPORT)