

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333547

Luminaire Tested: **S125RDIP-S610D1205U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333547
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S610D1205U835-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1205 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7194.2 lumens
Efficiency: N/A
Efficacy: 145.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333547

CATALOG NUMBER: S125RDIP-S610D1205U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333547

CATALOG NUMBER: S125RDIP-S610D1205U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33
1	94	90	86	83	85	81	78	75	65	63	61	50	49	47	36	35	35	28
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	30	29	24
3	78	69	62	57	70	63	57	52	50	46	43	39	36	34	28	27	25	20
4	72	61	54	48	64	56	49	44	45	40	36	35	31	29	25	23	22	18
5	66	55	47	41	59	49	43	38	40	35	31	31	28	25	23	21	19	15
6	60	49	41	35	54	44	38	33	36	31	27	28	25	22	21	18	17	13
7	56	44	36	31	50	40	33	29	33	28	24	26	22	19	19	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	23	20	17	17	15	13	11
9	48	36	29	24	43	33	27	22	27	22	19	21	18	15	16	14	12	10
10	45	33	26	22	40	30	24	20	25	20	17	20	16	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6497	6497	6497
5°	6512	6438	6477
10°	6462	6378	6378
15°	6386	6248	6197
20°	6287	6068	5994
25°	6173	5890	5761
30°	6029	5683	5502
35°	5882	5469	5211
40°	5746	5246	4926
45°	5580	4996	4615
50°	5413	4725	4290
55°	5219	4466	3944
60°	5025	4151	3573
65°	4795	3785	3147
70°	4534	3329	2712
75°	4172	2805	2256
80°	3675	2205	1893
85°	3097	1801	1690



TEST NUMBER: P333547

CATALOG NUMBER: S125RDIP-S610D1205U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.6	1.3
10°-20°	264.3	3.7
20°-30°	383.3	5.3
30°-40°	436.9	6.1
40°-50°	425.9	5.9
50°-60°	358.5	5.0
60°-70°	251.3	3.5
70°-80°	129.2	1.8
80°-90°	35.9	0.5
90°-100°	57.0	0.8
100°-110°	351.1	4.9
110°-120°	636.8	8.9
120°-130°	817.3	11.4
130°-140°	879.1	12.2
140°-150°	825.1	11.5
150°-160°	667.5	9.3
160°-170°	431.7	6.0
170°-180°	148.9	2.1
0°-30°	742.3	10.3
0°-40°	1179.2	16.4
0°-60°	1963.5	27.3
0°-90°	2379.8	33.1
90°-120°	1044.9	14.5
90°-150°	3566.4	49.6
90°-180°	4814.0	66.9
0°-180°	7194.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1006	1006	1006	1006	1006	
5°	1004	1001	993	1000	999	95
15°	955	950	934	933	927	269
25°	866	854	827	817	808	398
35°	746	727	694	672	661	467
45°	611	588	547	518	505	471
55°	464	438	397	364	350	414
65°	314	287	248	218	206	311
75°	167	144	112	96	90	177
85°	42	29	24	24	23	47
90°	1	10	19	24	28	5
95°	66	60	19	24	24	84
105°	342	346	346	346	345	362
115°	642	647	648	644	637	636
125°	912	920	920	916	912	815
135°	1138	1144	1142	1140	1133	877
145°	1319	1321	1321	1322	1316	825
155°	1453	1446	1448	1451	1442	669
165°	1533	1526	1527	1533	1525	433
175°	1568	1561	1562	1570	1561	149
180°	1568	1568	1568	1568	1568	



TEST NUMBER: P333547

CATALOG NUMBER: S125RDIP-S610D1205U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0
2.5°	1007.8	1007.4	1007.0	1006.6	1006.2	1005.3	1003.9	1002.6	1001.2	999.9	1001.2
5°	1004.4	1003.8	1003.1	1002.4	1001.7	1000.5	998.6	996.8	994.9	993.0	994.7
7.5°	994.6	993.9	993.3	992.6	992.0	990.6	988.3	986.1	983.9	981.6	982.8
10°	985.4	984.9	984.4	983.9	983.4	982.0	979.6	977.3	974.9	972.5	973.0
12.5°	975.1	974.5	973.8	973.2	972.5	970.6	967.5	964.3	961.1	957.9	958.3
15°	955.1	954.0	953.0	952.0	951.0	948.7	945.2	941.6	938.1	934.5	934.4
17.5°	932.4	930.9	929.3	927.8	926.2	923.2	918.7	914.3	909.8	905.4	904.5
20°	914.8	913.1	911.4	909.7	908.0	904.5	899.1	893.7	888.3	882.9	882.0
22.5°	895.3	893.6	892.0	890.3	888.6	884.9	879.2	873.6	867.9	862.2	860.6
25°	866.2	863.6	861.1	858.6	856.0	851.6	845.4	839.1	832.9	826.6	824.5
27.5°	832.7	829.7	826.6	823.5	820.4	815.6	808.9	802.2	795.5	788.8	785.7
30°	808.4	805.2	802.0	798.8	795.6	790.4	783.3	776.3	769.2	762.1	758.2
32.5°	784.7	781.0	777.2	773.5	769.7	764.2	757.0	749.8	742.5	735.3	731.0
35°	746.1	742.1	738.0	734.0	729.9	724.1	716.5	708.9	701.3	693.7	688.8
37.5°	708.3	703.3	698.4	693.5	688.6	682.2	674.3	666.5	658.7	650.8	645.0
40°	681.5	676.5	671.4	666.3	661.3	654.7	646.6	638.5	630.4	622.3	615.9
42.5°	653.6	648.4	643.2	638.0	632.8	626.0	617.6	609.2	600.9	592.5	586.3
45°	610.9	606.0	601.1	596.2	591.3	584.2	574.9	565.6	556.3	547.0	540.3
47.5°	566.7	561.5	556.3	551.2	546.0	538.7	529.4	520.0	510.7	501.3	494.4
50°	538.7	533.1	527.5	522.0	516.4	508.8	499.2	489.6	479.9	470.3	463.2
52.5°	508.3	502.6	496.9	491.2	485.5	478.1	469.0	459.9	450.8	441.7	434.1
55°	463.5	458.1	452.7	447.3	441.9	434.4	425.0	415.5	406.1	396.6	389.0
57.5°	418.2	412.4	406.6	400.9	395.1	387.6	378.5	369.4	360.3	351.2	343.7
60°	389.0	383.1	377.2	371.3	365.4	357.9	348.7	339.6	330.5	321.4	314.0
62.5°	358.0	352.4	346.7	341.1	335.5	328.0	318.8	309.5	300.3	291.0	284.1
65°	313.8	308.1	302.3	296.6	290.8	283.5	274.5	265.6	256.6	247.7	240.9
67.5°	269.9	264.1	258.4	252.7	246.9	239.8	231.2	222.6	214.0	205.4	199.3
70°	240.1	234.4	228.6	222.9	217.1	210.0	201.6	193.2	184.7	176.3	171.0
72.5°	210.9	205.3	199.7	194.1	188.5	181.7	173.8	165.9	158.0	150.1	145.3
75°	167.2	162.1	157.0	152.0	146.9	140.8	133.7	126.6	119.5	112.4	108.7
77.5°	123.7	119.6	115.6	111.5	107.5	102.6	96.9	91.3	85.6	79.9	77.3
80°	98.8	94.7	90.7	86.6	82.6	78.2	73.4	68.7	64.0	59.3	57.7
82.5°	74.5	70.8	67.2	63.5	59.9	56.4	53.2	49.9	46.7	43.5	42.8
85°	41.8	38.7	35.7	32.7	29.6	27.7	26.8	26.0	25.2	24.3	24.1
87.5°	14.2	13.7	13.1	12.6	12.1	11.9	12.2	12.4	12.6	12.8	13.1
90°	1.2	3.2	5.3	7.4	9.4	11.4	13.2	15.0	16.8	18.6	19.9
92.5°	17.9	16.5	15.0	13.6	12.1	12.2	13.8	15.4	17.0	18.6	19.9
95°	66.2	65.5	64.7	63.9	63.1	57.9	48.0	38.2	28.4	18.6	19.9
97.5°	138.3	139.7	141.1	142.5	143.9	134.9	115.4	96.0	76.6	57.2	49.9
100°	194.1	194.9	195.6	196.4	197.2	198.1	199.1	200.2	201.2	202.2	163.7
102.5°	250.8	251.8	252.8	253.7	254.7	255.5	256.1	256.8	257.4	258.0	250.7
105°	341.7	342.7	343.7	344.8	345.8	346.3	346.3	346.3	346.3	346.3	346.3
107.5°	436.1	436.1	436.1	436.1	436.1	436.3	436.8	437.3	437.9	438.4	438.4
110°	497.4	497.4	497.4	497.4	497.4	497.7	498.2	498.7	499.2	499.7	499.0



TEST NUMBER: P333547

CATALOG NUMBER: S125RDIP-S610D1205U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	555.1	555.7	556.3	556.9	557.5	558.0	558.3	558.6	558.9	559.2	558.3
115°	641.5	642.8	644.1	645.4	646.7	647.5	647.7	648.0	648.2	648.5	647.5
117.5°	731.0	731.0	730.9	730.9	730.8	731.3	732.3	733.2	734.2	735.2	733.9
120°	786.8	786.5	786.3	786.0	785.8	786.0	786.8	787.6	788.3	789.1	788.6
122.5°	836.1	837.1	838.0	839.0	840.0	840.7	841.0	841.4	841.8	842.1	841.6
125°	912.3	914.1	915.9	917.7	919.5	920.4	920.4	920.4	920.4	920.4	919.4
127.5°	985.1	986.4	987.6	988.9	990.2	990.8	990.6	990.5	990.3	990.2	989.6
130°	1029.7	1031.0	1032.3	1033.6	1034.9	1035.6	1035.9	1036.2	1036.4	1036.7	1035.9
132.5°	1074.3	1075.8	1077.3	1078.8	1080.3	1080.8	1080.2	1079.6	1079.1	1078.5	1078.4
135°	1137.8	1139.3	1140.9	1142.4	1144.0	1144.5	1144.0	1143.5	1142.9	1142.4	1141.9
137.5°	1196.1	1197.5	1198.8	1200.1	1201.5	1201.9	1201.5	1201.0	1200.5	1200.1	1200.2
140°	1234.2	1234.8	1235.3	1235.8	1236.3	1236.4	1236.2	1235.9	1235.7	1235.4	1235.9
142.5°	1268.6	1268.9	1269.3	1269.6	1269.9	1270.2	1270.6	1270.9	1271.3	1271.7	1271.8
145°	1319.1	1319.6	1320.1	1320.6	1321.1	1321.4	1321.4	1321.4	1321.4	1321.4	1321.7
147.5°	1363.2	1363.1	1363.0	1362.9	1362.8	1362.9	1363.2	1363.5	1363.9	1364.2	1364.5
150°	1391.1	1390.6	1390.1	1389.6	1389.1	1389.1	1389.6	1390.1	1390.6	1391.1	1391.6
152.5°	1418.1	1417.0	1415.8	1414.7	1413.5	1413.2	1413.8	1414.3	1414.8	1415.3	1415.8
155°	1452.7	1451.2	1449.6	1448.1	1446.5	1446.0	1446.5	1447.0	1447.6	1448.1	1448.9
157.5°	1479.5	1478.5	1477.6	1476.7	1475.7	1475.3	1475.4	1475.4	1475.5	1475.5	1476.3
160°	1498.1	1496.5	1495.0	1493.4	1491.9	1491.2	1491.5	1491.7	1492.0	1492.2	1493.3
162.5°	1512.9	1511.4	1509.8	1508.3	1506.7	1506.1	1506.3	1506.6	1506.9	1507.1	1508.6
165°	1532.9	1531.4	1529.8	1528.3	1526.7	1526.1	1526.3	1526.6	1526.8	1527.1	1528.7
167.5°	1547.8	1546.2	1544.6	1543.0	1541.4	1540.7	1541.0	1541.2	1541.5	1541.8	1543.6
170°	1556.2	1554.4	1552.5	1550.7	1548.9	1548.2	1548.4	1548.7	1548.9	1549.2	1551.3
172.5°	1561.7	1559.9	1558.1	1556.3	1554.5	1553.8	1554.3	1554.8	1555.2	1555.7	1557.6
175°	1567.8	1566.2	1564.7	1563.1	1561.6	1560.9	1561.2	1561.5	1561.7	1562.0	1564.0
177.5°	1570.6	1569.3	1568.1	1566.9	1565.6	1565.1	1565.3	1565.5	1565.7	1565.9	1567.4
180°	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8



TEST NUMBER: P333547

CATALOG NUMBER: S125RDIP-S610D1205U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0
2.5°	1002.6	1003.9	1005.3	1005.9	1005.8	1005.6	1005.5	1005.4
5°	996.4	998.1	999.8	1000.5	1000.1	999.8	999.5	999.1
7.5°	984.0	985.2	986.4	986.8	986.4	986.0	985.7	985.3
10°	973.5	974.0	974.6	974.6	974.0	973.5	973.0	972.5
12.5°	958.7	959.1	959.4	959.2	958.4	957.7	956.9	956.1
15°	934.2	934.0	933.9	933.0	931.5	930.0	928.5	926.9
17.5°	903.7	902.8	902.0	900.9	899.7	898.4	897.2	895.9
20°	881.2	880.3	879.5	878.3	876.8	875.3	873.8	872.2
22.5°	858.9	857.2	855.6	854.1	852.9	851.6	850.4	849.1
25°	822.3	820.1	817.9	815.8	814.0	812.1	810.3	808.4
27.5°	782.7	779.6	776.5	774.1	772.3	770.5	768.7	766.9
30°	754.3	750.4	746.5	743.8	742.3	740.8	739.3	737.8
32.5°	726.7	722.5	718.2	715.1	713.1	711.2	709.3	707.4
35°	683.9	679.0	674.1	670.5	668.1	665.7	663.4	661.0
37.5°	639.1	633.2	627.3	623.2	620.9	618.7	616.4	614.1
40°	609.4	603.0	596.6	592.4	590.4	588.3	586.3	584.3
42.5°	580.2	574.0	567.9	563.3	560.4	557.4	554.4	551.5
45°	533.5	526.8	520.0	515.4	512.9	510.3	507.8	505.3
47.5°	487.4	480.4	473.5	468.6	465.8	463.0	460.2	457.4
50°	456.1	449.0	441.9	437.1	434.6	432.1	429.5	427.0
52.5°	426.5	418.8	411.2	406.1	403.6	401.1	398.5	396.0
55°	381.4	373.8	366.2	361.1	358.4	355.7	353.0	350.3
57.5°	336.3	328.9	321.5	316.5	314.1	311.7	309.4	307.0
60°	306.5	299.1	291.7	286.7	284.2	281.6	279.1	276.6
62.5°	277.2	270.3	263.4	258.7	256.2	253.7	251.1	248.6
65°	234.2	227.4	220.7	216.0	213.5	211.0	208.4	205.9
67.5°	193.1	186.9	180.7	176.6	174.6	172.6	170.5	168.5
70°	165.8	160.6	155.3	151.7	149.7	147.7	145.6	143.6
72.5°	140.5	135.6	130.8	127.7	126.4	125.0	123.7	122.3
75°	105.0	101.3	97.6	95.1	94.0	92.8	91.6	90.4
77.5°	74.7	72.1	69.5	67.8	66.9	66.0	65.2	64.3
80°	56.2	54.7	53.2	52.3	51.9	51.6	51.2	50.9
82.5°	42.0	41.3	40.6	40.2	40.0	39.8	39.6	39.4
85°	24.0	23.8	23.6	23.5	23.3	23.1	23.0	22.8
87.5°	13.4	13.6	13.9	14.0	14.0	14.0	14.1	14.1
90°	21.2	22.5	23.8	24.8	25.6	26.3	27.1	27.9
92.5°	21.2	22.5	23.8	24.6	24.9	25.3	25.7	26.0
95°	21.2	22.5	23.8	24.4	24.4	24.4	24.4	24.4
97.5°	42.6	35.3	28.0	24.4	24.4	24.4	24.4	24.4
100°	125.3	86.8	48.3	28.5	27.5	26.5	25.4	24.4
102.5°	243.4	236.2	228.9	216.5	198.9	181.3	163.8	146.2
105°	346.3	346.3	346.3	346.2	345.9	345.7	345.4	345.2
107.5°	438.5	438.5	438.6	438.2	437.4	436.7	435.9	435.1
110°	498.2	497.4	496.6	496.4	496.6	496.9	497.2	497.4



TEST NUMBER: P333547

CATALOG NUMBER: S125RDIP-S610D1205U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	557.3	556.3	555.3	554.6	554.3	553.9	553.6	553.2
115°	646.4	645.4	644.4	643.1	641.5	640.0	638.4	636.9
117.5°	732.5	731.2	729.8	728.8	728.1	727.5	726.8	726.1
120°	788.1	787.6	787.1	786.2	784.9	783.6	782.3	781.0
122.5°	841.1	840.6	840.1	839.0	837.5	836.0	834.6	833.1
125°	918.4	917.3	916.3	915.4	914.6	913.9	913.1	912.3
127.5°	989.0	988.5	987.9	986.7	984.8	982.8	980.9	979.0
130°	1035.1	1034.3	1033.6	1032.5	1031.2	1030.0	1028.7	1027.4
132.5°	1078.2	1078.0	1077.9	1077.2	1075.9	1074.6	1073.3	1072.0
135°	1141.4	1140.9	1140.4	1139.3	1137.8	1136.2	1134.7	1133.1
137.5°	1200.3	1200.4	1200.5	1199.9	1198.5	1197.2	1195.8	1194.5
140°	1236.4	1236.9	1237.5	1236.9	1235.4	1233.9	1232.3	1230.8
142.5°	1271.9	1272.0	1272.1	1271.4	1269.8	1268.3	1266.7	1265.2
145°	1321.9	1322.2	1322.4	1321.8	1320.2	1318.7	1317.1	1315.6
147.5°	1364.8	1365.1	1365.4	1364.6	1362.8	1360.9	1359.1	1357.2
150°	1392.2	1392.7	1393.2	1392.4	1390.4	1388.3	1386.2	1384.2
152.5°	1416.3	1416.9	1417.4	1416.7	1414.8	1413.0	1411.1	1409.3
155°	1449.6	1450.4	1451.2	1450.5	1448.5	1446.4	1444.3	1442.3
157.5°	1477.2	1478.0	1478.8	1478.2	1476.1	1474.1	1472.0	1469.9
160°	1494.3	1495.3	1496.4	1495.9	1493.8	1491.7	1489.7	1487.6
162.5°	1510.0	1511.5	1512.9	1512.5	1510.2	1507.9	1505.7	1503.4
165°	1530.2	1531.8	1533.3	1533.0	1531.0	1528.9	1526.8	1524.8
167.5°	1545.5	1547.3	1549.2	1549.0	1546.6	1544.3	1542.0	1539.7
170°	1553.3	1555.4	1557.5	1557.3	1555.0	1552.7	1550.4	1548.0
172.5°	1559.4	1561.3	1563.1	1562.9	1560.6	1558.3	1555.9	1553.6
175°	1566.1	1568.2	1570.2	1570.1	1567.8	1565.5	1563.1	1560.8
177.5°	1568.8	1570.3	1571.7	1571.6	1570.0	1568.3	1566.6	1565.0
180°	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8

(END OF REPORT)