

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333523

Luminaire Tested: **S125RDIP-S610D365U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333523
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S610D365U835-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3841.8 lumens
Efficiency: N/A
Efficacy: 139.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333523

CATALOG NUMBER: S125RDIP-S610D365U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333523

CATALOG NUMBER: S125RDIP-S610D365U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	101	96	93	89	94	90	87	84	79	77	75	69	67	66	60	58	57	53
2	92	85	78	73	86	79	74	69	70	66	62	61	58	55	53	51	49	45
3	84	75	67	61	78	70	64	58	62	57	53	54	50	47	47	44	42	38
4	77	66	58	52	72	62	55	50	55	50	45	48	44	40	42	39	36	33
5	71	59	51	45	66	56	48	43	50	44	39	44	39	35	38	35	32	29
6	65	53	45	39	61	50	43	38	45	39	34	40	35	31	35	31	28	25
7	61	48	40	35	57	46	38	33	41	35	30	36	31	28	32	28	25	22
8	56	44	36	31	53	42	34	29	37	31	27	33	28	25	29	25	22	20
9	53	40	33	27	49	38	31	26	34	28	24	30	26	22	27	23	20	18
10	49	37	30	25	46	35	28	24	32	26	22	28	24	20	25	21	18	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6497	6497	6497
5°	6512	6438	6477
10°	6462	6378	6378
15°	6386	6248	6197
20°	6287	6068	5994
25°	6173	5890	5761
30°	6029	5683	5502
35°	5882	5469	5211
40°	5746	5246	4926
45°	5580	4996	4615
50°	5413	4725	4290
55°	5219	4466	3944
60°	5025	4151	3573
65°	4795	3785	3147
70°	4534	3329	2712
75°	4172	2805	2256
80°	3675	2205	1893
85°	3097	1801	1690



TEST NUMBER: P333523

CATALOG NUMBER: S125RDIP-S610D365U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.6	2.5
10°-20°	264.3	6.9
20°-30°	383.3	10.0
30°-40°	436.9	11.4
40°-50°	425.9	11.1
50°-60°	358.5	9.3
60°-70°	251.3	6.5
70°-80°	129.2	3.4
80°-90°	33.6	0.9
90°-100°	17.3	0.5
100°-110°	106.8	2.8
110°-120°	193.7	5.0
120°-130°	248.6	6.5
130°-140°	267.4	7.0
140°-150°	251.0	6.5
150°-160°	203.0	5.3
160°-170°	131.3	3.4
170°-180°	45.3	1.2
0°-30°	742.3	19.3
0°-40°	1179.2	30.7
0°-60°	1963.5	51.1
0°-90°	2377.5	61.9
90°-120°	317.8	8.3
90°-150°	1084.7	28.2
90°-180°	1464.0	38.1
0°-180°	3841.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1006	1006	1006	1006	1006	
5°	1004	1001	993	1000	999	95
15°	955	950	934	933	927	269
25°	866	854	827	817	808	398
35°	746	727	694	672	661	467
45°	611	588	547	518	505	471
55°	464	438	397	364	350	414
65°	314	287	248	218	206	311
75°	167	144	112	96	90	177
85°	42	29	24	24	23	47
90°	0	3	6	7	8	3
95°	20	18	6	7	7	26
105°	104	105	105	105	105	110
115°	195	197	197	196	194	193
125°	278	280	280	279	278	248
135°	346	348	348	347	345	267
145°	401	402	402	402	400	251
155°	442	440	440	441	439	203
165°	466	464	464	466	464	132
175°	477	475	475	478	475	45
180°	477	477	477	477	477	



TEST NUMBER: P333523

CATALOG NUMBER: S125RDIP-S610D365U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0
2.5°	1007.8	1007.4	1007.0	1006.6	1006.2	1005.3	1003.9	1002.6	1001.2	999.9	1001.2
5°	1004.4	1003.8	1003.1	1002.4	1001.7	1000.5	998.6	996.8	994.9	993.0	994.7
7.5°	994.6	993.9	993.3	992.6	992.0	990.6	988.3	986.1	983.9	981.6	982.8
10°	985.4	984.9	984.4	983.9	983.4	982.0	979.6	977.3	974.9	972.5	973.0
12.5°	975.1	974.5	973.8	973.2	972.5	970.6	967.5	964.3	961.1	957.9	958.3
15°	955.1	954.0	953.0	952.0	951.0	948.7	945.2	941.6	938.1	934.5	934.4
17.5°	932.4	930.9	929.3	927.8	926.2	923.2	918.7	914.3	909.8	905.4	904.5
20°	914.8	913.1	911.4	909.7	908.0	904.5	899.1	893.7	888.3	882.9	882.0
22.5°	895.3	893.6	892.0	890.3	888.6	884.9	879.2	873.6	867.9	862.2	860.6
25°	866.2	863.6	861.1	858.6	856.0	851.6	845.4	839.1	832.9	826.6	824.5
27.5°	832.7	829.7	826.6	823.5	820.4	815.6	808.9	802.2	795.5	788.8	785.7
30°	808.4	805.2	802.0	798.8	795.6	790.4	783.3	776.3	769.2	762.1	758.2
32.5°	784.7	781.0	777.2	773.5	769.7	764.2	757.0	749.8	742.5	735.3	731.0
35°	746.1	742.1	738.0	734.0	729.9	724.1	716.5	708.9	701.3	693.7	688.8
37.5°	708.3	703.3	698.4	693.5	688.6	682.2	674.3	666.5	658.7	650.8	645.0
40°	681.5	676.5	671.4	666.3	661.3	654.7	646.6	638.5	630.4	622.3	615.9
42.5°	653.6	648.4	643.2	638.0	632.8	626.0	617.6	609.2	600.9	592.5	586.3
45°	610.9	606.0	601.1	596.2	591.3	584.2	574.9	565.6	556.3	547.0	540.3
47.5°	566.7	561.5	556.3	551.2	546.0	538.7	529.4	520.0	510.7	501.3	494.4
50°	538.7	533.1	527.5	522.0	516.4	508.8	499.2	489.6	479.9	470.3	463.2
52.5°	508.3	502.6	496.9	491.2	485.5	478.1	469.0	459.9	450.8	441.7	434.1
55°	463.5	458.1	452.7	447.3	441.9	434.4	425.0	415.5	406.1	396.6	389.0
57.5°	418.2	412.4	406.6	400.9	395.1	387.6	378.5	369.4	360.3	351.2	343.7
60°	389.0	383.1	377.2	371.3	365.4	357.9	348.7	339.6	330.5	321.4	314.0
62.5°	358.0	352.4	346.7	341.1	335.5	328.0	318.8	309.5	300.3	291.0	284.1
65°	313.8	308.1	302.3	296.6	290.8	283.5	274.5	265.6	256.6	247.7	240.9
67.5°	269.9	264.1	258.4	252.7	246.9	239.8	231.2	222.6	214.0	205.4	199.3
70°	240.1	234.4	228.6	222.9	217.1	210.0	201.6	193.2	184.7	176.3	171.0
72.5°	210.9	205.3	199.7	194.1	188.5	181.7	173.8	165.9	158.0	150.1	145.3
75°	167.2	162.1	157.0	152.0	146.9	140.8	133.7	126.6	119.5	112.4	108.7
77.5°	123.7	119.6	115.6	111.5	107.5	102.6	96.9	91.3	85.6	79.9	77.3
80°	98.8	94.7	90.7	86.6	82.6	78.2	73.4	68.7	64.0	59.3	57.7
82.5°	74.5	70.8	67.2	63.5	59.9	56.4	53.2	49.9	46.7	43.5	42.8
85°	41.8	38.7	35.7	32.7	29.6	27.7	26.8	26.0	25.2	24.3	24.1
87.5°	14.1	13.2	12.4	11.6	10.8	10.3	10.3	10.3	10.3	10.2	10.3
90°	0.4	1.0	1.6	2.2	2.9	3.5	4.0	4.6	5.1	5.7	6.0
92.5°	5.4	5.0	4.6	4.1	3.7	3.7	4.2	4.7	5.2	5.7	6.0
95°	20.1	19.9	19.7	19.4	19.2	17.6	14.6	11.6	8.6	5.7	6.0
97.5°	42.1	42.5	42.9	43.3	43.8	41.0	35.1	29.2	23.3	17.4	15.2
100°	59.0	59.3	59.5	59.7	60.0	60.2	60.6	60.9	61.2	61.5	49.8
102.5°	76.3	76.6	76.9	77.2	77.5	77.7	77.9	78.1	78.3	78.5	76.3
105°	103.9	104.2	104.6	104.9	105.2	105.3	105.3	105.3	105.3	105.3	105.3
107.5°	132.6	132.6	132.6	132.6	132.6	132.7	132.9	133.0	133.2	133.3	133.3
110°	151.3	151.3	151.3	151.3	151.3	151.4	151.5	151.7	151.8	152.0	151.8



TEST NUMBER: P333523

CATALOG NUMBER: S125RDIP-S610D365U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	168.8	169.0	169.2	169.4	169.6	169.7	169.8	169.9	170.0	170.1	169.8
115°	195.1	195.5	195.9	196.3	196.7	196.9	197.0	197.1	197.2	197.2	196.9
117.5°	222.3	222.3	222.3	222.3	222.3	222.4	222.7	223.0	223.3	223.6	223.2
120°	239.3	239.2	239.2	239.1	239.0	239.1	239.3	239.5	239.8	240.0	239.9
122.5°	254.3	254.6	254.9	255.2	255.5	255.7	255.8	255.9	256.0	256.1	256.0
125°	277.5	278.0	278.6	279.1	279.7	280.0	280.0	280.0	280.0	280.0	279.6
127.5°	299.6	300.0	300.4	300.8	301.2	301.4	301.3	301.3	301.2	301.2	301.0
130°	313.2	313.6	314.0	314.4	314.8	315.0	315.1	315.1	315.2	315.3	315.1
132.5°	326.8	327.2	327.7	328.1	328.6	328.7	328.6	328.4	328.2	328.0	328.0
135°	346.1	346.5	347.0	347.5	347.9	348.1	347.9	347.8	347.6	347.5	347.3
137.5°	363.8	364.2	364.6	365.0	365.4	365.6	365.4	365.3	365.1	365.0	365.0
140°	375.4	375.6	375.7	375.9	376.0	376.1	376.0	375.9	375.8	375.8	375.9
142.5°	385.9	386.0	386.1	386.1	386.2	386.3	386.5	386.6	386.7	386.8	386.8
145°	401.2	401.4	401.5	401.7	401.8	401.9	401.9	401.9	401.9	401.9	402.0
147.5°	414.6	414.6	414.6	414.5	414.5	414.5	414.6	414.7	414.8	414.9	415.0
150°	423.1	423.0	422.8	422.6	422.5	422.5	422.6	422.8	423.0	423.1	423.3
152.5°	431.3	431.0	430.6	430.3	429.9	429.8	430.0	430.2	430.3	430.5	430.6
155°	441.9	441.4	440.9	440.4	440.0	439.8	440.0	440.1	440.3	440.4	440.7
157.5°	450.0	449.7	449.4	449.1	448.9	448.7	448.7	448.8	448.8	448.8	449.0
160°	455.6	455.2	454.7	454.2	453.8	453.6	453.6	453.7	453.8	453.9	454.2
162.5°	460.2	459.7	459.2	458.7	458.3	458.1	458.2	458.2	458.3	458.4	458.8
165°	466.2	465.8	465.3	464.8	464.4	464.2	464.2	464.3	464.4	464.5	464.9
167.5°	470.8	470.3	469.8	469.3	468.8	468.6	468.7	468.8	468.9	468.9	469.5
170°	473.3	472.8	472.2	471.7	471.1	470.9	471.0	471.0	471.1	471.2	471.8
172.5°	475.0	474.5	473.9	473.4	472.8	472.6	472.7	472.9	473.0	473.2	473.7
175°	476.8	476.4	475.9	475.4	475.0	474.8	474.8	474.9	475.0	475.1	475.7
177.5°	477.7	477.3	476.9	476.6	476.2	476.0	476.1	476.2	476.2	476.3	476.7
180°	476.8	476.8	476.8	476.8	476.8	476.8	476.8	476.8	476.8	476.8	476.8



TEST NUMBER: P333523

CATALOG NUMBER: S125RDIP-S610D365U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0
2.5°	1002.6	1003.9	1005.3	1005.9	1005.8	1005.6	1005.5	1005.4
5°	996.4	998.1	999.8	1000.5	1000.1	999.8	999.5	999.1
7.5°	984.0	985.2	986.4	986.8	986.4	986.0	985.7	985.3
10°	973.5	974.0	974.6	974.6	974.0	973.5	973.0	972.5
12.5°	958.7	959.1	959.4	959.2	958.4	957.7	956.9	956.1
15°	934.2	934.0	933.9	933.0	931.5	930.0	928.5	926.9
17.5°	903.7	902.8	902.0	900.9	899.7	898.4	897.2	895.9
20°	881.2	880.3	879.5	878.3	876.8	875.3	873.8	872.2
22.5°	858.9	857.2	855.6	854.1	852.9	851.6	850.4	849.1
25°	822.3	820.1	817.9	815.8	814.0	812.1	810.3	808.4
27.5°	782.7	779.6	776.5	774.1	772.3	770.5	768.7	766.9
30°	754.3	750.4	746.5	743.8	742.3	740.8	739.3	737.8
32.5°	726.7	722.5	718.2	715.1	713.1	711.2	709.3	707.4
35°	683.9	679.0	674.1	670.5	668.1	665.7	663.4	661.0
37.5°	639.1	633.2	627.3	623.2	620.9	618.7	616.4	614.1
40°	609.4	603.0	596.6	592.4	590.4	588.3	586.3	584.3
42.5°	580.2	574.0	567.9	563.3	560.4	557.4	554.4	551.5
45°	533.5	526.8	520.0	515.4	512.9	510.3	507.8	505.3
47.5°	487.4	480.4	473.5	468.6	465.8	463.0	460.2	457.4
50°	456.1	449.0	441.9	437.1	434.6	432.1	429.5	427.0
52.5°	426.5	418.8	411.2	406.1	403.6	401.1	398.5	396.0
55°	381.4	373.8	366.2	361.1	358.4	355.7	353.0	350.3
57.5°	336.3	328.9	321.5	316.5	314.1	311.7	309.4	307.0
60°	306.5	299.1	291.7	286.7	284.2	281.6	279.1	276.6
62.5°	277.2	270.3	263.4	258.7	256.2	253.7	251.1	248.6
65°	234.2	227.4	220.7	216.0	213.5	211.0	208.4	205.9
67.5°	193.1	186.9	180.7	176.6	174.6	172.6	170.5	168.5
70°	165.8	160.6	155.3	151.7	149.7	147.7	145.6	143.6
72.5°	140.5	135.6	130.8	127.7	126.4	125.0	123.7	122.3
75°	105.0	101.3	97.6	95.1	94.0	92.8	91.6	90.4
77.5°	74.7	72.1	69.5	67.8	66.9	66.0	65.2	64.3
80°	56.2	54.7	53.2	52.3	51.9	51.6	51.2	50.9
82.5°	42.0	41.3	40.6	40.2	40.0	39.8	39.6	39.4
85°	24.0	23.8	23.6	23.5	23.3	23.1	23.0	22.8
87.5°	10.4	10.5	10.6	10.6	10.5	10.4	10.3	10.2
90°	6.4	6.8	7.2	7.5	7.8	8.0	8.2	8.5
92.5°	6.4	6.8	7.2	7.5	7.6	7.7	7.8	7.9
95°	6.4	6.8	7.2	7.4	7.4	7.4	7.4	7.4
97.5°	13.0	10.7	8.5	7.4	7.4	7.4	7.4	7.4
100°	38.1	26.4	14.7	8.7	8.4	8.1	7.7	7.4
102.5°	74.0	71.8	69.6	65.8	60.5	55.2	49.8	44.5
105°	105.3	105.3	105.3	105.3	105.2	105.1	105.1	105.0
107.5°	133.4	133.4	133.4	133.3	133.1	132.8	132.6	132.3
110°	151.5	151.3	151.1	151.0	151.1	151.1	151.2	151.3



TEST NUMBER: P333523

CATALOG NUMBER: S125RDIP-S610D365U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	169.5	169.2	168.9	168.7	168.6	168.5	168.4	168.3
115°	196.6	196.3	196.0	195.6	195.1	194.7	194.2	193.7
117.5°	222.8	222.4	222.0	221.7	221.5	221.3	221.1	220.9
120°	239.7	239.5	239.4	239.1	238.7	238.3	237.9	237.5
122.5°	255.8	255.7	255.5	255.2	254.7	254.3	253.8	253.4
125°	279.3	279.0	278.7	278.4	278.2	278.0	277.7	277.5
127.5°	300.8	300.6	300.5	300.1	299.5	298.9	298.4	297.8
130°	314.8	314.6	314.4	314.0	313.7	313.3	312.9	312.5
132.5°	327.9	327.9	327.8	327.6	327.2	326.8	326.4	326.1
135°	347.2	347.0	346.8	346.5	346.1	345.6	345.1	344.6
137.5°	365.1	365.1	365.1	364.9	364.5	364.1	363.7	363.3
140°	376.1	376.2	376.4	376.2	375.8	375.3	374.8	374.3
142.5°	386.8	386.9	386.9	386.7	386.2	385.7	385.3	384.8
145°	402.1	402.1	402.2	402.0	401.6	401.1	400.6	400.1
147.5°	415.1	415.2	415.3	415.1	414.5	413.9	413.4	412.8
150°	423.4	423.6	423.7	423.5	422.9	422.3	421.6	421.0
152.5°	430.8	430.9	431.1	430.9	430.3	429.8	429.2	428.6
155°	440.9	441.1	441.4	441.2	440.6	439.9	439.3	438.7
157.5°	449.3	449.5	449.8	449.6	449.0	448.3	447.7	447.1
160°	454.5	454.8	455.1	455.0	454.3	453.7	453.1	452.5
162.5°	459.3	459.7	460.2	460.0	459.3	458.6	458.0	457.3
165°	465.4	465.9	466.4	466.3	465.7	465.0	464.4	463.8
167.5°	470.1	470.6	471.2	471.1	470.4	469.7	469.0	468.3
170°	472.4	473.1	473.7	473.7	473.0	472.3	471.5	470.8
172.5°	474.3	474.9	475.4	475.4	474.7	473.9	473.2	472.5
175°	476.3	477.0	477.6	477.6	476.8	476.1	475.4	474.7
177.5°	477.2	477.6	478.0	478.0	477.5	477.0	476.5	476.0
180°	476.8	476.8	476.8	476.8	476.8	476.8	476.8	476.8

(END OF REPORT)