

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333240-927

Luminaire Tested: **S125DIP-S850D1035U927-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333240-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S850D1035U927-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5649.8 lumens
Efficiency: N/A
Efficacy: 108.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333240-927

CATALOG NUMBER: S125DIP-S850D1035U927-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333240-927

CATALOG NUMBER: S125DIP-S850D1035U927-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48
1	97	93	89	85	89	86	82	79	72	70	67	59	58	56	48	47	46	40
2	89	81	75	70	81	75	69	65	63	59	56	52	49	47	42	40	38	34
3	81	71	64	58	74	66	59	54	56	51	47	46	43	40	37	35	33	28
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	30	28	24
5	68	56	48	42	62	52	45	39	44	39	34	37	33	29	30	27	24	21
6	62	50	42	36	57	47	39	34	40	34	30	33	29	26	27	24	22	19
7	58	45	37	32	53	42	35	30	36	30	26	30	26	23	25	22	19	16
8	54	41	33	28	49	38	31	27	33	27	23	28	23	20	23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15	13
10	47	34	27	22	43	32	26	21	28	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6716	6716	6716
5°	6731	6667	6710
10°	6690	6620	6658
15°	6618	6540	6568
20°	6514	6429	6441
25°	6402	6297	6291
30°	6264	6154	6123
35°	6117	6000	5916
40°	5966	5833	5751
45°	5802	5681	5569
50°	5621	5497	5332
55°	5447	5290	5141
60°	5239	5079	4899
65°	4991	4828	4664
70°	4755	4538	4381
75°	4332	4190	4045
80°	3857	3794	3704
85°	3349	3416	3231



TEST NUMBER: P333240-927

CATALOG NUMBER: S125DIP-S850D1035U927-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.1	1.7
10°-20°	277.0	4.9
20°-30°	409.0	7.2
30°-40°	477.2	8.4
40°-50°	479.3	8.5
50°-60°	420.7	7.4
60°-70°	313.5	5.5
70°-80°	179.3	3.2
80°-90°	54.3	1.0
90°-100°	284.3	5.0
100°-110°	611.2	10.8
110°-120°	573.6	10.2
120°-130°	464.9	8.2
130°-140°	373.0	6.6
140°-150°	281.5	5.0
150°-160°	198.2	3.5
160°-170°	116.8	2.1
170°-180°	38.0	0.7
0°-30°	784.0	13.9
0°-40°	1261.2	22.3
0°-60°	2161.2	38.3
0°-90°	2708.3	47.9
90°-120°	1469.1	26.0
90°-150°	2588.5	45.8
90°-180°	2941.0	52.1
0°-180°	5649.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1040	1040	1040	1040	1040	
5°	1038	1036	1028	1035	1035	98
15°	990	987	978	982	982	279
25°	898	894	884	885	883	413
35°	776	772	761	757	750	485
45°	635	631	622	612	610	489
55°	484	481	470	462	457	432
65°	327	325	316	309	305	324
75°	174	172	168	165	162	185
85°	45	46	46	45	44	51
90°	1	7	13	17	18	4
95°	26	77	701	318	186	28
105°	89	125	573	1129	1048	94
115°	160	193	460	992	1167	157
125°	221	259	441	789	920	196
135°	259	312	438	662	764	201
145°	302	346	440	548	603	189
155°	345	371	429	484	505	159
165°	376	387	411	436	443	106
175°	391	391	395	399	398	37
180°	392	392	392	392	392	



TEST NUMBER: P333240-927

CATALOG NUMBER: S125DIP-S850D1035U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9
2.5°	1042.6	1042.1	1041.7	1041.2	1040.8	1039.8	1038.4	1037.0	1035.5	1034.0	1035.5
5°	1038.3	1037.9	1037.5	1037.2	1036.8	1035.7	1033.9	1032.1	1030.2	1028.4	1030.1
7.5°	1028.7	1028.4	1028.0	1027.6	1027.3	1026.1	1024.1	1022.1	1020.1	1018.0	1019.6
10°	1020.2	1019.9	1019.5	1019.1	1018.7	1017.6	1015.5	1013.5	1011.5	1009.5	1011.0
12.5°	1009.6	1009.0	1008.4	1007.7	1007.0	1005.8	1003.9	1002.0	1000.1	998.3	999.5
15°	989.8	989.2	988.6	988.1	987.5	986.3	984.3	982.2	980.2	978.2	979.1
17.5°	966.9	966.1	965.3	964.5	963.7	962.2	960.1	958.1	955.9	953.9	955.0
20°	947.8	947.5	947.1	946.7	946.3	944.9	942.5	940.2	937.8	935.4	936.8
22.5°	928.7	928.0	927.4	926.7	926.1	924.6	922.4	920.1	917.9	915.7	916.6
25°	898.4	897.5	896.6	895.6	894.8	893.1	890.7	888.4	886.0	883.6	884.0
27.5°	863.0	862.5	862.0	861.4	860.9	859.4	856.9	854.4	852.0	849.5	849.6
30°	840.0	839.5	838.9	838.4	837.8	836.1	833.5	830.7	827.9	825.2	824.8
32.5°	815.0	814.1	813.3	812.5	811.7	810.0	807.6	805.1	802.6	800.2	799.5
35°	775.9	775.1	774.4	773.6	772.9	771.3	768.7	766.1	763.6	761.0	760.1
37.5°	735.2	734.3	733.3	732.5	731.5	729.8	727.5	725.0	722.6	720.3	718.8
40°	707.6	706.6	705.8	704.8	703.9	702.2	699.6	697.0	694.5	691.9	690.3
42.5°	677.9	677.2	676.4	675.7	674.9	673.2	670.7	668.0	665.5	663.0	661.5
45°	635.2	634.4	633.7	633.0	632.2	630.7	628.6	626.4	624.2	622.0	619.8
47.5°	589.1	589.1	589.1	589.1	589.2	588.0	585.3	582.7	580.0	577.4	575.1
50°	559.4	558.9	558.3	557.8	557.3	555.9	553.7	551.5	549.3	547.1	544.7
52.5°	529.2	528.8	528.4	528.0	527.6	526.2	523.9	521.5	519.2	516.8	514.8
55°	483.8	483.2	482.7	482.1	481.6	480.0	477.4	474.9	472.3	469.8	468.1
57.5°	435.9	435.6	435.3	435.0	434.7	433.5	431.3	429.2	427.0	424.8	422.7
60°	405.6	404.9	404.2	403.4	402.7	401.3	399.3	397.3	395.3	393.2	391.4
62.5°	374.0	373.4	372.9	372.2	371.7	370.5	368.8	367.1	365.4	363.6	361.7
65°	326.6	326.2	325.9	325.5	325.2	324.0	321.9	320.0	317.9	315.9	314.3
67.5°	280.7	280.0	279.2	278.4	277.7	276.5	275.0	273.5	272.0	270.5	269.1
70°	251.8	250.8	249.9	249.0	248.1	246.8	245.2	243.5	241.9	240.3	239.2
72.5°	220.1	219.5	218.9	218.3	217.7	216.8	215.8	214.7	213.7	212.6	211.4
75°	173.6	173.3	172.9	172.5	172.1	171.5	170.6	169.7	168.7	167.9	167.3
77.5°	130.6	130.5	130.4	130.2	130.1	129.8	129.2	128.7	128.2	127.7	127.4
80°	103.7	103.7	103.7	103.7	103.7	103.5	103.1	102.7	102.3	102.0	101.9
82.5°	79.9	79.7	79.4	79.1	78.8	78.6	78.5	78.5	78.4	78.3	78.0
85°	45.2	45.5	45.6	45.8	45.9	46.1	46.1	46.1	46.1	46.1	45.9
87.5°	17.9	18.1	18.4	18.7	19.0	19.3	19.3	19.5	19.5	19.6	19.8
90°	0.8	1.6	3.2	4.8	6.3	7.9	8.7	10.3	11.1	12.7	13.5
92.5°	9.7	11.7	18.4	28.1	41.7	64.9	108.1	180.5	259.0	254.9	206.4
95°	26.1	26.9	33.2	41.9	59.3	94.9	179.5	353.5	571.8	700.7	685.6
97.5°	43.3	44.3	48.7	57.4	73.0	98.7	154.7	282.2	510.6	748.3	867.5
100°	55.4	57.0	60.1	68.8	83.8	107.6	153.4	256.2	455.5	714.1	911.8
102.5°	68.7	69.6	72.1	81.4	95.2	118.3	159.1	245.5	413.8	654.0	885.3
105°	89.4	89.4	93.3	101.2	113.9	136.0	170.8	241.2	373.3	573.3	800.3
107.5°	109.6	111.2	114.9	121.4	134.6	154.6	188.2	248.5	356.2	517.8	713.6
110°	124.1	125.7	128.9	136.0	147.9	168.4	200.9	255.4	351.1	491.9	664.2



TEST NUMBER: P333240-927

CATALOG NUMBER: S125DIP-S850D1035U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	138.7	140.3	142.8	150.0	161.8	181.7	212.9	264.3	351.1	476.7	627.6
115°	159.8	161.3	163.7	170.8	182.7	202.5	231.7	277.6	353.5	460.3	587.6
117.5°	178.7	181.1	183.6	190.8	204.2	223.3	251.0	292.8	358.7	452.2	563.7
120°	191.4	193.8	196.9	204.1	217.5	237.3	264.9	302.9	363.8	448.4	550.4
122.5°	204.7	206.4	208.9	216.0	230.8	250.6	278.2	314.3	368.2	445.2	539.0
125°	221.4	223.0	227.0	234.1	249.1	269.7	295.8	329.8	375.7	441.2	523.6
127.5°	234.6	236.9	242.0	251.0	267.0	287.6	312.7	344.0	384.0	439.3	509.3
130°	242.8	245.2	251.5	261.7	278.4	298.9	323.4	353.5	389.1	438.1	499.8
132.5°	249.1	252.1	259.7	271.2	288.5	309.0	333.6	361.7	394.7	438.1	492.2
135°	259.4	262.5	272.0	284.7	301.3	322.7	347.1	373.3	402.5	438.1	483.2
137.5°	272.4	274.7	283.6	296.3	312.5	334.5	356.8	381.8	409.6	439.0	475.2
140°	280.0	282.3	291.8	304.4	319.5	340.9	363.8	387.5	412.8	439.7	471.3
142.5°	288.8	290.6	299.4	312.0	326.5	346.5	368.2	390.6	414.7	440.3	468.2
145°	302.1	303.6	311.6	322.7	336.9	355.1	375.7	395.4	416.8	439.7	463.4
147.5°	316.0	317.0	323.8	334.1	346.3	362.3	380.4	398.2	417.6	437.6	458.5
150°	324.2	325.8	331.4	341.7	352.7	366.1	383.6	400.1	417.6	435.7	454.7
152.5°	333.1	334.1	339.0	347.9	358.4	370.6	386.7	401.4	416.9	433.2	450.3
155°	344.8	344.8	349.5	357.4	365.4	376.4	389.8	402.5	415.2	428.6	442.8
157.5°	355.2	355.1	358.9	365.7	372.6	381.0	392.5	403.3	413.1	423.9	435.9
160°	362.2	361.4	364.6	370.1	376.4	383.6	393.8	403.3	411.2	420.7	430.2
162.5°	367.9	367.1	370.3	375.2	380.2	386.1	395.1	402.7	409.3	416.9	425.2
165°	376.4	374.9	377.2	381.2	384.4	389.1	395.4	401.7	406.5	411.2	417.6
167.5°	382.1	381.4	382.8	385.0	387.2	390.1	395.4	399.8	402.0	405.7	410.1
170°	386.0	385.2	386.0	387.5	389.1	391.4	395.4	398.5	400.1	402.5	405.7
172.5°	388.5	387.1	387.9	389.4	390.3	391.4	394.7	397.3	397.6	398.7	401.2
175°	391.4	389.8	390.6	391.4	391.4	391.4	393.8	395.4	394.6	394.6	395.4
177.5°	392.8	391.6	391.6	392.2	391.6	391.6	392.8	393.5	392.2	392.2	392.8
180°	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2



TEST NUMBER: P333240-927

CATALOG NUMBER: S125DIP-S850D1035U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9
2.5°	1037.0	1038.4	1039.8	1040.5	1040.4	1040.2	1040.1	1039.9
5°	1031.7	1033.3	1035.0	1035.7	1035.5	1035.4	1035.1	1035.0
7.5°	1021.3	1022.9	1024.5	1025.2	1025.0	1024.8	1024.6	1024.5
10°	1012.4	1013.9	1015.3	1016.0	1015.8	1015.6	1015.4	1015.3
12.5°	1000.6	1001.8	1003.0	1003.5	1003.5	1003.5	1003.5	1003.4
15°	980.1	981.0	981.9	982.3	982.3	982.3	982.3	982.3
17.5°	956.2	957.3	958.4	958.5	957.6	956.7	955.8	954.9
20°	938.0	939.3	940.6	940.7	939.8	938.9	938.0	937.1
22.5°	917.3	918.2	919.1	919.2	918.5	917.9	917.3	916.7
25°	884.3	884.7	885.1	884.9	884.5	883.9	883.4	882.8
27.5°	849.7	849.8	849.9	849.6	849.1	848.5	848.0	847.4
30°	824.5	824.1	823.7	823.3	822.8	822.2	821.7	821.1
32.5°	798.8	798.2	797.6	796.7	795.7	794.7	793.8	792.8
35°	759.2	758.3	757.4	756.2	754.7	753.3	751.8	750.4
37.5°	717.5	716.1	714.8	713.7	712.9	712.0	711.2	710.3
40°	688.6	687.0	685.3	684.2	683.7	683.2	682.6	682.1
42.5°	660.0	658.5	657.0	655.8	655.0	654.1	653.2	652.4
45°	617.6	615.4	613.2	611.8	611.3	610.8	610.2	609.7
47.5°	572.9	570.7	568.5	566.7	565.5	564.2	562.8	561.6
50°	542.3	540.0	537.6	535.8	534.5	533.2	532.0	530.7
52.5°	512.7	510.6	508.5	506.8	505.3	503.9	502.5	501.1
55°	466.5	464.9	463.2	461.8	460.4	459.1	457.9	456.6
57.5°	420.6	418.5	416.4	414.9	414.2	413.6	412.9	412.2
60°	389.6	387.8	386.0	384.4	383.1	381.8	380.6	379.3
62.5°	359.7	357.7	355.8	354.3	353.3	352.3	351.3	350.3
65°	312.7	311.0	309.3	308.2	307.4	306.7	305.9	305.2
67.5°	267.8	266.3	265.0	264.0	263.6	263.2	262.7	262.3
70°	238.1	236.9	235.8	235.0	234.2	233.5	232.7	232.0
72.5°	210.1	208.9	207.6	206.6	205.9	205.2	204.5	203.7
75°	166.8	166.2	165.6	165.0	164.3	163.5	162.8	162.1
77.5°	127.1	126.7	126.4	126.0	125.4	124.9	124.5	123.9
80°	101.6	101.5	101.3	101.0	100.7	100.3	99.9	99.6
82.5°	77.6	77.3	77.0	76.8	76.8	76.7	76.6	76.5
85°	45.7	45.6	45.3	45.1	44.7	44.4	44.0	43.6
87.5°	20.0	20.1	20.3	20.4	20.1	19.9	19.7	19.4
90°	14.3	15.1	15.8	17.4	17.4	17.4	18.2	18.2
92.5°	140.1	101.7	76.5	64.9	54.7	52.8	51.7	50.5
95°	568.6	448.4	351.1	284.7	228.5	204.9	198.5	185.8
97.5°	846.8	762.5	667.7	575.4	526.6	482.2	459.3	449.2
100°	972.7	934.0	852.5	770.2	715.7	658.8	629.5	616.9
102.5°	1015.1	1038.9	999.9	944.2	885.9	845.4	813.6	804.1
105°	990.1	1098.4	1133.2	1124.5	1099.2	1073.2	1057.3	1047.8
107.5°	900.9	1045.4	1134.8	1176.1	1188.9	1188.7	1183.5	1177.2
110°	835.1	985.3	1096.9	1164.1	1199.7	1214.7	1220.2	1220.2



TEST NUMBER: P333240-927

CATALOG NUMBER: S125DIP-S850D1035U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	783.2	925.9	1038.6	1117.9	1169.9	1195.7	1209.5	1215.1
115°	718.0	840.7	949.0	1035.1	1096.9	1134.8	1157.0	1167.3
117.5°	676.0	781.6	875.0	954.0	1015.7	1054.9	1076.9	1083.2
120°	653.2	748.1	835.1	904.7	963.2	1001.2	1022.5	1028.9
122.5°	636.1	724.1	801.5	866.7	918.9	953.7	975.1	980.8
125°	611.3	692.0	760.7	817.7	862.0	894.4	911.8	919.7
127.5°	586.0	661.3	725.5	778.8	819.0	847.6	864.0	867.5
130°	570.2	639.8	701.5	752.9	792.4	818.5	834.3	839.1
132.5°	554.4	619.5	675.5	725.0	764.5	790.7	805.2	810.6
135°	533.8	588.4	639.0	684.0	718.8	745.0	759.1	763.9
137.5°	516.4	560.5	602.6	640.9	672.0	695.8	708.9	714.1
140°	506.9	544.1	580.4	613.7	642.9	663.5	675.3	679.3
142.5°	498.7	530.1	561.5	590.3	615.1	632.5	643.7	647.1
145°	487.9	512.5	536.9	558.3	577.3	590.7	599.4	602.6
147.5°	477.8	497.7	516.6	532.7	547.7	558.5	563.6	565.0
150°	472.1	489.5	504.5	518.8	530.6	540.1	543.3	544.1
152.5°	465.8	481.3	495.0	506.1	516.1	523.7	526.8	527.6
155°	456.3	469.0	480.1	488.7	496.6	502.2	504.5	505.3
157.5°	446.8	457.2	465.8	472.6	478.8	483.3	485.5	485.4
160°	440.5	448.4	456.3	461.8	467.4	471.3	472.9	472.1
162.5°	433.6	440.8	447.4	452.3	456.6	459.9	460.3	460.1
165°	423.9	429.4	434.2	438.1	441.2	442.8	442.8	442.8
167.5°	414.7	418.4	422.0	424.8	426.4	427.9	427.2	427.1
170°	409.6	412.0	414.4	416.0	417.6	418.4	418.4	417.6
172.5°	403.9	406.3	408.1	409.0	409.3	410.7	409.5	408.7
175°	397.8	397.8	399.3	399.3	399.3	400.1	398.5	397.8
177.5°	393.5	394.1	394.1	394.1	393.5	394.1	392.2	392.2
180°	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2

(END OF REPORT)