

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333220-927

Luminaire Tested: **S125DIP-S850D590U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333220-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S850D590U927-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4579.7 lumens
Efficiency: N/A
Efficacy: 113.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333220-927

CATALOG NUMBER: S125DIP-S850D590U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333220-927

CATALOG NUMBER: S125DIP-S850D590U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59
1	100	95	91	88	93	89	86	83	77	75	73	67	65	63	57	56	54	50
2	91	83	77	72	84	78	72	68	68	64	60	59	55	53	50	48	46	42
3	83	73	66	60	77	69	62	57	60	55	50	52	48	45	44	41	39	35
4	76	65	57	51	70	61	54	48	53	47	43	46	42	38	40	36	33	30
5	70	58	49	43	65	54	47	41	48	42	37	41	37	33	36	32	29	26
6	64	52	44	38	60	49	41	36	43	37	32	37	33	29	32	29	26	23
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23	20
8	55	43	35	29	51	40	33	28	36	30	25	31	26	23	27	23	20	18
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	18	16
10	48	36	28	24	45	34	27	23	30	24	21	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6716	6716	6716
5°	6731	6667	6710
10°	6690	6620	6658
15°	6618	6540	6568
20°	6514	6429	6441
25°	6402	6297	6291
30°	6264	6154	6123
35°	6117	6000	5916
40°	5966	5833	5751
45°	5802	5681	5569
50°	5621	5497	5332
55°	5447	5290	5141
60°	5239	5079	4899
65°	4991	4828	4664
70°	4755	4538	4381
75°	4332	4190	4045
80°	3857	3794	3704
85°	3349	3416	3231



TEST NUMBER: P333220-927

CATALOG NUMBER: S125DIP-S850D590U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.1	2.1
10°-20°	277.0	6.0
20°-30°	409.0	8.9
30°-40°	477.2	10.4
40°-50°	479.3	10.5
50°-60°	420.7	9.2
60°-70°	313.5	6.8
70°-80°	179.3	3.9
80°-90°	53.4	1.2
90°-100°	22.2	0.5
100°-110°	136.6	3.0
110°-120°	247.7	5.4
120°-130°	317.8	6.9
130°-140°	341.9	7.5
140°-150°	320.9	7.0
150°-160°	259.6	5.7
160°-170°	167.9	3.7
170°-180°	57.9	1.3
0°-30°	784.0	17.1
0°-40°	1261.2	27.5
0°-60°	2161.2	47.2
0°-90°	2707.4	59.1
90°-120°	406.4	8.9
90°-150°	1387.0	30.3
90°-180°	1872.0	40.9
0°-180°	4579.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1040	1040	1040	1040	1040	
5°	1038	1036	1028	1035	1035	98
15°	990	987	978	982	982	279
25°	898	894	884	885	883	413
35°	776	772	761	757	750	485
45°	635	631	622	612	610	489
55°	484	481	470	462	457	432
65°	327	325	316	309	305	324
75°	174	172	168	165	162	185
85°	45	46	46	45	44	51
90°	0	4	7	10	11	4
95°	26	24	7	9	10	33
105°	133	135	135	135	134	141
115°	250	252	252	250	248	247
125°	355	358	358	356	355	317
135°	442	445	444	443	441	341
145°	513	514	514	514	512	321
155°	565	562	563	564	561	260
165°	596	594	594	596	593	168
175°	610	607	607	611	607	58
180°	610	610	610	610	610	



TEST NUMBER: P333220-927

CATALOG NUMBER: S125DIP-S850D590U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9
2.5°	1042.6	1042.1	1041.7	1041.2	1040.8	1039.8	1038.4	1037.0	1035.5	1034.0	1035.5
5°	1038.3	1037.9	1037.5	1037.2	1036.8	1035.7	1033.9	1032.1	1030.2	1028.4	1030.1
7.5°	1028.7	1028.4	1028.0	1027.6	1027.3	1026.1	1024.1	1022.1	1020.1	1018.0	1019.6
10°	1020.2	1019.9	1019.5	1019.1	1018.7	1017.6	1015.5	1013.5	1011.5	1009.5	1011.0
12.5°	1009.6	1009.0	1008.4	1007.7	1007.0	1005.8	1003.9	1002.0	1000.1	998.3	999.5
15°	989.8	989.2	988.6	988.1	987.5	986.3	984.3	982.2	980.2	978.2	979.1
17.5°	966.9	966.1	965.3	964.5	963.7	962.2	960.1	958.1	955.9	953.9	955.0
20°	947.8	947.5	947.1	946.7	946.3	944.9	942.5	940.2	937.8	935.4	936.8
22.5°	928.7	928.0	927.4	926.7	926.1	924.6	922.4	920.1	917.9	915.7	916.6
25°	898.4	897.5	896.6	895.6	894.8	893.1	890.7	888.4	886.0	883.6	884.0
27.5°	863.0	862.5	862.0	861.4	860.9	859.4	856.9	854.4	852.0	849.5	849.6
30°	840.0	839.5	838.9	838.4	837.8	836.1	833.5	830.7	827.9	825.2	824.8
32.5°	815.0	814.1	813.3	812.5	811.7	810.0	807.6	805.1	802.6	800.2	799.5
35°	775.9	775.1	774.4	773.6	772.9	771.3	768.7	766.1	763.6	761.0	760.1
37.5°	735.2	734.3	733.3	732.5	731.5	729.8	727.5	725.0	722.6	720.3	718.8
40°	707.6	706.6	705.8	704.8	703.9	702.2	699.6	697.0	694.5	691.9	690.3
42.5°	677.9	677.2	676.4	675.7	674.9	673.2	670.7	668.0	665.5	663.0	661.5
45°	635.2	634.4	633.7	633.0	632.2	630.7	628.6	626.4	624.2	622.0	619.8
47.5°	589.1	589.1	589.1	589.1	589.2	588.0	585.3	582.7	580.0	577.4	575.1
50°	559.4	558.9	558.3	557.8	557.3	555.9	553.7	551.5	549.3	547.1	544.7
52.5°	529.2	528.8	528.4	528.0	527.6	526.2	523.9	521.5	519.2	516.8	514.8
55°	483.8	483.2	482.7	482.1	481.6	480.0	477.4	474.9	472.3	469.8	468.1
57.5°	435.9	435.6	435.3	435.0	434.7	433.5	431.3	429.2	427.0	424.8	422.7
60°	405.6	404.9	404.2	403.4	402.7	401.3	399.3	397.3	395.3	393.2	391.4
62.5°	374.0	373.4	372.9	372.2	371.7	370.5	368.8	367.1	365.4	363.6	361.7
65°	326.6	326.2	325.9	325.5	325.2	324.0	321.9	320.0	317.9	315.9	314.3
67.5°	280.7	280.0	279.2	278.4	277.7	276.5	275.0	273.5	272.0	270.5	269.1
70°	251.8	250.8	249.9	249.0	248.1	246.8	245.2	243.5	241.9	240.3	239.2
72.5°	220.1	219.5	218.9	218.3	217.7	216.8	215.8	214.7	213.7	212.6	211.4
75°	173.6	173.3	172.9	172.5	172.1	171.5	170.6	169.7	168.7	167.9	167.3
77.5°	130.6	130.5	130.4	130.2	130.1	129.8	129.2	128.7	128.2	127.7	127.4
80°	103.7	103.7	103.7	103.7	103.7	103.5	103.1	102.7	102.3	102.0	101.9
82.5°	79.9	79.7	79.4	79.1	78.8	78.6	78.5	78.5	78.4	78.3	78.0
85°	45.2	45.5	45.6	45.8	45.9	46.1	46.1	46.1	46.1	46.1	45.9
87.5°	17.8	18.0	18.2	18.4	18.5	18.6	18.5	18.5	18.5	18.5	18.7
90°	0.5	1.3	2.1	2.9	3.6	4.4	5.1	5.9	6.5	7.2	7.8
92.5°	7.0	6.4	5.9	5.3	4.7	4.8	5.4	6.0	6.6	7.2	7.8
95°	25.7	25.4	25.2	24.9	24.6	22.5	18.7	14.9	11.0	7.2	7.8
97.5°	53.8	54.3	54.9	55.4	55.9	52.4	44.9	37.3	29.8	22.3	19.4
100°	75.5	75.8	76.0	76.4	76.7	77.0	77.5	77.9	78.3	78.7	63.7
102.5°	97.5	97.9	98.3	98.7	99.0	99.3	99.6	99.9	100.1	100.4	97.5
105°	132.8	133.2	133.7	134.1	134.5	134.7	134.7	134.7	134.7	134.7	134.7
107.5°	169.6	169.6	169.6	169.6	169.6	169.7	169.8	170.1	170.3	170.5	170.5
110°	193.5	193.5	193.5	193.5	193.5	193.5	193.8	193.9	194.2	194.3	194.1



TEST NUMBER: P333220-927

CATALOG NUMBER: S125DIP-S850D590U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	215.9	216.1	216.3	216.6	216.8	217.0	217.1	217.2	217.4	217.5	217.1
115°	249.5	250.0	250.5	251.0	251.5	251.8	251.9	252.0	252.1	252.2	251.8
117.5°	284.3	284.2	284.2	284.2	284.2	284.4	284.8	285.2	285.5	285.9	285.4
120°	306.0	305.9	305.8	305.7	305.5	305.7	306.0	306.3	306.6	306.9	306.7
122.5°	325.1	325.5	325.9	326.3	326.7	326.9	327.1	327.3	327.3	327.5	327.3
125°	354.8	355.5	356.2	356.9	357.6	358.0	358.0	358.0	358.0	358.0	357.6
127.5°	383.1	383.6	384.1	384.6	385.1	385.3	385.2	385.2	385.2	385.1	384.8
130°	400.4	400.9	401.5	402.0	402.4	402.7	402.8	403.0	403.1	403.1	402.8
132.5°	417.8	418.4	419.0	419.5	420.1	420.3	420.1	419.9	419.6	419.5	419.4
135°	442.5	443.1	443.7	444.3	444.9	445.1	444.9	444.7	444.5	444.3	444.1
137.5°	465.2	465.7	466.2	466.8	467.2	467.5	467.2	467.1	466.9	466.7	466.8
140°	480.0	480.2	480.4	480.6	480.8	480.9	480.8	480.6	480.5	480.5	480.6
142.5°	493.4	493.5	493.6	493.8	493.8	494.0	494.2	494.2	494.4	494.6	494.6
145°	513.0	513.2	513.4	513.6	513.8	513.9	513.9	513.9	513.9	513.9	514.0
147.5°	530.1	530.1	530.0	530.0	530.0	530.0	530.1	530.3	530.4	530.5	530.7
150°	541.0	540.8	540.6	540.4	540.2	540.2	540.4	540.6	540.8	541.0	541.2
152.5°	551.5	551.0	550.6	550.2	549.7	549.6	549.8	550.0	550.2	550.4	550.6
155°	565.0	564.4	563.8	563.2	562.5	562.4	562.5	562.8	562.9	563.2	563.5
157.5°	575.4	575.0	574.6	574.3	573.9	573.8	573.8	573.8	573.8	573.9	574.2
160°	582.6	582.0	581.4	580.7	580.2	580.0	580.0	580.1	580.2	580.4	580.7
162.5°	588.4	587.8	587.2	586.5	586.0	585.7	585.8	585.9	586.0	586.1	586.7
165°	596.1	595.6	594.9	594.4	593.7	593.5	593.6	593.7	593.8	593.9	594.5
167.5°	601.9	601.3	600.7	600.1	599.4	599.2	599.3	599.4	599.4	599.6	600.3
170°	605.2	604.5	603.8	603.1	602.4	602.1	602.1	602.3	602.4	602.5	603.2
172.5°	607.4	606.7	605.9	605.2	604.5	604.3	604.4	604.7	604.8	605.0	605.7
175°	609.7	609.1	608.5	607.9	607.3	607.0	607.1	607.3	607.4	607.4	608.2
177.5°	610.8	610.3	609.8	609.3	608.9	608.6	608.7	608.8	608.9	609.0	609.6
180°	609.7	609.7	609.7	609.7	609.7	609.7	609.7	609.7	609.7	609.7	609.7



TEST NUMBER: P333220-927

CATALOG NUMBER: S125DIP-S850D590U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9
2.5°	1037.0	1038.4	1039.8	1040.5	1040.4	1040.2	1040.1	1039.9
5°	1031.7	1033.3	1035.0	1035.7	1035.5	1035.4	1035.1	1035.0
7.5°	1021.3	1022.9	1024.5	1025.2	1025.0	1024.8	1024.6	1024.5
10°	1012.4	1013.9	1015.3	1016.0	1015.8	1015.6	1015.4	1015.3
12.5°	1000.6	1001.8	1003.0	1003.5	1003.5	1003.5	1003.5	1003.4
15°	980.1	981.0	981.9	982.3	982.3	982.3	982.3	982.3
17.5°	956.2	957.3	958.4	958.5	957.6	956.7	955.8	954.9
20°	938.0	939.3	940.6	940.7	939.8	938.9	938.0	937.1
22.5°	917.3	918.2	919.1	919.2	918.5	917.9	917.3	916.7
25°	884.3	884.7	885.1	884.9	884.5	883.9	883.4	882.8
27.5°	849.7	849.8	849.9	849.6	849.1	848.5	848.0	847.4
30°	824.5	824.1	823.7	823.3	822.8	822.2	821.7	821.1
32.5°	798.8	798.2	797.6	796.7	795.7	794.7	793.8	792.8
35°	759.2	758.3	757.4	756.2	754.7	753.3	751.8	750.4
37.5°	717.5	716.1	714.8	713.7	712.9	712.0	711.2	710.3
40°	688.6	687.0	685.3	684.2	683.7	683.2	682.6	682.1
42.5°	660.0	658.5	657.0	655.8	655.0	654.1	653.2	652.4
45°	617.6	615.4	613.2	611.8	611.3	610.8	610.2	609.7
47.5°	572.9	570.7	568.5	566.7	565.5	564.2	562.8	561.6
50°	542.3	540.0	537.6	535.8	534.5	533.2	532.0	530.7
52.5°	512.7	510.6	508.5	506.8	505.3	503.9	502.5	501.1
55°	466.5	464.9	463.2	461.8	460.4	459.1	457.9	456.6
57.5°	420.6	418.5	416.4	414.9	414.2	413.6	412.9	412.2
60°	389.6	387.8	386.0	384.4	383.1	381.8	380.6	379.3
62.5°	359.7	357.7	355.8	354.3	353.3	352.3	351.3	350.3
65°	312.7	311.0	309.3	308.2	307.4	306.7	305.9	305.2
67.5°	267.8	266.3	265.0	264.0	263.6	263.2	262.7	262.3
70°	238.1	236.9	235.8	235.0	234.2	233.5	232.7	232.0
72.5°	210.1	208.9	207.6	206.6	205.9	205.2	204.5	203.7
75°	166.8	166.2	165.6	165.0	164.3	163.5	162.8	162.1
77.5°	127.1	126.7	126.4	126.0	125.4	124.9	124.5	123.9
80°	101.6	101.5	101.3	101.0	100.7	100.3	99.9	99.6
82.5°	77.6	77.3	77.0	76.8	76.8	76.7	76.6	76.5
85°	45.7	45.6	45.3	45.1	44.7	44.4	44.0	43.6
87.5°	18.8	18.9	18.9	18.9	18.7	18.5	18.2	18.0
90°	8.2	8.7	9.3	9.7	10.0	10.2	10.5	10.9
92.5°	8.2	8.7	9.3	9.6	9.7	9.8	10.0	10.1
95°	8.2	8.7	9.3	9.5	9.5	9.5	9.5	9.5
97.5°	16.6	13.7	10.9	9.5	9.5	9.5	9.5	9.5
100°	48.7	33.7	18.8	11.1	10.7	10.3	9.9	9.5
102.5°	94.7	91.8	89.0	84.2	77.3	70.5	63.7	56.9
105°	134.7	134.7	134.7	134.7	134.5	134.4	134.4	134.2
107.5°	170.6	170.6	170.6	170.4	170.2	169.8	169.5	169.2
110°	193.8	193.5	193.1	193.1	193.1	193.2	193.4	193.5



TEST NUMBER: P333220-927

CATALOG NUMBER: S125DIP-S850D590U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	216.7	216.3	215.9	215.7	215.6	215.4	215.3	215.2
115°	251.4	251.0	250.6	250.1	249.5	248.9	248.3	247.7
117.5°	284.9	284.3	283.8	283.4	283.2	282.9	282.7	282.4
120°	306.5	306.3	306.1	305.7	305.2	304.8	304.2	303.7
122.5°	327.1	326.9	326.7	326.3	325.7	325.1	324.6	324.0
125°	357.2	356.7	356.3	356.0	355.7	355.4	355.1	354.8
127.5°	384.6	384.4	384.2	383.7	382.9	382.2	381.5	380.7
130°	402.6	402.3	402.0	401.6	401.1	400.5	400.1	399.6
132.5°	419.3	419.2	419.2	418.9	418.4	417.9	417.4	416.9
135°	443.9	443.7	443.5	443.1	442.5	441.9	441.2	440.7
137.5°	466.8	466.8	466.8	466.6	466.1	465.6	465.1	464.5
140°	480.9	481.0	481.3	481.0	480.5	479.8	479.3	478.6
142.5°	494.6	494.6	494.7	494.4	493.8	493.2	492.6	492.0
145°	514.1	514.2	514.3	514.0	513.4	512.9	512.2	511.6
147.5°	530.8	530.9	531.0	530.7	530.0	529.3	528.5	527.8
150°	541.4	541.6	541.8	541.5	540.7	539.9	539.1	538.3
152.5°	550.8	551.0	551.2	551.0	550.2	549.5	548.7	548.0
155°	563.8	564.0	564.4	564.1	563.3	562.5	561.7	560.9
157.5°	574.5	574.8	575.1	574.9	574.1	573.2	572.4	571.6
160°	581.1	581.5	581.9	581.7	580.9	580.1	579.3	578.5
162.5°	587.2	587.8	588.4	588.2	587.3	586.5	585.6	584.6
165°	595.1	595.7	596.3	596.2	595.4	594.6	593.8	592.9
167.5°	601.0	601.7	602.5	602.4	601.5	600.6	599.7	598.7
170°	604.1	604.9	605.7	605.6	604.8	603.8	602.9	602.1
172.5°	606.4	607.2	607.9	607.8	606.9	606.0	605.1	604.2
175°	609.0	609.8	610.7	610.6	609.7	608.8	607.9	607.0
177.5°	610.1	610.7	611.2	611.2	610.5	609.9	609.3	608.6
180°	609.7	609.7	609.7	609.7	609.7	609.7	609.7	609.7

(END OF REPORT)