

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333224-927

Luminaire Tested: **S125DIP-S850D810U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333224-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S850D810U927-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4957.6 lumens
Efficiency: N/A
Efficacy: 108.0 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333224-927

CATALOG NUMBER: S125DIP-S850D810U927-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333224-927

CATALOG NUMBER: S125DIP-S850D810U927-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	95	91	88	92	88	85	82	76	74	71	65	63	61	54	53	52	47
2	91	83	77	72	84	78	72	68	67	63	59	57	54	52	48	46	44	40
3	83	73	66	60	77	68	62	57	59	54	50	51	47	44	43	40	38	34
4	76	65	57	51	70	61	54	48	53	47	43	45	41	38	38	35	33	29
5	70	58	50	44	64	54	47	42	47	42	37	41	36	33	35	31	29	25
6	64	52	44	38	59	49	42	36	43	37	32	37	32	29	31	28	25	22
7	59	47	39	33	55	44	37	32	39	33	29	33	29	26	29	25	22	20
8	55	43	35	30	51	40	33	28	35	30	25	31	26	23	26	23	20	18
9	51	39	32	26	48	37	30	25	32	27	23	28	24	20	24	21	18	16
10	48	36	29	24	45	34	27	23	30	24	21	26	22	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6259	6259	6259	6259
5°	7248	6280	5499	6280
10°	8433	6248	4818	6248
15°	9335	6202	4444	6202
20°	10449	6129	4144	6129
25°	12241	6047	3998	6047
30°	13221	5967	3871	5967
35°	10871	5815	3788	5815
40°	7727	5604	3697	5604
45°	5936	5320	3644	5320
50°	5067	4967	3636	4967
55°	4512	4622	3668	4622
60°	4070	4246	3761	4246
65°	3759	3865	3859	3865
70°	3418	3473	3914	3473
75°	3019	3059	3880	3059
80°	2540	2492	3552	2492
85°	2016	1793	2868	1793



TEST NUMBER: P333224-927

CATALOG NUMBER: S125DIP-S850D810U927-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.3	1.9
10°-20°	277.8	5.6
20°-30°	451.1	9.1
30°-40°	550.2	11.1
40°-50°	500.5	10.1
50°-60°	398.7	8.0
60°-70°	277.7	5.6
70°-80°	148.1	3.0
80°-90°	39.1	0.8
90°-100°	53.3	1.1
100°-110°	157.4	3.2
110°-120°	266.7	5.4
120°-130°	350.9	7.1
130°-140°	393.2	7.9
140°-150°	385.4	7.8
150°-160°	323.7	6.5
160°-170°	215.2	4.3
170°-180°	75.3	1.5
0°-30°	822.1	16.6
0°-40°	1372.3	27.7
0°-60°	2271.6	45.8
0°-90°	2736.4	55.2
90°-120°	477.4	9.6
90°-150°	1607.0	32.4
90°-180°	2221.0	44.8
0°-180°	4957.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	969	969	969	969	969	
5°	1118	969	848	969	1118	113
15°	1396	928	665	928	1396	400
25°	1718	849	561	849	1718	785
35°	1379	738	480	738	1379	844
45°	650	582	399	582	650	520
55°	401	410	326	410	401	361
65°	246	253	252	253	246	244
75°	121	123	156	123	121	130
85°	27	24	39	24	27	32
90°	15	1	15	1	15	10
95°	53	40	53	40	53	54
105°	154	141	154	141	154	163
115°	270	267	270	267	270	267
125°	392	390	392	390	392	350
135°	509	507	509	507	509	392
145°	616	614	616	614	616	385
155°	702	702	702	702	702	323
165°	762	764	762	764	762	215
175°	791	794	791	794	791	75
180°	796	796	796	796	796	



TEST NUMBER: P333224-927

CATALOG NUMBER: S125DIP-S850D810U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2
2.5°	1025.1	1023.7	1022.5	1019.8	1021.8	1016.2	1013.5	1008.9	1003.4	1001.4	999.1
5°	1118.0	1120.1	1122.1	1113.5	1114.4	1108.6	1095.4	1084.7	1076.1	1065.0	1057.2
7.5°	1229.9	1225.0	1224.6	1219.1	1209.4	1201.7	1187.9	1170.3	1153.3	1133.9	1117.8
10°	1285.9	1286.3	1282.5	1276.0	1265.7	1258.3	1240.2	1222.9	1202.0	1177.3	1159.6
12.5°	1328.0	1329.7	1325.0	1316.1	1311.1	1294.5	1280.3	1259.8	1234.9	1215.1	1188.2
15°	1396.1	1391.5	1388.3	1377.2	1368.6	1351.3	1328.6	1307.3	1280.1	1255.0	1229.9
17.5°	1461.7	1465.4	1459.2	1449.1	1422.3	1402.1	1371.7	1342.4	1308.7	1275.0	1245.1
20°	1520.4	1523.6	1514.2	1496.5	1464.4	1444.2	1404.3	1366.5	1327.4	1284.2	1251.3
22.5°	1593.4	1590.8	1578.0	1551.1	1523.3	1486.1	1442.8	1396.8	1347.8	1299.0	1255.3
25°	1717.8	1700.5	1692.7	1659.4	1622.8	1568.0	1508.8	1441.4	1380.5	1315.9	1260.0
27.5°	1786.7	1781.3	1772.6	1749.4	1710.9	1652.4	1582.5	1500.3	1414.4	1332.9	1259.7
30°	1772.9	1773.7	1774.6	1767.1	1742.5	1698.4	1629.0	1540.5	1438.4	1346.7	1262.0
32.5°	1650.5	1665.5	1679.7	1696.7	1703.6	1695.2	1651.6	1571.8	1466.8	1362.6	1260.7
35°	1378.8	1383.4	1429.8	1475.9	1538.4	1587.0	1619.5	1584.1	1495.6	1375.9	1259.1
37.5°	1075.1	1097.3	1129.5	1181.5	1271.8	1352.6	1456.5	1504.3	1475.8	1380.3	1256.2
40°	916.5	937.1	958.0	1011.1	1087.2	1185.1	1303.1	1403.9	1427.4	1366.5	1246.3
42.5°	794.1	810.3	833.6	873.5	937.2	1023.8	1136.6	1268.4	1349.4	1326.4	1225.7
45°	649.9	660.2	678.3	710.0	756.1	823.9	923.4	1067.5	1192.9	1234.5	1176.5
47.5°	556.3	556.2	570.3	592.2	625.4	683.1	756.7	869.5	1003.5	1102.6	1098.0
50°	504.3	502.2	513.3	532.3	558.6	596.8	667.2	757.2	886.1	998.3	1029.6
52.5°	459.5	459.8	466.6	480.6	502.6	535.4	587.9	669.1	779.1	894.4	953.2
55°	400.7	399.0	406.8	416.3	432.3	453.7	491.5	553.7	642.9	756.5	833.0
57.5°	346.7	351.2	354.3	360.9	374.2	388.6	420.5	466.0	536.9	634.3	715.2
60°	315.1	319.6	322.1	328.7	339.4	351.7	376.4	413.4	473.0	557.0	637.2
62.5°	286.8	290.3	291.1	297.1	305.8	317.8	337.2	368.3	415.4	488.9	567.4
65°	246.0	246.0	247.6	253.8	257.9	268.6	283.4	306.0	343.9	401.1	468.1
67.5°	206.7	208.7	208.2	211.0	214.8	223.0	233.6	252.3	280.4	322.1	375.7
70°	181.0	182.6	182.2	184.3	188.4	193.8	202.4	220.1	240.2	276.0	322.1
72.5°	158.0	158.6	157.6	160.3	162.7	167.4	177.1	186.5	205.3	235.5	273.4
75°	121.0	121.8	122.6	124.2	126.7	129.1	134.1	143.5	155.9	178.6	202.8
77.5°	90.6	89.1	91.1	90.9	92.2	94.1	98.5	103.5	113.6	127.9	146.7
80°	68.3	68.7	68.7	69.1	71.1	72.4	76.1	79.8	87.6	98.3	111.5
82.5°	49.8	50.9	50.3	51.0	52.8	53.6	55.7	58.7	63.3	71.7	81.2
85°	27.2	25.1	25.9	26.8	26.8	27.2	28.8	30.0	32.5	35.8	39.5
87.5°	10.9	11.4	11.7	11.6	11.9	11.7	12.9	12.8	13.6	14.5	15.6
90°	14.9	14.4	14.0	13.6	13.2	12.7	12.0	11.2	10.6	9.9	9.0
92.5°	29.2	28.9	28.6	28.4	28.0	27.4	26.5	25.6	24.7	23.8	22.6
95°	53.2	53.0	52.8	52.4	52.2	51.6	50.6	49.6	48.6	47.7	46.3
97.5°	80.8	80.6	80.4	80.2	80.1	79.6	78.7	77.8	76.8	76.0	74.1
100°	101.6	101.3	101.0	100.8	100.5	99.7	98.5	97.3	96.0	94.7	93.0
102.5°	122.4	122.0	121.6	121.3	120.9	120.0	118.7	117.3	116.0	114.6	113.7
105°	153.6	153.2	152.8	152.4	151.9	151.4	150.5	149.7	148.9	148.1	147.2
107.5°	185.6	185.6	185.6	185.7	185.7	185.5	185.1	184.7	184.3	183.9	183.2
110°	209.4	209.5	209.6	209.8	209.9	209.8	209.4	209.0	208.6	208.1	207.7



TEST NUMBER: P333224-927

CATALOG NUMBER: S125DIP-S850D810U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	232.7	232.9	233.1	233.4	233.7	233.7	233.5	233.3	233.1	232.9	232.4
115°	269.5	269.6	269.7	269.9	270.0	270.1	270.3	270.5	270.5	270.7	270.5
117.5°	305.4	305.9	306.5	307.0	307.6	307.8	307.7	307.6	307.4	307.4	307.1
120°	330.2	330.7	331.3	331.8	332.4	332.6	332.6	332.6	332.6	332.6	332.5
122.5°	355.0	355.4	355.8	356.2	356.7	357.0	357.1	357.2	357.3	357.4	357.0
125°	392.1	392.3	392.4	392.5	392.7	392.8	393.2	393.4	393.7	394.0	393.8
127.5°	427.8	428.1	428.3	428.6	428.9	429.1	429.2	429.4	429.5	429.7	429.5
130°	451.5	451.9	452.1	452.4	452.7	452.9	453.0	453.1	453.3	453.4	453.1
132.5°	473.9	474.3	474.7	475.1	475.4	475.7	475.8	475.9	476.1	476.3	476.3
135°	508.6	509.1	509.7	510.2	510.8	511.0	511.0	511.0	511.0	511.0	510.9
137.5°	542.5	543.2	543.9	544.5	545.3	545.5	545.3	545.2	545.0	544.9	544.5
140°	564.4	565.0	565.7	566.4	567.0	567.3	567.0	566.7	566.5	566.2	565.8
142.5°	585.1	585.8	586.5	587.2	587.9	588.1	588.0	587.8	587.6	587.5	586.9
145°	616.3	616.8	617.2	617.6	618.0	618.2	618.2	618.2	618.2	618.2	617.8
147.5°	643.0	644.0	644.8	645.8	646.7	647.1	646.7	646.3	646.0	645.7	645.4
150°	662.8	663.1	663.4	663.6	663.9	664.1	664.1	664.1	664.1	664.1	663.5
152.5°	679.1	679.7	680.2	680.6	681.1	681.2	680.9	680.6	680.2	679.9	679.7
155°	702.4	703.1	703.9	704.5	705.2	705.3	704.7	704.2	703.6	703.1	702.9
157.5°	721.9	722.8	723.7	724.6	725.6	725.7	725.2	724.6	724.1	723.5	723.3
160°	735.3	735.9	736.7	737.4	738.1	738.1	737.5	737.0	736.5	735.9	735.8
162.5°	746.7	747.5	748.3	749.1	749.9	750.0	749.3	748.6	748.0	747.3	747.3
165°	761.9	762.7	763.6	764.4	765.2	765.3	764.9	764.3	763.7	763.2	763.0
167.5°	774.0	774.9	775.8	776.7	777.4	777.5	776.7	775.9	775.0	774.2	774.2
170°	780.5	781.5	782.4	783.4	784.3	784.4	783.6	782.8	782.0	781.1	781.1
172.5°	785.9	786.8	787.7	788.5	789.4	789.4	788.5	787.7	786.9	786.1	786.1
175°	791.1	792.0	793.0	793.9	794.9	795.0	794.2	793.3	792.5	791.6	791.6
177.5°	794.0	794.8	795.6	796.3	797.1	797.2	796.5	795.8	795.2	794.5	794.6
180°	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0



TEST NUMBER: P333224-927

CATALOG NUMBER: S125DIP-S850D810U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2
2.5°	997.1	994.8	992.1	987.5	982.0	979.0	974.4	971.5	965.5	960.6	955.3
5°	1047.7	1037.0	1027.1	1014.4	1000.4	991.3	980.6	968.7	956.4	943.6	929.6
7.5°	1100.1	1081.2	1060.6	1038.5	1016.8	997.0	977.9	959.3	941.8	920.8	902.9
10°	1135.3	1111.4	1085.9	1055.9	1026.7	1001.2	975.3	952.7	929.6	905.0	883.1
12.5°	1170.5	1138.8	1102.7	1069.8	1034.6	1003.9	973.4	944.4	915.5	888.2	862.8
15°	1195.4	1167.4	1134.1	1087.2	1047.7	1005.4	965.0	927.6	892.6	862.2	830.1
17.5°	1211.7	1175.7	1140.0	1095.0	1043.1	995.8	950.1	907.3	867.8	829.3	798.4
20°	1214.7	1177.7	1140.3	1096.2	1043.1	988.9	943.3	891.8	849.5	809.5	771.7
22.5°	1213.7	1171.8	1131.0	1085.7	1034.0	984.0	928.8	876.3	830.4	791.1	751.6
25°	1204.4	1159.6	1108.6	1063.0	1011.9	958.9	902.9	848.6	801.7	756.9	717.8
27.5°	1196.7	1138.5	1080.8	1027.5	978.3	929.6	876.1	820.5	768.5	723.0	686.2
30°	1187.2	1123.4	1058.4	1002.8	952.3	905.0	854.4	800.1	745.8	701.3	661.9
32.5°	1178.6	1104.3	1035.7	975.3	921.6	875.7	829.0	777.4	724.1	679.0	639.4
35°	1162.1	1076.1	997.5	929.2	872.0	824.7	785.7	737.5	688.6	645.0	607.1
37.5°	1141.1	1039.0	954.7	883.1	820.5	770.6	734.3	697.3	650.3	608.3	574.1
40°	1124.6	1012.7	923.4	850.2	785.3	733.4	699.7	664.7	625.7	586.6	550.4
42.5°	1103.9	989.0	891.9	813.1	748.7	698.2	662.8	633.1	598.7	562.2	528.6
45°	1065.8	946.1	840.8	756.1	691.0	641.3	604.7	582.5	556.6	522.0	493.6
47.5°	1009.8	894.5	785.6	698.2	631.1	584.9	550.6	529.3	511.0	485.4	459.6
50°	960.0	856.0	745.8	658.9	591.9	545.4	513.8	494.4	478.8	459.1	437.3
52.5°	904.4	807.6	706.6	620.8	554.4	508.6	477.6	460.6	447.6	433.4	411.9
55°	816.1	733.9	640.1	558.6	497.3	452.5	425.3	410.5	399.8	389.1	376.0
57.5°	718.7	654.4	571.3	496.9	440.5	399.7	374.3	359.9	351.6	346.1	338.3
60°	650.3	595.2	523.6	455.7	400.7	364.5	339.8	328.7	321.7	317.1	311.4
62.5°	586.8	541.6	475.2	413.3	365.1	330.9	308.9	298.1	291.4	289.1	284.4
65°	493.2	458.3	403.5	352.1	311.0	281.8	263.2	252.9	248.8	246.4	246.8
67.5°	401.0	379.7	335.7	291.9	259.0	234.6	219.8	211.8	209.8	206.5	206.4
70°	344.7	328.7	291.7	253.4	224.2	205.3	192.1	183.9	181.8	180.1	179.7
72.5°	295.0	281.0	248.8	218.2	191.9	175.3	164.5	159.5	156.1	155.2	155.1
75°	221.7	213.9	188.4	164.1	146.0	134.5	127.1	122.6	120.1	119.7	120.1
77.5°	157.6	150.8	134.6	117.4	106.0	97.3	91.0	89.4	86.7	86.7	86.3
80°	118.4	113.9	103.7	90.1	80.6	73.2	69.9	67.0	66.2	65.0	66.2
82.5°	85.9	81.0	74.1	65.4	57.6	53.2	49.8	49.0	48.5	47.8	48.2
85°	42.4	42.8	38.7	32.1	28.8	26.3	24.2	24.2	23.8	23.4	23.8
87.5°	16.1	15.2	13.7	12.5	10.7	9.4	8.9	9.0	8.2	8.2	8.7
90°	8.0	7.1	6.0	5.0	4.0	2.9	1.7	0.6	1.7	2.9	4.0
92.5°	21.4	20.2	19.0	18.1	17.3	16.6	15.8	15.0	15.8	16.6	17.3
95°	44.9	43.6	42.2	41.4	41.1	40.8	40.6	40.2	40.6	40.8	41.1
97.5°	72.2	70.3	68.4	67.3	67.3	67.1	67.0	66.9	67.0	67.1	67.3
100°	91.2	89.4	87.6	86.7	86.7	86.7	86.7	86.7	86.7	86.7	86.7
102.5°	112.8	111.9	111.0	110.3	109.7	109.2	108.6	108.1	108.6	109.2	109.7
105°	146.4	145.6	144.7	144.0	143.3	142.6	142.0	141.2	142.0	142.6	143.3
107.5°	182.6	182.0	181.3	180.7	180.0	179.3	178.6	177.9	178.6	179.3	180.0
110°	207.3	206.9	206.5	206.0	205.3	204.5	203.9	203.2	203.9	204.5	205.3



TEST NUMBER: P333224-927

CATALOG NUMBER: S125DIP-S850D810U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	231.9	231.3	230.8	230.4	230.0	229.7	229.3	228.9	229.3	229.7	230.0
115°	270.1	269.9	269.6	269.2	268.6	268.1	267.5	267.0	267.5	268.1	268.6
117.5°	306.9	306.7	306.4	306.1	305.9	305.6	305.4	305.1	305.4	305.6	305.9
120°	332.4	332.2	332.1	331.7	331.0	330.3	329.6	328.9	329.6	330.3	331.0
122.5°	356.7	356.3	356.0	355.7	355.5	355.2	355.0	354.7	355.0	355.2	355.5
125°	393.7	393.6	393.4	392.9	392.1	391.3	390.5	389.6	390.5	391.3	392.1
127.5°	429.3	429.1	429.0	428.6	428.2	427.7	427.3	426.8	427.3	427.7	428.2
130°	452.9	452.6	452.3	451.9	451.1	450.5	449.8	449.1	449.8	450.5	451.1
132.5°	476.3	476.4	476.4	475.9	474.8	473.6	472.5	471.4	472.5	473.6	474.8
135°	510.8	510.6	510.5	510.0	509.2	508.3	507.6	506.7	507.6	508.3	509.2
137.5°	544.2	544.0	543.7	543.1	542.3	541.5	540.7	540.0	540.7	541.5	542.3
140°	565.4	564.9	564.5	564.0	563.3	562.6	561.9	561.3	561.9	562.6	563.3
142.5°	586.5	585.9	585.4	584.9	584.2	583.7	583.1	582.6	583.1	583.7	584.2
145°	617.3	617.0	616.6	616.1	615.5	615.0	614.4	613.9	614.4	615.0	615.5
147.5°	645.1	644.8	644.4	644.0	643.8	643.5	643.2	642.9	643.2	643.5	643.8
150°	663.0	662.4	661.9	661.6	661.8	661.9	662.0	662.2	662.0	661.9	661.8
152.5°	679.5	679.2	679.1	678.8	678.7	678.4	678.3	678.0	678.3	678.4	678.7
155°	702.8	702.7	702.5	702.4	702.4	702.4	702.4	702.4	702.4	702.4	702.4
157.5°	723.3	723.1	722.9	723.0	723.3	723.7	724.0	724.3	724.0	723.7	723.3
160°	735.6	735.5	735.4	735.5	735.9	736.3	736.7	737.1	736.7	736.3	735.9
162.5°	747.3	747.2	747.2	747.3	747.7	747.9	748.2	748.5	748.2	747.9	747.7
165°	762.9	762.7	762.6	762.7	763.0	763.3	763.5	763.8	763.5	763.3	763.0
167.5°	774.2	774.2	774.2	774.4	775.0	775.5	776.1	776.7	776.1	775.5	775.0
170°	781.1	781.1	781.1	781.4	782.0	782.5	783.1	783.6	783.1	782.5	782.0
172.5°	786.1	786.1	786.1	786.3	786.9	787.4	788.0	788.5	788.0	787.4	786.9
175°	791.6	791.6	791.6	791.9	792.5	793.1	793.6	794.2	793.6	793.1	792.5
177.5°	794.7	794.9	795.0	795.2	795.7	796.1	796.5	797.0	796.5	796.1	795.7
180°	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0



TEST NUMBER: P333224-927

CATALOG NUMBER: S125DIP-S850D810U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2
2.5°	952.4	948.7	945.8	939.2	935.6	930.7	926.7	931.0	926.4	928.4	925.3
5°	922.7	911.2	902.9	891.0	880.7	871.2	864.3	863.0	859.7	858.1	853.1
7.5°	886.9	872.5	858.4	842.8	829.6	816.2	807.6	800.6	795.9	789.7	785.5
10°	865.9	846.5	830.1	811.2	794.7	780.3	768.8	763.0	757.7	749.9	747.0
12.5°	839.9	819.9	799.8	779.6	763.8	747.7	737.8	729.1	725.5	716.6	715.7
15°	808.7	778.7	758.9	738.4	716.5	703.4	695.1	685.7	681.6	675.4	670.9
17.5°	771.5	744.7	720.0	698.7	680.0	668.9	658.7	652.2	645.2	641.1	633.7
20°	744.6	719.1	694.3	671.7	657.4	644.6	636.4	630.2	622.8	620.8	613.3
22.5°	721.8	693.7	670.0	651.0	635.3	620.9	612.0	607.8	602.7	596.4	594.8
25°	684.9	655.7	635.6	616.6	602.6	589.5	583.3	578.0	573.0	568.5	566.8
27.5°	653.0	626.9	602.9	585.8	573.7	561.7	556.2	549.7	546.1	542.5	538.1
30°	630.6	603.9	582.9	566.4	553.3	542.6	536.8	532.3	529.0	525.7	523.2
32.5°	607.5	582.8	562.4	546.4	533.2	525.1	520.0	516.8	513.2	509.2	506.1
35°	577.1	549.9	530.2	516.3	506.0	499.8	494.0	491.2	487.0	487.0	483.7
37.5°	542.8	519.4	501.9	489.2	480.0	474.4	468.2	466.2	463.6	461.8	460.7
40°	522.4	500.6	484.2	471.4	461.5	457.0	452.1	448.8	447.1	445.0	444.3
42.5°	501.4	480.5	464.8	453.0	444.4	440.5	435.9	433.6	430.3	427.6	427.1
45°	469.4	449.2	434.8	425.3	418.0	413.4	410.5	405.6	403.9	400.7	400.2
47.5°	438.9	419.6	405.5	397.8	391.3	387.5	383.0	378.1	376.2	374.5	374.4
50°	416.3	398.6	385.4	378.0	371.9	366.5	361.9	358.7	357.4	357.4	358.3
52.5°	393.2	378.2	367.0	358.0	352.1	346.4	342.2	340.2	338.3	340.3	341.8
55°	359.5	344.3	336.0	327.4	321.7	315.1	313.1	312.2	311.0	314.3	315.9
57.5°	323.8	313.1	303.5	294.9	289.8	286.0	283.2	282.7	284.9	286.5	291.9
60°	301.1	288.8	280.1	273.5	267.4	264.9	264.1	263.2	264.9	269.4	276.4
62.5°	276.1	266.1	256.7	251.8	247.3	243.2	243.0	243.5	246.8	252.0	259.0
65°	239.4	230.8	224.6	218.8	215.2	212.7	213.5	215.2	218.8	225.9	233.6
67.5°	202.2	196.2	190.7	186.0	182.4	182.4	183.3	185.8	190.1	198.2	205.3
70°	178.1	171.5	167.0	164.9	162.1	160.4	162.9	167.0	170.7	178.1	184.3
72.5°	154.1	148.5	145.0	143.5	142.4	141.0	141.8	146.2	151.3	158.7	165.9
75°	118.4	116.4	113.9	112.3	111.1	111.9	112.7	116.8	121.0	128.7	137.0
77.5°	86.4	84.3	82.9	82.5	81.8	82.1	84.5	87.5	91.6	97.3	103.5
80°	65.4	64.6	63.8	63.4	63.4	63.8	67.0	69.1	72.8	78.2	83.1
82.5°	47.6	47.1	47.0	46.9	47.2	47.3	49.3	52.0	55.1	59.1	63.4
85°	25.1	24.2	25.5	25.9	25.1	26.3	27.2	28.8	30.0	32.1	34.1
87.5°	9.3	10.1	10.0	10.5	10.7	11.5	11.3	12.8	13.5	14.4	14.2
90°	5.0	6.0	7.1	8.0	9.0	9.9	10.6	11.2	12.0	12.7	13.2
92.5°	18.1	19.0	20.2	21.4	22.6	23.8	24.7	25.6	26.5	27.4	28.0
95°	41.4	42.2	43.6	44.9	46.3	47.7	48.6	49.6	50.6	51.6	52.2
97.5°	67.3	68.4	70.3	72.2	74.1	76.0	76.8	77.8	78.7	79.6	80.1
100°	86.7	87.6	89.4	91.2	93.0	94.7	96.0	97.3	98.5	99.7	100.5
102.5°	110.3	111.0	111.9	112.8	113.7	114.6	116.0	117.3	118.7	120.0	120.9
105°	144.0	144.7	145.6	146.4	147.2	148.1	148.9	149.7	150.5	151.4	151.9
107.5°	180.7	181.3	182.0	182.6	183.2	183.9	184.3	184.7	185.1	185.5	185.7
110°	206.0	206.5	206.9	207.3	207.7	208.1	208.6	209.0	209.4	209.8	209.9



TEST NUMBER: P333224-927

CATALOG NUMBER: S125DIP-S850D810U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	230.4	230.8	231.3	231.9	232.4	232.9	233.1	233.3	233.5	233.7	233.7
115°	269.2	269.6	269.9	270.1	270.5	270.7	270.5	270.5	270.3	270.1	270.0
117.5°	306.1	306.4	306.7	306.9	307.1	307.4	307.4	307.6	307.7	307.8	307.6
120°	331.7	332.1	332.2	332.4	332.5	332.6	332.6	332.6	332.6	332.6	332.4
122.5°	355.7	356.0	356.3	356.7	357.0	357.4	357.3	357.2	357.1	357.0	356.7
125°	392.9	393.4	393.6	393.7	393.8	394.0	393.7	393.4	393.2	392.8	392.7
127.5°	428.6	429.0	429.1	429.3	429.5	429.7	429.5	429.4	429.2	429.1	428.9
130°	451.9	452.3	452.6	452.9	453.1	453.4	453.3	453.1	453.0	452.9	452.7
132.5°	475.9	476.4	476.4	476.3	476.3	476.3	476.1	475.9	475.8	475.7	475.4
135°	510.0	510.5	510.6	510.8	510.9	511.0	511.0	511.0	511.0	511.0	510.8
137.5°	543.1	543.7	544.0	544.2	544.5	544.9	545.0	545.2	545.3	545.5	545.3
140°	564.0	564.5	564.9	565.4	565.8	566.2	566.5	566.7	567.0	567.3	567.0
142.5°	584.9	585.4	585.9	586.5	586.9	587.5	587.6	587.8	588.0	588.1	587.9
145°	616.1	616.6	617.0	617.3	617.8	618.2	618.2	618.2	618.2	618.2	618.0
147.5°	644.0	644.4	644.8	645.1	645.4	645.7	646.0	646.3	646.7	647.1	646.7
150°	661.6	661.9	662.4	663.0	663.5	664.1	664.1	664.1	664.1	664.1	663.9
152.5°	678.8	679.1	679.2	679.5	679.7	679.9	680.2	680.6	680.9	681.2	681.1
155°	702.4	702.5	702.7	702.8	702.9	703.1	703.6	704.2	704.7	705.3	705.2
157.5°	723.0	722.9	723.1	723.3	723.3	723.5	724.1	724.6	725.2	725.7	725.6
160°	735.5	735.4	735.5	735.6	735.8	735.9	736.5	737.0	737.5	738.1	738.1
162.5°	747.3	747.2	747.2	747.3	747.3	747.3	748.0	748.6	749.3	750.0	749.9
165°	762.7	762.6	762.7	762.9	763.0	763.2	763.7	764.3	764.9	765.3	765.2
167.5°	774.4	774.2	774.2	774.2	774.2	774.2	775.0	775.9	776.7	777.5	777.4
170°	781.4	781.1	781.1	781.1	781.1	781.1	782.0	782.8	783.6	784.4	784.3
172.5°	786.3	786.1	786.1	786.1	786.1	786.1	786.9	787.7	788.5	789.4	789.4
175°	791.9	791.6	791.6	791.6	791.6	791.6	792.5	793.3	794.2	795.0	794.9
177.5°	795.2	795.0	794.9	794.7	794.6	794.5	795.2	795.8	796.5	797.2	797.1
180°	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0



TEST NUMBER: P333224-927

CATALOG NUMBER: S125DIP-S850D810U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2
2.5°	923.4	925.7	923.7	926.4	923.7	925.7	923.4	925.3	928.4	926.4	931.0
5°	851.0	847.4	849.9	848.2	849.9	847.4	851.0	853.1	858.1	859.7	863.0
7.5°	784.3	780.7	776.7	774.8	776.7	780.7	784.3	785.5	789.7	795.9	800.6
10°	742.5	737.9	737.5	734.7	737.5	737.9	742.5	747.0	749.9	757.7	763.0
12.5°	711.9	707.7	703.0	701.8	703.0	707.7	711.9	715.7	716.6	725.5	729.1
15°	668.4	665.1	662.3	664.7	662.3	665.1	668.4	670.9	675.4	681.6	685.7
17.5°	632.3	629.6	629.1	626.1	629.1	629.6	632.3	633.7	641.1	645.2	652.2
20°	609.6	607.5	608.4	603.0	608.4	607.5	609.6	613.3	620.8	622.8	630.2
22.5°	591.5	587.5	587.0	585.9	587.0	587.5	591.5	594.8	596.4	602.7	607.8
25°	563.2	561.1	559.0	561.1	559.0	561.1	563.2	566.8	568.5	573.0	578.0
27.5°	538.4	535.9	535.4	535.6	535.4	535.9	538.4	538.1	542.5	546.1	549.7
30°	523.2	519.1	519.5	519.1	519.5	519.1	523.2	523.2	525.7	529.0	532.3
32.5°	506.8	504.0	503.4	502.6	503.4	504.0	506.8	506.1	509.2	513.2	516.8
35°	482.5	482.5	480.5	480.5	480.5	482.5	482.5	483.7	487.0	487.0	491.2
37.5°	459.7	459.3	458.0	458.3	458.0	459.3	459.7	460.7	461.8	463.6	466.2
40°	442.6	442.2	440.9	438.5	440.9	442.2	442.6	444.3	445.0	447.1	448.8
42.5°	426.1	424.8	424.2	423.3	424.2	424.8	426.1	427.1	427.6	430.3	433.6
45°	400.2	400.2	399.4	399.0	399.4	400.2	400.2	400.2	400.7	403.9	405.6
47.5°	375.1	375.8	377.4	377.2	377.4	375.8	375.1	374.4	374.5	376.2	378.1
50°	359.9	360.4	361.6	361.9	361.6	360.4	359.9	358.3	357.4	357.4	358.7
52.5°	343.2	345.5	347.1	346.8	347.1	345.5	343.2	341.8	340.3	338.3	340.2
55°	319.6	322.5	325.3	325.8	325.3	322.5	319.6	315.9	314.3	311.0	312.2
57.5°	296.4	300.4	303.4	304.4	303.4	300.4	296.4	291.9	286.5	284.9	282.7
60°	280.5	285.9	289.6	291.2	289.6	285.9	280.5	276.4	269.4	264.9	263.2
62.5°	265.4	271.4	275.1	275.4	275.1	271.4	265.4	259.0	252.0	246.8	243.5
65°	240.7	246.8	250.1	252.5	250.1	246.8	240.7	233.6	225.9	218.8	215.2
67.5°	214.0	220.1	223.8	225.8	223.8	220.1	214.0	205.3	198.2	190.1	185.8
70°	194.6	200.7	205.7	207.3	205.7	200.7	194.6	184.3	178.1	170.7	167.0
72.5°	175.5	181.0	185.0	186.9	185.0	181.0	175.5	165.9	158.7	151.3	146.2
75°	142.4	149.7	153.4	155.5	153.4	149.7	142.4	137.0	128.7	121.0	116.8
77.5°	109.7	116.5	118.7	119.8	118.7	116.5	109.7	103.5	97.3	91.6	87.5
80°	88.0	92.1	95.0	95.5	95.0	92.1	88.0	83.1	78.2	72.8	69.1
82.5°	67.7	71.1	72.0	73.0	72.0	71.1	67.7	63.4	59.1	55.1	52.0
85°	37.0	38.7	39.1	38.7	39.1	38.7	37.0	34.1	32.1	30.0	28.8
87.5°	14.9	14.7	14.7	15.4	14.7	14.7	14.9	14.2	14.4	13.5	12.8
90°	13.6	14.0	14.4	14.9	14.4	14.0	13.6	13.2	12.7	12.0	11.2
92.5°	28.4	28.6	28.9	29.2	28.9	28.6	28.4	28.0	27.4	26.5	25.6
95°	52.4	52.8	53.0	53.2	53.0	52.8	52.4	52.2	51.6	50.6	49.6
97.5°	80.2	80.4	80.6	80.8	80.6	80.4	80.2	80.1	79.6	78.7	77.8
100°	100.8	101.0	101.3	101.6	101.3	101.0	100.8	100.5	99.7	98.5	97.3
102.5°	121.3	121.6	122.0	122.4	122.0	121.6	121.3	120.9	120.0	118.7	117.3
105°	152.4	152.8	153.2	153.6	153.2	152.8	152.4	151.9	151.4	150.5	149.7
107.5°	185.7	185.6	185.6	185.6	185.6	185.6	185.7	185.7	185.5	185.1	184.7
110°	209.8	209.6	209.5	209.4	209.5	209.6	209.8	209.9	209.8	209.4	209.0



TEST NUMBER: P333224-927

CATALOG NUMBER: S125DIP-S850D810U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	233.4	233.1	232.9	232.7	232.9	233.1	233.4	233.7	233.7	233.5	233.3
115°	269.9	269.7	269.6	269.5	269.6	269.7	269.9	270.0	270.1	270.3	270.5
117.5°	307.0	306.5	305.9	305.4	305.9	306.5	307.0	307.6	307.8	307.7	307.6
120°	331.8	331.3	330.7	330.2	330.7	331.3	331.8	332.4	332.6	332.6	332.6
122.5°	356.2	355.8	355.4	355.0	355.4	355.8	356.2	356.7	357.0	357.1	357.2
125°	392.5	392.4	392.3	392.1	392.3	392.4	392.5	392.7	392.8	393.2	393.4
127.5°	428.6	428.3	428.1	427.8	428.1	428.3	428.6	428.9	429.1	429.2	429.4
130°	452.4	452.1	451.9	451.5	451.9	452.1	452.4	452.7	452.9	453.0	453.1
132.5°	475.1	474.7	474.3	473.9	474.3	474.7	475.1	475.4	475.7	475.8	475.9
135°	510.2	509.7	509.1	508.6	509.1	509.7	510.2	510.8	511.0	511.0	511.0
137.5°	544.5	543.9	543.2	542.5	543.2	543.9	544.5	545.3	545.5	545.3	545.2
140°	566.4	565.7	565.0	564.4	565.0	565.7	566.4	567.0	567.3	567.0	566.7
142.5°	587.2	586.5	585.8	585.1	585.8	586.5	587.2	587.9	588.1	588.0	587.8
145°	617.6	617.2	616.8	616.3	616.8	617.2	617.6	618.0	618.2	618.2	618.2
147.5°	645.8	644.8	644.0	643.0	644.0	644.8	645.8	646.7	647.1	646.7	646.3
150°	663.6	663.4	663.1	662.8	663.1	663.4	663.6	663.9	664.1	664.1	664.1
152.5°	680.6	680.2	679.7	679.1	679.7	680.2	680.6	681.1	681.2	680.9	680.6
155°	704.5	703.9	703.1	702.4	703.1	703.9	704.5	705.2	705.3	704.7	704.2
157.5°	724.6	723.7	722.8	721.9	722.8	723.7	724.6	725.6	725.7	725.2	724.6
160°	737.4	736.7	735.9	735.3	735.9	736.7	737.4	738.1	738.1	737.5	737.0
162.5°	749.1	748.3	747.5	746.7	747.5	748.3	749.1	749.9	750.0	749.3	748.6
165°	764.4	763.6	762.7	761.9	762.7	763.6	764.4	765.2	765.3	764.9	764.3
167.5°	776.7	775.8	774.9	774.0	774.9	775.8	776.7	777.4	777.5	776.7	775.9
170°	783.4	782.4	781.5	780.5	781.5	782.4	783.4	784.3	784.4	783.6	782.8
172.5°	788.5	787.7	786.8	785.9	786.8	787.7	788.5	789.4	789.4	788.5	787.7
175°	793.9	793.0	792.0	791.1	792.0	793.0	793.9	794.9	795.0	794.2	793.3
177.5°	796.3	795.6	794.8	794.0	794.8	795.6	796.3	797.1	797.2	796.5	795.8
180°	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0



TEST NUMBER: P333224-927

CATALOG NUMBER: S125DIP-S850D810U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2
2.5°	926.7	930.7	935.6	939.2	945.8	948.7	952.4	955.3	960.6	965.5	971.5
5°	864.3	871.2	880.7	891.0	902.9	911.2	922.7	929.6	943.6	956.4	968.7
7.5°	807.6	816.2	829.6	842.8	858.4	872.5	886.9	902.9	920.8	941.8	959.3
10°	768.8	780.3	794.7	811.2	830.1	846.5	865.9	883.1	905.0	929.6	952.7
12.5°	737.8	747.7	763.8	779.6	799.8	819.9	839.9	862.8	888.2	915.5	944.4
15°	695.1	703.4	716.5	738.4	758.9	778.7	808.7	830.1	862.2	892.6	927.6
17.5°	658.7	668.9	680.0	698.7	720.0	744.7	771.5	798.4	829.3	867.8	907.3
20°	636.4	644.6	657.4	671.7	694.3	719.1	744.6	771.7	809.5	849.5	891.8
22.5°	612.0	620.9	635.3	651.0	670.0	693.7	721.8	751.6	791.1	830.4	876.3
25°	583.3	589.5	602.6	616.6	635.6	655.7	684.9	717.8	756.9	801.7	848.6
27.5°	556.2	561.7	573.7	585.8	602.9	626.9	653.0	686.2	723.0	768.5	820.5
30°	536.8	542.6	553.3	566.4	582.9	603.9	630.6	661.9	701.3	745.8	800.1
32.5°	520.0	525.1	533.2	546.4	562.4	582.8	607.5	639.4	679.0	724.1	777.4
35°	494.0	499.8	506.0	516.3	530.2	549.9	577.1	607.1	645.0	688.6	737.5
37.5°	468.2	474.4	480.0	489.2	501.9	519.4	542.8	574.1	608.3	650.3	697.3
40°	452.1	457.0	461.5	471.4	484.2	500.6	522.4	550.4	586.6	625.7	664.7
42.5°	435.9	440.5	444.4	453.0	464.8	480.5	501.4	528.6	562.2	598.7	633.1
45°	410.5	413.4	418.0	425.3	434.8	449.2	469.4	493.6	522.0	556.6	582.5
47.5°	383.0	387.5	391.3	397.8	405.5	419.6	438.9	459.6	485.4	511.0	529.3
50°	361.9	366.5	371.9	378.0	385.4	398.6	416.3	437.3	459.1	478.8	494.4
52.5°	342.2	346.4	352.1	358.0	367.0	378.2	393.2	411.9	433.4	447.6	460.6
55°	313.1	315.1	321.7	327.4	336.0	344.3	359.5	376.0	389.1	399.8	410.5
57.5°	283.2	286.0	289.8	294.9	303.5	313.1	323.8	338.3	346.1	351.6	359.9
60°	264.1	264.9	267.4	273.5	280.1	288.8	301.1	311.4	317.1	321.7	328.7
62.5°	243.0	243.2	247.3	251.8	256.7	266.1	276.1	284.4	289.1	291.4	298.1
65°	213.5	212.7	215.2	218.8	224.6	230.8	239.4	246.8	246.4	248.8	252.9
67.5°	183.3	182.4	182.4	186.0	190.7	196.2	202.2	206.4	206.5	209.8	211.8
70°	162.9	160.4	162.1	164.9	167.0	171.5	178.1	179.7	180.1	181.8	183.9
72.5°	141.8	141.0	142.4	143.5	145.0	148.5	154.1	155.1	155.2	156.1	159.5
75°	112.7	111.9	111.1	112.3	113.9	116.4	118.4	120.1	119.7	120.1	122.6
77.5°	84.5	82.1	81.8	82.5	82.9	84.3	86.4	86.3	86.7	86.7	89.4
80°	67.0	63.8	63.4	63.4	63.8	64.6	65.4	66.2	65.0	66.2	67.0
82.5°	49.3	47.3	47.2	46.9	47.0	47.1	47.6	48.2	47.8	48.5	49.0
85°	27.2	26.3	25.1	25.9	25.5	24.2	25.1	23.8	23.4	23.8	24.2
87.5°	11.3	11.5	10.7	10.5	10.0	10.1	9.3	8.7	8.2	8.2	9.0
90°	10.6	9.9	9.0	8.0	7.1	6.0	5.0	4.0	2.9	1.7	0.6
92.5°	24.7	23.8	22.6	21.4	20.2	19.0	18.1	17.3	16.6	15.8	15.0
95°	48.6	47.7	46.3	44.9	43.6	42.2	41.4	41.1	40.8	40.6	40.2
97.5°	76.8	76.0	74.1	72.2	70.3	68.4	67.3	67.3	67.1	67.0	66.9
100°	96.0	94.7	93.0	91.2	89.4	87.6	86.7	86.7	86.7	86.7	86.7
102.5°	116.0	114.6	113.7	112.8	111.9	111.0	110.3	109.7	109.2	108.6	108.1
105°	148.9	148.1	147.2	146.4	145.6	144.7	144.0	143.3	142.6	142.0	141.2
107.5°	184.3	183.9	183.2	182.6	182.0	181.3	180.7	180.0	179.3	178.6	177.9
110°	208.6	208.1	207.7	207.3	206.9	206.5	206.0	205.3	204.5	203.9	203.2



TEST NUMBER: P333224-927

CATALOG NUMBER: S125DIP-S850D810U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	233.1	232.9	232.4	231.9	231.3	230.8	230.4	230.0	229.7	229.3	228.9
115°	270.5	270.7	270.5	270.1	269.9	269.6	269.2	268.6	268.1	267.5	267.0
117.5°	307.4	307.4	307.1	306.9	306.7	306.4	306.1	305.9	305.6	305.4	305.1
120°	332.6	332.6	332.5	332.4	332.2	332.1	331.7	331.0	330.3	329.6	328.9
122.5°	357.3	357.4	357.0	356.7	356.3	356.0	355.7	355.5	355.2	355.0	354.7
125°	393.7	394.0	393.8	393.7	393.6	393.4	392.9	392.1	391.3	390.5	389.6
127.5°	429.5	429.7	429.5	429.3	429.1	429.0	428.6	428.2	427.7	427.3	426.8
130°	453.3	453.4	453.1	452.9	452.6	452.3	451.9	451.1	450.5	449.8	449.1
132.5°	476.1	476.3	476.3	476.3	476.4	476.4	475.9	474.8	473.6	472.5	471.4
135°	511.0	511.0	510.9	510.8	510.6	510.5	510.0	509.2	508.3	507.6	506.7
137.5°	545.0	544.9	544.5	544.2	544.0	543.7	543.1	542.3	541.5	540.7	540.0
140°	566.5	566.2	565.8	565.4	564.9	564.5	564.0	563.3	562.6	561.9	561.3
142.5°	587.6	587.5	586.9	586.5	585.9	585.4	584.9	584.2	583.7	583.1	582.6
145°	618.2	618.2	617.8	617.3	617.0	616.6	616.1	615.5	615.0	614.4	613.9
147.5°	646.0	645.7	645.4	645.1	644.8	644.4	644.0	643.8	643.5	643.2	642.9
150°	664.1	664.1	663.5	663.0	662.4	661.9	661.6	661.8	661.9	662.0	662.2
152.5°	680.2	679.9	679.7	679.5	679.2	679.1	678.8	678.7	678.4	678.3	678.0
155°	703.6	703.1	702.9	702.8	702.7	702.5	702.4	702.4	702.4	702.4	702.4
157.5°	724.1	723.5	723.3	723.3	723.1	722.9	723.0	723.3	723.7	724.0	724.3
160°	736.5	735.9	735.8	735.6	735.5	735.4	735.5	735.9	736.3	736.7	737.1
162.5°	748.0	747.3	747.3	747.3	747.2	747.2	747.3	747.7	747.9	748.2	748.5
165°	763.7	763.2	763.0	762.9	762.7	762.6	762.7	763.0	763.3	763.5	763.8
167.5°	775.0	774.2	774.2	774.2	774.2	774.2	774.4	775.0	775.5	776.1	776.7
170°	782.0	781.1	781.1	781.1	781.1	781.1	781.4	782.0	782.5	783.1	783.6
172.5°	786.9	786.1	786.1	786.1	786.1	786.1	786.3	786.9	787.4	788.0	788.5
175°	792.5	791.6	791.6	791.6	791.6	791.6	791.9	792.5	793.1	793.6	794.2
177.5°	795.2	794.5	794.6	794.7	794.9	795.0	795.2	795.7	796.1	796.5	797.0
180°	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0



TEST NUMBER: P333224-927

CATALOG NUMBER: S125DIP-S850D810U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2
2.5°	974.4	979.0	982.0	987.5	992.1	994.8	997.1	999.1	1001.4	1003.4	1008.9
5°	980.6	991.3	1000.4	1014.4	1027.1	1037.0	1047.7	1057.2	1065.0	1076.1	1084.7
7.5°	977.9	997.0	1016.8	1038.5	1060.6	1081.2	1100.1	1117.8	1133.9	1153.3	1170.3
10°	975.3	1001.2	1026.7	1055.9	1085.9	1111.4	1135.3	1159.6	1177.3	1202.0	1222.9
12.5°	973.4	1003.9	1034.6	1069.8	1102.7	1138.8	1170.5	1188.2	1215.1	1234.9	1259.8
15°	965.0	1005.4	1047.7	1087.2	1134.1	1167.4	1195.4	1229.9	1255.0	1280.1	1307.3
17.5°	950.1	995.8	1043.1	1095.0	1140.0	1175.7	1211.7	1245.1	1275.0	1308.7	1342.4
20°	943.3	988.9	1043.1	1096.2	1140.3	1177.7	1214.7	1251.3	1284.2	1327.4	1366.5
22.5°	928.8	984.0	1034.0	1085.7	1131.0	1171.8	1213.7	1255.3	1299.0	1347.8	1396.8
25°	902.9	958.9	1011.9	1063.0	1108.6	1159.6	1204.4	1260.0	1315.9	1380.5	1441.4
27.5°	876.1	929.6	978.3	1027.5	1080.8	1138.5	1196.7	1259.7	1332.9	1414.4	1500.3
30°	854.4	905.0	952.3	1002.8	1058.4	1123.4	1187.2	1262.0	1346.7	1438.4	1540.5
32.5°	829.0	875.7	921.6	975.3	1035.7	1104.3	1178.6	1260.7	1362.6	1466.8	1571.8
35°	785.7	824.7	872.0	929.2	997.5	1076.1	1162.1	1259.1	1375.9	1495.6	1584.1
37.5°	734.3	770.6	820.5	883.1	954.7	1039.0	1141.1	1256.2	1380.3	1475.8	1504.3
40°	699.7	733.4	785.3	850.2	923.4	1012.7	1124.6	1246.3	1366.5	1427.4	1403.9
42.5°	662.8	698.2	748.7	813.1	891.9	989.0	1103.9	1225.7	1326.4	1349.4	1268.4
45°	604.7	641.3	691.0	756.1	840.8	946.1	1065.8	1176.5	1234.5	1192.9	1067.5
47.5°	550.6	584.9	631.1	698.2	785.6	894.5	1009.8	1098.0	1102.6	1003.5	869.5
50°	513.8	545.4	591.9	658.9	745.8	856.0	960.0	1029.6	998.3	886.1	757.2
52.5°	477.6	508.6	554.4	620.8	706.6	807.6	904.4	953.2	894.4	779.1	669.1
55°	425.3	452.5	497.3	558.6	640.1	733.9	816.1	833.0	756.5	642.9	553.7
57.5°	374.3	399.7	440.5	496.9	571.3	654.4	718.7	715.2	634.3	536.9	466.0
60°	339.8	364.5	400.7	455.7	523.6	595.2	650.3	637.2	557.0	473.0	413.4
62.5°	308.9	330.9	365.1	413.3	475.2	541.6	586.8	567.4	488.9	415.4	368.3
65°	263.2	281.8	311.0	352.1	403.5	458.3	493.2	468.1	401.1	343.9	306.0
67.5°	219.8	234.6	259.0	291.9	335.7	379.7	401.0	375.7	322.1	280.4	252.3
70°	192.1	205.3	224.2	253.4	291.7	328.7	344.7	322.1	276.0	240.2	220.1
72.5°	164.5	175.3	191.9	218.2	248.8	281.0	295.0	273.4	235.5	205.3	186.5
75°	127.1	134.5	146.0	164.1	188.4	213.9	221.7	202.8	178.6	155.9	143.5
77.5°	91.0	97.3	106.0	117.4	134.6	150.8	157.6	146.7	127.9	113.6	103.5
80°	69.9	73.2	80.6	90.1	103.7	113.9	118.4	111.5	98.3	87.6	79.8
82.5°	49.8	53.2	57.6	65.4	74.1	81.0	85.9	81.2	71.7	63.3	58.7
85°	24.2	26.3	28.8	32.1	38.7	42.8	42.4	39.5	35.8	32.5	30.0
87.5°	8.9	9.4	10.7	12.5	13.7	15.2	16.1	15.6	14.5	13.6	12.8
90°	1.7	2.9	4.0	5.0	6.0	7.1	8.0	9.0	9.9	10.6	11.2
92.5°	15.8	16.6	17.3	18.1	19.0	20.2	21.4	22.6	23.8	24.7	25.6
95°	40.6	40.8	41.1	41.4	42.2	43.6	44.9	46.3	47.7	48.6	49.6
97.5°	67.0	67.1	67.3	67.3	68.4	70.3	72.2	74.1	76.0	76.8	77.8
100°	86.7	86.7	86.7	86.7	87.6	89.4	91.2	93.0	94.7	96.0	97.3
102.5°	108.6	109.2	109.7	110.3	111.0	111.9	112.8	113.7	114.6	116.0	117.3
105°	142.0	142.6	143.3	144.0	144.7	145.6	146.4	147.2	148.1	148.9	149.7
107.5°	178.6	179.3	180.0	180.7	181.3	182.0	182.6	183.2	183.9	184.3	184.7
110°	203.9	204.5	205.3	206.0	206.5	206.9	207.3	207.7	208.1	208.6	209.0



TEST NUMBER: P333224-927

CATALOG NUMBER: S125DIP-S850D810U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	229.3	229.7	230.0	230.4	230.8	231.3	231.9	232.4	232.9	233.1	233.3
115°	267.5	268.1	268.6	269.2	269.6	269.9	270.1	270.5	270.7	270.5	270.5
117.5°	305.4	305.6	305.9	306.1	306.4	306.7	306.9	307.1	307.4	307.4	307.6
120°	329.6	330.3	331.0	331.7	332.1	332.2	332.4	332.5	332.6	332.6	332.6
122.5°	355.0	355.2	355.5	355.7	356.0	356.3	356.7	357.0	357.4	357.3	357.2
125°	390.5	391.3	392.1	392.9	393.4	393.6	393.7	393.8	394.0	393.7	393.4
127.5°	427.3	427.7	428.2	428.6	429.0	429.1	429.3	429.5	429.7	429.5	429.4
130°	449.8	450.5	451.1	451.9	452.3	452.6	452.9	453.1	453.4	453.3	453.1
132.5°	472.5	473.6	474.8	475.9	476.4	476.4	476.3	476.3	476.3	476.1	475.9
135°	507.6	508.3	509.2	510.0	510.5	510.6	510.8	510.9	511.0	511.0	511.0
137.5°	540.7	541.5	542.3	543.1	543.7	544.0	544.2	544.5	544.9	545.0	545.2
140°	561.9	562.6	563.3	564.0	564.5	564.9	565.4	565.8	566.2	566.5	566.7
142.5°	583.1	583.7	584.2	584.9	585.4	585.9	586.5	586.9	587.5	587.6	587.8
145°	614.4	615.0	615.5	616.1	616.6	617.0	617.3	617.8	618.2	618.2	618.2
147.5°	643.2	643.5	643.8	644.0	644.4	644.8	645.1	645.4	645.7	646.0	646.3
150°	662.0	661.9	661.8	661.6	661.9	662.4	663.0	663.5	664.1	664.1	664.1
152.5°	678.3	678.4	678.7	678.8	679.1	679.2	679.5	679.7	679.9	680.2	680.6
155°	702.4	702.4	702.4	702.4	702.5	702.7	702.8	702.9	703.1	703.6	704.2
157.5°	724.0	723.7	723.3	723.0	722.9	723.1	723.3	723.3	723.5	724.1	724.6
160°	736.7	736.3	735.9	735.5	735.4	735.5	735.6	735.8	735.9	736.5	737.0
162.5°	748.2	747.9	747.7	747.3	747.2	747.2	747.3	747.3	747.3	748.0	748.6
165°	763.5	763.3	763.0	762.7	762.6	762.7	762.9	763.0	763.2	763.7	764.3
167.5°	776.1	775.5	775.0	774.4	774.2	774.2	774.2	774.2	774.2	775.0	775.9
170°	783.1	782.5	782.0	781.4	781.1	781.1	781.1	781.1	781.1	782.0	782.8
172.5°	788.0	787.4	786.9	786.3	786.1	786.1	786.1	786.1	786.1	786.9	787.7
175°	793.6	793.1	792.5	791.9	791.6	791.6	791.6	791.6	791.6	792.5	793.3
177.5°	796.5	796.1	795.7	795.2	795.0	794.9	794.7	794.6	794.5	795.2	795.8
180°	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0



TEST NUMBER: P333224-927

CATALOG NUMBER: S125DIP-S850D810U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	969.2	969.2	969.2	969.2	969.2	969.2	969.2
2.5°	1013.5	1016.2	1021.8	1019.8	1022.5	1023.7	1025.1
5°	1095.4	1108.6	1114.4	1113.5	1122.1	1120.1	1118.0
7.5°	1187.9	1201.7	1209.4	1219.1	1224.6	1225.0	1229.9
10°	1240.2	1258.3	1265.7	1276.0	1282.5	1286.3	1285.9
12.5°	1280.3	1294.5	1311.1	1316.1	1325.0	1329.7	1328.0
15°	1328.6	1351.3	1368.6	1377.2	1388.3	1391.5	1396.1
17.5°	1371.7	1402.1	1422.3	1449.1	1459.2	1465.4	1461.7
20°	1404.3	1444.2	1464.4	1496.5	1514.2	1523.6	1520.4
22.5°	1442.8	1486.1	1523.3	1551.1	1578.0	1590.8	1593.4
25°	1508.8	1568.0	1622.8	1659.4	1692.7	1700.5	1717.8
27.5°	1582.5	1652.4	1710.9	1749.4	1772.6	1781.3	1786.7
30°	1629.0	1698.4	1742.5	1767.1	1774.6	1773.7	1772.9
32.5°	1651.6	1695.2	1703.6	1696.7	1679.7	1665.5	1650.5
35°	1619.5	1587.0	1538.4	1475.9	1429.8	1383.4	1378.8
37.5°	1456.5	1352.6	1271.8	1181.5	1129.5	1097.3	1075.1
40°	1303.1	1185.1	1087.2	1011.1	958.0	937.1	916.5
42.5°	1136.6	1023.8	937.2	873.5	833.6	810.3	794.1
45°	923.4	823.9	756.1	710.0	678.3	660.2	649.9
47.5°	756.7	683.1	625.4	592.2	570.3	556.2	556.3
50°	667.2	596.8	558.6	532.3	513.3	502.2	504.3
52.5°	587.9	535.4	502.6	480.6	466.6	459.8	459.5
55°	491.5	453.7	432.3	416.3	406.8	399.0	400.7
57.5°	420.5	388.6	374.2	360.9	354.3	351.2	346.7
60°	376.4	351.7	339.4	328.7	322.1	319.6	315.1
62.5°	337.2	317.8	305.8	297.1	291.1	290.3	286.8
65°	283.4	268.6	257.9	253.8	247.6	246.0	246.0
67.5°	233.6	223.0	214.8	211.0	208.2	208.7	206.7
70°	202.4	193.8	188.4	184.3	182.2	182.6	181.0
72.5°	177.1	167.4	162.7	160.3	157.6	158.6	158.0
75°	134.1	129.1	126.7	124.2	122.6	121.8	121.0
77.5°	98.5	94.1	92.2	90.9	91.1	89.1	90.6
80°	76.1	72.4	71.1	69.1	68.7	68.7	68.3
82.5°	55.7	53.6	52.8	51.0	50.3	50.9	49.8
85°	28.8	27.2	26.8	26.8	25.9	25.1	27.2
87.5°	12.9	11.7	11.9	11.6	11.7	11.4	10.9
90°	12.0	12.7	13.2	13.6	14.0	14.4	14.9
92.5°	26.5	27.4	28.0	28.4	28.6	28.9	29.2
95°	50.6	51.6	52.2	52.4	52.8	53.0	53.2
97.5°	78.7	79.6	80.1	80.2	80.4	80.6	80.8
100°	98.5	99.7	100.5	100.8	101.0	101.3	101.6
102.5°	118.7	120.0	120.9	121.3	121.6	122.0	122.4
105°	150.5	151.4	151.9	152.4	152.8	153.2	153.6
107.5°	185.1	185.5	185.7	185.7	185.6	185.6	185.6
110°	209.4	209.8	209.9	209.8	209.6	209.5	209.4



TEST NUMBER: P333224-927

CATALOG NUMBER: S125DIP-S850D810U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	233.5	233.7	233.7	233.4	233.1	232.9	232.7
115°	270.3	270.1	270.0	269.9	269.7	269.6	269.5
117.5°	307.7	307.8	307.6	307.0	306.5	305.9	305.4
120°	332.6	332.6	332.4	331.8	331.3	330.7	330.2
122.5°	357.1	357.0	356.7	356.2	355.8	355.4	355.0
125°	393.2	392.8	392.7	392.5	392.4	392.3	392.1
127.5°	429.2	429.1	428.9	428.6	428.3	428.1	427.8
130°	453.0	452.9	452.7	452.4	452.1	451.9	451.5
132.5°	475.8	475.7	475.4	475.1	474.7	474.3	473.9
135°	511.0	511.0	510.8	510.2	509.7	509.1	508.6
137.5°	545.3	545.5	545.3	544.5	543.9	543.2	542.5
140°	567.0	567.3	567.0	566.4	565.7	565.0	564.4
142.5°	588.0	588.1	587.9	587.2	586.5	585.8	585.1
145°	618.2	618.2	618.0	617.6	617.2	616.8	616.3
147.5°	646.7	647.1	646.7	645.8	644.8	644.0	643.0
150°	664.1	664.1	663.9	663.6	663.4	663.1	662.8
152.5°	680.9	681.2	681.1	680.6	680.2	679.7	679.1
155°	704.7	705.3	705.2	704.5	703.9	703.1	702.4
157.5°	725.2	725.7	725.6	724.6	723.7	722.8	721.9
160°	737.5	738.1	738.1	737.4	736.7	735.9	735.3
162.5°	749.3	750.0	749.9	749.1	748.3	747.5	746.7
165°	764.9	765.3	765.2	764.4	763.6	762.7	761.9
167.5°	776.7	777.5	777.4	776.7	775.8	774.9	774.0
170°	783.6	784.4	784.3	783.4	782.4	781.5	780.5
172.5°	788.5	789.4	789.4	788.5	787.7	786.8	785.9
175°	794.2	795.0	794.9	793.9	793.0	792.0	791.1
177.5°	796.5	797.2	797.1	796.3	795.6	794.8	794.0
180°	796.0	796.0	796.0	796.0	796.0	796.0	796.0

(END OF REPORT)