

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333231-927

Luminaire Tested: **S125DIP-S850D810U927-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333231-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S850D810U927-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5011.7 lumens
Efficiency: N/A
Efficacy: 109.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333231-927

CATALOG NUMBER: S125DIP-S850D810U927-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333231-927

CATALOG NUMBER: S125DIP-S850D810U927-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	94	90	87	91	88	84	81	75	72	70	63	62	60	53	52	50	45
2	90	82	76	71	83	76	71	66	66	62	58	56	53	50	46	44	42	38
3	82	72	65	59	76	67	61	55	58	53	49	49	45	42	41	38	36	32
4	75	64	56	50	69	60	53	47	51	46	42	44	40	36	37	34	31	28
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	30	27	24
6	63	51	43	37	59	48	40	35	41	36	31	36	31	28	30	27	24	21
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	27	24	21	19
8	54	42	34	29	50	39	32	27	34	29	25	30	25	22	25	22	19	17
9	51	38	31	26	47	36	29	24	31	26	22	27	23	20	23	20	17	15
10	47	35	28	23	44	33	26	22	29	24	20	25	21	18	22	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6716	6716	6716
5°	6731	6667	6710
10°	6690	6620	6658
15°	6618	6540	6568
20°	6514	6429	6441
25°	6402	6297	6291
30°	6264	6154	6123
35°	6117	6000	5916
40°	5966	5833	5751
45°	5802	5681	5569
50°	5621	5497	5332
55°	5447	5290	5141
60°	5239	5079	4899
65°	4991	4828	4664
70°	4755	4538	4381
75°	4332	4190	4045
80°	3857	3794	3704
85°	3349	3416	3231



TEST NUMBER: P333231-927

CATALOG NUMBER: S125DIP-S850D810U927-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.1	2.0
10°-20°	277.0	5.5
20°-30°	409.0	8.2
30°-40°	477.2	9.5
40°-50°	479.3	9.6
50°-60°	420.7	8.4
60°-70°	313.5	6.3
70°-80°	179.3	3.6
80°-90°	53.9	1.1
90°-100°	222.7	4.4
100°-110°	478.7	9.6
110°-120°	449.3	9.0
120°-130°	364.1	7.3
130°-140°	292.2	5.8
140°-150°	220.5	4.4
150°-160°	155.2	3.1
160°-170°	91.5	1.8
170°-180°	29.8	0.6
0°-30°	784.0	15.6
0°-40°	1261.2	25.2
0°-60°	2161.2	43.1
0°-90°	2707.8	54.0
90°-120°	1150.7	23.0
90°-150°	2027.5	40.5
90°-180°	2304.0	46.0
0°-180°	5011.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1040	1040	1040	1040	1040	
5°	1038	1036	1028	1035	1035	98
15°	990	987	978	982	982	279
25°	898	894	884	885	883	413
35°	776	772	761	757	750	485
45°	635	631	622	612	610	489
55°	484	481	470	462	457	432
65°	327	325	316	309	305	324
75°	174	172	168	165	162	185
85°	45	46	46	45	44	51
90°	1	6	10	13	14	4
95°	20	60	549	249	146	22
105°	70	98	449	884	821	74
115°	125	151	360	777	914	123
125°	173	203	346	618	720	154
135°	203	244	343	518	598	158
145°	237	271	344	429	472	148
155°	270	290	336	379	396	124
165°	295	303	322	342	347	83
175°	307	307	309	313	312	29
180°	307	307	307	307	307	



TEST NUMBER: P333231-927

CATALOG NUMBER: S125DIP-S850D810U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9
2.5°	1042.6	1042.1	1041.7	1041.2	1040.8	1039.8	1038.4	1037.0	1035.5	1034.0	1035.5
5°	1038.3	1037.9	1037.5	1037.2	1036.8	1035.7	1033.9	1032.1	1030.2	1028.4	1030.1
7.5°	1028.7	1028.4	1028.0	1027.6	1027.3	1026.1	1024.1	1022.1	1020.1	1018.0	1019.6
10°	1020.2	1019.9	1019.5	1019.1	1018.7	1017.6	1015.5	1013.5	1011.5	1009.5	1011.0
12.5°	1009.6	1009.0	1008.4	1007.7	1007.0	1005.8	1003.9	1002.0	1000.1	998.3	999.5
15°	989.8	989.2	988.6	988.1	987.5	986.3	984.3	982.2	980.2	978.2	979.1
17.5°	966.9	966.1	965.3	964.5	963.7	962.2	960.1	958.1	955.9	953.9	955.0
20°	947.8	947.5	947.1	946.7	946.3	944.9	942.5	940.2	937.8	935.4	936.8
22.5°	928.7	928.0	927.4	926.7	926.1	924.6	922.4	920.1	917.9	915.7	916.6
25°	898.4	897.5	896.6	895.6	894.8	893.1	890.7	888.4	886.0	883.6	884.0
27.5°	863.0	862.5	862.0	861.4	860.9	859.4	856.9	854.4	852.0	849.5	849.6
30°	840.0	839.5	838.9	838.4	837.8	836.1	833.5	830.7	827.9	825.2	824.8
32.5°	815.0	814.1	813.3	812.5	811.7	810.0	807.6	805.1	802.6	800.2	799.5
35°	775.9	775.1	774.4	773.6	772.9	771.3	768.7	766.1	763.6	761.0	760.1
37.5°	735.2	734.3	733.3	732.5	731.5	729.8	727.5	725.0	722.6	720.3	718.8
40°	707.6	706.6	705.8	704.8	703.9	702.2	699.6	697.0	694.5	691.9	690.3
42.5°	677.9	677.2	676.4	675.7	674.9	673.2	670.7	668.0	665.5	663.0	661.5
45°	635.2	634.4	633.7	633.0	632.2	630.7	628.6	626.4	624.2	622.0	619.8
47.5°	589.1	589.1	589.1	589.1	589.2	588.0	585.3	582.7	580.0	577.4	575.1
50°	559.4	558.9	558.3	557.8	557.3	555.9	553.7	551.5	549.3	547.1	544.7
52.5°	529.2	528.8	528.4	528.0	527.6	526.2	523.9	521.5	519.2	516.8	514.8
55°	483.8	483.2	482.7	482.1	481.6	480.0	477.4	474.9	472.3	469.8	468.1
57.5°	435.9	435.6	435.3	435.0	434.7	433.5	431.3	429.2	427.0	424.8	422.7
60°	405.6	404.9	404.2	403.4	402.7	401.3	399.3	397.3	395.3	393.2	391.4
62.5°	374.0	373.4	372.9	372.2	371.7	370.5	368.8	367.1	365.4	363.6	361.7
65°	326.6	326.2	325.9	325.5	325.2	324.0	321.9	320.0	317.9	315.9	314.3
67.5°	280.7	280.0	279.2	278.4	277.7	276.5	275.0	273.5	272.0	270.5	269.1
70°	251.8	250.8	249.9	249.0	248.1	246.8	245.2	243.5	241.9	240.3	239.2
72.5°	220.1	219.5	218.9	218.3	217.7	216.8	215.8	214.7	213.7	212.6	211.4
75°	173.6	173.3	172.9	172.5	172.1	171.5	170.6	169.7	168.7	167.9	167.3
77.5°	130.6	130.5	130.4	130.2	130.1	129.8	129.2	128.7	128.2	127.7	127.4
80°	103.7	103.7	103.7	103.7	103.7	103.5	103.1	102.7	102.3	102.0	101.9
82.5°	79.9	79.7	79.4	79.1	78.8	78.6	78.5	78.5	78.4	78.3	78.0
85°	45.2	45.5	45.6	45.8	45.9	46.1	46.1	46.1	46.1	46.1	45.9
87.5°	17.9	18.0	18.3	18.5	18.8	18.9	18.9	19.0	19.0	19.1	19.3
90°	0.6	1.3	2.5	3.7	5.0	6.2	6.8	8.1	8.6	9.9	10.5
92.5°	7.5	9.2	14.3	22.0	32.7	50.8	84.6	141.3	202.9	199.7	161.7
95°	20.4	21.1	26.0	32.8	46.4	74.3	140.6	276.9	447.8	548.8	537.0
97.5°	33.9	34.7	38.2	45.0	57.2	77.3	121.1	221.0	399.9	586.1	679.5
100°	43.3	44.6	47.1	53.9	65.7	84.2	120.2	200.7	356.8	559.4	714.2
102.5°	53.8	54.5	56.5	63.8	74.5	92.7	124.6	192.3	324.1	512.2	693.4
105°	70.0	70.0	73.1	79.3	89.2	106.5	133.8	188.9	292.4	449.1	626.9
107.5°	85.9	87.1	90.1	95.1	105.4	121.0	147.4	194.6	279.0	405.6	559.0
110°	97.3	98.5	100.9	106.5	115.8	131.9	157.3	200.1	275.0	385.2	520.3



TEST NUMBER: P333231-927

CATALOG NUMBER: S125DIP-S850D810U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	108.6	109.9	111.9	117.4	126.7	142.4	166.8	207.0	275.0	373.4	491.5
115°	125.1	126.4	128.3	133.8	143.1	158.6	181.5	217.4	276.9	360.5	460.2
117.5°	140.0	141.9	143.9	149.4	159.9	174.9	196.6	229.3	281.0	354.2	441.5
120°	149.9	151.8	154.2	159.8	170.3	185.8	207.5	237.3	284.9	351.2	431.1
122.5°	160.3	161.7	163.7	169.2	180.8	196.2	217.9	246.1	288.4	348.7	422.2
125°	173.4	174.7	177.8	183.3	195.1	211.2	231.6	258.3	294.2	345.6	410.0
127.5°	183.7	185.6	189.6	196.6	209.1	225.2	244.9	269.4	300.8	344.1	398.9
130°	190.1	192.0	196.9	205.0	218.0	234.2	253.3	276.9	304.8	343.2	391.5
132.5°	195.1	197.5	203.4	212.5	225.9	242.1	261.3	283.3	309.2	343.2	385.6
135°	203.2	205.7	213.1	223.0	236.0	252.7	272.0	292.4	315.3	343.2	378.4
137.5°	213.3	215.2	222.1	232.0	244.8	262.0	279.5	299.0	320.8	343.9	372.2
140°	219.3	221.1	228.5	238.4	250.3	267.0	284.9	303.5	323.3	344.4	369.2
142.5°	226.2	227.6	234.5	244.4	255.7	271.4	288.4	306.0	324.8	344.9	366.7
145°	236.6	237.8	244.1	252.7	263.9	278.1	294.2	309.7	326.5	344.4	363.0
147.5°	247.5	248.3	253.6	261.7	271.3	283.8	297.9	312.0	327.0	342.8	359.1
150°	254.0	255.2	259.5	267.6	276.2	286.8	300.4	313.4	327.0	341.3	356.2
152.5°	260.9	261.7	265.5	272.5	280.7	290.3	302.9	314.4	326.5	339.3	352.7
155°	270.1	270.1	273.8	280.0	286.1	294.9	305.4	315.3	325.2	335.7	346.9
157.5°	278.2	278.1	281.1	286.4	291.8	298.4	307.4	315.9	323.6	332.0	341.4
160°	283.7	283.0	285.6	289.9	294.9	300.4	308.5	315.9	322.1	329.5	337.0
162.5°	288.1	287.6	290.0	293.8	297.8	302.4	309.4	315.4	320.6	326.5	333.0
165°	294.9	293.6	295.5	298.6	301.0	304.8	309.7	314.7	318.4	322.1	327.0
167.5°	299.3	298.7	299.8	301.5	303.2	305.6	309.7	313.1	314.9	317.7	321.2
170°	302.3	301.7	302.3	303.5	304.8	306.6	309.7	312.2	313.4	315.3	317.7
172.5°	304.3	303.2	303.7	305.0	305.7	306.6	309.2	311.2	311.4	312.3	314.3
175°	306.6	305.4	306.0	306.6	306.6	306.6	308.5	309.7	309.1	309.1	309.7
177.5°	307.7	306.7	306.7	307.2	306.7	306.7	307.7	308.2	307.2	307.2	307.7
180°	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2



TEST NUMBER: P333231-927

CATALOG NUMBER: S125DIP-S850D810U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9
2.5°	1037.0	1038.4	1039.8	1040.5	1040.4	1040.2	1040.1	1039.9
5°	1031.7	1033.3	1035.0	1035.7	1035.5	1035.4	1035.1	1035.0
7.5°	1021.3	1022.9	1024.5	1025.2	1025.0	1024.8	1024.6	1024.5
10°	1012.4	1013.9	1015.3	1016.0	1015.8	1015.6	1015.4	1015.3
12.5°	1000.6	1001.8	1003.0	1003.5	1003.5	1003.5	1003.5	1003.4
15°	980.1	981.0	981.9	982.3	982.3	982.3	982.3	982.3
17.5°	956.2	957.3	958.4	958.5	957.6	956.7	955.8	954.9
20°	938.0	939.3	940.6	940.7	939.8	938.9	938.0	937.1
22.5°	917.3	918.2	919.1	919.2	918.5	917.9	917.3	916.7
25°	884.3	884.7	885.1	884.9	884.5	883.9	883.4	882.8
27.5°	849.7	849.8	849.9	849.6	849.1	848.5	848.0	847.4
30°	824.5	824.1	823.7	823.3	822.8	822.2	821.7	821.1
32.5°	798.8	798.2	797.6	796.7	795.7	794.7	793.8	792.8
35°	759.2	758.3	757.4	756.2	754.7	753.3	751.8	750.4
37.5°	717.5	716.1	714.8	713.7	712.9	712.0	711.2	710.3
40°	688.6	687.0	685.3	684.2	683.7	683.2	682.6	682.1
42.5°	660.0	658.5	657.0	655.8	655.0	654.1	653.2	652.4
45°	617.6	615.4	613.2	611.8	611.3	610.8	610.2	609.7
47.5°	572.9	570.7	568.5	566.7	565.5	564.2	562.8	561.6
50°	542.3	540.0	537.6	535.8	534.5	533.2	532.0	530.7
52.5°	512.7	510.6	508.5	506.8	505.3	503.9	502.5	501.1
55°	466.5	464.9	463.2	461.8	460.4	459.1	457.9	456.6
57.5°	420.6	418.5	416.4	414.9	414.2	413.6	412.9	412.2
60°	389.6	387.8	386.0	384.4	383.1	381.8	380.6	379.3
62.5°	359.7	357.7	355.8	354.3	353.3	352.3	351.3	350.3
65°	312.7	311.0	309.3	308.2	307.4	306.7	305.9	305.2
67.5°	267.8	266.3	265.0	264.0	263.6	263.2	262.7	262.3
70°	238.1	236.9	235.8	235.0	234.2	233.5	232.7	232.0
72.5°	210.1	208.9	207.6	206.6	205.9	205.2	204.5	203.7
75°	166.8	166.2	165.6	165.0	164.3	163.5	162.8	162.1
77.5°	127.1	126.7	126.4	126.0	125.4	124.9	124.5	123.9
80°	101.6	101.5	101.3	101.0	100.7	100.3	99.9	99.6
82.5°	77.6	77.3	77.0	76.8	76.8	76.7	76.6	76.5
85°	45.7	45.6	45.3	45.1	44.7	44.4	44.0	43.6
87.5°	19.3	19.5	19.6	19.7	19.4	19.1	18.9	18.6
90°	11.2	11.8	12.4	13.6	13.6	13.6	14.3	14.3
92.5°	109.8	79.7	60.0	50.8	42.9	41.4	40.5	39.5
95°	445.4	351.2	275.0	223.0	179.0	160.4	155.5	145.5
97.5°	663.3	597.2	523.0	450.7	412.4	377.7	359.7	351.8
100°	761.8	731.5	667.7	603.3	560.5	515.9	493.1	483.2
102.5°	795.0	813.8	783.2	739.6	693.9	662.1	637.2	629.8
105°	775.5	860.4	887.6	880.8	860.9	840.5	828.1	820.7
107.5°	705.6	818.9	888.8	921.1	931.2	931.1	927.0	922.0
110°	654.1	771.7	859.1	911.7	939.6	951.4	955.8	955.8



TEST NUMBER: P333231-927

CATALOG NUMBER: S125DIP-S850D810U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	613.5	725.2	813.5	875.6	916.3	936.5	947.3	951.8
115°	562.4	658.5	743.3	810.8	859.1	888.8	906.2	914.3
117.5°	529.5	612.2	685.3	747.3	795.6	826.2	843.5	848.4
120°	511.6	586.0	654.1	708.6	754.4	784.2	800.9	805.8
122.5°	498.3	567.1	627.8	678.9	719.8	747.0	763.7	768.2
125°	478.8	542.0	595.9	640.5	675.2	700.5	714.2	720.3
127.5°	459.0	517.9	568.2	610.0	641.4	663.8	676.8	679.5
130°	446.6	501.1	549.4	589.7	620.7	641.1	653.5	657.2
132.5°	434.2	485.2	529.1	567.8	598.8	619.2	630.7	634.9
135°	418.1	460.8	500.5	535.8	563.0	583.4	594.6	598.3
137.5°	404.5	439.0	472.0	501.9	526.4	544.9	555.2	559.4
140°	397.0	426.1	454.6	480.6	503.6	519.7	528.9	532.0
142.5°	390.6	415.3	439.7	462.3	481.8	495.4	504.2	506.8
145°	382.1	401.4	420.6	437.3	452.2	462.7	469.5	472.0
147.5°	374.2	389.8	404.6	417.2	429.0	437.4	441.4	442.5
150°	369.8	383.4	395.1	406.3	415.7	423.0	425.6	426.1
152.5°	364.8	377.0	387.8	396.4	404.3	410.2	412.6	413.3
155°	357.4	367.3	376.0	382.8	389.0	393.3	395.1	395.8
157.5°	350.0	358.1	364.8	370.2	375.0	378.6	380.3	380.2
160°	345.0	351.2	357.4	361.7	366.1	369.2	370.4	369.8
162.5°	339.5	345.2	350.5	354.3	357.7	360.2	360.5	360.4
165°	332.0	336.4	340.1	343.2	345.6	346.9	346.9	346.9
167.5°	324.8	327.6	330.5	332.7	334.0	335.1	334.6	334.5
170°	320.8	322.7	324.6	325.8	327.0	327.6	327.6	327.0
172.5°	316.4	318.2	319.6	320.4	320.6	321.7	320.8	320.1
175°	311.6	311.6	312.8	312.8	312.8	313.4	312.2	311.6
177.5°	308.2	308.7	308.7	308.7	308.2	308.7	307.2	307.2
180°	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2

(END OF REPORT)