

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333618-927

Luminaire Tested: **S125RDIP-S1270D590U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333618-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1270D590U927-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5579.4 lumens
Efficiency: N/A
Efficacy: 101.3 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333618-927

CATALOG NUMBER: S125RDIP-S1270D590U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333618-927

CATALOG NUMBER: S125RDIP-S1270D590U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	70
1	103	99	95	91	97	93	90	87	84	81	79	75	73	71	67	65	64	60
2	94	87	81	76	89	82	77	72	74	70	66	66	63	60	59	57	55	51
3	86	77	70	64	81	73	66	61	66	61	56	59	55	52	53	50	47	44
4	79	68	60	54	75	65	58	52	59	53	49	53	48	45	48	44	41	38
5	73	61	53	47	69	58	51	45	53	47	42	48	43	39	43	39	36	33
6	67	55	47	41	64	53	45	40	48	42	37	43	38	34	39	35	32	29
7	62	50	42	36	59	48	40	35	44	37	33	40	35	31	36	32	28	26
8	58	46	38	32	55	44	36	31	40	34	29	36	31	27	33	29	26	23
9	54	42	34	29	51	40	33	28	37	31	26	34	28	25	31	26	23	21
10	51	38	31	26	48	37	30	25	34	28	24	31	26	23	28	24	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9715	9715	9715	9715
5°	11177	9728	8591	9728
10°	12821	9678	7581	9678
15°	13848	9579	6738	9579
20°	15270	9465	6222	9465
25°	17672	9311	5773	9311
30°	19231	9150	5480	9150
35°	16222	8964	5210	8964
40°	11328	8627	4977	8627
45°	8404	8173	4748	8173
50°	6701	7700	4554	7700
55°	5687	7113	4380	7113
60°	4914	6589	4100	6589
65°	4378	6021	3529	6021
70°	3846	5516	3218	5516
75°	3329	4776	3019	4776
80°	2525	4020	2525	4020
85°	2104	3157	2379	3157



TEST NUMBER: P333618-927

CATALOG NUMBER: S125RDIP-S1270D590U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.3	2.6
10°-20°	422.7	7.6
20°-30°	670.3	12.0
30°-40°	808.3	14.5
40°-50°	721.8	12.9
50°-60°	553.6	9.9
60°-70°	359.7	6.4
70°-80°	174.9	3.1
80°-90°	43.0	0.8
90°-100°	162.5	2.9
100°-110°	349.2	6.3
110°-120°	327.8	5.9
120°-130°	265.6	4.8
130°-140°	213.2	3.8
140°-150°	160.9	2.9
150°-160°	113.2	2.0
160°-170°	66.7	1.2
170°-180°	21.7	0.4
0°-30°	1237.3	22.2
0°-40°	2045.6	36.7
0°-60°	3320.9	59.5
0°-90°	3898.6	69.9
90°-120°	839.5	15.0
90°-150°	1479.1	26.5
90°-180°	1681.0	30.1
0°-180°	5579.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1504	1504	1504	1504	1504	
5°	1724	1501	1325	1501	1724	172
15°	2071	1433	1008	1433	2071	593
25°	2480	1307	810	1307	2480	1139
35°	2058	1137	661	1137	2058	1243
45°	920	895	520	895	920	734
55°	505	632	389	632	505	458
65°	286	394	231	394	286	285
75°	133	191	121	191	133	142
85°	28	43	32	43	28	33
90°	10	0	10	0	10	9
95°	106	15	106	15	106	150
105°	599	51	599	51	599	595
115°	667	91	667	91	667	652
125°	526	126	526	126	526	475
135°	436	148	436	148	436	338
145°	344	173	344	173	344	219
155°	289	197	289	197	289	135
165°	253	215	253	215	253	72
175°	227	224	227	224	227	22
180°	224	224	224	224	224	



TEST NUMBER: P333618-927

CATALOG NUMBER: S125RDIP-S1270D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3
2.5°	1582.3	1581.4	1583.3	1577.9	1578.3	1569.9	1569.9	1563.5	1555.1	1548.7	1545.8
5°	1724.1	1725.4	1722.8	1713.6	1707.5	1698.2	1687.7	1669.1	1653.7	1638.9	1627.1
7.5°	1870.1	1871.0	1862.8	1860.0	1844.4	1833.0	1809.7	1784.5	1762.1	1733.8	1712.0
10°	1955.0	1954.5	1945.8	1939.0	1925.4	1908.1	1885.3	1855.6	1827.9	1797.0	1767.4
12.5°	2004.5	2002.9	2000.1	1991.9	1979.3	1964.0	1944.6	1915.4	1881.2	1847.4	1812.8
15°	2071.2	2066.8	2058.8	2048.3	2030.4	2012.5	1990.8	1964.9	1932.2	1893.9	1861.8
17.5°	2153.6	2153.8	2141.4	2126.9	2102.5	2070.9	2037.6	1995.7	1951.2	1909.1	1874.9
20°	2221.8	2219.9	2207.7	2179.2	2151.4	2111.9	2073.6	2022.4	1968.0	1913.0	1870.4
22.5°	2319.7	2314.8	2302.0	2264.7	2221.6	2170.7	2112.1	2049.5	1983.9	1921.4	1865.5
25°	2479.9	2476.2	2450.9	2407.7	2347.2	2268.7	2192.2	2106.3	2011.9	1929.8	1861.8
27.5°	2589.6	2585.5	2566.7	2530.9	2475.0	2392.5	2288.9	2174.1	2056.2	1943.2	1845.2
30°	2578.7	2588.0	2585.5	2568.9	2526.9	2452.8	2357.1	2228.0	2087.8	1955.0	1838.3
32.5°	2423.6	2431.9	2453.6	2486.3	2488.8	2459.2	2387.7	2268.5	2123.4	1972.4	1832.9
35°	2057.5	2068.7	2110.7	2176.8	2263.2	2335.4	2350.2	2286.1	2155.8	1993.4	1824.8
37.5°	1581.8	1642.6	1677.9	1747.5	1878.1	2011.0	2138.8	2185.9	2130.4	1984.7	1811.6
40°	1343.7	1358.5	1421.5	1499.9	1609.9	1748.2	1930.4	2061.9	2066.2	1964.9	1790.8
42.5°	1150.1	1168.9	1212.0	1274.7	1368.8	1507.1	1695.2	1868.8	1949.2	1910.6	1763.6
45°	920.1	934.3	965.8	1014.0	1086.2	1200.5	1362.2	1562.9	1722.3	1784.6	1690.8
47.5°	755.8	763.5	790.9	827.6	881.1	964.3	1089.6	1263.8	1454.8	1588.9	1575.7
50°	666.9	675.6	696.6	724.4	769.4	839.8	939.8	1085.0	1282.0	1445.6	1478.4
52.5°	597.8	604.9	618.0	644.3	681.5	735.6	816.3	947.6	1124.9	1298.9	1374.6
55°	505.1	510.1	520.5	535.4	565.1	604.0	673.7	764.5	907.8	1083.2	1194.3
57.5°	428.8	431.3	437.9	451.6	472.1	500.6	551.0	627.9	730.6	888.6	1011.2
60°	380.4	382.9	391.5	400.8	416.8	442.8	482.3	536.0	634.8	765.1	889.2
62.5°	341.8	343.3	347.1	356.3	370.4	390.4	421.5	465.3	543.9	658.4	775.6
65°	286.5	287.2	288.4	295.8	304.4	319.2	339.6	370.5	429.8	516.3	620.0
67.5°	233.5	234.2	238.6	241.2	250.3	258.0	270.0	293.6	335.3	393.6	474.3
70°	203.7	203.2	207.5	210.6	213.7	222.9	230.9	250.1	276.0	320.5	387.8
72.5°	176.1	174.5	176.3	177.4	181.6	187.8	195.9	207.6	227.6	258.3	309.7
75°	133.4	134.0	134.0	135.2	138.3	140.8	143.2	149.4	160.6	180.9	208.7
77.5°	93.6	92.6	95.2	95.6	97.4	100.1	102.3	104.7	109.3	117.7	132.1
80°	67.9	67.9	68.5	70.4	69.8	71.0	74.1	76.6	82.1	87.1	92.0
82.5°	52.1	51.7	52.2	52.6	52.5	53.7	54.8	55.3	57.4	59.9	63.4
85°	28.4	28.4	29.0	29.0	29.6	29.6	30.3	30.3	30.3	30.9	31.5
87.5°	12.9	12.4	11.9	11.9	12.4	13.2	12.6	12.0	11.9	11.8	12.1
90°	10.4	10.4	9.9	9.9	9.9	9.0	8.6	8.2	7.7	7.2	6.3
92.5°	28.8	29.5	30.2	31.3	37.1	43.7	58.1	80.1	118.0	145.7	148.1
95°	106.2	113.4	117.0	130.6	162.7	200.7	256.2	324.9	391.8	400.4	326.7
97.5°	256.7	262.4	275.5	300.9	328.8	381.6	435.7	483.9	495.7	427.5	291.8
100°	352.4	359.7	376.4	408.9	440.1	487.1	533.7	555.8	521.0	408.1	260.3
102.5°	459.5	464.9	483.1	506.2	539.6	571.3	593.7	580.0	505.8	373.7	236.4
105°	598.7	604.2	613.2	628.1	642.5	647.5	627.6	565.8	457.3	327.6	213.3
107.5°	672.6	676.3	679.3	679.4	672.0	648.5	597.4	514.8	407.8	295.9	203.5
110°	697.3	697.3	694.1	685.5	665.2	626.8	563.1	477.2	379.6	281.1	200.7



TEST NUMBER: P333618-927

CATALOG NUMBER: S125RDIP-S1270D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	694.3	691.1	683.3	668.5	638.8	593.5	529.1	447.6	358.6	272.4	200.7
115°	667.0	661.1	648.5	626.8	591.5	542.2	480.4	410.3	335.7	263.0	202.0
117.5°	619.0	615.4	602.9	580.4	545.2	499.9	446.6	386.3	322.1	258.4	204.9
120°	587.9	584.3	572.1	550.4	517.0	477.2	427.5	373.3	314.5	256.2	207.9
122.5°	560.4	557.1	544.9	525.1	495.3	458.0	413.8	363.5	308.0	254.4	210.4
125°	525.5	521.0	511.1	492.6	467.2	434.7	395.4	349.3	299.1	252.2	214.7
127.5°	495.7	493.7	484.3	467.9	445.0	414.5	377.9	334.9	291.0	251.0	219.4
130°	479.4	476.7	467.7	452.8	430.2	400.8	365.6	325.8	285.6	250.3	222.4
132.5°	463.2	460.1	451.8	436.9	414.3	386.0	354.0	316.8	281.2	250.3	225.6
135°	436.5	433.8	425.6	410.7	390.9	365.1	336.2	305.0	276.1	250.3	230.0
137.5°	408.1	405.0	397.6	384.0	366.2	344.4	320.3	295.1	271.5	250.9	234.1
140°	388.2	385.9	379.1	367.4	350.7	331.7	310.9	289.6	269.3	251.3	235.9
142.5°	369.7	367.8	361.4	351.5	337.3	320.8	302.9	284.9	267.5	251.6	236.9
145°	344.4	342.5	337.5	329.9	319.0	306.8	292.8	278.8	264.8	251.3	238.1
147.5°	322.8	322.0	319.1	313.0	304.4	295.2	284.4	273.1	262.0	250.1	238.6
150°	310.9	310.5	308.6	303.2	296.4	288.3	279.7	269.7	259.8	249.0	238.6
152.5°	301.5	301.0	299.2	294.9	289.2	282.9	275.0	266.2	257.3	247.6	238.2
155°	288.8	288.3	286.9	283.8	279.2	274.3	268.0	260.7	253.0	244.9	237.3
157.5°	277.3	277.4	276.2	273.5	270.1	266.2	261.3	255.3	249.1	242.2	236.1
160°	269.7	270.2	269.3	267.0	263.9	260.7	256.2	251.7	245.8	240.4	235.0
162.5°	262.9	263.0	262.8	260.9	258.5	255.6	251.9	247.7	243.0	238.2	233.9
165°	253.0	253.0	253.0	252.2	250.3	248.1	245.3	242.2	238.6	235.0	232.3
167.5°	244.0	244.1	244.5	243.7	242.7	241.1	239.1	236.9	234.3	231.8	229.7
170°	238.6	239.1	239.1	238.6	237.7	236.8	235.4	234.1	231.8	230.0	228.6
172.5°	233.5	234.0	234.7	233.9	233.7	233.1	232.2	230.8	229.3	227.8	227.2
175°	227.3	227.8	228.6	228.2	228.2	228.2	227.3	227.3	225.9	225.5	225.5
177.5°	224.1	224.1	225.2	224.8	225.2	225.2	225.2	224.8	224.5	224.1	224.1
180°	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1



TEST NUMBER: P333618-927

CATALOG NUMBER: S125RDIP-S1270D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3
2.5°	1545.8	1542.3	1535.9	1529.9	1522.6	1516.2	1511.6	1506.3	1499.4	1491.0	1484.0
5°	1614.2	1600.6	1582.7	1567.3	1547.5	1532.1	1516.0	1500.6	1485.1	1465.4	1448.1
7.5°	1690.0	1662.0	1634.7	1600.4	1569.2	1541.4	1514.7	1487.7	1461.3	1433.2	1406.2
10°	1736.5	1702.5	1664.9	1621.6	1582.1	1544.4	1509.8	1475.8	1440.0	1408.6	1374.6
12.5°	1780.0	1736.1	1693.0	1638.4	1590.9	1544.9	1500.9	1458.6	1420.3	1379.4	1343.0
15°	1819.2	1776.0	1727.8	1661.1	1595.1	1539.4	1487.6	1432.7	1385.1	1339.4	1298.6
17.5°	1834.4	1789.1	1733.1	1669.0	1596.8	1526.9	1460.1	1399.8	1343.9	1290.6	1244.8
20°	1828.4	1784.6	1727.2	1666.0	1588.9	1516.0	1443.8	1377.1	1314.7	1258.5	1209.7
22.5°	1814.2	1768.8	1713.3	1648.8	1575.5	1498.3	1421.0	1349.9	1284.5	1226.4	1173.1
25°	1792.6	1730.9	1674.1	1611.1	1541.3	1464.7	1385.1	1306.6	1236.9	1177.6	1119.6
27.5°	1770.3	1693.2	1621.0	1558.4	1484.6	1416.3	1339.5	1259.1	1185.7	1125.4	1065.8
30°	1750.0	1663.6	1583.9	1512.9	1443.1	1378.3	1305.4	1227.0	1151.7	1089.3	1028.8
32.5°	1724.8	1632.9	1545.4	1463.5	1396.2	1331.9	1265.9	1191.0	1117.6	1053.2	991.7
35°	1693.2	1575.9	1480.8	1393.8	1319.0	1256.6	1197.4	1136.9	1063.3	996.6	936.8
37.5°	1651.7	1518.6	1408.6	1313.7	1234.9	1172.3	1125.5	1070.2	1003.1	939.2	883.7
40°	1626.5	1477.1	1356.7	1262.8	1180.0	1114.0	1070.2	1023.3	962.1	902.2	846.6
42.5°	1592.9	1439.1	1304.3	1206.5	1123.2	1059.6	1015.3	974.3	923.1	866.6	807.1
45°	1527.1	1365.3	1223.9	1119.0	1035.0	972.6	931.2	894.8	855.9	804.0	752.1
47.5°	1441.4	1288.4	1140.4	1025.8	943.6	885.7	845.5	816.7	788.9	744.8	694.4
50°	1372.8	1225.2	1080.6	969.5	881.8	826.9	789.2	766.4	741.0	700.8	658.9
52.5°	1291.7	1159.9	1018.4	904.8	822.0	770.6	734.4	711.5	690.6	657.9	617.9
55°	1164.0	1048.5	918.9	815.7	739.8	687.9	653.3	631.7	619.4	591.6	560.1
57.5°	1016.7	933.9	819.6	720.2	653.0	601.7	576.4	558.0	544.1	524.4	502.2
60°	913.9	855.9	753.4	658.9	597.1	548.3	525.5	510.1	497.1	480.5	463.1
62.5°	809.7	767.5	678.3	597.1	540.3	499.5	478.1	464.1	449.2	437.9	421.1
65°	670.0	632.3	570.6	507.0	454.5	421.8	406.3	394.0	384.7	372.3	360.6
67.5°	521.2	505.9	463.3	419.4	381.8	352.6	339.3	330.7	319.5	312.1	304.0
70°	429.8	422.4	392.1	363.1	327.9	308.2	295.8	292.1	278.5	271.1	265.5
72.5°	348.8	345.3	327.9	307.8	283.0	265.6	254.3	250.1	241.5	235.5	232.0
75°	239.0	240.2	237.1	224.2	214.9	203.7	193.9	191.4	185.3	180.3	177.2
77.5°	151.1	157.5	157.7	157.1	153.4	146.6	142.5	140.7	134.6	132.8	132.1
80°	103.8	110.5	116.7	116.1	114.9	113.0	110.0	108.1	105.0	103.1	101.9
82.5°	69.2	75.5	80.6	84.0	83.7	81.9	79.8	78.9	78.3	76.9	76.7
85°	32.7	34.0	35.8	40.2	43.3	43.8	43.3	42.6	40.7	41.4	42.0
87.5°	12.5	12.4	12.8	12.6	11.9	14.2	15.5	15.9	15.0	14.2	13.4
90°	5.9	5.0	4.5	3.6	2.7	1.8	0.9	0.5	0.9	1.8	2.7
92.5°	103.1	61.7	37.1	23.8	16.1	10.5	6.7	5.5	6.7	10.5	16.1
95°	202.0	102.6	54.3	33.9	23.9	19.0	15.4	14.9	15.4	19.0	23.9
97.5°	161.2	88.4	56.4	41.7	32.8	27.8	25.3	24.8	25.3	27.8	32.8
100°	146.4	87.7	61.5	47.9	39.3	34.4	32.6	31.6	32.6	34.4	39.3
102.5°	140.3	90.9	67.6	54.4	46.6	41.2	39.8	39.2	39.8	41.2	46.6
105°	137.8	97.6	77.7	65.0	57.8	53.3	51.1	51.1	51.1	53.3	57.8
107.5°	142.0	107.6	88.3	76.9	69.4	65.7	63.5	62.7	63.5	65.7	69.4
110°	145.9	114.8	96.3	84.5	77.7	73.7	71.9	71.0	71.9	73.7	77.7



TEST NUMBER: P333618-927

CATALOG NUMBER: S125RDIP-S1270D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	151.0	121.7	103.9	92.4	85.7	81.6	80.2	79.3	80.2	81.6	85.7
115°	158.6	132.4	115.7	104.4	97.6	93.6	92.2	91.3	92.2	93.6	97.6
117.5°	167.3	143.5	127.6	116.7	109.0	105.0	103.5	102.1	103.5	105.0	109.0
120°	173.1	151.4	135.5	124.3	116.6	112.5	110.7	109.3	110.7	112.5	116.6
122.5°	179.6	159.0	143.1	131.9	123.4	119.4	118.0	116.9	118.0	119.4	123.4
125°	188.5	169.0	154.1	142.4	133.7	129.7	127.5	126.5	127.5	129.7	133.7
127.5°	196.5	178.6	164.3	152.6	143.5	138.3	135.4	134.0	135.4	138.3	143.5
130°	202.0	184.8	170.8	159.1	149.6	143.7	140.1	138.7	140.1	143.7	149.6
132.5°	206.7	190.6	176.6	164.9	155.0	148.4	144.1	142.4	144.1	148.4	155.0
135°	213.3	198.4	184.3	172.1	162.7	155.4	150.0	148.2	150.0	155.4	162.7
137.5°	218.2	203.9	191.2	178.6	169.3	162.1	157.0	155.7	157.0	162.1	169.3
140°	221.4	207.9	194.8	182.6	174.0	166.8	161.3	159.9	161.3	166.8	174.0
142.5°	223.2	210.4	198.0	186.6	178.3	171.1	166.0	165.0	166.0	171.1	178.3
145°	225.9	214.7	202.9	192.5	184.3	178.0	173.5	172.6	173.5	178.0	184.3
147.5°	227.6	217.4	207.1	197.9	190.8	185.0	181.1	180.5	181.1	185.0	190.8
150°	228.6	219.2	209.2	201.5	195.2	189.3	186.2	185.3	186.2	189.3	195.2
152.5°	229.3	220.9	211.8	204.8	198.8	193.7	190.8	190.4	190.8	193.7	198.8
155°	230.0	222.8	215.1	208.7	204.2	199.7	197.0	197.0	197.0	199.7	204.2
157.5°	230.4	224.3	217.7	212.9	209.0	205.1	202.9	203.0	202.9	205.1	209.0
160°	230.4	225.1	219.2	215.1	211.5	208.3	206.5	207.0	206.5	208.3	211.5
162.5°	230.1	225.8	220.6	217.3	214.4	211.6	209.8	210.2	209.8	211.6	214.4
165°	229.6	225.9	222.4	219.6	217.8	215.6	214.2	215.1	214.2	215.6	217.8
167.5°	228.5	225.9	222.9	221.3	220.0	218.7	217.9	218.3	217.9	218.7	220.0
170°	227.8	225.9	223.7	222.4	221.4	220.5	220.1	220.5	220.1	220.5	221.4
172.5°	227.0	225.6	223.7	223.1	222.5	221.6	221.2	222.0	221.2	221.6	222.5
175°	225.9	225.1	223.7	223.7	223.7	223.2	222.8	223.7	222.8	223.2	223.7
177.5°	224.8	224.5	223.8	223.8	224.1	223.8	223.8	224.5	223.8	223.8	224.1
180°	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1



TEST NUMBER: P333618-927

CATALOG NUMBER: S125RDIP-S1270D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3
2.5°	1479.1	1472.2	1467.2	1457.3	1450.4	1447.5	1442.0	1440.5	1446.0	1442.0	1441.5
5°	1435.1	1417.2	1403.0	1388.8	1373.3	1363.5	1348.7	1346.2	1342.5	1336.9	1335.7
7.5°	1382.4	1359.1	1340.8	1317.3	1296.9	1280.5	1261.9	1253.2	1248.4	1241.2	1231.6
10°	1346.8	1319.0	1294.3	1270.8	1245.5	1225.2	1206.7	1192.4	1183.1	1174.5	1170.8
12.5°	1311.7	1283.4	1251.8	1223.4	1195.2	1172.3	1151.8	1142.6	1132.3	1122.1	1113.5
15°	1257.3	1219.6	1185.0	1152.3	1128.2	1103.5	1083.7	1070.2	1054.7	1050.4	1033.7
17.5°	1199.4	1162.5	1122.0	1087.6	1059.6	1032.5	1010.7	995.3	983.7	967.8	960.1
20°	1163.4	1119.6	1080.1	1048.5	1017.6	985.6	963.3	950.4	939.2	926.3	920.1
22.5°	1124.9	1082.0	1041.5	1004.6	973.2	941.6	925.7	912.4	899.7	887.7	879.6
25°	1068.3	1025.1	982.5	944.2	911.5	888.6	870.1	854.6	847.9	836.1	827.4
27.5°	1012.3	966.4	922.2	884.0	858.3	835.8	820.5	808.3	796.1	785.8	778.3
30°	976.3	929.4	881.2	851.0	823.8	802.2	785.4	773.7	764.5	755.2	749.6
32.5°	940.2	891.8	849.1	816.3	790.7	772.0	754.9	743.6	733.9	723.6	717.1
35°	882.4	833.1	798.4	766.4	741.0	723.7	712.0	695.9	687.9	680.5	673.7
37.5°	828.7	782.8	745.4	717.2	695.2	678.0	662.8	654.2	644.3	637.6	632.0
40°	789.2	747.2	713.2	683.6	667.6	648.4	634.2	623.1	615.7	607.0	600.9
42.5°	753.6	714.6	681.6	655.0	634.9	618.8	605.1	593.9	584.6	578.4	573.1
45°	703.4	664.5	632.3	607.6	589.1	573.7	559.4	553.9	541.5	534.2	531.7
47.5°	651.3	616.6	585.5	562.8	543.8	529.2	515.9	504.5	497.7	490.4	486.5
50°	616.3	583.0	553.9	531.7	513.2	497.1	484.7	477.4	468.1	461.3	456.4
52.5°	581.2	550.3	521.3	500.0	484.0	467.9	454.2	446.7	437.9	433.6	430.2
55°	531.1	498.4	473.6	452.7	435.9	421.1	408.2	400.8	395.2	390.9	389.7
57.5°	474.3	448.3	425.3	406.5	389.1	375.2	363.8	356.8	351.9	351.3	347.5
60°	437.2	413.8	392.8	372.3	357.5	344.6	334.7	326.7	321.7	321.1	319.9
62.5°	400.1	377.6	358.1	340.2	326.9	314.4	305.1	296.0	293.1	290.0	287.2
65°	345.2	324.8	308.8	294.5	280.4	269.8	260.6	255.0	248.3	244.5	237.7
67.5°	291.2	275.4	260.0	248.0	236.9	226.9	219.2	211.0	206.4	203.4	198.4
70°	255.6	243.3	227.8	214.9	206.3	198.2	192.0	182.8	179.7	177.2	174.8
72.5°	222.0	211.2	198.2	187.7	179.1	171.5	164.4	160.0	157.0	154.5	153.0
75°	174.8	164.3	153.1	145.8	139.6	133.4	129.7	126.6	125.3	124.8	122.2
77.5°	128.3	122.8	113.8	108.0	103.9	101.4	98.1	96.5	96.3	93.6	92.8
80°	98.2	95.1	87.7	85.2	82.1	79.7	77.8	74.7	71.6	70.4	68.5
82.5°	73.0	69.9	66.9	63.0	60.4	58.9	57.0	55.9	56.3	54.6	53.7
85°	38.9	35.8	34.6	34.0	32.7	34.0	33.4	32.7	32.1	31.5	32.1
87.5°	13.1	13.2	12.8	14.0	12.6	13.3	13.4	13.0	13.1	13.2	12.8
90°	3.6	4.5	5.0	5.9	6.3	7.2	7.7	8.2	8.6	9.0	9.9
92.5°	23.8	37.1	61.7	103.1	148.1	145.7	118.0	80.1	58.1	43.7	37.1
95°	33.9	54.3	102.6	202.0	326.7	400.4	391.8	324.9	256.2	200.7	162.7
97.5°	41.7	56.4	88.4	161.2	291.8	427.5	495.7	483.9	435.7	381.6	328.8
100°	47.9	61.5	87.7	146.4	260.3	408.1	521.0	555.8	533.7	487.1	440.1
102.5°	54.4	67.6	90.9	140.3	236.4	373.7	505.8	580.0	593.7	571.3	539.6
105°	65.0	77.7	97.6	137.8	213.3	327.6	457.3	565.8	627.6	647.5	642.5
107.5°	76.9	88.3	107.6	142.0	203.5	295.9	407.8	514.8	597.4	648.5	672.0
110°	84.5	96.3	114.8	145.9	200.7	281.1	379.6	477.2	563.1	626.8	665.2



TEST NUMBER: P333618-927

CATALOG NUMBER: S125RDIP-S1270D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	92.4	103.9	121.7	151.0	200.7	272.4	358.6	447.6	529.1	593.5	638.8
115°	104.4	115.7	132.4	158.6	202.0	263.0	335.7	410.3	480.4	542.2	591.5
117.5°	116.7	127.6	143.5	167.3	204.9	258.4	322.1	386.3	446.6	499.9	545.2
120°	124.3	135.5	151.4	173.1	207.9	256.2	314.5	373.3	427.5	477.2	517.0
122.5°	131.9	143.1	159.0	179.6	210.4	254.4	308.0	363.5	413.8	458.0	495.3
125°	142.4	154.1	169.0	188.5	214.7	252.2	299.1	349.3	395.4	434.7	467.2
127.5°	152.6	164.3	178.6	196.5	219.4	251.0	291.0	334.9	377.9	414.5	445.0
130°	159.1	170.8	184.8	202.0	222.4	250.3	285.6	325.8	365.6	400.8	430.2
132.5°	164.9	176.6	190.6	206.7	225.6	250.3	281.2	316.8	354.0	386.0	414.3
135°	172.1	184.3	198.4	213.3	230.0	250.3	276.1	305.0	336.2	365.1	390.9
137.5°	178.6	191.2	203.9	218.2	234.1	250.9	271.5	295.1	320.3	344.4	366.2
140°	182.6	194.8	207.9	221.4	235.9	251.3	269.3	289.6	310.9	331.7	350.7
142.5°	186.6	198.0	210.4	223.2	236.9	251.6	267.5	284.9	302.9	320.8	337.3
145°	192.5	202.9	214.7	225.9	238.1	251.3	264.8	278.8	292.8	306.8	319.0
147.5°	197.9	207.1	217.4	227.6	238.6	250.1	262.0	273.1	284.4	295.2	304.4
150°	201.5	209.2	219.2	228.6	238.6	249.0	259.8	269.7	279.7	288.3	296.4
152.5°	204.8	211.8	220.9	229.3	238.2	247.6	257.3	266.2	275.0	282.9	289.2
155°	208.7	215.1	222.8	230.0	237.3	244.9	253.0	260.7	268.0	274.3	279.2
157.5°	212.9	217.7	224.3	230.4	236.1	242.2	249.1	255.3	261.3	266.2	270.1
160°	215.1	219.2	225.1	230.4	235.0	240.4	245.8	251.7	256.2	260.7	263.9
162.5°	217.3	220.6	225.8	230.1	233.9	238.2	243.0	247.7	251.9	255.6	258.5
165°	219.6	222.4	225.9	229.6	232.3	235.0	238.6	242.2	245.3	248.1	250.3
167.5°	221.3	222.9	225.9	228.5	229.7	231.8	234.3	236.9	239.1	241.1	242.7
170°	222.4	223.7	225.9	227.8	228.6	230.0	231.8	234.1	235.4	236.8	237.7
172.5°	223.1	223.7	225.6	227.0	227.2	227.8	229.3	230.8	232.2	233.1	233.7
175°	223.7	223.7	225.1	225.9	225.5	225.5	225.9	227.3	227.3	228.2	228.2
177.5°	223.8	223.8	224.5	224.8	224.1	224.1	224.5	224.8	225.2	225.2	225.2
180°	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1

TEST NUMBER: P333618-927

CATALOG NUMBER: S125RDIP-S1270D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3
2.5°	1441.1	1435.6	1434.1	1436.1	1434.1	1435.6	1441.1	1441.5	1442.0	1446.0	1440.5
5°	1329.5	1323.3	1326.4	1325.2	1326.4	1323.3	1329.5	1335.7	1336.9	1342.5	1346.2
7.5°	1231.4	1223.8	1215.6	1218.2	1215.6	1223.8	1231.4	1231.6	1241.2	1248.4	1253.2
10°	1162.8	1156.6	1152.9	1156.0	1152.9	1156.6	1162.8	1170.8	1174.5	1183.1	1192.4
12.5°	1105.0	1101.3	1098.0	1096.7	1098.0	1101.3	1105.0	1113.5	1122.1	1132.3	1142.6
15°	1026.3	1018.9	1015.8	1007.8	1015.8	1018.9	1026.3	1033.7	1050.4	1054.7	1070.2
17.5°	953.8	951.3	943.3	939.8	943.3	951.3	953.8	960.1	967.8	983.7	995.3
20°	910.9	908.4	900.3	905.3	900.3	908.4	910.9	920.1	926.3	939.2	950.4
22.5°	875.3	869.8	867.2	865.8	867.2	869.8	875.3	879.6	887.7	899.7	912.4
25°	825.0	817.0	813.9	810.2	813.9	817.0	825.0	827.4	836.1	847.9	854.6
27.5°	774.8	770.6	766.4	765.5	766.4	770.6	774.8	778.3	785.8	796.1	808.3
30°	742.3	737.9	734.8	734.8	734.8	737.9	742.3	749.6	755.2	764.5	773.7
32.5°	713.1	709.8	706.7	706.2	706.7	709.8	713.1	717.1	723.6	733.9	743.6
35°	670.7	665.7	664.5	660.8	664.5	665.7	670.7	673.7	680.5	687.9	695.9
37.5°	626.5	622.4	622.3	621.9	622.3	622.4	626.5	632.0	637.6	644.3	654.2
40°	598.3	595.2	594.7	590.3	594.7	595.2	598.3	600.9	607.0	615.7	623.1
42.5°	568.2	566.6	564.5	562.7	564.5	566.6	568.2	573.1	578.4	584.6	593.9
45°	527.4	523.0	523.0	519.9	523.0	523.0	527.4	531.7	534.2	541.5	553.9
47.5°	485.1	481.8	482.1	479.0	482.1	481.8	485.1	486.5	490.4	497.7	504.5
50°	456.9	455.1	454.5	453.3	454.5	455.1	456.9	456.4	461.3	468.1	477.4
52.5°	428.8	427.9	430.3	427.5	430.3	427.9	428.8	430.2	433.6	437.9	446.7
55°	390.9	389.0	392.8	389.0	392.8	389.0	390.9	389.7	390.9	395.2	400.8
57.5°	347.3	345.5	348.9	347.1	348.9	345.5	347.3	347.5	351.3	351.9	356.8
60°	318.6	315.0	316.8	317.4	316.8	315.0	318.6	319.9	321.1	321.7	326.7
62.5°	284.6	282.3	283.7	280.8	283.7	282.3	284.6	287.2	290.0	293.1	296.0
65°	236.5	234.6	232.2	230.9	232.2	234.6	236.5	237.7	244.5	248.3	255.0
67.5°	198.7	194.2	194.2	195.1	194.2	194.2	198.7	198.4	203.4	206.4	211.0
70°	171.0	171.0	170.4	170.4	170.4	171.0	171.0	174.8	177.2	179.7	182.8
72.5°	151.8	151.3	150.2	149.7	150.2	151.3	151.8	153.0	154.5	157.0	160.0
75°	122.2	122.9	121.7	121.0	121.7	122.9	122.2	122.2	124.8	125.3	126.6
77.5°	90.3	87.7	89.0	87.7	89.0	87.7	90.3	92.8	93.6	96.3	96.5
80°	68.5	67.9	69.8	67.9	69.8	67.9	68.5	68.5	70.4	71.6	74.7
82.5°	54.2	53.6	54.5	53.1	54.5	53.6	54.2	53.7	54.6	56.3	55.9
85°	32.7	32.1	31.5	32.1	31.5	32.1	32.7	32.1	31.5	32.1	32.7
87.5°	13.4	12.8	12.9	12.9	12.9	12.8	13.4	12.8	13.2	13.1	13.0
90°	9.9	9.9	10.4	10.4	10.4	9.9	9.9	9.9	9.0	8.6	8.2
92.5°	31.3	30.2	29.5	28.8	29.5	30.2	31.3	37.1	43.7	58.1	80.1
95°	130.6	117.0	113.4	106.2	113.4	117.0	130.6	162.7	200.7	256.2	324.9
97.5°	300.9	275.5	262.4	256.7	262.4	275.5	300.9	328.8	381.6	435.7	483.9
100°	408.9	376.4	359.7	352.4	359.7	376.4	408.9	440.1	487.1	533.7	555.8
102.5°	506.2	483.1	464.9	459.5	464.9	483.1	506.2	539.6	571.3	593.7	580.0
105°	628.1	613.2	604.2	598.7	604.2	613.2	628.1	642.5	647.5	627.6	565.8
107.5°	679.4	679.3	676.3	672.6	676.3	679.3	679.4	672.0	648.5	597.4	514.8
110°	685.5	694.1	697.3	697.3	697.3	694.1	685.5	665.2	626.8	563.1	477.2



TEST NUMBER: P333618-927

CATALOG NUMBER: S125RDIP-S1270D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	668.5	683.3	691.1	694.3	691.1	683.3	668.5	638.8	593.5	529.1	447.6
115°	626.8	648.5	661.1	667.0	661.1	648.5	626.8	591.5	542.2	480.4	410.3
117.5°	580.4	602.9	615.4	619.0	615.4	602.9	580.4	545.2	499.9	446.6	386.3
120°	550.4	572.1	584.3	587.9	584.3	572.1	550.4	517.0	477.2	427.5	373.3
122.5°	525.1	544.9	557.1	560.4	557.1	544.9	525.1	495.3	458.0	413.8	363.5
125°	492.6	511.1	521.0	525.5	521.0	511.1	492.6	467.2	434.7	395.4	349.3
127.5°	467.9	484.3	493.7	495.7	493.7	484.3	467.9	445.0	414.5	377.9	334.9
130°	452.8	467.7	476.7	479.4	476.7	467.7	452.8	430.2	400.8	365.6	325.8
132.5°	436.9	451.8	460.1	463.2	460.1	451.8	436.9	414.3	386.0	354.0	316.8
135°	410.7	425.6	433.8	436.5	433.8	425.6	410.7	390.9	365.1	336.2	305.0
137.5°	384.0	397.6	405.0	408.1	405.0	397.6	384.0	366.2	344.4	320.3	295.1
140°	367.4	379.1	385.9	388.2	385.9	379.1	367.4	350.7	331.7	310.9	289.6
142.5°	351.5	361.4	367.8	369.7	367.8	361.4	351.5	337.3	320.8	302.9	284.9
145°	329.9	337.5	342.5	344.4	342.5	337.5	329.9	319.0	306.8	292.8	278.8
147.5°	313.0	319.1	322.0	322.8	322.0	319.1	313.0	304.4	295.2	284.4	273.1
150°	303.2	308.6	310.5	310.9	310.5	308.6	303.2	296.4	288.3	279.7	269.7
152.5°	294.9	299.2	301.0	301.5	301.0	299.2	294.9	289.2	282.9	275.0	266.2
155°	283.8	286.9	288.3	288.8	288.3	286.9	283.8	279.2	274.3	268.0	260.7
157.5°	273.5	276.2	277.4	277.3	277.4	276.2	273.5	270.1	266.2	261.3	255.3
160°	267.0	269.3	270.2	269.7	270.2	269.3	267.0	263.9	260.7	256.2	251.7
162.5°	260.9	262.8	263.0	262.9	263.0	262.8	260.9	258.5	255.6	251.9	247.7
165°	252.2	253.0	253.0	253.0	253.0	253.0	252.2	250.3	248.1	245.3	242.2
167.5°	243.7	244.5	244.1	244.0	244.1	244.5	243.7	242.7	241.1	239.1	236.9
170°	238.6	239.1	239.1	238.6	239.1	239.1	238.6	237.7	236.8	235.4	234.1
172.5°	233.9	234.7	234.0	233.5	234.0	234.7	233.9	233.7	233.1	232.2	230.8
175°	228.2	228.6	227.8	227.3	227.8	228.6	228.2	228.2	228.2	227.3	227.3
177.5°	224.8	225.2	224.1	224.1	224.1	225.2	224.8	225.2	225.2	225.2	224.8
180°	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1



TEST NUMBER: P333618-927

CATALOG NUMBER: S125RDIP-S1270D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3
2.5°	1442.0	1447.5	1450.4	1457.3	1467.2	1472.2	1479.1	1484.0	1491.0	1499.4	1506.3
5°	1348.7	1363.5	1373.3	1388.8	1403.0	1417.2	1435.1	1448.1	1465.4	1485.1	1500.6
7.5°	1261.9	1280.5	1296.9	1317.3	1340.8	1359.1	1382.4	1406.2	1433.2	1461.3	1487.7
10°	1206.7	1225.2	1245.5	1270.8	1294.3	1319.0	1346.8	1374.6	1408.6	1440.0	1475.8
12.5°	1151.8	1172.3	1195.2	1223.4	1251.8	1283.4	1311.7	1343.0	1379.4	1420.3	1458.6
15°	1083.7	1103.5	1128.2	1152.3	1185.0	1219.6	1257.3	1298.6	1339.4	1385.1	1432.7
17.5°	1010.7	1032.5	1059.6	1087.6	1122.0	1162.5	1199.4	1244.8	1290.6	1343.9	1399.8
20°	963.3	985.6	1017.6	1048.5	1080.1	1119.6	1163.4	1209.7	1258.5	1314.7	1377.1
22.5°	925.7	941.6	973.2	1004.6	1041.5	1082.0	1124.9	1173.1	1226.4	1284.5	1349.9
25°	870.1	888.6	911.5	944.2	982.5	1025.1	1068.3	1119.6	1177.6	1236.9	1306.6
27.5°	820.5	835.8	858.3	884.0	922.2	966.4	1012.3	1065.8	1125.4	1185.7	1259.1
30°	785.4	802.2	823.8	851.0	881.2	929.4	976.3	1028.8	1089.3	1151.7	1227.0
32.5°	754.9	772.0	790.7	816.3	849.1	891.8	940.2	991.7	1053.2	1117.6	1191.0
35°	712.0	723.7	741.0	766.4	798.4	833.1	882.4	936.8	996.6	1063.3	1136.9
37.5°	662.8	678.0	695.2	717.2	745.4	782.8	828.7	883.7	939.2	1003.1	1070.2
40°	634.2	648.4	667.6	683.6	713.2	747.2	789.2	846.6	902.2	962.1	1023.3
42.5°	605.1	618.8	634.9	655.0	681.6	714.6	753.6	807.1	866.6	923.1	974.3
45°	559.4	573.7	589.1	607.6	632.3	664.5	703.4	752.1	804.0	855.9	894.8
47.5°	515.9	529.2	543.8	562.8	585.5	616.6	651.3	694.4	744.8	788.9	816.7
50°	484.7	497.1	513.2	531.7	553.9	583.0	616.3	658.9	700.8	741.0	766.4
52.5°	454.2	467.9	484.0	500.0	521.3	550.3	581.2	617.9	657.9	690.6	711.5
55°	408.2	421.1	435.9	452.7	473.6	498.4	531.1	560.1	591.6	619.4	631.7
57.5°	363.8	375.2	389.1	406.5	425.3	448.3	474.3	502.2	524.4	544.1	558.0
60°	334.7	344.6	357.5	372.3	392.8	413.8	437.2	463.1	480.5	497.1	510.1
62.5°	305.1	314.4	326.9	340.2	358.1	377.6	400.1	421.1	437.9	449.2	464.1
65°	260.6	269.8	280.4	294.5	308.8	324.8	345.2	360.6	372.3	384.7	394.0
67.5°	219.2	226.9	236.9	248.0	260.0	275.4	291.2	304.0	312.1	319.5	330.7
70°	192.0	198.2	206.3	214.9	227.8	243.3	255.6	265.5	271.1	278.5	292.1
72.5°	164.4	171.5	179.1	187.7	198.2	211.2	222.0	232.0	235.5	241.5	250.1
75°	129.7	133.4	139.6	145.8	153.1	164.3	174.8	177.2	180.3	185.3	191.4
77.5°	98.1	101.4	103.9	108.0	113.8	122.8	128.3	132.1	132.8	134.6	140.7
80°	77.8	79.7	82.1	85.2	87.7	95.1	98.2	101.9	103.1	105.0	108.1
82.5°	57.0	58.9	60.4	63.0	66.9	69.9	73.0	76.7	76.9	78.3	78.9
85°	33.4	34.0	32.7	34.0	34.6	35.8	38.9	42.0	41.4	40.7	42.6
87.5°	13.4	13.3	12.6	14.0	12.8	13.2	13.1	13.4	14.2	15.0	15.9
90°	7.7	7.2	6.3	5.9	5.0	4.5	3.6	2.7	1.8	0.9	0.5
92.5°	118.0	145.7	148.1	103.1	61.7	37.1	23.8	16.1	10.5	6.7	5.5
95°	391.8	400.4	326.7	202.0	102.6	54.3	33.9	23.9	19.0	15.4	14.9
97.5°	495.7	427.5	291.8	161.2	88.4	56.4	41.7	32.8	27.8	25.3	24.8
100°	521.0	408.1	260.3	146.4	87.7	61.5	47.9	39.3	34.4	32.6	31.6
102.5°	505.8	373.7	236.4	140.3	90.9	67.6	54.4	46.6	41.2	39.8	39.2
105°	457.3	327.6	213.3	137.8	97.6	77.7	65.0	57.8	53.3	51.1	51.1
107.5°	407.8	295.9	203.5	142.0	107.6	88.3	76.9	69.4	65.7	63.5	62.7
110°	379.6	281.1	200.7	145.9	114.8	96.3	84.5	77.7	73.7	71.9	71.0



TEST NUMBER: P333618-927

CATALOG NUMBER: S125RDIP-S1270D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	358.6	272.4	200.7	151.0	121.7	103.9	92.4	85.7	81.6	80.2	79.3
115°	335.7	263.0	202.0	158.6	132.4	115.7	104.4	97.6	93.6	92.2	91.3
117.5°	322.1	258.4	204.9	167.3	143.5	127.6	116.7	109.0	105.0	103.5	102.1
120°	314.5	256.2	207.9	173.1	151.4	135.5	124.3	116.6	112.5	110.7	109.3
122.5°	308.0	254.4	210.4	179.6	159.0	143.1	131.9	123.4	119.4	118.0	116.9
125°	299.1	252.2	214.7	188.5	169.0	154.1	142.4	133.7	129.7	127.5	126.5
127.5°	291.0	251.0	219.4	196.5	178.6	164.3	152.6	143.5	138.3	135.4	134.0
130°	285.6	250.3	222.4	202.0	184.8	170.8	159.1	149.6	143.7	140.1	138.7
132.5°	281.2	250.3	225.6	206.7	190.6	176.6	164.9	155.0	148.4	144.1	142.4
135°	276.1	250.3	230.0	213.3	198.4	184.3	172.1	162.7	155.4	150.0	148.2
137.5°	271.5	250.9	234.1	218.2	203.9	191.2	178.6	169.3	162.1	157.0	155.7
140°	269.3	251.3	235.9	221.4	207.9	194.8	182.6	174.0	166.8	161.3	159.9
142.5°	267.5	251.6	236.9	223.2	210.4	198.0	186.6	178.3	171.1	166.0	165.0
145°	264.8	251.3	238.1	225.9	214.7	202.9	192.5	184.3	178.0	173.5	172.6
147.5°	262.0	250.1	238.6	227.6	217.4	207.1	197.9	190.8	185.0	181.1	180.5
150°	259.8	249.0	238.6	228.6	219.2	209.2	201.5	195.2	189.3	186.2	185.3
152.5°	257.3	247.6	238.2	229.3	220.9	211.8	204.8	198.8	193.7	190.8	190.4
155°	253.0	244.9	237.3	230.0	222.8	215.1	208.7	204.2	199.7	197.0	197.0
157.5°	249.1	242.2	236.1	230.4	224.3	217.7	212.9	209.0	205.1	202.9	203.0
160°	245.8	240.4	235.0	230.4	225.1	219.2	215.1	211.5	208.3	206.5	207.0
162.5°	243.0	238.2	233.9	230.1	225.8	220.6	217.3	214.4	211.6	209.8	210.2
165°	238.6	235.0	232.3	229.6	225.9	222.4	219.6	217.8	215.6	214.2	215.1
167.5°	234.3	231.8	229.7	228.5	225.9	222.9	221.3	220.0	218.7	217.9	218.3
170°	231.8	230.0	228.6	227.8	225.9	223.7	222.4	221.4	220.5	220.1	220.5
172.5°	229.3	227.8	227.2	227.0	225.6	223.7	223.1	222.5	221.6	221.2	222.0
175°	225.9	225.5	225.5	225.9	225.1	223.7	223.7	223.7	223.2	222.8	223.7
177.5°	224.5	224.1	224.1	224.8	224.5	223.8	223.8	224.1	223.8	223.8	224.5
180°	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1



TEST NUMBER: P333618-927

CATALOG NUMBER: S125RDIP-S1270D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3
2.5°	1511.6	1516.2	1522.6	1529.9	1535.9	1542.3	1545.8	1545.8	1548.7	1555.1	1563.5
5°	1516.0	1532.1	1547.5	1567.3	1582.7	1600.6	1614.2	1627.1	1638.9	1653.7	1669.1
7.5°	1514.7	1541.4	1569.2	1600.4	1634.7	1662.0	1690.0	1712.0	1733.8	1762.1	1784.5
10°	1509.8	1544.4	1582.1	1621.6	1664.9	1702.5	1736.5	1767.4	1797.0	1827.9	1855.6
12.5°	1500.9	1544.9	1590.9	1638.4	1693.0	1736.1	1780.0	1812.8	1847.4	1881.2	1915.4
15°	1487.6	1539.4	1595.1	1661.1	1727.8	1776.0	1819.2	1861.8	1893.9	1932.2	1964.9
17.5°	1460.1	1526.9	1596.8	1669.0	1733.1	1789.1	1834.4	1874.9	1909.1	1951.2	1995.7
20°	1443.8	1516.0	1588.9	1666.0	1727.2	1784.6	1828.4	1870.4	1913.0	1968.0	2022.4
22.5°	1421.0	1498.3	1575.5	1648.8	1713.3	1768.8	1814.2	1865.5	1921.4	1983.9	2049.5
25°	1385.1	1464.7	1541.3	1611.1	1674.1	1730.9	1792.6	1861.8	1929.8	2011.9	2106.3
27.5°	1339.5	1416.3	1484.6	1558.4	1621.0	1693.2	1770.3	1845.2	1943.2	2056.2	2174.1
30°	1305.4	1378.3	1443.1	1512.9	1583.9	1663.6	1750.0	1838.3	1955.0	2087.8	2228.0
32.5°	1265.9	1331.9	1396.2	1463.5	1545.4	1632.9	1724.8	1832.9	1972.4	2123.4	2268.5
35°	1197.4	1256.6	1319.0	1393.8	1480.8	1575.9	1693.2	1824.8	1993.4	2155.8	2286.1
37.5°	1125.5	1172.3	1234.9	1313.7	1408.6	1518.6	1651.7	1811.6	1984.7	2130.4	2185.9
40°	1070.2	1114.0	1180.0	1262.8	1356.7	1477.1	1626.5	1790.8	1964.9	2066.2	2061.9
42.5°	1015.3	1059.6	1123.2	1206.5	1304.3	1439.1	1592.9	1763.6	1910.6	1949.2	1868.8
45°	931.2	972.6	1035.0	1119.0	1223.9	1365.3	1527.1	1690.8	1784.6	1722.3	1562.9
47.5°	845.5	885.7	943.6	1025.8	1140.4	1288.4	1441.4	1575.7	1588.9	1454.8	1263.8
50°	789.2	826.9	881.8	969.5	1080.6	1225.2	1372.8	1478.4	1445.6	1282.0	1085.0
52.5°	734.4	770.6	822.0	904.8	1018.4	1159.9	1291.7	1374.6	1298.9	1124.9	947.6
55°	653.3	687.9	739.8	815.7	918.9	1048.5	1164.0	1194.3	1083.2	907.8	764.5
57.5°	576.4	601.7	653.0	720.2	819.6	933.9	1016.7	1011.2	888.6	730.6	627.9
60°	525.5	548.3	597.1	658.9	753.4	855.9	913.9	889.2	765.1	634.8	536.0
62.5°	478.1	499.5	540.3	597.1	678.3	767.5	809.7	775.6	658.4	543.9	465.3
65°	406.3	421.8	454.5	507.0	570.6	632.3	670.0	620.0	516.3	429.8	370.5
67.5°	339.3	352.6	381.8	419.4	463.3	505.9	521.2	474.3	393.6	335.3	293.6
70°	295.8	308.2	327.9	363.1	392.1	422.4	429.8	387.8	320.5	276.0	250.1
72.5°	254.3	265.6	283.0	307.8	327.9	345.3	348.8	309.7	258.3	227.6	207.6
75°	193.9	203.7	214.9	224.2	237.1	240.2	239.0	208.7	180.9	160.6	149.4
77.5°	142.5	146.6	153.4	157.1	157.7	157.5	151.1	132.1	117.7	109.3	104.7
80°	110.0	113.0	114.9	116.1	116.7	110.5	103.8	92.0	87.1	82.1	76.6
82.5°	79.8	81.9	83.7	84.0	80.6	75.5	69.2	63.4	59.9	57.4	55.3
85°	43.3	43.8	43.3	40.2	35.8	34.0	32.7	31.5	30.9	30.3	30.3
87.5°	15.5	14.2	11.9	12.6	12.8	12.4	12.5	12.1	11.8	11.9	12.0
90°	0.9	1.8	2.7	3.6	4.5	5.0	5.9	6.3	7.2	7.7	8.2
92.5°	6.7	10.5	16.1	23.8	37.1	61.7	103.1	148.1	145.7	118.0	80.1
95°	15.4	19.0	23.9	33.9	54.3	102.6	202.0	326.7	400.4	391.8	324.9
97.5°	25.3	27.8	32.8	41.7	56.4	88.4	161.2	291.8	427.5	495.7	483.9
100°	32.6	34.4	39.3	47.9	61.5	87.7	146.4	260.3	408.1	521.0	555.8
102.5°	39.8	41.2	46.6	54.4	67.6	90.9	140.3	236.4	373.7	505.8	580.0
105°	51.1	53.3	57.8	65.0	77.7	97.6	137.8	213.3	327.6	457.3	565.8
107.5°	63.5	65.7	69.4	76.9	88.3	107.6	142.0	203.5	295.9	407.8	514.8
110°	71.9	73.7	77.7	84.5	96.3	114.8	145.9	200.7	281.1	379.6	477.2



TEST NUMBER: P333618-927

CATALOG NUMBER: S125RDIP-S1270D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	80.2	81.6	85.7	92.4	103.9	121.7	151.0	200.7	272.4	358.6	447.6
115°	92.2	93.6	97.6	104.4	115.7	132.4	158.6	202.0	263.0	335.7	410.3
117.5°	103.5	105.0	109.0	116.7	127.6	143.5	167.3	204.9	258.4	322.1	386.3
120°	110.7	112.5	116.6	124.3	135.5	151.4	173.1	207.9	256.2	314.5	373.3
122.5°	118.0	119.4	123.4	131.9	143.1	159.0	179.6	210.4	254.4	308.0	363.5
125°	127.5	129.7	133.7	142.4	154.1	169.0	188.5	214.7	252.2	299.1	349.3
127.5°	135.4	138.3	143.5	152.6	164.3	178.6	196.5	219.4	251.0	291.0	334.9
130°	140.1	143.7	149.6	159.1	170.8	184.8	202.0	222.4	250.3	285.6	325.8
132.5°	144.1	148.4	155.0	164.9	176.6	190.6	206.7	225.6	250.3	281.2	316.8
135°	150.0	155.4	162.7	172.1	184.3	198.4	213.3	230.0	250.3	276.1	305.0
137.5°	157.0	162.1	169.3	178.6	191.2	203.9	218.2	234.1	250.9	271.5	295.1
140°	161.3	166.8	174.0	182.6	194.8	207.9	221.4	235.9	251.3	269.3	289.6
142.5°	166.0	171.1	178.3	186.6	198.0	210.4	223.2	236.9	251.6	267.5	284.9
145°	173.5	178.0	184.3	192.5	202.9	214.7	225.9	238.1	251.3	264.8	278.8
147.5°	181.1	185.0	190.8	197.9	207.1	217.4	227.6	238.6	250.1	262.0	273.1
150°	186.2	189.3	195.2	201.5	209.2	219.2	228.6	238.6	249.0	259.8	269.7
152.5°	190.8	193.7	198.8	204.8	211.8	220.9	229.3	238.2	247.6	257.3	266.2
155°	197.0	199.7	204.2	208.7	215.1	222.8	230.0	237.3	244.9	253.0	260.7
157.5°	202.9	205.1	209.0	212.9	217.7	224.3	230.4	236.1	242.2	249.1	255.3
160°	206.5	208.3	211.5	215.1	219.2	225.1	230.4	235.0	240.4	245.8	251.7
162.5°	209.8	211.6	214.4	217.3	220.6	225.8	230.1	233.9	238.2	243.0	247.7
165°	214.2	215.6	217.8	219.6	222.4	225.9	229.6	232.3	235.0	238.6	242.2
167.5°	217.9	218.7	220.0	221.3	222.9	225.9	228.5	229.7	231.8	234.3	236.9
170°	220.1	220.5	221.4	222.4	223.7	225.9	227.8	228.6	230.0	231.8	234.1
172.5°	221.2	221.6	222.5	223.1	223.7	225.6	227.0	227.2	227.8	229.3	230.8
175°	222.8	223.2	223.7	223.7	223.7	225.1	225.9	225.5	225.5	225.9	227.3
177.5°	223.8	223.8	224.1	223.8	223.8	224.5	224.8	224.1	224.1	224.5	224.8
180°	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1



TEST NUMBER: P333618-927

CATALOG NUMBER: S125RDIP-S1270D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3
2.5°	1569.9	1569.9	1578.3	1577.9	1583.3	1581.4	1582.3
5°	1687.7	1698.2	1707.5	1713.6	1722.8	1725.4	1724.1
7.5°	1809.7	1833.0	1844.4	1860.0	1862.8	1871.0	1870.1
10°	1885.3	1908.1	1925.4	1939.0	1945.8	1954.5	1955.0
12.5°	1944.6	1964.0	1979.3	1991.9	2000.1	2002.9	2004.5
15°	1990.8	2012.5	2030.4	2048.3	2058.8	2066.8	2071.2
17.5°	2037.6	2070.9	2102.5	2126.9	2141.4	2153.8	2153.6
20°	2073.6	2111.9	2151.4	2179.2	2207.7	2219.9	2221.8
22.5°	2112.1	2170.7	2221.6	2264.7	2302.0	2314.8	2319.7
25°	2192.2	2268.7	2347.2	2407.7	2450.9	2476.2	2479.9
27.5°	2288.9	2392.5	2475.0	2530.9	2566.7	2585.5	2589.6
30°	2357.1	2452.8	2526.9	2568.9	2585.5	2588.0	2578.7
32.5°	2387.7	2459.2	2488.8	2486.3	2453.6	2431.9	2423.6
35°	2350.2	2335.4	2263.2	2176.8	2110.7	2068.7	2057.5
37.5°	2138.8	2011.0	1878.1	1747.5	1677.9	1642.6	1581.8
40°	1930.4	1748.2	1609.9	1499.9	1421.5	1358.5	1343.7
42.5°	1695.2	1507.1	1368.8	1274.7	1212.0	1168.9	1150.1
45°	1362.2	1200.5	1086.2	1014.0	965.8	934.3	920.1
47.5°	1089.6	964.3	881.1	827.6	790.9	763.5	755.8
50°	939.8	839.8	769.4	724.4	696.6	675.6	666.9
52.5°	816.3	735.6	681.5	644.3	618.0	604.9	597.8
55°	673.7	604.0	565.1	535.4	520.5	510.1	505.1
57.5°	551.0	500.6	472.1	451.6	437.9	431.3	428.8
60°	482.3	442.8	416.8	400.8	391.5	382.9	380.4
62.5°	421.5	390.4	370.4	356.3	347.1	343.3	341.8
65°	339.6	319.2	304.4	295.8	288.4	287.2	286.5
67.5°	270.0	258.0	250.3	241.2	238.6	234.2	233.5
70°	230.9	222.9	213.7	210.6	207.5	203.2	203.7
72.5°	195.9	187.8	181.6	177.4	176.3	174.5	176.1
75°	143.2	140.8	138.3	135.2	134.0	134.0	133.4
77.5°	102.3	100.1	97.4	95.6	95.2	92.6	93.6
80°	74.1	71.0	69.8	70.4	68.5	67.9	67.9
82.5°	54.8	53.7	52.5	52.6	52.2	51.7	52.1
85°	30.3	29.6	29.6	29.0	29.0	28.4	28.4
87.5°	12.6	13.2	12.4	11.9	11.9	12.4	12.9
90°	8.6	9.0	9.9	9.9	9.9	10.4	10.4
92.5°	58.1	43.7	37.1	31.3	30.2	29.5	28.8
95°	256.2	200.7	162.7	130.6	117.0	113.4	106.2
97.5°	435.7	381.6	328.8	300.9	275.5	262.4	256.7
100°	533.7	487.1	440.1	408.9	376.4	359.7	352.4
102.5°	593.7	571.3	539.6	506.2	483.1	464.9	459.5
105°	627.6	647.5	642.5	628.1	613.2	604.2	598.7
107.5°	597.4	648.5	672.0	679.4	679.3	676.3	672.6
110°	563.1	626.8	665.2	685.5	694.1	697.3	697.3



TEST NUMBER: P333618-927

CATALOG NUMBER: S125RDIP-S1270D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	529.1	593.5	638.8	668.5	683.3	691.1	694.3
115°	480.4	542.2	591.5	626.8	648.5	661.1	667.0
117.5°	446.6	499.9	545.2	580.4	602.9	615.4	619.0
120°	427.5	477.2	517.0	550.4	572.1	584.3	587.9
122.5°	413.8	458.0	495.3	525.1	544.9	557.1	560.4
125°	395.4	434.7	467.2	492.6	511.1	521.0	525.5
127.5°	377.9	414.5	445.0	467.9	484.3	493.7	495.7
130°	365.6	400.8	430.2	452.8	467.7	476.7	479.4
132.5°	354.0	386.0	414.3	436.9	451.8	460.1	463.2
135°	336.2	365.1	390.9	410.7	425.6	433.8	436.5
137.5°	320.3	344.4	366.2	384.0	397.6	405.0	408.1
140°	310.9	331.7	350.7	367.4	379.1	385.9	388.2
142.5°	302.9	320.8	337.3	351.5	361.4	367.8	369.7
145°	292.8	306.8	319.0	329.9	337.5	342.5	344.4
147.5°	284.4	295.2	304.4	313.0	319.1	322.0	322.8
150°	279.7	288.3	296.4	303.2	308.6	310.5	310.9
152.5°	275.0	282.9	289.2	294.9	299.2	301.0	301.5
155°	268.0	274.3	279.2	283.8	286.9	288.3	288.8
157.5°	261.3	266.2	270.1	273.5	276.2	277.4	277.3
160°	256.2	260.7	263.9	267.0	269.3	270.2	269.7
162.5°	251.9	255.6	258.5	260.9	262.8	263.0	262.9
165°	245.3	248.1	250.3	252.2	253.0	253.0	253.0
167.5°	239.1	241.1	242.7	243.7	244.5	244.1	244.0
170°	235.4	236.8	237.7	238.6	239.1	239.1	238.6
172.5°	232.2	233.1	233.7	233.9	234.7	234.0	233.5
175°	227.3	228.2	228.2	228.2	228.6	227.8	227.3
177.5°	225.2	225.2	225.2	224.8	225.2	224.1	224.1
180°	224.1	224.1	224.1	224.1	224.1	224.1	224.1

(END OF REPORT)