

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333556

Luminaire Tested: **S125RDIP-S850D590U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333556  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S850D590U835-4F0-1E-UDD-A  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 590 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5642.2 lumens  
Efficiency: N/A  
Efficacy: 140.0 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 40.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333556

CATALOG NUMBER: S125RDIP-S850D590U835-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333556

CATALOG NUMBER: S125RDIP-S850D590U835-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64	58
1	100	96	92	89	93	90	86	83	78	75	73	67	65	64	57	56	55	50
2	92	84	78	73	85	79	74	69	69	65	61	59	56	54	51	49	47	43
3	84	74	67	62	78	70	63	58	61	56	52	53	49	46	45	43	40	37
4	77	66	58	52	71	62	55	50	54	49	45	47	43	40	41	38	35	32
5	71	59	51	45	66	56	48	43	49	43	39	43	38	35	37	33	31	28
6	65	53	45	39	61	50	43	38	44	38	34	39	34	31	33	30	27	24
7	60	48	40	35	56	45	38	33	40	34	30	35	31	27	31	27	24	22
8	56	44	36	31	52	41	34	29	37	31	27	32	28	24	28	25	22	20
9	52	40	33	28	49	38	31	26	34	28	24	30	25	22	26	22	20	18
10	49	37	30	25	46	35	28	24	31	26	22	27	23	20	24	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	8169	8169	8169	8169
5°	9398	8180	7224	8180
10°	10781	8138	6374	8138
15°	11645	8055	5666	8055
20°	12841	7958	5232	7958
25°	14860	7829	4855	7829
30°	16171	7694	4608	7694
35°	13640	7536	4380	7536
40°	9526	7254	4185	7254
45°	7067	6872	3993	6872
50°	5635	6475	3829	6475
55°	4782	5981	3683	5981
60°	4132	5540	3447	5540
65°	3681	5063	2968	5063
70°	3237	4638	2706	4638
75°	2800	4017	2540	4017
80°	2124	3381	2124	3381
85°	1771	2653	2001	2653



TEST NUMBER: P333556

CATALOG NUMBER: S125RDIP-S850D590U835-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	121.3	2.1
10°-20°	355.5	6.3
20°-30°	563.6	10.0
30°-40°	679.7	12.0
40°-50°	607.0	10.8
50°-60°	465.5	8.2
60°-70°	302.5	5.4
70°-80°	147.1	2.6
80°-90°	36.7	0.7
90°-100°	28.0	0.5
100°-110°	172.4	3.1
110°-120°	312.6	5.5
120°-130°	401.2	7.1
130°-140°	431.5	7.6
140°-150°	405.1	7.2
150°-160°	327.7	5.8
160°-170°	211.9	3.8
170°-180°	73.1	1.3
0°-30°	1040.4	18.4
0°-40°	1720.1	30.5
0°-60°	2792.5	49.5
0°-90°	3278.7	58.1
90°-120°	513.0	9.1
90°-150°	1750.8	31.0
90°-180°	2364.0	41.9
0°-180°	5642.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1265	1265	1265	1265	1265	
5°	1450	1262	1114	1262	1450	145
15°	1742	1205	847	1205	1742	499
25°	2085	1099	681	1099	2085	957
35°	1730	956	556	956	1730	1045
45°	774	752	437	752	774	617
55°	425	531	327	531	425	385
65°	241	331	194	331	241	240
75°	112	161	102	161	112	119
85°	24	36	27	36	24	28
90°	14	1	14	1	14	7
95°	12	32	12	32	12	10
105°	169	168	169	168	169	153
115°	313	315	313	315	313	310
125°	448	448	448	448	448	398
135°	556	559	556	559	556	429
145°	646	648	646	648	646	403
155°	708	713	708	713	708	326
165°	748	752	748	752	748	211
175°	766	770	766	770	766	73
180°	770	770	770	770	770	



TEST NUMBER: P333556

CATALOG NUMBER: S125RDIP-S850D590U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1330.5	1329.7	1331.4	1326.8	1327.2	1320.1	1320.1	1314.7	1307.7	1302.3	1299.8
5°	1449.7	1450.8	1448.7	1440.9	1435.7	1427.9	1419.1	1403.5	1390.5	1378.1	1368.2
7.5°	1572.5	1573.2	1566.4	1564.0	1550.9	1541.3	1521.7	1500.5	1481.7	1457.8	1439.6
10°	1643.9	1643.4	1636.2	1630.4	1619.0	1604.5	1585.3	1560.3	1537.0	1511.0	1486.1
12.5°	1685.5	1684.1	1681.8	1674.9	1664.3	1651.4	1635.1	1610.6	1581.8	1553.4	1524.3
15°	1741.6	1737.9	1731.2	1722.3	1707.3	1692.2	1674.1	1652.3	1624.7	1592.5	1565.5
17.5°	1810.9	1811.0	1800.7	1788.4	1767.9	1741.4	1713.3	1678.1	1640.7	1605.3	1576.5
20°	1868.3	1866.7	1856.3	1832.4	1809.1	1775.8	1743.6	1700.5	1654.8	1608.6	1572.8
22.5°	1950.5	1946.5	1935.7	1904.3	1868.1	1825.3	1776.0	1723.4	1668.1	1615.7	1568.7
25°	2085.3	2082.2	2060.9	2024.6	1973.7	1907.7	1843.3	1771.2	1691.7	1622.7	1565.5
27.5°	2177.5	2174.1	2158.3	2128.1	2081.2	2011.8	1924.6	1828.2	1729.0	1634.0	1551.6
30°	2168.4	2176.2	2174.1	2160.1	2124.8	2062.5	1982.0	1873.5	1755.6	1643.9	1545.8
32.5°	2037.9	2044.9	2063.2	2090.7	2092.8	2067.9	2007.7	1907.5	1785.5	1658.5	1541.2
35°	1730.1	1739.5	1774.8	1830.4	1903.0	1963.8	1976.3	1922.3	1812.7	1676.1	1534.4
37.5°	1330.1	1381.2	1410.9	1469.4	1579.2	1691.0	1798.5	1838.0	1791.4	1668.9	1523.3
40°	1129.9	1142.3	1195.3	1261.3	1353.7	1470.0	1623.2	1733.8	1737.4	1652.3	1505.8
42.5°	967.0	982.8	1019.2	1071.8	1151.0	1267.3	1425.4	1571.4	1639.0	1606.6	1483.0
45°	773.7	785.6	812.1	852.6	913.4	1009.4	1145.5	1314.2	1448.2	1500.6	1421.7
47.5°	635.6	642.0	665.1	695.9	740.9	810.9	916.2	1062.7	1223.4	1336.0	1324.9
50°	560.8	568.1	585.7	609.1	647.0	706.2	790.3	912.3	1078.0	1215.6	1243.1
52.5°	502.6	508.7	519.7	541.8	573.0	618.5	686.4	796.8	945.9	1092.2	1155.8
55°	424.7	428.9	437.7	450.2	475.1	507.8	566.5	642.8	763.3	910.8	1004.2
57.5°	360.6	362.6	368.3	379.8	397.0	420.9	463.3	528.0	614.4	747.2	850.3
60°	319.9	321.9	329.2	337.0	350.5	372.3	405.5	450.7	533.8	643.3	747.7
62.5°	287.5	288.7	291.8	299.6	311.4	328.3	354.4	391.3	457.4	553.6	652.2
65°	240.9	241.5	242.5	248.7	256.0	268.5	285.6	311.5	361.4	434.1	521.3
67.5°	196.3	197.0	200.6	202.8	210.4	216.9	227.0	246.9	282.0	331.0	398.8
70°	171.4	170.8	174.5	177.1	179.7	187.4	194.2	210.3	232.1	269.5	326.1
72.5°	148.1	146.7	148.3	149.2	152.7	158.0	164.7	174.6	191.4	217.1	260.5
75°	112.2	112.7	112.7	113.7	116.3	118.4	120.5	125.7	135.0	152.1	175.5
77.5°	78.7	77.9	80.1	80.4	81.9	84.2	86.0	88.1	91.9	99.0	111.0
80°	57.1	57.1	57.6	59.2	58.7	59.7	62.3	64.4	69.1	73.2	77.4
82.5°	43.8	43.4	43.9	44.2	44.1	45.2	46.1	46.5	48.3	50.4	53.3
85°	23.9	23.9	24.4	24.4	24.9	24.9	25.4	25.4	25.4	26.0	26.5
87.5°	11.9	11.4	10.9	10.8	11.2	11.9	11.3	10.8	10.7	10.5	10.8
90°	13.7	13.3	12.9	12.6	12.2	11.7	11.0	10.4	9.8	9.1	8.2
92.5°	12.8	12.6	12.4	12.2	12.1	11.7	11.0	10.4	9.8	9.1	8.3
95°	12.0	12.0	12.0	12.0	12.0	11.7	11.0	10.4	9.8	9.1	13.9
97.5°	12.0	12.0	12.0	12.0	12.0	13.8	17.3	20.9	24.5	28.1	37.6
100°	12.0	12.5	13.0	13.5	14.0	23.7	42.6	61.5	80.4	99.3	98.8
102.5°	71.8	80.4	89.0	97.6	106.3	112.4	115.9	119.5	123.1	126.7	126.4
105°	169.4	169.6	169.7	169.8	170.0	170.0	170.0	170.0	170.0	170.0	170.0
107.5°	213.6	214.0	214.4	214.8	215.1	215.3	215.3	215.3	215.2	215.2	215.0
110°	244.2	244.1	243.9	243.8	243.7	243.8	244.2	244.6	245.0	245.3	245.1



TEST NUMBER: P333556

CATALOG NUMBER: S125RDIP-S850D590U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	271.6	271.8	271.9	272.1	272.3	272.6	273.1	273.6	274.1	274.5	274.4
115°	312.7	313.4	314.2	314.9	315.7	316.3	316.8	317.3	317.9	318.4	318.2
117.5°	356.5	356.8	357.1	357.5	357.8	358.3	358.9	359.6	360.3	360.9	360.4
120°	383.4	384.0	384.7	385.3	385.9	386.4	386.6	386.9	387.1	387.4	387.0
122.5°	409.0	409.7	410.4	411.2	411.9	412.4	412.7	412.9	413.2	413.4	413.2
125°	447.9	448.3	448.6	449.0	449.4	449.8	450.3	450.9	451.4	451.9	451.9
127.5°	480.6	481.6	482.5	483.4	484.4	485.0	485.3	485.5	485.8	486.1	486.2
130°	504.4	505.0	505.6	506.3	506.9	507.4	507.8	508.2	508.5	508.9	508.8
132.5°	526.3	526.9	527.5	528.2	528.8	529.2	529.2	529.3	529.4	529.5	529.7
135°	556.3	557.0	557.8	558.6	559.3	559.8	560.1	560.3	560.6	560.8	561.1
137.5°	586.4	587.1	587.7	588.4	589.0	589.3	589.3	589.2	589.2	589.1	589.4
140°	604.2	605.0	605.7	606.5	607.2	607.5	607.2	607.0	606.7	606.5	606.6
142.5°	621.1	621.8	622.6	623.4	624.1	624.5	624.4	624.4	624.3	624.3	624.1
145°	645.8	646.6	647.4	648.1	648.9	649.2	649.1	649.0	648.8	648.7	648.7
147.5°	666.3	667.2	668.1	669.0	669.9	670.3	670.2	670.0	669.9	669.7	669.5
150°	679.5	680.5	681.5	682.6	683.6	683.9	683.7	683.4	683.2	682.9	682.7
152.5°	691.8	692.7	693.7	694.6	695.5	695.8	695.6	695.3	695.1	694.8	694.5
155°	708.0	709.1	710.1	711.1	712.1	712.4	712.0	711.7	711.3	710.9	710.6
157.5°	721.6	722.6	723.6	724.7	725.7	726.0	725.6	725.2	724.8	724.4	724.3
160°	730.3	731.3	732.3	733.3	734.3	734.6	734.1	733.6	733.1	732.6	732.4
162.5°	738.0	739.2	740.3	741.4	742.5	742.7	742.0	741.3	740.6	739.9	739.7
165°	748.5	749.6	750.6	751.6	752.6	752.7	752.0	751.2	750.4	749.7	749.6
167.5°	755.8	757.0	758.1	759.3	760.4	760.5	759.6	758.7	757.8	756.9	756.7
170°	760.0	761.1	762.2	763.4	764.5	764.6	763.6	762.6	761.5	760.5	760.4
172.5°	762.7	763.8	765.0	766.1	767.3	767.4	766.5	765.5	764.6	763.7	763.5
175°	766.2	767.4	768.5	769.7	770.8	770.9	769.8	768.8	767.8	766.8	766.7
177.5°	768.3	769.1	769.9	770.7	771.5	771.6	770.9	770.2	769.5	768.7	768.6
180°	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7



TEST NUMBER: P333556

CATALOG NUMBER: S125RDIP-S850D590U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1299.8	1296.9	1291.5	1286.5	1280.3	1274.9	1271.1	1266.6	1260.7	1253.7	1247.9
5°	1357.3	1345.9	1330.8	1317.9	1301.2	1288.3	1274.8	1261.8	1248.8	1232.2	1217.6
7.5°	1421.1	1397.5	1374.6	1345.7	1319.5	1296.1	1273.7	1251.0	1228.8	1205.2	1182.4
10°	1460.1	1431.6	1399.9	1363.5	1330.3	1298.6	1269.6	1241.0	1210.9	1184.4	1155.8
12.5°	1496.7	1459.8	1423.6	1377.7	1337.8	1299.1	1262.1	1226.5	1194.3	1159.9	1129.3
15°	1529.7	1493.4	1452.9	1396.8	1341.2	1294.5	1250.9	1204.7	1164.7	1126.3	1092.0
17.5°	1542.5	1504.4	1457.3	1403.4	1342.7	1283.9	1227.7	1177.0	1130.0	1085.2	1046.7
20°	1537.5	1500.6	1452.3	1400.9	1336.0	1274.8	1214.0	1157.9	1105.5	1058.2	1017.2
22.5°	1525.4	1487.3	1440.7	1386.4	1324.8	1259.8	1194.9	1135.1	1080.1	1031.2	986.5
25°	1507.4	1455.5	1407.7	1354.7	1296.0	1231.7	1164.7	1098.7	1040.1	990.2	941.4
27.5°	1488.6	1423.8	1363.0	1310.4	1248.4	1190.9	1126.4	1058.7	997.1	946.3	896.2
30°	1471.6	1398.9	1331.9	1272.2	1213.5	1159.0	1097.7	1031.7	968.4	916.0	865.1
32.5°	1450.4	1373.1	1299.5	1230.6	1174.0	1119.9	1064.5	1001.4	939.7	885.6	833.9
35°	1423.8	1325.1	1245.2	1171.9	1109.1	1056.7	1006.8	955.9	894.1	838.1	787.7
37.5°	1388.9	1276.9	1184.4	1104.7	1038.4	985.7	946.4	899.9	843.5	789.8	743.0
40°	1367.7	1242.0	1140.8	1061.9	992.3	936.7	899.9	860.4	809.0	758.6	711.9
42.5°	1339.5	1210.1	1096.8	1014.5	944.5	891.0	853.7	819.3	776.2	728.7	678.7
45°	1284.1	1148.1	1029.2	940.9	870.3	817.8	783.0	752.4	719.7	676.1	632.4
47.5°	1212.0	1083.4	958.9	862.6	793.4	744.7	711.0	686.8	663.4	626.3	583.9
50°	1154.3	1030.2	908.7	815.2	741.5	695.3	663.6	644.4	623.1	589.3	554.0
52.5°	1086.2	975.4	856.3	760.8	691.2	647.9	617.5	598.3	580.7	553.2	519.6
55°	978.8	881.7	772.6	685.9	622.1	578.4	549.4	531.2	520.8	497.4	471.0
57.5°	854.9	785.3	689.1	605.5	549.1	506.0	484.7	469.2	457.5	440.9	422.3
60°	768.5	719.7	633.5	554.0	502.1	461.1	441.9	428.9	418.0	404.0	389.4
62.5°	680.8	645.3	570.3	502.1	454.3	420.0	402.0	390.3	377.7	368.3	354.1
65°	563.4	531.7	479.8	426.3	382.2	354.6	341.7	331.3	323.5	313.1	303.2
67.5°	438.2	425.4	389.5	352.7	321.0	296.5	285.3	278.0	268.7	262.4	255.7
70°	361.4	355.2	329.7	305.3	275.7	259.1	248.7	245.6	234.2	228.0	223.3
72.5°	293.3	290.4	275.7	258.8	237.9	223.4	213.8	210.3	203.0	198.0	195.0
75°	200.9	202.0	199.4	188.5	180.7	171.4	163.0	161.0	155.8	151.6	149.0
77.5°	127.1	132.4	132.6	132.1	129.0	123.3	119.8	118.3	113.2	111.6	111.0
80°	87.2	92.9	98.1	97.6	96.6	95.0	92.4	90.9	88.3	86.7	85.7
82.5°	58.2	63.5	67.8	70.6	70.4	68.9	67.1	66.4	65.8	64.7	64.5
85°	27.5	28.6	30.1	33.8	36.3	36.9	36.3	35.8	34.3	34.8	35.3
87.5°	11.0	10.8	11.1	10.9	10.3	12.2	13.2	13.4	12.8	12.2	11.5
90°	7.4	6.5	5.6	4.6	3.6	2.6	1.6	0.6	1.6	2.6	3.6
92.5°	7.6	6.8	6.0	5.9	6.7	7.4	8.1	8.8	8.1	7.4	6.7
95°	18.8	23.6	28.4	31.0	31.4	31.8	32.1	32.5	32.1	31.8	31.4
97.5°	47.1	56.7	66.2	70.6	69.9	69.3	68.6	67.9	68.6	69.3	69.9
100°	98.3	97.8	97.2	96.8	96.4	96.0	95.7	95.3	95.7	96.0	96.4
102.5°	126.1	125.7	125.4	125.0	124.6	124.1	123.6	123.1	123.6	124.1	124.6
105°	170.0	170.0	170.0	169.8	169.3	168.8	168.2	167.7	168.2	168.8	169.3
107.5°	214.7	214.4	214.2	214.1	214.1	214.1	214.1	214.1	214.1	214.1	214.1
110°	244.8	244.6	244.3	244.2	244.2	244.2	244.2	244.2	244.2	244.2	244.2





TEST NUMBER: P333556

CATALOG NUMBER: S125RDIP-S850D590U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	274.2	274.1	273.9	273.7	273.4	273.1	272.8	272.5	272.8	273.1	273.4
115°	318.1	318.0	317.9	317.5	316.8	316.2	315.6	314.9	315.6	316.2	316.8
117.5°	360.0	359.5	359.0	358.8	358.8	358.8	358.8	358.9	358.8	358.8	358.8
120°	386.6	386.3	385.9	385.7	385.9	386.0	386.1	386.3	386.1	386.0	385.9
122.5°	413.1	412.9	412.7	412.4	411.9	411.4	410.9	410.4	410.9	411.4	411.9
125°	451.9	451.9	451.9	451.4	450.5	449.6	448.8	447.9	448.8	449.6	450.5
127.5°	486.3	486.3	486.4	486.1	485.5	484.9	484.2	483.6	484.2	484.9	485.5
130°	508.7	508.5	508.4	508.0	507.4	506.8	506.1	505.5	506.1	506.8	507.4
132.5°	530.0	530.3	530.6	530.3	529.6	528.9	528.1	527.4	528.1	528.9	529.6
135°	561.3	561.6	561.9	561.6	560.8	560.1	559.3	558.6	559.3	560.1	560.8
137.5°	589.6	589.8	590.1	589.8	589.2	588.5	587.9	587.2	587.9	588.5	589.2
140°	606.7	606.9	607.0	606.9	606.7	606.4	606.2	605.9	606.2	606.4	606.7
142.5°	623.9	623.8	623.6	623.4	623.3	623.1	623.0	622.8	623.0	623.1	623.3
145°	648.7	648.7	648.7	648.6	648.3	648.1	647.8	647.6	647.8	648.1	648.3
147.5°	669.4	669.2	669.1	669.0	669.1	669.1	669.2	669.2	669.2	669.1	669.1
150°	682.4	682.2	681.9	681.9	682.2	682.4	682.7	682.9	682.7	682.4	682.2
152.5°	694.3	694.0	693.8	693.9	694.5	695.1	695.6	696.2	695.6	695.1	694.5
155°	710.4	710.1	709.9	710.1	710.9	711.7	712.4	713.2	712.4	711.7	710.9
157.5°	724.3	724.3	724.3	724.5	724.9	725.4	725.8	726.3	725.8	725.4	724.9
160°	732.3	732.2	732.1	732.4	733.1	733.9	734.7	735.4	734.7	733.9	733.1
162.5°	739.6	739.5	739.4	739.7	740.4	741.2	742.0	742.7	742.0	741.2	740.4
165°	749.4	749.3	749.2	749.5	750.3	751.0	751.8	752.5	751.8	751.0	750.3
167.5°	756.6	756.5	756.4	756.7	757.5	758.3	759.1	759.8	759.1	758.3	757.5
170°	760.3	760.1	760.0	760.4	761.3	762.2	763.1	764.0	763.1	762.2	761.3
172.5°	763.3	763.0	762.8	763.1	764.0	764.9	765.8	766.7	765.8	764.9	764.0
175°	766.6	766.4	766.3	766.6	767.4	768.1	768.9	769.7	768.9	768.1	767.4
177.5°	768.5	768.4	768.3	768.6	769.2	769.8	770.4	771.0	770.4	769.8	769.2
180°	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7



TEST NUMBER: P333556

CATALOG NUMBER: S125RDIP-S850D590U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1243.7	1237.9	1233.7	1225.4	1219.6	1217.1	1212.6	1211.3	1215.9	1212.6	1212.1
5°	1206.7	1191.7	1179.7	1167.8	1154.8	1146.5	1134.0	1132.0	1128.8	1124.2	1123.1
7.5°	1162.4	1142.8	1127.4	1107.7	1090.5	1076.7	1061.1	1053.8	1049.7	1043.7	1035.6
10°	1132.5	1109.1	1088.3	1068.6	1047.3	1030.2	1014.6	1002.7	994.9	987.6	984.5
12.5°	1103.0	1079.2	1052.6	1028.7	1005.0	985.7	968.5	960.7	952.1	943.6	936.3
15°	1057.2	1025.5	996.4	968.9	948.7	927.9	911.3	899.9	886.9	883.2	869.2
17.5°	1008.6	977.5	943.5	914.5	891.0	868.2	849.9	836.9	827.2	813.8	807.3
20°	978.3	941.4	908.2	881.7	855.7	828.7	810.0	799.1	789.8	778.9	773.7
22.5°	945.9	909.8	875.8	844.7	818.3	791.8	778.5	767.1	756.5	746.5	739.6
25°	898.3	862.0	826.1	793.9	766.4	747.2	731.6	718.6	712.9	703.1	695.8
27.5°	851.3	812.6	775.4	743.4	721.8	702.8	690.0	679.7	669.4	660.8	654.5
30°	820.9	781.5	741.0	715.5	692.7	674.5	660.5	650.6	642.8	635.0	630.4
32.5°	790.6	749.9	714.0	686.4	664.8	649.2	634.7	625.3	617.1	608.5	603.0
35°	742.0	700.5	671.4	644.4	623.1	608.6	598.7	585.2	578.4	572.2	566.5
37.5°	696.8	658.2	626.7	603.1	584.6	570.1	557.4	550.1	541.8	536.2	531.4
40°	663.6	628.3	599.7	574.8	561.3	545.2	533.3	523.9	517.7	510.4	505.2
42.5°	633.7	600.9	573.1	550.7	533.9	520.3	508.8	499.4	491.5	486.3	482.0
45°	591.4	558.7	531.7	510.9	495.4	482.4	470.4	465.8	455.4	449.2	447.1
47.5°	547.7	518.4	492.4	473.2	457.3	445.0	433.8	424.2	418.5	412.4	409.1
50°	518.2	490.2	465.8	447.1	431.5	418.0	407.6	401.4	393.6	387.9	383.7
52.5°	488.7	462.8	438.4	420.5	407.0	393.5	381.9	375.6	368.3	364.6	361.7
55°	446.6	419.0	398.3	380.6	366.6	354.1	343.2	337.0	332.3	328.7	327.6
57.5°	398.8	377.0	357.7	341.8	327.2	315.5	305.9	300.0	295.9	295.3	292.2
60°	367.6	347.9	330.2	313.1	300.6	289.7	281.4	274.7	270.5	270.0	269.0
62.5°	336.5	317.6	301.2	286.1	274.9	264.4	256.5	248.9	246.4	243.8	241.6
65°	290.3	273.1	259.6	247.7	235.7	226.9	219.1	214.4	208.7	205.6	199.9
67.5°	244.9	231.6	218.6	208.5	199.2	190.8	184.3	177.4	173.5	171.0	166.9
70°	215.0	204.6	191.6	180.7	173.4	166.7	161.5	153.7	151.1	149.0	146.9
72.5°	186.7	177.6	166.7	157.9	150.6	144.2	138.2	134.6	132.0	129.9	128.7
75°	146.9	138.1	128.8	122.5	117.4	112.2	109.0	106.4	105.4	104.9	102.8
77.5°	107.9	103.2	95.7	90.8	87.3	85.3	82.5	81.1	81.0	78.7	78.0
80°	82.6	80.0	73.7	71.7	69.1	67.0	65.4	62.8	60.2	59.2	57.6
82.5°	61.4	58.8	56.3	53.0	50.8	49.5	48.0	47.0	47.4	45.9	45.2
85°	32.7	30.1	29.1	28.6	27.5	28.6	28.0	27.5	27.0	26.5	27.0
87.5°	11.3	11.5	11.3	12.3	11.2	11.8	11.9	11.6	11.8	11.9	11.6
90°	4.6	5.6	6.5	7.4	8.2	9.1	9.8	10.4	11.0	11.7	12.2
92.5°	5.9	6.0	6.8	7.6	8.3	9.1	9.8	10.4	11.0	11.7	12.1
95°	31.0	28.4	23.6	18.8	13.9	9.1	9.8	10.4	11.0	11.7	12.0
97.5°	70.6	66.2	56.7	47.1	37.6	28.1	24.5	20.9	17.3	13.8	12.0
100°	96.8	97.2	97.8	98.3	98.8	99.3	80.4	61.5	42.6	23.7	14.0
102.5°	125.0	125.4	125.7	126.1	126.4	126.7	123.1	119.5	115.9	112.4	106.3
105°	169.8	170.0	170.0	170.0	170.0	170.0	170.0	170.0	170.0	170.0	170.0
107.5°	214.1	214.2	214.4	214.7	215.0	215.2	215.2	215.3	215.3	215.3	215.1
110°	244.2	244.3	244.6	244.8	245.1	245.3	245.0	244.6	244.2	243.8	243.7



TEST NUMBER: P333556

CATALOG NUMBER: S125RDIP-S850D590U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	273.7	273.9	274.1	274.2	274.4	274.5	274.1	273.6	273.1	272.6	272.3
115°	317.5	317.9	318.0	318.1	318.2	318.4	317.9	317.3	316.8	316.3	315.7
117.5°	358.8	359.0	359.5	360.0	360.4	360.9	360.3	359.6	358.9	358.3	357.8
120°	385.7	385.9	386.3	386.6	387.0	387.4	387.1	386.9	386.6	386.4	385.9
122.5°	412.4	412.7	412.9	413.1	413.2	413.4	413.2	412.9	412.7	412.4	411.9
125°	451.4	451.9	451.9	451.9	451.9	451.9	451.4	450.9	450.3	449.8	449.4
127.5°	486.1	486.4	486.3	486.3	486.2	486.1	485.8	485.5	485.3	485.0	484.4
130°	508.0	508.4	508.5	508.7	508.8	508.9	508.5	508.2	507.8	507.4	506.9
132.5°	530.3	530.6	530.3	530.0	529.7	529.5	529.4	529.3	529.2	529.2	528.8
135°	561.6	561.9	561.6	561.3	561.1	560.8	560.6	560.3	560.1	559.8	559.3
137.5°	589.8	590.1	589.8	589.6	589.4	589.1	589.2	589.2	589.3	589.3	589.0
140°	606.9	607.0	606.9	606.7	606.6	606.5	606.7	607.0	607.2	607.5	607.2
142.5°	623.4	623.6	623.8	623.9	624.1	624.3	624.3	624.4	624.4	624.5	624.1
145°	648.6	648.7	648.7	648.7	648.7	648.7	648.8	649.0	649.1	649.2	648.9
147.5°	669.0	669.1	669.2	669.4	669.5	669.7	669.9	670.0	670.2	670.3	669.9
150°	681.9	681.9	682.2	682.4	682.7	682.9	683.2	683.4	683.7	683.9	683.6
152.5°	693.9	693.8	694.0	694.3	694.5	694.8	695.1	695.3	695.6	695.8	695.5
155°	710.1	709.9	710.1	710.4	710.6	710.9	711.3	711.7	712.0	712.4	712.1
157.5°	724.5	724.3	724.3	724.3	724.3	724.4	724.8	725.2	725.6	726.0	725.7
160°	732.4	732.1	732.2	732.3	732.4	732.6	733.1	733.6	734.1	734.6	734.3
162.5°	739.7	739.4	739.5	739.6	739.7	739.9	740.6	741.3	742.0	742.7	742.5
165°	749.5	749.2	749.3	749.4	749.6	749.7	750.4	751.2	752.0	752.7	752.6
167.5°	756.7	756.4	756.5	756.6	756.7	756.9	757.8	758.7	759.6	760.5	760.4
170°	760.4	760.0	760.1	760.3	760.4	760.5	761.5	762.6	763.6	764.6	764.5
172.5°	763.1	762.8	763.0	763.3	763.5	763.7	764.6	765.5	766.5	767.4	767.3
175°	766.6	766.3	766.4	766.6	766.7	766.8	767.8	768.8	769.8	770.9	770.8
177.5°	768.6	768.3	768.4	768.5	768.6	768.7	769.5	770.2	770.9	771.6	771.5
180°	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7



TEST NUMBER: P333556

CATALOG NUMBER: S125RDIP-S850D590U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1211.7	1207.2	1205.9	1207.6	1205.9	1207.2	1211.7	1212.1	1212.6	1215.9	1211.3
5°	1117.9	1112.8	1115.3	1114.3	1115.3	1112.8	1117.9	1123.1	1124.2	1128.8	1132.0
7.5°	1035.5	1029.0	1022.2	1024.4	1022.2	1029.0	1035.5	1035.6	1043.7	1049.7	1053.8
10°	977.7	972.6	969.4	972.0	969.4	972.6	977.7	984.5	987.6	994.9	1002.7
12.5°	929.1	926.0	923.3	922.2	923.3	926.0	929.1	936.3	943.6	952.1	960.7
15°	863.0	856.8	854.2	847.4	854.2	856.8	863.0	869.2	883.2	886.9	899.9
17.5°	802.0	800.0	793.2	790.3	793.2	800.0	802.0	807.3	813.8	827.2	836.9
20°	765.9	763.8	757.1	761.2	757.1	763.8	765.9	773.7	778.9	789.8	799.1
22.5°	736.0	731.4	729.2	728.0	729.2	731.4	736.0	739.6	746.5	756.5	767.1
25°	693.7	687.0	684.4	681.3	684.4	687.0	693.7	695.8	703.1	712.9	718.6
27.5°	651.6	647.9	644.5	643.7	644.5	647.9	651.6	654.5	660.8	669.4	679.7
30°	624.1	620.5	617.9	617.9	617.9	620.5	624.1	630.4	635.0	642.8	650.6
32.5°	599.6	596.8	594.2	593.8	594.2	596.8	599.6	603.0	608.5	617.1	625.3
35°	563.9	559.8	558.7	555.6	558.7	559.8	563.9	566.5	572.2	578.4	585.2
37.5°	526.8	523.4	523.3	523.0	523.3	523.4	526.8	531.4	536.2	541.8	550.1
40°	503.2	500.6	500.0	496.4	500.0	500.6	503.2	505.2	510.4	517.7	523.9
42.5°	477.8	476.5	474.7	473.1	474.7	476.5	477.8	482.0	486.3	491.5	499.4
45°	443.4	439.8	439.8	437.2	439.8	439.8	443.4	447.1	449.2	455.4	465.8
47.5°	407.9	405.1	405.4	402.7	405.4	405.1	407.9	409.1	412.4	418.5	424.2
50°	384.2	382.7	382.2	381.1	382.2	382.7	384.2	383.7	387.9	393.6	401.4
52.5°	360.6	359.8	361.8	359.5	361.8	359.8	360.6	361.7	364.6	368.3	375.6
55°	328.7	327.1	330.2	327.1	330.2	327.1	328.7	327.6	328.7	332.3	337.0
57.5°	292.0	290.6	293.4	291.8	293.4	290.6	292.0	292.2	295.3	295.9	300.0
60°	267.9	264.8	266.4	266.9	266.4	264.8	267.9	269.0	270.0	270.5	274.7
62.5°	239.3	237.4	238.5	236.2	238.5	237.4	239.3	241.6	243.8	246.4	248.9
65°	198.9	197.3	195.2	194.2	195.2	197.3	198.9	199.9	205.6	208.7	214.4
67.5°	167.1	163.4	163.3	164.1	163.3	163.4	167.1	166.9	171.0	173.5	177.4
70°	143.8	143.8	143.3	143.3	143.3	143.8	143.8	146.9	149.0	151.1	153.7
72.5°	127.6	127.2	126.3	125.9	126.3	127.2	127.6	128.7	129.9	132.0	134.6
75°	102.8	103.3	102.3	101.8	102.3	103.3	102.8	102.8	104.9	105.4	106.4
77.5°	75.9	73.7	74.9	73.7	74.9	73.7	75.9	78.0	78.7	81.0	81.1
80°	57.6	57.1	58.7	57.1	58.7	57.1	57.6	57.6	59.2	60.2	62.8
82.5°	45.6	45.1	45.8	44.7	45.8	45.1	45.6	45.2	45.9	47.4	47.0
85°	27.5	27.0	26.5	27.0	26.5	27.0	27.5	27.0	26.5	27.0	27.5
87.5°	12.1	11.7	11.8	11.9	11.8	11.7	12.1	11.6	11.9	11.8	11.6
90°	12.6	12.9	13.3	13.7	13.3	12.9	12.6	12.2	11.7	11.0	10.4
92.5°	12.2	12.4	12.6	12.8	12.6	12.4	12.2	12.1	11.7	11.0	10.4
95°	12.0	12.0	12.0	12.0	12.0	12.0	12.0	12.0	11.7	11.0	10.4
97.5°	12.0	12.0	12.0	12.0	12.0	12.0	12.0	12.0	13.8	17.3	20.9
100°	13.5	13.0	12.5	12.0	12.5	13.0	13.5	14.0	23.7	42.6	61.5
102.5°	97.6	89.0	80.4	71.8	80.4	89.0	97.6	106.3	112.4	115.9	119.5
105°	169.8	169.7	169.6	169.4	169.6	169.7	169.8	170.0	170.0	170.0	170.0
107.5°	214.8	214.4	214.0	213.6	214.0	214.4	214.8	215.1	215.3	215.3	215.3
110°	243.8	243.9	244.1	244.2	244.1	243.9	243.8	243.7	243.8	244.2	244.6



TEST NUMBER: P333556

CATALOG NUMBER: S125RDIP-S850D590U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	272.1	271.9	271.8	271.6	271.8	271.9	272.1	272.3	272.6	273.1	273.6
115°	314.9	314.2	313.4	312.7	313.4	314.2	314.9	315.7	316.3	316.8	317.3
117.5°	357.5	357.1	356.8	356.5	356.8	357.1	357.5	357.8	358.3	358.9	359.6
120°	385.3	384.7	384.0	383.4	384.0	384.7	385.3	385.9	386.4	386.6	386.9
122.5°	411.2	410.4	409.7	409.0	409.7	410.4	411.2	411.9	412.4	412.7	412.9
125°	449.0	448.6	448.3	447.9	448.3	448.6	449.0	449.4	449.8	450.3	450.9
127.5°	483.4	482.5	481.6	480.6	481.6	482.5	483.4	484.4	485.0	485.3	485.5
130°	506.3	505.6	505.0	504.4	505.0	505.6	506.3	506.9	507.4	507.8	508.2
132.5°	528.2	527.5	526.9	526.3	526.9	527.5	528.2	528.8	529.2	529.2	529.3
135°	558.6	557.8	557.0	556.3	557.0	557.8	558.6	559.3	559.8	560.1	560.3
137.5°	588.4	587.7	587.1	586.4	587.1	587.7	588.4	589.0	589.3	589.3	589.2
140°	606.5	605.7	605.0	604.2	605.0	605.7	606.5	607.2	607.5	607.2	607.0
142.5°	623.4	622.6	621.8	621.1	621.8	622.6	623.4	624.1	624.5	624.4	624.4
145°	648.1	647.4	646.6	645.8	646.6	647.4	648.1	648.9	649.2	649.1	649.0
147.5°	669.0	668.1	667.2	666.3	667.2	668.1	669.0	669.9	670.3	670.2	670.0
150°	682.6	681.5	680.5	679.5	680.5	681.5	682.6	683.6	683.9	683.7	683.4
152.5°	694.6	693.7	692.7	691.8	692.7	693.7	694.6	695.5	695.8	695.6	695.3
155°	711.1	710.1	709.1	708.0	709.1	710.1	711.1	712.1	712.4	712.0	711.7
157.5°	724.7	723.6	722.6	721.6	722.6	723.6	724.7	725.7	726.0	725.6	725.2
160°	733.3	732.3	731.3	730.3	731.3	732.3	733.3	734.3	734.6	734.1	733.6
162.5°	741.4	740.3	739.2	738.0	739.2	740.3	741.4	742.5	742.7	742.0	741.3
165°	751.6	750.6	749.6	748.5	749.6	750.6	751.6	752.6	752.7	752.0	751.2
167.5°	759.3	758.1	757.0	755.8	757.0	758.1	759.3	760.4	760.5	759.6	758.7
170°	763.4	762.2	761.1	760.0	761.1	762.2	763.4	764.5	764.6	763.6	762.6
172.5°	766.1	765.0	763.8	762.7	763.8	765.0	766.1	767.3	767.4	766.5	765.5
175°	769.7	768.5	767.4	766.2	767.4	768.5	769.7	770.8	770.9	769.8	768.8
177.5°	770.7	769.9	769.1	768.3	769.1	769.9	770.7	771.5	771.6	770.9	770.2
180°	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7



TEST NUMBER: P333556

CATALOG NUMBER: S125RDIP-S850D590U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1212.6	1217.1	1219.6	1225.4	1233.7	1237.9	1243.7	1247.9	1253.7	1260.7	1266.6
5°	1134.0	1146.5	1154.8	1167.8	1179.7	1191.7	1206.7	1217.6	1232.2	1248.8	1261.8
7.5°	1061.1	1076.7	1090.5	1107.7	1127.4	1142.8	1162.4	1182.4	1205.2	1228.8	1251.0
10°	1014.6	1030.2	1047.3	1068.6	1088.3	1109.1	1132.5	1155.8	1184.4	1210.9	1241.0
12.5°	968.5	985.7	1005.0	1028.7	1052.6	1079.2	1103.0	1129.3	1159.9	1194.3	1226.5
15°	911.3	927.9	948.7	968.9	996.4	1025.5	1057.2	1092.0	1126.3	1164.7	1204.7
17.5°	849.9	868.2	891.0	914.5	943.5	977.5	1008.6	1046.7	1085.2	1130.0	1177.0
20°	810.0	828.7	855.7	881.7	908.2	941.4	978.3	1017.2	1058.2	1105.5	1157.9
22.5°	778.5	791.8	818.3	844.7	875.8	909.8	945.9	986.5	1031.2	1080.1	1135.1
25°	731.6	747.2	766.4	793.9	826.1	862.0	898.3	941.4	990.2	1040.1	1098.7
27.5°	690.0	702.8	721.8	743.4	775.4	812.6	851.3	896.2	946.3	997.1	1058.7
30°	660.5	674.5	692.7	715.5	741.0	781.5	820.9	865.1	916.0	968.4	1031.7
32.5°	634.7	649.2	664.8	686.4	714.0	749.9	790.6	833.9	885.6	939.7	1001.4
35°	598.7	608.6	623.1	644.4	671.4	700.5	742.0	787.7	838.1	894.1	955.9
37.5°	557.4	570.1	584.6	603.1	626.7	658.2	696.8	743.0	789.8	843.5	899.9
40°	533.3	545.2	561.3	574.8	599.7	628.3	663.6	711.9	758.6	809.0	860.4
42.5°	508.8	520.3	533.9	550.7	573.1	600.9	633.7	678.7	728.7	776.2	819.3
45°	470.4	482.4	495.4	510.9	531.7	558.7	591.4	632.4	676.1	719.7	752.4
47.5°	433.8	445.0	457.3	473.2	492.4	518.4	547.7	583.9	626.3	663.4	686.8
50°	407.6	418.0	431.5	447.1	465.8	490.2	518.2	554.0	589.3	623.1	644.4
52.5°	381.9	393.5	407.0	420.5	438.4	462.8	488.7	519.6	553.2	580.7	598.3
55°	343.2	354.1	366.6	380.6	398.3	419.0	446.6	471.0	497.4	520.8	531.2
57.5°	305.9	315.5	327.2	341.8	357.7	377.0	398.8	422.3	440.9	457.5	469.2
60°	281.4	289.7	300.6	313.1	330.2	347.9	367.6	389.4	404.0	418.0	428.9
62.5°	256.5	264.4	274.9	286.1	301.2	317.6	336.5	354.1	368.3	377.7	390.3
65°	219.1	226.9	235.7	247.7	259.6	273.1	290.3	303.2	313.1	323.5	331.3
67.5°	184.3	190.8	199.2	208.5	218.6	231.6	244.9	255.7	262.4	268.7	278.0
70°	161.5	166.7	173.4	180.7	191.6	204.6	215.0	223.3	228.0	234.2	245.6
72.5°	138.2	144.2	150.6	157.9	166.7	177.6	186.7	195.0	198.0	203.0	210.3
75°	109.0	112.2	117.4	122.5	128.8	138.1	146.9	149.0	151.6	155.8	161.0
77.5°	82.5	85.3	87.3	90.8	95.7	103.2	107.9	111.0	111.6	113.2	118.3
80°	65.4	67.0	69.1	71.7	73.7	80.0	82.6	85.7	86.7	88.3	90.9
82.5°	48.0	49.5	50.8	53.0	56.3	58.8	61.4	64.5	64.7	65.8	66.4
85°	28.0	28.6	27.5	28.6	29.1	30.1	32.7	35.3	34.8	34.3	35.8
87.5°	11.9	11.8	11.2	12.3	11.3	11.5	11.3	11.5	12.2	12.8	13.4
90°	9.8	9.1	8.2	7.4	6.5	5.6	4.6	3.6	2.6	1.6	0.6
92.5°	9.8	9.1	8.3	7.6	6.8	6.0	5.9	6.7	7.4	8.1	8.8
95°	9.8	9.1	13.9	18.8	23.6	28.4	31.0	31.4	31.8	32.1	32.5
97.5°	24.5	28.1	37.6	47.1	56.7	66.2	70.6	69.9	69.3	68.6	67.9
100°	80.4	99.3	98.8	98.3	97.8	97.2	96.8	96.4	96.0	95.7	95.3
102.5°	123.1	126.7	126.4	126.1	125.7	125.4	125.0	124.6	124.1	123.6	123.1
105°	170.0	170.0	170.0	170.0	170.0	170.0	169.8	169.3	168.8	168.2	167.7
107.5°	215.2	215.2	215.0	214.7	214.4	214.2	214.1	214.1	214.1	214.1	214.1
110°	245.0	245.3	245.1	244.8	244.6	244.3	244.2	244.2	244.2	244.2	244.2



TEST NUMBER: P333556

CATALOG NUMBER: S125RDIP-S850D590U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	274.1	274.5	274.4	274.2	274.1	273.9	273.7	273.4	273.1	272.8	272.5
115°	317.9	318.4	318.2	318.1	318.0	317.9	317.5	316.8	316.2	315.6	314.9
117.5°	360.3	360.9	360.4	360.0	359.5	359.0	358.8	358.8	358.8	358.8	358.9
120°	387.1	387.4	387.0	386.6	386.3	385.9	385.7	385.9	386.0	386.1	386.3
122.5°	413.2	413.4	413.2	413.1	412.9	412.7	412.4	411.9	411.4	410.9	410.4
125°	451.4	451.9	451.9	451.9	451.9	451.9	451.4	450.5	449.6	448.8	447.9
127.5°	485.8	486.1	486.2	486.3	486.3	486.4	486.1	485.5	484.9	484.2	483.6
130°	508.5	508.9	508.8	508.7	508.5	508.4	508.0	507.4	506.8	506.1	505.5
132.5°	529.4	529.5	529.7	530.0	530.3	530.6	530.3	529.6	528.9	528.1	527.4
135°	560.6	560.8	561.1	561.3	561.6	561.9	561.6	560.8	560.1	559.3	558.6
137.5°	589.2	589.1	589.4	589.6	589.8	590.1	589.8	589.2	588.5	587.9	587.2
140°	606.7	606.5	606.6	606.7	606.9	607.0	606.9	606.7	606.4	606.2	605.9
142.5°	624.3	624.3	624.1	623.9	623.8	623.6	623.4	623.3	623.1	623.0	622.8
145°	648.8	648.7	648.7	648.7	648.7	648.7	648.6	648.3	648.1	647.8	647.6
147.5°	669.9	669.7	669.5	669.4	669.2	669.1	669.0	669.1	669.1	669.2	669.2
150°	683.2	682.9	682.7	682.4	682.2	681.9	681.9	682.2	682.4	682.7	682.9
152.5°	695.1	694.8	694.5	694.3	694.0	693.8	693.9	694.5	695.1	695.6	696.2
155°	711.3	710.9	710.6	710.4	710.1	709.9	710.1	710.9	711.7	712.4	713.2
157.5°	724.8	724.4	724.3	724.3	724.3	724.3	724.5	724.9	725.4	725.8	726.3
160°	733.1	732.6	732.4	732.3	732.2	732.1	732.4	733.1	733.9	734.7	735.4
162.5°	740.6	739.9	739.7	739.6	739.5	739.4	739.7	740.4	741.2	742.0	742.7
165°	750.4	749.7	749.6	749.4	749.3	749.2	749.5	750.3	751.0	751.8	752.5
167.5°	757.8	756.9	756.7	756.6	756.5	756.4	756.7	757.5	758.3	759.1	759.8
170°	761.5	760.5	760.4	760.3	760.1	760.0	760.4	761.3	762.2	763.1	764.0
172.5°	764.6	763.7	763.5	763.3	763.0	762.8	763.1	764.0	764.9	765.8	766.7
175°	767.8	766.8	766.7	766.6	766.4	766.3	766.6	767.4	768.1	768.9	769.7
177.5°	769.5	768.7	768.6	768.5	768.4	768.3	768.6	769.2	769.8	770.4	771.0
180°	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7



TEST NUMBER: P333556

CATALOG NUMBER: S125RDIP-S850D590U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1271.1	1274.9	1280.3	1286.5	1291.5	1296.9	1299.8	1299.8	1302.3	1307.7	1314.7
5°	1274.8	1288.3	1301.2	1317.9	1330.8	1345.9	1357.3	1368.2	1378.1	1390.5	1403.5
7.5°	1273.7	1296.1	1319.5	1345.7	1374.6	1397.5	1421.1	1439.6	1457.8	1481.7	1500.5
10°	1269.6	1298.6	1330.3	1363.5	1399.9	1431.6	1460.1	1486.1	1511.0	1537.0	1560.3
12.5°	1262.1	1299.1	1337.8	1377.7	1423.6	1459.8	1496.7	1524.3	1553.4	1581.8	1610.6
15°	1250.9	1294.5	1341.2	1396.8	1452.9	1493.4	1529.7	1565.5	1592.5	1624.7	1652.3
17.5°	1227.7	1283.9	1342.7	1403.4	1457.3	1504.4	1542.5	1576.5	1605.3	1640.7	1678.1
20°	1214.0	1274.8	1336.0	1400.9	1452.3	1500.6	1537.5	1572.8	1608.6	1654.8	1700.5
22.5°	1194.9	1259.8	1324.8	1386.4	1440.7	1487.3	1525.4	1568.7	1615.7	1668.1	1723.4
25°	1164.7	1231.7	1296.0	1354.7	1407.7	1455.5	1507.4	1565.5	1622.7	1691.7	1771.2
27.5°	1126.4	1190.9	1248.4	1310.4	1363.0	1423.8	1488.6	1551.6	1634.0	1729.0	1828.2
30°	1097.7	1159.0	1213.5	1272.2	1331.9	1398.9	1471.6	1545.8	1643.9	1755.6	1873.5
32.5°	1064.5	1119.9	1174.0	1230.6	1299.5	1373.1	1450.4	1541.2	1658.5	1785.5	1907.5
35°	1006.8	1056.7	1109.1	1171.9	1245.2	1325.1	1423.8	1534.4	1676.1	1812.7	1922.3
37.5°	946.4	985.7	1038.4	1104.7	1184.4	1276.9	1388.9	1523.3	1668.9	1791.4	1838.0
40°	899.9	936.7	992.3	1061.9	1140.8	1242.0	1367.7	1505.8	1652.3	1737.4	1733.8
42.5°	853.7	891.0	944.5	1014.5	1096.8	1210.1	1339.5	1483.0	1606.6	1639.0	1571.4
45°	783.0	817.8	870.3	940.9	1029.2	1148.1	1284.1	1421.7	1500.6	1448.2	1314.2
47.5°	711.0	744.7	793.4	862.6	958.9	1083.4	1212.0	1324.9	1336.0	1223.4	1062.7
50°	663.6	695.3	741.5	815.2	908.7	1030.2	1154.3	1243.1	1215.6	1078.0	912.3
52.5°	617.5	647.9	691.2	760.8	856.3	975.4	1086.2	1155.8	1092.2	945.9	796.8
55°	549.4	578.4	622.1	685.9	772.6	881.7	978.8	1004.2	910.8	763.3	642.8
57.5°	484.7	506.0	549.1	605.5	689.1	785.3	854.9	850.3	747.2	614.4	528.0
60°	441.9	461.1	502.1	554.0	633.5	719.7	768.5	747.7	643.3	533.8	450.7
62.5°	402.0	420.0	454.3	502.1	570.3	645.3	680.8	652.2	553.6	457.4	391.3
65°	341.7	354.6	382.2	426.3	479.8	531.7	563.4	521.3	434.1	361.4	311.5
67.5°	285.3	296.5	321.0	352.7	389.5	425.4	438.2	398.8	331.0	282.0	246.9
70°	248.7	259.1	275.7	305.3	329.7	355.2	361.4	326.1	269.5	232.1	210.3
72.5°	213.8	223.4	237.9	258.8	275.7	290.4	293.3	260.5	217.1	191.4	174.6
75°	163.0	171.4	180.7	188.5	199.4	202.0	200.9	175.5	152.1	135.0	125.7
77.5°	119.8	123.3	129.0	132.1	132.6	132.4	127.1	111.0	99.0	91.9	88.1
80°	92.4	95.0	96.6	97.6	98.1	92.9	87.2	77.4	73.2	69.1	64.4
82.5°	67.1	68.9	70.4	70.6	67.8	63.5	58.2	53.3	50.4	48.3	46.5
85°	36.3	36.9	36.3	33.8	30.1	28.6	27.5	26.5	26.0	25.4	25.4
87.5°	13.2	12.2	10.3	10.9	11.1	10.8	11.0	10.8	10.5	10.7	10.8
90°	1.6	2.6	3.6	4.6	5.6	6.5	7.4	8.2	9.1	9.8	10.4
92.5°	8.1	7.4	6.7	5.9	6.0	6.8	7.6	8.3	9.1	9.8	10.4
95°	32.1	31.8	31.4	31.0	28.4	23.6	18.8	13.9	9.1	9.8	10.4
97.5°	68.6	69.3	69.9	70.6	66.2	56.7	47.1	37.6	28.1	24.5	20.9
100°	95.7	96.0	96.4	96.8	97.2	97.8	98.3	98.8	99.3	80.4	61.5
102.5°	123.6	124.1	124.6	125.0	125.4	125.7	126.1	126.4	126.7	123.1	119.5
105°	168.2	168.8	169.3	169.8	170.0	170.0	170.0	170.0	170.0	170.0	170.0
107.5°	214.1	214.1	214.1	214.1	214.2	214.4	214.7	215.0	215.2	215.2	215.3
110°	244.2	244.2	244.2	244.2	244.3	244.6	244.8	245.1	245.3	245.0	244.6





TEST NUMBER: P333556

CATALOG NUMBER: S125RDIP-S850D590U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	272.8	273.1	273.4	273.7	273.9	274.1	274.2	274.4	274.5	274.1	273.6
115°	315.6	316.2	316.8	317.5	317.9	318.0	318.1	318.2	318.4	317.9	317.3
117.5°	358.8	358.8	358.8	358.8	359.0	359.5	360.0	360.4	360.9	360.3	359.6
120°	386.1	386.0	385.9	385.7	385.9	386.3	386.6	387.0	387.4	387.1	386.9
122.5°	410.9	411.4	411.9	412.4	412.7	412.9	413.1	413.2	413.4	413.2	412.9
125°	448.8	449.6	450.5	451.4	451.9	451.9	451.9	451.9	451.9	451.4	450.9
127.5°	484.2	484.9	485.5	486.1	486.4	486.3	486.3	486.2	486.1	485.8	485.5
130°	506.1	506.8	507.4	508.0	508.4	508.5	508.7	508.8	508.9	508.5	508.2
132.5°	528.1	528.9	529.6	530.3	530.6	530.3	530.0	529.7	529.5	529.4	529.3
135°	559.3	560.1	560.8	561.6	561.9	561.6	561.3	561.1	560.8	560.6	560.3
137.5°	587.9	588.5	589.2	589.8	590.1	589.8	589.6	589.4	589.1	589.2	589.2
140°	606.2	606.4	606.7	606.9	607.0	606.9	606.7	606.6	606.5	606.7	607.0
142.5°	623.0	623.1	623.3	623.4	623.6	623.8	623.9	624.1	624.3	624.3	624.4
145°	647.8	648.1	648.3	648.6	648.7	648.7	648.7	648.7	648.7	648.8	649.0
147.5°	669.2	669.1	669.1	669.0	669.1	669.2	669.4	669.5	669.7	669.9	670.0
150°	682.7	682.4	682.2	681.9	681.9	682.2	682.4	682.7	682.9	683.2	683.4
152.5°	695.6	695.1	694.5	693.9	693.8	694.0	694.3	694.5	694.8	695.1	695.3
155°	712.4	711.7	710.9	710.1	709.9	710.1	710.4	710.6	710.9	711.3	711.7
157.5°	725.8	725.4	724.9	724.5	724.3	724.3	724.3	724.3	724.4	724.8	725.2
160°	734.7	733.9	733.1	732.4	732.1	732.2	732.3	732.4	732.6	733.1	733.6
162.5°	742.0	741.2	740.4	739.7	739.4	739.5	739.6	739.7	739.9	740.6	741.3
165°	751.8	751.0	750.3	749.5	749.2	749.3	749.4	749.6	749.7	750.4	751.2
167.5°	759.1	758.3	757.5	756.7	756.4	756.5	756.6	756.7	756.9	757.8	758.7
170°	763.1	762.2	761.3	760.4	760.0	760.1	760.3	760.4	760.5	761.5	762.6
172.5°	765.8	764.9	764.0	763.1	762.8	763.0	763.3	763.5	763.7	764.6	765.5
175°	768.9	768.1	767.4	766.6	766.3	766.4	766.6	766.7	766.8	767.8	768.8
177.5°	770.4	769.8	769.2	768.6	768.3	768.4	768.5	768.6	768.7	769.5	770.2
180°	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7



TEST NUMBER: P333556

CATALOG NUMBER: S125RDIP-S850D590U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1320.1	1320.1	1327.2	1326.8	1331.4	1329.7	1330.5
5°	1419.1	1427.9	1435.7	1440.9	1448.7	1450.8	1449.7
7.5°	1521.7	1541.3	1550.9	1564.0	1566.4	1573.2	1572.5
10°	1585.3	1604.5	1619.0	1630.4	1636.2	1643.4	1643.9
12.5°	1635.1	1651.4	1664.3	1674.9	1681.8	1684.1	1685.5
15°	1674.1	1692.2	1707.3	1722.3	1731.2	1737.9	1741.6
17.5°	1713.3	1741.4	1767.9	1788.4	1800.7	1811.0	1810.9
20°	1743.6	1775.8	1809.1	1832.4	1856.3	1866.7	1868.3
22.5°	1776.0	1825.3	1868.1	1904.3	1935.7	1946.5	1950.5
25°	1843.3	1907.7	1973.7	2024.6	2060.9	2082.2	2085.3
27.5°	1924.6	2011.8	2081.2	2128.1	2158.3	2174.1	2177.5
30°	1982.0	2062.5	2124.8	2160.1	2174.1	2176.2	2168.4
32.5°	2007.7	2067.9	2092.8	2090.7	2063.2	2044.9	2037.9
35°	1976.3	1963.8	1903.0	1830.4	1774.8	1739.5	1730.1
37.5°	1798.5	1691.0	1579.2	1469.4	1410.9	1381.2	1330.1
40°	1623.2	1470.0	1353.7	1261.3	1195.3	1142.3	1129.9
42.5°	1425.4	1267.3	1151.0	1071.8	1019.2	982.8	967.0
45°	1145.5	1009.4	913.4	852.6	812.1	785.6	773.7
47.5°	916.2	810.9	740.9	695.9	665.1	642.0	635.6
50°	790.3	706.2	647.0	609.1	585.7	568.1	560.8
52.5°	686.4	618.5	573.0	541.8	519.7	508.7	502.6
55°	566.5	507.8	475.1	450.2	437.7	428.9	424.7
57.5°	463.3	420.9	397.0	379.8	368.3	362.6	360.6
60°	405.5	372.3	350.5	337.0	329.2	321.9	319.9
62.5°	354.4	328.3	311.4	299.6	291.8	288.7	287.5
65°	285.6	268.5	256.0	248.7	242.5	241.5	240.9
67.5°	227.0	216.9	210.4	202.8	200.6	197.0	196.3
70°	194.2	187.4	179.7	177.1	174.5	170.8	171.4
72.5°	164.7	158.0	152.7	149.2	148.3	146.7	148.1
75°	120.5	118.4	116.3	113.7	112.7	112.7	112.2
77.5°	86.0	84.2	81.9	80.4	80.1	77.9	78.7
80°	62.3	59.7	58.7	59.2	57.6	57.1	57.1
82.5°	46.1	45.2	44.1	44.2	43.9	43.4	43.8
85°	25.4	24.9	24.9	24.4	24.4	23.9	23.9
87.5°	11.3	11.9	11.2	10.8	10.9	11.4	11.9
90°	11.0	11.7	12.2	12.6	12.9	13.3	13.7
92.5°	11.0	11.7	12.1	12.2	12.4	12.6	12.8
95°	11.0	11.7	12.0	12.0	12.0	12.0	12.0
97.5°	17.3	13.8	12.0	12.0	12.0	12.0	12.0
100°	42.6	23.7	14.0	13.5	13.0	12.5	12.0
102.5°	115.9	112.4	106.3	97.6	89.0	80.4	71.8
105°	170.0	170.0	170.0	169.8	169.7	169.6	169.4
107.5°	215.3	215.3	215.1	214.8	214.4	214.0	213.6
110°	244.2	243.8	243.7	243.8	243.9	244.1	244.2



TEST NUMBER: P333556

CATALOG NUMBER: S125RDIP-S850D590U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	273.1	272.6	272.3	272.1	271.9	271.8	271.6
115°	316.8	316.3	315.7	314.9	314.2	313.4	312.7
117.5°	358.9	358.3	357.8	357.5	357.1	356.8	356.5
120°	386.6	386.4	385.9	385.3	384.7	384.0	383.4
122.5°	412.7	412.4	411.9	411.2	410.4	409.7	409.0
125°	450.3	449.8	449.4	449.0	448.6	448.3	447.9
127.5°	485.3	485.0	484.4	483.4	482.5	481.6	480.6
130°	507.8	507.4	506.9	506.3	505.6	505.0	504.4
132.5°	529.2	529.2	528.8	528.2	527.5	526.9	526.3
135°	560.1	559.8	559.3	558.6	557.8	557.0	556.3
137.5°	589.3	589.3	589.0	588.4	587.7	587.1	586.4
140°	607.2	607.5	607.2	606.5	605.7	605.0	604.2
142.5°	624.4	624.5	624.1	623.4	622.6	621.8	621.1
145°	649.1	649.2	648.9	648.1	647.4	646.6	645.8
147.5°	670.2	670.3	669.9	669.0	668.1	667.2	666.3
150°	683.7	683.9	683.6	682.6	681.5	680.5	679.5
152.5°	695.6	695.8	695.5	694.6	693.7	692.7	691.8
155°	712.0	712.4	712.1	711.1	710.1	709.1	708.0
157.5°	725.6	726.0	725.7	724.7	723.6	722.6	721.6
160°	734.1	734.6	734.3	733.3	732.3	731.3	730.3
162.5°	742.0	742.7	742.5	741.4	740.3	739.2	738.0
165°	752.0	752.7	752.6	751.6	750.6	749.6	748.5
167.5°	759.6	760.5	760.4	759.3	758.1	757.0	755.8
170°	763.6	764.6	764.5	763.4	762.2	761.1	760.0
172.5°	766.5	767.4	767.3	766.1	765.0	763.8	762.7
175°	769.8	770.9	770.8	769.7	768.5	767.4	766.2
177.5°	770.9	771.6	771.5	770.7	769.9	769.1	768.3
180°	769.7	769.7	769.7	769.7	769.7	769.7	769.7

(END OF REPORT)