

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333627-927

Luminaire Tested: **S125RDIP-S1270D810U927-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333627-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1270D810U927-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6168.9 lumens
Efficiency: N/A
Efficacy: 101.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333627-927

CATALOG NUMBER: S125RDIP-S1270D810U927-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333627-927

CATALOG NUMBER: S125RDIP-S1270D810U927-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	63
1	101	97	93	89	94	91	87	84	80	77	75	70	68	66	60	59	58	53
2	92	85	79	73	86	80	74	70	70	66	62	61	58	56	53	51	49	45
3	84	75	67	61	79	70	64	59	62	57	53	55	51	47	48	45	42	38
4	77	66	58	52	72	63	55	50	55	50	45	49	44	41	43	39	36	33
5	71	59	51	45	66	56	49	43	50	44	39	44	39	36	39	35	32	29
6	66	53	45	39	61	50	43	38	45	39	34	40	35	31	35	31	28	26
7	61	48	40	35	57	46	38	33	41	35	31	36	31	28	32	28	25	23
8	56	44	36	31	53	42	35	30	37	31	27	33	28	25	30	26	23	20
9	53	40	33	28	49	38	31	27	34	29	25	31	26	22	27	23	21	18
10	49	37	30	25	46	35	28	24	32	26	22	28	24	20	25	21	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10561	10561	10561
5°	10585	10466	10529
10°	10506	10368	10368
15°	10380	10158	10075
20°	10221	9864	9745
25°	10033	9576	9365
30°	9801	9238	8944
35°	9563	8891	8472
40°	9340	8528	8008
45°	9070	8122	7501
50°	8799	7681	6974
55°	8483	7260	6411
60°	8169	6748	5807
65°	7795	6154	5115
70°	7370	5410	4409
75°	6780	4561	3666
80°	5973	3582	3080
85°	5039	2927	2749



TEST NUMBER: P333627-927

CATALOG NUMBER: S125RDIP-S1270D810U927-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.8	2.5
10°-20°	429.7	7.0
20°-30°	623.1	10.1
30°-40°	710.2	11.5
40°-50°	692.3	11.2
50°-60°	582.7	9.4
60°-70°	408.5	6.6
70°-80°	210.0	3.4
80°-90°	54.7	0.9
90°-100°	222.7	3.6
100°-110°	478.7	7.8
110°-120°	449.3	7.3
120°-130°	364.1	5.9
130°-140°	292.2	4.7
140°-150°	220.5	3.6
150°-160°	155.2	2.5
160°-170°	91.5	1.5
170°-180°	29.8	0.5
0°-30°	1206.6	19.6
0°-40°	1916.8	31.1
0°-60°	3191.8	51.7
0°-90°	3865.0	62.7
90°-120°	1150.7	18.7
90°-150°	2027.5	32.9
90°-180°	2304.0	37.3
0°-180°	6168.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1635	1635	1635	1635	1635	
5°	1633	1627	1614	1626	1624	155
15°	1552	1544	1519	1517	1507	437
25°	1408	1388	1344	1328	1314	648
35°	1213	1182	1128	1093	1074	759
45°	993	955	889	842	821	766
55°	753	712	645	591	569	674
65°	510	467	403	355	335	505
75°	272	234	183	157	147	288
85°	68	47	40	38	37	76
90°	1	6	10	13	14	4
95°	20	60	549	249	146	22
105°	70	98	449	884	821	74
115°	125	151	360	777	914	123
125°	173	203	346	618	720	154
135°	203	244	343	518	598	158
145°	237	271	344	429	472	148
155°	270	290	336	379	396	124
165°	295	303	322	342	347	83
175°	307	307	309	313	312	29
180°	307	307	307	307	307	



TEST NUMBER: P333627-927

CATALOG NUMBER: S125RDIP-S1270D810U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3
2.5°	1638.2	1637.6	1636.9	1636.3	1635.6	1634.2	1632.0	1629.8	1627.6	1625.4	1627.6
5°	1632.8	1631.7	1630.6	1629.5	1628.4	1626.4	1623.3	1620.3	1617.3	1614.3	1617.0
7.5°	1616.8	1615.7	1614.7	1613.6	1612.6	1610.3	1606.6	1603.0	1599.4	1595.8	1597.7
10°	1602.0	1601.1	1600.3	1599.5	1598.6	1596.3	1592.4	1588.6	1584.8	1581.0	1581.8
12.5°	1585.2	1584.1	1583.0	1582.0	1581.0	1577.9	1572.7	1567.6	1562.3	1557.2	1557.8
15°	1552.5	1550.9	1549.3	1547.6	1545.9	1542.2	1536.4	1530.7	1525.0	1519.2	1518.9
17.5°	1515.7	1513.2	1510.7	1508.2	1505.6	1500.7	1493.5	1486.2	1479.0	1471.7	1470.4
20°	1487.1	1484.3	1481.5	1478.8	1476.1	1470.3	1461.6	1452.8	1444.0	1435.2	1433.8
22.5°	1455.5	1452.7	1449.9	1447.2	1444.5	1438.5	1429.3	1420.1	1410.8	1401.6	1398.9
25°	1408.0	1403.9	1399.8	1395.7	1391.5	1384.4	1374.3	1364.1	1353.9	1343.8	1340.2
27.5°	1353.7	1348.7	1343.7	1338.7	1333.7	1325.8	1314.9	1304.0	1293.2	1282.3	1277.3
30°	1314.2	1308.9	1303.7	1298.5	1293.3	1284.9	1273.4	1261.9	1250.3	1238.8	1232.5
32.5°	1275.7	1269.6	1263.5	1257.4	1251.3	1242.3	1230.6	1218.9	1207.0	1195.3	1188.4
35°	1212.9	1206.3	1199.7	1193.1	1186.5	1177.0	1164.7	1152.4	1140.0	1127.7	1119.7
37.5°	1151.4	1143.4	1135.4	1127.4	1119.3	1108.9	1096.2	1083.5	1070.7	1058.0	1048.5
40°	1107.9	1099.6	1091.4	1083.2	1075.0	1064.2	1051.1	1037.9	1024.7	1011.5	1001.2
42.5°	1062.5	1054.0	1045.5	1037.0	1028.6	1017.6	1004.0	990.4	976.8	963.1	953.2
45°	993.0	985.1	977.1	969.2	961.2	949.7	934.5	919.5	904.4	889.3	878.3
47.5°	921.1	912.8	904.4	896.0	887.6	875.8	860.5	845.3	830.1	814.9	803.6
50°	875.7	866.6	857.5	848.5	839.5	827.1	811.4	795.8	780.1	764.5	753.0
52.5°	826.2	817.0	807.7	798.4	789.2	777.1	762.4	747.7	732.8	718.1	705.7
55°	753.4	744.7	735.9	727.1	718.3	706.2	690.9	675.5	660.1	644.8	632.4
57.5°	679.8	670.4	661.0	651.6	642.2	630.2	615.4	600.5	585.7	570.8	558.8
60°	632.4	622.7	613.1	603.6	594.0	581.7	566.9	552.1	537.3	522.4	510.4
62.5°	582.0	572.8	563.6	554.4	545.3	533.2	518.2	503.1	488.1	473.0	461.8
65°	510.1	500.7	491.5	482.1	472.8	460.8	446.3	431.7	417.2	402.7	391.7
67.5°	438.7	429.4	420.0	410.7	401.4	389.8	375.8	361.9	347.9	334.0	323.9
70°	390.3	381.0	371.6	362.3	353.0	341.4	327.7	314.0	300.2	286.5	278.1
72.5°	342.9	333.7	324.6	315.5	306.4	295.4	282.6	269.7	256.9	244.1	236.2
75°	271.7	263.5	255.2	247.0	238.8	228.9	217.4	205.9	194.3	182.8	176.7
77.5°	201.1	194.5	187.9	181.3	174.8	166.8	157.6	148.4	139.2	129.9	125.7
80°	160.6	154.0	147.4	140.8	134.2	127.1	119.4	111.7	104.0	96.3	93.9
82.5°	121.0	115.1	109.2	103.2	97.4	91.7	86.4	81.2	75.9	70.7	69.5
85°	68.0	63.0	58.1	53.1	48.2	45.0	43.6	42.3	40.9	39.5	39.2
87.5°	22.8	21.5	20.1	18.9	17.6	17.0	16.9	16.9	16.8	16.8	17.0
90°	0.6	1.3	2.5	3.7	5.0	6.2	6.8	8.1	8.6	9.9	10.5
92.5°	7.5	9.2	14.3	22.0	32.7	50.8	84.6	141.3	202.9	199.7	161.7
95°	20.4	21.1	26.0	32.8	46.4	74.3	140.6	276.9	447.8	548.8	537.0
97.5°	33.9	34.7	38.2	45.0	57.2	77.3	121.1	221.0	399.9	586.1	679.5
100°	43.3	44.6	47.1	53.9	65.7	84.2	120.2	200.7	356.8	559.4	714.2
102.5°	53.8	54.5	56.5	63.8	74.5	92.7	124.6	192.3	324.1	512.2	693.4
105°	70.0	70.0	73.1	79.3	89.2	106.5	133.8	188.9	292.4	449.1	626.9
107.5°	85.9	87.1	90.1	95.1	105.4	121.0	147.4	194.6	279.0	405.6	559.0
110°	97.3	98.5	100.9	106.5	115.8	131.9	157.3	200.1	275.0	385.2	520.3



TEST NUMBER: P333627-927

CATALOG NUMBER: S125RDIP-S1270D810U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	108.6	109.9	111.9	117.4	126.7	142.4	166.8	207.0	275.0	373.4	491.5
115°	125.1	126.4	128.3	133.8	143.1	158.6	181.5	217.4	276.9	360.5	460.2
117.5°	140.0	141.9	143.9	149.4	159.9	174.9	196.6	229.3	281.0	354.2	441.5
120°	149.9	151.8	154.2	159.8	170.3	185.8	207.5	237.3	284.9	351.2	431.1
122.5°	160.3	161.7	163.7	169.2	180.8	196.2	217.9	246.1	288.4	348.7	422.2
125°	173.4	174.7	177.8	183.3	195.1	211.2	231.6	258.3	294.2	345.6	410.0
127.5°	183.7	185.6	189.6	196.6	209.1	225.2	244.9	269.4	300.8	344.1	398.9
130°	190.1	192.0	196.9	205.0	218.0	234.2	253.3	276.9	304.8	343.2	391.5
132.5°	195.1	197.5	203.4	212.5	225.9	242.1	261.3	283.3	309.2	343.2	385.6
135°	203.2	205.7	213.1	223.0	236.0	252.7	272.0	292.4	315.3	343.2	378.4
137.5°	213.3	215.2	222.1	232.0	244.8	262.0	279.5	299.0	320.8	343.9	372.2
140°	219.3	221.1	228.5	238.4	250.3	267.0	284.9	303.5	323.3	344.4	369.2
142.5°	226.2	227.6	234.5	244.4	255.7	271.4	288.4	306.0	324.8	344.9	366.7
145°	236.6	237.8	244.1	252.7	263.9	278.1	294.2	309.7	326.5	344.4	363.0
147.5°	247.5	248.3	253.6	261.7	271.3	283.8	297.9	312.0	327.0	342.8	359.1
150°	254.0	255.2	259.5	267.6	276.2	286.8	300.4	313.4	327.0	341.3	356.2
152.5°	260.9	261.7	265.5	272.5	280.7	290.3	302.9	314.4	326.5	339.3	352.7
155°	270.1	270.1	273.8	280.0	286.1	294.9	305.4	315.3	325.2	335.7	346.9
157.5°	278.2	278.1	281.1	286.4	291.8	298.4	307.4	315.9	323.6	332.0	341.4
160°	283.7	283.0	285.6	289.9	294.9	300.4	308.5	315.9	322.1	329.5	337.0
162.5°	288.1	287.6	290.0	293.8	297.8	302.4	309.4	315.4	320.6	326.5	333.0
165°	294.9	293.6	295.5	298.6	301.0	304.8	309.7	314.7	318.4	322.1	327.0
167.5°	299.3	298.7	299.8	301.5	303.2	305.6	309.7	313.1	314.9	317.7	321.2
170°	302.3	301.7	302.3	303.5	304.8	306.6	309.7	312.2	313.4	315.3	317.7
172.5°	304.3	303.2	303.7	305.0	305.7	306.6	309.2	311.2	311.4	312.3	314.3
175°	306.6	305.4	306.0	306.6	306.6	306.6	308.5	309.7	309.1	309.1	309.7
177.5°	307.7	306.7	306.7	307.2	306.7	306.7	307.7	308.2	307.2	307.2	307.7
180°	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2



TEST NUMBER: P333627-927

CATALOG NUMBER: S125RDIP-S1270D810U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3
2.5°	1629.8	1632.0	1634.2	1635.1	1635.0	1634.7	1634.5	1634.3
5°	1619.8	1622.5	1625.2	1626.4	1625.8	1625.2	1624.7	1624.1
7.5°	1599.6	1601.6	1603.5	1604.1	1603.5	1602.9	1602.3	1601.7
10°	1582.5	1583.4	1584.2	1584.2	1583.4	1582.5	1581.8	1581.0
12.5°	1558.5	1559.0	1559.6	1559.3	1558.1	1556.8	1555.5	1554.3
15°	1518.6	1518.4	1518.1	1516.7	1514.3	1511.8	1509.3	1506.8
17.5°	1469.0	1467.6	1466.3	1464.6	1462.5	1460.5	1458.5	1456.4
20°	1432.4	1431.1	1429.7	1427.8	1425.3	1422.8	1420.4	1417.9
22.5°	1396.2	1393.5	1390.8	1388.5	1386.5	1384.4	1382.4	1380.4
25°	1336.6	1333.1	1329.5	1326.2	1323.2	1320.2	1317.2	1314.2
27.5°	1272.3	1267.3	1262.3	1258.4	1255.5	1252.5	1249.6	1246.7
30°	1226.2	1219.9	1213.5	1209.2	1206.7	1204.2	1201.7	1199.3
32.5°	1181.4	1174.4	1167.4	1162.4	1159.3	1156.1	1153.0	1149.9
35°	1111.7	1103.7	1095.8	1089.9	1086.1	1082.2	1078.4	1074.5
37.5°	1038.9	1029.4	1019.8	1013.1	1009.4	1005.7	1002.0	998.2
40°	990.7	980.2	969.9	963.0	959.6	956.4	953.1	949.8
42.5°	943.2	933.2	923.2	915.8	910.9	906.1	901.3	896.4
45°	867.3	856.3	845.3	837.8	833.7	829.6	825.5	821.3
47.5°	792.3	781.0	769.7	761.8	757.2	752.7	748.1	743.5
50°	741.5	729.9	718.4	710.6	706.5	702.3	698.2	694.1
52.5°	693.2	680.9	668.4	660.2	656.1	652.0	647.8	643.7
55°	620.0	607.7	595.3	586.9	582.6	578.1	573.8	569.4
57.5°	546.7	534.6	522.5	514.6	510.6	506.8	502.9	499.0
60°	498.3	486.2	474.1	466.0	461.9	457.8	453.7	449.6
62.5°	450.7	439.4	428.3	420.6	416.5	412.3	408.2	404.1
65°	380.7	369.7	358.7	351.2	347.1	342.9	338.8	334.7
67.5°	313.9	303.8	293.8	287.1	283.8	280.5	277.3	273.9
70°	269.5	261.0	252.5	246.6	243.3	240.0	236.7	233.5
72.5°	228.4	220.5	212.6	207.6	205.4	203.3	201.1	198.8
75°	170.7	164.7	158.7	154.6	152.7	150.8	148.9	146.9
77.5°	121.4	117.2	113.0	110.2	108.8	107.3	105.9	104.5
80°	91.4	89.0	86.4	84.9	84.4	83.8	83.3	82.8
82.5°	68.4	67.2	66.1	65.3	65.0	64.6	64.3	64.0
85°	39.0	38.7	38.4	38.2	37.9	37.6	37.3	37.1
87.5°	17.0	17.2	17.3	17.4	17.2	17.0	16.9	16.7
90°	11.2	11.8	12.4	13.6	13.6	13.6	14.3	14.3
92.5°	109.8	79.7	60.0	50.8	42.9	41.4	40.5	39.5
95°	445.4	351.2	275.0	223.0	179.0	160.4	155.5	145.5
97.5°	663.3	597.2	523.0	450.7	412.4	377.7	359.7	351.8
100°	761.8	731.5	667.7	603.3	560.5	515.9	493.1	483.2
102.5°	795.0	813.8	783.2	739.6	693.9	662.1	637.2	629.8
105°	775.5	860.4	887.6	880.8	860.9	840.5	828.1	820.7
107.5°	705.6	818.9	888.8	921.1	931.2	931.1	927.0	922.0
110°	654.1	771.7	859.1	911.7	939.6	951.4	955.8	955.8



TEST NUMBER: P333627-927

CATALOG NUMBER: S125RDIP-S1270D810U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	613.5	725.2	813.5	875.6	916.3	936.5	947.3	951.8
115°	562.4	658.5	743.3	810.8	859.1	888.8	906.2	914.3
117.5°	529.5	612.2	685.3	747.3	795.6	826.2	843.5	848.4
120°	511.6	586.0	654.1	708.6	754.4	784.2	800.9	805.8
122.5°	498.3	567.1	627.8	678.9	719.8	747.0	763.7	768.2
125°	478.8	542.0	595.9	640.5	675.2	700.5	714.2	720.3
127.5°	459.0	517.9	568.2	610.0	641.4	663.8	676.8	679.5
130°	446.6	501.1	549.4	589.7	620.7	641.1	653.5	657.2
132.5°	434.2	485.2	529.1	567.8	598.8	619.2	630.7	634.9
135°	418.1	460.8	500.5	535.8	563.0	583.4	594.6	598.3
137.5°	404.5	439.0	472.0	501.9	526.4	544.9	555.2	559.4
140°	397.0	426.1	454.6	480.6	503.6	519.7	528.9	532.0
142.5°	390.6	415.3	439.7	462.3	481.8	495.4	504.2	506.8
145°	382.1	401.4	420.6	437.3	452.2	462.7	469.5	472.0
147.5°	374.2	389.8	404.6	417.2	429.0	437.4	441.4	442.5
150°	369.8	383.4	395.1	406.3	415.7	423.0	425.6	426.1
152.5°	364.8	377.0	387.8	396.4	404.3	410.2	412.6	413.3
155°	357.4	367.3	376.0	382.8	389.0	393.3	395.1	395.8
157.5°	350.0	358.1	364.8	370.2	375.0	378.6	380.3	380.2
160°	345.0	351.2	357.4	361.7	366.1	369.2	370.4	369.8
162.5°	339.5	345.2	350.5	354.3	357.7	360.2	360.5	360.4
165°	332.0	336.4	340.1	343.2	345.6	346.9	346.9	346.9
167.5°	324.8	327.6	330.5	332.7	334.0	335.1	334.6	334.5
170°	320.8	322.7	324.6	325.8	327.0	327.6	327.6	327.0
172.5°	316.4	318.2	319.6	320.4	320.6	321.7	320.8	320.1
175°	311.6	311.6	312.8	312.8	312.8	313.4	312.2	311.6
177.5°	308.2	308.7	308.7	308.7	308.2	308.7	307.2	307.2
180°	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2

(END OF REPORT)