

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333564

Luminaire Tested: **S125RDIP-S850D810U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333564  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S850D810U835-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6187.6 lumens  
Efficiency: N/A  
Efficacy: 134.8 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 45.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333564

CATALOG NUMBER: S125RDIP-S850D810U835-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333564

CATALOG NUMBER: S125RDIP-S850D810U835-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	95	91	88	92	88	85	82	75	73	71	64	62	60	53	52	51	46
2	90	83	77	72	84	77	72	68	66	63	59	56	54	51	47	45	43	39
3	83	73	66	61	76	68	62	57	59	54	50	50	47	44	42	39	37	33
4	76	65	58	52	70	61	54	49	53	47	43	45	41	38	38	35	32	29
5	70	58	50	44	64	54	47	42	47	42	37	40	36	33	34	31	28	25
6	64	52	44	39	59	49	42	37	43	37	33	37	32	29	31	28	25	22
7	60	47	40	34	55	44	37	32	39	33	29	33	29	26	28	25	22	20
8	55	43	35	30	51	40	33	29	35	30	26	31	26	23	26	23	20	18
9	51	39	32	27	48	37	30	26	32	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	22	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	8169	8169	8169	8169
5°	9398	8180	7224	8180
10°	10781	8138	6374	8138
15°	11645	8055	5666	8055
20°	12841	7958	5232	7958
25°	14860	7829	4855	7829
30°	16171	7694	4608	7694
35°	13640	7536	4380	7536
40°	9526	7254	4185	7254
45°	7067	6872	3993	6872
50°	5635	6475	3829	6475
55°	4782	5981	3683	5981
60°	4132	5540	3447	5540
65°	3681	5063	2968	5063
70°	3237	4638	2706	4638
75°	2800	4017	2540	4017
80°	2124	3381	2124	3381
85°	1771	2653	2001	2653



TEST NUMBER: P333564

CATALOG NUMBER: S125RDIP-S850D810U835-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	121.3	2.0
10°-20°	355.5	5.7
20°-30°	563.6	9.1
30°-40°	679.7	11.0
40°-50°	607.0	9.8
50°-60°	465.5	7.5
60°-70°	302.5	4.9
70°-80°	147.1	2.4
80°-90°	37.3	0.6
90°-100°	281.1	4.5
100°-110°	604.3	9.8
110°-120°	567.1	9.2
120°-130°	459.6	7.4
130°-140°	368.8	6.0
140°-150°	278.3	4.5
150°-160°	195.9	3.2
160°-170°	115.5	1.9
170°-180°	37.6	0.6
0°-30°	1040.4	16.8
0°-40°	1720.1	27.8
0°-60°	2792.5	45.1
0°-90°	3279.3	53.0
90°-120°	1452.5	23.5
90°-150°	2559.3	41.4
90°-180°	2908.0	47.0
0°-180°	6187.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1265	1265	1265	1265	1265	
5°	1450	1262	1114	1262	1450	145
15°	1742	1205	847	1205	1742	499
25°	2085	1099	681	1099	2085	957
35°	1730	956	556	956	1730	1045
45°	774	752	437	752	774	617
55°	425	531	327	531	425	385
65°	241	331	194	331	241	240
75°	112	161	102	161	112	119
85°	24	36	27	36	24	28
90°	18	1	18	1	18	14
95°	184	26	184	26	184	260
105°	1036	88	1036	88	1036	1030
115°	1154	158	1154	158	1154	1128
125°	909	219	909	219	909	823
135°	755	256	755	256	755	585
145°	596	299	596	299	596	379
155°	500	341	500	341	500	233
165°	438	372	438	372	438	125
175°	393	387	393	387	393	38
180°	388	388	388	388	388	



TEST NUMBER: P333564

CATALOG NUMBER: S125RDIP-S850D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1330.5	1329.7	1331.4	1326.8	1327.2	1320.1	1320.1	1314.7	1307.7	1302.3	1299.8
5°	1449.7	1450.8	1448.7	1440.9	1435.7	1427.9	1419.1	1403.5	1390.5	1378.1	1368.2
7.5°	1572.5	1573.2	1566.4	1564.0	1550.9	1541.3	1521.7	1500.5	1481.7	1457.8	1439.6
10°	1643.9	1643.4	1636.2	1630.4	1619.0	1604.5	1585.3	1560.3	1537.0	1511.0	1486.1
12.5°	1685.5	1684.1	1681.8	1674.9	1664.3	1651.4	1635.1	1610.6	1581.8	1553.4	1524.3
15°	1741.6	1737.9	1731.2	1722.3	1707.3	1692.2	1674.1	1652.3	1624.7	1592.5	1565.5
17.5°	1810.9	1811.0	1800.7	1788.4	1767.9	1741.4	1713.3	1678.1	1640.7	1605.3	1576.5
20°	1868.3	1866.7	1856.3	1832.4	1809.1	1775.8	1743.6	1700.5	1654.8	1608.6	1572.8
22.5°	1950.5	1946.5	1935.7	1904.3	1868.1	1825.3	1776.0	1723.4	1668.1	1615.7	1568.7
25°	2085.3	2082.2	2060.9	2024.6	1973.7	1907.7	1843.3	1771.2	1691.7	1622.7	1565.5
27.5°	2177.5	2174.1	2158.3	2128.1	2081.2	2011.8	1924.6	1828.2	1729.0	1634.0	1551.6
30°	2168.4	2176.2	2174.1	2160.1	2124.8	2062.5	1982.0	1873.5	1755.6	1643.9	1545.8
32.5°	2037.9	2044.9	2063.2	2090.7	2092.8	2067.9	2007.7	1907.5	1785.5	1658.5	1541.2
35°	1730.1	1739.5	1774.8	1830.4	1903.0	1963.8	1976.3	1922.3	1812.7	1676.1	1534.4
37.5°	1330.1	1381.2	1410.9	1469.4	1579.2	1691.0	1798.5	1838.0	1791.4	1668.9	1523.3
40°	1129.9	1142.3	1195.3	1261.3	1353.7	1470.0	1623.2	1733.8	1737.4	1652.3	1505.8
42.5°	967.0	982.8	1019.2	1071.8	1151.0	1267.3	1425.4	1571.4	1639.0	1606.6	1483.0
45°	773.7	785.6	812.1	852.6	913.4	1009.4	1145.5	1314.2	1448.2	1500.6	1421.7
47.5°	635.6	642.0	665.1	695.9	740.9	810.9	916.2	1062.7	1223.4	1336.0	1324.9
50°	560.8	568.1	585.7	609.1	647.0	706.2	790.3	912.3	1078.0	1215.6	1243.1
52.5°	502.6	508.7	519.7	541.8	573.0	618.5	686.4	796.8	945.9	1092.2	1155.8
55°	424.7	428.9	437.7	450.2	475.1	507.8	566.5	642.8	763.3	910.8	1004.2
57.5°	360.6	362.6	368.3	379.8	397.0	420.9	463.3	528.0	614.4	747.2	850.3
60°	319.9	321.9	329.2	337.0	350.5	372.3	405.5	450.7	533.8	643.3	747.7
62.5°	287.5	288.7	291.8	299.6	311.4	328.3	354.4	391.3	457.4	553.6	652.2
65°	240.9	241.5	242.5	248.7	256.0	268.5	285.6	311.5	361.4	434.1	521.3
67.5°	196.3	197.0	200.6	202.8	210.4	216.9	227.0	246.9	282.0	331.0	398.8
70°	171.4	170.8	174.5	177.1	179.7	187.4	194.2	210.3	232.1	269.5	326.1
72.5°	148.1	146.7	148.3	149.2	152.7	158.0	164.7	174.6	191.4	217.1	260.5
75°	112.2	112.7	112.7	113.7	116.3	118.4	120.5	125.7	135.0	152.1	175.5
77.5°	78.7	77.9	80.1	80.4	81.9	84.2	86.0	88.1	91.9	99.0	111.0
80°	57.1	57.1	57.6	59.2	58.7	59.7	62.3	64.4	69.1	73.2	77.4
82.5°	43.8	43.4	43.9	44.2	44.1	45.2	46.1	46.5	48.3	50.4	53.3
85°	23.9	23.9	24.4	24.4	24.9	24.9	25.4	25.4	25.4	26.0	26.5
87.5°	12.7	12.3	11.7	11.7	12.2	12.7	12.1	11.5	11.4	11.2	11.3
90°	18.0	18.0	17.2	17.2	17.2	15.6	14.9	14.1	13.3	12.5	10.9
92.5°	49.9	51.1	52.2	54.1	64.1	75.7	100.6	138.6	204.1	252.1	256.1
95°	183.7	196.3	202.5	226.0	281.5	347.2	443.3	562.2	677.9	692.8	565.3
97.5°	444.1	454.1	476.8	520.6	568.9	660.2	753.9	837.3	857.7	739.8	504.8
100°	609.9	622.4	651.3	707.6	761.6	842.9	923.4	961.7	901.5	706.1	450.4
102.5°	795.0	804.4	835.8	875.9	933.6	988.6	1027.3	1003.6	875.3	646.6	409.1
105°	1036.0	1045.4	1061.0	1086.8	1111.9	1120.5	1086.1	978.9	791.3	566.9	369.1
107.5°	1163.9	1170.2	1175.3	1175.5	1162.8	1122.0	1033.7	890.7	705.6	512.0	352.2
110°	1206.5	1206.5	1201.0	1186.1	1150.9	1084.5	974.2	825.7	656.8	486.3	347.2



TEST NUMBER: P333564

CATALOG NUMBER: S125RDIP-S850D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1201.5	1195.8	1182.2	1156.7	1105.3	1026.9	915.4	774.4	620.5	471.3	347.2
115°	1154.1	1143.9	1122.0	1084.5	1023.5	938.3	831.2	710.0	580.9	455.1	349.5
117.5°	1071.0	1064.8	1043.0	1004.3	943.3	865.1	772.8	668.4	557.3	447.1	354.7
120°	1017.2	1011.0	989.9	952.3	894.5	825.7	739.7	645.8	544.2	443.3	359.7
122.5°	969.7	964.1	943.0	908.6	857.0	792.5	715.9	629.0	532.9	440.2	364.0
125°	909.3	901.5	884.3	852.3	808.5	752.2	684.2	604.4	517.6	436.3	371.4
127.5°	857.7	854.3	838.0	809.7	770.0	717.3	653.8	579.4	503.5	434.4	379.7
130°	829.6	824.9	809.3	783.5	744.4	693.5	632.6	563.7	494.2	433.2	384.7
132.5°	801.4	796.1	781.7	755.9	716.8	667.9	612.5	548.1	486.7	433.2	390.3
135°	755.3	750.6	736.5	710.7	676.3	631.8	581.7	527.8	477.7	433.2	398.0
137.5°	706.1	700.9	687.9	664.5	633.6	595.8	554.2	510.6	469.8	434.1	405.0
140°	671.6	667.7	656.0	635.7	606.7	573.9	537.9	501.2	466.0	434.7	408.1
142.5°	639.7	636.5	625.4	608.2	583.6	555.1	524.2	493.1	462.9	435.4	410.0
145°	595.8	592.7	584.1	570.8	552.0	530.9	506.7	482.4	458.2	434.7	412.1
147.5°	558.6	557.2	552.2	541.5	526.7	510.7	492.1	472.4	453.3	432.7	412.8
150°	537.9	537.2	534.0	524.7	512.9	498.8	484.0	466.8	449.6	430.8	412.8
152.5°	521.7	520.9	517.8	510.3	500.4	489.5	475.9	460.5	445.2	428.3	412.2
155°	499.6	498.8	496.5	491.0	483.2	474.6	463.7	451.2	437.9	423.8	410.5
157.5°	479.9	480.1	477.9	473.4	467.3	460.5	452.1	441.8	431.0	419.1	408.5
160°	466.8	467.6	466.0	462.1	456.6	451.2	443.3	435.5	425.4	416.0	406.6
162.5°	454.9	455.1	454.7	451.5	447.2	442.4	435.8	428.6	420.3	412.2	404.7
165°	437.9	437.9	437.9	436.3	433.2	429.3	424.6	419.1	412.8	406.6	401.9
167.5°	422.2	422.4	423.0	421.6	420.0	417.2	413.6	410.0	405.5	401.1	397.5
170°	412.8	413.6	413.6	412.8	411.3	409.7	407.4	405.0	401.1	398.0	395.6
172.5°	404.1	404.9	406.1	404.7	404.4	403.5	401.7	399.4	396.7	394.2	393.1
175°	393.3	394.1	395.6	394.9	394.9	394.9	393.3	393.3	390.9	390.2	390.2
177.5°	387.8	387.8	389.7	389.1	389.7	389.7	389.7	389.1	388.4	387.8	387.8
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P333564

CATALOG NUMBER: S125RDIP-S850D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1299.8	1296.9	1291.5	1286.5	1280.3	1274.9	1271.1	1266.6	1260.7	1253.7	1247.9
5°	1357.3	1345.9	1330.8	1317.9	1301.2	1288.3	1274.8	1261.8	1248.8	1232.2	1217.6
7.5°	1421.1	1397.5	1374.6	1345.7	1319.5	1296.1	1273.7	1251.0	1228.8	1205.2	1182.4
10°	1460.1	1431.6	1399.9	1363.5	1330.3	1298.6	1269.6	1241.0	1210.9	1184.4	1155.8
12.5°	1496.7	1459.8	1423.6	1377.7	1337.8	1299.1	1262.1	1226.5	1194.3	1159.9	1129.3
15°	1529.7	1493.4	1452.9	1396.8	1341.2	1294.5	1250.9	1204.7	1164.7	1126.3	1092.0
17.5°	1542.5	1504.4	1457.3	1403.4	1342.7	1283.9	1227.7	1177.0	1130.0	1085.2	1046.7
20°	1537.5	1500.6	1452.3	1400.9	1336.0	1274.8	1214.0	1157.9	1105.5	1058.2	1017.2
22.5°	1525.4	1487.3	1440.7	1386.4	1324.8	1259.8	1194.9	1135.1	1080.1	1031.2	986.5
25°	1507.4	1455.5	1407.7	1354.7	1296.0	1231.7	1164.7	1098.7	1040.1	990.2	941.4
27.5°	1488.6	1423.8	1363.0	1310.4	1248.4	1190.9	1126.4	1058.7	997.1	946.3	896.2
30°	1471.6	1398.9	1331.9	1272.2	1213.5	1159.0	1097.7	1031.7	968.4	916.0	865.1
32.5°	1450.4	1373.1	1299.5	1230.6	1174.0	1119.9	1064.5	1001.4	939.7	885.6	833.9
35°	1423.8	1325.1	1245.2	1171.9	1109.1	1056.7	1006.8	955.9	894.1	838.1	787.7
37.5°	1388.9	1276.9	1184.4	1104.7	1038.4	985.7	946.4	899.9	843.5	789.8	743.0
40°	1367.7	1242.0	1140.8	1061.9	992.3	936.7	899.9	860.4	809.0	758.6	711.9
42.5°	1339.5	1210.1	1096.8	1014.5	944.5	891.0	853.7	819.3	776.2	728.7	678.7
45°	1284.1	1148.1	1029.2	940.9	870.3	817.8	783.0	752.4	719.7	676.1	632.4
47.5°	1212.0	1083.4	958.9	862.6	793.4	744.7	711.0	686.8	663.4	626.3	583.9
50°	1154.3	1030.2	908.7	815.2	741.5	695.3	663.6	644.4	623.1	589.3	554.0
52.5°	1086.2	975.4	856.3	760.8	691.2	647.9	617.5	598.3	580.7	553.2	519.6
55°	978.8	881.7	772.6	685.9	622.1	578.4	549.4	531.2	520.8	497.4	471.0
57.5°	854.9	785.3	689.1	605.5	549.1	506.0	484.7	469.2	457.5	440.9	422.3
60°	768.5	719.7	633.5	554.0	502.1	461.1	441.9	428.9	418.0	404.0	389.4
62.5°	680.8	645.3	570.3	502.1	454.3	420.0	402.0	390.3	377.7	368.3	354.1
65°	563.4	531.7	479.8	426.3	382.2	354.6	341.7	331.3	323.5	313.1	303.2
67.5°	438.2	425.4	389.5	352.7	321.0	296.5	285.3	278.0	268.7	262.4	255.7
70°	361.4	355.2	329.7	305.3	275.7	259.1	248.7	245.6	234.2	228.0	223.3
72.5°	293.3	290.4	275.7	258.8	237.9	223.4	213.8	210.3	203.0	198.0	195.0
75°	200.9	202.0	199.4	188.5	180.7	171.4	163.0	161.0	155.8	151.6	149.0
77.5°	127.1	132.4	132.6	132.1	129.0	123.3	119.8	118.3	113.2	111.6	111.0
80°	87.2	92.9	98.1	97.6	96.6	95.0	92.4	90.9	88.3	86.7	85.7
82.5°	58.2	63.5	67.8	70.6	70.4	68.9	67.1	66.4	65.8	64.7	64.5
85°	27.5	28.6	30.1	33.8	36.3	36.9	36.3	35.8	34.3	34.8	35.3
87.5°	11.6	11.3	11.5	11.2	10.5	12.3	13.2	13.4	12.8	12.3	11.7
90°	10.2	8.6	7.8	6.3	4.7	3.1	1.6	0.8	1.6	3.1	4.7
92.5°	178.4	106.8	64.1	41.3	27.8	18.1	11.6	9.5	11.6	18.1	27.8
95°	349.5	177.5	93.8	58.6	41.4	32.8	26.6	25.8	26.6	32.8	41.4
97.5°	279.0	152.9	97.6	72.2	56.8	48.2	43.8	42.8	43.8	48.2	56.8
100°	253.3	151.7	106.3	82.9	68.0	59.4	56.3	54.7	56.3	59.4	68.0
102.5°	242.7	157.3	117.0	94.1	80.5	71.3	68.8	67.9	68.8	71.3	80.5
105°	238.5	168.9	134.5	112.6	100.1	92.3	88.4	88.4	88.4	92.3	100.1
107.5°	245.7	186.1	152.8	133.1	120.1	113.7	109.9	108.4	109.9	113.7	120.1
110°	252.6	198.6	166.5	146.2	134.5	127.4	124.3	122.8	124.3	127.4	134.5





TEST NUMBER: P333564

CATALOG NUMBER: S125RDIP-S850D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	261.3	210.5	179.7	160.0	148.2	141.2	138.7	137.1	138.7	141.2	148.2
115°	274.4	229.1	200.2	180.6	168.9	161.9	159.5	157.9	159.5	161.9	168.9
117.5°	289.5	248.2	220.8	201.9	188.6	181.6	179.1	176.7	179.1	181.6	188.6
120°	299.5	261.9	234.6	215.0	201.7	194.7	191.6	189.2	191.6	194.7	201.7
122.5°	310.7	275.1	247.7	228.2	213.6	206.6	204.1	202.4	204.1	206.6	213.6
125°	326.0	292.4	266.6	246.3	231.4	224.4	220.5	218.9	220.5	224.4	231.4
127.5°	340.1	309.2	284.3	264.0	248.2	239.3	234.3	231.9	234.3	239.3	248.2
130°	349.5	319.8	295.6	275.2	258.8	248.6	242.4	240.0	242.4	248.6	258.8
132.5°	357.6	329.8	305.6	285.2	268.2	256.8	249.3	246.3	249.3	256.8	268.2
135°	369.1	343.3	319.0	297.9	281.5	269.0	259.6	256.5	259.6	269.0	281.5
137.5°	377.5	352.8	330.7	309.0	292.9	280.4	271.6	269.3	271.6	280.4	292.9
140°	383.1	359.7	337.0	315.9	301.0	288.5	279.1	276.8	279.1	288.5	301.0
142.5°	386.3	364.0	342.6	322.8	308.5	296.0	287.3	285.5	287.3	296.0	308.5
145°	390.9	371.4	351.1	333.1	319.0	308.1	300.2	298.7	300.2	308.1	319.0
147.5°	393.8	376.1	358.3	342.5	330.3	320.1	313.4	312.4	313.4	320.1	330.3
150°	395.6	379.2	362.0	348.7	337.8	327.6	322.1	320.6	322.1	327.6	337.8
152.5°	396.9	382.3	366.4	354.4	344.0	335.1	330.3	329.3	330.3	335.1	344.0
155°	398.0	385.5	372.2	361.2	353.4	345.6	340.9	340.9	340.9	345.6	353.4
157.5°	398.8	388.1	376.7	368.4	361.5	354.8	351.1	351.2	351.1	354.8	361.5
160°	398.8	389.4	379.2	372.2	365.9	360.5	357.3	358.1	357.3	360.5	365.9
162.5°	398.1	390.6	381.7	375.9	370.9	366.1	363.0	363.7	363.0	366.1	370.9
165°	397.2	390.9	384.7	380.0	376.9	373.0	370.6	372.2	370.6	373.0	376.9
167.5°	395.3	390.9	385.8	382.8	380.6	378.4	377.0	377.8	377.0	378.4	380.6
170°	394.1	390.9	387.0	384.7	383.1	381.6	380.8	381.6	380.8	381.6	383.1
172.5°	392.8	390.3	387.0	385.9	385.0	383.4	382.7	384.1	382.7	383.4	385.0
175°	390.9	389.4	387.0	387.0	387.0	386.3	385.5	387.0	385.5	386.3	387.0
177.5°	389.1	388.4	387.2	387.2	387.8	387.2	387.2	388.4	387.2	387.2	387.8
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P333564

CATALOG NUMBER: S125RDIP-S850D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1243.7	1237.9	1233.7	1225.4	1219.6	1217.1	1212.6	1211.3	1215.9	1212.6	1212.1
5°	1206.7	1191.7	1179.7	1167.8	1154.8	1146.5	1134.0	1132.0	1128.8	1124.2	1123.1
7.5°	1162.4	1142.8	1127.4	1107.7	1090.5	1076.7	1061.1	1053.8	1049.7	1043.7	1035.6
10°	1132.5	1109.1	1088.3	1068.6	1047.3	1030.2	1014.6	1002.7	994.9	987.6	984.5
12.5°	1103.0	1079.2	1052.6	1028.7	1005.0	985.7	968.5	960.7	952.1	943.6	936.3
15°	1057.2	1025.5	996.4	968.9	948.7	927.9	911.3	899.9	886.9	883.2	869.2
17.5°	1008.6	977.5	943.5	914.5	891.0	868.2	849.9	836.9	827.2	813.8	807.3
20°	978.3	941.4	908.2	881.7	855.7	828.7	810.0	799.1	789.8	778.9	773.7
22.5°	945.9	909.8	875.8	844.7	818.3	791.8	778.5	767.1	756.5	746.5	739.6
25°	898.3	862.0	826.1	793.9	766.4	747.2	731.6	718.6	712.9	703.1	695.8
27.5°	851.3	812.6	775.4	743.4	721.8	702.8	690.0	679.7	669.4	660.8	654.5
30°	820.9	781.5	741.0	715.5	692.7	674.5	660.5	650.6	642.8	635.0	630.4
32.5°	790.6	749.9	714.0	686.4	664.8	649.2	634.7	625.3	617.1	608.5	603.0
35°	742.0	700.5	671.4	644.4	623.1	608.6	598.7	585.2	578.4	572.2	566.5
37.5°	696.8	658.2	626.7	603.1	584.6	570.1	557.4	550.1	541.8	536.2	531.4
40°	663.6	628.3	599.7	574.8	561.3	545.2	533.3	523.9	517.7	510.4	505.2
42.5°	633.7	600.9	573.1	550.7	533.9	520.3	508.8	499.4	491.5	486.3	482.0
45°	591.4	558.7	531.7	510.9	495.4	482.4	470.4	465.8	455.4	449.2	447.1
47.5°	547.7	518.4	492.4	473.2	457.3	445.0	433.8	424.2	418.5	412.4	409.1
50°	518.2	490.2	465.8	447.1	431.5	418.0	407.6	401.4	393.6	387.9	383.7
52.5°	488.7	462.8	438.4	420.5	407.0	393.5	381.9	375.6	368.3	364.6	361.7
55°	446.6	419.0	398.3	380.6	366.6	354.1	343.2	337.0	332.3	328.7	327.6
57.5°	398.8	377.0	357.7	341.8	327.2	315.5	305.9	300.0	295.9	295.3	292.2
60°	367.6	347.9	330.2	313.1	300.6	289.7	281.4	274.7	270.5	270.0	269.0
62.5°	336.5	317.6	301.2	286.1	274.9	264.4	256.5	248.9	246.4	243.8	241.6
65°	290.3	273.1	259.6	247.7	235.7	226.9	219.1	214.4	208.7	205.6	199.9
67.5°	244.9	231.6	218.6	208.5	199.2	190.8	184.3	177.4	173.5	171.0	166.9
70°	215.0	204.6	191.6	180.7	173.4	166.7	161.5	153.7	151.1	149.0	146.9
72.5°	186.7	177.6	166.7	157.9	150.6	144.2	138.2	134.6	132.0	129.9	128.7
75°	146.9	138.1	128.8	122.5	117.4	112.2	109.0	106.4	105.4	104.9	102.8
77.5°	107.9	103.2	95.7	90.8	87.3	85.3	82.5	81.1	81.0	78.7	78.0
80°	82.6	80.0	73.7	71.7	69.1	67.0	65.4	62.8	60.2	59.2	57.6
82.5°	61.4	58.8	56.3	53.0	50.8	49.5	48.0	47.0	47.4	45.9	45.2
85°	32.7	30.1	29.1	28.6	27.5	28.6	28.0	27.5	27.0	26.5	27.0
87.5°	11.6	11.9	11.7	12.8	11.7	12.5	12.6	12.4	12.5	12.7	12.6
90°	6.3	7.8	8.6	10.2	10.9	12.5	13.3	14.1	14.9	15.6	17.2
92.5°	41.3	64.1	106.8	178.4	256.1	252.1	204.1	138.6	100.6	75.7	64.1
95°	58.6	93.8	177.5	349.5	565.3	692.8	677.9	562.2	443.3	347.2	281.5
97.5°	72.2	97.6	152.9	279.0	504.8	739.8	857.7	837.3	753.9	660.2	568.9
100°	82.9	106.3	151.7	253.3	450.4	706.1	901.5	961.7	923.4	842.9	761.6
102.5°	94.1	117.0	157.3	242.7	409.1	646.6	875.3	1003.6	1027.3	988.6	933.6
105°	112.6	134.5	168.9	238.5	369.1	566.9	791.3	978.9	1086.1	1120.5	1111.9
107.5°	133.1	152.8	186.1	245.7	352.2	512.0	705.6	890.7	1033.7	1122.0	1162.8
110°	146.2	166.5	198.6	252.6	347.2	486.3	656.8	825.7	974.2	1084.5	1150.9



TEST NUMBER: P333564

CATALOG NUMBER: S125RDIP-S850D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	160.0	179.7	210.5	261.3	347.2	471.3	620.5	774.4	915.4	1026.9	1105.3
115°	180.6	200.2	229.1	274.4	349.5	455.1	580.9	710.0	831.2	938.3	1023.5
117.5°	201.9	220.8	248.2	289.5	354.7	447.1	557.3	668.4	772.8	865.1	943.3
120°	215.0	234.6	261.9	299.5	359.7	443.3	544.2	645.8	739.7	825.7	894.5
122.5°	228.2	247.7	275.1	310.7	364.0	440.2	532.9	629.0	715.9	792.5	857.0
125°	246.3	266.6	292.4	326.0	371.4	436.3	517.6	604.4	684.2	752.2	808.5
127.5°	264.0	284.3	309.2	340.1	379.7	434.4	503.5	579.4	653.8	717.3	770.0
130°	275.2	295.6	319.8	349.5	384.7	433.2	494.2	563.7	632.6	693.5	744.4
132.5°	285.2	305.6	329.8	357.6	390.3	433.2	486.7	548.1	612.5	667.9	716.8
135°	297.9	319.0	343.3	369.1	398.0	433.2	477.7	527.8	581.7	631.8	676.3
137.5°	309.0	330.7	352.8	377.5	405.0	434.1	469.8	510.6	554.2	595.8	633.6
140°	315.9	337.0	359.7	383.1	408.1	434.7	466.0	501.2	537.9	573.9	606.7
142.5°	322.8	342.6	364.0	386.3	410.0	435.4	462.9	493.1	524.2	555.1	583.6
145°	333.1	351.1	371.4	390.9	412.1	434.7	458.2	482.4	506.7	530.9	552.0
147.5°	342.5	358.3	376.1	393.8	412.8	432.7	453.3	472.4	492.1	510.7	526.7
150°	348.7	362.0	379.2	395.6	412.8	430.8	449.6	466.8	484.0	498.8	512.9
152.5°	354.4	366.4	382.3	396.9	412.2	428.3	445.2	460.5	475.9	489.5	500.4
155°	361.2	372.2	385.5	398.0	410.5	423.8	437.9	451.2	463.7	474.6	483.2
157.5°	368.4	376.7	388.1	398.8	408.5	419.1	431.0	441.8	452.1	460.5	467.3
160°	372.2	379.2	389.4	398.8	406.6	416.0	425.4	435.5	443.3	451.2	456.6
162.5°	375.9	381.7	390.6	398.1	404.7	412.2	420.3	428.6	435.8	442.4	447.2
165°	380.0	384.7	390.9	397.2	401.9	406.6	412.8	419.1	424.6	429.3	433.2
167.5°	382.8	385.8	390.9	395.3	397.5	401.1	405.5	410.0	413.6	417.2	420.0
170°	384.7	387.0	390.9	394.1	395.6	398.0	401.1	405.0	407.4	409.7	411.3
172.5°	385.9	387.0	390.3	392.8	393.1	394.2	396.7	399.4	401.7	403.5	404.4
175°	387.0	387.0	389.4	390.9	390.2	390.2	390.9	393.3	393.3	394.9	394.9
177.5°	387.2	387.2	388.4	389.1	387.8	387.8	388.4	389.1	389.7	389.7	389.7
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P333564

CATALOG NUMBER: S125RDIP-S850D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1211.7	1207.2	1205.9	1207.6	1205.9	1207.2	1211.7	1212.1	1212.6	1215.9	1211.3
5°	1117.9	1112.8	1115.3	1114.3	1115.3	1112.8	1117.9	1123.1	1124.2	1128.8	1132.0
7.5°	1035.5	1029.0	1022.2	1024.4	1022.2	1029.0	1035.5	1035.6	1043.7	1049.7	1053.8
10°	977.7	972.6	969.4	972.0	969.4	972.6	977.7	984.5	987.6	994.9	1002.7
12.5°	929.1	926.0	923.3	922.2	923.3	926.0	929.1	936.3	943.6	952.1	960.7
15°	863.0	856.8	854.2	847.4	854.2	856.8	863.0	869.2	883.2	886.9	899.9
17.5°	802.0	800.0	793.2	790.3	793.2	800.0	802.0	807.3	813.8	827.2	836.9
20°	765.9	763.8	757.1	761.2	757.1	763.8	765.9	773.7	778.9	789.8	799.1
22.5°	736.0	731.4	729.2	728.0	729.2	731.4	736.0	739.6	746.5	756.5	767.1
25°	693.7	687.0	684.4	681.3	684.4	687.0	693.7	695.8	703.1	712.9	718.6
27.5°	651.6	647.9	644.5	643.7	644.5	647.9	651.6	654.5	660.8	669.4	679.7
30°	624.1	620.5	617.9	617.9	617.9	620.5	624.1	630.4	635.0	642.8	650.6
32.5°	599.6	596.8	594.2	593.8	594.2	596.8	599.6	603.0	608.5	617.1	625.3
35°	563.9	559.8	558.7	555.6	558.7	559.8	563.9	566.5	572.2	578.4	585.2
37.5°	526.8	523.4	523.3	523.0	523.3	523.4	526.8	531.4	536.2	541.8	550.1
40°	503.2	500.6	500.0	496.4	500.0	500.6	503.2	505.2	510.4	517.7	523.9
42.5°	477.8	476.5	474.7	473.1	474.7	476.5	477.8	482.0	486.3	491.5	499.4
45°	443.4	439.8	439.8	437.2	439.8	439.8	443.4	447.1	449.2	455.4	465.8
47.5°	407.9	405.1	405.4	402.7	405.4	405.1	407.9	409.1	412.4	418.5	424.2
50°	384.2	382.7	382.2	381.1	382.2	382.7	384.2	383.7	387.9	393.6	401.4
52.5°	360.6	359.8	361.8	359.5	361.8	359.8	360.6	361.7	364.6	368.3	375.6
55°	328.7	327.1	330.2	327.1	330.2	327.1	328.7	327.6	328.7	332.3	337.0
57.5°	292.0	290.6	293.4	291.8	293.4	290.6	292.0	292.2	295.3	295.9	300.0
60°	267.9	264.8	266.4	266.9	266.4	264.8	267.9	269.0	270.0	270.5	274.7
62.5°	239.3	237.4	238.5	236.2	238.5	237.4	239.3	241.6	243.8	246.4	248.9
65°	198.9	197.3	195.2	194.2	195.2	197.3	198.9	199.9	205.6	208.7	214.4
67.5°	167.1	163.4	163.3	164.1	163.3	163.4	167.1	166.9	171.0	173.5	177.4
70°	143.8	143.8	143.3	143.3	143.3	143.8	143.8	146.9	149.0	151.1	153.7
72.5°	127.6	127.2	126.3	125.9	126.3	127.2	127.6	128.7	129.9	132.0	134.6
75°	102.8	103.3	102.3	101.8	102.3	103.3	102.8	102.8	104.9	105.4	106.4
77.5°	75.9	73.7	74.9	73.7	74.9	73.7	75.9	78.0	78.7	81.0	81.1
80°	57.6	57.1	58.7	57.1	58.7	57.1	57.6	57.6	59.2	60.2	62.8
82.5°	45.6	45.1	45.8	44.7	45.8	45.1	45.6	45.2	45.9	47.4	47.0
85°	27.5	27.0	26.5	27.0	26.5	27.0	27.5	27.0	26.5	27.0	27.5
87.5°	13.0	12.6	12.7	12.7	12.7	12.6	13.0	12.6	12.7	12.5	12.4
90°	17.2	17.2	18.0	18.0	18.0	17.2	17.2	17.2	15.6	14.9	14.1
92.5°	54.1	52.2	51.1	49.9	51.1	52.2	54.1	64.1	75.7	100.6	138.6
95°	226.0	202.5	196.3	183.7	196.3	202.5	226.0	281.5	347.2	443.3	562.2
97.5°	520.6	476.8	454.1	444.1	454.1	476.8	520.6	568.9	660.2	753.9	837.3
100°	707.6	651.3	622.4	609.9	622.4	651.3	707.6	761.6	842.9	923.4	961.7
102.5°	875.9	835.8	804.4	795.0	804.4	835.8	875.9	933.6	988.6	1027.3	1003.6
105°	1086.8	1061.0	1045.4	1036.0	1045.4	1061.0	1086.8	1111.9	1120.5	1086.1	978.9
107.5°	1175.5	1175.3	1170.2	1163.9	1170.2	1175.3	1175.5	1162.8	1122.0	1033.7	890.7
110°	1186.1	1201.0	1206.5	1206.5	1206.5	1201.0	1186.1	1150.9	1084.5	974.2	825.7



TEST NUMBER: P333564

CATALOG NUMBER: S125RDIP-S850D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1156.7	1182.2	1195.8	1201.5	1195.8	1182.2	1156.7	1105.3	1026.9	915.4	774.4
115°	1084.5	1122.0	1143.9	1154.1	1143.9	1122.0	1084.5	1023.5	938.3	831.2	710.0
117.5°	1004.3	1043.0	1064.8	1071.0	1064.8	1043.0	1004.3	943.3	865.1	772.8	668.4
120°	952.3	989.9	1011.0	1017.2	1011.0	989.9	952.3	894.5	825.7	739.7	645.8
122.5°	908.6	943.0	964.1	969.7	964.1	943.0	908.6	857.0	792.5	715.9	629.0
125°	852.3	884.3	901.5	909.3	901.5	884.3	852.3	808.5	752.2	684.2	604.4
127.5°	809.7	838.0	854.3	857.7	854.3	838.0	809.7	770.0	717.3	653.8	579.4
130°	783.5	809.3	824.9	829.6	824.9	809.3	783.5	744.4	693.5	632.6	563.7
132.5°	755.9	781.7	796.1	801.4	796.1	781.7	755.9	716.8	667.9	612.5	548.1
135°	710.7	736.5	750.6	755.3	750.6	736.5	710.7	676.3	631.8	581.7	527.8
137.5°	664.5	687.9	700.9	706.1	700.9	687.9	664.5	633.6	595.8	554.2	510.6
140°	635.7	656.0	667.7	671.6	667.7	656.0	635.7	606.7	573.9	537.9	501.2
142.5°	608.2	625.4	636.5	639.7	636.5	625.4	608.2	583.6	555.1	524.2	493.1
145°	570.8	584.1	592.7	595.8	592.7	584.1	570.8	552.0	530.9	506.7	482.4
147.5°	541.5	552.2	557.2	558.6	557.2	552.2	541.5	526.7	510.7	492.1	472.4
150°	524.7	534.0	537.2	537.9	537.2	534.0	524.7	512.9	498.8	484.0	466.8
152.5°	510.3	517.8	520.9	521.7	520.9	517.8	510.3	500.4	489.5	475.9	460.5
155°	491.0	496.5	498.8	499.6	498.8	496.5	491.0	483.2	474.6	463.7	451.2
157.5°	473.4	477.9	480.1	479.9	480.1	477.9	473.4	467.3	460.5	452.1	441.8
160°	462.1	466.0	467.6	466.8	467.6	466.0	462.1	456.6	451.2	443.3	435.5
162.5°	451.5	454.7	455.1	454.9	455.1	454.7	451.5	447.2	442.4	435.8	428.6
165°	436.3	437.9	437.9	437.9	437.9	437.9	436.3	433.2	429.3	424.6	419.1
167.5°	421.6	423.0	422.4	422.2	422.4	423.0	421.6	420.0	417.2	413.6	410.0
170°	412.8	413.6	413.6	412.8	413.6	413.6	412.8	411.3	409.7	407.4	405.0
172.5°	404.7	406.1	404.9	404.1	404.9	406.1	404.7	404.4	403.5	401.7	399.4
175°	394.9	395.6	394.1	393.3	394.1	395.6	394.9	394.9	394.9	393.3	393.3
177.5°	389.1	389.7	387.8	387.8	387.8	389.7	389.1	389.7	389.7	389.7	389.1
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P333564

CATALOG NUMBER: S125RDIP-S850D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1212.6	1217.1	1219.6	1225.4	1233.7	1237.9	1243.7	1247.9	1253.7	1260.7	1266.6
5°	1134.0	1146.5	1154.8	1167.8	1179.7	1191.7	1206.7	1217.6	1232.2	1248.8	1261.8
7.5°	1061.1	1076.7	1090.5	1107.7	1127.4	1142.8	1162.4	1182.4	1205.2	1228.8	1251.0
10°	1014.6	1030.2	1047.3	1068.6	1088.3	1109.1	1132.5	1155.8	1184.4	1210.9	1241.0
12.5°	968.5	985.7	1005.0	1028.7	1052.6	1079.2	1103.0	1129.3	1159.9	1194.3	1226.5
15°	911.3	927.9	948.7	968.9	996.4	1025.5	1057.2	1092.0	1126.3	1164.7	1204.7
17.5°	849.9	868.2	891.0	914.5	943.5	977.5	1008.6	1046.7	1085.2	1130.0	1177.0
20°	810.0	828.7	855.7	881.7	908.2	941.4	978.3	1017.2	1058.2	1105.5	1157.9
22.5°	778.5	791.8	818.3	844.7	875.8	909.8	945.9	986.5	1031.2	1080.1	1135.1
25°	731.6	747.2	766.4	793.9	826.1	862.0	898.3	941.4	990.2	1040.1	1098.7
27.5°	690.0	702.8	721.8	743.4	775.4	812.6	851.3	896.2	946.3	997.1	1058.7
30°	660.5	674.5	692.7	715.5	741.0	781.5	820.9	865.1	916.0	968.4	1031.7
32.5°	634.7	649.2	664.8	686.4	714.0	749.9	790.6	833.9	885.6	939.7	1001.4
35°	598.7	608.6	623.1	644.4	671.4	700.5	742.0	787.7	838.1	894.1	955.9
37.5°	557.4	570.1	584.6	603.1	626.7	658.2	696.8	743.0	789.8	843.5	899.9
40°	533.3	545.2	561.3	574.8	599.7	628.3	663.6	711.9	758.6	809.0	860.4
42.5°	508.8	520.3	533.9	550.7	573.1	600.9	633.7	678.7	728.7	776.2	819.3
45°	470.4	482.4	495.4	510.9	531.7	558.7	591.4	632.4	676.1	719.7	752.4
47.5°	433.8	445.0	457.3	473.2	492.4	518.4	547.7	583.9	626.3	663.4	686.8
50°	407.6	418.0	431.5	447.1	465.8	490.2	518.2	554.0	589.3	623.1	644.4
52.5°	381.9	393.5	407.0	420.5	438.4	462.8	488.7	519.6	553.2	580.7	598.3
55°	343.2	354.1	366.6	380.6	398.3	419.0	446.6	471.0	497.4	520.8	531.2
57.5°	305.9	315.5	327.2	341.8	357.7	377.0	398.8	422.3	440.9	457.5	469.2
60°	281.4	289.7	300.6	313.1	330.2	347.9	367.6	389.4	404.0	418.0	428.9
62.5°	256.5	264.4	274.9	286.1	301.2	317.6	336.5	354.1	368.3	377.7	390.3
65°	219.1	226.9	235.7	247.7	259.6	273.1	290.3	303.2	313.1	323.5	331.3
67.5°	184.3	190.8	199.2	208.5	218.6	231.6	244.9	255.7	262.4	268.7	278.0
70°	161.5	166.7	173.4	180.7	191.6	204.6	215.0	223.3	228.0	234.2	245.6
72.5°	138.2	144.2	150.6	157.9	166.7	177.6	186.7	195.0	198.0	203.0	210.3
75°	109.0	112.2	117.4	122.5	128.8	138.1	146.9	149.0	151.6	155.8	161.0
77.5°	82.5	85.3	87.3	90.8	95.7	103.2	107.9	111.0	111.6	113.2	118.3
80°	65.4	67.0	69.1	71.7	73.7	80.0	82.6	85.7	86.7	88.3	90.9
82.5°	48.0	49.5	50.8	53.0	56.3	58.8	61.4	64.5	64.7	65.8	66.4
85°	28.0	28.6	27.5	28.6	29.1	30.1	32.7	35.3	34.8	34.3	35.8
87.5°	12.6	12.5	11.7	12.8	11.7	11.9	11.6	11.7	12.3	12.8	13.4
90°	13.3	12.5	10.9	10.2	8.6	7.8	6.3	4.7	3.1	1.6	0.8
92.5°	204.1	252.1	256.1	178.4	106.8	64.1	41.3	27.8	18.1	11.6	9.5
95°	677.9	692.8	565.3	349.5	177.5	93.8	58.6	41.4	32.8	26.6	25.8
97.5°	857.7	739.8	504.8	279.0	152.9	97.6	72.2	56.8	48.2	43.8	42.8
100°	901.5	706.1	450.4	253.3	151.7	106.3	82.9	68.0	59.4	56.3	54.7
102.5°	875.3	646.6	409.1	242.7	157.3	117.0	94.1	80.5	71.3	68.8	67.9
105°	791.3	566.9	369.1	238.5	168.9	134.5	112.6	100.1	92.3	88.4	88.4
107.5°	705.6	512.0	352.2	245.7	186.1	152.8	133.1	120.1	113.7	109.9	108.4
110°	656.8	486.3	347.2	252.6	198.6	166.5	146.2	134.5	127.4	124.3	122.8



TEST NUMBER: P333564

CATALOG NUMBER: S125RDIP-S850D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	620.5	471.3	347.2	261.3	210.5	179.7	160.0	148.2	141.2	138.7	137.1
115°	580.9	455.1	349.5	274.4	229.1	200.2	180.6	168.9	161.9	159.5	157.9
117.5°	557.3	447.1	354.7	289.5	248.2	220.8	201.9	188.6	181.6	179.1	176.7
120°	544.2	443.3	359.7	299.5	261.9	234.6	215.0	201.7	194.7	191.6	189.2
122.5°	532.9	440.2	364.0	310.7	275.1	247.7	228.2	213.6	206.6	204.1	202.4
125°	517.6	436.3	371.4	326.0	292.4	266.6	246.3	231.4	224.4	220.5	218.9
127.5°	503.5	434.4	379.7	340.1	309.2	284.3	264.0	248.2	239.3	234.3	231.9
130°	494.2	433.2	384.7	349.5	319.8	295.6	275.2	258.8	248.6	242.4	240.0
132.5°	486.7	433.2	390.3	357.6	329.8	305.6	285.2	268.2	256.8	249.3	246.3
135°	477.7	433.2	398.0	369.1	343.3	319.0	297.9	281.5	269.0	259.6	256.5
137.5°	469.8	434.1	405.0	377.5	352.8	330.7	309.0	292.9	280.4	271.6	269.3
140°	466.0	434.7	408.1	383.1	359.7	337.0	315.9	301.0	288.5	279.1	276.8
142.5°	462.9	435.4	410.0	386.3	364.0	342.6	322.8	308.5	296.0	287.3	285.5
145°	458.2	434.7	412.1	390.9	371.4	351.1	333.1	319.0	308.1	300.2	298.7
147.5°	453.3	432.7	412.8	393.8	376.1	358.3	342.5	330.3	320.1	313.4	312.4
150°	449.6	430.8	412.8	395.6	379.2	362.0	348.7	337.8	327.6	322.1	320.6
152.5°	445.2	428.3	412.2	396.9	382.3	366.4	354.4	344.0	335.1	330.3	329.3
155°	437.9	423.8	410.5	398.0	385.5	372.2	361.2	353.4	345.6	340.9	340.9
157.5°	431.0	419.1	408.5	398.8	388.1	376.7	368.4	361.5	354.8	351.1	351.2
160°	425.4	416.0	406.6	398.8	389.4	379.2	372.2	365.9	360.5	357.3	358.1
162.5°	420.3	412.2	404.7	398.1	390.6	381.7	375.9	370.9	366.1	363.0	363.7
165°	412.8	406.6	401.9	397.2	390.9	384.7	380.0	376.9	373.0	370.6	372.2
167.5°	405.5	401.1	397.5	395.3	390.9	385.8	382.8	380.6	378.4	377.0	377.8
170°	401.1	398.0	395.6	394.1	390.9	387.0	384.7	383.1	381.6	380.8	381.6
172.5°	396.7	394.2	393.1	392.8	390.3	387.0	385.9	385.0	383.4	382.7	384.1
175°	390.9	390.2	390.2	390.9	389.4	387.0	387.0	387.0	386.3	385.5	387.0
177.5°	388.4	387.8	387.8	389.1	388.4	387.2	387.2	387.8	387.2	387.2	388.4
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P333564

CATALOG NUMBER: S125RDIP-S850D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1271.1	1274.9	1280.3	1286.5	1291.5	1296.9	1299.8	1299.8	1302.3	1307.7	1314.7
5°	1274.8	1288.3	1301.2	1317.9	1330.8	1345.9	1357.3	1368.2	1378.1	1390.5	1403.5
7.5°	1273.7	1296.1	1319.5	1345.7	1374.6	1397.5	1421.1	1439.6	1457.8	1481.7	1500.5
10°	1269.6	1298.6	1330.3	1363.5	1399.9	1431.6	1460.1	1486.1	1511.0	1537.0	1560.3
12.5°	1262.1	1299.1	1337.8	1377.7	1423.6	1459.8	1496.7	1524.3	1553.4	1581.8	1610.6
15°	1250.9	1294.5	1341.2	1396.8	1452.9	1493.4	1529.7	1565.5	1592.5	1624.7	1652.3
17.5°	1227.7	1283.9	1342.7	1403.4	1457.3	1504.4	1542.5	1576.5	1605.3	1640.7	1678.1
20°	1214.0	1274.8	1336.0	1400.9	1452.3	1500.6	1537.5	1572.8	1608.6	1654.8	1700.5
22.5°	1194.9	1259.8	1324.8	1386.4	1440.7	1487.3	1525.4	1568.7	1615.7	1668.1	1723.4
25°	1164.7	1231.7	1296.0	1354.7	1407.7	1455.5	1507.4	1565.5	1622.7	1691.7	1771.2
27.5°	1126.4	1190.9	1248.4	1310.4	1363.0	1423.8	1488.6	1551.6	1634.0	1729.0	1828.2
30°	1097.7	1159.0	1213.5	1272.2	1331.9	1398.9	1471.6	1545.8	1643.9	1755.6	1873.5
32.5°	1064.5	1119.9	1174.0	1230.6	1299.5	1373.1	1450.4	1541.2	1658.5	1785.5	1907.5
35°	1006.8	1056.7	1109.1	1171.9	1245.2	1325.1	1423.8	1534.4	1676.1	1812.7	1922.3
37.5°	946.4	985.7	1038.4	1104.7	1184.4	1276.9	1388.9	1523.3	1668.9	1791.4	1838.0
40°	899.9	936.7	992.3	1061.9	1140.8	1242.0	1367.7	1505.8	1652.3	1737.4	1733.8
42.5°	853.7	891.0	944.5	1014.5	1096.8	1210.1	1339.5	1483.0	1606.6	1639.0	1571.4
45°	783.0	817.8	870.3	940.9	1029.2	1148.1	1284.1	1421.7	1500.6	1448.2	1314.2
47.5°	711.0	744.7	793.4	862.6	958.9	1083.4	1212.0	1324.9	1336.0	1223.4	1062.7
50°	663.6	695.3	741.5	815.2	908.7	1030.2	1154.3	1243.1	1215.6	1078.0	912.3
52.5°	617.5	647.9	691.2	760.8	856.3	975.4	1086.2	1155.8	1092.2	945.9	796.8
55°	549.4	578.4	622.1	685.9	772.6	881.7	978.8	1004.2	910.8	763.3	642.8
57.5°	484.7	506.0	549.1	605.5	689.1	785.3	854.9	850.3	747.2	614.4	528.0
60°	441.9	461.1	502.1	554.0	633.5	719.7	768.5	747.7	643.3	533.8	450.7
62.5°	402.0	420.0	454.3	502.1	570.3	645.3	680.8	652.2	553.6	457.4	391.3
65°	341.7	354.6	382.2	426.3	479.8	531.7	563.4	521.3	434.1	361.4	311.5
67.5°	285.3	296.5	321.0	352.7	389.5	425.4	438.2	398.8	331.0	282.0	246.9
70°	248.7	259.1	275.7	305.3	329.7	355.2	361.4	326.1	269.5	232.1	210.3
72.5°	213.8	223.4	237.9	258.8	275.7	290.4	293.3	260.5	217.1	191.4	174.6
75°	163.0	171.4	180.7	188.5	199.4	202.0	200.9	175.5	152.1	135.0	125.7
77.5°	119.8	123.3	129.0	132.1	132.6	132.4	127.1	111.0	99.0	91.9	88.1
80°	92.4	95.0	96.6	97.6	98.1	92.9	87.2	77.4	73.2	69.1	64.4
82.5°	67.1	68.9	70.4	70.6	67.8	63.5	58.2	53.3	50.4	48.3	46.5
85°	36.3	36.9	36.3	33.8	30.1	28.6	27.5	26.5	26.0	25.4	25.4
87.5°	13.2	12.3	10.5	11.2	11.5	11.3	11.6	11.3	11.2	11.4	11.5
90°	1.6	3.1	4.7	6.3	7.8	8.6	10.2	10.9	12.5	13.3	14.1
92.5°	11.6	18.1	27.8	41.3	64.1	106.8	178.4	256.1	252.1	204.1	138.6
95°	26.6	32.8	41.4	58.6	93.8	177.5	349.5	565.3	692.8	677.9	562.2
97.5°	43.8	48.2	56.8	72.2	97.6	152.9	279.0	504.8	739.8	857.7	837.3
100°	56.3	59.4	68.0	82.9	106.3	151.7	253.3	450.4	706.1	901.5	961.7
102.5°	68.8	71.3	80.5	94.1	117.0	157.3	242.7	409.1	646.6	875.3	1003.6
105°	88.4	92.3	100.1	112.6	134.5	168.9	238.5	369.1	566.9	791.3	978.9
107.5°	109.9	113.7	120.1	133.1	152.8	186.1	245.7	352.2	512.0	705.6	890.7
110°	124.3	127.4	134.5	146.2	166.5	198.6	252.6	347.2	486.3	656.8	825.7





TEST NUMBER: P333564

CATALOG NUMBER: S125RDIP-S850D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	138.7	141.2	148.2	160.0	179.7	210.5	261.3	347.2	471.3	620.5	774.4
115°	159.5	161.9	168.9	180.6	200.2	229.1	274.4	349.5	455.1	580.9	710.0
117.5°	179.1	181.6	188.6	201.9	220.8	248.2	289.5	354.7	447.1	557.3	668.4
120°	191.6	194.7	201.7	215.0	234.6	261.9	299.5	359.7	443.3	544.2	645.8
122.5°	204.1	206.6	213.6	228.2	247.7	275.1	310.7	364.0	440.2	532.9	629.0
125°	220.5	224.4	231.4	246.3	266.6	292.4	326.0	371.4	436.3	517.6	604.4
127.5°	234.3	239.3	248.2	264.0	284.3	309.2	340.1	379.7	434.4	503.5	579.4
130°	242.4	248.6	258.8	275.2	295.6	319.8	349.5	384.7	433.2	494.2	563.7
132.5°	249.3	256.8	268.2	285.2	305.6	329.8	357.6	390.3	433.2	486.7	548.1
135°	259.6	269.0	281.5	297.9	319.0	343.3	369.1	398.0	433.2	477.7	527.8
137.5°	271.6	280.4	292.9	309.0	330.7	352.8	377.5	405.0	434.1	469.8	510.6
140°	279.1	288.5	301.0	315.9	337.0	359.7	383.1	408.1	434.7	466.0	501.2
142.5°	287.3	296.0	308.5	322.8	342.6	364.0	386.3	410.0	435.4	462.9	493.1
145°	300.2	308.1	319.0	333.1	351.1	371.4	390.9	412.1	434.7	458.2	482.4
147.5°	313.4	320.1	330.3	342.5	358.3	376.1	393.8	412.8	432.7	453.3	472.4
150°	322.1	327.6	337.8	348.7	362.0	379.2	395.6	412.8	430.8	449.6	466.8
152.5°	330.3	335.1	344.0	354.4	366.4	382.3	396.9	412.2	428.3	445.2	460.5
155°	340.9	345.6	353.4	361.2	372.2	385.5	398.0	410.5	423.8	437.9	451.2
157.5°	351.1	354.8	361.5	368.4	376.7	388.1	398.8	408.5	419.1	431.0	441.8
160°	357.3	360.5	365.9	372.2	379.2	389.4	398.8	406.6	416.0	425.4	435.5
162.5°	363.0	366.1	370.9	375.9	381.7	390.6	398.1	404.7	412.2	420.3	428.6
165°	370.6	373.0	376.9	380.0	384.7	390.9	397.2	401.9	406.6	412.8	419.1
167.5°	377.0	378.4	380.6	382.8	385.8	390.9	395.3	397.5	401.1	405.5	410.0
170°	380.8	381.6	383.1	384.7	387.0	390.9	394.1	395.6	398.0	401.1	405.0
172.5°	382.7	383.4	385.0	385.9	387.0	390.3	392.8	393.1	394.2	396.7	399.4
175°	385.5	386.3	387.0	387.0	387.0	389.4	390.9	390.2	390.2	390.9	393.3
177.5°	387.2	387.2	387.8	387.2	387.2	388.4	389.1	387.8	387.8	388.4	389.1
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P333564

CATALOG NUMBER: S125RDIP-S850D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1320.1	1320.1	1327.2	1326.8	1331.4	1329.7	1330.5
5°	1419.1	1427.9	1435.7	1440.9	1448.7	1450.8	1449.7
7.5°	1521.7	1541.3	1550.9	1564.0	1566.4	1573.2	1572.5
10°	1585.3	1604.5	1619.0	1630.4	1636.2	1643.4	1643.9
12.5°	1635.1	1651.4	1664.3	1674.9	1681.8	1684.1	1685.5
15°	1674.1	1692.2	1707.3	1722.3	1731.2	1737.9	1741.6
17.5°	1713.3	1741.4	1767.9	1788.4	1800.7	1811.0	1810.9
20°	1743.6	1775.8	1809.1	1832.4	1856.3	1866.7	1868.3
22.5°	1776.0	1825.3	1868.1	1904.3	1935.7	1946.5	1950.5
25°	1843.3	1907.7	1973.7	2024.6	2060.9	2082.2	2085.3
27.5°	1924.6	2011.8	2081.2	2128.1	2158.3	2174.1	2177.5
30°	1982.0	2062.5	2124.8	2160.1	2174.1	2176.2	2168.4
32.5°	2007.7	2067.9	2092.8	2090.7	2063.2	2044.9	2037.9
35°	1976.3	1963.8	1903.0	1830.4	1774.8	1739.5	1730.1
37.5°	1798.5	1691.0	1579.2	1469.4	1410.9	1381.2	1330.1
40°	1623.2	1470.0	1353.7	1261.3	1195.3	1142.3	1129.9
42.5°	1425.4	1267.3	1151.0	1071.8	1019.2	982.8	967.0
45°	1145.5	1009.4	913.4	852.6	812.1	785.6	773.7
47.5°	916.2	810.9	740.9	695.9	665.1	642.0	635.6
50°	790.3	706.2	647.0	609.1	585.7	568.1	560.8
52.5°	686.4	618.5	573.0	541.8	519.7	508.7	502.6
55°	566.5	507.8	475.1	450.2	437.7	428.9	424.7
57.5°	463.3	420.9	397.0	379.8	368.3	362.6	360.6
60°	405.5	372.3	350.5	337.0	329.2	321.9	319.9
62.5°	354.4	328.3	311.4	299.6	291.8	288.7	287.5
65°	285.6	268.5	256.0	248.7	242.5	241.5	240.9
67.5°	227.0	216.9	210.4	202.8	200.6	197.0	196.3
70°	194.2	187.4	179.7	177.1	174.5	170.8	171.4
72.5°	164.7	158.0	152.7	149.2	148.3	146.7	148.1
75°	120.5	118.4	116.3	113.7	112.7	112.7	112.2
77.5°	86.0	84.2	81.9	80.4	80.1	77.9	78.7
80°	62.3	59.7	58.7	59.2	57.6	57.1	57.1
82.5°	46.1	45.2	44.1	44.2	43.9	43.4	43.8
85°	25.4	24.9	24.9	24.4	24.4	23.9	23.9
87.5°	12.1	12.7	12.2	11.7	11.7	12.3	12.7
90°	14.9	15.6	17.2	17.2	17.2	18.0	18.0
92.5°	100.6	75.7	64.1	54.1	52.2	51.1	49.9
95°	443.3	347.2	281.5	226.0	202.5	196.3	183.7
97.5°	753.9	660.2	568.9	520.6	476.8	454.1	444.1
100°	923.4	842.9	761.6	707.6	651.3	622.4	609.9
102.5°	1027.3	988.6	933.6	875.9	835.8	804.4	795.0
105°	1086.1	1120.5	1111.9	1086.8	1061.0	1045.4	1036.0
107.5°	1033.7	1122.0	1162.8	1175.5	1175.3	1170.2	1163.9
110°	974.2	1084.5	1150.9	1186.1	1201.0	1206.5	1206.5



TEST NUMBER: P333564

CATALOG NUMBER: S125RDIP-S850D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	915.4	1026.9	1105.3	1156.7	1182.2	1195.8	1201.5
115°	831.2	938.3	1023.5	1084.5	1122.0	1143.9	1154.1
117.5°	772.8	865.1	943.3	1004.3	1043.0	1064.8	1071.0
120°	739.7	825.7	894.5	952.3	989.9	1011.0	1017.2
122.5°	715.9	792.5	857.0	908.6	943.0	964.1	969.7
125°	684.2	752.2	808.5	852.3	884.3	901.5	909.3
127.5°	653.8	717.3	770.0	809.7	838.0	854.3	857.7
130°	632.6	693.5	744.4	783.5	809.3	824.9	829.6
132.5°	612.5	667.9	716.8	755.9	781.7	796.1	801.4
135°	581.7	631.8	676.3	710.7	736.5	750.6	755.3
137.5°	554.2	595.8	633.6	664.5	687.9	700.9	706.1
140°	537.9	573.9	606.7	635.7	656.0	667.7	671.6
142.5°	524.2	555.1	583.6	608.2	625.4	636.5	639.7
145°	506.7	530.9	552.0	570.8	584.1	592.7	595.8
147.5°	492.1	510.7	526.7	541.5	552.2	557.2	558.6
150°	484.0	498.8	512.9	524.7	534.0	537.2	537.9
152.5°	475.9	489.5	500.4	510.3	517.8	520.9	521.7
155°	463.7	474.6	483.2	491.0	496.5	498.8	499.6
157.5°	452.1	460.5	467.3	473.4	477.9	480.1	479.9
160°	443.3	451.2	456.6	462.1	466.0	467.6	466.8
162.5°	435.8	442.4	447.2	451.5	454.7	455.1	454.9
165°	424.6	429.3	433.2	436.3	437.9	437.9	437.9
167.5°	413.6	417.2	420.0	421.6	423.0	422.4	422.2
170°	407.4	409.7	411.3	412.8	413.6	413.6	412.8
172.5°	401.7	403.5	404.4	404.7	406.1	404.9	404.1
175°	393.3	394.9	394.9	394.9	395.6	394.1	393.3
177.5°	389.7	389.7	389.7	389.1	389.7	387.8	387.8
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8

(END OF REPORT)