

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333519-927

Luminaire Tested: **S125RDIP-S375D1205U927-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333519-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S375D1205U927-4F0-1E-UDD-F4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4571.5 lumens  
Efficiency: N/A  
Efficacy: 108.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 42.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333519-927

CATALOG NUMBER: S125RDIP-S375D1205U927-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P333519-927

CATALOG NUMBER: S125RDIP-S375D1205U927-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	33	33	33	25
1	92	88	84	81	82	79	76	73	61	59	57	45	43	42	29	29	28	21
2	84	77	71	66	75	69	64	60	53	50	47	39	37	35	26	25	24	18
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	23	22	20	15
4	70	60	52	47	62	54	47	42	42	37	34	31	28	26	21	19	18	13
5	64	53	46	40	57	48	41	36	37	33	29	28	25	22	19	17	15	12
6	59	48	40	34	52	43	36	31	34	29	25	25	22	19	17	15	14	10
7	55	43	35	30	48	39	32	27	30	26	22	23	19	17	15	14	12	9
8	50	39	31	26	45	35	28	24	28	23	20	21	17	15	14	12	11	8
9	47	35	28	23	42	32	26	21	25	21	17	19	16	14	13	11	10	7
10	44	32	25	21	39	29	23	19	23	19	16	17	14	12	12	10	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3130	3130	3130
5°	3138	3102	3121
10°	3114	3074	3074
15°	3077	3011	2986
20°	3030	2924	2889
25°	2974	2838	2776
30°	2905	2738	2651
35°	2834	2636	2511
40°	2769	2528	2373
45°	2689	2408	2223
50°	2608	2277	2067
55°	2514	2152	1901
60°	2421	2001	1721
65°	2311	1825	1516
70°	2185	1603	1307
75°	2011	1352	1088
80°	1770	1060	915
85°	1489	867	815



TEST NUMBER: P333519-927

CATALOG NUMBER: S125RDIP-S375D1205U927-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	45.6	1.0
10°-20°	127.4	2.8
20°-30°	184.7	4.0
30°-40°	210.5	4.6
40°-50°	205.2	4.5
50°-60°	172.7	3.8
60°-70°	121.1	2.6
70°-80°	62.2	1.4
80°-90°	18.3	0.4
90°-100°	330.9	7.2
100°-110°	711.4	15.6
110°-120°	667.6	14.6
120°-130°	541.1	11.8
130°-140°	434.2	9.5
140°-150°	327.7	7.2
150°-160°	230.6	5.0
160°-170°	136.0	3.0
170°-180°	44.2	1.0
0°-30°	357.7	7.8
0°-40°	568.2	12.4
0°-60°	946.1	20.7
0°-90°	1147.7	25.1
90°-120°	1710.0	37.4
90°-150°	3013.0	65.9
90°-180°	3424.0	74.9
0°-180°	4571.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	485	485	485	485	485	
5°	484	482	478	482	481	46
15°	460	458	450	450	447	130
25°	417	411	398	394	390	192
35°	360	350	334	324	318	225
45°	294	283	264	249	243	227
55°	223	211	191	175	169	200
65°	151	138	119	105	99	150
75°	81	69	54	46	44	85
85°	20	14	12	11	11	23
90°	1	8	15	19	21	3
95°	30	90	816	370	216	32
105°	104	145	667	1314	1220	110
115°	186	224	536	1155	1359	183
125°	258	302	514	919	1071	229
135°	302	363	510	770	889	234
145°	352	403	512	637	701	220
155°	401	432	499	564	588	185
165°	438	450	479	508	516	123
175°	456	456	459	465	463	43
180°	456	456	456	456	456	



TEST NUMBER: P333519-927

CATALOG NUMBER: S125RDIP-S375D1205U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7
2.5°	485.6	485.4	485.2	485.1	484.8	484.4	483.8	483.1	482.4	481.8	482.4
5°	484.0	483.7	483.4	483.0	482.7	482.1	481.2	480.3	479.4	478.5	479.3
7.5°	479.3	479.0	478.6	478.3	478.0	477.3	476.3	475.2	474.1	473.0	473.6
10°	474.8	474.6	474.4	474.1	473.9	473.2	472.1	470.9	469.8	468.7	468.9
12.5°	469.8	469.5	469.3	469.0	468.7	467.7	466.2	464.7	463.1	461.6	461.8
15°	460.2	459.7	459.2	458.8	458.3	457.2	455.4	453.8	452.0	450.4	450.3
17.5°	449.3	448.5	447.8	447.0	446.3	444.9	442.7	440.5	438.4	436.3	435.9
20°	440.8	440.0	439.2	438.4	437.5	435.9	433.2	430.6	428.0	425.4	425.0
22.5°	431.4	430.6	429.8	429.0	428.2	426.4	423.7	421.0	418.2	415.5	414.7
25°	417.4	416.1	414.9	413.7	412.5	410.4	407.3	404.3	401.3	398.3	397.3
27.5°	401.2	399.8	398.3	396.8	395.3	393.0	389.8	386.5	383.3	380.1	378.6
30°	389.5	388.0	386.4	384.9	383.3	380.9	377.5	374.1	370.7	367.2	365.4
32.5°	378.1	376.3	374.5	372.7	370.9	368.3	364.8	361.3	357.8	354.3	352.3
35°	359.5	357.6	355.6	353.6	351.7	348.9	345.2	341.6	337.9	334.3	331.9
37.5°	341.3	338.9	336.5	334.1	331.8	328.7	325.0	321.2	317.4	313.6	310.8
40°	328.4	326.0	323.5	321.1	318.6	315.4	311.6	307.7	303.7	299.8	296.8
42.5°	314.9	312.4	309.9	307.4	304.9	301.7	297.6	293.6	289.5	285.5	282.6
45°	294.4	292.0	289.6	287.2	284.9	281.5	277.0	272.6	268.1	263.6	260.3
47.5°	273.1	270.5	268.1	265.5	263.1	259.6	255.1	250.6	246.1	241.5	238.2
50°	259.6	256.9	254.2	251.5	248.8	245.2	240.5	235.9	231.2	226.6	223.2
52.5°	244.9	242.2	239.4	236.7	233.9	230.4	226.0	221.6	217.2	212.9	209.2
55°	223.3	220.7	218.1	215.6	212.9	209.4	204.8	200.2	195.7	191.1	187.4
57.5°	201.5	198.8	195.9	193.1	190.4	186.8	182.4	178.0	173.6	169.2	165.6
60°	187.4	184.6	181.7	178.9	176.0	172.5	168.0	163.7	159.2	154.9	151.3
62.5°	172.5	169.8	167.1	164.4	161.6	158.0	153.6	149.2	144.7	140.2	136.9
65°	151.2	148.5	145.7	142.9	140.1	136.6	132.3	128.0	123.7	119.4	116.1
67.5°	130.1	127.3	124.5	121.8	119.0	115.5	111.4	107.3	103.1	99.0	96.0
70°	115.7	113.0	110.2	107.4	104.6	101.2	97.1	93.1	89.0	84.9	82.4
72.5°	101.6	98.9	96.3	93.6	90.9	87.5	83.7	79.9	76.1	72.3	70.0
75°	80.6	78.1	75.7	73.2	70.8	67.9	64.4	61.0	57.6	54.2	52.4
77.5°	59.6	57.7	55.7	53.7	51.8	49.4	46.7	44.0	41.3	38.5	37.2
80°	47.6	45.6	43.7	41.7	39.8	37.7	35.4	33.1	30.8	28.5	27.8
82.5°	35.9	34.1	32.4	30.6	28.8	27.2	25.7	24.1	22.5	20.9	20.6
85°	20.1	18.7	17.2	15.8	14.3	13.3	12.9	12.5	12.1	11.7	11.6
87.5°	6.9	6.7	6.6	6.5	6.4	6.5	6.6	6.9	7.1	7.4	7.5
90°	1.0	1.8	3.6	5.5	7.4	9.2	10.1	12.0	12.9	14.7	15.7
92.5°	11.2	13.6	21.4	32.8	48.6	75.5	125.7	210.1	301.6	296.8	240.3
95°	30.3	31.3	38.7	48.8	69.0	110.4	209.0	411.5	665.5	815.6	798.0
97.5°	50.5	51.6	56.7	66.9	85.1	114.9	180.1	328.4	594.3	870.9	1009.8
100°	64.4	66.3	69.9	80.1	97.6	125.2	178.6	298.3	530.2	831.2	1061.3
102.5°	79.9	81.0	84.0	94.8	110.8	137.7	185.2	285.7	481.6	761.2	1030.4
105°	104.0	104.0	108.6	117.8	132.5	158.4	198.8	280.7	434.4	667.3	931.5
107.5°	127.5	129.4	133.8	141.4	156.7	179.8	219.0	289.2	414.5	602.7	830.7
110°	144.5	146.4	150.0	158.4	172.1	196.1	233.8	297.3	408.7	572.5	773.2



TEST NUMBER: P333519-927

CATALOG NUMBER: S125RDIP-S375D1205U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	161.4	163.3	166.2	174.5	188.3	211.5	247.8	307.6	408.7	554.8	730.5
115°	185.9	187.7	190.5	198.8	212.6	235.7	269.7	323.1	411.5	535.8	683.9
117.5°	208.0	210.8	213.7	222.0	237.7	259.9	292.2	340.8	417.6	526.3	656.1
120°	222.8	225.5	229.2	237.5	253.1	276.2	308.4	352.5	423.4	521.9	640.6
122.5°	238.2	240.3	243.2	251.4	268.6	291.6	323.8	365.8	428.6	518.2	627.4
125°	257.7	259.6	264.2	272.4	289.9	313.9	344.3	383.8	437.2	513.7	609.3
127.5°	273.0	275.8	281.7	292.2	310.8	334.7	363.9	400.4	446.9	511.4	592.8
130°	282.6	285.3	292.7	304.7	324.0	347.9	376.4	411.5	452.9	509.9	581.8
132.5°	289.9	293.4	302.3	315.8	335.8	359.7	388.2	421.0	459.5	509.9	572.9
135°	301.9	305.6	316.6	331.4	350.7	375.6	404.1	434.4	468.5	509.9	562.4
137.5°	317.0	319.8	330.1	344.8	363.8	389.4	415.3	444.4	476.8	511.0	553.0
140°	325.8	328.6	339.7	354.4	371.9	396.7	423.4	451.1	480.5	511.7	548.6
142.5°	336.1	338.2	348.5	363.2	380.0	403.4	428.6	454.7	482.7	512.5	544.9
145°	351.6	353.5	362.7	375.6	392.1	413.3	437.2	460.3	485.1	511.7	539.4
147.5°	367.8	368.9	376.8	388.8	403.1	421.8	442.8	463.6	486.0	509.4	533.7
150°	377.4	379.2	385.7	397.7	410.5	426.2	446.4	465.8	486.0	507.2	529.3
152.5°	387.7	388.8	394.5	405.0	417.2	431.3	450.1	467.2	485.3	504.2	524.1
155°	401.3	401.3	406.9	416.1	425.2	438.2	453.8	468.5	483.2	498.9	515.5
157.5°	413.5	413.3	417.7	425.6	433.7	443.5	456.9	469.4	480.9	493.4	507.4
160°	421.6	420.6	424.4	430.8	438.2	446.4	458.4	469.4	478.6	489.7	500.7
162.5°	428.2	427.3	430.9	436.7	442.6	449.4	459.9	468.7	476.4	485.3	494.9
165°	438.2	436.3	439.1	443.7	447.3	452.9	460.3	467.6	473.1	478.6	486.0
167.5°	444.8	443.9	445.5	448.1	450.7	454.2	460.3	465.4	467.9	472.2	477.4
170°	449.2	448.3	449.2	451.1	452.9	455.7	460.3	463.9	465.8	468.5	472.2
172.5°	452.2	450.5	451.4	453.2	454.3	455.7	459.5	462.5	462.8	464.1	467.1
175°	455.7	453.8	454.7	455.7	455.7	455.7	458.4	460.3	459.3	459.3	460.3
177.5°	457.3	455.8	455.8	456.5	455.8	455.8	457.3	458.0	456.5	456.5	457.3
180°	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5



TEST NUMBER: P333519-927

CATALOG NUMBER: S125RDIP-S375D1205U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7
2.5°	483.1	483.8	484.4	484.7	484.7	484.6	484.5	484.4
5°	480.1	480.9	481.7	482.1	482.0	481.7	481.6	481.4
7.5°	474.1	474.8	475.3	475.5	475.3	475.2	475.0	474.8
10°	469.1	469.4	469.6	469.6	469.4	469.1	468.9	468.7
12.5°	461.9	462.2	462.3	462.2	461.8	461.4	461.1	460.7
15°	450.1	450.0	450.0	449.6	448.9	448.1	447.4	446.6
17.5°	435.5	435.1	434.7	434.1	433.6	432.9	432.3	431.7
20°	424.6	424.2	423.8	423.3	422.5	421.8	421.0	420.3
22.5°	413.8	413.0	412.3	411.5	411.0	410.4	409.8	409.2
25°	396.2	395.1	394.1	393.2	392.2	391.3	390.5	389.5
27.5°	377.2	375.7	374.1	373.0	372.2	371.3	370.4	369.6
30°	363.5	361.6	359.7	358.5	357.7	357.0	356.2	355.5
32.5°	350.2	348.2	346.0	344.6	343.6	342.7	341.7	340.9
35°	329.5	327.2	324.8	323.1	321.9	320.8	319.6	318.5
37.5°	307.9	305.1	302.3	300.3	299.2	298.1	297.0	295.9
40°	293.7	290.6	287.5	285.4	284.5	283.5	282.5	281.5
42.5°	279.6	276.6	273.6	271.5	270.1	268.5	267.1	265.7
45°	257.1	253.8	250.6	248.3	247.2	245.9	244.7	243.4
47.5°	234.9	231.5	228.1	225.8	224.4	223.1	221.7	220.4
50°	219.8	216.3	212.9	210.6	209.5	208.2	207.0	205.7
52.5°	205.5	201.8	198.1	195.7	194.5	193.3	192.0	190.8
55°	183.8	180.1	176.5	174.0	172.7	171.3	170.1	168.8
57.5°	162.1	158.5	154.9	152.5	151.4	150.2	149.1	147.9
60°	147.7	144.1	140.5	138.2	136.9	135.7	134.5	133.2
62.5°	133.6	130.2	126.9	124.7	123.4	122.2	121.0	119.8
65°	112.8	109.6	106.3	104.1	102.9	101.6	100.4	99.2
67.5°	93.0	90.1	87.1	85.1	84.1	83.2	82.1	81.2
70°	79.9	77.4	74.9	73.1	72.1	71.1	70.2	69.2
72.5°	67.7	65.4	63.1	61.6	60.9	60.3	59.6	58.9
75°	50.6	48.8	47.1	45.9	45.3	44.7	44.1	43.6
77.5°	36.0	34.8	33.5	32.6	32.2	31.8	31.4	31.0
80°	27.1	26.4	25.7	25.2	25.0	24.9	24.7	24.6
82.5°	20.3	19.9	19.6	19.3	19.3	19.2	19.1	18.9
85°	11.6	11.5	11.4	11.3	11.2	11.2	11.1	11.0
87.5°	7.7	7.9	8.1	8.4	8.3	8.3	8.4	8.3
90°	16.6	17.5	18.4	20.3	20.3	20.3	21.2	21.2
92.5°	163.1	118.4	89.1	75.5	63.7	61.5	60.2	58.7
95°	661.8	521.9	408.7	331.4	266.0	238.4	231.1	216.3
97.5°	985.6	887.6	777.3	669.7	612.8	561.3	534.6	522.8
100°	1132.2	1087.1	992.3	896.5	833.1	766.8	732.7	718.0
102.5°	1181.5	1209.3	1163.9	1099.1	1031.1	984.0	947.0	936.0
105°	1152.5	1278.6	1319.1	1308.9	1279.5	1249.1	1230.7	1219.6
107.5°	1048.6	1216.9	1320.9	1369.0	1383.9	1383.7	1377.6	1370.2
110°	972.0	1146.9	1276.7	1354.9	1396.4	1413.9	1420.3	1420.3





TEST NUMBER: P333519-927

CATALOG NUMBER: S125RDIP-S375D1205U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	911.6	1077.7	1208.9	1301.2	1361.8	1391.8	1407.8	1414.4
115°	835.8	978.5	1104.5	1204.9	1276.7	1320.9	1346.6	1358.6
117.5°	786.8	909.8	1018.4	1110.5	1182.3	1228.0	1253.5	1260.8
120°	760.3	870.8	972.0	1053.0	1121.2	1165.3	1190.2	1197.5
122.5°	740.5	842.8	933.0	1008.8	1069.6	1110.1	1135.0	1141.6
125°	711.5	805.4	885.5	951.8	1003.3	1041.1	1061.3	1070.6
127.5°	682.1	769.7	844.5	906.5	953.2	986.6	1005.8	1009.8
130°	663.7	744.7	816.5	876.3	922.3	952.7	971.1	976.6
132.5°	645.2	721.1	786.2	843.9	889.9	920.3	937.2	943.5
135°	621.3	684.8	743.8	796.2	836.7	867.1	883.7	889.2
137.5°	601.1	652.4	701.4	746.0	782.2	809.8	825.1	831.2
140°	590.0	633.3	675.7	714.3	748.4	772.3	786.1	790.7
142.5°	580.4	617.1	653.6	687.1	716.0	736.2	749.2	753.1
145°	567.9	596.4	625.0	649.8	671.9	687.6	697.8	701.4
147.5°	556.2	579.3	601.3	620.0	637.5	650.1	655.9	657.6
150°	549.5	569.8	587.2	603.8	617.7	628.7	632.4	633.3
152.5°	542.2	560.2	576.2	589.1	600.7	609.5	613.2	614.2
155°	531.1	545.8	558.7	568.9	578.1	584.5	587.2	588.2
157.5°	520.1	532.2	542.2	550.1	557.2	562.6	565.1	565.0
160°	512.7	521.9	531.1	537.6	544.0	548.6	550.5	549.5
162.5°	504.6	513.1	520.8	526.5	531.5	535.4	535.8	535.5
165°	493.4	499.8	505.3	509.9	513.7	515.5	515.5	515.5
167.5°	482.7	487.0	491.2	494.5	496.3	498.0	497.3	497.1
170°	476.8	479.6	482.4	484.2	486.0	487.0	487.0	486.0
172.5°	470.2	472.9	475.0	476.1	476.4	478.1	476.7	475.7
175°	463.0	463.0	464.9	464.9	464.9	465.8	463.9	463.0
177.5°	458.0	458.8	458.8	458.8	458.0	458.8	456.5	456.5
180°	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5

(END OF REPORT)