

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333493-927

Luminaire Tested: **S125RDIP-S375D365U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333493-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S375D365U927-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 365 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2306.0 lumens  
Efficiency: N/A  
Efficacy: 113.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 20.3  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333493-927

CATALOG NUMBER: S125RDIP-S375D365U927-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333493-927

CATALOG NUMBER: S125RDIP-S375D365U927-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	94	90	86	90	87	83	80	73	71	69	61	59	58	50	49	48	42
2	89	82	76	71	82	76	71	66	64	61	57	54	51	49	44	42	40	36
3	82	72	65	59	75	67	61	56	57	52	48	48	44	41	39	37	35	31
4	75	64	56	50	69	59	53	47	51	46	41	43	39	36	35	32	30	26
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	32	29	26	23
6	63	51	43	38	58	48	41	35	41	35	31	35	30	27	29	26	23	20
7	59	46	39	33	54	43	36	31	37	32	28	32	27	24	26	23	21	18
8	54	42	34	29	50	39	32	28	34	29	25	29	25	22	24	21	19	16
9	51	39	31	26	47	36	29	25	31	26	22	27	22	19	22	19	17	15
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	21	18	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3130	3130	3130
5°	3138	3102	3121
10°	3114	3074	3074
15°	3077	3011	2986
20°	3030	2924	2889
25°	2974	2838	2776
30°	2905	2738	2651
35°	2834	2636	2511
40°	2769	2528	2373
45°	2689	2408	2223
50°	2608	2277	2067
55°	2514	2152	1901
60°	2421	2001	1721
65°	2311	1825	1516
70°	2185	1603	1307
75°	2011	1352	1088
80°	1770	1060	915
85°	1489	867	815



TEST NUMBER: P333493-927

CATALOG NUMBER: S125RDIP-S375D365U927-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	45.6	2.0
10°-20°	127.4	5.5
20°-30°	184.7	8.0
30°-40°	210.5	9.1
40°-50°	205.2	8.9
50°-60°	172.7	7.5
60°-70°	121.1	5.3
70°-80°	62.2	2.7
80°-90°	16.5	0.7
90°-100°	13.7	0.6
100°-110°	84.6	3.7
110°-120°	153.4	6.7
120°-130°	196.9	8.5
130°-140°	211.8	9.2
140°-150°	198.8	8.6
150°-160°	160.8	7.0
160°-170°	104.0	4.5
170°-180°	35.9	1.6
0°-30°	357.7	15.5
0°-40°	568.2	24.6
0°-60°	946.1	41.0
0°-90°	1145.9	49.7
90°-120°	251.8	10.9
90°-150°	859.3	37.3
90°-180°	1160.0	50.3
0°-180°	2306.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	485	485	485	485	485	
5°	484	482	478	482	481	46
15°	460	458	450	450	447	130
25°	417	411	398	394	390	192
35°	360	350	334	324	318	225
45°	294	283	264	249	243	227
55°	223	211	191	175	169	200
65°	151	138	119	105	99	150
75°	81	69	54	46	44	85
85°	20	14	12	11	11	23
90°	0	3	4	6	7	2
95°	16	15	4	6	6	20
105°	82	83	83	83	83	87
115°	155	156	156	155	153	153
125°	220	222	222	221	220	196
135°	274	276	275	275	273	211
145°	318	318	318	319	317	199
155°	350	348	349	350	348	161
165°	369	368	368	369	367	104
175°	378	376	376	378	376	36
180°	378	378	378	378	378	



TEST NUMBER: P333493-927

CATALOG NUMBER: S125RDIP-S375D365U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7
2.5°	485.6	485.4	485.2	485.1	484.8	484.4	483.8	483.1	482.4	481.8	482.4
5°	484.0	483.7	483.4	483.0	482.7	482.1	481.2	480.3	479.4	478.5	479.3
7.5°	479.3	479.0	478.6	478.3	478.0	477.3	476.3	475.2	474.1	473.0	473.6
10°	474.8	474.6	474.4	474.1	473.9	473.2	472.1	470.9	469.8	468.7	468.9
12.5°	469.8	469.5	469.3	469.0	468.7	467.7	466.2	464.7	463.1	461.6	461.8
15°	460.2	459.7	459.2	458.8	458.3	457.2	455.4	453.8	452.0	450.4	450.3
17.5°	449.3	448.5	447.8	447.0	446.3	444.9	442.7	440.5	438.4	436.3	435.9
20°	440.8	440.0	439.2	438.4	437.5	435.9	433.2	430.6	428.0	425.4	425.0
22.5°	431.4	430.6	429.8	429.0	428.2	426.4	423.7	421.0	418.2	415.5	414.7
25°	417.4	416.1	414.9	413.7	412.5	410.4	407.3	404.3	401.3	398.3	397.3
27.5°	401.2	399.8	398.3	396.8	395.3	393.0	389.8	386.5	383.3	380.1	378.6
30°	389.5	388.0	386.4	384.9	383.3	380.9	377.5	374.1	370.7	367.2	365.4
32.5°	378.1	376.3	374.5	372.7	370.9	368.3	364.8	361.3	357.8	354.3	352.3
35°	359.5	357.6	355.6	353.6	351.7	348.9	345.2	341.6	337.9	334.3	331.9
37.5°	341.3	338.9	336.5	334.1	331.8	328.7	325.0	321.2	317.4	313.6	310.8
40°	328.4	326.0	323.5	321.1	318.6	315.4	311.6	307.7	303.7	299.8	296.8
42.5°	314.9	312.4	309.9	307.4	304.9	301.7	297.6	293.6	289.5	285.5	282.6
45°	294.4	292.0	289.6	287.2	284.9	281.5	277.0	272.6	268.1	263.6	260.3
47.5°	273.1	270.5	268.1	265.5	263.1	259.6	255.1	250.6	246.1	241.5	238.2
50°	259.6	256.9	254.2	251.5	248.8	245.2	240.5	235.9	231.2	226.6	223.2
52.5°	244.9	242.2	239.4	236.7	233.9	230.4	226.0	221.6	217.2	212.9	209.2
55°	223.3	220.7	218.1	215.6	212.9	209.4	204.8	200.2	195.7	191.1	187.4
57.5°	201.5	198.8	195.9	193.1	190.4	186.8	182.4	178.0	173.6	169.2	165.6
60°	187.4	184.6	181.7	178.9	176.0	172.5	168.0	163.7	159.2	154.9	151.3
62.5°	172.5	169.8	167.1	164.4	161.6	158.0	153.6	149.2	144.7	140.2	136.9
65°	151.2	148.5	145.7	142.9	140.1	136.6	132.3	128.0	123.7	119.4	116.1
67.5°	130.1	127.3	124.5	121.8	119.0	115.5	111.4	107.3	103.1	99.0	96.0
70°	115.7	113.0	110.2	107.4	104.6	101.2	97.1	93.1	89.0	84.9	82.4
72.5°	101.6	98.9	96.3	93.6	90.9	87.5	83.7	79.9	76.1	72.3	70.0
75°	80.6	78.1	75.7	73.2	70.8	67.9	64.4	61.0	57.6	54.2	52.4
77.5°	59.6	57.7	55.7	53.7	51.8	49.4	46.7	44.0	41.3	38.5	37.2
80°	47.6	45.6	43.7	41.7	39.8	37.7	35.4	33.1	30.8	28.5	27.8
82.5°	35.9	34.1	32.4	30.6	28.8	27.2	25.7	24.1	22.5	20.9	20.6
85°	20.1	18.7	17.2	15.8	14.3	13.3	12.9	12.5	12.1	11.7	11.6
87.5°	6.8	6.4	6.1	5.7	5.4	5.2	5.2	5.2	5.2	5.3	5.4
90°	0.3	0.8	1.3	1.7	2.3	2.8	3.2	3.6	4.0	4.5	4.8
92.5°	4.3	4.0	3.6	3.2	2.9	2.9	3.3	3.7	4.1	4.5	4.8
95°	15.9	15.8	15.6	15.4	15.2	13.9	11.6	9.2	6.8	4.5	4.8
97.5°	33.4	33.7	34.0	34.3	34.7	32.5	27.8	23.1	18.5	13.8	12.0
100°	46.7	47.0	47.1	47.3	47.5	47.7	48.0	48.2	48.5	48.7	39.5
102.5°	60.4	60.7	60.9	61.2	61.4	61.6	61.7	61.9	62.0	62.2	60.4
105°	82.3	82.5	82.9	83.1	83.3	83.4	83.4	83.4	83.4	83.4	83.4
107.5°	105.0	105.0	105.0	105.0	105.0	105.1	105.3	105.4	105.5	105.6	105.6
110°	119.9	119.9	119.9	119.9	119.9	119.9	120.0	120.2	120.3	120.4	120.3



TEST NUMBER: P333493-927

CATALOG NUMBER: S125RDIP-S375D365U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	133.7	133.9	134.0	134.2	134.4	134.4	134.5	134.6	134.7	134.8	134.5
115°	154.6	154.9	155.2	155.5	155.8	156.0	156.1	156.1	156.2	156.2	156.0
117.5°	176.1	176.1	176.1	176.1	176.1	176.2	176.4	176.7	176.9	177.1	176.8
120°	189.6	189.5	189.5	189.4	189.3	189.4	189.6	189.7	190.0	190.1	190.0
122.5°	201.5	201.7	201.9	202.2	202.4	202.6	202.6	202.7	202.8	202.9	202.8
125°	219.8	220.2	220.7	221.1	221.6	221.8	221.8	221.8	221.8	221.8	221.5
127.5°	237.3	237.7	238.0	238.3	238.6	238.8	238.7	238.7	238.6	238.6	238.4
130°	248.1	248.4	248.7	249.1	249.4	249.5	249.6	249.6	249.7	249.8	249.6
132.5°	258.9	259.2	259.6	259.9	260.3	260.4	260.3	260.2	260.0	259.8	259.8
135°	274.2	274.5	274.9	275.3	275.6	275.8	275.6	275.5	275.4	275.3	275.1
137.5°	288.2	288.5	288.8	289.1	289.5	289.6	289.5	289.4	289.2	289.1	289.1
140°	297.4	297.5	297.6	297.8	297.9	297.9	297.9	297.8	297.7	297.7	297.8
142.5°	305.7	305.8	305.9	305.9	305.9	306.0	306.2	306.3	306.3	306.4	306.4
145°	317.8	318.0	318.1	318.2	318.3	318.4	318.4	318.4	318.4	318.4	318.5
147.5°	328.4	328.4	328.4	328.4	328.4	328.4	328.4	328.5	328.6	328.7	328.8
150°	335.2	335.1	334.9	334.8	334.7	334.7	334.8	334.9	335.1	335.2	335.3
152.5°	341.7	341.4	341.1	340.9	340.6	340.5	340.6	340.8	340.9	341.0	341.1
155°	350.1	349.7	349.3	348.9	348.6	348.4	348.6	348.6	348.8	348.9	349.1
157.5°	356.5	356.2	356.0	355.8	355.6	355.5	355.5	355.5	355.5	355.5	355.7
160°	360.9	360.6	360.2	359.8	359.5	359.3	359.3	359.4	359.5	359.6	359.8
162.5°	364.6	364.2	363.8	363.4	363.1	362.9	363.0	363.0	363.1	363.1	363.5
165°	369.3	369.0	368.6	368.2	367.9	367.7	367.7	367.8	367.9	368.0	368.3
167.5°	373.0	372.6	372.2	371.8	371.4	371.2	371.3	371.4	371.5	371.5	371.9
170°	374.9	374.5	374.1	373.7	373.2	373.0	373.1	373.1	373.2	373.3	373.8
172.5°	376.3	375.9	375.4	375.0	374.5	374.4	374.5	374.6	374.7	374.9	375.3
175°	377.7	377.4	377.0	376.6	376.3	376.1	376.1	376.2	376.3	376.4	376.8
177.5°	378.4	378.1	377.8	377.6	377.2	377.1	377.2	377.2	377.2	377.3	377.6
180°	377.7	377.7	377.7	377.7	377.7	377.7	377.7	377.7	377.7	377.7	377.7



TEST NUMBER: P333493-927

CATALOG NUMBER: S125RDIP-S375D365U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7
2.5°	483.1	483.8	484.4	484.7	484.7	484.6	484.5	484.4
5°	480.1	480.9	481.7	482.1	482.0	481.7	481.6	481.4
7.5°	474.1	474.8	475.3	475.5	475.3	475.2	475.0	474.8
10°	469.1	469.4	469.6	469.6	469.4	469.1	468.9	468.7
12.5°	461.9	462.2	462.3	462.2	461.8	461.4	461.1	460.7
15°	450.1	450.0	450.0	449.6	448.9	448.1	447.4	446.6
17.5°	435.5	435.1	434.7	434.1	433.6	432.9	432.3	431.7
20°	424.6	424.2	423.8	423.3	422.5	421.8	421.0	420.3
22.5°	413.8	413.0	412.3	411.5	411.0	410.4	409.8	409.2
25°	396.2	395.1	394.1	393.2	392.2	391.3	390.5	389.5
27.5°	377.2	375.7	374.1	373.0	372.2	371.3	370.4	369.6
30°	363.5	361.6	359.7	358.5	357.7	357.0	356.2	355.5
32.5°	350.2	348.2	346.0	344.6	343.6	342.7	341.7	340.9
35°	329.5	327.2	324.8	323.1	321.9	320.8	319.6	318.5
37.5°	307.9	305.1	302.3	300.3	299.2	298.1	297.0	295.9
40°	293.7	290.6	287.5	285.4	284.5	283.5	282.5	281.5
42.5°	279.6	276.6	273.6	271.5	270.1	268.5	267.1	265.7
45°	257.1	253.8	250.6	248.3	247.2	245.9	244.7	243.4
47.5°	234.9	231.5	228.1	225.8	224.4	223.1	221.7	220.4
50°	219.8	216.3	212.9	210.6	209.5	208.2	207.0	205.7
52.5°	205.5	201.8	198.1	195.7	194.5	193.3	192.0	190.8
55°	183.8	180.1	176.5	174.0	172.7	171.3	170.1	168.8
57.5°	162.1	158.5	154.9	152.5	151.4	150.2	149.1	147.9
60°	147.7	144.1	140.5	138.2	136.9	135.7	134.5	133.2
62.5°	133.6	130.2	126.9	124.7	123.4	122.2	121.0	119.8
65°	112.8	109.6	106.3	104.1	102.9	101.6	100.4	99.2
67.5°	93.0	90.1	87.1	85.1	84.1	83.2	82.1	81.2
70°	79.9	77.4	74.9	73.1	72.1	71.1	70.2	69.2
72.5°	67.7	65.4	63.1	61.6	60.9	60.3	59.6	58.9
75°	50.6	48.8	47.1	45.9	45.3	44.7	44.1	43.6
77.5°	36.0	34.8	33.5	32.6	32.2	31.8	31.4	31.0
80°	27.1	26.4	25.7	25.2	25.0	24.9	24.7	24.6
82.5°	20.3	19.9	19.6	19.3	19.3	19.2	19.1	18.9
85°	11.6	11.5	11.4	11.3	11.2	11.2	11.1	11.0
87.5°	5.4	5.5	5.5	5.5	5.5	5.5	5.5	5.5
90°	5.1	5.4	5.7	5.9	6.2	6.3	6.5	6.7
92.5°	5.1	5.4	5.7	5.9	6.0	6.1	6.2	6.3
95°	5.1	5.4	5.7	5.9	5.9	5.9	5.9	5.9
97.5°	10.3	8.5	6.7	5.9	5.9	5.9	5.9	5.9
100°	30.2	20.9	11.6	6.9	6.7	6.4	6.1	5.9
102.5°	58.6	56.9	55.1	52.1	47.9	43.7	39.5	35.3
105°	83.4	83.4	83.4	83.4	83.3	83.3	83.3	83.2
107.5°	105.7	105.7	105.7	105.6	105.4	105.2	105.0	104.8
110°	120.0	119.9	119.7	119.6	119.7	119.7	119.8	119.9





TEST NUMBER: P333493-927

CATALOG NUMBER: S125RDIP-S375D365U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	134.3	134.0	133.8	133.6	133.6	133.5	133.4	133.3
115°	155.7	155.5	155.3	155.0	154.6	154.2	153.8	153.4
117.5°	176.5	176.2	175.9	175.6	175.5	175.3	175.2	175.0
120°	189.9	189.7	189.6	189.4	189.1	188.8	188.5	188.1
122.5°	202.6	202.6	202.4	202.2	201.8	201.5	201.1	200.7
125°	221.3	221.0	220.8	220.5	220.4	220.2	220.0	219.8
127.5°	238.3	238.1	238.1	237.7	237.3	236.8	236.4	235.9
130°	249.4	249.2	249.1	248.7	248.5	248.2	247.9	247.6
132.5°	259.8	259.8	259.7	259.5	259.2	258.9	258.6	258.3
135°	275.0	274.9	274.7	274.5	274.2	273.8	273.4	273.0
137.5°	289.2	289.2	289.2	289.1	288.8	288.4	288.1	287.8
140°	297.9	298.0	298.2	298.0	297.7	297.3	296.9	296.5
142.5°	306.4	306.5	306.5	306.3	305.9	305.5	305.2	304.8
145°	318.5	318.5	318.6	318.5	318.1	317.7	317.3	317.0
147.5°	328.8	328.9	329.0	328.8	328.4	327.9	327.5	327.0
150°	335.4	335.6	335.6	335.5	335.0	334.5	334.0	333.5
152.5°	341.3	341.4	341.5	341.4	340.9	340.5	340.0	339.5
155°	349.3	349.4	349.7	349.5	349.0	348.5	348.0	347.5
157.5°	355.9	356.1	356.3	356.2	355.7	355.1	354.7	354.2
160°	360.0	360.3	360.5	360.4	359.9	359.4	358.9	358.5
162.5°	363.8	364.2	364.6	364.4	363.8	363.3	362.8	362.3
165°	368.7	369.1	369.5	369.4	368.9	368.4	367.9	367.4
167.5°	372.4	372.8	373.3	373.2	372.6	372.1	371.5	371.0
170°	374.2	374.8	375.3	375.3	374.7	374.1	373.5	373.0
172.5°	375.7	376.2	376.6	376.6	376.0	375.4	374.9	374.3
175°	377.3	377.9	378.3	378.3	377.7	377.2	376.6	376.0
177.5°	378.0	378.3	378.7	378.7	378.3	377.9	377.5	377.1
180°	377.7	377.7	377.7	377.7	377.7	377.7	377.7	377.7

(END OF REPORT)