

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333251-935

Luminaire Tested: **S125DIP-S1090D365U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333251-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1090D365U935-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4955.5 lumens
Efficiency: N/A
Efficacy: 113.9 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333251-935

CATALOG NUMBER: S125DIP-S1090D365U935-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333251-935

CATALOG NUMBER: S125DIP-S1090D365U935-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	114	114	114	114	109	109	109	109	99	99	99	90	90	90	82	82	82	78				
1	104	100	96	93	100	96	92	89	87	85	82	80	78	76	73	71	70	66				
2	95	88	82	76	91	84	78	74	77	73	69	71	67	64	65	62	59	56				
3	87	78	70	64	83	74	67	62	68	63	58	63	58	54	58	54	51	48				
4	80	69	61	54	76	66	59	53	61	55	50	56	51	47	52	47	44	41				
5	74	62	53	47	70	59	52	46	55	48	43	50	45	41	47	42	39	36				
6	68	56	47	41	65	53	46	40	49	43	38	46	40	36	42	38	34	32				
7	63	50	42	36	60	48	41	35	45	38	34	42	36	32	39	34	30	28				
8	59	46	38	32	56	44	37	32	41	35	30	38	33	29	36	31	27	25				
9	55	42	34	29	52	41	33	28	38	31	27	35	30	26	33	28	25	23				
10	51	39	31	26	49	37	30	26	35	29	24	33	27	23	30	26	22	20				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8843	8843	8843	8843
5°	10240	8873	7769	8873
10°	11913	8826	6807	8826
15°	13188	8762	6279	8762
20°	14762	8659	5856	8659
25°	17293	8543	5648	8543
30°	18678	8429	5469	8429
35°	15358	8215	5351	8215
40°	10916	7917	5223	7917
45°	8386	7516	5149	7516
50°	7159	7018	5138	7018
55°	6373	6531	5183	6531
60°	5749	5997	5315	5997
65°	5310	5462	5453	5462
70°	4828	4906	5531	4906
75°	4262	4319	5480	4319
80°	3585	3522	5013	3522
85°	2838	2542	4046	2542



TEST NUMBER: P333251-935

CATALOG NUMBER: S125DIP-S1090D365U935-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.8	2.7
10°-20°	392.4	7.9
20°-30°	637.2	12.9
30°-40°	777.3	15.7
40°-50°	707.1	14.3
50°-60°	563.2	11.4
60°-70°	392.3	7.9
70°-80°	209.2	4.2
80°-90°	53.7	1.1
90°-100°	26.2	0.5
100°-110°	77.3	1.6
110°-120°	131.0	2.6
120°-130°	172.4	3.5
130°-140°	193.2	3.9
140°-150°	189.3	3.8
150°-160°	159.0	3.2
160°-170°	105.7	2.1
170°-180°	37.0	0.7
0°-30°	1161.5	23.4
0°-40°	1938.8	39.1
0°-60°	3209.2	64.8
0°-90°	3864.3	78.0
90°-120°	234.5	4.7
90°-150°	789.5	15.9
90°-180°	1091.0	22.0
0°-180°	4955.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1369	1369	1369	1369	1369	
5°	1580	1369	1198	1369	1580	159
15°	1972	1310	939	1310	1972	565
25°	2427	1199	793	1199	2427	1108
35°	1948	1042	679	1042	1948	1192
45°	918	823	564	823	918	735
55°	566	580	460	580	566	510
65°	348	357	357	357	348	345
75°	171	173	220	173	171	184
85°	38	34	55	34	38	44
90°	7	0	7	0	7	6
95°	26	20	26	20	26	27
105°	76	69	76	69	76	80
115°	132	131	132	131	132	131
125°	193	191	193	191	193	172
135°	250	249	250	249	250	193
145°	303	302	303	302	303	189
155°	345	345	345	345	345	159
165°	374	375	374	375	374	106
175°	389	390	389	390	389	37
180°	391	391	391	391	391	



TEST NUMBER: P333251-935

CATALOG NUMBER: S125DIP-S1090D365U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2
2.5°	1448.2	1446.3	1444.5	1440.7	1443.6	1435.6	1431.9	1425.4	1417.5	1414.7	1411.4
5°	1579.5	1582.4	1585.4	1573.1	1574.3	1566.2	1547.6	1532.4	1520.3	1504.5	1493.5
7.5°	1737.6	1730.7	1730.2	1722.3	1708.7	1697.7	1678.2	1653.3	1629.3	1601.8	1579.2
10°	1816.6	1817.2	1812.0	1802.7	1788.1	1777.7	1752.1	1727.7	1698.1	1663.2	1638.2
12.5°	1876.1	1878.5	1872.0	1859.4	1852.3	1828.9	1808.9	1779.8	1744.6	1716.7	1678.7
15°	1972.4	1966.0	1961.4	1945.6	1933.5	1909.0	1877.1	1846.8	1808.4	1773.1	1737.6
17.5°	2065.1	2070.2	2061.5	2047.2	2009.3	1980.8	1937.9	1896.6	1848.8	1801.3	1758.9
20°	2147.9	2152.5	2139.2	2114.2	2068.8	2040.4	1984.0	1930.5	1875.3	1814.3	1767.8
22.5°	2251.1	2247.4	2229.3	2191.3	2152.1	2099.4	2038.4	1973.3	1904.1	1835.2	1773.4
25°	2426.8	2402.4	2391.3	2344.3	2292.6	2215.3	2131.6	2036.3	1950.3	1859.1	1780.0
27.5°	2524.2	2516.5	2504.2	2471.4	2417.1	2334.4	2235.8	2119.6	1998.3	1883.1	1779.7
30°	2504.6	2505.9	2507.0	2496.6	2461.7	2399.5	2301.3	2176.3	2032.2	1902.6	1782.9
32.5°	2331.8	2352.9	2373.1	2397.0	2406.8	2394.9	2333.4	2220.5	2072.2	1924.9	1781.1
35°	1947.9	1954.4	2020.0	2085.1	2173.4	2242.0	2287.9	2237.9	2113.0	1943.9	1778.8
37.5°	1518.9	1550.2	1595.7	1669.2	1796.7	1910.9	2057.7	2125.2	2084.9	1950.1	1774.8
40°	1294.8	1323.8	1353.5	1428.4	1535.9	1674.2	1841.0	1983.4	2016.5	1930.5	1760.8
42.5°	1121.8	1144.9	1177.8	1234.1	1324.0	1446.5	1605.8	1791.8	1906.3	1873.8	1731.6
45°	918.2	932.7	958.3	1003.1	1068.2	1164.0	1304.7	1508.0	1685.3	1744.0	1662.1
47.5°	785.9	785.8	805.7	836.6	883.6	965.0	1069.0	1228.4	1417.7	1557.8	1551.3
50°	712.5	709.6	725.2	752.0	789.2	843.3	942.6	1069.9	1251.7	1410.4	1454.6
52.5°	649.3	649.6	659.3	679.0	710.2	756.3	830.5	945.3	1100.7	1263.5	1346.7
55°	566.0	563.7	574.7	588.1	610.8	641.0	694.5	782.2	908.3	1068.7	1176.8
57.5°	489.7	496.2	500.6	509.9	528.7	549.0	594.0	658.4	758.5	896.1	1010.4
60°	445.1	451.5	455.0	464.3	479.4	496.9	531.8	584.0	668.3	786.9	900.2
62.5°	405.2	410.2	411.3	419.7	432.0	449.0	476.4	520.4	586.9	690.6	801.6
65°	347.5	347.5	349.8	358.5	364.4	379.4	400.4	432.4	485.9	566.6	661.3
67.5°	292.0	294.7	294.2	298.0	303.3	315.1	330.1	356.5	396.1	455.0	530.8
70°	255.7	258.0	257.4	260.4	266.1	273.7	285.9	310.9	339.4	389.9	455.0
72.5°	223.2	224.1	222.6	226.4	229.9	236.5	250.1	263.5	290.1	332.8	386.2
75°	170.8	172.0	173.1	175.5	179.0	182.4	189.4	202.9	220.2	252.2	286.5
77.5°	128.1	125.9	128.6	128.3	130.3	132.9	139.1	146.2	160.5	180.7	207.2
80°	96.4	97.0	97.0	97.6	100.6	102.3	107.5	112.7	123.8	138.9	157.5
82.5°	70.4	72.0	71.0	72.1	74.5	75.8	78.7	83.0	89.4	101.3	114.7
85°	38.3	35.5	36.6	37.8	37.8	38.3	40.6	42.4	45.9	50.5	55.8
87.5°	12.7	13.5	13.9	13.9	14.3	14.3	16.0	16.0	17.3	18.6	20.4
90°	7.3	7.1	6.9	6.7	6.5	6.2	5.9	5.5	5.2	4.9	4.4
92.5°	14.4	14.2	14.0	13.9	13.8	13.4	13.0	12.6	12.1	11.7	11.1
95°	26.2	26.0	25.9	25.7	25.7	25.3	24.9	24.4	23.9	23.4	22.7
97.5°	39.7	39.6	39.5	39.4	39.3	39.1	38.7	38.2	37.8	37.3	36.3
100°	49.9	49.8	49.7	49.5	49.3	49.0	48.4	47.8	47.2	46.6	45.7
102.5°	60.1	59.9	59.8	59.6	59.4	59.0	58.3	57.6	57.0	56.3	55.9
105°	75.5	75.3	75.1	74.8	74.6	74.4	74.0	73.5	73.1	72.8	72.3
107.5°	91.2	91.2	91.2	91.2	91.3	91.1	90.9	90.7	90.5	90.3	90.0
110°	102.9	102.9	103.0	103.1	103.1	103.1	102.9	102.6	102.5	102.3	102.0



TEST NUMBER: P333251-935

CATALOG NUMBER: S125DIP-S1090D365U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	114.3	114.4	114.5	114.7	114.8	114.8	114.7	114.6	114.5	114.4	114.2
115°	132.3	132.4	132.5	132.6	132.7	132.7	132.8	132.9	132.9	133.0	132.9
117.5°	150.0	150.3	150.6	150.8	151.1	151.2	151.2	151.1	151.0	151.0	150.8
120°	162.2	162.5	162.7	163.0	163.2	163.4	163.4	163.4	163.4	163.4	163.3
122.5°	174.4	174.6	174.8	175.0	175.2	175.4	175.4	175.5	175.6	175.6	175.4
125°	192.6	192.7	192.8	192.9	192.9	193.0	193.1	193.3	193.4	193.6	193.5
127.5°	210.2	210.3	210.4	210.6	210.7	210.8	210.9	210.9	211.0	211.0	211.0
130°	221.9	222.0	222.1	222.2	222.4	222.5	222.6	222.7	222.7	222.7	222.7
132.5°	232.8	233.0	233.2	233.3	233.6	233.7	233.8	233.8	233.8	233.9	234.0
135°	249.9	250.1	250.4	250.6	250.9	251.1	251.1	251.1	251.1	251.1	251.0
137.5°	266.5	266.8	267.2	267.5	267.9	268.0	267.9	267.9	267.8	267.7	267.5
140°	277.2	277.6	277.9	278.3	278.6	278.7	278.5	278.4	278.3	278.1	277.9
142.5°	287.5	287.8	288.1	288.4	288.8	289.0	288.9	288.8	288.7	288.6	288.3
145°	302.8	303.0	303.2	303.4	303.6	303.7	303.7	303.7	303.7	303.7	303.5
147.5°	315.9	316.3	316.8	317.3	317.7	317.9	317.7	317.5	317.4	317.2	317.0
150°	325.6	325.7	325.9	326.1	326.1	326.2	326.2	326.2	326.2	326.2	326.0
152.5°	333.6	333.9	334.2	334.4	334.6	334.7	334.5	334.3	334.2	334.0	333.9
155°	345.1	345.4	345.8	346.1	346.5	346.5	346.2	345.9	345.7	345.4	345.3
157.5°	354.6	355.1	355.5	356.0	356.5	356.5	356.3	355.9	355.7	355.4	355.3
160°	361.2	361.5	361.9	362.2	362.6	362.6	362.3	362.1	361.8	361.5	361.4
162.5°	366.8	367.2	367.6	368.0	368.4	368.4	368.1	367.7	367.5	367.1	367.1
165°	374.3	374.7	375.1	375.5	375.9	376.0	375.7	375.5	375.2	374.9	374.9
167.5°	380.3	380.6	381.1	381.5	381.9	381.9	381.5	381.2	380.7	380.3	380.3
170°	383.4	383.9	384.4	384.9	385.3	385.4	385.0	384.5	384.2	383.7	383.7
172.5°	386.1	386.5	386.9	387.4	387.8	387.8	387.4	387.0	386.6	386.2	386.2
175°	388.6	389.1	389.5	390.0	390.5	390.5	390.1	389.7	389.3	388.9	388.9
177.5°	390.0	390.5	390.8	391.2	391.6	391.6	391.3	391.0	390.6	390.3	390.4
180°	391.1	391.1	391.1	391.1	391.1	391.1	391.1	391.1	391.1	391.1	391.1



TEST NUMBER: P333251-935

CATALOG NUMBER: S125DIP-S1090D365U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2
2.5°	1408.7	1405.4	1401.7	1395.2	1387.2	1383.1	1376.6	1372.4	1364.0	1357.0	1349.6
5°	1480.1	1465.1	1451.1	1433.0	1413.3	1400.5	1385.4	1368.6	1351.2	1333.1	1313.4
7.5°	1554.2	1527.4	1498.4	1467.1	1436.6	1408.4	1381.6	1355.2	1330.6	1300.8	1275.6
10°	1604.0	1570.2	1534.2	1491.8	1450.5	1414.5	1377.9	1345.9	1313.4	1278.5	1247.7
12.5°	1653.6	1608.8	1557.9	1511.3	1461.6	1418.2	1375.1	1334.3	1293.4	1254.8	1218.8
15°	1688.8	1649.2	1602.1	1535.9	1480.1	1420.3	1363.3	1310.4	1261.0	1218.1	1172.8
17.5°	1711.9	1661.0	1610.4	1546.9	1473.8	1406.8	1342.3	1281.8	1226.1	1171.6	1127.8
20°	1716.1	1663.8	1610.9	1548.7	1473.8	1397.1	1332.6	1259.9	1200.1	1143.7	1090.2
22.5°	1714.7	1655.4	1597.8	1533.9	1460.8	1390.1	1312.1	1238.0	1173.1	1117.7	1061.9
25°	1701.6	1638.2	1566.2	1501.7	1429.6	1354.6	1275.6	1198.9	1132.6	1069.3	1014.1
27.5°	1690.7	1608.4	1526.9	1451.6	1382.1	1313.4	1237.7	1159.2	1085.6	1021.5	969.5
30°	1677.1	1587.1	1495.2	1416.8	1345.3	1278.5	1207.0	1130.3	1053.6	990.8	935.0
32.5°	1665.1	1560.1	1463.2	1377.8	1302.1	1237.1	1171.2	1098.2	1022.9	959.2	903.4
35°	1641.7	1520.3	1409.3	1312.8	1232.0	1165.2	1110.0	1042.0	972.8	911.2	857.7
37.5°	1612.1	1467.9	1348.8	1247.7	1159.2	1088.7	1037.3	985.2	918.8	859.4	811.1
40°	1588.8	1430.7	1304.7	1201.2	1109.4	1036.1	988.5	939.1	883.9	828.7	777.6
42.5°	1559.5	1397.3	1260.0	1148.7	1057.7	986.4	936.4	894.5	845.8	794.3	746.8
45°	1505.7	1336.6	1187.8	1068.2	976.3	905.9	854.3	822.9	786.3	737.4	697.3
47.5°	1426.6	1263.7	1109.8	986.3	891.6	826.4	777.9	747.8	722.0	685.7	649.4
50°	1356.3	1209.4	1053.6	931.0	836.3	770.6	725.8	698.5	676.4	648.5	617.8
52.5°	1277.8	1141.0	998.2	877.0	783.3	718.5	674.7	650.7	632.2	612.3	581.9
55°	1153.0	1036.7	904.2	789.2	702.6	639.2	600.9	580.0	564.9	549.7	531.2
57.5°	1015.5	924.5	807.2	702.0	622.2	564.6	528.8	508.5	496.7	489.0	478.0
60°	918.8	840.9	739.8	643.9	566.0	514.9	480.0	464.3	454.4	448.1	439.9
62.5°	829.1	765.1	671.4	583.9	515.8	467.4	436.4	421.1	411.6	408.5	401.8
65°	696.8	647.4	570.1	497.5	439.4	398.0	372.0	357.4	351.5	348.1	348.7
67.5°	566.5	536.4	474.3	412.3	366.0	331.4	310.5	299.3	296.4	291.7	291.6
70°	487.0	464.3	412.0	358.0	316.7	290.0	271.4	259.8	256.8	254.5	254.0
72.5°	416.8	396.9	351.5	308.2	271.1	247.7	232.3	225.3	220.6	219.2	219.1
75°	313.2	302.2	266.1	231.9	206.3	190.0	179.6	173.1	169.7	169.1	169.7
77.5°	222.7	213.0	190.1	165.8	149.7	137.4	128.5	126.3	122.3	122.5	121.9
80°	167.4	161.0	146.5	127.3	113.9	103.4	98.8	94.7	93.6	91.8	93.6
82.5°	121.3	114.5	104.6	92.4	81.4	75.1	70.4	69.1	68.4	67.7	68.0
85°	59.8	60.4	54.6	45.3	40.6	37.2	34.3	34.3	33.7	33.1	33.7
87.5°	21.3	20.2	18.3	16.8	14.3	12.8	12.2	12.6	11.4	10.9	11.5
90°	4.0	3.4	3.0	2.5	1.9	1.4	0.9	0.3	0.9	1.4	1.9
92.5°	10.5	9.9	9.4	8.9	8.5	8.1	7.7	7.4	7.7	8.1	8.5
95°	22.0	21.4	20.8	20.3	20.1	20.1	19.9	19.8	19.9	20.1	20.1
97.5°	35.5	34.5	33.6	33.1	33.1	33.0	32.9	32.9	32.9	33.0	33.1
100°	44.8	43.9	43.0	42.6	42.6	42.6	42.6	42.6	42.6	42.6	42.6
102.5°	55.4	54.9	54.5	54.2	53.9	53.6	53.4	53.0	53.4	53.6	53.9
105°	71.9	71.5	71.1	70.8	70.4	70.1	69.7	69.4	69.7	70.1	70.4
107.5°	89.7	89.4	89.1	88.8	88.4	88.1	87.7	87.4	87.7	88.1	88.4
110°	101.9	101.6	101.4	101.2	100.8	100.5	100.1	99.8	100.1	100.5	100.8



TEST NUMBER: P333251-935

CATALOG NUMBER: S125DIP-S1090D365U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	113.9	113.7	113.4	113.1	113.0	112.8	112.6	112.4	112.6	112.8	113.0
115°	132.7	132.6	132.4	132.2	132.0	131.7	131.4	131.1	131.4	131.7	132.0
117.5°	150.8	150.7	150.5	150.4	150.2	150.2	150.0	149.9	150.0	150.2	150.2
120°	163.2	163.2	163.2	162.9	162.6	162.3	162.0	161.6	162.0	162.3	162.6
122.5°	175.2	175.0	174.9	174.7	174.6	174.5	174.4	174.3	174.4	174.5	174.6
125°	193.4	193.4	193.3	193.0	192.6	192.3	191.8	191.4	191.8	192.3	192.6
127.5°	210.9	210.9	210.8	210.6	210.3	210.2	209.9	209.7	209.9	210.2	210.3
130°	222.5	222.3	222.2	222.0	221.6	221.3	220.9	220.6	220.9	221.3	221.6
132.5°	234.0	234.0	234.1	233.8	233.2	232.7	232.1	231.6	232.1	232.7	233.2
135°	250.9	250.9	250.8	250.6	250.1	249.8	249.3	248.9	249.3	249.8	250.1
137.5°	267.3	267.3	267.1	266.8	266.4	266.0	265.6	265.3	265.6	266.0	266.4
140°	277.8	277.5	277.3	277.1	276.7	276.4	276.0	275.7	276.0	276.4	276.7
142.5°	288.1	287.8	287.6	287.3	287.1	286.7	286.5	286.2	286.5	286.7	287.1
145°	303.3	303.1	302.9	302.6	302.4	302.1	301.9	301.6	301.9	302.1	302.4
147.5°	316.9	316.8	316.6	316.4	316.2	316.1	316.0	315.8	316.0	316.1	316.2
150°	325.7	325.4	325.1	325.0	325.1	325.2	325.3	325.3	325.3	325.2	325.1
152.5°	333.8	333.7	333.6	333.5	333.4	333.3	333.2	333.1	333.2	333.3	333.4
155°	345.3	345.2	345.1	345.1	345.1	345.1	345.1	345.1	345.1	345.1	345.1
157.5°	355.3	355.2	355.2	355.2	355.3	355.5	355.7	355.8	355.7	355.5	355.3
160°	361.4	361.4	361.3	361.4	361.5	361.7	362.0	362.1	362.0	361.7	361.5
162.5°	367.1	367.0	367.0	367.1	367.3	367.5	367.6	367.7	367.6	367.5	367.3
165°	374.8	374.7	374.6	374.7	374.8	375.0	375.1	375.2	375.1	375.0	374.8
167.5°	380.3	380.3	380.3	380.5	380.7	381.0	381.3	381.5	381.3	381.0	380.7
170°	383.7	383.7	383.7	383.8	384.2	384.4	384.7	385.0	384.7	384.4	384.2
172.5°	386.2	386.2	386.2	386.3	386.6	386.8	387.1	387.4	387.1	386.8	386.6
175°	388.9	388.9	388.9	389.1	389.3	389.6	389.9	390.1	389.9	389.6	389.3
177.5°	390.5	390.5	390.5	390.6	390.9	391.1	391.3	391.5	391.3	391.1	390.9
180°	391.1	391.1	391.1	391.1	391.1	391.1	391.1	391.1	391.1	391.1	391.1



TEST NUMBER: P333251-935

CATALOG NUMBER: S125DIP-S1090D365U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2
2.5°	1345.4	1340.3	1336.1	1326.8	1321.7	1314.7	1309.2	1315.2	1308.7	1311.5	1307.3
5°	1303.5	1287.2	1275.6	1258.7	1244.2	1230.8	1221.0	1219.2	1214.5	1212.2	1205.2
7.5°	1253.0	1232.7	1212.7	1190.6	1172.0	1153.1	1141.0	1131.0	1124.4	1115.7	1109.7
10°	1223.3	1195.9	1172.8	1146.0	1122.7	1102.4	1086.2	1078.0	1070.5	1059.4	1055.3
12.5°	1186.5	1158.3	1130.0	1101.4	1079.0	1056.4	1042.4	1030.1	1024.8	1012.4	1011.2
15°	1142.5	1100.1	1072.2	1043.1	1012.4	993.8	982.1	968.7	962.9	954.2	947.8
17.5°	1089.9	1052.1	1017.2	987.1	960.7	945.0	930.7	921.4	911.5	905.8	895.3
20°	1051.9	1015.8	980.9	949.0	928.7	910.6	899.0	890.3	879.9	876.9	866.5
22.5°	1019.8	980.0	946.6	919.7	897.5	877.2	864.6	858.7	851.4	842.5	840.4
25°	967.6	926.3	897.9	871.2	851.4	832.8	824.1	816.5	809.5	803.1	800.8
27.5°	922.5	885.6	851.8	827.7	810.5	793.5	785.8	776.6	771.5	766.4	760.1
30°	890.9	853.1	823.5	800.2	781.6	766.5	758.4	752.0	747.3	742.7	739.2
32.5°	858.3	823.4	794.6	771.9	753.3	741.8	734.7	730.1	725.0	719.5	715.1
35°	815.4	777.0	749.1	729.4	714.8	706.1	697.9	693.9	688.0	688.0	683.4
37.5°	766.9	733.7	709.1	691.1	678.0	670.3	661.4	658.7	655.0	652.5	650.8
40°	738.0	707.2	684.0	666.0	652.0	645.7	638.7	634.0	631.7	628.8	627.6
42.5°	708.3	678.9	656.6	640.0	627.8	622.4	615.9	612.6	608.0	604.2	603.5
45°	663.1	634.6	614.2	600.9	590.4	584.0	580.0	573.0	570.7	566.0	565.4
47.5°	620.2	592.9	572.9	562.0	552.8	547.5	541.1	534.2	531.5	529.2	528.9
50°	588.1	563.1	544.5	534.1	525.4	517.8	511.4	506.8	505.0	505.0	506.2
52.5°	555.6	534.3	518.5	505.7	497.5	489.4	483.5	480.7	478.0	480.9	482.9
55°	507.9	486.4	474.8	462.6	454.4	445.1	442.2	441.1	439.4	444.0	446.3
57.5°	457.4	442.4	428.8	416.6	409.3	404.0	400.0	399.3	402.6	404.8	412.3
60°	425.4	407.9	395.7	386.4	377.7	374.3	373.1	372.0	374.3	380.6	390.5
62.5°	390.0	375.9	362.7	355.8	349.4	343.5	343.4	344.1	348.7	356.0	365.8
65°	338.2	326.0	317.3	309.2	303.9	300.4	301.6	303.9	309.2	319.0	330.1
67.5°	285.6	277.2	269.4	262.8	257.8	257.8	259.0	262.4	268.6	280.0	290.1
70°	251.7	242.4	235.9	233.1	228.9	226.6	230.1	235.9	241.2	251.7	260.4
72.5°	217.7	209.8	204.8	202.9	201.0	199.2	200.4	206.6	213.7	224.2	234.3
75°	167.4	164.5	161.0	158.7	156.9	158.1	159.2	165.1	170.8	181.9	193.6
77.5°	122.2	119.2	117.0	116.5	115.5	116.1	119.3	123.6	129.3	137.4	146.2
80°	92.4	91.3	90.1	89.5	89.5	90.1	94.7	97.6	102.9	110.4	117.4
82.5°	67.3	66.6	66.4	66.2	66.7	66.8	69.7	73.4	77.7	83.4	89.5
85°	35.5	34.3	36.0	36.6	35.5	37.2	38.3	40.6	42.4	45.3	48.2
87.5°	12.1	13.2	12.7	13.3	13.4	14.5	14.0	16.0	17.0	18.0	17.6
90°	2.5	3.0	3.4	4.0	4.4	4.9	5.2	5.5	5.9	6.2	6.5
92.5°	8.9	9.4	9.9	10.5	11.1	11.7	12.1	12.6	13.0	13.4	13.8
95°	20.3	20.8	21.4	22.0	22.7	23.4	23.9	24.4	24.9	25.3	25.7
97.5°	33.1	33.6	34.5	35.5	36.3	37.3	37.8	38.2	38.7	39.1	39.3
100°	42.6	43.0	43.9	44.8	45.7	46.6	47.2	47.8	48.4	49.0	49.3
102.5°	54.2	54.5	54.9	55.4	55.9	56.3	57.0	57.6	58.3	59.0	59.4
105°	70.8	71.1	71.5	71.9	72.3	72.8	73.1	73.5	74.0	74.4	74.6
107.5°	88.8	89.1	89.4	89.7	90.0	90.3	90.5	90.7	90.9	91.1	91.3
110°	101.2	101.4	101.6	101.9	102.0	102.3	102.5	102.6	102.9	103.1	103.1



TEST NUMBER: P333251-935

CATALOG NUMBER: S125DIP-S1090D365U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	113.1	113.4	113.7	113.9	114.2	114.4	114.5	114.6	114.7	114.8	114.8
115°	132.2	132.4	132.6	132.7	132.9	133.0	132.9	132.9	132.8	132.7	132.7
117.5°	150.4	150.5	150.7	150.8	150.8	151.0	151.0	151.1	151.2	151.2	151.1
120°	162.9	163.2	163.2	163.2	163.3	163.4	163.4	163.4	163.4	163.4	163.2
122.5°	174.7	174.9	175.0	175.2	175.4	175.6	175.6	175.5	175.4	175.4	175.2
125°	193.0	193.3	193.4	193.4	193.5	193.6	193.4	193.3	193.1	193.0	192.9
127.5°	210.6	210.8	210.9	210.9	211.0	211.0	211.0	210.9	210.9	210.8	210.7
130°	222.0	222.2	222.3	222.5	222.7	222.7	222.7	222.7	222.6	222.5	222.4
132.5°	233.8	234.1	234.0	234.0	234.0	233.9	233.8	233.8	233.8	233.7	233.6
135°	250.6	250.8	250.9	250.9	251.0	251.1	251.1	251.1	251.1	251.1	250.9
137.5°	266.8	267.1	267.3	267.3	267.5	267.7	267.8	267.9	267.9	268.0	267.9
140°	277.1	277.3	277.5	277.8	277.9	278.1	278.3	278.4	278.5	278.7	278.6
142.5°	287.3	287.6	287.8	288.1	288.3	288.6	288.7	288.8	288.9	289.0	288.8
145°	302.6	302.9	303.1	303.3	303.5	303.7	303.7	303.7	303.7	303.7	303.6
147.5°	316.4	316.6	316.8	316.9	317.0	317.2	317.4	317.5	317.7	317.9	317.7
150°	325.0	325.1	325.4	325.7	326.0	326.2	326.2	326.2	326.2	326.2	326.1
152.5°	333.5	333.6	333.7	333.8	333.9	334.0	334.2	334.3	334.5	334.7	334.6
155°	345.1	345.1	345.2	345.3	345.3	345.4	345.7	345.9	346.2	346.5	346.5
157.5°	355.2	355.2	355.2	355.3	355.3	355.4	355.7	355.9	356.3	356.5	356.5
160°	361.4	361.3	361.4	361.4	361.4	361.5	361.8	362.1	362.3	362.6	362.6
162.5°	367.1	367.0	367.0	367.1	367.1	367.1	367.5	367.7	368.1	368.4	368.4
165°	374.7	374.6	374.7	374.8	374.9	374.9	375.2	375.5	375.7	376.0	375.9
167.5°	380.5	380.3	380.3	380.3	380.3	380.3	380.7	381.2	381.5	381.9	381.9
170°	383.8	383.7	383.7	383.7	383.7	383.7	384.2	384.5	385.0	385.4	385.3
172.5°	386.3	386.2	386.2	386.2	386.2	386.2	386.6	387.0	387.4	387.8	387.8
175°	389.1	388.9	388.9	388.9	388.9	388.9	389.3	389.7	390.1	390.5	390.5
177.5°	390.6	390.5	390.5	390.5	390.4	390.3	390.6	391.0	391.3	391.6	391.6
180°	391.1	391.1	391.1	391.1	391.1	391.1	391.1	391.1	391.1	391.1	391.1



TEST NUMBER: P333251-935

CATALOG NUMBER: S125DIP-S1090D365U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2
2.5°	1304.5	1307.8	1305.0	1308.7	1305.0	1307.8	1304.5	1307.3	1311.5	1308.7	1315.2
5°	1202.4	1197.1	1200.6	1198.3	1200.6	1197.1	1202.4	1205.2	1212.2	1214.5	1219.2
7.5°	1108.0	1103.0	1097.3	1094.6	1097.3	1103.0	1108.0	1109.7	1115.7	1124.4	1131.0
10°	1049.0	1042.6	1042.0	1037.9	1042.0	1042.6	1049.0	1055.3	1059.4	1070.5	1078.0
12.5°	1005.7	999.8	993.2	991.4	993.2	999.8	1005.7	1011.2	1012.4	1024.8	1030.1
15°	944.3	939.7	935.6	939.1	935.6	939.7	944.3	947.8	954.2	962.9	968.7
17.5°	893.3	889.5	888.8	884.5	888.8	889.5	893.3	895.3	905.8	911.5	921.4
20°	861.3	858.3	859.5	852.0	859.5	858.3	861.3	866.5	876.9	879.9	890.3
22.5°	835.7	830.0	829.3	827.8	829.3	830.0	835.7	840.4	842.5	851.4	858.7
25°	795.6	792.6	789.8	792.6	789.8	792.6	795.6	800.8	803.1	809.5	816.5
27.5°	760.6	757.1	756.3	756.6	756.3	757.1	760.6	760.1	766.4	771.5	776.6
30°	739.2	733.4	734.0	733.4	734.0	733.4	739.2	739.2	742.7	747.3	752.0
32.5°	715.9	712.0	711.2	710.2	711.2	712.0	715.9	715.1	719.5	725.0	730.1
35°	681.7	681.7	678.7	678.7	678.7	681.7	681.7	683.4	688.0	688.0	693.9
37.5°	649.5	648.8	647.1	647.4	647.1	648.8	649.5	650.8	652.5	655.0	658.7
40°	625.3	624.7	622.9	619.5	622.9	624.7	625.3	627.6	628.8	631.7	634.0
42.5°	602.0	600.1	599.3	598.1	599.3	600.1	602.0	603.5	604.2	608.0	612.6
45°	565.4	565.4	564.3	563.7	564.3	565.4	565.4	565.4	566.0	570.7	573.0
47.5°	529.9	530.9	533.1	532.8	533.1	530.9	529.9	528.9	529.2	531.5	534.2
50°	508.5	509.1	510.8	511.4	510.8	509.1	508.5	506.2	505.0	505.0	506.8
52.5°	484.7	488.2	490.3	490.0	490.3	488.2	484.7	482.9	480.9	478.0	480.7
55°	451.5	455.6	459.7	460.3	459.7	455.6	451.5	446.3	444.0	439.4	441.1
57.5°	418.6	424.3	428.6	430.1	428.6	424.3	418.6	412.3	404.8	402.6	399.3
60°	396.3	403.9	409.1	411.5	409.1	403.9	396.3	390.5	380.6	374.3	372.0
62.5°	375.0	383.4	388.7	389.1	388.7	383.4	375.0	365.8	356.0	348.7	344.1
65°	339.9	348.7	353.4	356.8	353.4	348.7	339.9	330.1	319.0	309.2	303.9
67.5°	302.3	311.0	316.2	318.9	316.2	311.0	302.3	290.1	280.0	268.6	262.4
70°	274.9	283.6	290.6	292.9	290.6	283.6	274.9	260.4	251.7	241.2	235.9
72.5°	247.9	255.7	261.3	264.1	261.3	255.7	247.9	234.3	224.2	213.7	206.6
75°	201.0	211.5	216.8	219.6	216.8	211.5	201.0	193.6	181.9	170.8	165.1
77.5°	155.1	164.5	167.7	169.2	167.7	164.5	155.1	146.2	137.4	129.3	123.6
80°	124.3	130.2	134.2	134.8	134.2	130.2	124.3	117.4	110.4	102.9	97.6
82.5°	95.6	100.4	101.7	103.2	101.7	100.4	95.6	89.5	83.4	77.7	73.4
85°	52.3	54.6	55.2	54.6	55.2	54.6	52.3	48.2	45.3	42.4	40.6
87.5°	18.5	18.1	18.2	19.1	18.2	18.1	18.5	17.6	18.0	17.0	16.0
90°	6.7	6.9	7.1	7.3	7.1	6.9	6.7	6.5	6.2	5.9	5.5
92.5°	13.9	14.0	14.2	14.4	14.2	14.0	13.9	13.8	13.4	13.0	12.6
95°	25.7	25.9	26.0	26.2	26.0	25.9	25.7	25.7	25.3	24.9	24.4
97.5°	39.4	39.5	39.6	39.7	39.6	39.5	39.4	39.3	39.1	38.7	38.2
100°	49.5	49.7	49.8	49.9	49.8	49.7	49.5	49.3	49.0	48.4	47.8
102.5°	59.6	59.8	59.9	60.1	59.9	59.8	59.6	59.4	59.0	58.3	57.6
105°	74.8	75.1	75.3	75.5	75.3	75.1	74.8	74.6	74.4	74.0	73.5
107.5°	91.2	91.2	91.2	91.2	91.2	91.2	91.2	91.3	91.1	90.9	90.7
110°	103.1	103.0	102.9	102.9	102.9	103.0	103.1	103.1	103.1	102.9	102.6



TEST NUMBER: P333251-935

CATALOG NUMBER: S125DIP-S1090D365U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	114.7	114.5	114.4	114.3	114.4	114.5	114.7	114.8	114.8	114.7	114.6
115°	132.6	132.5	132.4	132.3	132.4	132.5	132.6	132.7	132.7	132.8	132.9
117.5°	150.8	150.6	150.3	150.0	150.3	150.6	150.8	151.1	151.2	151.2	151.1
120°	163.0	162.7	162.5	162.2	162.5	162.7	163.0	163.2	163.4	163.4	163.4
122.5°	175.0	174.8	174.6	174.4	174.6	174.8	175.0	175.2	175.4	175.4	175.5
125°	192.9	192.8	192.7	192.6	192.7	192.8	192.9	192.9	193.0	193.1	193.3
127.5°	210.6	210.4	210.3	210.2	210.3	210.4	210.6	210.7	210.8	210.9	210.9
130°	222.2	222.1	222.0	221.9	222.0	222.1	222.2	222.4	222.5	222.6	222.7
132.5°	233.3	233.2	233.0	232.8	233.0	233.2	233.3	233.6	233.7	233.8	233.8
135°	250.6	250.4	250.1	249.9	250.1	250.4	250.6	250.9	251.1	251.1	251.1
137.5°	267.5	267.2	266.8	266.5	266.8	267.2	267.5	267.9	268.0	267.9	267.9
140°	278.3	277.9	277.6	277.2	277.6	277.9	278.3	278.6	278.7	278.5	278.4
142.5°	288.4	288.1	287.8	287.5	287.8	288.1	288.4	288.8	289.0	288.9	288.8
145°	303.4	303.2	303.0	302.8	303.0	303.2	303.4	303.6	303.7	303.7	303.7
147.5°	317.3	316.8	316.3	315.9	316.3	316.8	317.3	317.7	317.9	317.7	317.5
150°	326.1	325.9	325.7	325.6	325.7	325.9	326.1	326.1	326.2	326.2	326.2
152.5°	334.4	334.2	333.9	333.6	333.9	334.2	334.4	334.6	334.7	334.5	334.3
155°	346.1	345.8	345.4	345.1	345.4	345.8	346.1	346.5	346.5	346.2	345.9
157.5°	356.0	355.5	355.1	354.6	355.1	355.5	356.0	356.5	356.5	356.3	355.9
160°	362.2	361.9	361.5	361.2	361.5	361.9	362.2	362.6	362.6	362.3	362.1
162.5°	368.0	367.6	367.2	366.8	367.2	367.6	368.0	368.4	368.4	368.1	367.7
165°	375.5	375.1	374.7	374.3	374.7	375.1	375.5	375.9	376.0	375.7	375.5
167.5°	381.5	381.1	380.6	380.3	380.6	381.1	381.5	381.9	381.9	381.5	381.2
170°	384.9	384.4	383.9	383.4	383.9	384.4	384.9	385.3	385.4	385.0	384.5
172.5°	387.4	386.9	386.5	386.1	386.5	386.9	387.4	387.8	387.8	387.4	387.0
175°	390.0	389.5	389.1	388.6	389.1	389.5	390.0	390.5	390.5	390.1	389.7
177.5°	391.2	390.8	390.5	390.0	390.5	390.8	391.2	391.6	391.6	391.3	391.0
180°	391.1	391.1	391.1	391.1	391.1	391.1	391.1	391.1	391.1	391.1	391.1



TEST NUMBER: P333251-935

CATALOG NUMBER: S125DIP-S1090D365U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2
2.5°	1309.2	1314.7	1321.7	1326.8	1336.1	1340.3	1345.4	1349.6	1357.0	1364.0	1372.4
5°	1221.0	1230.8	1244.2	1258.7	1275.6	1287.2	1303.5	1313.4	1333.1	1351.2	1368.6
7.5°	1141.0	1153.1	1172.0	1190.6	1212.7	1232.7	1253.0	1275.6	1300.8	1330.6	1355.2
10°	1086.2	1102.4	1122.7	1146.0	1172.8	1195.9	1223.3	1247.7	1278.5	1313.4	1345.9
12.5°	1042.4	1056.4	1079.0	1101.4	1130.0	1158.3	1186.5	1218.8	1254.8	1293.4	1334.3
15°	982.1	993.8	1012.4	1043.1	1072.2	1100.1	1142.5	1172.8	1218.1	1261.0	1310.4
17.5°	930.7	945.0	960.7	987.1	1017.2	1052.1	1089.9	1127.8	1171.6	1226.1	1281.8
20°	899.0	910.6	928.7	949.0	980.9	1015.8	1051.9	1090.2	1143.7	1200.1	1259.9
22.5°	864.6	877.2	897.5	919.7	946.6	980.0	1019.8	1061.9	1117.7	1173.1	1238.0
25°	824.1	832.8	851.4	871.2	897.9	926.3	967.6	1014.1	1069.3	1132.6	1198.9
27.5°	785.8	793.5	810.5	827.7	851.8	885.6	922.5	969.5	1021.5	1085.6	1159.2
30°	758.4	766.5	781.6	800.2	823.5	853.1	890.9	935.0	990.8	1053.6	1130.3
32.5°	734.7	741.8	753.3	771.9	794.6	823.4	858.3	903.4	959.2	1022.9	1098.2
35°	697.9	706.1	714.8	729.4	749.1	777.0	815.4	857.7	911.2	972.8	1042.0
37.5°	661.4	670.3	678.0	691.1	709.1	733.7	766.9	811.1	859.4	918.8	985.2
40°	638.7	645.7	652.0	666.0	684.0	707.2	738.0	777.6	828.7	883.9	939.1
42.5°	615.9	622.4	627.8	640.0	656.6	678.9	708.3	746.8	794.3	845.8	894.5
45°	580.0	584.0	590.4	600.9	614.2	634.6	663.1	697.3	737.4	786.3	822.9
47.5°	541.1	547.5	552.8	562.0	572.9	592.9	620.2	649.4	685.7	722.0	747.8
50°	511.4	517.8	525.4	534.1	544.5	563.1	588.1	617.8	648.5	676.4	698.5
52.5°	483.5	489.4	497.5	505.7	518.5	534.3	555.6	581.9	612.3	632.2	650.7
55°	442.2	445.1	454.4	462.6	474.8	486.4	507.9	531.2	549.7	564.9	580.0
57.5°	400.0	404.0	409.3	416.6	428.8	442.4	457.4	478.0	489.0	496.7	508.5
60°	373.1	374.3	377.7	386.4	395.7	407.9	425.4	439.9	448.1	454.4	464.3
62.5°	343.4	343.5	349.4	355.8	362.7	375.9	390.0	401.8	408.5	411.6	421.1
65°	301.6	300.4	303.9	309.2	317.3	326.0	338.2	348.7	348.1	351.5	357.4
67.5°	259.0	257.8	257.8	262.8	269.4	277.2	285.6	291.6	291.7	296.4	299.3
70°	230.1	226.6	228.9	233.1	235.9	242.4	251.7	254.0	254.5	256.8	259.8
72.5°	200.4	199.2	201.0	202.9	204.8	209.8	217.7	219.1	219.2	220.6	225.3
75°	159.2	158.1	156.9	158.7	161.0	164.5	167.4	169.7	169.1	169.7	173.1
77.5°	119.3	116.1	115.5	116.5	117.0	119.2	122.2	121.9	122.5	122.3	126.3
80°	94.7	90.1	89.5	89.5	90.1	91.3	92.4	93.6	91.8	93.6	94.7
82.5°	69.7	66.8	66.7	66.2	66.4	66.6	67.3	68.0	67.7	68.4	69.1
85°	38.3	37.2	35.5	36.6	36.0	34.3	35.5	33.7	33.1	33.7	34.3
87.5°	14.0	14.5	13.4	13.3	12.7	13.2	12.1	11.5	10.9	11.4	12.6
90°	5.2	4.9	4.4	4.0	3.4	3.0	2.5	1.9	1.4	0.9	0.3
92.5°	12.1	11.7	11.1	10.5	9.9	9.4	8.9	8.5	8.1	7.7	7.4
95°	23.9	23.4	22.7	22.0	21.4	20.8	20.3	20.1	20.1	19.9	19.8
97.5°	37.8	37.3	36.3	35.5	34.5	33.6	33.1	33.1	33.0	32.9	32.9
100°	47.2	46.6	45.7	44.8	43.9	43.0	42.6	42.6	42.6	42.6	42.6
102.5°	57.0	56.3	55.9	55.4	54.9	54.5	54.2	53.9	53.6	53.4	53.0
105°	73.1	72.8	72.3	71.9	71.5	71.1	70.8	70.4	70.1	69.7	69.4
107.5°	90.5	90.3	90.0	89.7	89.4	89.1	88.8	88.4	88.1	87.7	87.4
110°	102.5	102.3	102.0	101.9	101.6	101.4	101.2	100.8	100.5	100.1	99.8



TEST NUMBER: P333251-935

CATALOG NUMBER: S125DIP-S1090D365U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	114.5	114.4	114.2	113.9	113.7	113.4	113.1	113.0	112.8	112.6	112.4
115°	132.9	133.0	132.9	132.7	132.6	132.4	132.2	132.0	131.7	131.4	131.1
117.5°	151.0	151.0	150.8	150.8	150.7	150.5	150.4	150.2	150.2	150.0	149.9
120°	163.4	163.4	163.3	163.2	163.2	163.2	162.9	162.6	162.3	162.0	161.6
122.5°	175.6	175.6	175.4	175.2	175.0	174.9	174.7	174.6	174.5	174.4	174.3
125°	193.4	193.6	193.5	193.4	193.4	193.3	193.0	192.6	192.3	191.8	191.4
127.5°	211.0	211.0	211.0	210.9	210.9	210.8	210.6	210.3	210.2	209.9	209.7
130°	222.7	222.7	222.7	222.5	222.3	222.2	222.0	221.6	221.3	220.9	220.6
132.5°	233.8	233.9	234.0	234.0	234.0	234.1	233.8	233.2	232.7	232.1	231.6
135°	251.1	251.1	251.0	250.9	250.9	250.8	250.6	250.1	249.8	249.3	248.9
137.5°	267.8	267.7	267.5	267.3	267.3	267.1	266.8	266.4	266.0	265.6	265.3
140°	278.3	278.1	277.9	277.8	277.5	277.3	277.1	276.7	276.4	276.0	275.7
142.5°	288.7	288.6	288.3	288.1	287.8	287.6	287.3	287.1	286.7	286.5	286.2
145°	303.7	303.7	303.5	303.3	303.1	302.9	302.6	302.4	302.1	301.9	301.6
147.5°	317.4	317.2	317.0	316.9	316.8	316.6	316.4	316.2	316.1	316.0	315.8
150°	326.2	326.2	326.0	325.7	325.4	325.1	325.0	325.1	325.2	325.3	325.3
152.5°	334.2	334.0	333.9	333.8	333.7	333.6	333.5	333.4	333.3	333.2	333.1
155°	345.7	345.4	345.3	345.3	345.2	345.1	345.1	345.1	345.1	345.1	345.1
157.5°	355.7	355.4	355.3	355.3	355.2	355.2	355.2	355.3	355.5	355.7	355.8
160°	361.8	361.5	361.4	361.4	361.4	361.3	361.4	361.5	361.7	362.0	362.1
162.5°	367.5	367.1	367.1	367.1	367.0	367.0	367.1	367.3	367.5	367.6	367.7
165°	375.2	374.9	374.9	374.8	374.7	374.6	374.7	374.8	375.0	375.1	375.2
167.5°	380.7	380.3	380.3	380.3	380.3	380.3	380.5	380.7	381.0	381.3	381.5
170°	384.2	383.7	383.7	383.7	383.7	383.7	383.8	384.2	384.4	384.7	385.0
172.5°	386.6	386.2	386.2	386.2	386.2	386.2	386.3	386.6	386.8	387.1	387.4
175°	389.3	388.9	388.9	388.9	388.9	388.9	389.1	389.3	389.6	389.9	390.1
177.5°	390.6	390.3	390.4	390.5	390.5	390.5	390.6	390.9	391.1	391.3	391.5
180°	391.1	391.1	391.1	391.1	391.1	391.1	391.1	391.1	391.1	391.1	391.1



TEST NUMBER: P333251-935

CATALOG NUMBER: S125DIP-S1090D365U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2
2.5°	1376.6	1383.1	1387.2	1395.2	1401.7	1405.4	1408.7	1411.4	1414.7	1417.5	1425.4
5°	1385.4	1400.5	1413.3	1433.0	1451.1	1465.1	1480.1	1493.5	1504.5	1520.3	1532.4
7.5°	1381.6	1408.4	1436.6	1467.1	1498.4	1527.4	1554.2	1579.2	1601.8	1629.3	1653.3
10°	1377.9	1414.5	1450.5	1491.8	1534.2	1570.2	1604.0	1638.2	1663.2	1698.1	1727.7
12.5°	1375.1	1418.2	1461.6	1511.3	1557.9	1608.8	1653.6	1678.7	1716.7	1744.6	1779.8
15°	1363.3	1420.3	1480.1	1535.9	1602.1	1649.2	1688.8	1737.6	1773.1	1808.4	1846.8
17.5°	1342.3	1406.8	1473.8	1546.9	1610.4	1661.0	1711.9	1758.9	1801.3	1848.8	1896.6
20°	1332.6	1397.1	1473.8	1548.7	1610.9	1663.8	1716.1	1767.8	1814.3	1875.3	1930.5
22.5°	1312.1	1390.1	1460.8	1533.9	1597.8	1655.4	1714.7	1773.4	1835.2	1904.1	1973.3
25°	1275.6	1354.6	1429.6	1501.7	1566.2	1638.2	1701.6	1780.0	1859.1	1950.3	2036.3
27.5°	1237.7	1313.4	1382.1	1451.6	1526.9	1608.4	1690.7	1779.7	1883.1	1998.3	2119.6
30°	1207.0	1278.5	1345.3	1416.8	1495.2	1587.1	1677.1	1782.9	1902.6	2032.2	2176.3
32.5°	1171.2	1237.1	1302.1	1377.8	1463.2	1560.1	1665.1	1781.1	1924.9	2072.2	2220.5
35°	1110.0	1165.2	1232.0	1312.8	1409.3	1520.3	1641.7	1778.8	1943.9	2113.0	2237.9
37.5°	1037.3	1088.7	1159.2	1247.7	1348.8	1467.9	1612.1	1774.8	1950.1	2084.9	2125.2
40°	988.5	1036.1	1109.4	1201.2	1304.7	1430.7	1588.8	1760.8	1930.5	2016.5	1983.4
42.5°	936.4	986.4	1057.7	1148.7	1260.0	1397.3	1559.5	1731.6	1873.8	1906.3	1791.8
45°	854.3	905.9	976.3	1068.2	1187.8	1336.6	1505.7	1662.1	1744.0	1685.3	1508.0
47.5°	777.9	826.4	891.6	986.3	1109.8	1263.7	1426.6	1551.3	1557.8	1417.7	1228.4
50°	725.8	770.6	836.3	931.0	1053.6	1209.4	1356.3	1454.6	1410.4	1251.7	1069.9
52.5°	674.7	718.5	783.3	877.0	998.2	1141.0	1277.8	1346.7	1263.5	1100.7	945.3
55°	600.9	639.2	702.6	789.2	904.2	1036.7	1153.0	1176.8	1068.7	908.3	782.2
57.5°	528.8	564.6	622.2	702.0	807.2	924.5	1015.5	1010.4	896.1	758.5	658.4
60°	480.0	514.9	566.0	643.9	739.8	840.9	918.8	900.2	786.9	668.3	584.0
62.5°	436.4	467.4	515.8	583.9	671.4	765.1	829.1	801.6	690.6	586.9	520.4
65°	372.0	398.0	439.4	497.5	570.1	647.4	696.8	661.3	566.6	485.9	432.4
67.5°	310.5	331.4	366.0	412.3	474.3	536.4	566.5	530.8	455.0	396.1	356.5
70°	271.4	290.0	316.7	358.0	412.0	464.3	487.0	455.0	389.9	339.4	310.9
72.5°	232.3	247.7	271.1	308.2	351.5	396.9	416.8	386.2	332.8	290.1	263.5
75°	179.6	190.0	206.3	231.9	266.1	302.2	313.2	286.5	252.2	220.2	202.9
77.5°	128.5	137.4	149.7	165.8	190.1	213.0	222.7	207.2	180.7	160.5	146.2
80°	98.8	103.4	113.9	127.3	146.5	161.0	167.4	157.5	138.9	123.8	112.7
82.5°	70.4	75.1	81.4	92.4	104.6	114.5	121.3	114.7	101.3	89.4	83.0
85°	34.3	37.2	40.6	45.3	54.6	60.4	59.8	55.8	50.5	45.9	42.4
87.5°	12.2	12.8	14.3	16.8	18.3	20.2	21.3	20.4	18.6	17.3	16.0
90°	0.9	1.4	1.9	2.5	3.0	3.4	4.0	4.4	4.9	5.2	5.5
92.5°	7.7	8.1	8.5	8.9	9.4	9.9	10.5	11.1	11.7	12.1	12.6
95°	19.9	20.1	20.1	20.3	20.8	21.4	22.0	22.7	23.4	23.9	24.4
97.5°	32.9	33.0	33.1	33.1	33.6	34.5	35.5	36.3	37.3	37.8	38.2
100°	42.6	42.6	42.6	42.6	43.0	43.9	44.8	45.7	46.6	47.2	47.8
102.5°	53.4	53.6	53.9	54.2	54.5	54.9	55.4	55.9	56.3	57.0	57.6
105°	69.7	70.1	70.4	70.8	71.1	71.5	71.9	72.3	72.8	73.1	73.5
107.5°	87.7	88.1	88.4	88.8	89.1	89.4	89.7	90.0	90.3	90.5	90.7
110°	100.1	100.5	100.8	101.2	101.4	101.6	101.9	102.0	102.3	102.5	102.6



TEST NUMBER: P333251-935

CATALOG NUMBER: S125DIP-S1090D365U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	112.6	112.8	113.0	113.1	113.4	113.7	113.9	114.2	114.4	114.5	114.6
115°	131.4	131.7	132.0	132.2	132.4	132.6	132.7	132.9	133.0	132.9	132.9
117.5°	150.0	150.2	150.2	150.4	150.5	150.7	150.8	150.8	151.0	151.0	151.1
120°	162.0	162.3	162.6	162.9	163.2	163.2	163.2	163.3	163.4	163.4	163.4
122.5°	174.4	174.5	174.6	174.7	174.9	175.0	175.2	175.4	175.6	175.6	175.5
125°	191.8	192.3	192.6	193.0	193.3	193.4	193.4	193.5	193.6	193.4	193.3
127.5°	209.9	210.2	210.3	210.6	210.8	210.9	210.9	211.0	211.0	211.0	210.9
130°	220.9	221.3	221.6	222.0	222.2	222.3	222.5	222.7	222.7	222.7	222.7
132.5°	232.1	232.7	233.2	233.8	234.1	234.0	234.0	234.0	233.9	233.8	233.8
135°	249.3	249.8	250.1	250.6	250.8	250.9	250.9	251.0	251.1	251.1	251.1
137.5°	265.6	266.0	266.4	266.8	267.1	267.3	267.3	267.5	267.7	267.8	267.9
140°	276.0	276.4	276.7	277.1	277.3	277.5	277.8	277.9	278.1	278.3	278.4
142.5°	286.5	286.7	287.1	287.3	287.6	287.8	288.1	288.3	288.6	288.7	288.8
145°	301.9	302.1	302.4	302.6	302.9	303.1	303.3	303.5	303.7	303.7	303.7
147.5°	316.0	316.1	316.2	316.4	316.6	316.8	316.9	317.0	317.2	317.4	317.5
150°	325.3	325.2	325.1	325.0	325.1	325.4	325.7	326.0	326.2	326.2	326.2
152.5°	333.2	333.3	333.4	333.5	333.6	333.7	333.8	333.9	334.0	334.2	334.3
155°	345.1	345.1	345.1	345.1	345.1	345.2	345.3	345.3	345.4	345.7	345.9
157.5°	355.7	355.5	355.3	355.2	355.2	355.2	355.3	355.3	355.4	355.7	355.9
160°	362.0	361.7	361.5	361.4	361.3	361.4	361.4	361.4	361.5	361.8	362.1
162.5°	367.6	367.5	367.3	367.1	367.0	367.0	367.1	367.1	367.1	367.5	367.7
165°	375.1	375.0	374.8	374.7	374.6	374.7	374.8	374.9	374.9	375.2	375.5
167.5°	381.3	381.0	380.7	380.5	380.3	380.3	380.3	380.3	380.3	380.7	381.2
170°	384.7	384.4	384.2	383.8	383.7	383.7	383.7	383.7	383.7	384.2	384.5
172.5°	387.1	386.8	386.6	386.3	386.2	386.2	386.2	386.2	386.2	386.6	387.0
175°	389.9	389.6	389.3	389.1	388.9	388.9	388.9	388.9	388.9	389.3	389.7
177.5°	391.3	391.1	390.9	390.6	390.5	390.5	390.5	390.4	390.3	390.6	391.0
180°	391.1	391.1	391.1	391.1	391.1	391.1	391.1	391.1	391.1	391.1	391.1



TEST NUMBER: P333251-935

CATALOG NUMBER: S125DIP-S1090D365U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2
2.5°	1431.9	1435.6	1443.6	1440.7	1444.5	1446.3	1448.2
5°	1547.6	1566.2	1574.3	1573.1	1585.4	1582.4	1579.5
7.5°	1678.2	1697.7	1708.7	1722.3	1730.2	1730.7	1737.6
10°	1752.1	1777.7	1788.1	1802.7	1812.0	1817.2	1816.6
12.5°	1808.9	1828.9	1852.3	1859.4	1872.0	1878.5	1876.1
15°	1877.1	1909.0	1933.5	1945.6	1961.4	1966.0	1972.4
17.5°	1937.9	1980.8	2009.3	2047.2	2061.5	2070.2	2065.1
20°	1984.0	2040.4	2068.8	2114.2	2139.2	2152.5	2147.9
22.5°	2038.4	2099.4	2152.1	2191.3	2229.3	2247.4	2251.1
25°	2131.6	2215.3	2292.6	2344.3	2391.3	2402.4	2426.8
27.5°	2235.8	2334.4	2417.1	2471.4	2504.2	2516.5	2524.2
30°	2301.3	2399.5	2461.7	2496.6	2507.0	2505.9	2504.6
32.5°	2333.4	2394.9	2406.8	2397.0	2373.1	2352.9	2331.8
35°	2287.9	2242.0	2173.4	2085.1	2020.0	1954.4	1947.9
37.5°	2057.7	1910.9	1796.7	1669.2	1595.7	1550.2	1518.9
40°	1841.0	1674.2	1535.9	1428.4	1353.5	1323.8	1294.8
42.5°	1605.8	1446.5	1324.0	1234.1	1177.8	1144.9	1121.8
45°	1304.7	1164.0	1068.2	1003.1	958.3	932.7	918.2
47.5°	1069.0	965.0	883.6	836.6	805.7	785.8	785.9
50°	942.6	843.3	789.2	752.0	725.2	709.6	712.5
52.5°	830.5	756.3	710.2	679.0	659.3	649.6	649.3
55°	694.5	641.0	610.8	588.1	574.7	563.7	566.0
57.5°	594.0	549.0	528.7	509.9	500.6	496.2	489.7
60°	531.8	496.9	479.4	464.3	455.0	451.5	445.1
62.5°	476.4	449.0	432.0	419.7	411.3	410.2	405.2
65°	400.4	379.4	364.4	358.5	349.8	347.5	347.5
67.5°	330.1	315.1	303.3	298.0	294.2	294.7	292.0
70°	285.9	273.7	266.1	260.4	257.4	258.0	255.7
72.5°	250.1	236.5	229.9	226.4	222.6	224.1	223.2
75°	189.4	182.4	179.0	175.5	173.1	172.0	170.8
77.5°	139.1	132.9	130.3	128.3	128.6	125.9	128.1
80°	107.5	102.3	100.6	97.6	97.0	97.0	96.4
82.5°	78.7	75.8	74.5	72.1	71.0	72.0	70.4
85°	40.6	38.3	37.8	37.8	36.6	35.5	38.3
87.5°	16.0	14.3	14.3	13.9	13.9	13.5	12.7
90°	5.9	6.2	6.5	6.7	6.9	7.1	7.3
92.5°	13.0	13.4	13.8	13.9	14.0	14.2	14.4
95°	24.9	25.3	25.7	25.7	25.9	26.0	26.2
97.5°	38.7	39.1	39.3	39.4	39.5	39.6	39.7
100°	48.4	49.0	49.3	49.5	49.7	49.8	49.9
102.5°	58.3	59.0	59.4	59.6	59.8	59.9	60.1
105°	74.0	74.4	74.6	74.8	75.1	75.3	75.5
107.5°	90.9	91.1	91.3	91.2	91.2	91.2	91.2
110°	102.9	103.1	103.1	103.1	103.0	102.9	102.9



TEST NUMBER: P333251-935

CATALOG NUMBER: S125DIP-S1090D365U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	114.7	114.8	114.8	114.7	114.5	114.4	114.3
115°	132.8	132.7	132.7	132.6	132.5	132.4	132.3
117.5°	151.2	151.2	151.1	150.8	150.6	150.3	150.0
120°	163.4	163.4	163.2	163.0	162.7	162.5	162.2
122.5°	175.4	175.4	175.2	175.0	174.8	174.6	174.4
125°	193.1	193.0	192.9	192.9	192.8	192.7	192.6
127.5°	210.9	210.8	210.7	210.6	210.4	210.3	210.2
130°	222.6	222.5	222.4	222.2	222.1	222.0	221.9
132.5°	233.8	233.7	233.6	233.3	233.2	233.0	232.8
135°	251.1	251.1	250.9	250.6	250.4	250.1	249.9
137.5°	267.9	268.0	267.9	267.5	267.2	266.8	266.5
140°	278.5	278.7	278.6	278.3	277.9	277.6	277.2
142.5°	288.9	289.0	288.8	288.4	288.1	287.8	287.5
145°	303.7	303.7	303.6	303.4	303.2	303.0	302.8
147.5°	317.7	317.9	317.7	317.3	316.8	316.3	315.9
150°	326.2	326.2	326.1	326.1	325.9	325.7	325.6
152.5°	334.5	334.7	334.6	334.4	334.2	333.9	333.6
155°	346.2	346.5	346.5	346.1	345.8	345.4	345.1
157.5°	356.3	356.5	356.5	356.0	355.5	355.1	354.6
160°	362.3	362.6	362.6	362.2	361.9	361.5	361.2
162.5°	368.1	368.4	368.4	368.0	367.6	367.2	366.8
165°	375.7	376.0	375.9	375.5	375.1	374.7	374.3
167.5°	381.5	381.9	381.9	381.5	381.1	380.6	380.3
170°	385.0	385.4	385.3	384.9	384.4	383.9	383.4
172.5°	387.4	387.8	387.8	387.4	386.9	386.5	386.1
175°	390.1	390.5	390.5	390.0	389.5	389.1	388.6
177.5°	391.3	391.6	391.6	391.2	390.8	390.5	390.0
180°	391.1	391.1	391.1	391.1	391.1	391.1	391.1

(END OF REPORT)