

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333525-927

Luminaire Tested: **S125RDIP-S610D365U927-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333525-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S610D365U927-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2924.8 lumens
Efficiency: N/A
Efficacy: 106.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333525-927

CATALOG NUMBER: S125RDIP-S610D365U927-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333525-927

CATALOG NUMBER: S125RDIP-S610D365U927-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69	64
1	101	97	93	90	95	91	88	85	81	78	76	71	69	67	62	60	59	55
2	92	85	79	74	87	80	75	70	71	67	63	63	59	57	55	52	50	46
3	85	75	68	62	79	71	64	59	63	58	53	56	52	48	49	46	43	40
4	78	67	59	53	73	63	56	50	56	50	46	50	45	42	44	40	37	34
5	71	60	51	45	67	56	49	43	50	44	40	45	40	36	39	36	33	30
6	66	54	45	39	62	51	43	38	45	39	35	41	36	32	36	32	29	26
7	61	49	40	35	57	46	39	34	41	35	31	37	32	28	33	29	26	23
8	57	44	36	31	53	42	35	30	38	32	28	34	29	25	30	26	23	21
9	53	40	33	28	50	39	32	27	35	29	25	31	26	23	28	24	21	19
10	50	37	30	25	47	36	29	24	32	26	23	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5147	5147	5147
5°	5159	5100	5131
10°	5119	5052	5052
15°	5059	4950	4910
20°	4981	4807	4748
25°	4890	4666	4563
30°	4776	4502	4359
35°	4660	4332	4128
40°	4552	4156	3903
45°	4420	3958	3656
50°	4287	3744	3399
55°	4135	3538	3125
60°	3981	3289	2830
65°	3799	2998	2492
70°	3592	2638	2149
75°	3306	2221	1787
80°	2912	1748	1499
85°	2453	1430	1341



TEST NUMBER: P333525-927

CATALOG NUMBER: S125RDIP-S610D365U927-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.9	2.6
10°-20°	209.4	7.2
20°-30°	303.7	10.4
30°-40°	346.1	11.8
40°-50°	337.4	11.5
50°-60°	284.0	9.7
60°-70°	199.1	6.8
70°-80°	102.3	3.5
80°-90°	26.6	0.9
90°-100°	100.7	3.4
100°-110°	216.4	7.4
110°-120°	203.1	6.9
120°-130°	164.6	5.6
130°-140°	132.1	4.5
140°-150°	99.7	3.4
150°-160°	70.1	2.4
160°-170°	41.4	1.4
170°-180°	13.5	0.5
0°-30°	588.0	20.1
0°-40°	934.1	31.9
0°-60°	1555.4	53.2
0°-90°	1883.4	64.4
90°-120°	520.1	17.8
90°-150°	916.4	31.3
90°-180°	1041.0	35.6
0°-180°	2924.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	797	797	797	797	797	
5°	796	793	787	792	792	75
15°	757	752	740	739	734	213
25°	686	676	655	647	640	316
35°	591	576	550	533	524	370
45°	484	466	433	410	400	373
55°	367	347	314	288	278	328
65°	249	228	196	173	163	246
75°	132	114	89	76	72	140
85°	33	23	19	19	18	37
90°	0	2	4	6	6	2
95°	9	27	248	113	66	10
105°	32	44	203	400	371	33
115°	57	68	163	351	413	56
125°	78	92	156	279	326	70
135°	92	110	155	234	270	71
145°	107	122	156	194	213	67
155°	122	131	152	171	179	56
165°	133	137	146	154	157	38
175°	139	139	140	141	141	13
180°	139	139	139	139	139	



TEST NUMBER: P333525-927

CATALOG NUMBER: S125RDIP-S610D365U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	796.9	796.9	796.9	796.9	796.9	796.9	796.9	796.9	796.9	796.9	796.9
2.5°	798.4	798.0	797.7	797.4	797.1	796.4	795.3	794.2	793.1	792.1	793.1
5°	795.7	795.2	794.6	794.1	793.5	792.6	791.1	789.6	788.1	786.6	788.0
7.5°	787.9	787.3	786.9	786.3	785.8	784.7	782.9	781.2	779.4	777.6	778.6
10°	780.6	780.2	779.8	779.4	779.0	777.9	776.0	774.2	772.3	770.4	770.8
12.5°	772.5	772.0	771.4	771.0	770.4	768.9	766.4	763.9	761.4	758.8	759.1
15°	756.6	755.7	754.9	754.2	753.4	751.5	748.8	745.9	743.1	740.3	740.2
17.5°	738.6	737.4	736.2	735.0	733.7	731.3	727.8	724.3	720.7	717.2	716.5
20°	724.7	723.3	722.0	720.6	719.3	716.5	712.3	708.0	703.7	699.4	698.7
22.5°	709.2	707.9	706.6	705.3	703.9	701.0	696.5	692.1	687.5	683.0	681.8
25°	686.2	684.1	682.1	680.2	678.1	674.6	669.7	664.7	659.8	654.8	653.2
27.5°	659.7	657.3	654.8	652.4	649.9	646.1	640.8	635.5	630.2	624.9	622.4
30°	640.4	637.9	635.3	632.8	630.3	626.1	620.5	615.0	609.3	603.7	600.6
32.5°	621.6	618.7	615.7	612.8	609.7	605.4	599.7	594.0	588.2	582.5	579.1
35°	591.0	587.9	584.6	581.5	578.2	573.6	567.6	561.6	555.6	549.5	545.7
37.5°	561.1	557.1	553.3	549.4	545.5	540.4	534.2	528.0	521.8	515.6	511.0
40°	539.9	535.9	531.9	527.8	523.9	518.6	512.2	505.8	499.4	493.0	487.9
42.5°	517.8	513.7	509.5	505.4	501.3	495.9	489.3	482.6	476.0	469.4	464.5
45°	483.9	480.1	476.2	472.3	468.4	462.8	455.4	448.1	440.7	433.3	428.0
47.5°	448.9	444.8	440.7	436.7	432.5	426.7	419.4	411.9	404.6	397.1	391.7
50°	426.7	422.3	417.9	413.5	409.1	403.1	395.5	387.9	380.2	372.6	366.9
52.5°	402.7	398.2	393.6	389.1	384.6	378.7	371.5	364.3	357.1	349.9	343.9
55°	367.2	362.9	358.6	354.3	350.1	344.1	336.7	329.2	321.7	314.2	308.2
57.5°	331.3	326.7	322.1	317.6	313.0	307.0	299.8	292.6	285.4	278.2	272.3
60°	308.2	303.5	298.8	294.1	289.5	283.5	276.2	269.0	261.8	254.6	248.7
62.5°	283.6	279.2	274.6	270.2	265.8	259.8	252.5	245.2	237.9	230.5	225.1
65°	248.6	244.1	239.5	235.0	230.4	224.6	217.5	210.4	203.3	196.2	190.8
67.5°	213.8	209.2	204.7	200.2	195.6	190.0	183.2	176.3	169.5	162.7	157.9
70°	190.2	185.7	181.1	176.6	172.0	166.4	159.7	153.0	146.3	139.7	135.5
72.5°	167.1	162.6	158.2	153.8	149.3	143.9	137.7	131.4	125.2	118.9	115.1
75°	132.5	128.4	124.4	120.4	116.4	111.5	105.9	100.3	94.7	89.0	86.1
77.5°	98.0	94.7	91.6	88.3	85.2	81.3	76.8	72.3	67.8	63.3	61.2
80°	78.3	75.0	71.9	68.6	65.4	61.9	58.1	54.4	50.7	47.0	45.7
82.5°	59.0	56.1	53.2	50.3	47.5	44.7	42.1	39.5	37.0	34.5	33.9
85°	33.1	30.7	28.3	25.9	23.4	21.9	21.2	20.6	20.0	19.3	19.1
87.5°	11.2	10.5	9.8	9.2	8.6	8.2	8.2	8.2	8.1	8.1	8.2
90°	0.3	0.6	1.1	1.7	2.2	2.8	3.1	3.6	3.9	4.5	4.8
92.5°	3.4	4.1	6.5	10.0	14.8	23.0	38.3	63.8	91.7	90.2	73.0
95°	9.3	9.5	11.7	14.8	21.0	33.6	63.5	125.2	202.4	248.0	242.7
97.5°	15.4	15.7	17.3	20.4	25.9	34.9	54.7	99.9	180.8	264.9	307.1
100°	19.6	20.1	21.3	24.3	29.7	38.1	54.3	90.7	161.3	252.8	322.8
102.5°	24.3	24.6	25.5	28.8	33.7	41.9	56.3	86.9	146.5	231.6	313.4
105°	31.6	31.6	33.0	35.8	40.3	48.2	60.4	85.4	132.1	203.0	283.4
107.5°	38.8	39.4	40.7	43.0	47.7	54.7	66.6	87.9	126.1	183.3	252.6
110°	44.0	44.5	45.6	48.2	52.4	59.7	71.1	90.5	124.3	174.1	235.2



TEST NUMBER: P333525-927

CATALOG NUMBER: S125RDIP-S610D365U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	49.1	49.7	50.5	53.1	57.3	64.3	75.3	93.6	124.3	168.7	222.2
115°	56.6	57.1	58.0	60.4	64.6	71.7	82.1	98.2	125.2	163.0	208.0
117.5°	63.3	64.1	65.0	67.5	72.3	79.1	88.9	103.6	127.0	160.1	199.6
120°	67.7	68.6	69.7	72.2	77.0	84.0	93.8	107.3	128.8	158.8	194.9
122.5°	72.5	73.0	74.0	76.5	81.7	88.7	98.5	111.2	130.3	157.6	190.8
125°	78.4	79.0	80.3	82.9	88.2	95.5	104.7	116.8	133.0	156.2	185.4
127.5°	83.0	83.9	85.6	88.9	94.5	101.8	110.7	121.8	135.9	155.6	180.3
130°	86.0	86.8	89.0	92.7	98.5	105.8	114.5	125.2	137.8	155.1	177.0
132.5°	88.2	89.3	92.0	96.0	102.1	109.4	118.1	128.1	139.7	155.1	174.3
135°	91.8	92.9	96.3	100.8	106.7	114.2	122.9	132.1	142.5	155.1	171.0
137.5°	96.4	97.3	100.4	104.9	110.7	118.4	126.4	135.1	145.0	155.4	168.2
140°	99.1	100.0	103.3	107.8	113.1	120.6	128.8	137.2	146.2	155.7	166.8
142.5°	102.3	102.8	106.0	110.5	115.6	122.7	130.3	138.3	146.8	155.9	165.7
145°	106.9	107.5	110.3	114.2	119.3	125.7	133.0	140.0	147.5	155.7	164.1
147.5°	111.9	112.2	114.6	118.3	122.6	128.3	134.7	141.0	147.8	155.0	162.3
150°	114.8	115.3	117.3	121.0	124.8	129.6	135.8	141.6	147.8	154.2	161.0
152.5°	118.0	118.3	120.0	123.2	126.9	131.2	136.9	142.1	147.6	153.4	159.4
155°	122.1	122.1	123.7	126.5	129.4	133.2	138.0	142.5	146.9	151.8	156.8
157.5°	125.8	125.7	127.1	129.4	131.9	134.9	138.9	142.8	146.2	150.0	154.3
160°	128.3	127.9	129.0	131.0	133.2	135.8	139.4	142.8	145.6	148.9	152.3
162.5°	130.2	130.0	131.1	132.8	134.6	136.7	139.9	142.6	144.9	147.6	150.5
165°	133.2	132.7	133.6	134.9	136.1	137.8	140.0	142.2	143.9	145.6	147.8
167.5°	135.3	135.0	135.5	136.3	137.0	138.2	140.0	141.6	142.4	143.6	145.2
170°	136.7	136.3	136.7	137.2	137.8	138.6	140.0	141.1	141.6	142.5	143.6
172.5°	137.5	137.0	137.3	137.8	138.2	138.6	139.7	140.7	140.8	141.2	142.0
175°	138.6	138.0	138.3	138.6	138.6	138.6	139.4	140.0	139.7	139.7	140.0
177.5°	139.1	138.6	138.6	138.9	138.6	138.6	139.1	139.3	138.9	138.9	139.1
180°	138.9	138.9	138.9	138.9	138.9	138.9	138.9	138.9	138.9	138.9	138.9



TEST NUMBER: P333525-927

CATALOG NUMBER: S125RDIP-S610D365U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	796.9	796.9	796.9	796.9	796.9	796.9	796.9	796.9
2.5°	794.2	795.3	796.4	796.9	796.8	796.6	796.5	796.5
5°	789.3	790.7	792.0	792.6	792.3	792.0	791.8	791.5
7.5°	779.5	780.5	781.4	781.7	781.4	781.1	780.9	780.5
10°	771.2	771.6	772.1	772.1	771.6	771.2	770.8	770.4
12.5°	759.5	759.8	760.0	759.9	759.2	758.7	758.0	757.4
15°	740.1	739.9	739.8	739.1	737.9	736.7	735.5	734.3
17.5°	715.9	715.2	714.5	713.7	712.7	711.7	710.7	709.7
20°	698.1	697.4	696.7	695.8	694.6	693.4	692.2	690.9
22.5°	680.4	679.1	677.8	676.6	675.7	674.6	673.7	672.6
25°	651.4	649.7	647.9	646.3	644.8	643.3	641.9	640.4
27.5°	620.0	617.6	615.1	613.2	611.8	610.4	609.0	607.5
30°	597.5	594.5	591.4	589.2	588.0	586.8	585.7	584.5
32.5°	575.7	572.4	568.9	566.5	564.9	563.4	561.9	560.4
35°	541.8	537.9	534.0	531.2	529.3	527.4	525.5	523.6
37.5°	506.3	501.6	496.9	493.7	491.9	490.1	488.3	486.5
40°	482.8	477.7	472.6	469.3	467.7	466.0	464.5	462.9
42.5°	459.6	454.7	449.9	446.2	443.9	441.6	439.2	436.9
45°	422.6	417.3	411.9	408.3	406.3	404.3	402.3	400.3
47.5°	386.1	380.6	375.1	371.2	369.0	366.8	364.6	362.3
50°	361.3	355.7	350.1	346.3	344.3	342.3	340.2	338.3
52.5°	337.9	331.8	325.7	321.7	319.7	317.7	315.7	313.7
55°	302.1	296.1	290.1	286.1	283.9	281.8	279.6	277.5
57.5°	266.4	260.5	254.7	250.7	248.8	246.9	245.1	243.2
60°	242.8	236.9	231.1	227.1	225.1	223.1	221.1	219.1
62.5°	219.6	214.1	208.7	204.9	203.0	201.0	198.9	196.9
65°	185.5	180.1	174.8	171.1	169.1	167.2	165.1	163.1
67.5°	153.0	148.1	143.1	139.9	138.3	136.7	135.1	133.5
70°	131.3	127.2	123.0	120.2	118.6	117.0	115.3	113.8
72.5°	111.3	107.4	103.6	101.2	100.1	99.0	98.0	96.9
75°	83.2	80.2	77.3	75.3	74.5	73.5	72.6	71.6
77.5°	59.2	57.1	55.1	53.7	53.0	52.3	51.7	50.9
80°	44.5	43.3	42.1	41.4	41.1	40.9	40.6	40.3
82.5°	33.3	32.7	32.2	31.8	31.7	31.5	31.4	31.2
85°	19.0	18.9	18.7	18.6	18.5	18.3	18.2	18.1
87.5°	8.2	8.3	8.3	8.4	8.3	8.2	8.2	8.0
90°	5.1	5.3	5.6	6.2	6.2	6.2	6.4	6.4
92.5°	49.6	36.0	27.1	23.0	19.4	18.7	18.3	17.8
95°	201.3	158.8	124.3	100.8	80.9	72.5	70.3	65.8
97.5°	299.8	270.0	236.4	203.7	186.4	170.7	162.6	159.0
100°	344.4	330.7	301.8	272.7	253.3	233.2	222.8	218.4
102.5°	359.3	367.8	354.0	334.3	313.6	299.3	288.0	284.7
105°	350.5	388.9	401.2	398.2	389.1	379.9	374.3	371.0
107.5°	318.9	370.1	401.7	416.4	420.9	420.9	419.0	416.8
110°	295.6	348.9	388.3	412.1	424.7	430.0	432.0	432.0



TEST NUMBER: P333525-927

CATALOG NUMBER: S125RDIP-S610D365U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	277.3	327.8	367.7	395.8	414.2	423.3	428.2	430.2
115°	254.2	297.6	336.0	366.5	388.3	401.7	409.6	413.2
117.5°	239.3	276.7	309.7	337.8	359.6	373.5	381.3	383.5
120°	231.2	264.8	295.6	320.3	341.0	354.4	362.0	364.2
122.5°	225.2	256.4	283.8	306.8	325.3	337.6	345.2	347.2
125°	216.4	244.9	269.3	289.5	305.1	316.6	322.8	325.6
127.5°	207.5	234.1	256.8	275.7	289.9	300.1	305.9	307.1
130°	201.8	226.5	248.3	266.6	280.5	289.8	295.4	297.1
132.5°	196.2	219.4	239.2	256.7	270.7	279.9	285.0	286.9
135°	189.0	208.3	226.2	242.2	254.5	263.7	268.8	270.5
137.5°	182.8	198.4	213.3	226.9	237.9	246.3	251.0	252.8
140°	179.4	192.6	205.5	217.2	227.6	234.9	239.1	240.5
142.5°	176.6	187.7	198.8	209.0	217.8	223.9	227.9	229.1
145°	172.8	181.4	190.1	197.6	204.4	209.1	212.2	213.3
147.5°	169.1	176.2	182.9	188.6	193.9	197.7	199.5	200.0
150°	167.2	173.3	178.6	183.6	187.8	191.2	192.3	192.6
152.5°	164.9	170.4	175.2	179.2	182.7	185.4	186.5	186.8
155°	161.5	166.0	169.9	173.0	175.8	177.8	178.6	178.9
157.5°	158.2	161.8	164.9	167.3	169.5	171.1	171.9	171.8
160°	156.0	158.8	161.5	163.5	165.5	166.8	167.4	167.2
162.5°	153.4	156.1	158.4	160.2	161.7	162.8	163.0	162.9
165°	150.0	152.0	153.7	155.1	156.2	156.8	156.8	156.8
167.5°	146.8	148.1	149.4	150.4	151.0	151.5	151.2	151.1
170°	145.0	145.8	146.7	147.3	147.8	148.1	148.1	147.8
172.5°	143.0	143.9	144.5	144.8	144.9	145.4	145.0	144.7
175°	140.9	140.9	141.4	141.4	141.4	141.6	141.1	140.9
177.5°	139.3	139.5	139.5	139.5	139.3	139.5	138.9	138.9
180°	138.9	138.9	138.9	138.9	138.9	138.9	138.9	138.9

(END OF REPORT)