

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333530-927

Luminaire Tested: **S125RDIP-S610D590U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333530-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S610D590U927-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3504.4 lumens
Efficiency: N/A
Efficacy: 106.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333530-927

CATALOG NUMBER: S125RDIP-S610D590U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333530-927

CATALOG NUMBER: S125RDIP-S610D590U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	60	60	60	54
1	99	95	91	87	92	88	85	82	75	73	71	64	62	60	53	52	51	46
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43	39
3	82	73	66	60	76	68	62	57	59	54	50	50	46	43	42	39	37	33
4	76	65	57	51	70	60	53	48	52	47	43	45	41	37	37	34	32	28
5	69	58	50	44	64	54	47	41	47	41	37	40	36	32	34	31	28	25
6	64	52	44	38	59	49	41	36	42	37	32	36	32	28	31	27	25	22
7	59	47	39	34	55	44	37	32	38	33	29	33	29	25	28	25	22	20
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	26	22	20	18
9	51	39	32	27	48	37	30	25	32	27	23	28	24	20	24	20	18	16
10	48	36	29	24	45	34	27	23	30	24	21	26	22	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5147	5147	5147
5°	5159	5100	5131
10°	5119	5052	5052
15°	5059	4950	4910
20°	4981	4807	4748
25°	4890	4666	4563
30°	4776	4502	4359
35°	4660	4332	4128
40°	4552	4156	3903
45°	4420	3958	3656
50°	4287	3744	3399
55°	4135	3538	3125
60°	3981	3289	2830
65°	3799	2998	2492
70°	3592	2638	2149
75°	3306	2221	1787
80°	2912	1748	1499
85°	2453	1430	1341



TEST NUMBER: P333530-927

CATALOG NUMBER: S125RDIP-S610D590U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.9	2.1
10°-20°	209.4	6.0
20°-30°	303.7	8.7
30°-40°	346.1	9.9
40°-50°	337.4	9.6
50°-60°	284.0	8.1
60°-70°	199.1	5.7
70°-80°	102.3	2.9
80°-90°	27.1	0.8
90°-100°	38.9	1.1
100°-110°	114.9	3.3
110°-120°	194.5	5.6
120°-130°	256.0	7.3
130°-140°	286.9	8.2
140°-150°	281.2	8.0
150°-160°	236.2	6.7
160°-170°	157.0	4.5
170°-180°	54.9	1.6
0°-30°	588.0	16.8
0°-40°	934.1	26.7
0°-60°	1555.4	44.4
0°-90°	1883.9	53.8
90°-120°	348.3	9.9
90°-150°	1172.4	33.5
90°-180°	1620.0	46.2
0°-180°	3504.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	797	797	797	797	797	
5°	796	793	787	792	792	75
15°	757	752	740	739	734	213
25°	686	676	655	647	640	316
35°	591	576	550	533	524	370
45°	484	466	433	410	400	373
55°	367	347	314	288	278	328
65°	249	228	196	173	163	246
75°	132	114	89	76	72	140
85°	33	23	19	19	18	37
90°	0	4	7	10	11	3
95°	29	30	35	38	39	31
105°	103	105	108	111	112	110
115°	195	197	198	197	197	193
125°	284	287	287	287	286	254
135°	370	372	373	373	371	285
145°	448	450	451	451	450	280
155°	512	512	513	514	512	236
165°	557	556	557	558	556	157
175°	579	578	578	580	577	55
180°	581	581	581	581	581	



TEST NUMBER: P333530-927

CATALOG NUMBER: S125RDIP-S610D590U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	796.9	796.9	796.9	796.9	796.9	796.9	796.9	796.9	796.9	796.9	796.9
2.5°	798.4	798.0	797.7	797.4	797.1	796.4	795.3	794.2	793.1	792.1	793.1
5°	795.7	795.2	794.6	794.1	793.5	792.6	791.1	789.6	788.1	786.6	788.0
7.5°	787.9	787.3	786.9	786.3	785.8	784.7	782.9	781.2	779.4	777.6	778.6
10°	780.6	780.2	779.8	779.4	779.0	777.9	776.0	774.2	772.3	770.4	770.8
12.5°	772.5	772.0	771.4	771.0	770.4	768.9	766.4	763.9	761.4	758.8	759.1
15°	756.6	755.7	754.9	754.2	753.4	751.5	748.8	745.9	743.1	740.3	740.2
17.5°	738.6	737.4	736.2	735.0	733.7	731.3	727.8	724.3	720.7	717.2	716.5
20°	724.7	723.3	722.0	720.6	719.3	716.5	712.3	708.0	703.7	699.4	698.7
22.5°	709.2	707.9	706.6	705.3	703.9	701.0	696.5	692.1	687.5	683.0	681.8
25°	686.2	684.1	682.1	680.2	678.1	674.6	669.7	664.7	659.8	654.8	653.2
27.5°	659.7	657.3	654.8	652.4	649.9	646.1	640.8	635.5	630.2	624.9	622.4
30°	640.4	637.9	635.3	632.8	630.3	626.1	620.5	615.0	609.3	603.7	600.6
32.5°	621.6	618.7	615.7	612.8	609.7	605.4	599.7	594.0	588.2	582.5	579.1
35°	591.0	587.9	584.6	581.5	578.2	573.6	567.6	561.6	555.6	549.5	545.7
37.5°	561.1	557.1	553.3	549.4	545.5	540.4	534.2	528.0	521.8	515.6	511.0
40°	539.9	535.9	531.9	527.8	523.9	518.6	512.2	505.8	499.4	493.0	487.9
42.5°	517.8	513.7	509.5	505.4	501.3	495.9	489.3	482.6	476.0	469.4	464.5
45°	483.9	480.1	476.2	472.3	468.4	462.8	455.4	448.1	440.7	433.3	428.0
47.5°	448.9	444.8	440.7	436.7	432.5	426.7	419.4	411.9	404.6	397.1	391.7
50°	426.7	422.3	417.9	413.5	409.1	403.1	395.5	387.9	380.2	372.6	366.9
52.5°	402.7	398.2	393.6	389.1	384.6	378.7	371.5	364.3	357.1	349.9	343.9
55°	367.2	362.9	358.6	354.3	350.1	344.1	336.7	329.2	321.7	314.2	308.2
57.5°	331.3	326.7	322.1	317.6	313.0	307.0	299.8	292.6	285.4	278.2	272.3
60°	308.2	303.5	298.8	294.1	289.5	283.5	276.2	269.0	261.8	254.6	248.7
62.5°	283.6	279.2	274.6	270.2	265.8	259.8	252.5	245.2	237.9	230.5	225.1
65°	248.6	244.1	239.5	235.0	230.4	224.6	217.5	210.4	203.3	196.2	190.8
67.5°	213.8	209.2	204.7	200.2	195.6	190.0	183.2	176.3	169.5	162.7	157.9
70°	190.2	185.7	181.1	176.6	172.0	166.4	159.7	153.0	146.3	139.7	135.5
72.5°	167.1	162.6	158.2	153.8	149.3	143.9	137.7	131.4	125.2	118.9	115.1
75°	132.5	128.4	124.4	120.4	116.4	111.5	105.9	100.3	94.7	89.0	86.1
77.5°	98.0	94.7	91.6	88.3	85.2	81.3	76.8	72.3	67.8	63.3	61.2
80°	78.3	75.0	71.9	68.6	65.4	61.9	58.1	54.4	50.7	47.0	45.7
82.5°	59.0	56.1	53.2	50.3	47.5	44.7	42.1	39.5	37.0	34.5	33.9
85°	33.1	30.7	28.3	25.9	23.4	21.9	21.2	20.6	20.0	19.3	19.1
87.5°	11.2	10.6	10.0	9.4	8.8	8.6	8.6	8.6	8.6	8.6	8.8
90°	0.5	1.3	2.1	2.9	3.6	4.4	5.1	5.9	6.5	7.2	7.8
92.5°	10.9	11.5	12.0	12.6	13.2	13.9	14.7	15.6	16.5	17.3	18.0
95°	29.4	29.5	29.8	29.9	30.2	30.8	31.8	32.8	33.8	34.8	35.5
97.5°	48.8	48.9	49.0	49.0	49.1	49.8	51.3	52.6	54.0	55.4	56.1
100°	63.3	63.3	63.3	63.3	63.3	63.9	65.2	66.5	67.8	69.2	70.0
102.5°	78.8	79.2	79.6	80.0	80.4	81.0	81.6	82.3	82.9	83.6	84.6
105°	103.1	103.5	104.0	104.6	105.0	105.6	106.2	106.8	107.4	108.0	108.6
107.5°	129.8	130.3	130.8	131.3	131.8	132.3	132.8	133.2	133.6	134.1	134.4
110°	148.2	148.7	149.2	149.7	150.3	150.7	150.9	151.2	151.5	151.9	152.2



TEST NUMBER: P333530-927

CATALOG NUMBER: S125RDIP-S610D590U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	167.0	167.3	167.5	167.8	168.1	168.4	168.8	169.1	169.5	169.9	170.1
115°	194.8	195.2	195.6	196.0	196.4	196.7	196.9	197.1	197.3	197.5	197.4
117.5°	222.6	222.8	223.0	223.2	223.3	223.6	223.7	223.9	224.0	224.3	224.3
120°	240.0	240.5	241.0	241.5	242.0	242.2	242.4	242.5	242.6	242.6	242.6
122.5°	258.8	259.0	259.1	259.3	259.5	259.7	260.0	260.2	260.5	260.8	260.7
125°	284.2	284.9	285.4	286.1	286.7	287.0	287.1	287.2	287.3	287.4	287.2
127.5°	311.4	311.7	312.0	312.4	312.8	313.0	313.1	313.2	313.3	313.5	313.4
130°	327.6	328.1	328.7	329.2	329.6	330.0	330.2	330.4	330.6	330.8	330.7
132.5°	343.9	344.8	345.5	346.3	347.2	347.6	347.5	347.5	347.5	347.5	347.4
135°	369.6	370.3	370.9	371.5	372.1	372.4	372.6	372.6	372.7	372.8	372.8
137.5°	393.9	394.5	395.1	395.6	396.2	396.6	396.9	397.0	397.3	397.5	397.6
140°	409.4	410.0	410.4	410.9	411.5	411.9	412.2	412.5	412.7	413.0	413.3
142.5°	425.0	425.4	425.8	426.3	426.7	427.1	427.5	427.9	428.3	428.6	428.7
145°	447.8	448.2	448.7	449.1	449.5	449.8	450.1	450.4	450.8	451.0	451.0
147.5°	469.0	469.2	469.4	469.7	469.9	470.1	470.3	470.6	470.9	471.1	471.3
150°	483.1	483.0	482.9	482.8	482.7	482.8	483.2	483.6	484.0	484.4	484.4
152.5°	494.6	494.8	495.0	495.1	495.2	495.4	495.5	495.7	495.8	496.1	496.3
155°	512.5	512.5	512.5	512.5	512.5	512.5	512.6	512.7	512.9	512.9	513.3
157.5°	528.4	528.1	527.9	527.8	527.5	527.4	527.5	527.7	527.8	527.8	528.2
160°	537.8	537.5	537.2	536.9	536.5	536.5	536.5	536.7	536.8	536.9	537.3
162.5°	546.1	545.9	545.7	545.4	545.2	545.1	545.1	545.2	545.2	545.2	545.7
165°	557.2	557.0	556.8	556.6	556.4	556.3	556.4	556.6	556.7	556.7	557.1
167.5°	566.6	566.3	565.8	565.4	565.0	564.8	564.8	564.8	564.8	564.8	565.4
170°	571.6	571.2	570.8	570.5	570.1	569.9	569.9	569.9	569.9	569.9	570.5
172.5°	575.3	574.9	574.5	574.1	573.7	573.5	573.5	573.5	573.5	573.5	574.1
175°	579.3	578.9	578.5	578.1	577.7	577.6	577.6	577.6	577.6	577.6	578.1
177.5°	581.5	581.1	580.8	580.5	580.1	580.0	579.9	579.8	579.7	579.6	580.1
180°	580.7	580.7	580.7	580.7	580.7	580.7	580.7	580.7	580.7	580.7	580.7



TEST NUMBER: P333530-927

CATALOG NUMBER: S125RDIP-S610D590U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	796.9	796.9	796.9	796.9	796.9	796.9	796.9	796.9
2.5°	794.2	795.3	796.4	796.9	796.8	796.6	796.5	796.5
5°	789.3	790.7	792.0	792.6	792.3	792.0	791.8	791.5
7.5°	779.5	780.5	781.4	781.7	781.4	781.1	780.9	780.5
10°	771.2	771.6	772.1	772.1	771.6	771.2	770.8	770.4
12.5°	759.5	759.8	760.0	759.9	759.2	758.7	758.0	757.4
15°	740.1	739.9	739.8	739.1	737.9	736.7	735.5	734.3
17.5°	715.9	715.2	714.5	713.7	712.7	711.7	710.7	709.7
20°	698.1	697.4	696.7	695.8	694.6	693.4	692.2	690.9
22.5°	680.4	679.1	677.8	676.6	675.7	674.6	673.7	672.6
25°	651.4	649.7	647.9	646.3	644.8	643.3	641.9	640.4
27.5°	620.0	617.6	615.1	613.2	611.8	610.4	609.0	607.5
30°	597.5	594.5	591.4	589.2	588.0	586.8	585.7	584.5
32.5°	575.7	572.4	568.9	566.5	564.9	563.4	561.9	560.4
35°	541.8	537.9	534.0	531.2	529.3	527.4	525.5	523.6
37.5°	506.3	501.6	496.9	493.7	491.9	490.1	488.3	486.5
40°	482.8	477.7	472.6	469.3	467.7	466.0	464.5	462.9
42.5°	459.6	454.7	449.9	446.2	443.9	441.6	439.2	436.9
45°	422.6	417.3	411.9	408.3	406.3	404.3	402.3	400.3
47.5°	386.1	380.6	375.1	371.2	369.0	366.8	364.6	362.3
50°	361.3	355.7	350.1	346.3	344.3	342.3	340.2	338.3
52.5°	337.9	331.8	325.7	321.7	319.7	317.7	315.7	313.7
55°	302.1	296.1	290.1	286.1	283.9	281.8	279.6	277.5
57.5°	266.4	260.5	254.7	250.7	248.8	246.9	245.1	243.2
60°	242.8	236.9	231.1	227.1	225.1	223.1	221.1	219.1
62.5°	219.6	214.1	208.7	204.9	203.0	201.0	198.9	196.9
65°	185.5	180.1	174.8	171.1	169.1	167.2	165.1	163.1
67.5°	153.0	148.1	143.1	139.9	138.3	136.7	135.1	133.5
70°	131.3	127.2	123.0	120.2	118.6	117.0	115.3	113.8
72.5°	111.3	107.4	103.6	101.2	100.1	99.0	98.0	96.9
75°	83.2	80.2	77.3	75.3	74.5	73.5	72.6	71.6
77.5°	59.2	57.1	55.1	53.7	53.0	52.3	51.7	50.9
80°	44.5	43.3	42.1	41.4	41.1	40.9	40.6	40.3
82.5°	33.3	32.7	32.2	31.8	31.7	31.5	31.4	31.2
85°	19.0	18.9	18.7	18.6	18.5	18.3	18.2	18.1
87.5°	8.9	9.0	9.1	9.1	9.0	9.0	9.0	8.9
90°	8.2	8.7	9.3	9.7	10.0	10.2	10.5	10.9
92.5°	18.7	19.3	20.0	20.4	20.7	20.9	21.1	21.3
95°	36.2	36.9	37.6	38.0	38.3	38.5	38.7	38.9
97.5°	56.7	57.4	58.1	58.5	58.5	58.7	58.8	58.9
100°	71.0	71.9	72.7	73.3	73.5	73.8	73.9	74.1
102.5°	85.6	86.6	87.5	88.2	88.5	88.7	89.0	89.3
105°	109.2	109.8	110.4	110.9	111.1	111.5	111.8	112.1
107.5°	134.8	135.1	135.3	135.5	135.5	135.5	135.4	135.4
110°	152.4	152.7	153.0	153.1	153.0	153.0	152.8	152.7



TEST NUMBER: P333530-927

CATALOG NUMBER: S125RDIP-S610D590U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	170.2	170.3	170.5	170.5	170.3	170.1	169.9	169.8
115°	197.3	197.2	197.1	197.0	196.9	196.8	196.7	196.6
117.5°	224.4	224.5	224.6	224.4	224.0	223.6	223.2	222.8
120°	242.6	242.6	242.6	242.5	242.1	241.7	241.3	240.9
122.5°	260.6	260.5	260.5	260.2	259.9	259.6	259.3	259.0
125°	287.0	286.8	286.6	286.5	286.4	286.3	286.1	286.1
127.5°	313.2	313.1	313.1	312.9	312.7	312.5	312.3	312.1
130°	330.6	330.5	330.4	330.3	330.0	329.9	329.6	329.5
132.5°	347.2	347.1	347.1	346.8	346.6	346.3	346.0	345.7
135°	372.8	372.8	372.8	372.6	372.2	371.9	371.5	371.1
137.5°	397.8	397.8	398.0	397.8	397.3	396.8	396.3	395.8
140°	413.4	413.7	413.8	413.7	413.2	412.7	412.2	411.7
142.5°	428.8	429.0	429.0	428.9	428.4	427.9	427.4	426.9
145°	451.0	451.0	451.0	450.8	450.6	450.3	450.0	449.6
147.5°	471.6	471.8	472.1	471.8	471.1	470.5	469.8	469.1
150°	484.4	484.4	484.4	484.3	484.2	483.9	483.8	483.5
152.5°	496.5	496.8	497.0	496.9	496.5	496.2	495.8	495.5
155°	513.7	514.1	514.5	514.5	514.0	513.5	512.9	512.5
157.5°	528.6	529.0	529.4	529.3	528.6	528.0	527.4	526.6
160°	537.7	538.1	538.4	538.4	538.0	537.4	536.9	536.5
162.5°	546.1	546.6	547.2	547.1	546.5	545.9	545.3	544.7
165°	557.5	557.9	558.4	558.3	557.7	557.1	556.4	555.9
167.5°	566.0	566.6	567.2	567.2	566.6	565.9	565.3	564.7
170°	571.1	571.6	572.3	572.2	571.6	570.8	570.1	569.4
172.5°	574.7	575.3	575.9	575.9	575.3	574.6	574.0	573.4
175°	578.8	579.3	580.0	579.9	579.2	578.5	577.8	577.1
177.5°	580.6	581.1	581.5	581.5	581.0	580.4	579.8	579.2
180°	580.7	580.7	580.7	580.7	580.7	580.7	580.7	580.7

(END OF REPORT)