

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333269-935

Luminaire Tested: **S125DIP-S1090D810U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333269-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S1090D810U935-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6279.5 lumens  
Efficiency: N/A  
Efficacy: 115.4 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Direct  
  
Input Watts (W): 54.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333269-935

CATALOG NUMBER: S125DIP-S1090D810U935-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333269-935

CATALOG NUMBER: S125DIP-S1090D810U935-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	101	96	93	89	94	90	87	84	79	77	74	69	67	65	59	58	57	52
2	92	84	78	73	86	79	74	69	70	66	62	61	58	55	53	50	48	44
3	84	74	67	61	78	70	64	58	62	57	52	54	50	47	47	44	41	38
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	42	39	36	33
5	71	59	51	45	66	56	48	43	49	43	39	43	39	35	38	34	31	28
6	65	53	45	39	61	50	43	37	45	39	34	39	34	31	34	31	28	25
7	60	48	40	34	56	45	38	33	40	34	30	36	31	27	31	28	25	22
8	56	44	36	30	52	41	34	29	37	31	27	33	28	24	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	27	23	20	18
10	49	37	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	8843	8843	8843	8843
5°	10240	8873	7769	8873
10°	11913	8826	6807	8826
15°	13188	8762	6279	8762
20°	14762	8659	5856	8659
25°	17293	8543	5648	8543
30°	18678	8429	5469	8429
35°	15358	8215	5351	8215
40°	10916	7917	5223	7917
45°	8386	7516	5149	7516
50°	7159	7018	5138	7018
55°	6373	6531	5183	6531
60°	5749	5997	5315	5997
65°	5310	5462	5453	5462
70°	4828	4906	5531	4906
75°	4262	4319	5480	4319
80°	3585	3522	5013	3522
85°	2838	2542	4046	2542



TEST NUMBER: P333269-935

CATALOG NUMBER: S125DIP-S1090D810U935-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	131.8	2.1
10°-20°	392.4	6.2
20°-30°	637.2	10.1
30°-40°	777.3	12.4
40°-50°	707.1	11.3
50°-60°	563.2	9.0
60°-70°	392.3	6.2
70°-80°	209.2	3.3
80°-90°	54.7	0.9
90°-100°	57.9	0.9
100°-110°	171.1	2.7
110°-120°	289.8	4.6
120°-130°	381.4	6.1
130°-140°	427.4	6.8
140°-150°	418.9	6.7
150°-160°	351.8	5.6
160°-170°	233.9	3.7
170°-180°	81.8	1.3
0°-30°	1161.5	18.5
0°-40°	1938.8	30.9
0°-60°	3209.2	51.1
0°-90°	3865.4	61.6
90°-120°	518.9	8.3
90°-150°	1746.6	27.8
90°-180°	2414.0	38.4
0°-180°	6279.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1369	1369	1369	1369	1369	
5°	1580	1369	1198	1369	1580	159
15°	1972	1310	939	1310	1972	565
25°	2427	1199	793	1199	2427	1108
35°	1948	1042	679	1042	1948	1192
45°	918	823	564	823	918	735
55°	566	580	460	580	566	510
65°	348	357	357	357	348	345
75°	171	173	220	173	171	184
85°	38	34	55	34	38	45
90°	16	1	16	1	16	11
95°	58	44	58	44	58	59
105°	167	154	167	154	167	177
115°	293	290	293	290	293	290
125°	426	423	426	423	426	380
135°	553	551	553	551	553	426
145°	670	667	670	667	670	418
155°	763	763	763	763	763	351
165°	828	830	828	830	828	233
175°	860	863	860	863	860	82
180°	865	865	865	865	865	



TEST NUMBER: P333269-935

CATALOG NUMBER: S125DIP-S1090D810U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2
2.5°	1448.2	1446.3	1444.5	1440.7	1443.6	1435.6	1431.9	1425.4	1417.5	1414.7	1411.4
5°	1579.5	1582.4	1585.4	1573.1	1574.3	1566.2	1547.6	1532.4	1520.3	1504.5	1493.5
7.5°	1737.6	1730.7	1730.2	1722.3	1708.7	1697.7	1678.2	1653.3	1629.3	1601.8	1579.2
10°	1816.6	1817.2	1812.0	1802.7	1788.1	1777.7	1752.1	1727.7	1698.1	1663.2	1638.2
12.5°	1876.1	1878.5	1872.0	1859.4	1852.3	1828.9	1808.9	1779.8	1744.6	1716.7	1678.7
15°	1972.4	1966.0	1961.4	1945.6	1933.5	1909.0	1877.1	1846.8	1808.4	1773.1	1737.6
17.5°	2065.1	2070.2	2061.5	2047.2	2009.3	1980.8	1937.9	1896.6	1848.8	1801.3	1758.9
20°	2147.9	2152.5	2139.2	2114.2	2068.8	2040.4	1984.0	1930.5	1875.3	1814.3	1767.8
22.5°	2251.1	2247.4	2229.3	2191.3	2152.1	2099.4	2038.4	1973.3	1904.1	1835.2	1773.4
25°	2426.8	2402.4	2391.3	2344.3	2292.6	2215.3	2131.6	2036.3	1950.3	1859.1	1780.0
27.5°	2524.2	2516.5	2504.2	2471.4	2417.1	2334.4	2235.8	2119.6	1998.3	1883.1	1779.7
30°	2504.6	2505.9	2507.0	2496.6	2461.7	2399.5	2301.3	2176.3	2032.2	1902.6	1782.9
32.5°	2331.8	2352.9	2373.1	2397.0	2406.8	2394.9	2333.4	2220.5	2072.2	1924.9	1781.1
35°	1947.9	1954.4	2020.0	2085.1	2173.4	2242.0	2287.9	2237.9	2113.0	1943.9	1778.8
37.5°	1518.9	1550.2	1595.7	1669.2	1796.7	1910.9	2057.7	2125.2	2084.9	1950.1	1774.8
40°	1294.8	1323.8	1353.5	1428.4	1535.9	1674.2	1841.0	1983.4	2016.5	1930.5	1760.8
42.5°	1121.8	1144.9	1177.8	1234.1	1324.0	1446.5	1605.8	1791.8	1906.3	1873.8	1731.6
45°	918.2	932.7	958.3	1003.1	1068.2	1164.0	1304.7	1508.0	1685.3	1744.0	1662.1
47.5°	785.9	785.8	805.7	836.6	883.6	965.0	1069.0	1228.4	1417.7	1557.8	1551.3
50°	712.5	709.6	725.2	752.0	789.2	843.3	942.6	1069.9	1251.7	1410.4	1454.6
52.5°	649.3	649.6	659.3	679.0	710.2	756.3	830.5	945.3	1100.7	1263.5	1346.7
55°	566.0	563.7	574.7	588.1	610.8	641.0	694.5	782.2	908.3	1068.7	1176.8
57.5°	489.7	496.2	500.6	509.9	528.7	549.0	594.0	658.4	758.5	896.1	1010.4
60°	445.1	451.5	455.0	464.3	479.4	496.9	531.8	584.0	668.3	786.9	900.2
62.5°	405.2	410.2	411.3	419.7	432.0	449.0	476.4	520.4	586.9	690.6	801.6
65°	347.5	347.5	349.8	358.5	364.4	379.4	400.4	432.4	485.9	566.6	661.3
67.5°	292.0	294.7	294.2	298.0	303.3	315.1	330.1	356.5	396.1	455.0	530.8
70°	255.7	258.0	257.4	260.4	266.1	273.7	285.9	310.9	339.4	389.9	455.0
72.5°	223.2	224.1	222.6	226.4	229.9	236.5	250.1	263.5	290.1	332.8	386.2
75°	170.8	172.0	173.1	175.5	179.0	182.4	189.4	202.9	220.2	252.2	286.5
77.5°	128.1	125.9	128.6	128.3	130.3	132.9	139.1	146.2	160.5	180.7	207.2
80°	96.4	97.0	97.0	97.6	100.6	102.3	107.5	112.7	123.8	138.9	157.5
82.5°	70.4	72.0	71.0	72.1	74.5	75.8	78.7	83.0	89.4	101.3	114.7
85°	38.3	35.5	36.6	37.8	37.8	38.3	40.6	42.4	45.9	50.5	55.8
87.5°	14.4	15.2	15.6	15.5	15.9	15.8	17.5	17.3	18.6	19.8	21.4
90°	16.2	15.7	15.2	14.8	14.4	13.8	13.0	12.2	11.5	10.8	9.7
92.5°	31.8	31.4	31.1	30.8	30.5	29.8	28.8	27.8	26.9	25.8	24.5
95°	57.9	57.6	57.3	57.0	56.7	56.1	55.0	53.9	52.9	51.8	50.4
97.5°	87.8	87.6	87.4	87.2	87.0	86.5	85.5	84.6	83.5	82.6	80.5
100°	110.4	110.1	109.8	109.5	109.3	108.4	107.0	105.7	104.4	103.0	101.1
102.5°	133.0	132.6	132.2	131.8	131.4	130.4	129.0	127.5	126.1	124.6	123.6
105°	166.9	166.5	166.1	165.7	165.1	164.5	163.6	162.7	161.8	160.9	160.0
107.5°	201.7	201.7	201.7	201.8	201.8	201.6	201.1	200.7	200.3	199.8	199.1
110°	227.6	227.7	227.8	228.0	228.2	228.0	227.6	227.1	226.7	226.2	225.8



TEST NUMBER: P333269-935

CATALOG NUMBER: S125DIP-S1090D810U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	252.9	253.1	253.4	253.7	254.0	254.0	253.7	253.6	253.4	253.1	252.6
115°	292.9	293.0	293.2	293.3	293.4	293.6	293.8	293.9	294.0	294.2	293.9
117.5°	331.9	332.5	333.1	333.7	334.3	334.6	334.4	334.3	334.2	334.1	333.8
120°	358.9	359.5	360.1	360.7	361.3	361.5	361.5	361.5	361.5	361.5	361.4
122.5°	385.8	386.2	386.8	387.2	387.7	388.0	388.1	388.2	388.3	388.5	388.1
125°	426.2	426.4	426.5	426.6	426.8	427.0	427.3	427.6	427.9	428.2	428.0
127.5°	464.9	465.3	465.5	465.9	466.1	466.4	466.5	466.7	466.8	467.0	466.8
130°	490.8	491.1	491.4	491.7	492.0	492.2	492.4	492.5	492.7	492.8	492.5
132.5°	515.1	515.5	515.9	516.3	516.7	517.0	517.1	517.3	517.5	517.6	517.6
135°	552.8	553.4	554.0	554.6	555.2	555.4	555.4	555.4	555.4	555.4	555.3
137.5°	589.6	590.4	591.2	591.9	592.6	592.9	592.7	592.5	592.4	592.2	591.9
140°	613.4	614.1	614.8	615.6	616.3	616.6	616.2	616.0	615.7	615.4	614.9
142.5°	635.9	636.7	637.5	638.2	638.9	639.2	639.0	638.9	638.7	638.5	637.9
145°	669.9	670.4	670.8	671.2	671.7	671.9	671.9	671.9	671.9	671.9	671.5
147.5°	698.9	699.9	700.9	701.9	702.9	703.3	702.9	702.5	702.1	701.8	701.5
150°	720.4	720.7	721.0	721.3	721.6	721.8	721.8	721.8	721.8	721.8	721.2
152.5°	738.1	738.7	739.3	739.8	740.3	740.4	740.0	739.7	739.3	739.0	738.7
155°	763.4	764.2	765.0	765.7	766.5	766.5	765.9	765.3	764.7	764.1	764.0
157.5°	784.6	785.6	786.6	787.6	788.6	788.8	788.2	787.6	787.0	786.4	786.2
160°	799.2	799.9	800.6	801.4	802.2	802.2	801.6	801.1	800.5	799.9	799.7
162.5°	811.6	812.4	813.3	814.2	815.0	815.1	814.4	813.6	813.0	812.3	812.2
165°	828.1	829.0	829.9	830.8	831.7	831.8	831.3	830.7	830.1	829.5	829.3
167.5°	841.3	842.2	843.2	844.1	845.0	845.1	844.1	843.3	842.3	841.5	841.5
170°	848.3	849.4	850.4	851.4	852.5	852.6	851.7	850.8	849.9	848.9	848.9
172.5°	854.2	855.1	856.1	857.0	858.0	858.0	857.0	856.2	855.2	854.4	854.4
175°	859.8	860.8	861.9	862.9	863.9	864.0	863.2	862.2	861.3	860.4	860.4
177.5°	863.0	863.8	864.7	865.5	866.3	866.4	865.6	865.0	864.3	863.5	863.7
180°	865.1	865.1	865.1	865.1	865.1	865.1	865.1	865.1	865.1	865.1	865.1



TEST NUMBER: P333269-935

CATALOG NUMBER: S125DIP-S1090D810U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2
2.5°	1408.7	1405.4	1401.7	1395.2	1387.2	1383.1	1376.6	1372.4	1364.0	1357.0	1349.6
5°	1480.1	1465.1	1451.1	1433.0	1413.3	1400.5	1385.4	1368.6	1351.2	1333.1	1313.4
7.5°	1554.2	1527.4	1498.4	1467.1	1436.6	1408.4	1381.6	1355.2	1330.6	1300.8	1275.6
10°	1604.0	1570.2	1534.2	1491.8	1450.5	1414.5	1377.9	1345.9	1313.4	1278.5	1247.7
12.5°	1653.6	1608.8	1557.9	1511.3	1461.6	1418.2	1375.1	1334.3	1293.4	1254.8	1218.8
15°	1688.8	1649.2	1602.1	1535.9	1480.1	1420.3	1363.3	1310.4	1261.0	1218.1	1172.8
17.5°	1711.9	1661.0	1610.4	1546.9	1473.8	1406.8	1342.3	1281.8	1226.1	1171.6	1127.8
20°	1716.1	1663.8	1610.9	1548.7	1473.8	1397.1	1332.6	1259.9	1200.1	1143.7	1090.2
22.5°	1714.7	1655.4	1597.8	1533.9	1460.8	1390.1	1312.1	1238.0	1173.1	1117.7	1061.9
25°	1701.6	1638.2	1566.2	1501.7	1429.6	1354.6	1275.6	1198.9	1132.6	1069.3	1014.1
27.5°	1690.7	1608.4	1526.9	1451.6	1382.1	1313.4	1237.7	1159.2	1085.6	1021.5	969.5
30°	1677.1	1587.1	1495.2	1416.8	1345.3	1278.5	1207.0	1130.3	1053.6	990.8	935.0
32.5°	1665.1	1560.1	1463.2	1377.8	1302.1	1237.1	1171.2	1098.2	1022.9	959.2	903.4
35°	1641.7	1520.3	1409.3	1312.8	1232.0	1165.2	1110.0	1042.0	972.8	911.2	857.7
37.5°	1612.1	1467.9	1348.8	1247.7	1159.2	1088.7	1037.3	985.2	918.8	859.4	811.1
40°	1588.8	1430.7	1304.7	1201.2	1109.4	1036.1	988.5	939.1	883.9	828.7	777.6
42.5°	1559.5	1397.3	1260.0	1148.7	1057.7	986.4	936.4	894.5	845.8	794.3	746.8
45°	1505.7	1336.6	1187.8	1068.2	976.3	905.9	854.3	822.9	786.3	737.4	697.3
47.5°	1426.6	1263.7	1109.8	986.3	891.6	826.4	777.9	747.8	722.0	685.7	649.4
50°	1356.3	1209.4	1053.6	931.0	836.3	770.6	725.8	698.5	676.4	648.5	617.8
52.5°	1277.8	1141.0	998.2	877.0	783.3	718.5	674.7	650.7	632.2	612.3	581.9
55°	1153.0	1036.7	904.2	789.2	702.6	639.2	600.9	580.0	564.9	549.7	531.2
57.5°	1015.5	924.5	807.2	702.0	622.2	564.6	528.8	508.5	496.7	489.0	478.0
60°	918.8	840.9	739.8	643.9	566.0	514.9	480.0	464.3	454.4	448.1	439.9
62.5°	829.1	765.1	671.4	583.9	515.8	467.4	436.4	421.1	411.6	408.5	401.8
65°	696.8	647.4	570.1	497.5	439.4	398.0	372.0	357.4	351.5	348.1	348.7
67.5°	566.5	536.4	474.3	412.3	366.0	331.4	310.5	299.3	296.4	291.7	291.6
70°	487.0	464.3	412.0	358.0	316.7	290.0	271.4	259.8	256.8	254.5	254.0
72.5°	416.8	396.9	351.5	308.2	271.1	247.7	232.3	225.3	220.6	219.2	219.1
75°	313.2	302.2	266.1	231.9	206.3	190.0	179.6	173.1	169.7	169.1	169.7
77.5°	222.7	213.0	190.1	165.8	149.7	137.4	128.5	126.3	122.3	122.5	121.9
80°	167.4	161.0	146.5	127.3	113.9	103.4	98.8	94.7	93.6	91.8	93.6
82.5°	121.3	114.5	104.6	92.4	81.4	75.1	70.4	69.1	68.4	67.7	68.0
85°	59.8	60.4	54.6	45.3	40.6	37.2	34.3	34.3	33.7	33.1	33.7
87.5°	22.2	21.1	18.9	17.4	14.8	13.2	12.5	12.7	11.5	11.3	12.0
90°	8.7	7.7	6.5	5.4	4.3	3.1	1.9	0.7	1.9	3.1	4.3
92.5°	23.2	22.0	20.7	19.6	18.8	18.0	17.1	16.3	17.1	18.0	18.8
95°	48.8	47.4	45.9	44.9	44.7	44.3	44.1	43.7	44.1	44.3	44.7
97.5°	78.4	76.4	74.3	73.2	73.1	72.9	72.8	72.8	72.8	72.9	73.1
100°	99.1	97.2	95.2	94.3	94.3	94.3	94.3	94.3	94.3	94.3	94.3
102.5°	122.6	121.6	120.6	119.9	119.2	118.6	118.0	117.4	118.0	118.6	119.2
105°	159.1	158.3	157.3	156.5	155.8	155.0	154.3	153.5	154.3	155.0	155.8
107.5°	198.5	197.8	197.1	196.4	195.6	194.8	194.1	193.4	194.1	194.8	195.6
110°	225.3	224.9	224.5	223.9	223.1	222.3	221.6	220.8	221.6	222.3	223.1





TEST NUMBER: P333269-935

CATALOG NUMBER: S125DIP-S1090D810U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	252.0	251.4	250.9	250.4	250.0	249.6	249.3	248.8	249.3	249.6	250.0
115°	293.6	293.3	293.0	292.6	292.0	291.4	290.8	290.2	290.8	291.4	292.0
117.5°	333.6	333.3	333.0	332.7	332.4	332.2	331.9	331.7	331.9	332.2	332.4
120°	361.3	361.1	360.9	360.5	359.7	359.0	358.3	357.5	358.3	359.0	359.7
122.5°	387.7	387.3	386.9	386.6	386.3	386.1	385.8	385.5	385.8	386.1	386.3
125°	427.9	427.7	427.6	427.1	426.2	425.2	424.4	423.4	424.4	425.2	426.2
127.5°	466.6	466.4	466.2	465.9	465.4	464.9	464.4	463.9	464.4	464.9	465.4
130°	492.2	491.9	491.6	491.1	490.3	489.7	488.9	488.1	488.9	489.7	490.3
132.5°	517.7	517.8	517.8	517.3	516.0	514.8	513.6	512.4	513.6	514.8	516.0
135°	555.2	555.0	554.8	554.3	553.5	552.5	551.6	550.7	551.6	552.5	553.5
137.5°	591.5	591.2	590.9	590.3	589.4	588.6	587.7	586.9	587.7	588.6	589.4
140°	614.5	614.0	613.5	612.9	612.3	611.5	610.7	610.0	610.7	611.5	612.3
142.5°	637.4	636.8	636.3	635.7	635.0	634.4	633.8	633.2	633.8	634.4	635.0
145°	671.0	670.5	670.1	669.6	669.0	668.4	667.8	667.2	667.8	668.4	669.0
147.5°	701.1	700.8	700.3	700.0	699.7	699.4	699.0	698.7	699.0	699.4	699.7
150°	720.6	720.0	719.4	719.1	719.3	719.5	719.5	719.7	719.5	719.5	719.3
152.5°	738.5	738.2	738.0	737.8	737.6	737.4	737.2	736.9	737.2	737.4	737.6
155°	763.9	763.7	763.5	763.4	763.4	763.4	763.4	763.4	763.4	763.4	763.4
157.5°	786.1	785.9	785.7	785.8	786.2	786.5	786.9	787.2	786.9	786.5	786.2
160°	799.5	799.4	799.3	799.4	799.9	800.3	800.7	801.2	800.7	800.3	799.9
162.5°	812.2	812.1	812.1	812.3	812.6	812.9	813.2	813.6	813.2	812.9	812.6
165°	829.1	829.0	828.9	829.0	829.2	829.6	829.8	830.2	829.8	829.6	829.2
167.5°	841.5	841.5	841.5	841.7	842.3	842.9	843.5	844.1	843.5	842.9	842.3
170°	848.9	848.9	848.9	849.3	849.9	850.5	851.1	851.7	851.1	850.5	849.9
172.5°	854.4	854.4	854.4	854.6	855.2	855.8	856.4	857.0	856.4	855.8	855.2
175°	860.4	860.4	860.4	860.7	861.3	861.9	862.5	863.2	862.5	861.9	861.3
177.5°	863.8	863.9	864.0	864.3	864.8	865.3	865.7	866.3	865.7	865.3	864.8
180°	865.1	865.1	865.1	865.1	865.1	865.1	865.1	865.1	865.1	865.1	865.1



TEST NUMBER: P333269-935

CATALOG NUMBER: S125DIP-S1090D810U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2
2.5°	1345.4	1340.3	1336.1	1326.8	1321.7	1314.7	1309.2	1315.2	1308.7	1311.5	1307.3
5°	1303.5	1287.2	1275.6	1258.7	1244.2	1230.8	1221.0	1219.2	1214.5	1212.2	1205.2
7.5°	1253.0	1232.7	1212.7	1190.6	1172.0	1153.1	1141.0	1131.0	1124.4	1115.7	1109.7
10°	1223.3	1195.9	1172.8	1146.0	1122.7	1102.4	1086.2	1078.0	1070.5	1059.4	1055.3
12.5°	1186.5	1158.3	1130.0	1101.4	1079.0	1056.4	1042.4	1030.1	1024.8	1012.4	1011.2
15°	1142.5	1100.1	1072.2	1043.1	1012.4	993.8	982.1	968.7	962.9	954.2	947.8
17.5°	1089.9	1052.1	1017.2	987.1	960.7	945.0	930.7	921.4	911.5	905.8	895.3
20°	1051.9	1015.8	980.9	949.0	928.7	910.6	899.0	890.3	879.9	876.9	866.5
22.5°	1019.8	980.0	946.6	919.7	897.5	877.2	864.6	858.7	851.4	842.5	840.4
25°	967.6	926.3	897.9	871.2	851.4	832.8	824.1	816.5	809.5	803.1	800.8
27.5°	922.5	885.6	851.8	827.7	810.5	793.5	785.8	776.6	771.5	766.4	760.1
30°	890.9	853.1	823.5	800.2	781.6	766.5	758.4	752.0	747.3	742.7	739.2
32.5°	858.3	823.4	794.6	771.9	753.3	741.8	734.7	730.1	725.0	719.5	715.1
35°	815.4	777.0	749.1	729.4	714.8	706.1	697.9	693.9	688.0	688.0	683.4
37.5°	766.9	733.7	709.1	691.1	678.0	670.3	661.4	658.7	655.0	652.5	650.8
40°	738.0	707.2	684.0	666.0	652.0	645.7	638.7	634.0	631.7	628.8	627.6
42.5°	708.3	678.9	656.6	640.0	627.8	622.4	615.9	612.6	608.0	604.2	603.5
45°	663.1	634.6	614.2	600.9	590.4	584.0	580.0	573.0	570.7	566.0	565.4
47.5°	620.2	592.9	572.9	562.0	552.8	547.5	541.1	534.2	531.5	529.2	528.9
50°	588.1	563.1	544.5	534.1	525.4	517.8	511.4	506.8	505.0	505.0	506.2
52.5°	555.6	534.3	518.5	505.7	497.5	489.4	483.5	480.7	478.0	480.9	482.9
55°	507.9	486.4	474.8	462.6	454.4	445.1	442.2	441.1	439.4	444.0	446.3
57.5°	457.4	442.4	428.8	416.6	409.3	404.0	400.0	399.3	402.6	404.8	412.3
60°	425.4	407.9	395.7	386.4	377.7	374.3	373.1	372.0	374.3	380.6	390.5
62.5°	390.0	375.9	362.7	355.8	349.4	343.5	343.4	344.1	348.7	356.0	365.8
65°	338.2	326.0	317.3	309.2	303.9	300.4	301.6	303.9	309.2	319.0	330.1
67.5°	285.6	277.2	269.4	262.8	257.8	257.8	259.0	262.4	268.6	280.0	290.1
70°	251.7	242.4	235.9	233.1	228.9	226.6	230.1	235.9	241.2	251.7	260.4
72.5°	217.7	209.8	204.8	202.9	201.0	199.2	200.4	206.6	213.7	224.2	234.3
75°	167.4	164.5	161.0	158.7	156.9	158.1	159.2	165.1	170.8	181.9	193.6
77.5°	122.2	119.2	117.0	116.5	115.5	116.1	119.3	123.6	129.3	137.4	146.2
80°	92.4	91.3	90.1	89.5	89.5	90.1	94.7	97.6	102.9	110.4	117.4
82.5°	67.3	66.6	66.4	66.2	66.7	66.8	69.7	73.4	77.7	83.4	89.5
85°	35.5	34.3	36.0	36.6	35.5	37.2	38.3	40.6	42.4	45.3	48.2
87.5°	12.7	13.9	13.6	14.3	14.5	15.7	15.3	17.3	18.4	19.5	19.1
90°	5.4	6.5	7.7	8.7	9.7	10.8	11.5	12.2	13.0	13.8	14.4
92.5°	19.6	20.7	22.0	23.2	24.5	25.8	26.9	27.8	28.8	29.8	30.5
95°	44.9	45.9	47.4	48.8	50.4	51.8	52.9	53.9	55.0	56.1	56.7
97.5°	73.2	74.3	76.4	78.4	80.5	82.6	83.5	84.6	85.5	86.5	87.0
100°	94.3	95.2	97.2	99.1	101.1	103.0	104.4	105.7	107.0	108.4	109.3
102.5°	119.9	120.6	121.6	122.6	123.6	124.6	126.1	127.5	129.0	130.4	131.4
105°	156.5	157.3	158.3	159.1	160.0	160.9	161.8	162.7	163.6	164.5	165.1
107.5°	196.4	197.1	197.8	198.5	199.1	199.8	200.3	200.7	201.1	201.6	201.8
110°	223.9	224.5	224.9	225.3	225.8	226.2	226.7	227.1	227.6	228.0	228.2



TEST NUMBER: P333269-935

CATALOG NUMBER: S125DIP-S1090D810U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	250.4	250.9	251.4	252.0	252.6	253.1	253.4	253.6	253.7	254.0	254.0
115°	292.6	293.0	293.3	293.6	293.9	294.2	294.0	293.9	293.8	293.6	293.4
117.5°	332.7	333.0	333.3	333.6	333.8	334.1	334.2	334.3	334.4	334.6	334.3
120°	360.5	360.9	361.1	361.3	361.4	361.5	361.5	361.5	361.5	361.5	361.3
122.5°	386.6	386.9	387.3	387.7	388.1	388.5	388.3	388.2	388.1	388.0	387.7
125°	427.1	427.6	427.7	427.9	428.0	428.2	427.9	427.6	427.3	427.0	426.8
127.5°	465.9	466.2	466.4	466.6	466.8	467.0	466.8	466.7	466.5	466.4	466.1
130°	491.1	491.6	491.9	492.2	492.5	492.8	492.7	492.5	492.4	492.2	492.0
132.5°	517.3	517.8	517.8	517.7	517.6	517.6	517.5	517.3	517.1	517.0	516.7
135°	554.3	554.8	555.0	555.2	555.3	555.4	555.4	555.4	555.4	555.4	555.2
137.5°	590.3	590.9	591.2	591.5	591.9	592.2	592.4	592.5	592.7	592.9	592.6
140°	612.9	613.5	614.0	614.5	614.9	615.4	615.7	616.0	616.2	616.6	616.3
142.5°	635.7	636.3	636.8	637.4	637.9	638.5	638.7	638.9	639.0	639.2	638.9
145°	669.6	670.1	670.5	671.0	671.5	671.9	671.9	671.9	671.9	671.9	671.7
147.5°	700.0	700.3	700.8	701.1	701.5	701.8	702.1	702.5	702.9	703.3	702.9
150°	719.1	719.4	720.0	720.6	721.2	721.8	721.8	721.8	721.8	721.8	721.6
152.5°	737.8	738.0	738.2	738.5	738.7	739.0	739.3	739.7	740.0	740.4	740.3
155°	763.4	763.5	763.7	763.9	764.0	764.1	764.7	765.3	765.9	766.5	766.5
157.5°	785.8	785.7	785.9	786.1	786.2	786.4	787.0	787.6	788.2	788.8	788.6
160°	799.4	799.3	799.4	799.5	799.7	799.9	800.5	801.1	801.6	802.2	802.2
162.5°	812.3	812.1	812.1	812.2	812.2	812.3	813.0	813.6	814.4	815.1	815.0
165°	829.0	828.9	829.0	829.1	829.3	829.5	830.1	830.7	831.3	831.8	831.7
167.5°	841.7	841.5	841.5	841.5	841.5	841.5	842.3	843.3	844.1	845.1	845.0
170°	849.3	848.9	848.9	848.9	848.9	848.9	849.9	850.8	851.7	852.6	852.5
172.5°	854.6	854.4	854.4	854.4	854.4	854.4	855.2	856.2	857.0	858.0	858.0
175°	860.7	860.4	860.4	860.4	860.4	860.4	861.3	862.2	863.2	864.0	863.9
177.5°	864.3	864.0	863.9	863.8	863.7	863.5	864.3	865.0	865.6	866.4	866.3
180°	865.1	865.1	865.1	865.1	865.1	865.1	865.1	865.1	865.1	865.1	865.1



TEST NUMBER: P333269-935

CATALOG NUMBER: S125DIP-S1090D810U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2
2.5°	1304.5	1307.8	1305.0	1308.7	1305.0	1307.8	1304.5	1307.3	1311.5	1308.7	1315.2
5°	1202.4	1197.1	1200.6	1198.3	1200.6	1197.1	1202.4	1205.2	1212.2	1214.5	1219.2
7.5°	1108.0	1103.0	1097.3	1094.6	1097.3	1103.0	1108.0	1109.7	1115.7	1124.4	1131.0
10°	1049.0	1042.6	1042.0	1037.9	1042.0	1042.6	1049.0	1055.3	1059.4	1070.5	1078.0
12.5°	1005.7	999.8	993.2	991.4	993.2	999.8	1005.7	1011.2	1012.4	1024.8	1030.1
15°	944.3	939.7	935.6	939.1	935.6	939.7	944.3	947.8	954.2	962.9	968.7
17.5°	893.3	889.5	888.8	884.5	888.8	889.5	893.3	895.3	905.8	911.5	921.4
20°	861.3	858.3	859.5	852.0	859.5	858.3	861.3	866.5	876.9	879.9	890.3
22.5°	835.7	830.0	829.3	827.8	829.3	830.0	835.7	840.4	842.5	851.4	858.7
25°	795.6	792.6	789.8	792.6	789.8	792.6	795.6	800.8	803.1	809.5	816.5
27.5°	760.6	757.1	756.3	756.6	756.3	757.1	760.6	760.1	766.4	771.5	776.6
30°	739.2	733.4	734.0	733.4	734.0	733.4	739.2	739.2	742.7	747.3	752.0
32.5°	715.9	712.0	711.2	710.2	711.2	712.0	715.9	715.1	719.5	725.0	730.1
35°	681.7	681.7	678.7	678.7	678.7	681.7	681.7	683.4	688.0	688.0	693.9
37.5°	649.5	648.8	647.1	647.4	647.1	648.8	649.5	650.8	652.5	655.0	658.7
40°	625.3	624.7	622.9	619.5	622.9	624.7	625.3	627.6	628.8	631.7	634.0
42.5°	602.0	600.1	599.3	598.1	599.3	600.1	602.0	603.5	604.2	608.0	612.6
45°	565.4	565.4	564.3	563.7	564.3	565.4	565.4	565.4	566.0	570.7	573.0
47.5°	529.9	530.9	533.1	532.8	533.1	530.9	529.9	528.9	529.2	531.5	534.2
50°	508.5	509.1	510.8	511.4	510.8	509.1	508.5	506.2	505.0	505.0	506.8
52.5°	484.7	488.2	490.3	490.0	490.3	488.2	484.7	482.9	480.9	478.0	480.7
55°	451.5	455.6	459.7	460.3	459.7	455.6	451.5	446.3	444.0	439.4	441.1
57.5°	418.6	424.3	428.6	430.1	428.6	424.3	418.6	412.3	404.8	402.6	399.3
60°	396.3	403.9	409.1	411.5	409.1	403.9	396.3	390.5	380.6	374.3	372.0
62.5°	375.0	383.4	388.7	389.1	388.7	383.4	375.0	365.8	356.0	348.7	344.1
65°	339.9	348.7	353.4	356.8	353.4	348.7	339.9	330.1	319.0	309.2	303.9
67.5°	302.3	311.0	316.2	318.9	316.2	311.0	302.3	290.1	280.0	268.6	262.4
70°	274.9	283.6	290.6	292.9	290.6	283.6	274.9	260.4	251.7	241.2	235.9
72.5°	247.9	255.7	261.3	264.1	261.3	255.7	247.9	234.3	224.2	213.7	206.6
75°	201.0	211.5	216.8	219.6	216.8	211.5	201.0	193.6	181.9	170.8	165.1
77.5°	155.1	164.5	167.7	169.2	167.7	164.5	155.1	146.2	137.4	129.3	123.6
80°	124.3	130.2	134.2	134.8	134.2	130.2	124.3	117.4	110.4	102.9	97.6
82.5°	95.6	100.4	101.7	103.2	101.7	100.4	95.6	89.5	83.4	77.7	73.4
85°	52.3	54.6	55.2	54.6	55.2	54.6	52.3	48.2	45.3	42.4	40.6
87.5°	20.1	19.8	19.9	20.9	19.9	19.8	20.1	19.1	19.5	18.4	17.3
90°	14.8	15.2	15.7	16.2	15.7	15.2	14.8	14.4	13.8	13.0	12.2
92.5°	30.8	31.1	31.4	31.8	31.4	31.1	30.8	30.5	29.8	28.8	27.8
95°	57.0	57.3	57.6	57.9	57.6	57.3	57.0	56.7	56.1	55.0	53.9
97.5°	87.2	87.4	87.6	87.8	87.6	87.4	87.2	87.0	86.5	85.5	84.6
100°	109.5	109.8	110.1	110.4	110.1	109.8	109.5	109.3	108.4	107.0	105.7
102.5°	131.8	132.2	132.6	133.0	132.6	132.2	131.8	131.4	130.4	129.0	127.5
105°	165.7	166.1	166.5	166.9	166.5	166.1	165.7	165.1	164.5	163.6	162.7
107.5°	201.8	201.7	201.7	201.7	201.7	201.7	201.8	201.8	201.6	201.1	200.7
110°	228.0	227.8	227.7	227.6	227.7	227.8	228.0	228.2	228.0	227.6	227.1



TEST NUMBER: P333269-935

CATALOG NUMBER: S125DIP-S1090D810U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	253.7	253.4	253.1	252.9	253.1	253.4	253.7	254.0	254.0	253.7	253.6
115°	293.3	293.2	293.0	292.9	293.0	293.2	293.3	293.4	293.6	293.8	293.9
117.5°	333.7	333.1	332.5	331.9	332.5	333.1	333.7	334.3	334.6	334.4	334.3
120°	360.7	360.1	359.5	358.9	359.5	360.1	360.7	361.3	361.5	361.5	361.5
122.5°	387.2	386.8	386.2	385.8	386.2	386.8	387.2	387.7	388.0	388.1	388.2
125°	426.6	426.5	426.4	426.2	426.4	426.5	426.6	426.8	427.0	427.3	427.6
127.5°	465.9	465.5	465.3	464.9	465.3	465.5	465.9	466.1	466.4	466.5	466.7
130°	491.7	491.4	491.1	490.8	491.1	491.4	491.7	492.0	492.2	492.4	492.5
132.5°	516.3	515.9	515.5	515.1	515.5	515.9	516.3	516.7	517.0	517.1	517.3
135°	554.6	554.0	553.4	552.8	553.4	554.0	554.6	555.2	555.4	555.4	555.4
137.5°	591.9	591.2	590.4	589.6	590.4	591.2	591.9	592.6	592.9	592.7	592.5
140°	615.6	614.8	614.1	613.4	614.1	614.8	615.6	616.3	616.6	616.2	616.0
142.5°	638.2	637.5	636.7	635.9	636.7	637.5	638.2	638.9	639.2	639.0	638.9
145°	671.2	670.8	670.4	669.9	670.4	670.8	671.2	671.7	671.9	671.9	671.9
147.5°	701.9	700.9	699.9	698.9	699.9	700.9	701.9	702.9	703.3	702.9	702.5
150°	721.3	721.0	720.7	720.4	720.7	721.0	721.3	721.6	721.8	721.8	721.8
152.5°	739.8	739.3	738.7	738.1	738.7	739.3	739.8	740.3	740.4	740.0	739.7
155°	765.7	765.0	764.2	763.4	764.2	765.0	765.7	766.5	766.5	765.9	765.3
157.5°	787.6	786.6	785.6	784.6	785.6	786.6	787.6	788.6	788.8	788.2	787.6
160°	801.4	800.6	799.9	799.2	799.9	800.6	801.4	802.2	802.2	801.6	801.1
162.5°	814.2	813.3	812.4	811.6	812.4	813.3	814.2	815.0	815.1	814.4	813.6
165°	830.8	829.9	829.0	828.1	829.0	829.9	830.8	831.7	831.8	831.3	830.7
167.5°	844.1	843.2	842.2	841.3	842.2	843.2	844.1	845.0	845.1	844.1	843.3
170°	851.4	850.4	849.4	848.3	849.4	850.4	851.4	852.5	852.6	851.7	850.8
172.5°	857.0	856.1	855.1	854.2	855.1	856.1	857.0	858.0	858.0	857.0	856.2
175°	862.9	861.9	860.8	859.8	860.8	861.9	862.9	863.9	864.0	863.2	862.2
177.5°	865.5	864.7	863.8	863.0	863.8	864.7	865.5	866.3	866.4	865.6	865.0
180°	865.1	865.1	865.1	865.1	865.1	865.1	865.1	865.1	865.1	865.1	865.1



TEST NUMBER: P333269-935

CATALOG NUMBER: S125DIP-S1090D810U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2
2.5°	1309.2	1314.7	1321.7	1326.8	1336.1	1340.3	1345.4	1349.6	1357.0	1364.0	1372.4
5°	1221.0	1230.8	1244.2	1258.7	1275.6	1287.2	1303.5	1313.4	1333.1	1351.2	1368.6
7.5°	1141.0	1153.1	1172.0	1190.6	1212.7	1232.7	1253.0	1275.6	1300.8	1330.6	1355.2
10°	1086.2	1102.4	1122.7	1146.0	1172.8	1195.9	1223.3	1247.7	1278.5	1313.4	1345.9
12.5°	1042.4	1056.4	1079.0	1101.4	1130.0	1158.3	1186.5	1218.8	1254.8	1293.4	1334.3
15°	982.1	993.8	1012.4	1043.1	1072.2	1100.1	1142.5	1172.8	1218.1	1261.0	1310.4
17.5°	930.7	945.0	960.7	987.1	1017.2	1052.1	1089.9	1127.8	1171.6	1226.1	1281.8
20°	899.0	910.6	928.7	949.0	980.9	1015.8	1051.9	1090.2	1143.7	1200.1	1259.9
22.5°	864.6	877.2	897.5	919.7	946.6	980.0	1019.8	1061.9	1117.7	1173.1	1238.0
25°	824.1	832.8	851.4	871.2	897.9	926.3	967.6	1014.1	1069.3	1132.6	1198.9
27.5°	785.8	793.5	810.5	827.7	851.8	885.6	922.5	969.5	1021.5	1085.6	1159.2
30°	758.4	766.5	781.6	800.2	823.5	853.1	890.9	935.0	990.8	1053.6	1130.3
32.5°	734.7	741.8	753.3	771.9	794.6	823.4	858.3	903.4	959.2	1022.9	1098.2
35°	697.9	706.1	714.8	729.4	749.1	777.0	815.4	857.7	911.2	972.8	1042.0
37.5°	661.4	670.3	678.0	691.1	709.1	733.7	766.9	811.1	859.4	918.8	985.2
40°	638.7	645.7	652.0	666.0	684.0	707.2	738.0	777.6	828.7	883.9	939.1
42.5°	615.9	622.4	627.8	640.0	656.6	678.9	708.3	746.8	794.3	845.8	894.5
45°	580.0	584.0	590.4	600.9	614.2	634.6	663.1	697.3	737.4	786.3	822.9
47.5°	541.1	547.5	552.8	562.0	572.9	592.9	620.2	649.4	685.7	722.0	747.8
50°	511.4	517.8	525.4	534.1	544.5	563.1	588.1	617.8	648.5	676.4	698.5
52.5°	483.5	489.4	497.5	505.7	518.5	534.3	555.6	581.9	612.3	632.2	650.7
55°	442.2	445.1	454.4	462.6	474.8	486.4	507.9	531.2	549.7	564.9	580.0
57.5°	400.0	404.0	409.3	416.6	428.8	442.4	457.4	478.0	489.0	496.7	508.5
60°	373.1	374.3	377.7	386.4	395.7	407.9	425.4	439.9	448.1	454.4	464.3
62.5°	343.4	343.5	349.4	355.8	362.7	375.9	390.0	401.8	408.5	411.6	421.1
65°	301.6	300.4	303.9	309.2	317.3	326.0	338.2	348.7	348.1	351.5	357.4
67.5°	259.0	257.8	257.8	262.8	269.4	277.2	285.6	291.6	291.7	296.4	299.3
70°	230.1	226.6	228.9	233.1	235.9	242.4	251.7	254.0	254.5	256.8	259.8
72.5°	200.4	199.2	201.0	202.9	204.8	209.8	217.7	219.1	219.2	220.6	225.3
75°	159.2	158.1	156.9	158.7	161.0	164.5	167.4	169.7	169.1	169.7	173.1
77.5°	119.3	116.1	115.5	116.5	117.0	119.2	122.2	121.9	122.5	122.3	126.3
80°	94.7	90.1	89.5	89.5	90.1	91.3	92.4	93.6	91.8	93.6	94.7
82.5°	69.7	66.8	66.7	66.2	66.4	66.6	67.3	68.0	67.7	68.4	69.1
85°	38.3	37.2	35.5	36.6	36.0	34.3	35.5	33.7	33.1	33.7	34.3
87.5°	15.3	15.7	14.5	14.3	13.6	13.9	12.7	12.0	11.3	11.5	12.7
90°	11.5	10.8	9.7	8.7	7.7	6.5	5.4	4.3	3.1	1.9	0.7
92.5°	26.9	25.8	24.5	23.2	22.0	20.7	19.6	18.8	18.0	17.1	16.3
95°	52.9	51.8	50.4	48.8	47.4	45.9	44.9	44.7	44.3	44.1	43.7
97.5°	83.5	82.6	80.5	78.4	76.4	74.3	73.2	73.1	72.9	72.8	72.8
100°	104.4	103.0	101.1	99.1	97.2	95.2	94.3	94.3	94.3	94.3	94.3
102.5°	126.1	124.6	123.6	122.6	121.6	120.6	119.9	119.2	118.6	118.0	117.4
105°	161.8	160.9	160.0	159.1	158.3	157.3	156.5	155.8	155.0	154.3	153.5
107.5°	200.3	199.8	199.1	198.5	197.8	197.1	196.4	195.6	194.8	194.1	193.4
110°	226.7	226.2	225.8	225.3	224.9	224.5	223.9	223.1	222.3	221.6	220.8



TEST NUMBER: P333269-935

CATALOG NUMBER: S125DIP-S1090D810U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	253.4	253.1	252.6	252.0	251.4	250.9	250.4	250.0	249.6	249.3	248.8
115°	294.0	294.2	293.9	293.6	293.3	293.0	292.6	292.0	291.4	290.8	290.2
117.5°	334.2	334.1	333.8	333.6	333.3	333.0	332.7	332.4	332.2	331.9	331.7
120°	361.5	361.5	361.4	361.3	361.1	360.9	360.5	359.7	359.0	358.3	357.5
122.5°	388.3	388.5	388.1	387.7	387.3	386.9	386.6	386.3	386.1	385.8	385.5
125°	427.9	428.2	428.0	427.9	427.7	427.6	427.1	426.2	425.2	424.4	423.4
127.5°	466.8	467.0	466.8	466.6	466.4	466.2	465.9	465.4	464.9	464.4	463.9
130°	492.7	492.8	492.5	492.2	491.9	491.6	491.1	490.3	489.7	488.9	488.1
132.5°	517.5	517.6	517.6	517.7	517.8	517.8	517.3	516.0	514.8	513.6	512.4
135°	555.4	555.4	555.3	555.2	555.0	554.8	554.3	553.5	552.5	551.6	550.7
137.5°	592.4	592.2	591.9	591.5	591.2	590.9	590.3	589.4	588.6	587.7	586.9
140°	615.7	615.4	614.9	614.5	614.0	613.5	612.9	612.3	611.5	610.7	610.0
142.5°	638.7	638.5	637.9	637.4	636.8	636.3	635.7	635.0	634.4	633.8	633.2
145°	671.9	671.9	671.5	671.0	670.5	670.1	669.6	669.0	668.4	667.8	667.2
147.5°	702.1	701.8	701.5	701.1	700.8	700.3	700.0	699.7	699.4	699.0	698.7
150°	721.8	721.8	721.2	720.6	720.0	719.4	719.1	719.3	719.5	719.5	719.7
152.5°	739.3	739.0	738.7	738.5	738.2	738.0	737.8	737.6	737.4	737.2	736.9
155°	764.7	764.1	764.0	763.9	763.7	763.5	763.4	763.4	763.4	763.4	763.4
157.5°	787.0	786.4	786.2	786.1	785.9	785.7	785.8	786.2	786.5	786.9	787.2
160°	800.5	799.9	799.7	799.5	799.4	799.3	799.4	799.9	800.3	800.7	801.2
162.5°	813.0	812.3	812.2	812.2	812.1	812.1	812.3	812.6	812.9	813.2	813.6
165°	830.1	829.5	829.3	829.1	829.0	828.9	829.0	829.2	829.6	829.8	830.2
167.5°	842.3	841.5	841.5	841.5	841.5	841.5	841.7	842.3	842.9	843.5	844.1
170°	849.9	848.9	848.9	848.9	848.9	848.9	849.3	849.9	850.5	851.1	851.7
172.5°	855.2	854.4	854.4	854.4	854.4	854.4	854.6	855.2	855.8	856.4	857.0
175°	861.3	860.4	860.4	860.4	860.4	860.4	860.7	861.3	861.9	862.5	863.2
177.5°	864.3	863.5	863.7	863.8	863.9	864.0	864.3	864.8	865.3	865.7	866.3
180°	865.1	865.1	865.1	865.1	865.1	865.1	865.1	865.1	865.1	865.1	865.1



TEST NUMBER: P333269-935

CATALOG NUMBER: S125DIP-S1090D810U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2
2.5°	1376.6	1383.1	1387.2	1395.2	1401.7	1405.4	1408.7	1411.4	1414.7	1417.5	1425.4
5°	1385.4	1400.5	1413.3	1433.0	1451.1	1465.1	1480.1	1493.5	1504.5	1520.3	1532.4
7.5°	1381.6	1408.4	1436.6	1467.1	1498.4	1527.4	1554.2	1579.2	1601.8	1629.3	1653.3
10°	1377.9	1414.5	1450.5	1491.8	1534.2	1570.2	1604.0	1638.2	1663.2	1698.1	1727.7
12.5°	1375.1	1418.2	1461.6	1511.3	1557.9	1608.8	1653.6	1678.7	1716.7	1744.6	1779.8
15°	1363.3	1420.3	1480.1	1535.9	1602.1	1649.2	1688.8	1737.6	1773.1	1808.4	1846.8
17.5°	1342.3	1406.8	1473.8	1546.9	1610.4	1661.0	1711.9	1758.9	1801.3	1848.8	1896.6
20°	1332.6	1397.1	1473.8	1548.7	1610.9	1663.8	1716.1	1767.8	1814.3	1875.3	1930.5
22.5°	1312.1	1390.1	1460.8	1533.9	1597.8	1655.4	1714.7	1773.4	1835.2	1904.1	1973.3
25°	1275.6	1354.6	1429.6	1501.7	1566.2	1638.2	1701.6	1780.0	1859.1	1950.3	2036.3
27.5°	1237.7	1313.4	1382.1	1451.6	1526.9	1608.4	1690.7	1779.7	1883.1	1998.3	2119.6
30°	1207.0	1278.5	1345.3	1416.8	1495.2	1587.1	1677.1	1782.9	1902.6	2032.2	2176.3
32.5°	1171.2	1237.1	1302.1	1377.8	1463.2	1560.1	1665.1	1781.1	1924.9	2072.2	2220.5
35°	1110.0	1165.2	1232.0	1312.8	1409.3	1520.3	1641.7	1778.8	1943.9	2113.0	2237.9
37.5°	1037.3	1088.7	1159.2	1247.7	1348.8	1467.9	1612.1	1774.8	1950.1	2084.9	2125.2
40°	988.5	1036.1	1109.4	1201.2	1304.7	1430.7	1588.8	1760.8	1930.5	2016.5	1983.4
42.5°	936.4	986.4	1057.7	1148.7	1260.0	1397.3	1559.5	1731.6	1873.8	1906.3	1791.8
45°	854.3	905.9	976.3	1068.2	1187.8	1336.6	1505.7	1662.1	1744.0	1685.3	1508.0
47.5°	777.9	826.4	891.6	986.3	1109.8	1263.7	1426.6	1551.3	1557.8	1417.7	1228.4
50°	725.8	770.6	836.3	931.0	1053.6	1209.4	1356.3	1454.6	1410.4	1251.7	1069.9
52.5°	674.7	718.5	783.3	877.0	998.2	1141.0	1277.8	1346.7	1263.5	1100.7	945.3
55°	600.9	639.2	702.6	789.2	904.2	1036.7	1153.0	1176.8	1068.7	908.3	782.2
57.5°	528.8	564.6	622.2	702.0	807.2	924.5	1015.5	1010.4	896.1	758.5	658.4
60°	480.0	514.9	566.0	643.9	739.8	840.9	918.8	900.2	786.9	668.3	584.0
62.5°	436.4	467.4	515.8	583.9	671.4	765.1	829.1	801.6	690.6	586.9	520.4
65°	372.0	398.0	439.4	497.5	570.1	647.4	696.8	661.3	566.6	485.9	432.4
67.5°	310.5	331.4	366.0	412.3	474.3	536.4	566.5	530.8	455.0	396.1	356.5
70°	271.4	290.0	316.7	358.0	412.0	464.3	487.0	455.0	389.9	339.4	310.9
72.5°	232.3	247.7	271.1	308.2	351.5	396.9	416.8	386.2	332.8	290.1	263.5
75°	179.6	190.0	206.3	231.9	266.1	302.2	313.2	286.5	252.2	220.2	202.9
77.5°	128.5	137.4	149.7	165.8	190.1	213.0	222.7	207.2	180.7	160.5	146.2
80°	98.8	103.4	113.9	127.3	146.5	161.0	167.4	157.5	138.9	123.8	112.7
82.5°	70.4	75.1	81.4	92.4	104.6	114.5	121.3	114.7	101.3	89.4	83.0
85°	34.3	37.2	40.6	45.3	54.6	60.4	59.8	55.8	50.5	45.9	42.4
87.5°	12.5	13.2	14.8	17.4	18.9	21.1	22.2	21.4	19.8	18.6	17.3
90°	1.9	3.1	4.3	5.4	6.5	7.7	8.7	9.7	10.8	11.5	12.2
92.5°	17.1	18.0	18.8	19.6	20.7	22.0	23.2	24.5	25.8	26.9	27.8
95°	44.1	44.3	44.7	44.9	45.9	47.4	48.8	50.4	51.8	52.9	53.9
97.5°	72.8	72.9	73.1	73.2	74.3	76.4	78.4	80.5	82.6	83.5	84.6
100°	94.3	94.3	94.3	94.3	95.2	97.2	99.1	101.1	103.0	104.4	105.7
102.5°	118.0	118.6	119.2	119.9	120.6	121.6	122.6	123.6	124.6	126.1	127.5
105°	154.3	155.0	155.8	156.5	157.3	158.3	159.1	160.0	160.9	161.8	162.7
107.5°	194.1	194.8	195.6	196.4	197.1	197.8	198.5	199.1	199.8	200.3	200.7
110°	221.6	222.3	223.1	223.9	224.5	224.9	225.3	225.8	226.2	226.7	227.1





TEST NUMBER: P333269-935

CATALOG NUMBER: S125DIP-S1090D810U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	249.3	249.6	250.0	250.4	250.9	251.4	252.0	252.6	253.1	253.4	253.6
115°	290.8	291.4	292.0	292.6	293.0	293.3	293.6	293.9	294.2	294.0	293.9
117.5°	331.9	332.2	332.4	332.7	333.0	333.3	333.6	333.8	334.1	334.2	334.3
120°	358.3	359.0	359.7	360.5	360.9	361.1	361.3	361.4	361.5	361.5	361.5
122.5°	385.8	386.1	386.3	386.6	386.9	387.3	387.7	388.1	388.5	388.3	388.2
125°	424.4	425.2	426.2	427.1	427.6	427.7	427.9	428.0	428.2	427.9	427.6
127.5°	464.4	464.9	465.4	465.9	466.2	466.4	466.6	466.8	467.0	466.8	466.7
130°	488.9	489.7	490.3	491.1	491.6	491.9	492.2	492.5	492.8	492.7	492.5
132.5°	513.6	514.8	516.0	517.3	517.8	517.8	517.7	517.6	517.6	517.5	517.3
135°	551.6	552.5	553.5	554.3	554.8	555.0	555.2	555.3	555.4	555.4	555.4
137.5°	587.7	588.6	589.4	590.3	590.9	591.2	591.5	591.9	592.2	592.4	592.5
140°	610.7	611.5	612.3	612.9	613.5	614.0	614.5	614.9	615.4	615.7	616.0
142.5°	633.8	634.4	635.0	635.7	636.3	636.8	637.4	637.9	638.5	638.7	638.9
145°	667.8	668.4	669.0	669.6	670.1	670.5	671.0	671.5	671.9	671.9	671.9
147.5°	699.0	699.4	699.7	700.0	700.3	700.8	701.1	701.5	701.8	702.1	702.5
150°	719.5	719.5	719.3	719.1	719.4	720.0	720.6	721.2	721.8	721.8	721.8
152.5°	737.2	737.4	737.6	737.8	738.0	738.2	738.5	738.7	739.0	739.3	739.7
155°	763.4	763.4	763.4	763.4	763.5	763.7	763.9	764.0	764.1	764.7	765.3
157.5°	786.9	786.5	786.2	785.8	785.7	785.9	786.1	786.2	786.4	787.0	787.6
160°	800.7	800.3	799.9	799.4	799.3	799.4	799.5	799.7	799.9	800.5	801.1
162.5°	813.2	812.9	812.6	812.3	812.1	812.1	812.2	812.2	812.3	813.0	813.6
165°	829.8	829.6	829.2	829.0	828.9	829.0	829.1	829.3	829.5	830.1	830.7
167.5°	843.5	842.9	842.3	841.7	841.5	841.5	841.5	841.5	841.5	842.3	843.3
170°	851.1	850.5	849.9	849.3	848.9	848.9	848.9	848.9	848.9	849.9	850.8
172.5°	856.4	855.8	855.2	854.6	854.4	854.4	854.4	854.4	854.4	855.2	856.2
175°	862.5	861.9	861.3	860.7	860.4	860.4	860.4	860.4	860.4	861.3	862.2
177.5°	865.7	865.3	864.8	864.3	864.0	863.9	863.8	863.7	863.5	864.3	865.0
180°	865.1	865.1	865.1	865.1	865.1	865.1	865.1	865.1	865.1	865.1	865.1



TEST NUMBER: P333269-935

CATALOG NUMBER: S125DIP-S1090D810U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2
2.5°	1431.9	1435.6	1443.6	1440.7	1444.5	1446.3	1448.2
5°	1547.6	1566.2	1574.3	1573.1	1585.4	1582.4	1579.5
7.5°	1678.2	1697.7	1708.7	1722.3	1730.2	1730.7	1737.6
10°	1752.1	1777.7	1788.1	1802.7	1812.0	1817.2	1816.6
12.5°	1808.9	1828.9	1852.3	1859.4	1872.0	1878.5	1876.1
15°	1877.1	1909.0	1933.5	1945.6	1961.4	1966.0	1972.4
17.5°	1937.9	1980.8	2009.3	2047.2	2061.5	2070.2	2065.1
20°	1984.0	2040.4	2068.8	2114.2	2139.2	2152.5	2147.9
22.5°	2038.4	2099.4	2152.1	2191.3	2229.3	2247.4	2251.1
25°	2131.6	2215.3	2292.6	2344.3	2391.3	2402.4	2426.8
27.5°	2235.8	2334.4	2417.1	2471.4	2504.2	2516.5	2524.2
30°	2301.3	2399.5	2461.7	2496.6	2507.0	2505.9	2504.6
32.5°	2333.4	2394.9	2406.8	2397.0	2373.1	2352.9	2331.8
35°	2287.9	2242.0	2173.4	2085.1	2020.0	1954.4	1947.9
37.5°	2057.7	1910.9	1796.7	1669.2	1595.7	1550.2	1518.9
40°	1841.0	1674.2	1535.9	1428.4	1353.5	1323.8	1294.8
42.5°	1605.8	1446.5	1324.0	1234.1	1177.8	1144.9	1121.8
45°	1304.7	1164.0	1068.2	1003.1	958.3	932.7	918.2
47.5°	1069.0	965.0	883.6	836.6	805.7	785.8	785.9
50°	942.6	843.3	789.2	752.0	725.2	709.6	712.5
52.5°	830.5	756.3	710.2	679.0	659.3	649.6	649.3
55°	694.5	641.0	610.8	588.1	574.7	563.7	566.0
57.5°	594.0	549.0	528.7	509.9	500.6	496.2	489.7
60°	531.8	496.9	479.4	464.3	455.0	451.5	445.1
62.5°	476.4	449.0	432.0	419.7	411.3	410.2	405.2
65°	400.4	379.4	364.4	358.5	349.8	347.5	347.5
67.5°	330.1	315.1	303.3	298.0	294.2	294.7	292.0
70°	285.9	273.7	266.1	260.4	257.4	258.0	255.7
72.5°	250.1	236.5	229.9	226.4	222.6	224.1	223.2
75°	189.4	182.4	179.0	175.5	173.1	172.0	170.8
77.5°	139.1	132.9	130.3	128.3	128.6	125.9	128.1
80°	107.5	102.3	100.6	97.6	97.0	97.0	96.4
82.5°	78.7	75.8	74.5	72.1	71.0	72.0	70.4
85°	40.6	38.3	37.8	37.8	36.6	35.5	38.3
87.5°	17.5	15.8	15.9	15.5	15.6	15.2	14.4
90°	13.0	13.8	14.4	14.8	15.2	15.7	16.2
92.5°	28.8	29.8	30.5	30.8	31.1	31.4	31.8
95°	55.0	56.1	56.7	57.0	57.3	57.6	57.9
97.5°	85.5	86.5	87.0	87.2	87.4	87.6	87.8
100°	107.0	108.4	109.3	109.5	109.8	110.1	110.4
102.5°	129.0	130.4	131.4	131.8	132.2	132.6	133.0
105°	163.6	164.5	165.1	165.7	166.1	166.5	166.9
107.5°	201.1	201.6	201.8	201.8	201.7	201.7	201.7
110°	227.6	228.0	228.2	228.0	227.8	227.7	227.6



TEST NUMBER: P333269-935

CATALOG NUMBER: S125DIP-S1090D810U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	253.7	254.0	254.0	253.7	253.4	253.1	252.9
115°	293.8	293.6	293.4	293.3	293.2	293.0	292.9
117.5°	334.4	334.6	334.3	333.7	333.1	332.5	331.9
120°	361.5	361.5	361.3	360.7	360.1	359.5	358.9
122.5°	388.1	388.0	387.7	387.2	386.8	386.2	385.8
125°	427.3	427.0	426.8	426.6	426.5	426.4	426.2
127.5°	466.5	466.4	466.1	465.9	465.5	465.3	464.9
130°	492.4	492.2	492.0	491.7	491.4	491.1	490.8
132.5°	517.1	517.0	516.7	516.3	515.9	515.5	515.1
135°	555.4	555.4	555.2	554.6	554.0	553.4	552.8
137.5°	592.7	592.9	592.6	591.9	591.2	590.4	589.6
140°	616.2	616.6	616.3	615.6	614.8	614.1	613.4
142.5°	639.0	639.2	638.9	638.2	637.5	636.7	635.9
145°	671.9	671.9	671.7	671.2	670.8	670.4	669.9
147.5°	702.9	703.3	702.9	701.9	700.9	699.9	698.9
150°	721.8	721.8	721.6	721.3	721.0	720.7	720.4
152.5°	740.0	740.4	740.3	739.8	739.3	738.7	738.1
155°	765.9	766.5	766.5	765.7	765.0	764.2	763.4
157.5°	788.2	788.8	788.6	787.6	786.6	785.6	784.6
160°	801.6	802.2	802.2	801.4	800.6	799.9	799.2
162.5°	814.4	815.1	815.0	814.2	813.3	812.4	811.6
165°	831.3	831.8	831.7	830.8	829.9	829.0	828.1
167.5°	844.1	845.1	845.0	844.1	843.2	842.2	841.3
170°	851.7	852.6	852.5	851.4	850.4	849.4	848.3
172.5°	857.0	858.0	858.0	857.0	856.1	855.1	854.2
175°	863.2	864.0	863.9	862.9	861.9	860.8	859.8
177.5°	865.6	866.4	866.3	865.5	864.7	863.8	863.0
180°	865.1	865.1	865.1	865.1	865.1	865.1	865.1

(END OF REPORT)