

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333531-927

Luminaire Tested: **S125RDIP-S610D590U927-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333531-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S610D590U927-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3564.7 lumens
Efficiency: N/A
Efficacy: 108.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333531-927

CATALOG NUMBER: S125RDIP-S610D590U927-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333531-927

CATALOG NUMBER: S125RDIP-S610D590U927-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59
1	99	94	91	87	91	88	84	81	75	72	70	63	61	60	52	51	50
2	90	83	77	72	83	77	72	67	66	62	59	56	53	50	46	44	43
3	82	73	66	60	76	68	61	56	58	53	49	49	46	43	41	39	36
4	75	65	57	51	70	60	53	48	52	47	42	44	40	37	37	34	32
5	69	58	50	44	64	54	47	41	47	41	37	40	35	32	33	30	28
6	64	52	44	38	59	48	41	36	42	36	32	36	32	28	30	27	24
7	59	47	39	33	55	44	37	32	38	32	28	33	28	25	28	24	22
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	26	22	20
9	51	39	31	26	47	37	30	25	32	26	23	28	23	20	24	20	18
10	48	36	29	24	44	34	27	23	29	24	20	26	21	18	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5147	5147	5147
5°	5159	5100	5131
10°	5119	5052	5052
15°	5059	4950	4910
20°	4981	4807	4748
25°	4890	4666	4563
30°	4776	4502	4359
35°	4660	4332	4128
40°	4552	4156	3903
45°	4420	3958	3656
50°	4287	3744	3399
55°	4135	3538	3125
60°	3981	3289	2830
65°	3799	2998	2492
70°	3592	2638	2149
75°	3306	2221	1787
80°	2912	1748	1499
85°	2453	1430	1341



TEST NUMBER: P333531-927

CATALOG NUMBER: S125RDIP-S610D590U927-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.9	2.1
10°-20°	209.4	5.9
20°-30°	303.7	8.5
30°-40°	346.1	9.7
40°-50°	337.4	9.5
50°-60°	284.0	8.0
60°-70°	199.1	5.6
70°-80°	102.3	2.9
80°-90°	27.1	0.8
90°-100°	162.5	4.6
100°-110°	349.2	9.8
110°-120°	327.8	9.2
120°-130°	265.6	7.5
130°-140°	213.2	6.0
140°-150°	160.9	4.5
150°-160°	113.2	3.2
160°-170°	66.7	1.9
170°-180°	21.7	0.6
0°-30°	588.0	16.5
0°-40°	934.1	26.2
0°-60°	1555.4	43.6
0°-90°	1883.9	52.8
90°-120°	839.5	23.5
90°-150°	1479.1	41.5
90°-180°	1681.0	47.2
0°-180°	3564.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	797	797	797	797	797	
5°	796	793	787	792	792	75
15°	757	752	740	739	734	213
25°	686	676	655	647	640	316
35°	591	576	550	533	524	370
45°	484	466	433	410	400	373
55°	367	347	314	288	278	328
65°	249	228	196	173	163	246
75°	132	114	89	76	72	140
85°	33	23	19	19	18	37
90°	0	4	7	9	10	2
95°	15	44	400	182	106	16
105°	51	71	328	645	599	54
115°	91	110	263	567	667	90
125°	126	148	252	451	526	112
135°	148	178	250	378	436	115
145°	173	198	251	313	344	108
155°	197	212	245	277	289	91
165°	215	221	235	249	253	61
175°	224	224	226	228	227	21
180°	224	224	224	224	224	



TEST NUMBER: P333531-927

CATALOG NUMBER: S125RDIP-S610D590U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	796.9	796.9	796.9	796.9	796.9	796.9	796.9	796.9	796.9	796.9	796.9
2.5°	798.4	798.0	797.7	797.4	797.1	796.4	795.3	794.2	793.1	792.1	793.1
5°	795.7	795.2	794.6	794.1	793.5	792.6	791.1	789.6	788.1	786.6	788.0
7.5°	787.9	787.3	786.9	786.3	785.8	784.7	782.9	781.2	779.4	777.6	778.6
10°	780.6	780.2	779.8	779.4	779.0	777.9	776.0	774.2	772.3	770.4	770.8
12.5°	772.5	772.0	771.4	771.0	770.4	768.9	766.4	763.9	761.4	758.8	759.1
15°	756.6	755.7	754.9	754.2	753.4	751.5	748.8	745.9	743.1	740.3	740.2
17.5°	738.6	737.4	736.2	735.0	733.7	731.3	727.8	724.3	720.7	717.2	716.5
20°	724.7	723.3	722.0	720.6	719.3	716.5	712.3	708.0	703.7	699.4	698.7
22.5°	709.2	707.9	706.6	705.3	703.9	701.0	696.5	692.1	687.5	683.0	681.8
25°	686.2	684.1	682.1	680.2	678.1	674.6	669.7	664.7	659.8	654.8	653.2
27.5°	659.7	657.3	654.8	652.4	649.9	646.1	640.8	635.5	630.2	624.9	622.4
30°	640.4	637.9	635.3	632.8	630.3	626.1	620.5	615.0	609.3	603.7	600.6
32.5°	621.6	618.7	615.7	612.8	609.7	605.4	599.7	594.0	588.2	582.5	579.1
35°	591.0	587.9	584.6	581.5	578.2	573.6	567.6	561.6	555.6	549.5	545.7
37.5°	561.1	557.1	553.3	549.4	545.5	540.4	534.2	528.0	521.8	515.6	511.0
40°	539.9	535.9	531.9	527.8	523.9	518.6	512.2	505.8	499.4	493.0	487.9
42.5°	517.8	513.7	509.5	505.4	501.3	495.9	489.3	482.6	476.0	469.4	464.5
45°	483.9	480.1	476.2	472.3	468.4	462.8	455.4	448.1	440.7	433.3	428.0
47.5°	448.9	444.8	440.7	436.7	432.5	426.7	419.4	411.9	404.6	397.1	391.7
50°	426.7	422.3	417.9	413.5	409.1	403.1	395.5	387.9	380.2	372.6	366.9
52.5°	402.7	398.2	393.6	389.1	384.6	378.7	371.5	364.3	357.1	349.9	343.9
55°	367.2	362.9	358.6	354.3	350.1	344.1	336.7	329.2	321.7	314.2	308.2
57.5°	331.3	326.7	322.1	317.6	313.0	307.0	299.8	292.6	285.4	278.2	272.3
60°	308.2	303.5	298.8	294.1	289.5	283.5	276.2	269.0	261.8	254.6	248.7
62.5°	283.6	279.2	274.6	270.2	265.8	259.8	252.5	245.2	237.9	230.5	225.1
65°	248.6	244.1	239.5	235.0	230.4	224.6	217.5	210.4	203.3	196.2	190.8
67.5°	213.8	209.2	204.7	200.2	195.6	190.0	183.2	176.3	169.5	162.7	157.9
70°	190.2	185.7	181.1	176.6	172.0	166.4	159.7	153.0	146.3	139.7	135.5
72.5°	167.1	162.6	158.2	153.8	149.3	143.9	137.7	131.4	125.2	118.9	115.1
75°	132.5	128.4	124.4	120.4	116.4	111.5	105.9	100.3	94.7	89.0	86.1
77.5°	98.0	94.7	91.6	88.3	85.2	81.3	76.8	72.3	67.8	63.3	61.2
80°	78.3	75.0	71.9	68.6	65.4	61.9	58.1	54.4	50.7	47.0	45.7
82.5°	59.0	56.1	53.2	50.3	47.5	44.7	42.1	39.5	37.0	34.5	33.9
85°	33.1	30.7	28.3	25.9	23.4	21.9	21.2	20.6	20.0	19.3	19.1
87.5°	11.2	10.5	9.9	9.3	8.8	8.6	8.6	8.6	8.6	8.6	8.8
90°	0.5	0.9	1.8	2.7	3.6	4.5	5.0	5.9	6.3	7.2	7.7
92.5°	5.5	6.7	10.5	16.1	23.8	37.1	61.7	103.1	148.1	145.7	118.0
95°	14.9	15.4	19.0	23.9	33.9	54.3	102.6	202.0	326.7	400.4	391.8
97.5°	24.8	25.3	27.8	32.8	41.7	56.4	88.4	161.2	291.8	427.5	495.7
100°	31.6	32.6	34.4	39.3	47.9	61.5	87.7	146.4	260.3	408.1	521.0
102.5°	39.2	39.8	41.2	46.6	54.4	67.6	90.9	140.3	236.4	373.7	505.8
105°	51.1	51.1	53.3	57.8	65.0	77.7	97.6	137.8	213.3	327.6	457.3
107.5°	62.7	63.5	65.7	69.4	76.9	88.3	107.6	142.0	203.5	295.9	407.8
110°	71.0	71.9	73.7	77.7	84.5	96.3	114.8	145.9	200.7	281.1	379.6



TEST NUMBER: P333531-927

CATALOG NUMBER: S125RDIP-S610D590U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	79.3	80.2	81.6	85.7	92.4	103.9	121.7	151.0	200.7	272.4	358.6
115°	91.3	92.2	93.6	97.6	104.4	115.7	132.4	158.6	202.0	263.0	335.7
117.5°	102.1	103.5	105.0	109.0	116.7	127.6	143.5	167.3	204.9	258.4	322.1
120°	109.3	110.7	112.5	116.6	124.3	135.5	151.4	173.1	207.9	256.2	314.5
122.5°	116.9	118.0	119.4	123.4	131.9	143.1	159.0	179.6	210.4	254.4	308.0
125°	126.5	127.5	129.7	133.7	142.4	154.1	169.0	188.5	214.7	252.2	299.1
127.5°	134.0	135.4	138.3	143.5	152.6	164.3	178.6	196.5	219.4	251.0	291.0
130°	138.7	140.1	143.7	149.6	159.1	170.8	184.8	202.0	222.4	250.3	285.6
132.5°	142.4	144.1	148.4	155.0	164.9	176.6	190.6	206.7	225.6	250.3	281.2
135°	148.2	150.0	155.4	162.7	172.1	184.3	198.4	213.3	230.0	250.3	276.1
137.5°	155.7	157.0	162.1	169.3	178.6	191.2	203.9	218.2	234.1	250.9	271.5
140°	159.9	161.3	166.8	174.0	182.6	194.8	207.9	221.4	235.9	251.3	269.3
142.5°	165.0	166.0	171.1	178.3	186.6	198.0	210.4	223.2	236.9	251.6	267.5
145°	172.6	173.5	178.0	184.3	192.5	202.9	214.7	225.9	238.1	251.3	264.8
147.5°	180.5	181.1	185.0	190.8	197.9	207.1	217.4	227.6	238.6	250.1	262.0
150°	185.3	186.2	189.3	195.2	201.5	209.2	219.2	228.6	238.6	249.0	259.8
152.5°	190.4	190.8	193.7	198.8	204.8	211.8	220.9	229.3	238.2	247.6	257.3
155°	197.0	197.0	199.7	204.2	208.7	215.1	222.8	230.0	237.3	244.9	253.0
157.5°	203.0	202.9	205.1	209.0	212.9	217.7	224.3	230.4	236.1	242.2	249.1
160°	207.0	206.5	208.3	211.5	215.1	219.2	225.1	230.4	235.0	240.4	245.8
162.5°	210.2	209.8	211.6	214.4	217.3	220.6	225.8	230.1	233.9	238.2	243.0
165°	215.1	214.2	215.6	217.8	219.6	222.4	225.9	229.6	232.3	235.0	238.6
167.5°	218.3	217.9	218.7	220.0	221.3	222.9	225.9	228.5	229.7	231.8	234.3
170°	220.5	220.1	220.5	221.4	222.4	223.7	225.9	227.8	228.6	230.0	231.8
172.5°	222.0	221.2	221.6	222.5	223.1	223.7	225.6	227.0	227.2	227.8	229.3
175°	223.7	222.8	223.2	223.7	223.7	223.7	225.1	225.9	225.5	225.5	225.9
177.5°	224.5	223.8	223.8	224.1	223.8	223.8	224.5	224.8	224.1	224.1	224.5
180°	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1



TEST NUMBER: P333531-927

CATALOG NUMBER: S125RDIP-S610D590U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	796.9	796.9	796.9	796.9	796.9	796.9	796.9	796.9
2.5°	794.2	795.3	796.4	796.9	796.8	796.6	796.5	796.5
5°	789.3	790.7	792.0	792.6	792.3	792.0	791.8	791.5
7.5°	779.5	780.5	781.4	781.7	781.4	781.1	780.9	780.5
10°	771.2	771.6	772.1	772.1	771.6	771.2	770.8	770.4
12.5°	759.5	759.8	760.0	759.9	759.2	758.7	758.0	757.4
15°	740.1	739.9	739.8	739.1	737.9	736.7	735.5	734.3
17.5°	715.9	715.2	714.5	713.7	712.7	711.7	710.7	709.7
20°	698.1	697.4	696.7	695.8	694.6	693.4	692.2	690.9
22.5°	680.4	679.1	677.8	676.6	675.7	674.6	673.7	672.6
25°	651.4	649.7	647.9	646.3	644.8	643.3	641.9	640.4
27.5°	620.0	617.6	615.1	613.2	611.8	610.4	609.0	607.5
30°	597.5	594.5	591.4	589.2	588.0	586.8	585.7	584.5
32.5°	575.7	572.4	568.9	566.5	564.9	563.4	561.9	560.4
35°	541.8	537.9	534.0	531.2	529.3	527.4	525.5	523.6
37.5°	506.3	501.6	496.9	493.7	491.9	490.1	488.3	486.5
40°	482.8	477.7	472.6	469.3	467.7	466.0	464.5	462.9
42.5°	459.6	454.7	449.9	446.2	443.9	441.6	439.2	436.9
45°	422.6	417.3	411.9	408.3	406.3	404.3	402.3	400.3
47.5°	386.1	380.6	375.1	371.2	369.0	366.8	364.6	362.3
50°	361.3	355.7	350.1	346.3	344.3	342.3	340.2	338.3
52.5°	337.9	331.8	325.7	321.7	319.7	317.7	315.7	313.7
55°	302.1	296.1	290.1	286.1	283.9	281.8	279.6	277.5
57.5°	266.4	260.5	254.7	250.7	248.8	246.9	245.1	243.2
60°	242.8	236.9	231.1	227.1	225.1	223.1	221.1	219.1
62.5°	219.6	214.1	208.7	204.9	203.0	201.0	198.9	196.9
65°	185.5	180.1	174.8	171.1	169.1	167.2	165.1	163.1
67.5°	153.0	148.1	143.1	139.9	138.3	136.7	135.1	133.5
70°	131.3	127.2	123.0	120.2	118.6	117.0	115.3	113.8
72.5°	111.3	107.4	103.6	101.2	100.1	99.0	98.0	96.9
75°	83.2	80.2	77.3	75.3	74.5	73.5	72.6	71.6
77.5°	59.2	57.1	55.1	53.7	53.0	52.3	51.7	50.9
80°	44.5	43.3	42.1	41.4	41.1	40.9	40.6	40.3
82.5°	33.3	32.7	32.2	31.8	31.7	31.5	31.4	31.2
85°	19.0	18.9	18.7	18.6	18.5	18.3	18.2	18.1
87.5°	8.9	9.0	9.0	9.2	9.0	9.0	9.0	8.8
90°	8.2	8.6	9.0	9.9	9.9	9.9	10.4	10.4
92.5°	80.1	58.1	43.7	37.1	31.3	30.2	29.5	28.8
95°	324.9	256.2	200.7	162.7	130.6	117.0	113.4	106.2
97.5°	483.9	435.7	381.6	328.8	300.9	275.5	262.4	256.7
100°	555.8	533.7	487.1	440.1	408.9	376.4	359.7	352.4
102.5°	580.0	593.7	571.3	539.6	506.2	483.1	464.9	459.5
105°	565.8	627.6	647.5	642.5	628.1	613.2	604.2	598.7
107.5°	514.8	597.4	648.5	672.0	679.4	679.3	676.3	672.6
110°	477.2	563.1	626.8	665.2	685.5	694.1	697.3	697.3



TEST NUMBER: P333531-927

CATALOG NUMBER: S125RDIP-S610D590U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	447.6	529.1	593.5	638.8	668.5	683.3	691.1	694.3
115°	410.3	480.4	542.2	591.5	626.8	648.5	661.1	667.0
117.5°	386.3	446.6	499.9	545.2	580.4	602.9	615.4	619.0
120°	373.3	427.5	477.2	517.0	550.4	572.1	584.3	587.9
122.5°	363.5	413.8	458.0	495.3	525.1	544.9	557.1	560.4
125°	349.3	395.4	434.7	467.2	492.6	511.1	521.0	525.5
127.5°	334.9	377.9	414.5	445.0	467.9	484.3	493.7	495.7
130°	325.8	365.6	400.8	430.2	452.8	467.7	476.7	479.4
132.5°	316.8	354.0	386.0	414.3	436.9	451.8	460.1	463.2
135°	305.0	336.2	365.1	390.9	410.7	425.6	433.8	436.5
137.5°	295.1	320.3	344.4	366.2	384.0	397.6	405.0	408.1
140°	289.6	310.9	331.7	350.7	367.4	379.1	385.9	388.2
142.5°	284.9	302.9	320.8	337.3	351.5	361.4	367.8	369.7
145°	278.8	292.8	306.8	319.0	329.9	337.5	342.5	344.4
147.5°	273.1	284.4	295.2	304.4	313.0	319.1	322.0	322.8
150°	269.7	279.7	288.3	296.4	303.2	308.6	310.5	310.9
152.5°	266.2	275.0	282.9	289.2	294.9	299.2	301.0	301.5
155°	260.7	268.0	274.3	279.2	283.8	286.9	288.3	288.8
157.5°	255.3	261.3	266.2	270.1	273.5	276.2	277.4	277.3
160°	251.7	256.2	260.7	263.9	267.0	269.3	270.2	269.7
162.5°	247.7	251.9	255.6	258.5	260.9	262.8	263.0	262.9
165°	242.2	245.3	248.1	250.3	252.2	253.0	253.0	253.0
167.5°	236.9	239.1	241.1	242.7	243.7	244.5	244.1	244.0
170°	234.1	235.4	236.8	237.7	238.6	239.1	239.1	238.6
172.5°	230.8	232.2	233.1	233.7	233.9	234.7	234.0	233.5
175°	227.3	227.3	228.2	228.2	228.2	228.6	227.8	227.3
177.5°	224.8	225.2	225.2	225.2	224.8	225.2	224.1	224.1
180°	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1

(END OF REPORT)