

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333322-935

Luminaire Tested: **S125DIP-S1270D1035U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333322-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1270D1035U935-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8025.8 lumens
Efficiency: N/A
Efficacy: 120.1 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333322-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333322-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	56																				
1	99	95	91	88	92	88	85	82	76	74	72	65	63	62	55	53	52	47																				
2	91	83	77	72	84	78	72	68	67	63	60	57	54	52	48	46	44	40																				
3	83	73	66	60	77	69	62	57	59	54	50	51	47	44	43	40	38	34																				
4	76	65	57	51	70	61	54	48	53	47	43	45	41	38	39	35	33	29																				
5	70	58	50	44	65	54	47	42	47	42	37	41	36	33	35	31	29	26																				
6	64	52	44	38	60	49	42	36	43	37	33	37	32	29	32	28	25	23																				
7	59	47	39	34	55	44	37	32	39	33	29	34	29	26	29	25	23	20																				
8	55	43	35	30	51	40	33	28	35	30	26	31	26	23	26	23	20	18																				
9	51	39	32	26	48	37	30	25	32	27	23	28	24	21	24	21	18	16																				
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	23	19	17	15																				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10213	10213	10213	10213
5°	11826	10247	8972	10247
10°	13759	10194	7861	10194
15°	15230	10120	7252	10120
20°	17049	10001	6763	10001
25°	19973	9867	6524	9867
30°	21572	9735	6317	9735
35°	17738	9488	6180	9488
40°	12607	9144	6032	9144
45°	9685	8680	5946	8680
50°	8268	8106	5934	8106
55°	7362	7543	5986	7543
60°	6640	6926	6138	6926
65°	6134	6308	6298	6308
70°	5576	5665	6388	5665
75°	4923	4991	6331	4991
80°	4143	4069	5791	4069
85°	3283	2934	4676	2934



TEST NUMBER: P333322-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.2	1.9
10°-20°	453.2	5.6
20°-30°	736.0	9.2
30°-40°	897.7	11.2
40°-50°	816.7	10.2
50°-60°	650.5	8.1
60°-70°	453.1	5.6
70°-80°	241.6	3.0
80°-90°	63.4	0.8
90°-100°	42.2	0.5
100°-110°	259.7	3.2
110°-120°	471.1	5.9
120°-130°	604.6	7.5
130°-140°	650.2	8.1
140°-150°	610.3	7.6
150°-160°	493.7	6.2
160°-170°	319.3	4.0
170°-180°	110.1	1.4
0°-30°	1341.4	16.7
0°-40°	2239.2	27.9
0°-60°	3706.4	46.2
0°-90°	4464.5	55.6
90°-120°	772.9	9.6
90°-150°	2638.1	32.9
90°-180°	3561.0	44.4
0°-180°	8025.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1581	1581	1581	1581	1581	
5°	1824	1581	1384	1581	1824	184
15°	2278	1514	1085	1514	2278	652
25°	2803	1385	916	1385	2803	1280
35°	2250	1203	784	1203	2250	1377
45°	1060	950	651	950	1060	849
55°	654	670	532	670	654	589
65°	401	413	412	413	401	398
75°	197	200	254	200	197	212
85°	44	40	63	40	44	52
90°	21	1	21	1	21	11
95°	18	49	18	49	18	15
105°	255	253	255	253	255	231
115°	471	475	471	475	471	468
125°	675	675	675	675	675	600
135°	838	842	838	842	838	647
145°	973	976	973	976	973	608
155°	1067	1075	1067	1075	1067	492
165°	1128	1134	1128	1134	1128	318
175°	1154	1160	1154	1160	1154	110
180°	1160	1160	1160	1160	1160	



TEST NUMBER: P333322-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1672.6	1670.4	1668.3	1664.0	1667.2	1658.0	1653.7	1646.2	1637.1	1633.9	1630.1
5°	1824.2	1827.6	1830.9	1816.9	1818.2	1808.8	1787.3	1769.9	1755.8	1737.7	1724.9
7.5°	2006.8	1998.9	1998.2	1989.1	1973.4	1960.8	1938.2	1909.4	1881.7	1850.0	1823.9
10°	2098.1	2098.8	2092.7	2082.0	2065.2	2053.1	2023.6	1995.4	1961.2	1920.9	1892.0
12.5°	2166.8	2169.6	2162.0	2147.5	2139.2	2112.2	2089.0	2055.6	2014.8	1982.6	1938.7
15°	2277.9	2270.5	2265.2	2247.0	2233.0	2204.8	2167.9	2133.0	2088.7	2047.7	2006.8
17.5°	2385.1	2391.0	2380.9	2364.4	2320.7	2287.8	2238.3	2190.4	2135.3	2080.3	2031.5
20°	2480.6	2486.1	2470.6	2441.7	2389.4	2356.5	2291.4	2229.6	2165.8	2095.4	2041.7
22.5°	2599.9	2595.6	2574.7	2530.8	2485.4	2424.7	2354.2	2279.0	2199.2	2119.5	2048.1
25°	2802.8	2774.6	2761.8	2707.5	2647.7	2558.5	2461.9	2351.7	2252.5	2147.1	2055.8
27.5°	2915.3	2906.4	2892.2	2854.4	2791.5	2696.0	2582.1	2448.0	2307.9	2174.9	2055.4
30°	2892.7	2894.1	2895.5	2883.3	2843.1	2771.2	2657.8	2513.5	2347.1	2197.4	2059.2
32.5°	2693.0	2717.4	2740.8	2768.5	2779.7	2765.9	2694.8	2564.6	2393.2	2223.2	2057.0
35°	2249.8	2257.1	2333.0	2408.1	2510.2	2589.4	2642.4	2584.6	2440.3	2245.1	2054.4
37.5°	1754.2	1790.4	1842.9	1927.9	2075.1	2206.9	2376.4	2454.5	2407.9	2252.2	2049.8
40°	1495.4	1529.0	1563.1	1649.8	1773.9	1933.6	2126.2	2290.7	2328.9	2229.6	2033.7
42.5°	1295.6	1322.2	1360.2	1425.3	1529.0	1670.5	1854.6	2069.5	2201.7	2164.1	1999.8
45°	1060.4	1077.2	1106.7	1158.5	1233.6	1344.4	1506.8	1741.7	1946.4	2014.1	1919.5
47.5°	907.7	907.6	930.5	966.2	1020.5	1114.6	1234.7	1418.8	1637.4	1799.1	1791.7
50°	822.9	819.5	837.6	868.5	911.5	973.9	1088.6	1235.6	1445.7	1628.9	1679.9
52.5°	749.8	750.2	761.4	784.2	820.2	873.5	959.2	1091.7	1271.2	1459.2	1555.4
55°	653.8	651.0	663.7	679.2	705.4	740.3	802.0	903.4	1049.0	1234.2	1359.1
57.5°	565.7	573.1	578.2	588.9	610.6	634.0	686.0	760.4	876.0	1034.9	1166.9
60°	514.1	521.5	525.6	536.2	553.7	573.9	614.2	674.5	771.9	908.8	1039.7
62.5°	468.0	473.7	475.0	484.7	498.9	518.6	550.3	601.0	677.9	797.6	925.8
65°	401.4	401.4	404.1	414.1	420.9	438.2	462.4	499.4	561.1	654.4	763.8
67.5°	337.2	340.4	339.8	344.1	350.3	363.9	381.3	411.7	457.4	525.6	613.0
70°	295.3	298.0	297.3	300.7	307.4	316.2	330.2	359.0	391.9	450.4	525.6
72.5°	257.7	258.8	257.1	261.5	265.5	273.2	288.9	304.3	335.0	384.4	446.1
75°	197.3	198.6	200.0	202.7	206.7	210.8	218.8	234.3	254.3	291.3	330.9
77.5°	147.9	145.3	148.6	148.2	150.5	153.6	160.7	168.8	185.4	208.7	239.4
80°	111.4	112.1	112.1	112.8	116.1	118.1	124.2	130.2	142.9	160.4	181.9
82.5°	81.4	83.1	82.1	83.3	86.0	87.5	90.8	95.8	103.2	116.9	132.5
85°	44.3	41.0	42.3	43.7	43.7	44.3	47.0	49.0	53.0	58.4	64.4
87.5°	17.0	18.0	18.4	18.3	18.7	18.5	20.5	20.3	21.7	23.2	25.1
90°	20.7	20.1	19.5	18.9	18.3	17.6	16.6	15.7	14.7	13.8	12.4
92.5°	19.3	19.0	18.7	18.4	18.2	17.6	16.6	15.7	14.7	13.8	12.6
95°	18.1	18.1	18.1	18.1	18.1	17.6	16.6	15.7	14.7	13.8	21.0
97.5°	18.1	18.1	18.1	18.1	18.1	20.8	26.2	31.5	36.9	42.3	56.7
100°	18.1	18.9	19.5	20.3	21.1	35.7	64.2	92.6	121.1	149.6	148.8
102.5°	108.1	121.1	134.1	147.1	160.1	169.3	174.7	180.0	185.5	190.9	190.4
105°	255.3	255.5	255.7	255.9	256.1	256.1	256.1	256.1	256.1	256.1	256.1
107.5°	321.8	322.4	323.0	323.6	324.2	324.4	324.4	324.3	324.3	324.3	323.9
110°	367.9	367.7	367.6	367.4	367.2	367.4	367.9	368.5	369.1	369.6	369.3



TEST NUMBER: P333322-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	409.2	409.5	409.7	410.0	410.3	410.8	411.5	412.2	412.9	413.7	413.5
115°	471.1	472.3	473.4	474.6	475.7	476.6	477.4	478.2	479.0	479.7	479.5
117.5°	537.1	537.6	538.1	538.6	539.1	539.8	540.9	541.8	542.9	543.8	543.1
120°	577.7	578.7	579.6	580.6	581.5	582.2	582.6	583.0	583.3	583.8	583.2
122.5°	616.2	617.3	618.5	619.6	620.6	621.4	621.8	622.2	622.5	622.9	622.7
125°	674.9	675.5	676.0	676.6	677.2	677.8	678.6	679.3	680.1	680.9	680.9
127.5°	724.2	725.7	727.0	728.4	729.9	730.7	731.2	731.6	732.0	732.5	732.5
130°	759.9	761.0	761.9	762.8	763.8	764.6	765.1	765.7	766.3	766.8	766.6
132.5°	793.0	793.9	794.9	795.8	796.8	797.3	797.5	797.5	797.6	797.8	798.2
135°	838.2	839.3	840.5	841.6	842.7	843.5	844.0	844.3	844.6	845.1	845.4
137.5°	883.6	884.6	885.5	886.6	887.5	888.0	887.9	887.9	887.8	887.7	888.0
140°	910.4	911.5	912.7	913.9	915.0	915.3	915.0	914.6	914.2	913.9	914.0
142.5°	935.8	937.0	938.1	939.3	940.5	941.0	940.9	940.8	940.7	940.6	940.4
145°	973.2	974.3	975.4	976.6	977.8	978.2	978.0	977.8	977.7	977.5	977.5
147.5°	1003.9	1005.3	1006.7	1008.1	1009.4	1010.0	1009.8	1009.5	1009.4	1009.1	1008.8
150°	1023.9	1025.4	1026.9	1028.5	1030.0	1030.5	1030.2	1029.8	1029.4	1029.1	1028.6
152.5°	1042.4	1043.8	1045.2	1046.5	1047.9	1048.4	1048.1	1047.7	1047.3	1046.9	1046.5
155°	1066.9	1068.4	1069.9	1071.4	1073.0	1073.5	1072.9	1072.3	1071.8	1071.2	1070.7
157.5°	1087.4	1088.8	1090.4	1091.9	1093.5	1093.9	1093.3	1092.7	1092.1	1091.5	1091.4
160°	1100.4	1101.9	1103.5	1105.0	1106.5	1106.9	1106.1	1105.4	1104.6	1103.8	1103.6
162.5°	1112.1	1113.8	1115.4	1117.1	1118.8	1119.1	1118.0	1117.0	1115.9	1114.8	1114.7
165°	1127.9	1129.5	1130.9	1132.5	1134.0	1134.2	1133.1	1131.9	1130.8	1129.6	1129.5
167.5°	1138.9	1140.7	1142.4	1144.1	1145.8	1146.0	1144.6	1143.2	1141.9	1140.5	1140.2
170°	1145.1	1146.9	1148.6	1150.2	1151.9	1152.1	1150.6	1149.0	1147.5	1146.0	1145.7
172.5°	1149.3	1150.9	1152.6	1154.3	1156.1	1156.2	1154.9	1153.5	1152.1	1150.7	1150.4
175°	1154.5	1156.2	1158.0	1159.7	1161.4	1161.5	1160.0	1158.5	1156.9	1155.4	1155.2
177.5°	1157.6	1158.9	1160.1	1161.3	1162.5	1162.6	1161.6	1160.5	1159.4	1158.3	1158.2
180°	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7



TEST NUMBER: P333322-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1626.9	1623.2	1618.9	1611.4	1602.2	1597.4	1589.8	1585.0	1575.4	1567.3	1558.8
5°	1709.4	1692.0	1675.9	1655.1	1632.3	1617.5	1600.1	1580.6	1560.5	1539.6	1516.8
7.5°	1795.0	1764.1	1730.5	1694.4	1659.1	1626.6	1595.6	1565.1	1536.7	1502.4	1473.3
10°	1852.4	1813.5	1771.9	1722.9	1675.2	1633.7	1591.3	1554.4	1516.8	1476.5	1441.0
12.5°	1909.9	1858.0	1799.2	1745.4	1688.2	1637.9	1588.1	1541.0	1493.7	1449.1	1407.7
15°	1950.4	1904.8	1850.4	1773.9	1709.4	1640.4	1574.6	1513.5	1456.5	1406.8	1354.4
17.5°	1977.1	1918.3	1859.9	1786.5	1702.1	1624.8	1550.2	1480.3	1416.0	1353.1	1302.6
20°	1981.9	1921.6	1860.4	1788.6	1702.1	1613.5	1539.0	1455.1	1386.0	1320.9	1259.1
22.5°	1980.4	1911.9	1845.5	1771.5	1687.0	1605.4	1515.4	1429.9	1354.8	1290.8	1226.3
25°	1965.1	1892.0	1808.8	1734.3	1651.1	1564.5	1473.3	1384.7	1308.1	1234.9	1171.2
27.5°	1952.6	1857.7	1763.4	1676.5	1596.2	1516.8	1429.4	1338.7	1253.9	1179.7	1119.6
30°	1937.0	1833.0	1726.9	1636.3	1553.8	1476.5	1394.0	1305.4	1216.9	1144.4	1080.0
32.5°	1923.0	1801.8	1689.9	1591.2	1503.8	1428.7	1352.6	1268.3	1181.4	1107.8	1043.4
35°	1896.1	1755.8	1627.5	1516.1	1422.9	1345.7	1281.9	1203.4	1123.5	1052.4	990.7
37.5°	1861.8	1695.4	1557.8	1441.0	1338.7	1257.4	1198.0	1137.7	1061.1	992.6	936.7
40°	1835.0	1652.4	1506.8	1387.3	1281.3	1196.7	1141.7	1084.6	1020.9	957.1	898.0
42.5°	1801.1	1613.8	1455.3	1326.6	1221.7	1139.3	1081.5	1033.0	976.8	917.4	862.5
45°	1739.0	1543.7	1371.8	1233.6	1127.6	1046.4	986.6	950.4	908.1	851.7	805.4
47.5°	1647.6	1459.5	1281.8	1139.1	1029.7	954.4	898.5	863.7	833.9	791.9	749.9
50°	1566.5	1396.7	1216.9	1075.2	965.8	889.9	838.3	806.8	781.3	749.0	713.4
52.5°	1475.8	1317.8	1153.0	1013.0	904.6	829.8	779.2	751.5	730.2	707.1	672.1
55°	1331.6	1197.4	1044.3	911.5	811.4	738.3	694.0	669.9	652.4	634.9	613.5
57.5°	1172.8	1067.8	932.3	810.8	718.7	652.1	610.8	587.3	573.7	564.7	552.1
60°	1061.1	971.2	854.4	743.6	653.8	594.7	554.4	536.2	524.9	517.5	508.1
62.5°	957.5	883.6	775.5	674.4	595.7	539.8	503.9	486.3	475.4	471.8	464.1
65°	804.7	747.7	658.4	574.5	507.4	459.8	429.6	412.8	406.0	402.0	402.7
67.5°	654.3	619.5	547.8	476.2	422.7	382.7	358.5	345.7	342.3	336.9	336.8
70°	562.4	536.2	475.9	413.5	365.8	334.9	313.4	300.0	296.6	293.9	293.3
72.5°	481.4	458.4	406.0	356.0	313.1	286.0	268.4	260.3	254.8	253.1	253.0
75°	361.8	349.0	307.4	267.8	238.2	219.5	207.4	200.0	196.0	195.3	196.0
77.5°	257.2	246.1	219.6	191.6	172.9	158.7	148.4	145.9	141.4	141.5	140.8
80°	193.3	185.9	169.1	147.0	131.6	119.5	114.1	109.4	108.1	106.1	108.1
82.5°	140.2	132.2	120.8	106.7	93.9	86.7	81.4	79.9	79.0	78.1	78.5
85°	69.1	69.8	63.1	52.3	47.0	43.0	39.6	39.6	38.9	38.2	38.9
87.5°	25.8	24.5	22.1	20.1	17.2	15.2	14.5	14.6	13.3	13.2	13.9
90°	11.1	9.7	8.4	7.0	5.4	3.9	2.4	0.9	2.4	3.9	5.4
92.5°	11.4	10.2	9.0	9.0	10.0	11.1	12.1	13.3	12.1	11.1	10.0
95°	28.2	35.6	42.8	46.8	47.3	47.9	48.4	49.0	48.4	47.9	47.3
97.5°	71.0	85.4	99.8	106.4	105.4	104.4	103.3	102.3	103.3	104.4	105.4
100°	148.1	147.3	146.5	145.9	145.3	144.7	144.1	143.5	144.1	144.7	145.3
102.5°	189.9	189.5	189.0	188.4	187.7	187.0	186.2	185.5	186.2	187.0	187.7
105°	256.1	256.1	256.1	255.8	255.0	254.3	253.5	252.7	253.5	254.3	255.0
107.5°	323.5	323.1	322.7	322.5	322.5	322.5	322.5	322.5	322.5	322.5	322.5
110°	368.9	368.5	368.2	367.9	367.9	367.9	367.9	367.9	367.9	367.9	367.9



TEST NUMBER: P333322-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	413.2	413.0	412.8	412.4	412.0	411.5	411.0	410.6	411.0	411.5	412.0
115°	479.3	479.1	479.0	478.4	477.4	476.5	475.5	474.6	475.5	476.5	477.4
117.5°	542.3	541.7	541.0	540.6	540.6	540.6	540.7	540.7	540.7	540.6	540.6
120°	582.6	582.0	581.4	581.3	581.4	581.6	581.8	582.0	581.8	581.6	581.4
122.5°	622.4	622.2	621.8	621.4	620.6	619.9	619.1	618.5	619.1	619.9	620.6
125°	680.9	680.9	680.9	680.2	678.9	677.5	676.1	674.9	676.1	677.5	678.9
127.5°	732.7	732.8	732.9	732.5	731.5	730.6	729.6	728.7	729.6	730.6	731.5
130°	766.5	766.3	766.0	765.5	764.6	763.6	762.7	761.6	762.7	763.6	764.6
132.5°	798.7	799.0	799.4	799.1	798.0	796.9	795.8	794.7	795.8	796.9	798.0
135°	845.8	846.2	846.6	846.2	845.1	844.0	842.7	841.6	842.7	844.0	845.1
137.5°	888.4	888.7	889.1	888.7	887.8	886.7	885.8	884.8	885.8	886.7	887.8
140°	914.2	914.4	914.6	914.5	914.1	913.8	913.3	913.0	913.3	913.8	914.1
142.5°	940.1	939.9	939.6	939.4	939.1	938.9	938.7	938.4	938.7	938.9	939.1
145°	977.5	977.5	977.5	977.2	976.9	976.5	976.1	975.8	976.1	976.5	976.9
147.5°	1008.7	1008.4	1008.1	1008.1	1008.1	1008.2	1008.3	1008.4	1008.3	1008.2	1008.1
150°	1028.3	1027.9	1027.5	1027.5	1027.9	1028.3	1028.6	1029.1	1028.6	1028.3	1027.9
152.5°	1046.1	1045.8	1045.4	1045.6	1046.5	1047.3	1048.2	1049.0	1048.2	1047.3	1046.5
155°	1070.4	1070.1	1069.6	1070.1	1071.2	1072.3	1073.5	1074.6	1073.5	1072.3	1071.2
157.5°	1091.4	1091.3	1091.3	1091.7	1092.4	1093.0	1093.6	1094.3	1093.6	1093.0	1092.4
160°	1103.5	1103.3	1103.0	1103.5	1104.7	1105.9	1107.0	1108.1	1107.0	1105.9	1104.7
162.5°	1114.5	1114.2	1114.0	1114.6	1115.7	1116.8	1118.0	1119.1	1118.0	1116.8	1115.7
165°	1129.2	1129.0	1128.9	1129.4	1130.5	1131.6	1132.7	1133.9	1132.7	1131.6	1130.5
167.5°	1140.1	1139.9	1139.7	1140.2	1141.3	1142.5	1143.8	1145.0	1143.8	1142.5	1141.3
170°	1145.6	1145.4	1145.2	1145.7	1147.1	1148.4	1149.8	1151.1	1149.8	1148.4	1147.1
172.5°	1150.0	1149.7	1149.4	1149.9	1151.2	1152.5	1153.9	1155.2	1153.9	1152.5	1151.2
175°	1155.0	1154.9	1154.7	1155.1	1156.2	1157.4	1158.6	1159.7	1158.6	1157.4	1156.2
177.5°	1158.0	1157.9	1157.7	1158.1	1159.0	1159.9	1160.9	1161.7	1160.9	1159.9	1159.0
180°	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7



TEST NUMBER: P333322-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1553.8	1548.0	1543.2	1532.4	1526.5	1518.5	1512.0	1519.0	1511.5	1514.7	1509.8
5°	1505.5	1486.6	1473.3	1453.7	1437.0	1421.5	1410.1	1408.1	1402.7	1400.1	1392.0
7.5°	1447.2	1423.7	1400.6	1375.1	1353.6	1331.7	1317.8	1306.2	1298.6	1288.5	1281.7
10°	1412.8	1381.3	1354.4	1323.5	1296.7	1273.2	1254.4	1245.0	1236.3	1223.6	1218.8
12.5°	1370.4	1337.7	1305.0	1272.0	1246.2	1220.0	1203.9	1189.7	1183.7	1169.3	1167.9
15°	1319.5	1270.5	1238.3	1204.7	1169.2	1147.7	1134.3	1118.9	1112.2	1102.1	1094.7
17.5°	1258.9	1215.0	1174.8	1140.1	1109.6	1091.5	1074.8	1064.2	1052.7	1046.1	1034.0
20°	1214.8	1173.2	1132.9	1096.1	1072.5	1051.7	1038.3	1028.2	1016.2	1012.8	1000.7
22.5°	1177.8	1131.9	1093.2	1062.2	1036.6	1013.1	998.6	991.7	983.4	973.1	970.6
25°	1117.5	1069.9	1037.0	1006.1	983.3	961.8	951.7	943.0	935.0	927.6	924.9
27.5°	1065.4	1022.9	983.8	955.9	936.0	916.4	907.6	897.0	891.0	885.1	877.9
30°	1028.9	985.2	951.1	924.2	902.8	885.3	875.9	868.5	863.2	857.7	853.8
32.5°	991.4	950.9	917.7	891.5	870.0	856.8	848.5	843.3	837.3	830.9	825.8
35°	941.7	897.3	865.1	842.3	825.5	815.5	806.1	801.3	794.7	794.7	789.3
37.5°	885.7	847.4	819.0	798.1	783.1	774.1	764.0	760.7	756.4	753.5	751.7
40°	852.4	816.8	790.0	769.1	753.0	745.6	737.6	732.3	729.5	726.2	724.9
42.5°	818.0	784.0	758.3	739.1	725.1	718.8	711.3	707.6	702.1	697.8	697.0
45°	765.8	732.9	709.5	694.0	681.9	674.5	669.9	661.8	659.1	653.8	653.1
47.5°	716.3	684.8	661.7	649.0	638.4	632.4	625.0	616.9	613.9	611.1	610.9
50°	679.2	650.4	628.9	616.8	606.7	598.1	590.6	585.2	583.2	583.2	584.6
52.5°	641.6	617.1	598.8	584.0	574.5	565.2	558.4	555.2	552.1	555.3	557.8
55°	586.6	561.8	548.4	534.3	524.9	514.1	510.7	509.5	507.4	512.8	515.5
57.5°	528.3	510.9	495.2	481.2	472.8	466.6	462.0	461.2	465.0	467.5	476.2
60°	491.3	471.1	457.1	446.3	436.3	432.2	430.9	429.6	432.2	439.6	451.0
62.5°	450.5	434.1	419.0	410.9	403.5	396.8	396.5	397.4	402.7	411.1	422.6
65°	390.6	376.5	366.4	357.1	351.0	347.0	348.4	351.0	357.1	368.5	381.3
67.5°	329.8	320.1	311.2	303.5	297.7	297.7	299.1	303.1	310.2	323.4	335.0
70°	290.6	279.9	272.5	269.1	264.4	261.7	265.8	272.5	278.5	290.6	300.7
72.5°	251.4	242.3	236.5	234.3	232.2	230.1	231.4	238.7	246.8	258.9	270.6
75°	193.3	189.9	185.9	183.2	181.2	182.5	183.9	190.6	197.3	210.1	223.5
77.5°	141.1	137.6	135.2	134.5	133.5	134.1	137.8	142.8	149.4	158.7	168.8
80°	106.7	105.4	104.0	103.3	103.3	104.0	109.4	112.8	118.8	127.5	135.6
82.5°	77.7	76.9	76.6	76.5	77.1	77.1	80.4	84.8	89.8	96.3	103.3
85°	41.0	39.6	41.6	42.3	41.0	43.0	44.3	47.0	49.0	52.3	55.7
87.5°	14.8	16.2	15.9	16.7	17.0	18.3	18.0	20.3	21.6	22.8	22.5
90°	7.0	8.4	9.7	11.1	12.4	13.8	14.7	15.7	16.6	17.6	18.3
92.5°	9.0	9.0	10.2	11.4	12.6	13.8	14.7	15.7	16.6	17.6	18.2
95°	46.8	42.8	35.6	28.2	21.0	13.8	14.7	15.7	16.6	17.6	18.1
97.5°	106.4	99.8	85.4	71.0	56.7	42.3	36.9	31.5	26.2	20.8	18.1
100°	145.9	146.5	147.3	148.1	148.8	149.6	121.1	92.6	64.2	35.7	21.1
102.5°	188.4	189.0	189.5	189.9	190.4	190.9	185.5	180.0	174.7	169.3	160.1
105°	255.8	256.1	256.1	256.1	256.1	256.1	256.1	256.1	256.1	256.1	256.1
107.5°	322.5	322.7	323.1	323.5	323.9	324.3	324.3	324.3	324.4	324.4	324.2
110°	367.9	368.2	368.5	368.9	369.3	369.6	369.1	368.5	367.9	367.4	367.2



TEST NUMBER: P333322-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	412.4	412.8	413.0	413.2	413.5	413.7	412.9	412.2	411.5	410.8	410.3
115°	478.4	479.0	479.1	479.3	479.5	479.7	479.0	478.2	477.4	476.6	475.7
117.5°	540.6	541.0	541.7	542.3	543.1	543.8	542.9	541.8	540.9	539.8	539.1
120°	581.3	581.4	582.0	582.6	583.2	583.8	583.3	583.0	582.6	582.2	581.5
122.5°	621.4	621.8	622.2	622.4	622.7	622.9	622.5	622.2	621.8	621.4	620.6
125°	680.2	680.9	680.9	680.9	680.9	680.9	680.1	679.3	678.6	677.8	677.2
127.5°	732.5	732.9	732.8	732.7	732.5	732.5	732.0	731.6	731.2	730.7	729.9
130°	765.5	766.0	766.3	766.5	766.6	766.8	766.3	765.7	765.1	764.6	763.8
132.5°	799.1	799.4	799.0	798.7	798.2	797.8	797.6	797.5	797.5	797.3	796.8
135°	846.2	846.6	846.2	845.8	845.4	845.1	844.6	844.3	844.0	843.5	842.7
137.5°	888.7	889.1	888.7	888.4	888.0	887.7	887.8	887.9	887.9	888.0	887.5
140°	914.5	914.6	914.4	914.2	914.0	913.9	914.2	914.6	915.0	915.3	915.0
142.5°	939.4	939.6	939.9	940.1	940.4	940.6	940.7	940.8	940.9	941.0	940.5
145°	977.2	977.5	977.5	977.5	977.5	977.5	977.7	977.8	978.0	978.2	977.8
147.5°	1008.1	1008.1	1008.4	1008.7	1008.8	1009.1	1009.4	1009.5	1009.8	1010.0	1009.4
150°	1027.5	1027.5	1027.9	1028.3	1028.6	1029.1	1029.4	1029.8	1030.2	1030.5	1030.0
152.5°	1045.6	1045.4	1045.8	1046.1	1046.5	1046.9	1047.3	1047.7	1048.1	1048.4	1047.9
155°	1070.1	1069.6	1070.1	1070.4	1070.7	1071.2	1071.8	1072.3	1072.9	1073.5	1073.0
157.5°	1091.7	1091.3	1091.3	1091.4	1091.4	1091.5	1092.1	1092.7	1093.3	1093.9	1093.5
160°	1103.5	1103.0	1103.3	1103.5	1103.6	1103.8	1104.6	1105.4	1106.1	1106.9	1106.5
162.5°	1114.6	1114.0	1114.2	1114.5	1114.7	1114.8	1115.9	1117.0	1118.0	1119.1	1118.8
165°	1129.4	1128.9	1129.0	1129.2	1129.5	1129.6	1130.8	1131.9	1133.1	1134.2	1134.0
167.5°	1140.2	1139.7	1139.9	1140.1	1140.2	1140.5	1141.9	1143.2	1144.6	1146.0	1145.8
170°	1145.7	1145.2	1145.4	1145.6	1145.7	1146.0	1147.5	1149.0	1150.6	1152.1	1151.9
172.5°	1149.9	1149.4	1149.7	1150.0	1150.4	1150.7	1152.1	1153.5	1154.9	1156.2	1156.1
175°	1155.1	1154.7	1154.9	1155.0	1155.2	1155.4	1156.9	1158.5	1160.0	1161.5	1161.4
177.5°	1158.1	1157.7	1157.9	1158.0	1158.2	1158.3	1159.4	1160.5	1161.6	1162.6	1162.5
180°	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7



TEST NUMBER: P333322-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1506.7	1510.4	1507.2	1511.5	1507.2	1510.4	1506.7	1509.8	1514.7	1511.5	1519.0
5°	1388.6	1382.6	1386.6	1384.0	1386.6	1382.6	1388.6	1392.0	1400.1	1402.7	1408.1
7.5°	1279.6	1273.8	1267.3	1264.2	1267.3	1273.8	1279.6	1281.7	1288.5	1298.6	1306.2
10°	1211.4	1204.1	1203.4	1198.7	1203.4	1204.1	1211.4	1218.8	1223.6	1236.3	1245.0
12.5°	1161.5	1154.7	1147.0	1145.0	1147.0	1154.7	1161.5	1167.9	1169.3	1183.7	1189.7
15°	1090.6	1085.3	1080.6	1084.6	1080.6	1085.3	1090.6	1094.7	1102.1	1112.2	1118.9
17.5°	1031.7	1027.3	1026.5	1021.5	1026.5	1027.3	1031.7	1034.0	1046.1	1052.7	1064.2
20°	994.7	991.4	992.6	984.0	992.6	991.4	994.7	1000.7	1012.8	1016.2	1028.2
22.5°	965.2	958.6	957.8	956.1	957.8	958.6	965.2	970.6	973.1	983.4	991.7
25°	918.9	915.5	912.1	915.5	912.1	915.5	918.9	924.9	927.6	935.0	943.0
27.5°	878.4	874.4	873.5	873.8	873.5	874.4	878.4	877.9	885.1	891.0	897.0
30°	853.8	847.1	847.7	847.1	847.7	847.1	853.8	853.8	857.7	863.2	868.5
32.5°	826.9	822.3	821.4	820.2	821.4	822.3	826.9	825.8	830.9	837.3	843.3
35°	787.3	787.3	783.9	783.9	783.9	787.3	787.3	789.3	794.7	794.7	801.3
37.5°	750.1	749.4	747.4	747.7	747.4	749.4	750.1	751.7	753.5	756.4	760.7
40°	722.2	721.5	719.5	715.5	719.5	721.5	722.2	724.9	726.2	729.5	732.3
42.5°	695.3	693.0	692.1	690.8	692.1	693.0	695.3	697.0	697.8	702.1	707.6
45°	653.1	653.1	651.7	651.0	651.7	653.1	653.1	653.1	653.8	659.1	661.8
47.5°	612.0	613.2	615.7	615.4	615.7	613.2	612.0	610.9	611.1	613.9	616.9
50°	587.3	588.0	590.0	590.6	590.0	588.0	587.3	584.6	583.2	583.2	585.2
52.5°	559.9	563.8	566.4	565.9	566.4	563.8	559.9	557.8	555.3	552.1	555.2
55°	521.5	526.2	530.9	531.6	530.9	526.2	521.5	515.5	512.8	507.4	509.5
57.5°	483.5	490.1	495.1	496.6	495.1	490.1	483.5	476.2	467.5	465.0	461.2
60°	457.7	466.5	472.5	475.2	472.5	466.5	457.7	451.0	439.6	432.2	429.6
62.5°	433.0	442.8	448.8	449.4	448.8	442.8	433.0	422.6	411.1	402.7	397.4
65°	392.6	402.7	408.0	412.1	408.0	402.7	392.6	381.3	368.5	357.1	351.0
67.5°	349.1	359.2	365.2	368.3	365.2	359.2	349.1	335.0	323.4	310.2	303.1
70°	317.5	327.5	335.6	338.3	335.6	327.5	317.5	300.7	290.6	278.5	272.5
72.5°	286.3	295.3	301.8	305.0	301.8	295.3	286.3	270.6	258.9	246.8	238.7
75°	232.2	244.3	250.4	253.7	250.4	244.3	232.2	223.5	210.1	197.3	190.6
77.5°	179.1	190.1	193.7	195.4	193.7	190.1	179.1	168.8	158.7	149.4	142.8
80°	143.6	150.3	155.1	155.7	155.1	150.3	143.6	135.6	127.5	118.8	112.8
82.5°	110.4	116.0	117.4	119.2	117.4	116.0	110.4	103.3	96.3	89.8	84.8
85°	60.4	63.1	63.8	63.1	63.8	63.1	60.4	55.7	52.3	49.0	47.0
87.5°	23.7	23.2	23.3	24.5	23.3	23.2	23.7	22.5	22.8	21.6	20.3
90°	18.9	19.5	20.1	20.7	20.1	19.5	18.9	18.3	17.6	16.6	15.7
92.5°	18.4	18.7	19.0	19.3	19.0	18.7	18.4	18.2	17.6	16.6	15.7
95°	18.1	18.1	18.1	18.1	18.1	18.1	18.1	18.1	17.6	16.6	15.7
97.5°	18.1	18.1	18.1	18.1	18.1	18.1	18.1	18.1	20.8	26.2	31.5
100°	20.3	19.5	18.9	18.1	18.9	19.5	20.3	21.1	35.7	64.2	92.6
102.5°	147.1	134.1	121.1	108.1	121.1	134.1	147.1	160.1	169.3	174.7	180.0
105°	255.9	255.7	255.5	255.3	255.5	255.7	255.9	256.1	256.1	256.1	256.1
107.5°	323.6	323.0	322.4	321.8	322.4	323.0	323.6	324.2	324.4	324.4	324.3
110°	367.4	367.6	367.7	367.9	367.7	367.6	367.4	367.2	367.4	367.9	368.5



TEST NUMBER: P333322-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	410.0	409.7	409.5	409.2	409.5	409.7	410.0	410.3	410.8	411.5	412.2
115°	474.6	473.4	472.3	471.1	472.3	473.4	474.6	475.7	476.6	477.4	478.2
117.5°	538.6	538.1	537.6	537.1	537.6	538.1	538.6	539.1	539.8	540.9	541.8
120°	580.6	579.6	578.7	577.7	578.7	579.6	580.6	581.5	582.2	582.6	583.0
122.5°	619.6	618.5	617.3	616.2	617.3	618.5	619.6	620.6	621.4	621.8	622.2
125°	676.6	676.0	675.5	674.9	675.5	676.0	676.6	677.2	677.8	678.6	679.3
127.5°	728.4	727.0	725.7	724.2	725.7	727.0	728.4	729.9	730.7	731.2	731.6
130°	762.8	761.9	761.0	759.9	761.0	761.9	762.8	763.8	764.6	765.1	765.7
132.5°	795.8	794.9	793.9	793.0	793.9	794.9	795.8	796.8	797.3	797.5	797.5
135°	841.6	840.5	839.3	838.2	839.3	840.5	841.6	842.7	843.5	844.0	844.3
137.5°	886.6	885.5	884.6	883.6	884.6	885.5	886.6	887.5	888.0	887.9	887.9
140°	913.9	912.7	911.5	910.4	911.5	912.7	913.9	915.0	915.3	915.0	914.6
142.5°	939.3	938.1	937.0	935.8	937.0	938.1	939.3	940.5	941.0	940.9	940.8
145°	976.6	975.4	974.3	973.2	974.3	975.4	976.6	977.8	978.2	978.0	977.8
147.5°	1008.1	1006.7	1005.3	1003.9	1005.3	1006.7	1008.1	1009.4	1010.0	1009.8	1009.5
150°	1028.5	1026.9	1025.4	1023.9	1025.4	1026.9	1028.5	1030.0	1030.5	1030.2	1029.8
152.5°	1046.5	1045.2	1043.8	1042.4	1043.8	1045.2	1046.5	1047.9	1048.4	1048.1	1047.7
155°	1071.4	1069.9	1068.4	1066.9	1068.4	1069.9	1071.4	1073.0	1073.5	1072.9	1072.3
157.5°	1091.9	1090.4	1088.8	1087.4	1088.8	1090.4	1091.9	1093.5	1093.9	1093.3	1092.7
160°	1105.0	1103.5	1101.9	1100.4	1101.9	1103.5	1105.0	1106.5	1106.9	1106.1	1105.4
162.5°	1117.1	1115.4	1113.8	1112.1	1113.8	1115.4	1117.1	1118.8	1119.1	1118.0	1117.0
165°	1132.5	1130.9	1129.5	1127.9	1129.5	1130.9	1132.5	1134.0	1134.2	1133.1	1131.9
167.5°	1144.1	1142.4	1140.7	1138.9	1140.7	1142.4	1144.1	1145.8	1146.0	1144.6	1143.2
170°	1150.2	1148.6	1146.9	1145.1	1146.9	1148.6	1150.2	1151.9	1152.1	1150.6	1149.0
172.5°	1154.3	1152.6	1150.9	1149.3	1150.9	1152.6	1154.3	1156.1	1156.2	1154.9	1153.5
175°	1159.7	1158.0	1156.2	1154.5	1156.2	1158.0	1159.7	1161.4	1161.5	1160.0	1158.5
177.5°	1161.3	1160.1	1158.9	1157.6	1158.9	1160.1	1161.3	1162.5	1162.6	1161.6	1160.5
180°	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7



TEST NUMBER: P333322-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1512.0	1518.5	1526.5	1532.4	1543.2	1548.0	1553.8	1558.8	1567.3	1575.4	1585.0
5°	1410.1	1421.5	1437.0	1453.7	1473.3	1486.6	1505.5	1516.8	1539.6	1560.5	1580.6
7.5°	1317.8	1331.7	1353.6	1375.1	1400.6	1423.7	1447.2	1473.3	1502.4	1536.7	1565.1
10°	1254.4	1273.2	1296.7	1323.5	1354.4	1381.3	1412.8	1441.0	1476.5	1516.8	1554.4
12.5°	1203.9	1220.0	1246.2	1272.0	1305.0	1337.7	1370.4	1407.7	1449.1	1493.7	1541.0
15°	1134.3	1147.7	1169.2	1204.7	1238.3	1270.5	1319.5	1354.4	1406.8	1456.5	1513.5
17.5°	1074.8	1091.5	1109.6	1140.1	1174.8	1215.0	1258.9	1302.6	1353.1	1416.0	1480.3
20°	1038.3	1051.7	1072.5	1096.1	1132.9	1173.2	1214.8	1259.1	1320.9	1386.0	1455.1
22.5°	998.6	1013.1	1036.6	1062.2	1093.2	1131.9	1177.8	1226.3	1290.8	1354.8	1429.9
25°	951.7	961.8	983.3	1006.1	1037.0	1069.9	1117.5	1171.2	1234.9	1308.1	1384.7
27.5°	907.6	916.4	936.0	955.9	983.8	1022.9	1065.4	1119.6	1179.7	1253.9	1338.7
30°	875.9	885.3	902.8	924.2	951.1	985.2	1028.9	1080.0	1144.4	1216.9	1305.4
32.5°	848.5	856.8	870.0	891.5	917.7	950.9	991.4	1043.4	1107.8	1181.4	1268.3
35°	806.1	815.5	825.5	842.3	865.1	897.3	941.7	990.7	1052.4	1123.5	1203.4
37.5°	764.0	774.1	783.1	798.1	819.0	847.4	885.7	936.7	992.6	1061.1	1137.7
40°	737.6	745.6	753.0	769.1	790.0	816.8	852.4	898.0	957.1	1020.9	1084.6
42.5°	711.3	718.8	725.1	739.1	758.3	784.0	818.0	862.5	917.4	976.8	1033.0
45°	669.9	674.5	681.9	694.0	709.5	732.9	765.8	805.4	851.7	908.1	950.4
47.5°	625.0	632.4	638.4	649.0	661.7	684.8	716.3	749.9	791.9	833.9	863.7
50°	590.6	598.1	606.7	616.8	628.9	650.4	679.2	713.4	749.0	781.3	806.8
52.5°	558.4	565.2	574.5	584.0	598.8	617.1	641.6	672.1	707.1	730.2	751.5
55°	510.7	514.1	524.9	534.3	548.4	561.8	586.6	613.5	634.9	652.4	669.9
57.5°	462.0	466.6	472.8	481.2	495.2	510.9	528.3	552.1	564.7	573.7	587.3
60°	430.9	432.2	436.3	446.3	457.1	471.1	491.3	508.1	517.5	524.9	536.2
62.5°	396.5	396.8	403.5	410.9	419.0	434.1	450.5	464.1	471.8	475.4	486.3
65°	348.4	347.0	351.0	357.1	366.4	376.5	390.6	402.7	402.0	406.0	412.8
67.5°	299.1	297.7	297.7	303.5	311.2	320.1	329.8	336.8	336.9	342.3	345.7
70°	265.8	261.7	264.4	269.1	272.5	279.9	290.6	293.3	293.9	296.6	300.0
72.5°	231.4	230.1	232.2	234.3	236.5	242.3	251.4	253.0	253.1	254.8	260.3
75°	183.9	182.5	181.2	183.2	185.9	189.9	193.3	196.0	195.3	196.0	200.0
77.5°	137.8	134.1	133.5	134.5	135.2	137.6	141.1	140.8	141.5	141.4	145.9
80°	109.4	104.0	103.3	103.3	104.0	105.4	106.7	108.1	106.1	108.1	109.4
82.5°	80.4	77.1	77.1	76.5	76.6	76.9	77.7	78.5	78.1	79.0	79.9
85°	44.3	43.0	41.0	42.3	41.6	39.6	41.0	38.9	38.2	38.9	39.6
87.5°	18.0	18.3	17.0	16.7	15.9	16.2	14.8	13.9	13.2	13.3	14.6
90°	14.7	13.8	12.4	11.1	9.7	8.4	7.0	5.4	3.9	2.4	0.9
92.5°	14.7	13.8	12.6	11.4	10.2	9.0	9.0	10.0	11.1	12.1	13.3
95°	14.7	13.8	21.0	28.2	35.6	42.8	46.8	47.3	47.9	48.4	49.0
97.5°	36.9	42.3	56.7	71.0	85.4	99.8	106.4	105.4	104.4	103.3	102.3
100°	121.1	149.6	148.8	148.1	147.3	146.5	145.9	145.3	144.7	144.1	143.5
102.5°	185.5	190.9	190.4	189.9	189.5	189.0	188.4	187.7	187.0	186.2	185.5
105°	256.1	256.1	256.1	256.1	256.1	256.1	255.8	255.0	254.3	253.5	252.7
107.5°	324.3	324.3	323.9	323.5	323.1	322.7	322.5	322.5	322.5	322.5	322.5
110°	369.1	369.6	369.3	368.9	368.5	368.2	367.9	367.9	367.9	367.9	367.9



TEST NUMBER: P333322-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	412.9	413.7	413.5	413.2	413.0	412.8	412.4	412.0	411.5	411.0	410.6
115°	479.0	479.7	479.5	479.3	479.1	479.0	478.4	477.4	476.5	475.5	474.6
117.5°	542.9	543.8	543.1	542.3	541.7	541.0	540.6	540.6	540.6	540.7	540.7
120°	583.3	583.8	583.2	582.6	582.0	581.4	581.3	581.4	581.6	581.8	582.0
122.5°	622.5	622.9	622.7	622.4	622.2	621.8	621.4	620.6	619.9	619.1	618.5
125°	680.1	680.9	680.9	680.9	680.9	680.9	680.2	678.9	677.5	676.1	674.9
127.5°	732.0	732.5	732.5	732.7	732.8	732.9	732.5	731.5	730.6	729.6	728.7
130°	766.3	766.8	766.6	766.5	766.3	766.0	765.5	764.6	763.6	762.7	761.6
132.5°	797.6	797.8	798.2	798.7	799.0	799.4	799.1	798.0	796.9	795.8	794.7
135°	844.6	845.1	845.4	845.8	846.2	846.6	846.2	845.1	844.0	842.7	841.6
137.5°	887.8	887.7	888.0	888.4	888.7	889.1	888.7	887.8	886.7	885.8	884.8
140°	914.2	913.9	914.0	914.2	914.4	914.6	914.5	914.1	913.8	913.3	913.0
142.5°	940.7	940.6	940.4	940.1	939.9	939.6	939.4	939.1	938.9	938.7	938.4
145°	977.7	977.5	977.5	977.5	977.5	977.5	977.2	976.9	976.5	976.1	975.8
147.5°	1009.4	1009.1	1008.8	1008.7	1008.4	1008.1	1008.1	1008.1	1008.2	1008.3	1008.4
150°	1029.4	1029.1	1028.6	1028.3	1027.9	1027.5	1027.5	1027.9	1028.3	1028.6	1029.1
152.5°	1047.3	1046.9	1046.5	1046.1	1045.8	1045.4	1045.6	1046.5	1047.3	1048.2	1049.0
155°	1071.8	1071.2	1070.7	1070.4	1070.1	1069.6	1070.1	1071.2	1072.3	1073.5	1074.6
157.5°	1092.1	1091.5	1091.4	1091.4	1091.3	1091.3	1091.7	1092.4	1093.0	1093.6	1094.3
160°	1104.6	1103.8	1103.6	1103.5	1103.3	1103.0	1103.5	1104.7	1105.9	1107.0	1108.1
162.5°	1115.9	1114.8	1114.7	1114.5	1114.2	1114.0	1114.6	1115.7	1116.8	1118.0	1119.1
165°	1130.8	1129.6	1129.5	1129.2	1129.0	1128.9	1129.4	1130.5	1131.6	1132.7	1133.9
167.5°	1141.9	1140.5	1140.2	1140.1	1139.9	1139.7	1140.2	1141.3	1142.5	1143.8	1145.0
170°	1147.5	1146.0	1145.7	1145.6	1145.4	1145.2	1145.7	1147.1	1148.4	1149.8	1151.1
172.5°	1152.1	1150.7	1150.4	1150.0	1149.7	1149.4	1149.9	1151.2	1152.5	1153.9	1155.2
175°	1156.9	1155.4	1155.2	1155.0	1154.9	1154.7	1155.1	1156.2	1157.4	1158.6	1159.7
177.5°	1159.4	1158.3	1158.2	1158.0	1157.9	1157.7	1158.1	1159.0	1159.9	1160.9	1161.7
180°	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7



TEST NUMBER: P333322-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1589.8	1597.4	1602.2	1611.4	1618.9	1623.2	1626.9	1630.1	1633.9	1637.1	1646.2
5°	1600.1	1617.5	1632.3	1655.1	1675.9	1692.0	1709.4	1724.9	1737.7	1755.8	1769.9
7.5°	1595.6	1626.6	1659.1	1694.4	1730.5	1764.1	1795.0	1823.9	1850.0	1881.7	1909.4
10°	1591.3	1633.7	1675.2	1722.9	1771.9	1813.5	1852.4	1892.0	1920.9	1961.2	1995.4
12.5°	1588.1	1637.9	1688.2	1745.4	1799.2	1858.0	1909.9	1938.7	1982.6	2014.8	2055.6
15°	1574.6	1640.4	1709.4	1773.9	1850.4	1904.8	1950.4	2006.8	2047.7	2088.7	2133.0
17.5°	1550.2	1624.8	1702.1	1786.5	1859.9	1918.3	1977.1	2031.5	2080.3	2135.3	2190.4
20°	1539.0	1613.5	1702.1	1788.6	1860.4	1921.6	1981.9	2041.7	2095.4	2165.8	2229.6
22.5°	1515.4	1605.4	1687.0	1771.5	1845.5	1911.9	1980.4	2048.1	2119.5	2199.2	2279.0
25°	1473.3	1564.5	1651.1	1734.3	1808.8	1892.0	1965.1	2055.8	2147.1	2252.5	2351.7
27.5°	1429.4	1516.8	1596.2	1676.5	1763.4	1857.7	1952.6	2055.4	2174.9	2307.9	2448.0
30°	1394.0	1476.5	1553.8	1636.3	1726.9	1833.0	1937.0	2059.2	2197.4	2347.1	2513.5
32.5°	1352.6	1428.7	1503.8	1591.2	1689.9	1801.8	1923.0	2057.0	2223.2	2393.2	2564.6
35°	1281.9	1345.7	1422.9	1516.1	1627.5	1755.8	1896.1	2054.4	2245.1	2440.3	2584.6
37.5°	1198.0	1257.4	1338.7	1441.0	1557.8	1695.4	1861.8	2049.8	2252.2	2407.9	2454.5
40°	1141.7	1196.7	1281.3	1387.3	1506.8	1652.4	1835.0	2033.7	2229.6	2328.9	2290.7
42.5°	1081.5	1139.3	1221.7	1326.6	1455.3	1613.8	1801.1	1999.8	2164.1	2201.7	2069.5
45°	986.6	1046.4	1127.6	1233.6	1371.8	1543.7	1739.0	1919.5	2014.1	1946.4	1741.7
47.5°	898.5	954.4	1029.7	1139.1	1281.8	1459.5	1647.6	1791.7	1799.1	1637.4	1418.8
50°	838.3	889.9	965.8	1075.2	1216.9	1396.7	1566.5	1679.9	1628.9	1445.7	1235.6
52.5°	779.2	829.8	904.6	1013.0	1153.0	1317.8	1475.8	1555.4	1459.2	1271.2	1091.7
55°	694.0	738.3	811.4	911.5	1044.3	1197.4	1331.6	1359.1	1234.2	1049.0	903.4
57.5°	610.8	652.1	718.7	810.8	932.3	1067.8	1172.8	1166.9	1034.9	876.0	760.4
60°	554.4	594.7	653.8	743.6	854.4	971.2	1061.1	1039.7	908.8	771.9	674.5
62.5°	503.9	539.8	595.7	674.4	775.5	883.6	957.5	925.8	797.6	677.9	601.0
65°	429.6	459.8	507.4	574.5	658.4	747.7	804.7	763.8	654.4	561.1	499.4
67.5°	358.5	382.7	422.7	476.2	547.8	619.5	654.3	613.0	525.6	457.4	411.7
70°	313.4	334.9	365.8	413.5	475.9	536.2	562.4	525.6	450.4	391.9	359.0
72.5°	268.4	286.0	313.1	356.0	406.0	458.4	481.4	446.1	384.4	335.0	304.3
75°	207.4	219.5	238.2	267.8	307.4	349.0	361.8	330.9	291.3	254.3	234.3
77.5°	148.4	158.7	172.9	191.6	219.6	246.1	257.2	239.4	208.7	185.4	168.8
80°	114.1	119.5	131.6	147.0	169.1	185.9	193.3	181.9	160.4	142.9	130.2
82.5°	81.4	86.7	93.9	106.7	120.8	132.2	140.2	132.5	116.9	103.2	95.8
85°	39.6	43.0	47.0	52.3	63.1	69.8	69.1	64.4	58.4	53.0	49.0
87.5°	14.5	15.2	17.2	20.1	22.1	24.5	25.8	25.1	23.2	21.7	20.3
90°	2.4	3.9	5.4	7.0	8.4	9.7	11.1	12.4	13.8	14.7	15.7
92.5°	12.1	11.1	10.0	9.0	9.0	10.2	11.4	12.6	13.8	14.7	15.7
95°	48.4	47.9	47.3	46.8	42.8	35.6	28.2	21.0	13.8	14.7	15.7
97.5°	103.3	104.4	105.4	106.4	99.8	85.4	71.0	56.7	42.3	36.9	31.5
100°	144.1	144.7	145.3	145.9	146.5	147.3	148.1	148.8	149.6	121.1	92.6
102.5°	186.2	187.0	187.7	188.4	189.0	189.5	189.9	190.4	190.9	185.5	180.0
105°	253.5	254.3	255.0	255.8	256.1	256.1	256.1	256.1	256.1	256.1	256.1
107.5°	322.5	322.5	322.5	322.5	322.7	323.1	323.5	323.9	324.3	324.3	324.3
110°	367.9	367.9	367.9	367.9	368.2	368.5	368.9	369.3	369.6	369.1	368.5



TEST NUMBER: P333322-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	411.0	411.5	412.0	412.4	412.8	413.0	413.2	413.5	413.7	412.9	412.2
115°	475.5	476.5	477.4	478.4	479.0	479.1	479.3	479.5	479.7	479.0	478.2
117.5°	540.7	540.6	540.6	540.6	541.0	541.7	542.3	543.1	543.8	542.9	541.8
120°	581.8	581.6	581.4	581.3	581.4	582.0	582.6	583.2	583.8	583.3	583.0
122.5°	619.1	619.9	620.6	621.4	621.8	622.2	622.4	622.7	622.9	622.5	622.2
125°	676.1	677.5	678.9	680.2	680.9	680.9	680.9	680.9	680.9	680.1	679.3
127.5°	729.6	730.6	731.5	732.5	732.9	732.8	732.7	732.5	732.5	732.0	731.6
130°	762.7	763.6	764.6	765.5	766.0	766.3	766.5	766.6	766.8	766.3	765.7
132.5°	795.8	796.9	798.0	799.1	799.4	799.0	798.7	798.2	797.8	797.6	797.5
135°	842.7	844.0	845.1	846.2	846.6	846.2	845.8	845.4	845.1	844.6	844.3
137.5°	885.8	886.7	887.8	888.7	889.1	888.7	888.4	888.0	887.7	887.8	887.9
140°	913.3	913.8	914.1	914.5	914.6	914.4	914.2	914.0	913.9	914.2	914.6
142.5°	938.7	938.9	939.1	939.4	939.6	939.9	940.1	940.4	940.6	940.7	940.8
145°	976.1	976.5	976.9	977.2	977.5	977.5	977.5	977.5	977.5	977.7	977.8
147.5°	1008.3	1008.2	1008.1	1008.1	1008.1	1008.4	1008.7	1008.8	1009.1	1009.4	1009.5
150°	1028.6	1028.3	1027.9	1027.5	1027.5	1027.9	1028.3	1028.6	1029.1	1029.4	1029.8
152.5°	1048.2	1047.3	1046.5	1045.6	1045.4	1045.8	1046.1	1046.5	1046.9	1047.3	1047.7
155°	1073.5	1072.3	1071.2	1070.1	1069.6	1070.1	1070.4	1070.7	1071.2	1071.8	1072.3
157.5°	1093.6	1093.0	1092.4	1091.7	1091.3	1091.3	1091.4	1091.4	1091.5	1092.1	1092.7
160°	1107.0	1105.9	1104.7	1103.5	1103.0	1103.3	1103.5	1103.6	1103.8	1104.6	1105.4
162.5°	1118.0	1116.8	1115.7	1114.6	1114.0	1114.2	1114.5	1114.7	1114.8	1115.9	1117.0
165°	1132.7	1131.6	1130.5	1129.4	1128.9	1129.0	1129.2	1129.5	1129.6	1130.8	1131.9
167.5°	1143.8	1142.5	1141.3	1140.2	1139.7	1139.9	1140.1	1140.2	1140.5	1141.9	1143.2
170°	1149.8	1148.4	1147.1	1145.7	1145.2	1145.4	1145.6	1145.7	1146.0	1147.5	1149.0
172.5°	1153.9	1152.5	1151.2	1149.9	1149.4	1149.7	1150.0	1150.4	1150.7	1152.1	1153.5
175°	1158.6	1157.4	1156.2	1155.1	1154.7	1154.9	1155.0	1155.2	1155.4	1156.9	1158.5
177.5°	1160.9	1159.9	1159.0	1158.1	1157.7	1157.9	1158.0	1158.2	1158.3	1159.4	1160.5
180°	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7



TEST NUMBER: P333322-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1653.7	1658.0	1667.2	1664.0	1668.3	1670.4	1672.6
5°	1787.3	1808.8	1818.2	1816.9	1830.9	1827.6	1824.2
7.5°	1938.2	1960.8	1973.4	1989.1	1998.2	1998.9	2006.8
10°	2023.6	2053.1	2065.2	2082.0	2092.7	2098.8	2098.1
12.5°	2089.0	2112.2	2139.2	2147.5	2162.0	2169.6	2166.8
15°	2167.9	2204.8	2233.0	2247.0	2265.2	2270.5	2277.9
17.5°	2238.3	2287.8	2320.7	2364.4	2380.9	2391.0	2385.1
20°	2291.4	2356.5	2389.4	2441.7	2470.6	2486.1	2480.6
22.5°	2354.2	2424.7	2485.4	2530.8	2574.7	2595.6	2599.9
25°	2461.9	2558.5	2647.7	2707.5	2761.8	2774.6	2802.8
27.5°	2582.1	2696.0	2791.5	2854.4	2892.2	2906.4	2915.3
30°	2657.8	2771.2	2843.1	2883.3	2895.5	2894.1	2892.7
32.5°	2694.8	2765.9	2779.7	2768.5	2740.8	2717.4	2693.0
35°	2642.4	2589.4	2510.2	2408.1	2333.0	2257.1	2249.8
37.5°	2376.4	2206.9	2075.1	1927.9	1842.9	1790.4	1754.2
40°	2126.2	1933.6	1773.9	1649.8	1563.1	1529.0	1495.4
42.5°	1854.6	1670.5	1529.0	1425.3	1360.2	1322.2	1295.6
45°	1506.8	1344.4	1233.6	1158.5	1106.7	1077.2	1060.4
47.5°	1234.7	1114.6	1020.5	966.2	930.5	907.6	907.7
50°	1088.6	973.9	911.5	868.5	837.6	819.5	822.9
52.5°	959.2	873.5	820.2	784.2	761.4	750.2	749.8
55°	802.0	740.3	705.4	679.2	663.7	651.0	653.8
57.5°	686.0	634.0	610.6	588.9	578.2	573.1	565.7
60°	614.2	573.9	553.7	536.2	525.6	521.5	514.1
62.5°	550.3	518.6	498.9	484.7	475.0	473.7	468.0
65°	462.4	438.2	420.9	414.1	404.1	401.4	401.4
67.5°	381.3	363.9	350.3	344.1	339.8	340.4	337.2
70°	330.2	316.2	307.4	300.7	297.3	298.0	295.3
72.5°	288.9	273.2	265.5	261.5	257.1	258.8	257.7
75°	218.8	210.8	206.7	202.7	200.0	198.6	197.3
77.5°	160.7	153.6	150.5	148.2	148.6	145.3	147.9
80°	124.2	118.1	116.1	112.8	112.1	112.1	111.4
82.5°	90.8	87.5	86.0	83.3	82.1	83.1	81.4
85°	47.0	44.3	43.7	43.7	42.3	41.0	44.3
87.5°	20.5	18.5	18.7	18.3	18.4	18.0	17.0
90°	16.6	17.6	18.3	18.9	19.5	20.1	20.7
92.5°	16.6	17.6	18.2	18.4	18.7	19.0	19.3
95°	16.6	17.6	18.1	18.1	18.1	18.1	18.1
97.5°	26.2	20.8	18.1	18.1	18.1	18.1	18.1
100°	64.2	35.7	21.1	20.3	19.5	18.9	18.1
102.5°	174.7	169.3	160.1	147.1	134.1	121.1	108.1
105°	256.1	256.1	256.1	255.9	255.7	255.5	255.3
107.5°	324.4	324.4	324.2	323.6	323.0	322.4	321.8
110°	367.9	367.4	367.2	367.4	367.6	367.7	367.9



TEST NUMBER: P333322-935

CATALOG NUMBER: S125DIP-S1270D1035U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	411.5	410.8	410.3	410.0	409.7	409.5	409.2
115°	477.4	476.6	475.7	474.6	473.4	472.3	471.1
117.5°	540.9	539.8	539.1	538.6	538.1	537.6	537.1
120°	582.6	582.2	581.5	580.6	579.6	578.7	577.7
122.5°	621.8	621.4	620.6	619.6	618.5	617.3	616.2
125°	678.6	677.8	677.2	676.6	676.0	675.5	674.9
127.5°	731.2	730.7	729.9	728.4	727.0	725.7	724.2
130°	765.1	764.6	763.8	762.8	761.9	761.0	759.9
132.5°	797.5	797.3	796.8	795.8	794.9	793.9	793.0
135°	844.0	843.5	842.7	841.6	840.5	839.3	838.2
137.5°	887.9	888.0	887.5	886.6	885.5	884.6	883.6
140°	915.0	915.3	915.0	913.9	912.7	911.5	910.4
142.5°	940.9	941.0	940.5	939.3	938.1	937.0	935.8
145°	978.0	978.2	977.8	976.6	975.4	974.3	973.2
147.5°	1009.8	1010.0	1009.4	1008.1	1006.7	1005.3	1003.9
150°	1030.2	1030.5	1030.0	1028.5	1026.9	1025.4	1023.9
152.5°	1048.1	1048.4	1047.9	1046.5	1045.2	1043.8	1042.4
155°	1072.9	1073.5	1073.0	1071.4	1069.9	1068.4	1066.9
157.5°	1093.3	1093.9	1093.5	1091.9	1090.4	1088.8	1087.4
160°	1106.1	1106.9	1106.5	1105.0	1103.5	1101.9	1100.4
162.5°	1118.0	1119.1	1118.8	1117.1	1115.4	1113.8	1112.1
165°	1133.1	1134.2	1134.0	1132.5	1130.9	1129.5	1127.9
167.5°	1144.6	1146.0	1145.8	1144.1	1142.4	1140.7	1138.9
170°	1150.6	1152.1	1151.9	1150.2	1148.6	1146.9	1145.1
172.5°	1154.9	1156.2	1156.1	1154.3	1152.6	1150.9	1149.3
175°	1160.0	1161.5	1161.4	1159.7	1158.0	1156.2	1154.5
177.5°	1161.6	1162.6	1162.5	1161.3	1160.1	1158.9	1157.6
180°	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7

(END OF REPORT)