

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333567-927

Luminaire Tested: **S125RDIP-S850D810U927-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333567-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S850D810U927-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4879.0 lumens
Efficiency: N/A
Efficacy: 106.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333567-927

CATALOG NUMBER: S125RDIP-S850D810U927-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333567-927

CATALOG NUMBER: S125RDIP-S850D810U927-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	94	91	87	91	88	84	81	75	72	70	63	61	60	52	51	50	45
2	90	83	77	72	83	77	72	67	66	62	58	56	53	50	46	44	42	38
3	82	73	66	60	76	68	61	56	58	53	49	49	46	43	41	39	36	32
4	75	65	57	51	70	60	53	48	52	47	42	44	40	37	37	34	31	28
5	69	58	50	44	64	54	47	41	46	41	37	40	35	32	33	30	28	24
6	64	52	44	38	59	48	41	36	42	36	32	36	32	28	30	27	24	22
7	59	47	39	33	55	44	37	32	38	32	28	33	28	25	28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	25	22	20	17
9	51	39	31	26	47	37	30	25	32	26	23	28	23	20	24	20	18	16
10	48	36	29	24	44	34	27	23	29	24	20	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7035	7035	7035
5°	7052	6971	7014
10°	6998	6906	6906
15°	6915	6766	6711
20°	6808	6570	6491
25°	6683	6379	6238
30°	6528	6154	5957
35°	6370	5922	5643
40°	6222	5681	5334
45°	6042	5411	4997
50°	5861	5117	4646
55°	5650	4835	4271
60°	5441	4495	3867
65°	5193	4099	3406
70°	4910	3603	2936
75°	4517	3039	2443
80°	3976	2388	2049
85°	3349	1949	1830



TEST NUMBER: P333567-927

CATALOG NUMBER: S125RDIP-S850D810U927-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.4	2.1
10°-20°	286.2	5.9
20°-30°	415.1	8.5
30°-40°	473.1	9.7
40°-50°	461.1	9.5
50°-60°	388.2	8.0
60°-70°	272.1	5.6
70°-80°	139.9	2.9
80°-90°	37.0	0.8
90°-100°	222.7	4.6
100°-110°	478.7	9.8
110°-120°	449.3	9.2
120°-130°	364.1	7.5
130°-140°	292.2	6.0
140°-150°	220.5	4.5
150°-160°	155.2	3.2
160°-170°	91.5	1.9
170°-180°	29.8	0.6
0°-30°	803.8	16.5
0°-40°	1276.8	26.2
0°-60°	2126.1	43.6
0°-90°	2575.1	52.8
90°-120°	1150.7	23.6
90°-150°	2027.5	41.6
90°-180°	2304.0	47.2
0°-180°	4879.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1089	1089	1089	1089	1089	
5°	1088	1084	1075	1083	1082	103
15°	1034	1029	1012	1011	1004	291
25°	938	925	895	885	875	431
35°	808	787	751	728	716	506
45°	662	636	592	561	547	510
55°	502	474	429	394	379	449
65°	340	311	268	236	223	336
75°	181	156	122	104	98	192
85°	45	31	26	26	25	51
90°	1	6	10	13	14	3
95°	20	60	549	249	146	22
105°	70	98	449	884	821	74
115°	125	151	360	777	914	123
125°	173	203	346	618	720	154
135°	203	244	343	518	598	158
145°	237	271	344	429	472	148
155°	270	290	336	379	396	124
165°	295	303	322	342	347	83
175°	307	307	309	313	312	29
180°	307	307	307	307	307	



TEST NUMBER: P333567-927

CATALOG NUMBER: S125RDIP-S850D810U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3
2.5°	1091.2	1090.8	1090.4	1090.0	1089.5	1088.5	1087.1	1085.6	1084.2	1082.7	1084.2
5°	1087.7	1087.0	1086.2	1085.4	1084.7	1083.4	1081.3	1079.3	1077.3	1075.3	1077.1
7.5°	1077.0	1076.3	1075.5	1074.8	1074.2	1072.6	1070.2	1067.8	1065.4	1063.0	1064.2
10°	1067.1	1066.5	1066.0	1065.4	1064.9	1063.3	1060.8	1058.2	1055.7	1053.1	1053.6
12.5°	1055.9	1055.2	1054.5	1053.8	1053.1	1051.1	1047.6	1044.2	1040.8	1037.3	1037.7
15°	1034.2	1033.1	1032.0	1030.9	1029.8	1027.3	1023.5	1019.6	1015.8	1011.9	1011.8
17.5°	1009.6	1008.0	1006.3	1004.6	1002.9	999.7	994.8	990.0	985.2	980.3	979.5
20°	990.5	988.7	986.9	985.1	983.3	979.4	973.6	967.7	961.9	956.0	955.1
22.5°	969.5	967.7	965.8	964.0	962.2	958.2	952.0	945.9	939.8	933.7	931.8
25°	937.9	935.2	932.4	929.7	926.9	922.2	915.4	908.6	901.9	895.2	892.8
27.5°	901.7	898.4	895.1	891.8	888.4	883.1	875.9	868.6	861.4	854.1	850.8
30°	875.4	871.9	868.5	865.0	861.5	855.9	848.3	840.6	832.9	825.2	821.0
32.5°	849.7	845.7	841.6	837.6	833.5	827.5	819.8	811.9	804.1	796.2	791.6
35°	807.9	803.5	799.2	794.7	790.4	784.0	775.9	767.6	759.4	751.1	745.8
37.5°	766.9	761.6	756.3	750.9	745.6	738.7	730.2	721.7	713.2	704.7	698.4
40°	738.0	732.5	727.0	721.5	716.1	708.9	700.1	691.3	682.6	673.8	666.9
42.5°	707.7	702.1	696.5	690.8	685.2	677.9	668.8	659.7	650.6	641.6	634.9
45°	661.5	656.2	650.9	645.5	640.2	632.6	622.5	612.5	602.5	592.4	585.0
47.5°	613.6	608.0	602.4	596.8	591.2	583.4	573.2	563.1	552.9	542.8	535.3
50°	583.3	577.3	571.2	565.2	559.2	551.0	540.5	530.1	519.7	509.3	501.6
52.5°	550.4	544.2	538.1	531.9	525.7	517.7	507.9	498.0	488.1	478.3	470.1
55°	501.8	496.0	490.2	484.3	478.5	470.4	460.2	450.0	439.7	429.4	421.2
57.5°	452.8	446.6	440.3	434.0	427.9	419.8	409.9	400.0	390.1	380.2	372.2
60°	421.2	414.9	408.4	402.0	395.6	387.5	377.6	367.7	357.9	348.0	340.0
62.5°	387.7	381.6	375.5	369.3	363.2	355.2	345.2	335.2	325.1	315.1	307.7
65°	339.8	333.6	327.3	321.2	314.9	307.0	297.3	287.6	277.9	268.2	260.9
67.5°	292.2	286.0	279.8	273.6	267.4	259.6	250.3	241.1	231.8	222.4	215.8
70°	260.0	253.7	247.6	241.3	235.1	227.4	218.3	209.1	200.0	190.8	185.2
72.5°	228.4	222.3	216.3	210.2	204.1	196.8	188.2	179.7	171.1	162.6	157.3
75°	181.0	175.5	170.0	164.5	159.1	152.5	144.8	137.1	129.4	121.8	117.7
77.5°	134.0	129.5	125.2	120.8	116.4	111.1	105.0	98.9	92.7	86.6	83.7
80°	106.9	102.6	98.2	93.8	89.4	84.7	79.5	74.4	69.3	64.2	62.5
82.5°	80.6	76.7	72.7	68.8	64.8	61.1	57.6	54.1	50.5	47.1	46.3
85°	45.2	42.0	38.7	35.4	32.1	29.9	29.1	28.1	27.3	26.3	26.1
87.5°	15.3	14.3	13.6	12.8	12.0	11.7	11.6	11.8	11.7	11.9	12.0
90°	0.6	1.3	2.5	3.7	5.0	6.2	6.8	8.1	8.6	9.9	10.5
92.5°	7.5	9.2	14.3	22.0	32.7	50.8	84.6	141.3	202.9	199.7	161.7
95°	20.4	21.1	26.0	32.8	46.4	74.3	140.6	276.9	447.8	548.8	537.0
97.5°	33.9	34.7	38.2	45.0	57.2	77.3	121.1	221.0	399.9	586.1	679.5
100°	43.3	44.6	47.1	53.9	65.7	84.2	120.2	200.7	356.8	559.4	714.2
102.5°	53.8	54.5	56.5	63.8	74.5	92.7	124.6	192.3	324.1	512.2	693.4
105°	70.0	70.0	73.1	79.3	89.2	106.5	133.8	188.9	292.4	449.1	626.9
107.5°	85.9	87.1	90.1	95.1	105.4	121.0	147.4	194.6	279.0	405.6	559.0
110°	97.3	98.5	100.9	106.5	115.8	131.9	157.3	200.1	275.0	385.2	520.3



TEST NUMBER: P333567-927

CATALOG NUMBER: S125RDIP-S850D810U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	108.6	109.9	111.9	117.4	126.7	142.4	166.8	207.0	275.0	373.4	491.5
115°	125.1	126.4	128.3	133.8	143.1	158.6	181.5	217.4	276.9	360.5	460.2
117.5°	140.0	141.9	143.9	149.4	159.9	174.9	196.6	229.3	281.0	354.2	441.5
120°	149.9	151.8	154.2	159.8	170.3	185.8	207.5	237.3	284.9	351.2	431.1
122.5°	160.3	161.7	163.7	169.2	180.8	196.2	217.9	246.1	288.4	348.7	422.2
125°	173.4	174.7	177.8	183.3	195.1	211.2	231.6	258.3	294.2	345.6	410.0
127.5°	183.7	185.6	189.6	196.6	209.1	225.2	244.9	269.4	300.8	344.1	398.9
130°	190.1	192.0	196.9	205.0	218.0	234.2	253.3	276.9	304.8	343.2	391.5
132.5°	195.1	197.5	203.4	212.5	225.9	242.1	261.3	283.3	309.2	343.2	385.6
135°	203.2	205.7	213.1	223.0	236.0	252.7	272.0	292.4	315.3	343.2	378.4
137.5°	213.3	215.2	222.1	232.0	244.8	262.0	279.5	299.0	320.8	343.9	372.2
140°	219.3	221.1	228.5	238.4	250.3	267.0	284.9	303.5	323.3	344.4	369.2
142.5°	226.2	227.6	234.5	244.4	255.7	271.4	288.4	306.0	324.8	344.9	366.7
145°	236.6	237.8	244.1	252.7	263.9	278.1	294.2	309.7	326.5	344.4	363.0
147.5°	247.5	248.3	253.6	261.7	271.3	283.8	297.9	312.0	327.0	342.8	359.1
150°	254.0	255.2	259.5	267.6	276.2	286.8	300.4	313.4	327.0	341.3	356.2
152.5°	260.9	261.7	265.5	272.5	280.7	290.3	302.9	314.4	326.5	339.3	352.7
155°	270.1	270.1	273.8	280.0	286.1	294.9	305.4	315.3	325.2	335.7	346.9
157.5°	278.2	278.1	281.1	286.4	291.8	298.4	307.4	315.9	323.6	332.0	341.4
160°	283.7	283.0	285.6	289.9	294.9	300.4	308.5	315.9	322.1	329.5	337.0
162.5°	288.1	287.6	290.0	293.8	297.8	302.4	309.4	315.4	320.6	326.5	333.0
165°	294.9	293.6	295.5	298.6	301.0	304.8	309.7	314.7	318.4	322.1	327.0
167.5°	299.3	298.7	299.8	301.5	303.2	305.6	309.7	313.1	314.9	317.7	321.2
170°	302.3	301.7	302.3	303.5	304.8	306.6	309.7	312.2	313.4	315.3	317.7
172.5°	304.3	303.2	303.7	305.0	305.7	306.6	309.2	311.2	311.4	312.3	314.3
175°	306.6	305.4	306.0	306.6	306.6	306.6	308.5	309.7	309.1	309.1	309.7
177.5°	307.7	306.7	306.7	307.2	306.7	306.7	307.7	308.2	307.2	307.2	307.7
180°	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2



TEST NUMBER: P333567-927

CATALOG NUMBER: S125RDIP-S850D810U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3
2.5°	1085.6	1087.1	1088.5	1089.3	1089.1	1088.9	1088.8	1088.6
5°	1079.0	1080.8	1082.6	1083.4	1083.0	1082.6	1082.3	1081.9
7.5°	1065.6	1066.8	1068.1	1068.5	1068.1	1067.7	1067.3	1066.9
10°	1054.2	1054.7	1055.3	1055.3	1054.7	1054.2	1053.6	1053.1
12.5°	1038.1	1038.5	1038.9	1038.7	1037.8	1037.0	1036.2	1035.3
15°	1011.6	1011.4	1011.2	1010.3	1008.7	1007.0	1005.4	1003.7
17.5°	978.5	977.6	976.7	975.6	974.2	972.9	971.5	970.2
20°	954.2	953.2	952.4	951.1	949.4	947.8	946.1	944.5
22.5°	930.0	928.3	926.5	924.9	923.5	922.2	920.8	919.5
25°	890.4	888.0	885.7	883.4	881.4	879.4	877.4	875.4
27.5°	847.5	844.1	840.8	838.2	836.3	834.3	832.4	830.4
30°	816.8	812.6	808.3	805.5	803.8	802.2	800.5	798.8
32.5°	787.0	782.3	777.7	774.3	772.2	770.2	768.0	766.0
35°	740.5	735.2	729.9	726.0	723.4	720.9	718.4	715.7
37.5°	692.1	685.6	679.3	674.9	672.4	669.9	667.4	665.0
40°	659.9	653.0	646.0	641.4	639.3	637.1	634.9	632.7
42.5°	628.3	621.6	615.0	610.0	606.8	603.6	600.3	597.1
45°	577.7	570.5	563.1	558.1	555.3	552.6	549.9	547.1
47.5°	527.8	520.2	512.7	507.4	504.4	501.4	498.3	495.3
50°	493.9	486.2	478.6	473.3	470.6	467.9	465.1	462.4
52.5°	461.8	453.5	445.3	439.7	437.0	434.3	431.6	428.8
55°	413.0	404.8	396.6	390.9	388.1	385.2	382.2	379.3
57.5°	364.2	356.2	348.1	342.8	340.2	337.5	335.0	332.4
60°	331.9	323.8	315.8	310.5	307.7	305.0	302.2	299.4
62.5°	300.2	292.7	285.3	280.2	277.4	274.6	272.0	269.2
65°	253.6	246.3	238.9	233.9	231.2	228.5	225.7	222.9
67.5°	209.1	202.4	195.7	191.2	189.1	186.9	184.7	182.5
70°	179.5	173.9	168.2	164.3	162.1	159.9	157.7	155.5
72.5°	152.1	146.9	141.6	138.3	136.8	135.4	134.0	132.5
75°	113.8	109.7	105.7	103.1	101.7	100.4	99.2	97.9
77.5°	80.9	78.1	75.3	73.4	72.5	71.5	70.6	69.6
80°	60.9	59.3	57.6	56.6	56.2	55.8	55.5	55.1
82.5°	45.6	44.8	44.0	43.5	43.3	43.1	42.9	42.6
85°	26.0	25.7	25.6	25.4	25.2	25.0	24.9	24.7
87.5°	12.1	12.2	12.4	12.5	12.4	12.2	12.2	12.0
90°	11.2	11.8	12.4	13.6	13.6	13.6	14.3	14.3
92.5°	109.8	79.7	60.0	50.8	42.9	41.4	40.5	39.5
95°	445.4	351.2	275.0	223.0	179.0	160.4	155.5	145.5
97.5°	663.3	597.2	523.0	450.7	412.4	377.7	359.7	351.8
100°	761.8	731.5	667.7	603.3	560.5	515.9	493.1	483.2
102.5°	795.0	813.8	783.2	739.6	693.9	662.1	637.2	629.8
105°	775.5	860.4	887.6	880.8	860.9	840.5	828.1	820.7
107.5°	705.6	818.9	888.8	921.1	931.2	931.1	927.0	922.0
110°	654.1	771.7	859.1	911.7	939.6	951.4	955.8	955.8



TEST NUMBER: P333567-927

CATALOG NUMBER: S125RDIP-S850D810U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	613.5	725.2	813.5	875.6	916.3	936.5	947.3	951.8
115°	562.4	658.5	743.3	810.8	859.1	888.8	906.2	914.3
117.5°	529.5	612.2	685.3	747.3	795.6	826.2	843.5	848.4
120°	511.6	586.0	654.1	708.6	754.4	784.2	800.9	805.8
122.5°	498.3	567.1	627.8	678.9	719.8	747.0	763.7	768.2
125°	478.8	542.0	595.9	640.5	675.2	700.5	714.2	720.3
127.5°	459.0	517.9	568.2	610.0	641.4	663.8	676.8	679.5
130°	446.6	501.1	549.4	589.7	620.7	641.1	653.5	657.2
132.5°	434.2	485.2	529.1	567.8	598.8	619.2	630.7	634.9
135°	418.1	460.8	500.5	535.8	563.0	583.4	594.6	598.3
137.5°	404.5	439.0	472.0	501.9	526.4	544.9	555.2	559.4
140°	397.0	426.1	454.6	480.6	503.6	519.7	528.9	532.0
142.5°	390.6	415.3	439.7	462.3	481.8	495.4	504.2	506.8
145°	382.1	401.4	420.6	437.3	452.2	462.7	469.5	472.0
147.5°	374.2	389.8	404.6	417.2	429.0	437.4	441.4	442.5
150°	369.8	383.4	395.1	406.3	415.7	423.0	425.6	426.1
152.5°	364.8	377.0	387.8	396.4	404.3	410.2	412.6	413.3
155°	357.4	367.3	376.0	382.8	389.0	393.3	395.1	395.8
157.5°	350.0	358.1	364.8	370.2	375.0	378.6	380.3	380.2
160°	345.0	351.2	357.4	361.7	366.1	369.2	370.4	369.8
162.5°	339.5	345.2	350.5	354.3	357.7	360.2	360.5	360.4
165°	332.0	336.4	340.1	343.2	345.6	346.9	346.9	346.9
167.5°	324.8	327.6	330.5	332.7	334.0	335.1	334.6	334.5
170°	320.8	322.7	324.6	325.8	327.0	327.6	327.6	327.0
172.5°	316.4	318.2	319.6	320.4	320.6	321.7	320.8	320.1
175°	311.6	311.6	312.8	312.8	312.8	313.4	312.2	311.6
177.5°	308.2	308.7	308.7	308.7	308.2	308.7	307.2	307.2
180°	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2

(END OF REPORT)