

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333286-830

Luminaire Tested: **S125DIP-S1090D1205U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333286-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1090D1205U830-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8770.2 lumens
Efficiency: N/A
Efficacy: 134.1 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333286-830

CATALOG NUMBER: S125DIP-S1090D1205U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333286-830

CATALOG NUMBER: S125DIP-S1090D1205U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55	48																												
1	98	93	90	86	90	86	83	80	73	70	68	60	58	57	49	47	46	41																												
2	89	82	76	71	82	76	70	66	64	60	57	53	50	48	43	41	39	35																												
3	81	72	65	59	75	67	60	55	56	52	48	47	44	41	38	36	34	30																												
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29	26																												
5	68	57	49	43	63	53	46	40	45	39	35	38	34	30	31	28	26	22																												
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	22	20																												
7	58	46	38	33	53	43	36	31	37	31	27	31	27	24	26	22	20	17																												
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18	16																												
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	18	16	14																												
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	13																												

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9680	9680	9680	9680
5°	11210	9713	8504	9713
10°	13042	9663	7451	9663
15°	14437	9591	6873	9591
20°	16160	9479	6410	9479
25°	18932	9352	6183	9352
30°	20448	9228	5988	9228
35°	16812	8993	5858	8993
40°	11950	8667	5718	8667
45°	9180	8227	5636	8227
50°	7837	7683	5626	7683
55°	6977	7149	5674	7149
60°	6294	6566	5818	6566
65°	5813	5978	5969	5978
70°	5285	5370	6056	5370
75°	4666	4729	5999	4729
80°	3927	3857	5490	3857
85°	3105	2779	4431	2779



TEST NUMBER: P333286-830

CATALOG NUMBER: S125DIP-S1090D1205U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.3	1.6
10°-20°	429.6	4.9
20°-30°	697.6	8.0
30°-40°	850.9	9.7
40°-50°	774.1	8.8
50°-60°	616.6	7.0
60°-70°	429.5	4.9
70°-80°	229.0	2.6
80°-90°	60.9	0.7
90°-100°	53.7	0.6
100°-110°	330.9	3.8
110°-120°	600.2	6.8
120°-130°	770.3	8.8
130°-140°	828.6	9.4
140°-150°	777.7	8.9
150°-160°	629.1	7.2
160°-170°	406.9	4.6
170°-180°	140.3	1.6
0°-30°	1271.5	14.5
0°-40°	2122.4	24.2
0°-60°	3513.1	40.1
0°-90°	4232.5	48.3
90°-120°	984.9	11.2
90°-150°	3361.5	38.3
90°-180°	4538.0	51.7
0°-180°	8770.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1499	1499	1499	1499	1499	
5°	1729	1498	1312	1498	1729	174
15°	2159	1434	1028	1434	2159	618
25°	2657	1312	868	1312	2657	1213
35°	2132	1141	743	1141	2132	1305
45°	1005	901	617	901	1005	804
55°	620	635	504	635	620	558
65°	380	391	391	391	380	378
75°	187	190	240	190	187	201
85°	42	38	60	38	42	49
90°	26	1	26	1	26	13
95°	23	62	23	62	23	19
105°	325	322	325	322	325	294
115°	600	605	600	605	600	596
125°	860	860	860	860	860	765
135°	1068	1072	1068	1072	1068	824
145°	1240	1243	1240	1243	1240	775
155°	1359	1369	1359	1369	1359	627
165°	1437	1445	1437	1445	1437	406
175°	1471	1478	1471	1478	1471	140
180°	1478	1478	1478	1478	1478	



TEST NUMBER: P333286-830

CATALOG NUMBER: S125DIP-S1090D1205U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1585.4	1583.3	1581.3	1577.2	1580.3	1571.6	1567.5	1560.4	1551.7	1548.7	1545.1
5°	1729.1	1732.3	1735.5	1722.1	1723.3	1714.5	1694.1	1677.5	1664.2	1647.0	1634.9
7.5°	1902.1	1894.6	1894.0	1885.4	1870.5	1858.5	1837.1	1809.9	1783.6	1753.5	1728.7
10°	1988.7	1989.3	1983.6	1973.4	1957.5	1946.1	1918.1	1891.3	1858.9	1820.7	1793.4
12.5°	2053.8	2056.4	2049.3	2035.5	2027.7	2002.1	1980.2	1948.3	1909.8	1879.2	1837.7
15°	2159.2	2152.2	2147.1	2129.9	2116.6	2089.8	2054.8	2021.8	1979.7	1941.0	1902.1
17.5°	2260.7	2266.2	2256.7	2241.1	2199.6	2168.4	2121.5	2076.2	2023.9	1971.9	1925.5
20°	2351.3	2356.4	2341.7	2314.4	2264.7	2233.6	2171.9	2113.4	2053.0	1986.1	1935.2
22.5°	2464.3	2460.2	2440.4	2398.9	2355.9	2298.2	2231.5	2160.2	2084.4	2009.0	1941.4
25°	2656.7	2629.9	2617.8	2566.4	2509.7	2425.1	2333.5	2229.1	2135.0	2035.1	1948.6
27.5°	2763.3	2754.9	2741.4	2705.5	2646.0	2555.5	2447.5	2320.4	2187.5	2061.4	1948.2
30°	2741.9	2743.2	2744.4	2733.0	2694.8	2626.8	2519.2	2382.5	2224.7	2082.8	1951.7
32.5°	2552.6	2575.7	2597.8	2624.0	2634.8	2621.7	2554.4	2430.8	2268.4	2107.2	1949.7
35°	2132.4	2139.5	2211.3	2282.6	2379.3	2454.4	2504.6	2449.9	2313.1	2128.0	1947.3
37.5°	1662.7	1697.0	1746.8	1827.3	1966.9	2091.9	2252.6	2326.5	2282.4	2134.8	1942.9
40°	1417.4	1449.2	1481.7	1563.7	1681.4	1832.8	2015.3	2171.2	2207.5	2113.4	1927.6
42.5°	1228.0	1253.3	1289.3	1350.9	1449.3	1583.5	1757.8	1961.5	2086.9	2051.3	1895.5
45°	1005.1	1021.1	1049.0	1098.1	1169.3	1274.2	1428.2	1650.9	1844.9	1909.1	1819.5
47.5°	860.4	860.3	882.0	915.9	967.2	1056.4	1170.3	1344.7	1552.0	1705.3	1698.2
50°	780.0	776.7	793.9	823.2	863.9	923.1	1031.9	1171.2	1370.3	1544.0	1592.3
52.5°	710.8	711.1	721.7	743.3	777.4	827.9	909.2	1034.8	1204.9	1383.2	1474.2
55°	619.6	617.1	629.1	643.9	668.6	701.7	760.3	856.3	994.3	1169.9	1288.3
57.5°	536.1	543.2	548.0	558.2	578.8	601.0	650.3	720.8	830.3	981.0	1106.1
60°	487.3	494.3	498.1	508.3	524.8	543.9	582.1	639.3	731.6	861.4	985.4
62.5°	443.6	449.0	450.3	459.4	473.0	491.5	521.5	569.7	642.5	756.0	877.5
65°	380.4	380.4	383.0	392.5	398.9	415.4	438.3	473.3	531.9	620.3	724.0
67.5°	319.6	322.6	322.1	326.2	332.1	345.0	361.4	390.2	433.6	498.1	581.1
70°	279.9	282.5	281.8	285.0	291.3	299.6	313.0	340.4	371.6	426.9	498.1
72.5°	244.3	245.3	243.6	247.9	251.7	258.9	273.8	288.4	317.5	364.3	422.8
75°	187.0	188.3	189.5	192.1	196.0	199.7	207.4	222.1	241.1	276.1	313.7
77.5°	140.3	137.8	140.8	140.4	142.6	145.5	152.3	160.0	175.7	197.8	226.9
80°	105.6	106.2	106.2	106.9	110.1	112.0	117.7	123.4	135.5	152.0	172.4
82.5°	77.1	78.8	77.8	78.9	81.5	82.9	86.1	90.9	97.8	110.8	125.5
85°	41.9	38.8	40.1	41.4	41.4	41.9	44.5	46.5	50.2	55.3	61.1
87.5°	17.4	18.4	18.7	18.6	18.9	18.8	20.5	20.3	21.6	22.8	24.5
90°	26.3	25.5	24.8	24.1	23.4	22.4	21.2	20.0	18.8	17.5	15.8
92.5°	24.5	24.2	23.8	23.5	23.2	22.4	21.2	20.0	18.8	17.5	16.0
95°	23.0	23.0	23.0	23.0	23.0	22.4	21.2	20.0	18.8	17.5	26.8
97.5°	23.0	23.0	23.0	23.0	23.0	26.4	33.3	40.2	47.0	53.9	72.2
100°	23.0	23.9	25.0	25.9	26.9	45.5	81.8	118.1	154.3	190.6	189.6
102.5°	137.8	154.4	170.9	187.5	204.1	215.7	222.6	229.4	236.3	243.2	242.6
105°	325.4	325.6	325.8	326.0	326.3	326.4	326.4	326.4	326.4	326.4	326.4
107.5°	410.1	410.9	411.6	412.3	413.0	413.4	413.3	413.3	413.2	413.2	412.7
110°	468.8	468.6	468.3	468.1	467.9	468.1	468.8	469.6	470.3	471.0	470.5



TEST NUMBER: P333286-830

CATALOG NUMBER: S125DIP-S1090D1205U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	521.4	521.8	522.1	522.5	522.7	523.4	524.3	525.3	526.2	527.1	526.8
115°	600.3	601.7	603.2	604.6	606.1	607.4	608.3	609.3	610.3	611.2	611.0
117.5°	684.4	685.0	685.7	686.3	686.9	687.9	689.2	690.4	691.7	693.0	692.0
120°	736.1	737.4	738.6	739.8	741.0	741.9	742.3	742.8	743.3	743.8	743.0
122.5°	785.2	786.6	788.0	789.4	790.8	791.8	792.3	792.8	793.2	793.7	793.4
125°	859.9	860.6	861.4	862.0	862.8	863.7	864.6	865.6	866.6	867.5	867.5
127.5°	922.7	924.5	926.3	928.2	930.0	931.1	931.7	932.2	932.7	933.3	933.4
130°	968.4	969.6	970.8	971.9	973.2	974.2	974.9	975.6	976.4	977.1	976.9
132.5°	1010.4	1011.6	1012.9	1014.1	1015.3	1016.0	1016.1	1016.2	1016.4	1016.5	1017.1
135°	1068.0	1069.5	1070.9	1072.4	1073.8	1074.9	1075.3	1075.8	1076.3	1076.8	1077.2
137.5°	1125.9	1127.1	1128.4	1129.6	1131.0	1131.5	1131.4	1131.3	1131.2	1131.1	1131.5
140°	1160.1	1161.5	1163.0	1164.4	1165.8	1166.4	1165.8	1165.4	1164.9	1164.4	1164.7
142.5°	1192.5	1193.9	1195.4	1196.8	1198.3	1199.0	1198.9	1198.8	1198.7	1198.6	1198.3
145°	1240.0	1241.4	1242.9	1244.3	1245.9	1246.4	1246.2	1245.9	1245.8	1245.5	1245.5
147.5°	1279.2	1281.0	1282.7	1284.5	1286.2	1286.9	1286.7	1286.4	1286.1	1285.8	1285.5
150°	1304.7	1306.6	1308.5	1310.5	1312.4	1313.2	1312.7	1312.2	1311.6	1311.2	1310.7
152.5°	1328.3	1330.0	1331.8	1333.5	1335.3	1336.0	1335.5	1334.9	1334.5	1334.0	1333.5
155°	1359.4	1361.3	1363.3	1365.3	1367.2	1367.8	1367.1	1366.3	1365.6	1364.9	1364.4
157.5°	1385.4	1387.4	1389.4	1391.3	1393.3	1393.8	1393.1	1392.3	1391.5	1390.7	1390.7
160°	1402.1	1404.1	1406.0	1408.0	1409.9	1410.4	1409.4	1408.4	1407.5	1406.5	1406.3
162.5°	1417.0	1419.2	1421.3	1423.4	1425.6	1426.0	1424.7	1423.2	1421.9	1420.5	1420.3
165°	1437.2	1439.1	1441.1	1443.0	1444.9	1445.2	1443.8	1442.3	1440.9	1439.4	1439.1
167.5°	1451.2	1453.4	1455.6	1457.7	1460.0	1460.2	1458.4	1456.7	1454.9	1453.2	1452.9
170°	1459.1	1461.3	1463.5	1465.7	1467.8	1468.0	1466.0	1464.1	1462.2	1460.2	1459.9
172.5°	1464.3	1466.5	1468.8	1470.9	1473.1	1473.3	1471.6	1469.8	1468.1	1466.3	1465.8
175°	1471.1	1473.3	1475.6	1477.7	1479.9	1480.0	1478.1	1476.1	1474.1	1472.3	1472.0
177.5°	1475.1	1476.6	1478.2	1479.8	1481.3	1481.4	1480.1	1478.7	1477.3	1475.9	1475.7
180°	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7



TEST NUMBER: P333286-830

CATALOG NUMBER: S125DIP-S1090D1205U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1542.1	1538.5	1534.5	1527.3	1518.6	1514.1	1506.9	1502.4	1493.2	1485.5	1477.4
5°	1620.3	1603.8	1588.6	1568.8	1547.2	1533.1	1516.6	1498.2	1479.1	1459.3	1437.8
7.5°	1701.4	1672.1	1640.3	1606.1	1572.6	1541.8	1512.4	1483.6	1456.6	1424.0	1396.4
10°	1755.9	1718.9	1679.5	1633.0	1587.9	1548.4	1508.4	1473.4	1437.8	1399.6	1365.8
12.5°	1810.2	1761.1	1705.4	1654.4	1600.1	1552.5	1505.3	1460.7	1415.9	1373.7	1334.3
15°	1848.7	1805.4	1753.9	1681.4	1620.3	1554.8	1492.4	1434.5	1380.4	1333.4	1283.8
17.5°	1874.1	1818.3	1762.9	1693.4	1613.4	1540.0	1469.4	1403.2	1342.2	1282.5	1234.6
20°	1878.6	1821.4	1763.5	1695.4	1613.4	1529.4	1458.8	1379.2	1313.7	1252.0	1193.4
22.5°	1877.1	1812.2	1749.2	1679.1	1599.1	1521.7	1436.3	1355.3	1284.2	1223.5	1162.4
25°	1862.7	1793.4	1714.5	1643.9	1565.0	1482.9	1396.4	1312.4	1239.9	1170.5	1110.1
27.5°	1850.8	1760.8	1671.5	1589.1	1513.0	1437.8	1354.9	1268.9	1188.5	1118.2	1061.3
30°	1836.0	1737.4	1636.8	1551.0	1472.7	1399.6	1321.4	1237.4	1153.4	1084.7	1023.6
32.5°	1822.8	1707.9	1601.8	1508.3	1425.4	1354.2	1282.1	1202.2	1119.7	1050.1	989.0
35°	1797.1	1664.2	1542.8	1437.1	1348.7	1275.5	1215.1	1140.7	1065.0	997.5	939.0
37.5°	1764.7	1606.9	1476.6	1365.8	1268.9	1191.8	1135.6	1078.5	1005.8	940.8	887.9
40°	1739.3	1566.2	1428.2	1314.9	1214.5	1134.3	1082.1	1028.0	967.6	907.2	851.2
42.5°	1707.2	1529.7	1379.3	1257.4	1157.9	1079.9	1025.1	979.2	925.9	869.5	817.6
45°	1648.3	1463.2	1300.3	1169.3	1068.7	991.7	935.2	900.8	860.7	807.3	763.4
47.5°	1561.7	1383.4	1214.9	1079.7	976.0	904.7	851.6	818.6	790.4	750.6	710.9
50°	1484.8	1323.9	1153.4	1019.2	915.5	843.6	794.6	764.7	740.5	709.9	676.3
52.5°	1398.8	1249.1	1092.8	960.1	857.4	786.6	738.6	712.3	692.1	670.2	637.1
55°	1262.2	1134.9	989.9	863.9	769.1	699.7	657.8	634.9	618.4	601.8	581.5
57.5°	1111.6	1012.1	883.6	768.5	681.2	618.1	578.9	556.7	543.8	535.3	523.3
60°	1005.8	920.6	809.8	704.8	619.6	563.6	525.5	508.3	497.5	490.5	481.5
62.5°	907.6	837.5	735.0	639.2	564.7	511.7	477.7	461.0	450.6	447.2	439.9
65°	762.8	708.7	624.1	544.6	481.0	435.7	407.2	391.2	384.8	381.1	381.7
67.5°	620.1	587.2	519.2	451.4	400.7	362.8	339.9	327.6	324.4	319.3	319.2
70°	533.1	508.3	451.0	391.9	346.7	317.4	297.1	284.4	281.2	278.6	278.1
72.5°	456.3	434.5	384.8	337.4	296.8	271.2	254.3	246.7	241.5	240.0	239.9
75°	342.9	330.8	291.3	253.8	225.8	208.0	196.6	189.5	185.8	185.1	185.8
77.5°	243.7	233.2	208.1	181.5	163.9	150.4	140.7	138.3	133.9	134.1	133.5
80°	183.2	176.3	160.3	139.3	124.7	113.2	108.1	103.7	102.5	100.5	102.5
82.5°	132.8	125.4	114.5	101.1	89.1	82.2	77.1	75.7	74.9	74.1	74.5
85°	65.5	66.2	59.8	49.6	44.5	40.7	37.5	37.5	36.9	36.3	36.9
87.5°	25.3	23.8	21.5	19.6	16.7	14.7	13.9	13.9	12.8	12.7	13.6
90°	14.1	12.4	10.7	8.9	7.0	5.0	3.0	1.1	3.0	5.0	7.0
92.5°	14.5	13.0	11.5	11.4	12.8	14.1	15.6	16.9	15.6	14.1	12.8
95°	36.0	45.2	54.6	59.5	60.2	61.0	61.7	62.4	61.7	61.0	60.2
97.5°	90.5	108.8	127.1	135.6	134.3	133.0	131.7	130.4	131.7	133.0	134.3
100°	188.7	187.7	186.7	185.9	185.1	184.4	183.7	182.9	183.7	184.4	185.1
102.5°	242.0	241.4	240.8	240.1	239.1	238.3	237.3	236.4	237.3	238.3	239.1
105°	326.4	326.4	326.4	325.9	325.0	324.0	323.0	322.1	323.0	324.0	325.0
107.5°	412.2	411.7	411.2	411.0	411.0	411.0	411.0	411.0	411.0	411.0	411.0
110°	470.0	469.6	469.1	468.8	468.8	468.8	468.8	468.8	468.8	468.8	468.8



TEST NUMBER: P333286-830

CATALOG NUMBER: S125DIP-S1090D1205U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	526.5	526.2	525.9	525.5	524.9	524.3	523.8	523.2	523.8	524.3	524.9
115°	610.8	610.5	610.3	609.5	608.3	607.1	605.9	604.6	605.9	607.1	608.3
117.5°	691.1	690.2	689.3	688.8	688.9	688.9	689.0	689.0	689.0	688.9	688.9
120°	742.3	741.6	740.8	740.6	740.8	741.1	741.3	741.6	741.3	741.1	740.8
122.5°	793.1	792.7	792.4	791.7	790.8	789.9	789.0	788.1	789.0	789.9	790.8
125°	867.5	867.5	867.5	866.7	865.0	863.3	861.6	859.9	861.6	863.3	865.0
127.5°	933.6	933.7	933.9	933.3	932.1	930.9	929.7	928.5	929.7	930.9	932.1
130°	976.7	976.4	976.1	975.4	974.2	973.0	971.8	970.5	971.8	973.0	974.2
132.5°	1017.6	1018.1	1018.7	1018.2	1016.8	1015.4	1014.0	1012.6	1014.0	1015.4	1016.8
135°	1077.8	1078.3	1078.7	1078.3	1076.8	1075.3	1073.8	1072.4	1073.8	1075.3	1076.8
137.5°	1132.0	1132.5	1132.8	1132.5	1131.1	1129.9	1128.7	1127.4	1128.7	1129.9	1131.1
140°	1164.9	1165.2	1165.4	1165.3	1164.8	1164.3	1163.9	1163.3	1163.9	1164.3	1164.8
142.5°	1197.9	1197.6	1197.2	1196.9	1196.7	1196.4	1196.0	1195.7	1196.0	1196.4	1196.7
145°	1245.5	1245.5	1245.5	1245.2	1244.7	1244.3	1243.8	1243.3	1243.8	1244.3	1244.7
147.5°	1285.2	1284.9	1284.6	1284.5	1284.6	1284.7	1284.8	1284.9	1284.8	1284.7	1284.6
150°	1310.2	1309.8	1309.3	1309.3	1309.8	1310.2	1310.7	1311.2	1310.7	1310.2	1309.8
152.5°	1333.0	1332.6	1332.0	1332.3	1333.4	1334.5	1335.6	1336.6	1335.6	1334.5	1333.4
155°	1363.9	1363.4	1362.9	1363.4	1364.9	1366.3	1367.8	1369.2	1367.8	1366.3	1364.9
157.5°	1390.6	1390.6	1390.5	1390.9	1391.9	1392.7	1393.5	1394.5	1393.5	1392.7	1391.9
160°	1406.0	1405.8	1405.5	1406.2	1407.6	1409.1	1410.5	1412.0	1410.5	1409.1	1407.6
162.5°	1420.0	1419.8	1419.6	1420.1	1421.6	1423.1	1424.6	1426.0	1424.6	1423.1	1421.6
165°	1438.9	1438.6	1438.4	1439.0	1440.5	1441.9	1443.4	1444.8	1443.4	1441.9	1440.5
167.5°	1452.6	1452.5	1452.2	1452.8	1454.3	1455.9	1457.4	1458.9	1457.4	1455.9	1454.3
170°	1459.7	1459.4	1459.2	1459.9	1461.6	1463.3	1465.1	1466.8	1465.1	1463.3	1461.6
172.5°	1465.5	1465.0	1464.5	1465.2	1466.9	1468.6	1470.3	1472.0	1470.3	1468.6	1466.9
175°	1471.8	1471.5	1471.2	1471.9	1473.3	1474.8	1476.2	1477.7	1476.2	1474.8	1473.3
177.5°	1475.6	1475.4	1475.2	1475.6	1476.9	1478.0	1479.1	1480.4	1479.1	1478.0	1476.9
180°	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7



TEST NUMBER: P333286-830

CATALOG NUMBER: S125DIP-S1090D1205U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1472.8	1467.3	1462.6	1452.5	1446.9	1439.3	1433.1	1439.7	1432.7	1435.7	1431.2
5°	1426.9	1409.1	1396.4	1377.9	1362.1	1347.4	1336.6	1334.6	1329.6	1327.0	1319.4
7.5°	1371.7	1349.4	1327.6	1303.3	1283.0	1262.3	1249.1	1238.1	1230.9	1221.3	1214.8
10°	1339.2	1309.2	1283.8	1254.5	1229.1	1206.8	1189.0	1180.1	1171.9	1159.7	1155.3
12.5°	1298.9	1268.0	1237.0	1205.7	1181.2	1156.4	1141.1	1127.7	1121.9	1108.3	1106.9
15°	1250.8	1204.3	1173.7	1141.9	1108.2	1087.9	1075.2	1060.5	1054.1	1044.6	1037.6
17.5°	1193.2	1151.7	1113.5	1080.6	1051.7	1034.5	1018.8	1008.7	997.8	991.6	980.1
20°	1151.5	1112.0	1073.8	1038.9	1016.6	996.8	984.1	974.6	963.2	960.0	948.6
22.5°	1116.3	1072.8	1036.2	1006.8	982.5	960.3	946.5	940.0	932.1	922.3	920.0
25°	1059.2	1014.1	982.9	953.7	932.0	911.6	902.1	893.8	886.2	879.2	876.7
27.5°	1009.8	969.5	932.5	906.1	887.2	868.6	860.3	850.2	844.6	839.0	832.1
30°	975.2	933.9	901.4	876.0	855.6	839.1	830.2	823.2	818.1	813.0	809.2
32.5°	939.6	901.4	869.9	845.0	824.6	812.1	804.3	799.3	793.7	787.6	782.8
35°	892.6	850.6	820.0	798.4	782.5	773.0	764.0	759.6	753.2	753.2	748.1
37.5°	839.5	803.2	776.3	756.6	742.3	733.8	724.1	721.0	717.0	714.3	712.5
40°	807.9	774.2	748.8	729.1	713.8	706.8	699.2	694.1	691.5	688.3	687.0
42.5°	775.3	743.2	718.8	700.6	687.3	681.4	674.2	670.6	665.5	661.4	660.6
45°	725.9	694.7	672.4	657.8	646.3	639.3	634.9	627.3	624.7	619.6	619.0
47.5°	678.9	649.0	627.2	615.2	605.1	599.4	592.4	584.8	581.8	579.3	579.0
50°	643.9	616.4	596.1	584.7	575.1	566.8	559.9	554.8	552.8	552.8	554.1
52.5°	608.2	584.8	567.6	553.6	544.6	535.7	529.3	526.2	523.3	526.4	528.7
55°	556.0	532.4	519.7	506.4	497.5	487.3	484.1	482.9	481.0	486.1	488.6
57.5°	500.8	484.3	469.4	456.1	448.1	442.2	437.9	437.2	440.7	443.2	451.4
60°	465.7	446.6	433.2	423.0	413.5	409.7	408.4	407.2	409.7	416.7	427.5
62.5°	427.0	411.5	397.1	389.5	382.5	376.1	375.9	376.6	381.7	389.7	400.5
65°	370.2	356.8	347.3	338.5	332.7	328.9	330.2	332.7	338.5	349.2	361.4
67.5°	312.6	303.5	294.9	287.7	282.2	282.2	283.5	287.3	294.1	306.5	317.5
70°	275.5	265.3	258.3	255.1	250.6	248.1	251.9	258.3	264.0	275.5	285.0
72.5°	238.3	229.7	224.2	222.1	220.1	218.1	219.3	226.2	233.9	245.4	256.5
75°	183.2	180.0	176.3	173.7	171.7	173.1	174.3	180.7	187.0	199.2	211.9
77.5°	133.7	130.4	128.1	127.5	126.5	127.1	130.6	135.3	141.6	150.4	160.0
80°	101.1	99.9	98.6	97.9	97.9	98.6	103.7	106.9	112.6	120.8	128.5
82.5°	73.7	72.9	72.7	72.5	73.0	73.1	76.3	80.4	85.1	91.3	97.9
85°	38.8	37.5	39.4	40.1	38.8	40.7	41.9	44.5	46.5	49.6	52.8
87.5°	14.5	15.9	15.7	16.6	16.9	18.3	18.0	20.3	21.6	22.8	22.5
90°	8.9	10.7	12.4	14.1	15.8	17.5	18.8	20.0	21.2	22.4	23.4
92.5°	11.4	11.5	13.0	14.5	16.0	17.5	18.8	20.0	21.2	22.4	23.2
95°	59.5	54.6	45.2	36.0	26.8	17.5	18.8	20.0	21.2	22.4	23.0
97.5°	135.6	127.1	108.8	90.5	72.2	53.9	47.0	40.2	33.3	26.4	23.0
100°	185.9	186.7	187.7	188.7	189.6	190.6	154.3	118.1	81.8	45.5	26.9
102.5°	240.1	240.8	241.4	242.0	242.6	243.2	236.3	229.4	222.6	215.7	204.1
105°	325.9	326.4	326.4	326.4	326.4	326.4	326.4	326.4	326.4	326.4	326.3
107.5°	411.0	411.2	411.7	412.2	412.7	413.2	413.2	413.3	413.3	413.4	413.0
110°	468.8	469.1	469.6	470.0	470.5	471.0	470.3	469.6	468.8	468.1	467.9



TEST NUMBER: P333286-830

CATALOG NUMBER: S125DIP-S1090D1205U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	525.5	525.9	526.2	526.5	526.8	527.1	526.2	525.3	524.3	523.4	522.7
115°	609.5	610.3	610.5	610.8	611.0	611.2	610.3	609.3	608.3	607.4	606.1
117.5°	688.8	689.3	690.2	691.1	692.0	693.0	691.7	690.4	689.2	687.9	686.9
120°	740.6	740.8	741.6	742.3	743.0	743.8	743.3	742.8	742.3	741.9	741.0
122.5°	791.7	792.4	792.7	793.1	793.4	793.7	793.2	792.8	792.3	791.8	790.8
125°	866.7	867.5	867.5	867.5	867.5	867.5	866.6	865.6	864.6	863.7	862.8
127.5°	933.3	933.9	933.7	933.6	933.4	933.3	932.7	932.2	931.7	931.1	930.0
130°	975.4	976.1	976.4	976.7	976.9	977.1	976.4	975.6	974.9	974.2	973.2
132.5°	1018.2	1018.7	1018.1	1017.6	1017.1	1016.5	1016.4	1016.2	1016.1	1016.0	1015.3
135°	1078.3	1078.7	1078.3	1077.8	1077.2	1076.8	1076.3	1075.8	1075.3	1074.9	1073.8
137.5°	1132.5	1132.8	1132.5	1132.0	1131.5	1131.1	1131.2	1131.3	1131.4	1131.5	1131.0
140°	1165.3	1165.4	1165.2	1164.9	1164.7	1164.4	1164.9	1165.4	1165.8	1166.4	1165.8
142.5°	1196.9	1197.2	1197.6	1197.9	1198.3	1198.6	1198.7	1198.8	1198.9	1199.0	1198.3
145°	1245.2	1245.5	1245.5	1245.5	1245.5	1245.5	1245.8	1245.9	1246.2	1246.4	1245.9
147.5°	1284.5	1284.6	1284.9	1285.2	1285.5	1285.8	1286.1	1286.4	1286.7	1286.9	1286.2
150°	1309.3	1309.3	1309.8	1310.2	1310.7	1311.2	1311.6	1312.2	1312.7	1313.2	1312.4
152.5°	1332.3	1332.0	1332.6	1333.0	1333.5	1334.0	1334.5	1334.9	1335.5	1336.0	1335.3
155°	1363.4	1362.9	1363.4	1363.9	1364.4	1364.9	1365.6	1366.3	1367.1	1367.8	1367.2
157.5°	1390.9	1390.5	1390.6	1390.6	1390.7	1390.7	1391.5	1392.3	1393.1	1393.8	1393.3
160°	1406.2	1405.5	1405.8	1406.0	1406.3	1406.5	1407.5	1408.4	1409.4	1410.4	1409.9
162.5°	1420.1	1419.6	1419.8	1420.0	1420.3	1420.5	1421.9	1423.2	1424.7	1426.0	1425.6
165°	1439.0	1438.4	1438.6	1438.9	1439.1	1439.4	1440.9	1442.3	1443.8	1445.2	1444.9
167.5°	1452.8	1452.2	1452.5	1452.6	1452.9	1453.2	1454.9	1456.7	1458.4	1460.2	1460.0
170°	1459.9	1459.2	1459.4	1459.7	1459.9	1460.2	1462.2	1464.1	1466.0	1468.0	1467.8
172.5°	1465.2	1464.5	1465.0	1465.5	1465.8	1466.3	1468.1	1469.8	1471.6	1473.3	1473.1
175°	1471.9	1471.2	1471.5	1471.8	1472.0	1472.3	1474.1	1476.1	1478.1	1480.0	1479.9
177.5°	1475.6	1475.2	1475.4	1475.6	1475.7	1475.9	1477.3	1478.7	1480.1	1481.4	1481.3
180°	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7



TEST NUMBER: P333286-830

CATALOG NUMBER: S125DIP-S1090D1205U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1428.0	1431.6	1428.6	1432.7	1428.6	1431.6	1428.0	1431.2	1435.7	1432.7	1439.7
5°	1316.3	1310.5	1314.3	1311.7	1314.3	1310.5	1316.3	1319.4	1327.0	1329.6	1334.6
7.5°	1213.0	1207.5	1201.2	1198.3	1201.2	1207.5	1213.0	1214.8	1221.3	1230.9	1238.1
10°	1148.3	1141.3	1140.7	1136.2	1140.7	1141.3	1148.3	1155.3	1159.7	1171.9	1180.1
12.5°	1101.0	1094.5	1087.2	1085.3	1087.2	1094.5	1101.0	1106.9	1108.3	1121.9	1127.7
15°	1033.8	1028.7	1024.3	1028.0	1024.3	1028.7	1033.8	1037.6	1044.6	1054.1	1060.5
17.5°	977.9	973.7	973.0	968.3	973.0	973.7	977.9	980.1	991.6	997.8	1008.7
20°	942.8	939.6	940.9	932.6	940.9	939.6	942.8	948.6	960.0	963.2	974.6
22.5°	914.8	908.6	907.9	906.2	907.9	908.6	914.8	920.0	922.3	932.1	940.0
25°	870.9	867.7	864.6	867.7	864.6	867.7	870.9	876.7	879.2	886.2	893.8
27.5°	832.6	828.8	827.9	828.3	827.9	828.8	832.6	832.1	839.0	844.6	850.2
30°	809.2	802.9	803.5	802.9	803.5	802.9	809.2	809.2	813.0	818.1	823.2
32.5°	783.7	779.4	778.5	777.4	778.5	779.4	783.7	782.8	787.6	793.7	799.3
35°	746.2	746.2	743.0	743.0	743.0	746.2	746.2	748.1	753.2	753.2	759.6
37.5°	711.0	710.3	708.4	708.7	708.4	710.3	711.0	712.5	714.3	717.0	721.0
40°	684.5	683.9	681.9	678.2	681.9	683.9	684.5	687.0	688.3	691.5	694.1
42.5°	659.0	657.0	656.0	654.8	656.0	657.0	659.0	660.6	661.4	665.5	670.6
45°	619.0	619.0	617.7	617.1	617.7	619.0	619.0	619.0	619.6	624.7	627.3
47.5°	580.0	581.2	583.6	583.2	583.6	581.2	580.0	579.0	579.3	581.8	584.8
50°	556.7	557.3	559.2	559.9	559.2	557.3	556.7	554.1	552.8	552.8	554.8
52.5°	530.7	534.4	536.8	536.4	536.8	534.4	530.7	528.7	526.4	523.3	526.2
55°	494.3	498.8	503.2	503.9	503.2	498.8	494.3	488.6	486.1	481.0	482.9
57.5°	458.3	464.5	469.2	470.8	469.2	464.5	458.3	451.4	443.2	440.7	437.2
60°	433.9	442.1	447.9	450.4	447.9	442.1	433.9	427.5	416.7	409.7	407.2
62.5°	410.5	419.7	425.5	425.9	425.5	419.7	410.5	400.5	389.7	381.7	376.6
65°	372.1	381.7	386.8	390.6	386.8	381.7	372.1	361.4	349.2	338.5	332.7
67.5°	330.9	340.4	346.1	349.1	346.1	340.4	330.9	317.5	306.5	294.1	287.3
70°	301.0	310.5	318.1	320.7	318.1	310.5	301.0	285.0	275.5	264.0	258.3
72.5°	271.4	279.9	286.1	289.1	286.1	279.9	271.4	256.5	245.4	233.9	226.2
75°	220.1	231.6	237.3	240.4	237.3	231.6	220.1	211.9	199.2	187.0	180.7
77.5°	169.8	180.1	183.6	185.2	183.6	180.1	169.8	160.0	150.4	141.6	135.3
80°	136.1	142.5	146.9	147.6	146.9	142.5	136.1	128.5	120.8	112.6	106.9
82.5°	104.6	109.9	111.3	113.0	111.3	109.9	104.6	97.9	91.3	85.1	80.4
85°	57.2	59.8	60.4	59.8	60.4	59.8	57.2	52.8	49.6	46.5	44.5
87.5°	23.7	23.3	23.5	24.6	23.5	23.3	23.7	22.5	22.8	21.6	20.3
90°	24.1	24.8	25.5	26.3	25.5	24.8	24.1	23.4	22.4	21.2	20.0
92.5°	23.5	23.8	24.2	24.5	24.2	23.8	23.5	23.2	22.4	21.2	20.0
95°	23.0	23.0	23.0	23.0	23.0	23.0	23.0	23.0	22.4	21.2	20.0
97.5°	23.0	23.0	23.0	23.0	23.0	23.0	23.0	23.0	26.4	33.3	40.2
100°	25.9	25.0	23.9	23.0	23.9	25.0	25.9	26.9	45.5	81.8	118.1
102.5°	187.5	170.9	154.4	137.8	154.4	170.9	187.5	204.1	215.7	222.6	229.4
105°	326.0	325.8	325.6	325.4	325.6	325.8	326.0	326.3	326.4	326.4	326.4
107.5°	412.3	411.6	410.9	410.1	410.9	411.6	412.3	413.0	413.4	413.3	413.3
110°	468.1	468.3	468.6	468.8	468.6	468.3	468.1	467.9	468.1	468.8	469.6



TEST NUMBER: P333286-830

CATALOG NUMBER: S125DIP-S1090D1205U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	522.5	522.1	521.8	521.4	521.8	522.1	522.5	522.7	523.4	524.3	525.3
115°	604.6	603.2	601.7	600.3	601.7	603.2	604.6	606.1	607.4	608.3	609.3
117.5°	686.3	685.7	685.0	684.4	685.0	685.7	686.3	686.9	687.9	689.2	690.4
120°	739.8	738.6	737.4	736.1	737.4	738.6	739.8	741.0	741.9	742.3	742.8
122.5°	789.4	788.0	786.6	785.2	786.6	788.0	789.4	790.8	791.8	792.3	792.8
125°	862.0	861.4	860.6	859.9	860.6	861.4	862.0	862.8	863.7	864.6	865.6
127.5°	928.2	926.3	924.5	922.7	924.5	926.3	928.2	930.0	931.1	931.7	932.2
130°	971.9	970.8	969.6	968.4	969.6	970.8	971.9	973.2	974.2	974.9	975.6
132.5°	1014.1	1012.9	1011.6	1010.4	1011.6	1012.9	1014.1	1015.3	1016.0	1016.1	1016.2
135°	1072.4	1070.9	1069.5	1068.0	1069.5	1070.9	1072.4	1073.8	1074.9	1075.3	1075.8
137.5°	1129.6	1128.4	1127.1	1125.9	1127.1	1128.4	1129.6	1131.0	1131.5	1131.4	1131.3
140°	1164.4	1163.0	1161.5	1160.1	1161.5	1163.0	1164.4	1165.8	1166.4	1165.8	1165.4
142.5°	1196.8	1195.4	1193.9	1192.5	1193.9	1195.4	1196.8	1198.3	1199.0	1198.9	1198.8
145°	1244.3	1242.9	1241.4	1240.0	1241.4	1242.9	1244.3	1245.9	1246.4	1246.2	1245.9
147.5°	1284.5	1282.7	1281.0	1279.2	1281.0	1282.7	1284.5	1286.2	1286.9	1286.7	1286.4
150°	1310.5	1308.5	1306.6	1304.7	1306.6	1308.5	1310.5	1312.4	1313.2	1312.7	1312.2
152.5°	1333.5	1331.8	1330.0	1328.3	1330.0	1331.8	1333.5	1335.3	1336.0	1335.5	1334.9
155°	1365.3	1363.3	1361.3	1359.4	1361.3	1363.3	1365.3	1367.2	1367.8	1367.1	1366.3
157.5°	1391.3	1389.4	1387.4	1385.4	1387.4	1389.4	1391.3	1393.3	1393.8	1393.1	1392.3
160°	1408.0	1406.0	1404.1	1402.1	1404.1	1406.0	1408.0	1409.9	1410.4	1409.4	1408.4
162.5°	1423.4	1421.3	1419.2	1417.0	1419.2	1421.3	1423.4	1425.6	1426.0	1424.7	1423.2
165°	1443.0	1441.1	1439.1	1437.2	1439.1	1441.1	1443.0	1444.9	1445.2	1443.8	1442.3
167.5°	1457.7	1455.6	1453.4	1451.2	1453.4	1455.6	1457.7	1460.0	1460.2	1458.4	1456.7
170°	1465.7	1463.5	1461.3	1459.1	1461.3	1463.5	1465.7	1467.8	1468.0	1466.0	1464.1
172.5°	1470.9	1468.8	1466.5	1464.3	1466.5	1468.8	1470.9	1473.1	1473.3	1471.6	1469.8
175°	1477.7	1475.6	1473.3	1471.1	1473.3	1475.6	1477.7	1479.9	1480.0	1478.1	1476.1
177.5°	1479.8	1478.2	1476.6	1475.1	1476.6	1478.2	1479.8	1481.3	1481.4	1480.1	1478.7
180°	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7



TEST NUMBER: P333286-830

CATALOG NUMBER: S125DIP-S1090D1205U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1433.1	1439.3	1446.9	1452.5	1462.6	1467.3	1472.8	1477.4	1485.5	1493.2	1502.4
5°	1336.6	1347.4	1362.1	1377.9	1396.4	1409.1	1426.9	1437.8	1459.3	1479.1	1498.2
7.5°	1249.1	1262.3	1283.0	1303.3	1327.6	1349.4	1371.7	1396.4	1424.0	1456.6	1483.6
10°	1189.0	1206.8	1229.1	1254.5	1283.8	1309.2	1339.2	1365.8	1399.6	1437.8	1473.4
12.5°	1141.1	1156.4	1181.2	1205.7	1237.0	1268.0	1298.9	1334.3	1373.7	1415.9	1460.7
15°	1075.2	1087.9	1108.2	1141.9	1173.7	1204.3	1250.8	1283.8	1333.4	1380.4	1434.5
17.5°	1018.8	1034.5	1051.7	1080.6	1113.5	1151.7	1193.2	1234.6	1282.5	1342.2	1403.2
20°	984.1	996.8	1016.6	1038.9	1073.8	1112.0	1151.5	1193.4	1252.0	1313.7	1379.2
22.5°	946.5	960.3	982.5	1006.8	1036.2	1072.8	1116.3	1162.4	1223.5	1284.2	1355.3
25°	902.1	911.6	932.0	953.7	982.9	1014.1	1059.2	1110.1	1170.5	1239.9	1312.4
27.5°	860.3	868.6	887.2	906.1	932.5	969.5	1009.8	1061.3	1118.2	1188.5	1268.9
30°	830.2	839.1	855.6	876.0	901.4	933.9	975.2	1023.6	1084.7	1153.4	1237.4
32.5°	804.3	812.1	824.6	845.0	869.9	901.4	939.6	989.0	1050.1	1119.7	1202.2
35°	764.0	773.0	782.5	798.4	820.0	850.6	892.6	939.0	997.5	1065.0	1140.7
37.5°	724.1	733.8	742.3	756.6	776.3	803.2	839.5	887.9	940.8	1005.8	1078.5
40°	699.2	706.8	713.8	729.1	748.8	774.2	807.9	851.2	907.2	967.6	1028.0
42.5°	674.2	681.4	687.3	700.6	718.8	743.2	775.3	817.6	869.5	925.9	979.2
45°	634.9	639.3	646.3	657.8	672.4	694.7	725.9	763.4	807.3	860.7	900.8
47.5°	592.4	599.4	605.1	615.2	627.2	649.0	678.9	710.9	750.6	790.4	818.6
50°	559.9	566.8	575.1	584.7	596.1	616.4	643.9	676.3	709.9	740.5	764.7
52.5°	529.3	535.7	544.6	553.6	567.6	584.8	608.2	637.1	670.2	692.1	712.3
55°	484.1	487.3	497.5	506.4	519.7	532.4	556.0	581.5	601.8	618.4	634.9
57.5°	437.9	442.2	448.1	456.1	469.4	484.3	500.8	523.3	535.3	543.8	556.7
60°	408.4	409.7	413.5	423.0	433.2	446.6	465.7	481.5	490.5	497.5	508.3
62.5°	375.9	376.1	382.5	389.5	397.1	411.5	427.0	439.9	447.2	450.6	461.0
65°	330.2	328.9	332.7	338.5	347.3	356.8	370.2	381.7	381.1	384.8	391.2
67.5°	283.5	282.2	282.2	287.7	294.9	303.5	312.6	319.2	319.3	324.4	327.6
70°	251.9	248.1	250.6	255.1	258.3	265.3	275.5	278.1	278.6	281.2	284.4
72.5°	219.3	218.1	220.1	222.1	224.2	229.7	238.3	239.9	240.0	241.5	246.7
75°	174.3	173.1	171.7	173.7	176.3	180.0	183.2	185.8	185.1	185.8	189.5
77.5°	130.6	127.1	126.5	127.5	128.1	130.4	133.7	133.5	134.1	133.9	138.3
80°	103.7	98.6	97.9	97.9	98.6	99.9	101.1	102.5	100.5	102.5	103.7
82.5°	76.3	73.1	73.0	72.5	72.7	72.9	73.7	74.5	74.1	74.9	75.7
85°	41.9	40.7	38.8	40.1	39.4	37.5	38.8	36.9	36.3	36.9	37.5
87.5°	18.0	18.3	16.9	16.6	15.7	15.9	14.5	13.6	12.7	12.8	13.9
90°	18.8	17.5	15.8	14.1	12.4	10.7	8.9	7.0	5.0	3.0	1.1
92.5°	18.8	17.5	16.0	14.5	13.0	11.5	11.4	12.8	14.1	15.6	16.9
95°	18.8	17.5	26.8	36.0	45.2	54.6	59.5	60.2	61.0	61.7	62.4
97.5°	47.0	53.9	72.2	90.5	108.8	127.1	135.6	134.3	133.0	131.7	130.4
100°	154.3	190.6	189.6	188.7	187.7	186.7	185.9	185.1	184.4	183.7	182.9
102.5°	236.3	243.2	242.6	242.0	241.4	240.8	240.1	239.1	238.3	237.3	236.4
105°	326.4	326.4	326.4	326.4	326.4	326.4	325.9	325.0	324.0	323.0	322.1
107.5°	413.2	413.2	412.7	412.2	411.7	411.2	411.0	411.0	411.0	411.0	411.0
110°	470.3	471.0	470.5	470.0	469.6	469.1	468.8	468.8	468.8	468.8	468.8



TEST NUMBER: P333286-830

CATALOG NUMBER: S125DIP-S1090D1205U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	526.2	527.1	526.8	526.5	526.2	525.9	525.5	524.9	524.3	523.8	523.2
115°	610.3	611.2	611.0	610.8	610.5	610.3	609.5	608.3	607.1	605.9	604.6
117.5°	691.7	693.0	692.0	691.1	690.2	689.3	688.8	688.9	688.9	689.0	689.0
120°	743.3	743.8	743.0	742.3	741.6	740.8	740.6	740.8	741.1	741.3	741.6
122.5°	793.2	793.7	793.4	793.1	792.7	792.4	791.7	790.8	789.9	789.0	788.1
125°	866.6	867.5	867.5	867.5	867.5	867.5	866.7	865.0	863.3	861.6	859.9
127.5°	932.7	933.3	933.4	933.6	933.7	933.9	933.3	932.1	930.9	929.7	928.5
130°	976.4	977.1	976.9	976.7	976.4	976.1	975.4	974.2	973.0	971.8	970.5
132.5°	1016.4	1016.5	1017.1	1017.6	1018.1	1018.7	1018.2	1016.8	1015.4	1014.0	1012.6
135°	1076.3	1076.8	1077.2	1077.8	1078.3	1078.7	1078.3	1076.8	1075.3	1073.8	1072.4
137.5°	1131.2	1131.1	1131.5	1132.0	1132.5	1132.8	1132.5	1131.1	1129.9	1128.7	1127.4
140°	1164.9	1164.4	1164.7	1164.9	1165.2	1165.4	1165.3	1164.8	1164.3	1163.9	1163.3
142.5°	1198.7	1198.6	1198.3	1197.9	1197.6	1197.2	1196.9	1196.7	1196.4	1196.0	1195.7
145°	1245.8	1245.5	1245.5	1245.5	1245.5	1245.5	1245.2	1244.7	1244.3	1243.8	1243.3
147.5°	1286.1	1285.8	1285.5	1285.2	1284.9	1284.6	1284.5	1284.6	1284.7	1284.8	1284.9
150°	1311.6	1311.2	1310.7	1310.2	1309.8	1309.3	1309.3	1309.8	1310.2	1310.7	1311.2
152.5°	1334.5	1334.0	1333.5	1333.0	1332.6	1332.0	1332.3	1333.4	1334.5	1335.6	1336.6
155°	1365.6	1364.9	1364.4	1363.9	1363.4	1362.9	1363.4	1364.9	1366.3	1367.8	1369.2
157.5°	1391.5	1390.7	1390.7	1390.6	1390.6	1390.5	1390.9	1391.9	1392.7	1393.5	1394.5
160°	1407.5	1406.5	1406.3	1406.0	1405.8	1405.5	1406.2	1407.6	1409.1	1410.5	1412.0
162.5°	1421.9	1420.5	1420.3	1420.0	1419.8	1419.6	1420.1	1421.6	1423.1	1424.6	1426.0
165°	1440.9	1439.4	1439.1	1438.9	1438.6	1438.4	1439.0	1440.5	1441.9	1443.4	1444.8
167.5°	1454.9	1453.2	1452.9	1452.6	1452.5	1452.2	1452.8	1454.3	1455.9	1457.4	1458.9
170°	1462.2	1460.2	1459.9	1459.7	1459.4	1459.2	1459.9	1461.6	1463.3	1465.1	1466.8
172.5°	1468.1	1466.3	1465.8	1465.5	1465.0	1464.5	1465.2	1466.9	1468.6	1470.3	1472.0
175°	1474.1	1472.3	1472.0	1471.8	1471.5	1471.2	1471.9	1473.3	1474.8	1476.2	1477.7
177.5°	1477.3	1475.9	1475.7	1475.6	1475.4	1475.2	1475.6	1476.9	1478.0	1479.1	1480.4
180°	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7



TEST NUMBER: P333286-830

CATALOG NUMBER: S125DIP-S1090D1205U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1506.9	1514.1	1518.6	1527.3	1534.5	1538.5	1542.1	1545.1	1548.7	1551.7	1560.4
5°	1516.6	1533.1	1547.2	1568.8	1588.6	1603.8	1620.3	1634.9	1647.0	1664.2	1677.5
7.5°	1512.4	1541.8	1572.6	1606.1	1640.3	1672.1	1701.4	1728.7	1753.5	1783.6	1809.9
10°	1508.4	1548.4	1587.9	1633.0	1679.5	1718.9	1755.9	1793.4	1820.7	1858.9	1891.3
12.5°	1505.3	1552.5	1600.1	1654.4	1705.4	1761.1	1810.2	1837.7	1879.2	1909.8	1948.3
15°	1492.4	1554.8	1620.3	1681.4	1753.9	1805.4	1848.7	1902.1	1941.0	1979.7	2021.8
17.5°	1469.4	1540.0	1613.4	1693.4	1762.9	1818.3	1874.1	1925.5	1971.9	2023.9	2076.2
20°	1458.8	1529.4	1613.4	1695.4	1763.5	1821.4	1878.6	1935.2	1986.1	2053.0	2113.4
22.5°	1436.3	1521.7	1599.1	1679.1	1749.2	1812.2	1877.1	1941.4	2009.0	2084.4	2160.2
25°	1396.4	1482.9	1565.0	1643.9	1714.5	1793.4	1862.7	1948.6	2035.1	2135.0	2229.1
27.5°	1354.9	1437.8	1513.0	1589.1	1671.5	1760.8	1850.8	1948.2	2061.4	2187.5	2320.4
30°	1321.4	1399.6	1472.7	1551.0	1636.8	1737.4	1836.0	1951.7	2082.8	2224.7	2382.5
32.5°	1282.1	1354.2	1425.4	1508.3	1601.8	1707.9	1822.8	1949.7	2107.2	2268.4	2430.8
35°	1215.1	1275.5	1348.7	1437.1	1542.8	1664.2	1797.1	1947.3	2128.0	2313.1	2449.9
37.5°	1135.6	1191.8	1268.9	1365.8	1476.6	1606.9	1764.7	1942.9	2134.8	2282.4	2326.5
40°	1082.1	1134.3	1214.5	1314.9	1428.2	1566.2	1739.3	1927.6	2113.4	2207.5	2171.2
42.5°	1025.1	1079.9	1157.9	1257.4	1379.3	1529.7	1707.2	1895.5	2051.3	2086.9	1961.5
45°	935.2	991.7	1068.7	1169.3	1300.3	1463.2	1648.3	1819.5	1909.1	1844.9	1650.9
47.5°	851.6	904.7	976.0	1079.7	1214.9	1383.4	1561.7	1698.2	1705.3	1552.0	1344.7
50°	794.6	843.6	915.5	1019.2	1153.4	1323.9	1484.8	1592.3	1544.0	1370.3	1171.2
52.5°	738.6	786.6	857.4	960.1	1092.8	1249.1	1398.8	1474.2	1383.2	1204.9	1034.8
55°	657.8	699.7	769.1	863.9	989.9	1134.9	1262.2	1288.3	1169.9	994.3	856.3
57.5°	578.9	618.1	681.2	768.5	883.6	1012.1	1111.6	1106.1	981.0	830.3	720.8
60°	525.5	563.6	619.6	704.8	809.8	920.6	1005.8	985.4	861.4	731.6	639.3
62.5°	477.7	511.7	564.7	639.2	735.0	837.5	907.6	877.5	756.0	642.5	569.7
65°	407.2	435.7	481.0	544.6	624.1	708.7	762.8	724.0	620.3	531.9	473.3
67.5°	339.9	362.8	400.7	451.4	519.2	587.2	620.1	581.1	498.1	433.6	390.2
70°	297.1	317.4	346.7	391.9	451.0	508.3	533.1	498.1	426.9	371.6	340.4
72.5°	254.3	271.2	296.8	337.4	384.8	434.5	456.3	422.8	364.3	317.5	288.4
75°	196.6	208.0	225.8	253.8	291.3	330.8	342.9	313.7	276.1	241.1	222.1
77.5°	140.7	150.4	163.9	181.5	208.1	233.2	243.7	226.9	197.8	175.7	160.0
80°	108.1	113.2	124.7	139.3	160.3	176.3	183.2	172.4	152.0	135.5	123.4
82.5°	77.1	82.2	89.1	101.1	114.5	125.4	132.8	125.5	110.8	97.8	90.9
85°	37.5	40.7	44.5	49.6	59.8	66.2	65.5	61.1	55.3	50.2	46.5
87.5°	13.9	14.7	16.7	19.6	21.5	23.8	25.3	24.5	22.8	21.6	20.3
90°	3.0	5.0	7.0	8.9	10.7	12.4	14.1	15.8	17.5	18.8	20.0
92.5°	15.6	14.1	12.8	11.4	11.5	13.0	14.5	16.0	17.5	18.8	20.0
95°	61.7	61.0	60.2	59.5	54.6	45.2	36.0	26.8	17.5	18.8	20.0
97.5°	131.7	133.0	134.3	135.6	127.1	108.8	90.5	72.2	53.9	47.0	40.2
100°	183.7	184.4	185.1	185.9	186.7	187.7	188.7	189.6	190.6	154.3	118.1
102.5°	237.3	238.3	239.1	240.1	240.8	241.4	242.0	242.6	243.2	236.3	229.4
105°	323.0	324.0	325.0	325.9	326.4	326.4	326.4	326.4	326.4	326.4	326.4
107.5°	411.0	411.0	411.0	411.0	411.2	411.7	412.2	412.7	413.2	413.2	413.3
110°	468.8	468.8	468.8	468.8	469.1	469.6	470.0	470.5	471.0	470.3	469.6



TEST NUMBER: P333286-830

CATALOG NUMBER: S125DIP-S1090D1205U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	523.8	524.3	524.9	525.5	525.9	526.2	526.5	526.8	527.1	526.2	525.3
115°	605.9	607.1	608.3	609.5	610.3	610.5	610.8	611.0	611.2	610.3	609.3
117.5°	689.0	688.9	688.9	688.8	689.3	690.2	691.1	692.0	693.0	691.7	690.4
120°	741.3	741.1	740.8	740.6	740.8	741.6	742.3	743.0	743.8	743.3	742.8
122.5°	789.0	789.9	790.8	791.7	792.4	792.7	793.1	793.4	793.7	793.2	792.8
125°	861.6	863.3	865.0	866.7	867.5	867.5	867.5	867.5	867.5	866.6	865.6
127.5°	929.7	930.9	932.1	933.3	933.9	933.7	933.6	933.4	933.3	932.7	932.2
130°	971.8	973.0	974.2	975.4	976.1	976.4	976.7	976.9	977.1	976.4	975.6
132.5°	1014.0	1015.4	1016.8	1018.2	1018.7	1018.1	1017.6	1017.1	1016.5	1016.4	1016.2
135°	1073.8	1075.3	1076.8	1078.3	1078.7	1078.3	1077.8	1077.2	1076.8	1076.3	1075.8
137.5°	1128.7	1129.9	1131.1	1132.5	1132.8	1132.5	1132.0	1131.5	1131.1	1131.2	1131.3
140°	1163.9	1164.3	1164.8	1165.3	1165.4	1165.2	1164.9	1164.7	1164.4	1164.9	1165.4
142.5°	1196.0	1196.4	1196.7	1196.9	1197.2	1197.6	1197.9	1198.3	1198.6	1198.7	1198.8
145°	1243.8	1244.3	1244.7	1245.2	1245.5	1245.5	1245.5	1245.5	1245.5	1245.8	1245.9
147.5°	1284.8	1284.7	1284.6	1284.5	1284.6	1284.9	1285.2	1285.5	1285.8	1286.1	1286.4
150°	1310.7	1310.2	1309.8	1309.3	1309.3	1309.8	1310.2	1310.7	1311.2	1311.6	1312.2
152.5°	1335.6	1334.5	1333.4	1332.3	1332.0	1332.6	1333.0	1333.5	1334.0	1334.5	1334.9
155°	1367.8	1366.3	1364.9	1363.4	1362.9	1363.4	1363.9	1364.4	1364.9	1365.6	1366.3
157.5°	1393.5	1392.7	1391.9	1390.9	1390.5	1390.6	1390.6	1390.7	1390.7	1391.5	1392.3
160°	1410.5	1409.1	1407.6	1406.2	1405.5	1405.8	1406.0	1406.3	1406.5	1407.5	1408.4
162.5°	1424.6	1423.1	1421.6	1420.1	1419.6	1419.8	1420.0	1420.3	1420.5	1421.9	1423.2
165°	1443.4	1441.9	1440.5	1439.0	1438.4	1438.6	1438.9	1439.1	1439.4	1440.9	1442.3
167.5°	1457.4	1455.9	1454.3	1452.8	1452.2	1452.5	1452.6	1452.9	1453.2	1454.9	1456.7
170°	1465.1	1463.3	1461.6	1459.9	1459.2	1459.4	1459.7	1459.9	1460.2	1462.2	1464.1
172.5°	1470.3	1468.6	1466.9	1465.2	1464.5	1465.0	1465.5	1465.8	1466.3	1468.1	1469.8
175°	1476.2	1474.8	1473.3	1471.9	1471.2	1471.5	1471.8	1472.0	1472.3	1474.1	1476.1
177.5°	1479.1	1478.0	1476.9	1475.6	1475.2	1475.4	1475.6	1475.7	1475.9	1477.3	1478.7
180°	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7



TEST NUMBER: P333286-830

CATALOG NUMBER: S125DIP-S1090D1205U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1567.5	1571.6	1580.3	1577.2	1581.3	1583.3	1585.4
5°	1694.1	1714.5	1723.3	1722.1	1735.5	1732.3	1729.1
7.5°	1837.1	1858.5	1870.5	1885.4	1894.0	1894.6	1902.1
10°	1918.1	1946.1	1957.5	1973.4	1983.6	1989.3	1988.7
12.5°	1980.2	2002.1	2027.7	2035.5	2049.3	2056.4	2053.8
15°	2054.8	2089.8	2116.6	2129.9	2147.1	2152.2	2159.2
17.5°	2121.5	2168.4	2199.6	2241.1	2256.7	2266.2	2260.7
20°	2171.9	2233.6	2264.7	2314.4	2341.7	2356.4	2351.3
22.5°	2231.5	2298.2	2355.9	2398.9	2440.4	2460.2	2464.3
25°	2333.5	2425.1	2509.7	2566.4	2617.8	2629.9	2656.7
27.5°	2447.5	2555.5	2646.0	2705.5	2741.4	2754.9	2763.3
30°	2519.2	2626.8	2694.8	2733.0	2744.4	2743.2	2741.9
32.5°	2554.4	2621.7	2634.8	2624.0	2597.8	2575.7	2552.6
35°	2504.6	2454.4	2379.3	2282.6	2211.3	2139.5	2132.4
37.5°	2252.6	2091.9	1966.9	1827.3	1746.8	1697.0	1662.7
40°	2015.3	1832.8	1681.4	1563.7	1481.7	1449.2	1417.4
42.5°	1757.8	1583.5	1449.3	1350.9	1289.3	1253.3	1228.0
45°	1428.2	1274.2	1169.3	1098.1	1049.0	1021.1	1005.1
47.5°	1170.3	1056.4	967.2	915.9	882.0	860.3	860.4
50°	1031.9	923.1	863.9	823.2	793.9	776.7	780.0
52.5°	909.2	827.9	777.4	743.3	721.7	711.1	710.8
55°	760.3	701.7	668.6	643.9	629.1	617.1	619.6
57.5°	650.3	601.0	578.8	558.2	548.0	543.2	536.1
60°	582.1	543.9	524.8	508.3	498.1	494.3	487.3
62.5°	521.5	491.5	473.0	459.4	450.3	449.0	443.6
65°	438.3	415.4	398.9	392.5	383.0	380.4	380.4
67.5°	361.4	345.0	332.1	326.2	322.1	322.6	319.6
70°	313.0	299.6	291.3	285.0	281.8	282.5	279.9
72.5°	273.8	258.9	251.7	247.9	243.6	245.3	244.3
75°	207.4	199.7	196.0	192.1	189.5	188.3	187.0
77.5°	152.3	145.5	142.6	140.4	140.8	137.8	140.3
80°	117.7	112.0	110.1	106.9	106.2	106.2	105.6
82.5°	86.1	82.9	81.5	78.9	77.8	78.8	77.1
85°	44.5	41.9	41.4	41.4	40.1	38.8	41.9
87.5°	20.5	18.8	18.9	18.6	18.7	18.4	17.4
90°	21.2	22.4	23.4	24.1	24.8	25.5	26.3
92.5°	21.2	22.4	23.2	23.5	23.8	24.2	24.5
95°	21.2	22.4	23.0	23.0	23.0	23.0	23.0
97.5°	33.3	26.4	23.0	23.0	23.0	23.0	23.0
100°	81.8	45.5	26.9	25.9	25.0	23.9	23.0
102.5°	222.6	215.7	204.1	187.5	170.9	154.4	137.8
105°	326.4	326.4	326.3	326.0	325.8	325.6	325.4
107.5°	413.3	413.4	413.0	412.3	411.6	410.9	410.1
110°	468.8	468.1	467.9	468.1	468.3	468.6	468.8



TEST NUMBER: P333286-830

CATALOG NUMBER: S125DIP-S1090D1205U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	524.3	523.4	522.7	522.5	522.1	521.8	521.4
115°	608.3	607.4	606.1	604.6	603.2	601.7	600.3
117.5°	689.2	687.9	686.9	686.3	685.7	685.0	684.4
120°	742.3	741.9	741.0	739.8	738.6	737.4	736.1
122.5°	792.3	791.8	790.8	789.4	788.0	786.6	785.2
125°	864.6	863.7	862.8	862.0	861.4	860.6	859.9
127.5°	931.7	931.1	930.0	928.2	926.3	924.5	922.7
130°	974.9	974.2	973.2	971.9	970.8	969.6	968.4
132.5°	1016.1	1016.0	1015.3	1014.1	1012.9	1011.6	1010.4
135°	1075.3	1074.9	1073.8	1072.4	1070.9	1069.5	1068.0
137.5°	1131.4	1131.5	1131.0	1129.6	1128.4	1127.1	1125.9
140°	1165.8	1166.4	1165.8	1164.4	1163.0	1161.5	1160.1
142.5°	1198.9	1199.0	1198.3	1196.8	1195.4	1193.9	1192.5
145°	1246.2	1246.4	1245.9	1244.3	1242.9	1241.4	1240.0
147.5°	1286.7	1286.9	1286.2	1284.5	1282.7	1281.0	1279.2
150°	1312.7	1313.2	1312.4	1310.5	1308.5	1306.6	1304.7
152.5°	1335.5	1336.0	1335.3	1333.5	1331.8	1330.0	1328.3
155°	1367.1	1367.8	1367.2	1365.3	1363.3	1361.3	1359.4
157.5°	1393.1	1393.8	1393.3	1391.3	1389.4	1387.4	1385.4
160°	1409.4	1410.4	1409.9	1408.0	1406.0	1404.1	1402.1
162.5°	1424.7	1426.0	1425.6	1423.4	1421.3	1419.2	1417.0
165°	1443.8	1445.2	1444.9	1443.0	1441.1	1439.1	1437.2
167.5°	1458.4	1460.2	1460.0	1457.7	1455.6	1453.4	1451.2
170°	1466.0	1468.0	1467.8	1465.7	1463.5	1461.3	1459.1
172.5°	1471.6	1473.3	1473.1	1470.9	1468.8	1466.5	1464.3
175°	1478.1	1480.0	1479.9	1477.7	1475.6	1473.3	1471.1
177.5°	1480.1	1481.4	1481.3	1479.8	1478.2	1476.6	1475.1
180°	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7	1477.7

(END OF REPORT)