

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333303-935

Luminaire Tested: **S125DIP-S1270D365U935-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333303-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1270D365U935-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5548.0 lumens
Efficiency: N/A
Efficacy: 111.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333303-935

CATALOG NUMBER: S125DIP-S1270D365U935-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333303-935

CATALOG NUMBER: S125DIP-S1270D365U935-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	100	100	100	91	91	91	83	83	83	80
1	104	100	96	92	100	96	92	89	88	85	82	80	78	76	74	72	70	67
2	95	87	81	75	91	84	78	73	77	72	68	70	67	63	65	62	59	56
3	87	77	69	63	83	74	66	61	68	62	57	62	58	54	57	54	50	47
4	79	68	60	53	76	65	58	52	60	54	49	56	50	46	51	47	43	41
5	73	61	52	46	70	58	50	45	54	47	42	50	44	40	46	42	38	35
6	67	55	46	40	64	53	45	39	49	42	37	45	40	35	42	37	33	31
7	62	50	41	35	60	48	40	34	44	38	33	41	35	31	38	33	30	27
8	58	45	37	31	55	44	36	31	41	34	29	38	32	28	35	30	27	25
9	54	41	33	28	52	40	33	28	37	31	26	35	29	25	33	28	24	22
10	51	38	31	25	49	37	30	25	35	28	24	32	27	23	30	25	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10959	10959	10959
5°	10983	10878	10949
10°	10916	10802	10864
15°	10797	10672	10717
20°	10628	10490	10509
25°	10446	10274	10264
30°	10221	10041	9991
35°	9980	9790	9653
40°	9732	9517	9382
45°	9465	9270	9085
50°	9171	8969	8699
55°	8888	8631	8389
60°	8548	8289	7994
65°	8145	7878	7610
70°	7757	7402	7149
75°	7069	6835	6598
80°	6289	6189	6044
85°	5476	5572	5269



TEST NUMBER: P333303-935

CATALOG NUMBER: S125DIP-S1270D365U935-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.0	2.9
10°-20°	451.9	8.1
20°-30°	667.3	12.0
30°-40°	778.6	14.0
40°-50°	782.0	14.1
50°-60°	686.5	12.4
60°-70°	511.5	9.2
70°-80°	292.5	5.3
80°-90°	85.9	1.5
90°-100°	109.4	2.0
100°-110°	235.2	4.2
110°-120°	220.7	4.0
120°-130°	178.9	3.2
130°-140°	143.5	2.6
140°-150°	108.3	2.0
150°-160°	76.2	1.4
160°-170°	44.9	0.8
170°-180°	14.6	0.3
0°-30°	1279.2	23.1
0°-40°	2057.8	37.1
0°-60°	3526.3	63.6
0°-90°	4416.2	79.6
90°-120°	565.3	10.2
90°-150°	996.0	18.0
90°-180°	1132.0	20.4
0°-180°	5548.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1697	1697	1697	1697	1697	
5°	1694	1691	1678	1689	1689	161
15°	1615	1610	1596	1602	1603	455
25°	1466	1459	1442	1444	1440	674
35°	1266	1260	1242	1235	1224	791
45°	1036	1030	1015	999	995	798
55°	789	784	766	755	745	704
65°	533	530	516	504	498	529
75°	283	280	274	270	264	302
85°	74	75	75	74	71	82
90°	0	3	5	6	7	5
95°	10	30	270	122	72	11
105°	34	48	221	434	403	36
115°	62	74	177	382	449	60
125°	85	100	170	304	354	76
135°	100	120	169	255	294	77
145°	116	133	169	211	232	73
155°	133	143	165	186	194	61
165°	145	149	158	168	170	41
175°	151	151	152	154	153	14
180°	151	151	151	151	151	



TEST NUMBER: P333303-935

CATALOG NUMBER: S125DIP-S1270D365U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8
2.5°	1701.1	1700.4	1699.7	1698.9	1698.2	1696.7	1694.3	1691.9	1689.5	1687.1	1689.5
5°	1694.1	1693.5	1692.9	1692.3	1691.7	1690.0	1687.0	1683.9	1681.0	1678.0	1680.7
7.5°	1678.5	1677.9	1677.3	1676.7	1676.1	1674.2	1670.9	1667.7	1664.4	1661.1	1663.7
10°	1664.6	1664.0	1663.4	1662.8	1662.2	1660.3	1657.0	1653.7	1650.4	1647.1	1649.5
12.5°	1647.4	1646.3	1645.3	1644.2	1643.1	1641.1	1638.0	1635.0	1631.9	1628.8	1630.8
15°	1614.9	1614.0	1613.1	1612.2	1611.4	1609.2	1605.9	1602.7	1599.4	1596.1	1597.6
17.5°	1577.6	1576.3	1574.9	1573.6	1572.4	1569.9	1566.6	1563.1	1559.8	1556.3	1558.2
20°	1546.4	1545.8	1545.2	1544.6	1544.0	1541.8	1537.9	1534.0	1530.2	1526.3	1528.4
22.5°	1515.3	1514.2	1513.1	1512.1	1511.0	1508.6	1505.0	1501.4	1497.7	1494.1	1495.5
25°	1465.9	1464.4	1462.9	1461.5	1459.9	1457.2	1453.4	1449.5	1445.6	1441.7	1442.3
27.5°	1408.2	1407.3	1406.4	1405.5	1404.6	1402.1	1398.2	1394.1	1390.2	1386.1	1386.3
30°	1370.6	1369.7	1368.8	1367.9	1367.0	1364.3	1359.9	1355.4	1350.9	1346.4	1345.8
32.5°	1329.8	1328.4	1327.1	1325.7	1324.3	1321.6	1317.6	1313.6	1309.6	1305.6	1304.6
35°	1265.8	1264.7	1263.5	1262.3	1261.1	1258.4	1254.2	1250.1	1245.9	1241.7	1240.3
37.5°	1199.5	1198.1	1196.6	1195.1	1193.6	1190.8	1187.0	1183.0	1179.1	1175.2	1172.9
40°	1154.4	1153.0	1151.5	1150.0	1148.5	1145.6	1141.5	1137.3	1133.2	1128.9	1126.3
42.5°	1106.1	1104.9	1103.6	1102.3	1101.1	1098.4	1094.2	1090.0	1085.9	1081.7	1079.3
45°	1036.3	1035.2	1034.0	1032.8	1031.6	1029.2	1025.6	1022.0	1018.5	1014.9	1011.2
47.5°	961.1	961.2	961.3	961.3	961.4	959.2	955.0	950.7	946.4	942.1	938.5
50°	912.8	912.0	911.0	910.2	909.2	907.0	903.4	899.8	896.3	892.7	888.8
52.5°	863.4	862.8	862.1	861.4	860.8	858.6	854.7	850.9	847.1	843.3	839.9
55°	789.4	788.4	787.6	786.6	785.7	783.3	779.0	774.9	770.7	766.5	763.8
57.5°	711.2	710.8	710.2	709.8	709.3	707.3	703.8	700.3	696.7	693.2	689.7
60°	661.8	660.6	659.4	658.2	657.0	654.8	651.5	648.2	645.0	641.7	638.7
62.5°	610.3	609.3	608.4	607.3	606.4	604.6	601.8	598.9	596.2	593.3	590.1
65°	533.0	532.4	531.8	531.2	530.5	528.6	525.3	522.0	518.8	515.5	512.8
67.5°	458.1	456.8	455.6	454.3	453.1	451.2	448.8	446.3	443.8	441.3	439.1
70°	410.8	409.3	407.8	406.3	404.8	402.7	400.0	397.4	394.7	392.0	390.2
72.5°	359.2	358.2	357.2	356.2	355.2	353.8	352.1	350.3	348.6	346.9	344.8
75°	283.3	282.7	282.1	281.5	280.9	279.8	278.4	276.8	275.3	273.9	272.9
77.5°	213.2	212.9	212.7	212.5	212.2	211.7	210.9	210.0	209.1	208.4	207.8
80°	169.1	169.1	169.1	169.1	169.1	168.8	168.2	167.6	167.0	166.4	166.2
82.5°	130.4	130.0	129.5	129.1	128.5	128.3	128.1	128.0	127.9	127.8	127.3
85°	73.9	74.1	74.4	74.7	75.0	75.2	75.2	75.2	75.2	75.2	74.9
87.5°	29.0	29.1	29.3	29.4	29.4	29.4	29.3	29.2	29.0	28.9	28.9
90°	0.3	0.6	1.2	1.8	2.4	3.0	3.4	4.0	4.2	4.9	5.2
92.5°	3.7	4.5	7.1	10.8	16.1	25.0	41.6	69.4	99.7	98.1	79.4
95°	10.1	10.3	12.7	16.1	22.8	36.5	69.1	136.0	220.0	269.6	263.8
97.5°	16.7	17.0	18.8	22.1	28.2	38.0	59.5	108.6	196.5	287.9	333.8
100°	21.3	21.9	23.2	26.4	32.3	41.4	59.1	98.6	175.3	274.7	350.9
102.5°	26.4	26.8	27.7	31.3	36.7	45.5	61.2	94.5	159.2	251.7	340.6
105°	34.4	34.4	35.9	38.9	43.8	52.3	65.7	92.8	143.6	220.6	308.0
107.5°	42.2	42.8	44.3	46.8	51.8	59.5	72.4	95.6	137.1	199.2	274.6
110°	47.8	48.4	49.6	52.3	56.9	64.8	77.3	98.3	135.1	189.2	255.6



TEST NUMBER: P333303-935

CATALOG NUMBER: S125DIP-S1270D365U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	53.4	54.0	54.9	57.7	62.3	69.9	81.9	101.7	135.1	183.4	241.5
115°	61.5	62.1	63.0	65.7	70.3	77.9	89.2	106.8	136.0	177.1	226.1
117.5°	68.8	69.7	70.7	73.4	78.6	85.9	96.6	112.6	138.0	174.0	216.9
120°	73.6	74.6	75.8	78.5	83.7	91.3	101.9	116.6	140.0	172.5	211.8
122.5°	78.8	79.4	80.4	83.2	88.8	96.4	107.0	120.9	141.6	171.3	207.4
125°	85.2	85.8	87.3	90.1	95.8	103.8	113.8	126.9	144.6	169.8	201.5
127.5°	90.2	91.2	93.1	96.6	102.7	110.6	120.3	132.3	147.7	169.1	196.0
130°	93.4	94.4	96.8	100.7	107.1	115.0	124.4	136.0	149.7	168.6	192.3
132.5°	95.8	97.0	100.0	104.4	111.0	118.9	128.4	139.2	151.9	168.6	189.4
135°	99.8	101.0	104.7	109.5	116.0	124.2	133.5	143.6	154.9	168.6	185.9
137.5°	104.8	105.7	109.1	114.0	120.3	128.7	137.3	146.9	157.6	168.9	182.8
140°	107.7	108.7	112.3	117.2	123.0	131.1	140.0	149.1	158.9	169.2	181.3
142.5°	111.2	111.8	115.2	120.1	125.6	133.4	141.6	150.3	159.5	169.4	180.1
145°	116.2	116.8	119.9	124.2	129.7	136.6	144.6	152.1	160.3	169.2	178.3
147.5°	121.6	121.9	124.6	128.5	133.3	139.4	146.4	153.3	160.7	168.4	176.4
150°	124.8	125.4	127.5	131.5	135.7	140.9	147.6	153.9	160.7	167.6	175.0
152.5°	128.2	128.5	130.4	133.9	137.9	142.6	148.8	154.5	160.4	166.7	173.2
155°	132.7	132.7	134.5	137.5	140.6	144.8	150.0	154.9	159.7	165.0	170.4
157.5°	136.7	136.6	138.1	140.7	143.4	146.6	151.0	155.2	158.9	163.1	167.7
160°	139.4	139.1	140.3	142.4	144.8	147.6	151.5	155.2	158.3	161.9	165.6
162.5°	141.5	141.3	142.5	144.4	146.3	148.5	152.1	155.0	157.5	160.4	163.6
165°	144.8	144.2	145.2	146.6	147.9	149.7	152.1	154.5	156.4	158.3	160.7
167.5°	147.1	146.7	147.3	148.1	149.0	150.2	152.1	153.9	154.7	156.1	157.8
170°	148.5	148.2	148.5	149.1	149.7	150.6	152.1	153.3	153.9	154.9	156.1
172.5°	149.5	149.0	149.2	149.8	150.2	150.6	151.9	152.9	153.0	153.4	154.4
175°	150.6	150.0	150.3	150.6	150.6	150.6	151.5	152.1	151.9	151.9	152.1
177.5°	151.2	150.7	150.7	150.9	150.7	150.7	151.2	151.4	150.9	150.9	151.2
180°	150.9	150.9	150.9	150.9	150.9	150.9	150.9	150.9	150.9	150.9	150.9



TEST NUMBER: P333303-935

CATALOG NUMBER: S125DIP-S1270D365U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8
2.5°	1691.9	1694.3	1696.7	1697.7	1697.5	1697.3	1697.0	1696.8
5°	1683.3	1686.1	1688.8	1690.0	1689.6	1689.4	1689.0	1688.8
7.5°	1666.3	1669.0	1671.5	1672.8	1672.5	1672.1	1671.9	1671.5
10°	1651.9	1654.3	1656.7	1657.7	1657.4	1657.1	1656.8	1656.6
12.5°	1632.7	1634.6	1636.5	1637.4	1637.4	1637.3	1637.3	1637.2
15°	1599.1	1600.6	1602.1	1602.8	1602.8	1602.8	1602.8	1602.8
17.5°	1560.0	1561.9	1563.7	1563.9	1562.5	1561.0	1559.4	1558.0
20°	1530.5	1532.6	1534.6	1535.0	1533.4	1532.0	1530.5	1529.0
22.5°	1496.8	1498.2	1499.6	1499.8	1498.7	1497.7	1496.7	1495.7
25°	1442.9	1443.6	1444.2	1444.0	1443.1	1442.2	1441.3	1440.4
27.5°	1386.4	1386.6	1386.6	1386.2	1385.3	1384.5	1383.5	1382.7
30°	1345.2	1344.6	1344.0	1343.3	1342.4	1341.5	1340.6	1339.7
32.5°	1303.5	1302.4	1301.3	1299.9	1298.4	1296.8	1295.1	1293.6
35°	1238.7	1237.3	1235.8	1233.8	1231.4	1229.1	1226.7	1224.3
37.5°	1170.7	1168.5	1166.3	1164.5	1163.1	1161.7	1160.4	1159.0
40°	1123.6	1120.9	1118.2	1116.5	1115.5	1114.7	1113.7	1112.8
42.5°	1076.9	1074.4	1071.9	1070.1	1068.7	1067.3	1065.9	1064.5
45°	1007.7	1004.1	1000.6	998.3	997.4	996.5	995.6	994.7
47.5°	934.8	931.2	927.6	924.7	922.6	920.5	918.4	916.4
50°	884.9	881.1	877.2	874.2	872.1	870.0	868.0	865.8
52.5°	836.5	833.1	829.7	826.8	824.5	822.2	819.8	817.5
55°	761.1	758.5	755.8	753.4	751.3	749.2	747.1	745.0
57.5°	686.3	682.9	679.4	677.1	676.0	674.9	673.6	672.5
60°	635.7	632.7	629.7	627.2	625.1	623.0	621.0	618.9
62.5°	586.9	583.7	580.5	578.1	576.4	574.8	573.2	571.6
65°	510.1	507.4	504.7	502.8	501.6	500.4	499.2	498.0
67.5°	436.9	434.5	432.3	430.8	430.1	429.4	428.7	427.9
70°	388.4	386.6	384.8	383.3	382.1	380.9	379.8	378.6
72.5°	342.9	340.8	338.8	337.2	336.0	334.8	333.6	332.3
75°	272.1	271.1	270.3	269.2	268.0	266.8	265.6	264.4
77.5°	207.2	206.7	206.2	205.5	204.7	203.8	203.0	202.2
80°	165.8	165.6	165.2	164.8	164.2	163.6	163.0	162.5
82.5°	126.7	126.2	125.6	125.4	125.2	125.1	124.9	124.8
85°	74.6	74.3	74.0	73.5	72.9	72.3	71.7	71.1
87.5°	29.0	29.1	29.1	29.0	28.6	28.1	27.6	27.2
90°	5.5	5.8	6.1	6.7	6.7	6.7	7.0	7.0
92.5°	53.9	39.1	29.4	25.0	21.1	20.3	19.9	19.4
95°	218.8	172.5	135.1	109.5	87.9	78.8	76.4	71.5
97.5°	325.8	293.4	256.9	221.4	202.6	185.5	176.8	172.8
100°	374.3	359.4	328.0	296.4	275.3	253.5	242.2	237.4
102.5°	390.5	399.8	384.8	363.3	340.9	325.3	313.1	309.4
105°	381.0	422.7	436.0	432.7	422.9	412.9	406.8	403.2
107.5°	346.6	402.3	436.6	452.5	457.4	457.4	455.4	453.0
110°	321.3	379.2	422.1	447.9	461.6	467.4	469.5	469.5



TEST NUMBER: P333303-935

CATALOG NUMBER: S125DIP-S1270D365U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	301.4	356.3	399.7	430.2	450.1	460.1	465.4	467.6
115°	276.3	323.5	365.2	398.3	422.1	436.6	445.1	449.1
117.5°	260.1	300.7	336.7	367.1	390.8	406.0	414.4	416.8
120°	251.3	287.8	321.3	348.1	370.7	385.2	393.5	395.9
122.5°	244.8	278.6	308.4	333.5	353.6	367.0	375.2	377.4
125°	235.2	266.2	292.7	314.6	331.7	344.1	350.9	353.9
127.5°	225.5	254.4	279.1	299.6	315.1	326.1	332.4	333.8
130°	219.4	246.2	269.9	289.7	304.9	315.0	321.1	322.9
132.5°	213.3	238.4	259.9	279.0	294.2	304.2	309.8	311.9
135°	205.4	226.4	245.9	263.2	276.6	286.6	292.1	293.9
137.5°	198.7	215.7	231.9	246.6	258.6	267.7	272.8	274.7
140°	195.0	209.3	223.3	236.1	247.4	255.3	259.8	261.4
142.5°	191.9	204.0	216.0	227.1	236.7	243.4	247.7	249.0
145°	187.8	197.2	206.6	214.8	222.1	227.3	230.7	231.9
147.5°	183.8	191.5	198.8	205.0	210.8	214.9	216.8	217.4
150°	181.7	188.4	194.2	199.6	204.1	207.8	209.1	209.3
152.5°	179.3	185.2	190.5	194.8	198.5	201.5	202.7	203.0
155°	175.6	180.5	184.7	188.0	191.1	193.2	194.2	194.4
157.5°	171.9	175.9	179.3	181.8	184.3	186.0	186.8	186.8
160°	169.5	172.5	175.6	177.7	179.9	181.3	181.9	181.7
162.5°	166.8	169.6	172.2	174.1	175.7	176.9	177.1	177.0
165°	163.1	165.2	167.0	168.6	169.8	170.4	170.4	170.4
167.5°	159.5	161.0	162.4	163.5	164.1	164.6	164.4	164.3
170°	157.6	158.5	159.5	160.1	160.7	161.0	161.0	160.7
172.5°	155.4	156.4	157.0	157.4	157.5	158.1	157.6	157.2
175°	153.1	153.1	153.7	153.7	153.7	153.9	153.3	153.1
177.5°	151.4	151.6	151.6	151.6	151.4	151.6	150.9	150.9
180°	150.9	150.9	150.9	150.9	150.9	150.9	150.9	150.9

(END OF REPORT)