

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333260-830

Luminaire Tested: **S125DIP-S1090D590U830-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333260-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1090D590U830-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6158.9 lumens
Efficiency: N/A
Efficacy: 126.2 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333260-830

CATALOG NUMBER: S125DIP-S1090D590U830-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333260-830

CATALOG NUMBER: S125DIP-S1090D590U830-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	69
1	102	98	94	91	96	93	89	86	83	80	78	74	72	70	65	64	63	59
2	93	86	80	75	88	81	76	71	73	69	65	65	62	59	58	55	53	49
3	85	76	68	62	80	72	65	60	65	59	55	58	54	50	51	48	46	42
4	78	67	59	53	74	64	57	51	58	52	47	52	47	43	46	42	39	36
5	72	60	52	46	68	57	50	44	52	46	41	46	42	38	42	38	34	32
6	66	54	46	40	63	52	44	38	47	40	36	42	37	33	38	34	30	28
7	62	49	41	35	58	47	39	34	42	36	32	38	33	29	35	30	27	25
8	57	45	37	31	54	43	35	30	39	33	28	35	30	26	32	27	24	22
9	53	41	33	28	50	39	32	27	36	30	25	32	27	24	29	25	22	20
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9680	9680	9680	9680
5°	11210	9713	8504	9713
10°	13042	9663	7451	9663
15°	14437	9591	6873	9591
20°	16160	9479	6410	9479
25°	18932	9352	6183	9352
30°	20448	9228	5988	9228
35°	16812	8993	5858	8993
40°	11950	8667	5718	8667
45°	9180	8227	5636	8227
50°	7837	7683	5626	7683
55°	6977	7149	5674	7149
60°	6294	6566	5818	6566
65°	5813	5978	5969	5978
70°	5285	5370	6056	5370
75°	4666	4729	5999	4729
80°	3927	3857	5490	3857
85°	3105	2779	4431	2779



TEST NUMBER: P333260-830

CATALOG NUMBER: S125DIP-S1090D590U830-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.3	2.3
10°-20°	429.6	7.0
20°-30°	697.6	11.3
30°-40°	850.9	13.8
40°-50°	774.1	12.6
50°-60°	616.6	10.0
60°-70°	429.5	7.0
70°-80°	229.0	3.7
80°-90°	59.3	1.0
90°-100°	46.3	0.8
100°-110°	136.7	2.2
110°-120°	231.5	3.8
120°-130°	304.6	4.9
130°-140°	341.3	5.5
140°-150°	334.5	5.4
150°-160°	281.0	4.6
160°-170°	186.8	3.0
170°-180°	65.4	1.1
0°-30°	1271.5	20.6
0°-40°	2122.4	34.5
0°-60°	3513.1	57.0
0°-90°	4230.9	68.7
90°-120°	414.4	6.7
90°-150°	1394.9	22.6
90°-180°	1928.0	31.3
0°-180°	6158.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1499	1499	1499	1499	1499	
5°	1729	1498	1312	1498	1729	174
15°	2159	1434	1028	1434	2159	618
25°	2657	1312	868	1312	2657	1213
35°	2132	1141	743	1141	2132	1305
45°	1005	901	617	901	1005	804
55°	620	635	504	635	620	558
65°	380	391	391	391	380	378
75°	187	190	240	190	187	201
85°	42	38	60	38	42	49
90°	13	1	13	1	13	9
95°	46	35	46	35	46	47
105°	133	123	133	123	133	141
115°	234	232	234	232	234	231
125°	340	338	340	338	340	304
135°	442	440	442	440	442	341
145°	535	533	535	533	535	334
155°	610	610	610	610	610	281
165°	661	663	661	663	661	186
175°	687	689	687	689	687	65
180°	691	691	691	691	691	



TEST NUMBER: P333260-830

CATALOG NUMBER: S125DIP-S1090D590U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1585.4	1583.3	1581.3	1577.2	1580.3	1571.6	1567.5	1560.4	1551.7	1548.7	1545.1
5°	1729.1	1732.3	1735.5	1722.1	1723.3	1714.5	1694.1	1677.5	1664.2	1647.0	1634.9
7.5°	1902.1	1894.6	1894.0	1885.4	1870.5	1858.5	1837.1	1809.9	1783.6	1753.5	1728.7
10°	1988.7	1989.3	1983.6	1973.4	1957.5	1946.1	1918.1	1891.3	1858.9	1820.7	1793.4
12.5°	2053.8	2056.4	2049.3	2035.5	2027.7	2002.1	1980.2	1948.3	1909.8	1879.2	1837.7
15°	2159.2	2152.2	2147.1	2129.9	2116.6	2089.8	2054.8	2021.8	1979.7	1941.0	1902.1
17.5°	2260.7	2266.2	2256.7	2241.1	2199.6	2168.4	2121.5	2076.2	2023.9	1971.9	1925.5
20°	2351.3	2356.4	2341.7	2314.4	2264.7	2233.6	2171.9	2113.4	2053.0	1986.1	1935.2
22.5°	2464.3	2460.2	2440.4	2398.9	2355.9	2298.2	2231.5	2160.2	2084.4	2009.0	1941.4
25°	2656.7	2629.9	2617.8	2566.4	2509.7	2425.1	2333.5	2229.1	2135.0	2035.1	1948.6
27.5°	2763.3	2754.9	2741.4	2705.5	2646.0	2555.5	2447.5	2320.4	2187.5	2061.4	1948.2
30°	2741.9	2743.2	2744.4	2733.0	2694.8	2626.8	2519.2	2382.5	2224.7	2082.8	1951.7
32.5°	2552.6	2575.7	2597.8	2624.0	2634.8	2621.7	2554.4	2430.8	2268.4	2107.2	1949.7
35°	2132.4	2139.5	2211.3	2282.6	2379.3	2454.4	2504.6	2449.9	2313.1	2128.0	1947.3
37.5°	1662.7	1697.0	1746.8	1827.3	1966.9	2091.9	2252.6	2326.5	2282.4	2134.8	1942.9
40°	1417.4	1449.2	1481.7	1563.7	1681.4	1832.8	2015.3	2171.2	2207.5	2113.4	1927.6
42.5°	1228.0	1253.3	1289.3	1350.9	1449.3	1583.5	1757.8	1961.5	2086.9	2051.3	1895.5
45°	1005.1	1021.1	1049.0	1098.1	1169.3	1274.2	1428.2	1650.9	1844.9	1909.1	1819.5
47.5°	860.4	860.3	882.0	915.9	967.2	1056.4	1170.3	1344.7	1552.0	1705.3	1698.2
50°	780.0	776.7	793.9	823.2	863.9	923.1	1031.9	1171.2	1370.3	1544.0	1592.3
52.5°	710.8	711.1	721.7	743.3	777.4	827.9	909.2	1034.8	1204.9	1383.2	1474.2
55°	619.6	617.1	629.1	643.9	668.6	701.7	760.3	856.3	994.3	1169.9	1288.3
57.5°	536.1	543.2	548.0	558.2	578.8	601.0	650.3	720.8	830.3	981.0	1106.1
60°	487.3	494.3	498.1	508.3	524.8	543.9	582.1	639.3	731.6	861.4	985.4
62.5°	443.6	449.0	450.3	459.4	473.0	491.5	521.5	569.7	642.5	756.0	877.5
65°	380.4	380.4	383.0	392.5	398.9	415.4	438.3	473.3	531.9	620.3	724.0
67.5°	319.6	322.6	322.1	326.2	332.1	345.0	361.4	390.2	433.6	498.1	581.1
70°	279.9	282.5	281.8	285.0	291.3	299.6	313.0	340.4	371.6	426.9	498.1
72.5°	244.3	245.3	243.6	247.9	251.7	258.9	273.8	288.4	317.5	364.3	422.8
75°	187.0	188.3	189.5	192.1	196.0	199.7	207.4	222.1	241.1	276.1	313.7
77.5°	140.3	137.8	140.8	140.4	142.6	145.5	152.3	160.0	175.7	197.8	226.9
80°	105.6	106.2	106.2	106.9	110.1	112.0	117.7	123.4	135.5	152.0	172.4
82.5°	77.1	78.8	77.8	78.9	81.5	82.9	86.1	90.9	97.8	110.8	125.5
85°	41.9	38.8	40.1	41.4	41.4	41.9	44.5	46.5	50.2	55.3	61.1
87.5°	14.8	15.7	16.2	16.1	16.6	16.5	18.4	18.3	19.7	21.0	22.9
90°	12.9	12.5	12.2	11.9	11.5	11.0	10.4	9.8	9.2	8.6	7.7
92.5°	25.4	25.1	24.9	24.6	24.3	23.8	23.0	22.2	21.4	20.6	19.6
95°	46.3	46.0	45.8	45.5	45.2	44.8	43.9	43.1	42.2	41.4	40.2
97.5°	70.1	69.9	69.8	69.7	69.6	69.1	68.3	67.5	66.7	65.9	64.3
100°	88.2	87.9	87.8	87.5	87.2	86.5	85.5	84.5	83.3	82.3	80.7
102.5°	106.2	105.9	105.6	105.3	104.9	104.2	103.0	101.8	100.7	99.4	98.7
105°	133.4	133.0	132.6	132.2	132.0	131.4	130.6	130.0	129.2	128.5	127.8
107.5°	161.1	161.1	161.2	161.2	161.2	161.0	160.7	160.3	159.9	159.6	159.0
110°	181.7	181.8	182.0	182.1	182.2	182.1	181.7	181.3	181.1	180.7	180.3



TEST NUMBER: P333260-830

CATALOG NUMBER: S125DIP-S1090D590U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	202.0	202.2	202.4	202.6	202.8	202.8	202.6	202.6	202.4	202.2	201.7
115°	233.9	234.0	234.1	234.2	234.4	234.5	234.6	234.7	234.9	235.0	234.7
117.5°	265.0	265.6	266.1	266.6	267.0	267.2	267.1	267.0	266.9	266.8	266.6
120°	286.6	287.1	287.6	288.0	288.5	288.7	288.7	288.7	288.7	288.7	288.6
122.5°	308.1	308.5	308.9	309.2	309.6	309.9	310.0	310.1	310.2	310.3	309.9
125°	340.4	340.4	340.6	340.7	340.8	341.0	341.3	341.5	341.8	342.0	341.9
127.5°	371.4	371.6	371.8	372.0	372.3	372.5	372.6	372.7	372.9	373.0	372.8
130°	392.0	392.2	392.5	392.7	392.9	393.1	393.2	393.3	393.5	393.6	393.3
132.5°	411.3	411.7	412.0	412.4	412.6	412.9	413.0	413.1	413.3	413.4	413.4
135°	441.5	442.0	442.4	442.9	443.4	443.6	443.6	443.6	443.6	443.6	443.5
137.5°	470.9	471.6	472.1	472.7	473.3	473.5	473.3	473.3	473.1	473.0	472.7
140°	489.8	490.4	491.1	491.6	492.2	492.4	492.2	491.9	491.7	491.4	491.1
142.5°	507.9	508.5	509.1	509.7	510.3	510.5	510.4	510.2	510.1	509.9	509.5
145°	535.0	535.4	535.7	536.1	536.4	536.6	536.6	536.6	536.6	536.6	536.3
147.5°	558.2	558.9	559.8	560.5	561.4	561.7	561.4	561.1	560.8	560.5	560.2
150°	575.3	575.6	575.8	576.1	576.3	576.4	576.4	576.4	576.4	576.4	575.9
152.5°	589.6	589.9	590.4	590.8	591.3	591.4	591.1	590.8	590.5	590.2	589.9
155°	609.7	610.3	611.0	611.5	612.2	612.2	611.7	611.2	610.8	610.3	610.2
157.5°	626.6	627.5	628.2	629.0	629.8	629.9	629.4	629.0	628.5	628.0	627.9
160°	638.3	638.9	639.4	640.1	640.6	640.6	640.2	639.7	639.2	638.8	638.7
162.5°	648.1	648.8	649.5	650.3	650.9	651.0	650.4	649.8	649.2	648.7	648.7
165°	661.4	662.0	662.8	663.5	664.2	664.4	663.8	663.4	662.9	662.4	662.3
167.5°	671.9	672.6	673.4	674.1	674.9	674.9	674.2	673.4	672.7	672.0	672.0
170°	677.5	678.3	679.2	680.0	680.8	680.9	680.1	679.5	678.7	678.1	678.1
172.5°	682.2	683.0	683.7	684.5	685.2	685.2	684.5	683.8	683.1	682.3	682.3
175°	686.6	687.5	688.3	689.2	689.9	690.0	689.3	688.6	687.9	687.2	687.2
177.5°	689.2	689.8	690.6	691.3	691.9	691.9	691.4	690.8	690.2	689.7	689.8
180°	691.0	691.0	691.0	691.0	691.0	691.0	691.0	691.0	691.0	691.0	691.0



TEST NUMBER: P333260-830

CATALOG NUMBER: S125DIP-S1090D590U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1542.1	1538.5	1534.5	1527.3	1518.6	1514.1	1506.9	1502.4	1493.2	1485.5	1477.4
5°	1620.3	1603.8	1588.6	1568.8	1547.2	1533.1	1516.6	1498.2	1479.1	1459.3	1437.8
7.5°	1701.4	1672.1	1640.3	1606.1	1572.6	1541.8	1512.4	1483.6	1456.6	1424.0	1396.4
10°	1755.9	1718.9	1679.5	1633.0	1587.9	1548.4	1508.4	1473.4	1437.8	1399.6	1365.8
12.5°	1810.2	1761.1	1705.4	1654.4	1600.1	1552.5	1505.3	1460.7	1415.9	1373.7	1334.3
15°	1848.7	1805.4	1753.9	1681.4	1620.3	1554.8	1492.4	1434.5	1380.4	1333.4	1283.8
17.5°	1874.1	1818.3	1762.9	1693.4	1613.4	1540.0	1469.4	1403.2	1342.2	1282.5	1234.6
20°	1878.6	1821.4	1763.5	1695.4	1613.4	1529.4	1458.8	1379.2	1313.7	1252.0	1193.4
22.5°	1877.1	1812.2	1749.2	1679.1	1599.1	1521.7	1436.3	1355.3	1284.2	1223.5	1162.4
25°	1862.7	1793.4	1714.5	1643.9	1565.0	1482.9	1396.4	1312.4	1239.9	1170.5	1110.1
27.5°	1850.8	1760.8	1671.5	1589.1	1513.0	1437.8	1354.9	1268.9	1188.5	1118.2	1061.3
30°	1836.0	1737.4	1636.8	1551.0	1472.7	1399.6	1321.4	1237.4	1153.4	1084.7	1023.6
32.5°	1822.8	1707.9	1601.8	1508.3	1425.4	1354.2	1282.1	1202.2	1119.7	1050.1	989.0
35°	1797.1	1664.2	1542.8	1437.1	1348.7	1275.5	1215.1	1140.7	1065.0	997.5	939.0
37.5°	1764.7	1606.9	1476.6	1365.8	1268.9	1191.8	1135.6	1078.5	1005.8	940.8	887.9
40°	1739.3	1566.2	1428.2	1314.9	1214.5	1134.3	1082.1	1028.0	967.6	907.2	851.2
42.5°	1707.2	1529.7	1379.3	1257.4	1157.9	1079.9	1025.1	979.2	925.9	869.5	817.6
45°	1648.3	1463.2	1300.3	1169.3	1068.7	991.7	935.2	900.8	860.7	807.3	763.4
47.5°	1561.7	1383.4	1214.9	1079.7	976.0	904.7	851.6	818.6	790.4	750.6	710.9
50°	1484.8	1323.9	1153.4	1019.2	915.5	843.6	794.6	764.7	740.5	709.9	676.3
52.5°	1398.8	1249.1	1092.8	960.1	857.4	786.6	738.6	712.3	692.1	670.2	637.1
55°	1262.2	1134.9	989.9	863.9	769.1	699.7	657.8	634.9	618.4	601.8	581.5
57.5°	1111.6	1012.1	883.6	768.5	681.2	618.1	578.9	556.7	543.8	535.3	523.3
60°	1005.8	920.6	809.8	704.8	619.6	563.6	525.5	508.3	497.5	490.5	481.5
62.5°	907.6	837.5	735.0	639.2	564.7	511.7	477.7	461.0	450.6	447.2	439.9
65°	762.8	708.7	624.1	544.6	481.0	435.7	407.2	391.2	384.8	381.1	381.7
67.5°	620.1	587.2	519.2	451.4	400.7	362.8	339.9	327.6	324.4	319.3	319.2
70°	533.1	508.3	451.0	391.9	346.7	317.4	297.1	284.4	281.2	278.6	278.1
72.5°	456.3	434.5	384.8	337.4	296.8	271.2	254.3	246.7	241.5	240.0	239.9
75°	342.9	330.8	291.3	253.8	225.8	208.0	196.6	189.5	185.8	185.1	185.8
77.5°	243.7	233.2	208.1	181.5	163.9	150.4	140.7	138.3	133.9	134.1	133.5
80°	183.2	176.3	160.3	139.3	124.7	113.2	108.1	103.7	102.5	100.5	102.5
82.5°	132.8	125.4	114.5	101.1	89.1	82.2	77.1	75.7	74.9	74.1	74.5
85°	65.5	66.2	59.8	49.6	44.5	40.7	37.5	37.5	36.9	36.3	36.9
87.5°	23.8	22.6	20.4	18.7	15.9	14.2	13.6	13.9	12.5	12.2	12.9
90°	7.0	6.1	5.3	4.3	3.4	2.5	1.5	0.6	1.5	2.5	3.4
92.5°	18.6	17.5	16.5	15.6	15.0	14.3	13.7	13.0	13.7	14.3	15.0
95°	39.0	37.8	36.7	35.9	35.6	35.4	35.2	35.0	35.2	35.4	35.6
97.5°	62.6	61.0	59.3	58.4	58.3	58.2	58.2	58.1	58.2	58.2	58.3
100°	79.2	77.6	76.1	75.3	75.3	75.3	75.3	75.3	75.3	75.3	75.3
102.5°	97.9	97.1	96.3	95.7	95.2	94.7	94.3	93.8	94.3	94.7	95.2
105°	127.1	126.4	125.6	125.0	124.4	123.8	123.2	122.6	123.2	123.8	124.4
107.5°	158.4	158.0	157.4	156.8	156.2	155.6	155.0	154.4	155.0	155.6	156.2
110°	179.9	179.6	179.3	178.8	178.1	177.6	176.9	176.3	176.9	177.6	178.1



TEST NUMBER: P333260-830

CATALOG NUMBER: S125DIP-S1090D590U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	201.2	200.9	200.4	200.0	199.6	199.3	199.1	198.7	199.1	199.3	199.6
115°	234.5	234.2	234.0	233.7	233.2	232.7	232.2	231.8	232.2	232.7	233.2
117.5°	266.4	266.2	266.0	265.7	265.5	265.3	265.0	264.9	265.0	265.3	265.5
120°	288.5	288.4	288.2	287.9	287.3	286.7	286.2	285.5	286.2	286.7	287.3
122.5°	309.6	309.3	309.0	308.8	308.5	308.3	308.1	307.9	308.1	308.3	308.5
125°	341.8	341.6	341.5	341.1	340.4	339.6	338.9	338.2	338.9	339.6	340.4
127.5°	372.7	372.5	372.4	372.1	371.6	371.3	370.9	370.5	370.9	371.3	371.6
130°	393.1	392.9	392.7	392.2	391.6	391.1	390.4	389.8	390.4	391.1	391.6
132.5°	413.5	413.5	413.6	413.1	412.1	411.1	410.2	409.2	410.2	411.1	412.1
135°	443.4	443.3	443.1	442.7	442.0	441.3	440.5	439.8	440.5	441.3	442.0
137.5°	472.4	472.2	471.9	471.5	470.7	470.0	469.4	468.6	469.4	470.0	470.7
140°	490.8	490.4	490.0	489.6	488.9	488.3	487.8	487.1	487.8	488.3	488.9
142.5°	509.1	508.6	508.1	507.7	507.2	506.6	506.1	505.7	506.1	506.6	507.2
145°	535.9	535.6	535.2	534.8	534.3	533.9	533.3	532.8	533.3	533.9	534.3
147.5°	560.0	559.6	559.3	559.1	558.8	558.6	558.3	558.0	558.3	558.6	558.8
150°	575.4	575.0	574.5	574.3	574.5	574.6	574.7	574.8	574.7	574.6	574.5
152.5°	589.7	589.6	589.4	589.2	589.1	588.9	588.7	588.5	588.7	588.9	589.1
155°	610.0	609.9	609.8	609.7	609.7	609.7	609.7	609.7	609.7	609.7	609.7
157.5°	627.8	627.6	627.5	627.6	627.9	628.1	628.4	628.7	628.4	628.1	627.9
160°	638.6	638.4	638.3	638.4	638.8	639.1	639.5	639.9	639.5	639.1	638.8
162.5°	648.7	648.6	648.6	648.7	648.9	649.2	649.5	649.8	649.5	649.2	648.9
165°	662.2	662.0	661.9	662.0	662.2	662.5	662.7	663.0	662.7	662.5	662.2
167.5°	672.0	672.0	672.0	672.2	672.7	673.2	673.7	674.2	673.7	673.2	672.7
170°	678.1	678.1	678.1	678.3	678.7	679.2	679.7	680.1	679.7	679.2	678.7
172.5°	682.3	682.3	682.3	682.6	683.1	683.5	684.0	684.5	684.0	683.5	683.1
175°	687.2	687.2	687.2	687.4	687.9	688.3	688.8	689.3	688.8	688.3	687.9
177.5°	689.8	689.9	690.0	690.2	690.7	691.1	691.4	691.8	691.4	691.1	690.7
180°	691.0	691.0	691.0	691.0	691.0	691.0	691.0	691.0	691.0	691.0	691.0



TEST NUMBER: P333260-830

CATALOG NUMBER: S125DIP-S1090D590U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1472.8	1467.3	1462.6	1452.5	1446.9	1439.3	1433.1	1439.7	1432.7	1435.7	1431.2
5°	1426.9	1409.1	1396.4	1377.9	1362.1	1347.4	1336.6	1334.6	1329.6	1327.0	1319.4
7.5°	1371.7	1349.4	1327.6	1303.3	1283.0	1262.3	1249.1	1238.1	1230.9	1221.3	1214.8
10°	1339.2	1309.2	1283.8	1254.5	1229.1	1206.8	1189.0	1180.1	1171.9	1159.7	1155.3
12.5°	1298.9	1268.0	1237.0	1205.7	1181.2	1156.4	1141.1	1127.7	1121.9	1108.3	1106.9
15°	1250.8	1204.3	1173.7	1141.9	1108.2	1087.9	1075.2	1060.5	1054.1	1044.6	1037.6
17.5°	1193.2	1151.7	1113.5	1080.6	1051.7	1034.5	1018.8	1008.7	997.8	991.6	980.1
20°	1151.5	1112.0	1073.8	1038.9	1016.6	996.8	984.1	974.6	963.2	960.0	948.6
22.5°	1116.3	1072.8	1036.2	1006.8	982.5	960.3	946.5	940.0	932.1	922.3	920.0
25°	1059.2	1014.1	982.9	953.7	932.0	911.6	902.1	893.8	886.2	879.2	876.7
27.5°	1009.8	969.5	932.5	906.1	887.2	868.6	860.3	850.2	844.6	839.0	832.1
30°	975.2	933.9	901.4	876.0	855.6	839.1	830.2	823.2	818.1	813.0	809.2
32.5°	939.6	901.4	869.9	845.0	824.6	812.1	804.3	799.3	793.7	787.6	782.8
35°	892.6	850.6	820.0	798.4	782.5	773.0	764.0	759.6	753.2	753.2	748.1
37.5°	839.5	803.2	776.3	756.6	742.3	733.8	724.1	721.0	717.0	714.3	712.5
40°	807.9	774.2	748.8	729.1	713.8	706.8	699.2	694.1	691.5	688.3	687.0
42.5°	775.3	743.2	718.8	700.6	687.3	681.4	674.2	670.6	665.5	661.4	660.6
45°	725.9	694.7	672.4	657.8	646.3	639.3	634.9	627.3	624.7	619.6	619.0
47.5°	678.9	649.0	627.2	615.2	605.1	599.4	592.4	584.8	581.8	579.3	579.0
50°	643.9	616.4	596.1	584.7	575.1	566.8	559.9	554.8	552.8	552.8	554.1
52.5°	608.2	584.8	567.6	553.6	544.6	535.7	529.3	526.2	523.3	526.4	528.7
55°	556.0	532.4	519.7	506.4	497.5	487.3	484.1	482.9	481.0	486.1	488.6
57.5°	500.8	484.3	469.4	456.1	448.1	442.2	437.9	437.2	440.7	443.2	451.4
60°	465.7	446.6	433.2	423.0	413.5	409.7	408.4	407.2	409.7	416.7	427.5
62.5°	427.0	411.5	397.1	389.5	382.5	376.1	375.9	376.6	381.7	389.7	400.5
65°	370.2	356.8	347.3	338.5	332.7	328.9	330.2	332.7	338.5	349.2	361.4
67.5°	312.6	303.5	294.9	287.7	282.2	282.2	283.5	287.3	294.1	306.5	317.5
70°	275.5	265.3	258.3	255.1	250.6	248.1	251.9	258.3	264.0	275.5	285.0
72.5°	238.3	229.7	224.2	222.1	220.1	218.1	219.3	226.2	233.9	245.4	256.5
75°	183.2	180.0	176.3	173.7	171.7	173.1	174.3	180.7	187.0	199.2	211.9
77.5°	133.7	130.4	128.1	127.5	126.5	127.1	130.6	135.3	141.6	150.4	160.0
80°	101.1	99.9	98.6	97.9	97.9	98.6	103.7	106.9	112.6	120.8	128.5
82.5°	73.7	72.9	72.7	72.5	73.0	73.1	76.3	80.4	85.1	91.3	97.9
85°	38.8	37.5	39.4	40.1	38.8	40.7	41.9	44.5	46.5	49.6	52.8
87.5°	13.6	14.8	14.4	15.1	15.3	16.5	16.1	18.3	19.4	20.5	20.1
90°	4.3	5.3	6.1	7.0	7.7	8.6	9.2	9.8	10.4	11.0	11.5
92.5°	15.6	16.5	17.5	18.6	19.6	20.6	21.4	22.2	23.0	23.8	24.3
95°	35.9	36.7	37.8	39.0	40.2	41.4	42.2	43.1	43.9	44.8	45.2
97.5°	58.4	59.3	61.0	62.6	64.3	65.9	66.7	67.5	68.3	69.1	69.6
100°	75.3	76.1	77.6	79.2	80.7	82.3	83.3	84.5	85.5	86.5	87.2
102.5°	95.7	96.3	97.1	97.9	98.7	99.4	100.7	101.8	103.0	104.2	104.9
105°	125.0	125.6	126.4	127.1	127.8	128.5	129.2	130.0	130.6	131.4	132.0
107.5°	156.8	157.4	158.0	158.4	159.0	159.6	159.9	160.3	160.7	161.0	161.2
110°	178.8	179.3	179.6	179.9	180.3	180.7	181.1	181.3	181.7	182.1	182.2



TEST NUMBER: P333260-830

CATALOG NUMBER: S125DIP-S1090D590U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	200.0	200.4	200.9	201.2	201.7	202.2	202.4	202.6	202.6	202.8	202.8
115°	233.7	234.0	234.2	234.5	234.7	235.0	234.9	234.7	234.6	234.5	234.4
117.5°	265.7	266.0	266.2	266.4	266.6	266.8	266.9	267.0	267.1	267.2	267.0
120°	287.9	288.2	288.4	288.5	288.6	288.7	288.7	288.7	288.7	288.7	288.5
122.5°	308.8	309.0	309.3	309.6	309.9	310.3	310.2	310.1	310.0	309.9	309.6
125°	341.1	341.5	341.6	341.8	341.9	342.0	341.8	341.5	341.3	341.0	340.8
127.5°	372.1	372.4	372.5	372.7	372.8	373.0	372.9	372.7	372.6	372.5	372.3
130°	392.2	392.7	392.9	393.1	393.3	393.6	393.5	393.3	393.2	393.1	392.9
132.5°	413.1	413.6	413.5	413.5	413.4	413.4	413.3	413.1	413.0	412.9	412.6
135°	442.7	443.1	443.3	443.4	443.5	443.6	443.6	443.6	443.6	443.6	443.4
137.5°	471.5	471.9	472.2	472.4	472.7	473.0	473.1	473.3	473.3	473.5	473.3
140°	489.6	490.0	490.4	490.8	491.1	491.4	491.7	491.9	492.2	492.4	492.2
142.5°	507.7	508.1	508.6	509.1	509.5	509.9	510.1	510.2	510.4	510.5	510.3
145°	534.8	535.2	535.6	535.9	536.3	536.6	536.6	536.6	536.6	536.6	536.4
147.5°	559.1	559.3	559.6	560.0	560.2	560.5	560.8	561.1	561.4	561.7	561.4
150°	574.3	574.5	575.0	575.4	575.9	576.4	576.4	576.4	576.4	576.4	576.3
152.5°	589.2	589.4	589.6	589.7	589.9	590.2	590.5	590.8	591.1	591.4	591.3
155°	609.7	609.8	609.9	610.0	610.2	610.3	610.8	611.2	611.7	612.2	612.2
157.5°	627.6	627.5	627.6	627.8	627.9	628.0	628.5	629.0	629.4	629.9	629.8
160°	638.4	638.3	638.4	638.6	638.7	638.8	639.2	639.7	640.2	640.6	640.6
162.5°	648.7	648.6	648.6	648.7	648.7	648.7	649.2	649.8	650.4	651.0	650.9
165°	662.0	661.9	662.0	662.2	662.3	662.4	662.9	663.4	663.8	664.4	664.2
167.5°	672.2	672.0	672.0	672.0	672.0	672.0	672.7	673.4	674.2	674.9	674.9
170°	678.3	678.1	678.1	678.1	678.1	678.1	678.7	679.5	680.1	680.9	680.8
172.5°	682.6	682.3	682.3	682.3	682.3	682.3	683.1	683.8	684.5	685.2	685.2
175°	687.4	687.2	687.2	687.2	687.2	687.2	687.9	688.6	689.3	690.0	689.9
177.5°	690.2	690.0	689.9	689.8	689.8	689.7	690.2	690.8	691.4	691.9	691.9
180°	691.0	691.0	691.0	691.0	691.0	691.0	691.0	691.0	691.0	691.0	691.0



TEST NUMBER: P333260-830

CATALOG NUMBER: S125DIP-S1090D590U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1428.0	1431.6	1428.6	1432.7	1428.6	1431.6	1428.0	1431.2	1435.7	1432.7	1439.7
5°	1316.3	1310.5	1314.3	1311.7	1314.3	1310.5	1316.3	1319.4	1327.0	1329.6	1334.6
7.5°	1213.0	1207.5	1201.2	1198.3	1201.2	1207.5	1213.0	1214.8	1221.3	1230.9	1238.1
10°	1148.3	1141.3	1140.7	1136.2	1140.7	1141.3	1148.3	1155.3	1159.7	1171.9	1180.1
12.5°	1101.0	1094.5	1087.2	1085.3	1087.2	1094.5	1101.0	1106.9	1108.3	1121.9	1127.7
15°	1033.8	1028.7	1024.3	1028.0	1024.3	1028.7	1033.8	1037.6	1044.6	1054.1	1060.5
17.5°	977.9	973.7	973.0	968.3	973.0	973.7	977.9	980.1	991.6	997.8	1008.7
20°	942.8	939.6	940.9	932.6	940.9	939.6	942.8	948.6	960.0	963.2	974.6
22.5°	914.8	908.6	907.9	906.2	907.9	908.6	914.8	920.0	922.3	932.1	940.0
25°	870.9	867.7	864.6	867.7	864.6	867.7	870.9	876.7	879.2	886.2	893.8
27.5°	832.6	828.8	827.9	828.3	827.9	828.8	832.6	832.1	839.0	844.6	850.2
30°	809.2	802.9	803.5	802.9	803.5	802.9	809.2	809.2	813.0	818.1	823.2
32.5°	783.7	779.4	778.5	777.4	778.5	779.4	783.7	782.8	787.6	793.7	799.3
35°	746.2	746.2	743.0	743.0	743.0	746.2	746.2	748.1	753.2	753.2	759.6
37.5°	711.0	710.3	708.4	708.7	708.4	710.3	711.0	712.5	714.3	717.0	721.0
40°	684.5	683.9	681.9	678.2	681.9	683.9	684.5	687.0	688.3	691.5	694.1
42.5°	659.0	657.0	656.0	654.8	656.0	657.0	659.0	660.6	661.4	665.5	670.6
45°	619.0	619.0	617.7	617.1	617.7	619.0	619.0	619.0	619.6	624.7	627.3
47.5°	580.0	581.2	583.6	583.2	583.6	581.2	580.0	579.0	579.3	581.8	584.8
50°	556.7	557.3	559.2	559.9	559.2	557.3	556.7	554.1	552.8	552.8	554.8
52.5°	530.7	534.4	536.8	536.4	536.8	534.4	530.7	528.7	526.4	523.3	526.2
55°	494.3	498.8	503.2	503.9	503.2	498.8	494.3	488.6	486.1	481.0	482.9
57.5°	458.3	464.5	469.2	470.8	469.2	464.5	458.3	451.4	443.2	440.7	437.2
60°	433.9	442.1	447.9	450.4	447.9	442.1	433.9	427.5	416.7	409.7	407.2
62.5°	410.5	419.7	425.5	425.9	425.5	419.7	410.5	400.5	389.7	381.7	376.6
65°	372.1	381.7	386.8	390.6	386.8	381.7	372.1	361.4	349.2	338.5	332.7
67.5°	330.9	340.4	346.1	349.1	346.1	340.4	330.9	317.5	306.5	294.1	287.3
70°	301.0	310.5	318.1	320.7	318.1	310.5	301.0	285.0	275.5	264.0	258.3
72.5°	271.4	279.9	286.1	289.1	286.1	279.9	271.4	256.5	245.4	233.9	226.2
75°	220.1	231.6	237.3	240.4	237.3	231.6	220.1	211.9	199.2	187.0	180.7
77.5°	169.8	180.1	183.6	185.2	183.6	180.1	169.8	160.0	150.4	141.6	135.3
80°	136.1	142.5	146.9	147.6	146.9	142.5	136.1	128.5	120.8	112.6	106.9
82.5°	104.6	109.9	111.3	113.0	111.3	109.9	104.6	97.9	91.3	85.1	80.4
85°	57.2	59.8	60.4	59.8	60.4	59.8	57.2	52.8	49.6	46.5	44.5
87.5°	21.2	20.7	20.8	22.0	20.8	20.7	21.2	20.1	20.5	19.4	18.3
90°	11.9	12.2	12.5	12.9	12.5	12.2	11.9	11.5	11.0	10.4	9.8
92.5°	24.6	24.9	25.1	25.4	25.1	24.9	24.6	24.3	23.8	23.0	22.2
95°	45.5	45.8	46.0	46.3	46.0	45.8	45.5	45.2	44.8	43.9	43.1
97.5°	69.7	69.8	69.9	70.1	69.9	69.8	69.7	69.6	69.1	68.3	67.5
100°	87.5	87.8	87.9	88.2	87.9	87.8	87.5	87.2	86.5	85.5	84.5
102.5°	105.3	105.6	105.9	106.2	105.9	105.6	105.3	104.9	104.2	103.0	101.8
105°	132.2	132.6	133.0	133.4	133.0	132.6	132.2	132.0	131.4	130.6	130.0
107.5°	161.2	161.2	161.1	161.1	161.1	161.2	161.2	161.2	161.0	160.7	160.3
110°	182.1	182.0	181.8	181.7	181.8	182.0	182.1	182.2	182.1	181.7	181.3



TEST NUMBER: P333260-830

CATALOG NUMBER: S125DIP-S1090D590U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	202.6	202.4	202.2	202.0	202.2	202.4	202.6	202.8	202.8	202.6	202.6
115°	234.2	234.1	234.0	233.9	234.0	234.1	234.2	234.4	234.5	234.6	234.7
117.5°	266.6	266.1	265.6	265.0	265.6	266.1	266.6	267.0	267.2	267.1	267.0
120°	288.0	287.6	287.1	286.6	287.1	287.6	288.0	288.5	288.7	288.7	288.7
122.5°	309.2	308.9	308.5	308.1	308.5	308.9	309.2	309.6	309.9	310.0	310.1
125°	340.7	340.6	340.4	340.4	340.4	340.6	340.7	340.8	341.0	341.3	341.5
127.5°	372.0	371.8	371.6	371.4	371.6	371.8	372.0	372.3	372.5	372.6	372.7
130°	392.7	392.5	392.2	392.0	392.2	392.5	392.7	392.9	393.1	393.2	393.3
132.5°	412.4	412.0	411.7	411.3	411.7	412.0	412.4	412.6	412.9	413.0	413.1
135°	442.9	442.4	442.0	441.5	442.0	442.4	442.9	443.4	443.6	443.6	443.6
137.5°	472.7	472.1	471.6	470.9	471.6	472.1	472.7	473.3	473.5	473.3	473.3
140°	491.6	491.1	490.4	489.8	490.4	491.1	491.6	492.2	492.4	492.2	491.9
142.5°	509.7	509.1	508.5	507.9	508.5	509.1	509.7	510.3	510.5	510.4	510.2
145°	536.1	535.7	535.4	535.0	535.4	535.7	536.1	536.4	536.6	536.6	536.6
147.5°	560.5	559.8	558.9	558.2	558.9	559.8	560.5	561.4	561.7	561.4	561.1
150°	576.1	575.8	575.6	575.3	575.6	575.8	576.1	576.3	576.4	576.4	576.4
152.5°	590.8	590.4	589.9	589.6	589.9	590.4	590.8	591.3	591.4	591.1	590.8
155°	611.5	611.0	610.3	609.7	610.3	611.0	611.5	612.2	612.2	611.7	611.2
157.5°	629.0	628.2	627.5	626.6	627.5	628.2	629.0	629.8	629.9	629.4	629.0
160°	640.1	639.4	638.9	638.3	638.9	639.4	640.1	640.6	640.6	640.2	639.7
162.5°	650.3	649.5	648.8	648.1	648.8	649.5	650.3	650.9	651.0	650.4	649.8
165°	663.5	662.8	662.0	661.4	662.0	662.8	663.5	664.2	664.4	663.8	663.4
167.5°	674.1	673.4	672.6	671.9	672.6	673.4	674.1	674.9	674.9	674.2	673.4
170°	680.0	679.2	678.3	677.5	678.3	679.2	680.0	680.8	680.9	680.1	679.5
172.5°	684.5	683.7	683.0	682.2	683.0	683.7	684.5	685.2	685.2	684.5	683.8
175°	689.2	688.3	687.5	686.6	687.5	688.3	689.2	689.9	690.0	689.3	688.6
177.5°	691.3	690.6	689.8	689.2	689.8	690.6	691.3	691.9	691.9	691.4	690.8
180°	691.0	691.0	691.0	691.0	691.0	691.0	691.0	691.0	691.0	691.0	691.0



TEST NUMBER: P333260-830

CATALOG NUMBER: S125DIP-S1090D590U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1433.1	1439.3	1446.9	1452.5	1462.6	1467.3	1472.8	1477.4	1485.5	1493.2	1502.4
5°	1336.6	1347.4	1362.1	1377.9	1396.4	1409.1	1426.9	1437.8	1459.3	1479.1	1498.2
7.5°	1249.1	1262.3	1283.0	1303.3	1327.6	1349.4	1371.7	1396.4	1424.0	1456.6	1483.6
10°	1189.0	1206.8	1229.1	1254.5	1283.8	1309.2	1339.2	1365.8	1399.6	1437.8	1473.4
12.5°	1141.1	1156.4	1181.2	1205.7	1237.0	1268.0	1298.9	1334.3	1373.7	1415.9	1460.7
15°	1075.2	1087.9	1108.2	1141.9	1173.7	1204.3	1250.8	1283.8	1333.4	1380.4	1434.5
17.5°	1018.8	1034.5	1051.7	1080.6	1113.5	1151.7	1193.2	1234.6	1282.5	1342.2	1403.2
20°	984.1	996.8	1016.6	1038.9	1073.8	1112.0	1151.5	1193.4	1252.0	1313.7	1379.2
22.5°	946.5	960.3	982.5	1006.8	1036.2	1072.8	1116.3	1162.4	1223.5	1284.2	1355.3
25°	902.1	911.6	932.0	953.7	982.9	1014.1	1059.2	1110.1	1170.5	1239.9	1312.4
27.5°	860.3	868.6	887.2	906.1	932.5	969.5	1009.8	1061.3	1118.2	1188.5	1268.9
30°	830.2	839.1	855.6	876.0	901.4	933.9	975.2	1023.6	1084.7	1153.4	1237.4
32.5°	804.3	812.1	824.6	845.0	869.9	901.4	939.6	989.0	1050.1	1119.7	1202.2
35°	764.0	773.0	782.5	798.4	820.0	850.6	892.6	939.0	997.5	1065.0	1140.7
37.5°	724.1	733.8	742.3	756.6	776.3	803.2	839.5	887.9	940.8	1005.8	1078.5
40°	699.2	706.8	713.8	729.1	748.8	774.2	807.9	851.2	907.2	967.6	1028.0
42.5°	674.2	681.4	687.3	700.6	718.8	743.2	775.3	817.6	869.5	925.9	979.2
45°	634.9	639.3	646.3	657.8	672.4	694.7	725.9	763.4	807.3	860.7	900.8
47.5°	592.4	599.4	605.1	615.2	627.2	649.0	678.9	710.9	750.6	790.4	818.6
50°	559.9	566.8	575.1	584.7	596.1	616.4	643.9	676.3	709.9	740.5	764.7
52.5°	529.3	535.7	544.6	553.6	567.6	584.8	608.2	637.1	670.2	692.1	712.3
55°	484.1	487.3	497.5	506.4	519.7	532.4	556.0	581.5	601.8	618.4	634.9
57.5°	437.9	442.2	448.1	456.1	469.4	484.3	500.8	523.3	535.3	543.8	556.7
60°	408.4	409.7	413.5	423.0	433.2	446.6	465.7	481.5	490.5	497.5	508.3
62.5°	375.9	376.1	382.5	389.5	397.1	411.5	427.0	439.9	447.2	450.6	461.0
65°	330.2	328.9	332.7	338.5	347.3	356.8	370.2	381.7	381.1	384.8	391.2
67.5°	283.5	282.2	282.2	287.7	294.9	303.5	312.6	319.2	319.3	324.4	327.6
70°	251.9	248.1	250.6	255.1	258.3	265.3	275.5	278.1	278.6	281.2	284.4
72.5°	219.3	218.1	220.1	222.1	224.2	229.7	238.3	239.9	240.0	241.5	246.7
75°	174.3	173.1	171.7	173.7	176.3	180.0	183.2	185.8	185.1	185.8	189.5
77.5°	130.6	127.1	126.5	127.5	128.1	130.4	133.7	133.5	134.1	133.9	138.3
80°	103.7	98.6	97.9	97.9	98.6	99.9	101.1	102.5	100.5	102.5	103.7
82.5°	76.3	73.1	73.0	72.5	72.7	72.9	73.7	74.5	74.1	74.9	75.7
85°	41.9	40.7	38.8	40.1	39.4	37.5	38.8	36.9	36.3	36.9	37.5
87.5°	16.1	16.5	15.3	15.1	14.4	14.8	13.6	12.9	12.2	12.5	13.9
90°	9.2	8.6	7.7	7.0	6.1	5.3	4.3	3.4	2.5	1.5	0.6
92.5°	21.4	20.6	19.6	18.6	17.5	16.5	15.6	15.0	14.3	13.7	13.0
95°	42.2	41.4	40.2	39.0	37.8	36.7	35.9	35.6	35.4	35.2	35.0
97.5°	66.7	65.9	64.3	62.6	61.0	59.3	58.4	58.3	58.2	58.2	58.1
100°	83.3	82.3	80.7	79.2	77.6	76.1	75.3	75.3	75.3	75.3	75.3
102.5°	100.7	99.4	98.7	97.9	97.1	96.3	95.7	95.2	94.7	94.3	93.8
105°	129.2	128.5	127.8	127.1	126.4	125.6	125.0	124.4	123.8	123.2	122.6
107.5°	159.9	159.6	159.0	158.4	158.0	157.4	156.8	156.2	155.6	155.0	154.4
110°	181.1	180.7	180.3	179.9	179.6	179.3	178.8	178.1	177.6	176.9	176.3



TEST NUMBER: P333260-830

CATALOG NUMBER: S125DIP-S1090D590U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	202.4	202.2	201.7	201.2	200.9	200.4	200.0	199.6	199.3	199.1	198.7
115°	234.9	235.0	234.7	234.5	234.2	234.0	233.7	233.2	232.7	232.2	231.8
117.5°	266.9	266.8	266.6	266.4	266.2	266.0	265.7	265.5	265.3	265.0	264.9
120°	288.7	288.7	288.6	288.5	288.4	288.2	287.9	287.3	286.7	286.2	285.5
122.5°	310.2	310.3	309.9	309.6	309.3	309.0	308.8	308.5	308.3	308.1	307.9
125°	341.8	342.0	341.9	341.8	341.6	341.5	341.1	340.4	339.6	338.9	338.2
127.5°	372.9	373.0	372.8	372.7	372.5	372.4	372.1	371.6	371.3	370.9	370.5
130°	393.5	393.6	393.3	393.1	392.9	392.7	392.2	391.6	391.1	390.4	389.8
132.5°	413.3	413.4	413.4	413.5	413.5	413.6	413.1	412.1	411.1	410.2	409.2
135°	443.6	443.6	443.5	443.4	443.3	443.1	442.7	442.0	441.3	440.5	439.8
137.5°	473.1	473.0	472.7	472.4	472.2	471.9	471.5	470.7	470.0	469.4	468.6
140°	491.7	491.4	491.1	490.8	490.4	490.0	489.6	488.9	488.3	487.8	487.1
142.5°	510.1	509.9	509.5	509.1	508.6	508.1	507.7	507.2	506.6	506.1	505.7
145°	536.6	536.6	536.3	535.9	535.6	535.2	534.8	534.3	533.9	533.3	532.8
147.5°	560.8	560.5	560.2	560.0	559.6	559.3	559.1	558.8	558.6	558.3	558.0
150°	576.4	576.4	575.9	575.4	575.0	574.5	574.3	574.5	574.6	574.7	574.8
152.5°	590.5	590.2	589.9	589.7	589.6	589.4	589.2	589.1	588.9	588.7	588.5
155°	610.8	610.3	610.2	610.0	609.9	609.8	609.7	609.7	609.7	609.7	609.7
157.5°	628.5	628.0	627.9	627.8	627.6	627.5	627.6	627.9	628.1	628.4	628.7
160°	639.2	638.8	638.7	638.6	638.4	638.3	638.4	638.8	639.1	639.5	639.9
162.5°	649.2	648.7	648.7	648.7	648.6	648.6	648.7	648.9	649.2	649.5	649.8
165°	662.9	662.4	662.3	662.2	662.0	661.9	662.0	662.2	662.5	662.7	663.0
167.5°	672.7	672.0	672.0	672.0	672.0	672.0	672.2	672.7	673.2	673.7	674.2
170°	678.7	678.1	678.1	678.1	678.1	678.1	678.3	678.7	679.2	679.7	680.1
172.5°	683.1	682.3	682.3	682.3	682.3	682.3	682.6	683.1	683.5	684.0	684.5
175°	687.9	687.2	687.2	687.2	687.2	687.2	687.4	687.9	688.3	688.8	689.3
177.5°	690.2	689.7	689.8	689.8	689.9	690.0	690.2	690.7	691.1	691.4	691.8
180°	691.0	691.0	691.0	691.0	691.0	691.0	691.0	691.0	691.0	691.0	691.0



TEST NUMBER: P333260-830

CATALOG NUMBER: S125DIP-S1090D590U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1506.9	1514.1	1518.6	1527.3	1534.5	1538.5	1542.1	1545.1	1548.7	1551.7	1560.4
5°	1516.6	1533.1	1547.2	1568.8	1588.6	1603.8	1620.3	1634.9	1647.0	1664.2	1677.5
7.5°	1512.4	1541.8	1572.6	1606.1	1640.3	1672.1	1701.4	1728.7	1753.5	1783.6	1809.9
10°	1508.4	1548.4	1587.9	1633.0	1679.5	1718.9	1755.9	1793.4	1820.7	1858.9	1891.3
12.5°	1505.3	1552.5	1600.1	1654.4	1705.4	1761.1	1810.2	1837.7	1879.2	1909.8	1948.3
15°	1492.4	1554.8	1620.3	1681.4	1753.9	1805.4	1848.7	1902.1	1941.0	1979.7	2021.8
17.5°	1469.4	1540.0	1613.4	1693.4	1762.9	1818.3	1874.1	1925.5	1971.9	2023.9	2076.2
20°	1458.8	1529.4	1613.4	1695.4	1763.5	1821.4	1878.6	1935.2	1986.1	2053.0	2113.4
22.5°	1436.3	1521.7	1599.1	1679.1	1749.2	1812.2	1877.1	1941.4	2009.0	2084.4	2160.2
25°	1396.4	1482.9	1565.0	1643.9	1714.5	1793.4	1862.7	1948.6	2035.1	2135.0	2229.1
27.5°	1354.9	1437.8	1513.0	1589.1	1671.5	1760.8	1850.8	1948.2	2061.4	2187.5	2320.4
30°	1321.4	1399.6	1472.7	1551.0	1636.8	1737.4	1836.0	1951.7	2082.8	2224.7	2382.5
32.5°	1282.1	1354.2	1425.4	1508.3	1601.8	1707.9	1822.8	1949.7	2107.2	2268.4	2430.8
35°	1215.1	1275.5	1348.7	1437.1	1542.8	1664.2	1797.1	1947.3	2128.0	2313.1	2449.9
37.5°	1135.6	1191.8	1268.9	1365.8	1476.6	1606.9	1764.7	1942.9	2134.8	2282.4	2326.5
40°	1082.1	1134.3	1214.5	1314.9	1428.2	1566.2	1739.3	1927.6	2113.4	2207.5	2171.2
42.5°	1025.1	1079.9	1157.9	1257.4	1379.3	1529.7	1707.2	1895.5	2051.3	2086.9	1961.5
45°	935.2	991.7	1068.7	1169.3	1300.3	1463.2	1648.3	1819.5	1909.1	1844.9	1650.9
47.5°	851.6	904.7	976.0	1079.7	1214.9	1383.4	1561.7	1698.2	1705.3	1552.0	1344.7
50°	794.6	843.6	915.5	1019.2	1153.4	1323.9	1484.8	1592.3	1544.0	1370.3	1171.2
52.5°	738.6	786.6	857.4	960.1	1092.8	1249.1	1398.8	1474.2	1383.2	1204.9	1034.8
55°	657.8	699.7	769.1	863.9	989.9	1134.9	1262.2	1288.3	1169.9	994.3	856.3
57.5°	578.9	618.1	681.2	768.5	883.6	1012.1	1111.6	1106.1	981.0	830.3	720.8
60°	525.5	563.6	619.6	704.8	809.8	920.6	1005.8	985.4	861.4	731.6	639.3
62.5°	477.7	511.7	564.7	639.2	735.0	837.5	907.6	877.5	756.0	642.5	569.7
65°	407.2	435.7	481.0	544.6	624.1	708.7	762.8	724.0	620.3	531.9	473.3
67.5°	339.9	362.8	400.7	451.4	519.2	587.2	620.1	581.1	498.1	433.6	390.2
70°	297.1	317.4	346.7	391.9	451.0	508.3	533.1	498.1	426.9	371.6	340.4
72.5°	254.3	271.2	296.8	337.4	384.8	434.5	456.3	422.8	364.3	317.5	288.4
75°	196.6	208.0	225.8	253.8	291.3	330.8	342.9	313.7	276.1	241.1	222.1
77.5°	140.7	150.4	163.9	181.5	208.1	233.2	243.7	226.9	197.8	175.7	160.0
80°	108.1	113.2	124.7	139.3	160.3	176.3	183.2	172.4	152.0	135.5	123.4
82.5°	77.1	82.2	89.1	101.1	114.5	125.4	132.8	125.5	110.8	97.8	90.9
85°	37.5	40.7	44.5	49.6	59.8	66.2	65.5	61.1	55.3	50.2	46.5
87.5°	13.6	14.2	15.9	18.7	20.4	22.6	23.8	22.9	21.0	19.7	18.3
90°	1.5	2.5	3.4	4.3	5.3	6.1	7.0	7.7	8.6	9.2	9.8
92.5°	13.7	14.3	15.0	15.6	16.5	17.5	18.6	19.6	20.6	21.4	22.2
95°	35.2	35.4	35.6	35.9	36.7	37.8	39.0	40.2	41.4	42.2	43.1
97.5°	58.2	58.2	58.3	58.4	59.3	61.0	62.6	64.3	65.9	66.7	67.5
100°	75.3	75.3	75.3	75.3	76.1	77.6	79.2	80.7	82.3	83.3	84.5
102.5°	94.3	94.7	95.2	95.7	96.3	97.1	97.9	98.7	99.4	100.7	101.8
105°	123.2	123.8	124.4	125.0	125.6	126.4	127.1	127.8	128.5	129.2	130.0
107.5°	155.0	155.6	156.2	156.8	157.4	158.0	158.4	159.0	159.6	159.9	160.3
110°	176.9	177.6	178.1	178.8	179.3	179.6	179.9	180.3	180.7	181.1	181.3



TEST NUMBER: P333260-830

CATALOG NUMBER: S125DIP-S1090D590U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	199.1	199.3	199.6	200.0	200.4	200.9	201.2	201.7	202.2	202.4	202.6
115°	232.2	232.7	233.2	233.7	234.0	234.2	234.5	234.7	235.0	234.9	234.7
117.5°	265.0	265.3	265.5	265.7	266.0	266.2	266.4	266.6	266.8	266.9	267.0
120°	286.2	286.7	287.3	287.9	288.2	288.4	288.5	288.6	288.7	288.7	288.7
122.5°	308.1	308.3	308.5	308.8	309.0	309.3	309.6	309.9	310.3	310.2	310.1
125°	338.9	339.6	340.4	341.1	341.5	341.6	341.8	341.9	342.0	341.8	341.5
127.5°	370.9	371.3	371.6	372.1	372.4	372.5	372.7	372.8	373.0	372.9	372.7
130°	390.4	391.1	391.6	392.2	392.7	392.9	393.1	393.3	393.6	393.5	393.3
132.5°	410.2	411.1	412.1	413.1	413.6	413.5	413.5	413.4	413.4	413.3	413.1
135°	440.5	441.3	442.0	442.7	443.1	443.3	443.4	443.5	443.6	443.6	443.6
137.5°	469.4	470.0	470.7	471.5	471.9	472.2	472.4	472.7	473.0	473.1	473.3
140°	487.8	488.3	488.9	489.6	490.0	490.4	490.8	491.1	491.4	491.7	491.9
142.5°	506.1	506.6	507.2	507.7	508.1	508.6	509.1	509.5	509.9	510.1	510.2
145°	533.3	533.9	534.3	534.8	535.2	535.6	535.9	536.3	536.6	536.6	536.6
147.5°	558.3	558.6	558.8	559.1	559.3	559.6	560.0	560.2	560.5	560.8	561.1
150°	574.7	574.6	574.5	574.3	574.5	575.0	575.4	575.9	576.4	576.4	576.4
152.5°	588.7	588.9	589.1	589.2	589.4	589.6	589.7	589.9	590.2	590.5	590.8
155°	609.7	609.7	609.7	609.7	609.8	609.9	610.0	610.2	610.3	610.8	611.2
157.5°	628.4	628.1	627.9	627.6	627.5	627.6	627.8	627.9	628.0	628.5	629.0
160°	639.5	639.1	638.8	638.4	638.3	638.4	638.6	638.7	638.8	639.2	639.7
162.5°	649.5	649.2	648.9	648.7	648.6	648.6	648.7	648.7	648.7	649.2	649.8
165°	662.7	662.5	662.2	662.0	661.9	662.0	662.2	662.3	662.4	662.9	663.4
167.5°	673.7	673.2	672.7	672.2	672.0	672.0	672.0	672.0	672.0	672.7	673.4
170°	679.7	679.2	678.7	678.3	678.1	678.1	678.1	678.1	678.1	678.7	679.5
172.5°	684.0	683.5	683.1	682.6	682.3	682.3	682.3	682.3	682.3	683.1	683.8
175°	688.8	688.3	687.9	687.4	687.2	687.2	687.2	687.2	687.2	687.9	688.6
177.5°	691.4	691.1	690.7	690.2	690.0	689.9	689.8	689.8	689.7	690.2	690.8
180°	691.0	691.0	691.0	691.0	691.0	691.0	691.0	691.0	691.0	691.0	691.0



TEST NUMBER: P333260-830

CATALOG NUMBER: S125DIP-S1090D590U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1567.5	1571.6	1580.3	1577.2	1581.3	1583.3	1585.4
5°	1694.1	1714.5	1723.3	1722.1	1735.5	1732.3	1729.1
7.5°	1837.1	1858.5	1870.5	1885.4	1894.0	1894.6	1902.1
10°	1918.1	1946.1	1957.5	1973.4	1983.6	1989.3	1988.7
12.5°	1980.2	2002.1	2027.7	2035.5	2049.3	2056.4	2053.8
15°	2054.8	2089.8	2116.6	2129.9	2147.1	2152.2	2159.2
17.5°	2121.5	2168.4	2199.6	2241.1	2256.7	2266.2	2260.7
20°	2171.9	2233.6	2264.7	2314.4	2341.7	2356.4	2351.3
22.5°	2231.5	2298.2	2355.9	2398.9	2440.4	2460.2	2464.3
25°	2333.5	2425.1	2509.7	2566.4	2617.8	2629.9	2656.7
27.5°	2447.5	2555.5	2646.0	2705.5	2741.4	2754.9	2763.3
30°	2519.2	2626.8	2694.8	2733.0	2744.4	2743.2	2741.9
32.5°	2554.4	2621.7	2634.8	2624.0	2597.8	2575.7	2552.6
35°	2504.6	2454.4	2379.3	2282.6	2211.3	2139.5	2132.4
37.5°	2252.6	2091.9	1966.9	1827.3	1746.8	1697.0	1662.7
40°	2015.3	1832.8	1681.4	1563.7	1481.7	1449.2	1417.4
42.5°	1757.8	1583.5	1449.3	1350.9	1289.3	1253.3	1228.0
45°	1428.2	1274.2	1169.3	1098.1	1049.0	1021.1	1005.1
47.5°	1170.3	1056.4	967.2	915.9	882.0	860.3	860.4
50°	1031.9	923.1	863.9	823.2	793.9	776.7	780.0
52.5°	909.2	827.9	777.4	743.3	721.7	711.1	710.8
55°	760.3	701.7	668.6	643.9	629.1	617.1	619.6
57.5°	650.3	601.0	578.8	558.2	548.0	543.2	536.1
60°	582.1	543.9	524.8	508.3	498.1	494.3	487.3
62.5°	521.5	491.5	473.0	459.4	450.3	449.0	443.6
65°	438.3	415.4	398.9	392.5	383.0	380.4	380.4
67.5°	361.4	345.0	332.1	326.2	322.1	322.6	319.6
70°	313.0	299.6	291.3	285.0	281.8	282.5	279.9
72.5°	273.8	258.9	251.7	247.9	243.6	245.3	244.3
75°	207.4	199.7	196.0	192.1	189.5	188.3	187.0
77.5°	152.3	145.5	142.6	140.4	140.8	137.8	140.3
80°	117.7	112.0	110.1	106.9	106.2	106.2	105.6
82.5°	86.1	82.9	81.5	78.9	77.8	78.8	77.1
85°	44.5	41.9	41.4	41.4	40.1	38.8	41.9
87.5°	18.4	16.5	16.6	16.1	16.2	15.7	14.8
90°	10.4	11.0	11.5	11.9	12.2	12.5	12.9
92.5°	23.0	23.8	24.3	24.6	24.9	25.1	25.4
95°	43.9	44.8	45.2	45.5	45.8	46.0	46.3
97.5°	68.3	69.1	69.6	69.7	69.8	69.9	70.1
100°	85.5	86.5	87.2	87.5	87.8	87.9	88.2
102.5°	103.0	104.2	104.9	105.3	105.6	105.9	106.2
105°	130.6	131.4	132.0	132.2	132.6	133.0	133.4
107.5°	160.7	161.0	161.2	161.2	161.2	161.1	161.1
110°	181.7	182.1	182.2	182.1	182.0	181.8	181.7



TEST NUMBER: P333260-830

CATALOG NUMBER: S125DIP-S1090D590U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	202.6	202.8	202.8	202.6	202.4	202.2	202.0
115°	234.6	234.5	234.4	234.2	234.1	234.0	233.9
117.5°	267.1	267.2	267.0	266.6	266.1	265.6	265.0
120°	288.7	288.7	288.5	288.0	287.6	287.1	286.6
122.5°	310.0	309.9	309.6	309.2	308.9	308.5	308.1
125°	341.3	341.0	340.8	340.7	340.6	340.4	340.4
127.5°	372.6	372.5	372.3	372.0	371.8	371.6	371.4
130°	393.2	393.1	392.9	392.7	392.5	392.2	392.0
132.5°	413.0	412.9	412.6	412.4	412.0	411.7	411.3
135°	443.6	443.6	443.4	442.9	442.4	442.0	441.5
137.5°	473.3	473.5	473.3	472.7	472.1	471.6	470.9
140°	492.2	492.4	492.2	491.6	491.1	490.4	489.8
142.5°	510.4	510.5	510.3	509.7	509.1	508.5	507.9
145°	536.6	536.6	536.4	536.1	535.7	535.4	535.0
147.5°	561.4	561.7	561.4	560.5	559.8	558.9	558.2
150°	576.4	576.4	576.3	576.1	575.8	575.6	575.3
152.5°	591.1	591.4	591.3	590.8	590.4	589.9	589.6
155°	611.7	612.2	612.2	611.5	611.0	610.3	609.7
157.5°	629.4	629.9	629.8	629.0	628.2	627.5	626.6
160°	640.2	640.6	640.6	640.1	639.4	638.9	638.3
162.5°	650.4	651.0	650.9	650.3	649.5	648.8	648.1
165°	663.8	664.4	664.2	663.5	662.8	662.0	661.4
167.5°	674.2	674.9	674.9	674.1	673.4	672.6	671.9
170°	680.1	680.9	680.8	680.0	679.2	678.3	677.5
172.5°	684.5	685.2	685.2	684.5	683.7	683.0	682.2
175°	689.3	690.0	689.9	689.2	688.3	687.5	686.6
177.5°	691.4	691.9	691.9	691.3	690.6	689.8	689.2
180°	691.0	691.0	691.0	691.0	691.0	691.0	691.0

(END OF REPORT)