

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333319-935

Luminaire Tested: **S125DIP-S1270D810U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333319-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1270D810U935-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7206.6 lumens
Efficiency: N/A
Efficacy: 118.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333319-935

CATALOG NUMBER: S125DIP-S1270D810U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333319-935

CATALOG NUMBER: S125DIP-S1270D810U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	66	66	66	61
1	100	96	92	88	94	90	86	83	79	76	74	68	66	65	59	57	56	51
2	91	84	77	72	85	78	73	68	69	65	61	60	57	54	52	49	47	43
3	83	74	66	60	78	69	62	57	61	55	51	53	49	46	46	43	40	36
4	76	65	57	51	71	61	54	48	54	48	44	47	43	39	41	37	35	31
5	70	58	50	44	65	55	47	42	48	42	38	42	38	34	37	33	30	27
6	65	52	44	38	60	49	42	36	44	37	33	38	33	30	33	30	27	24
7	60	47	39	33	56	45	37	32	40	33	29	35	30	26	30	27	24	21
8	55	43	35	30	52	41	33	28	36	30	26	32	27	23	28	24	21	19
9	52	39	32	26	48	37	30	25	33	27	23	29	25	21	26	22	19	17
10	48	36	29	24	45	34	27	23	31	25	21	27	22	19	24	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10959	10959	10959
5°	10983	10878	10949
10°	10916	10802	10864
15°	10797	10672	10717
20°	10628	10490	10509
25°	10446	10274	10264
30°	10221	10041	9991
35°	9980	9790	9653
40°	9732	9517	9382
45°	9465	9270	9085
50°	9171	8969	8699
55°	8888	8631	8389
60°	8548	8289	7994
65°	8145	7878	7610
70°	7757	7402	7149
75°	7069	6835	6598
80°	6289	6189	6044
85°	5476	5572	5269



TEST NUMBER: P333319-935

CATALOG NUMBER: S125DIP-S1270D810U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.0	2.2
10°-20°	451.9	6.3
20°-30°	667.3	9.3
30°-40°	778.6	10.8
40°-50°	782.0	10.9
50°-60°	686.5	9.5
60°-70°	511.5	7.1
70°-80°	292.5	4.1
80°-90°	87.0	1.2
90°-100°	33.0	0.5
100°-110°	203.4	2.8
110°-120°	369.0	5.1
120°-130°	473.5	6.6
130°-140°	509.3	7.1
140°-150°	478.1	6.6
150°-160°	386.7	5.4
160°-170°	250.1	3.5
170°-180°	86.3	1.2
0°-30°	1279.2	17.8
0°-40°	2057.8	28.6
0°-60°	3526.3	48.9
0°-90°	4417.2	61.3
90°-120°	605.4	8.4
90°-150°	2066.3	28.7
90°-180°	2789.0	38.7
0°-180°	7206.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1697	1697	1697	1697	1697	
5°	1694	1691	1678	1689	1689	161
15°	1615	1610	1596	1602	1603	455
25°	1466	1459	1442	1444	1440	674
35°	1266	1260	1242	1235	1224	791
45°	1036	1030	1015	999	995	798
55°	789	784	766	755	745	704
65°	533	530	516	504	498	529
75°	283	280	274	270	264	302
85°	74	75	75	74	71	82
90°	1	6	11	14	16	6
95°	38	35	11	14	14	49
105°	198	200	201	201	200	210
115°	372	375	376	373	369	368
125°	529	533	533	531	529	472
135°	659	663	662	660	656	508
145°	764	766	766	766	762	478
155°	842	838	839	841	836	388
165°	888	884	885	888	883	251
175°	908	905	905	910	904	86
180°	908	908	908	908	908	



TEST NUMBER: P333319-935

CATALOG NUMBER: S125DIP-S1270D810U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8
2.5°	1701.1	1700.4	1699.7	1698.9	1698.2	1696.7	1694.3	1691.9	1689.5	1687.1	1689.5
5°	1694.1	1693.5	1692.9	1692.3	1691.7	1690.0	1687.0	1683.9	1681.0	1678.0	1680.7
7.5°	1678.5	1677.9	1677.3	1676.7	1676.1	1674.2	1670.9	1667.7	1664.4	1661.1	1663.7
10°	1664.6	1664.0	1663.4	1662.8	1662.2	1660.3	1657.0	1653.7	1650.4	1647.1	1649.5
12.5°	1647.4	1646.3	1645.3	1644.2	1643.1	1641.1	1638.0	1635.0	1631.9	1628.8	1630.8
15°	1614.9	1614.0	1613.1	1612.2	1611.4	1609.2	1605.9	1602.7	1599.4	1596.1	1597.6
17.5°	1577.6	1576.3	1574.9	1573.6	1572.4	1569.9	1566.6	1563.1	1559.8	1556.3	1558.2
20°	1546.4	1545.8	1545.2	1544.6	1544.0	1541.8	1537.9	1534.0	1530.2	1526.3	1528.4
22.5°	1515.3	1514.2	1513.1	1512.1	1511.0	1508.6	1505.0	1501.4	1497.7	1494.1	1495.5
25°	1465.9	1464.4	1462.9	1461.5	1459.9	1457.2	1453.4	1449.5	1445.6	1441.7	1442.3
27.5°	1408.2	1407.3	1406.4	1405.5	1404.6	1402.1	1398.2	1394.1	1390.2	1386.1	1386.3
30°	1370.6	1369.7	1368.8	1367.9	1367.0	1364.3	1359.9	1355.4	1350.9	1346.4	1345.8
32.5°	1329.8	1328.4	1327.1	1325.7	1324.3	1321.6	1317.6	1313.6	1309.6	1305.6	1304.6
35°	1265.8	1264.7	1263.5	1262.3	1261.1	1258.4	1254.2	1250.1	1245.9	1241.7	1240.3
37.5°	1199.5	1198.1	1196.6	1195.1	1193.6	1190.8	1187.0	1183.0	1179.1	1175.2	1172.9
40°	1154.4	1153.0	1151.5	1150.0	1148.5	1145.6	1141.5	1137.3	1133.2	1128.9	1126.3
42.5°	1106.1	1104.9	1103.6	1102.3	1101.1	1098.4	1094.2	1090.0	1085.9	1081.7	1079.3
45°	1036.3	1035.2	1034.0	1032.8	1031.6	1029.2	1025.6	1022.0	1018.5	1014.9	1011.2
47.5°	961.1	961.2	961.3	961.3	961.4	959.2	955.0	950.7	946.4	942.1	938.5
50°	912.8	912.0	911.0	910.2	909.2	907.0	903.4	899.8	896.3	892.7	888.8
52.5°	863.4	862.8	862.1	861.4	860.8	858.6	854.7	850.9	847.1	843.3	839.9
55°	789.4	788.4	787.6	786.6	785.7	783.3	779.0	774.9	770.7	766.5	763.8
57.5°	711.2	710.8	710.2	709.8	709.3	707.3	703.8	700.3	696.7	693.2	689.7
60°	661.8	660.6	659.4	658.2	657.0	654.8	651.5	648.2	645.0	641.7	638.7
62.5°	610.3	609.3	608.4	607.3	606.4	604.6	601.8	598.9	596.2	593.3	590.1
65°	533.0	532.4	531.8	531.2	530.5	528.6	525.3	522.0	518.8	515.5	512.8
67.5°	458.1	456.8	455.6	454.3	453.1	451.2	448.8	446.3	443.8	441.3	439.1
70°	410.8	409.3	407.8	406.3	404.8	402.7	400.0	397.4	394.7	392.0	390.2
72.5°	359.2	358.2	357.2	356.2	355.2	353.8	352.1	350.3	348.6	346.9	344.8
75°	283.3	282.7	282.1	281.5	280.9	279.8	278.4	276.8	275.3	273.9	272.9
77.5°	213.2	212.9	212.7	212.5	212.2	211.7	210.9	210.0	209.1	208.4	207.8
80°	169.1	169.1	169.1	169.1	169.1	168.8	168.2	167.6	167.0	166.4	166.2
82.5°	130.4	130.0	129.5	129.1	128.5	128.3	128.1	128.0	127.9	127.8	127.3
85°	73.9	74.1	74.4	74.7	75.0	75.2	75.2	75.2	75.2	75.2	74.9
87.5°	29.1	29.4	29.6	29.9	30.0	30.2	30.1	30.1	30.1	30.0	30.2
90°	0.7	1.9	3.1	4.3	5.4	6.5	7.7	8.7	9.7	10.8	11.5
92.5°	10.3	9.6	8.7	7.8	7.1	7.1	8.0	9.0	9.8	10.8	11.5
95°	38.4	38.0	37.5	37.0	36.6	33.5	27.8	22.1	16.4	10.8	11.5
97.5°	80.2	80.9	81.7	82.6	83.3	78.2	66.9	55.6	44.3	33.1	28.9
100°	112.4	112.9	113.3	113.8	114.3	114.8	115.4	116.0	116.6	117.2	94.9
102.5°	145.3	145.9	146.5	147.0	147.6	148.0	148.4	148.8	149.1	149.5	145.3
105°	197.9	198.5	199.1	199.8	200.4	200.6	200.6	200.6	200.6	200.6	200.6
107.5°	252.6	252.6	252.6	252.6	252.6	252.8	253.0	253.4	253.7	254.0	254.0
110°	288.2	288.2	288.2	288.2	288.2	288.3	288.6	289.0	289.2	289.6	289.1



TEST NUMBER: P333319-935

CATALOG NUMBER: S125DIP-S1270D810U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	321.6	321.9	322.3	322.7	323.0	323.3	323.5	323.6	323.8	324.0	323.5
115°	371.7	372.5	373.2	373.9	374.7	375.1	375.3	375.4	375.6	375.7	375.1
117.5°	423.5	423.5	423.4	423.4	423.4	423.7	424.2	424.8	425.4	425.9	425.2
120°	455.8	455.7	455.6	455.4	455.2	455.4	455.8	456.3	456.8	457.2	456.9
122.5°	484.4	485.0	485.5	486.1	486.6	487.1	487.2	487.5	487.7	487.9	487.6
125°	528.6	529.6	530.6	531.8	532.8	533.3	533.3	533.3	533.3	533.3	532.7
127.5°	570.8	571.4	572.2	573.0	573.7	574.0	573.9	573.9	573.8	573.7	573.3
130°	596.6	597.4	598.1	598.8	599.6	600.0	600.2	600.3	600.5	600.6	600.2
132.5°	622.4	623.3	624.1	625.0	625.9	626.2	625.9	625.5	625.2	624.8	624.7
135°	659.2	660.1	661.0	661.9	662.8	663.1	662.8	662.5	662.2	661.9	661.6
137.5°	693.0	693.8	694.6	695.3	696.1	696.4	696.1	695.9	695.6	695.3	695.3
140°	715.1	715.4	715.7	716.0	716.3	716.4	716.2	716.1	715.9	715.7	716.1
142.5°	735.0	735.2	735.4	735.6	735.7	735.9	736.2	736.3	736.6	736.8	736.8
145°	764.2	764.6	764.8	765.2	765.4	765.6	765.6	765.6	765.6	765.6	765.8
147.5°	789.8	789.8	789.7	789.6	789.6	789.6	789.8	790.0	790.2	790.4	790.6
150°	806.0	805.7	805.4	805.1	804.8	804.8	805.1	805.4	805.7	806.0	806.3
152.5°	821.7	821.0	820.3	819.7	819.0	818.8	819.1	819.4	819.7	820.0	820.3
155°	841.7	840.8	839.9	839.0	838.1	837.8	838.1	838.4	838.7	839.0	839.4
157.5°	857.1	856.6	856.1	855.6	855.0	854.7	854.8	854.8	854.8	854.9	855.3
160°	868.0	867.0	866.2	865.2	864.4	864.0	864.1	864.3	864.4	864.5	865.1
162.5°	876.6	875.6	874.8	873.8	873.0	872.6	872.7	872.9	873.1	873.2	874.0
165°	888.1	887.3	886.3	885.5	884.5	884.2	884.3	884.5	884.6	884.8	885.7
167.5°	896.7	895.9	894.9	894.0	893.0	892.7	892.8	892.9	893.1	893.3	894.3
170°	901.6	900.5	899.5	898.5	897.4	897.0	897.1	897.2	897.4	897.6	898.8
172.5°	904.8	903.8	902.8	901.7	900.6	900.3	900.5	900.8	901.0	901.3	902.4
175°	908.4	907.4	906.5	905.7	904.7	904.4	904.5	904.7	904.8	905.0	906.2
177.5°	910.0	909.2	908.5	907.8	907.1	906.8	906.9	907.0	907.1	907.2	908.1
180°	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4



TEST NUMBER: P333319-935

CATALOG NUMBER: S125DIP-S1270D810U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8
2.5°	1691.9	1694.3	1696.7	1697.7	1697.5	1697.3	1697.0	1696.8
5°	1683.3	1686.1	1688.8	1690.0	1689.6	1689.4	1689.0	1688.8
7.5°	1666.3	1669.0	1671.5	1672.8	1672.5	1672.1	1671.9	1671.5
10°	1651.9	1654.3	1656.7	1657.7	1657.4	1657.1	1656.8	1656.6
12.5°	1632.7	1634.6	1636.5	1637.4	1637.4	1637.3	1637.3	1637.2
15°	1599.1	1600.6	1602.1	1602.8	1602.8	1602.8	1602.8	1602.8
17.5°	1560.0	1561.9	1563.7	1563.9	1562.5	1561.0	1559.4	1558.0
20°	1530.5	1532.6	1534.6	1535.0	1533.4	1532.0	1530.5	1529.0
22.5°	1496.8	1498.2	1499.6	1499.8	1498.7	1497.7	1496.7	1495.7
25°	1442.9	1443.6	1444.2	1444.0	1443.1	1442.2	1441.3	1440.4
27.5°	1386.4	1386.6	1386.6	1386.2	1385.3	1384.5	1383.5	1382.7
30°	1345.2	1344.6	1344.0	1343.3	1342.4	1341.5	1340.6	1339.7
32.5°	1303.5	1302.4	1301.3	1299.9	1298.4	1296.8	1295.1	1293.6
35°	1238.7	1237.3	1235.8	1233.8	1231.4	1229.1	1226.7	1224.3
37.5°	1170.7	1168.5	1166.3	1164.5	1163.1	1161.7	1160.4	1159.0
40°	1123.6	1120.9	1118.2	1116.5	1115.5	1114.7	1113.7	1112.8
42.5°	1076.9	1074.4	1071.9	1070.1	1068.7	1067.3	1065.9	1064.5
45°	1007.7	1004.1	1000.6	998.3	997.4	996.5	995.6	994.7
47.5°	934.8	931.2	927.6	924.7	922.6	920.5	918.4	916.4
50°	884.9	881.1	877.2	874.2	872.1	870.0	868.0	865.8
52.5°	836.5	833.1	829.7	826.8	824.5	822.2	819.8	817.5
55°	761.1	758.5	755.8	753.4	751.3	749.2	747.1	745.0
57.5°	686.3	682.9	679.4	677.1	676.0	674.9	673.6	672.5
60°	635.7	632.7	629.7	627.2	625.1	623.0	621.0	618.9
62.5°	586.9	583.7	580.5	578.1	576.4	574.8	573.2	571.6
65°	510.1	507.4	504.7	502.8	501.6	500.4	499.2	498.0
67.5°	436.9	434.5	432.3	430.8	430.1	429.4	428.7	427.9
70°	388.4	386.6	384.8	383.3	382.1	380.9	379.8	378.6
72.5°	342.9	340.8	338.8	337.2	336.0	334.8	333.6	332.3
75°	272.1	271.1	270.3	269.2	268.0	266.8	265.6	264.4
77.5°	207.2	206.7	206.2	205.5	204.7	203.8	203.0	202.2
80°	165.8	165.6	165.2	164.8	164.2	163.6	163.0	162.5
82.5°	126.7	126.2	125.6	125.4	125.2	125.1	124.9	124.8
85°	74.6	74.3	74.0	73.5	72.9	72.3	71.7	71.1
87.5°	30.4	30.6	30.7	30.6	30.1	29.8	29.4	29.0
90°	12.3	13.0	13.8	14.4	14.8	15.2	15.7	16.2
92.5°	12.3	13.0	13.8	14.2	14.5	14.6	14.9	15.1
95°	12.3	13.0	13.8	14.1	14.1	14.1	14.1	14.1
97.5°	24.7	20.5	16.3	14.1	14.1	14.1	14.1	14.1
100°	72.6	50.3	28.0	16.5	15.9	15.3	14.7	14.1
102.5°	141.0	136.8	132.6	125.4	115.2	105.0	94.9	84.7
105°	200.6	200.6	200.6	200.6	200.4	200.3	200.1	200.0
107.5°	254.1	254.1	254.1	253.9	253.5	253.0	252.5	252.1
110°	288.6	288.2	287.7	287.6	287.7	287.9	288.0	288.2



TEST NUMBER: P333319-935

CATALOG NUMBER: S125DIP-S1270D810U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	322.9	322.3	321.8	321.3	321.2	320.9	320.7	320.6
115°	374.5	373.9	373.3	372.6	371.7	370.7	369.9	369.0
117.5°	424.4	423.6	422.8	422.2	421.9	421.5	421.1	420.7
120°	456.6	456.3	456.0	455.5	454.7	454.0	453.2	452.5
122.5°	487.3	487.0	486.7	486.1	485.3	484.4	483.5	482.7
125°	532.1	531.5	530.9	530.4	529.9	529.4	529.0	528.6
127.5°	573.0	572.7	572.4	571.6	570.6	569.5	568.3	567.2
130°	599.7	599.3	598.8	598.2	597.4	596.8	596.0	595.2
132.5°	624.7	624.6	624.5	624.1	623.4	622.6	621.8	621.1
135°	661.3	661.0	660.7	660.1	659.2	658.3	657.4	656.5
137.5°	695.4	695.4	695.5	695.2	694.4	693.6	692.8	692.1
140°	716.4	716.7	717.0	716.7	715.7	714.9	713.9	713.1
142.5°	736.9	736.9	737.0	736.6	735.7	734.8	733.9	733.0
145°	765.9	766.0	766.2	765.8	764.9	764.1	763.1	762.2
147.5°	790.7	790.9	791.1	790.7	789.5	788.5	787.4	786.4
150°	806.6	806.9	807.2	806.8	805.6	804.3	803.1	801.9
152.5°	820.6	820.9	821.2	820.8	819.8	818.6	817.6	816.5
155°	839.9	840.3	840.8	840.4	839.2	838.0	836.8	835.6
157.5°	855.8	856.4	856.8	856.4	855.2	854.0	852.8	851.6
160°	865.7	866.3	866.9	866.7	865.5	864.3	863.1	861.9
162.5°	874.9	875.7	876.5	876.3	874.9	873.7	872.4	871.1
165°	886.6	887.4	888.4	888.2	887.0	885.8	884.6	883.4
167.5°	895.4	896.5	897.6	897.4	896.0	894.8	893.4	892.1
170°	899.9	901.1	902.3	902.2	901.0	899.6	898.2	896.9
172.5°	903.4	904.6	905.7	905.5	904.1	902.8	901.5	900.1
175°	907.3	908.5	909.7	909.6	908.4	907.0	905.7	904.3
177.5°	909.0	909.7	910.6	910.6	909.6	908.6	907.7	906.7
180°	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4

(END OF REPORT)