

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333268-830

Luminaire Tested: **S125DIP-S1090D810U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333268-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S1090D810U830-4F0-1E-UDD-A  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 810 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7285.0 lumens  
Efficiency: N/A  
Efficacy: 133.9 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 54.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333268-830

CATALOG NUMBER: S125DIP-S1090D810U830-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333268-830

CATALOG NUMBER: S125DIP-S1090D810U830-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64	58
1	100	96	92	88	93	89	86	83	77	75	73	67	65	63	57	55	54	49
2	91	84	78	73	85	78	73	68	68	64	61	59	56	53	50	48	46	42
3	83	74	67	61	77	69	63	57	60	55	51	52	48	45	45	42	39	36
4	76	65	58	52	71	61	54	49	54	48	44	47	42	39	40	37	34	31
5	70	58	50	44	65	55	48	42	48	42	38	42	37	34	36	33	30	27
6	65	53	44	39	60	49	42	37	43	38	33	38	33	30	33	29	26	24
7	60	47	39	34	56	45	37	32	39	34	29	35	30	26	30	26	23	21
8	56	43	35	30	52	41	34	29	36	30	26	32	27	23	27	24	21	19
9	52	39	32	27	48	37	30	26	33	27	23	29	24	21	25	22	19	17
10	48	36	29	24	45	34	28	23	30	25	21	27	22	19	23	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9680	9680	9680	9680
5°	11210	9713	8504	9713
10°	13042	9663	7451	9663
15°	14437	9591	6873	9591
20°	16160	9479	6410	9479
25°	18932	9352	6183	9352
30°	20448	9228	5988	9228
35°	16812	8993	5858	8993
40°	11950	8667	5718	8667
45°	9180	8227	5636	8227
50°	7837	7683	5626	7683
55°	6977	7149	5674	7149
60°	6294	6566	5818	6566
65°	5813	5978	5969	5978
70°	5285	5370	6056	5370
75°	4666	4729	5999	4729
80°	3927	3857	5490	3857
85°	3105	2779	4431	2779



TEST NUMBER: P333268-830

CATALOG NUMBER: S125DIP-S1090D810U830-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	144.3	2.0
10°-20°	429.6	5.9
20°-30°	697.6	9.6
30°-40°	850.9	11.7
40°-50°	774.1	10.6
50°-60°	616.6	8.5
60°-70°	429.5	5.9
70°-80°	229.0	3.1
80°-90°	59.9	0.8
90°-100°	36.1	0.5
100°-110°	222.7	3.1
110°-120°	403.9	5.5
120°-130°	518.4	7.1
130°-140°	557.5	7.7
140°-150°	523.3	7.2
150°-160°	423.3	5.8
160°-170°	273.8	3.8
170°-180°	94.4	1.3
0°-30°	1271.5	17.5
0°-40°	2122.4	29.1
0°-60°	3513.1	48.2
0°-90°	4231.4	58.1
90°-120°	662.7	9.1
90°-150°	2262.0	31.0
90°-180°	3054.0	41.9
0°-180°	7285.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1499	1499	1499	1499	1499	
5°	1729	1498	1312	1498	1729	174
15°	2159	1434	1028	1434	2159	618
25°	2657	1312	868	1312	2657	1213
35°	2132	1141	743	1141	2132	1305
45°	1005	901	617	901	1005	804
55°	620	635	504	635	620	558
65°	380	391	391	391	380	378
75°	187	190	240	190	187	201
85°	42	38	60	38	42	49
90°	18	1	18	1	18	9
95°	16	42	16	42	16	13
105°	219	217	219	217	219	198
115°	404	407	404	407	404	401
125°	579	579	579	579	579	515
135°	719	722	719	722	719	555
145°	834	837	834	837	834	521
155°	915	921	915	921	915	422
165°	967	972	967	972	967	273
175°	990	994	990	994	990	94
180°	994	994	994	994	994	



TEST NUMBER: P333268-830

CATALOG NUMBER: S125DIP-S1090D810U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1585.4	1583.3	1581.3	1577.2	1580.3	1571.6	1567.5	1560.4	1551.7	1548.7	1545.1
5°	1729.1	1732.3	1735.5	1722.1	1723.3	1714.5	1694.1	1677.5	1664.2	1647.0	1634.9
7.5°	1902.1	1894.6	1894.0	1885.4	1870.5	1858.5	1837.1	1809.9	1783.6	1753.5	1728.7
10°	1988.7	1989.3	1983.6	1973.4	1957.5	1946.1	1918.1	1891.3	1858.9	1820.7	1793.4
12.5°	2053.8	2056.4	2049.3	2035.5	2027.7	2002.1	1980.2	1948.3	1909.8	1879.2	1837.7
15°	2159.2	2152.2	2147.1	2129.9	2116.6	2089.8	2054.8	2021.8	1979.7	1941.0	1902.1
17.5°	2260.7	2266.2	2256.7	2241.1	2199.6	2168.4	2121.5	2076.2	2023.9	1971.9	1925.5
20°	2351.3	2356.4	2341.7	2314.4	2264.7	2233.6	2171.9	2113.4	2053.0	1986.1	1935.2
22.5°	2464.3	2460.2	2440.4	2398.9	2355.9	2298.2	2231.5	2160.2	2084.4	2009.0	1941.4
25°	2656.7	2629.9	2617.8	2566.4	2509.7	2425.1	2333.5	2229.1	2135.0	2035.1	1948.6
27.5°	2763.3	2754.9	2741.4	2705.5	2646.0	2555.5	2447.5	2320.4	2187.5	2061.4	1948.2
30°	2741.9	2743.2	2744.4	2733.0	2694.8	2626.8	2519.2	2382.5	2224.7	2082.8	1951.7
32.5°	2552.6	2575.7	2597.8	2624.0	2634.8	2621.7	2554.4	2430.8	2268.4	2107.2	1949.7
35°	2132.4	2139.5	2211.3	2282.6	2379.3	2454.4	2504.6	2449.9	2313.1	2128.0	1947.3
37.5°	1662.7	1697.0	1746.8	1827.3	1966.9	2091.9	2252.6	2326.5	2282.4	2134.8	1942.9
40°	1417.4	1449.2	1481.7	1563.7	1681.4	1832.8	2015.3	2171.2	2207.5	2113.4	1927.6
42.5°	1228.0	1253.3	1289.3	1350.9	1449.3	1583.5	1757.8	1961.5	2086.9	2051.3	1895.5
45°	1005.1	1021.1	1049.0	1098.1	1169.3	1274.2	1428.2	1650.9	1844.9	1909.1	1819.5
47.5°	860.4	860.3	882.0	915.9	967.2	1056.4	1170.3	1344.7	1552.0	1705.3	1698.2
50°	780.0	776.7	793.9	823.2	863.9	923.1	1031.9	1171.2	1370.3	1544.0	1592.3
52.5°	710.8	711.1	721.7	743.3	777.4	827.9	909.2	1034.8	1204.9	1383.2	1474.2
55°	619.6	617.1	629.1	643.9	668.6	701.7	760.3	856.3	994.3	1169.9	1288.3
57.5°	536.1	543.2	548.0	558.2	578.8	601.0	650.3	720.8	830.3	981.0	1106.1
60°	487.3	494.3	498.1	508.3	524.8	543.9	582.1	639.3	731.6	861.4	985.4
62.5°	443.6	449.0	450.3	459.4	473.0	491.5	521.5	569.7	642.5	756.0	877.5
65°	380.4	380.4	383.0	392.5	398.9	415.4	438.3	473.3	531.9	620.3	724.0
67.5°	319.6	322.6	322.1	326.2	332.1	345.0	361.4	390.2	433.6	498.1	581.1
70°	279.9	282.5	281.8	285.0	291.3	299.6	313.0	340.4	371.6	426.9	498.1
72.5°	244.3	245.3	243.6	247.9	251.7	258.9	273.8	288.4	317.5	364.3	422.8
75°	187.0	188.3	189.5	192.1	196.0	199.7	207.4	222.1	241.1	276.1	313.7
77.5°	140.3	137.8	140.8	140.4	142.6	145.5	152.3	160.0	175.7	197.8	226.9
80°	105.6	106.2	106.2	106.9	110.1	112.0	117.7	123.4	135.5	152.0	172.4
82.5°	77.1	78.8	77.8	78.9	81.5	82.9	86.1	90.9	97.8	110.8	125.5
85°	41.9	38.8	40.1	41.4	41.4	41.9	44.5	46.5	50.2	55.3	61.1
87.5°	15.7	16.7	17.1	17.0	17.4	17.2	19.1	18.9	20.4	21.7	23.5
90°	17.7	17.2	16.7	16.2	15.7	15.1	14.2	13.5	12.6	11.8	10.7
92.5°	16.5	16.3	16.0	15.8	15.6	15.1	14.2	13.5	12.6	11.8	10.7
95°	15.5	15.5	15.5	15.5	15.5	15.1	14.2	13.5	12.6	11.8	18.0
97.5°	15.5	15.5	15.5	15.5	15.5	17.8	22.4	27.1	31.7	36.3	48.5
100°	15.5	16.1	16.8	17.4	18.1	30.6	55.0	79.5	103.9	128.3	127.6
102.5°	92.7	103.9	115.0	126.1	137.3	145.2	149.8	154.4	159.0	163.6	163.2
105°	219.0	219.0	219.2	219.4	219.6	219.6	219.6	219.6	219.6	219.6	219.6
107.5°	276.0	276.4	276.9	277.5	278.0	278.1	278.1	278.1	278.1	278.1	277.7
110°	315.5	315.3	315.2	315.0	314.8	315.0	315.5	315.9	316.5	317.0	316.6



TEST NUMBER: P333268-830

CATALOG NUMBER: S125DIP-S1090D810U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	350.9	351.1	351.3	351.6	351.8	352.2	352.8	353.5	354.1	354.7	354.5
115°	404.0	404.9	405.9	406.9	407.8	408.7	409.3	410.0	410.7	411.3	411.1
117.5°	460.5	461.0	461.4	461.8	462.2	462.9	463.7	464.6	465.4	466.3	465.7
120°	495.3	496.2	497.0	497.8	498.6	499.2	499.5	499.8	500.2	500.5	500.0
122.5°	528.4	529.3	530.3	531.2	532.2	532.8	533.1	533.5	533.8	534.1	533.9
125°	578.6	579.1	579.6	580.1	580.6	581.2	581.8	582.5	583.2	583.8	583.8
127.5°	620.9	622.2	623.4	624.6	625.8	626.6	627.0	627.3	627.6	628.0	628.1
130°	651.6	652.4	653.3	654.0	654.9	655.5	656.0	656.5	657.0	657.5	657.3
132.5°	680.0	680.7	681.6	682.4	683.2	683.6	683.7	683.8	683.9	684.0	684.4
135°	718.7	719.6	720.7	721.6	722.6	723.3	723.6	724.0	724.2	724.6	724.9
137.5°	757.6	758.5	759.3	760.2	761.0	761.4	761.3	761.3	761.2	761.1	761.5
140°	780.6	781.6	782.6	783.5	784.6	784.9	784.6	784.2	783.9	783.5	783.7
142.5°	802.4	803.4	804.4	805.4	806.3	806.8	806.7	806.7	806.6	806.5	806.3
145°	834.4	835.4	836.4	837.4	838.3	838.8	838.6	838.4	838.3	838.1	838.1
147.5°	860.8	862.0	863.2	864.3	865.5	866.0	865.8	865.6	865.4	865.3	865.1
150°	877.9	879.2	880.5	881.8	883.2	883.6	883.4	883.0	882.7	882.3	882.0
152.5°	893.8	895.0	896.2	897.4	898.5	899.0	898.6	898.3	898.0	897.7	897.3
155°	914.7	916.1	917.4	918.7	920.0	920.4	919.9	919.5	918.9	918.4	918.1
157.5°	932.3	933.6	934.9	936.2	937.5	937.9	937.5	936.9	936.3	935.9	935.8
160°	943.5	944.8	946.1	947.4	948.8	949.0	948.4	947.7	947.1	946.4	946.3
162.5°	953.6	955.0	956.4	957.8	959.3	959.5	958.7	957.7	956.8	955.9	955.7
165°	967.0	968.4	969.7	971.0	972.3	972.5	971.5	970.5	969.6	968.6	968.4
167.5°	976.6	978.0	979.5	980.9	982.4	982.6	981.4	980.2	979.0	977.9	977.7
170°	981.8	983.3	984.8	986.3	987.7	987.8	986.5	985.1	983.9	982.6	982.4
172.5°	985.3	986.8	988.4	989.8	991.3	991.5	990.2	989.0	987.9	986.7	986.4
175°	990.0	991.5	992.9	994.4	995.8	995.9	994.6	993.3	992.0	990.7	990.5
177.5°	992.6	993.6	994.7	995.7	996.8	996.8	995.9	995.0	994.1	993.2	993.1
180°	994.4	994.4	994.4	994.4	994.4	994.4	994.4	994.4	994.4	994.4	994.4



TEST NUMBER: P333268-830

CATALOG NUMBER: S125DIP-S1090D810U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1542.1	1538.5	1534.5	1527.3	1518.6	1514.1	1506.9	1502.4	1493.2	1485.5	1477.4
5°	1620.3	1603.8	1588.6	1568.8	1547.2	1533.1	1516.6	1498.2	1479.1	1459.3	1437.8
7.5°	1701.4	1672.1	1640.3	1606.1	1572.6	1541.8	1512.4	1483.6	1456.6	1424.0	1396.4
10°	1755.9	1718.9	1679.5	1633.0	1587.9	1548.4	1508.4	1473.4	1437.8	1399.6	1365.8
12.5°	1810.2	1761.1	1705.4	1654.4	1600.1	1552.5	1505.3	1460.7	1415.9	1373.7	1334.3
15°	1848.7	1805.4	1753.9	1681.4	1620.3	1554.8	1492.4	1434.5	1380.4	1333.4	1283.8
17.5°	1874.1	1818.3	1762.9	1693.4	1613.4	1540.0	1469.4	1403.2	1342.2	1282.5	1234.6
20°	1878.6	1821.4	1763.5	1695.4	1613.4	1529.4	1458.8	1379.2	1313.7	1252.0	1193.4
22.5°	1877.1	1812.2	1749.2	1679.1	1599.1	1521.7	1436.3	1355.3	1284.2	1223.5	1162.4
25°	1862.7	1793.4	1714.5	1643.9	1565.0	1482.9	1396.4	1312.4	1239.9	1170.5	1110.1
27.5°	1850.8	1760.8	1671.5	1589.1	1513.0	1437.8	1354.9	1268.9	1188.5	1118.2	1061.3
30°	1836.0	1737.4	1636.8	1551.0	1472.7	1399.6	1321.4	1237.4	1153.4	1084.7	1023.6
32.5°	1822.8	1707.9	1601.8	1508.3	1425.4	1354.2	1282.1	1202.2	1119.7	1050.1	989.0
35°	1797.1	1664.2	1542.8	1437.1	1348.7	1275.5	1215.1	1140.7	1065.0	997.5	939.0
37.5°	1764.7	1606.9	1476.6	1365.8	1268.9	1191.8	1135.6	1078.5	1005.8	940.8	887.9
40°	1739.3	1566.2	1428.2	1314.9	1214.5	1134.3	1082.1	1028.0	967.6	907.2	851.2
42.5°	1707.2	1529.7	1379.3	1257.4	1157.9	1079.9	1025.1	979.2	925.9	869.5	817.6
45°	1648.3	1463.2	1300.3	1169.3	1068.7	991.7	935.2	900.8	860.7	807.3	763.4
47.5°	1561.7	1383.4	1214.9	1079.7	976.0	904.7	851.6	818.6	790.4	750.6	710.9
50°	1484.8	1323.9	1153.4	1019.2	915.5	843.6	794.6	764.7	740.5	709.9	676.3
52.5°	1398.8	1249.1	1092.8	960.1	857.4	786.6	738.6	712.3	692.1	670.2	637.1
55°	1262.2	1134.9	989.9	863.9	769.1	699.7	657.8	634.9	618.4	601.8	581.5
57.5°	1111.6	1012.1	883.6	768.5	681.2	618.1	578.9	556.7	543.8	535.3	523.3
60°	1005.8	920.6	809.8	704.8	619.6	563.6	525.5	508.3	497.5	490.5	481.5
62.5°	907.6	837.5	735.0	639.2	564.7	511.7	477.7	461.0	450.6	447.2	439.9
65°	762.8	708.7	624.1	544.6	481.0	435.7	407.2	391.2	384.8	381.1	381.7
67.5°	620.1	587.2	519.2	451.4	400.7	362.8	339.9	327.6	324.4	319.3	319.2
70°	533.1	508.3	451.0	391.9	346.7	317.4	297.1	284.4	281.2	278.6	278.1
72.5°	456.3	434.5	384.8	337.4	296.8	271.2	254.3	246.7	241.5	240.0	239.9
75°	342.9	330.8	291.3	253.8	225.8	208.0	196.6	189.5	185.8	185.1	185.8
77.5°	243.7	233.2	208.1	181.5	163.9	150.4	140.7	138.3	133.9	134.1	133.5
80°	183.2	176.3	160.3	139.3	124.7	113.2	108.1	103.7	102.5	100.5	102.5
82.5°	132.8	125.4	114.5	101.1	89.1	82.2	77.1	75.7	74.9	74.1	74.5
85°	65.5	66.2	59.8	49.6	44.5	40.7	37.5	37.5	36.9	36.3	36.9
87.5°	24.3	23.1	20.7	19.0	16.2	14.4	13.7	13.9	12.6	12.3	13.1
90°	9.5	8.4	7.2	5.9	4.7	3.4	2.1	0.8	2.1	3.4	4.7
92.5°	9.8	8.8	7.7	7.7	8.6	9.5	10.5	11.3	10.5	9.5	8.6
95°	24.2	30.4	36.7	40.1	40.5	41.0	41.6	42.0	41.6	41.0	40.5
97.5°	60.9	73.2	85.6	91.2	90.4	89.4	88.6	87.8	88.6	89.4	90.4
100°	127.0	126.3	125.6	125.1	124.6	124.0	123.6	123.1	123.6	124.0	124.6
102.5°	162.9	162.5	162.0	161.6	160.9	160.3	159.7	159.1	159.7	160.3	160.9
105°	219.6	219.6	219.6	219.3	218.7	218.0	217.4	216.7	217.4	218.0	218.7
107.5°	277.4	277.0	276.7	276.5	276.5	276.5	276.5	276.5	276.5	276.5	276.5
110°	316.3	315.9	315.7	315.5	315.5	315.5	315.5	315.5	315.5	315.5	315.5





TEST NUMBER: P333268-830

CATALOG NUMBER: S125DIP-S1090D810U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	354.3	354.1	353.9	353.6	353.3	352.8	352.4	352.0	352.4	352.8	353.3
115°	410.9	410.9	410.7	410.2	409.3	408.5	407.7	406.9	407.7	408.5	409.3
117.5°	465.1	464.4	463.8	463.5	463.5	463.5	463.6	463.6	463.6	463.5	463.5
120°	499.5	499.0	498.5	498.3	498.5	498.7	498.9	499.0	498.9	498.7	498.5
122.5°	533.7	533.4	533.2	532.7	532.2	531.5	530.9	530.3	530.9	531.5	532.2
125°	583.8	583.8	583.8	583.2	582.1	580.9	579.8	578.6	579.8	580.9	582.1
127.5°	628.2	628.3	628.4	628.0	627.3	626.4	625.6	624.8	625.6	626.4	627.3
130°	657.1	657.0	656.9	656.4	655.5	654.7	653.9	653.1	653.9	654.7	655.5
132.5°	684.8	685.1	685.5	685.2	684.2	683.2	682.3	681.4	682.3	683.2	684.2
135°	725.2	725.6	725.9	725.6	724.6	723.6	722.6	721.6	722.6	723.6	724.6
137.5°	761.8	762.0	762.3	762.0	761.2	760.3	759.5	758.7	759.5	760.3	761.2
140°	783.9	784.0	784.2	784.1	783.8	783.4	783.2	782.8	783.2	783.4	783.8
142.5°	806.1	805.9	805.6	805.4	805.2	805.0	804.8	804.6	804.8	805.0	805.2
145°	838.1	838.1	838.1	837.9	837.6	837.3	837.0	836.6	837.0	837.3	837.6
147.5°	864.8	864.6	864.4	864.4	864.4	864.5	864.6	864.6	864.6	864.5	864.4
150°	881.7	881.4	881.0	881.0	881.4	881.7	882.0	882.3	882.0	881.7	881.4
152.5°	897.0	896.6	896.4	896.5	897.3	898.0	898.7	899.5	898.7	898.0	897.3
155°	917.8	917.5	917.1	917.5	918.4	919.5	920.4	921.4	920.4	919.5	918.4
157.5°	935.8	935.8	935.7	935.9	936.6	937.2	937.7	938.3	937.7	937.2	936.6
160°	946.1	945.9	945.8	946.2	947.2	948.2	949.1	950.2	949.1	948.2	947.2
162.5°	955.5	955.4	955.3	955.6	956.6	957.6	958.6	959.6	958.6	957.6	956.6
165°	968.3	968.1	967.9	968.3	969.3	970.3	971.3	972.2	971.3	970.3	969.3
167.5°	977.5	977.3	977.2	977.6	978.6	979.7	980.7	981.7	980.7	979.7	978.6
170°	982.2	982.0	981.9	982.4	983.5	984.7	985.8	987.0	985.8	984.7	983.5
172.5°	986.1	985.8	985.5	985.9	987.1	988.3	989.4	990.5	989.4	988.3	987.1
175°	990.3	990.1	990.0	990.4	991.5	992.4	993.3	994.4	993.3	992.4	991.5
177.5°	992.9	992.8	992.7	993.0	993.8	994.6	995.3	996.2	995.3	994.6	993.8
180°	994.4	994.4	994.4	994.4	994.4	994.4	994.4	994.4	994.4	994.4	994.4



TEST NUMBER: P333268-830

CATALOG NUMBER: S125DIP-S1090D810U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1472.8	1467.3	1462.6	1452.5	1446.9	1439.3	1433.1	1439.7	1432.7	1435.7	1431.2
5°	1426.9	1409.1	1396.4	1377.9	1362.1	1347.4	1336.6	1334.6	1329.6	1327.0	1319.4
7.5°	1371.7	1349.4	1327.6	1303.3	1283.0	1262.3	1249.1	1238.1	1230.9	1221.3	1214.8
10°	1339.2	1309.2	1283.8	1254.5	1229.1	1206.8	1189.0	1180.1	1171.9	1159.7	1155.3
12.5°	1298.9	1268.0	1237.0	1205.7	1181.2	1156.4	1141.1	1127.7	1121.9	1108.3	1106.9
15°	1250.8	1204.3	1173.7	1141.9	1108.2	1087.9	1075.2	1060.5	1054.1	1044.6	1037.6
17.5°	1193.2	1151.7	1113.5	1080.6	1051.7	1034.5	1018.8	1008.7	997.8	991.6	980.1
20°	1151.5	1112.0	1073.8	1038.9	1016.6	996.8	984.1	974.6	963.2	960.0	948.6
22.5°	1116.3	1072.8	1036.2	1006.8	982.5	960.3	946.5	940.0	932.1	922.3	920.0
25°	1059.2	1014.1	982.9	953.7	932.0	911.6	902.1	893.8	886.2	879.2	876.7
27.5°	1009.8	969.5	932.5	906.1	887.2	868.6	860.3	850.2	844.6	839.0	832.1
30°	975.2	933.9	901.4	876.0	855.6	839.1	830.2	823.2	818.1	813.0	809.2
32.5°	939.6	901.4	869.9	845.0	824.6	812.1	804.3	799.3	793.7	787.6	782.8
35°	892.6	850.6	820.0	798.4	782.5	773.0	764.0	759.6	753.2	753.2	748.1
37.5°	839.5	803.2	776.3	756.6	742.3	733.8	724.1	721.0	717.0	714.3	712.5
40°	807.9	774.2	748.8	729.1	713.8	706.8	699.2	694.1	691.5	688.3	687.0
42.5°	775.3	743.2	718.8	700.6	687.3	681.4	674.2	670.6	665.5	661.4	660.6
45°	725.9	694.7	672.4	657.8	646.3	639.3	634.9	627.3	624.7	619.6	619.0
47.5°	678.9	649.0	627.2	615.2	605.1	599.4	592.4	584.8	581.8	579.3	579.0
50°	643.9	616.4	596.1	584.7	575.1	566.8	559.9	554.8	552.8	552.8	554.1
52.5°	608.2	584.8	567.6	553.6	544.6	535.7	529.3	526.2	523.3	526.4	528.7
55°	556.0	532.4	519.7	506.4	497.5	487.3	484.1	482.9	481.0	486.1	488.6
57.5°	500.8	484.3	469.4	456.1	448.1	442.2	437.9	437.2	440.7	443.2	451.4
60°	465.7	446.6	433.2	423.0	413.5	409.7	408.4	407.2	409.7	416.7	427.5
62.5°	427.0	411.5	397.1	389.5	382.5	376.1	375.9	376.6	381.7	389.7	400.5
65°	370.2	356.8	347.3	338.5	332.7	328.9	330.2	332.7	338.5	349.2	361.4
67.5°	312.6	303.5	294.9	287.7	282.2	282.2	283.5	287.3	294.1	306.5	317.5
70°	275.5	265.3	258.3	255.1	250.6	248.1	251.9	258.3	264.0	275.5	285.0
72.5°	238.3	229.7	224.2	222.1	220.1	218.1	219.3	226.2	233.9	245.4	256.5
75°	183.2	180.0	176.3	173.7	171.7	173.1	174.3	180.7	187.0	199.2	211.9
77.5°	133.7	130.4	128.1	127.5	126.5	127.1	130.6	135.3	141.6	150.4	160.0
80°	101.1	99.9	98.6	97.9	97.9	98.6	103.7	106.9	112.6	120.8	128.5
82.5°	73.7	72.9	72.7	72.5	73.0	73.1	76.3	80.4	85.1	91.3	97.9
85°	38.8	37.5	39.4	40.1	38.8	40.7	41.9	44.5	46.5	49.6	52.8
87.5°	13.9	15.2	14.9	15.6	15.8	17.2	16.8	18.9	20.2	21.3	20.9
90°	5.9	7.2	8.4	9.5	10.7	11.8	12.6	13.5	14.2	15.1	15.7
92.5°	7.7	7.7	8.8	9.8	10.7	11.8	12.6	13.5	14.2	15.1	15.6
95°	40.1	36.7	30.4	24.2	18.0	11.8	12.6	13.5	14.2	15.1	15.5
97.5°	91.2	85.6	73.2	60.9	48.5	36.3	31.7	27.1	22.4	17.8	15.5
100°	125.1	125.6	126.3	127.0	127.6	128.3	103.9	79.5	55.0	30.6	18.1
102.5°	161.6	162.0	162.5	162.9	163.2	163.6	159.0	154.4	149.8	145.2	137.3
105°	219.3	219.6	219.6	219.6	219.6	219.6	219.6	219.6	219.6	219.6	219.6
107.5°	276.5	276.7	277.0	277.4	277.7	278.1	278.1	278.1	278.1	278.1	278.0
110°	315.5	315.7	315.9	316.3	316.6	317.0	316.5	315.9	315.5	315.0	314.8



TEST NUMBER: P333268-830

CATALOG NUMBER: S125DIP-S1090D810U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	353.6	353.9	354.1	354.3	354.5	354.7	354.1	353.5	352.8	352.2	351.8
115°	410.2	410.7	410.9	410.9	411.1	411.3	410.7	410.0	409.3	408.7	407.8
117.5°	463.5	463.8	464.4	465.1	465.7	466.3	465.4	464.6	463.7	462.9	462.2
120°	498.3	498.5	499.0	499.5	500.0	500.5	500.2	499.8	499.5	499.2	498.6
122.5°	532.7	533.2	533.4	533.7	533.9	534.1	533.8	533.5	533.1	532.8	532.2
125°	583.2	583.8	583.8	583.8	583.8	583.8	583.2	582.5	581.8	581.2	580.6
127.5°	628.0	628.4	628.3	628.2	628.1	628.0	627.6	627.3	627.0	626.6	625.8
130°	656.4	656.9	657.0	657.1	657.3	657.5	657.0	656.5	656.0	655.5	654.9
132.5°	685.2	685.5	685.1	684.8	684.4	684.0	683.9	683.8	683.7	683.6	683.2
135°	725.6	725.9	725.6	725.2	724.9	724.6	724.2	724.0	723.6	723.3	722.6
137.5°	762.0	762.3	762.0	761.8	761.5	761.1	761.2	761.3	761.3	761.4	761.0
140°	784.1	784.2	784.0	783.9	783.7	783.5	783.9	784.2	784.6	784.9	784.6
142.5°	805.4	805.6	805.9	806.1	806.3	806.5	806.6	806.7	806.7	806.8	806.3
145°	837.9	838.1	838.1	838.1	838.1	838.1	838.3	838.4	838.6	838.8	838.3
147.5°	864.4	864.4	864.6	864.8	865.1	865.3	865.4	865.6	865.8	866.0	865.5
150°	881.0	881.0	881.4	881.7	882.0	882.3	882.7	883.0	883.4	883.6	883.2
152.5°	896.5	896.4	896.6	897.0	897.3	897.7	898.0	898.3	898.6	899.0	898.5
155°	917.5	917.1	917.5	917.8	918.1	918.4	918.9	919.5	919.9	920.4	920.0
157.5°	935.9	935.7	935.8	935.8	935.8	935.9	936.3	936.9	937.5	937.9	937.5
160°	946.2	945.8	945.9	946.1	946.3	946.4	947.1	947.7	948.4	949.0	948.8
162.5°	955.6	955.3	955.4	955.5	955.7	955.9	956.8	957.7	958.7	959.5	959.3
165°	968.3	967.9	968.1	968.3	968.4	968.6	969.6	970.5	971.5	972.5	972.3
167.5°	977.6	977.2	977.3	977.5	977.7	977.9	979.0	980.2	981.4	982.6	982.4
170°	982.4	981.9	982.0	982.2	982.4	982.6	983.9	985.1	986.5	987.8	987.7
172.5°	985.9	985.5	985.8	986.1	986.4	986.7	987.9	989.0	990.2	991.5	991.3
175°	990.4	990.0	990.1	990.3	990.5	990.7	992.0	993.3	994.6	995.9	995.8
177.5°	993.0	992.7	992.8	992.9	993.1	993.2	994.1	995.0	995.9	996.8	996.8
180°	994.4	994.4	994.4	994.4	994.4	994.4	994.4	994.4	994.4	994.4	994.4



TEST NUMBER: P333268-830

CATALOG NUMBER: S125DIP-S1090D810U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1428.0	1431.6	1428.6	1432.7	1428.6	1431.6	1428.0	1431.2	1435.7	1432.7	1439.7
5°	1316.3	1310.5	1314.3	1311.7	1314.3	1310.5	1316.3	1319.4	1327.0	1329.6	1334.6
7.5°	1213.0	1207.5	1201.2	1198.3	1201.2	1207.5	1213.0	1214.8	1221.3	1230.9	1238.1
10°	1148.3	1141.3	1140.7	1136.2	1140.7	1141.3	1148.3	1155.3	1159.7	1171.9	1180.1
12.5°	1101.0	1094.5	1087.2	1085.3	1087.2	1094.5	1101.0	1106.9	1108.3	1121.9	1127.7
15°	1033.8	1028.7	1024.3	1028.0	1024.3	1028.7	1033.8	1037.6	1044.6	1054.1	1060.5
17.5°	977.9	973.7	973.0	968.3	973.0	973.7	977.9	980.1	991.6	997.8	1008.7
20°	942.8	939.6	940.9	932.6	940.9	939.6	942.8	948.6	960.0	963.2	974.6
22.5°	914.8	908.6	907.9	906.2	907.9	908.6	914.8	920.0	922.3	932.1	940.0
25°	870.9	867.7	864.6	867.7	864.6	867.7	870.9	876.7	879.2	886.2	893.8
27.5°	832.6	828.8	827.9	828.3	827.9	828.8	832.6	832.1	839.0	844.6	850.2
30°	809.2	802.9	803.5	802.9	803.5	802.9	809.2	809.2	813.0	818.1	823.2
32.5°	783.7	779.4	778.5	777.4	778.5	779.4	783.7	782.8	787.6	793.7	799.3
35°	746.2	746.2	743.0	743.0	743.0	746.2	746.2	748.1	753.2	753.2	759.6
37.5°	711.0	710.3	708.4	708.7	708.4	710.3	711.0	712.5	714.3	717.0	721.0
40°	684.5	683.9	681.9	678.2	681.9	683.9	684.5	687.0	688.3	691.5	694.1
42.5°	659.0	657.0	656.0	654.8	656.0	657.0	659.0	660.6	661.4	665.5	670.6
45°	619.0	619.0	617.7	617.1	617.7	619.0	619.0	619.0	619.6	624.7	627.3
47.5°	580.0	581.2	583.6	583.2	583.6	581.2	580.0	579.0	579.3	581.8	584.8
50°	556.7	557.3	559.2	559.9	559.2	557.3	556.7	554.1	552.8	552.8	554.8
52.5°	530.7	534.4	536.8	536.4	536.8	534.4	530.7	528.7	526.4	523.3	526.2
55°	494.3	498.8	503.2	503.9	503.2	498.8	494.3	488.6	486.1	481.0	482.9
57.5°	458.3	464.5	469.2	470.8	469.2	464.5	458.3	451.4	443.2	440.7	437.2
60°	433.9	442.1	447.9	450.4	447.9	442.1	433.9	427.5	416.7	409.7	407.2
62.5°	410.5	419.7	425.5	425.9	425.5	419.7	410.5	400.5	389.7	381.7	376.6
65°	372.1	381.7	386.8	390.6	386.8	381.7	372.1	361.4	349.2	338.5	332.7
67.5°	330.9	340.4	346.1	349.1	346.1	340.4	330.9	317.5	306.5	294.1	287.3
70°	301.0	310.5	318.1	320.7	318.1	310.5	301.0	285.0	275.5	264.0	258.3
72.5°	271.4	279.9	286.1	289.1	286.1	279.9	271.4	256.5	245.4	233.9	226.2
75°	220.1	231.6	237.3	240.4	237.3	231.6	220.1	211.9	199.2	187.0	180.7
77.5°	169.8	180.1	183.6	185.2	183.6	180.1	169.8	160.0	150.4	141.6	135.3
80°	136.1	142.5	146.9	147.6	146.9	142.5	136.1	128.5	120.8	112.6	106.9
82.5°	104.6	109.9	111.3	113.0	111.3	109.9	104.6	97.9	91.3	85.1	80.4
85°	57.2	59.8	60.4	59.8	60.4	59.8	57.2	52.8	49.6	46.5	44.5
87.5°	22.1	21.7	21.8	22.9	21.8	21.7	22.1	20.9	21.3	20.2	18.9
90°	16.2	16.7	17.2	17.7	17.2	16.7	16.2	15.7	15.1	14.2	13.5
92.5°	15.8	16.0	16.3	16.5	16.3	16.0	15.8	15.6	15.1	14.2	13.5
95°	15.5	15.5	15.5	15.5	15.5	15.5	15.5	15.5	15.1	14.2	13.5
97.5°	15.5	15.5	15.5	15.5	15.5	15.5	15.5	15.5	17.8	22.4	27.1
100°	17.4	16.8	16.1	15.5	16.1	16.8	17.4	18.1	30.6	55.0	79.5
102.5°	126.1	115.0	103.9	92.7	103.9	115.0	126.1	137.3	145.2	149.8	154.4
105°	219.4	219.2	219.0	219.0	219.0	219.2	219.4	219.6	219.6	219.6	219.6
107.5°	277.5	276.9	276.4	276.0	276.4	276.9	277.5	278.0	278.1	278.1	278.1
110°	315.0	315.2	315.3	315.5	315.3	315.2	315.0	314.8	315.0	315.5	315.9



TEST NUMBER: P333268-830

CATALOG NUMBER: S125DIP-S1090D810U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	351.6	351.3	351.1	350.9	351.1	351.3	351.6	351.8	352.2	352.8	353.5
115°	406.9	405.9	404.9	404.0	404.9	405.9	406.9	407.8	408.7	409.3	410.0
117.5°	461.8	461.4	461.0	460.5	461.0	461.4	461.8	462.2	462.9	463.7	464.6
120°	497.8	497.0	496.2	495.3	496.2	497.0	497.8	498.6	499.2	499.5	499.8
122.5°	531.2	530.3	529.3	528.4	529.3	530.3	531.2	532.2	532.8	533.1	533.5
125°	580.1	579.6	579.1	578.6	579.1	579.6	580.1	580.6	581.2	581.8	582.5
127.5°	624.6	623.4	622.2	620.9	622.2	623.4	624.6	625.8	626.6	627.0	627.3
130°	654.0	653.3	652.4	651.6	652.4	653.3	654.0	654.9	655.5	656.0	656.5
132.5°	682.4	681.6	680.7	680.0	680.7	681.6	682.4	683.2	683.6	683.7	683.8
135°	721.6	720.7	719.6	718.7	719.6	720.7	721.6	722.6	723.3	723.6	724.0
137.5°	760.2	759.3	758.5	757.6	758.5	759.3	760.2	761.0	761.4	761.3	761.3
140°	783.5	782.6	781.6	780.6	781.6	782.6	783.5	784.6	784.9	784.6	784.2
142.5°	805.4	804.4	803.4	802.4	803.4	804.4	805.4	806.3	806.8	806.7	806.7
145°	837.4	836.4	835.4	834.4	835.4	836.4	837.4	838.3	838.8	838.6	838.4
147.5°	864.3	863.2	862.0	860.8	862.0	863.2	864.3	865.5	866.0	865.8	865.6
150°	881.8	880.5	879.2	877.9	879.2	880.5	881.8	883.2	883.6	883.4	883.0
152.5°	897.4	896.2	895.0	893.8	895.0	896.2	897.4	898.5	899.0	898.6	898.3
155°	918.7	917.4	916.1	914.7	916.1	917.4	918.7	920.0	920.4	919.9	919.5
157.5°	936.2	934.9	933.6	932.3	933.6	934.9	936.2	937.5	937.9	937.5	936.9
160°	947.4	946.1	944.8	943.5	944.8	946.1	947.4	948.8	949.0	948.4	947.7
162.5°	957.8	956.4	955.0	953.6	955.0	956.4	957.8	959.3	959.5	958.7	957.7
165°	971.0	969.7	968.4	967.0	968.4	969.7	971.0	972.3	972.5	971.5	970.5
167.5°	980.9	979.5	978.0	976.6	978.0	979.5	980.9	982.4	982.6	981.4	980.2
170°	986.3	984.8	983.3	981.8	983.3	984.8	986.3	987.7	987.8	986.5	985.1
172.5°	989.8	988.4	986.8	985.3	986.8	988.4	989.8	991.3	991.5	990.2	989.0
175°	994.4	992.9	991.5	990.0	991.5	992.9	994.4	995.8	995.9	994.6	993.3
177.5°	995.7	994.7	993.6	992.6	993.6	994.7	995.7	996.8	996.8	995.9	995.0
180°	994.4	994.4	994.4	994.4	994.4	994.4	994.4	994.4	994.4	994.4	994.4



TEST NUMBER: P333268-830

CATALOG NUMBER: S125DIP-S1090D810U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1433.1	1439.3	1446.9	1452.5	1462.6	1467.3	1472.8	1477.4	1485.5	1493.2	1502.4
5°	1336.6	1347.4	1362.1	1377.9	1396.4	1409.1	1426.9	1437.8	1459.3	1479.1	1498.2
7.5°	1249.1	1262.3	1283.0	1303.3	1327.6	1349.4	1371.7	1396.4	1424.0	1456.6	1483.6
10°	1189.0	1206.8	1229.1	1254.5	1283.8	1309.2	1339.2	1365.8	1399.6	1437.8	1473.4
12.5°	1141.1	1156.4	1181.2	1205.7	1237.0	1268.0	1298.9	1334.3	1373.7	1415.9	1460.7
15°	1075.2	1087.9	1108.2	1141.9	1173.7	1204.3	1250.8	1283.8	1333.4	1380.4	1434.5
17.5°	1018.8	1034.5	1051.7	1080.6	1113.5	1151.7	1193.2	1234.6	1282.5	1342.2	1403.2
20°	984.1	996.8	1016.6	1038.9	1073.8	1112.0	1151.5	1193.4	1252.0	1313.7	1379.2
22.5°	946.5	960.3	982.5	1006.8	1036.2	1072.8	1116.3	1162.4	1223.5	1284.2	1355.3
25°	902.1	911.6	932.0	953.7	982.9	1014.1	1059.2	1110.1	1170.5	1239.9	1312.4
27.5°	860.3	868.6	887.2	906.1	932.5	969.5	1009.8	1061.3	1118.2	1188.5	1268.9
30°	830.2	839.1	855.6	876.0	901.4	933.9	975.2	1023.6	1084.7	1153.4	1237.4
32.5°	804.3	812.1	824.6	845.0	869.9	901.4	939.6	989.0	1050.1	1119.7	1202.2
35°	764.0	773.0	782.5	798.4	820.0	850.6	892.6	939.0	997.5	1065.0	1140.7
37.5°	724.1	733.8	742.3	756.6	776.3	803.2	839.5	887.9	940.8	1005.8	1078.5
40°	699.2	706.8	713.8	729.1	748.8	774.2	807.9	851.2	907.2	967.6	1028.0
42.5°	674.2	681.4	687.3	700.6	718.8	743.2	775.3	817.6	869.5	925.9	979.2
45°	634.9	639.3	646.3	657.8	672.4	694.7	725.9	763.4	807.3	860.7	900.8
47.5°	592.4	599.4	605.1	615.2	627.2	649.0	678.9	710.9	750.6	790.4	818.6
50°	559.9	566.8	575.1	584.7	596.1	616.4	643.9	676.3	709.9	740.5	764.7
52.5°	529.3	535.7	544.6	553.6	567.6	584.8	608.2	637.1	670.2	692.1	712.3
55°	484.1	487.3	497.5	506.4	519.7	532.4	556.0	581.5	601.8	618.4	634.9
57.5°	437.9	442.2	448.1	456.1	469.4	484.3	500.8	523.3	535.3	543.8	556.7
60°	408.4	409.7	413.5	423.0	433.2	446.6	465.7	481.5	490.5	497.5	508.3
62.5°	375.9	376.1	382.5	389.5	397.1	411.5	427.0	439.9	447.2	450.6	461.0
65°	330.2	328.9	332.7	338.5	347.3	356.8	370.2	381.7	381.1	384.8	391.2
67.5°	283.5	282.2	282.2	287.7	294.9	303.5	312.6	319.2	319.3	324.4	327.6
70°	251.9	248.1	250.6	255.1	258.3	265.3	275.5	278.1	278.6	281.2	284.4
72.5°	219.3	218.1	220.1	222.1	224.2	229.7	238.3	239.9	240.0	241.5	246.7
75°	174.3	173.1	171.7	173.7	176.3	180.0	183.2	185.8	185.1	185.8	189.5
77.5°	130.6	127.1	126.5	127.5	128.1	130.4	133.7	133.5	134.1	133.9	138.3
80°	103.7	98.6	97.9	97.9	98.6	99.9	101.1	102.5	100.5	102.5	103.7
82.5°	76.3	73.1	73.0	72.5	72.7	72.9	73.7	74.5	74.1	74.9	75.7
85°	41.9	40.7	38.8	40.1	39.4	37.5	38.8	36.9	36.3	36.9	37.5
87.5°	16.8	17.2	15.8	15.6	14.9	15.2	13.9	13.1	12.3	12.6	13.9
90°	12.6	11.8	10.7	9.5	8.4	7.2	5.9	4.7	3.4	2.1	0.8
92.5°	12.6	11.8	10.7	9.8	8.8	7.7	7.7	8.6	9.5	10.5	11.3
95°	12.6	11.8	18.0	24.2	30.4	36.7	40.1	40.5	41.0	41.6	42.0
97.5°	31.7	36.3	48.5	60.9	73.2	85.6	91.2	90.4	89.4	88.6	87.8
100°	103.9	128.3	127.6	127.0	126.3	125.6	125.1	124.6	124.0	123.6	123.1
102.5°	159.0	163.6	163.2	162.9	162.5	162.0	161.6	160.9	160.3	159.7	159.1
105°	219.6	219.6	219.6	219.6	219.6	219.6	219.3	218.7	218.0	217.4	216.7
107.5°	278.1	278.1	277.7	277.4	277.0	276.7	276.5	276.5	276.5	276.5	276.5
110°	316.5	317.0	316.6	316.3	315.9	315.7	315.5	315.5	315.5	315.5	315.5



TEST NUMBER: P333268-830

CATALOG NUMBER: S125DIP-S1090D810U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	354.1	354.7	354.5	354.3	354.1	353.9	353.6	353.3	352.8	352.4	352.0
115°	410.7	411.3	411.1	410.9	410.9	410.7	410.2	409.3	408.5	407.7	406.9
117.5°	465.4	466.3	465.7	465.1	464.4	463.8	463.5	463.5	463.5	463.6	463.6
120°	500.2	500.5	500.0	499.5	499.0	498.5	498.3	498.5	498.7	498.9	499.0
122.5°	533.8	534.1	533.9	533.7	533.4	533.2	532.7	532.2	531.5	530.9	530.3
125°	583.2	583.8	583.8	583.8	583.8	583.8	583.2	582.1	580.9	579.8	578.6
127.5°	627.6	628.0	628.1	628.2	628.3	628.4	628.0	627.3	626.4	625.6	624.8
130°	657.0	657.5	657.3	657.1	657.0	656.9	656.4	655.5	654.7	653.9	653.1
132.5°	683.9	684.0	684.4	684.8	685.1	685.5	685.2	684.2	683.2	682.3	681.4
135°	724.2	724.6	724.9	725.2	725.6	725.9	725.6	724.6	723.6	722.6	721.6
137.5°	761.2	761.1	761.5	761.8	762.0	762.3	762.0	761.2	760.3	759.5	758.7
140°	783.9	783.5	783.7	783.9	784.0	784.2	784.1	783.8	783.4	783.2	782.8
142.5°	806.6	806.5	806.3	806.1	805.9	805.6	805.4	805.2	805.0	804.8	804.6
145°	838.3	838.1	838.1	838.1	838.1	838.1	837.9	837.6	837.3	837.0	836.6
147.5°	865.4	865.3	865.1	864.8	864.6	864.4	864.4	864.4	864.5	864.6	864.6
150°	882.7	882.3	882.0	881.7	881.4	881.0	881.0	881.4	881.7	882.0	882.3
152.5°	898.0	897.7	897.3	897.0	896.6	896.4	896.5	897.3	898.0	898.7	899.5
155°	918.9	918.4	918.1	917.8	917.5	917.1	917.5	918.4	919.5	920.4	921.4
157.5°	936.3	935.9	935.8	935.8	935.8	935.7	935.9	936.6	937.2	937.7	938.3
160°	947.1	946.4	946.3	946.1	945.9	945.8	946.2	947.2	948.2	949.1	950.2
162.5°	956.8	955.9	955.7	955.5	955.4	955.3	955.6	956.6	957.6	958.6	959.6
165°	969.6	968.6	968.4	968.3	968.1	967.9	968.3	969.3	970.3	971.3	972.2
167.5°	979.0	977.9	977.7	977.5	977.3	977.2	977.6	978.6	979.7	980.7	981.7
170°	983.9	982.6	982.4	982.2	982.0	981.9	982.4	983.5	984.7	985.8	987.0
172.5°	987.9	986.7	986.4	986.1	985.8	985.5	985.9	987.1	988.3	989.4	990.5
175°	992.0	990.7	990.5	990.3	990.1	990.0	990.4	991.5	992.4	993.3	994.4
177.5°	994.1	993.2	993.1	992.9	992.8	992.7	993.0	993.8	994.6	995.3	996.2
180°	994.4	994.4	994.4	994.4	994.4	994.4	994.4	994.4	994.4	994.4	994.4



TEST NUMBER: P333268-830

CATALOG NUMBER: S125DIP-S1090D810U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1506.9	1514.1	1518.6	1527.3	1534.5	1538.5	1542.1	1545.1	1548.7	1551.7	1560.4
5°	1516.6	1533.1	1547.2	1568.8	1588.6	1603.8	1620.3	1634.9	1647.0	1664.2	1677.5
7.5°	1512.4	1541.8	1572.6	1606.1	1640.3	1672.1	1701.4	1728.7	1753.5	1783.6	1809.9
10°	1508.4	1548.4	1587.9	1633.0	1679.5	1718.9	1755.9	1793.4	1820.7	1858.9	1891.3
12.5°	1505.3	1552.5	1600.1	1654.4	1705.4	1761.1	1810.2	1837.7	1879.2	1909.8	1948.3
15°	1492.4	1554.8	1620.3	1681.4	1753.9	1805.4	1848.7	1902.1	1941.0	1979.7	2021.8
17.5°	1469.4	1540.0	1613.4	1693.4	1762.9	1818.3	1874.1	1925.5	1971.9	2023.9	2076.2
20°	1458.8	1529.4	1613.4	1695.4	1763.5	1821.4	1878.6	1935.2	1986.1	2053.0	2113.4
22.5°	1436.3	1521.7	1599.1	1679.1	1749.2	1812.2	1877.1	1941.4	2009.0	2084.4	2160.2
25°	1396.4	1482.9	1565.0	1643.9	1714.5	1793.4	1862.7	1948.6	2035.1	2135.0	2229.1
27.5°	1354.9	1437.8	1513.0	1589.1	1671.5	1760.8	1850.8	1948.2	2061.4	2187.5	2320.4
30°	1321.4	1399.6	1472.7	1551.0	1636.8	1737.4	1836.0	1951.7	2082.8	2224.7	2382.5
32.5°	1282.1	1354.2	1425.4	1508.3	1601.8	1707.9	1822.8	1949.7	2107.2	2268.4	2430.8
35°	1215.1	1275.5	1348.7	1437.1	1542.8	1664.2	1797.1	1947.3	2128.0	2313.1	2449.9
37.5°	1135.6	1191.8	1268.9	1365.8	1476.6	1606.9	1764.7	1942.9	2134.8	2282.4	2326.5
40°	1082.1	1134.3	1214.5	1314.9	1428.2	1566.2	1739.3	1927.6	2113.4	2207.5	2171.2
42.5°	1025.1	1079.9	1157.9	1257.4	1379.3	1529.7	1707.2	1895.5	2051.3	2086.9	1961.5
45°	935.2	991.7	1068.7	1169.3	1300.3	1463.2	1648.3	1819.5	1909.1	1844.9	1650.9
47.5°	851.6	904.7	976.0	1079.7	1214.9	1383.4	1561.7	1698.2	1705.3	1552.0	1344.7
50°	794.6	843.6	915.5	1019.2	1153.4	1323.9	1484.8	1592.3	1544.0	1370.3	1171.2
52.5°	738.6	786.6	857.4	960.1	1092.8	1249.1	1398.8	1474.2	1383.2	1204.9	1034.8
55°	657.8	699.7	769.1	863.9	989.9	1134.9	1262.2	1288.3	1169.9	994.3	856.3
57.5°	578.9	618.1	681.2	768.5	883.6	1012.1	1111.6	1106.1	981.0	830.3	720.8
60°	525.5	563.6	619.6	704.8	809.8	920.6	1005.8	985.4	861.4	731.6	639.3
62.5°	477.7	511.7	564.7	639.2	735.0	837.5	907.6	877.5	756.0	642.5	569.7
65°	407.2	435.7	481.0	544.6	624.1	708.7	762.8	724.0	620.3	531.9	473.3
67.5°	339.9	362.8	400.7	451.4	519.2	587.2	620.1	581.1	498.1	433.6	390.2
70°	297.1	317.4	346.7	391.9	451.0	508.3	533.1	498.1	426.9	371.6	340.4
72.5°	254.3	271.2	296.8	337.4	384.8	434.5	456.3	422.8	364.3	317.5	288.4
75°	196.6	208.0	225.8	253.8	291.3	330.8	342.9	313.7	276.1	241.1	222.1
77.5°	140.7	150.4	163.9	181.5	208.1	233.2	243.7	226.9	197.8	175.7	160.0
80°	108.1	113.2	124.7	139.3	160.3	176.3	183.2	172.4	152.0	135.5	123.4
82.5°	77.1	82.2	89.1	101.1	114.5	125.4	132.8	125.5	110.8	97.8	90.9
85°	37.5	40.7	44.5	49.6	59.8	66.2	65.5	61.1	55.3	50.2	46.5
87.5°	13.7	14.4	16.2	19.0	20.7	23.1	24.3	23.5	21.7	20.4	18.9
90°	2.1	3.4	4.7	5.9	7.2	8.4	9.5	10.7	11.8	12.6	13.5
92.5°	10.5	9.5	8.6	7.7	7.7	8.8	9.8	10.7	11.8	12.6	13.5
95°	41.6	41.0	40.5	40.1	36.7	30.4	24.2	18.0	11.8	12.6	13.5
97.5°	88.6	89.4	90.4	91.2	85.6	73.2	60.9	48.5	36.3	31.7	27.1
100°	123.6	124.0	124.6	125.1	125.6	126.3	127.0	127.6	128.3	103.9	79.5
102.5°	159.7	160.3	160.9	161.6	162.0	162.5	162.9	163.2	163.6	159.0	154.4
105°	217.4	218.0	218.7	219.3	219.6	219.6	219.6	219.6	219.6	219.6	219.6
107.5°	276.5	276.5	276.5	276.5	276.7	277.0	277.4	277.7	278.1	278.1	278.1
110°	315.5	315.5	315.5	315.5	315.7	315.9	316.3	316.6	317.0	316.5	315.9





TEST NUMBER: P333268-830

CATALOG NUMBER: S125DIP-S1090D810U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	352.4	352.8	353.3	353.6	353.9	354.1	354.3	354.5	354.7	354.1	353.5
115°	407.7	408.5	409.3	410.2	410.7	410.9	410.9	411.1	411.3	410.7	410.0
117.5°	463.6	463.5	463.5	463.5	463.8	464.4	465.1	465.7	466.3	465.4	464.6
120°	498.9	498.7	498.5	498.3	498.5	499.0	499.5	500.0	500.5	500.2	499.8
122.5°	530.9	531.5	532.2	532.7	533.2	533.4	533.7	533.9	534.1	533.8	533.5
125°	579.8	580.9	582.1	583.2	583.8	583.8	583.8	583.8	583.8	583.2	582.5
127.5°	625.6	626.4	627.3	628.0	628.4	628.3	628.2	628.1	628.0	627.6	627.3
130°	653.9	654.7	655.5	656.4	656.9	657.0	657.1	657.3	657.5	657.0	656.5
132.5°	682.3	683.2	684.2	685.2	685.5	685.1	684.8	684.4	684.0	683.9	683.8
135°	722.6	723.6	724.6	725.6	725.9	725.6	725.2	724.9	724.6	724.2	724.0
137.5°	759.5	760.3	761.2	762.0	762.3	762.0	761.8	761.5	761.1	761.2	761.3
140°	783.2	783.4	783.8	784.1	784.2	784.0	783.9	783.7	783.5	783.9	784.2
142.5°	804.8	805.0	805.2	805.4	805.6	805.9	806.1	806.3	806.5	806.6	806.7
145°	837.0	837.3	837.6	837.9	838.1	838.1	838.1	838.1	838.1	838.3	838.4
147.5°	864.6	864.5	864.4	864.4	864.4	864.6	864.8	865.1	865.3	865.4	865.6
150°	882.0	881.7	881.4	881.0	881.0	881.4	881.7	882.0	882.3	882.7	883.0
152.5°	898.7	898.0	897.3	896.5	896.4	896.6	897.0	897.3	897.7	898.0	898.3
155°	920.4	919.5	918.4	917.5	917.1	917.5	917.8	918.1	918.4	918.9	919.5
157.5°	937.7	937.2	936.6	935.9	935.7	935.8	935.8	935.8	935.9	936.3	936.9
160°	949.1	948.2	947.2	946.2	945.8	945.9	946.1	946.3	946.4	947.1	947.7
162.5°	958.6	957.6	956.6	955.6	955.3	955.4	955.5	955.7	955.9	956.8	957.7
165°	971.3	970.3	969.3	968.3	967.9	968.1	968.3	968.4	968.6	969.6	970.5
167.5°	980.7	979.7	978.6	977.6	977.2	977.3	977.5	977.7	977.9	979.0	980.2
170°	985.8	984.7	983.5	982.4	981.9	982.0	982.2	982.4	982.6	983.9	985.1
172.5°	989.4	988.3	987.1	985.9	985.5	985.8	986.1	986.4	986.7	987.9	989.0
175°	993.3	992.4	991.5	990.4	990.0	990.1	990.3	990.5	990.7	992.0	993.3
177.5°	995.3	994.6	993.8	993.0	992.7	992.8	992.9	993.1	993.2	994.1	995.0
180°	994.4	994.4	994.4	994.4	994.4	994.4	994.4	994.4	994.4	994.4	994.4



TEST NUMBER: P333268-830

CATALOG NUMBER: S125DIP-S1090D810U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1567.5	1571.6	1580.3	1577.2	1581.3	1583.3	1585.4
5°	1694.1	1714.5	1723.3	1722.1	1735.5	1732.3	1729.1
7.5°	1837.1	1858.5	1870.5	1885.4	1894.0	1894.6	1902.1
10°	1918.1	1946.1	1957.5	1973.4	1983.6	1989.3	1988.7
12.5°	1980.2	2002.1	2027.7	2035.5	2049.3	2056.4	2053.8
15°	2054.8	2089.8	2116.6	2129.9	2147.1	2152.2	2159.2
17.5°	2121.5	2168.4	2199.6	2241.1	2256.7	2266.2	2260.7
20°	2171.9	2233.6	2264.7	2314.4	2341.7	2356.4	2351.3
22.5°	2231.5	2298.2	2355.9	2398.9	2440.4	2460.2	2464.3
25°	2333.5	2425.1	2509.7	2566.4	2617.8	2629.9	2656.7
27.5°	2447.5	2555.5	2646.0	2705.5	2741.4	2754.9	2763.3
30°	2519.2	2626.8	2694.8	2733.0	2744.4	2743.2	2741.9
32.5°	2554.4	2621.7	2634.8	2624.0	2597.8	2575.7	2552.6
35°	2504.6	2454.4	2379.3	2282.6	2211.3	2139.5	2132.4
37.5°	2252.6	2091.9	1966.9	1827.3	1746.8	1697.0	1662.7
40°	2015.3	1832.8	1681.4	1563.7	1481.7	1449.2	1417.4
42.5°	1757.8	1583.5	1449.3	1350.9	1289.3	1253.3	1228.0
45°	1428.2	1274.2	1169.3	1098.1	1049.0	1021.1	1005.1
47.5°	1170.3	1056.4	967.2	915.9	882.0	860.3	860.4
50°	1031.9	923.1	863.9	823.2	793.9	776.7	780.0
52.5°	909.2	827.9	777.4	743.3	721.7	711.1	710.8
55°	760.3	701.7	668.6	643.9	629.1	617.1	619.6
57.5°	650.3	601.0	578.8	558.2	548.0	543.2	536.1
60°	582.1	543.9	524.8	508.3	498.1	494.3	487.3
62.5°	521.5	491.5	473.0	459.4	450.3	449.0	443.6
65°	438.3	415.4	398.9	392.5	383.0	380.4	380.4
67.5°	361.4	345.0	332.1	326.2	322.1	322.6	319.6
70°	313.0	299.6	291.3	285.0	281.8	282.5	279.9
72.5°	273.8	258.9	251.7	247.9	243.6	245.3	244.3
75°	207.4	199.7	196.0	192.1	189.5	188.3	187.0
77.5°	152.3	145.5	142.6	140.4	140.8	137.8	140.3
80°	117.7	112.0	110.1	106.9	106.2	106.2	105.6
82.5°	86.1	82.9	81.5	78.9	77.8	78.8	77.1
85°	44.5	41.9	41.4	41.4	40.1	38.8	41.9
87.5°	19.1	17.2	17.4	17.0	17.1	16.7	15.7
90°	14.2	15.1	15.7	16.2	16.7	17.2	17.7
92.5°	14.2	15.1	15.6	15.8	16.0	16.3	16.5
95°	14.2	15.1	15.5	15.5	15.5	15.5	15.5
97.5°	22.4	17.8	15.5	15.5	15.5	15.5	15.5
100°	55.0	30.6	18.1	17.4	16.8	16.1	15.5
102.5°	149.8	145.2	137.3	126.1	115.0	103.9	92.7
105°	219.6	219.6	219.6	219.4	219.2	219.0	219.0
107.5°	278.1	278.1	278.0	277.5	276.9	276.4	276.0
110°	315.5	315.0	314.8	315.0	315.2	315.3	315.5



TEST NUMBER: P333268-830

CATALOG NUMBER: S125DIP-S1090D810U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	352.8	352.2	351.8	351.6	351.3	351.1	350.9
115°	409.3	408.7	407.8	406.9	405.9	404.9	404.0
117.5°	463.7	462.9	462.2	461.8	461.4	461.0	460.5
120°	499.5	499.2	498.6	497.8	497.0	496.2	495.3
122.5°	533.1	532.8	532.2	531.2	530.3	529.3	528.4
125°	581.8	581.2	580.6	580.1	579.6	579.1	578.6
127.5°	627.0	626.6	625.8	624.6	623.4	622.2	620.9
130°	656.0	655.5	654.9	654.0	653.3	652.4	651.6
132.5°	683.7	683.6	683.2	682.4	681.6	680.7	680.0
135°	723.6	723.3	722.6	721.6	720.7	719.6	718.7
137.5°	761.3	761.4	761.0	760.2	759.3	758.5	757.6
140°	784.6	784.9	784.6	783.5	782.6	781.6	780.6
142.5°	806.7	806.8	806.3	805.4	804.4	803.4	802.4
145°	838.6	838.8	838.3	837.4	836.4	835.4	834.4
147.5°	865.8	866.0	865.5	864.3	863.2	862.0	860.8
150°	883.4	883.6	883.2	881.8	880.5	879.2	877.9
152.5°	898.6	899.0	898.5	897.4	896.2	895.0	893.8
155°	919.9	920.4	920.0	918.7	917.4	916.1	914.7
157.5°	937.5	937.9	937.5	936.2	934.9	933.6	932.3
160°	948.4	949.0	948.8	947.4	946.1	944.8	943.5
162.5°	958.7	959.5	959.3	957.8	956.4	955.0	953.6
165°	971.5	972.5	972.3	971.0	969.7	968.4	967.0
167.5°	981.4	982.6	982.4	980.9	979.5	978.0	976.6
170°	986.5	987.8	987.7	986.3	984.8	983.3	981.8
172.5°	990.2	991.5	991.3	989.8	988.4	986.8	985.3
175°	994.6	995.9	995.8	994.4	992.9	991.5	990.0
177.5°	995.9	996.8	996.8	995.7	994.7	993.6	992.6
180°	994.4	994.4	994.4	994.4	994.4	994.4	994.4

(END OF REPORT)