

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333142-935

Luminaire Tested: **S125DIP-S375D1035U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333142-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S375D1035U935-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4886.3 lumens
Efficiency: N/A
Efficacy: 131.0 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333142-935

CATALOG NUMBER: S125DIP-S375D1035U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333142-935

CATALOG NUMBER: S125DIP-S375D1035U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35	27
1	93	89	85	82	83	79	76	73	62	60	58	46	45	43	31	30	30	23
2	85	77	72	67	75	69	65	60	54	51	48	40	38	36	28	26	25	20
3	77	68	61	56	69	61	55	50	48	44	41	36	33	31	24	23	22	17
4	70	60	53	47	63	54	48	43	43	38	34	32	29	26	22	20	19	14
5	65	54	46	40	57	48	42	37	38	33	30	29	25	23	20	18	16	12
6	59	48	40	35	53	43	36	32	34	29	26	26	22	20	18	16	14	11
7	55	43	35	30	49	39	32	28	31	26	23	23	20	18	16	14	13	10
8	51	39	32	26	45	35	29	24	28	23	20	21	18	16	15	13	11	9
9	47	35	28	23	42	32	26	21	26	21	18	19	16	14	14	12	10	8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3027	3027	3027	3027
5°	3505	3038	2660	3038
10°	4078	3022	2330	3022
15°	4515	3000	2150	3000
20°	5054	2965	2004	2965
25°	5920	2925	1934	2925
30°	6395	2885	1873	2885
35°	5257	2812	1832	2812
40°	3737	2710	1788	2710
45°	2872	2573	1763	2573
50°	2451	2402	1758	2402
55°	2182	2235	1775	2235
60°	1969	2052	1820	2052
65°	1819	1869	1867	1869
70°	1654	1679	1894	1679
75°	1460	1480	1876	1480
80°	1231	1209	1715	1209
85°	978	867	1386	867



TEST NUMBER: P333142-935

CATALOG NUMBER: S125DIP-S375D1035U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.1	0.9
10°-20°	134.4	2.7
20°-30°	218.2	4.5
30°-40°	266.1	5.4
40°-50°	242.1	5.0
50°-60°	192.8	3.9
60°-70°	134.3	2.7
70°-80°	71.6	1.5
80°-90°	20.5	0.4
90°-100°	42.2	0.9
100°-110°	259.7	5.3
110°-120°	471.1	9.6
120°-130°	604.6	12.4
130°-140°	650.2	13.3
140°-150°	610.3	12.5
150°-160°	493.7	10.1
160°-170°	319.3	6.5
170°-180°	110.1	2.3
0°-30°	397.6	8.1
0°-40°	663.7	13.6
0°-60°	1098.7	22.5
0°-90°	1325.1	27.1
90°-120°	772.9	15.8
90°-150°	2638.1	54.0
90°-180°	3561.0	72.9
0°-180°	4886.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	469	469	469	469	469	
5°	541	469	410	469	541	54
15°	675	449	322	449	675	193
25°	831	410	271	410	831	379
35°	667	357	232	357	667	408
45°	314	282	193	282	314	252
55°	194	198	158	198	194	174
65°	119	122	122	122	119	118
75°	58	59	75	59	58	63
85°	13	12	19	12	13	16
90°	21	1	21	1	21	9
95°	18	49	18	49	18	15
105°	255	253	255	253	255	231
115°	471	475	471	475	471	468
125°	675	675	675	675	675	600
135°	838	842	838	842	838	647
145°	973	976	973	976	973	608
155°	1067	1075	1067	1075	1067	492
165°	1128	1134	1128	1134	1128	318
175°	1154	1160	1154	1160	1154	110
180°	1160	1160	1160	1160	1160	



TEST NUMBER: P333142-935

CATALOG NUMBER: S125DIP-S375D1035U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	495.8	495.2	494.5	493.3	494.2	491.5	490.3	488.0	485.3	484.3	483.2
5°	540.7	541.7	542.8	538.6	539.0	536.1	529.8	524.6	520.5	515.1	511.3
7.5°	594.9	592.5	592.3	589.6	585.0	581.2	574.5	566.0	557.8	548.4	540.6
10°	621.9	622.2	620.4	617.2	612.2	608.6	599.9	591.5	581.3	569.4	560.9
12.5°	642.3	643.2	640.8	636.5	634.1	626.1	619.2	609.3	597.3	587.7	574.7
15°	675.2	673.0	671.5	666.1	661.9	653.6	642.7	632.2	619.1	607.0	594.9
17.5°	707.0	708.8	705.8	700.9	687.9	678.1	663.5	649.3	632.9	616.6	602.2
20°	735.3	736.9	732.4	723.8	708.3	698.5	679.2	660.9	642.0	621.1	605.2
22.5°	770.7	769.4	763.2	750.2	736.8	718.8	697.8	675.5	651.9	628.3	607.1
25°	830.8	822.4	818.6	802.5	784.9	758.4	729.8	697.2	667.7	636.5	609.4
27.5°	864.2	861.5	857.3	846.1	827.5	799.2	765.4	725.7	684.2	644.7	609.2
30°	857.5	857.9	858.2	854.7	842.7	821.5	787.8	745.1	695.7	651.3	610.4
32.5°	798.2	805.5	812.4	820.6	824.0	819.8	798.8	760.2	709.4	659.0	609.8
35°	666.8	669.1	691.6	713.9	744.1	767.6	783.3	766.1	723.4	665.5	609.0
37.5°	520.0	530.7	546.3	571.4	615.1	654.2	704.5	727.5	713.8	667.6	607.6
40°	443.2	453.2	463.4	489.0	525.8	573.2	630.3	679.0	690.3	660.9	602.8
42.5°	384.1	391.9	403.2	422.5	453.2	495.2	549.7	613.5	652.6	641.5	592.8
45°	314.4	319.3	328.0	343.4	365.7	398.5	446.6	516.3	577.0	597.0	569.0
47.5°	269.1	269.1	275.9	286.4	302.5	330.4	366.0	420.5	485.3	533.3	531.1
50°	243.9	242.9	248.3	257.4	270.2	288.7	322.7	366.3	428.5	482.8	498.0
52.5°	222.2	222.4	225.7	232.5	243.1	258.9	284.3	323.6	376.8	432.6	461.1
55°	193.8	193.0	196.7	201.3	209.1	219.5	237.7	267.8	311.0	365.8	402.9
57.5°	167.6	169.9	171.3	174.5	181.0	188.0	203.4	225.4	259.7	306.8	345.9
60°	152.4	154.5	155.8	158.9	164.1	170.1	182.0	199.9	228.8	269.4	308.2
62.5°	138.7	140.4	140.9	143.7	147.9	153.7	163.1	178.1	201.0	236.4	274.4
65°	119.0	119.0	119.8	122.8	124.8	129.9	137.1	148.0	166.3	194.0	226.4
67.5°	100.0	100.9	100.7	102.0	103.8	107.9	113.0	122.0	135.6	155.8	181.8
70°	87.6	88.3	88.2	89.1	91.1	93.7	97.9	106.4	116.1	133.5	155.8
72.5°	76.4	76.7	76.2	77.5	78.7	80.9	85.7	90.2	99.3	113.9	132.2
75°	58.5	58.9	59.3	60.1	61.3	62.5	64.8	69.4	75.4	86.4	98.1
77.5°	43.8	43.0	44.1	43.9	44.6	45.5	47.6	50.0	54.9	61.9	70.9
80°	33.1	33.2	33.2	33.4	34.4	35.0	36.8	38.6	42.4	47.5	53.9
82.5°	24.1	24.6	24.3	24.7	25.5	25.9	26.9	28.4	30.6	34.7	39.3
85°	13.2	12.1	12.6	12.9	12.9	13.2	13.9	14.6	15.8	17.3	19.1
87.5°	7.9	8.2	8.2	8.1	8.1	8.0	8.4	8.3	8.5	8.8	9.1
90°	20.7	20.1	19.5	18.9	18.3	17.6	16.6	15.7	14.7	13.8	12.4
92.5°	19.3	19.0	18.7	18.4	18.2	17.6	16.6	15.7	14.7	13.8	12.6
95°	18.1	18.1	18.1	18.1	18.1	17.6	16.6	15.7	14.7	13.8	21.0
97.5°	18.1	18.1	18.1	18.1	18.1	20.8	26.2	31.5	36.9	42.3	56.7
100°	18.1	18.9	19.5	20.3	21.1	35.7	64.2	92.6	121.1	149.6	148.8
102.5°	108.1	121.1	134.1	147.1	160.1	169.3	174.7	180.0	185.5	190.9	190.4
105°	255.3	255.5	255.7	255.9	256.1	256.1	256.1	256.1	256.1	256.1	256.1
107.5°	321.8	322.4	323.0	323.6	324.2	324.4	324.4	324.3	324.3	324.3	323.9
110°	367.9	367.7	367.6	367.4	367.2	367.4	367.9	368.5	369.1	369.6	369.3



TEST NUMBER: P333142-935

CATALOG NUMBER: S125DIP-S375D1035U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	409.2	409.5	409.7	410.0	410.3	410.8	411.5	412.2	412.9	413.7	413.5
115°	471.1	472.3	473.4	474.6	475.7	476.6	477.4	478.2	479.0	479.7	479.5
117.5°	537.1	537.6	538.1	538.6	539.1	539.8	540.9	541.8	542.9	543.8	543.1
120°	577.7	578.7	579.6	580.6	581.5	582.2	582.6	583.0	583.3	583.8	583.2
122.5°	616.2	617.3	618.5	619.6	620.6	621.4	621.8	622.2	622.5	622.9	622.7
125°	674.9	675.5	676.0	676.6	677.2	677.8	678.6	679.3	680.1	680.9	680.9
127.5°	724.2	725.7	727.0	728.4	729.9	730.7	731.2	731.6	732.0	732.5	732.5
130°	759.9	761.0	761.9	762.8	763.8	764.6	765.1	765.7	766.3	766.8	766.6
132.5°	793.0	793.9	794.9	795.8	796.8	797.3	797.5	797.5	797.6	797.8	798.2
135°	838.2	839.3	840.5	841.6	842.7	843.5	844.0	844.3	844.6	845.1	845.4
137.5°	883.6	884.6	885.5	886.6	887.5	888.0	887.9	887.9	887.8	887.7	888.0
140°	910.4	911.5	912.7	913.9	915.0	915.3	915.0	914.6	914.2	913.9	914.0
142.5°	935.8	937.0	938.1	939.3	940.5	941.0	940.9	940.8	940.7	940.6	940.4
145°	973.2	974.3	975.4	976.6	977.8	978.2	978.0	977.8	977.7	977.5	977.5
147.5°	1003.9	1005.3	1006.7	1008.1	1009.4	1010.0	1009.8	1009.5	1009.4	1009.1	1008.8
150°	1023.9	1025.4	1026.9	1028.5	1030.0	1030.5	1030.2	1029.8	1029.4	1029.1	1028.6
152.5°	1042.4	1043.8	1045.2	1046.5	1047.9	1048.4	1048.1	1047.7	1047.3	1046.9	1046.5
155°	1066.9	1068.4	1069.9	1071.4	1073.0	1073.5	1072.9	1072.3	1071.8	1071.2	1070.7
157.5°	1087.4	1088.8	1090.4	1091.9	1093.5	1093.9	1093.3	1092.7	1092.1	1091.5	1091.4
160°	1100.4	1101.9	1103.5	1105.0	1106.5	1106.9	1106.1	1105.4	1104.6	1103.8	1103.6
162.5°	1112.1	1113.8	1115.4	1117.1	1118.8	1119.1	1118.0	1117.0	1115.9	1114.8	1114.7
165°	1127.9	1129.5	1130.9	1132.5	1134.0	1134.2	1133.1	1131.9	1130.8	1129.6	1129.5
167.5°	1138.9	1140.7	1142.4	1144.1	1145.8	1146.0	1144.6	1143.2	1141.9	1140.5	1140.2
170°	1145.1	1146.9	1148.6	1150.2	1151.9	1152.1	1150.6	1149.0	1147.5	1146.0	1145.7
172.5°	1149.3	1150.9	1152.6	1154.3	1156.1	1156.2	1154.9	1153.5	1152.1	1150.7	1150.4
175°	1154.5	1156.2	1158.0	1159.7	1161.4	1161.5	1160.0	1158.5	1156.9	1155.4	1155.2
177.5°	1157.6	1158.9	1160.1	1161.3	1162.5	1162.6	1161.6	1160.5	1159.4	1158.3	1158.2
180°	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7



TEST NUMBER: P333142-935

CATALOG NUMBER: S125DIP-S375D1035U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	482.2	481.1	479.8	477.6	474.9	473.5	471.3	469.8	467.0	464.6	462.0
5°	506.7	501.5	496.8	490.6	483.9	479.5	474.3	468.6	462.5	456.4	449.6
7.5°	532.1	522.9	513.0	502.3	491.8	482.2	472.9	464.0	455.6	445.3	436.7
10°	549.1	537.5	525.2	510.7	496.5	484.2	471.7	460.8	449.6	437.7	427.1
12.5°	566.1	550.8	533.3	517.4	500.4	485.5	470.8	456.8	442.8	429.6	417.2
15°	578.2	564.6	548.5	525.8	506.7	486.2	466.7	448.7	431.7	417.0	401.5
17.5°	586.1	568.6	551.3	529.6	504.5	481.6	459.5	438.8	419.7	401.1	386.2
20°	587.5	569.6	551.5	530.2	504.5	478.3	456.2	431.4	410.9	391.5	373.2
22.5°	587.0	566.7	547.0	525.1	500.1	475.9	449.2	423.9	401.6	382.6	363.5
25°	582.6	560.9	536.1	514.1	489.4	463.7	436.7	410.4	387.8	366.1	347.2
27.5°	578.8	550.7	522.7	497.0	473.1	449.6	423.7	396.8	371.7	349.7	331.9
30°	574.2	543.3	511.9	485.0	460.5	437.7	413.2	386.9	360.7	339.2	320.1
32.5°	570.1	534.1	500.9	471.7	445.7	423.5	401.0	376.0	350.2	328.4	309.3
35°	562.1	520.5	482.4	449.4	421.8	398.9	380.0	356.7	333.0	311.9	293.7
37.5°	551.9	502.6	461.8	427.1	396.8	372.7	355.2	337.3	314.5	294.2	277.7
40°	543.9	489.8	446.6	411.2	379.8	354.7	338.4	321.5	302.6	283.7	266.2
42.5°	533.9	478.4	431.4	393.2	362.1	337.7	320.6	306.3	289.6	271.9	255.7
45°	515.5	457.6	406.7	365.7	334.2	310.1	292.5	281.7	269.1	252.4	238.8
47.5°	488.4	432.7	380.0	337.7	305.2	282.9	266.3	256.0	247.2	234.8	222.3
50°	464.3	414.1	360.7	318.7	286.3	263.8	248.5	239.1	231.6	222.1	211.5
52.5°	437.5	390.6	341.7	300.2	268.1	246.0	231.0	222.7	216.5	209.7	199.2
55°	394.7	354.9	309.5	270.2	240.6	218.9	205.7	198.5	193.4	188.2	181.8
57.5°	347.7	316.5	276.4	240.3	213.0	193.3	181.1	174.1	170.0	167.4	163.7
60°	314.5	287.9	253.3	220.4	193.8	176.2	164.4	158.9	155.6	153.4	150.6
62.5°	283.8	261.9	229.9	199.9	176.6	160.1	149.4	144.1	140.9	139.8	137.6
65°	238.6	221.6	195.2	170.3	150.4	136.3	127.3	122.3	120.4	119.2	119.3
67.5°	193.9	183.7	162.4	141.2	125.3	113.5	106.2	102.5	101.4	99.9	99.9
70°	166.7	158.9	141.0	122.5	108.4	99.3	92.9	88.9	87.9	87.1	87.0
72.5°	142.7	135.9	120.4	105.6	92.8	84.8	79.6	77.1	75.5	75.1	75.0
75°	107.2	103.5	91.1	79.4	70.6	65.1	61.5	59.3	58.1	57.9	58.1
77.5°	76.2	72.9	65.1	56.7	51.2	47.0	44.0	43.2	41.9	41.9	41.8
80°	57.3	55.1	50.1	43.6	39.0	35.4	33.8	32.5	32.0	31.4	32.0
82.5°	41.5	39.2	35.8	31.6	27.8	25.7	24.1	23.7	23.4	23.2	23.2
85°	20.5	20.7	18.7	15.5	13.9	12.7	11.7	11.7	11.5	11.4	11.5
87.5°	9.2	8.6	7.7	7.0	5.9	5.1	4.6	4.5	4.3	4.5	4.9
90°	11.1	9.7	8.4	7.0	5.4	3.9	2.4	0.9	2.4	3.9	5.4
92.5°	11.4	10.2	9.0	9.0	10.0	11.1	12.1	13.3	12.1	11.1	10.0
95°	28.2	35.6	42.8	46.8	47.3	47.9	48.4	49.0	48.4	47.9	47.3
97.5°	71.0	85.4	99.8	106.4	105.4	104.4	103.3	102.3	103.3	104.4	105.4
100°	148.1	147.3	146.5	145.9	145.3	144.7	144.1	143.5	144.1	144.7	145.3
102.5°	189.9	189.5	189.0	188.4	187.7	187.0	186.2	185.5	186.2	187.0	187.7
105°	256.1	256.1	256.1	255.8	255.0	254.3	253.5	252.7	253.5	254.3	255.0
107.5°	323.5	323.1	322.7	322.5	322.5	322.5	322.5	322.5	322.5	322.5	322.5
110°	368.9	368.5	368.2	367.9	367.9	367.9	367.9	367.9	367.9	367.9	367.9



TEST NUMBER: P333142-935

CATALOG NUMBER: S125DIP-S375D1035U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	413.2	413.0	412.8	412.4	412.0	411.5	411.0	410.6	411.0	411.5	412.0
115°	479.3	479.1	479.0	478.4	477.4	476.5	475.5	474.6	475.5	476.5	477.4
117.5°	542.3	541.7	541.0	540.6	540.6	540.6	540.7	540.7	540.7	540.6	540.6
120°	582.6	582.0	581.4	581.3	581.4	581.6	581.8	582.0	581.8	581.6	581.4
122.5°	622.4	622.2	621.8	621.4	620.6	619.9	619.1	618.5	619.1	619.9	620.6
125°	680.9	680.9	680.9	680.2	678.9	677.5	676.1	674.9	676.1	677.5	678.9
127.5°	732.7	732.8	732.9	732.5	731.5	730.6	729.6	728.7	729.6	730.6	731.5
130°	766.5	766.3	766.0	765.5	764.6	763.6	762.7	761.6	762.7	763.6	764.6
132.5°	798.7	799.0	799.4	799.1	798.0	796.9	795.8	794.7	795.8	796.9	798.0
135°	845.8	846.2	846.6	846.2	845.1	844.0	842.7	841.6	842.7	844.0	845.1
137.5°	888.4	888.7	889.1	888.7	887.8	886.7	885.8	884.8	885.8	886.7	887.8
140°	914.2	914.4	914.6	914.5	914.1	913.8	913.3	913.0	913.3	913.8	914.1
142.5°	940.1	939.9	939.6	939.4	939.1	938.9	938.7	938.4	938.7	938.9	939.1
145°	977.5	977.5	977.5	977.2	976.9	976.5	976.1	975.8	976.1	976.5	976.9
147.5°	1008.7	1008.4	1008.1	1008.1	1008.1	1008.2	1008.3	1008.4	1008.3	1008.2	1008.1
150°	1028.3	1027.9	1027.5	1027.5	1027.9	1028.3	1028.6	1029.1	1028.6	1028.3	1027.9
152.5°	1046.1	1045.8	1045.4	1045.6	1046.5	1047.3	1048.2	1049.0	1048.2	1047.3	1046.5
155°	1070.4	1070.1	1069.6	1070.1	1071.2	1072.3	1073.5	1074.6	1073.5	1072.3	1071.2
157.5°	1091.4	1091.3	1091.3	1091.7	1092.4	1093.0	1093.6	1094.3	1093.6	1093.0	1092.4
160°	1103.5	1103.3	1103.0	1103.5	1104.7	1105.9	1107.0	1108.1	1107.0	1105.9	1104.7
162.5°	1114.5	1114.2	1114.0	1114.6	1115.7	1116.8	1118.0	1119.1	1118.0	1116.8	1115.7
165°	1129.2	1129.0	1128.9	1129.4	1130.5	1131.6	1132.7	1133.9	1132.7	1131.6	1130.5
167.5°	1140.1	1139.9	1139.7	1140.2	1141.3	1142.5	1143.8	1145.0	1143.8	1142.5	1141.3
170°	1145.6	1145.4	1145.2	1145.7	1147.1	1148.4	1149.8	1151.1	1149.8	1148.4	1147.1
172.5°	1150.0	1149.7	1149.4	1149.9	1151.2	1152.5	1153.9	1155.2	1153.9	1152.5	1151.2
175°	1155.0	1154.9	1154.7	1155.1	1156.2	1157.4	1158.6	1159.7	1158.6	1157.4	1156.2
177.5°	1158.0	1157.9	1157.7	1158.1	1159.0	1159.9	1160.9	1161.7	1160.9	1159.9	1159.0
180°	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7



TEST NUMBER: P333142-935

CATALOG NUMBER: S125DIP-S375D1035U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	460.6	458.8	457.4	454.3	452.5	450.1	448.2	450.3	448.1	449.0	447.5
5°	446.3	440.7	436.7	430.9	425.9	421.4	418.0	417.4	415.8	415.0	412.6
7.5°	429.0	422.0	415.2	407.6	401.2	394.8	390.6	387.2	385.0	381.9	379.9
10°	418.8	409.4	401.5	392.4	384.4	377.4	371.9	369.0	366.4	362.7	361.3
12.5°	406.2	396.6	386.8	377.0	369.4	361.6	356.9	352.7	350.9	346.6	346.2
15°	391.2	376.6	367.0	357.1	346.6	340.2	336.2	331.7	329.7	326.7	324.5
17.5°	373.2	360.2	348.3	337.9	328.9	323.6	318.6	315.5	312.0	310.0	306.5
20°	360.1	347.8	335.8	324.9	317.9	311.8	307.8	304.8	301.2	300.2	296.6
22.5°	349.1	335.5	324.1	314.9	307.3	300.3	296.0	293.9	291.5	288.4	287.7
25°	331.2	317.1	307.4	298.3	291.4	285.1	282.1	279.6	277.2	274.9	274.1
27.5°	315.8	303.2	291.6	283.4	277.4	271.6	269.1	265.9	264.2	262.3	260.2
30°	305.0	292.1	281.9	274.0	267.6	262.4	259.6	257.4	255.9	254.3	253.0
32.5°	293.9	281.9	272.1	264.2	257.9	254.0	251.5	249.9	248.2	246.3	244.8
35°	279.1	266.0	256.4	249.7	244.7	241.7	238.9	237.5	235.6	235.6	233.9
37.5°	262.5	251.2	242.7	236.6	232.1	229.5	226.4	225.5	224.2	223.3	222.8
40°	252.7	242.1	234.2	228.0	223.3	221.0	218.6	217.1	216.3	215.2	214.9
42.5°	242.5	232.4	224.8	219.1	214.9	213.1	210.9	209.7	208.1	206.8	206.6
45°	227.0	217.2	210.3	205.7	202.2	199.9	198.5	196.1	195.4	193.8	193.6
47.5°	212.3	202.9	196.1	192.3	189.2	187.4	185.3	182.9	181.9	181.2	181.1
50°	201.3	192.8	186.4	182.9	179.9	177.3	175.0	173.5	172.9	172.9	173.3
52.5°	190.2	182.9	177.5	173.1	170.3	167.6	165.5	164.5	163.7	164.6	165.3
55°	173.9	166.5	162.6	158.3	155.6	152.4	151.4	151.0	150.4	152.0	152.8
57.5°	156.6	151.4	146.8	142.7	140.2	138.3	137.0	136.7	137.8	138.6	141.2
60°	145.6	139.7	135.5	132.3	129.3	128.1	127.7	127.3	128.1	130.3	133.7
62.5°	133.5	128.7	124.2	121.8	119.6	117.6	117.5	117.8	119.3	121.9	125.3
65°	115.8	111.6	108.7	105.8	104.0	102.9	103.2	104.0	105.8	109.3	113.0
67.5°	97.7	94.9	92.2	90.0	88.3	88.3	88.7	89.9	92.0	95.8	99.3
70°	86.2	83.0	80.8	79.8	78.4	77.6	78.8	80.8	82.6	86.2	89.1
72.5°	74.6	71.8	70.1	69.4	68.8	68.2	68.6	70.8	73.2	76.7	80.2
75°	57.3	56.3	55.1	54.3	53.7	54.2	54.5	56.5	58.5	62.3	66.2
77.5°	41.8	40.8	40.0	39.9	39.5	39.8	40.9	42.4	44.3	47.0	50.0
80°	31.6	31.3	30.8	30.7	30.7	30.8	32.5	33.4	35.2	37.8	40.2
82.5°	23.1	22.8	22.7	22.6	22.8	22.9	23.8	25.1	26.6	28.6	30.7
85°	12.1	11.7	12.3	12.6	12.1	12.7	13.2	13.9	14.6	15.5	16.5
87.5°	5.3	5.9	6.1	6.5	6.8	7.4	7.4	8.3	8.7	9.2	9.2
90°	7.0	8.4	9.7	11.1	12.4	13.8	14.7	15.7	16.6	17.6	18.3
92.5°	9.0	9.0	10.2	11.4	12.6	13.8	14.7	15.7	16.6	17.6	18.2
95°	46.8	42.8	35.6	28.2	21.0	13.8	14.7	15.7	16.6	17.6	18.1
97.5°	106.4	99.8	85.4	71.0	56.7	42.3	36.9	31.5	26.2	20.8	18.1
100°	145.9	146.5	147.3	148.1	148.8	149.6	121.1	92.6	64.2	35.7	21.1
102.5°	188.4	189.0	189.5	189.9	190.4	190.9	185.5	180.0	174.7	169.3	160.1
105°	255.8	256.1	256.1	256.1	256.1	256.1	256.1	256.1	256.1	256.1	256.1
107.5°	322.5	322.7	323.1	323.5	323.9	324.3	324.3	324.3	324.4	324.4	324.2
110°	367.9	368.2	368.5	368.9	369.3	369.6	369.1	368.5	367.9	367.4	367.2



TEST NUMBER: P333142-935

CATALOG NUMBER: S125DIP-S375D1035U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	412.4	412.8	413.0	413.2	413.5	413.7	412.9	412.2	411.5	410.8	410.3
115°	478.4	479.0	479.1	479.3	479.5	479.7	479.0	478.2	477.4	476.6	475.7
117.5°	540.6	541.0	541.7	542.3	543.1	543.8	542.9	541.8	540.9	539.8	539.1
120°	581.3	581.4	582.0	582.6	583.2	583.8	583.3	583.0	582.6	582.2	581.5
122.5°	621.4	621.8	622.2	622.4	622.7	622.9	622.5	622.2	621.8	621.4	620.6
125°	680.2	680.9	680.9	680.9	680.9	680.9	680.1	679.3	678.6	677.8	677.2
127.5°	732.5	732.9	732.8	732.7	732.5	732.5	732.0	731.6	731.2	730.7	729.9
130°	765.5	766.0	766.3	766.5	766.6	766.8	766.3	765.7	765.1	764.6	763.8
132.5°	799.1	799.4	799.0	798.7	798.2	797.8	797.6	797.5	797.5	797.3	796.8
135°	846.2	846.6	846.2	845.8	845.4	845.1	844.6	844.3	844.0	843.5	842.7
137.5°	888.7	889.1	888.7	888.4	888.0	887.7	887.8	887.9	887.9	888.0	887.5
140°	914.5	914.6	914.4	914.2	914.0	913.9	914.2	914.6	915.0	915.3	915.0
142.5°	939.4	939.6	939.9	940.1	940.4	940.6	940.7	940.8	940.9	941.0	940.5
145°	977.2	977.5	977.5	977.5	977.5	977.5	977.7	977.8	978.0	978.2	977.8
147.5°	1008.1	1008.1	1008.4	1008.7	1008.8	1009.1	1009.4	1009.5	1009.8	1010.0	1009.4
150°	1027.5	1027.5	1027.9	1028.3	1028.6	1029.1	1029.4	1029.8	1030.2	1030.5	1030.0
152.5°	1045.6	1045.4	1045.8	1046.1	1046.5	1046.9	1047.3	1047.7	1048.1	1048.4	1047.9
155°	1070.1	1069.6	1070.1	1070.4	1070.7	1071.2	1071.8	1072.3	1072.9	1073.5	1073.0
157.5°	1091.7	1091.3	1091.3	1091.4	1091.4	1091.5	1092.1	1092.7	1093.3	1093.9	1093.5
160°	1103.5	1103.0	1103.3	1103.5	1103.6	1103.8	1104.6	1105.4	1106.1	1106.9	1106.5
162.5°	1114.6	1114.0	1114.2	1114.5	1114.7	1114.8	1115.9	1117.0	1118.0	1119.1	1118.8
165°	1129.4	1128.9	1129.0	1129.2	1129.5	1129.6	1130.8	1131.9	1133.1	1134.2	1134.0
167.5°	1140.2	1139.7	1139.9	1140.1	1140.2	1140.5	1141.9	1143.2	1144.6	1146.0	1145.8
170°	1145.7	1145.2	1145.4	1145.6	1145.7	1146.0	1147.5	1149.0	1150.6	1152.1	1151.9
172.5°	1149.9	1149.4	1149.7	1150.0	1150.4	1150.7	1152.1	1153.5	1154.9	1156.2	1156.1
175°	1155.1	1154.7	1154.9	1155.0	1155.2	1155.4	1156.9	1158.5	1160.0	1161.5	1161.4
177.5°	1158.1	1157.7	1157.9	1158.0	1158.2	1158.3	1159.4	1160.5	1161.6	1162.6	1162.5
180°	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7



TEST NUMBER: P333142-935

CATALOG NUMBER: S125DIP-S375D1035U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	446.6	447.7	446.8	448.1	446.8	447.7	446.6	447.5	449.0	448.1	450.3
5°	411.6	409.8	411.0	410.3	411.0	409.8	411.6	412.6	415.0	415.8	417.4
7.5°	379.4	377.6	375.7	374.7	375.7	377.6	379.4	379.9	381.9	385.0	387.2
10°	359.1	356.9	356.7	355.3	356.7	356.9	359.1	361.3	362.7	366.4	369.0
12.5°	344.3	342.2	340.0	339.4	340.0	342.2	344.3	346.2	346.6	350.9	352.7
15°	323.3	321.7	320.3	321.5	320.3	321.7	323.3	324.5	326.7	329.7	331.7
17.5°	305.8	304.5	304.3	302.8	304.3	304.5	305.8	306.5	310.0	312.0	315.5
20°	294.8	293.9	294.3	291.6	294.3	293.9	294.8	296.6	300.2	301.2	304.8
22.5°	286.1	284.1	283.9	283.4	283.9	284.1	286.1	287.7	288.4	291.5	293.9
25°	272.3	271.4	270.4	271.4	270.4	271.4	272.3	274.1	274.9	277.2	279.6
27.5°	260.4	259.2	258.9	259.1	258.9	259.2	260.4	260.2	262.3	264.2	265.9
30°	253.0	251.1	251.2	251.1	251.2	251.1	253.0	253.0	254.3	255.9	257.4
32.5°	245.1	243.7	243.5	243.1	243.5	243.7	245.1	244.8	246.3	248.2	249.9
35°	233.3	233.3	232.4	232.4	232.4	233.3	233.3	233.9	235.6	235.6	237.5
37.5°	222.3	222.1	221.5	221.6	221.5	222.1	222.3	222.8	223.3	224.2	225.5
40°	214.0	213.9	213.3	212.1	213.3	213.9	214.0	214.9	215.2	216.3	217.1
42.5°	206.1	205.4	205.2	204.7	205.2	205.4	206.1	206.6	206.8	208.1	209.7
45°	193.6	193.6	193.2	193.0	193.2	193.6	193.6	193.6	193.8	195.4	196.1
47.5°	181.4	181.8	182.5	182.4	182.5	181.8	181.4	181.1	181.2	181.9	182.9
50°	174.1	174.3	174.9	175.0	174.9	174.3	174.1	173.3	172.9	172.9	173.5
52.5°	166.0	167.1	167.9	167.7	167.9	167.1	166.0	165.3	164.6	163.7	164.5
55°	154.5	156.0	157.4	157.6	157.4	156.0	154.5	152.8	152.0	150.4	151.0
57.5°	143.4	145.3	146.7	147.2	146.7	145.3	143.4	141.2	138.6	137.8	136.7
60°	135.7	138.3	140.1	140.9	140.1	138.3	135.7	133.7	130.3	128.1	127.3
62.5°	128.4	131.3	133.0	133.2	133.0	131.3	128.4	125.3	121.9	119.3	117.8
65°	116.4	119.3	121.0	122.2	121.0	119.3	116.4	113.0	109.3	105.8	104.0
67.5°	103.5	106.5	108.2	109.2	108.2	106.5	103.5	99.3	95.8	92.0	89.9
70°	94.1	97.1	99.4	100.3	99.4	97.1	94.1	89.1	86.2	82.6	80.8
72.5°	84.9	87.6	89.5	90.4	89.5	87.6	84.9	80.2	76.7	73.2	70.8
75°	68.8	72.4	74.2	75.2	74.2	72.4	68.8	66.2	62.3	58.5	56.5
77.5°	53.0	56.3	57.4	57.9	57.4	56.3	53.0	50.0	47.0	44.3	42.4
80°	42.5	44.6	46.0	46.1	46.0	44.6	42.5	40.2	37.8	35.2	33.4
82.5°	32.7	34.4	34.8	35.3	34.8	34.4	32.7	30.7	28.6	26.6	25.1
85°	17.9	18.7	18.9	18.7	18.9	18.7	17.9	16.5	15.5	14.6	13.9
87.5°	9.6	9.6	9.7	10.2	9.7	9.6	9.6	9.2	9.2	8.7	8.3
90°	18.9	19.5	20.1	20.7	20.1	19.5	18.9	18.3	17.6	16.6	15.7
92.5°	18.4	18.7	19.0	19.3	19.0	18.7	18.4	18.2	17.6	16.6	15.7
95°	18.1	18.1	18.1	18.1	18.1	18.1	18.1	18.1	17.6	16.6	15.7
97.5°	18.1	18.1	18.1	18.1	18.1	18.1	18.1	18.1	20.8	26.2	31.5
100°	20.3	19.5	18.9	18.1	18.9	19.5	20.3	21.1	35.7	64.2	92.6
102.5°	147.1	134.1	121.1	108.1	121.1	134.1	147.1	160.1	169.3	174.7	180.0
105°	255.9	255.7	255.5	255.3	255.5	255.7	255.9	256.1	256.1	256.1	256.1
107.5°	323.6	323.0	322.4	321.8	322.4	323.0	323.6	324.2	324.4	324.4	324.3
110°	367.4	367.6	367.7	367.9	367.7	367.6	367.4	367.2	367.4	367.9	368.5



TEST NUMBER: P333142-935

CATALOG NUMBER: S125DIP-S375D1035U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	410.0	409.7	409.5	409.2	409.5	409.7	410.0	410.3	410.8	411.5	412.2
115°	474.6	473.4	472.3	471.1	472.3	473.4	474.6	475.7	476.6	477.4	478.2
117.5°	538.6	538.1	537.6	537.1	537.6	538.1	538.6	539.1	539.8	540.9	541.8
120°	580.6	579.6	578.7	577.7	578.7	579.6	580.6	581.5	582.2	582.6	583.0
122.5°	619.6	618.5	617.3	616.2	617.3	618.5	619.6	620.6	621.4	621.8	622.2
125°	676.6	676.0	675.5	674.9	675.5	676.0	676.6	677.2	677.8	678.6	679.3
127.5°	728.4	727.0	725.7	724.2	725.7	727.0	728.4	729.9	730.7	731.2	731.6
130°	762.8	761.9	761.0	759.9	761.0	761.9	762.8	763.8	764.6	765.1	765.7
132.5°	795.8	794.9	793.9	793.0	793.9	794.9	795.8	796.8	797.3	797.5	797.5
135°	841.6	840.5	839.3	838.2	839.3	840.5	841.6	842.7	843.5	844.0	844.3
137.5°	886.6	885.5	884.6	883.6	884.6	885.5	886.6	887.5	888.0	887.9	887.9
140°	913.9	912.7	911.5	910.4	911.5	912.7	913.9	915.0	915.3	915.0	914.6
142.5°	939.3	938.1	937.0	935.8	937.0	938.1	939.3	940.5	941.0	940.9	940.8
145°	976.6	975.4	974.3	973.2	974.3	975.4	976.6	977.8	978.2	978.0	977.8
147.5°	1008.1	1006.7	1005.3	1003.9	1005.3	1006.7	1008.1	1009.4	1010.0	1009.8	1009.5
150°	1028.5	1026.9	1025.4	1023.9	1025.4	1026.9	1028.5	1030.0	1030.5	1030.2	1029.8
152.5°	1046.5	1045.2	1043.8	1042.4	1043.8	1045.2	1046.5	1047.9	1048.4	1048.1	1047.7
155°	1071.4	1069.9	1068.4	1066.9	1068.4	1069.9	1071.4	1073.0	1073.5	1072.9	1072.3
157.5°	1091.9	1090.4	1088.8	1087.4	1088.8	1090.4	1091.9	1093.5	1093.9	1093.3	1092.7
160°	1105.0	1103.5	1101.9	1100.4	1101.9	1103.5	1105.0	1106.5	1106.9	1106.1	1105.4
162.5°	1117.1	1115.4	1113.8	1112.1	1113.8	1115.4	1117.1	1118.8	1119.1	1118.0	1117.0
165°	1132.5	1130.9	1129.5	1127.9	1129.5	1130.9	1132.5	1134.0	1134.2	1133.1	1131.9
167.5°	1144.1	1142.4	1140.7	1138.9	1140.7	1142.4	1144.1	1145.8	1146.0	1144.6	1143.2
170°	1150.2	1148.6	1146.9	1145.1	1146.9	1148.6	1150.2	1151.9	1152.1	1150.6	1149.0
172.5°	1154.3	1152.6	1150.9	1149.3	1150.9	1152.6	1154.3	1156.1	1156.2	1154.9	1153.5
175°	1159.7	1158.0	1156.2	1154.5	1156.2	1158.0	1159.7	1161.4	1161.5	1160.0	1158.5
177.5°	1161.3	1160.1	1158.9	1157.6	1158.9	1160.1	1161.3	1162.5	1162.6	1161.6	1160.5
180°	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7



TEST NUMBER: P333142-935

CATALOG NUMBER: S125DIP-S375D1035U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	448.2	450.1	452.5	454.3	457.4	458.8	460.6	462.0	464.6	467.0	469.8
5°	418.0	421.4	425.9	430.9	436.7	440.7	446.3	449.6	456.4	462.5	468.6
7.5°	390.6	394.8	401.2	407.6	415.2	422.0	429.0	436.7	445.3	455.6	464.0
10°	371.9	377.4	384.4	392.4	401.5	409.4	418.8	427.1	437.7	449.6	460.8
12.5°	356.9	361.6	369.4	377.0	386.8	396.6	406.2	417.2	429.6	442.8	456.8
15°	336.2	340.2	346.6	357.1	367.0	376.6	391.2	401.5	417.0	431.7	448.7
17.5°	318.6	323.6	328.9	337.9	348.3	360.2	373.2	386.2	401.1	419.7	438.8
20°	307.8	311.8	317.9	324.9	335.8	347.8	360.1	373.2	391.5	410.9	431.4
22.5°	296.0	300.3	307.3	314.9	324.1	335.5	349.1	363.5	382.6	401.6	423.9
25°	282.1	285.1	291.4	298.3	307.4	317.1	331.2	347.2	366.1	387.8	410.4
27.5°	269.1	271.6	277.4	283.4	291.6	303.2	315.8	331.9	349.7	371.7	396.8
30°	259.6	262.4	267.6	274.0	281.9	292.1	305.0	320.1	339.2	360.7	386.9
32.5°	251.5	254.0	257.9	264.2	272.1	281.9	293.9	309.3	328.4	350.2	376.0
35°	238.9	241.7	244.7	249.7	256.4	266.0	279.1	293.7	311.9	333.0	356.7
37.5°	226.4	229.5	232.1	236.6	242.7	251.2	262.5	277.7	294.2	314.5	337.3
40°	218.6	221.0	223.3	228.0	234.2	242.1	252.7	266.2	283.7	302.6	321.5
42.5°	210.9	213.1	214.9	219.1	224.8	232.4	242.5	255.7	271.9	289.6	306.3
45°	198.5	199.9	202.2	205.7	210.3	217.2	227.0	238.8	252.4	269.1	281.7
47.5°	185.3	187.4	189.2	192.3	196.1	202.9	212.3	222.3	234.8	247.2	256.0
50°	175.0	177.3	179.9	182.9	186.4	192.8	201.3	211.5	222.1	231.6	239.1
52.5°	165.5	167.6	170.3	173.1	177.5	182.9	190.2	199.2	209.7	216.5	222.7
55°	151.4	152.4	155.6	158.3	162.6	166.5	173.9	181.8	188.2	193.4	198.5
57.5°	137.0	138.3	140.2	142.7	146.8	151.4	156.6	163.7	167.4	170.0	174.1
60°	127.7	128.1	129.3	132.3	135.5	139.7	145.6	150.6	153.4	155.6	158.9
62.5°	117.5	117.6	119.6	121.8	124.2	128.7	133.5	137.6	139.8	140.9	144.1
65°	103.2	102.9	104.0	105.8	108.7	111.6	115.8	119.3	119.2	120.4	122.3
67.5°	88.7	88.3	88.3	90.0	92.2	94.9	97.7	99.9	99.9	101.4	102.5
70°	78.8	77.6	78.4	79.8	80.8	83.0	86.2	87.0	87.1	87.9	88.9
72.5°	68.6	68.2	68.8	69.4	70.1	71.8	74.6	75.0	75.1	75.5	77.1
75°	54.5	54.2	53.7	54.3	55.1	56.3	57.3	58.1	57.9	58.1	59.3
77.5°	40.9	39.8	39.5	39.9	40.0	40.8	41.8	41.8	41.9	41.9	43.2
80°	32.5	30.8	30.7	30.7	30.8	31.3	31.6	32.0	31.4	32.0	32.5
82.5°	23.8	22.9	22.8	22.6	22.7	22.8	23.1	23.2	23.2	23.4	23.7
85°	13.2	12.7	12.1	12.6	12.3	11.7	12.1	11.5	11.4	11.5	11.7
87.5°	7.4	7.4	6.8	6.5	6.1	5.9	5.3	4.9	4.5	4.3	4.5
90°	14.7	13.8	12.4	11.1	9.7	8.4	7.0	5.4	3.9	2.4	0.9
92.5°	14.7	13.8	12.6	11.4	10.2	9.0	9.0	10.0	11.1	12.1	13.3
95°	14.7	13.8	21.0	28.2	35.6	42.8	46.8	47.3	47.9	48.4	49.0
97.5°	36.9	42.3	56.7	71.0	85.4	99.8	106.4	105.4	104.4	103.3	102.3
100°	121.1	149.6	148.8	148.1	147.3	146.5	145.9	145.3	144.7	144.1	143.5
102.5°	185.5	190.9	190.4	189.9	189.5	189.0	188.4	187.7	187.0	186.2	185.5
105°	256.1	256.1	256.1	256.1	256.1	256.1	255.8	255.0	254.3	253.5	252.7
107.5°	324.3	324.3	323.9	323.5	323.1	322.7	322.5	322.5	322.5	322.5	322.5
110°	369.1	369.6	369.3	368.9	368.5	368.2	367.9	367.9	367.9	367.9	367.9



TEST NUMBER: P333142-935

CATALOG NUMBER: S125DIP-S375D1035U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	412.9	413.7	413.5	413.2	413.0	412.8	412.4	412.0	411.5	411.0	410.6
115°	479.0	479.7	479.5	479.3	479.1	479.0	478.4	477.4	476.5	475.5	474.6
117.5°	542.9	543.8	543.1	542.3	541.7	541.0	540.6	540.6	540.6	540.7	540.7
120°	583.3	583.8	583.2	582.6	582.0	581.4	581.3	581.4	581.6	581.8	582.0
122.5°	622.5	622.9	622.7	622.4	622.2	621.8	621.4	620.6	619.9	619.1	618.5
125°	680.1	680.9	680.9	680.9	680.9	680.9	680.2	678.9	677.5	676.1	674.9
127.5°	732.0	732.5	732.5	732.7	732.8	732.9	732.5	731.5	730.6	729.6	728.7
130°	766.3	766.8	766.6	766.5	766.3	766.0	765.5	764.6	763.6	762.7	761.6
132.5°	797.6	797.8	798.2	798.7	799.0	799.4	799.1	798.0	796.9	795.8	794.7
135°	844.6	845.1	845.4	845.8	846.2	846.6	846.2	845.1	844.0	842.7	841.6
137.5°	887.8	887.7	888.0	888.4	888.7	889.1	888.7	887.8	886.7	885.8	884.8
140°	914.2	913.9	914.0	914.2	914.4	914.6	914.5	914.1	913.8	913.3	913.0
142.5°	940.7	940.6	940.4	940.1	939.9	939.6	939.4	939.1	938.9	938.7	938.4
145°	977.7	977.5	977.5	977.5	977.5	977.5	977.2	976.9	976.5	976.1	975.8
147.5°	1009.4	1009.1	1008.8	1008.7	1008.4	1008.1	1008.1	1008.1	1008.2	1008.3	1008.4
150°	1029.4	1029.1	1028.6	1028.3	1027.9	1027.5	1027.5	1027.9	1028.3	1028.6	1029.1
152.5°	1047.3	1046.9	1046.5	1046.1	1045.8	1045.4	1045.6	1046.5	1047.3	1048.2	1049.0
155°	1071.8	1071.2	1070.7	1070.4	1070.1	1069.6	1070.1	1071.2	1072.3	1073.5	1074.6
157.5°	1092.1	1091.5	1091.4	1091.4	1091.3	1091.3	1091.7	1092.4	1093.0	1093.6	1094.3
160°	1104.6	1103.8	1103.6	1103.5	1103.3	1103.0	1103.5	1104.7	1105.9	1107.0	1108.1
162.5°	1115.9	1114.8	1114.7	1114.5	1114.2	1114.0	1114.6	1115.7	1116.8	1118.0	1119.1
165°	1130.8	1129.6	1129.5	1129.2	1129.0	1128.9	1129.4	1130.5	1131.6	1132.7	1133.9
167.5°	1141.9	1140.5	1140.2	1140.1	1139.9	1139.7	1140.2	1141.3	1142.5	1143.8	1145.0
170°	1147.5	1146.0	1145.7	1145.6	1145.4	1145.2	1145.7	1147.1	1148.4	1149.8	1151.1
172.5°	1152.1	1150.7	1150.4	1150.0	1149.7	1149.4	1149.9	1151.2	1152.5	1153.9	1155.2
175°	1156.9	1155.4	1155.2	1155.0	1154.9	1154.7	1155.1	1156.2	1157.4	1158.6	1159.7
177.5°	1159.4	1158.3	1158.2	1158.0	1157.9	1157.7	1158.1	1159.0	1159.9	1160.9	1161.7
180°	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7



TEST NUMBER: P333142-935

CATALOG NUMBER: S125DIP-S375D1035U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	471.3	473.5	474.9	477.6	479.8	481.1	482.2	483.2	484.3	485.3	488.0
5°	474.3	479.5	483.9	490.6	496.8	501.5	506.7	511.3	515.1	520.5	524.6
7.5°	472.9	482.2	491.8	502.3	513.0	522.9	532.1	540.6	548.4	557.8	566.0
10°	471.7	484.2	496.5	510.7	525.2	537.5	549.1	560.9	569.4	581.3	591.5
12.5°	470.8	485.5	500.4	517.4	533.3	550.8	566.1	574.7	587.7	597.3	609.3
15°	466.7	486.2	506.7	525.8	548.5	564.6	578.2	594.9	607.0	619.1	632.2
17.5°	459.5	481.6	504.5	529.6	551.3	568.6	586.1	602.2	616.6	632.9	649.3
20°	456.2	478.3	504.5	530.2	551.5	569.6	587.5	605.2	621.1	642.0	660.9
22.5°	449.2	475.9	500.1	525.1	547.0	566.7	587.0	607.1	628.3	651.9	675.5
25°	436.7	463.7	489.4	514.1	536.1	560.9	582.6	609.4	636.5	667.7	697.2
27.5°	423.7	449.6	473.1	497.0	522.7	550.7	578.8	609.2	644.7	684.2	725.7
30°	413.2	437.7	460.5	485.0	511.9	543.3	574.2	610.4	651.3	695.7	745.1
32.5°	401.0	423.5	445.7	471.7	500.9	534.1	570.1	609.8	659.0	709.4	760.2
35°	380.0	398.9	421.8	449.4	482.4	520.5	562.1	609.0	665.5	723.4	766.1
37.5°	355.2	372.7	396.8	427.1	461.8	502.6	551.9	607.6	667.6	713.8	727.5
40°	338.4	354.7	379.8	411.2	446.6	489.8	543.9	602.8	660.9	690.3	679.0
42.5°	320.6	337.7	362.1	393.2	431.4	478.4	533.9	592.8	641.5	652.6	613.5
45°	292.5	310.1	334.2	365.7	406.7	457.6	515.5	569.0	597.0	577.0	516.3
47.5°	266.3	282.9	305.2	337.7	380.0	432.7	488.4	531.1	533.3	485.3	420.5
50°	248.5	263.8	286.3	318.7	360.7	414.1	464.3	498.0	482.8	428.5	366.3
52.5°	231.0	246.0	268.1	300.2	341.7	390.6	437.5	461.1	432.6	376.8	323.6
55°	205.7	218.9	240.6	270.2	309.5	354.9	394.7	402.9	365.8	311.0	267.8
57.5°	181.1	193.3	213.0	240.3	276.4	316.5	347.7	345.9	306.8	259.7	225.4
60°	164.4	176.2	193.8	220.4	253.3	287.9	314.5	308.2	269.4	228.8	199.9
62.5°	149.4	160.1	176.6	199.9	229.9	261.9	283.8	274.4	236.4	201.0	178.1
65°	127.3	136.3	150.4	170.3	195.2	221.6	238.6	226.4	194.0	166.3	148.0
67.5°	106.2	113.5	125.3	141.2	162.4	183.7	193.9	181.8	155.8	135.6	122.0
70°	92.9	99.3	108.4	122.5	141.0	158.9	166.7	155.8	133.5	116.1	106.4
72.5°	79.6	84.8	92.8	105.6	120.4	135.9	142.7	132.2	113.9	99.3	90.2
75°	61.5	65.1	70.6	79.4	91.1	103.5	107.2	98.1	86.4	75.4	69.4
77.5°	44.0	47.0	51.2	56.7	65.1	72.9	76.2	70.9	61.9	54.9	50.0
80°	33.8	35.4	39.0	43.6	50.1	55.1	57.3	53.9	47.5	42.4	38.6
82.5°	24.1	25.7	27.8	31.6	35.8	39.2	41.5	39.3	34.7	30.6	28.4
85°	11.7	12.7	13.9	15.5	18.7	20.7	20.5	19.1	17.3	15.8	14.6
87.5°	4.6	5.1	5.9	7.0	7.7	8.6	9.2	9.1	8.8	8.5	8.3
90°	2.4	3.9	5.4	7.0	8.4	9.7	11.1	12.4	13.8	14.7	15.7
92.5°	12.1	11.1	10.0	9.0	9.0	10.2	11.4	12.6	13.8	14.7	15.7
95°	48.4	47.9	47.3	46.8	42.8	35.6	28.2	21.0	13.8	14.7	15.7
97.5°	103.3	104.4	105.4	106.4	99.8	85.4	71.0	56.7	42.3	36.9	31.5
100°	144.1	144.7	145.3	145.9	146.5	147.3	148.1	148.8	149.6	121.1	92.6
102.5°	186.2	187.0	187.7	188.4	189.0	189.5	189.9	190.4	190.9	185.5	180.0
105°	253.5	254.3	255.0	255.8	256.1	256.1	256.1	256.1	256.1	256.1	256.1
107.5°	322.5	322.5	322.5	322.5	322.7	323.1	323.5	323.9	324.3	324.3	324.3
110°	367.9	367.9	367.9	367.9	368.2	368.5	368.9	369.3	369.6	369.1	368.5



TEST NUMBER: P333142-935

CATALOG NUMBER: S125DIP-S375D1035U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	411.0	411.5	412.0	412.4	412.8	413.0	413.2	413.5	413.7	412.9	412.2
115°	475.5	476.5	477.4	478.4	479.0	479.1	479.3	479.5	479.7	479.0	478.2
117.5°	540.7	540.6	540.6	540.6	541.0	541.7	542.3	543.1	543.8	542.9	541.8
120°	581.8	581.6	581.4	581.3	581.4	582.0	582.6	583.2	583.8	583.3	583.0
122.5°	619.1	619.9	620.6	621.4	621.8	622.2	622.4	622.7	622.9	622.5	622.2
125°	676.1	677.5	678.9	680.2	680.9	680.9	680.9	680.9	680.9	680.1	679.3
127.5°	729.6	730.6	731.5	732.5	732.9	732.8	732.7	732.5	732.5	732.0	731.6
130°	762.7	763.6	764.6	765.5	766.0	766.3	766.5	766.6	766.8	766.3	765.7
132.5°	795.8	796.9	798.0	799.1	799.4	799.0	798.7	798.2	797.8	797.6	797.5
135°	842.7	844.0	845.1	846.2	846.6	846.2	845.8	845.4	845.1	844.6	844.3
137.5°	885.8	886.7	887.8	888.7	889.1	888.7	888.4	888.0	887.7	887.8	887.9
140°	913.3	913.8	914.1	914.5	914.6	914.4	914.2	914.0	913.9	914.2	914.6
142.5°	938.7	938.9	939.1	939.4	939.6	939.9	940.1	940.4	940.6	940.7	940.8
145°	976.1	976.5	976.9	977.2	977.5	977.5	977.5	977.5	977.5	977.7	977.8
147.5°	1008.3	1008.2	1008.1	1008.1	1008.1	1008.4	1008.7	1008.8	1009.1	1009.4	1009.5
150°	1028.6	1028.3	1027.9	1027.5	1027.5	1027.9	1028.3	1028.6	1029.1	1029.4	1029.8
152.5°	1048.2	1047.3	1046.5	1045.6	1045.4	1045.8	1046.1	1046.5	1046.9	1047.3	1047.7
155°	1073.5	1072.3	1071.2	1070.1	1069.6	1070.1	1070.4	1070.7	1071.2	1071.8	1072.3
157.5°	1093.6	1093.0	1092.4	1091.7	1091.3	1091.3	1091.4	1091.4	1091.5	1092.1	1092.7
160°	1107.0	1105.9	1104.7	1103.5	1103.0	1103.3	1103.5	1103.6	1103.8	1104.6	1105.4
162.5°	1118.0	1116.8	1115.7	1114.6	1114.0	1114.2	1114.5	1114.7	1114.8	1115.9	1117.0
165°	1132.7	1131.6	1130.5	1129.4	1128.9	1129.0	1129.2	1129.5	1129.6	1130.8	1131.9
167.5°	1143.8	1142.5	1141.3	1140.2	1139.7	1139.9	1140.1	1140.2	1140.5	1141.9	1143.2
170°	1149.8	1148.4	1147.1	1145.7	1145.2	1145.4	1145.6	1145.7	1146.0	1147.5	1149.0
172.5°	1153.9	1152.5	1151.2	1149.9	1149.4	1149.7	1150.0	1150.4	1150.7	1152.1	1153.5
175°	1158.6	1157.4	1156.2	1155.1	1154.7	1154.9	1155.0	1155.2	1155.4	1156.9	1158.5
177.5°	1160.9	1159.9	1159.0	1158.1	1157.7	1157.9	1158.0	1158.2	1158.3	1159.4	1160.5
180°	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7



TEST NUMBER: P333142-935

CATALOG NUMBER: S125DIP-S375D1035U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	490.3	491.5	494.2	493.3	494.5	495.2	495.8
5°	529.8	536.1	539.0	538.6	542.8	541.7	540.7
7.5°	574.5	581.2	585.0	589.6	592.3	592.5	594.9
10°	599.9	608.6	612.2	617.2	620.4	622.2	621.9
12.5°	619.2	626.1	634.1	636.5	640.8	643.2	642.3
15°	642.7	653.6	661.9	666.1	671.5	673.0	675.2
17.5°	663.5	678.1	687.9	700.9	705.8	708.8	707.0
20°	679.2	698.5	708.3	723.8	732.4	736.9	735.3
22.5°	697.8	718.8	736.8	750.2	763.2	769.4	770.7
25°	729.8	758.4	784.9	802.5	818.6	822.4	830.8
27.5°	765.4	799.2	827.5	846.1	857.3	861.5	864.2
30°	787.8	821.5	842.7	854.7	858.2	857.9	857.5
32.5°	798.8	819.8	824.0	820.6	812.4	805.5	798.2
35°	783.3	767.6	744.1	713.9	691.6	669.1	666.8
37.5°	704.5	654.2	615.1	571.4	546.3	530.7	520.0
40°	630.3	573.2	525.8	489.0	463.4	453.2	443.2
42.5°	549.7	495.2	453.2	422.5	403.2	391.9	384.1
45°	446.6	398.5	365.7	343.4	328.0	319.3	314.4
47.5°	366.0	330.4	302.5	286.4	275.9	269.1	269.1
50°	322.7	288.7	270.2	257.4	248.3	242.9	243.9
52.5°	284.3	258.9	243.1	232.5	225.7	222.4	222.2
55°	237.7	219.5	209.1	201.3	196.7	193.0	193.8
57.5°	203.4	188.0	181.0	174.5	171.3	169.9	167.6
60°	182.0	170.1	164.1	158.9	155.8	154.5	152.4
62.5°	163.1	153.7	147.9	143.7	140.9	140.4	138.7
65°	137.1	129.9	124.8	122.8	119.8	119.0	119.0
67.5°	113.0	107.9	103.8	102.0	100.7	100.9	100.0
70°	97.9	93.7	91.1	89.1	88.2	88.3	87.6
72.5°	85.7	80.9	78.7	77.5	76.2	76.7	76.4
75°	64.8	62.5	61.3	60.1	59.3	58.9	58.5
77.5°	47.6	45.5	44.6	43.9	44.1	43.0	43.8
80°	36.8	35.0	34.4	33.4	33.2	33.2	33.1
82.5°	26.9	25.9	25.5	24.7	24.3	24.6	24.1
85°	13.9	13.2	12.9	12.9	12.6	12.1	13.2
87.5°	8.4	8.0	8.1	8.1	8.2	8.2	7.9
90°	16.6	17.6	18.3	18.9	19.5	20.1	20.7
92.5°	16.6	17.6	18.2	18.4	18.7	19.0	19.3
95°	16.6	17.6	18.1	18.1	18.1	18.1	18.1
97.5°	26.2	20.8	18.1	18.1	18.1	18.1	18.1
100°	64.2	35.7	21.1	20.3	19.5	18.9	18.1
102.5°	174.7	169.3	160.1	147.1	134.1	121.1	108.1
105°	256.1	256.1	256.1	255.9	255.7	255.5	255.3
107.5°	324.4	324.4	324.2	323.6	323.0	322.4	321.8
110°	367.9	367.4	367.2	367.4	367.6	367.7	367.9



TEST NUMBER: P333142-935

CATALOG NUMBER: S125DIP-S375D1035U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	411.5	410.8	410.3	410.0	409.7	409.5	409.2
115°	477.4	476.6	475.7	474.6	473.4	472.3	471.1
117.5°	540.9	539.8	539.1	538.6	538.1	537.6	537.1
120°	582.6	582.2	581.5	580.6	579.6	578.7	577.7
122.5°	621.8	621.4	620.6	619.6	618.5	617.3	616.2
125°	678.6	677.8	677.2	676.6	676.0	675.5	674.9
127.5°	731.2	730.7	729.9	728.4	727.0	725.7	724.2
130°	765.1	764.6	763.8	762.8	761.9	761.0	759.9
132.5°	797.5	797.3	796.8	795.8	794.9	793.9	793.0
135°	844.0	843.5	842.7	841.6	840.5	839.3	838.2
137.5°	887.9	888.0	887.5	886.6	885.5	884.6	883.6
140°	915.0	915.3	915.0	913.9	912.7	911.5	910.4
142.5°	940.9	941.0	940.5	939.3	938.1	937.0	935.8
145°	978.0	978.2	977.8	976.6	975.4	974.3	973.2
147.5°	1009.8	1010.0	1009.4	1008.1	1006.7	1005.3	1003.9
150°	1030.2	1030.5	1030.0	1028.5	1026.9	1025.4	1023.9
152.5°	1048.1	1048.4	1047.9	1046.5	1045.2	1043.8	1042.4
155°	1072.9	1073.5	1073.0	1071.4	1069.9	1068.4	1066.9
157.5°	1093.3	1093.9	1093.5	1091.9	1090.4	1088.8	1087.4
160°	1106.1	1106.9	1106.5	1105.0	1103.5	1101.9	1100.4
162.5°	1118.0	1119.1	1118.8	1117.1	1115.4	1113.8	1112.1
165°	1133.1	1134.2	1134.0	1132.5	1130.9	1129.5	1127.9
167.5°	1144.6	1146.0	1145.8	1144.1	1142.4	1140.7	1138.9
170°	1150.6	1152.1	1151.9	1150.2	1148.6	1146.9	1145.1
172.5°	1154.9	1156.2	1156.1	1154.3	1152.6	1150.9	1149.3
175°	1160.0	1161.5	1161.4	1159.7	1158.0	1156.2	1154.5
177.5°	1161.6	1162.6	1162.5	1161.3	1160.1	1158.9	1157.6
180°	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7	1159.7

(END OF REPORT)