

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333275-830

Luminaire Tested: **S125DIP-S1090D810U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333275-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1090D810U830-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6829.9 lumens
Efficiency: N/A
Efficacy: 125.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333275-830

CATALOG NUMBER: S125DIP-S1090D810U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333275-830

CATALOG NUMBER: S125DIP-S1090D810U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	61
1	100	96	92	88	94	90	86	83	79	76	74	68	66	65	59	57	56	51
2	91	84	77	72	85	78	73	68	69	65	61	60	57	54	52	49	47	43
3	83	74	66	60	78	69	62	57	61	55	51	53	49	46	46	43	40	36
4	76	65	57	51	71	61	54	48	54	48	44	47	43	39	41	37	35	31
5	70	58	50	44	65	55	47	42	48	42	38	42	38	34	37	33	30	27
6	65	52	44	38	60	49	42	36	44	37	33	38	33	30	33	30	27	24
7	60	47	39	33	56	45	37	32	40	33	29	35	30	26	30	27	24	21
8	55	43	35	30	52	41	33	28	36	30	26	32	27	23	28	24	21	19
9	52	39	32	26	48	37	30	25	33	27	23	29	25	21	26	22	19	17
10	48	36	29	24	45	34	27	23	31	25	21	27	22	19	24	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10388	10388	10388
5°	10410	10311	10377
10°	10347	10238	10297
15°	10235	10116	10158
20°	10074	9943	9961
25°	9902	9738	9729
30°	9688	9517	9470
35°	9460	9280	9150
40°	9226	9022	8893
45°	8972	8786	8611
50°	8694	8501	8246
55°	8425	8180	7952
60°	8103	7856	7576
65°	7719	7467	7213
70°	7353	7017	6775
75°	6697	6478	6253
80°	5962	5869	5724
85°	5180	5283	4994



TEST NUMBER: P333275-830

CATALOG NUMBER: S125DIP-S1090D810U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.6	2.2
10°-20°	428.4	6.3
20°-30°	632.5	9.3
30°-40°	738.0	10.8
40°-50°	741.2	10.9
50°-60°	650.7	9.5
60°-70°	484.8	7.1
70°-80°	277.2	4.1
80°-90°	82.7	1.2
90°-100°	63.4	0.9
100°-110°	187.3	2.7
110°-120°	317.3	4.6
120°-130°	417.5	6.1
130°-140°	467.9	6.9
140°-150°	458.6	6.7
150°-160°	385.1	5.6
160°-170°	256.0	3.7
170°-180°	89.6	1.3
0°-30°	1212.5	17.8
0°-40°	1950.5	28.6
0°-60°	3342.4	48.9
0°-90°	4187.2	61.3
90°-120°	568.0	8.3
90°-150°	1912.0	28.0
90°-180°	2643.0	38.7
0°-180°	6829.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1608	1608	1608	1608	1608	
5°	1606	1603	1590	1601	1601	152
15°	1531	1526	1513	1519	1519	431
25°	1390	1383	1367	1369	1365	639
35°	1200	1194	1177	1170	1160	750
45°	982	977	962	947	943	757
55°	748	744	726	715	706	668
65°	505	502	489	477	472	501
75°	268	266	260	256	251	286
85°	70	71	71	70	67	78
90°	1	7	12	15	18	6
95°	48	50	57	62	63	51
105°	168	172	176	180	183	180
115°	318	320	322	321	321	314
125°	464	468	469	467	467	415
135°	603	607	608	608	605	465
145°	730	733	736	735	733	456
155°	836	836	836	839	836	385
165°	909	907	908	911	906	256
175°	945	942	942	946	941	90
180°	947	947	947	947	947	



TEST NUMBER: P333275-830

CATALOG NUMBER: S125DIP-S1090D810U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4
2.5°	1612.4	1611.7	1611.0	1610.3	1609.7	1608.2	1605.9	1603.6	1601.4	1599.1	1601.4
5°	1605.8	1605.2	1604.7	1604.1	1603.5	1601.9	1599.0	1596.2	1593.4	1590.5	1593.1
7.5°	1591.0	1590.4	1589.9	1589.3	1588.7	1586.9	1583.8	1580.6	1577.5	1574.4	1577.0
10°	1577.8	1577.3	1576.7	1576.1	1575.6	1573.7	1570.6	1567.4	1564.3	1561.2	1563.5
12.5°	1561.5	1560.5	1559.4	1558.4	1557.5	1555.5	1552.6	1549.7	1546.8	1543.9	1545.8
15°	1530.7	1529.8	1529.0	1528.1	1527.3	1525.3	1522.2	1519.1	1516.0	1512.9	1514.3
17.5°	1495.3	1494.1	1492.8	1491.6	1490.3	1488.1	1484.9	1481.7	1478.5	1475.2	1477.0
20°	1465.8	1465.3	1464.7	1464.1	1463.6	1461.4	1457.7	1454.1	1450.4	1446.7	1448.7
22.5°	1436.2	1435.3	1434.3	1433.2	1432.2	1429.9	1426.5	1423.1	1419.7	1416.2	1417.5
25°	1389.5	1388.1	1386.7	1385.3	1383.8	1381.3	1377.6	1373.9	1370.3	1366.6	1367.2
27.5°	1334.7	1333.9	1333.0	1332.2	1331.3	1329.1	1325.2	1321.4	1317.7	1313.9	1314.0
30°	1299.1	1298.3	1297.4	1296.6	1295.7	1293.2	1288.9	1284.7	1280.4	1276.2	1275.6
32.5°	1260.5	1259.1	1257.8	1256.5	1255.3	1252.7	1248.9	1245.1	1241.3	1237.6	1236.5
35°	1199.9	1198.7	1197.6	1196.5	1195.3	1192.8	1188.8	1184.9	1180.9	1177.0	1175.5
37.5°	1137.0	1135.6	1134.2	1132.7	1131.3	1128.8	1125.0	1121.3	1117.6	1113.9	1111.7
40°	1094.3	1092.9	1091.5	1090.1	1088.6	1085.9	1081.9	1078.0	1074.0	1070.1	1067.5
42.5°	1048.5	1047.3	1046.1	1044.9	1043.7	1041.1	1037.2	1033.2	1029.3	1025.3	1022.9
45°	982.3	981.2	980.1	978.9	977.8	975.5	972.1	968.7	965.4	962.0	958.6
47.5°	911.1	911.1	911.2	911.3	911.3	909.3	905.2	901.1	897.0	893.0	889.5
50°	865.3	864.4	863.6	862.7	861.9	859.7	856.3	852.9	849.5	846.1	842.4
52.5°	818.4	817.7	817.2	816.5	816.0	813.8	810.2	806.5	803.0	799.3	796.1
55°	748.2	747.3	746.5	745.6	744.8	742.3	738.4	734.4	730.5	726.5	724.0
57.5°	674.1	673.6	673.3	672.8	672.3	670.4	667.0	663.7	660.4	657.0	653.7
60°	627.3	626.1	625.0	623.9	622.7	620.7	617.6	614.4	611.3	608.2	605.4
62.5°	578.4	577.5	576.6	575.7	574.9	573.1	570.3	567.7	565.1	562.4	559.3
65°	505.1	504.5	504.0	503.4	502.8	501.1	497.9	494.8	491.7	488.6	486.1
67.5°	434.1	432.9	431.8	430.6	429.4	427.6	425.3	423.0	420.7	418.4	416.2
70°	389.4	388.0	386.5	385.1	383.7	381.7	379.2	376.6	374.1	371.6	369.9
72.5°	340.5	339.5	338.6	337.6	336.7	335.4	333.8	332.1	330.5	328.8	326.9
75°	268.4	267.9	267.3	266.7	266.2	265.2	263.8	262.4	261.0	259.6	258.7
77.5°	202.1	201.8	201.6	201.4	201.1	200.7	199.8	199.1	198.3	197.5	197.0
80°	160.3	160.3	160.3	160.3	160.3	160.0	159.5	158.9	158.3	157.8	157.5
82.5°	123.7	123.2	122.8	122.3	121.9	121.6	121.5	121.4	121.2	121.1	120.6
85°	69.9	70.2	70.5	70.8	71.1	71.3	71.3	71.3	71.3	71.3	71.0
87.5°	27.6	27.9	28.2	28.4	28.7	28.8	28.8	28.8	28.8	28.8	29.0
90°	0.8	2.1	3.4	4.7	5.9	7.2	8.4	9.5	10.7	11.8	12.6
92.5°	17.8	18.8	19.7	20.5	21.5	22.6	24.0	25.4	26.9	28.3	29.4
95°	47.9	48.3	48.5	48.9	49.2	50.2	51.8	53.4	55.1	56.7	57.9
97.5°	79.6	79.7	79.8	80.0	80.1	81.3	83.6	85.9	88.1	90.4	91.4
100°	103.2	103.2	103.2	103.2	103.2	104.2	106.4	108.5	110.7	112.7	114.2
102.5°	128.6	129.2	129.9	130.5	131.2	132.1	133.1	134.2	135.3	136.4	138.0
105°	168.1	168.9	169.7	170.5	171.4	172.2	173.2	174.2	175.1	176.2	177.1
107.5°	211.7	212.4	213.3	214.1	215.0	215.7	216.5	217.3	218.0	218.8	219.2
110°	241.8	242.6	243.4	244.2	245.1	245.7	246.2	246.7	247.1	247.6	248.2



TEST NUMBER: P333275-830

CATALOG NUMBER: S125DIP-S1090D810U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	272.4	272.9	273.2	273.7	274.1	274.7	275.2	275.9	276.5	277.1	277.4
115°	317.6	318.3	319.0	319.6	320.3	320.7	321.1	321.4	321.8	322.1	321.9
117.5°	363.1	363.4	363.6	363.9	364.2	364.6	364.9	365.1	365.4	365.7	365.8
120°	391.3	392.2	393.0	393.8	394.6	395.1	395.3	395.5	395.6	395.8	395.8
122.5°	422.0	422.4	422.6	422.9	423.2	423.6	424.0	424.4	424.8	425.3	425.1
125°	463.5	464.6	465.5	466.6	467.5	468.1	468.3	468.4	468.5	468.7	468.4
127.5°	507.8	508.4	508.9	509.4	510.0	510.4	510.6	510.8	511.0	511.2	511.0
130°	534.3	535.2	536.0	536.8	537.6	538.2	538.5	538.9	539.1	539.5	539.3
132.5°	560.9	562.2	563.5	564.9	566.3	566.8	566.8	566.8	566.7	566.7	566.5
135°	602.9	603.9	604.8	605.9	606.8	607.4	607.6	607.8	607.8	608.0	608.0
137.5°	642.4	643.4	644.3	645.3	646.2	646.9	647.2	647.5	647.9	648.3	648.5
140°	667.8	668.5	669.4	670.2	671.0	671.7	672.1	672.7	673.2	673.6	674.0
142.5°	693.1	693.8	694.5	695.1	695.9	696.5	697.1	697.8	698.3	699.0	699.2
145°	730.4	731.0	731.7	732.4	733.0	733.6	734.1	734.5	735.1	735.6	735.6
147.5°	764.9	765.3	765.6	766.0	766.3	766.7	767.1	767.5	767.9	768.3	768.6
150°	787.9	787.7	787.6	787.4	787.2	787.5	788.2	788.8	789.5	790.1	790.1
152.5°	806.7	807.0	807.2	807.5	807.7	807.9	808.1	808.4	808.7	809.0	809.4
155°	835.8	835.8	835.8	835.8	835.8	835.8	836.0	836.2	836.3	836.5	837.2
157.5°	861.8	861.4	861.0	860.6	860.3	860.2	860.4	860.5	860.6	860.8	861.5
160°	877.0	876.6	876.1	875.6	875.1	875.0	875.1	875.2	875.4	875.6	876.3
162.5°	890.6	890.2	889.9	889.6	889.2	889.0	889.0	889.1	889.1	889.2	889.9
165°	908.8	908.4	908.1	907.8	907.5	907.4	907.5	907.7	907.9	908.0	908.7
167.5°	924.1	923.4	922.7	922.1	921.4	921.1	921.1	921.1	921.1	921.1	922.1
170°	932.4	931.7	931.0	930.4	929.7	929.3	929.3	929.3	929.3	929.3	930.4
172.5°	938.2	937.5	936.9	936.2	935.6	935.3	935.3	935.3	935.3	935.3	936.2
175°	944.9	944.2	943.6	942.9	942.3	941.9	941.9	941.9	941.9	941.9	942.9
177.5°	948.3	947.7	947.3	946.7	946.1	945.8	945.7	945.6	945.5	945.3	946.1
180°	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1



TEST NUMBER: P333275-830

CATALOG NUMBER: S125DIP-S1090D810U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4
2.5°	1603.6	1605.9	1608.2	1609.2	1609.0	1608.7	1608.5	1608.4
5°	1595.6	1598.2	1600.7	1601.9	1601.6	1601.3	1601.0	1600.7
7.5°	1579.4	1582.0	1584.4	1585.5	1585.3	1585.0	1584.7	1584.4
10°	1565.8	1568.0	1570.3	1571.3	1571.0	1570.7	1570.5	1570.2
12.5°	1547.6	1549.4	1551.1	1552.1	1552.0	1551.9	1551.9	1551.8
15°	1515.7	1517.1	1518.5	1519.3	1519.3	1519.3	1519.3	1519.3
17.5°	1478.8	1480.5	1482.2	1482.4	1481.0	1479.6	1478.2	1476.8
20°	1450.7	1452.6	1454.6	1454.9	1453.5	1452.1	1450.7	1449.3
22.5°	1418.8	1420.1	1421.4	1421.5	1420.6	1419.7	1418.7	1417.7
25°	1367.7	1368.3	1368.9	1368.7	1367.8	1367.0	1366.1	1365.3
27.5°	1314.1	1314.2	1314.4	1314.0	1313.2	1312.3	1311.5	1310.6
30°	1275.1	1274.5	1273.9	1273.3	1272.4	1271.6	1270.7	1269.9
32.5°	1235.5	1234.4	1233.5	1232.2	1230.7	1229.2	1227.6	1226.1
35°	1174.1	1172.7	1171.3	1169.5	1167.2	1165.0	1162.7	1160.5
37.5°	1109.7	1107.6	1105.5	1103.8	1102.5	1101.2	1099.9	1098.6
40°	1065.0	1062.4	1059.9	1058.2	1057.3	1056.5	1055.6	1054.8
42.5°	1020.7	1018.3	1016.1	1014.2	1013.0	1011.6	1010.3	1009.0
45°	955.2	951.8	948.4	946.2	945.4	944.5	943.7	942.8
47.5°	886.1	882.6	879.2	876.5	874.5	872.5	870.5	868.6
50°	838.8	835.1	831.4	828.6	826.6	824.6	822.7	820.7
52.5°	792.9	789.7	786.5	783.7	781.5	779.3	777.1	774.9
55°	721.4	718.9	716.3	714.1	712.1	710.1	708.1	706.2
57.5°	650.5	647.2	643.9	641.8	640.7	639.6	638.6	637.4
60°	602.6	599.7	596.9	594.5	592.5	590.5	588.5	586.5
62.5°	556.3	553.3	550.2	547.9	546.4	544.9	543.3	541.8
65°	483.5	481.0	478.4	476.5	475.4	474.3	473.2	472.0
67.5°	414.1	411.9	409.7	408.3	407.6	407.0	406.3	405.7
70°	368.2	366.5	364.8	363.4	362.2	361.1	360.0	358.8
72.5°	325.0	323.0	321.1	319.6	318.5	317.4	316.2	315.1
75°	257.9	257.0	256.2	255.1	254.0	252.9	251.8	250.6
77.5°	196.4	196.0	195.5	194.8	194.0	193.2	192.4	191.6
80°	157.2	156.9	156.7	156.2	155.6	155.0	154.5	153.9
82.5°	120.1	119.6	119.1	118.8	118.7	118.6	118.5	118.3
85°	70.7	70.4	70.1	69.7	69.1	68.5	68.0	67.4
87.5°	29.1	29.3	29.5	29.4	29.0	28.7	28.3	28.0
90°	13.4	14.2	15.1	15.7	16.2	16.7	17.2	17.7
92.5°	30.4	31.6	32.6	33.4	33.7	34.0	34.4	34.8
95°	59.0	60.2	61.4	62.1	62.4	62.8	63.1	63.3
97.5°	92.6	93.6	94.7	95.3	95.5	95.7	96.0	96.1
100°	115.7	117.2	118.7	119.6	119.9	120.2	120.6	120.8
102.5°	139.6	141.2	142.8	143.8	144.3	144.7	145.2	145.6
105°	178.1	179.1	180.1	180.8	181.3	181.8	182.3	182.8
107.5°	219.7	220.2	220.7	220.9	220.9	220.8	220.8	220.8
110°	248.6	249.1	249.6	249.8	249.6	249.4	249.3	249.1



TEST NUMBER: P333275-830

CATALOG NUMBER: S125DIP-S1090D810U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	277.6	277.8	278.1	278.1	277.7	277.4	277.1	276.8
115°	321.8	321.6	321.4	321.2	321.1	320.9	320.7	320.7
117.5°	366.0	366.1	366.3	366.0	365.3	364.7	364.0	363.4
120°	395.8	395.8	395.8	395.5	394.8	394.2	393.5	392.9
122.5°	425.0	424.9	424.7	424.4	423.9	423.4	422.8	422.4
125°	468.1	467.8	467.4	467.2	467.0	466.8	466.7	466.6
127.5°	510.9	510.7	510.6	510.3	510.0	509.6	509.3	509.0
130°	539.1	539.0	538.9	538.6	538.3	537.9	537.6	537.2
132.5°	566.3	566.1	566.0	565.6	565.2	564.8	564.3	563.8
135°	608.0	608.0	608.0	607.8	607.1	606.4	605.8	605.1
137.5°	648.7	648.8	649.0	648.8	647.9	647.1	646.3	645.5
140°	674.3	674.6	675.0	674.7	673.9	673.1	672.2	671.5
142.5°	699.4	699.6	699.7	699.5	698.6	697.9	697.0	696.2
145°	735.6	735.6	735.6	735.3	734.8	734.3	733.9	733.3
147.5°	769.0	769.5	769.9	769.5	768.4	767.2	766.2	765.1
150°	790.1	790.1	790.1	789.9	789.6	789.3	788.9	788.6
152.5°	809.7	810.1	810.5	810.4	809.8	809.3	808.7	808.0
155°	837.8	838.5	839.1	839.1	838.2	837.4	836.6	835.8
157.5°	862.1	862.8	863.5	863.3	862.1	861.1	860.0	858.9
160°	876.9	877.5	878.2	878.2	877.3	876.5	875.6	874.9
162.5°	890.7	891.6	892.3	892.2	891.3	890.3	889.4	888.4
165°	909.4	910.0	910.6	910.5	909.5	908.5	907.5	906.5
167.5°	923.1	924.1	925.1	925.0	924.1	923.0	922.0	921.0
170°	931.3	932.4	933.3	933.2	932.1	930.9	929.8	928.7
172.5°	937.3	938.2	939.2	939.2	938.2	937.2	936.1	935.1
175°	943.9	944.9	945.8	945.7	944.6	943.5	942.4	941.2
177.5°	946.9	947.6	948.5	948.4	947.4	946.6	945.7	944.7
180°	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1

(END OF REPORT)