

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333130-935

Luminaire Tested: **S125DIP-S375D590U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333130-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S375D590U935-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3345.2 lumens
Efficiency: N/A
Efficacy: 130.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333130-935

CATALOG NUMBER: S125DIP-S375D590U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333130-935

CATALOG NUMBER: S125DIP-S375D590U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	95	91	87	84	86	83	80	77	68	65	63	54	52	51	41	40	39	33
2	87	79	73	68	79	72	67	63	59	56	52	47	44	42	36	34	33	27
3	79	70	63	57	72	64	57	52	52	48	44	42	38	36	32	30	28	23
4	72	62	54	48	65	56	50	44	46	41	37	37	33	31	28	26	24	20
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21	17
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	20	18	15
7	56	44	36	31	51	41	34	29	34	28	25	27	23	20	21	18	16	13
8	52	40	33	27	47	37	30	25	31	25	22	25	21	18	19	17	15	12
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13	11
10	45	33	26	22	41	31	24	20	26	21	17	21	17	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3249	3249	3249
5°	3255	3225	3245
10°	3236	3202	3220
15°	3201	3163	3177
20°	3151	3110	3115
25°	3096	3046	3043
30°	3030	2976	2961
35°	2958	2902	2861
40°	2885	2822	2780
45°	2806	2747	2693
50°	2719	2659	2579
55°	2634	2558	2486
60°	2533	2457	2370
65°	2415	2335	2257
70°	2298	2194	2119
75°	2094	2026	1956
80°	1863	1834	1789
85°	1623	1652	1564



TEST NUMBER: P333130-935

CATALOG NUMBER: S125DIP-S375D590U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.4	1.4
10°-20°	134.0	4.0
20°-30°	197.8	5.9
30°-40°	230.8	6.9
40°-50°	231.8	6.9
50°-60°	203.5	6.1
60°-70°	151.6	4.5
70°-80°	86.7	2.6
80°-90°	26.6	0.8
90°-100°	24.1	0.7
100°-110°	148.4	4.4
110°-120°	269.2	8.0
120°-130°	345.5	10.3
130°-140°	371.6	11.1
140°-150°	348.8	10.4
150°-160°	282.1	8.4
160°-170°	182.5	5.5
170°-180°	62.9	1.9
0°-30°	379.2	11.3
0°-40°	610.0	18.2
0°-60°	1045.3	31.2
0°-90°	1310.2	39.2
90°-120°	441.7	13.2
90°-150°	1507.5	45.1
90°-180°	2035.0	60.8
0°-180°	3345.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	503	503	503	503	503	
5°	502	501	497	501	501	48
15°	479	477	473	475	475	135
25°	434	432	427	428	427	200
35°	375	373	368	366	363	235
45°	307	305	301	296	295	237
55°	234	232	227	224	221	209
65°	158	157	153	149	148	157
75°	84	83	81	80	78	89
85°	22	22	22	22	21	24
90°	0	4	8	10	12	2
95°	28	26	8	10	10	36
105°	144	146	146	146	146	153
115°	271	274	274	272	269	269
125°	386	389	389	387	386	344
135°	481	484	483	482	479	371
145°	558	558	558	559	556	349
155°	614	611	612	613	610	283
165°	648	645	646	648	644	183
175°	663	660	660	664	660	63
180°	663	663	663	663	663	



TEST NUMBER: P333130-935

CATALOG NUMBER: S125DIP-S375D590U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	503.0	503.0	503.0	503.0	503.0	503.0	503.0	503.0	503.0	503.0	503.0
2.5°	504.2	504.0	503.9	503.6	503.4	502.9	502.2	501.5	500.8	500.1	500.8
5°	502.1	502.0	501.8	501.6	501.4	500.9	500.1	499.2	498.3	497.4	498.2
7.5°	497.6	497.4	497.2	497.1	496.9	496.3	495.3	494.3	493.4	492.4	493.2
10°	493.4	493.3	493.1	492.9	492.8	492.1	491.2	490.2	489.2	488.3	489.0
12.5°	488.4	488.0	487.7	487.4	487.1	486.5	485.5	484.7	483.7	482.8	483.4
15°	478.7	478.5	478.2	477.9	477.6	477.0	476.0	475.1	474.1	473.1	473.6
17.5°	467.6	467.3	466.8	466.5	466.1	465.4	464.3	463.4	462.4	461.3	461.9
20°	458.4	458.2	458.1	457.9	457.7	457.0	455.9	454.7	453.6	452.5	453.1
22.5°	449.2	448.8	448.5	448.2	447.9	447.2	446.1	445.1	443.9	442.9	443.3
25°	434.5	434.1	433.6	433.2	432.7	432.0	430.8	429.6	428.5	427.4	427.6
27.5°	417.4	417.2	416.9	416.6	416.4	415.6	414.5	413.3	412.1	410.9	411.0
30°	406.3	406.0	405.7	405.4	405.2	404.4	403.1	401.7	400.5	399.1	398.9
32.5°	394.2	393.7	393.4	393.0	392.5	391.8	390.5	389.3	388.2	387.0	386.7
35°	375.2	374.9	374.5	374.2	373.8	373.0	371.8	370.6	369.3	368.1	367.6
37.5°	355.6	355.2	354.7	354.2	353.8	353.0	351.8	350.7	349.5	348.4	347.7
40°	342.2	341.7	341.3	340.9	340.4	339.6	338.4	337.2	335.9	334.7	333.9
42.5°	327.9	327.5	327.2	326.7	326.4	325.6	324.3	323.1	321.8	320.6	319.9
45°	307.2	306.9	306.5	306.2	305.7	305.1	304.0	303.0	301.9	300.8	299.8
47.5°	284.9	284.9	284.9	285.0	285.0	284.4	283.1	281.8	280.5	279.2	278.2
50°	270.6	270.4	270.1	269.8	269.5	268.9	267.8	266.7	265.7	264.6	263.5
52.5°	256.0	255.7	255.5	255.4	255.2	254.5	253.4	252.3	251.1	249.9	249.0
55°	233.9	233.7	233.4	233.2	232.9	232.1	230.9	229.7	228.4	227.2	226.4
57.5°	210.9	210.7	210.5	210.4	210.3	209.7	208.6	207.6	206.6	205.5	204.5
60°	196.1	195.8	195.4	195.1	194.8	194.1	193.1	192.2	191.1	190.2	189.3
62.5°	180.9	180.6	180.3	180.0	179.8	179.2	178.4	177.5	176.7	175.9	175.0
65°	158.0	157.8	157.6	157.5	157.3	156.7	155.8	154.7	153.8	152.8	152.0
67.5°	135.8	135.4	135.0	134.7	134.3	133.7	133.0	132.2	131.6	130.9	130.2
70°	121.7	121.3	120.9	120.5	120.0	119.3	118.6	117.8	117.0	116.2	115.6
72.5°	106.5	106.2	105.9	105.6	105.3	104.9	104.4	103.8	103.3	102.8	102.2
75°	83.9	83.8	83.6	83.4	83.3	82.9	82.5	82.1	81.6	81.2	80.9
77.5°	63.2	63.1	63.0	62.9	62.9	62.8	62.5	62.3	62.0	61.7	61.6
80°	50.1	50.1	50.1	50.1	50.1	50.0	49.9	49.7	49.5	49.3	49.2
82.5°	38.7	38.6	38.4	38.2	38.1	38.1	38.0	38.0	37.9	37.9	37.7
85°	21.9	22.0	22.0	22.1	22.2	22.3	22.3	22.3	22.3	22.3	22.2
87.5°	8.7	8.9	9.0	9.2	9.4	9.6	9.6	9.6	9.7	9.8	10.0
90°	0.5	1.4	2.2	3.1	4.0	4.8	5.6	6.4	7.1	7.8	8.4
92.5°	7.6	7.0	6.4	5.8	5.1	5.2	5.9	6.5	7.1	7.8	8.4
95°	28.0	27.6	27.4	27.0	26.7	24.5	20.3	16.2	12.0	7.8	8.4
97.5°	58.5	59.1	59.7	60.2	60.8	57.0	48.8	40.6	32.4	24.2	21.1
100°	82.1	82.4	82.7	83.0	83.3	83.7	84.2	84.6	85.1	85.5	69.2
102.5°	106.0	106.4	106.9	107.3	107.6	108.0	108.2	108.6	108.8	109.1	106.0
105°	144.4	144.8	145.3	145.8	146.2	146.4	146.4	146.4	146.4	146.4	146.4
107.5°	184.3	184.3	184.3	184.3	184.3	184.4	184.6	184.9	185.1	185.3	185.3
110°	210.3	210.3	210.3	210.3	210.3	210.3	210.6	210.8	211.0	211.2	210.9



TEST NUMBER: P333130-935

CATALOG NUMBER: S125DIP-S375D590U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	234.6	234.9	235.1	235.4	235.7	235.8	236.0	236.1	236.3	236.3	236.0
115°	271.1	271.7	272.2	272.8	273.4	273.7	273.8	273.9	274.0	274.1	273.7
117.5°	309.0	308.9	308.9	308.9	308.9	309.1	309.5	310.0	310.3	310.7	310.2
120°	332.6	332.4	332.3	332.3	332.1	332.3	332.6	332.9	333.2	333.6	333.3
122.5°	353.4	353.8	354.2	354.6	355.1	355.3	355.5	355.7	355.8	355.9	355.8
125°	385.6	386.4	387.1	387.9	388.7	389.1	389.1	389.1	389.1	389.1	388.7
127.5°	416.4	416.9	417.5	418.0	418.5	418.8	418.7	418.7	418.6	418.5	418.3
130°	435.2	435.8	436.4	436.9	437.4	437.7	437.8	438.0	438.1	438.2	437.8
132.5°	454.1	454.7	455.4	456.0	456.6	456.8	456.6	456.3	456.1	455.9	455.8
135°	481.0	481.6	482.2	482.8	483.5	483.8	483.5	483.3	483.1	482.8	482.7
137.5°	505.6	506.2	506.7	507.3	507.8	508.1	507.8	507.6	507.5	507.2	507.3
140°	521.7	521.9	522.1	522.4	522.5	522.6	522.5	522.4	522.3	522.2	522.4
142.5°	536.2	536.4	536.5	536.7	536.7	536.9	537.1	537.2	537.4	537.5	537.5
145°	557.6	557.8	558.0	558.2	558.4	558.5	558.5	558.5	558.5	558.5	558.6
147.5°	576.2	576.2	576.1	576.1	576.0	576.1	576.2	576.4	576.4	576.6	576.8
150°	588.0	587.8	587.5	587.4	587.1	587.1	587.4	587.5	587.8	588.0	588.2
152.5°	599.4	598.9	598.5	598.0	597.4	597.4	597.5	597.8	598.0	598.2	598.5
155°	614.1	613.4	612.8	612.1	611.4	611.2	611.4	611.7	611.8	612.1	612.4
157.5°	625.3	624.9	624.6	624.1	623.8	623.6	623.6	623.6	623.6	623.7	624.1
160°	633.2	632.6	631.9	631.2	630.6	630.3	630.4	630.5	630.6	630.8	631.2
162.5°	639.5	638.9	638.2	637.5	636.9	636.6	636.7	636.8	636.9	637.1	637.7
165°	647.9	647.3	646.6	646.0	645.3	645.1	645.1	645.2	645.4	645.5	646.1
167.5°	654.2	653.6	652.9	652.2	651.5	651.3	651.3	651.4	651.5	651.7	652.5
170°	657.8	657.0	656.3	655.5	654.7	654.4	654.4	654.6	654.7	654.8	655.7
172.5°	660.1	659.4	658.6	657.8	657.0	656.8	656.9	657.2	657.4	657.5	658.3
175°	662.7	662.0	661.3	660.7	660.0	659.8	659.9	660.0	660.1	660.2	661.1
177.5°	663.8	663.3	662.8	662.3	661.8	661.5	661.6	661.7	661.8	661.9	662.5
180°	662.7	662.7	662.7	662.7	662.7	662.7	662.7	662.7	662.7	662.7	662.7



TEST NUMBER: P333130-935

CATALOG NUMBER: S125DIP-S375D590U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	503.0	503.0	503.0	503.0	503.0	503.0	503.0	503.0
2.5°	501.5	502.2	502.9	503.3	503.2	503.1	503.1	503.0
5°	498.9	499.8	500.6	500.9	500.8	500.8	500.7	500.6
7.5°	494.0	494.7	495.5	495.8	495.8	495.7	495.6	495.5
10°	489.7	490.3	491.1	491.4	491.3	491.2	491.1	491.0
12.5°	484.0	484.6	485.1	485.3	485.3	485.3	485.3	485.3
15°	474.0	474.4	474.9	475.1	475.1	475.1	475.1	475.1
17.5°	462.4	463.0	463.6	463.6	463.1	462.7	462.3	461.8
20°	453.7	454.3	454.9	455.0	454.5	454.1	453.7	453.2
22.5°	443.7	444.1	444.5	444.5	444.3	443.9	443.7	443.3
25°	427.7	427.9	428.1	428.0	427.7	427.5	427.2	427.0
27.5°	411.0	411.0	411.0	411.0	410.6	410.4	410.1	409.8
30°	398.7	398.6	398.4	398.2	398.0	397.7	397.4	397.1
32.5°	386.4	386.1	385.7	385.4	384.9	384.4	383.9	383.4
35°	367.2	366.8	366.3	365.8	365.1	364.3	363.6	362.9
37.5°	347.1	346.4	345.7	345.2	344.7	344.4	344.0	343.5
40°	333.0	332.3	331.5	331.0	330.7	330.4	330.1	329.8
42.5°	319.2	318.5	317.7	317.2	316.8	316.3	316.0	315.6
45°	298.7	297.6	296.6	295.9	295.7	295.4	295.2	294.9
47.5°	277.1	276.0	274.9	274.1	273.5	272.9	272.2	271.6
50°	262.3	261.1	260.0	259.2	258.5	257.9	257.3	256.7
52.5°	248.0	246.9	245.9	245.1	244.4	243.7	243.1	242.4
55°	225.6	224.8	224.0	223.3	222.7	222.1	221.4	220.8
57.5°	203.5	202.4	201.4	200.7	200.4	200.0	199.7	199.3
60°	188.5	187.5	186.7	185.9	185.3	184.7	184.1	183.5
62.5°	174.0	173.0	172.0	171.3	170.9	170.4	169.9	169.4
65°	151.2	150.4	149.6	149.0	148.7	148.4	148.0	147.7
67.5°	129.5	128.8	128.1	127.7	127.5	127.3	127.1	126.8
70°	115.1	114.6	114.1	113.7	113.3	113.0	112.5	112.2
72.5°	101.6	101.0	100.4	100.0	99.6	99.3	98.8	98.5
75°	80.7	80.4	80.1	79.8	79.5	79.1	78.8	78.4
77.5°	61.5	61.3	61.1	61.0	60.7	60.4	60.2	59.9
80°	49.2	49.1	49.0	48.8	48.6	48.5	48.3	48.1
82.5°	37.5	37.4	37.3	37.1	37.1	37.1	37.0	37.0
85°	22.1	22.0	22.0	21.8	21.6	21.4	21.3	21.1
87.5°	10.1	10.2	10.2	10.3	10.2	10.2	10.1	10.0
90°	9.0	9.5	10.1	10.5	10.8	11.1	11.5	11.8
92.5°	9.0	9.5	10.1	10.4	10.5	10.7	10.8	11.0
95°	9.0	9.5	10.1	10.3	10.3	10.3	10.3	10.3
97.5°	18.0	14.9	11.9	10.3	10.3	10.3	10.3	10.3
100°	53.0	36.7	20.4	12.1	11.6	11.2	10.8	10.3
102.5°	102.9	99.8	96.8	91.5	84.0	76.6	69.2	61.8
105°	146.4	146.4	146.4	146.4	146.2	146.1	146.0	145.9
107.5°	185.4	185.4	185.4	185.2	184.9	184.6	184.3	183.9
110°	210.6	210.3	209.9	209.8	209.9	210.0	210.2	210.3



TEST NUMBER: P333130-935

CATALOG NUMBER: S125DIP-S375D590U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	235.6	235.1	234.7	234.5	234.3	234.1	234.0	233.8
115°	273.2	272.8	272.3	271.8	271.1	270.5	269.8	269.2
117.5°	309.6	309.0	308.5	308.1	307.8	307.5	307.2	306.9
120°	333.1	332.9	332.7	332.3	331.7	331.2	330.6	330.1
122.5°	355.5	355.3	355.1	354.6	354.0	353.4	352.8	352.1
125°	388.2	387.7	387.3	386.9	386.6	386.2	386.0	385.6
127.5°	418.0	417.8	417.6	417.1	416.2	415.4	414.7	413.8
130°	437.6	437.2	436.9	436.4	435.9	435.3	434.8	434.3
132.5°	455.7	455.6	455.6	455.3	454.8	454.2	453.7	453.1
135°	482.4	482.2	482.0	481.6	481.0	480.3	479.6	479.0
137.5°	507.3	507.4	507.4	507.1	506.6	506.0	505.5	504.9
140°	522.6	522.8	523.1	522.8	522.2	521.5	520.9	520.2
142.5°	537.6	537.6	537.7	537.4	536.7	536.1	535.4	534.8
145°	558.8	558.9	559.0	558.7	558.0	557.4	556.7	556.0
147.5°	576.9	577.0	577.1	576.8	576.0	575.2	574.5	573.7
150°	588.4	588.7	588.8	588.6	587.7	586.8	585.9	585.0
152.5°	598.7	598.9	599.1	598.8	598.1	597.3	596.4	595.6
155°	612.8	613.0	613.4	613.1	612.3	611.4	610.5	609.6
157.5°	624.4	624.7	625.1	624.8	624.0	623.0	622.2	621.3
160°	631.6	632.1	632.5	632.2	631.4	630.5	629.6	628.8
162.5°	638.3	638.9	639.5	639.3	638.3	637.4	636.5	635.4
165°	646.8	647.5	648.1	648.0	647.1	646.3	645.4	644.5
167.5°	653.2	654.0	654.8	654.7	653.8	652.7	651.8	650.7
170°	656.6	657.5	658.3	658.2	657.3	656.3	655.3	654.4
172.5°	659.1	660.0	660.7	660.6	659.6	658.7	657.6	656.7
175°	661.9	662.8	663.7	663.7	662.7	661.7	660.7	659.7
177.5°	663.1	663.7	664.3	664.3	663.6	662.9	662.2	661.5
180°	662.7	662.7	662.7	662.7	662.7	662.7	662.7	662.7

(END OF REPORT)