

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333333-830

Luminaire Tested: **S125DIP-S1270D1205U830-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333333-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1270D1205U830-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8961.3 lumens
Efficiency: N/A
Efficacy: 125.0 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333333-830

CATALOG NUMBER: S125DIP-S1270D1205U830-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333333-830

CATALOG NUMBER: S125DIP-S1270D1205U830-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60	55
1	99	95	91	88	92	88	85	82	76	73	71	64	63	61	54	53	51	46
2	90	83	77	72	84	77	72	68	67	63	59	57	54	51	48	45	44	39
3	83	73	66	60	76	68	62	57	59	54	50	50	47	44	42	40	37	33
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	38	35	32	29
5	69	58	50	44	64	54	47	42	47	41	37	40	36	33	34	31	28	25
6	64	52	44	38	59	49	41	36	42	37	32	37	32	29	31	28	25	22
7	59	47	39	33	55	44	37	32	38	33	29	33	29	25	28	25	22	20
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	26	22	20	18
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	24	20	18	16
10	48	36	28	24	44	34	27	23	30	24	20	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11180	11180	11180	11180
5°	12947	11218	9822	11218
10°	15062	11160	8605	11160
15°	16673	11078	7938	11078
20°	18664	10948	7403	10948
25°	21865	10802	7142	10802
30°	23616	10657	6915	10657
35°	19418	10387	6766	10387
40°	13801	10010	6604	10010
45°	10602	9502	6509	9502
50°	9051	8874	6497	8874
55°	8059	8257	6552	8257
60°	7270	7582	6719	7582
65°	6715	6906	6894	6906
70°	6105	6201	6992	6201
75°	5390	5465	6932	5465
80°	4537	4456	6338	4456
85°	3586	3216	5120	3216



TEST NUMBER: P333333-830

CATALOG NUMBER: S125DIP-S1270D1205U830-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.6	1.9
10°-20°	496.2	5.5
20°-30°	805.7	9.0
30°-40°	982.8	11.0
40°-50°	894.0	10.0
50°-60°	712.1	7.9
60°-70°	496.0	5.5
70°-80°	264.5	3.0
80°-90°	69.8	0.8
90°-100°	393.7	4.4
100°-110°	846.4	9.4
110°-120°	794.4	8.9
120°-130°	643.8	7.2
130°-140°	516.6	5.8
140°-150°	389.9	4.4
150°-160°	274.4	3.1
160°-170°	161.8	1.8
170°-180°	52.6	0.6
0°-30°	1468.5	16.4
0°-40°	2451.2	27.4
0°-60°	4057.4	45.3
0°-90°	4887.7	54.5
90°-120°	2034.5	22.7
90°-150°	3584.8	40.0
90°-180°	4074.0	45.5
0°-180°	8961.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1731	1731	1731	1731	1731	
5°	1997	1730	1515	1730	1997	201
15°	2494	1657	1187	1657	2494	714
25°	3068	1516	1002	1516	3068	1401
35°	2463	1317	858	1317	2463	1507
45°	1161	1040	713	1040	1161	929
55°	716	733	582	733	716	645
65°	439	452	451	452	439	436
75°	216	219	278	219	216	233
85°	48	43	69	43	48	57
90°	25	1	25	1	25	19
95°	257	36	257	36	257	365
105°	1451	124	1451	124	1451	1442
115°	1616	221	1616	221	1616	1579
125°	1274	307	1274	307	1274	1152
135°	1058	359	1058	359	1058	820
145°	834	418	834	418	834	530
155°	700	478	700	478	700	326
165°	613	521	613	521	613	175
175°	551	542	551	542	551	54
180°	543	543	543	543	543	



TEST NUMBER: P333333-830

CATALOG NUMBER: S125DIP-S1270D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1
2.5°	1831.0	1828.6	1826.3	1821.6	1825.0	1815.1	1810.3	1802.1	1792.2	1788.7	1784.5
5°	1997.0	2000.6	2004.3	1989.0	1990.4	1980.1	1956.6	1937.5	1922.0	1902.2	1888.3
7.5°	2196.9	2188.2	2187.5	2177.5	2160.3	2146.5	2121.8	2090.3	2059.9	2025.2	1996.6
10°	2296.8	2297.5	2290.9	2279.2	2260.8	2247.6	2215.3	2184.3	2146.9	2102.8	2071.2
12.5°	2372.0	2375.1	2366.7	2350.9	2341.8	2312.2	2286.9	2250.2	2205.6	2170.4	2122.3
15°	2493.7	2485.6	2479.7	2459.8	2444.5	2413.6	2373.2	2335.0	2286.5	2241.6	2196.9
17.5°	2610.9	2617.4	2606.4	2588.3	2540.4	2504.4	2450.2	2397.8	2337.5	2277.4	2223.9
20°	2715.6	2721.5	2704.5	2673.0	2615.6	2579.6	2508.4	2440.8	2371.0	2293.9	2235.1
22.5°	2846.1	2841.4	2818.6	2770.5	2720.8	2654.3	2577.2	2494.8	2407.4	2320.3	2242.1
25°	3068.3	3037.3	3023.4	2963.9	2898.5	2800.8	2695.0	2574.5	2465.8	2350.4	2250.5
27.5°	3191.4	3181.6	3166.1	3124.7	3055.9	2951.4	2826.7	2679.8	2526.5	2380.9	2250.0
30°	3166.7	3168.2	3169.7	3156.4	3112.4	3033.7	2909.5	2751.6	2569.4	2405.6	2254.2
32.5°	2948.1	2974.8	3000.4	3030.7	3043.0	3027.8	2950.1	2807.5	2619.9	2433.7	2251.8
35°	2462.9	2470.9	2553.9	2636.2	2747.9	2834.6	2892.7	2829.4	2671.4	2457.7	2249.0
37.5°	1920.3	1960.0	2017.4	2110.4	2271.6	2415.9	2601.5	2686.9	2635.9	2465.5	2243.9
40°	1637.0	1673.8	1711.2	1806.0	1941.9	2116.8	2327.6	2507.6	2549.5	2440.8	2226.3
42.5°	1418.3	1447.5	1489.0	1560.3	1673.9	1828.7	2030.2	2265.5	2410.2	2369.1	2189.2
45°	1160.8	1179.2	1211.5	1268.2	1350.5	1471.7	1649.4	1906.7	2130.7	2204.9	2101.3
47.5°	993.6	993.5	1018.6	1057.7	1117.1	1220.1	1351.6	1553.1	1792.4	1969.5	1961.3
50°	900.8	897.1	916.9	950.7	997.8	1066.1	1191.8	1352.6	1582.6	1783.2	1839.0
52.5°	820.9	821.2	833.5	858.5	897.9	956.2	1050.1	1195.1	1391.6	1597.4	1702.7
55°	715.7	712.7	726.6	743.6	772.2	810.4	878.0	988.9	1148.4	1351.1	1487.8
57.5°	619.3	627.4	632.9	644.7	668.5	694.0	751.0	832.5	958.9	1132.9	1277.4
60°	562.8	570.9	575.3	587.0	606.1	628.2	672.3	738.4	845.0	994.9	1138.1
62.5°	512.3	518.6	520.0	530.7	546.2	567.7	602.4	657.9	742.1	873.2	1013.5
65°	439.4	439.4	442.3	453.4	460.7	479.8	506.2	546.7	614.3	716.3	836.1
67.5°	369.1	372.7	371.9	376.7	383.5	398.4	417.4	450.7	500.8	575.3	671.1
70°	323.3	326.2	325.5	329.1	336.5	346.1	361.5	393.0	429.0	493.0	575.3
72.5°	282.1	283.3	281.4	286.3	290.7	299.1	316.2	333.1	366.7	420.8	488.3
75°	216.0	217.4	219.0	221.9	226.3	230.7	239.5	256.5	278.4	318.9	362.2
77.5°	161.9	159.1	162.7	162.2	164.8	168.1	175.9	184.8	202.9	228.5	262.0
80°	122.0	122.7	122.7	123.5	127.1	129.3	135.9	142.5	156.5	175.6	199.2
82.5°	89.1	91.0	89.8	91.1	94.2	95.8	99.4	104.9	113.0	128.0	145.1
85°	48.4	44.9	46.3	47.8	47.8	48.4	51.5	53.6	58.1	63.9	70.5
87.5°	19.1	20.4	20.7	20.7	21.3	20.8	23.0	22.7	24.3	25.8	27.7
90°	25.2	25.2	24.1	24.1	24.1	21.9	20.8	19.7	18.7	17.5	15.4
92.5°	69.8	71.6	73.1	75.8	89.8	106.0	140.8	194.1	285.9	353.1	358.8
95°	257.4	274.9	283.6	316.5	394.3	486.3	620.9	787.4	949.5	970.3	791.8
97.5°	622.1	636.1	667.9	729.2	796.8	924.8	1056.0	1172.7	1201.5	1036.2	707.1
100°	854.2	871.8	912.3	991.2	1066.7	1180.6	1293.5	1347.1	1262.7	988.9	630.8
102.5°	1113.6	1126.7	1170.7	1226.8	1307.7	1384.8	1438.9	1405.8	1226.0	905.7	573.0
105°	1451.1	1464.2	1486.2	1522.3	1557.4	1569.4	1521.3	1371.2	1108.3	794.0	516.9
107.5°	1630.3	1639.1	1646.3	1646.5	1628.8	1571.6	1447.8	1247.6	988.4	717.1	493.2
110°	1689.9	1689.9	1682.2	1661.4	1612.1	1519.0	1364.6	1156.5	919.9	681.2	486.3



TEST NUMBER: P333333-830

CATALOG NUMBER: S125DIP-S1270D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1682.9	1675.0	1656.0	1620.2	1548.1	1438.4	1282.2	1084.7	869.1	660.2	486.3
115°	1616.5	1602.2	1571.6	1519.0	1433.6	1314.2	1164.2	994.5	813.7	637.4	489.6
117.5°	1500.2	1491.5	1461.0	1406.7	1321.3	1211.7	1082.5	936.1	780.6	626.2	496.8
120°	1424.8	1416.1	1386.5	1334.0	1252.9	1156.5	1036.0	904.7	762.2	620.9	503.8
122.5°	1358.3	1350.4	1320.8	1272.6	1200.3	1110.1	1002.8	881.0	746.5	616.6	509.9
125°	1273.8	1262.7	1238.7	1193.7	1132.5	1053.6	958.3	846.6	725.0	611.1	520.2
127.5°	1201.5	1196.7	1173.8	1134.2	1078.6	1004.8	915.8	811.5	705.3	608.5	531.8
130°	1162.0	1155.5	1133.5	1097.4	1042.6	971.5	886.0	789.7	692.2	606.7	538.9
132.5°	1122.6	1115.1	1095.0	1058.9	1004.1	935.5	858.0	767.7	681.6	606.7	546.7
135°	1058.0	1051.4	1031.7	995.5	947.3	885.0	814.8	739.2	669.2	606.7	557.4
137.5°	988.9	981.8	963.6	930.7	887.6	834.5	776.3	715.2	658.0	608.0	567.3
140°	940.8	935.3	918.9	890.4	849.9	803.9	753.5	702.0	652.7	608.9	571.7
142.5°	896.1	891.5	875.9	851.9	817.5	777.6	734.2	690.6	648.4	609.8	574.3
145°	834.5	830.2	818.1	799.5	773.2	743.7	709.6	675.7	641.8	608.9	577.2
147.5°	782.4	780.4	773.5	758.6	737.7	715.4	689.3	661.8	635.0	606.1	578.2
150°	753.5	752.4	748.0	734.9	718.4	698.7	678.0	653.8	629.7	603.4	578.2
152.5°	730.8	729.6	725.2	714.7	701.0	685.6	666.6	645.1	623.6	599.9	577.4
155°	699.8	698.7	695.4	687.8	676.8	664.8	649.4	631.9	613.3	593.6	575.0
157.5°	672.2	672.4	669.4	663.0	654.5	645.1	633.2	618.8	603.7	587.0	572.1
160°	653.8	655.0	652.7	647.2	639.6	631.9	620.9	610.0	595.8	582.7	569.5
162.5°	637.2	637.4	637.0	632.4	626.4	619.6	610.5	600.4	588.8	577.4	566.8
165°	613.3	613.3	613.3	611.1	606.7	601.2	594.7	587.0	578.2	569.5	562.9
167.5°	591.4	591.6	592.5	590.5	588.3	584.4	579.4	574.3	568.0	561.8	556.8
170°	578.2	579.4	579.4	578.2	576.1	573.9	570.6	567.3	561.8	557.4	554.2
172.5°	566.0	567.1	568.8	566.8	566.5	565.1	562.7	559.4	555.7	552.2	550.6
175°	550.9	552.0	554.2	553.1	553.1	553.1	550.9	550.9	547.6	546.5	546.5
177.5°	543.2	543.2	545.8	545.0	545.8	545.8	545.8	545.0	544.1	543.2	543.2
180°	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2



TEST NUMBER: P333333-830

CATALOG NUMBER: S125DIP-S1270D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1
2.5°	1781.0	1776.9	1772.2	1764.0	1754.0	1748.7	1740.4	1735.1	1724.6	1715.7	1706.4
5°	1871.3	1852.3	1834.7	1811.8	1786.9	1770.7	1751.6	1730.3	1708.3	1685.5	1660.5
7.5°	1965.0	1931.2	1894.4	1854.9	1816.3	1780.7	1746.7	1713.4	1682.2	1644.6	1612.8
10°	2027.9	1985.3	1939.7	1886.0	1833.9	1788.4	1742.0	1701.7	1660.5	1616.4	1577.4
12.5°	2090.7	2034.0	1969.6	1910.7	1848.0	1793.0	1738.5	1687.0	1635.2	1586.4	1541.1
15°	2135.1	2085.2	2025.6	1941.9	1871.3	1795.7	1723.7	1656.8	1594.4	1540.0	1482.7
17.5°	2164.4	2100.0	2036.1	1955.7	1863.3	1778.7	1697.0	1620.5	1550.1	1481.2	1426.0
20°	2169.6	2103.6	2036.6	1958.0	1863.3	1766.3	1684.7	1592.9	1517.2	1446.0	1378.4
22.5°	2167.9	2092.9	2020.2	1939.3	1846.8	1757.5	1658.9	1565.3	1483.1	1413.1	1342.5
25°	2151.3	2071.2	1980.1	1898.6	1807.4	1712.7	1612.8	1515.8	1432.0	1351.9	1282.1
27.5°	2137.5	2033.6	1930.4	1835.3	1747.4	1660.5	1564.8	1465.5	1372.6	1291.5	1225.7
30°	2120.4	2006.6	1890.5	1791.3	1700.9	1616.4	1526.1	1429.1	1332.1	1252.7	1182.2
32.5°	2105.2	1972.5	1849.9	1741.9	1646.2	1564.1	1480.7	1388.5	1293.3	1212.8	1142.2
35°	2075.7	1922.0	1781.7	1659.7	1557.6	1473.1	1403.4	1317.4	1229.9	1152.1	1084.5
37.5°	2038.2	1856.0	1705.3	1577.4	1465.5	1376.5	1311.5	1245.5	1161.6	1086.6	1025.4
40°	2008.7	1808.9	1649.4	1518.7	1402.6	1310.0	1249.8	1187.3	1117.6	1047.7	983.1
42.5°	1971.7	1766.6	1593.1	1452.3	1337.4	1247.2	1183.9	1130.9	1069.3	1004.3	944.2
45°	1903.7	1689.9	1501.8	1350.5	1234.4	1145.5	1080.1	1040.4	994.1	932.4	881.7
47.5°	1803.6	1597.7	1403.2	1247.0	1127.2	1044.8	983.5	945.5	912.9	867.0	821.0
50°	1714.9	1529.0	1332.1	1177.0	1057.2	974.2	917.7	883.2	855.3	819.9	781.0
52.5°	1615.5	1442.6	1262.2	1108.9	990.2	908.4	853.0	822.7	799.4	774.1	735.7
55°	1457.7	1310.8	1143.2	997.8	888.3	808.2	759.7	733.3	714.2	695.0	671.6
57.5°	1283.8	1168.9	1020.6	887.6	786.7	713.9	668.6	642.9	628.0	618.2	604.4
60°	1161.6	1063.2	935.3	814.1	715.7	651.0	606.9	587.0	574.6	566.5	556.2
62.5°	1048.2	967.3	848.9	738.3	652.1	591.0	551.7	532.3	520.5	516.5	508.0
65°	880.9	818.5	720.8	629.0	555.4	503.3	470.2	451.9	444.5	440.1	440.8
67.5°	716.2	678.2	599.6	521.3	462.7	419.0	392.5	378.4	374.8	368.8	368.7
70°	615.7	587.0	520.9	452.6	400.4	366.6	343.1	328.4	324.7	321.8	321.1
72.5°	527.0	501.8	444.5	389.7	342.8	313.1	293.8	284.9	278.9	277.1	277.0
75°	396.1	382.1	336.5	293.1	260.8	240.3	227.1	219.0	214.5	213.8	214.5
77.5°	281.5	269.4	240.4	209.7	189.3	173.7	162.5	159.8	154.8	154.9	154.1
80°	211.6	203.5	185.1	160.9	144.0	130.8	124.9	119.8	118.3	116.1	118.3
82.5°	153.4	144.8	132.2	116.8	102.8	94.9	89.1	87.5	86.5	85.5	86.0
85°	75.7	76.4	69.1	57.3	51.5	47.0	43.4	43.4	42.6	41.8	42.6
87.5°	28.7	27.1	24.5	22.3	18.9	16.8	15.7	16.1	14.5	14.4	15.5
90°	14.2	12.1	10.9	8.8	6.6	4.3	2.2	1.1	2.2	4.3	6.6
92.5°	250.0	149.6	89.8	57.9	39.0	25.4	16.2	13.4	16.2	25.4	39.0
95°	489.6	248.6	131.4	82.1	58.1	46.0	37.2	36.1	37.2	46.0	58.1
97.5°	390.8	214.2	136.7	101.2	79.6	67.5	61.4	60.0	61.4	67.5	79.6
100°	354.9	212.4	148.9	116.1	95.3	83.2	78.9	76.6	78.9	83.2	95.3
102.5°	340.0	220.4	163.8	131.9	112.8	99.9	96.4	95.1	96.4	99.9	112.8
105°	334.0	236.6	188.4	157.7	140.2	129.2	123.8	123.8	123.8	129.2	140.2
107.5°	344.1	260.6	214.0	186.4	168.2	159.2	154.0	151.7	154.0	159.2	168.2
110°	353.7	278.1	233.3	204.8	188.4	178.5	174.2	171.9	174.2	178.5	188.4



TEST NUMBER: P333333-830

CATALOG NUMBER: S125DIP-S1270D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	366.0	294.8	251.7	224.0	207.6	197.7	194.3	192.1	194.3	197.7	207.6
115°	384.4	320.9	280.4	253.0	236.6	226.7	223.4	221.2	223.4	226.7	236.6
117.5°	405.5	347.6	309.2	282.8	264.2	254.3	250.8	247.5	250.8	254.3	264.2
120°	419.4	366.9	328.6	301.1	282.6	272.7	268.3	265.0	268.3	272.7	282.6
122.5°	435.3	385.3	346.9	319.6	299.2	289.4	285.9	283.4	285.9	289.4	299.2
125°	456.7	409.6	373.4	345.0	324.1	314.3	308.9	306.6	308.9	314.3	324.1
127.5°	476.5	433.0	398.2	369.8	347.6	335.2	328.1	324.8	328.1	335.2	347.6
130°	489.6	447.9	414.0	385.5	362.5	348.3	339.5	336.2	339.5	348.3	362.5
132.5°	501.0	461.9	428.0	399.5	375.7	359.7	349.1	345.0	349.1	359.7	375.7
135°	516.9	480.8	446.9	417.3	394.3	376.7	363.6	359.2	363.6	376.7	394.3
137.5°	528.8	494.2	463.3	432.8	410.3	392.8	380.5	377.2	380.5	392.8	410.3
140°	536.7	503.8	472.0	442.4	421.7	404.2	391.0	387.7	391.0	404.2	421.7
142.5°	541.0	509.9	479.9	452.1	432.2	414.6	402.4	399.9	402.4	414.6	432.2
145°	547.6	520.2	491.7	466.6	446.9	431.5	420.6	418.4	420.6	431.5	446.9
147.5°	551.6	526.8	501.8	479.7	462.6	448.4	438.9	437.6	438.9	448.4	462.6
150°	554.2	531.1	507.1	488.4	473.2	458.9	451.2	449.0	451.2	458.9	473.2
152.5°	555.9	535.6	513.2	496.3	481.9	469.4	462.6	461.3	462.6	469.4	481.9
155°	557.4	539.9	521.3	506.0	495.0	484.1	477.5	477.5	477.5	484.1	495.0
157.5°	558.6	543.7	527.6	516.0	506.4	497.0	491.7	492.0	491.7	497.0	506.4
160°	558.6	545.4	531.1	521.3	512.6	504.9	500.5	501.6	500.5	504.9	512.6
162.5°	557.7	547.1	534.7	526.6	519.5	512.7	508.4	509.4	508.4	512.7	519.5
165°	556.4	547.6	538.9	532.3	527.9	522.5	519.2	521.3	519.2	522.5	527.9
167.5°	553.7	547.6	540.4	536.2	533.1	530.1	528.1	529.2	528.1	530.1	533.1
170°	552.0	547.6	542.2	538.9	536.7	534.4	533.4	534.4	533.4	534.4	536.7
172.5°	550.3	546.7	542.2	540.5	539.2	537.1	536.0	538.0	536.0	537.1	539.2
175°	547.6	545.4	542.2	542.2	542.2	541.0	539.9	542.2	539.9	541.0	542.2
177.5°	545.0	544.1	542.3	542.3	543.2	542.3	542.3	544.1	542.3	542.3	543.2
180°	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2



TEST NUMBER: P333333-830

CATALOG NUMBER: S125DIP-S1270D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1
2.5°	1701.0	1694.6	1689.3	1677.5	1671.0	1662.3	1655.2	1662.8	1654.6	1658.1	1652.8
5°	1648.0	1627.4	1612.8	1591.4	1573.1	1556.1	1543.7	1541.4	1535.6	1532.7	1523.8
7.5°	1584.2	1558.5	1533.2	1505.3	1481.8	1457.8	1442.6	1429.9	1421.5	1410.5	1403.1
10°	1546.6	1512.1	1482.7	1448.9	1419.5	1393.8	1373.2	1362.9	1353.4	1339.4	1334.3
12.5°	1500.2	1464.4	1428.6	1392.5	1364.2	1335.6	1318.0	1302.4	1295.8	1280.1	1278.5
15°	1444.4	1390.8	1355.6	1318.8	1279.9	1256.4	1241.7	1224.8	1217.5	1206.5	1198.3
17.5°	1378.1	1330.1	1286.1	1248.0	1214.7	1194.9	1176.6	1165.0	1152.4	1145.2	1131.9
20°	1329.8	1284.3	1240.2	1199.9	1174.1	1151.3	1136.6	1125.6	1112.4	1108.7	1095.5
22.5°	1289.3	1239.1	1196.7	1162.8	1134.7	1109.0	1093.2	1085.6	1076.6	1065.3	1062.5
25°	1223.3	1171.2	1135.2	1101.4	1076.4	1052.9	1041.9	1032.3	1023.5	1015.4	1012.5
27.5°	1166.3	1119.7	1076.9	1046.4	1024.6	1003.2	993.5	981.9	975.4	968.9	961.0
30°	1126.3	1078.6	1041.1	1011.7	988.3	969.1	958.8	950.7	944.9	939.0	934.6
32.5°	1085.2	1040.9	1004.7	975.9	952.3	937.9	928.9	923.1	916.6	909.6	904.0
35°	1030.9	982.3	947.1	922.1	903.7	892.7	882.4	877.2	870.0	870.0	864.0
37.5°	969.6	927.7	896.5	873.7	857.2	847.4	836.3	832.7	828.0	824.9	822.9
40°	933.1	894.2	864.8	842.0	824.3	816.2	807.5	801.6	798.6	794.9	793.5
42.5°	895.5	858.3	830.1	809.1	793.8	786.9	778.6	774.6	768.6	763.8	763.0
45°	838.3	802.3	776.7	759.7	746.5	738.4	733.3	724.4	721.5	715.7	714.9
47.5°	784.1	749.6	724.3	710.5	698.9	692.3	684.2	675.3	672.0	669.0	668.7
50°	743.6	712.0	688.4	675.2	664.2	654.7	646.6	640.6	638.5	638.5	640.0
52.5°	702.4	675.5	655.5	639.3	629.0	618.8	611.3	607.8	604.4	607.9	610.6
55°	642.2	615.0	600.3	584.8	574.6	562.8	559.1	557.7	555.4	561.4	564.3
57.5°	578.3	559.3	542.1	526.8	517.6	510.8	505.8	504.9	509.1	511.8	521.3
60°	537.8	515.8	500.4	488.6	477.6	473.2	471.7	470.2	473.2	481.3	493.7
62.5°	493.1	475.2	458.6	449.8	441.7	434.4	434.0	435.0	440.8	450.1	462.6
65°	427.6	412.2	401.1	390.9	384.3	379.8	381.4	384.3	390.9	403.4	417.4
67.5°	361.1	350.4	340.6	332.2	325.9	325.9	327.4	331.8	339.6	354.0	366.7
70°	318.1	306.4	298.3	294.6	289.5	286.5	291.0	298.3	304.9	318.1	329.1
72.5°	275.2	265.2	258.9	256.5	254.2	251.8	253.4	261.3	270.2	283.4	296.2
75°	211.6	207.9	203.5	200.6	198.4	199.8	201.3	208.7	216.0	230.0	244.7
77.5°	154.5	150.6	148.0	147.2	146.1	146.8	150.9	156.4	163.5	173.7	184.8
80°	116.8	115.4	113.9	113.1	113.1	113.9	119.8	123.5	130.1	139.6	148.5
82.5°	85.1	84.2	83.9	83.8	84.4	84.5	88.0	92.8	98.3	105.5	113.1
85°	44.9	43.4	45.5	46.3	44.9	47.0	48.4	51.5	53.6	57.3	61.0
87.5°	16.4	18.1	17.7	18.8	18.9	20.5	20.2	22.7	24.1	25.5	25.4
90°	8.8	10.9	12.1	14.2	15.4	17.5	18.7	19.7	20.8	21.9	24.1
92.5°	57.9	89.8	149.6	250.0	358.8	353.1	285.9	194.1	140.8	106.0	89.8
95°	82.1	131.4	248.6	489.6	791.8	970.3	949.5	787.4	620.9	486.3	394.3
97.5°	101.2	136.7	214.2	390.8	707.1	1036.2	1201.5	1172.7	1056.0	924.8	796.8
100°	116.1	148.9	212.4	354.9	630.8	988.9	1262.7	1347.1	1293.5	1180.6	1066.7
102.5°	131.9	163.8	220.4	340.0	573.0	905.7	1226.0	1405.8	1438.9	1384.8	1307.7
105°	157.7	188.4	236.6	334.0	516.9	794.0	1108.3	1371.2	1521.3	1569.4	1557.4
107.5°	186.4	214.0	260.6	344.1	493.2	717.1	988.4	1247.6	1447.8	1571.6	1628.8
110°	204.8	233.3	278.1	353.7	486.3	681.2	919.9	1156.5	1364.6	1519.0	1612.1



TEST NUMBER: P333333-830

CATALOG NUMBER: S125DIP-S1270D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	224.0	251.7	294.8	366.0	486.3	660.2	869.1	1084.7	1282.2	1438.4	1548.1
115°	253.0	280.4	320.9	384.4	489.6	637.4	813.7	994.5	1164.2	1314.2	1433.6
117.5°	282.8	309.2	347.6	405.5	496.8	626.2	780.6	936.1	1082.5	1211.7	1321.3
120°	301.1	328.6	366.9	419.4	503.8	620.9	762.2	904.7	1036.0	1156.5	1252.9
122.5°	319.6	346.9	385.3	435.3	509.9	616.6	746.5	881.0	1002.8	1110.1	1200.3
125°	345.0	373.4	409.6	456.7	520.2	611.1	725.0	846.6	958.3	1053.6	1132.5
127.5°	369.8	398.2	433.0	476.5	531.8	608.5	705.3	811.5	915.8	1004.8	1078.6
130°	385.5	414.0	447.9	489.6	538.9	606.7	692.2	789.7	886.0	971.5	1042.6
132.5°	399.5	428.0	461.9	501.0	546.7	606.7	681.6	767.7	858.0	935.5	1004.1
135°	417.3	446.9	480.8	516.9	557.4	606.7	669.2	739.2	814.8	885.0	947.3
137.5°	432.8	463.3	494.2	528.8	567.3	608.0	658.0	715.2	776.3	834.5	887.6
140°	442.4	472.0	503.8	536.7	571.7	608.9	652.7	702.0	753.5	803.9	849.9
142.5°	452.1	479.9	509.9	541.0	574.3	609.8	648.4	690.6	734.2	777.6	817.5
145°	466.6	491.7	520.2	547.6	577.2	608.9	641.8	675.7	709.6	743.7	773.2
147.5°	479.7	501.8	526.8	551.6	578.2	606.1	635.0	661.8	689.3	715.4	737.7
150°	488.4	507.1	531.1	554.2	578.2	603.4	629.7	653.8	678.0	698.7	718.4
152.5°	496.3	513.2	535.6	555.9	577.4	599.9	623.6	645.1	666.6	685.6	701.0
155°	506.0	521.3	539.9	557.4	575.0	593.6	613.3	631.9	649.4	664.8	676.8
157.5°	516.0	527.6	543.7	558.6	572.1	587.0	603.7	618.8	633.2	645.1	654.5
160°	521.3	531.1	545.4	558.6	569.5	582.7	595.8	610.0	620.9	631.9	639.6
162.5°	526.6	534.7	547.1	557.7	566.8	577.4	588.8	600.4	610.5	619.6	626.4
165°	532.3	538.9	547.6	556.4	562.9	569.5	578.2	587.0	594.7	601.2	606.7
167.5°	536.2	540.4	547.6	553.7	556.8	561.8	568.0	574.3	579.4	584.4	588.3
170°	538.9	542.2	547.6	552.0	554.2	557.4	561.8	567.3	570.6	573.9	576.1
172.5°	540.5	542.2	546.7	550.3	550.6	552.2	555.7	559.4	562.7	565.1	566.5
175°	542.2	542.2	545.4	547.6	546.5	546.5	547.6	550.9	550.9	553.1	553.1
177.5°	542.3	542.3	544.1	545.0	543.2	543.2	544.1	545.0	545.8	545.8	545.8
180°	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2



TEST NUMBER: P333333-830

CATALOG NUMBER: S125DIP-S1270D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1
2.5°	1649.4	1653.4	1649.9	1654.6	1649.9	1653.4	1649.4	1652.8	1658.1	1654.6	1662.8
5°	1520.1	1513.5	1518.0	1515.0	1518.0	1513.5	1520.1	1523.8	1532.7	1535.6	1541.4
7.5°	1400.8	1394.5	1387.3	1383.9	1387.3	1394.5	1400.8	1403.1	1410.5	1421.5	1429.9
10°	1326.2	1318.1	1317.4	1312.2	1317.4	1318.1	1326.2	1334.3	1339.4	1353.4	1362.9
12.5°	1271.5	1264.0	1255.7	1253.5	1255.7	1264.0	1271.5	1278.5	1280.1	1295.8	1302.4
15°	1193.9	1188.1	1182.9	1187.3	1182.9	1188.1	1193.9	1198.3	1206.5	1217.5	1224.8
17.5°	1129.4	1124.5	1123.7	1118.2	1123.7	1124.5	1129.4	1131.9	1145.2	1152.4	1165.0
20°	1088.9	1085.2	1086.7	1077.1	1086.7	1085.2	1088.9	1095.5	1108.7	1112.4	1125.6
22.5°	1056.6	1049.3	1048.5	1046.6	1048.5	1049.3	1056.6	1062.5	1065.3	1076.6	1085.6
25°	1005.9	1002.2	998.5	1002.2	998.5	1002.2	1005.9	1012.5	1015.4	1023.5	1032.3
27.5°	961.6	957.2	956.2	956.6	956.2	957.2	961.6	961.0	968.9	975.4	981.9
30°	934.6	927.3	927.9	927.3	927.9	927.3	934.6	934.6	939.0	944.9	950.7
32.5°	905.2	900.2	899.2	897.9	899.2	900.2	905.2	904.0	909.6	916.6	923.1
35°	861.9	861.9	858.2	858.2	858.2	861.9	861.9	864.0	870.0	870.0	877.2
37.5°	821.1	820.4	818.2	818.5	818.2	820.4	821.1	822.9	824.9	828.0	832.7
40°	790.6	789.9	787.6	783.3	787.6	789.9	790.6	793.5	794.9	798.6	801.6
42.5°	761.2	758.7	757.6	756.2	757.6	758.7	761.2	763.0	763.8	768.6	774.6
45°	714.9	714.9	713.4	712.7	713.4	714.9	714.9	714.9	715.7	721.5	724.4
47.5°	670.0	671.3	674.0	673.6	674.0	671.3	670.0	668.7	669.0	672.0	675.3
50°	642.9	643.7	645.8	646.6	645.8	643.7	642.9	640.0	638.5	638.5	640.6
52.5°	612.9	617.2	620.0	619.5	620.0	617.2	612.9	610.6	607.9	604.4	607.8
55°	570.9	576.0	581.2	581.9	581.2	576.0	570.9	564.3	561.4	555.4	557.7
57.5°	529.3	536.5	542.0	543.7	542.0	536.5	529.3	521.3	511.8	509.1	504.9
60°	501.1	510.7	517.3	520.2	517.3	510.7	501.1	493.7	481.3	473.2	470.2
62.5°	474.0	484.7	491.3	492.0	491.3	484.7	474.0	462.6	450.1	440.8	435.0
65°	429.8	440.8	446.7	451.1	446.7	440.8	429.8	417.4	403.4	390.9	384.3
67.5°	382.2	393.2	399.7	403.2	399.7	393.2	382.2	366.7	354.0	339.6	331.8
70°	347.5	358.5	367.4	370.3	367.4	358.5	347.5	329.1	318.1	304.9	298.3
72.5°	313.4	323.3	330.4	333.8	330.4	323.3	313.4	296.2	283.4	270.2	261.3
75°	254.2	267.4	274.1	277.8	274.1	267.4	254.2	244.7	230.0	216.0	208.7
77.5°	196.0	208.1	212.1	214.0	212.1	208.1	196.0	184.8	173.7	163.5	156.4
80°	157.2	164.6	169.8	170.4	169.8	164.6	157.2	148.5	139.6	130.1	123.5
82.5°	120.8	127.0	128.6	130.4	128.6	127.0	120.8	113.1	105.5	98.3	92.8
85°	66.2	69.1	69.8	69.1	69.8	69.1	66.2	61.0	57.3	53.6	51.5
87.5°	26.6	26.0	26.2	27.3	26.2	26.0	26.6	25.4	25.5	24.1	22.7
90°	24.1	24.1	25.2	25.2	25.2	24.1	24.1	24.1	21.9	20.8	19.7
92.5°	75.8	73.1	71.6	69.8	71.6	73.1	75.8	89.8	106.0	140.8	194.1
95°	316.5	283.6	274.9	257.4	274.9	283.6	316.5	394.3	486.3	620.9	787.4
97.5°	729.2	667.9	636.1	622.1	636.1	667.9	729.2	796.8	924.8	1056.0	1172.7
100°	991.2	912.3	871.8	854.2	871.8	912.3	991.2	1066.7	1180.6	1293.5	1347.1
102.5°	1226.8	1170.7	1126.7	1113.6	1126.7	1170.7	1226.8	1307.7	1384.8	1438.9	1405.8
105°	1522.3	1486.2	1464.2	1451.1	1464.2	1486.2	1522.3	1557.4	1569.4	1521.3	1371.2
107.5°	1646.5	1646.3	1639.1	1630.3	1639.1	1646.3	1646.5	1628.8	1571.6	1447.8	1247.6
110°	1661.4	1682.2	1689.9	1689.9	1689.9	1682.2	1661.4	1612.1	1519.0	1364.6	1156.5



TEST NUMBER: P333333-830

CATALOG NUMBER: S125DIP-S1270D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1620.2	1656.0	1675.0	1682.9	1675.0	1656.0	1620.2	1548.1	1438.4	1282.2	1084.7
115°	1519.0	1571.6	1602.2	1616.5	1602.2	1571.6	1519.0	1433.6	1314.2	1164.2	994.5
117.5°	1406.7	1461.0	1491.5	1500.2	1491.5	1461.0	1406.7	1321.3	1211.7	1082.5	936.1
120°	1334.0	1386.5	1416.1	1424.8	1416.1	1386.5	1334.0	1252.9	1156.5	1036.0	904.7
122.5°	1272.6	1320.8	1350.4	1358.3	1350.4	1320.8	1272.6	1200.3	1110.1	1002.8	881.0
125°	1193.7	1238.7	1262.7	1273.8	1262.7	1238.7	1193.7	1132.5	1053.6	958.3	846.6
127.5°	1134.2	1173.8	1196.7	1201.5	1196.7	1173.8	1134.2	1078.6	1004.8	915.8	811.5
130°	1097.4	1133.5	1155.5	1162.0	1155.5	1133.5	1097.4	1042.6	971.5	886.0	789.7
132.5°	1058.9	1095.0	1115.1	1122.6	1115.1	1095.0	1058.9	1004.1	935.5	858.0	767.7
135°	995.5	1031.7	1051.4	1058.0	1051.4	1031.7	995.5	947.3	885.0	814.8	739.2
137.5°	930.7	963.6	981.8	988.9	981.8	963.6	930.7	887.6	834.5	776.3	715.2
140°	890.4	918.9	935.3	940.8	935.3	918.9	890.4	849.9	803.9	753.5	702.0
142.5°	851.9	875.9	891.5	896.1	891.5	875.9	851.9	817.5	777.6	734.2	690.6
145°	799.5	818.1	830.2	834.5	830.2	818.1	799.5	773.2	743.7	709.6	675.7
147.5°	758.6	773.5	780.4	782.4	780.4	773.5	758.6	737.7	715.4	689.3	661.8
150°	734.9	748.0	752.4	753.5	752.4	748.0	734.9	718.4	698.7	678.0	653.8
152.5°	714.7	725.2	729.6	730.8	729.6	725.2	714.7	701.0	685.6	666.6	645.1
155°	687.8	695.4	698.7	699.8	698.7	695.4	687.8	676.8	664.8	649.4	631.9
157.5°	663.0	669.4	672.4	672.2	672.4	669.4	663.0	654.5	645.1	633.2	618.8
160°	647.2	652.7	655.0	653.8	655.0	652.7	647.2	639.6	631.9	620.9	610.0
162.5°	632.4	637.0	637.4	637.2	637.4	637.0	632.4	626.4	619.6	610.5	600.4
165°	611.1	613.3	613.3	613.3	613.3	613.3	611.1	606.7	601.2	594.7	587.0
167.5°	590.5	592.5	591.6	591.4	591.6	592.5	590.5	588.3	584.4	579.4	574.3
170°	578.2	579.4	579.4	578.2	579.4	579.4	578.2	576.1	573.9	570.6	567.3
172.5°	566.8	568.8	567.1	566.0	567.1	568.8	566.8	566.5	565.1	562.7	559.4
175°	553.1	554.2	552.0	550.9	552.0	554.2	553.1	553.1	553.1	550.9	550.9
177.5°	545.0	545.8	543.2	543.2	543.2	545.8	545.0	545.8	545.8	545.8	545.0
180°	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2



TEST NUMBER: P333333-830

CATALOG NUMBER: S125DIP-S1270D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1
2.5°	1655.2	1662.3	1671.0	1677.5	1689.3	1694.6	1701.0	1706.4	1715.7	1724.6	1735.1
5°	1543.7	1556.1	1573.1	1591.4	1612.8	1627.4	1648.0	1660.5	1685.5	1708.3	1730.3
7.5°	1442.6	1457.8	1481.8	1505.3	1533.2	1558.5	1584.2	1612.8	1644.6	1682.2	1713.4
10°	1373.2	1393.8	1419.5	1448.9	1482.7	1512.1	1546.6	1577.4	1616.4	1660.5	1701.7
12.5°	1318.0	1335.6	1364.2	1392.5	1428.6	1464.4	1500.2	1541.1	1586.4	1635.2	1687.0
15°	1241.7	1256.4	1279.9	1318.8	1355.6	1390.8	1444.4	1482.7	1540.0	1594.4	1656.8
17.5°	1176.6	1194.9	1214.7	1248.0	1286.1	1330.1	1378.1	1426.0	1481.2	1550.1	1620.5
20°	1136.6	1151.3	1174.1	1199.9	1240.2	1284.3	1329.8	1378.4	1446.0	1517.2	1592.9
22.5°	1093.2	1109.0	1134.7	1162.8	1196.7	1239.1	1289.3	1342.5	1413.1	1483.1	1565.3
25°	1041.9	1052.9	1076.4	1101.4	1135.2	1171.2	1223.3	1282.1	1351.9	1432.0	1515.8
27.5°	993.5	1003.2	1024.6	1046.4	1076.9	1119.7	1166.3	1225.7	1291.5	1372.6	1465.5
30°	958.8	969.1	988.3	1011.7	1041.1	1078.6	1126.3	1182.2	1252.7	1332.1	1429.1
32.5°	928.9	937.9	952.3	975.9	1004.7	1040.9	1085.2	1142.2	1212.8	1293.3	1388.5
35°	882.4	892.7	903.7	922.1	947.1	982.3	1030.9	1084.5	1152.1	1229.9	1317.4
37.5°	836.3	847.4	857.2	873.7	896.5	927.7	969.6	1025.4	1086.6	1161.6	1245.5
40°	807.5	816.2	824.3	842.0	864.8	894.2	933.1	983.1	1047.7	1117.6	1187.3
42.5°	778.6	786.9	793.8	809.1	830.1	858.3	895.5	944.2	1004.3	1069.3	1130.9
45°	733.3	738.4	746.5	759.7	776.7	802.3	838.3	881.7	932.4	994.1	1040.4
47.5°	684.2	692.3	698.9	710.5	724.3	749.6	784.1	821.0	867.0	912.9	945.5
50°	646.6	654.7	664.2	675.2	688.4	712.0	743.6	781.0	819.9	855.3	883.2
52.5°	611.3	618.8	629.0	639.3	655.5	675.5	702.4	735.7	774.1	799.4	822.7
55°	559.1	562.8	574.6	584.8	600.3	615.0	642.2	671.6	695.0	714.2	733.3
57.5°	505.8	510.8	517.6	526.8	542.1	559.3	578.3	604.4	618.2	628.0	642.9
60°	471.7	473.2	477.6	488.6	500.4	515.8	537.8	556.2	566.5	574.6	587.0
62.5°	434.0	434.4	441.7	449.8	458.6	475.2	493.1	508.0	516.5	520.5	532.3
65°	381.4	379.8	384.3	390.9	401.1	412.2	427.6	440.8	440.1	444.5	451.9
67.5°	327.4	325.9	325.9	332.2	340.6	350.4	361.1	368.7	368.8	374.8	378.4
70°	291.0	286.5	289.5	294.6	298.3	306.4	318.1	321.1	321.8	324.7	328.4
72.5°	253.4	251.8	254.2	256.5	258.9	265.2	275.2	277.0	277.1	278.9	284.9
75°	201.3	199.8	198.4	200.6	203.5	207.9	211.6	214.5	213.8	214.5	219.0
77.5°	150.9	146.8	146.1	147.2	148.0	150.6	154.5	154.1	154.9	154.8	159.8
80°	119.8	113.9	113.1	113.1	113.9	115.4	116.8	118.3	116.1	118.3	119.8
82.5°	88.0	84.5	84.4	83.8	83.9	84.2	85.1	86.0	85.5	86.5	87.5
85°	48.4	47.0	44.9	46.3	45.5	43.4	44.9	42.6	41.8	42.6	43.4
87.5°	20.2	20.5	18.9	18.8	17.7	18.1	16.4	15.5	14.4	14.5	16.1
90°	18.7	17.5	15.4	14.2	12.1	10.9	8.8	6.6	4.3	2.2	1.1
92.5°	285.9	353.1	358.8	250.0	149.6	89.8	57.9	39.0	25.4	16.2	13.4
95°	949.5	970.3	791.8	489.6	248.6	131.4	82.1	58.1	46.0	37.2	36.1
97.5°	1201.5	1036.2	707.1	390.8	214.2	136.7	101.2	79.6	67.5	61.4	60.0
100°	1262.7	988.9	630.8	354.9	212.4	148.9	116.1	95.3	83.2	78.9	76.6
102.5°	1226.0	905.7	573.0	340.0	220.4	163.8	131.9	112.8	99.9	96.4	95.1
105°	1108.3	794.0	516.9	334.0	236.6	188.4	157.7	140.2	129.2	123.8	123.8
107.5°	988.4	717.1	493.2	344.1	260.6	214.0	186.4	168.2	159.2	154.0	151.7
110°	919.9	681.2	486.3	353.7	278.1	233.3	204.8	188.4	178.5	174.2	171.9



TEST NUMBER: P333333-830

CATALOG NUMBER: S125DIP-S1270D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	869.1	660.2	486.3	366.0	294.8	251.7	224.0	207.6	197.7	194.3	192.1
115°	813.7	637.4	489.6	384.4	320.9	280.4	253.0	236.6	226.7	223.4	221.2
117.5°	780.6	626.2	496.8	405.5	347.6	309.2	282.8	264.2	254.3	250.8	247.5
120°	762.2	620.9	503.8	419.4	366.9	328.6	301.1	282.6	272.7	268.3	265.0
122.5°	746.5	616.6	509.9	435.3	385.3	346.9	319.6	299.2	289.4	285.9	283.4
125°	725.0	611.1	520.2	456.7	409.6	373.4	345.0	324.1	314.3	308.9	306.6
127.5°	705.3	608.5	531.8	476.5	433.0	398.2	369.8	347.6	335.2	328.1	324.8
130°	692.2	606.7	538.9	489.6	447.9	414.0	385.5	362.5	348.3	339.5	336.2
132.5°	681.6	606.7	546.7	501.0	461.9	428.0	399.5	375.7	359.7	349.1	345.0
135°	669.2	606.7	557.4	516.9	480.8	446.9	417.3	394.3	376.7	363.6	359.2
137.5°	658.0	608.0	567.3	528.8	494.2	463.3	432.8	410.3	392.8	380.5	377.2
140°	652.7	608.9	571.7	536.7	503.8	472.0	442.4	421.7	404.2	391.0	387.7
142.5°	648.4	609.8	574.3	541.0	509.9	479.9	452.1	432.2	414.6	402.4	399.9
145°	641.8	608.9	577.2	547.6	520.2	491.7	466.6	446.9	431.5	420.6	418.4
147.5°	635.0	606.1	578.2	551.6	526.8	501.8	479.7	462.6	448.4	438.9	437.6
150°	629.7	603.4	578.2	554.2	531.1	507.1	488.4	473.2	458.9	451.2	449.0
152.5°	623.6	599.9	577.4	555.9	535.6	513.2	496.3	481.9	469.4	462.6	461.3
155°	613.3	593.6	575.0	557.4	539.9	521.3	506.0	495.0	484.1	477.5	477.5
157.5°	603.7	587.0	572.1	558.6	543.7	527.6	516.0	506.4	497.0	491.7	492.0
160°	595.8	582.7	569.5	558.6	545.4	531.1	521.3	512.6	504.9	500.5	501.6
162.5°	588.8	577.4	566.8	557.7	547.1	534.7	526.6	519.5	512.7	508.4	509.4
165°	578.2	569.5	562.9	556.4	547.6	538.9	532.3	527.9	522.5	519.2	521.3
167.5°	568.0	561.8	556.8	553.7	547.6	540.4	536.2	533.1	530.1	528.1	529.2
170°	561.8	557.4	554.2	552.0	547.6	542.2	538.9	536.7	534.4	533.4	534.4
172.5°	555.7	552.2	550.6	550.3	546.7	542.2	540.5	539.2	537.1	536.0	538.0
175°	547.6	546.5	546.5	547.6	545.4	542.2	542.2	542.2	541.0	539.9	542.2
177.5°	544.1	543.2	543.2	545.0	544.1	542.3	542.3	543.2	542.3	542.3	544.1
180°	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2



TEST NUMBER: P333333-830

CATALOG NUMBER: S125DIP-S1270D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1
2.5°	1740.4	1748.7	1754.0	1764.0	1772.2	1776.9	1781.0	1784.5	1788.7	1792.2	1802.1
5°	1751.6	1770.7	1786.9	1811.8	1834.7	1852.3	1871.3	1888.3	1902.2	1922.0	1937.5
7.5°	1746.7	1780.7	1816.3	1854.9	1894.4	1931.2	1965.0	1996.6	2025.2	2059.9	2090.3
10°	1742.0	1788.4	1833.9	1886.0	1939.7	1985.3	2027.9	2071.2	2102.8	2146.9	2184.3
12.5°	1738.5	1793.0	1848.0	1910.7	1969.6	2034.0	2090.7	2122.3	2170.4	2205.6	2250.2
15°	1723.7	1795.7	1871.3	1941.9	2025.6	2085.2	2135.1	2196.9	2241.6	2286.5	2335.0
17.5°	1697.0	1778.7	1863.3	1955.7	2036.1	2100.0	2164.4	2223.9	2277.4	2337.5	2397.8
20°	1684.7	1766.3	1863.3	1958.0	2036.6	2103.6	2169.6	2235.1	2293.9	2371.0	2440.8
22.5°	1658.9	1757.5	1846.8	1939.3	2020.2	2092.9	2167.9	2242.1	2320.3	2407.4	2494.8
25°	1612.8	1712.7	1807.4	1898.6	1980.1	2071.2	2151.3	2250.5	2350.4	2465.8	2574.5
27.5°	1564.8	1660.5	1747.4	1835.3	1930.4	2033.6	2137.5	2250.0	2380.9	2526.5	2679.8
30°	1526.1	1616.4	1700.9	1791.3	1890.5	2006.6	2120.4	2254.2	2405.6	2569.4	2751.6
32.5°	1480.7	1564.1	1646.2	1741.9	1849.9	1972.5	2105.2	2251.8	2433.7	2619.9	2807.5
35°	1403.4	1473.1	1557.6	1659.7	1781.7	1922.0	2075.7	2249.0	2457.7	2671.4	2829.4
37.5°	1311.5	1376.5	1465.5	1577.4	1705.3	1856.0	2038.2	2243.9	2465.5	2635.9	2686.9
40°	1249.8	1310.0	1402.6	1518.7	1649.4	1808.9	2008.7	2226.3	2440.8	2549.5	2507.6
42.5°	1183.9	1247.2	1337.4	1452.3	1593.1	1766.6	1971.7	2189.2	2369.1	2410.2	2265.5
45°	1080.1	1145.5	1234.4	1350.5	1501.8	1689.9	1903.7	2101.3	2204.9	2130.7	1906.7
47.5°	983.5	1044.8	1127.2	1247.0	1403.2	1597.7	1803.6	1961.3	1969.5	1792.4	1553.1
50°	917.7	974.2	1057.2	1177.0	1332.1	1529.0	1714.9	1839.0	1783.2	1582.6	1352.6
52.5°	853.0	908.4	990.2	1108.9	1262.2	1442.6	1615.5	1702.7	1597.4	1391.6	1195.1
55°	759.7	808.2	888.3	997.8	1143.2	1310.8	1457.7	1487.8	1351.1	1148.4	988.9
57.5°	668.6	713.9	786.7	887.6	1020.6	1168.9	1283.8	1277.4	1132.9	958.9	832.5
60°	606.9	651.0	715.7	814.1	935.3	1063.2	1161.6	1138.1	994.9	845.0	738.4
62.5°	551.7	591.0	652.1	738.3	848.9	967.3	1048.2	1013.5	873.2	742.1	657.9
65°	470.2	503.3	555.4	629.0	720.8	818.5	880.9	836.1	716.3	614.3	546.7
67.5°	392.5	419.0	462.7	521.3	599.6	678.2	716.2	671.1	575.3	500.8	450.7
70°	343.1	366.6	400.4	452.6	520.9	587.0	615.7	575.3	493.0	429.0	393.0
72.5°	293.8	313.1	342.8	389.7	444.5	501.8	527.0	488.3	420.8	366.7	333.1
75°	227.1	240.3	260.8	293.1	336.5	382.1	396.1	362.2	318.9	278.4	256.5
77.5°	162.5	173.7	189.3	209.7	240.4	269.4	281.5	262.0	228.5	202.9	184.8
80°	124.9	130.8	144.0	160.9	185.1	203.5	211.6	199.2	175.6	156.5	142.5
82.5°	89.1	94.9	102.8	116.8	132.2	144.8	153.4	145.1	128.0	113.0	104.9
85°	43.4	47.0	51.5	57.3	69.1	76.4	75.7	70.5	63.9	58.1	53.6
87.5°	15.7	16.8	18.9	22.3	24.5	27.1	28.7	27.7	25.8	24.3	22.7
90°	2.2	4.3	6.6	8.8	10.9	12.1	14.2	15.4	17.5	18.7	19.7
92.5°	16.2	25.4	39.0	57.9	89.8	149.6	250.0	358.8	353.1	285.9	194.1
95°	37.2	46.0	58.1	82.1	131.4	248.6	489.6	791.8	970.3	949.5	787.4
97.5°	61.4	67.5	79.6	101.2	136.7	214.2	390.8	707.1	1036.2	1201.5	1172.7
100°	78.9	83.2	95.3	116.1	148.9	212.4	354.9	630.8	988.9	1262.7	1347.1
102.5°	96.4	99.9	112.8	131.9	163.8	220.4	340.0	573.0	905.7	1226.0	1405.8
105°	123.8	129.2	140.2	157.7	188.4	236.6	334.0	516.9	794.0	1108.3	1371.2
107.5°	154.0	159.2	168.2	186.4	214.0	260.6	344.1	493.2	717.1	988.4	1247.6
110°	174.2	178.5	188.4	204.8	233.3	278.1	353.7	486.3	681.2	919.9	1156.5



TEST NUMBER: P333333-830

CATALOG NUMBER: S125DIP-S1270D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	194.3	197.7	207.6	224.0	251.7	294.8	366.0	486.3	660.2	869.1	1084.7
115°	223.4	226.7	236.6	253.0	280.4	320.9	384.4	489.6	637.4	813.7	994.5
117.5°	250.8	254.3	264.2	282.8	309.2	347.6	405.5	496.8	626.2	780.6	936.1
120°	268.3	272.7	282.6	301.1	328.6	366.9	419.4	503.8	620.9	762.2	904.7
122.5°	285.9	289.4	299.2	319.6	346.9	385.3	435.3	509.9	616.6	746.5	881.0
125°	308.9	314.3	324.1	345.0	373.4	409.6	456.7	520.2	611.1	725.0	846.6
127.5°	328.1	335.2	347.6	369.8	398.2	433.0	476.5	531.8	608.5	705.3	811.5
130°	339.5	348.3	362.5	385.5	414.0	447.9	489.6	538.9	606.7	692.2	789.7
132.5°	349.1	359.7	375.7	399.5	428.0	461.9	501.0	546.7	606.7	681.6	767.7
135°	363.6	376.7	394.3	417.3	446.9	480.8	516.9	557.4	606.7	669.2	739.2
137.5°	380.5	392.8	410.3	432.8	463.3	494.2	528.8	567.3	608.0	658.0	715.2
140°	391.0	404.2	421.7	442.4	472.0	503.8	536.7	571.7	608.9	652.7	702.0
142.5°	402.4	414.6	432.2	452.1	479.9	509.9	541.0	574.3	609.8	648.4	690.6
145°	420.6	431.5	446.9	466.6	491.7	520.2	547.6	577.2	608.9	641.8	675.7
147.5°	438.9	448.4	462.6	479.7	501.8	526.8	551.6	578.2	606.1	635.0	661.8
150°	451.2	458.9	473.2	488.4	507.1	531.1	554.2	578.2	603.4	629.7	653.8
152.5°	462.6	469.4	481.9	496.3	513.2	535.6	555.9	577.4	599.9	623.6	645.1
155°	477.5	484.1	495.0	506.0	521.3	539.9	557.4	575.0	593.6	613.3	631.9
157.5°	491.7	497.0	506.4	516.0	527.6	543.7	558.6	572.1	587.0	603.7	618.8
160°	500.5	504.9	512.6	521.3	531.1	545.4	558.6	569.5	582.7	595.8	610.0
162.5°	508.4	512.7	519.5	526.6	534.7	547.1	557.7	566.8	577.4	588.8	600.4
165°	519.2	522.5	527.9	532.3	538.9	547.6	556.4	562.9	569.5	578.2	587.0
167.5°	528.1	530.1	533.1	536.2	540.4	547.6	553.7	556.8	561.8	568.0	574.3
170°	533.4	534.4	536.7	538.9	542.2	547.6	552.0	554.2	557.4	561.8	567.3
172.5°	536.0	537.1	539.2	540.5	542.2	546.7	550.3	550.6	552.2	555.7	559.4
175°	539.9	541.0	542.2	542.2	542.2	545.4	547.6	546.5	546.5	547.6	550.9
177.5°	542.3	542.3	543.2	542.3	542.3	544.1	545.0	543.2	543.2	544.1	545.0
180°	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2



TEST NUMBER: P333333-830

CATALOG NUMBER: S125DIP-S1270D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1
2.5°	1810.3	1815.1	1825.0	1821.6	1826.3	1828.6	1831.0
5°	1956.6	1980.1	1990.4	1989.0	2004.3	2000.6	1997.0
7.5°	2121.8	2146.5	2160.3	2177.5	2187.5	2188.2	2196.9
10°	2215.3	2247.6	2260.8	2279.2	2290.9	2297.5	2296.8
12.5°	2286.9	2312.2	2341.8	2350.9	2366.7	2375.1	2372.0
15°	2373.2	2413.6	2444.5	2459.8	2479.7	2485.6	2493.7
17.5°	2450.2	2504.4	2540.4	2588.3	2606.4	2617.4	2610.9
20°	2508.4	2579.6	2615.6	2673.0	2704.5	2721.5	2715.6
22.5°	2577.2	2654.3	2720.8	2770.5	2818.6	2841.4	2846.1
25°	2695.0	2800.8	2898.5	2963.9	3023.4	3037.3	3068.3
27.5°	2826.7	2951.4	3055.9	3124.7	3166.1	3181.6	3191.4
30°	2909.5	3033.7	3112.4	3156.4	3169.7	3168.2	3166.7
32.5°	2950.1	3027.8	3043.0	3030.7	3000.4	2974.8	2948.1
35°	2892.7	2834.6	2747.9	2636.2	2553.9	2470.9	2462.9
37.5°	2601.5	2415.9	2271.6	2110.4	2017.4	1960.0	1920.3
40°	2327.6	2116.8	1941.9	1806.0	1711.2	1673.8	1637.0
42.5°	2030.2	1828.7	1673.9	1560.3	1489.0	1447.5	1418.3
45°	1649.4	1471.7	1350.5	1268.2	1211.5	1179.2	1160.8
47.5°	1351.6	1220.1	1117.1	1057.7	1018.6	993.5	993.6
50°	1191.8	1066.1	997.8	950.7	916.9	897.1	900.8
52.5°	1050.1	956.2	897.9	858.5	833.5	821.2	820.9
55°	878.0	810.4	772.2	743.6	726.6	712.7	715.7
57.5°	751.0	694.0	668.5	644.7	632.9	627.4	619.3
60°	672.3	628.2	606.1	587.0	575.3	570.9	562.8
62.5°	602.4	567.7	546.2	530.7	520.0	518.6	512.3
65°	506.2	479.8	460.7	453.4	442.3	439.4	439.4
67.5°	417.4	398.4	383.5	376.7	371.9	372.7	369.1
70°	361.5	346.1	336.5	329.1	325.5	326.2	323.3
72.5°	316.2	299.1	290.7	286.3	281.4	283.3	282.1
75°	239.5	230.7	226.3	221.9	219.0	217.4	216.0
77.5°	175.9	168.1	164.8	162.2	162.7	159.1	161.9
80°	135.9	129.3	127.1	123.5	122.7	122.7	122.0
82.5°	99.4	95.8	94.2	91.1	89.8	91.0	89.1
85°	51.5	48.4	47.8	47.8	46.3	44.9	48.4
87.5°	23.0	20.8	21.3	20.7	20.7	20.4	19.1
90°	20.8	21.9	24.1	24.1	24.1	25.2	25.2
92.5°	140.8	106.0	89.8	75.8	73.1	71.6	69.8
95°	620.9	486.3	394.3	316.5	283.6	274.9	257.4
97.5°	1056.0	924.8	796.8	729.2	667.9	636.1	622.1
100°	1293.5	1180.6	1066.7	991.2	912.3	871.8	854.2
102.5°	1438.9	1384.8	1307.7	1226.8	1170.7	1126.7	1113.6
105°	1521.3	1569.4	1557.4	1522.3	1486.2	1464.2	1451.1
107.5°	1447.8	1571.6	1628.8	1646.5	1646.3	1639.1	1630.3
110°	1364.6	1519.0	1612.1	1661.4	1682.2	1689.9	1689.9



TEST NUMBER: P333333-830

CATALOG NUMBER: S125DIP-S1270D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1282.2	1438.4	1548.1	1620.2	1656.0	1675.0	1682.9
115°	1164.2	1314.2	1433.6	1519.0	1571.6	1602.2	1616.5
117.5°	1082.5	1211.7	1321.3	1406.7	1461.0	1491.5	1500.2
120°	1036.0	1156.5	1252.9	1334.0	1386.5	1416.1	1424.8
122.5°	1002.8	1110.1	1200.3	1272.6	1320.8	1350.4	1358.3
125°	958.3	1053.6	1132.5	1193.7	1238.7	1262.7	1273.8
127.5°	915.8	1004.8	1078.6	1134.2	1173.8	1196.7	1201.5
130°	886.0	971.5	1042.6	1097.4	1133.5	1155.5	1162.0
132.5°	858.0	935.5	1004.1	1058.9	1095.0	1115.1	1122.6
135°	814.8	885.0	947.3	995.5	1031.7	1051.4	1058.0
137.5°	776.3	834.5	887.6	930.7	963.6	981.8	988.9
140°	753.5	803.9	849.9	890.4	918.9	935.3	940.8
142.5°	734.2	777.6	817.5	851.9	875.9	891.5	896.1
145°	709.6	743.7	773.2	799.5	818.1	830.2	834.5
147.5°	689.3	715.4	737.7	758.6	773.5	780.4	782.4
150°	678.0	698.7	718.4	734.9	748.0	752.4	753.5
152.5°	666.6	685.6	701.0	714.7	725.2	729.6	730.8
155°	649.4	664.8	676.8	687.8	695.4	698.7	699.8
157.5°	633.2	645.1	654.5	663.0	669.4	672.4	672.2
160°	620.9	631.9	639.6	647.2	652.7	655.0	653.8
162.5°	610.5	619.6	626.4	632.4	637.0	637.4	637.2
165°	594.7	601.2	606.7	611.1	613.3	613.3	613.3
167.5°	579.4	584.4	588.3	590.5	592.5	591.6	591.4
170°	570.6	573.9	576.1	578.2	579.4	579.4	578.2
172.5°	562.7	565.1	566.5	566.8	568.8	567.1	566.0
175°	550.9	553.1	553.1	553.1	554.2	552.0	550.9
177.5°	545.8	545.8	545.8	545.0	545.8	543.2	543.2
180°	543.2	543.2	543.2	543.2	543.2	543.2	543.2

(END OF REPORT)