

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333132-935

Luminaire Tested: **S125DIP-S375D590U935-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333132-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S375D590U935-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3137.0 lumens
Efficiency: N/A
Efficacy: 122.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333132-935

CATALOG NUMBER: S125DIP-S375D590U935-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333132-935

CATALOG NUMBER: S125DIP-S375D590U935-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42
1	96	92	88	84	87	84	80	77	69	67	64	55	54	52	43	42	41	35
2	87	80	74	69	79	73	68	63	60	57	53	49	46	44	38	36	34	29
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	33	31	29	25
4	73	62	54	48	66	57	50	45	47	42	38	38	34	32	30	27	25	21
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22	18
6	61	49	41	36	56	45	38	33	38	33	29	31	27	24	24	21	19	16
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	40	33	28	48	37	30	26	31	26	22	26	22	19	20	17	15	13
9	49	37	29	24	45	34	27	23	29	23	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3249	3249	3249
5°	3255	3225	3245
10°	3236	3202	3220
15°	3201	3163	3177
20°	3151	3110	3115
25°	3096	3046	3043
30°	3030	2976	2961
35°	2958	2902	2861
40°	2885	2822	2780
45°	2806	2747	2693
50°	2719	2659	2579
55°	2634	2558	2486
60°	2533	2457	2370
65°	2415	2335	2257
70°	2298	2194	2119
75°	2094	2026	1956
80°	1863	1834	1789
85°	1623	1652	1564



TEST NUMBER: P333132-935

CATALOG NUMBER: S125DIP-S375D590U935-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.4	1.5
10°-20°	134.0	4.3
20°-30°	197.8	6.3
30°-40°	230.8	7.4
40°-50°	231.8	7.4
50°-60°	203.5	6.5
60°-70°	151.6	4.8
70°-80°	86.7	2.8
80°-90°	26.6	0.8
90°-100°	176.6	5.6
100°-110°	379.6	12.1
110°-120°	356.2	11.4
120°-130°	288.7	9.2
130°-140°	231.7	7.4
140°-150°	174.8	5.6
150°-160°	123.1	3.9
160°-170°	72.5	2.3
170°-180°	23.6	0.8
0°-30°	379.2	12.1
0°-40°	610.0	19.4
0°-60°	1045.3	33.3
0°-90°	1310.2	41.8
90°-120°	912.4	29.1
90°-150°	1607.6	51.2
90°-180°	1827.0	58.2
0°-180°	3137.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	503	503	503	503	503	
5°	502	501	497	501	501	48
15°	479	477	473	475	475	135
25°	434	432	427	428	427	200
35°	375	373	368	366	363	235
45°	307	305	301	296	295	237
55°	234	232	227	224	221	209
65°	158	157	153	149	148	157
75°	84	83	81	80	78	89
85°	22	22	22	22	21	24
90°	0	4	8	10	11	2
95°	16	48	435	197	116	17
105°	56	78	356	701	651	59
115°	99	120	286	616	725	98
125°	138	161	274	490	571	122
135°	161	194	272	411	474	125
145°	188	215	273	340	374	118
155°	214	230	266	301	314	99
165°	234	240	255	271	275	66
175°	243	243	245	248	247	23
180°	244	244	244	244	244	



TEST NUMBER: P333132-935

CATALOG NUMBER: S125DIP-S375D590U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	503.0	503.0	503.0	503.0	503.0	503.0	503.0	503.0	503.0	503.0	503.0
2.5°	504.2	504.0	503.9	503.6	503.4	502.9	502.2	501.5	500.8	500.1	500.8
5°	502.1	502.0	501.8	501.6	501.4	500.9	500.1	499.2	498.3	497.4	498.2
7.5°	497.6	497.4	497.2	497.1	496.9	496.3	495.3	494.3	493.4	492.4	493.2
10°	493.4	493.3	493.1	492.9	492.8	492.1	491.2	490.2	489.2	488.3	489.0
12.5°	488.4	488.0	487.7	487.4	487.1	486.5	485.5	484.7	483.7	482.8	483.4
15°	478.7	478.5	478.2	477.9	477.6	477.0	476.0	475.1	474.1	473.1	473.6
17.5°	467.6	467.3	466.8	466.5	466.1	465.4	464.3	463.4	462.4	461.3	461.9
20°	458.4	458.2	458.1	457.9	457.7	457.0	455.9	454.7	453.6	452.5	453.1
22.5°	449.2	448.8	448.5	448.2	447.9	447.2	446.1	445.1	443.9	442.9	443.3
25°	434.5	434.1	433.6	433.2	432.7	432.0	430.8	429.6	428.5	427.4	427.6
27.5°	417.4	417.2	416.9	416.6	416.4	415.6	414.5	413.3	412.1	410.9	411.0
30°	406.3	406.0	405.7	405.4	405.2	404.4	403.1	401.7	400.5	399.1	398.9
32.5°	394.2	393.7	393.4	393.0	392.5	391.8	390.5	389.3	388.2	387.0	386.7
35°	375.2	374.9	374.5	374.2	373.8	373.0	371.8	370.6	369.3	368.1	367.6
37.5°	355.6	355.2	354.7	354.2	353.8	353.0	351.8	350.7	349.5	348.4	347.7
40°	342.2	341.7	341.3	340.9	340.4	339.6	338.4	337.2	335.9	334.7	333.9
42.5°	327.9	327.5	327.2	326.7	326.4	325.6	324.3	323.1	321.8	320.6	319.9
45°	307.2	306.9	306.5	306.2	305.7	305.1	304.0	303.0	301.9	300.8	299.8
47.5°	284.9	284.9	284.9	285.0	285.0	284.4	283.1	281.8	280.5	279.2	278.2
50°	270.6	270.4	270.1	269.8	269.5	268.9	267.8	266.7	265.7	264.6	263.5
52.5°	256.0	255.7	255.5	255.4	255.2	254.5	253.4	252.3	251.1	249.9	249.0
55°	233.9	233.7	233.4	233.2	232.9	232.1	230.9	229.7	228.4	227.2	226.4
57.5°	210.9	210.7	210.5	210.4	210.3	209.7	208.6	207.6	206.6	205.5	204.5
60°	196.1	195.8	195.4	195.1	194.8	194.1	193.1	192.2	191.1	190.2	189.3
62.5°	180.9	180.6	180.3	180.0	179.8	179.2	178.4	177.5	176.7	175.9	175.0
65°	158.0	157.8	157.6	157.5	157.3	156.7	155.8	154.7	153.8	152.8	152.0
67.5°	135.8	135.4	135.0	134.7	134.3	133.7	133.0	132.2	131.6	130.9	130.2
70°	121.7	121.3	120.9	120.5	120.0	119.3	118.6	117.8	117.0	116.2	115.6
72.5°	106.5	106.2	105.9	105.6	105.3	104.9	104.4	103.8	103.3	102.8	102.2
75°	83.9	83.8	83.6	83.4	83.3	82.9	82.5	82.1	81.6	81.2	80.9
77.5°	63.2	63.1	63.0	62.9	62.9	62.8	62.5	62.3	62.0	61.7	61.6
80°	50.1	50.1	50.1	50.1	50.1	50.0	49.9	49.7	49.5	49.3	49.2
82.5°	38.7	38.6	38.4	38.2	38.1	38.1	38.0	38.0	37.9	37.9	37.7
85°	21.9	22.0	22.0	22.1	22.2	22.3	22.3	22.3	22.3	22.3	22.2
87.5°	8.7	8.8	9.0	9.2	9.4	9.6	9.6	9.7	9.7	9.8	10.0
90°	0.5	0.9	2.0	2.9	4.0	4.9	5.4	6.4	6.9	7.8	8.4
92.5°	6.0	7.2	11.4	17.5	25.9	40.3	67.1	112.1	160.9	158.3	128.2
95°	16.2	16.7	20.7	26.0	36.9	59.0	111.5	219.6	355.1	435.1	425.9
97.5°	26.9	27.5	30.2	35.6	45.4	61.3	96.1	175.2	317.1	464.7	538.8
100°	34.4	35.4	37.4	42.7	52.1	66.8	95.3	159.1	282.9	443.5	566.3
102.5°	42.6	43.2	44.8	50.6	59.2	73.4	98.8	152.5	256.9	406.1	549.7
105°	55.5	55.5	57.9	62.9	70.7	84.5	106.1	149.8	231.8	356.1	497.1
107.5°	68.1	69.1	71.4	75.4	83.6	96.0	116.9	154.3	221.2	321.6	443.2
110°	77.1	78.1	80.1	84.5	91.9	104.6	124.8	158.6	218.1	305.5	412.6



TEST NUMBER: P333132-935

CATALOG NUMBER: S125DIP-S375D590U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	86.2	87.1	88.7	93.2	100.5	112.9	132.2	164.1	218.1	296.1	389.8
115°	99.2	100.2	101.7	106.1	113.5	125.7	143.9	172.4	219.6	285.9	364.9
117.5°	111.0	112.4	114.1	118.5	126.8	138.7	155.9	181.8	222.7	280.9	350.1
120°	118.8	120.4	122.3	126.7	135.1	147.3	164.5	188.1	225.9	278.4	341.8
122.5°	127.1	128.2	129.8	134.1	143.4	155.6	172.8	195.2	228.7	276.6	334.8
125°	137.5	138.5	140.9	145.3	154.7	167.5	183.7	204.8	233.3	274.1	325.1
127.5°	145.7	147.1	150.3	155.9	165.8	178.6	194.2	213.6	238.5	272.9	316.3
130°	150.8	152.2	156.2	162.6	172.9	185.6	200.9	219.6	241.7	272.1	310.4
132.5°	154.7	156.6	161.3	168.5	179.2	191.9	207.2	224.6	245.2	272.1	305.7
135°	161.1	163.1	168.9	176.8	187.1	200.4	215.6	231.8	249.9	272.1	300.1
137.5°	169.2	170.7	176.2	184.0	194.1	207.8	221.6	237.1	254.4	272.7	295.1
140°	173.8	175.3	181.2	189.1	198.5	211.7	225.9	240.6	256.4	273.1	292.7
142.5°	179.3	180.5	186.0	193.8	202.8	215.2	228.7	242.6	257.5	273.5	290.8
145°	187.6	188.6	193.5	200.4	209.2	220.5	233.3	245.6	258.8	273.1	287.8
147.5°	196.2	196.8	201.0	207.4	215.1	225.1	236.3	247.4	259.3	271.8	284.7
150°	201.4	202.3	205.8	212.2	219.0	227.4	238.2	248.5	259.3	270.6	282.4
152.5°	206.9	207.4	210.5	216.1	222.6	230.1	240.1	249.3	258.9	269.1	279.7
155°	214.1	214.1	217.1	222.0	226.9	233.8	242.1	249.9	257.9	266.2	275.0
157.5°	220.6	220.5	222.9	227.1	231.4	236.6	243.8	250.5	256.6	263.2	270.7
160°	225.0	224.5	226.4	229.9	233.8	238.2	244.6	250.5	255.4	261.3	267.2
162.5°	228.5	228.0	230.0	233.0	236.2	239.8	245.4	250.1	254.3	258.9	264.1
165°	233.8	232.8	234.3	236.7	238.7	241.7	245.6	249.5	252.4	255.4	259.3
167.5°	237.3	236.9	237.7	239.1	240.5	242.3	245.6	248.3	249.7	251.9	254.7
170°	239.7	239.2	239.7	240.6	241.7	243.1	245.6	247.5	248.5	249.9	251.9
172.5°	241.3	240.4	240.8	241.9	242.5	243.1	245.2	246.8	246.9	247.6	249.2
175°	243.1	242.1	242.6	243.1	243.1	243.1	244.6	245.6	245.0	245.0	245.6
177.5°	244.0	243.2	243.2	243.6	243.2	243.2	244.0	244.4	243.6	243.6	244.0
180°	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6



TEST NUMBER: P333132-935

CATALOG NUMBER: S125DIP-S375D590U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	503.0	503.0	503.0	503.0	503.0	503.0	503.0	503.0
2.5°	501.5	502.2	502.9	503.3	503.2	503.1	503.1	503.0
5°	498.9	499.8	500.6	500.9	500.8	500.8	500.7	500.6
7.5°	494.0	494.7	495.5	495.8	495.8	495.7	495.6	495.5
10°	489.7	490.3	491.1	491.4	491.3	491.2	491.1	491.0
12.5°	484.0	484.6	485.1	485.3	485.3	485.3	485.3	485.3
15°	474.0	474.4	474.9	475.1	475.1	475.1	475.1	475.1
17.5°	462.4	463.0	463.6	463.6	463.1	462.7	462.3	461.8
20°	453.7	454.3	454.9	455.0	454.5	454.1	453.7	453.2
22.5°	443.7	444.1	444.5	444.5	444.3	443.9	443.7	443.3
25°	427.7	427.9	428.1	428.0	427.7	427.5	427.2	427.0
27.5°	411.0	411.0	411.0	411.0	410.6	410.4	410.1	409.8
30°	398.7	398.6	398.4	398.2	398.0	397.7	397.4	397.1
32.5°	386.4	386.1	385.7	385.4	384.9	384.4	383.9	383.4
35°	367.2	366.8	366.3	365.8	365.1	364.3	363.6	362.9
37.5°	347.1	346.4	345.7	345.2	344.7	344.4	344.0	343.5
40°	333.0	332.3	331.5	331.0	330.7	330.4	330.1	329.8
42.5°	319.2	318.5	317.7	317.2	316.8	316.3	316.0	315.6
45°	298.7	297.6	296.6	295.9	295.7	295.4	295.2	294.9
47.5°	277.1	276.0	274.9	274.1	273.5	272.9	272.2	271.6
50°	262.3	261.1	260.0	259.2	258.5	257.9	257.3	256.7
52.5°	248.0	246.9	245.9	245.1	244.4	243.7	243.1	242.4
55°	225.6	224.8	224.0	223.3	222.7	222.1	221.4	220.8
57.5°	203.5	202.4	201.4	200.7	200.4	200.0	199.7	199.3
60°	188.5	187.5	186.7	185.9	185.3	184.7	184.1	183.5
62.5°	174.0	173.0	172.0	171.3	170.9	170.4	169.9	169.4
65°	151.2	150.4	149.6	149.0	148.7	148.4	148.0	147.7
67.5°	129.5	128.8	128.1	127.7	127.5	127.3	127.1	126.8
70°	115.1	114.6	114.1	113.7	113.3	113.0	112.5	112.2
72.5°	101.6	101.0	100.4	100.0	99.6	99.3	98.8	98.5
75°	80.7	80.4	80.1	79.8	79.5	79.1	78.8	78.4
77.5°	61.5	61.3	61.1	61.0	60.7	60.4	60.2	59.9
80°	49.2	49.1	49.0	48.8	48.6	48.5	48.3	48.1
82.5°	37.5	37.4	37.3	37.1	37.1	37.1	37.0	37.0
85°	22.1	22.0	22.0	21.8	21.6	21.4	21.3	21.1
87.5°	10.1	10.2	10.2	10.3	10.2	10.1	10.1	9.9
90°	8.9	9.3	9.8	10.8	10.8	10.8	11.3	11.3
92.5°	87.0	63.2	47.5	40.3	34.0	32.8	32.1	31.3
95°	353.1	278.4	218.1	176.8	142.0	127.2	123.3	115.5
97.5°	525.9	473.6	414.7	357.3	327.0	299.5	285.2	279.0
100°	604.1	580.1	529.4	478.4	444.4	409.1	391.0	383.1
102.5°	630.4	645.2	621.0	586.4	550.2	525.0	505.3	499.4
105°	614.9	682.2	703.8	698.4	682.7	666.5	656.7	650.7
107.5°	559.5	649.3	704.8	730.4	738.4	738.3	735.0	731.1
110°	518.7	612.0	681.2	723.0	745.0	754.4	757.9	757.9



TEST NUMBER: P333132-935

CATALOG NUMBER: S125DIP-S375D590U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	486.5	575.1	645.1	694.3	726.6	742.6	751.1	754.7
115°	445.9	522.1	589.4	642.9	681.2	704.8	718.5	725.0
117.5°	419.8	485.4	543.4	592.5	630.9	655.2	668.8	672.8
120°	405.7	464.6	518.7	561.9	598.2	621.8	635.1	638.9
122.5°	395.1	449.7	497.8	538.3	570.7	592.3	605.5	609.1
125°	379.6	429.7	472.5	507.8	535.4	555.5	566.3	571.2
127.5°	363.9	410.7	450.6	483.7	508.6	526.4	536.6	538.8
130°	354.1	397.4	435.7	467.5	492.1	508.3	518.1	521.1
132.5°	344.3	384.8	419.6	450.3	474.8	491.0	500.1	503.4
135°	331.5	365.4	396.8	424.8	446.4	462.6	471.5	474.4
137.5°	320.7	348.1	374.3	398.0	417.3	432.1	440.2	443.5
140°	314.8	337.9	360.5	381.2	399.3	412.1	419.4	421.9
142.5°	309.7	329.2	348.7	366.6	382.0	392.8	399.8	401.8
145°	303.1	318.2	333.5	346.7	358.5	366.9	372.3	374.3
147.5°	296.8	309.1	320.8	330.8	340.2	346.8	350.0	350.9
150°	293.2	304.0	313.3	322.2	329.6	335.4	337.4	337.9
152.5°	289.3	298.9	307.5	314.4	320.6	325.2	327.2	327.7
155°	283.4	291.3	298.1	303.5	308.4	311.9	313.3	313.8
157.5°	277.5	284.0	289.3	293.5	297.3	300.1	301.5	301.4
160°	273.5	278.4	283.4	286.8	290.2	292.7	293.7	293.2
162.5°	269.2	273.8	277.8	280.9	283.6	285.7	285.9	285.8
165°	263.2	266.7	269.7	272.1	274.1	275.0	275.0	275.0
167.5°	257.5	259.8	262.1	263.8	264.8	265.7	265.3	265.2
170°	254.4	255.9	257.4	258.3	259.3	259.8	259.8	259.3
172.5°	250.9	252.4	253.4	254.0	254.3	255.1	254.3	253.8
175°	247.0	247.0	248.1	248.1	248.1	248.5	247.5	247.0
177.5°	244.4	244.8	244.8	244.8	244.4	244.8	243.6	243.6
180°	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6

(END OF REPORT)