

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333296-830

Luminaire Tested: **S125DIP-S1270D365U830-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333296-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1270D365U830-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6080.1 lumens
Efficiency: N/A
Efficacy: 122.1 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333296-830

CATALOG NUMBER: S125DIP-S1270D365U830-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333296-830

CATALOG NUMBER: S125DIP-S1270D365U830-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	100	100	100	92	92	92	84	84	84	80
1	105	101	97	93	100	96	93	90	89	86	83	81	79	77	75	73	72	68
2	96	88	82	77	92	85	79	74	78	74	70	72	68	65	66	63	61	58
3	88	78	70	64	84	75	68	63	69	64	59	64	59	56	59	55	52	49
4	80	69	61	55	77	67	59	53	62	56	51	57	52	48	53	49	45	43
5	74	62	54	47	71	60	52	46	55	49	44	52	46	42	48	43	40	37
6	68	56	47	41	65	54	46	40	50	44	39	47	41	37	43	39	35	33
7	63	51	42	37	61	49	41	36	46	39	34	43	37	33	40	35	31	29
8	59	46	38	33	56	45	37	32	42	35	31	39	33	29	36	32	28	26
9	55	42	34	29	53	41	34	29	38	32	27	36	30	26	34	29	25	23
10	52	39	31	26	49	38	31	26	35	29	25	33	28	24	31	26	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11180	11180	11180	11180
5°	12947	11218	9822	11218
10°	15062	11160	8605	11160
15°	16673	11078	7938	11078
20°	18664	10948	7403	10948
25°	21865	10802	7142	10802
30°	23616	10657	6915	10657
35°	19418	10387	6766	10387
40°	13801	10010	6604	10010
45°	10602	9502	6509	9502
50°	9051	8874	6497	8874
55°	8059	8257	6552	8257
60°	7270	7582	6719	7582
65°	6715	6906	6894	6906
70°	6105	6201	6992	6201
75°	5390	5465	6932	5465
80°	4537	4456	6338	4456
85°	3586	3216	5120	3216



TEST NUMBER: P333296-830

CATALOG NUMBER: S125DIP-S1270D365U830-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.6	2.7
10°-20°	496.2	8.2
20°-30°	805.7	13.3
30°-40°	982.8	16.2
40°-50°	894.0	14.7
50°-60°	712.1	11.7
60°-70°	496.0	8.2
70°-80°	264.5	4.4
80°-90°	67.7	1.1
90°-100°	28.7	0.5
100°-110°	84.7	1.4
110°-120°	143.4	2.4
120°-130°	188.7	3.1
130°-140°	211.5	3.5
140°-150°	207.3	3.4
150°-160°	174.1	2.9
160°-170°	115.7	1.9
170°-180°	40.5	0.7
0°-30°	1468.5	24.2
0°-40°	2451.2	40.3
0°-60°	4057.4	66.7
0°-90°	4885.6	80.4
90°-120°	256.8	4.2
90°-150°	864.2	14.2
90°-180°	1195.0	19.7
0°-180°	6080.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1731	1731	1731	1731	1731	
5°	1997	1730	1515	1730	1997	201
15°	2494	1657	1187	1657	2494	714
25°	3068	1516	1002	1516	3068	1401
35°	2463	1317	858	1317	2463	1507
45°	1161	1040	713	1040	1161	929
55°	716	733	582	733	716	645
65°	439	452	451	452	439	436
75°	216	219	278	219	216	233
85°	48	43	69	43	48	56
90°	8	0	8	0	8	6
95°	29	22	29	22	29	29
105°	83	76	83	76	83	88
115°	145	144	145	144	145	143
125°	211	210	211	210	211	188
135°	274	272	274	272	274	211
145°	332	330	332	330	332	207
155°	378	378	378	378	378	174
165°	410	411	410	411	410	115
175°	425	427	425	427	425	40
180°	428	428	428	428	428	



TEST NUMBER: P333296-830

CATALOG NUMBER: S125DIP-S1270D365U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1
2.5°	1831.0	1828.6	1826.3	1821.6	1825.0	1815.1	1810.3	1802.1	1792.2	1788.7	1784.5
5°	1997.0	2000.6	2004.3	1989.0	1990.4	1980.1	1956.6	1937.5	1922.0	1902.2	1888.3
7.5°	2196.9	2188.2	2187.5	2177.5	2160.3	2146.5	2121.8	2090.3	2059.9	2025.2	1996.6
10°	2296.8	2297.5	2290.9	2279.2	2260.8	2247.6	2215.3	2184.3	2146.9	2102.8	2071.2
12.5°	2372.0	2375.1	2366.7	2350.9	2341.8	2312.2	2286.9	2250.2	2205.6	2170.4	2122.3
15°	2493.7	2485.6	2479.7	2459.8	2444.5	2413.6	2373.2	2335.0	2286.5	2241.6	2196.9
17.5°	2610.9	2617.4	2606.4	2588.3	2540.4	2504.4	2450.2	2397.8	2337.5	2277.4	2223.9
20°	2715.6	2721.5	2704.5	2673.0	2615.6	2579.6	2508.4	2440.8	2371.0	2293.9	2235.1
22.5°	2846.1	2841.4	2818.6	2770.5	2720.8	2654.3	2577.2	2494.8	2407.4	2320.3	2242.1
25°	3068.3	3037.3	3023.4	2963.9	2898.5	2800.8	2695.0	2574.5	2465.8	2350.4	2250.5
27.5°	3191.4	3181.6	3166.1	3124.7	3055.9	2951.4	2826.7	2679.8	2526.5	2380.9	2250.0
30°	3166.7	3168.2	3169.7	3156.4	3112.4	3033.7	2909.5	2751.6	2569.4	2405.6	2254.2
32.5°	2948.1	2974.8	3000.4	3030.7	3043.0	3027.8	2950.1	2807.5	2619.9	2433.7	2251.8
35°	2462.9	2470.9	2553.9	2636.2	2747.9	2834.6	2892.7	2829.4	2671.4	2457.7	2249.0
37.5°	1920.3	1960.0	2017.4	2110.4	2271.6	2415.9	2601.5	2686.9	2635.9	2465.5	2243.9
40°	1637.0	1673.8	1711.2	1806.0	1941.9	2116.8	2327.6	2507.6	2549.5	2440.8	2226.3
42.5°	1418.3	1447.5	1489.0	1560.3	1673.9	1828.7	2030.2	2265.5	2410.2	2369.1	2189.2
45°	1160.8	1179.2	1211.5	1268.2	1350.5	1471.7	1649.4	1906.7	2130.7	2204.9	2101.3
47.5°	993.6	993.5	1018.6	1057.7	1117.1	1220.1	1351.6	1553.1	1792.4	1969.5	1961.3
50°	900.8	897.1	916.9	950.7	997.8	1066.1	1191.8	1352.6	1582.6	1783.2	1839.0
52.5°	820.9	821.2	833.5	858.5	897.9	956.2	1050.1	1195.1	1391.6	1597.4	1702.7
55°	715.7	712.7	726.6	743.6	772.2	810.4	878.0	988.9	1148.4	1351.1	1487.8
57.5°	619.3	627.4	632.9	644.7	668.5	694.0	751.0	832.5	958.9	1132.9	1277.4
60°	562.8	570.9	575.3	587.0	606.1	628.2	672.3	738.4	845.0	994.9	1138.1
62.5°	512.3	518.6	520.0	530.7	546.2	567.7	602.4	657.9	742.1	873.2	1013.5
65°	439.4	439.4	442.3	453.4	460.7	479.8	506.2	546.7	614.3	716.3	836.1
67.5°	369.1	372.7	371.9	376.7	383.5	398.4	417.4	450.7	500.8	575.3	671.1
70°	323.3	326.2	325.5	329.1	336.5	346.1	361.5	393.0	429.0	493.0	575.3
72.5°	282.1	283.3	281.4	286.3	290.7	299.1	316.2	333.1	366.7	420.8	488.3
75°	216.0	217.4	219.0	221.9	226.3	230.7	239.5	256.5	278.4	318.9	362.2
77.5°	161.9	159.1	162.7	162.2	164.8	168.1	175.9	184.8	202.9	228.5	262.0
80°	122.0	122.7	122.7	123.5	127.1	129.3	135.9	142.5	156.5	175.6	199.2
82.5°	89.1	91.0	89.8	91.1	94.2	95.8	99.4	104.9	113.0	128.0	145.1
85°	48.4	44.9	46.3	47.8	47.8	48.4	51.5	53.6	58.1	63.9	70.5
87.5°	15.7	16.9	17.3	17.3	17.9	17.8	20.1	20.0	21.7	23.4	25.6
90°	8.0	7.7	7.5	7.4	7.1	6.8	6.4	6.0	5.7	5.4	4.8
92.5°	15.7	15.6	15.4	15.3	15.1	14.7	14.2	13.8	13.3	12.8	12.2
95°	28.7	28.5	28.4	28.2	28.1	27.7	27.2	26.7	26.2	25.6	24.9
97.5°	43.5	43.4	43.3	43.2	43.1	42.8	42.3	41.8	41.4	40.8	39.8
100°	54.7	54.5	54.4	54.2	54.0	53.6	53.0	52.3	51.7	51.0	50.0
102.5°	65.8	65.6	65.4	65.2	65.0	64.6	63.8	63.1	62.4	61.6	61.2
105°	82.7	82.4	82.2	81.9	81.7	81.4	81.0	80.5	80.0	79.6	79.2
107.5°	99.8	99.8	99.8	99.8	99.9	99.7	99.5	99.3	99.1	98.9	98.5
110°	112.6	112.6	112.7	112.8	112.9	112.8	112.6	112.4	112.2	112.0	111.7



TEST NUMBER: P333296-830

CATALOG NUMBER: S125DIP-S1270D365U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	125.2	125.3	125.4	125.5	125.6	125.6	125.5	125.5	125.4	125.3	125.0
115°	144.9	145.0	145.1	145.2	145.2	145.2	145.3	145.4	145.5	145.6	145.4
117.5°	164.2	164.6	164.9	165.1	165.4	165.5	165.5	165.4	165.3	165.3	165.1
120°	177.6	177.9	178.1	178.4	178.7	178.9	178.9	178.9	178.9	178.9	178.8
122.5°	190.9	191.1	191.3	191.6	191.8	192.0	192.0	192.1	192.2	192.2	192.0
125°	210.8	210.9	211.0	211.1	211.1	211.3	211.4	211.6	211.7	211.9	211.8
127.5°	230.1	230.2	230.4	230.5	230.6	230.7	230.8	230.9	231.0	231.0	231.0
130°	242.9	243.0	243.2	243.3	243.5	243.6	243.6	243.7	243.7	243.8	243.7
132.5°	254.9	255.1	255.2	255.4	255.7	255.8	255.9	256.0	256.0	256.1	256.2
135°	273.5	273.8	274.1	274.4	274.7	274.8	274.8	274.8	274.8	274.8	274.8
137.5°	291.7	292.1	292.5	292.8	293.2	293.4	293.3	293.2	293.1	293.0	292.8
140°	303.5	303.9	304.3	304.6	305.0	305.1	304.9	304.8	304.6	304.4	304.3
142.5°	314.7	315.1	315.4	315.8	316.1	316.3	316.2	316.1	316.0	315.9	315.7
145°	331.5	331.7	331.9	332.2	332.3	332.4	332.4	332.4	332.4	332.4	332.2
147.5°	345.8	346.3	346.8	347.3	347.8	348.0	347.8	347.6	347.4	347.2	347.0
150°	356.5	356.6	356.8	356.9	357.0	357.1	357.1	357.1	357.1	357.1	356.8
152.5°	365.2	365.5	365.8	366.1	366.3	366.4	366.2	366.0	365.8	365.6	365.5
155°	377.8	378.1	378.5	378.9	379.3	379.3	379.0	378.7	378.4	378.1	378.1
157.5°	388.2	388.7	389.2	389.7	390.2	390.3	390.0	389.6	389.4	389.1	389.0
160°	395.4	395.8	396.2	396.5	396.9	396.9	396.6	396.3	396.1	395.8	395.7
162.5°	401.5	402.0	402.4	402.8	403.3	403.3	402.9	402.6	402.3	401.9	401.9
165°	409.7	410.2	410.7	411.0	411.5	411.6	411.3	411.0	410.8	410.4	410.4
167.5°	416.3	416.7	417.2	417.6	418.1	418.1	417.6	417.3	416.8	416.3	416.3
170°	419.7	420.3	420.8	421.3	421.8	421.9	421.4	420.9	420.6	420.1	420.1
172.5°	422.6	423.1	423.6	424.0	424.5	424.5	424.0	423.7	423.2	422.7	422.7
175°	425.4	425.9	426.4	427.0	427.4	427.5	427.1	426.6	426.2	425.7	425.7
177.5°	427.0	427.4	427.8	428.3	428.7	428.7	428.4	428.0	427.6	427.3	427.3
180°	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1



TEST NUMBER: P333296-830

CATALOG NUMBER: S125DIP-S1270D365U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1
2.5°	1781.0	1776.9	1772.2	1764.0	1754.0	1748.7	1740.4	1735.1	1724.6	1715.7	1706.4
5°	1871.3	1852.3	1834.7	1811.8	1786.9	1770.7	1751.6	1730.3	1708.3	1685.5	1660.5
7.5°	1965.0	1931.2	1894.4	1854.9	1816.3	1780.7	1746.7	1713.4	1682.2	1644.6	1612.8
10°	2027.9	1985.3	1939.7	1886.0	1833.9	1788.4	1742.0	1701.7	1660.5	1616.4	1577.4
12.5°	2090.7	2034.0	1969.6	1910.7	1848.0	1793.0	1738.5	1687.0	1635.2	1586.4	1541.1
15°	2135.1	2085.2	2025.6	1941.9	1871.3	1795.7	1723.7	1656.8	1594.4	1540.0	1482.7
17.5°	2164.4	2100.0	2036.1	1955.7	1863.3	1778.7	1697.0	1620.5	1550.1	1481.2	1426.0
20°	2169.6	2103.6	2036.6	1958.0	1863.3	1766.3	1684.7	1592.9	1517.2	1446.0	1378.4
22.5°	2167.9	2092.9	2020.2	1939.3	1846.8	1757.5	1658.9	1565.3	1483.1	1413.1	1342.5
25°	2151.3	2071.2	1980.1	1898.6	1807.4	1712.7	1612.8	1515.8	1432.0	1351.9	1282.1
27.5°	2137.5	2033.6	1930.4	1835.3	1747.4	1660.5	1564.8	1465.5	1372.6	1291.5	1225.7
30°	2120.4	2006.6	1890.5	1791.3	1700.9	1616.4	1526.1	1429.1	1332.1	1252.7	1182.2
32.5°	2105.2	1972.5	1849.9	1741.9	1646.2	1564.1	1480.7	1388.5	1293.3	1212.8	1142.2
35°	2075.7	1922.0	1781.7	1659.7	1557.6	1473.1	1403.4	1317.4	1229.9	1152.1	1084.5
37.5°	2038.2	1856.0	1705.3	1577.4	1465.5	1376.5	1311.5	1245.5	1161.6	1086.6	1025.4
40°	2008.7	1808.9	1649.4	1518.7	1402.6	1310.0	1249.8	1187.3	1117.6	1047.7	983.1
42.5°	1971.7	1766.6	1593.1	1452.3	1337.4	1247.2	1183.9	1130.9	1069.3	1004.3	944.2
45°	1903.7	1689.9	1501.8	1350.5	1234.4	1145.5	1080.1	1040.4	994.1	932.4	881.7
47.5°	1803.6	1597.7	1403.2	1247.0	1127.2	1044.8	983.5	945.5	912.9	867.0	821.0
50°	1714.9	1529.0	1332.1	1177.0	1057.2	974.2	917.7	883.2	855.3	819.9	781.0
52.5°	1615.5	1442.6	1262.2	1108.9	990.2	908.4	853.0	822.7	799.4	774.1	735.7
55°	1457.7	1310.8	1143.2	997.8	888.3	808.2	759.7	733.3	714.2	695.0	671.6
57.5°	1283.8	1168.9	1020.6	887.6	786.7	713.9	668.6	642.9	628.0	618.2	604.4
60°	1161.6	1063.2	935.3	814.1	715.7	651.0	606.9	587.0	574.6	566.5	556.2
62.5°	1048.2	967.3	848.9	738.3	652.1	591.0	551.7	532.3	520.5	516.5	508.0
65°	880.9	818.5	720.8	629.0	555.4	503.3	470.2	451.9	444.5	440.1	440.8
67.5°	716.2	678.2	599.6	521.3	462.7	419.0	392.5	378.4	374.8	368.8	368.7
70°	615.7	587.0	520.9	452.6	400.4	366.6	343.1	328.4	324.7	321.8	321.1
72.5°	527.0	501.8	444.5	389.7	342.8	313.1	293.8	284.9	278.9	277.1	277.0
75°	396.1	382.1	336.5	293.1	260.8	240.3	227.1	219.0	214.5	213.8	214.5
77.5°	281.5	269.4	240.4	209.7	189.3	173.7	162.5	159.8	154.8	154.9	154.1
80°	211.6	203.5	185.1	160.9	144.0	130.8	124.9	119.8	118.3	116.1	118.3
82.5°	153.4	144.8	132.2	116.8	102.8	94.9	89.1	87.5	86.5	85.5	86.0
85°	75.7	76.4	69.1	57.3	51.5	47.0	43.4	43.4	42.6	41.8	42.6
87.5°	26.8	25.4	23.0	21.1	18.1	16.2	15.5	15.9	14.3	13.9	14.5
90°	4.3	3.8	3.3	2.7	2.1	1.5	0.9	0.4	0.9	1.5	2.1
92.5°	11.5	10.8	10.3	9.7	9.3	8.9	8.5	8.1	8.5	8.9	9.3
95°	24.1	23.5	22.7	22.2	22.1	22.0	21.8	21.7	21.8	22.0	22.1
97.5°	38.8	37.8	36.8	36.2	36.2	36.1	36.0	36.0	36.0	36.1	36.2
100°	49.0	48.1	47.1	46.7	46.7	46.7	46.7	46.7	46.7	46.7	46.7
102.5°	60.6	60.1	59.7	59.3	59.0	58.7	58.4	58.1	58.4	58.7	59.0
105°	78.7	78.3	77.9	77.5	77.1	76.7	76.3	76.0	76.3	76.7	77.1
107.5°	98.2	97.8	97.6	97.2	96.8	96.4	96.0	95.7	96.0	96.4	96.8
110°	111.5	111.2	111.0	110.7	110.4	110.0	109.6	109.2	109.6	110.0	110.4



TEST NUMBER: P333296-830

CATALOG NUMBER: S125DIP-S1270D365U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	124.7	124.4	124.1	123.9	123.7	123.5	123.3	123.1	123.3	123.5	123.7
115°	145.2	145.2	145.0	144.8	144.5	144.2	143.8	143.5	143.8	144.2	144.5
117.5°	165.0	164.9	164.8	164.7	164.5	164.4	164.2	164.1	164.2	164.4	164.5
120°	178.7	178.7	178.6	178.3	178.0	177.7	177.3	176.9	177.3	177.7	178.0
122.5°	191.8	191.6	191.4	191.2	191.1	191.1	190.9	190.8	190.9	191.1	191.1
125°	211.7	211.7	211.6	211.3	210.8	210.5	210.0	209.5	210.0	210.5	210.8
127.5°	230.9	230.8	230.7	230.5	230.3	230.1	229.8	229.5	229.8	230.1	230.3
130°	243.6	243.4	243.3	243.0	242.6	242.2	241.9	241.5	241.9	242.2	242.6
132.5°	256.2	256.2	256.3	255.9	255.3	254.8	254.1	253.5	254.1	254.8	255.3
135°	274.7	274.7	274.6	274.3	273.8	273.4	273.0	272.5	273.0	273.4	273.8
137.5°	292.7	292.6	292.4	292.1	291.6	291.2	290.8	290.4	290.8	291.2	291.6
140°	304.1	303.8	303.6	303.3	302.9	302.6	302.2	301.8	302.2	302.6	302.9
142.5°	315.4	315.1	314.8	314.5	314.2	313.9	313.6	313.3	313.6	313.9	314.2
145°	332.1	331.8	331.6	331.3	331.0	330.7	330.5	330.2	330.5	330.7	331.0
147.5°	346.9	346.8	346.6	346.4	346.2	346.0	345.9	345.7	345.9	346.0	346.2
150°	356.6	356.2	355.9	355.8	355.9	356.0	356.1	356.1	356.1	356.0	355.9
152.5°	365.4	365.3	365.1	365.0	365.0	364.9	364.8	364.7	364.8	364.9	365.0
155°	378.0	377.9	377.8	377.8	377.8	377.8	377.8	377.8	377.8	377.8	377.8
157.5°	389.0	388.9	388.8	388.9	389.0	389.2	389.4	389.5	389.4	389.2	389.0
160°	395.6	395.6	395.5	395.6	395.8	396.0	396.2	396.4	396.2	396.0	395.8
162.5°	401.9	401.8	401.8	401.9	402.1	402.3	402.4	402.6	402.4	402.3	402.1
165°	410.3	410.2	410.1	410.2	410.3	410.5	410.6	410.8	410.6	410.5	410.3
167.5°	416.3	416.3	416.3	416.5	416.8	417.1	417.4	417.6	417.4	417.1	416.8
170°	420.1	420.1	420.1	420.2	420.6	420.8	421.1	421.4	421.1	420.8	420.6
172.5°	422.7	422.7	422.7	422.9	423.2	423.5	423.8	424.0	423.8	423.5	423.2
175°	425.7	425.7	425.7	425.9	426.2	426.5	426.8	427.1	426.8	426.5	426.2
177.5°	427.4	427.4	427.5	427.6	427.9	428.1	428.4	428.6	428.4	428.1	427.9
180°	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1



TEST NUMBER: P333296-830

CATALOG NUMBER: S125DIP-S1270D365U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1
2.5°	1701.0	1694.6	1689.3	1677.5	1671.0	1662.3	1655.2	1662.8	1654.6	1658.1	1652.8
5°	1648.0	1627.4	1612.8	1591.4	1573.1	1556.1	1543.7	1541.4	1535.6	1532.7	1523.8
7.5°	1584.2	1558.5	1533.2	1505.3	1481.8	1457.8	1442.6	1429.9	1421.5	1410.5	1403.1
10°	1546.6	1512.1	1482.7	1448.9	1419.5	1393.8	1373.2	1362.9	1353.4	1339.4	1334.3
12.5°	1500.2	1464.4	1428.6	1392.5	1364.2	1335.6	1318.0	1302.4	1295.8	1280.1	1278.5
15°	1444.4	1390.8	1355.6	1318.8	1279.9	1256.4	1241.7	1224.8	1217.5	1206.5	1198.3
17.5°	1378.1	1330.1	1286.1	1248.0	1214.7	1194.9	1176.6	1165.0	1152.4	1145.2	1131.9
20°	1329.8	1284.3	1240.2	1199.9	1174.1	1151.3	1136.6	1125.6	1112.4	1108.7	1095.5
22.5°	1289.3	1239.1	1196.7	1162.8	1134.7	1109.0	1093.2	1085.6	1076.6	1065.3	1062.5
25°	1223.3	1171.2	1135.2	1101.4	1076.4	1052.9	1041.9	1032.3	1023.5	1015.4	1012.5
27.5°	1166.3	1119.7	1076.9	1046.4	1024.6	1003.2	993.5	981.9	975.4	968.9	961.0
30°	1126.3	1078.6	1041.1	1011.7	988.3	969.1	958.8	950.7	944.9	939.0	934.6
32.5°	1085.2	1040.9	1004.7	975.9	952.3	937.9	928.9	923.1	916.6	909.6	904.0
35°	1030.9	982.3	947.1	922.1	903.7	892.7	882.4	877.2	870.0	870.0	864.0
37.5°	969.6	927.7	896.5	873.7	857.2	847.4	836.3	832.7	828.0	824.9	822.9
40°	933.1	894.2	864.8	842.0	824.3	816.2	807.5	801.6	798.6	794.9	793.5
42.5°	895.5	858.3	830.1	809.1	793.8	786.9	778.6	774.6	768.6	763.8	763.0
45°	838.3	802.3	776.7	759.7	746.5	738.4	733.3	724.4	721.5	715.7	714.9
47.5°	784.1	749.6	724.3	710.5	698.9	692.3	684.2	675.3	672.0	669.0	668.7
50°	743.6	712.0	688.4	675.2	664.2	654.7	646.6	640.6	638.5	638.5	640.0
52.5°	702.4	675.5	655.5	639.3	629.0	618.8	611.3	607.8	604.4	607.9	610.6
55°	642.2	615.0	600.3	584.8	574.6	562.8	559.1	557.7	555.4	561.4	564.3
57.5°	578.3	559.3	542.1	526.8	517.6	510.8	505.8	504.9	509.1	511.8	521.3
60°	537.8	515.8	500.4	488.6	477.6	473.2	471.7	470.2	473.2	481.3	493.7
62.5°	493.1	475.2	458.6	449.8	441.7	434.4	434.0	435.0	440.8	450.1	462.6
65°	427.6	412.2	401.1	390.9	384.3	379.8	381.4	384.3	390.9	403.4	417.4
67.5°	361.1	350.4	340.6	332.2	325.9	325.9	327.4	331.8	339.6	354.0	366.7
70°	318.1	306.4	298.3	294.6	289.5	286.5	291.0	298.3	304.9	318.1	329.1
72.5°	275.2	265.2	258.9	256.5	254.2	251.8	253.4	261.3	270.2	283.4	296.2
75°	211.6	207.9	203.5	200.6	198.4	199.8	201.3	208.7	216.0	230.0	244.7
77.5°	154.5	150.6	148.0	147.2	146.1	146.8	150.9	156.4	163.5	173.7	184.8
80°	116.8	115.4	113.9	113.1	113.1	113.9	119.8	123.5	130.1	139.6	148.5
82.5°	85.1	84.2	83.9	83.8	84.4	84.5	88.0	92.8	98.3	105.5	113.1
85°	44.9	43.4	45.5	46.3	44.9	47.0	48.4	51.5	53.6	57.3	61.0
87.5°	15.3	16.5	16.0	16.7	16.9	18.1	17.6	20.0	21.3	22.5	22.0
90°	2.7	3.3	3.8	4.3	4.8	5.4	5.7	6.0	6.4	6.8	7.1
92.5°	9.7	10.3	10.8	11.5	12.2	12.8	13.3	13.8	14.2	14.7	15.1
95°	22.2	22.7	23.5	24.1	24.9	25.6	26.2	26.7	27.2	27.7	28.1
97.5°	36.2	36.8	37.8	38.8	39.8	40.8	41.4	41.8	42.3	42.8	43.1
100°	46.7	47.1	48.1	49.0	50.0	51.0	51.7	52.3	53.0	53.6	54.0
102.5°	59.3	59.7	60.1	60.6	61.2	61.6	62.4	63.1	63.8	64.6	65.0
105°	77.5	77.9	78.3	78.7	79.2	79.6	80.0	80.5	81.0	81.4	81.7
107.5°	97.2	97.6	97.8	98.2	98.5	98.9	99.1	99.3	99.5	99.7	99.9
110°	110.7	111.0	111.2	111.5	111.7	112.0	112.2	112.4	112.6	112.8	112.9



TEST NUMBER: P333296-830

CATALOG NUMBER: S125DIP-S1270D365U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	123.9	124.1	124.4	124.7	125.0	125.3	125.4	125.5	125.5	125.6	125.6
115°	144.8	145.0	145.2	145.2	145.4	145.6	145.5	145.4	145.3	145.2	145.2
117.5°	164.7	164.8	164.9	165.0	165.1	165.3	165.3	165.4	165.5	165.5	165.4
120°	178.3	178.6	178.7	178.7	178.8	178.9	178.9	178.9	178.9	178.9	178.7
122.5°	191.2	191.4	191.6	191.8	192.0	192.2	192.2	192.1	192.0	192.0	191.8
125°	211.3	211.6	211.7	211.7	211.8	211.9	211.7	211.6	211.4	211.3	211.1
127.5°	230.5	230.7	230.8	230.9	231.0	231.0	231.0	230.9	230.8	230.7	230.6
130°	243.0	243.3	243.4	243.6	243.7	243.8	243.7	243.7	243.6	243.6	243.5
132.5°	255.9	256.3	256.2	256.2	256.2	256.1	256.0	256.0	255.9	255.8	255.7
135°	274.3	274.6	274.7	274.7	274.8	274.8	274.8	274.8	274.8	274.8	274.7
137.5°	292.1	292.4	292.6	292.7	292.8	293.0	293.1	293.2	293.3	293.4	293.2
140°	303.3	303.6	303.8	304.1	304.3	304.4	304.6	304.8	304.9	305.1	305.0
142.5°	314.5	314.8	315.1	315.4	315.7	315.9	316.0	316.1	316.2	316.3	316.1
145°	331.3	331.6	331.8	332.1	332.2	332.4	332.4	332.4	332.4	332.4	332.3
147.5°	346.4	346.6	346.8	346.9	347.0	347.2	347.4	347.6	347.8	348.0	347.8
150°	355.8	355.9	356.2	356.6	356.8	357.1	357.1	357.1	357.1	357.1	357.0
152.5°	365.0	365.1	365.3	365.4	365.5	365.6	365.8	366.0	366.2	366.4	366.3
155°	377.8	377.8	377.9	378.0	378.1	378.1	378.4	378.7	379.0	379.3	379.3
157.5°	388.9	388.8	388.9	389.0	389.0	389.1	389.4	389.6	390.0	390.3	390.2
160°	395.6	395.5	395.6	395.6	395.7	395.8	396.1	396.3	396.6	396.9	396.9
162.5°	401.9	401.8	401.8	401.9	401.9	401.9	402.3	402.6	402.9	403.3	403.3
165°	410.2	410.1	410.2	410.3	410.4	410.4	410.8	411.0	411.3	411.6	411.5
167.5°	416.5	416.3	416.3	416.3	416.3	416.3	416.8	417.3	417.6	418.1	418.1
170°	420.2	420.1	420.1	420.1	420.1	420.1	420.6	420.9	421.4	421.9	421.8
172.5°	422.9	422.7	422.7	422.7	422.7	422.7	423.2	423.7	424.0	424.5	424.5
175°	425.9	425.7	425.7	425.7	425.7	425.7	426.2	426.6	427.1	427.5	427.4
177.5°	427.6	427.5	427.4	427.4	427.3	427.3	427.6	428.0	428.4	428.7	428.7
180°	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1



TEST NUMBER: P333296-830

CATALOG NUMBER: S125DIP-S1270D365U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1
2.5°	1649.4	1653.4	1649.9	1654.6	1649.9	1653.4	1649.4	1652.8	1658.1	1654.6	1662.8
5°	1520.1	1513.5	1518.0	1515.0	1518.0	1513.5	1520.1	1523.8	1532.7	1535.6	1541.4
7.5°	1400.8	1394.5	1387.3	1383.9	1387.3	1394.5	1400.8	1403.1	1410.5	1421.5	1429.9
10°	1326.2	1318.1	1317.4	1312.2	1317.4	1318.1	1326.2	1334.3	1339.4	1353.4	1362.9
12.5°	1271.5	1264.0	1255.7	1253.5	1255.7	1264.0	1271.5	1278.5	1280.1	1295.8	1302.4
15°	1193.9	1188.1	1182.9	1187.3	1182.9	1188.1	1193.9	1198.3	1206.5	1217.5	1224.8
17.5°	1129.4	1124.5	1123.7	1118.2	1123.7	1124.5	1129.4	1131.9	1145.2	1152.4	1165.0
20°	1088.9	1085.2	1086.7	1077.1	1086.7	1085.2	1088.9	1095.5	1108.7	1112.4	1125.6
22.5°	1056.6	1049.3	1048.5	1046.6	1048.5	1049.3	1056.6	1062.5	1065.3	1076.6	1085.6
25°	1005.9	1002.2	998.5	1002.2	998.5	1002.2	1005.9	1012.5	1015.4	1023.5	1032.3
27.5°	961.6	957.2	956.2	956.6	956.2	957.2	961.6	961.0	968.9	975.4	981.9
30°	934.6	927.3	927.9	927.3	927.9	927.3	934.6	934.6	939.0	944.9	950.7
32.5°	905.2	900.2	899.2	897.9	899.2	900.2	905.2	904.0	909.6	916.6	923.1
35°	861.9	861.9	858.2	858.2	858.2	861.9	861.9	864.0	870.0	870.0	877.2
37.5°	821.1	820.4	818.2	818.5	818.2	820.4	821.1	822.9	824.9	828.0	832.7
40°	790.6	789.9	787.6	783.3	787.6	789.9	790.6	793.5	794.9	798.6	801.6
42.5°	761.2	758.7	757.6	756.2	757.6	758.7	761.2	763.0	763.8	768.6	774.6
45°	714.9	714.9	713.4	712.7	713.4	714.9	714.9	714.9	715.7	721.5	724.4
47.5°	670.0	671.3	674.0	673.6	674.0	671.3	670.0	668.7	669.0	672.0	675.3
50°	642.9	643.7	645.8	646.6	645.8	643.7	642.9	640.0	638.5	638.5	640.6
52.5°	612.9	617.2	620.0	619.5	620.0	617.2	612.9	610.6	607.9	604.4	607.8
55°	570.9	576.0	581.2	581.9	581.2	576.0	570.9	564.3	561.4	555.4	557.7
57.5°	529.3	536.5	542.0	543.7	542.0	536.5	529.3	521.3	511.8	509.1	504.9
60°	501.1	510.7	517.3	520.2	517.3	510.7	501.1	493.7	481.3	473.2	470.2
62.5°	474.0	484.7	491.3	492.0	491.3	484.7	474.0	462.6	450.1	440.8	435.0
65°	429.8	440.8	446.7	451.1	446.7	440.8	429.8	417.4	403.4	390.9	384.3
67.5°	382.2	393.2	399.7	403.2	399.7	393.2	382.2	366.7	354.0	339.6	331.8
70°	347.5	358.5	367.4	370.3	367.4	358.5	347.5	329.1	318.1	304.9	298.3
72.5°	313.4	323.3	330.4	333.8	330.4	323.3	313.4	296.2	283.4	270.2	261.3
75°	254.2	267.4	274.1	277.8	274.1	267.4	254.2	244.7	230.0	216.0	208.7
77.5°	196.0	208.1	212.1	214.0	212.1	208.1	196.0	184.8	173.7	163.5	156.4
80°	157.2	164.6	169.8	170.4	169.8	164.6	157.2	148.5	139.6	130.1	123.5
82.5°	120.8	127.0	128.6	130.4	128.6	127.0	120.8	113.1	105.5	98.3	92.8
85°	66.2	69.1	69.8	69.1	69.8	69.1	66.2	61.0	57.3	53.6	51.5
87.5°	23.2	22.7	22.7	23.9	22.7	22.7	23.2	22.0	22.5	21.3	20.0
90°	7.4	7.5	7.7	8.0	7.7	7.5	7.4	7.1	6.8	6.4	6.0
92.5°	15.3	15.4	15.6	15.7	15.6	15.4	15.3	15.1	14.7	14.2	13.8
95°	28.2	28.4	28.5	28.7	28.5	28.4	28.2	28.1	27.7	27.2	26.7
97.5°	43.2	43.3	43.4	43.5	43.4	43.3	43.2	43.1	42.8	42.3	41.8
100°	54.2	54.4	54.5	54.7	54.5	54.4	54.2	54.0	53.6	53.0	52.3
102.5°	65.2	65.4	65.6	65.8	65.6	65.4	65.2	65.0	64.6	63.8	63.1
105°	81.9	82.2	82.4	82.7	82.4	82.2	81.9	81.7	81.4	81.0	80.5
107.5°	99.8	99.8	99.8	99.8	99.8	99.8	99.8	99.9	99.7	99.5	99.3
110°	112.8	112.7	112.6	112.6	112.6	112.7	112.8	112.9	112.8	112.6	112.4



TEST NUMBER: P333296-830

CATALOG NUMBER: S125DIP-S1270D365U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	125.5	125.4	125.3	125.2	125.3	125.4	125.5	125.6	125.6	125.5	125.5
115°	145.2	145.1	145.0	144.9	145.0	145.1	145.2	145.2	145.2	145.3	145.4
117.5°	165.1	164.9	164.6	164.2	164.6	164.9	165.1	165.4	165.5	165.5	165.4
120°	178.4	178.1	177.9	177.6	177.9	178.1	178.4	178.7	178.9	178.9	178.9
122.5°	191.6	191.3	191.1	190.9	191.1	191.3	191.6	191.8	192.0	192.0	192.1
125°	211.1	211.0	210.9	210.8	210.9	211.0	211.1	211.1	211.3	211.4	211.6
127.5°	230.5	230.4	230.2	230.1	230.2	230.4	230.5	230.6	230.7	230.8	230.9
130°	243.3	243.2	243.0	242.9	243.0	243.2	243.3	243.5	243.6	243.6	243.7
132.5°	255.4	255.2	255.1	254.9	255.1	255.2	255.4	255.7	255.8	255.9	256.0
135°	274.4	274.1	273.8	273.5	273.8	274.1	274.4	274.7	274.8	274.8	274.8
137.5°	292.8	292.5	292.1	291.7	292.1	292.5	292.8	293.2	293.4	293.3	293.2
140°	304.6	304.3	303.9	303.5	303.9	304.3	304.6	305.0	305.1	304.9	304.8
142.5°	315.8	315.4	315.1	314.7	315.1	315.4	315.8	316.1	316.3	316.2	316.1
145°	332.2	331.9	331.7	331.5	331.7	331.9	332.2	332.3	332.4	332.4	332.4
147.5°	347.3	346.8	346.3	345.8	346.3	346.8	347.3	347.8	348.0	347.8	347.6
150°	356.9	356.8	356.6	356.5	356.6	356.8	356.9	357.0	357.1	357.1	357.1
152.5°	366.1	365.8	365.5	365.2	365.5	365.8	366.1	366.3	366.4	366.2	366.0
155°	378.9	378.5	378.1	377.8	378.1	378.5	378.9	379.3	379.3	379.0	378.7
157.5°	389.7	389.2	388.7	388.2	388.7	389.2	389.7	390.2	390.3	390.0	389.6
160°	396.5	396.2	395.8	395.4	395.8	396.2	396.5	396.9	396.9	396.6	396.3
162.5°	402.8	402.4	402.0	401.5	402.0	402.4	402.8	403.3	403.3	402.9	402.6
165°	411.0	410.7	410.2	409.7	410.2	410.7	411.0	411.5	411.6	411.3	411.0
167.5°	417.6	417.2	416.7	416.3	416.7	417.2	417.6	418.1	418.1	417.6	417.3
170°	421.3	420.8	420.3	419.7	420.3	420.8	421.3	421.8	421.9	421.4	420.9
172.5°	424.0	423.6	423.1	422.6	423.1	423.6	424.0	424.5	424.5	424.0	423.7
175°	427.0	426.4	425.9	425.4	425.9	426.4	427.0	427.4	427.5	427.1	426.6
177.5°	428.3	427.8	427.4	427.0	427.4	427.8	428.3	428.7	428.7	428.4	428.0
180°	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1



TEST NUMBER: P333296-830

CATALOG NUMBER: S125DIP-S1270D365U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1
2.5°	1655.2	1662.3	1671.0	1677.5	1689.3	1694.6	1701.0	1706.4	1715.7	1724.6	1735.1
5°	1543.7	1556.1	1573.1	1591.4	1612.8	1627.4	1648.0	1660.5	1685.5	1708.3	1730.3
7.5°	1442.6	1457.8	1481.8	1505.3	1533.2	1558.5	1584.2	1612.8	1644.6	1682.2	1713.4
10°	1373.2	1393.8	1419.5	1448.9	1482.7	1512.1	1546.6	1577.4	1616.4	1660.5	1701.7
12.5°	1318.0	1335.6	1364.2	1392.5	1428.6	1464.4	1500.2	1541.1	1586.4	1635.2	1687.0
15°	1241.7	1256.4	1279.9	1318.8	1355.6	1390.8	1444.4	1482.7	1540.0	1594.4	1656.8
17.5°	1176.6	1194.9	1214.7	1248.0	1286.1	1330.1	1378.1	1426.0	1481.2	1550.1	1620.5
20°	1136.6	1151.3	1174.1	1199.9	1240.2	1284.3	1329.8	1378.4	1446.0	1517.2	1592.9
22.5°	1093.2	1109.0	1134.7	1162.8	1196.7	1239.1	1289.3	1342.5	1413.1	1483.1	1565.3
25°	1041.9	1052.9	1076.4	1101.4	1135.2	1171.2	1223.3	1282.1	1351.9	1432.0	1515.8
27.5°	993.5	1003.2	1024.6	1046.4	1076.9	1119.7	1166.3	1225.7	1291.5	1372.6	1465.5
30°	958.8	969.1	988.3	1011.7	1041.1	1078.6	1126.3	1182.2	1252.7	1332.1	1429.1
32.5°	928.9	937.9	952.3	975.9	1004.7	1040.9	1085.2	1142.2	1212.8	1293.3	1388.5
35°	882.4	892.7	903.7	922.1	947.1	982.3	1030.9	1084.5	1152.1	1229.9	1317.4
37.5°	836.3	847.4	857.2	873.7	896.5	927.7	969.6	1025.4	1086.6	1161.6	1245.5
40°	807.5	816.2	824.3	842.0	864.8	894.2	933.1	983.1	1047.7	1117.6	1187.3
42.5°	778.6	786.9	793.8	809.1	830.1	858.3	895.5	944.2	1004.3	1069.3	1130.9
45°	733.3	738.4	746.5	759.7	776.7	802.3	838.3	881.7	932.4	994.1	1040.4
47.5°	684.2	692.3	698.9	710.5	724.3	749.6	784.1	821.0	867.0	912.9	945.5
50°	646.6	654.7	664.2	675.2	688.4	712.0	743.6	781.0	819.9	855.3	883.2
52.5°	611.3	618.8	629.0	639.3	655.5	675.5	702.4	735.7	774.1	799.4	822.7
55°	559.1	562.8	574.6	584.8	600.3	615.0	642.2	671.6	695.0	714.2	733.3
57.5°	505.8	510.8	517.6	526.8	542.1	559.3	578.3	604.4	618.2	628.0	642.9
60°	471.7	473.2	477.6	488.6	500.4	515.8	537.8	556.2	566.5	574.6	587.0
62.5°	434.0	434.4	441.7	449.8	458.6	475.2	493.1	508.0	516.5	520.5	532.3
65°	381.4	379.8	384.3	390.9	401.1	412.2	427.6	440.8	440.1	444.5	451.9
67.5°	327.4	325.9	325.9	332.2	340.6	350.4	361.1	368.7	368.8	374.8	378.4
70°	291.0	286.5	289.5	294.6	298.3	306.4	318.1	321.1	321.8	324.7	328.4
72.5°	253.4	251.8	254.2	256.5	258.9	265.2	275.2	277.0	277.1	278.9	284.9
75°	201.3	199.8	198.4	200.6	203.5	207.9	211.6	214.5	213.8	214.5	219.0
77.5°	150.9	146.8	146.1	147.2	148.0	150.6	154.5	154.1	154.9	154.8	159.8
80°	119.8	113.9	113.1	113.1	113.9	115.4	116.8	118.3	116.1	118.3	119.8
82.5°	88.0	84.5	84.4	83.8	83.9	84.2	85.1	86.0	85.5	86.5	87.5
85°	48.4	47.0	44.9	46.3	45.5	43.4	44.9	42.6	41.8	42.6	43.4
87.5°	17.6	18.1	16.9	16.7	16.0	16.5	15.3	14.5	13.9	14.3	15.9
90°	5.7	5.4	4.8	4.3	3.8	3.3	2.7	2.1	1.5	0.9	0.4
92.5°	13.3	12.8	12.2	11.5	10.8	10.3	9.7	9.3	8.9	8.5	8.1
95°	26.2	25.6	24.9	24.1	23.5	22.7	22.2	22.1	22.0	21.8	21.7
97.5°	41.4	40.8	39.8	38.8	37.8	36.8	36.2	36.2	36.1	36.0	36.0
100°	51.7	51.0	50.0	49.0	48.1	47.1	46.7	46.7	46.7	46.7	46.7
102.5°	62.4	61.6	61.2	60.6	60.1	59.7	59.3	59.0	58.7	58.4	58.1
105°	80.0	79.6	79.2	78.7	78.3	77.9	77.5	77.1	76.7	76.3	76.0
107.5°	99.1	98.9	98.5	98.2	97.8	97.6	97.2	96.8	96.4	96.0	95.7
110°	112.2	112.0	111.7	111.5	111.2	111.0	110.7	110.4	110.0	109.6	109.2



TEST NUMBER: P333296-830

CATALOG NUMBER: S125DIP-S1270D365U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	125.4	125.3	125.0	124.7	124.4	124.1	123.9	123.7	123.5	123.3	123.1
115°	145.5	145.6	145.4	145.2	145.2	145.0	144.8	144.5	144.2	143.8	143.5
117.5°	165.3	165.3	165.1	165.0	164.9	164.8	164.7	164.5	164.4	164.2	164.1
120°	178.9	178.9	178.8	178.7	178.7	178.6	178.3	178.0	177.7	177.3	176.9
122.5°	192.2	192.2	192.0	191.8	191.6	191.4	191.2	191.1	191.1	190.9	190.8
125°	211.7	211.9	211.8	211.7	211.7	211.6	211.3	210.8	210.5	210.0	209.5
127.5°	231.0	231.0	231.0	230.9	230.8	230.7	230.5	230.3	230.1	229.8	229.5
130°	243.7	243.8	243.7	243.6	243.4	243.3	243.0	242.6	242.2	241.9	241.5
132.5°	256.0	256.1	256.2	256.2	256.2	256.3	255.9	255.3	254.8	254.1	253.5
135°	274.8	274.8	274.8	274.7	274.7	274.6	274.3	273.8	273.4	273.0	272.5
137.5°	293.1	293.0	292.8	292.7	292.6	292.4	292.1	291.6	291.2	290.8	290.4
140°	304.6	304.4	304.3	304.1	303.8	303.6	303.3	302.9	302.6	302.2	301.8
142.5°	316.0	315.9	315.7	315.4	315.1	314.8	314.5	314.2	313.9	313.6	313.3
145°	332.4	332.4	332.2	332.1	331.8	331.6	331.3	331.0	330.7	330.5	330.2
147.5°	347.4	347.2	347.0	346.9	346.8	346.6	346.4	346.2	346.0	345.9	345.7
150°	357.1	357.1	356.8	356.6	356.2	355.9	355.8	355.9	356.0	356.1	356.1
152.5°	365.8	365.6	365.5	365.4	365.3	365.1	365.0	365.0	364.9	364.8	364.7
155°	378.4	378.1	378.1	378.0	377.9	377.8	377.8	377.8	377.8	377.8	377.8
157.5°	389.4	389.1	389.0	389.0	388.9	388.8	388.9	389.0	389.2	389.4	389.5
160°	396.1	395.8	395.7	395.6	395.6	395.5	395.6	395.8	396.0	396.2	396.4
162.5°	402.3	401.9	401.9	401.9	401.8	401.8	401.9	402.1	402.3	402.4	402.6
165°	410.8	410.4	410.4	410.3	410.2	410.1	410.2	410.3	410.5	410.6	410.8
167.5°	416.8	416.3	416.3	416.3	416.3	416.3	416.5	416.8	417.1	417.4	417.6
170°	420.6	420.1	420.1	420.1	420.1	420.1	420.2	420.6	420.8	421.1	421.4
172.5°	423.2	422.7	422.7	422.7	422.7	422.7	422.9	423.2	423.5	423.8	424.0
175°	426.2	425.7	425.7	425.7	425.7	425.7	425.9	426.2	426.5	426.8	427.1
177.5°	427.6	427.3	427.3	427.4	427.4	427.5	427.6	427.9	428.1	428.4	428.6
180°	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1



TEST NUMBER: P333296-830

CATALOG NUMBER: S125DIP-S1270D365U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1
2.5°	1740.4	1748.7	1754.0	1764.0	1772.2	1776.9	1781.0	1784.5	1788.7	1792.2	1802.1
5°	1751.6	1770.7	1786.9	1811.8	1834.7	1852.3	1871.3	1888.3	1902.2	1922.0	1937.5
7.5°	1746.7	1780.7	1816.3	1854.9	1894.4	1931.2	1965.0	1996.6	2025.2	2059.9	2090.3
10°	1742.0	1788.4	1833.9	1886.0	1939.7	1985.3	2027.9	2071.2	2102.8	2146.9	2184.3
12.5°	1738.5	1793.0	1848.0	1910.7	1969.6	2034.0	2090.7	2122.3	2170.4	2205.6	2250.2
15°	1723.7	1795.7	1871.3	1941.9	2025.6	2085.2	2135.1	2196.9	2241.6	2286.5	2335.0
17.5°	1697.0	1778.7	1863.3	1955.7	2036.1	2100.0	2164.4	2223.9	2277.4	2337.5	2397.8
20°	1684.7	1766.3	1863.3	1958.0	2036.6	2103.6	2169.6	2235.1	2293.9	2371.0	2440.8
22.5°	1658.9	1757.5	1846.8	1939.3	2020.2	2092.9	2167.9	2242.1	2320.3	2407.4	2494.8
25°	1612.8	1712.7	1807.4	1898.6	1980.1	2071.2	2151.3	2250.5	2350.4	2465.8	2574.5
27.5°	1564.8	1660.5	1747.4	1835.3	1930.4	2033.6	2137.5	2250.0	2380.9	2526.5	2679.8
30°	1526.1	1616.4	1700.9	1791.3	1890.5	2006.6	2120.4	2254.2	2405.6	2569.4	2751.6
32.5°	1480.7	1564.1	1646.2	1741.9	1849.9	1972.5	2105.2	2251.8	2433.7	2619.9	2807.5
35°	1403.4	1473.1	1557.6	1659.7	1781.7	1922.0	2075.7	2249.0	2457.7	2671.4	2829.4
37.5°	1311.5	1376.5	1465.5	1577.4	1705.3	1856.0	2038.2	2243.9	2465.5	2635.9	2686.9
40°	1249.8	1310.0	1402.6	1518.7	1649.4	1808.9	2008.7	2226.3	2440.8	2549.5	2507.6
42.5°	1183.9	1247.2	1337.4	1452.3	1593.1	1766.6	1971.7	2189.2	2369.1	2410.2	2265.5
45°	1080.1	1145.5	1234.4	1350.5	1501.8	1689.9	1903.7	2101.3	2204.9	2130.7	1906.7
47.5°	983.5	1044.8	1127.2	1247.0	1403.2	1597.7	1803.6	1961.3	1969.5	1792.4	1553.1
50°	917.7	974.2	1057.2	1177.0	1332.1	1529.0	1714.9	1839.0	1783.2	1582.6	1352.6
52.5°	853.0	908.4	990.2	1108.9	1262.2	1442.6	1615.5	1702.7	1597.4	1391.6	1195.1
55°	759.7	808.2	888.3	997.8	1143.2	1310.8	1457.7	1487.8	1351.1	1148.4	988.9
57.5°	668.6	713.9	786.7	887.6	1020.6	1168.9	1283.8	1277.4	1132.9	958.9	832.5
60°	606.9	651.0	715.7	814.1	935.3	1063.2	1161.6	1138.1	994.9	845.0	738.4
62.5°	551.7	591.0	652.1	738.3	848.9	967.3	1048.2	1013.5	873.2	742.1	657.9
65°	470.2	503.3	555.4	629.0	720.8	818.5	880.9	836.1	716.3	614.3	546.7
67.5°	392.5	419.0	462.7	521.3	599.6	678.2	716.2	671.1	575.3	500.8	450.7
70°	343.1	366.6	400.4	452.6	520.9	587.0	615.7	575.3	493.0	429.0	393.0
72.5°	293.8	313.1	342.8	389.7	444.5	501.8	527.0	488.3	420.8	366.7	333.1
75°	227.1	240.3	260.8	293.1	336.5	382.1	396.1	362.2	318.9	278.4	256.5
77.5°	162.5	173.7	189.3	209.7	240.4	269.4	281.5	262.0	228.5	202.9	184.8
80°	124.9	130.8	144.0	160.9	185.1	203.5	211.6	199.2	175.6	156.5	142.5
82.5°	89.1	94.9	102.8	116.8	132.2	144.8	153.4	145.1	128.0	113.0	104.9
85°	43.4	47.0	51.5	57.3	69.1	76.4	75.7	70.5	63.9	58.1	53.6
87.5°	15.5	16.2	18.1	21.1	23.0	25.4	26.8	25.6	23.4	21.7	20.0
90°	0.9	1.5	2.1	2.7	3.3	3.8	4.3	4.8	5.4	5.7	6.0
92.5°	8.5	8.9	9.3	9.7	10.3	10.8	11.5	12.2	12.8	13.3	13.8
95°	21.8	22.0	22.1	22.2	22.7	23.5	24.1	24.9	25.6	26.2	26.7
97.5°	36.0	36.1	36.2	36.2	36.8	37.8	38.8	39.8	40.8	41.4	41.8
100°	46.7	46.7	46.7	46.7	47.1	48.1	49.0	50.0	51.0	51.7	52.3
102.5°	58.4	58.7	59.0	59.3	59.7	60.1	60.6	61.2	61.6	62.4	63.1
105°	76.3	76.7	77.1	77.5	77.9	78.3	78.7	79.2	79.6	80.0	80.5
107.5°	96.0	96.4	96.8	97.2	97.6	97.8	98.2	98.5	98.9	99.1	99.3
110°	109.6	110.0	110.4	110.7	111.0	111.2	111.5	111.7	112.0	112.2	112.4



TEST NUMBER: P333296-830

CATALOG NUMBER: S125DIP-S1270D365U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	123.3	123.5	123.7	123.9	124.1	124.4	124.7	125.0	125.3	125.4	125.5
115°	143.8	144.2	144.5	144.8	145.0	145.2	145.2	145.4	145.6	145.5	145.4
117.5°	164.2	164.4	164.5	164.7	164.8	164.9	165.0	165.1	165.3	165.3	165.4
120°	177.3	177.7	178.0	178.3	178.6	178.7	178.7	178.8	178.9	178.9	178.9
122.5°	190.9	191.1	191.1	191.2	191.4	191.6	191.8	192.0	192.2	192.2	192.1
125°	210.0	210.5	210.8	211.3	211.6	211.7	211.7	211.8	211.9	211.7	211.6
127.5°	229.8	230.1	230.3	230.5	230.7	230.8	230.9	231.0	231.0	231.0	230.9
130°	241.9	242.2	242.6	243.0	243.3	243.4	243.6	243.7	243.8	243.7	243.7
132.5°	254.1	254.8	255.3	255.9	256.3	256.2	256.2	256.2	256.1	256.0	256.0
135°	273.0	273.4	273.8	274.3	274.6	274.7	274.7	274.8	274.8	274.8	274.8
137.5°	290.8	291.2	291.6	292.1	292.4	292.6	292.7	292.8	293.0	293.1	293.2
140°	302.2	302.6	302.9	303.3	303.6	303.8	304.1	304.3	304.4	304.6	304.8
142.5°	313.6	313.9	314.2	314.5	314.8	315.1	315.4	315.7	315.9	316.0	316.1
145°	330.5	330.7	331.0	331.3	331.6	331.8	332.1	332.2	332.4	332.4	332.4
147.5°	345.9	346.0	346.2	346.4	346.6	346.8	346.9	347.0	347.2	347.4	347.6
150°	356.1	356.0	355.9	355.8	355.9	356.2	356.6	356.8	357.1	357.1	357.1
152.5°	364.8	364.9	365.0	365.0	365.1	365.3	365.4	365.5	365.6	365.8	366.0
155°	377.8	377.8	377.8	377.8	377.8	377.9	378.0	378.1	378.1	378.4	378.7
157.5°	389.4	389.2	389.0	388.9	388.8	388.9	389.0	389.0	389.1	389.4	389.6
160°	396.2	396.0	395.8	395.6	395.5	395.6	395.6	395.7	395.8	396.1	396.3
162.5°	402.4	402.3	402.1	401.9	401.8	401.8	401.9	401.9	401.9	402.3	402.6
165°	410.6	410.5	410.3	410.2	410.1	410.2	410.3	410.4	410.4	410.8	411.0
167.5°	417.4	417.1	416.8	416.5	416.3	416.3	416.3	416.3	416.3	416.8	417.3
170°	421.1	420.8	420.6	420.2	420.1	420.1	420.1	420.1	420.1	420.6	420.9
172.5°	423.8	423.5	423.2	422.9	422.7	422.7	422.7	422.7	422.7	423.2	423.7
175°	426.8	426.5	426.2	425.9	425.7	425.7	425.7	425.7	425.7	426.2	426.6
177.5°	428.4	428.1	427.9	427.6	427.5	427.4	427.4	427.3	427.3	427.6	428.0
180°	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1



TEST NUMBER: P333296-830

CATALOG NUMBER: S125DIP-S1270D365U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1
2.5°	1810.3	1815.1	1825.0	1821.6	1826.3	1828.6	1831.0
5°	1956.6	1980.1	1990.4	1989.0	2004.3	2000.6	1997.0
7.5°	2121.8	2146.5	2160.3	2177.5	2187.5	2188.2	2196.9
10°	2215.3	2247.6	2260.8	2279.2	2290.9	2297.5	2296.8
12.5°	2286.9	2312.2	2341.8	2350.9	2366.7	2375.1	2372.0
15°	2373.2	2413.6	2444.5	2459.8	2479.7	2485.6	2493.7
17.5°	2450.2	2504.4	2540.4	2588.3	2606.4	2617.4	2610.9
20°	2508.4	2579.6	2615.6	2673.0	2704.5	2721.5	2715.6
22.5°	2577.2	2654.3	2720.8	2770.5	2818.6	2841.4	2846.1
25°	2695.0	2800.8	2898.5	2963.9	3023.4	3037.3	3068.3
27.5°	2826.7	2951.4	3055.9	3124.7	3166.1	3181.6	3191.4
30°	2909.5	3033.7	3112.4	3156.4	3169.7	3168.2	3166.7
32.5°	2950.1	3027.8	3043.0	3030.7	3000.4	2974.8	2948.1
35°	2892.7	2834.6	2747.9	2636.2	2553.9	2470.9	2462.9
37.5°	2601.5	2415.9	2271.6	2110.4	2017.4	1960.0	1920.3
40°	2327.6	2116.8	1941.9	1806.0	1711.2	1673.8	1637.0
42.5°	2030.2	1828.7	1673.9	1560.3	1489.0	1447.5	1418.3
45°	1649.4	1471.7	1350.5	1268.2	1211.5	1179.2	1160.8
47.5°	1351.6	1220.1	1117.1	1057.7	1018.6	993.5	993.6
50°	1191.8	1066.1	997.8	950.7	916.9	897.1	900.8
52.5°	1050.1	956.2	897.9	858.5	833.5	821.2	820.9
55°	878.0	810.4	772.2	743.6	726.6	712.7	715.7
57.5°	751.0	694.0	668.5	644.7	632.9	627.4	619.3
60°	672.3	628.2	606.1	587.0	575.3	570.9	562.8
62.5°	602.4	567.7	546.2	530.7	520.0	518.6	512.3
65°	506.2	479.8	460.7	453.4	442.3	439.4	439.4
67.5°	417.4	398.4	383.5	376.7	371.9	372.7	369.1
70°	361.5	346.1	336.5	329.1	325.5	326.2	323.3
72.5°	316.2	299.1	290.7	286.3	281.4	283.3	282.1
75°	239.5	230.7	226.3	221.9	219.0	217.4	216.0
77.5°	175.9	168.1	164.8	162.2	162.7	159.1	161.9
80°	135.9	129.3	127.1	123.5	122.7	122.7	122.0
82.5°	99.4	95.8	94.2	91.1	89.8	91.0	89.1
85°	51.5	48.4	47.8	47.8	46.3	44.9	48.4
87.5°	20.1	17.8	17.9	17.3	17.3	16.9	15.7
90°	6.4	6.8	7.1	7.4	7.5	7.7	8.0
92.5°	14.2	14.7	15.1	15.3	15.4	15.6	15.7
95°	27.2	27.7	28.1	28.2	28.4	28.5	28.7
97.5°	42.3	42.8	43.1	43.2	43.3	43.4	43.5
100°	53.0	53.6	54.0	54.2	54.4	54.5	54.7
102.5°	63.8	64.6	65.0	65.2	65.4	65.6	65.8
105°	81.0	81.4	81.7	81.9	82.2	82.4	82.7
107.5°	99.5	99.7	99.9	99.8	99.8	99.8	99.8
110°	112.6	112.8	112.9	112.8	112.7	112.6	112.6



TEST NUMBER: P333296-830

CATALOG NUMBER: S125DIP-S1270D365U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	125.5	125.6	125.6	125.5	125.4	125.3	125.2
115°	145.3	145.2	145.2	145.2	145.1	145.0	144.9
117.5°	165.5	165.5	165.4	165.1	164.9	164.6	164.2
120°	178.9	178.9	178.7	178.4	178.1	177.9	177.6
122.5°	192.0	192.0	191.8	191.6	191.3	191.1	190.9
125°	211.4	211.3	211.1	211.1	211.0	210.9	210.8
127.5°	230.8	230.7	230.6	230.5	230.4	230.2	230.1
130°	243.6	243.6	243.5	243.3	243.2	243.0	242.9
132.5°	255.9	255.8	255.7	255.4	255.2	255.1	254.9
135°	274.8	274.8	274.7	274.4	274.1	273.8	273.5
137.5°	293.3	293.4	293.2	292.8	292.5	292.1	291.7
140°	304.9	305.1	305.0	304.6	304.3	303.9	303.5
142.5°	316.2	316.3	316.1	315.8	315.4	315.1	314.7
145°	332.4	332.4	332.3	332.2	331.9	331.7	331.5
147.5°	347.8	348.0	347.8	347.3	346.8	346.3	345.8
150°	357.1	357.1	357.0	356.9	356.8	356.6	356.5
152.5°	366.2	366.4	366.3	366.1	365.8	365.5	365.2
155°	379.0	379.3	379.3	378.9	378.5	378.1	377.8
157.5°	390.0	390.3	390.2	389.7	389.2	388.7	388.2
160°	396.6	396.9	396.9	396.5	396.2	395.8	395.4
162.5°	402.9	403.3	403.3	402.8	402.4	402.0	401.5
165°	411.3	411.6	411.5	411.0	410.7	410.2	409.7
167.5°	417.6	418.1	418.1	417.6	417.2	416.7	416.3
170°	421.4	421.9	421.8	421.3	420.8	420.3	419.7
172.5°	424.0	424.5	424.5	424.0	423.6	423.1	422.6
175°	427.1	427.5	427.4	427.0	426.4	425.9	425.4
177.5°	428.4	428.7	428.7	428.3	427.8	427.4	427.0
180°	428.1	428.1	428.1	428.1	428.1	428.1	428.1

(END OF REPORT)