

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333139-935

Luminaire Tested: **S125DIP-S375D810U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333139-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S375D810U935-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4100.0 lumens
Efficiency: N/A
Efficacy: 131.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333139-935

CATALOG NUMBER: S125DIP-S375D810U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333139-935

CATALOG NUMBER: S125DIP-S375D810U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40	32
1	94	89	86	82	84	81	77	75	64	62	60	49	47	46	35	34	33	27
2	85	78	72	67	76	70	65	61	56	53	50	43	41	38	31	29	28	22
3	78	69	61	56	70	62	56	51	49	45	42	38	35	33	27	25	24	19
4	71	61	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20	16
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	20	18	14
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	16	12
7	55	43	36	30	50	39	33	28	32	27	23	25	21	18	18	16	14	11
8	51	39	32	27	46	36	29	24	29	24	20	22	19	16	16	14	12	10
9	48	36	28	24	43	32	26	22	26	22	18	21	17	15	15	13	11	9
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3249	3249	3249
5°	3255	3225	3245
10°	3236	3202	3220
15°	3201	3163	3177
20°	3151	3110	3115
25°	3096	3046	3043
30°	3030	2976	2961
35°	2958	2902	2861
40°	2885	2822	2780
45°	2806	2747	2693
50°	2719	2659	2579
55°	2634	2558	2486
60°	2533	2457	2370
65°	2415	2335	2257
70°	2298	2194	2119
75°	2094	2026	1956
80°	1863	1834	1789
85°	1623	1652	1564



TEST NUMBER: P333139-935

CATALOG NUMBER: S125DIP-S375D810U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.4	1.2
10°-20°	134.0	3.3
20°-30°	197.8	4.8
30°-40°	230.8	5.6
40°-50°	231.8	5.7
50°-60°	203.5	5.0
60°-70°	151.6	3.7
70°-80°	86.7	2.1
80°-90°	27.1	0.7
90°-100°	33.0	0.8
100°-110°	203.4	5.0
110°-120°	369.0	9.0
120°-130°	473.5	11.5
130°-140°	509.3	12.4
140°-150°	478.1	11.7
150°-160°	386.7	9.4
160°-170°	250.1	6.1
170°-180°	86.3	2.1
0°-30°	379.2	9.2
0°-40°	610.0	14.9
0°-60°	1045.3	25.5
0°-90°	1310.7	32.0
90°-120°	605.4	14.8
90°-150°	2066.3	50.4
90°-180°	2789.0	68.0
0°-180°	4100.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	503	503	503	503	503	
5°	502	501	497	501	501	48
15°	479	477	473	475	475	135
25°	434	432	427	428	427	200
35°	375	373	368	366	363	235
45°	307	305	301	296	295	237
55°	234	232	227	224	221	209
65°	158	157	153	149	148	157
75°	84	83	81	80	78	89
85°	22	22	22	22	21	24
90°	1	6	11	14	16	3
95°	38	35	11	14	14	49
105°	198	200	201	201	200	210
115°	372	375	376	373	369	368
125°	529	533	533	531	529	472
135°	659	663	662	660	656	508
145°	764	766	766	766	762	478
155°	842	838	839	841	836	388
165°	888	884	885	888	883	251
175°	908	905	905	910	904	86
180°	908	908	908	908	908	



TEST NUMBER: P333139-935

CATALOG NUMBER: S125DIP-S375D810U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	503.0	503.0	503.0	503.0	503.0	503.0	503.0	503.0	503.0	503.0	503.0
2.5°	504.2	504.0	503.9	503.6	503.4	502.9	502.2	501.5	500.8	500.1	500.8
5°	502.1	502.0	501.8	501.6	501.4	500.9	500.1	499.2	498.3	497.4	498.2
7.5°	497.6	497.4	497.2	497.1	496.9	496.3	495.3	494.3	493.4	492.4	493.2
10°	493.4	493.3	493.1	492.9	492.8	492.1	491.2	490.2	489.2	488.3	489.0
12.5°	488.4	488.0	487.7	487.4	487.1	486.5	485.5	484.7	483.7	482.8	483.4
15°	478.7	478.5	478.2	477.9	477.6	477.0	476.0	475.1	474.1	473.1	473.6
17.5°	467.6	467.3	466.8	466.5	466.1	465.4	464.3	463.4	462.4	461.3	461.9
20°	458.4	458.2	458.1	457.9	457.7	457.0	455.9	454.7	453.6	452.5	453.1
22.5°	449.2	448.8	448.5	448.2	447.9	447.2	446.1	445.1	443.9	442.9	443.3
25°	434.5	434.1	433.6	433.2	432.7	432.0	430.8	429.6	428.5	427.4	427.6
27.5°	417.4	417.2	416.9	416.6	416.4	415.6	414.5	413.3	412.1	410.9	411.0
30°	406.3	406.0	405.7	405.4	405.2	404.4	403.1	401.7	400.5	399.1	398.9
32.5°	394.2	393.7	393.4	393.0	392.5	391.8	390.5	389.3	388.2	387.0	386.7
35°	375.2	374.9	374.5	374.2	373.8	373.0	371.8	370.6	369.3	368.1	367.6
37.5°	355.6	355.2	354.7	354.2	353.8	353.0	351.8	350.7	349.5	348.4	347.7
40°	342.2	341.7	341.3	340.9	340.4	339.6	338.4	337.2	335.9	334.7	333.9
42.5°	327.9	327.5	327.2	326.7	326.4	325.6	324.3	323.1	321.8	320.6	319.9
45°	307.2	306.9	306.5	306.2	305.7	305.1	304.0	303.0	301.9	300.8	299.8
47.5°	284.9	284.9	284.9	285.0	285.0	284.4	283.1	281.8	280.5	279.2	278.2
50°	270.6	270.4	270.1	269.8	269.5	268.9	267.8	266.7	265.7	264.6	263.5
52.5°	256.0	255.7	255.5	255.4	255.2	254.5	253.4	252.3	251.1	249.9	249.0
55°	233.9	233.7	233.4	233.2	232.9	232.1	230.9	229.7	228.4	227.2	226.4
57.5°	210.9	210.7	210.5	210.4	210.3	209.7	208.6	207.6	206.6	205.5	204.5
60°	196.1	195.8	195.4	195.1	194.8	194.1	193.1	192.2	191.1	190.2	189.3
62.5°	180.9	180.6	180.3	180.0	179.8	179.2	178.4	177.5	176.7	175.9	175.0
65°	158.0	157.8	157.6	157.5	157.3	156.7	155.8	154.7	153.8	152.8	152.0
67.5°	135.8	135.4	135.0	134.7	134.3	133.7	133.0	132.2	131.6	130.9	130.2
70°	121.7	121.3	120.9	120.5	120.0	119.3	118.6	117.8	117.0	116.2	115.6
72.5°	106.5	106.2	105.9	105.6	105.3	104.9	104.4	103.8	103.3	102.8	102.2
75°	83.9	83.8	83.6	83.4	83.3	82.9	82.5	82.1	81.6	81.2	80.9
77.5°	63.2	63.1	63.0	62.9	62.9	62.8	62.5	62.3	62.0	61.7	61.6
80°	50.1	50.1	50.1	50.1	50.1	50.0	49.9	49.7	49.5	49.3	49.2
82.5°	38.7	38.6	38.4	38.2	38.1	38.1	38.0	38.0	37.9	37.9	37.7
85°	21.9	22.0	22.0	22.1	22.2	22.3	22.3	22.3	22.3	22.3	22.2
87.5°	8.7	9.0	9.2	9.5	9.7	9.9	10.0	10.2	10.3	10.4	10.6
90°	0.7	1.9	3.1	4.3	5.4	6.5	7.7	8.7	9.7	10.8	11.5
92.5°	10.3	9.6	8.7	7.8	7.1	7.1	8.0	9.0	9.8	10.8	11.5
95°	38.4	38.0	37.5	37.0	36.6	33.5	27.8	22.1	16.4	10.8	11.5
97.5°	80.2	80.9	81.7	82.6	83.3	78.2	66.9	55.6	44.3	33.1	28.9
100°	112.4	112.9	113.3	113.8	114.3	114.8	115.4	116.0	116.6	117.2	94.9
102.5°	145.3	145.9	146.5	147.0	147.6	148.0	148.4	148.8	149.1	149.5	145.3
105°	197.9	198.5	199.1	199.8	200.4	200.6	200.6	200.6	200.6	200.6	200.6
107.5°	252.6	252.6	252.6	252.6	252.6	252.8	253.0	253.4	253.7	254.0	254.0
110°	288.2	288.2	288.2	288.2	288.2	288.3	288.6	289.0	289.2	289.6	289.1



TEST NUMBER: P333139-935

CATALOG NUMBER: S125DIP-S375D810U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	321.6	321.9	322.3	322.7	323.0	323.3	323.5	323.6	323.8	324.0	323.5
115°	371.7	372.5	373.2	373.9	374.7	375.1	375.3	375.4	375.6	375.7	375.1
117.5°	423.5	423.5	423.4	423.4	423.4	423.7	424.2	424.8	425.4	425.9	425.2
120°	455.8	455.7	455.6	455.4	455.2	455.4	455.8	456.3	456.8	457.2	456.9
122.5°	484.4	485.0	485.5	486.1	486.6	487.1	487.2	487.5	487.7	487.9	487.6
125°	528.6	529.6	530.6	531.8	532.8	533.3	533.3	533.3	533.3	533.3	532.7
127.5°	570.8	571.4	572.2	573.0	573.7	574.0	573.9	573.9	573.8	573.7	573.3
130°	596.6	597.4	598.1	598.8	599.6	600.0	600.2	600.3	600.5	600.6	600.2
132.5°	622.4	623.3	624.1	625.0	625.9	626.2	625.9	625.5	625.2	624.8	624.7
135°	659.2	660.1	661.0	661.9	662.8	663.1	662.8	662.5	662.2	661.9	661.6
137.5°	693.0	693.8	694.6	695.3	696.1	696.4	696.1	695.9	695.6	695.3	695.3
140°	715.1	715.4	715.7	716.0	716.3	716.4	716.2	716.1	715.9	715.7	716.1
142.5°	735.0	735.2	735.4	735.6	735.7	735.9	736.2	736.3	736.6	736.8	736.8
145°	764.2	764.6	764.8	765.2	765.4	765.6	765.6	765.6	765.6	765.6	765.8
147.5°	789.8	789.8	789.7	789.6	789.6	789.6	789.8	790.0	790.2	790.4	790.6
150°	806.0	805.7	805.4	805.1	804.8	804.8	805.1	805.4	805.7	806.0	806.3
152.5°	821.7	821.0	820.3	819.7	819.0	818.8	819.1	819.4	819.7	820.0	820.3
155°	841.7	840.8	839.9	839.0	838.1	837.8	838.1	838.4	838.7	839.0	839.4
157.5°	857.1	856.6	856.1	855.6	855.0	854.7	854.8	854.8	854.8	854.9	855.3
160°	868.0	867.0	866.2	865.2	864.4	864.0	864.1	864.3	864.4	864.5	865.1
162.5°	876.6	875.6	874.8	873.8	873.0	872.6	872.7	872.9	873.1	873.2	874.0
165°	888.1	887.3	886.3	885.5	884.5	884.2	884.3	884.5	884.6	884.8	885.7
167.5°	896.7	895.9	894.9	894.0	893.0	892.7	892.8	892.9	893.1	893.3	894.3
170°	901.6	900.5	899.5	898.5	897.4	897.0	897.1	897.2	897.4	897.6	898.8
172.5°	904.8	903.8	902.8	901.7	900.6	900.3	900.5	900.8	901.0	901.3	902.4
175°	908.4	907.4	906.5	905.7	904.7	904.4	904.5	904.7	904.8	905.0	906.2
177.5°	910.0	909.2	908.5	907.8	907.1	906.8	906.9	907.0	907.1	907.2	908.1
180°	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4



TEST NUMBER: P333139-935

CATALOG NUMBER: S125DIP-S375D810U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	503.0	503.0	503.0	503.0	503.0	503.0	503.0	503.0
2.5°	501.5	502.2	502.9	503.3	503.2	503.1	503.1	503.0
5°	498.9	499.8	500.6	500.9	500.8	500.8	500.7	500.6
7.5°	494.0	494.7	495.5	495.8	495.8	495.7	495.6	495.5
10°	489.7	490.3	491.1	491.4	491.3	491.2	491.1	491.0
12.5°	484.0	484.6	485.1	485.3	485.3	485.3	485.3	485.3
15°	474.0	474.4	474.9	475.1	475.1	475.1	475.1	475.1
17.5°	462.4	463.0	463.6	463.6	463.1	462.7	462.3	461.8
20°	453.7	454.3	454.9	455.0	454.5	454.1	453.7	453.2
22.5°	443.7	444.1	444.5	444.5	444.3	443.9	443.7	443.3
25°	427.7	427.9	428.1	428.0	427.7	427.5	427.2	427.0
27.5°	411.0	411.0	411.0	411.0	410.6	410.4	410.1	409.8
30°	398.7	398.6	398.4	398.2	398.0	397.7	397.4	397.1
32.5°	386.4	386.1	385.7	385.4	384.9	384.4	383.9	383.4
35°	367.2	366.8	366.3	365.8	365.1	364.3	363.6	362.9
37.5°	347.1	346.4	345.7	345.2	344.7	344.4	344.0	343.5
40°	333.0	332.3	331.5	331.0	330.7	330.4	330.1	329.8
42.5°	319.2	318.5	317.7	317.2	316.8	316.3	316.0	315.6
45°	298.7	297.6	296.6	295.9	295.7	295.4	295.2	294.9
47.5°	277.1	276.0	274.9	274.1	273.5	272.9	272.2	271.6
50°	262.3	261.1	260.0	259.2	258.5	257.9	257.3	256.7
52.5°	248.0	246.9	245.9	245.1	244.4	243.7	243.1	242.4
55°	225.6	224.8	224.0	223.3	222.7	222.1	221.4	220.8
57.5°	203.5	202.4	201.4	200.7	200.4	200.0	199.7	199.3
60°	188.5	187.5	186.7	185.9	185.3	184.7	184.1	183.5
62.5°	174.0	173.0	172.0	171.3	170.9	170.4	169.9	169.4
65°	151.2	150.4	149.6	149.0	148.7	148.4	148.0	147.7
67.5°	129.5	128.8	128.1	127.7	127.5	127.3	127.1	126.8
70°	115.1	114.6	114.1	113.7	113.3	113.0	112.5	112.2
72.5°	101.6	101.0	100.4	100.0	99.6	99.3	98.8	98.5
75°	80.7	80.4	80.1	79.8	79.5	79.1	78.8	78.4
77.5°	61.5	61.3	61.1	61.0	60.7	60.4	60.2	59.9
80°	49.2	49.1	49.0	48.8	48.6	48.5	48.3	48.1
82.5°	37.5	37.4	37.3	37.1	37.1	37.1	37.0	37.0
85°	22.1	22.0	22.0	21.8	21.6	21.4	21.3	21.1
87.5°	10.8	10.8	11.0	11.1	11.0	10.9	10.9	10.8
90°	12.3	13.0	13.8	14.4	14.8	15.2	15.7	16.2
92.5°	12.3	13.0	13.8	14.2	14.5	14.6	14.9	15.1
95°	12.3	13.0	13.8	14.1	14.1	14.1	14.1	14.1
97.5°	24.7	20.5	16.3	14.1	14.1	14.1	14.1	14.1
100°	72.6	50.3	28.0	16.5	15.9	15.3	14.7	14.1
102.5°	141.0	136.8	132.6	125.4	115.2	105.0	94.9	84.7
105°	200.6	200.6	200.6	200.6	200.4	200.3	200.1	200.0
107.5°	254.1	254.1	254.1	253.9	253.5	253.0	252.5	252.1
110°	288.6	288.2	287.7	287.6	287.7	287.9	288.0	288.2



TEST NUMBER: P333139-935

CATALOG NUMBER: S125DIP-S375D810U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	322.9	322.3	321.8	321.3	321.2	320.9	320.7	320.6
115°	374.5	373.9	373.3	372.6	371.7	370.7	369.9	369.0
117.5°	424.4	423.6	422.8	422.2	421.9	421.5	421.1	420.7
120°	456.6	456.3	456.0	455.5	454.7	454.0	453.2	452.5
122.5°	487.3	487.0	486.7	486.1	485.3	484.4	483.5	482.7
125°	532.1	531.5	530.9	530.4	529.9	529.4	529.0	528.6
127.5°	573.0	572.7	572.4	571.6	570.6	569.5	568.3	567.2
130°	599.7	599.3	598.8	598.2	597.4	596.8	596.0	595.2
132.5°	624.7	624.6	624.5	624.1	623.4	622.6	621.8	621.1
135°	661.3	661.0	660.7	660.1	659.2	658.3	657.4	656.5
137.5°	695.4	695.4	695.5	695.2	694.4	693.6	692.8	692.1
140°	716.4	716.7	717.0	716.7	715.7	714.9	713.9	713.1
142.5°	736.9	736.9	737.0	736.6	735.7	734.8	733.9	733.0
145°	765.9	766.0	766.2	765.8	764.9	764.1	763.1	762.2
147.5°	790.7	790.9	791.1	790.7	789.5	788.5	787.4	786.4
150°	806.6	806.9	807.2	806.8	805.6	804.3	803.1	801.9
152.5°	820.6	820.9	821.2	820.8	819.8	818.6	817.6	816.5
155°	839.9	840.3	840.8	840.4	839.2	838.0	836.8	835.6
157.5°	855.8	856.4	856.8	856.4	855.2	854.0	852.8	851.6
160°	865.7	866.3	866.9	866.7	865.5	864.3	863.1	861.9
162.5°	874.9	875.7	876.5	876.3	874.9	873.7	872.4	871.1
165°	886.6	887.4	888.4	888.2	887.0	885.8	884.6	883.4
167.5°	895.4	896.5	897.6	897.4	896.0	894.8	893.4	892.1
170°	899.9	901.1	902.3	902.2	901.0	899.6	898.2	896.9
172.5°	903.4	904.6	905.7	905.5	904.1	902.8	901.5	900.1
175°	907.3	908.5	909.7	909.6	908.4	907.0	905.7	904.3
177.5°	909.0	909.7	910.6	910.6	909.6	908.6	907.7	906.7
180°	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4

(END OF REPORT)