

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333304-830

Luminaire Tested: **S125DIP-S1270D590U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333304-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S1270D590U830-4F0-1E-UDD-A  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 590 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7113.9 lumens  
Efficiency: N/A  
Efficacy: 129.1 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 55.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333304-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333304-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	69
1	102	98	94	91	96	93	89	86	83	80	78	74	72	70	65	64	63	59
2	93	86	80	75	88	81	76	71	73	69	65	65	62	59	58	55	53	49
3	85	76	68	62	80	72	65	60	65	59	55	58	54	50	51	48	46	42
4	78	67	59	53	74	64	57	51	58	52	47	52	47	43	46	42	39	36
5	72	60	52	46	68	57	50	44	52	46	41	46	42	38	42	38	34	32
6	66	54	46	40	63	52	44	38	47	40	36	42	37	33	38	34	30	28
7	62	49	41	35	58	47	39	34	42	36	32	38	33	29	35	30	27	25
8	57	45	37	31	54	43	35	30	39	33	28	35	30	26	32	27	24	22
9	53	41	33	28	50	39	32	27	36	30	25	32	27	24	29	25	22	20
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	27	23	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	11180	11180	11180	11180
5°	12947	11218	9822	11218
10°	15062	11160	8605	11160
15°	16673	11078	7938	11078
20°	18664	10948	7403	10948
25°	21865	10802	7142	10802
30°	23616	10657	6915	10657
35°	19418	10387	6766	10387
40°	13801	10010	6604	10010
45°	10602	9502	6509	9502
50°	9051	8874	6497	8874
55°	8059	8257	6552	8257
60°	7270	7582	6719	7582
65°	6715	6906	6894	6906
70°	6105	6201	6992	6201
75°	5390	5465	6932	5465
80°	4537	4456	6338	4456
85°	3586	3216	5120	3216



TEST NUMBER: P333304-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	166.6	2.3
10°-20°	496.2	7.0
20°-30°	805.7	11.3
30°-40°	982.8	13.8
40°-50°	894.0	12.6
50°-60°	712.1	10.0
60°-70°	496.0	7.0
70°-80°	264.5	3.7
80°-90°	68.3	1.0
90°-100°	26.4	0.4
100°-110°	162.5	2.3
110°-120°	294.7	4.1
120°-130°	378.2	5.3
130°-140°	406.7	5.7
140°-150°	381.8	5.4
150°-160°	308.8	4.3
160°-170°	199.7	2.8
170°-180°	68.9	1.0
0°-30°	1468.5	20.6
0°-40°	2451.2	34.5
0°-60°	4057.4	57.0
0°-90°	4886.2	68.7
90°-120°	483.5	6.8
90°-150°	1650.2	23.2
90°-180°	2228.0	31.3
0°-180°	7113.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1731	1731	1731	1731	1731	
5°	1997	1730	1515	1730	1997	201
15°	2494	1657	1187	1657	2494	714
25°	3068	1516	1002	1516	3068	1401
35°	2463	1317	858	1317	2463	1507
45°	1161	1040	713	1040	1161	929
55°	716	733	582	733	716	645
65°	439	452	451	452	439	436
75°	216	219	278	219	216	233
85°	48	43	69	43	48	56
90°	13	1	13	1	13	7
95°	11	31	11	31	11	9
105°	160	158	160	158	160	144
115°	295	297	295	297	295	293
125°	422	422	422	422	422	376
135°	524	526	524	526	524	405
145°	609	610	609	610	609	380
155°	667	672	667	672	667	308
165°	706	709	706	709	706	199
175°	722	726	722	726	722	69
180°	726	726	726	726	726	



TEST NUMBER: P333304-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1
2.5°	1831.0	1828.6	1826.3	1821.6	1825.0	1815.1	1810.3	1802.1	1792.2	1788.7	1784.5
5°	1997.0	2000.6	2004.3	1989.0	1990.4	1980.1	1956.6	1937.5	1922.0	1902.2	1888.3
7.5°	2196.9	2188.2	2187.5	2177.5	2160.3	2146.5	2121.8	2090.3	2059.9	2025.2	1996.6
10°	2296.8	2297.5	2290.9	2279.2	2260.8	2247.6	2215.3	2184.3	2146.9	2102.8	2071.2
12.5°	2372.0	2375.1	2366.7	2350.9	2341.8	2312.2	2286.9	2250.2	2205.6	2170.4	2122.3
15°	2493.7	2485.6	2479.7	2459.8	2444.5	2413.6	2373.2	2335.0	2286.5	2241.6	2196.9
17.5°	2610.9	2617.4	2606.4	2588.3	2540.4	2504.4	2450.2	2397.8	2337.5	2277.4	2223.9
20°	2715.6	2721.5	2704.5	2673.0	2615.6	2579.6	2508.4	2440.8	2371.0	2293.9	2235.1
22.5°	2846.1	2841.4	2818.6	2770.5	2720.8	2654.3	2577.2	2494.8	2407.4	2320.3	2242.1
25°	3068.3	3037.3	3023.4	2963.9	2898.5	2800.8	2695.0	2574.5	2465.8	2350.4	2250.5
27.5°	3191.4	3181.6	3166.1	3124.7	3055.9	2951.4	2826.7	2679.8	2526.5	2380.9	2250.0
30°	3166.7	3168.2	3169.7	3156.4	3112.4	3033.7	2909.5	2751.6	2569.4	2405.6	2254.2
32.5°	2948.1	2974.8	3000.4	3030.7	3043.0	3027.8	2950.1	2807.5	2619.9	2433.7	2251.8
35°	2462.9	2470.9	2553.9	2636.2	2747.9	2834.6	2892.7	2829.4	2671.4	2457.7	2249.0
37.5°	1920.3	1960.0	2017.4	2110.4	2271.6	2415.9	2601.5	2686.9	2635.9	2465.5	2243.9
40°	1637.0	1673.8	1711.2	1806.0	1941.9	2116.8	2327.6	2507.6	2549.5	2440.8	2226.3
42.5°	1418.3	1447.5	1489.0	1560.3	1673.9	1828.7	2030.2	2265.5	2410.2	2369.1	2189.2
45°	1160.8	1179.2	1211.5	1268.2	1350.5	1471.7	1649.4	1906.7	2130.7	2204.9	2101.3
47.5°	993.6	993.5	1018.6	1057.7	1117.1	1220.1	1351.6	1553.1	1792.4	1969.5	1961.3
50°	900.8	897.1	916.9	950.7	997.8	1066.1	1191.8	1352.6	1582.6	1783.2	1839.0
52.5°	820.9	821.2	833.5	858.5	897.9	956.2	1050.1	1195.1	1391.6	1597.4	1702.7
55°	715.7	712.7	726.6	743.6	772.2	810.4	878.0	988.9	1148.4	1351.1	1487.8
57.5°	619.3	627.4	632.9	644.7	668.5	694.0	751.0	832.5	958.9	1132.9	1277.4
60°	562.8	570.9	575.3	587.0	606.1	628.2	672.3	738.4	845.0	994.9	1138.1
62.5°	512.3	518.6	520.0	530.7	546.2	567.7	602.4	657.9	742.1	873.2	1013.5
65°	439.4	439.4	442.3	453.4	460.7	479.8	506.2	546.7	614.3	716.3	836.1
67.5°	369.1	372.7	371.9	376.7	383.5	398.4	417.4	450.7	500.8	575.3	671.1
70°	323.3	326.2	325.5	329.1	336.5	346.1	361.5	393.0	429.0	493.0	575.3
72.5°	282.1	283.3	281.4	286.3	290.7	299.1	316.2	333.1	366.7	420.8	488.3
75°	216.0	217.4	219.0	221.9	226.3	230.7	239.5	256.5	278.4	318.9	362.2
77.5°	161.9	159.1	162.7	162.2	164.8	168.1	175.9	184.8	202.9	228.5	262.0
80°	122.0	122.7	122.7	123.5	127.1	129.3	135.9	142.5	156.5	175.6	199.2
82.5°	89.1	91.0	89.8	91.1	94.2	95.8	99.4	104.9	113.0	128.0	145.1
85°	48.4	44.9	46.3	47.8	47.8	48.4	51.5	53.6	58.1	63.9	70.5
87.5°	16.7	17.8	18.3	18.2	18.8	18.7	20.9	20.7	22.4	24.0	26.2
90°	12.9	12.5	12.2	11.9	11.5	11.0	10.4	9.8	9.2	8.6	7.7
92.5°	12.1	11.9	11.7	11.5	11.4	11.0	10.4	9.8	9.2	8.6	7.8
95°	11.3	11.3	11.3	11.3	11.3	11.0	10.4	9.8	9.2	8.6	13.1
97.5°	11.3	11.3	11.3	11.3	11.3	13.0	16.3	19.7	23.1	26.5	35.4
100°	11.3	11.8	12.3	12.7	13.2	22.3	40.2	58.0	75.8	93.6	93.1
102.5°	67.7	75.8	83.9	92.0	100.2	105.9	109.2	112.6	116.0	119.4	119.1
105°	159.7	159.9	159.9	160.0	160.2	160.2	160.2	160.2	160.2	160.2	160.2
107.5°	201.3	201.7	202.1	202.5	202.7	202.9	202.9	202.9	202.8	202.8	202.6
110°	230.2	230.1	229.9	229.8	229.7	229.8	230.2	230.5	230.9	231.2	231.0



TEST NUMBER: P333304-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	256.0	256.2	256.3	256.5	256.7	256.9	257.4	257.9	258.4	258.7	258.6
115°	294.7	295.4	296.1	296.8	297.6	298.1	298.6	299.1	299.6	300.1	299.9
117.5°	336.0	336.3	336.6	337.0	337.2	337.7	338.3	338.9	339.6	340.2	339.7
120°	361.4	361.9	362.6	363.2	363.7	364.2	364.4	364.7	364.9	365.1	364.8
122.5°	385.5	386.2	386.8	387.6	388.2	388.7	389.0	389.2	389.5	389.6	389.5
125°	422.2	422.5	422.8	423.2	423.6	424.0	424.4	425.0	425.5	425.9	425.9
127.5°	453.0	453.9	454.8	455.6	456.6	457.1	457.4	457.6	457.9	458.2	458.3
130°	475.4	476.0	476.5	477.2	477.8	478.2	478.6	479.0	479.3	479.7	479.6
132.5°	496.1	496.6	497.2	497.9	498.4	498.8	498.8	498.9	499.0	499.1	499.3
135°	524.3	525.0	525.8	526.5	527.2	527.6	527.9	528.1	528.4	528.6	528.9
137.5°	552.7	553.4	553.9	554.6	555.2	555.4	555.4	555.3	555.3	555.3	555.5
140°	569.5	570.2	570.9	571.7	572.3	572.6	572.3	572.1	571.8	571.7	571.7
142.5°	585.4	586.1	586.8	587.6	588.2	588.6	588.5	588.5	588.4	588.4	588.2
145°	608.7	609.4	610.2	610.9	611.6	611.9	611.8	611.7	611.5	611.4	611.4
147.5°	628.0	628.9	629.7	630.6	631.4	631.8	631.7	631.5	631.4	631.2	631.0
150°	640.5	641.4	642.3	643.4	644.3	644.6	644.4	644.1	643.9	643.7	643.5
152.5°	652.1	652.9	653.8	654.7	655.5	655.8	655.6	655.3	655.2	654.9	654.6
155°	667.3	668.4	669.3	670.2	671.2	671.5	671.1	670.8	670.4	670.1	669.8
157.5°	680.1	681.1	682.0	683.1	684.0	684.3	683.9	683.5	683.2	682.8	682.7
160°	688.3	689.3	690.2	691.2	692.1	692.4	691.9	691.4	691.0	690.5	690.3
162.5°	695.6	696.7	697.8	698.8	699.8	700.0	699.4	698.7	698.0	697.4	697.2
165°	705.5	706.5	707.5	708.4	709.4	709.5	708.8	708.0	707.3	706.6	706.5
167.5°	712.4	713.5	714.5	715.7	716.7	716.8	716.0	715.1	714.3	713.4	713.2
170°	716.3	717.4	718.4	719.5	720.6	720.7	719.7	718.8	717.7	716.8	716.7
172.5°	718.9	719.9	721.0	722.1	723.2	723.3	722.5	721.5	720.7	719.8	719.6
175°	722.2	723.3	724.3	725.5	726.5	726.6	725.6	724.6	723.7	722.7	722.6
177.5°	724.2	724.9	725.7	726.4	727.2	727.3	726.6	725.9	725.3	724.5	724.4
180°	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5



TEST NUMBER: P333304-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1
2.5°	1781.0	1776.9	1772.2	1764.0	1754.0	1748.7	1740.4	1735.1	1724.6	1715.7	1706.4
5°	1871.3	1852.3	1834.7	1811.8	1786.9	1770.7	1751.6	1730.3	1708.3	1685.5	1660.5
7.5°	1965.0	1931.2	1894.4	1854.9	1816.3	1780.7	1746.7	1713.4	1682.2	1644.6	1612.8
10°	2027.9	1985.3	1939.7	1886.0	1833.9	1788.4	1742.0	1701.7	1660.5	1616.4	1577.4
12.5°	2090.7	2034.0	1969.6	1910.7	1848.0	1793.0	1738.5	1687.0	1635.2	1586.4	1541.1
15°	2135.1	2085.2	2025.6	1941.9	1871.3	1795.7	1723.7	1656.8	1594.4	1540.0	1482.7
17.5°	2164.4	2100.0	2036.1	1955.7	1863.3	1778.7	1697.0	1620.5	1550.1	1481.2	1426.0
20°	2169.6	2103.6	2036.6	1958.0	1863.3	1766.3	1684.7	1592.9	1517.2	1446.0	1378.4
22.5°	2167.9	2092.9	2020.2	1939.3	1846.8	1757.5	1658.9	1565.3	1483.1	1413.1	1342.5
25°	2151.3	2071.2	1980.1	1898.6	1807.4	1712.7	1612.8	1515.8	1432.0	1351.9	1282.1
27.5°	2137.5	2033.6	1930.4	1835.3	1747.4	1660.5	1564.8	1465.5	1372.6	1291.5	1225.7
30°	2120.4	2006.6	1890.5	1791.3	1700.9	1616.4	1526.1	1429.1	1332.1	1252.7	1182.2
32.5°	2105.2	1972.5	1849.9	1741.9	1646.2	1564.1	1480.7	1388.5	1293.3	1212.8	1142.2
35°	2075.7	1922.0	1781.7	1659.7	1557.6	1473.1	1403.4	1317.4	1229.9	1152.1	1084.5
37.5°	2038.2	1856.0	1705.3	1577.4	1465.5	1376.5	1311.5	1245.5	1161.6	1086.6	1025.4
40°	2008.7	1808.9	1649.4	1518.7	1402.6	1310.0	1249.8	1187.3	1117.6	1047.7	983.1
42.5°	1971.7	1766.6	1593.1	1452.3	1337.4	1247.2	1183.9	1130.9	1069.3	1004.3	944.2
45°	1903.7	1689.9	1501.8	1350.5	1234.4	1145.5	1080.1	1040.4	994.1	932.4	881.7
47.5°	1803.6	1597.7	1403.2	1247.0	1127.2	1044.8	983.5	945.5	912.9	867.0	821.0
50°	1714.9	1529.0	1332.1	1177.0	1057.2	974.2	917.7	883.2	855.3	819.9	781.0
52.5°	1615.5	1442.6	1262.2	1108.9	990.2	908.4	853.0	822.7	799.4	774.1	735.7
55°	1457.7	1310.8	1143.2	997.8	888.3	808.2	759.7	733.3	714.2	695.0	671.6
57.5°	1283.8	1168.9	1020.6	887.6	786.7	713.9	668.6	642.9	628.0	618.2	604.4
60°	1161.6	1063.2	935.3	814.1	715.7	651.0	606.9	587.0	574.6	566.5	556.2
62.5°	1048.2	967.3	848.9	738.3	652.1	591.0	551.7	532.3	520.5	516.5	508.0
65°	880.9	818.5	720.8	629.0	555.4	503.3	470.2	451.9	444.5	440.1	440.8
67.5°	716.2	678.2	599.6	521.3	462.7	419.0	392.5	378.4	374.8	368.8	368.7
70°	615.7	587.0	520.9	452.6	400.4	366.6	343.1	328.4	324.7	321.8	321.1
72.5°	527.0	501.8	444.5	389.7	342.8	313.1	293.8	284.9	278.9	277.1	277.0
75°	396.1	382.1	336.5	293.1	260.8	240.3	227.1	219.0	214.5	213.8	214.5
77.5°	281.5	269.4	240.4	209.7	189.3	173.7	162.5	159.8	154.8	154.9	154.1
80°	211.6	203.5	185.1	160.9	144.0	130.8	124.9	119.8	118.3	116.1	118.3
82.5°	153.4	144.8	132.2	116.8	102.8	94.9	89.1	87.5	86.5	85.5	86.0
85°	75.7	76.4	69.1	57.3	51.5	47.0	43.4	43.4	42.6	41.8	42.6
87.5°	27.2	25.9	23.4	21.5	18.3	16.4	15.6	16.0	14.4	14.0	14.8
90°	7.0	6.1	5.3	4.3	3.4	2.5	1.5	0.6	1.5	2.5	3.4
92.5°	7.2	6.4	5.7	5.6	6.3	7.0	7.6	8.3	7.6	7.0	6.3
95°	17.7	22.2	26.8	29.2	29.6	30.0	30.3	30.6	30.3	30.0	29.6
97.5°	44.4	53.4	62.4	66.5	65.9	65.3	64.7	64.0	64.7	65.3	65.9
100°	92.7	92.2	91.6	91.2	90.9	90.5	90.2	89.8	90.2	90.5	90.9
102.5°	118.9	118.5	118.2	117.8	117.4	117.0	116.5	116.0	116.5	117.0	117.4
105°	160.2	160.2	160.2	160.0	159.6	159.1	158.5	158.1	158.5	159.1	159.6
107.5°	202.4	202.1	201.9	201.8	201.8	201.8	201.8	201.8	201.8	201.8	201.8
110°	230.7	230.5	230.3	230.2	230.2	230.2	230.2	230.2	230.2	230.2	230.2





TEST NUMBER: P333304-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	258.4	258.4	258.2	258.0	257.7	257.4	257.1	256.8	257.1	257.4	257.7
115°	299.8	299.7	299.6	299.3	298.6	298.0	297.5	296.8	297.5	298.0	298.6
117.5°	339.3	338.8	338.4	338.2	338.2	338.2	338.2	338.3	338.2	338.2	338.2
120°	364.4	364.1	363.7	363.5	363.7	363.8	363.9	364.1	363.9	363.8	363.7
122.5°	389.4	389.2	389.0	388.7	388.2	387.8	387.3	386.8	387.3	387.8	388.2
125°	425.9	425.9	425.9	425.5	424.6	423.8	423.0	422.2	423.0	423.8	424.6
127.5°	458.4	458.4	458.5	458.2	457.6	457.0	456.4	455.8	456.4	457.0	457.6
130°	479.5	479.3	479.2	478.8	478.2	477.7	477.0	476.5	477.0	477.7	478.2
132.5°	499.5	499.8	500.1	499.8	499.2	498.5	497.8	497.1	497.8	498.5	499.2
135°	529.0	529.3	529.6	529.3	528.6	527.9	527.2	526.5	527.2	527.9	528.6
137.5°	555.7	555.9	556.2	555.9	555.3	554.7	554.1	553.5	554.1	554.7	555.3
140°	571.8	572.0	572.1	572.0	571.8	571.6	571.4	571.1	571.4	571.6	571.8
142.5°	588.1	588.0	587.8	587.6	587.5	587.3	587.2	587.0	587.2	587.3	587.5
145°	611.4	611.4	611.4	611.3	611.1	610.9	610.6	610.4	610.6	610.9	611.1
147.5°	630.9	630.7	630.7	630.6	630.7	630.7	630.7	630.7	630.7	630.7	630.7
150°	643.2	643.0	642.7	642.7	643.0	643.2	643.5	643.7	643.5	643.2	643.0
152.5°	654.4	654.1	653.9	654.0	654.6	655.2	655.6	656.2	655.6	655.2	654.6
155°	669.6	669.3	669.1	669.3	670.1	670.8	671.5	672.2	671.5	670.8	670.1
157.5°	682.7	682.7	682.7	682.9	683.2	683.7	684.1	684.6	684.1	683.7	683.2
160°	690.2	690.1	690.0	690.3	691.0	691.7	692.5	693.1	692.5	691.7	691.0
162.5°	697.1	697.0	696.9	697.2	697.9	698.6	699.4	700.0	699.4	698.6	697.9
165°	706.3	706.2	706.2	706.4	707.2	707.8	708.6	709.3	708.6	707.8	707.2
167.5°	713.1	713.0	712.9	713.2	714.0	714.7	715.5	716.1	715.5	714.7	714.0
170°	716.6	716.4	716.3	716.7	717.6	718.4	719.3	720.1	719.3	718.4	717.6
172.5°	719.4	719.2	719.0	719.3	720.1	721.0	721.8	722.6	721.8	721.0	720.1
175°	722.6	722.4	722.3	722.6	723.3	724.0	724.7	725.5	724.7	724.0	723.3
177.5°	724.3	724.2	724.2	724.4	725.0	725.6	726.1	726.7	726.1	725.6	725.0
180°	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5



TEST NUMBER: P333304-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1
2.5°	1701.0	1694.6	1689.3	1677.5	1671.0	1662.3	1655.2	1662.8	1654.6	1658.1	1652.8
5°	1648.0	1627.4	1612.8	1591.4	1573.1	1556.1	1543.7	1541.4	1535.6	1532.7	1523.8
7.5°	1584.2	1558.5	1533.2	1505.3	1481.8	1457.8	1442.6	1429.9	1421.5	1410.5	1403.1
10°	1546.6	1512.1	1482.7	1448.9	1419.5	1393.8	1373.2	1362.9	1353.4	1339.4	1334.3
12.5°	1500.2	1464.4	1428.6	1392.5	1364.2	1335.6	1318.0	1302.4	1295.8	1280.1	1278.5
15°	1444.4	1390.8	1355.6	1318.8	1279.9	1256.4	1241.7	1224.8	1217.5	1206.5	1198.3
17.5°	1378.1	1330.1	1286.1	1248.0	1214.7	1194.9	1176.6	1165.0	1152.4	1145.2	1131.9
20°	1329.8	1284.3	1240.2	1199.9	1174.1	1151.3	1136.6	1125.6	1112.4	1108.7	1095.5
22.5°	1289.3	1239.1	1196.7	1162.8	1134.7	1109.0	1093.2	1085.6	1076.6	1065.3	1062.5
25°	1223.3	1171.2	1135.2	1101.4	1076.4	1052.9	1041.9	1032.3	1023.5	1015.4	1012.5
27.5°	1166.3	1119.7	1076.9	1046.4	1024.6	1003.2	993.5	981.9	975.4	968.9	961.0
30°	1126.3	1078.6	1041.1	1011.7	988.3	969.1	958.8	950.7	944.9	939.0	934.6
32.5°	1085.2	1040.9	1004.7	975.9	952.3	937.9	928.9	923.1	916.6	909.6	904.0
35°	1030.9	982.3	947.1	922.1	903.7	892.7	882.4	877.2	870.0	870.0	864.0
37.5°	969.6	927.7	896.5	873.7	857.2	847.4	836.3	832.7	828.0	824.9	822.9
40°	933.1	894.2	864.8	842.0	824.3	816.2	807.5	801.6	798.6	794.9	793.5
42.5°	895.5	858.3	830.1	809.1	793.8	786.9	778.6	774.6	768.6	763.8	763.0
45°	838.3	802.3	776.7	759.7	746.5	738.4	733.3	724.4	721.5	715.7	714.9
47.5°	784.1	749.6	724.3	710.5	698.9	692.3	684.2	675.3	672.0	669.0	668.7
50°	743.6	712.0	688.4	675.2	664.2	654.7	646.6	640.6	638.5	638.5	640.0
52.5°	702.4	675.5	655.5	639.3	629.0	618.8	611.3	607.8	604.4	607.9	610.6
55°	642.2	615.0	600.3	584.8	574.6	562.8	559.1	557.7	555.4	561.4	564.3
57.5°	578.3	559.3	542.1	526.8	517.6	510.8	505.8	504.9	509.1	511.8	521.3
60°	537.8	515.8	500.4	488.6	477.6	473.2	471.7	470.2	473.2	481.3	493.7
62.5°	493.1	475.2	458.6	449.8	441.7	434.4	434.0	435.0	440.8	450.1	462.6
65°	427.6	412.2	401.1	390.9	384.3	379.8	381.4	384.3	390.9	403.4	417.4
67.5°	361.1	350.4	340.6	332.2	325.9	325.9	327.4	331.8	339.6	354.0	366.7
70°	318.1	306.4	298.3	294.6	289.5	286.5	291.0	298.3	304.9	318.1	329.1
72.5°	275.2	265.2	258.9	256.5	254.2	251.8	253.4	261.3	270.2	283.4	296.2
75°	211.6	207.9	203.5	200.6	198.4	199.8	201.3	208.7	216.0	230.0	244.7
77.5°	154.5	150.6	148.0	147.2	146.1	146.8	150.9	156.4	163.5	173.7	184.8
80°	116.8	115.4	113.9	113.1	113.1	113.9	119.8	123.5	130.1	139.6	148.5
82.5°	85.1	84.2	83.9	83.8	84.4	84.5	88.0	92.8	98.3	105.5	113.1
85°	44.9	43.4	45.5	46.3	44.9	47.0	48.4	51.5	53.6	57.3	61.0
87.5°	15.6	17.0	16.5	17.2	17.4	18.8	18.3	20.7	22.1	23.4	22.9
90°	4.3	5.3	6.1	7.0	7.7	8.6	9.2	9.8	10.4	11.0	11.5
92.5°	5.6	5.7	6.4	7.2	7.8	8.6	9.2	9.8	10.4	11.0	11.4
95°	29.2	26.8	22.2	17.7	13.1	8.6	9.2	9.8	10.4	11.0	11.3
97.5°	66.5	62.4	53.4	44.4	35.4	26.5	23.1	19.7	16.3	13.0	11.3
100°	91.2	91.6	92.2	92.7	93.1	93.6	75.8	58.0	40.2	22.3	13.2
102.5°	117.8	118.2	118.5	118.9	119.1	119.4	116.0	112.6	109.2	105.9	100.2
105°	160.0	160.2	160.2	160.2	160.2	160.2	160.2	160.2	160.2	160.2	160.2
107.5°	201.8	201.9	202.1	202.4	202.6	202.8	202.8	202.9	202.9	202.9	202.7
110°	230.2	230.3	230.5	230.7	231.0	231.2	230.9	230.5	230.2	229.8	229.7



TEST NUMBER: P333304-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	258.0	258.2	258.4	258.4	258.6	258.7	258.4	257.9	257.4	256.9	256.7
115°	299.3	299.6	299.7	299.8	299.9	300.1	299.6	299.1	298.6	298.1	297.6
117.5°	338.2	338.4	338.8	339.3	339.7	340.2	339.6	338.9	338.3	337.7	337.2
120°	363.5	363.7	364.1	364.4	364.8	365.1	364.9	364.7	364.4	364.2	363.7
122.5°	388.7	389.0	389.2	389.4	389.5	389.6	389.5	389.2	389.0	388.7	388.2
125°	425.5	425.9	425.9	425.9	425.9	425.9	425.5	425.0	424.4	424.0	423.6
127.5°	458.2	458.5	458.4	458.4	458.3	458.2	457.9	457.6	457.4	457.1	456.6
130°	478.8	479.2	479.3	479.5	479.6	479.7	479.3	479.0	478.6	478.2	477.8
132.5°	499.8	500.1	499.8	499.5	499.3	499.1	499.0	498.9	498.8	498.8	498.4
135°	529.3	529.6	529.3	529.0	528.9	528.6	528.4	528.1	527.9	527.6	527.2
137.5°	555.9	556.2	555.9	555.7	555.5	555.3	555.3	555.3	555.4	555.4	555.2
140°	572.0	572.1	572.0	571.8	571.7	571.7	571.8	572.1	572.3	572.6	572.3
142.5°	587.6	587.8	588.0	588.1	588.2	588.4	588.4	588.5	588.5	588.6	588.2
145°	611.3	611.4	611.4	611.4	611.4	611.4	611.5	611.7	611.8	611.9	611.6
147.5°	630.6	630.7	630.7	630.9	631.0	631.2	631.4	631.5	631.7	631.8	631.4
150°	642.7	642.7	643.0	643.2	643.5	643.7	643.9	644.1	644.4	644.6	644.3
152.5°	654.0	653.9	654.1	654.4	654.6	654.9	655.2	655.3	655.6	655.8	655.5
155°	669.3	669.1	669.3	669.6	669.8	670.1	670.4	670.8	671.1	671.5	671.2
157.5°	682.9	682.7	682.7	682.7	682.7	682.8	683.2	683.5	683.9	684.3	684.0
160°	690.3	690.0	690.1	690.2	690.3	690.5	691.0	691.4	691.9	692.4	692.1
162.5°	697.2	696.9	697.0	697.1	697.2	697.4	698.0	698.7	699.4	700.0	699.8
165°	706.4	706.2	706.2	706.3	706.5	706.6	707.3	708.0	708.8	709.5	709.4
167.5°	713.2	712.9	713.0	713.1	713.2	713.4	714.3	715.1	716.0	716.8	716.7
170°	716.7	716.3	716.4	716.6	716.7	716.8	717.7	718.8	719.7	720.7	720.6
172.5°	719.3	719.0	719.2	719.4	719.6	719.8	720.7	721.5	722.5	723.3	723.2
175°	722.6	722.3	722.4	722.6	722.6	722.7	723.7	724.6	725.6	726.6	726.5
177.5°	724.4	724.2	724.2	724.3	724.4	724.5	725.3	725.9	726.6	727.3	727.2
180°	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5



TEST NUMBER: P333304-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1
2.5°	1649.4	1653.4	1649.9	1654.6	1649.9	1653.4	1649.4	1652.8	1658.1	1654.6	1662.8
5°	1520.1	1513.5	1518.0	1515.0	1518.0	1513.5	1520.1	1523.8	1532.7	1535.6	1541.4
7.5°	1400.8	1394.5	1387.3	1383.9	1387.3	1394.5	1400.8	1403.1	1410.5	1421.5	1429.9
10°	1326.2	1318.1	1317.4	1312.2	1317.4	1318.1	1326.2	1334.3	1339.4	1353.4	1362.9
12.5°	1271.5	1264.0	1255.7	1253.5	1255.7	1264.0	1271.5	1278.5	1280.1	1295.8	1302.4
15°	1193.9	1188.1	1182.9	1187.3	1182.9	1188.1	1193.9	1198.3	1206.5	1217.5	1224.8
17.5°	1129.4	1124.5	1123.7	1118.2	1123.7	1124.5	1129.4	1131.9	1145.2	1152.4	1165.0
20°	1088.9	1085.2	1086.7	1077.1	1086.7	1085.2	1088.9	1095.5	1108.7	1112.4	1125.6
22.5°	1056.6	1049.3	1048.5	1046.6	1048.5	1049.3	1056.6	1062.5	1065.3	1076.6	1085.6
25°	1005.9	1002.2	998.5	1002.2	998.5	1002.2	1005.9	1012.5	1015.4	1023.5	1032.3
27.5°	961.6	957.2	956.2	956.6	956.2	957.2	961.6	961.0	968.9	975.4	981.9
30°	934.6	927.3	927.9	927.3	927.9	927.3	934.6	934.6	939.0	944.9	950.7
32.5°	905.2	900.2	899.2	897.9	899.2	900.2	905.2	904.0	909.6	916.6	923.1
35°	861.9	861.9	858.2	858.2	858.2	861.9	861.9	864.0	870.0	870.0	877.2
37.5°	821.1	820.4	818.2	818.5	818.2	820.4	821.1	822.9	824.9	828.0	832.7
40°	790.6	789.9	787.6	783.3	787.6	789.9	790.6	793.5	794.9	798.6	801.6
42.5°	761.2	758.7	757.6	756.2	757.6	758.7	761.2	763.0	763.8	768.6	774.6
45°	714.9	714.9	713.4	712.7	713.4	714.9	714.9	714.9	715.7	721.5	724.4
47.5°	670.0	671.3	674.0	673.6	674.0	671.3	670.0	668.7	669.0	672.0	675.3
50°	642.9	643.7	645.8	646.6	645.8	643.7	642.9	640.0	638.5	638.5	640.6
52.5°	612.9	617.2	620.0	619.5	620.0	617.2	612.9	610.6	607.9	604.4	607.8
55°	570.9	576.0	581.2	581.9	581.2	576.0	570.9	564.3	561.4	555.4	557.7
57.5°	529.3	536.5	542.0	543.7	542.0	536.5	529.3	521.3	511.8	509.1	504.9
60°	501.1	510.7	517.3	520.2	517.3	510.7	501.1	493.7	481.3	473.2	470.2
62.5°	474.0	484.7	491.3	492.0	491.3	484.7	474.0	462.6	450.1	440.8	435.0
65°	429.8	440.8	446.7	451.1	446.7	440.8	429.8	417.4	403.4	390.9	384.3
67.5°	382.2	393.2	399.7	403.2	399.7	393.2	382.2	366.7	354.0	339.6	331.8
70°	347.5	358.5	367.4	370.3	367.4	358.5	347.5	329.1	318.1	304.9	298.3
72.5°	313.4	323.3	330.4	333.8	330.4	323.3	313.4	296.2	283.4	270.2	261.3
75°	254.2	267.4	274.1	277.8	274.1	267.4	254.2	244.7	230.0	216.0	208.7
77.5°	196.0	208.1	212.1	214.0	212.1	208.1	196.0	184.8	173.7	163.5	156.4
80°	157.2	164.6	169.8	170.4	169.8	164.6	157.2	148.5	139.6	130.1	123.5
82.5°	120.8	127.0	128.6	130.4	128.6	127.0	120.8	113.1	105.5	98.3	92.8
85°	66.2	69.1	69.8	69.1	69.8	69.1	66.2	61.0	57.3	53.6	51.5
87.5°	24.1	23.6	23.7	24.9	23.7	23.6	24.1	22.9	23.4	22.1	20.7
90°	11.9	12.2	12.5	12.9	12.5	12.2	11.9	11.5	11.0	10.4	9.8
92.5°	11.5	11.7	11.9	12.1	11.9	11.7	11.5	11.4	11.0	10.4	9.8
95°	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.0	10.4	9.8
97.5°	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.3	13.0	16.3	19.7
100°	12.7	12.3	11.8	11.3	11.8	12.3	12.7	13.2	22.3	40.2	58.0
102.5°	92.0	83.9	75.8	67.7	75.8	83.9	92.0	100.2	105.9	109.2	112.6
105°	160.0	159.9	159.9	159.7	159.9	159.9	160.0	160.2	160.2	160.2	160.2
107.5°	202.5	202.1	201.7	201.3	201.7	202.1	202.5	202.7	202.9	202.9	202.9
110°	229.8	229.9	230.1	230.2	230.1	229.9	229.8	229.7	229.8	230.2	230.5



TEST NUMBER: P333304-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	256.5	256.3	256.2	256.0	256.2	256.3	256.5	256.7	256.9	257.4	257.9
115°	296.8	296.1	295.4	294.7	295.4	296.1	296.8	297.6	298.1	298.6	299.1
117.5°	337.0	336.6	336.3	336.0	336.3	336.6	337.0	337.2	337.7	338.3	338.9
120°	363.2	362.6	361.9	361.4	361.9	362.6	363.2	363.7	364.2	364.4	364.7
122.5°	387.6	386.8	386.2	385.5	386.2	386.8	387.6	388.2	388.7	389.0	389.2
125°	423.2	422.8	422.5	422.2	422.5	422.8	423.2	423.6	424.0	424.4	425.0
127.5°	455.6	454.8	453.9	453.0	453.9	454.8	455.6	456.6	457.1	457.4	457.6
130°	477.2	476.5	476.0	475.4	476.0	476.5	477.2	477.8	478.2	478.6	479.0
132.5°	497.9	497.2	496.6	496.1	496.6	497.2	497.9	498.4	498.8	498.8	498.9
135°	526.5	525.8	525.0	524.3	525.0	525.8	526.5	527.2	527.6	527.9	528.1
137.5°	554.6	553.9	553.4	552.7	553.4	553.9	554.6	555.2	555.4	555.4	555.3
140°	571.7	570.9	570.2	569.5	570.2	570.9	571.7	572.3	572.6	572.3	572.1
142.5°	587.6	586.8	586.1	585.4	586.1	586.8	587.6	588.2	588.6	588.5	588.5
145°	610.9	610.2	609.4	608.7	609.4	610.2	610.9	611.6	611.9	611.8	611.7
147.5°	630.6	629.7	628.9	628.0	628.9	629.7	630.6	631.4	631.8	631.7	631.5
150°	643.4	642.3	641.4	640.5	641.4	642.3	643.4	644.3	644.6	644.4	644.1
152.5°	654.7	653.8	652.9	652.1	652.9	653.8	654.7	655.5	655.8	655.6	655.3
155°	670.2	669.3	668.4	667.3	668.4	669.3	670.2	671.2	671.5	671.1	670.8
157.5°	683.1	682.0	681.1	680.1	681.1	682.0	683.1	684.0	684.3	683.9	683.5
160°	691.2	690.2	689.3	688.3	689.3	690.2	691.2	692.1	692.4	691.9	691.4
162.5°	698.8	697.8	696.7	695.6	696.7	697.8	698.8	699.8	700.0	699.4	698.7
165°	708.4	707.5	706.5	705.5	706.5	707.5	708.4	709.4	709.5	708.8	708.0
167.5°	715.7	714.5	713.5	712.4	713.5	714.5	715.7	716.7	716.8	716.0	715.1
170°	719.5	718.4	717.4	716.3	717.4	718.4	719.5	720.6	720.7	719.7	718.8
172.5°	722.1	721.0	719.9	718.9	719.9	721.0	722.1	723.2	723.3	722.5	721.5
175°	725.5	724.3	723.3	722.2	723.3	724.3	725.5	726.5	726.6	725.6	724.6
177.5°	726.4	725.7	724.9	724.2	724.9	725.7	726.4	727.2	727.3	726.6	725.9
180°	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5



TEST NUMBER: P333304-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1
2.5°	1655.2	1662.3	1671.0	1677.5	1689.3	1694.6	1701.0	1706.4	1715.7	1724.6	1735.1
5°	1543.7	1556.1	1573.1	1591.4	1612.8	1627.4	1648.0	1660.5	1685.5	1708.3	1730.3
7.5°	1442.6	1457.8	1481.8	1505.3	1533.2	1558.5	1584.2	1612.8	1644.6	1682.2	1713.4
10°	1373.2	1393.8	1419.5	1448.9	1482.7	1512.1	1546.6	1577.4	1616.4	1660.5	1701.7
12.5°	1318.0	1335.6	1364.2	1392.5	1428.6	1464.4	1500.2	1541.1	1586.4	1635.2	1687.0
15°	1241.7	1256.4	1279.9	1318.8	1355.6	1390.8	1444.4	1482.7	1540.0	1594.4	1656.8
17.5°	1176.6	1194.9	1214.7	1248.0	1286.1	1330.1	1378.1	1426.0	1481.2	1550.1	1620.5
20°	1136.6	1151.3	1174.1	1199.9	1240.2	1284.3	1329.8	1378.4	1446.0	1517.2	1592.9
22.5°	1093.2	1109.0	1134.7	1162.8	1196.7	1239.1	1289.3	1342.5	1413.1	1483.1	1565.3
25°	1041.9	1052.9	1076.4	1101.4	1135.2	1171.2	1223.3	1282.1	1351.9	1432.0	1515.8
27.5°	993.5	1003.2	1024.6	1046.4	1076.9	1119.7	1166.3	1225.7	1291.5	1372.6	1465.5
30°	958.8	969.1	988.3	1011.7	1041.1	1078.6	1126.3	1182.2	1252.7	1332.1	1429.1
32.5°	928.9	937.9	952.3	975.9	1004.7	1040.9	1085.2	1142.2	1212.8	1293.3	1388.5
35°	882.4	892.7	903.7	922.1	947.1	982.3	1030.9	1084.5	1152.1	1229.9	1317.4
37.5°	836.3	847.4	857.2	873.7	896.5	927.7	969.6	1025.4	1086.6	1161.6	1245.5
40°	807.5	816.2	824.3	842.0	864.8	894.2	933.1	983.1	1047.7	1117.6	1187.3
42.5°	778.6	786.9	793.8	809.1	830.1	858.3	895.5	944.2	1004.3	1069.3	1130.9
45°	733.3	738.4	746.5	759.7	776.7	802.3	838.3	881.7	932.4	994.1	1040.4
47.5°	684.2	692.3	698.9	710.5	724.3	749.6	784.1	821.0	867.0	912.9	945.5
50°	646.6	654.7	664.2	675.2	688.4	712.0	743.6	781.0	819.9	855.3	883.2
52.5°	611.3	618.8	629.0	639.3	655.5	675.5	702.4	735.7	774.1	799.4	822.7
55°	559.1	562.8	574.6	584.8	600.3	615.0	642.2	671.6	695.0	714.2	733.3
57.5°	505.8	510.8	517.6	526.8	542.1	559.3	578.3	604.4	618.2	628.0	642.9
60°	471.7	473.2	477.6	488.6	500.4	515.8	537.8	556.2	566.5	574.6	587.0
62.5°	434.0	434.4	441.7	449.8	458.6	475.2	493.1	508.0	516.5	520.5	532.3
65°	381.4	379.8	384.3	390.9	401.1	412.2	427.6	440.8	440.1	444.5	451.9
67.5°	327.4	325.9	325.9	332.2	340.6	350.4	361.1	368.7	368.8	374.8	378.4
70°	291.0	286.5	289.5	294.6	298.3	306.4	318.1	321.1	321.8	324.7	328.4
72.5°	253.4	251.8	254.2	256.5	258.9	265.2	275.2	277.0	277.1	278.9	284.9
75°	201.3	199.8	198.4	200.6	203.5	207.9	211.6	214.5	213.8	214.5	219.0
77.5°	150.9	146.8	146.1	147.2	148.0	150.6	154.5	154.1	154.9	154.8	159.8
80°	119.8	113.9	113.1	113.1	113.9	115.4	116.8	118.3	116.1	118.3	119.8
82.5°	88.0	84.5	84.4	83.8	83.9	84.2	85.1	86.0	85.5	86.5	87.5
85°	48.4	47.0	44.9	46.3	45.5	43.4	44.9	42.6	41.8	42.6	43.4
87.5°	18.3	18.8	17.4	17.2	16.5	17.0	15.6	14.8	14.0	14.4	16.0
90°	9.2	8.6	7.7	7.0	6.1	5.3	4.3	3.4	2.5	1.5	0.6
92.5°	9.2	8.6	7.8	7.2	6.4	5.7	5.6	6.3	7.0	7.6	8.3
95°	9.2	8.6	13.1	17.7	22.2	26.8	29.2	29.6	30.0	30.3	30.6
97.5°	23.1	26.5	35.4	44.4	53.4	62.4	66.5	65.9	65.3	64.7	64.0
100°	75.8	93.6	93.1	92.7	92.2	91.6	91.2	90.9	90.5	90.2	89.8
102.5°	116.0	119.4	119.1	118.9	118.5	118.2	117.8	117.4	117.0	116.5	116.0
105°	160.2	160.2	160.2	160.2	160.2	160.2	160.0	159.6	159.1	158.5	158.1
107.5°	202.8	202.8	202.6	202.4	202.1	201.9	201.8	201.8	201.8	201.8	201.8
110°	230.9	231.2	231.0	230.7	230.5	230.3	230.2	230.2	230.2	230.2	230.2



TEST NUMBER: P333304-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	258.4	258.7	258.6	258.4	258.4	258.2	258.0	257.7	257.4	257.1	256.8
115°	299.6	300.1	299.9	299.8	299.7	299.6	299.3	298.6	298.0	297.5	296.8
117.5°	339.6	340.2	339.7	339.3	338.8	338.4	338.2	338.2	338.2	338.2	338.3
120°	364.9	365.1	364.8	364.4	364.1	363.7	363.5	363.7	363.8	363.9	364.1
122.5°	389.5	389.6	389.5	389.4	389.2	389.0	388.7	388.2	387.8	387.3	386.8
125°	425.5	425.9	425.9	425.9	425.9	425.9	425.5	424.6	423.8	423.0	422.2
127.5°	457.9	458.2	458.3	458.4	458.4	458.5	458.2	457.6	457.0	456.4	455.8
130°	479.3	479.7	479.6	479.5	479.3	479.2	478.8	478.2	477.7	477.0	476.5
132.5°	499.0	499.1	499.3	499.5	499.8	500.1	499.8	499.2	498.5	497.8	497.1
135°	528.4	528.6	528.9	529.0	529.3	529.6	529.3	528.6	527.9	527.2	526.5
137.5°	555.3	555.3	555.5	555.7	555.9	556.2	555.9	555.3	554.7	554.1	553.5
140°	571.8	571.7	571.7	571.8	572.0	572.1	572.0	571.8	571.6	571.4	571.1
142.5°	588.4	588.4	588.2	588.1	588.0	587.8	587.6	587.5	587.3	587.2	587.0
145°	611.5	611.4	611.4	611.4	611.4	611.4	611.3	611.1	610.9	610.6	610.4
147.5°	631.4	631.2	631.0	630.9	630.7	630.7	630.6	630.7	630.7	630.7	630.7
150°	643.9	643.7	643.5	643.2	643.0	642.7	642.7	643.0	643.2	643.5	643.7
152.5°	655.2	654.9	654.6	654.4	654.1	653.9	654.0	654.6	655.2	655.6	656.2
155°	670.4	670.1	669.8	669.6	669.3	669.1	669.3	670.1	670.8	671.5	672.2
157.5°	683.2	682.8	682.7	682.7	682.7	682.7	682.9	683.2	683.7	684.1	684.6
160°	691.0	690.5	690.3	690.2	690.1	690.0	690.3	691.0	691.7	692.5	693.1
162.5°	698.0	697.4	697.2	697.1	697.0	696.9	697.2	697.9	698.6	699.4	700.0
165°	707.3	706.6	706.5	706.3	706.2	706.2	706.4	707.2	707.8	708.6	709.3
167.5°	714.3	713.4	713.2	713.1	713.0	712.9	713.2	714.0	714.7	715.5	716.1
170°	717.7	716.8	716.7	716.6	716.4	716.3	716.7	717.6	718.4	719.3	720.1
172.5°	720.7	719.8	719.6	719.4	719.2	719.0	719.3	720.1	721.0	721.8	722.6
175°	723.7	722.7	722.6	722.6	722.4	722.3	722.6	723.3	724.0	724.7	725.5
177.5°	725.3	724.5	724.4	724.3	724.2	724.2	724.4	725.0	725.6	726.1	726.7
180°	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5



TEST NUMBER: P333304-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1
2.5°	1740.4	1748.7	1754.0	1764.0	1772.2	1776.9	1781.0	1784.5	1788.7	1792.2	1802.1
5°	1751.6	1770.7	1786.9	1811.8	1834.7	1852.3	1871.3	1888.3	1902.2	1922.0	1937.5
7.5°	1746.7	1780.7	1816.3	1854.9	1894.4	1931.2	1965.0	1996.6	2025.2	2059.9	2090.3
10°	1742.0	1788.4	1833.9	1886.0	1939.7	1985.3	2027.9	2071.2	2102.8	2146.9	2184.3
12.5°	1738.5	1793.0	1848.0	1910.7	1969.6	2034.0	2090.7	2122.3	2170.4	2205.6	2250.2
15°	1723.7	1795.7	1871.3	1941.9	2025.6	2085.2	2135.1	2196.9	2241.6	2286.5	2335.0
17.5°	1697.0	1778.7	1863.3	1955.7	2036.1	2100.0	2164.4	2223.9	2277.4	2337.5	2397.8
20°	1684.7	1766.3	1863.3	1958.0	2036.6	2103.6	2169.6	2235.1	2293.9	2371.0	2440.8
22.5°	1658.9	1757.5	1846.8	1939.3	2020.2	2092.9	2167.9	2242.1	2320.3	2407.4	2494.8
25°	1612.8	1712.7	1807.4	1898.6	1980.1	2071.2	2151.3	2250.5	2350.4	2465.8	2574.5
27.5°	1564.8	1660.5	1747.4	1835.3	1930.4	2033.6	2137.5	2250.0	2380.9	2526.5	2679.8
30°	1526.1	1616.4	1700.9	1791.3	1890.5	2006.6	2120.4	2254.2	2405.6	2569.4	2751.6
32.5°	1480.7	1564.1	1646.2	1741.9	1849.9	1972.5	2105.2	2251.8	2433.7	2619.9	2807.5
35°	1403.4	1473.1	1557.6	1659.7	1781.7	1922.0	2075.7	2249.0	2457.7	2671.4	2829.4
37.5°	1311.5	1376.5	1465.5	1577.4	1705.3	1856.0	2038.2	2243.9	2465.5	2635.9	2686.9
40°	1249.8	1310.0	1402.6	1518.7	1649.4	1808.9	2008.7	2226.3	2440.8	2549.5	2507.6
42.5°	1183.9	1247.2	1337.4	1452.3	1593.1	1766.6	1971.7	2189.2	2369.1	2410.2	2265.5
45°	1080.1	1145.5	1234.4	1350.5	1501.8	1689.9	1903.7	2101.3	2204.9	2130.7	1906.7
47.5°	983.5	1044.8	1127.2	1247.0	1403.2	1597.7	1803.6	1961.3	1969.5	1792.4	1553.1
50°	917.7	974.2	1057.2	1177.0	1332.1	1529.0	1714.9	1839.0	1783.2	1582.6	1352.6
52.5°	853.0	908.4	990.2	1108.9	1262.2	1442.6	1615.5	1702.7	1597.4	1391.6	1195.1
55°	759.7	808.2	888.3	997.8	1143.2	1310.8	1457.7	1487.8	1351.1	1148.4	988.9
57.5°	668.6	713.9	786.7	887.6	1020.6	1168.9	1283.8	1277.4	1132.9	958.9	832.5
60°	606.9	651.0	715.7	814.1	935.3	1063.2	1161.6	1138.1	994.9	845.0	738.4
62.5°	551.7	591.0	652.1	738.3	848.9	967.3	1048.2	1013.5	873.2	742.1	657.9
65°	470.2	503.3	555.4	629.0	720.8	818.5	880.9	836.1	716.3	614.3	546.7
67.5°	392.5	419.0	462.7	521.3	599.6	678.2	716.2	671.1	575.3	500.8	450.7
70°	343.1	366.6	400.4	452.6	520.9	587.0	615.7	575.3	493.0	429.0	393.0
72.5°	293.8	313.1	342.8	389.7	444.5	501.8	527.0	488.3	420.8	366.7	333.1
75°	227.1	240.3	260.8	293.1	336.5	382.1	396.1	362.2	318.9	278.4	256.5
77.5°	162.5	173.7	189.3	209.7	240.4	269.4	281.5	262.0	228.5	202.9	184.8
80°	124.9	130.8	144.0	160.9	185.1	203.5	211.6	199.2	175.6	156.5	142.5
82.5°	89.1	94.9	102.8	116.8	132.2	144.8	153.4	145.1	128.0	113.0	104.9
85°	43.4	47.0	51.5	57.3	69.1	76.4	75.7	70.5	63.9	58.1	53.6
87.5°	15.6	16.4	18.3	21.5	23.4	25.9	27.2	26.2	24.0	22.4	20.7
90°	1.5	2.5	3.4	4.3	5.3	6.1	7.0	7.7	8.6	9.2	9.8
92.5°	7.6	7.0	6.3	5.6	5.7	6.4	7.2	7.8	8.6	9.2	9.8
95°	30.3	30.0	29.6	29.2	26.8	22.2	17.7	13.1	8.6	9.2	9.8
97.5°	64.7	65.3	65.9	66.5	62.4	53.4	44.4	35.4	26.5	23.1	19.7
100°	90.2	90.5	90.9	91.2	91.6	92.2	92.7	93.1	93.6	75.8	58.0
102.5°	116.5	117.0	117.4	117.8	118.2	118.5	118.9	119.1	119.4	116.0	112.6
105°	158.5	159.1	159.6	160.0	160.2	160.2	160.2	160.2	160.2	160.2	160.2
107.5°	201.8	201.8	201.8	201.8	201.9	202.1	202.4	202.6	202.8	202.8	202.9
110°	230.2	230.2	230.2	230.2	230.3	230.5	230.7	231.0	231.2	230.9	230.5





TEST NUMBER: P333304-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	257.1	257.4	257.7	258.0	258.2	258.4	258.4	258.6	258.7	258.4	257.9
115°	297.5	298.0	298.6	299.3	299.6	299.7	299.8	299.9	300.1	299.6	299.1
117.5°	338.2	338.2	338.2	338.2	338.4	338.8	339.3	339.7	340.2	339.6	338.9
120°	363.9	363.8	363.7	363.5	363.7	364.1	364.4	364.8	365.1	364.9	364.7
122.5°	387.3	387.8	388.2	388.7	389.0	389.2	389.4	389.5	389.6	389.5	389.2
125°	423.0	423.8	424.6	425.5	425.9	425.9	425.9	425.9	425.9	425.5	425.0
127.5°	456.4	457.0	457.6	458.2	458.5	458.4	458.4	458.3	458.2	457.9	457.6
130°	477.0	477.7	478.2	478.8	479.2	479.3	479.5	479.6	479.7	479.3	479.0
132.5°	497.8	498.5	499.2	499.8	500.1	499.8	499.5	499.3	499.1	499.0	498.9
135°	527.2	527.9	528.6	529.3	529.6	529.3	529.0	528.9	528.6	528.4	528.1
137.5°	554.1	554.7	555.3	555.9	556.2	555.9	555.7	555.5	555.3	555.3	555.3
140°	571.4	571.6	571.8	572.0	572.1	572.0	571.8	571.7	571.7	571.8	572.1
142.5°	587.2	587.3	587.5	587.6	587.8	588.0	588.1	588.2	588.4	588.4	588.5
145°	610.6	610.9	611.1	611.3	611.4	611.4	611.4	611.4	611.4	611.5	611.7
147.5°	630.7	630.7	630.7	630.6	630.7	630.7	630.9	631.0	631.2	631.4	631.5
150°	643.5	643.2	643.0	642.7	642.7	643.0	643.2	643.5	643.7	643.9	644.1
152.5°	655.6	655.2	654.6	654.0	653.9	654.1	654.4	654.6	654.9	655.2	655.3
155°	671.5	670.8	670.1	669.3	669.1	669.3	669.6	669.8	670.1	670.4	670.8
157.5°	684.1	683.7	683.2	682.9	682.7	682.7	682.7	682.7	682.8	683.2	683.5
160°	692.5	691.7	691.0	690.3	690.0	690.1	690.2	690.3	690.5	691.0	691.4
162.5°	699.4	698.6	697.9	697.2	696.9	697.0	697.1	697.2	697.4	698.0	698.7
165°	708.6	707.8	707.2	706.4	706.2	706.2	706.3	706.5	706.6	707.3	708.0
167.5°	715.5	714.7	714.0	713.2	712.9	713.0	713.1	713.2	713.4	714.3	715.1
170°	719.3	718.4	717.6	716.7	716.3	716.4	716.6	716.7	716.8	717.7	718.8
172.5°	721.8	721.0	720.1	719.3	719.0	719.2	719.4	719.6	719.8	720.7	721.5
175°	724.7	724.0	723.3	722.6	722.3	722.4	722.6	722.6	722.7	723.7	724.6
177.5°	726.1	725.6	725.0	724.4	724.2	724.2	724.3	724.4	724.5	725.3	725.9
180°	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5



TEST NUMBER: P333304-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1
2.5°	1810.3	1815.1	1825.0	1821.6	1826.3	1828.6	1831.0
5°	1956.6	1980.1	1990.4	1989.0	2004.3	2000.6	1997.0
7.5°	2121.8	2146.5	2160.3	2177.5	2187.5	2188.2	2196.9
10°	2215.3	2247.6	2260.8	2279.2	2290.9	2297.5	2296.8
12.5°	2286.9	2312.2	2341.8	2350.9	2366.7	2375.1	2372.0
15°	2373.2	2413.6	2444.5	2459.8	2479.7	2485.6	2493.7
17.5°	2450.2	2504.4	2540.4	2588.3	2606.4	2617.4	2610.9
20°	2508.4	2579.6	2615.6	2673.0	2704.5	2721.5	2715.6
22.5°	2577.2	2654.3	2720.8	2770.5	2818.6	2841.4	2846.1
25°	2695.0	2800.8	2898.5	2963.9	3023.4	3037.3	3068.3
27.5°	2826.7	2951.4	3055.9	3124.7	3166.1	3181.6	3191.4
30°	2909.5	3033.7	3112.4	3156.4	3169.7	3168.2	3166.7
32.5°	2950.1	3027.8	3043.0	3030.7	3000.4	2974.8	2948.1
35°	2892.7	2834.6	2747.9	2636.2	2553.9	2470.9	2462.9
37.5°	2601.5	2415.9	2271.6	2110.4	2017.4	1960.0	1920.3
40°	2327.6	2116.8	1941.9	1806.0	1711.2	1673.8	1637.0
42.5°	2030.2	1828.7	1673.9	1560.3	1489.0	1447.5	1418.3
45°	1649.4	1471.7	1350.5	1268.2	1211.5	1179.2	1160.8
47.5°	1351.6	1220.1	1117.1	1057.7	1018.6	993.5	993.6
50°	1191.8	1066.1	997.8	950.7	916.9	897.1	900.8
52.5°	1050.1	956.2	897.9	858.5	833.5	821.2	820.9
55°	878.0	810.4	772.2	743.6	726.6	712.7	715.7
57.5°	751.0	694.0	668.5	644.7	632.9	627.4	619.3
60°	672.3	628.2	606.1	587.0	575.3	570.9	562.8
62.5°	602.4	567.7	546.2	530.7	520.0	518.6	512.3
65°	506.2	479.8	460.7	453.4	442.3	439.4	439.4
67.5°	417.4	398.4	383.5	376.7	371.9	372.7	369.1
70°	361.5	346.1	336.5	329.1	325.5	326.2	323.3
72.5°	316.2	299.1	290.7	286.3	281.4	283.3	282.1
75°	239.5	230.7	226.3	221.9	219.0	217.4	216.0
77.5°	175.9	168.1	164.8	162.2	162.7	159.1	161.9
80°	135.9	129.3	127.1	123.5	122.7	122.7	122.0
82.5°	99.4	95.8	94.2	91.1	89.8	91.0	89.1
85°	51.5	48.4	47.8	47.8	46.3	44.9	48.4
87.5°	20.9	18.7	18.8	18.2	18.3	17.8	16.7
90°	10.4	11.0	11.5	11.9	12.2	12.5	12.9
92.5°	10.4	11.0	11.4	11.5	11.7	11.9	12.1
95°	10.4	11.0	11.3	11.3	11.3	11.3	11.3
97.5°	16.3	13.0	11.3	11.3	11.3	11.3	11.3
100°	40.2	22.3	13.2	12.7	12.3	11.8	11.3
102.5°	109.2	105.9	100.2	92.0	83.9	75.8	67.7
105°	160.2	160.2	160.2	160.0	159.9	159.9	159.7
107.5°	202.9	202.9	202.7	202.5	202.1	201.7	201.3
110°	230.2	229.8	229.7	229.8	229.9	230.1	230.2



TEST NUMBER: P333304-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	257.4	256.9	256.7	256.5	256.3	256.2	256.0
115°	298.6	298.1	297.6	296.8	296.1	295.4	294.7
117.5°	338.3	337.7	337.2	337.0	336.6	336.3	336.0
120°	364.4	364.2	363.7	363.2	362.6	361.9	361.4
122.5°	389.0	388.7	388.2	387.6	386.8	386.2	385.5
125°	424.4	424.0	423.6	423.2	422.8	422.5	422.2
127.5°	457.4	457.1	456.6	455.6	454.8	453.9	453.0
130°	478.6	478.2	477.8	477.2	476.5	476.0	475.4
132.5°	498.8	498.8	498.4	497.9	497.2	496.6	496.1
135°	527.9	527.6	527.2	526.5	525.8	525.0	524.3
137.5°	555.4	555.4	555.2	554.6	553.9	553.4	552.7
140°	572.3	572.6	572.3	571.7	570.9	570.2	569.5
142.5°	588.5	588.6	588.2	587.6	586.8	586.1	585.4
145°	611.8	611.9	611.6	610.9	610.2	609.4	608.7
147.5°	631.7	631.8	631.4	630.6	629.7	628.9	628.0
150°	644.4	644.6	644.3	643.4	642.3	641.4	640.5
152.5°	655.6	655.8	655.5	654.7	653.8	652.9	652.1
155°	671.1	671.5	671.2	670.2	669.3	668.4	667.3
157.5°	683.9	684.3	684.0	683.1	682.0	681.1	680.1
160°	691.9	692.4	692.1	691.2	690.2	689.3	688.3
162.5°	699.4	700.0	699.8	698.8	697.8	696.7	695.6
165°	708.8	709.5	709.4	708.4	707.5	706.5	705.5
167.5°	716.0	716.8	716.7	715.7	714.5	713.5	712.4
170°	719.7	720.7	720.6	719.5	718.4	717.4	716.3
172.5°	722.5	723.3	723.2	722.1	721.0	719.9	718.9
175°	725.6	726.6	726.5	725.5	724.3	723.3	722.2
177.5°	726.6	727.3	727.2	726.4	725.7	724.9	724.2
180°	725.5	725.5	725.5	725.5	725.5	725.5	725.5

(END OF REPORT)