

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333196-935

Luminaire Tested: **S125DIP-S610D1205U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333196-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S610D1205U935-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6322.5 lumens
Efficiency: N/A
Efficacy: 128.0 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333196-935

CATALOG NUMBER: S125DIP-S610D1205U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333196-935

CATALOG NUMBER: S125DIP-S610D1205U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	75	75	75	58	58	58	42	42	42	34
1	94	90	87	83	85	82	79	76	66	63	61	51	49	48	37	36	36	29
2	86	79	73	68	78	72	67	62	58	54	51	45	42	40	33	31	30	25
3	79	69	62	57	71	63	57	52	51	47	43	40	37	34	29	27	26	21
4	72	61	54	48	65	56	49	44	45	40	37	35	32	29	26	24	22	18
5	66	55	47	41	59	50	43	38	40	35	32	32	28	25	24	21	19	16
6	61	49	41	35	55	45	38	33	36	31	27	29	25	22	21	19	17	14
7	56	44	36	31	50	40	33	29	33	28	24	26	22	20	20	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	15	14	11
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	16	14	12	10
10	45	33	26	22	41	30	24	20	25	20	17	20	17	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4977	4977	4977	4977
5°	5763	4994	4372	4994
10°	6705	4968	3831	4968
15°	7422	4931	3534	4931
20°	8308	4874	3296	4874
25°	9733	4809	3180	4809
30°	10513	4744	3078	4744
35°	8643	4623	3012	4623
40°	6144	4457	2939	4457
45°	4720	4230	2898	4230
50°	4029	3950	2892	3950
55°	3587	3675	2917	3675
60°	3237	3375	2992	3375
65°	2989	3073	3069	3073
70°	2717	2761	3114	2761
75°	2400	2433	3084	2433
80°	2020	1982	2823	1982
85°	1601	1430	2275	1430



TEST NUMBER: P333196-935

CATALOG NUMBER: S125DIP-S610D1205U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.2	1.2
10°-20°	220.9	3.5
20°-30°	358.6	5.7
30°-40°	437.5	6.9
40°-50°	398.0	6.3
50°-60°	317.0	5.0
60°-70°	220.8	3.5
70°-80°	117.7	1.9
80°-90°	32.5	0.5
90°-100°	49.1	0.8
100°-110°	302.3	4.8
110°-120°	548.3	8.7
120°-130°	703.7	11.1
130°-140°	756.9	12.0
140°-150°	710.4	11.2
150°-160°	574.7	9.1
160°-170°	371.7	5.9
170°-180°	128.2	2.0
0°-30°	653.7	10.3
0°-40°	1091.2	17.3
0°-60°	1806.2	28.6
0°-90°	2177.3	34.4
90°-120°	899.7	14.2
90°-150°	3070.7	48.6
90°-180°	4145.0	65.6
0°-180°	6322.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	771	771	771	771	771	
5°	889	770	674	770	889	90
15°	1110	738	529	738	1110	318
25°	1366	675	446	675	1366	624
35°	1096	586	382	586	1096	671
45°	517	463	317	463	517	414
55°	319	326	259	326	319	287
65°	196	201	201	201	196	194
75°	96	98	124	98	96	104
85°	22	19	31	19	22	26
90°	24	1	24	1	24	11
95°	21	57	21	57	21	17
105°	297	294	297	294	297	269
115°	548	552	548	552	548	544
125°	786	786	786	786	786	699
135°	976	980	976	980	976	753
145°	1133	1136	1133	1136	1133	708
155°	1242	1251	1242	1251	1242	572
165°	1313	1320	1313	1320	1313	371
175°	1344	1350	1344	1350	1344	128
180°	1350	1350	1350	1350	1350	



TEST NUMBER: P333196-935

CATALOG NUMBER: S125DIP-S610D1205U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6
2.5°	815.1	814.0	813.0	810.9	812.4	808.0	805.9	802.3	797.8	796.3	794.4
5°	889.0	890.6	892.3	885.4	886.1	881.5	871.0	862.5	855.7	846.8	840.6
7.5°	977.9	974.0	973.8	969.3	961.7	955.5	944.5	930.5	917.0	901.6	888.8
10°	1022.4	1022.8	1019.9	1014.6	1006.4	1000.5	986.1	972.4	955.7	936.1	922.0
12.5°	1055.9	1057.3	1053.6	1046.5	1042.5	1029.3	1018.0	1001.7	981.9	966.2	944.8
15°	1110.1	1106.5	1103.9	1095.0	1088.1	1074.4	1056.4	1039.4	1017.9	997.9	977.9
17.5°	1162.3	1165.2	1160.3	1152.2	1130.9	1114.8	1090.7	1067.5	1040.5	1013.8	990.0
20°	1208.8	1211.5	1203.9	1189.9	1164.4	1148.3	1116.6	1086.5	1055.5	1021.1	995.0
22.5°	1267.0	1264.9	1254.7	1233.3	1211.3	1181.6	1147.3	1110.6	1071.7	1032.9	998.1
25°	1365.9	1352.1	1345.9	1319.4	1290.3	1246.8	1199.7	1146.1	1097.7	1046.3	1001.9
27.5°	1420.6	1416.3	1409.5	1390.9	1360.4	1313.9	1258.4	1193.0	1124.6	1059.9	1001.6
30°	1409.7	1410.3	1411.0	1405.1	1385.5	1350.5	1295.2	1224.9	1143.8	1070.8	1003.5
32.5°	1312.3	1324.2	1335.7	1349.1	1354.6	1347.9	1313.3	1249.7	1166.3	1083.4	1002.4
35°	1096.3	1099.9	1137.0	1173.5	1223.2	1261.9	1287.7	1259.6	1189.2	1094.1	1001.2
37.5°	854.8	872.5	898.1	939.5	1011.2	1075.5	1158.1	1196.1	1173.4	1097.5	998.8
40°	728.8	745.1	761.7	803.9	864.4	942.3	1036.1	1116.3	1135.0	1086.5	991.0
42.5°	631.4	644.4	662.9	694.6	745.1	814.1	903.8	1008.5	1072.9	1054.6	974.6
45°	516.8	525.0	539.3	564.6	601.2	655.1	734.3	848.8	948.5	981.5	935.4
47.5°	442.3	442.3	453.5	470.9	497.3	543.1	601.7	691.4	797.9	876.8	873.1
50°	401.0	399.3	408.2	423.3	444.2	474.6	530.5	602.2	704.6	793.8	818.6
52.5°	365.4	365.6	371.0	382.1	399.7	425.7	467.4	532.0	619.5	711.1	757.9
55°	318.6	317.3	323.5	331.0	343.8	360.8	390.9	440.2	511.2	601.5	662.3
57.5°	275.7	279.2	281.7	287.0	297.6	308.9	334.3	370.6	426.9	504.4	568.7
60°	250.6	254.2	256.1	261.3	269.8	279.7	299.3	328.7	376.2	442.9	506.6
62.5°	228.0	230.8	231.5	236.2	243.1	252.7	268.1	292.8	330.4	388.7	451.2
65°	195.6	195.6	196.9	201.8	205.1	213.6	225.3	243.3	273.5	318.9	372.2
67.5°	164.3	165.9	165.6	167.7	170.7	177.4	185.8	200.6	222.9	256.1	298.8
70°	143.9	145.3	144.9	146.5	149.8	154.0	160.9	175.0	191.0	219.5	256.1
72.5°	125.6	126.1	125.3	127.4	129.4	133.1	140.8	148.3	163.2	187.3	217.4
75°	96.2	96.8	97.5	98.8	100.7	102.7	106.6	114.2	124.0	142.0	161.3
77.5°	72.1	70.9	72.4	72.2	73.4	74.8	78.3	82.3	90.3	101.7	116.7
80°	54.3	54.6	54.6	54.9	56.6	57.6	60.5	63.5	69.7	78.2	88.6
82.5°	39.6	40.5	40.0	40.6	41.9	42.6	44.3	46.7	50.3	57.0	64.6
85°	21.6	20.0	20.6	21.3	21.3	21.6	22.9	23.8	25.8	28.4	31.4
87.5°	11.1	11.5	11.6	11.5	11.6	11.5	12.2	12.1	12.6	13.2	13.9
90°	24.0	23.3	22.6	22.0	21.4	20.5	19.4	18.3	17.1	16.0	14.5
92.5°	22.4	22.1	21.8	21.4	21.2	20.5	19.4	18.3	17.1	16.0	14.6
95°	21.0	21.0	21.0	21.0	21.0	20.5	19.4	18.3	17.1	16.0	24.5
97.5°	21.0	21.0	21.0	21.0	21.0	24.1	30.4	36.7	43.0	49.2	66.0
100°	21.0	21.9	22.8	23.7	24.5	41.6	74.7	107.9	140.9	174.1	173.2
102.5°	125.9	141.0	156.1	171.3	186.4	197.1	203.4	209.6	215.9	222.1	221.6
105°	297.2	297.4	297.6	297.8	298.1	298.2	298.2	298.2	298.2	298.2	298.2
107.5°	374.6	375.3	376.0	376.6	377.3	377.6	377.5	377.5	377.5	377.5	377.0
110°	428.3	428.1	427.8	427.6	427.4	427.6	428.3	429.0	429.6	430.2	429.8



TEST NUMBER: P333196-935

CATALOG NUMBER: S125DIP-S610D1205U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	476.3	476.6	476.9	477.3	477.5	478.1	479.0	479.8	480.7	481.5	481.2
115°	548.4	549.7	551.0	552.3	553.7	554.8	555.7	556.6	557.5	558.4	558.1
117.5°	625.2	625.8	626.4	626.9	627.5	628.4	629.6	630.7	631.9	633.0	632.1
120°	672.4	673.6	674.7	675.8	676.9	677.7	678.1	678.6	679.0	679.4	678.7
122.5°	717.3	718.6	719.8	721.1	722.4	723.3	723.8	724.2	724.6	725.0	724.8
125°	785.5	786.2	786.9	787.5	788.2	788.9	789.8	790.7	791.6	792.5	792.5
127.5°	842.9	844.6	846.2	847.9	849.5	850.6	851.1	851.5	852.0	852.6	852.6
130°	884.6	885.7	886.8	887.9	889.0	889.9	890.5	891.2	891.9	892.6	892.3
132.5°	923.0	924.1	925.2	926.3	927.5	928.1	928.2	928.3	928.5	928.6	929.1
135°	975.6	977.0	978.3	979.6	980.9	981.9	982.3	982.7	983.2	983.6	984.0
137.5°	1028.5	1029.6	1030.8	1031.9	1033.1	1033.6	1033.5	1033.5	1033.4	1033.3	1033.6
140°	1059.7	1061.0	1062.4	1063.7	1065.0	1065.5	1065.0	1064.5	1064.1	1063.7	1063.9
142.5°	1089.3	1090.6	1092.0	1093.3	1094.7	1095.3	1095.2	1095.1	1095.0	1094.9	1094.6
145°	1132.7	1134.0	1135.4	1136.7	1138.1	1138.6	1138.4	1138.2	1138.0	1137.7	1137.7
147.5°	1168.5	1170.2	1171.7	1173.4	1174.9	1175.6	1175.4	1175.1	1174.8	1174.6	1174.3
150°	1191.8	1193.5	1195.3	1197.1	1198.9	1199.5	1199.1	1198.7	1198.2	1197.7	1197.3
152.5°	1213.4	1215.0	1216.6	1218.1	1219.8	1220.4	1220.0	1219.4	1219.0	1218.6	1218.1
155°	1241.8	1243.5	1245.4	1247.2	1248.9	1249.5	1248.8	1248.1	1247.5	1246.8	1246.4
157.5°	1265.6	1267.4	1269.2	1270.9	1272.7	1273.2	1272.6	1271.9	1271.1	1270.4	1270.4
160°	1280.8	1282.6	1284.4	1286.2	1288.0	1288.4	1287.5	1286.6	1285.7	1284.8	1284.6
162.5°	1294.4	1296.4	1298.3	1300.3	1302.3	1302.6	1301.4	1300.1	1298.9	1297.6	1297.4
165°	1312.9	1314.6	1316.4	1318.2	1319.9	1320.2	1318.9	1317.5	1316.2	1314.8	1314.6
167.5°	1325.7	1327.7	1329.6	1331.6	1333.7	1333.9	1332.2	1330.7	1329.0	1327.5	1327.2
170°	1332.8	1334.9	1336.9	1338.9	1340.8	1341.0	1339.2	1337.4	1335.7	1333.9	1333.6
172.5°	1337.6	1339.6	1341.7	1343.7	1345.7	1345.8	1344.3	1342.6	1341.1	1339.5	1339.0
175°	1343.8	1345.8	1347.9	1349.9	1351.9	1351.9	1350.2	1348.4	1346.6	1344.9	1344.6
177.5°	1347.5	1348.8	1350.3	1351.8	1353.1	1353.2	1352.0	1350.7	1349.5	1348.2	1348.1
180°	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9



TEST NUMBER: P333196-935

CATALOG NUMBER: S125DIP-S610D1205U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6
2.5°	792.8	791.0	788.9	785.2	780.8	778.4	774.8	772.4	767.7	763.8	759.6
5°	833.0	824.6	816.7	806.6	795.5	788.2	779.7	770.3	760.4	750.3	739.2
7.5°	874.7	859.7	843.3	825.7	808.6	792.7	777.6	762.8	748.9	732.1	717.9
10°	902.8	883.7	863.5	839.6	816.4	796.1	775.5	757.5	739.2	719.5	702.2
12.5°	930.7	905.4	876.8	850.6	822.7	798.2	774.0	751.0	728.0	706.2	686.0
15°	950.5	928.2	901.7	864.4	833.0	799.4	767.3	737.5	709.7	685.5	660.0
17.5°	963.5	934.9	906.4	870.6	829.5	791.8	755.4	721.4	690.1	659.4	634.8
20°	965.9	936.4	906.6	871.7	829.5	786.3	750.0	709.1	675.4	643.7	613.5
22.5°	965.1	931.7	899.3	863.2	822.2	782.4	738.5	696.8	660.2	629.0	597.6
25°	957.7	922.0	881.5	845.2	804.6	762.4	717.9	674.8	637.5	601.8	570.8
27.5°	951.5	905.3	859.4	817.0	777.8	739.2	696.6	652.4	611.1	574.9	545.6
30°	943.9	893.2	841.5	797.4	757.2	719.5	679.3	636.2	593.0	557.7	526.2
32.5°	937.1	878.0	823.5	775.4	732.9	696.3	659.2	618.1	575.8	539.8	508.5
35°	924.0	855.7	793.2	738.8	693.4	655.8	624.7	586.4	547.5	512.8	482.8
37.5°	907.3	826.2	759.1	702.2	652.4	612.8	583.8	554.5	517.1	483.7	456.5
40°	894.2	805.3	734.3	676.1	624.4	583.2	556.4	528.6	497.5	466.4	437.6
42.5°	877.7	786.4	709.1	646.5	595.4	555.2	527.0	503.4	476.0	447.0	420.3
45°	847.5	752.3	668.6	601.2	549.5	509.9	480.8	463.1	442.6	415.1	392.5
47.5°	802.9	711.3	624.7	555.1	501.8	465.1	437.8	420.9	406.4	386.0	365.5
50°	763.4	680.6	593.0	524.0	470.6	433.7	408.5	393.1	380.7	365.0	347.7
52.5°	719.2	642.1	561.9	493.6	440.8	404.4	379.7	366.2	355.9	344.6	327.5
55°	648.9	583.5	508.9	444.2	395.5	359.8	338.2	326.4	317.9	309.4	298.9
57.5°	571.5	520.4	454.3	395.1	350.3	317.8	297.6	286.2	279.6	275.2	269.1
60°	517.1	473.3	416.4	362.4	318.6	289.8	270.2	261.3	255.8	252.2	247.6
62.5°	466.6	430.6	377.9	328.6	290.3	263.1	245.6	237.0	231.7	230.0	226.1
65°	392.2	364.4	320.9	280.0	247.3	224.0	209.3	201.1	197.9	195.9	196.2
67.5°	318.8	301.9	267.0	232.1	206.0	186.5	174.7	168.4	166.8	164.2	164.1
70°	274.1	261.3	231.9	201.5	178.2	163.2	152.7	146.2	144.6	143.3	142.9
72.5°	234.5	223.4	197.9	173.5	152.7	139.4	130.8	126.8	124.2	123.4	123.3
75°	176.3	170.0	149.8	130.5	116.1	106.9	101.1	97.5	95.5	95.1	95.5
77.5°	125.4	119.9	107.0	93.3	84.3	77.3	72.3	71.1	68.9	69.0	68.6
80°	94.2	90.6	82.4	71.6	64.1	58.2	55.6	53.3	52.7	51.7	52.7
82.5°	68.3	64.4	58.9	52.0	45.8	42.3	39.6	38.9	38.5	38.1	38.2
85°	33.7	34.0	30.7	25.5	22.9	20.9	19.3	19.3	18.9	18.7	18.9
87.5°	14.1	13.3	11.9	10.8	9.1	8.0	7.3	7.2	6.8	6.9	7.6
90°	12.9	11.4	9.8	8.1	6.4	4.6	2.8	1.0	2.8	4.6	6.4
92.5°	13.3	11.9	10.5	10.4	11.7	12.9	14.2	15.4	14.2	12.9	11.7
95°	32.9	41.3	49.9	54.3	55.0	55.7	56.4	57.0	56.4	55.7	55.0
97.5°	82.7	99.4	116.1	123.9	122.7	121.5	120.3	119.1	120.3	121.5	122.7
100°	172.4	171.4	170.6	169.8	169.1	168.4	167.8	167.1	167.8	168.4	169.1
102.5°	221.1	220.5	220.0	219.3	218.4	217.7	216.8	215.9	216.8	217.7	218.4
105°	298.2	298.2	298.2	297.7	296.9	295.9	295.1	294.2	295.1	295.9	296.9
107.5°	376.5	376.1	375.7	375.5	375.5	375.5	375.5	375.5	375.5	375.5	375.5
110°	429.4	429.0	428.5	428.3	428.3	428.3	428.3	428.3	428.3	428.3	428.3



TEST NUMBER: P333196-935

CATALOG NUMBER: S125DIP-S610D1205U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	481.0	480.7	480.4	480.0	479.5	479.0	478.5	477.9	478.5	479.0	479.5
115°	557.9	557.7	557.5	556.8	555.7	554.6	553.5	552.3	553.5	554.6	555.7
117.5°	631.3	630.5	629.6	629.2	629.3	629.3	629.4	629.4	629.4	629.3	629.3
120°	678.1	677.4	676.7	676.6	676.7	677.0	677.2	677.4	677.2	677.0	676.7
122.5°	724.4	724.1	723.8	723.2	722.4	721.5	720.7	719.9	720.7	721.5	722.4
125°	792.5	792.5	792.5	791.7	790.1	788.6	787.0	785.5	787.0	788.6	790.1
127.5°	852.8	852.9	853.1	852.6	851.4	850.3	849.3	848.2	849.3	850.3	851.4
130°	892.2	891.9	891.7	891.0	889.9	888.8	887.7	886.6	887.7	888.8	889.9
132.5°	929.5	930.1	930.6	930.1	928.8	927.6	926.3	925.0	926.3	927.6	928.8
135°	984.6	985.0	985.4	985.0	983.6	982.3	980.9	979.6	980.9	982.3	983.6
137.5°	1034.1	1034.5	1034.8	1034.5	1033.3	1032.2	1031.0	1029.8	1031.0	1032.2	1033.3
140°	1064.1	1064.4	1064.5	1064.5	1064.0	1063.6	1063.2	1062.6	1063.2	1063.6	1064.0
142.5°	1094.2	1094.0	1093.6	1093.4	1093.1	1092.9	1092.5	1092.3	1092.5	1092.9	1093.1
145°	1137.7	1137.7	1137.7	1137.5	1137.0	1136.6	1136.2	1135.7	1136.2	1136.6	1137.0
147.5°	1174.0	1173.7	1173.5	1173.4	1173.5	1173.5	1173.6	1173.7	1173.6	1173.5	1173.5
150°	1196.9	1196.4	1196.0	1196.0	1196.4	1196.9	1197.3	1197.7	1197.3	1196.9	1196.4
152.5°	1217.7	1217.3	1216.8	1217.0	1218.1	1219.0	1220.0	1221.0	1220.0	1219.0	1218.1
155°	1245.9	1245.4	1245.0	1245.4	1246.8	1248.1	1249.5	1250.8	1249.5	1248.1	1246.8
157.5°	1270.3	1270.3	1270.2	1270.6	1271.4	1272.2	1273.0	1273.8	1273.0	1272.2	1271.4
160°	1284.4	1284.2	1283.9	1284.5	1285.8	1287.2	1288.5	1289.9	1288.5	1287.2	1285.8
162.5°	1297.2	1296.9	1296.8	1297.3	1298.6	1299.9	1301.3	1302.6	1301.3	1299.9	1298.6
165°	1314.4	1314.1	1314.0	1314.5	1315.9	1317.2	1318.5	1319.8	1318.5	1317.2	1315.9
167.5°	1327.0	1326.8	1326.5	1327.1	1328.5	1329.9	1331.3	1332.7	1331.3	1329.9	1328.5
170°	1333.4	1333.2	1333.0	1333.6	1335.2	1336.7	1338.3	1339.9	1338.3	1336.7	1335.2
172.5°	1338.7	1338.3	1337.8	1338.4	1340.0	1341.5	1343.1	1344.6	1343.1	1341.5	1340.0
175°	1344.5	1344.2	1343.9	1344.5	1345.8	1347.2	1348.5	1349.9	1348.5	1347.2	1345.8
177.5°	1347.9	1347.7	1347.6	1348.0	1349.1	1350.1	1351.2	1352.3	1351.2	1350.1	1349.1
180°	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9



TEST NUMBER: P333196-935

CATALOG NUMBER: S125DIP-S610D1205U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6
2.5°	757.2	754.3	752.0	746.7	743.9	739.9	736.8	740.2	736.6	738.1	735.8
5°	733.7	724.4	717.9	708.4	700.3	692.8	687.2	686.2	683.5	682.3	678.4
7.5°	705.2	693.8	682.5	670.1	659.6	649.0	642.1	636.5	632.8	627.9	624.6
10°	688.5	673.1	660.0	645.0	631.9	620.4	611.3	606.7	602.4	596.2	594.0
12.5°	667.8	651.9	635.9	619.8	607.3	594.5	586.7	579.8	576.9	569.8	569.1
15°	643.0	619.1	603.5	587.1	569.7	559.3	552.8	545.3	542.0	537.1	533.5
17.5°	613.5	592.1	572.5	555.6	540.7	531.9	523.7	518.6	513.0	509.8	503.9
20°	592.0	571.7	552.1	534.1	522.6	512.6	506.0	501.1	495.2	493.5	487.7
22.5°	573.9	551.6	532.7	517.6	505.1	493.7	486.6	483.3	479.2	474.2	473.0
25°	544.6	521.3	505.3	490.3	479.1	468.7	463.8	459.5	455.6	452.0	450.7
27.5°	519.2	498.4	479.4	465.8	456.2	446.6	442.3	437.1	434.2	431.4	427.8
30°	501.4	480.2	463.5	450.4	439.9	431.4	426.8	423.3	420.6	418.0	416.0
32.5°	483.1	463.4	447.2	434.5	424.0	417.6	413.5	411.0	408.0	404.9	402.4
35°	458.9	437.3	421.6	410.4	402.3	397.4	392.8	390.5	387.3	387.3	384.6
37.5°	431.6	412.9	399.1	388.9	381.6	377.2	372.3	370.7	368.6	367.2	366.4
40°	415.3	398.0	385.0	374.8	367.0	363.3	359.5	356.8	355.5	353.9	353.3
42.5°	398.6	382.1	369.5	360.2	353.4	350.3	346.6	344.8	342.2	340.0	339.7
45°	373.2	357.1	345.7	338.2	332.3	328.7	326.4	322.5	321.2	318.6	318.2
47.5°	349.0	333.6	322.4	316.2	311.1	308.2	304.5	300.7	299.1	297.8	297.7
50°	331.0	316.9	306.4	300.6	295.7	291.4	287.8	285.2	284.2	284.2	284.9
52.5°	312.7	300.7	291.8	284.6	280.0	275.4	272.2	270.5	269.1	270.6	271.8
55°	285.9	273.8	267.3	260.4	255.8	250.6	248.9	248.2	247.3	249.9	251.2
57.5°	257.4	249.0	241.3	234.5	230.4	227.4	225.2	224.8	226.6	227.8	232.1
60°	239.4	229.6	222.7	217.5	212.6	210.6	210.0	209.3	210.6	214.2	219.8
62.5°	219.6	211.5	204.1	200.3	196.7	193.4	193.2	193.6	196.2	200.4	206.0
65°	190.4	183.5	178.6	174.0	171.1	169.1	169.8	171.1	174.0	179.6	185.8
67.5°	160.7	156.0	151.6	147.9	145.1	145.1	145.8	147.7	151.2	157.6	163.2
70°	141.6	136.4	132.8	131.1	128.9	127.6	129.5	132.8	135.7	141.6	146.5
72.5°	122.5	118.0	115.3	114.2	113.1	112.1	112.8	116.3	120.3	126.2	131.9
75°	94.2	92.6	90.6	89.3	88.3	88.9	89.6	92.9	96.2	102.4	108.9
77.5°	68.8	67.1	65.9	65.5	65.0	65.3	67.2	69.6	72.8	77.3	82.3
80°	52.0	51.3	50.7	50.4	50.4	50.7	53.3	54.9	57.9	62.2	66.0
82.5°	37.9	37.5	37.4	37.3	37.5	37.6	39.2	41.3	43.7	47.0	50.4
85°	20.0	19.3	20.3	20.6	20.0	20.9	21.6	22.9	23.8	25.5	27.1
87.5°	8.2	9.0	9.0	9.6	10.0	10.8	10.8	12.1	12.7	13.5	13.4
90°	8.1	9.8	11.4	12.9	14.5	16.0	17.1	18.3	19.4	20.5	21.4
92.5°	10.4	10.5	11.9	13.3	14.6	16.0	17.1	18.3	19.4	20.5	21.2
95°	54.3	49.9	41.3	32.9	24.5	16.0	17.1	18.3	19.4	20.5	21.0
97.5°	123.9	116.1	99.4	82.7	66.0	49.2	43.0	36.7	30.4	24.1	21.0
100°	169.8	170.6	171.4	172.4	173.2	174.1	140.9	107.9	74.7	41.6	24.5
102.5°	219.3	220.0	220.5	221.1	221.6	222.1	215.9	209.6	203.4	197.1	186.4
105°	297.7	298.2	298.2	298.2	298.2	298.2	298.2	298.2	298.2	298.2	298.1
107.5°	375.5	375.7	376.1	376.5	377.0	377.5	377.5	377.5	377.5	377.6	377.3
110°	428.3	428.5	429.0	429.4	429.8	430.2	429.6	429.0	428.3	427.6	427.4



TEST NUMBER: P333196-935

CATALOG NUMBER: S125DIP-S610D1205U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	480.0	480.4	480.7	481.0	481.2	481.5	480.7	479.8	479.0	478.1	477.5
115°	556.8	557.5	557.7	557.9	558.1	558.4	557.5	556.6	555.7	554.8	553.7
117.5°	629.2	629.6	630.5	631.3	632.1	633.0	631.9	630.7	629.6	628.4	627.5
120°	676.6	676.7	677.4	678.1	678.7	679.4	679.0	678.6	678.1	677.7	676.9
122.5°	723.2	723.8	724.1	724.4	724.8	725.0	724.6	724.2	723.8	723.3	722.4
125°	791.7	792.5	792.5	792.5	792.5	792.5	791.6	790.7	789.8	788.9	788.2
127.5°	852.6	853.1	852.9	852.8	852.6	852.6	852.0	851.5	851.1	850.6	849.5
130°	891.0	891.7	891.9	892.2	892.3	892.6	891.9	891.2	890.5	889.9	889.0
132.5°	930.1	930.6	930.1	929.5	929.1	928.6	928.5	928.3	928.2	928.1	927.5
135°	985.0	985.4	985.0	984.6	984.0	983.6	983.2	982.7	982.3	981.9	980.9
137.5°	1034.5	1034.8	1034.5	1034.1	1033.6	1033.3	1033.4	1033.5	1033.5	1033.6	1033.1
140°	1064.5	1064.5	1064.4	1064.1	1063.9	1063.7	1064.1	1064.5	1065.0	1065.5	1065.0
142.5°	1093.4	1093.6	1094.0	1094.2	1094.6	1094.9	1095.0	1095.1	1095.2	1095.3	1094.7
145°	1137.5	1137.7	1137.7	1137.7	1137.7	1137.7	1138.0	1138.2	1138.4	1138.6	1138.1
147.5°	1173.4	1173.5	1173.7	1174.0	1174.3	1174.6	1174.8	1175.1	1175.4	1175.6	1174.9
150°	1196.0	1196.0	1196.4	1196.9	1197.3	1197.7	1198.2	1198.7	1199.1	1199.5	1198.9
152.5°	1217.0	1216.8	1217.3	1217.7	1218.1	1218.6	1219.0	1219.4	1220.0	1220.4	1219.8
155°	1245.4	1245.0	1245.4	1245.9	1246.4	1246.8	1247.5	1248.1	1248.8	1249.5	1248.9
157.5°	1270.6	1270.2	1270.3	1270.3	1270.4	1270.4	1271.1	1271.9	1272.6	1273.2	1272.7
160°	1284.5	1283.9	1284.2	1284.4	1284.6	1284.8	1285.7	1286.6	1287.5	1288.4	1288.0
162.5°	1297.3	1296.8	1296.9	1297.2	1297.4	1297.6	1298.9	1300.1	1301.4	1302.6	1302.3
165°	1314.5	1314.0	1314.1	1314.4	1314.6	1314.8	1316.2	1317.5	1318.9	1320.2	1319.9
167.5°	1327.1	1326.5	1326.8	1327.0	1327.2	1327.5	1329.0	1330.7	1332.2	1333.9	1333.7
170°	1333.6	1333.0	1333.2	1333.4	1333.6	1333.9	1335.7	1337.4	1339.2	1341.0	1340.8
172.5°	1338.4	1337.8	1338.3	1338.7	1339.0	1339.5	1341.1	1342.6	1344.3	1345.8	1345.7
175°	1344.5	1343.9	1344.2	1344.5	1344.6	1344.9	1346.6	1348.4	1350.2	1351.9	1351.9
177.5°	1348.0	1347.6	1347.7	1347.9	1348.1	1348.2	1349.5	1350.7	1352.0	1353.2	1353.1
180°	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9



TEST NUMBER: P333196-935

CATALOG NUMBER: S125DIP-S610D1205U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6
2.5°	734.2	736.1	734.5	736.6	734.5	736.1	734.2	735.8	738.1	736.6	740.2
5°	676.7	673.7	675.7	674.4	675.7	673.7	676.7	678.4	682.3	683.5	686.2
7.5°	623.6	620.8	617.6	616.0	617.6	620.8	623.6	624.6	627.9	632.8	636.5
10°	590.4	586.8	586.4	584.2	586.4	586.8	590.4	594.0	596.2	602.4	606.7
12.5°	566.0	562.7	559.0	558.0	559.0	562.7	566.0	569.1	569.8	576.9	579.8
15°	531.5	528.9	526.6	528.6	526.6	528.9	531.5	533.5	537.1	542.0	545.3
17.5°	502.7	500.6	500.2	497.8	500.2	500.6	502.7	503.9	509.8	513.0	518.6
20°	484.7	483.1	483.7	479.5	483.7	483.1	484.7	487.7	493.5	495.2	501.1
22.5°	470.4	467.1	466.7	465.9	466.7	467.1	470.4	473.0	474.2	479.2	483.3
25°	447.8	446.2	444.5	446.2	444.5	446.2	447.8	450.7	452.0	455.6	459.5
27.5°	428.1	426.1	425.7	425.9	425.7	426.1	428.1	427.8	431.4	434.2	437.1
30°	416.0	412.8	413.1	412.8	413.1	412.8	416.0	416.0	418.0	420.6	423.3
32.5°	402.9	400.7	400.3	399.7	400.3	400.7	402.9	402.4	404.9	408.0	411.0
35°	383.7	383.7	382.0	382.0	382.0	383.7	383.7	384.6	387.3	387.3	390.5
37.5°	365.5	365.2	364.2	364.4	364.2	365.2	365.5	366.4	367.2	368.6	370.7
40°	351.9	351.6	350.6	348.6	350.6	351.6	351.9	353.3	353.9	355.5	356.8
42.5°	338.9	337.8	337.3	336.7	337.3	337.8	338.9	339.7	340.0	342.2	344.8
45°	318.2	318.2	317.6	317.3	317.6	318.2	318.2	318.2	318.6	321.2	322.5
47.5°	298.3	298.9	300.1	299.9	300.1	298.9	298.3	297.7	297.8	299.1	300.7
50°	286.2	286.5	287.5	287.8	287.5	286.5	286.2	284.9	284.2	284.2	285.2
52.5°	272.9	274.7	276.0	275.8	276.0	274.7	272.9	271.8	270.6	269.1	270.5
55°	254.2	256.4	258.7	259.1	258.7	256.4	254.2	251.2	249.9	247.3	248.2
57.5°	235.7	238.8	241.3	242.0	241.3	238.8	235.7	232.1	227.8	226.6	224.8
60°	223.1	227.3	230.2	231.6	230.2	227.3	223.1	219.8	214.2	210.6	209.3
62.5°	211.0	215.8	218.8	219.0	218.8	215.8	211.0	206.0	200.4	196.2	193.6
65°	191.3	196.2	198.9	200.8	198.9	196.2	191.3	185.8	179.6	174.0	171.1
67.5°	170.1	175.0	178.0	179.5	178.0	175.0	170.1	163.2	157.6	151.2	147.7
70°	154.7	159.6	163.5	164.9	163.5	159.6	154.7	146.5	141.6	135.7	132.8
72.5°	139.6	143.9	147.1	148.6	147.1	143.9	139.6	131.9	126.2	120.3	116.3
75°	113.1	119.1	122.0	123.6	122.0	119.1	113.1	108.9	102.4	96.2	92.9
77.5°	87.3	92.6	94.4	95.2	94.4	92.6	87.3	82.3	77.3	72.8	69.6
80°	70.0	73.3	75.6	75.9	75.6	73.3	70.0	66.0	62.2	57.9	54.9
82.5°	53.8	56.5	57.3	58.1	57.3	56.5	53.8	50.4	47.0	43.7	41.3
85°	29.4	30.7	31.1	30.7	31.1	30.7	29.4	27.1	25.5	23.8	22.9
87.5°	14.1	13.9	14.1	14.7	14.1	13.9	14.1	13.4	13.5	12.7	12.1
90°	22.0	22.6	23.3	24.0	23.3	22.6	22.0	21.4	20.5	19.4	18.3
92.5°	21.4	21.8	22.1	22.4	22.1	21.8	21.4	21.2	20.5	19.4	18.3
95°	21.0	21.0	21.0	21.0	21.0	21.0	21.0	21.0	20.5	19.4	18.3
97.5°	21.0	21.0	21.0	21.0	21.0	21.0	21.0	21.0	24.1	30.4	36.7
100°	23.7	22.8	21.9	21.0	21.9	22.8	23.7	24.5	41.6	74.7	107.9
102.5°	171.3	156.1	141.0	125.9	141.0	156.1	171.3	186.4	197.1	203.4	209.6
105°	297.8	297.6	297.4	297.2	297.4	297.6	297.8	298.1	298.2	298.2	298.2
107.5°	376.6	376.0	375.3	374.6	375.3	376.0	376.6	377.3	377.6	377.5	377.5
110°	427.6	427.8	428.1	428.3	428.1	427.8	427.6	427.4	427.6	428.3	429.0



TEST NUMBER: P333196-935

CATALOG NUMBER: S125DIP-S610D1205U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	477.3	476.9	476.6	476.3	476.6	476.9	477.3	477.5	478.1	479.0	479.8
115°	552.3	551.0	549.7	548.4	549.7	551.0	552.3	553.7	554.8	555.7	556.6
117.5°	626.9	626.4	625.8	625.2	625.8	626.4	626.9	627.5	628.4	629.6	630.7
120°	675.8	674.7	673.6	672.4	673.6	674.7	675.8	676.9	677.7	678.1	678.6
122.5°	721.1	719.8	718.6	717.3	718.6	719.8	721.1	722.4	723.3	723.8	724.2
125°	787.5	786.9	786.2	785.5	786.2	786.9	787.5	788.2	788.9	789.8	790.7
127.5°	847.9	846.2	844.6	842.9	844.6	846.2	847.9	849.5	850.6	851.1	851.5
130°	887.9	886.8	885.7	884.6	885.7	886.8	887.9	889.0	889.9	890.5	891.2
132.5°	926.3	925.2	924.1	923.0	924.1	925.2	926.3	927.5	928.1	928.2	928.3
135°	979.6	978.3	977.0	975.6	977.0	978.3	979.6	980.9	981.9	982.3	982.7
137.5°	1031.9	1030.8	1029.6	1028.5	1029.6	1030.8	1031.9	1033.1	1033.6	1033.5	1033.5
140°	1063.7	1062.4	1061.0	1059.7	1061.0	1062.4	1063.7	1065.0	1065.5	1065.0	1064.5
142.5°	1093.3	1092.0	1090.6	1089.3	1090.6	1092.0	1093.3	1094.7	1095.3	1095.2	1095.1
145°	1136.7	1135.4	1134.0	1132.7	1134.0	1135.4	1136.7	1138.1	1138.6	1138.4	1138.2
147.5°	1173.4	1171.7	1170.2	1168.5	1170.2	1171.7	1173.4	1174.9	1175.6	1175.4	1175.1
150°	1197.1	1195.3	1193.5	1191.8	1193.5	1195.3	1197.1	1198.9	1199.5	1199.1	1198.7
152.5°	1218.1	1216.6	1215.0	1213.4	1215.0	1216.6	1218.1	1219.8	1220.4	1220.0	1219.4
155°	1247.2	1245.4	1243.5	1241.8	1243.5	1245.4	1247.2	1248.9	1249.5	1248.8	1248.1
157.5°	1270.9	1269.2	1267.4	1265.6	1267.4	1269.2	1270.9	1272.7	1273.2	1272.6	1271.9
160°	1286.2	1284.4	1282.6	1280.8	1282.6	1284.4	1286.2	1288.0	1288.4	1287.5	1286.6
162.5°	1300.3	1298.3	1296.4	1294.4	1296.4	1298.3	1300.3	1302.3	1302.6	1301.4	1300.1
165°	1318.2	1316.4	1314.6	1312.9	1314.6	1316.4	1318.2	1319.9	1320.2	1318.9	1317.5
167.5°	1331.6	1329.6	1327.7	1325.7	1327.7	1329.6	1331.6	1333.7	1333.9	1332.2	1330.7
170°	1338.9	1336.9	1334.9	1332.8	1334.9	1336.9	1338.9	1340.8	1341.0	1339.2	1337.4
172.5°	1343.7	1341.7	1339.6	1337.6	1339.6	1341.7	1343.7	1345.7	1345.8	1344.3	1342.6
175°	1349.9	1347.9	1345.8	1343.8	1345.8	1347.9	1349.9	1351.9	1351.9	1350.2	1348.4
177.5°	1351.8	1350.3	1348.8	1347.5	1348.8	1350.3	1351.8	1353.1	1353.2	1352.0	1350.7
180°	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9



TEST NUMBER: P333196-935

CATALOG NUMBER: S125DIP-S610D1205U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6
2.5°	736.8	739.9	743.9	746.7	752.0	754.3	757.2	759.6	763.8	767.7	772.4
5°	687.2	692.8	700.3	708.4	717.9	724.4	733.7	739.2	750.3	760.4	770.3
7.5°	642.1	649.0	659.6	670.1	682.5	693.8	705.2	717.9	732.1	748.9	762.8
10°	611.3	620.4	631.9	645.0	660.0	673.1	688.5	702.2	719.5	739.2	757.5
12.5°	586.7	594.5	607.3	619.8	635.9	651.9	667.8	686.0	706.2	728.0	751.0
15°	552.8	559.3	569.7	587.1	603.5	619.1	643.0	660.0	685.5	709.7	737.5
17.5°	523.7	531.9	540.7	555.6	572.5	592.1	613.5	634.8	659.4	690.1	721.4
20°	506.0	512.6	522.6	534.1	552.1	571.7	592.0	613.5	643.7	675.4	709.1
22.5°	486.6	493.7	505.1	517.6	532.7	551.6	573.9	597.6	629.0	660.2	696.8
25°	463.8	468.7	479.1	490.3	505.3	521.3	544.6	570.8	601.8	637.5	674.8
27.5°	442.3	446.6	456.2	465.8	479.4	498.4	519.2	545.6	574.9	611.1	652.4
30°	426.8	431.4	439.9	450.4	463.5	480.2	501.4	526.2	557.7	593.0	636.2
32.5°	413.5	417.6	424.0	434.5	447.2	463.4	483.1	508.5	539.8	575.8	618.1
35°	392.8	397.4	402.3	410.4	421.6	437.3	458.9	482.8	512.8	547.5	586.4
37.5°	372.3	377.2	381.6	388.9	399.1	412.9	431.6	456.5	483.7	517.1	554.5
40°	359.5	363.3	367.0	374.8	385.0	398.0	415.3	437.6	466.4	497.5	528.6
42.5°	346.6	350.3	353.4	360.2	369.5	382.1	398.6	420.3	447.0	476.0	503.4
45°	326.4	328.7	332.3	338.2	345.7	357.1	373.2	392.5	415.1	442.6	463.1
47.5°	304.5	308.2	311.1	316.2	322.4	333.6	349.0	365.5	386.0	406.4	420.9
50°	287.8	291.4	295.7	300.6	306.4	316.9	331.0	347.7	365.0	380.7	393.1
52.5°	272.2	275.4	280.0	284.6	291.8	300.7	312.7	327.5	344.6	355.9	366.2
55°	248.9	250.6	255.8	260.4	267.3	273.8	285.9	298.9	309.4	317.9	326.4
57.5°	225.2	227.4	230.4	234.5	241.3	249.0	257.4	269.1	275.2	279.6	286.2
60°	210.0	210.6	212.6	217.5	222.7	229.6	239.4	247.6	252.2	255.8	261.3
62.5°	193.2	193.4	196.7	200.3	204.1	211.5	219.6	226.1	230.0	231.7	237.0
65°	169.8	169.1	171.1	174.0	178.6	183.5	190.4	196.2	195.9	197.9	201.1
67.5°	145.8	145.1	145.1	147.9	151.6	156.0	160.7	164.1	164.2	166.8	168.4
70°	129.5	127.6	128.9	131.1	132.8	136.4	141.6	142.9	143.3	144.6	146.2
72.5°	112.8	112.1	113.1	114.2	115.3	118.0	122.5	123.3	123.4	124.2	126.8
75°	89.6	88.9	88.3	89.3	90.6	92.6	94.2	95.5	95.1	95.5	97.5
77.5°	67.2	65.3	65.0	65.5	65.9	67.1	68.8	68.6	69.0	68.9	71.1
80°	53.3	50.7	50.4	50.4	50.7	51.3	52.0	52.7	51.7	52.7	53.3
82.5°	39.2	37.6	37.5	37.3	37.4	37.5	37.9	38.2	38.1	38.5	38.9
85°	21.6	20.9	20.0	20.6	20.3	19.3	20.0	18.9	18.7	18.9	19.3
87.5°	10.8	10.8	10.0	9.6	9.0	9.0	8.2	7.6	6.9	6.8	7.2
90°	17.1	16.0	14.5	12.9	11.4	9.8	8.1	6.4	4.6	2.8	1.0
92.5°	17.1	16.0	14.6	13.3	11.9	10.5	10.4	11.7	12.9	14.2	15.4
95°	17.1	16.0	24.5	32.9	41.3	49.9	54.3	55.0	55.7	56.4	57.0
97.5°	43.0	49.2	66.0	82.7	99.4	116.1	123.9	122.7	121.5	120.3	119.1
100°	140.9	174.1	173.2	172.4	171.4	170.6	169.8	169.1	168.4	167.8	167.1
102.5°	215.9	222.1	221.6	221.1	220.5	220.0	219.3	218.4	217.7	216.8	215.9
105°	298.2	298.2	298.2	298.2	298.2	298.2	297.7	296.9	295.9	295.1	294.2
107.5°	377.5	377.5	377.0	376.5	376.1	375.7	375.5	375.5	375.5	375.5	375.5
110°	429.6	430.2	429.8	429.4	429.0	428.5	428.3	428.3	428.3	428.3	428.3



TEST NUMBER: P333196-935

CATALOG NUMBER: S125DIP-S610D1205U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	480.7	481.5	481.2	481.0	480.7	480.4	480.0	479.5	479.0	478.5	477.9
115°	557.5	558.4	558.1	557.9	557.7	557.5	556.8	555.7	554.6	553.5	552.3
117.5°	631.9	633.0	632.1	631.3	630.5	629.6	629.2	629.3	629.3	629.4	629.4
120°	679.0	679.4	678.7	678.1	677.4	676.7	676.6	676.7	677.0	677.2	677.4
122.5°	724.6	725.0	724.8	724.4	724.1	723.8	723.2	722.4	721.5	720.7	719.9
125°	791.6	792.5	792.5	792.5	792.5	792.5	791.7	790.1	788.6	787.0	785.5
127.5°	852.0	852.6	852.6	852.8	852.9	853.1	852.6	851.4	850.3	849.3	848.2
130°	891.9	892.6	892.3	892.2	891.9	891.7	891.0	889.9	888.8	887.7	886.6
132.5°	928.5	928.6	929.1	929.5	930.1	930.6	930.1	928.8	927.6	926.3	925.0
135°	983.2	983.6	984.0	984.6	985.0	985.4	985.0	983.6	982.3	980.9	979.6
137.5°	1033.4	1033.3	1033.6	1034.1	1034.5	1034.8	1034.5	1033.3	1032.2	1031.0	1029.8
140°	1064.1	1063.7	1063.9	1064.1	1064.4	1064.5	1064.5	1064.0	1063.6	1063.2	1062.6
142.5°	1095.0	1094.9	1094.6	1094.2	1094.0	1093.6	1093.4	1093.1	1092.9	1092.5	1092.3
145°	1138.0	1137.7	1137.7	1137.7	1137.7	1137.7	1137.5	1137.0	1136.6	1136.2	1135.7
147.5°	1174.8	1174.6	1174.3	1174.0	1173.7	1173.5	1173.4	1173.5	1173.5	1173.6	1173.7
150°	1198.2	1197.7	1197.3	1196.9	1196.4	1196.0	1196.0	1196.4	1196.9	1197.3	1197.7
152.5°	1219.0	1218.6	1218.1	1217.7	1217.3	1216.8	1217.0	1218.1	1219.0	1220.0	1221.0
155°	1247.5	1246.8	1246.4	1245.9	1245.4	1245.0	1245.4	1246.8	1248.1	1249.5	1250.8
157.5°	1271.1	1270.4	1270.4	1270.3	1270.3	1270.2	1270.6	1271.4	1272.2	1273.0	1273.8
160°	1285.7	1284.8	1284.6	1284.4	1284.2	1283.9	1284.5	1285.8	1287.2	1288.5	1289.9
162.5°	1298.9	1297.6	1297.4	1297.2	1296.9	1296.8	1297.3	1298.6	1299.9	1301.3	1302.6
165°	1316.2	1314.8	1314.6	1314.4	1314.1	1314.0	1314.5	1315.9	1317.2	1318.5	1319.8
167.5°	1329.0	1327.5	1327.2	1327.0	1326.8	1326.5	1327.1	1328.5	1329.9	1331.3	1332.7
170°	1335.7	1333.9	1333.6	1333.4	1333.2	1333.0	1333.6	1335.2	1336.7	1338.3	1339.9
172.5°	1341.1	1339.5	1339.0	1338.7	1338.3	1337.8	1338.4	1340.0	1341.5	1343.1	1344.6
175°	1346.6	1344.9	1344.6	1344.5	1344.2	1343.9	1344.5	1345.8	1347.2	1348.5	1349.9
177.5°	1349.5	1348.2	1348.1	1347.9	1347.7	1347.6	1348.0	1349.1	1350.1	1351.2	1352.3
180°	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9



TEST NUMBER: P333196-935

CATALOG NUMBER: S125DIP-S610D1205U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6
2.5°	774.8	778.4	780.8	785.2	788.9	791.0	792.8	794.4	796.3	797.8	802.3
5°	779.7	788.2	795.5	806.6	816.7	824.6	833.0	840.6	846.8	855.7	862.5
7.5°	777.6	792.7	808.6	825.7	843.3	859.7	874.7	888.8	901.6	917.0	930.5
10°	775.5	796.1	816.4	839.6	863.5	883.7	902.8	922.0	936.1	955.7	972.4
12.5°	774.0	798.2	822.7	850.6	876.8	905.4	930.7	944.8	966.2	981.9	1001.7
15°	767.3	799.4	833.0	864.4	901.7	928.2	950.5	977.9	997.9	1017.9	1039.4
17.5°	755.4	791.8	829.5	870.6	906.4	934.9	963.5	990.0	1013.8	1040.5	1067.5
20°	750.0	786.3	829.5	871.7	906.6	936.4	965.9	995.0	1021.1	1055.5	1086.5
22.5°	738.5	782.4	822.2	863.2	899.3	931.7	965.1	998.1	1032.9	1071.7	1110.6
25°	717.9	762.4	804.6	845.2	881.5	922.0	957.7	1001.9	1046.3	1097.7	1146.1
27.5°	696.6	739.2	777.8	817.0	859.4	905.3	951.5	1001.6	1059.9	1124.6	1193.0
30°	679.3	719.5	757.2	797.4	841.5	893.2	943.9	1003.5	1070.8	1143.8	1224.9
32.5°	659.2	696.3	732.9	775.4	823.5	878.0	937.1	1002.4	1083.4	1166.3	1249.7
35°	624.7	655.8	693.4	738.8	793.2	855.7	924.0	1001.2	1094.1	1189.2	1259.6
37.5°	583.8	612.8	652.4	702.2	759.1	826.2	907.3	998.8	1097.5	1173.4	1196.1
40°	556.4	583.2	624.4	676.1	734.3	805.3	894.2	991.0	1086.5	1135.0	1116.3
42.5°	527.0	555.2	595.4	646.5	709.1	786.4	877.7	974.6	1054.6	1072.9	1008.5
45°	480.8	509.9	549.5	601.2	668.6	752.3	847.5	935.4	981.5	948.5	848.8
47.5°	437.8	465.1	501.8	555.1	624.7	711.3	802.9	873.1	876.8	797.9	691.4
50°	408.5	433.7	470.6	524.0	593.0	680.6	763.4	818.6	793.8	704.6	602.2
52.5°	379.7	404.4	440.8	493.6	561.9	642.1	719.2	757.9	711.1	619.5	532.0
55°	338.2	359.8	395.5	444.2	508.9	583.5	648.9	662.3	601.5	511.2	440.2
57.5°	297.6	317.8	350.3	395.1	454.3	520.4	571.5	568.7	504.4	426.9	370.6
60°	270.2	289.8	318.6	362.4	416.4	473.3	517.1	506.6	442.9	376.2	328.7
62.5°	245.6	263.1	290.3	328.6	377.9	430.6	466.6	451.2	388.7	330.4	292.8
65°	209.3	224.0	247.3	280.0	320.9	364.4	392.2	372.2	318.9	273.5	243.3
67.5°	174.7	186.5	206.0	232.1	267.0	301.9	318.8	298.8	256.1	222.9	200.6
70°	152.7	163.2	178.2	201.5	231.9	261.3	274.1	256.1	219.5	191.0	175.0
72.5°	130.8	139.4	152.7	173.5	197.9	223.4	234.5	217.4	187.3	163.2	148.3
75°	101.1	106.9	116.1	130.5	149.8	170.0	176.3	161.3	142.0	124.0	114.2
77.5°	72.3	77.3	84.3	93.3	107.0	119.9	125.4	116.7	101.7	90.3	82.3
80°	55.6	58.2	64.1	71.6	82.4	90.6	94.2	88.6	78.2	69.7	63.5
82.5°	39.6	42.3	45.8	52.0	58.9	64.4	68.3	64.6	57.0	50.3	46.7
85°	19.3	20.9	22.9	25.5	30.7	34.0	33.7	31.4	28.4	25.8	23.8
87.5°	7.3	8.0	9.1	10.8	11.9	13.3	14.1	13.9	13.2	12.6	12.1
90°	2.8	4.6	6.4	8.1	9.8	11.4	12.9	14.5	16.0	17.1	18.3
92.5°	14.2	12.9	11.7	10.4	10.5	11.9	13.3	14.6	16.0	17.1	18.3
95°	56.4	55.7	55.0	54.3	49.9	41.3	32.9	24.5	16.0	17.1	18.3
97.5°	120.3	121.5	122.7	123.9	116.1	99.4	82.7	66.0	49.2	43.0	36.7
100°	167.8	168.4	169.1	169.8	170.6	171.4	172.4	173.2	174.1	140.9	107.9
102.5°	216.8	217.7	218.4	219.3	220.0	220.5	221.1	221.6	222.1	215.9	209.6
105°	295.1	295.9	296.9	297.7	298.2	298.2	298.2	298.2	298.2	298.2	298.2
107.5°	375.5	375.5	375.5	375.5	375.7	376.1	376.5	377.0	377.5	377.5	377.5
110°	428.3	428.3	428.3	428.3	428.5	429.0	429.4	429.8	430.2	429.6	429.0



TEST NUMBER: P333196-935

CATALOG NUMBER: S125DIP-S610D1205U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	478.5	479.0	479.5	480.0	480.4	480.7	481.0	481.2	481.5	480.7	479.8
115°	553.5	554.6	555.7	556.8	557.5	557.7	557.9	558.1	558.4	557.5	556.6
117.5°	629.4	629.3	629.3	629.2	629.6	630.5	631.3	632.1	633.0	631.9	630.7
120°	677.2	677.0	676.7	676.6	676.7	677.4	678.1	678.7	679.4	679.0	678.6
122.5°	720.7	721.5	722.4	723.2	723.8	724.1	724.4	724.8	725.0	724.6	724.2
125°	787.0	788.6	790.1	791.7	792.5	792.5	792.5	792.5	792.5	791.6	790.7
127.5°	849.3	850.3	851.4	852.6	853.1	852.9	852.8	852.6	852.6	852.0	851.5
130°	887.7	888.8	889.9	891.0	891.7	891.9	892.2	892.3	892.6	891.9	891.2
132.5°	926.3	927.6	928.8	930.1	930.6	930.1	929.5	929.1	928.6	928.5	928.3
135°	980.9	982.3	983.6	985.0	985.4	985.0	984.6	984.0	983.6	983.2	982.7
137.5°	1031.0	1032.2	1033.3	1034.5	1034.8	1034.5	1034.1	1033.6	1033.3	1033.4	1033.5
140°	1063.2	1063.6	1064.0	1064.5	1064.5	1064.4	1064.1	1063.9	1063.7	1064.1	1064.5
142.5°	1092.5	1092.9	1093.1	1093.4	1093.6	1094.0	1094.2	1094.6	1094.9	1095.0	1095.1
145°	1136.2	1136.6	1137.0	1137.5	1137.7	1137.7	1137.7	1137.7	1137.7	1138.0	1138.2
147.5°	1173.6	1173.5	1173.5	1173.4	1173.5	1173.7	1174.0	1174.3	1174.6	1174.8	1175.1
150°	1197.3	1196.9	1196.4	1196.0	1196.0	1196.4	1196.9	1197.3	1197.7	1198.2	1198.7
152.5°	1220.0	1219.0	1218.1	1217.0	1216.8	1217.3	1217.7	1218.1	1218.6	1219.0	1219.4
155°	1249.5	1248.1	1246.8	1245.4	1245.0	1245.4	1245.9	1246.4	1246.8	1247.5	1248.1
157.5°	1273.0	1272.2	1271.4	1270.6	1270.2	1270.3	1270.3	1270.4	1270.4	1271.1	1271.9
160°	1288.5	1287.2	1285.8	1284.5	1283.9	1284.2	1284.4	1284.6	1284.8	1285.7	1286.6
162.5°	1301.3	1299.9	1298.6	1297.3	1296.8	1296.9	1297.2	1297.4	1297.6	1298.9	1300.1
165°	1318.5	1317.2	1315.9	1314.5	1314.0	1314.1	1314.4	1314.6	1314.8	1316.2	1317.5
167.5°	1331.3	1329.9	1328.5	1327.1	1326.5	1326.8	1327.0	1327.2	1327.5	1329.0	1330.7
170°	1338.3	1336.7	1335.2	1333.6	1333.0	1333.2	1333.4	1333.6	1333.9	1335.7	1337.4
172.5°	1343.1	1341.5	1340.0	1338.4	1337.8	1338.3	1338.7	1339.0	1339.5	1341.1	1342.6
175°	1348.5	1347.2	1345.8	1344.5	1343.9	1344.2	1344.5	1344.6	1344.9	1346.6	1348.4
177.5°	1351.2	1350.1	1349.1	1348.0	1347.6	1347.7	1347.9	1348.1	1348.2	1349.5	1350.7
180°	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9



TEST NUMBER: P333196-935

CATALOG NUMBER: S125DIP-S610D1205U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	770.6	770.6	770.6	770.6	770.6	770.6	770.6
2.5°	805.9	808.0	812.4	810.9	813.0	814.0	815.1
5°	871.0	881.5	886.1	885.4	892.3	890.6	889.0
7.5°	944.5	955.5	961.7	969.3	973.8	974.0	977.9
10°	986.1	1000.5	1006.4	1014.6	1019.9	1022.8	1022.4
12.5°	1018.0	1029.3	1042.5	1046.5	1053.6	1057.3	1055.9
15°	1056.4	1074.4	1088.1	1095.0	1103.9	1106.5	1110.1
17.5°	1090.7	1114.8	1130.9	1152.2	1160.3	1165.2	1162.3
20°	1116.6	1148.3	1164.4	1189.9	1203.9	1211.5	1208.8
22.5°	1147.3	1181.6	1211.3	1233.3	1254.7	1264.9	1267.0
25°	1199.7	1246.8	1290.3	1319.4	1345.9	1352.1	1365.9
27.5°	1258.4	1313.9	1360.4	1390.9	1409.5	1416.3	1420.6
30°	1295.2	1350.5	1385.5	1405.1	1411.0	1410.3	1409.7
32.5°	1313.3	1347.9	1354.6	1349.1	1335.7	1324.2	1312.3
35°	1287.7	1261.9	1223.2	1173.5	1137.0	1099.9	1096.3
37.5°	1158.1	1075.5	1011.2	939.5	898.1	872.5	854.8
40°	1036.1	942.3	864.4	803.9	761.7	745.1	728.8
42.5°	903.8	814.1	745.1	694.6	662.9	644.4	631.4
45°	734.3	655.1	601.2	564.6	539.3	525.0	516.8
47.5°	601.7	543.1	497.3	470.9	453.5	442.3	442.3
50°	530.5	474.6	444.2	423.3	408.2	399.3	401.0
52.5°	467.4	425.7	399.7	382.1	371.0	365.6	365.4
55°	390.9	360.8	343.8	331.0	323.5	317.3	318.6
57.5°	334.3	308.9	297.6	287.0	281.7	279.2	275.7
60°	299.3	279.7	269.8	261.3	256.1	254.2	250.6
62.5°	268.1	252.7	243.1	236.2	231.5	230.8	228.0
65°	225.3	213.6	205.1	201.8	196.9	195.6	195.6
67.5°	185.8	177.4	170.7	167.7	165.6	165.9	164.3
70°	160.9	154.0	149.8	146.5	144.9	145.3	143.9
72.5°	140.8	133.1	129.4	127.4	125.3	126.1	125.6
75°	106.6	102.7	100.7	98.8	97.5	96.8	96.2
77.5°	78.3	74.8	73.4	72.2	72.4	70.9	72.1
80°	60.5	57.6	56.6	54.9	54.6	54.6	54.3
82.5°	44.3	42.6	41.9	40.6	40.0	40.5	39.6
85°	22.9	21.6	21.3	21.3	20.6	20.0	21.6
87.5°	12.2	11.5	11.6	11.5	11.6	11.5	11.1
90°	19.4	20.5	21.4	22.0	22.6	23.3	24.0
92.5°	19.4	20.5	21.2	21.4	21.8	22.1	22.4
95°	19.4	20.5	21.0	21.0	21.0	21.0	21.0
97.5°	30.4	24.1	21.0	21.0	21.0	21.0	21.0
100°	74.7	41.6	24.5	23.7	22.8	21.9	21.0
102.5°	203.4	197.1	186.4	171.3	156.1	141.0	125.9
105°	298.2	298.2	298.1	297.8	297.6	297.4	297.2
107.5°	377.5	377.6	377.3	376.6	376.0	375.3	374.6
110°	428.3	427.6	427.4	427.6	427.8	428.1	428.3



TEST NUMBER: P333196-935

CATALOG NUMBER: S125DIP-S610D1205U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	479.0	478.1	477.5	477.3	476.9	476.6	476.3
115°	555.7	554.8	553.7	552.3	551.0	549.7	548.4
117.5°	629.6	628.4	627.5	626.9	626.4	625.8	625.2
120°	678.1	677.7	676.9	675.8	674.7	673.6	672.4
122.5°	723.8	723.3	722.4	721.1	719.8	718.6	717.3
125°	789.8	788.9	788.2	787.5	786.9	786.2	785.5
127.5°	851.1	850.6	849.5	847.9	846.2	844.6	842.9
130°	890.5	889.9	889.0	887.9	886.8	885.7	884.6
132.5°	928.2	928.1	927.5	926.3	925.2	924.1	923.0
135°	982.3	981.9	980.9	979.6	978.3	977.0	975.6
137.5°	1033.5	1033.6	1033.1	1031.9	1030.8	1029.6	1028.5
140°	1065.0	1065.5	1065.0	1063.7	1062.4	1061.0	1059.7
142.5°	1095.2	1095.3	1094.7	1093.3	1092.0	1090.6	1089.3
145°	1138.4	1138.6	1138.1	1136.7	1135.4	1134.0	1132.7
147.5°	1175.4	1175.6	1174.9	1173.4	1171.7	1170.2	1168.5
150°	1199.1	1199.5	1198.9	1197.1	1195.3	1193.5	1191.8
152.5°	1220.0	1220.4	1219.8	1218.1	1216.6	1215.0	1213.4
155°	1248.8	1249.5	1248.9	1247.2	1245.4	1243.5	1241.8
157.5°	1272.6	1273.2	1272.7	1270.9	1269.2	1267.4	1265.6
160°	1287.5	1288.4	1288.0	1286.2	1284.4	1282.6	1280.8
162.5°	1301.4	1302.6	1302.3	1300.3	1298.3	1296.4	1294.4
165°	1318.9	1320.2	1319.9	1318.2	1316.4	1314.6	1312.9
167.5°	1332.2	1333.9	1333.7	1331.6	1329.6	1327.7	1325.7
170°	1339.2	1341.0	1340.8	1338.9	1336.9	1334.9	1332.8
172.5°	1344.3	1345.8	1345.7	1343.7	1341.7	1339.6	1337.6
175°	1350.2	1351.9	1351.9	1349.9	1347.9	1345.8	1343.8
177.5°	1352.0	1353.2	1353.1	1351.8	1350.3	1348.8	1347.5
180°	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9	1349.9

(END OF REPORT)