

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333312-830

Luminaire Tested: **S125DIP-S1270D590U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333312-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1270D590U830-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6834.8 lumens
Efficiency: N/A
Efficacy: 124.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333312-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333312-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	112	112	112	112	106	106	106	106	95	95	95		85	85	85		75	75	75	71
1	102	98	94	90	97	93	89	86	83	80	78		74	72	70		66	65	63	59
2	93	85	79	74	88	81	75	71	73	68	64		65	62	59		58	56	53	50
3	85	75	67	61	80	71	64	59	64	59	54		58	53	50		52	48	45	42
4	78	67	58	52	73	63	56	50	57	51	46		51	47	43		46	42	39	36
5	72	59	51	45	67	57	49	43	51	45	40		46	41	37		42	37	34	31
6	66	53	45	39	62	51	43	38	46	40	35		42	37	32		38	33	30	27
7	61	48	40	34	58	46	39	33	42	36	31		38	33	29		35	30	27	24
8	57	44	36	30	54	42	35	30	38	32	28		35	30	26		32	27	24	22
9	53	40	33	27	50	39	31	26	35	29	25		32	27	23		29	25	22	20
10	50	37	30	25	47	36	29	24	33	27	22		30	25	21		27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11996	11996	11996
5°	12023	11909	11985
10°	11950	11825	11893
15°	11820	11683	11732
20°	11635	11483	11504
25°	11436	11247	11236
30°	11189	10992	10937
35°	10925	10717	10566
40°	10655	10420	10270
45°	10361	10147	9945
50°	10040	9818	9523
55°	9730	9448	9183
60°	9357	9074	8751
65°	8915	8623	8332
70°	8492	8103	7825
75°	7738	7481	7224
80°	6884	6776	6616
85°	5995	6099	5772



TEST NUMBER: P333312-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	175.1	2.6
10°-20°	494.7	7.2
20°-30°	730.5	10.7
30°-40°	852.4	12.5
40°-50°	856.1	12.5
50°-60°	751.5	11.0
60°-70°	559.9	8.2
70°-80°	320.2	4.7
80°-90°	94.6	1.4
90°-100°	193.3	2.8
100°-110°	415.5	6.1
110°-120°	390.0	5.7
120°-130°	316.0	4.6
130°-140°	253.6	3.7
140°-150°	191.4	2.8
150°-160°	134.7	2.0
160°-170°	79.4	1.2
170°-180°	25.8	0.4
0°-30°	1400.3	20.5
0°-40°	2252.7	33.0
0°-60°	3860.3	56.5
0°-90°	4835.0	70.7
90°-120°	998.8	14.6
90°-150°	1759.9	25.7
90°-180°	2000.0	29.3
0°-180°	6834.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1858	1858	1858	1858	1858	
5°	1854	1851	1837	1849	1849	176
15°	1768	1763	1747	1754	1755	498
25°	1605	1597	1578	1581	1577	738
35°	1386	1379	1359	1352	1340	866
45°	1134	1128	1111	1094	1089	874
55°	864	859	839	826	816	771
65°	583	580	564	551	545	579
75°	310	307	300	295	290	331
85°	81	82	82	81	78	90
90°	1	5	9	11	12	5
95°	18	52	476	216	126	19
105°	61	85	390	767	712	64
115°	109	131	313	674	794	107
125°	150	176	300	537	625	134
135°	176	212	298	450	519	137
145°	205	235	299	372	410	129
155°	234	252	291	329	344	108
165°	256	263	280	296	301	72
175°	266	266	268	272	270	25
180°	267	267	267	267	267	



TEST NUMBER: P333312-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5
2.5°	1862.2	1861.4	1860.7	1859.8	1859.1	1857.4	1854.7	1852.1	1849.6	1846.9	1849.6
5°	1854.5	1853.9	1853.2	1852.6	1851.9	1850.0	1846.7	1843.4	1840.2	1836.9	1839.8
7.5°	1837.5	1836.8	1836.2	1835.5	1834.8	1832.8	1829.2	1825.6	1822.0	1818.4	1821.3
10°	1822.2	1821.6	1820.9	1820.2	1819.6	1817.5	1813.9	1810.3	1806.7	1803.1	1805.7
12.5°	1803.4	1802.2	1801.1	1799.9	1798.7	1796.5	1793.1	1789.8	1786.5	1783.1	1785.3
15°	1767.8	1766.9	1765.9	1764.9	1764.0	1761.6	1758.0	1754.4	1750.9	1747.3	1748.9
17.5°	1727.0	1725.6	1724.1	1722.7	1721.3	1718.6	1715.0	1711.2	1707.5	1703.7	1705.8
20°	1692.9	1692.2	1691.6	1690.9	1690.3	1687.8	1683.6	1679.3	1675.1	1670.8	1673.1
22.5°	1658.8	1657.6	1656.4	1655.3	1654.1	1651.5	1647.6	1643.6	1639.6	1635.6	1637.1
25°	1604.8	1603.1	1601.5	1599.9	1598.2	1595.3	1591.0	1586.8	1582.5	1578.3	1578.9
27.5°	1541.5	1540.6	1539.5	1538.6	1537.7	1534.9	1530.6	1526.2	1521.8	1517.4	1517.6
30°	1500.4	1499.4	1498.5	1497.4	1496.5	1493.6	1488.7	1483.8	1478.8	1473.9	1473.3
32.5°	1455.8	1454.2	1452.7	1451.2	1449.7	1446.8	1442.4	1438.0	1433.6	1429.3	1428.1
35°	1385.7	1384.5	1383.2	1381.9	1380.5	1377.6	1373.0	1368.5	1363.9	1359.3	1357.7
37.5°	1313.2	1311.5	1309.9	1308.2	1306.6	1303.6	1299.4	1295.1	1290.7	1286.5	1284.0
40°	1263.8	1262.2	1260.6	1258.9	1257.3	1254.1	1249.6	1245.0	1240.5	1235.9	1232.9
42.5°	1210.9	1209.6	1208.2	1206.7	1205.4	1202.4	1197.9	1193.3	1188.7	1184.1	1181.5
45°	1134.4	1133.2	1131.9	1130.6	1129.3	1126.6	1122.8	1118.8	1114.9	1111.0	1107.0
47.5°	1052.2	1052.3	1052.3	1052.3	1052.4	1050.1	1045.5	1040.8	1036.0	1031.3	1027.4
50°	999.3	998.3	997.3	996.4	995.3	992.9	989.0	985.1	981.2	977.2	973.0
52.5°	945.2	944.5	943.8	943.0	942.4	939.9	935.7	931.5	927.4	923.1	919.5
55°	864.1	863.1	862.1	861.1	860.2	857.4	852.8	848.3	843.7	839.1	836.1
57.5°	778.5	778.1	777.5	777.0	776.5	774.3	770.4	766.6	762.7	758.8	755.1
60°	724.4	723.2	721.9	720.6	719.3	716.8	713.2	709.6	706.1	702.5	699.2
62.5°	668.1	667.0	666.0	664.9	663.8	661.9	658.7	655.6	652.6	649.5	646.0
65°	583.4	582.8	582.1	581.5	580.8	578.6	575.0	571.5	567.9	564.3	561.4
67.5°	501.4	500.0	498.7	497.3	496.0	493.9	491.3	488.5	485.9	483.1	480.7
70°	449.7	448.1	446.4	444.8	443.2	440.8	437.9	435.0	432.1	429.1	427.2
72.5°	393.2	392.1	391.1	389.9	388.8	387.3	385.4	383.5	381.6	379.8	377.5
75°	310.1	309.4	308.8	308.1	307.5	306.3	304.7	303.0	301.4	299.8	298.8
77.5°	233.4	233.1	232.8	232.6	232.3	231.8	230.8	229.9	228.9	228.1	227.5
80°	185.1	185.1	185.1	185.1	185.1	184.8	184.2	183.5	182.9	182.2	181.9
82.5°	142.8	142.3	141.8	141.3	140.7	140.4	140.3	140.2	140.1	139.9	139.3
85°	80.9	81.2	81.4	81.8	82.1	82.3	82.3	82.3	82.3	82.3	82.0
87.5°	31.9	32.0	32.1	32.4	32.6	32.7	32.5	32.5	32.3	32.3	32.4
90°	0.6	1.0	2.2	3.2	4.3	5.4	5.9	7.0	7.5	8.6	9.1
92.5°	6.6	7.9	12.4	19.1	28.4	44.1	73.4	122.7	176.2	173.3	140.3
95°	17.7	18.3	22.6	28.5	40.3	64.6	122.1	240.3	388.7	476.4	466.2
97.5°	29.5	30.1	33.1	39.0	49.7	67.1	105.2	191.8	347.1	508.7	589.8
100°	37.6	38.7	40.9	46.8	57.0	73.1	104.3	174.2	309.7	485.5	619.9
102.5°	46.7	47.3	49.0	55.4	64.8	80.4	108.2	166.9	281.3	444.6	601.8
105°	60.8	60.8	63.4	68.8	77.4	92.5	116.1	164.0	253.7	389.8	544.1
107.5°	74.6	75.6	78.1	82.6	91.5	105.1	128.0	168.9	242.1	352.0	485.2
110°	84.5	85.5	87.7	92.5	100.6	114.5	136.6	173.6	238.7	334.4	451.7



TEST NUMBER: P333312-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	94.3	95.4	97.1	102.0	110.0	123.6	144.8	179.6	238.7	324.1	426.7
115°	108.6	109.7	111.3	116.1	124.2	137.6	157.5	188.7	240.3	312.9	399.4
117.5°	121.5	123.1	124.9	129.7	138.8	151.8	170.7	199.1	243.8	307.5	383.2
120°	130.1	131.8	133.8	138.7	147.9	161.3	180.1	205.9	247.3	304.8	374.2
122.5°	139.1	140.3	142.0	146.8	156.9	170.3	189.2	213.7	250.3	302.7	366.5
125°	150.5	151.7	154.3	159.1	169.4	183.3	201.0	224.2	255.4	300.0	355.9
127.5°	159.5	161.1	164.6	170.7	181.5	195.5	212.5	233.8	261.1	298.7	346.3
130°	165.0	166.6	171.0	178.0	189.3	203.2	219.9	240.3	264.6	297.8	339.8
132.5°	169.4	171.4	176.5	184.5	196.1	210.1	226.8	245.9	268.4	297.8	334.6
135°	176.3	178.5	184.9	193.6	204.8	219.3	236.0	253.7	273.6	297.8	328.5
137.5°	185.2	186.8	192.8	201.4	212.4	227.4	242.6	259.6	278.5	298.5	323.0
140°	190.3	191.9	198.4	207.0	217.3	231.8	247.3	263.4	280.7	299.0	320.5
142.5°	196.3	197.6	203.6	212.2	222.0	235.6	250.3	265.6	281.9	299.4	318.3
145°	205.4	206.4	211.8	219.3	229.0	241.4	255.4	268.8	283.3	299.0	315.1
147.5°	214.8	215.5	220.1	227.1	235.4	246.4	258.6	270.8	283.9	297.6	311.7
150°	220.5	221.5	225.3	232.2	239.8	248.9	260.8	272.0	283.9	296.2	309.2
152.5°	226.5	227.1	230.5	236.6	243.6	251.9	262.9	272.9	283.4	294.5	306.1
155°	234.4	234.4	237.6	243.0	248.4	255.9	265.0	273.6	282.3	291.4	301.0
157.5°	241.5	241.4	244.0	248.6	253.4	259.0	266.9	274.2	280.9	288.1	296.3
160°	246.3	245.7	247.9	251.7	255.9	260.8	267.8	274.2	279.6	286.1	292.5
162.5°	250.2	249.6	251.8	255.1	258.5	262.5	268.6	273.8	278.3	283.4	289.1
165°	255.9	254.9	256.5	259.1	261.3	264.6	268.8	273.1	276.4	279.6	283.9
167.5°	259.8	259.3	260.2	261.7	263.3	265.2	268.8	271.8	273.3	275.8	278.8
170°	262.4	261.8	262.4	263.4	264.6	266.2	268.8	271.0	272.0	273.6	275.8
172.5°	264.1	263.2	263.6	264.8	265.4	266.2	268.4	270.1	270.3	271.1	272.8
175°	266.2	265.0	265.6	266.2	266.2	266.2	267.8	268.8	268.2	268.2	268.8
177.5°	267.1	266.3	266.3	266.6	266.3	266.3	267.1	267.5	266.6	266.6	267.1
180°	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6



TEST NUMBER: P333312-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5
2.5°	1852.1	1854.7	1857.4	1858.5	1858.3	1858.0	1857.8	1857.5
5°	1842.8	1845.8	1848.7	1850.0	1849.6	1849.4	1849.0	1848.7
7.5°	1824.1	1827.0	1829.9	1831.2	1830.9	1830.5	1830.2	1829.9
10°	1808.4	1811.0	1813.5	1814.7	1814.4	1814.0	1813.7	1813.5
12.5°	1787.3	1789.4	1791.5	1792.5	1792.4	1792.3	1792.3	1792.2
15°	1750.6	1752.2	1753.8	1754.6	1754.6	1754.6	1754.6	1754.6
17.5°	1707.8	1709.9	1711.8	1712.0	1710.4	1708.8	1707.1	1705.5
20°	1675.5	1677.7	1680.0	1680.4	1678.7	1677.1	1675.5	1673.8
22.5°	1638.6	1640.1	1641.6	1641.8	1640.7	1639.6	1638.4	1637.4
25°	1579.6	1580.3	1580.9	1580.7	1579.8	1578.8	1577.8	1576.8
27.5°	1517.7	1517.9	1518.0	1517.5	1516.6	1515.6	1514.6	1513.6
30°	1472.6	1472.0	1471.3	1470.6	1469.5	1468.6	1467.5	1466.6
32.5°	1426.9	1425.8	1424.6	1423.1	1421.4	1419.6	1417.8	1416.1
35°	1356.0	1354.4	1352.8	1350.7	1348.0	1345.5	1342.8	1340.2
37.5°	1281.6	1279.2	1276.8	1274.8	1273.3	1271.8	1270.3	1268.8
40°	1230.0	1227.1	1224.1	1222.2	1221.2	1220.2	1219.2	1218.2
42.5°	1178.8	1176.1	1173.5	1171.4	1169.9	1168.4	1166.9	1165.4
45°	1103.2	1099.2	1095.3	1092.9	1091.8	1090.9	1089.9	1088.9
47.5°	1023.3	1019.4	1015.4	1012.3	1009.9	1007.7	1005.4	1003.1
50°	968.7	964.5	960.3	957.0	954.7	952.4	950.2	947.8
52.5°	915.7	912.0	908.2	905.1	902.6	900.0	897.5	894.9
55°	833.2	830.3	827.4	824.7	822.5	820.2	817.8	815.6
57.5°	751.3	747.5	743.8	741.2	740.0	738.8	737.4	736.2
60°	695.9	692.7	689.4	686.6	684.3	682.0	679.8	677.5
62.5°	642.4	638.9	635.5	632.8	631.0	629.2	627.5	625.8
65°	558.5	555.4	552.5	550.4	549.1	547.8	546.5	545.2
67.5°	478.2	475.7	473.3	471.6	470.8	470.0	469.3	468.4
70°	425.2	423.2	421.2	419.6	418.3	417.0	415.8	414.4
72.5°	375.3	373.1	370.9	369.1	367.8	366.5	365.1	363.8
75°	297.8	296.8	295.9	294.7	293.4	292.1	290.8	289.5
77.5°	226.9	226.3	225.7	225.0	224.0	223.1	222.3	221.3
80°	181.5	181.3	180.9	180.4	179.7	179.1	178.4	177.9
82.5°	138.7	138.2	137.5	137.2	137.0	137.0	136.8	136.7
85°	81.6	81.3	81.0	80.5	79.8	79.2	78.5	77.9
87.5°	32.5	32.6	32.7	32.7	32.1	31.7	31.2	30.7
90°	9.7	10.2	10.7	11.8	11.8	11.8	12.3	12.3
92.5°	95.3	69.2	52.0	44.1	37.2	35.9	35.2	34.3
95°	386.5	304.8	238.7	193.6	155.4	139.2	135.0	126.4
97.5°	575.7	518.4	454.0	391.2	358.0	327.8	312.3	305.4
100°	661.3	635.0	579.6	523.7	486.5	447.9	428.0	419.3
102.5°	690.1	706.3	679.8	642.0	602.3	574.8	553.2	546.7
105°	673.2	746.8	770.4	764.5	747.3	729.6	718.9	712.4
107.5°	612.5	710.8	771.6	799.6	808.3	808.2	804.6	800.3
110°	567.8	670.0	745.7	791.5	815.6	825.9	829.6	829.6



TEST NUMBER: P333312-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	532.5	629.5	706.2	760.1	795.4	812.9	822.3	826.1
115°	488.1	571.6	645.2	703.8	745.7	771.6	786.6	793.6
117.5°	459.6	531.4	594.8	648.7	690.6	717.3	732.2	736.5
120°	444.1	508.6	567.8	615.1	654.9	680.7	695.2	699.5
122.5°	432.5	492.3	545.0	589.3	624.7	648.4	662.9	666.8
125°	415.6	470.4	517.3	555.9	586.1	608.1	619.9	625.3
127.5°	398.4	449.6	493.2	529.5	556.8	576.3	587.4	589.8
130°	387.7	435.0	476.9	511.8	538.8	556.5	567.2	570.4
132.5°	376.9	421.2	459.3	492.9	519.8	537.5	547.4	551.1
135°	362.9	400.0	434.4	465.1	488.7	506.4	516.1	519.3
137.5°	351.1	381.1	409.7	435.7	456.9	473.1	481.9	485.5
140°	344.6	369.9	394.6	417.3	437.2	451.1	459.1	461.8
142.5°	339.0	360.4	381.7	401.3	418.2	430.0	437.6	439.9
145°	331.8	348.4	365.0	379.6	392.5	401.6	407.6	409.7
147.5°	324.9	338.4	351.2	362.1	372.4	379.7	383.1	384.1
150°	320.9	332.8	343.0	352.7	360.8	367.2	369.4	369.9
152.5°	316.7	327.3	336.6	344.1	350.9	356.0	358.2	358.7
155°	310.2	318.9	326.3	332.2	337.6	341.4	343.0	343.6
157.5°	303.8	310.9	316.7	321.3	325.5	328.6	330.1	330.0
160°	299.4	304.8	310.2	314.0	317.7	320.5	321.5	320.9
162.5°	294.7	299.7	304.2	307.6	310.5	312.7	312.9	312.8
165°	288.1	291.9	295.2	297.8	300.0	301.0	301.0	301.0
167.5°	281.9	284.5	286.9	288.8	289.9	290.9	290.4	290.3
170°	278.5	280.1	281.7	282.8	283.9	284.5	284.5	283.9
172.5°	274.7	276.3	277.4	278.1	278.3	279.3	278.4	277.9
175°	270.4	270.4	271.5	271.5	271.5	272.0	271.0	270.4
177.5°	267.5	268.0	268.0	268.0	267.5	268.0	266.6	266.6
180°	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6

(END OF REPORT)