

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333143-830

Luminaire Tested: **S125DIP-S375D1035U830-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333143-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S375D1035U830-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4824.7 lumens  
Efficiency: N/A  
Efficacy: 129.3 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 37.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333143-830

CATALOG NUMBER: S125DIP-S375D1035U830-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333143-830

CATALOG NUMBER: S125DIP-S375D1035U830-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38	30
1	93	89	86	82	84	80	77	74	63	61	59	48	47	45	34	33	32	26
2	85	78	72	67	76	70	65	61	56	52	49	42	40	38	30	28	27	22
3	78	69	62	56	69	62	56	51	49	45	42	37	35	32	26	25	23	18
4	71	61	53	47	64	55	48	43	44	39	35	33	30	28	24	22	20	16
5	65	54	46	40	58	49	42	37	39	34	30	30	26	24	21	19	18	14
6	60	48	41	35	54	44	37	32	35	30	26	27	23	21	19	17	15	12
7	55	43	36	30	49	39	33	28	32	27	23	24	21	18	18	15	14	11
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	14	12	10
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	15	13	11	9
10	44	33	26	21	40	30	24	19	24	19	16	19	15	13	14	12	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	3314	3314	3314	3314
5°	3837	3325	2912	3325
10°	4465	3308	2551	3308
15°	4942	3284	2353	3284
20°	5532	3245	2194	3245
25°	6481	3202	2117	3202
30°	7000	3159	2049	3159
35°	5755	3079	2006	3079
40°	4091	2967	1957	2967
45°	3143	2817	1929	2817
50°	2683	2629	1925	2629
55°	2389	2448	1942	2448
60°	2155	2248	1992	2248
65°	1991	2046	2043	2046
70°	1811	1839	2073	1839
75°	1597	1619	2054	1619
80°	1346	1320	1878	1320
85°	1067	948	1519	948



TEST NUMBER: P333143-830

CATALOG NUMBER: S125DIP-S375D1035U830-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	49.4	1.0
10°-20°	147.1	3.0
20°-30°	238.8	4.9
30°-40°	291.3	6.0
40°-50°	265.0	5.5
50°-60°	211.1	4.4
60°-70°	147.0	3.0
70°-80°	78.4	1.6
80°-90°	22.4	0.5
90°-100°	81.0	1.7
100°-110°	239.1	5.0
110°-120°	405.1	8.4
120°-130°	533.1	11.0
130°-140°	597.3	12.4
140°-150°	585.5	12.1
150°-160°	491.7	10.2
160°-170°	326.9	6.8
170°-180°	114.4	2.4
0°-30°	435.3	9.0
0°-40°	726.6	15.1
0°-60°	1202.7	24.9
0°-90°	1450.6	30.1
90°-120°	725.2	15.0
90°-150°	2441.1	50.6
90°-180°	3374.0	69.9
0°-180°	4824.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	513	513	513	513	513	
5°	592	513	449	513	592	60
15°	739	491	352	491	739	212
25°	910	449	297	449	910	415
35°	730	390	254	390	730	447
45°	344	308	211	308	344	275
55°	212	217	172	217	212	191
65°	130	134	134	134	130	129
75°	64	65	82	65	64	69
85°	14	13	20	13	14	17
90°	23	1	23	1	23	13
95°	81	61	81	61	81	82
105°	233	214	233	214	233	247
115°	409	406	409	406	409	405
125°	596	592	596	592	596	532
135°	772	770	772	770	772	596
145°	936	933	936	933	936	584
155°	1067	1067	1067	1067	1067	491
165°	1157	1160	1157	1160	1157	326
175°	1202	1206	1202	1206	1202	114
180°	1209	1209	1209	1209	1209	



TEST NUMBER: P333143-830

CATALOG NUMBER: S125DIP-S375D1035U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1
2.5°	542.7	542.1	541.3	540.0	541.0	538.0	536.7	534.2	531.2	530.2	529.0
5°	591.9	593.0	594.2	589.6	590.0	586.9	579.9	574.3	569.8	563.8	559.7
7.5°	651.2	648.7	648.4	645.5	640.4	636.2	629.0	619.6	610.6	600.3	591.8
10°	680.8	681.1	679.1	675.6	670.1	666.2	656.7	647.5	636.4	623.3	614.0
12.5°	703.1	704.1	701.5	696.8	694.2	685.4	677.9	667.0	653.8	643.4	629.1
15°	739.1	736.8	735.1	729.2	724.6	715.5	703.5	692.1	677.8	664.5	651.2
17.5°	773.9	775.9	772.6	767.2	753.0	742.3	726.3	710.8	692.9	675.0	659.2
20°	804.9	806.7	801.7	792.3	775.3	764.7	743.6	723.5	702.9	680.0	662.5
22.5°	843.7	842.3	835.5	821.2	806.5	786.8	763.9	739.5	713.6	687.8	664.6
25°	909.5	900.3	896.2	878.5	859.2	830.2	798.9	763.2	730.9	696.7	667.1
27.5°	946.0	943.1	938.5	926.2	905.9	874.9	837.9	794.4	748.9	705.8	666.9
30°	938.7	939.1	939.5	935.7	922.6	899.3	862.4	815.7	761.6	713.0	668.2
32.5°	873.8	881.7	889.4	898.3	902.0	897.5	874.5	832.2	776.6	721.4	667.5
35°	730.0	732.4	757.1	781.5	814.5	840.3	857.4	838.7	791.9	728.5	666.7
37.5°	569.2	581.0	598.0	625.6	673.4	716.1	771.2	796.4	781.4	730.8	665.2
40°	485.2	496.2	507.3	535.4	575.6	627.5	689.9	743.3	755.7	723.5	659.9
42.5°	420.5	429.0	441.4	462.5	496.2	542.1	601.8	671.6	714.4	702.3	648.9
45°	344.1	349.6	359.1	375.9	400.3	436.2	488.9	565.1	631.6	653.6	622.9
47.5°	294.5	294.5	302.0	313.5	331.1	361.7	400.7	460.3	531.3	583.8	581.4
50°	267.0	265.9	271.8	281.8	295.8	316.0	353.3	401.0	469.1	528.6	545.2
52.5°	243.3	243.5	247.0	254.5	266.2	283.4	311.2	354.3	412.5	473.5	504.7
55°	212.2	211.2	215.4	220.4	228.9	240.3	260.2	293.1	340.4	400.5	441.0
57.5°	183.5	186.0	187.6	191.1	198.1	205.8	222.6	246.8	284.3	335.8	378.6
60°	166.8	169.2	170.5	174.0	179.6	186.2	199.3	218.9	250.4	294.9	337.3
62.5°	151.8	153.7	154.2	157.3	161.9	168.2	178.5	195.0	220.0	258.8	300.4
65°	130.3	130.3	131.1	134.4	136.6	142.2	150.1	162.0	182.1	212.4	247.9
67.5°	109.4	110.5	110.3	111.7	113.7	118.1	123.7	133.6	148.5	170.5	199.0
70°	95.9	96.7	96.5	97.6	99.7	102.5	107.2	116.5	127.1	146.1	170.5
72.5°	83.6	84.0	83.4	84.8	86.1	88.6	93.8	98.8	108.7	124.7	144.8
75°	64.0	64.5	64.9	65.8	67.1	68.4	71.0	76.0	82.6	94.5	107.4
77.5°	48.0	47.1	48.3	48.1	48.8	49.9	52.1	54.8	60.1	67.8	77.7
80°	36.2	36.4	36.4	36.6	37.7	38.4	40.2	42.2	46.4	52.0	59.0
82.5°	26.4	27.0	26.6	27.1	27.9	28.4	29.5	31.1	33.5	38.0	43.0
85°	14.4	13.3	13.8	14.1	14.1	14.4	15.3	15.9	17.2	18.9	20.9
87.5°	8.7	9.0	9.0	8.9	8.9	8.8	9.2	9.0	9.3	9.6	10.0
90°	22.6	22.0	21.3	20.7	20.1	19.2	18.2	17.2	16.1	15.1	13.6
92.5°	44.4	43.9	43.5	43.1	42.6	41.7	40.2	38.9	37.5	36.1	34.3
95°	81.0	80.5	80.1	79.6	79.3	78.3	76.8	75.4	73.9	72.5	70.4
97.5°	122.7	122.4	122.2	122.0	121.7	120.9	119.5	118.1	116.8	115.4	112.4
100°	154.3	153.9	153.4	153.1	152.7	151.5	149.6	147.7	145.8	143.9	141.3
102.5°	186.0	185.4	184.7	184.2	183.6	182.3	180.2	178.1	176.2	174.1	172.7
105°	233.4	232.7	232.1	231.5	230.8	229.9	228.7	227.4	226.1	224.9	223.7
107.5°	281.9	282.0	282.0	282.0	282.1	281.8	281.2	280.5	279.9	279.3	278.3
110°	318.0	318.3	318.5	318.7	318.9	318.7	318.0	317.4	316.8	316.1	315.6



TEST NUMBER: P333143-830

CATALOG NUMBER: S125DIP-S375D1035U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	353.5	353.8	354.2	354.6	355.0	355.0	354.7	354.4	354.1	353.8	353.0
115°	409.3	409.5	409.7	409.9	410.2	410.4	410.6	410.8	411.0	411.2	410.8
117.5°	463.9	464.8	465.6	466.4	467.2	467.6	467.4	467.2	467.1	466.9	466.6
120°	501.5	502.4	503.2	504.1	504.9	505.3	505.3	505.3	505.3	505.3	505.1
122.5°	539.2	539.9	540.5	541.2	541.9	542.2	542.4	542.6	542.8	542.9	542.4
125°	595.7	595.9	596.1	596.3	596.4	596.8	597.2	597.7	598.0	598.5	598.2
127.5°	649.9	650.3	650.6	651.1	651.5	651.9	652.1	652.2	652.4	652.7	652.4
130°	686.0	686.4	686.8	687.2	687.7	688.0	688.2	688.3	688.6	688.8	688.3
132.5°	719.8	720.5	721.0	721.6	722.2	722.6	722.8	723.0	723.2	723.4	723.5
135°	772.5	773.4	774.2	775.1	775.9	776.3	776.3	776.3	776.3	776.3	776.1
137.5°	824.2	825.2	826.2	827.3	828.3	828.7	828.4	828.2	827.9	827.6	827.3
140°	857.2	858.3	859.3	860.4	861.4	861.8	861.3	860.9	860.4	860.1	859.4
142.5°	888.8	889.9	891.0	892.0	893.1	893.4	893.2	893.0	892.7	892.4	891.6
145°	936.3	936.9	937.5	938.2	938.8	939.1	939.1	939.1	939.1	939.1	938.5
147.5°	976.8	978.2	979.6	981.0	982.4	982.9	982.4	981.8	981.4	980.9	980.3
150°	1006.8	1007.3	1007.7	1008.1	1008.5	1008.7	1008.7	1008.7	1008.7	1008.7	1007.9
152.5°	1031.7	1032.5	1033.2	1034.0	1034.7	1034.8	1034.3	1033.9	1033.3	1032.8	1032.5
155°	1067.1	1068.1	1069.1	1070.3	1071.3	1071.4	1070.5	1069.7	1068.8	1068.0	1067.8
157.5°	1096.6	1098.0	1099.4	1100.8	1102.1	1102.4	1101.5	1100.7	1099.9	1099.1	1098.9
160°	1116.9	1118.0	1119.1	1120.1	1121.2	1121.2	1120.4	1119.6	1118.7	1117.9	1117.7
162.5°	1134.3	1135.5	1136.7	1137.9	1139.2	1139.3	1138.2	1137.2	1136.2	1135.2	1135.2
165°	1157.4	1158.7	1159.9	1161.2	1162.4	1162.6	1161.8	1160.9	1160.2	1159.3	1159.0
167.5°	1175.8	1177.1	1178.5	1179.8	1181.0	1181.1	1179.8	1178.6	1177.3	1176.0	1176.0
170°	1185.6	1187.1	1188.5	1190.1	1191.5	1191.6	1190.3	1189.1	1187.9	1186.6	1186.6
172.5°	1193.9	1195.2	1196.6	1197.8	1199.1	1199.1	1197.9	1196.7	1195.3	1194.1	1194.1
175°	1201.6	1203.1	1204.6	1206.1	1207.5	1207.6	1206.4	1205.1	1203.8	1202.6	1202.6
177.5°	1206.2	1207.3	1208.5	1209.7	1210.9	1210.9	1209.9	1208.9	1208.0	1206.9	1207.1
180°	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2



TEST NUMBER: P333143-830

CATALOG NUMBER: S125DIP-S375D1035U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1
2.5°	527.9	526.7	525.3	522.8	519.9	518.3	515.9	514.3	511.2	508.6	505.8
5°	554.7	549.0	543.8	537.1	529.7	524.9	519.2	512.9	506.3	499.6	492.2
7.5°	582.5	572.4	561.6	549.9	538.4	527.8	517.7	507.9	498.7	487.5	478.1
10°	601.1	588.4	575.0	559.1	543.6	530.1	516.4	504.4	492.2	479.2	467.6
12.5°	619.7	602.9	583.8	566.4	547.8	531.5	515.4	500.0	484.7	470.2	456.8
15°	632.9	618.1	600.5	575.6	554.7	532.3	511.0	491.2	472.6	456.5	439.5
17.5°	641.6	622.5	603.5	579.8	552.3	527.3	503.0	480.3	459.5	439.0	422.7
20°	643.1	623.5	603.7	580.4	552.3	523.6	499.4	472.2	449.8	428.6	408.6
22.5°	642.6	620.4	598.8	574.9	547.4	520.9	491.7	464.0	439.6	418.9	397.9
25°	637.7	614.0	586.9	562.8	535.7	507.7	478.1	449.3	424.5	400.8	380.0
27.5°	633.6	602.9	572.2	544.0	517.9	492.2	463.8	434.4	406.9	382.9	363.4
30°	628.6	594.7	560.3	530.9	504.2	479.2	452.3	423.6	394.8	371.4	350.4
32.5°	624.1	584.7	548.4	516.3	488.0	463.6	438.9	411.6	383.3	359.5	338.6
35°	615.3	569.8	528.1	492.0	461.8	436.7	415.9	390.5	364.6	341.5	321.5
37.5°	604.2	550.2	505.5	467.6	434.4	408.0	388.8	369.2	344.3	322.1	304.0
40°	595.4	536.2	488.9	450.2	415.8	388.3	370.4	351.9	331.3	310.6	291.4
42.5°	584.5	523.7	472.2	430.5	396.4	369.7	350.9	335.3	317.0	297.7	279.9
45°	564.3	501.0	445.2	400.3	365.9	339.5	320.2	308.4	294.6	276.4	261.4
47.5°	534.6	473.6	415.9	369.7	334.1	309.7	291.5	280.2	270.6	257.0	243.4
50°	508.3	453.3	394.8	348.9	313.4	288.8	272.0	261.7	253.5	243.1	231.5
52.5°	478.9	427.6	374.1	328.7	293.5	269.3	252.9	243.8	237.0	229.5	218.1
55°	432.1	388.5	338.8	295.8	263.3	239.6	225.2	217.4	211.7	206.0	199.1
57.5°	380.6	346.5	302.6	263.1	233.2	211.6	198.2	190.6	186.2	183.2	179.2
60°	344.3	315.2	277.3	241.3	212.2	192.9	179.9	174.0	170.3	168.0	164.9
62.5°	310.7	286.7	251.7	218.9	193.3	175.2	163.5	157.8	154.3	153.1	150.6
65°	261.2	242.6	213.7	186.4	164.7	149.2	139.4	133.9	131.8	130.4	130.6
67.5°	212.3	201.0	177.8	154.6	137.1	124.2	116.3	112.2	111.0	109.3	109.3
70°	182.5	174.0	154.4	134.1	118.7	108.7	101.7	97.4	96.2	95.4	95.2
72.5°	156.2	148.7	131.8	115.6	101.6	92.8	87.1	84.5	82.7	82.2	82.1
75°	117.3	113.3	99.7	86.9	77.3	71.3	67.3	64.9	63.6	63.3	63.6
77.5°	83.4	79.8	71.3	62.1	56.1	51.5	48.2	47.3	45.9	45.9	45.7
80°	62.7	60.3	54.9	47.7	42.7	38.7	37.0	35.5	35.1	34.4	35.1
82.5°	45.4	42.9	39.2	34.6	30.4	28.2	26.4	25.9	25.6	25.4	25.4
85°	22.4	22.6	20.5	17.0	15.3	13.9	12.8	12.8	12.6	12.4	12.6
87.5°	10.1	9.4	8.5	7.6	6.4	5.6	5.1	4.9	4.7	4.9	5.4
90°	12.2	10.7	9.2	7.6	5.9	4.2	2.6	0.9	2.6	4.2	5.9
92.5°	32.5	30.7	28.9	27.4	26.3	25.1	23.9	22.8	23.9	25.1	26.3
95°	68.2	66.2	64.1	62.9	62.4	62.0	61.5	61.2	61.5	62.0	62.4
97.5°	109.6	106.7	103.9	102.3	102.2	102.0	101.8	101.6	101.8	102.0	102.2
100°	138.6	135.8	133.1	131.8	131.8	131.8	131.8	131.8	131.8	131.8	131.8
102.5°	171.4	169.9	168.5	167.5	166.6	165.8	164.9	164.1	164.9	165.8	166.6
105°	222.3	221.1	219.9	218.8	217.7	216.6	215.6	214.5	215.6	216.6	217.7
107.5°	277.4	276.4	275.4	274.5	273.4	272.3	271.3	270.2	271.3	272.3	273.4
110°	314.9	314.2	313.7	312.8	311.8	310.8	309.7	308.7	309.7	310.8	311.8





TEST NUMBER: P333143-830

CATALOG NUMBER: S125DIP-S375D1035U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	352.2	351.5	350.6	350.0	349.4	348.8	348.4	347.8	348.4	348.8	349.4
115°	410.4	409.9	409.5	408.9	408.1	407.3	406.4	405.6	406.4	407.3	408.1
117.5°	466.2	465.8	465.4	465.1	464.7	464.3	463.9	463.5	463.9	464.3	464.7
120°	504.9	504.6	504.4	503.9	502.8	501.7	500.7	499.6	500.7	501.7	502.8
122.5°	541.9	541.3	540.7	540.4	540.0	539.6	539.2	538.9	539.2	539.6	540.0
125°	598.0	597.9	597.7	596.9	595.7	594.4	593.1	591.9	593.1	594.4	595.7
127.5°	652.1	652.0	651.7	651.2	650.4	649.8	649.0	648.4	649.0	649.8	650.4
130°	688.0	687.6	687.1	686.4	685.3	684.3	683.2	682.2	683.2	684.3	685.3
132.5°	723.6	723.7	723.8	722.9	721.2	719.5	717.8	716.0	717.8	719.5	721.2
135°	775.9	775.7	775.5	774.8	773.5	772.2	771.0	769.8	771.0	772.2	773.5
137.5°	826.8	826.3	825.9	825.0	823.8	822.6	821.3	820.2	821.3	822.6	823.8
140°	858.8	858.2	857.5	856.7	855.6	854.6	853.6	852.5	853.6	854.6	855.6
142.5°	890.9	890.0	889.3	888.4	887.5	886.6	885.8	884.9	885.8	886.6	887.5
145°	937.8	937.3	936.6	935.9	935.0	934.2	933.4	932.6	933.4	934.2	935.0
147.5°	979.9	979.4	978.9	978.4	978.0	977.5	977.0	976.6	977.0	977.5	978.0
150°	1007.1	1006.3	1005.4	1005.1	1005.3	1005.5	1005.7	1005.9	1005.7	1005.5	1005.3
152.5°	1032.2	1031.8	1031.5	1031.1	1030.9	1030.6	1030.3	1030.0	1030.3	1030.6	1030.9
155°	1067.6	1067.4	1067.1	1067.1	1067.1	1067.1	1067.1	1067.1	1067.1	1067.1	1067.1
157.5°	1098.6	1098.4	1098.3	1098.3	1098.8	1099.3	1099.8	1100.2	1099.8	1099.3	1098.8
160°	1117.5	1117.3	1117.1	1117.3	1117.9	1118.5	1119.2	1119.7	1119.2	1118.5	1117.9
162.5°	1135.1	1135.1	1135.0	1135.3	1135.7	1136.1	1136.6	1137.1	1136.6	1136.1	1135.7
165°	1158.9	1158.7	1158.5	1158.6	1159.0	1159.4	1159.8	1160.3	1159.8	1159.4	1159.0
167.5°	1176.0	1176.0	1176.0	1176.5	1177.3	1178.2	1178.9	1179.8	1178.9	1178.2	1177.3
170°	1186.6	1186.6	1186.6	1187.0	1187.9	1188.6	1189.5	1190.3	1189.5	1188.6	1187.9
172.5°	1194.1	1194.1	1194.1	1194.6	1195.3	1196.2	1197.0	1197.9	1197.0	1196.2	1195.3
175°	1202.6	1202.6	1202.6	1203.0	1203.8	1204.7	1205.5	1206.4	1205.5	1204.7	1203.8
177.5°	1207.2	1207.4	1207.6	1208.0	1208.6	1209.4	1210.0	1210.7	1210.0	1209.4	1208.6
180°	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2



TEST NUMBER: P333143-830

CATALOG NUMBER: S125DIP-S375D1035U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1
2.5°	504.3	502.3	500.8	497.3	495.3	492.8	490.7	492.9	490.5	491.5	489.9
5°	488.5	482.4	478.1	471.7	466.3	461.3	457.6	456.9	455.2	454.3	451.7
7.5°	469.6	461.9	454.5	446.2	439.2	432.2	427.6	423.9	421.4	418.1	415.8
10°	458.5	448.2	439.5	429.5	420.8	413.1	407.1	404.0	401.1	397.0	395.5
12.5°	444.7	434.1	423.5	412.7	404.4	395.9	390.7	386.1	384.1	379.5	379.0
15°	428.2	412.3	401.8	391.0	379.4	372.4	368.1	363.1	360.9	357.6	355.2
17.5°	408.5	394.3	381.3	369.9	360.1	354.2	348.7	345.3	341.6	339.4	335.5
20°	394.2	380.7	367.6	355.6	348.0	341.3	337.0	333.7	329.7	328.7	324.7
22.5°	382.2	367.3	354.8	344.7	336.4	328.8	324.0	321.8	319.1	315.8	315.0
25°	362.6	347.1	336.5	326.5	319.1	312.1	308.9	306.0	303.4	301.0	300.1
27.5°	345.7	331.9	319.2	310.2	303.7	297.4	294.5	291.1	289.2	287.2	284.8
30°	333.8	319.7	308.6	299.9	292.9	287.3	284.2	281.8	280.1	278.3	277.0
32.5°	321.7	308.6	297.8	289.3	282.3	278.1	275.3	273.6	271.7	269.7	268.0
35°	305.6	291.2	280.7	273.3	267.9	264.6	261.6	260.0	257.9	257.9	256.1
37.5°	287.4	274.9	265.7	259.0	254.1	251.2	247.9	246.9	245.4	244.5	243.9
40°	276.6	265.0	256.4	249.6	244.4	242.0	239.3	237.6	236.8	235.6	235.3
42.5°	265.4	254.4	246.1	239.9	235.3	233.3	230.8	229.6	227.8	226.4	226.1
45°	248.5	237.8	230.2	225.2	221.3	218.9	217.4	214.7	213.9	212.2	211.9
47.5°	232.4	222.2	214.7	210.6	207.2	205.2	202.8	200.2	199.2	198.3	198.2
50°	220.4	211.0	204.1	200.2	196.9	194.1	191.6	189.9	189.3	189.3	189.7
52.5°	208.2	200.2	194.4	189.5	186.4	183.4	181.2	180.1	179.2	180.2	181.0
55°	190.4	182.3	178.0	173.3	170.3	166.8	165.7	165.3	164.7	166.4	167.3
57.5°	171.4	165.8	160.7	156.2	153.4	151.4	150.0	149.7	150.9	151.7	154.6
60°	159.4	152.9	148.4	144.9	141.6	140.3	139.8	139.4	140.3	142.6	146.4
62.5°	146.2	140.9	135.9	133.4	130.9	128.8	128.7	128.9	130.6	133.5	137.1
65°	126.8	122.2	118.9	115.8	113.9	112.6	113.0	113.9	115.8	119.6	123.7
67.5°	107.0	103.9	100.9	98.5	96.6	96.6	97.1	98.4	100.7	104.9	108.7
70°	94.3	90.9	88.4	87.4	85.8	84.9	86.2	88.4	90.4	94.3	97.6
72.5°	81.6	78.6	76.7	76.0	75.3	74.6	75.1	77.5	80.1	84.0	87.8
75°	62.7	61.6	60.3	59.5	58.8	59.3	59.7	61.8	64.0	68.1	72.5
77.5°	45.8	44.7	43.8	43.6	43.3	43.5	44.8	46.4	48.4	51.5	54.8
80°	34.6	34.2	33.7	33.6	33.6	33.7	35.5	36.6	38.5	41.4	44.0
82.5°	25.3	25.0	24.9	24.8	25.0	25.1	26.1	27.5	29.1	31.3	33.6
85°	13.3	12.8	13.5	13.8	13.3	13.9	14.4	15.3	15.9	17.0	18.1
87.5°	5.8	6.5	6.7	7.2	7.4	8.1	8.1	9.0	9.5	10.1	10.1
90°	7.6	9.2	10.7	12.2	13.6	15.1	16.1	17.2	18.2	19.2	20.1
92.5°	27.4	28.9	30.7	32.5	34.3	36.1	37.5	38.9	40.2	41.7	42.6
95°	62.9	64.1	66.2	68.2	70.4	72.5	73.9	75.4	76.8	78.3	79.3
97.5°	102.3	103.9	106.7	109.6	112.4	115.4	116.8	118.1	119.5	120.9	121.7
100°	131.8	133.1	135.8	138.6	141.3	143.9	145.8	147.7	149.6	151.5	152.7
102.5°	167.5	168.5	169.9	171.4	172.7	174.1	176.2	178.1	180.2	182.3	183.6
105°	218.8	219.9	221.1	222.3	223.7	224.9	226.1	227.4	228.7	229.9	230.8
107.5°	274.5	275.4	276.4	277.4	278.3	279.3	279.9	280.5	281.2	281.8	282.1
110°	312.8	313.7	314.2	314.9	315.6	316.1	316.8	317.4	318.0	318.7	318.9



TEST NUMBER: P333143-830

CATALOG NUMBER: S125DIP-S375D1035U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	350.0	350.6	351.5	352.2	353.0	353.8	354.1	354.4	354.7	355.0	355.0
115°	408.9	409.5	409.9	410.4	410.8	411.2	411.0	410.8	410.6	410.4	410.2
117.5°	465.1	465.4	465.8	466.2	466.6	466.9	467.1	467.2	467.4	467.6	467.2
120°	503.9	504.4	504.6	504.9	505.1	505.3	505.3	505.3	505.3	505.3	504.9
122.5°	540.4	540.7	541.3	541.9	542.4	542.9	542.8	542.6	542.4	542.2	541.9
125°	596.9	597.7	597.9	598.0	598.2	598.5	598.0	597.7	597.2	596.8	596.4
127.5°	651.2	651.7	652.0	652.1	652.4	652.7	652.4	652.2	652.1	651.9	651.5
130°	686.4	687.1	687.6	688.0	688.3	688.8	688.6	688.3	688.2	688.0	687.7
132.5°	722.9	723.8	723.7	723.6	723.5	723.4	723.2	723.0	722.8	722.6	722.2
135°	774.8	775.5	775.7	775.9	776.1	776.3	776.3	776.3	776.3	776.3	775.9
137.5°	825.0	825.9	826.3	826.8	827.3	827.6	827.9	828.2	828.4	828.7	828.3
140°	856.7	857.5	858.2	858.8	859.4	860.1	860.4	860.9	861.3	861.8	861.4
142.5°	888.4	889.3	890.0	890.9	891.6	892.4	892.7	893.0	893.2	893.4	893.1
145°	935.9	936.6	937.3	937.8	938.5	939.1	939.1	939.1	939.1	939.1	938.8
147.5°	978.4	978.9	979.4	979.9	980.3	980.9	981.4	981.8	982.4	982.9	982.4
150°	1005.1	1005.4	1006.3	1007.1	1007.9	1008.7	1008.7	1008.7	1008.7	1008.7	1008.5
152.5°	1031.1	1031.5	1031.8	1032.2	1032.5	1032.8	1033.3	1033.9	1034.3	1034.8	1034.7
155°	1067.1	1067.1	1067.4	1067.6	1067.8	1068.0	1068.8	1069.7	1070.5	1071.4	1071.3
157.5°	1098.3	1098.3	1098.4	1098.6	1098.9	1099.1	1099.9	1100.7	1101.5	1102.4	1102.1
160°	1117.3	1117.1	1117.3	1117.5	1117.7	1117.9	1118.7	1119.6	1120.4	1121.2	1121.2
162.5°	1135.3	1135.0	1135.1	1135.1	1135.2	1135.2	1136.2	1137.2	1138.2	1139.3	1139.2
165°	1158.6	1158.5	1158.7	1158.9	1159.0	1159.3	1160.2	1160.9	1161.8	1162.6	1162.4
167.5°	1176.5	1176.0	1176.0	1176.0	1176.0	1176.0	1177.3	1178.6	1179.8	1181.1	1181.0
170°	1187.0	1186.6	1186.6	1186.6	1186.6	1186.6	1187.9	1189.1	1190.3	1191.6	1191.5
172.5°	1194.6	1194.1	1194.1	1194.1	1194.1	1194.1	1195.3	1196.7	1197.9	1199.1	1199.1
175°	1203.0	1202.6	1202.6	1202.6	1202.6	1202.6	1203.8	1205.1	1206.4	1207.6	1207.5
177.5°	1208.0	1207.6	1207.4	1207.2	1207.1	1206.9	1208.0	1208.9	1209.9	1210.9	1210.9
180°	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2



TEST NUMBER: P333143-830

CATALOG NUMBER: S125DIP-S375D1035U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1
2.5°	488.9	490.1	489.1	490.5	489.1	490.1	488.9	489.9	491.5	490.5	492.9
5°	450.6	448.7	450.0	449.1	450.0	448.7	450.6	451.7	454.3	455.2	456.9
7.5°	415.3	413.4	411.2	410.2	411.2	413.4	415.3	415.8	418.1	421.4	423.9
10°	393.1	390.7	390.5	389.0	390.5	390.7	393.1	395.5	397.0	401.1	404.0
12.5°	376.9	374.7	372.2	371.6	372.2	374.7	376.9	379.0	379.5	384.1	386.1
15°	353.9	352.1	350.6	351.9	350.6	352.1	353.9	355.2	357.6	360.9	363.1
17.5°	334.8	333.4	333.1	331.5	333.1	333.4	334.8	335.5	339.4	341.6	345.3
20°	322.7	321.7	322.2	319.2	322.2	321.7	322.7	324.7	328.7	329.7	333.7
22.5°	313.2	311.0	310.8	310.2	310.8	311.0	313.2	315.0	315.8	319.1	321.8
25°	298.1	297.1	296.0	297.1	296.0	297.1	298.1	300.1	301.0	303.4	306.0
27.5°	285.0	283.7	283.4	283.6	283.4	283.7	285.0	284.8	287.2	289.2	291.1
30°	277.0	274.8	275.0	274.8	275.0	274.8	277.0	277.0	278.3	280.1	281.8
32.5°	268.3	266.8	266.6	266.2	266.6	266.8	268.3	268.0	269.7	271.7	273.6
35°	255.4	255.4	254.4	254.4	254.4	255.4	255.4	256.1	257.9	257.9	260.0
37.5°	243.4	243.2	242.5	242.6	242.5	243.2	243.4	243.9	244.5	245.4	246.9
40°	234.3	234.1	233.5	232.1	233.5	234.1	234.3	235.3	235.6	236.8	237.6
42.5°	225.6	224.9	224.6	224.1	224.6	224.9	225.6	226.1	226.4	227.8	229.6
45°	211.9	211.9	211.5	211.2	211.5	211.9	211.9	211.9	212.2	213.9	214.7
47.5°	198.6	199.0	199.8	199.6	199.8	199.0	198.6	198.2	198.3	199.2	200.2
50°	190.6	190.8	191.4	191.6	191.4	190.8	190.6	189.7	189.3	189.3	189.9
52.5°	181.7	182.9	183.8	183.6	183.8	182.9	181.7	181.0	180.2	179.2	180.1
55°	169.2	170.8	172.3	172.5	172.3	170.8	169.2	167.3	166.4	164.7	165.3
57.5°	156.9	159.0	160.6	161.2	160.6	159.0	156.9	154.6	151.7	150.9	149.7
60°	148.5	151.4	153.4	154.2	153.4	151.4	148.5	146.4	142.6	140.3	139.4
62.5°	140.5	143.7	145.6	145.8	145.6	143.7	140.5	137.1	133.5	130.6	128.9
65°	127.4	130.6	132.4	133.7	132.4	130.6	127.4	123.7	119.6	115.8	113.9
67.5°	113.3	116.6	118.5	119.5	118.5	116.6	113.3	108.7	104.9	100.7	98.4
70°	103.0	106.3	108.9	109.8	108.9	106.3	103.0	97.6	94.3	90.4	88.4
72.5°	92.9	95.9	97.9	99.0	97.9	95.9	92.9	87.8	84.0	80.1	77.5
75°	75.3	79.3	81.2	82.3	81.2	79.3	75.3	72.5	68.1	64.0	61.8
77.5°	58.1	61.6	62.9	63.4	62.9	61.6	58.1	54.8	51.5	48.4	46.4
80°	46.6	48.8	50.3	50.5	50.3	48.8	46.6	44.0	41.4	38.5	36.6
82.5°	35.8	37.6	38.1	38.6	38.1	37.6	35.8	33.6	31.3	29.1	27.5
85°	19.6	20.5	20.7	20.5	20.7	20.5	19.6	18.1	17.0	15.9	15.3
87.5°	10.6	10.6	10.7	11.1	10.7	10.6	10.6	10.1	10.1	9.5	9.0
90°	20.7	21.3	22.0	22.6	22.0	21.3	20.7	20.1	19.2	18.2	17.2
92.5°	43.1	43.5	43.9	44.4	43.9	43.5	43.1	42.6	41.7	40.2	38.9
95°	79.6	80.1	80.5	81.0	80.5	80.1	79.6	79.3	78.3	76.8	75.4
97.5°	122.0	122.2	122.4	122.7	122.4	122.2	122.0	121.7	120.9	119.5	118.1
100°	153.1	153.4	153.9	154.3	153.9	153.4	153.1	152.7	151.5	149.6	147.7
102.5°	184.2	184.7	185.4	186.0	185.4	184.7	184.2	183.6	182.3	180.2	178.1
105°	231.5	232.1	232.7	233.4	232.7	232.1	231.5	230.8	229.9	228.7	227.4
107.5°	282.0	282.0	282.0	281.9	282.0	282.0	282.0	282.1	281.8	281.2	280.5
110°	318.7	318.5	318.3	318.0	318.3	318.5	318.7	318.9	318.7	318.0	317.4



TEST NUMBER: P333143-830

CATALOG NUMBER: S125DIP-S375D1035U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	354.6	354.2	353.8	353.5	353.8	354.2	354.6	355.0	355.0	354.7	354.4
115°	409.9	409.7	409.5	409.3	409.5	409.7	409.9	410.2	410.4	410.6	410.8
117.5°	466.4	465.6	464.8	463.9	464.8	465.6	466.4	467.2	467.6	467.4	467.2
120°	504.1	503.2	502.4	501.5	502.4	503.2	504.1	504.9	505.3	505.3	505.3
122.5°	541.2	540.5	539.9	539.2	539.9	540.5	541.2	541.9	542.2	542.4	542.6
125°	596.3	596.1	595.9	595.7	595.9	596.1	596.3	596.4	596.8	597.2	597.7
127.5°	651.1	650.6	650.3	649.9	650.3	650.6	651.1	651.5	651.9	652.1	652.2
130°	687.2	686.8	686.4	686.0	686.4	686.8	687.2	687.7	688.0	688.2	688.3
132.5°	721.6	721.0	720.5	719.8	720.5	721.0	721.6	722.2	722.6	722.8	723.0
135°	775.1	774.2	773.4	772.5	773.4	774.2	775.1	775.9	776.3	776.3	776.3
137.5°	827.3	826.2	825.2	824.2	825.2	826.2	827.3	828.3	828.7	828.4	828.2
140°	860.4	859.3	858.3	857.2	858.3	859.3	860.4	861.4	861.8	861.3	860.9
142.5°	892.0	891.0	889.9	888.8	889.9	891.0	892.0	893.1	893.4	893.2	893.0
145°	938.2	937.5	936.9	936.3	936.9	937.5	938.2	938.8	939.1	939.1	939.1
147.5°	981.0	979.6	978.2	976.8	978.2	979.6	981.0	982.4	982.9	982.4	981.8
150°	1008.1	1007.7	1007.3	1006.8	1007.3	1007.7	1008.1	1008.5	1008.7	1008.7	1008.7
152.5°	1034.0	1033.2	1032.5	1031.7	1032.5	1033.2	1034.0	1034.7	1034.8	1034.3	1033.9
155°	1070.3	1069.1	1068.1	1067.1	1068.1	1069.1	1070.3	1071.3	1071.4	1070.5	1069.7
157.5°	1100.8	1099.4	1098.0	1096.6	1098.0	1099.4	1100.8	1102.1	1102.4	1101.5	1100.7
160°	1120.1	1119.1	1118.0	1116.9	1118.0	1119.1	1120.1	1121.2	1121.2	1120.4	1119.6
162.5°	1137.9	1136.7	1135.5	1134.3	1135.5	1136.7	1137.9	1139.2	1139.3	1138.2	1137.2
165°	1161.2	1159.9	1158.7	1157.4	1158.7	1159.9	1161.2	1162.4	1162.6	1161.8	1160.9
167.5°	1179.8	1178.5	1177.1	1175.8	1177.1	1178.5	1179.8	1181.0	1181.1	1179.8	1178.6
170°	1190.1	1188.5	1187.1	1185.6	1187.1	1188.5	1190.1	1191.5	1191.6	1190.3	1189.1
172.5°	1197.8	1196.6	1195.2	1193.9	1195.2	1196.6	1197.8	1199.1	1199.1	1197.9	1196.7
175°	1206.1	1204.6	1203.1	1201.6	1203.1	1204.6	1206.1	1207.5	1207.6	1206.4	1205.1
177.5°	1209.7	1208.5	1207.3	1206.2	1207.3	1208.5	1209.7	1210.9	1210.9	1209.9	1208.9
180°	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2



TEST NUMBER: P333143-830

CATALOG NUMBER: S125DIP-S375D1035U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1
2.5°	490.7	492.8	495.3	497.3	500.8	502.3	504.3	505.8	508.6	511.2	514.3
5°	457.6	461.3	466.3	471.7	478.1	482.4	488.5	492.2	499.6	506.3	512.9
7.5°	427.6	432.2	439.2	446.2	454.5	461.9	469.6	478.1	487.5	498.7	507.9
10°	407.1	413.1	420.8	429.5	439.5	448.2	458.5	467.6	479.2	492.2	504.4
12.5°	390.7	395.9	404.4	412.7	423.5	434.1	444.7	456.8	470.2	484.7	500.0
15°	368.1	372.4	379.4	391.0	401.8	412.3	428.2	439.5	456.5	472.6	491.2
17.5°	348.7	354.2	360.1	369.9	381.3	394.3	408.5	422.7	439.0	459.5	480.3
20°	337.0	341.3	348.0	355.6	367.6	380.7	394.2	408.6	428.6	449.8	472.2
22.5°	324.0	328.8	336.4	344.7	354.8	367.3	382.2	397.9	418.9	439.6	464.0
25°	308.9	312.1	319.1	326.5	336.5	347.1	362.6	380.0	400.8	424.5	449.3
27.5°	294.5	297.4	303.7	310.2	319.2	331.9	345.7	363.4	382.9	406.9	434.4
30°	284.2	287.3	292.9	299.9	308.6	319.7	333.8	350.4	371.4	394.8	423.6
32.5°	275.3	278.1	282.3	289.3	297.8	308.6	321.7	338.6	359.5	383.3	411.6
35°	261.6	264.6	267.9	273.3	280.7	291.2	305.6	321.5	341.5	364.6	390.5
37.5°	247.9	251.2	254.1	259.0	265.7	274.9	287.4	304.0	322.1	344.3	369.2
40°	239.3	242.0	244.4	249.6	256.4	265.0	276.6	291.4	310.6	331.3	351.9
42.5°	230.8	233.3	235.3	239.9	246.1	254.4	265.4	279.9	297.7	317.0	335.3
45°	217.4	218.9	221.3	225.2	230.2	237.8	248.5	261.4	276.4	294.6	308.4
47.5°	202.8	205.2	207.2	210.6	214.7	222.2	232.4	243.4	257.0	270.6	280.2
50°	191.6	194.1	196.9	200.2	204.1	211.0	220.4	231.5	243.1	253.5	261.7
52.5°	181.2	183.4	186.4	189.5	194.4	200.2	208.2	218.1	229.5	237.0	243.8
55°	165.7	166.8	170.3	173.3	178.0	182.3	190.4	199.1	206.0	211.7	217.4
57.5°	150.0	151.4	153.4	156.2	160.7	165.8	171.4	179.2	183.2	186.2	190.6
60°	139.8	140.3	141.6	144.9	148.4	152.9	159.4	164.9	168.0	170.3	174.0
62.5°	128.7	128.8	130.9	133.4	135.9	140.9	146.2	150.6	153.1	154.3	157.8
65°	113.0	112.6	113.9	115.8	118.9	122.2	126.8	130.6	130.4	131.8	133.9
67.5°	97.1	96.6	96.6	98.5	100.9	103.9	107.0	109.3	109.3	111.0	112.2
70°	86.2	84.9	85.8	87.4	88.4	90.9	94.3	95.2	95.4	96.2	97.4
72.5°	75.1	74.6	75.3	76.0	76.7	78.6	81.6	82.1	82.2	82.7	84.5
75°	59.7	59.3	58.8	59.5	60.3	61.6	62.7	63.6	63.3	63.6	64.9
77.5°	44.8	43.5	43.3	43.6	43.8	44.7	45.8	45.7	45.9	45.9	47.3
80°	35.5	33.7	33.6	33.6	33.7	34.2	34.6	35.1	34.4	35.1	35.5
82.5°	26.1	25.1	25.0	24.8	24.9	25.0	25.3	25.4	25.4	25.6	25.9
85°	14.4	13.9	13.3	13.8	13.5	12.8	13.3	12.6	12.4	12.6	12.8
87.5°	8.1	8.1	7.4	7.2	6.7	6.5	5.8	5.4	4.9	4.7	4.9
90°	16.1	15.1	13.6	12.2	10.7	9.2	7.6	5.9	4.2	2.6	0.9
92.5°	37.5	36.1	34.3	32.5	30.7	28.9	27.4	26.3	25.1	23.9	22.8
95°	73.9	72.5	70.4	68.2	66.2	64.1	62.9	62.4	62.0	61.5	61.2
97.5°	116.8	115.4	112.4	109.6	106.7	103.9	102.3	102.2	102.0	101.8	101.6
100°	145.8	143.9	141.3	138.6	135.8	133.1	131.8	131.8	131.8	131.8	131.8
102.5°	176.2	174.1	172.7	171.4	169.9	168.5	167.5	166.6	165.8	164.9	164.1
105°	226.1	224.9	223.7	222.3	221.1	219.9	218.8	217.7	216.6	215.6	214.5
107.5°	279.9	279.3	278.3	277.4	276.4	275.4	274.5	273.4	272.3	271.3	270.2
110°	316.8	316.1	315.6	314.9	314.2	313.7	312.8	311.8	310.8	309.7	308.7



TEST NUMBER: P333143-830

CATALOG NUMBER: S125DIP-S375D1035U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	354.1	353.8	353.0	352.2	351.5	350.6	350.0	349.4	348.8	348.4	347.8
115°	411.0	411.2	410.8	410.4	409.9	409.5	408.9	408.1	407.3	406.4	405.6
117.5°	467.1	466.9	466.6	466.2	465.8	465.4	465.1	464.7	464.3	463.9	463.5
120°	505.3	505.3	505.1	504.9	504.6	504.4	503.9	502.8	501.7	500.7	499.6
122.5°	542.8	542.9	542.4	541.9	541.3	540.7	540.4	540.0	539.6	539.2	538.9
125°	598.0	598.5	598.2	598.0	597.9	597.7	596.9	595.7	594.4	593.1	591.9
127.5°	652.4	652.7	652.4	652.1	652.0	651.7	651.2	650.4	649.8	649.0	648.4
130°	688.6	688.8	688.3	688.0	687.6	687.1	686.4	685.3	684.3	683.2	682.2
132.5°	723.2	723.4	723.5	723.6	723.7	723.8	722.9	721.2	719.5	717.8	716.0
135°	776.3	776.3	776.1	775.9	775.7	775.5	774.8	773.5	772.2	771.0	769.8
137.5°	827.9	827.6	827.3	826.8	826.3	825.9	825.0	823.8	822.6	821.3	820.2
140°	860.4	860.1	859.4	858.8	858.2	857.5	856.7	855.6	854.6	853.6	852.5
142.5°	892.7	892.4	891.6	890.9	890.0	889.3	888.4	887.5	886.6	885.8	884.9
145°	939.1	939.1	938.5	937.8	937.3	936.6	935.9	935.0	934.2	933.4	932.6
147.5°	981.4	980.9	980.3	979.9	979.4	978.9	978.4	978.0	977.5	977.0	976.6
150°	1008.7	1008.7	1007.9	1007.1	1006.3	1005.4	1005.1	1005.3	1005.5	1005.7	1005.9
152.5°	1033.3	1032.8	1032.5	1032.2	1031.8	1031.5	1031.1	1030.9	1030.6	1030.3	1030.0
155°	1068.8	1068.0	1067.8	1067.6	1067.4	1067.1	1067.1	1067.1	1067.1	1067.1	1067.1
157.5°	1099.9	1099.1	1098.9	1098.6	1098.4	1098.3	1098.3	1098.8	1099.3	1099.8	1100.2
160°	1118.7	1117.9	1117.7	1117.5	1117.3	1117.1	1117.3	1117.9	1118.5	1119.2	1119.7
162.5°	1136.2	1135.2	1135.2	1135.1	1135.1	1135.0	1135.3	1135.7	1136.1	1136.6	1137.1
165°	1160.2	1159.3	1159.0	1158.9	1158.7	1158.5	1158.6	1159.0	1159.4	1159.8	1160.3
167.5°	1177.3	1176.0	1176.0	1176.0	1176.0	1176.0	1176.5	1177.3	1178.2	1178.9	1179.8
170°	1187.9	1186.6	1186.6	1186.6	1186.6	1186.6	1187.0	1187.9	1188.6	1189.5	1190.3
172.5°	1195.3	1194.1	1194.1	1194.1	1194.1	1194.1	1194.6	1195.3	1196.2	1197.0	1197.9
175°	1203.8	1202.6	1202.6	1202.6	1202.6	1202.6	1203.0	1203.8	1204.7	1205.5	1206.4
177.5°	1208.0	1206.9	1207.1	1207.2	1207.4	1207.6	1208.0	1208.6	1209.4	1210.0	1210.7
180°	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2



TEST NUMBER: P333143-830

CATALOG NUMBER: S125DIP-S375D1035U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1
2.5°	515.9	518.3	519.9	522.8	525.3	526.7	527.9	529.0	530.2	531.2	534.2
5°	519.2	524.9	529.7	537.1	543.8	549.0	554.7	559.7	563.8	569.8	574.3
7.5°	517.7	527.8	538.4	549.9	561.6	572.4	582.5	591.8	600.3	610.6	619.6
10°	516.4	530.1	543.6	559.1	575.0	588.4	601.1	614.0	623.3	636.4	647.5
12.5°	515.4	531.5	547.8	566.4	583.8	602.9	619.7	629.1	643.4	653.8	667.0
15°	511.0	532.3	554.7	575.6	600.5	618.1	632.9	651.2	664.5	677.8	692.1
17.5°	503.0	527.3	552.3	579.8	603.5	622.5	641.6	659.2	675.0	692.9	710.8
20°	499.4	523.6	552.3	580.4	603.7	623.5	643.1	662.5	680.0	702.9	723.5
22.5°	491.7	520.9	547.4	574.9	598.8	620.4	642.6	664.6	687.8	713.6	739.5
25°	478.1	507.7	535.7	562.8	586.9	614.0	637.7	667.1	696.7	730.9	763.2
27.5°	463.8	492.2	517.9	544.0	572.2	602.9	633.6	666.9	705.8	748.9	794.4
30°	452.3	479.2	504.2	530.9	560.3	594.7	628.6	668.2	713.0	761.6	815.7
32.5°	438.9	463.6	488.0	516.3	548.4	584.7	624.1	667.5	721.4	776.6	832.2
35°	415.9	436.7	461.8	492.0	528.1	569.8	615.3	666.7	728.5	791.9	838.7
37.5°	388.8	408.0	434.4	467.6	505.5	550.2	604.2	665.2	730.8	781.4	796.4
40°	370.4	388.3	415.8	450.2	488.9	536.2	595.4	659.9	723.5	755.7	743.3
42.5°	350.9	369.7	396.4	430.5	472.2	523.7	584.5	648.9	702.3	714.4	671.6
45°	320.2	339.5	365.9	400.3	445.2	501.0	564.3	622.9	653.6	631.6	565.1
47.5°	291.5	309.7	334.1	369.7	415.9	473.6	534.6	581.4	583.8	531.3	460.3
50°	272.0	288.8	313.4	348.9	394.8	453.3	508.3	545.2	528.6	469.1	401.0
52.5°	252.9	269.3	293.5	328.7	374.1	427.6	478.9	504.7	473.5	412.5	354.3
55°	225.2	239.6	263.3	295.8	338.8	388.5	432.1	441.0	400.5	340.4	293.1
57.5°	198.2	211.6	233.2	263.1	302.6	346.5	380.6	378.6	335.8	284.3	246.8
60°	179.9	192.9	212.2	241.3	277.3	315.2	344.3	337.3	294.9	250.4	218.9
62.5°	163.5	175.2	193.3	218.9	251.7	286.7	310.7	300.4	258.8	220.0	195.0
65°	139.4	149.2	164.7	186.4	213.7	242.6	261.2	247.9	212.4	182.1	162.0
67.5°	116.3	124.2	137.1	154.6	177.8	201.0	212.3	199.0	170.5	148.5	133.6
70°	101.7	108.7	118.7	134.1	154.4	174.0	182.5	170.5	146.1	127.1	116.5
72.5°	87.1	92.8	101.6	115.6	131.8	148.7	156.2	144.8	124.7	108.7	98.8
75°	67.3	71.3	77.3	86.9	99.7	113.3	117.3	107.4	94.5	82.6	76.0
77.5°	48.2	51.5	56.1	62.1	71.3	79.8	83.4	77.7	67.8	60.1	54.8
80°	37.0	38.7	42.7	47.7	54.9	60.3	62.7	59.0	52.0	46.4	42.2
82.5°	26.4	28.2	30.4	34.6	39.2	42.9	45.4	43.0	38.0	33.5	31.1
85°	12.8	13.9	15.3	17.0	20.5	22.6	22.4	20.9	18.9	17.2	15.9
87.5°	5.1	5.6	6.4	7.6	8.5	9.4	10.1	10.0	9.6	9.3	9.0
90°	2.6	4.2	5.9	7.6	9.2	10.7	12.2	13.6	15.1	16.1	17.2
92.5°	23.9	25.1	26.3	27.4	28.9	30.7	32.5	34.3	36.1	37.5	38.9
95°	61.5	62.0	62.4	62.9	64.1	66.2	68.2	70.4	72.5	73.9	75.4
97.5°	101.8	102.0	102.2	102.3	103.9	106.7	109.6	112.4	115.4	116.8	118.1
100°	131.8	131.8	131.8	131.8	133.1	135.8	138.6	141.3	143.9	145.8	147.7
102.5°	164.9	165.8	166.6	167.5	168.5	169.9	171.4	172.7	174.1	176.2	178.1
105°	215.6	216.6	217.7	218.8	219.9	221.1	222.3	223.7	224.9	226.1	227.4
107.5°	271.3	272.3	273.4	274.5	275.4	276.4	277.4	278.3	279.3	279.9	280.5
110°	309.7	310.8	311.8	312.8	313.7	314.2	314.9	315.6	316.1	316.8	317.4





TEST NUMBER: P333143-830

CATALOG NUMBER: S125DIP-S375D1035U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	348.4	348.8	349.4	350.0	350.6	351.5	352.2	353.0	353.8	354.1	354.4
115°	406.4	407.3	408.1	408.9	409.5	409.9	410.4	410.8	411.2	411.0	410.8
117.5°	463.9	464.3	464.7	465.1	465.4	465.8	466.2	466.6	466.9	467.1	467.2
120°	500.7	501.7	502.8	503.9	504.4	504.6	504.9	505.1	505.3	505.3	505.3
122.5°	539.2	539.6	540.0	540.4	540.7	541.3	541.9	542.4	542.9	542.8	542.6
125°	593.1	594.4	595.7	596.9	597.7	597.9	598.0	598.2	598.5	598.0	597.7
127.5°	649.0	649.8	650.4	651.2	651.7	652.0	652.1	652.4	652.7	652.4	652.2
130°	683.2	684.3	685.3	686.4	687.1	687.6	688.0	688.3	688.8	688.6	688.3
132.5°	717.8	719.5	721.2	722.9	723.8	723.7	723.6	723.5	723.4	723.2	723.0
135°	771.0	772.2	773.5	774.8	775.5	775.7	775.9	776.1	776.3	776.3	776.3
137.5°	821.3	822.6	823.8	825.0	825.9	826.3	826.8	827.3	827.6	827.9	828.2
140°	853.6	854.6	855.6	856.7	857.5	858.2	858.8	859.4	860.1	860.4	860.9
142.5°	885.8	886.6	887.5	888.4	889.3	890.0	890.9	891.6	892.4	892.7	893.0
145°	933.4	934.2	935.0	935.9	936.6	937.3	937.8	938.5	939.1	939.1	939.1
147.5°	977.0	977.5	978.0	978.4	978.9	979.4	979.9	980.3	980.9	981.4	981.8
150°	1005.7	1005.5	1005.3	1005.1	1005.4	1006.3	1007.1	1007.9	1008.7	1008.7	1008.7
152.5°	1030.3	1030.6	1030.9	1031.1	1031.5	1031.8	1032.2	1032.5	1032.8	1033.3	1033.9
155°	1067.1	1067.1	1067.1	1067.1	1067.1	1067.4	1067.6	1067.8	1068.0	1068.8	1069.7
157.5°	1099.8	1099.3	1098.8	1098.3	1098.3	1098.4	1098.6	1098.9	1099.1	1099.9	1100.7
160°	1119.2	1118.5	1117.9	1117.3	1117.1	1117.3	1117.5	1117.7	1117.9	1118.7	1119.6
162.5°	1136.6	1136.1	1135.7	1135.3	1135.0	1135.1	1135.1	1135.2	1135.2	1136.2	1137.2
165°	1159.8	1159.4	1159.0	1158.6	1158.5	1158.7	1158.9	1159.0	1159.3	1160.2	1160.9
167.5°	1178.9	1178.2	1177.3	1176.5	1176.0	1176.0	1176.0	1176.0	1176.0	1177.3	1178.6
170°	1189.5	1188.6	1187.9	1187.0	1186.6	1186.6	1186.6	1186.6	1186.6	1187.9	1189.1
172.5°	1197.0	1196.2	1195.3	1194.6	1194.1	1194.1	1194.1	1194.1	1194.1	1195.3	1196.7
175°	1205.5	1204.7	1203.8	1203.0	1202.6	1202.6	1202.6	1202.6	1202.6	1203.8	1205.1
177.5°	1210.0	1209.4	1208.6	1208.0	1207.6	1207.4	1207.2	1207.1	1206.9	1208.0	1208.9
180°	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2



TEST NUMBER: P333143-830

CATALOG NUMBER: S125DIP-S375D1035U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	513.1	513.1	513.1	513.1	513.1	513.1	513.1
2.5°	536.7	538.0	541.0	540.0	541.3	542.1	542.7
5°	579.9	586.9	590.0	589.6	594.2	593.0	591.9
7.5°	629.0	636.2	640.4	645.5	648.4	648.7	651.2
10°	656.7	666.2	670.1	675.6	679.1	681.1	680.8
12.5°	677.9	685.4	694.2	696.8	701.5	704.1	703.1
15°	703.5	715.5	724.6	729.2	735.1	736.8	739.1
17.5°	726.3	742.3	753.0	767.2	772.6	775.9	773.9
20°	743.6	764.7	775.3	792.3	801.7	806.7	804.9
22.5°	763.9	786.8	806.5	821.2	835.5	842.3	843.7
25°	798.9	830.2	859.2	878.5	896.2	900.3	909.5
27.5°	837.9	874.9	905.9	926.2	938.5	943.1	946.0
30°	862.4	899.3	922.6	935.7	939.5	939.1	938.7
32.5°	874.5	897.5	902.0	898.3	889.4	881.7	873.8
35°	857.4	840.3	814.5	781.5	757.1	732.4	730.0
37.5°	771.2	716.1	673.4	625.6	598.0	581.0	569.2
40°	689.9	627.5	575.6	535.4	507.3	496.2	485.2
42.5°	601.8	542.1	496.2	462.5	441.4	429.0	420.5
45°	488.9	436.2	400.3	375.9	359.1	349.6	344.1
47.5°	400.7	361.7	331.1	313.5	302.0	294.5	294.5
50°	353.3	316.0	295.8	281.8	271.8	265.9	267.0
52.5°	311.2	283.4	266.2	254.5	247.0	243.5	243.3
55°	260.2	240.3	228.9	220.4	215.4	211.2	212.2
57.5°	222.6	205.8	198.1	191.1	187.6	186.0	183.5
60°	199.3	186.2	179.6	174.0	170.5	169.2	166.8
62.5°	178.5	168.2	161.9	157.3	154.2	153.7	151.8
65°	150.1	142.2	136.6	134.4	131.1	130.3	130.3
67.5°	123.7	118.1	113.7	111.7	110.3	110.5	109.4
70°	107.2	102.5	99.7	97.6	96.5	96.7	95.9
72.5°	93.8	88.6	86.1	84.8	83.4	84.0	83.6
75°	71.0	68.4	67.1	65.8	64.9	64.5	64.0
77.5°	52.1	49.9	48.8	48.1	48.3	47.1	48.0
80°	40.2	38.4	37.7	36.6	36.4	36.4	36.2
82.5°	29.5	28.4	27.9	27.1	26.6	27.0	26.4
85°	15.3	14.4	14.1	14.1	13.8	13.3	14.4
87.5°	9.2	8.8	8.9	8.9	9.0	9.0	8.7
90°	18.2	19.2	20.1	20.7	21.3	22.0	22.6
92.5°	40.2	41.7	42.6	43.1	43.5	43.9	44.4
95°	76.8	78.3	79.3	79.6	80.1	80.5	81.0
97.5°	119.5	120.9	121.7	122.0	122.2	122.4	122.7
100°	149.6	151.5	152.7	153.1	153.4	153.9	154.3
102.5°	180.2	182.3	183.6	184.2	184.7	185.4	186.0
105°	228.7	229.9	230.8	231.5	232.1	232.7	233.4
107.5°	281.2	281.8	282.1	282.0	282.0	282.0	281.9
110°	318.0	318.7	318.9	318.7	318.5	318.3	318.0



TEST NUMBER: P333143-830

CATALOG NUMBER: S125DIP-S375D1035U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	354.7	355.0	355.0	354.6	354.2	353.8	353.5
115°	410.6	410.4	410.2	409.9	409.7	409.5	409.3
117.5°	467.4	467.6	467.2	466.4	465.6	464.8	463.9
120°	505.3	505.3	504.9	504.1	503.2	502.4	501.5
122.5°	542.4	542.2	541.9	541.2	540.5	539.9	539.2
125°	597.2	596.8	596.4	596.3	596.1	595.9	595.7
127.5°	652.1	651.9	651.5	651.1	650.6	650.3	649.9
130°	688.2	688.0	687.7	687.2	686.8	686.4	686.0
132.5°	722.8	722.6	722.2	721.6	721.0	720.5	719.8
135°	776.3	776.3	775.9	775.1	774.2	773.4	772.5
137.5°	828.4	828.7	828.3	827.3	826.2	825.2	824.2
140°	861.3	861.8	861.4	860.4	859.3	858.3	857.2
142.5°	893.2	893.4	893.1	892.0	891.0	889.9	888.8
145°	939.1	939.1	938.8	938.2	937.5	936.9	936.3
147.5°	982.4	982.9	982.4	981.0	979.6	978.2	976.8
150°	1008.7	1008.7	1008.5	1008.1	1007.7	1007.3	1006.8
152.5°	1034.3	1034.8	1034.7	1034.0	1033.2	1032.5	1031.7
155°	1070.5	1071.4	1071.3	1070.3	1069.1	1068.1	1067.1
157.5°	1101.5	1102.4	1102.1	1100.8	1099.4	1098.0	1096.6
160°	1120.4	1121.2	1121.2	1120.1	1119.1	1118.0	1116.9
162.5°	1138.2	1139.3	1139.2	1137.9	1136.7	1135.5	1134.3
165°	1161.8	1162.6	1162.4	1161.2	1159.9	1158.7	1157.4
167.5°	1179.8	1181.1	1181.0	1179.8	1178.5	1177.1	1175.8
170°	1190.3	1191.6	1191.5	1190.1	1188.5	1187.1	1185.6
172.5°	1197.9	1199.1	1199.1	1197.8	1196.6	1195.2	1193.9
175°	1206.4	1207.6	1207.5	1206.1	1204.6	1203.1	1201.6
177.5°	1209.9	1210.9	1210.9	1209.7	1208.5	1207.3	1206.2
180°	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2

(END OF REPORT)