

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333176-935

Luminaire Tested: **S125DIP-S610D590U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333176-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S610D590U935-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3914.3 lumens
Efficiency: N/A
Efficacy: 119.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333176-935

CATALOG NUMBER: S125DIP-S610D590U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333176-935

CATALOG NUMBER: S125DIP-S610D590U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	94	90	87	92	88	84	81	75	73	71	64	62	61	54	52	51	46
2	90	82	76	71	83	77	71	67	66	62	58	56	53	51	47	45	43	39
3	82	72	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37	33
4	75	64	56	50	69	60	53	47	52	46	42	44	40	37	37	34	32	28
5	69	57	49	43	64	53	46	41	46	41	36	40	35	32	34	30	27	24
6	64	51	43	37	59	48	41	35	42	36	31	36	31	28	30	27	24	21
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	21	19
8	55	42	34	29	51	39	32	27	35	29	25	30	25	22	26	22	19	17
9	51	38	31	26	47	36	29	25	32	26	22	28	23	20	24	20	17	15
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5340	5340	5340
5°	5352	5301	5335
10°	5319	5264	5294
15°	5262	5201	5223
20°	5179	5112	5121
25°	5091	5007	5002
30°	4981	4894	4869
35°	4864	4771	4704
40°	4743	4639	4572
45°	4613	4517	4427
50°	4470	4372	4240
55°	4332	4206	4088
60°	4166	4039	3896
65°	3969	3839	3709
70°	3780	3609	3484
75°	3444	3331	3216
80°	3065	3016	2942
85°	2668	2712	2571



TEST NUMBER: P333176-935

CATALOG NUMBER: S125DIP-S610D590U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.0	2.0
10°-20°	220.2	5.6
20°-30°	325.2	8.3
30°-40°	379.4	9.7
40°-50°	381.1	9.7
50°-60°	334.5	8.5
60°-70°	249.3	6.4
70°-80°	142.5	3.6
80°-90°	42.8	1.1
90°-100°	42.3	1.1
100°-110°	124.8	3.2
110°-120°	211.4	5.4
120°-130°	278.3	7.1
130°-140°	311.8	8.0
140°-150°	305.6	7.8
150°-160°	256.7	6.6
160°-170°	170.6	4.4
170°-180°	59.7	1.5
0°-30°	623.4	15.9
0°-40°	1002.8	25.6
0°-60°	1718.4	43.9
0°-90°	2153.1	55.0
90°-120°	378.5	9.7
90°-150°	1274.2	32.6
90°-180°	1761.0	45.0
0°-180°	3914.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	827	827	827	827	827	
5°	826	824	818	823	823	78
15°	787	785	778	781	781	222
25°	714	711	703	704	702	329
35°	617	614	605	602	597	386
45°	505	502	495	487	485	389
55°	385	382	374	368	363	343
65°	260	258	251	246	243	258
75°	138	137	134	131	129	147
85°	36	37	37	36	35	40
90°	0	4	8	10	12	4
95°	32	33	38	41	42	34
105°	112	114	117	120	122	120
115°	212	214	215	214	214	209
125°	309	312	312	311	311	277
135°	402	405	405	405	403	310
145°	487	489	490	490	489	304
155°	557	557	558	559	557	256
165°	606	605	605	607	604	171
175°	630	628	628	630	627	60
180°	631	631	631	631	631	



TEST NUMBER: P333176-935

CATALOG NUMBER: S125DIP-S610D590U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9
2.5°	829.0	828.6	828.3	827.9	827.6	826.8	825.7	824.5	823.4	822.2	823.4
5°	825.6	825.3	825.0	824.7	824.4	823.5	822.1	820.6	819.2	817.7	819.1
7.5°	817.9	817.7	817.4	817.1	816.8	815.9	814.2	812.7	811.1	809.5	810.7
10°	811.1	810.9	810.6	810.3	810.0	809.1	807.4	805.9	804.3	802.7	803.8
12.5°	802.8	802.3	801.8	801.2	800.7	799.7	798.2	796.8	795.2	793.8	794.7
15°	787.0	786.5	786.1	785.7	785.2	784.2	782.6	781.0	779.4	777.8	778.5
17.5°	768.8	768.2	767.5	766.9	766.2	765.1	763.4	761.7	760.1	758.5	759.3
20°	753.6	753.3	753.0	752.8	752.4	751.4	749.5	747.6	745.7	743.8	744.9
22.5°	738.4	737.9	737.4	736.8	736.3	735.2	733.4	731.7	729.9	728.1	728.8
25°	714.4	713.6	712.9	712.2	711.4	710.2	708.3	706.4	704.5	702.6	702.9
27.5°	686.2	685.8	685.4	684.9	684.5	683.3	681.3	679.4	677.4	675.5	675.5
30°	667.9	667.4	667.0	666.6	666.2	664.9	662.7	660.5	658.3	656.2	655.8
32.5°	648.0	647.4	646.7	646.0	645.3	644.0	642.1	640.2	638.2	636.3	635.8
35°	616.9	616.3	615.7	615.2	614.6	613.3	611.2	609.2	607.2	605.1	604.4
37.5°	584.5	583.8	583.2	582.4	581.7	580.3	578.4	576.5	574.5	572.7	571.6
40°	562.6	561.9	561.1	560.4	559.6	558.3	556.3	554.2	552.2	550.2	548.9
42.5°	539.1	538.5	537.8	537.2	536.6	535.3	533.2	531.2	529.2	527.1	526.0
45°	505.1	504.5	503.9	503.3	502.7	501.5	499.8	498.1	496.3	494.6	492.8
47.5°	468.4	468.4	468.5	468.5	468.5	467.4	465.4	463.3	461.2	459.1	457.4
50°	444.9	444.4	443.9	443.5	443.1	442.0	440.2	438.5	436.8	435.1	433.2
52.5°	420.8	420.4	420.2	419.8	419.5	418.4	416.6	414.7	412.8	411.0	409.3
55°	384.7	384.2	383.7	383.3	382.9	381.7	379.6	377.6	375.6	373.5	372.2
57.5°	346.6	346.4	346.1	345.9	345.7	344.7	342.9	341.2	339.5	337.9	336.1
60°	322.5	321.9	321.3	320.7	320.2	319.1	317.5	315.9	314.3	312.7	311.3
62.5°	297.4	297.0	296.4	296.0	295.5	294.6	293.3	291.9	290.5	289.1	287.6
65°	259.7	259.4	259.2	258.8	258.6	257.6	256.0	254.4	252.8	251.2	249.9
67.5°	223.2	222.6	222.0	221.4	220.8	219.9	218.7	217.5	216.3	215.1	214.0
70°	200.2	199.5	198.7	198.0	197.3	196.2	194.9	193.6	192.3	191.1	190.1
72.5°	175.0	174.5	174.1	173.6	173.1	172.4	171.6	170.7	169.9	169.0	168.1
75°	138.0	137.8	137.4	137.2	136.9	136.4	135.6	134.9	134.1	133.5	133.0
77.5°	103.9	103.8	103.7	103.5	103.4	103.1	102.7	102.4	101.9	101.5	101.3
80°	82.4	82.4	82.4	82.4	82.4	82.3	82.0	81.7	81.5	81.1	80.9
82.5°	63.6	63.4	63.1	62.9	62.7	62.5	62.4	62.4	62.3	62.3	62.0
85°	36.0	36.2	36.2	36.4	36.6	36.6	36.6	36.6	36.6	36.6	36.5
87.5°	14.2	14.4	14.6	14.7	14.9	15.1	15.1	15.1	15.2	15.2	15.3
90°	0.5	1.4	2.2	3.1	4.0	4.8	5.6	6.4	7.1	7.8	8.4
92.5°	11.9	12.5	13.1	13.7	14.3	15.1	16.0	17.0	17.9	18.9	19.5
95°	31.9	32.1	32.4	32.5	32.8	33.5	34.5	35.6	36.8	37.8	38.6
97.5°	53.0	53.1	53.2	53.3	53.4	54.2	55.7	57.2	58.7	60.2	61.0
100°	68.8	68.8	68.8	68.8	68.8	69.5	70.9	72.3	73.7	75.2	76.1
102.5°	85.7	86.1	86.5	87.0	87.4	88.0	88.7	89.5	90.1	90.8	92.0
105°	112.0	112.5	113.0	113.7	114.2	114.8	115.5	116.1	116.8	117.4	118.0
107.5°	141.0	141.6	142.2	142.7	143.3	143.8	144.3	144.7	145.3	145.8	146.1
110°	161.1	161.6	162.2	162.7	163.3	163.8	164.0	164.4	164.7	165.1	165.4



TEST NUMBER: P333176-935

CATALOG NUMBER: S125DIP-S610D590U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	181.5	181.8	182.1	182.4	182.7	183.0	183.5	183.8	184.3	184.7	184.9
115°	211.7	212.2	212.6	213.0	213.4	213.8	214.0	214.2	214.4	214.6	214.6
117.5°	241.9	242.1	242.4	242.5	242.7	243.0	243.1	243.3	243.5	243.7	243.8
120°	260.8	261.4	261.9	262.4	263.0	263.3	263.5	263.6	263.6	263.7	263.7
122.5°	281.3	281.5	281.6	281.8	282.1	282.2	282.6	282.8	283.1	283.4	283.4
125°	308.9	309.6	310.2	310.9	311.6	311.9	312.0	312.2	312.3	312.4	312.2
127.5°	338.5	338.8	339.1	339.5	339.9	340.2	340.3	340.4	340.5	340.7	340.6
130°	356.1	356.6	357.2	357.7	358.3	358.7	358.9	359.1	359.3	359.6	359.5
132.5°	373.8	374.7	375.6	376.4	377.4	377.8	377.7	377.7	377.6	377.6	377.5
135°	401.7	402.4	403.1	403.7	404.4	404.8	404.9	405.0	405.1	405.2	405.2
137.5°	428.1	428.8	429.4	430.0	430.7	431.1	431.4	431.5	431.8	432.0	432.1
140°	445.0	445.6	446.1	446.6	447.2	447.6	448.0	448.3	448.6	448.9	449.2
142.5°	461.9	462.4	462.8	463.3	463.7	464.2	464.6	465.0	465.5	465.8	466.0
145°	486.7	487.2	487.7	488.1	488.5	488.9	489.2	489.6	489.9	490.2	490.2
147.5°	509.7	510.0	510.2	510.5	510.7	510.9	511.2	511.5	511.8	512.0	512.3
150°	525.0	525.0	524.9	524.8	524.6	524.8	525.2	525.6	526.1	526.5	526.5
152.5°	537.6	537.8	538.0	538.1	538.2	538.4	538.6	538.7	538.9	539.2	539.4
155°	557.0	557.0	557.0	557.0	557.0	557.1	557.2	557.2	557.4	557.5	557.9
157.5°	574.3	574.0	573.8	573.6	573.3	573.3	573.3	573.5	573.6	573.7	574.1
160°	584.5	584.2	583.8	583.5	583.2	583.1	583.2	583.3	583.4	583.5	583.9
162.5°	593.6	593.3	593.1	592.8	592.5	592.5	592.5	592.5	592.5	592.5	593.1
165°	605.6	605.4	605.2	604.9	604.8	604.7	604.8	604.9	605.0	605.1	605.5
167.5°	615.9	615.4	614.9	614.5	614.1	613.9	613.9	613.9	613.9	613.9	614.5
170°	621.3	620.9	620.4	620.0	619.6	619.4	619.4	619.4	619.4	619.4	620.0
172.5°	625.3	624.8	624.4	624.0	623.5	623.3	623.3	623.3	623.3	623.3	624.0
175°	629.6	629.2	628.8	628.4	627.9	627.8	627.8	627.8	627.8	627.8	628.4
177.5°	632.0	631.6	631.3	630.9	630.5	630.3	630.3	630.2	630.1	630.0	630.5
180°	631.2	631.2	631.2	631.2	631.2	631.2	631.2	631.2	631.2	631.2	631.2



TEST NUMBER: P333176-935

CATALOG NUMBER: S125DIP-S610D590U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9
2.5°	824.5	825.7	826.8	827.3	827.2	827.1	827.0	826.9
5°	820.4	821.7	822.9	823.5	823.4	823.3	823.1	822.9
7.5°	812.0	813.3	814.6	815.2	815.0	814.9	814.8	814.6
10°	805.0	806.2	807.4	807.9	807.7	807.5	807.4	807.3
12.5°	795.7	796.6	797.5	798.0	797.9	797.9	797.9	797.8
15°	779.3	780.0	780.8	781.1	781.1	781.1	781.1	781.1
17.5°	760.3	761.1	762.1	762.2	761.4	760.7	760.0	759.2
20°	745.8	746.8	747.9	748.0	747.3	746.6	745.8	745.1
22.5°	729.4	730.1	730.8	730.9	730.4	729.9	729.4	728.9
25°	703.2	703.4	703.8	703.7	703.3	702.8	702.4	702.0
27.5°	675.6	675.7	675.7	675.5	675.1	674.7	674.2	673.8
30°	655.6	655.3	655.0	654.6	654.2	653.8	653.3	652.9
32.5°	635.2	634.6	634.1	633.5	632.7	632.0	631.1	630.3
35°	603.6	603.0	602.2	601.2	600.1	598.9	597.8	596.6
37.5°	570.5	569.5	568.3	567.5	566.8	566.2	565.5	564.8
40°	547.5	546.2	544.9	544.1	543.6	543.2	542.8	542.3
42.5°	524.8	523.6	522.4	521.4	520.7	520.1	519.4	518.8
45°	491.0	489.3	487.6	486.5	486.0	485.6	485.2	484.7
47.5°	455.6	453.7	452.0	450.6	449.6	448.6	447.5	446.5
50°	431.3	429.4	427.5	426.0	425.0	424.0	422.9	422.0
52.5°	407.6	406.0	404.3	402.9	401.8	400.6	399.5	398.4
55°	370.9	369.6	368.3	367.1	366.1	365.1	364.1	363.1
57.5°	334.4	332.8	331.1	329.9	329.4	328.8	328.3	327.8
60°	309.8	308.3	306.9	305.7	304.6	303.6	302.6	301.6
62.5°	286.0	284.5	282.8	281.7	280.9	280.1	279.3	278.5
65°	248.6	247.3	246.0	245.0	244.4	243.8	243.3	242.7
67.5°	212.9	211.8	210.7	209.9	209.6	209.2	208.9	208.5
70°	189.2	188.4	187.5	186.8	186.2	185.6	185.0	184.5
72.5°	167.0	166.1	165.1	164.3	163.7	163.2	162.6	162.0
75°	132.6	132.2	131.7	131.2	130.6	130.0	129.5	128.9
77.5°	101.0	100.7	100.5	100.1	99.7	99.4	98.9	98.5
80°	80.8	80.7	80.5	80.3	80.0	79.7	79.5	79.1
82.5°	61.7	61.5	61.2	61.0	61.0	61.0	60.9	60.9
85°	36.3	36.2	36.1	35.8	35.6	35.2	35.0	34.7
87.5°	15.4	15.5	15.6	15.6	15.4	15.2	15.1	14.9
90°	9.0	9.5	10.1	10.5	10.8	11.1	11.5	11.8
92.5°	20.3	21.0	21.8	22.2	22.5	22.7	22.9	23.2
95°	39.3	40.1	40.9	41.3	41.6	41.8	42.0	42.3
97.5°	61.6	62.4	63.1	63.5	63.6	63.8	63.9	64.1
100°	77.1	78.1	79.0	79.6	79.9	80.2	80.3	80.6
102.5°	93.0	94.1	95.1	95.8	96.2	96.4	96.8	97.0
105°	118.7	119.3	120.0	120.5	120.8	121.1	121.5	121.8
107.5°	146.5	146.8	147.1	147.2	147.2	147.2	147.1	147.1
110°	165.7	166.0	166.3	166.4	166.3	166.3	166.1	166.0



TEST NUMBER: P333176-935

CATALOG NUMBER: S125DIP-S610D590U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	185.0	185.1	185.3	185.3	185.1	184.9	184.7	184.5
115°	214.4	214.3	214.2	214.1	214.0	213.9	213.8	213.7
117.5°	243.9	244.0	244.1	243.9	243.5	243.1	242.6	242.1
120°	263.7	263.7	263.7	263.6	263.1	262.7	262.3	261.8
122.5°	283.3	283.2	283.1	282.8	282.5	282.1	281.8	281.5
125°	311.9	311.8	311.5	311.3	311.3	311.2	311.0	310.9
127.5°	340.4	340.4	340.3	340.1	339.8	339.7	339.4	339.2
130°	359.3	359.2	359.1	359.0	358.7	358.5	358.3	358.1
132.5°	377.4	377.3	377.2	376.9	376.7	376.3	376.1	375.7
135°	405.2	405.2	405.2	405.0	404.6	404.2	403.7	403.3
137.5°	432.3	432.4	432.6	432.4	431.8	431.3	430.8	430.2
140°	449.4	449.6	449.8	449.6	449.1	448.6	448.0	447.5
142.5°	466.1	466.2	466.3	466.1	465.6	465.0	464.5	464.0
145°	490.2	490.2	490.2	490.0	489.7	489.4	489.0	488.7
147.5°	512.6	512.8	513.1	512.8	512.0	511.3	510.6	509.9
150°	526.5	526.5	526.5	526.4	526.2	526.0	525.8	525.6
152.5°	539.7	539.9	540.2	540.1	539.7	539.3	538.9	538.6
155°	558.4	558.8	559.2	559.2	558.6	558.1	557.5	557.0
157.5°	574.5	575.0	575.4	575.3	574.5	573.9	573.2	572.4
160°	584.4	584.8	585.2	585.2	584.7	584.1	583.6	583.1
162.5°	593.6	594.1	594.7	594.6	594.0	593.3	592.7	592.0
165°	606.0	606.4	606.9	606.7	606.1	605.5	604.8	604.2
167.5°	615.2	615.9	616.5	616.5	615.8	615.1	614.4	613.8
170°	620.7	621.3	622.0	621.9	621.2	620.4	619.7	618.9
172.5°	624.7	625.3	625.9	625.9	625.3	624.6	623.9	623.2
175°	629.0	629.6	630.3	630.3	629.6	628.8	628.0	627.2
177.5°	631.0	631.5	632.1	632.1	631.5	630.9	630.2	629.6
180°	631.2	631.2	631.2	631.2	631.2	631.2	631.2	631.2

(END OF REPORT)