

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333122-830

Luminaire Tested: **S125DIP-S375D365U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333122-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S375D365U830-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2628.2 lumens  
Efficiency: N/A  
Efficacy: 129.5 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 20.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333122-830

CATALOG NUMBER: S125DIP-S375D365U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333122-830

CATALOG NUMBER: S125DIP-S375D365U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60
1	99	94	90	87	91	88	84	81	75	73	70	64	62	60	53	52	51
2	90	82	76	71	83	77	71	67	66	62	58	56	53	50	47	45	43
3	82	72	65	59	76	67	61	56	58	53	49	49	46	43	41	39	36
4	75	64	56	50	69	60	53	47	52	46	42	44	40	36	37	34	31
5	69	57	49	43	64	53	46	40	46	40	36	40	35	32	33	30	27
6	63	51	43	37	59	48	41	35	42	36	31	36	31	28	30	27	24
7	59	46	38	33	54	43	36	31	38	32	28	33	28	24	28	24	21
8	54	42	34	29	50	39	32	27	34	29	25	30	25	22	25	22	19
9	51	38	31	26	47	36	29	24	32	26	22	27	23	20	23	20	17
10	47	35	28	23	44	33	26	22	29	24	20	25	21	18	22	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3556	3556	3556
5°	3564	3530	3553
10°	3543	3505	3525
15°	3504	3463	3477
20°	3449	3404	3410
25°	3390	3334	3331
30°	3317	3258	3242
35°	3239	3177	3132
40°	3159	3089	3044
45°	3072	3008	2948
50°	2976	2910	2823
55°	2884	2800	2723
60°	2773	2689	2595
65°	2644	2557	2470
70°	2517	2402	2319
75°	2293	2218	2141
80°	2042	2008	1960
85°	1771	1808	1712



TEST NUMBER: P333122-830

CATALOG NUMBER: S125DIP-S375D365U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	51.9	2.0
10°-20°	146.6	5.6
20°-30°	216.5	8.2
30°-40°	252.7	9.6
40°-50°	253.8	9.7
50°-60°	222.8	8.5
60°-70°	166.0	6.3
70°-80°	94.9	3.6
80°-90°	28.5	1.1
90°-100°	28.7	1.1
100°-110°	84.7	3.2
110°-120°	143.4	5.5
120°-130°	188.7	7.2
130°-140°	211.5	8.0
140°-150°	207.3	7.9
150°-160°	174.1	6.6
160°-170°	115.7	4.4
170°-180°	40.5	1.5
0°-30°	415.1	15.8
0°-40°	667.8	25.4
0°-60°	1144.3	43.5
0°-90°	1433.7	54.6
90°-120°	256.8	9.8
90°-150°	864.2	32.9
90°-180°	1195.0	45.5
0°-180°	2628.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	551	551	551	551	551	
5°	550	549	544	548	548	52
15°	524	522	518	520	520	148
25°	476	473	468	469	467	219
35°	411	409	403	401	397	257
45°	336	334	329	324	323	259
55°	256	255	249	245	242	229
65°	173	172	167	164	162	172
75°	92	91	89	88	86	98
85°	24	24	24	24	23	27
90°	0	3	5	7	8	3
95°	22	22	26	28	29	23
105°	76	78	80	82	83	81
115°	144	145	146	145	145	142
125°	210	211	212	211	211	188
135°	272	274	275	275	274	210
145°	330	331	332	332	332	206
155°	378	378	378	379	378	174
165°	411	410	410	412	410	116
175°	427	426	426	427	425	41
180°	428	428	428	428	428	



TEST NUMBER: P333122-830

CATALOG NUMBER: S125DIP-S375D365U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	550.6	550.6	550.6	550.6	550.6	550.6	550.6	550.6	550.6	550.6	550.6
2.5°	552.0	551.8	551.6	551.3	551.1	550.5	549.8	549.0	548.3	547.4	548.3
5°	549.7	549.5	549.3	549.1	548.9	548.4	547.4	546.5	545.4	544.5	545.4
7.5°	544.7	544.5	544.3	544.1	543.9	543.3	542.2	541.1	540.1	539.0	539.9
10°	540.2	540.0	539.8	539.6	539.4	538.8	537.7	536.6	535.6	534.5	535.3
12.5°	534.6	534.2	533.9	533.6	533.2	532.5	531.5	530.6	529.5	528.6	529.1
15°	524.1	523.8	523.5	523.2	522.8	522.2	521.1	520.1	519.0	517.9	518.4
17.5°	511.9	511.5	511.0	510.7	510.2	509.4	508.3	507.3	506.1	505.0	505.7
20°	501.8	501.6	501.4	501.2	501.1	500.3	499.1	497.8	496.5	495.3	496.0
22.5°	491.7	491.3	491.0	490.7	490.3	489.6	488.3	487.2	486.0	484.8	485.3
25°	475.7	475.2	474.7	474.2	473.7	472.9	471.6	470.3	469.1	467.9	468.1
27.5°	456.9	456.7	456.4	456.1	455.8	455.0	453.7	452.4	451.1	449.8	449.9
30°	444.8	444.5	444.1	443.8	443.6	442.7	441.3	439.8	438.4	436.9	436.7
32.5°	431.5	431.0	430.6	430.2	429.7	428.9	427.5	426.2	425.0	423.7	423.3
35°	410.8	410.4	410.0	409.6	409.3	408.3	407.0	405.7	404.3	402.9	402.5
37.5°	389.3	388.8	388.3	387.8	387.3	386.4	385.1	383.9	382.6	381.4	380.6
40°	374.7	374.1	373.6	373.2	372.7	371.7	370.4	369.1	367.7	366.4	365.5
42.5°	358.9	358.5	358.2	357.7	357.3	356.5	355.1	353.7	352.3	351.0	350.2
45°	336.3	335.9	335.5	335.2	334.7	333.9	332.8	331.7	330.5	329.3	328.2
47.5°	311.9	311.9	311.9	312.0	312.0	311.3	309.9	308.5	307.1	305.7	304.5
50°	296.2	296.0	295.7	295.3	295.0	294.4	293.1	292.0	290.9	289.6	288.4
52.5°	280.2	279.9	279.7	279.6	279.4	278.6	277.4	276.2	274.8	273.6	272.6
55°	256.1	255.8	255.5	255.2	255.0	254.1	252.8	251.5	250.1	248.7	247.9
57.5°	230.8	230.6	230.5	230.4	230.2	229.5	228.4	227.2	226.1	225.0	223.9
60°	214.7	214.3	214.0	213.6	213.2	212.4	211.4	210.4	209.2	208.2	207.3
62.5°	198.0	197.7	197.4	197.1	196.8	196.1	195.3	194.4	193.4	192.6	191.5
65°	173.0	172.8	172.6	172.4	172.2	171.5	170.5	169.4	168.3	167.3	166.4
67.5°	148.6	148.3	147.8	147.4	147.0	146.4	145.6	144.8	144.0	143.3	142.5
70°	133.3	132.8	132.3	131.9	131.4	130.6	129.8	128.9	128.1	127.2	126.6
72.5°	116.6	116.2	115.9	115.6	115.3	114.8	114.2	113.7	113.1	112.5	111.9
75°	91.9	91.7	91.5	91.3	91.1	90.8	90.3	89.8	89.4	88.9	88.6
77.5°	69.2	69.1	69.0	68.9	68.9	68.7	68.4	68.1	67.9	67.6	67.4
80°	54.9	54.9	54.9	54.9	54.9	54.8	54.6	54.4	54.2	54.0	53.9
82.5°	42.3	42.2	42.0	41.8	41.8	41.7	41.6	41.6	41.5	41.5	41.3
85°	23.9	24.0	24.1	24.2	24.3	24.4	24.4	24.4	24.4	24.4	24.3
87.5°	9.5	9.6	9.7	9.8	10.0	10.0	10.1	10.1	10.1	10.1	10.2
90°	0.4	0.9	1.5	2.1	2.7	3.3	3.8	4.3	4.8	5.4	5.7
92.5°	8.1	8.5	8.9	9.3	9.7	10.3	10.8	11.5	12.2	12.8	13.3
95°	21.7	21.8	22.0	22.1	22.2	22.7	23.5	24.1	24.9	25.6	26.2
97.5°	36.0	36.0	36.1	36.2	36.2	36.8	37.8	38.8	39.8	40.8	41.4
100°	46.7	46.7	46.7	46.7	46.7	47.1	48.1	49.0	50.0	51.0	51.7
102.5°	58.1	58.4	58.7	59.0	59.3	59.7	60.1	60.6	61.2	61.6	62.4
105°	76.0	76.3	76.7	77.1	77.5	77.9	78.3	78.7	79.2	79.6	80.0
107.5°	95.7	96.0	96.4	96.8	97.2	97.6	97.8	98.2	98.5	98.9	99.1
110°	109.2	109.6	110.0	110.4	110.7	111.0	111.2	111.5	111.7	112.0	112.2



TEST NUMBER: P333122-830

CATALOG NUMBER: S125DIP-S375D365U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	123.1	123.3	123.5	123.7	123.9	124.1	124.4	124.7	125.0	125.3	125.4
115°	143.5	143.8	144.2	144.5	144.8	145.0	145.2	145.2	145.4	145.6	145.5
117.5°	164.1	164.2	164.4	164.5	164.7	164.8	164.9	165.0	165.1	165.3	165.3
120°	176.9	177.3	177.7	178.0	178.3	178.6	178.7	178.7	178.8	178.9	178.9
122.5°	190.8	190.9	191.1	191.1	191.2	191.4	191.6	191.8	192.0	192.2	192.2
125°	209.5	210.0	210.5	210.8	211.3	211.6	211.7	211.7	211.8	211.9	211.7
127.5°	229.5	229.8	230.1	230.3	230.5	230.7	230.8	230.9	231.0	231.0	231.0
130°	241.5	241.9	242.2	242.6	243.0	243.3	243.4	243.6	243.7	243.8	243.7
132.5°	253.5	254.1	254.8	255.3	255.9	256.3	256.2	256.2	256.2	256.1	256.0
135°	272.5	273.0	273.4	273.8	274.3	274.6	274.7	274.7	274.8	274.8	274.8
137.5°	290.4	290.8	291.2	291.6	292.1	292.4	292.6	292.7	292.8	293.0	293.1
140°	301.8	302.2	302.6	302.9	303.3	303.6	303.8	304.1	304.3	304.4	304.6
142.5°	313.3	313.6	313.9	314.2	314.5	314.8	315.1	315.4	315.7	315.9	316.0
145°	330.2	330.5	330.7	331.0	331.3	331.6	331.8	332.1	332.2	332.4	332.4
147.5°	345.7	345.9	346.0	346.2	346.4	346.6	346.8	346.9	347.0	347.2	347.4
150°	356.1	356.1	356.0	355.9	355.8	355.9	356.2	356.6	356.8	357.1	357.1
152.5°	364.7	364.8	364.9	365.0	365.0	365.1	365.3	365.4	365.5	365.6	365.8
155°	377.8	377.8	377.8	377.8	377.8	377.8	377.9	378.0	378.1	378.1	378.4
157.5°	389.5	389.4	389.2	389.0	388.9	388.8	388.9	389.0	389.0	389.1	389.4
160°	396.4	396.2	396.0	395.8	395.6	395.5	395.6	395.6	395.7	395.8	396.1
162.5°	402.6	402.4	402.3	402.1	401.9	401.8	401.8	401.9	401.9	401.9	402.3
165°	410.8	410.6	410.5	410.3	410.2	410.1	410.2	410.3	410.4	410.4	410.8
167.5°	417.6	417.4	417.1	416.8	416.5	416.3	416.3	416.3	416.3	416.3	416.8
170°	421.4	421.1	420.8	420.6	420.2	420.1	420.1	420.1	420.1	420.1	420.6
172.5°	424.0	423.8	423.5	423.2	422.9	422.7	422.7	422.7	422.7	422.7	423.2
175°	427.1	426.8	426.5	426.2	425.9	425.7	425.7	425.7	425.7	425.7	426.2
177.5°	428.6	428.4	428.1	427.9	427.6	427.5	427.4	427.4	427.3	427.3	427.6
180°	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1



TEST NUMBER: P333122-830

CATALOG NUMBER: S125DIP-S375D365U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	550.6	550.6	550.6	550.6	550.6	550.6	550.6	550.6
2.5°	549.0	549.8	550.5	550.9	550.8	550.7	550.7	550.6
5°	546.2	547.1	548.0	548.4	548.3	548.2	548.1	548.0
7.5°	540.7	541.6	542.4	542.8	542.7	542.6	542.5	542.4
10°	536.0	536.8	537.6	537.9	537.8	537.7	537.6	537.5
12.5°	529.8	530.5	531.0	531.3	531.3	531.3	531.3	531.2
15°	518.9	519.3	519.9	520.1	520.1	520.1	520.1	520.1
17.5°	506.2	506.8	507.5	507.5	507.0	506.5	506.1	505.6
20°	496.6	497.3	497.9	498.1	497.6	497.1	496.6	496.2
22.5°	485.7	486.2	486.6	486.6	486.4	486.0	485.7	485.3
25°	468.3	468.4	468.6	468.5	468.3	468.0	467.7	467.4
27.5°	449.9	449.9	450.0	449.9	449.5	449.2	448.9	448.7
30°	436.5	436.3	436.1	435.9	435.6	435.4	435.0	434.7
32.5°	423.0	422.6	422.3	421.9	421.3	420.8	420.3	419.7
35°	402.0	401.5	401.0	400.4	399.6	398.8	398.0	397.3
37.5°	379.9	379.2	378.4	377.9	377.4	377.0	376.5	376.1
40°	364.6	363.7	362.9	362.3	362.0	361.7	361.4	361.1
42.5°	349.4	348.6	347.8	347.2	346.8	346.3	345.9	345.4
45°	327.0	325.8	324.7	324.0	323.7	323.4	323.1	322.8
47.5°	303.3	302.2	301.0	300.0	299.4	298.7	298.0	297.4
50°	287.2	285.9	284.6	283.7	283.0	282.3	281.6	281.0
52.5°	271.5	270.3	269.2	268.3	267.6	266.8	266.1	265.3
55°	246.9	246.1	245.2	244.5	243.8	243.1	242.4	241.8
57.5°	222.7	221.6	220.5	219.7	219.3	219.0	218.6	218.2
60°	206.3	205.3	204.3	203.5	202.8	202.2	201.5	200.9
62.5°	190.5	189.4	188.3	187.6	187.1	186.5	186.0	185.5
65°	165.5	164.7	163.8	163.2	162.8	162.4	162.0	161.6
67.5°	141.8	141.0	140.3	139.8	139.6	139.3	139.1	138.8
70°	126.0	125.5	124.9	124.4	124.0	123.7	123.2	122.8
72.5°	111.2	110.6	109.9	109.4	109.1	108.7	108.2	107.8
75°	88.3	88.0	87.7	87.4	87.0	86.6	86.2	85.8
77.5°	67.3	67.1	66.9	66.7	66.4	66.2	65.9	65.6
80°	53.8	53.7	53.6	53.4	53.3	53.1	52.9	52.7
82.5°	41.1	40.9	40.8	40.6	40.6	40.6	40.5	40.5
85°	24.2	24.1	24.0	23.8	23.7	23.5	23.3	23.1
87.5°	10.3	10.4	10.5	10.4	10.3	10.2	10.1	10.0
90°	6.0	6.4	6.8	7.1	7.4	7.5	7.7	8.0
92.5°	13.8	14.2	14.7	15.1	15.3	15.4	15.6	15.7
95°	26.7	27.2	27.7	28.1	28.2	28.4	28.5	28.7
97.5°	41.8	42.3	42.8	43.1	43.2	43.3	43.4	43.5
100°	52.3	53.0	53.6	54.0	54.2	54.4	54.5	54.7
102.5°	63.1	63.8	64.6	65.0	65.2	65.4	65.6	65.8
105°	80.5	81.0	81.4	81.7	81.9	82.2	82.4	82.7
107.5°	99.3	99.5	99.7	99.9	99.8	99.8	99.8	99.8
110°	112.4	112.6	112.8	112.9	112.8	112.7	112.6	112.6





TEST NUMBER: P333122-830

CATALOG NUMBER: S125DIP-S375D365U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	125.5	125.5	125.6	125.6	125.5	125.4	125.3	125.2
115°	145.4	145.3	145.2	145.2	145.2	145.1	145.0	144.9
117.5°	165.4	165.5	165.5	165.4	165.1	164.9	164.6	164.2
120°	178.9	178.9	178.9	178.7	178.4	178.1	177.9	177.6
122.5°	192.1	192.0	192.0	191.8	191.6	191.3	191.1	190.9
125°	211.6	211.4	211.3	211.1	211.1	211.0	210.9	210.8
127.5°	230.9	230.8	230.7	230.6	230.5	230.4	230.2	230.1
130°	243.7	243.6	243.6	243.5	243.3	243.2	243.0	242.9
132.5°	256.0	255.9	255.8	255.7	255.4	255.2	255.1	254.9
135°	274.8	274.8	274.8	274.7	274.4	274.1	273.8	273.5
137.5°	293.2	293.3	293.4	293.2	292.8	292.5	292.1	291.7
140°	304.8	304.9	305.1	305.0	304.6	304.3	303.9	303.5
142.5°	316.1	316.2	316.3	316.1	315.8	315.4	315.1	314.7
145°	332.4	332.4	332.4	332.3	332.2	331.9	331.7	331.5
147.5°	347.6	347.8	348.0	347.8	347.3	346.8	346.3	345.8
150°	357.1	357.1	357.1	357.0	356.9	356.8	356.6	356.5
152.5°	366.0	366.2	366.4	366.3	366.1	365.8	365.5	365.2
155°	378.7	379.0	379.3	379.3	378.9	378.5	378.1	377.8
157.5°	389.6	390.0	390.3	390.2	389.7	389.2	388.7	388.2
160°	396.3	396.6	396.9	396.9	396.5	396.2	395.8	395.4
162.5°	402.6	402.9	403.3	403.3	402.8	402.4	402.0	401.5
165°	411.0	411.3	411.6	411.5	411.0	410.7	410.2	409.7
167.5°	417.3	417.6	418.1	418.1	417.6	417.2	416.7	416.3
170°	420.9	421.4	421.9	421.8	421.3	420.8	420.3	419.7
172.5°	423.7	424.0	424.5	424.5	424.0	423.6	423.1	422.6
175°	426.6	427.1	427.5	427.4	427.0	426.4	425.9	425.4
177.5°	428.0	428.4	428.7	428.7	428.3	427.8	427.4	427.0
180°	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1

(END OF REPORT)