

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333184-935

Luminaire Tested: **S125DIP-S610D810U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333184-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S610D810U935-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4942.9 lumens
Efficiency: N/A
Efficacy: 128.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333184-935

CATALOG NUMBER: S125DIP-S610D810U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333184-935

CATALOG NUMBER: S125DIP-S610D810U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44
1	96	92	88	85	88	84	81	78	70	67	65	57	55	53	44	43	42	37
2	88	80	74	69	80	74	68	64	61	57	54	50	47	45	39	37	36	31
3	80	71	63	57	73	65	58	53	54	49	45	44	40	38	34	32	30	26
4	73	62	55	49	67	57	50	45	48	43	39	39	35	32	31	28	26	22
5	67	55	47	41	61	51	44	39	43	37	33	35	31	28	28	25	23	19
6	62	50	42	36	56	46	39	34	38	33	29	32	27	24	25	22	20	17
7	57	45	37	31	52	41	34	29	35	29	25	29	25	22	23	20	18	15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	27	22	18	22	18	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5340	5340	5340
5°	5352	5301	5335
10°	5319	5264	5294
15°	5262	5201	5223
20°	5179	5112	5121
25°	5091	5007	5002
30°	4981	4894	4869
35°	4864	4771	4704
40°	4743	4639	4572
45°	4613	4517	4427
50°	4470	4372	4240
55°	4332	4206	4088
60°	4166	4039	3896
65°	3969	3839	3709
70°	3780	3609	3484
75°	3444	3331	3216
80°	3065	3016	2942
85°	2668	2712	2571



TEST NUMBER: P333184-935

CATALOG NUMBER: S125DIP-S610D810U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.0	1.6
10°-20°	220.2	4.5
20°-30°	325.2	6.6
30°-40°	379.4	7.7
40°-50°	381.1	7.7
50°-60°	334.5	6.8
60°-70°	249.3	5.0
70°-80°	142.5	2.9
80°-90°	43.4	0.9
90°-100°	33.0	0.7
100°-110°	203.4	4.1
110°-120°	369.0	7.5
120°-130°	473.5	9.6
130°-140°	509.3	10.3
140°-150°	478.1	9.7
150°-160°	386.7	7.8
160°-170°	250.1	5.1
170°-180°	86.3	1.7
0°-30°	623.4	12.6
0°-40°	1002.8	20.3
0°-60°	1718.4	34.8
0°-90°	2153.6	43.6
90°-120°	605.4	12.2
90°-150°	2066.3	41.8
90°-180°	2789.0	56.4
0°-180°	4942.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	827	827	827	827	827	
5°	826	824	818	823	823	78
15°	787	785	778	781	781	222
25°	714	711	703	704	702	329
35°	617	614	605	602	597	386
45°	505	502	495	487	485	389
55°	385	382	374	368	363	343
65°	260	258	251	246	243	258
75°	138	137	134	131	129	147
85°	36	37	37	36	35	40
90°	1	6	11	14	16	4
95°	38	35	11	14	14	49
105°	198	200	201	201	200	210
115°	372	375	376	373	369	368
125°	529	533	533	531	529	472
135°	659	663	662	660	656	508
145°	764	766	766	766	762	478
155°	842	838	839	841	836	388
165°	888	884	885	888	883	251
175°	908	905	905	910	904	86
180°	908	908	908	908	908	



TEST NUMBER: P333184-935

CATALOG NUMBER: S125DIP-S610D810U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9
2.5°	829.0	828.6	828.3	827.9	827.6	826.8	825.7	824.5	823.4	822.2	823.4
5°	825.6	825.3	825.0	824.7	824.4	823.5	822.1	820.6	819.2	817.7	819.1
7.5°	817.9	817.7	817.4	817.1	816.8	815.9	814.2	812.7	811.1	809.5	810.7
10°	811.1	810.9	810.6	810.3	810.0	809.1	807.4	805.9	804.3	802.7	803.8
12.5°	802.8	802.3	801.8	801.2	800.7	799.7	798.2	796.8	795.2	793.8	794.7
15°	787.0	786.5	786.1	785.7	785.2	784.2	782.6	781.0	779.4	777.8	778.5
17.5°	768.8	768.2	767.5	766.9	766.2	765.1	763.4	761.7	760.1	758.5	759.3
20°	753.6	753.3	753.0	752.8	752.4	751.4	749.5	747.6	745.7	743.8	744.9
22.5°	738.4	737.9	737.4	736.8	736.3	735.2	733.4	731.7	729.9	728.1	728.8
25°	714.4	713.6	712.9	712.2	711.4	710.2	708.3	706.4	704.5	702.6	702.9
27.5°	686.2	685.8	685.4	684.9	684.5	683.3	681.3	679.4	677.4	675.5	675.5
30°	667.9	667.4	667.0	666.6	666.2	664.9	662.7	660.5	658.3	656.2	655.8
32.5°	648.0	647.4	646.7	646.0	645.3	644.0	642.1	640.2	638.2	636.3	635.8
35°	616.9	616.3	615.7	615.2	614.6	613.3	611.2	609.2	607.2	605.1	604.4
37.5°	584.5	583.8	583.2	582.4	581.7	580.3	578.4	576.5	574.5	572.7	571.6
40°	562.6	561.9	561.1	560.4	559.6	558.3	556.3	554.2	552.2	550.2	548.9
42.5°	539.1	538.5	537.8	537.2	536.6	535.3	533.2	531.2	529.2	527.1	526.0
45°	505.1	504.5	503.9	503.3	502.7	501.5	499.8	498.1	496.3	494.6	492.8
47.5°	468.4	468.4	468.5	468.5	468.5	467.4	465.4	463.3	461.2	459.1	457.4
50°	444.9	444.4	443.9	443.5	443.1	442.0	440.2	438.5	436.8	435.1	433.2
52.5°	420.8	420.4	420.2	419.8	419.5	418.4	416.6	414.7	412.8	411.0	409.3
55°	384.7	384.2	383.7	383.3	382.9	381.7	379.6	377.6	375.6	373.5	372.2
57.5°	346.6	346.4	346.1	345.9	345.7	344.7	342.9	341.2	339.5	337.9	336.1
60°	322.5	321.9	321.3	320.7	320.2	319.1	317.5	315.9	314.3	312.7	311.3
62.5°	297.4	297.0	296.4	296.0	295.5	294.6	293.3	291.9	290.5	289.1	287.6
65°	259.7	259.4	259.2	258.8	258.6	257.6	256.0	254.4	252.8	251.2	249.9
67.5°	223.2	222.6	222.0	221.4	220.8	219.9	218.7	217.5	216.3	215.1	214.0
70°	200.2	199.5	198.7	198.0	197.3	196.2	194.9	193.6	192.3	191.1	190.1
72.5°	175.0	174.5	174.1	173.6	173.1	172.4	171.6	170.7	169.9	169.0	168.1
75°	138.0	137.8	137.4	137.2	136.9	136.4	135.6	134.9	134.1	133.5	133.0
77.5°	103.9	103.8	103.7	103.5	103.4	103.1	102.7	102.4	101.9	101.5	101.3
80°	82.4	82.4	82.4	82.4	82.4	82.3	82.0	81.7	81.5	81.1	80.9
82.5°	63.6	63.4	63.1	62.9	62.7	62.5	62.4	62.4	62.3	62.3	62.0
85°	36.0	36.2	36.2	36.4	36.6	36.6	36.6	36.6	36.6	36.6	36.5
87.5°	14.3	14.5	14.7	15.0	15.2	15.4	15.5	15.6	15.7	15.8	15.9
90°	0.7	1.9	3.1	4.3	5.4	6.5	7.7	8.7	9.7	10.8	11.5
92.5°	10.3	9.6	8.7	7.8	7.1	7.1	8.0	9.0	9.8	10.8	11.5
95°	38.4	38.0	37.5	37.0	36.6	33.5	27.8	22.1	16.4	10.8	11.5
97.5°	80.2	80.9	81.7	82.6	83.3	78.2	66.9	55.6	44.3	33.1	28.9
100°	112.4	112.9	113.3	113.8	114.3	114.8	115.4	116.0	116.6	117.2	94.9
102.5°	145.3	145.9	146.5	147.0	147.6	148.0	148.4	148.8	149.1	149.5	145.3
105°	197.9	198.5	199.1	199.8	200.4	200.6	200.6	200.6	200.6	200.6	200.6
107.5°	252.6	252.6	252.6	252.6	252.6	252.8	253.0	253.4	253.7	254.0	254.0
110°	288.2	288.2	288.2	288.2	288.2	288.3	288.6	289.0	289.2	289.6	289.1



TEST NUMBER: P333184-935

CATALOG NUMBER: S125DIP-S610D810U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	321.6	321.9	322.3	322.7	323.0	323.3	323.5	323.6	323.8	324.0	323.5
115°	371.7	372.5	373.2	373.9	374.7	375.1	375.3	375.4	375.6	375.7	375.1
117.5°	423.5	423.5	423.4	423.4	423.4	423.7	424.2	424.8	425.4	425.9	425.2
120°	455.8	455.7	455.6	455.4	455.2	455.4	455.8	456.3	456.8	457.2	456.9
122.5°	484.4	485.0	485.5	486.1	486.6	487.1	487.2	487.5	487.7	487.9	487.6
125°	528.6	529.6	530.6	531.8	532.8	533.3	533.3	533.3	533.3	533.3	532.7
127.5°	570.8	571.4	572.2	573.0	573.7	574.0	573.9	573.9	573.8	573.7	573.3
130°	596.6	597.4	598.1	598.8	599.6	600.0	600.2	600.3	600.5	600.6	600.2
132.5°	622.4	623.3	624.1	625.0	625.9	626.2	625.9	625.5	625.2	624.8	624.7
135°	659.2	660.1	661.0	661.9	662.8	663.1	662.8	662.5	662.2	661.9	661.6
137.5°	693.0	693.8	694.6	695.3	696.1	696.4	696.1	695.9	695.6	695.3	695.3
140°	715.1	715.4	715.7	716.0	716.3	716.4	716.2	716.1	715.9	715.7	716.1
142.5°	735.0	735.2	735.4	735.6	735.7	735.9	736.2	736.3	736.6	736.8	736.8
145°	764.2	764.6	764.8	765.2	765.4	765.6	765.6	765.6	765.6	765.6	765.8
147.5°	789.8	789.8	789.7	789.6	789.6	789.6	789.8	790.0	790.2	790.4	790.6
150°	806.0	805.7	805.4	805.1	804.8	804.8	805.1	805.4	805.7	806.0	806.3
152.5°	821.7	821.0	820.3	819.7	819.0	818.8	819.1	819.4	819.7	820.0	820.3
155°	841.7	840.8	839.9	839.0	838.1	837.8	838.1	838.4	838.7	839.0	839.4
157.5°	857.1	856.6	856.1	855.6	855.0	854.7	854.8	854.8	854.8	854.9	855.3
160°	868.0	867.0	866.2	865.2	864.4	864.0	864.1	864.3	864.4	864.5	865.1
162.5°	876.6	875.6	874.8	873.8	873.0	872.6	872.7	872.9	873.1	873.2	874.0
165°	888.1	887.3	886.3	885.5	884.5	884.2	884.3	884.5	884.6	884.8	885.7
167.5°	896.7	895.9	894.9	894.0	893.0	892.7	892.8	892.9	893.1	893.3	894.3
170°	901.6	900.5	899.5	898.5	897.4	897.0	897.1	897.2	897.4	897.6	898.8
172.5°	904.8	903.8	902.8	901.7	900.6	900.3	900.5	900.8	901.0	901.3	902.4
175°	908.4	907.4	906.5	905.7	904.7	904.4	904.5	904.7	904.8	905.0	906.2
177.5°	910.0	909.2	908.5	907.8	907.1	906.8	906.9	907.0	907.1	907.2	908.1
180°	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4



TEST NUMBER: P333184-935

CATALOG NUMBER: S125DIP-S610D810U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9
2.5°	824.5	825.7	826.8	827.3	827.2	827.1	827.0	826.9
5°	820.4	821.7	822.9	823.5	823.4	823.3	823.1	822.9
7.5°	812.0	813.3	814.6	815.2	815.0	814.9	814.8	814.6
10°	805.0	806.2	807.4	807.9	807.7	807.5	807.4	807.3
12.5°	795.7	796.6	797.5	798.0	797.9	797.9	797.9	797.8
15°	779.3	780.0	780.8	781.1	781.1	781.1	781.1	781.1
17.5°	760.3	761.1	762.1	762.2	761.4	760.7	760.0	759.2
20°	745.8	746.8	747.9	748.0	747.3	746.6	745.8	745.1
22.5°	729.4	730.1	730.8	730.9	730.4	729.9	729.4	728.9
25°	703.2	703.4	703.8	703.7	703.3	702.8	702.4	702.0
27.5°	675.6	675.7	675.7	675.5	675.1	674.7	674.2	673.8
30°	655.6	655.3	655.0	654.6	654.2	653.8	653.3	652.9
32.5°	635.2	634.6	634.1	633.5	632.7	632.0	631.1	630.3
35°	603.6	603.0	602.2	601.2	600.1	598.9	597.8	596.6
37.5°	570.5	569.5	568.3	567.5	566.8	566.2	565.5	564.8
40°	547.5	546.2	544.9	544.1	543.6	543.2	542.8	542.3
42.5°	524.8	523.6	522.4	521.4	520.7	520.1	519.4	518.8
45°	491.0	489.3	487.6	486.5	486.0	485.6	485.2	484.7
47.5°	455.6	453.7	452.0	450.6	449.6	448.6	447.5	446.5
50°	431.3	429.4	427.5	426.0	425.0	424.0	422.9	422.0
52.5°	407.6	406.0	404.3	402.9	401.8	400.6	399.5	398.4
55°	370.9	369.6	368.3	367.1	366.1	365.1	364.1	363.1
57.5°	334.4	332.8	331.1	329.9	329.4	328.8	328.3	327.8
60°	309.8	308.3	306.9	305.7	304.6	303.6	302.6	301.6
62.5°	286.0	284.5	282.8	281.7	280.9	280.1	279.3	278.5
65°	248.6	247.3	246.0	245.0	244.4	243.8	243.3	242.7
67.5°	212.9	211.8	210.7	209.9	209.6	209.2	208.9	208.5
70°	189.2	188.4	187.5	186.8	186.2	185.6	185.0	184.5
72.5°	167.0	166.1	165.1	164.3	163.7	163.2	162.6	162.0
75°	132.6	132.2	131.7	131.2	130.6	130.0	129.5	128.9
77.5°	101.0	100.7	100.5	100.1	99.7	99.4	98.9	98.5
80°	80.8	80.7	80.5	80.3	80.0	79.7	79.5	79.1
82.5°	61.7	61.5	61.2	61.0	61.0	61.0	60.9	60.9
85°	36.3	36.2	36.1	35.8	35.6	35.2	35.0	34.7
87.5°	16.1	16.2	16.4	16.4	16.2	16.1	15.9	15.8
90°	12.3	13.0	13.8	14.4	14.8	15.2	15.7	16.2
92.5°	12.3	13.0	13.8	14.2	14.5	14.6	14.9	15.1
95°	12.3	13.0	13.8	14.1	14.1	14.1	14.1	14.1
97.5°	24.7	20.5	16.3	14.1	14.1	14.1	14.1	14.1
100°	72.6	50.3	28.0	16.5	15.9	15.3	14.7	14.1
102.5°	141.0	136.8	132.6	125.4	115.2	105.0	94.9	84.7
105°	200.6	200.6	200.6	200.6	200.4	200.3	200.1	200.0
107.5°	254.1	254.1	254.1	253.9	253.5	253.0	252.5	252.1
110°	288.6	288.2	287.7	287.6	287.7	287.9	288.0	288.2



TEST NUMBER: P333184-935

CATALOG NUMBER: S125DIP-S610D810U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	322.9	322.3	321.8	321.3	321.2	320.9	320.7	320.6
115°	374.5	373.9	373.3	372.6	371.7	370.7	369.9	369.0
117.5°	424.4	423.6	422.8	422.2	421.9	421.5	421.1	420.7
120°	456.6	456.3	456.0	455.5	454.7	454.0	453.2	452.5
122.5°	487.3	487.0	486.7	486.1	485.3	484.4	483.5	482.7
125°	532.1	531.5	530.9	530.4	529.9	529.4	529.0	528.6
127.5°	573.0	572.7	572.4	571.6	570.6	569.5	568.3	567.2
130°	599.7	599.3	598.8	598.2	597.4	596.8	596.0	595.2
132.5°	624.7	624.6	624.5	624.1	623.4	622.6	621.8	621.1
135°	661.3	661.0	660.7	660.1	659.2	658.3	657.4	656.5
137.5°	695.4	695.4	695.5	695.2	694.4	693.6	692.8	692.1
140°	716.4	716.7	717.0	716.7	715.7	714.9	713.9	713.1
142.5°	736.9	736.9	737.0	736.6	735.7	734.8	733.9	733.0
145°	765.9	766.0	766.2	765.8	764.9	764.1	763.1	762.2
147.5°	790.7	790.9	791.1	790.7	789.5	788.5	787.4	786.4
150°	806.6	806.9	807.2	806.8	805.6	804.3	803.1	801.9
152.5°	820.6	820.9	821.2	820.8	819.8	818.6	817.6	816.5
155°	839.9	840.3	840.8	840.4	839.2	838.0	836.8	835.6
157.5°	855.8	856.4	856.8	856.4	855.2	854.0	852.8	851.6
160°	865.7	866.3	866.9	866.7	865.5	864.3	863.1	861.9
162.5°	874.9	875.7	876.5	876.3	874.9	873.7	872.4	871.1
165°	886.6	887.4	888.4	888.2	887.0	885.8	884.6	883.4
167.5°	895.4	896.5	897.6	897.4	896.0	894.8	893.4	892.1
170°	899.9	901.1	902.3	902.2	901.0	899.6	898.2	896.9
172.5°	903.4	904.6	905.7	905.5	904.1	902.8	901.5	900.1
175°	907.3	908.5	909.7	909.6	908.4	907.0	905.7	904.3
177.5°	909.0	909.7	910.6	910.6	909.6	908.6	907.7	906.7
180°	908.4	908.4	908.4	908.4	908.4	908.4	908.4	908.4

(END OF REPORT)