

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333123-830

Luminaire Tested: **S125DIP-S375D365U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333123-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S375D365U830-4F0-1E-UDD-F4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2672.7 lumens  
Efficiency: N/A  
Efficacy: 131.7 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 20.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333123-830

CATALOG NUMBER: S125DIP-S375D365U830-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P333123-830

CATALOG NUMBER: S125DIP-S375D365U830-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	54
1	99	94	90	87	91	87	84	81	75	72	70	63	61	60	52	51	50	45
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42	38
3	82	72	65	59	76	67	61	55	58	53	49	49	45	42	41	38	36	32
4	75	64	56	50	69	60	52	47	51	46	41	44	39	36	36	33	31	27
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	30	27	24
6	63	51	43	37	58	48	40	35	41	36	31	35	31	27	30	26	24	21
7	59	46	38	32	54	43	36	31	38	32	27	32	28	24	27	24	21	18
8	54	42	34	29	50	39	32	27	34	29	24	29	25	22	25	21	19	17
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17	15
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3556	3556	3556
5°	3564	3530	3553
10°	3543	3505	3525
15°	3504	3463	3477
20°	3449	3404	3410
25°	3390	3334	3331
30°	3317	3258	3242
35°	3239	3177	3132
40°	3159	3089	3044
45°	3072	3008	2948
50°	2976	2910	2823
55°	2884	2800	2723
60°	2773	2689	2595
65°	2644	2557	2470
70°	2517	2402	2319
75°	2293	2218	2141
80°	2042	2008	1960
85°	1771	1808	1712



TEST NUMBER: P333123-830

CATALOG NUMBER: S125DIP-S375D365U830-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	51.9	1.9
10°-20°	146.6	5.5
20°-30°	216.5	8.1
30°-40°	252.7	9.5
40°-50°	253.8	9.5
50°-60°	222.8	8.3
60°-70°	166.0	6.2
70°-80°	94.9	3.6
80°-90°	28.5	1.1
90°-100°	119.8	4.5
100°-110°	257.4	9.6
110°-120°	241.6	9.0
120°-130°	195.8	7.3
130°-140°	157.1	5.9
140°-150°	118.6	4.4
150°-160°	83.5	3.1
160°-170°	49.2	1.8
170°-180°	16.0	0.6
0°-30°	415.1	15.5
0°-40°	667.8	25.0
0°-60°	1144.3	42.8
0°-90°	1433.7	53.6
90°-120°	618.8	23.2
90°-150°	1090.3	40.8
90°-180°	1239.0	46.4
0°-180°	2672.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	551	551	551	551	551	
5°	550	549	544	548	548	52
15°	524	522	518	520	520	148
25°	476	473	468	469	467	219
35°	411	409	403	401	397	257
45°	336	334	329	324	323	259
55°	256	255	249	245	242	229
65°	173	172	167	164	162	172
75°	92	91	89	88	86	98
85°	24	24	24	24	23	27
90°	0	3	5	7	8	2
95°	11	32	295	134	78	12
105°	38	53	242	476	441	40
115°	67	81	194	418	492	66
125°	93	109	186	332	387	83
135°	109	131	184	279	322	85
145°	127	146	185	231	254	80
155°	145	156	181	204	213	67
165°	158	163	173	184	186	45
175°	165	165	166	168	168	16
180°	165	165	165	165	165	



TEST NUMBER: P333123-830

CATALOG NUMBER: S125DIP-S375D365U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	550.6	550.6	550.6	550.6	550.6	550.6	550.6	550.6	550.6	550.6	550.6
2.5°	552.0	551.8	551.6	551.3	551.1	550.5	549.8	549.0	548.3	547.4	548.3
5°	549.7	549.5	549.3	549.1	548.9	548.4	547.4	546.5	545.4	544.5	545.4
7.5°	544.7	544.5	544.3	544.1	543.9	543.3	542.2	541.1	540.1	539.0	539.9
10°	540.2	540.0	539.8	539.6	539.4	538.8	537.7	536.6	535.6	534.5	535.3
12.5°	534.6	534.2	533.9	533.6	533.2	532.5	531.5	530.6	529.5	528.6	529.1
15°	524.1	523.8	523.5	523.2	522.8	522.2	521.1	520.1	519.0	517.9	518.4
17.5°	511.9	511.5	511.0	510.7	510.2	509.4	508.3	507.3	506.1	505.0	505.7
20°	501.8	501.6	501.4	501.2	501.1	500.3	499.1	497.8	496.5	495.3	496.0
22.5°	491.7	491.3	491.0	490.7	490.3	489.6	488.3	487.2	486.0	484.8	485.3
25°	475.7	475.2	474.7	474.2	473.7	472.9	471.6	470.3	469.1	467.9	468.1
27.5°	456.9	456.7	456.4	456.1	455.8	455.0	453.7	452.4	451.1	449.8	449.9
30°	444.8	444.5	444.1	443.8	443.6	442.7	441.3	439.8	438.4	436.9	436.7
32.5°	431.5	431.0	430.6	430.2	429.7	428.9	427.5	426.2	425.0	423.7	423.3
35°	410.8	410.4	410.0	409.6	409.3	408.3	407.0	405.7	404.3	402.9	402.5
37.5°	389.3	388.8	388.3	387.8	387.3	386.4	385.1	383.9	382.6	381.4	380.6
40°	374.7	374.1	373.6	373.2	372.7	371.7	370.4	369.1	367.7	366.4	365.5
42.5°	358.9	358.5	358.2	357.7	357.3	356.5	355.1	353.7	352.3	351.0	350.2
45°	336.3	335.9	335.5	335.2	334.7	333.9	332.8	331.7	330.5	329.3	328.2
47.5°	311.9	311.9	311.9	312.0	312.0	311.3	309.9	308.5	307.1	305.7	304.5
50°	296.2	296.0	295.7	295.3	295.0	294.4	293.1	292.0	290.9	289.6	288.4
52.5°	280.2	279.9	279.7	279.6	279.4	278.6	277.4	276.2	274.8	273.6	272.6
55°	256.1	255.8	255.5	255.2	255.0	254.1	252.8	251.5	250.1	248.7	247.9
57.5°	230.8	230.6	230.5	230.4	230.2	229.5	228.4	227.2	226.1	225.0	223.9
60°	214.7	214.3	214.0	213.6	213.2	212.4	211.4	210.4	209.2	208.2	207.3
62.5°	198.0	197.7	197.4	197.1	196.8	196.1	195.3	194.4	193.4	192.6	191.5
65°	173.0	172.8	172.6	172.4	172.2	171.5	170.5	169.4	168.3	167.3	166.4
67.5°	148.6	148.3	147.8	147.4	147.0	146.4	145.6	144.8	144.0	143.3	142.5
70°	133.3	132.8	132.3	131.9	131.4	130.6	129.8	128.9	128.1	127.2	126.6
72.5°	116.6	116.2	115.9	115.6	115.3	114.8	114.2	113.7	113.1	112.5	111.9
75°	91.9	91.7	91.5	91.3	91.1	90.8	90.3	89.8	89.4	88.9	88.6
77.5°	69.2	69.1	69.0	68.9	68.9	68.7	68.4	68.1	67.9	67.6	67.4
80°	54.9	54.9	54.9	54.9	54.9	54.8	54.6	54.4	54.2	54.0	53.9
82.5°	42.3	42.2	42.0	41.8	41.8	41.7	41.6	41.6	41.5	41.5	41.3
85°	23.9	24.0	24.1	24.2	24.3	24.4	24.4	24.4	24.4	24.4	24.3
87.5°	9.5	9.5	9.7	9.8	9.9	10.0	10.0	10.1	10.1	10.1	10.2
90°	0.4	0.7	1.3	2.0	2.6	3.3	3.7	4.3	4.6	5.4	5.7
92.5°	4.1	4.9	7.7	11.9	17.6	27.3	45.5	76.0	109.1	107.4	86.9
95°	11.0	11.3	13.9	17.6	25.0	40.0	75.6	148.9	240.8	295.1	288.8
97.5°	18.3	18.7	20.5	24.2	30.8	41.6	65.1	118.9	215.1	315.2	365.4
100°	23.3	23.9	25.4	28.9	35.3	45.3	64.7	107.9	191.9	300.8	384.1
102.5°	28.9	29.3	30.3	34.3	40.2	49.9	67.0	103.4	174.3	275.5	372.9
105°	37.6	37.6	39.3	42.6	48.0	57.3	71.9	101.6	157.2	241.5	337.1
107.5°	46.2	46.8	48.4	51.2	56.7	65.1	79.3	104.6	150.1	218.1	300.6
110°	52.3	53.0	54.3	57.3	62.3	71.0	84.6	107.6	147.9	207.2	279.8



TEST NUMBER: P333123-830

CATALOG NUMBER: S125DIP-S375D365U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	58.4	59.1	60.1	63.2	68.1	76.5	89.6	111.3	147.9	200.8	264.4
115°	67.3	68.0	69.0	71.9	76.9	85.3	97.6	116.9	148.9	193.9	247.5
117.5°	75.3	76.3	77.4	80.3	86.1	94.1	105.8	123.3	151.1	190.5	237.4
120°	80.6	81.6	82.9	86.0	91.6	99.9	111.6	127.6	153.3	188.9	231.9
122.5°	86.2	86.9	88.0	91.0	97.2	105.6	117.2	132.3	155.0	187.6	227.1
125°	93.3	94.0	95.6	98.6	104.9	113.6	124.6	138.9	158.3	185.9	220.6
127.5°	98.8	99.8	101.9	105.8	112.4	121.1	131.7	144.9	161.7	185.1	214.5
130°	102.3	103.3	105.9	110.3	117.3	125.9	136.2	148.9	163.9	184.5	210.6
132.5°	104.9	106.2	109.4	114.2	121.5	130.2	140.5	152.4	166.3	184.5	207.4
135°	109.2	110.6	114.6	119.9	127.0	135.9	146.2	157.2	169.6	184.5	203.5
137.5°	114.7	115.7	119.4	124.8	131.7	140.9	150.3	160.8	172.6	184.9	200.1
140°	117.9	118.9	122.9	128.3	134.6	143.5	153.3	163.2	173.9	185.2	198.5
142.5°	121.7	122.3	126.1	131.5	137.5	146.0	155.0	164.6	174.7	185.5	197.2
145°	127.2	127.9	131.2	135.9	141.9	149.6	158.3	166.5	175.5	185.2	195.2
147.5°	133.1	133.5	136.4	140.7	145.9	152.6	160.2	167.8	175.9	184.4	193.1
150°	136.6	137.2	139.6	143.9	148.5	154.2	161.6	168.5	175.9	183.5	191.5
152.5°	140.3	140.7	142.8	146.6	151.0	156.1	162.9	169.1	175.6	182.5	189.6
155°	145.2	145.2	147.2	150.5	153.9	158.5	164.2	169.6	174.8	180.6	186.5
157.5°	149.7	149.6	151.2	154.0	156.9	160.5	165.3	169.8	174.0	178.5	183.6
160°	152.6	152.2	153.5	155.9	158.5	161.6	165.9	169.8	173.2	177.2	181.3
162.5°	155.0	154.7	156.0	158.1	160.1	162.6	166.5	169.7	172.4	175.6	179.1
165°	158.5	157.9	158.9	160.5	161.9	163.9	166.5	169.2	171.3	173.2	175.9
167.5°	161.0	160.6	161.3	162.1	163.1	164.4	166.5	168.4	169.4	170.9	172.8
170°	162.6	162.2	162.6	163.2	163.9	164.9	166.5	167.9	168.5	169.6	170.9
172.5°	163.6	163.1	163.3	164.0	164.4	164.9	166.3	167.4	167.5	168.0	169.0
175°	164.9	164.2	164.6	164.9	164.9	164.9	165.9	166.5	166.3	166.3	166.5
177.5°	165.5	164.9	164.9	165.2	164.9	164.9	165.5	165.8	165.2	165.2	165.5
180°	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2



TEST NUMBER: P333123-830

CATALOG NUMBER: S125DIP-S375D365U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	550.6	550.6	550.6	550.6	550.6	550.6	550.6	550.6
2.5°	549.0	549.8	550.5	550.9	550.8	550.7	550.7	550.6
5°	546.2	547.1	548.0	548.4	548.3	548.2	548.1	548.0
7.5°	540.7	541.6	542.4	542.8	542.7	542.6	542.5	542.4
10°	536.0	536.8	537.6	537.9	537.8	537.7	537.6	537.5
12.5°	529.8	530.5	531.0	531.3	531.3	531.3	531.3	531.2
15°	518.9	519.3	519.9	520.1	520.1	520.1	520.1	520.1
17.5°	506.2	506.8	507.5	507.5	507.0	506.5	506.1	505.6
20°	496.6	497.3	497.9	498.1	497.6	497.1	496.6	496.2
22.5°	485.7	486.2	486.6	486.6	486.4	486.0	485.7	485.3
25°	468.3	468.4	468.6	468.5	468.3	468.0	467.7	467.4
27.5°	449.9	449.9	450.0	449.9	449.5	449.2	448.9	448.7
30°	436.5	436.3	436.1	435.9	435.6	435.4	435.0	434.7
32.5°	423.0	422.6	422.3	421.9	421.3	420.8	420.3	419.7
35°	402.0	401.5	401.0	400.4	399.6	398.8	398.0	397.3
37.5°	379.9	379.2	378.4	377.9	377.4	377.0	376.5	376.1
40°	364.6	363.7	362.9	362.3	362.0	361.7	361.4	361.1
42.5°	349.4	348.6	347.8	347.2	346.8	346.3	345.9	345.4
45°	327.0	325.8	324.7	324.0	323.7	323.4	323.1	322.8
47.5°	303.3	302.2	301.0	300.0	299.4	298.7	298.0	297.4
50°	287.2	285.9	284.6	283.7	283.0	282.3	281.6	281.0
52.5°	271.5	270.3	269.2	268.3	267.6	266.8	266.1	265.3
55°	246.9	246.1	245.2	244.5	243.8	243.1	242.4	241.8
57.5°	222.7	221.6	220.5	219.7	219.3	219.0	218.6	218.2
60°	206.3	205.3	204.3	203.5	202.8	202.2	201.5	200.9
62.5°	190.5	189.4	188.3	187.6	187.1	186.5	186.0	185.5
65°	165.5	164.7	163.8	163.2	162.8	162.4	162.0	161.6
67.5°	141.8	141.0	140.3	139.8	139.6	139.3	139.1	138.8
70°	126.0	125.5	124.9	124.4	124.0	123.7	123.2	122.8
72.5°	111.2	110.6	109.9	109.4	109.1	108.7	108.2	107.8
75°	88.3	88.0	87.7	87.4	87.0	86.6	86.2	85.8
77.5°	67.3	67.1	66.9	66.7	66.4	66.2	65.9	65.6
80°	53.8	53.7	53.6	53.4	53.3	53.1	52.9	52.7
82.5°	41.1	40.9	40.8	40.6	40.6	40.6	40.5	40.5
85°	24.2	24.1	24.0	23.8	23.7	23.5	23.3	23.1
87.5°	10.3	10.4	10.4	10.5	10.3	10.2	10.1	9.9
90°	6.0	6.3	6.7	7.4	7.4	7.4	7.6	7.6
92.5°	59.0	42.8	32.2	27.3	23.1	22.2	21.8	21.2
95°	239.5	188.9	147.9	119.9	96.2	86.2	83.6	78.3
97.5°	356.7	321.2	281.3	242.3	221.8	203.1	193.5	189.2
100°	409.7	393.4	359.1	324.4	301.4	277.5	265.1	259.9
102.5°	427.5	437.6	421.2	397.8	373.2	356.1	342.7	338.7
105°	417.1	462.7	477.3	473.7	463.0	452.0	445.4	441.4
107.5°	379.5	440.4	478.0	495.4	500.8	500.8	498.5	495.9
110°	351.8	415.1	462.0	490.3	505.3	511.6	514.0	514.0





TEST NUMBER: P333123-830

CATALOG NUMBER: S125DIP-S375D365U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	329.9	390.0	437.5	470.9	492.8	503.7	509.4	511.9
115°	302.5	354.1	399.7	436.0	462.0	478.0	487.3	491.6
117.5°	284.7	329.2	368.5	401.9	427.8	444.4	453.6	456.3
120°	275.1	315.1	351.8	381.1	405.8	421.7	430.7	433.4
122.5°	268.0	305.0	337.6	365.0	387.1	401.7	410.8	413.1
125°	257.5	291.4	320.5	344.4	363.1	376.7	384.1	387.4
127.5°	246.9	278.5	305.6	328.0	345.0	357.0	363.9	365.4
130°	240.2	269.5	295.5	317.2	333.8	344.8	351.5	353.5
132.5°	233.5	261.0	284.6	305.4	322.1	333.0	339.1	341.4
135°	224.9	247.8	269.2	288.1	302.8	313.8	319.8	321.8
137.5°	217.5	236.1	253.8	269.9	283.0	293.0	298.6	300.8
140°	213.5	229.1	244.5	258.4	270.8	279.5	284.5	286.2
142.5°	210.1	223.3	236.5	248.6	259.1	266.5	271.2	272.6
145°	205.6	215.8	226.2	235.2	243.2	248.8	252.5	253.8
147.5°	201.2	209.6	217.6	224.4	230.7	235.3	237.3	238.0
150°	198.9	206.2	212.5	218.5	223.5	227.5	228.8	229.1
152.5°	196.2	202.7	208.5	213.2	217.4	220.6	221.9	222.3
155°	192.2	197.6	202.2	205.9	209.2	211.5	212.5	212.8
157.5°	188.2	192.6	196.2	199.1	201.7	203.6	204.5	204.4
160°	185.6	188.9	192.2	194.5	196.9	198.5	199.2	198.9
162.5°	182.6	185.7	188.5	190.6	192.4	193.7	193.9	193.8
165°	178.5	180.9	182.9	184.5	185.9	186.5	186.5	186.5
167.5°	174.7	176.3	177.8	179.0	179.6	180.2	179.9	179.8
170°	172.6	173.5	174.6	175.2	175.9	176.3	176.3	175.9
172.5°	170.1	171.2	171.9	172.3	172.4	173.1	172.5	172.1
175°	167.6	167.6	168.2	168.2	168.2	168.5	167.9	167.6
177.5°	165.8	166.0	166.0	166.0	165.8	166.0	165.2	165.2
180°	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2

(END OF REPORT)