

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333185-935

Luminaire Tested: **S125DIP-S610D810U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333185-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S610D810U935-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4567.7 lumens  
Efficiency: N/A  
Efficacy: 119.0 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 38.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333185-935

CATALOG NUMBER: S125DIP-S610D810U935-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333185-935

CATALOG NUMBER: S125DIP-S610D810U935-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	54	54	54	47
1	97	93	89	85	89	85	82	79	72	69	67	59	57	56	47	46	45	40
2	88	81	75	70	81	75	69	65	63	59	55	52	49	46	41	40	38	33
3	81	71	64	58	74	66	59	54	55	50	47	46	42	39	37	34	32	28
4	74	63	55	49	67	58	51	46	49	44	40	41	37	34	33	30	28	24
5	68	56	48	42	62	52	45	39	44	38	34	36	32	29	30	27	24	21
6	62	50	42	36	57	47	39	34	39	34	30	33	29	25	27	24	21	18
7	58	45	37	32	53	42	35	30	36	30	26	30	26	22	24	21	19	16
8	53	41	33	28	49	38	31	26	33	27	23	27	23	20	22	19	17	15
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15	13
10	46	34	27	22	43	32	26	21	28	22	19	23	19	16	19	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5340	5340	5340
5°	5352	5301	5335
10°	5319	5264	5294
15°	5262	5201	5223
20°	5179	5112	5121
25°	5091	5007	5002
30°	4981	4894	4869
35°	4864	4771	4704
40°	4743	4639	4572
45°	4613	4517	4427
50°	4470	4372	4240
55°	4332	4206	4088
60°	4166	4039	3896
65°	3969	3839	3709
70°	3780	3609	3484
75°	3444	3331	3216
80°	3065	3016	2942
85°	2668	2712	2571



TEST NUMBER: P333185-935

CATALOG NUMBER: S125DIP-S610D810U935-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	78.0	1.7
10°-20°	220.2	4.8
20°-30°	325.2	7.1
30°-40°	379.4	8.3
40°-50°	381.1	8.3
50°-60°	334.5	7.3
60°-70°	249.3	5.5
70°-80°	142.5	3.1
80°-90°	43.4	0.9
90°-100°	57.9	1.3
100°-110°	171.1	3.7
110°-120°	289.8	6.3
120°-130°	381.4	8.4
130°-140°	427.4	9.4
140°-150°	418.9	9.2
150°-160°	351.8	7.7
160°-170°	233.9	5.1
170°-180°	81.8	1.8
0°-30°	623.4	13.6
0°-40°	1002.8	22.0
0°-60°	1718.4	37.6
0°-90°	2153.6	47.1
90°-120°	518.9	11.4
90°-150°	1746.6	38.2
90°-180°	2414.0	52.8
0°-180°	4567.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	827	827	827	827	827	
5°	826	824	818	823	823	78
15°	787	785	778	781	781	222
25°	714	711	703	704	702	329
35°	617	614	605	602	597	386
45°	505	502	495	487	485	389
55°	385	382	374	368	363	343
65°	260	258	251	246	243	258
75°	138	137	134	131	129	147
85°	36	37	37	36	35	40
90°	1	6	11	14	16	4
95°	44	45	52	56	58	47
105°	154	157	161	165	167	164
115°	290	293	294	294	293	287
125°	423	427	428	427	426	379
135°	551	555	555	555	553	424
145°	667	670	672	672	670	417
155°	763	763	764	766	763	351
165°	830	829	830	832	828	234
175°	863	861	860	864	860	82
180°	865	865	865	865	865	



TEST NUMBER: P333185-935

CATALOG NUMBER: S125DIP-S610D810U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9
2.5°	829.0	828.6	828.3	827.9	827.6	826.8	825.7	824.5	823.4	822.2	823.4
5°	825.6	825.3	825.0	824.7	824.4	823.5	822.1	820.6	819.2	817.7	819.1
7.5°	817.9	817.7	817.4	817.1	816.8	815.9	814.2	812.7	811.1	809.5	810.7
10°	811.1	810.9	810.6	810.3	810.0	809.1	807.4	805.9	804.3	802.7	803.8
12.5°	802.8	802.3	801.8	801.2	800.7	799.7	798.2	796.8	795.2	793.8	794.7
15°	787.0	786.5	786.1	785.7	785.2	784.2	782.6	781.0	779.4	777.8	778.5
17.5°	768.8	768.2	767.5	766.9	766.2	765.1	763.4	761.7	760.1	758.5	759.3
20°	753.6	753.3	753.0	752.8	752.4	751.4	749.5	747.6	745.7	743.8	744.9
22.5°	738.4	737.9	737.4	736.8	736.3	735.2	733.4	731.7	729.9	728.1	728.8
25°	714.4	713.6	712.9	712.2	711.4	710.2	708.3	706.4	704.5	702.6	702.9
27.5°	686.2	685.8	685.4	684.9	684.5	683.3	681.3	679.4	677.4	675.5	675.5
30°	667.9	667.4	667.0	666.6	666.2	664.9	662.7	660.5	658.3	656.2	655.8
32.5°	648.0	647.4	646.7	646.0	645.3	644.0	642.1	640.2	638.2	636.3	635.8
35°	616.9	616.3	615.7	615.2	614.6	613.3	611.2	609.2	607.2	605.1	604.4
37.5°	584.5	583.8	583.2	582.4	581.7	580.3	578.4	576.5	574.5	572.7	571.6
40°	562.6	561.9	561.1	560.4	559.6	558.3	556.3	554.2	552.2	550.2	548.9
42.5°	539.1	538.5	537.8	537.2	536.6	535.3	533.2	531.2	529.2	527.1	526.0
45°	505.1	504.5	503.9	503.3	502.7	501.5	499.8	498.1	496.3	494.6	492.8
47.5°	468.4	468.4	468.5	468.5	468.5	467.4	465.4	463.3	461.2	459.1	457.4
50°	444.9	444.4	443.9	443.5	443.1	442.0	440.2	438.5	436.8	435.1	433.2
52.5°	420.8	420.4	420.2	419.8	419.5	418.4	416.6	414.7	412.8	411.0	409.3
55°	384.7	384.2	383.7	383.3	382.9	381.7	379.6	377.6	375.6	373.5	372.2
57.5°	346.6	346.4	346.1	345.9	345.7	344.7	342.9	341.2	339.5	337.9	336.1
60°	322.5	321.9	321.3	320.7	320.2	319.1	317.5	315.9	314.3	312.7	311.3
62.5°	297.4	297.0	296.4	296.0	295.5	294.6	293.3	291.9	290.5	289.1	287.6
65°	259.7	259.4	259.2	258.8	258.6	257.6	256.0	254.4	252.8	251.2	249.9
67.5°	223.2	222.6	222.0	221.4	220.8	219.9	218.7	217.5	216.3	215.1	214.0
70°	200.2	199.5	198.7	198.0	197.3	196.2	194.9	193.6	192.3	191.1	190.1
72.5°	175.0	174.5	174.1	173.6	173.1	172.4	171.6	170.7	169.9	169.0	168.1
75°	138.0	137.8	137.4	137.2	136.9	136.4	135.6	134.9	134.1	133.5	133.0
77.5°	103.9	103.8	103.7	103.5	103.4	103.1	102.7	102.4	101.9	101.5	101.3
80°	82.4	82.4	82.4	82.4	82.4	82.3	82.0	81.7	81.5	81.1	80.9
82.5°	63.6	63.4	63.1	62.9	62.7	62.5	62.4	62.4	62.3	62.3	62.0
85°	36.0	36.2	36.2	36.4	36.6	36.6	36.6	36.6	36.6	36.6	36.5
87.5°	14.3	14.5	14.7	15.0	15.2	15.4	15.5	15.6	15.7	15.8	15.9
90°	0.7	1.9	3.1	4.3	5.4	6.5	7.7	8.7	9.7	10.8	11.5
92.5°	16.3	17.1	18.0	18.8	19.6	20.7	22.0	23.2	24.5	25.8	26.9
95°	43.7	44.1	44.3	44.7	44.9	45.9	47.4	48.8	50.4	51.8	52.9
97.5°	72.8	72.8	72.9	73.1	73.2	74.3	76.4	78.4	80.5	82.6	83.5
100°	94.3	94.3	94.3	94.3	94.3	95.2	97.2	99.1	101.1	103.0	104.4
102.5°	117.4	118.0	118.6	119.2	119.9	120.6	121.6	122.6	123.6	124.6	126.1
105°	153.5	154.3	155.0	155.8	156.5	157.3	158.3	159.1	160.0	160.9	161.8
107.5°	193.4	194.1	194.8	195.6	196.4	197.1	197.8	198.5	199.1	199.8	200.3
110°	220.8	221.6	222.3	223.1	223.9	224.5	224.9	225.3	225.8	226.2	226.7



TEST NUMBER: P333185-935

CATALOG NUMBER: S125DIP-S610D810U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	248.8	249.3	249.6	250.0	250.4	250.9	251.4	252.0	252.6	253.1	253.4
115°	290.2	290.8	291.4	292.0	292.6	293.0	293.3	293.6	293.9	294.2	294.0
117.5°	331.7	331.9	332.2	332.4	332.7	333.0	333.3	333.6	333.8	334.1	334.2
120°	357.5	358.3	359.0	359.7	360.5	360.9	361.1	361.3	361.4	361.5	361.5
122.5°	385.5	385.8	386.1	386.3	386.6	386.9	387.3	387.7	388.1	388.5	388.3
125°	423.4	424.4	425.2	426.2	427.1	427.6	427.7	427.9	428.0	428.2	427.9
127.5°	463.9	464.4	464.9	465.4	465.9	466.2	466.4	466.6	466.8	467.0	466.8
130°	488.1	488.9	489.7	490.3	491.1	491.6	491.9	492.2	492.5	492.8	492.7
132.5°	512.4	513.6	514.8	516.0	517.3	517.8	517.8	517.7	517.6	517.6	517.5
135°	550.7	551.6	552.5	553.5	554.3	554.8	555.0	555.2	555.3	555.4	555.4
137.5°	586.9	587.7	588.6	589.4	590.3	590.9	591.2	591.5	591.9	592.2	592.4
140°	610.0	610.7	611.5	612.3	612.9	613.5	614.0	614.5	614.9	615.4	615.7
142.5°	633.2	633.8	634.4	635.0	635.7	636.3	636.8	637.4	637.9	638.5	638.7
145°	667.2	667.8	668.4	669.0	669.6	670.1	670.5	671.0	671.5	671.9	671.9
147.5°	698.7	699.0	699.4	699.7	700.0	700.3	700.8	701.1	701.5	701.8	702.1
150°	719.7	719.5	719.5	719.3	719.1	719.4	720.0	720.6	721.2	721.8	721.8
152.5°	736.9	737.2	737.4	737.6	737.8	738.0	738.2	738.5	738.7	739.0	739.3
155°	763.4	763.4	763.4	763.4	763.4	763.5	763.7	763.9	764.0	764.1	764.7
157.5°	787.2	786.9	786.5	786.2	785.8	785.7	785.9	786.1	786.2	786.4	787.0
160°	801.2	800.7	800.3	799.9	799.4	799.3	799.4	799.5	799.7	799.9	800.5
162.5°	813.6	813.2	812.9	812.6	812.3	812.1	812.1	812.2	812.2	812.3	813.0
165°	830.2	829.8	829.6	829.2	829.0	828.9	829.0	829.1	829.3	829.5	830.1
167.5°	844.1	843.5	842.9	842.3	841.7	841.5	841.5	841.5	841.5	841.5	842.3
170°	851.7	851.1	850.5	849.9	849.3	848.9	848.9	848.9	848.9	848.9	849.9
172.5°	857.0	856.4	855.8	855.2	854.6	854.4	854.4	854.4	854.4	854.4	855.2
175°	863.2	862.5	861.9	861.3	860.7	860.4	860.4	860.4	860.4	860.4	861.3
177.5°	866.3	865.7	865.3	864.8	864.3	864.0	863.9	863.8	863.7	863.5	864.3
180°	865.1	865.1	865.1	865.1	865.1	865.1	865.1	865.1	865.1	865.1	865.1



TEST NUMBER: P333185-935

CATALOG NUMBER: S125DIP-S610D810U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9
2.5°	824.5	825.7	826.8	827.3	827.2	827.1	827.0	826.9
5°	820.4	821.7	822.9	823.5	823.4	823.3	823.1	822.9
7.5°	812.0	813.3	814.6	815.2	815.0	814.9	814.8	814.6
10°	805.0	806.2	807.4	807.9	807.7	807.5	807.4	807.3
12.5°	795.7	796.6	797.5	798.0	797.9	797.9	797.9	797.8
15°	779.3	780.0	780.8	781.1	781.1	781.1	781.1	781.1
17.5°	760.3	761.1	762.1	762.2	761.4	760.7	760.0	759.2
20°	745.8	746.8	747.9	748.0	747.3	746.6	745.8	745.1
22.5°	729.4	730.1	730.8	730.9	730.4	729.9	729.4	728.9
25°	703.2	703.4	703.8	703.7	703.3	702.8	702.4	702.0
27.5°	675.6	675.7	675.7	675.5	675.1	674.7	674.2	673.8
30°	655.6	655.3	655.0	654.6	654.2	653.8	653.3	652.9
32.5°	635.2	634.6	634.1	633.5	632.7	632.0	631.1	630.3
35°	603.6	603.0	602.2	601.2	600.1	598.9	597.8	596.6
37.5°	570.5	569.5	568.3	567.5	566.8	566.2	565.5	564.8
40°	547.5	546.2	544.9	544.1	543.6	543.2	542.8	542.3
42.5°	524.8	523.6	522.4	521.4	520.7	520.1	519.4	518.8
45°	491.0	489.3	487.6	486.5	486.0	485.6	485.2	484.7
47.5°	455.6	453.7	452.0	450.6	449.6	448.6	447.5	446.5
50°	431.3	429.4	427.5	426.0	425.0	424.0	422.9	422.0
52.5°	407.6	406.0	404.3	402.9	401.8	400.6	399.5	398.4
55°	370.9	369.6	368.3	367.1	366.1	365.1	364.1	363.1
57.5°	334.4	332.8	331.1	329.9	329.4	328.8	328.3	327.8
60°	309.8	308.3	306.9	305.7	304.6	303.6	302.6	301.6
62.5°	286.0	284.5	282.8	281.7	280.9	280.1	279.3	278.5
65°	248.6	247.3	246.0	245.0	244.4	243.8	243.3	242.7
67.5°	212.9	211.8	210.7	209.9	209.6	209.2	208.9	208.5
70°	189.2	188.4	187.5	186.8	186.2	185.6	185.0	184.5
72.5°	167.0	166.1	165.1	164.3	163.7	163.2	162.6	162.0
75°	132.6	132.2	131.7	131.2	130.6	130.0	129.5	128.9
77.5°	101.0	100.7	100.5	100.1	99.7	99.4	98.9	98.5
80°	80.8	80.7	80.5	80.3	80.0	79.7	79.5	79.1
82.5°	61.7	61.5	61.2	61.0	61.0	61.0	60.9	60.9
85°	36.3	36.2	36.1	35.8	35.6	35.2	35.0	34.7
87.5°	16.1	16.2	16.4	16.4	16.2	16.1	15.9	15.8
90°	12.2	13.0	13.8	14.4	14.8	15.2	15.7	16.2
92.5°	27.8	28.8	29.8	30.5	30.8	31.1	31.4	31.8
95°	53.9	55.0	56.1	56.7	57.0	57.3	57.6	57.9
97.5°	84.6	85.5	86.5	87.0	87.2	87.4	87.6	87.8
100°	105.7	107.0	108.4	109.3	109.5	109.8	110.1	110.4
102.5°	127.5	129.0	130.4	131.4	131.8	132.2	132.6	133.0
105°	162.7	163.6	164.5	165.1	165.7	166.1	166.5	166.9
107.5°	200.7	201.1	201.6	201.8	201.8	201.7	201.7	201.7
110°	227.1	227.6	228.0	228.2	228.0	227.8	227.7	227.6





TEST NUMBER: P333185-935

CATALOG NUMBER: S125DIP-S610D810U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	253.6	253.7	254.0	254.0	253.7	253.4	253.1	252.9
115°	293.9	293.8	293.6	293.4	293.3	293.2	293.0	292.9
117.5°	334.3	334.4	334.6	334.3	333.7	333.1	332.5	331.9
120°	361.5	361.5	361.5	361.3	360.7	360.1	359.5	358.9
122.5°	388.2	388.1	388.0	387.7	387.2	386.8	386.2	385.8
125°	427.6	427.3	427.0	426.8	426.6	426.5	426.4	426.2
127.5°	466.7	466.5	466.4	466.1	465.9	465.5	465.3	464.9
130°	492.5	492.4	492.2	492.0	491.7	491.4	491.1	490.8
132.5°	517.3	517.1	517.0	516.7	516.3	515.9	515.5	515.1
135°	555.4	555.4	555.4	555.2	554.6	554.0	553.4	552.8
137.5°	592.5	592.7	592.9	592.6	591.9	591.2	590.4	589.6
140°	616.0	616.2	616.6	616.3	615.6	614.8	614.1	613.4
142.5°	638.9	639.0	639.2	638.9	638.2	637.5	636.7	635.9
145°	671.9	671.9	671.9	671.7	671.2	670.8	670.4	669.9
147.5°	702.5	702.9	703.3	702.9	701.9	700.9	699.9	698.9
150°	721.8	721.8	721.8	721.6	721.3	721.0	720.7	720.4
152.5°	739.7	740.0	740.4	740.3	739.8	739.3	738.7	738.1
155°	765.3	765.9	766.5	766.5	765.7	765.0	764.2	763.4
157.5°	787.6	788.2	788.8	788.6	787.6	786.6	785.6	784.6
160°	801.1	801.6	802.2	802.2	801.4	800.6	799.9	799.2
162.5°	813.6	814.4	815.1	815.0	814.2	813.3	812.4	811.6
165°	830.7	831.3	831.8	831.7	830.8	829.9	829.0	828.1
167.5°	843.3	844.1	845.1	845.0	844.1	843.2	842.2	841.3
170°	850.8	851.7	852.6	852.5	851.4	850.4	849.4	848.3
172.5°	856.2	857.0	858.0	858.0	857.0	856.1	855.1	854.2
175°	862.2	863.2	864.0	863.9	862.9	861.9	860.8	859.8
177.5°	865.0	865.6	866.4	866.3	865.5	864.7	863.8	863.0
180°	865.1	865.1	865.1	865.1	865.1	865.1	865.1	865.1

(END OF REPORT)