

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333216-935

Luminaire Tested: **S125DIP-S850D590U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333216-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S850D590U935-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4800.5 lumens  
Efficiency: N/A  
Efficacy: 119.1 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 40.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333216-935

CATALOG NUMBER: S125DIP-S850D590U935-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333216-935

CATALOG NUMBER: S125DIP-S850D590U935-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	101	96	93	89	94	91	87	84	79	77	75	69	67	66	60	58	57	53
2	92	85	78	73	86	79	74	69	70	66	62	61	58	55	53	51	49	45
3	84	75	67	61	78	70	64	58	62	57	53	54	50	47	47	44	42	38
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	42	39	36	33
5	71	59	51	45	66	56	48	43	49	44	39	44	39	35	38	34	32	29
6	65	53	45	39	61	50	43	37	45	39	34	39	35	31	35	31	28	25
7	60	48	40	34	57	45	38	33	41	35	30	36	31	27	32	28	25	22
8	56	44	36	30	53	41	34	29	37	31	27	33	28	24	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	27	23	20	18
10	49	37	29	24	46	35	28	24	31	26	22	28	23	20	25	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	6803	6803	6803	6803
5°	7878	6825	5977	6825
10°	9165	6790	5237	6790
15°	10146	6740	4831	6740
20°	11357	6661	4504	6661
25°	13304	6572	4345	6572
30°	14370	6485	4207	6485
35°	11815	6320	4117	6320
40°	8398	6091	4018	6091
45°	6452	5782	3961	5782
50°	5507	5399	3953	5399
55°	4904	5024	3987	5024
60°	4423	4614	4088	4614
65°	4085	4201	4195	4201
70°	3714	3773	4254	3773
75°	3281	3324	4217	3324
80°	2760	2708	3861	2708
85°	2186	1949	3112	1949



TEST NUMBER: P333216-935

CATALOG NUMBER: S125DIP-S850D590U935-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	101.4	2.1
10°-20°	301.9	6.3
20°-30°	490.2	10.2
30°-40°	598.0	12.5
40°-50°	544.0	11.3
50°-60°	433.3	9.0
60°-70°	301.8	6.3
70°-80°	160.9	3.4
80°-90°	42.0	0.9
90°-100°	176.6	3.7
100°-110°	379.6	7.9
110°-120°	356.2	7.4
120°-130°	288.7	6.0
130°-140°	231.7	4.8
140°-150°	174.8	3.6
150°-160°	123.1	2.6
160°-170°	72.5	1.5
170°-180°	23.6	0.5
0°-30°	893.6	18.6
0°-40°	1491.6	31.1
0°-60°	2468.9	51.4
0°-90°	2973.6	61.9
90°-120°	912.4	19.0
90°-150°	1607.6	33.5
90°-180°	1827.0	38.1
0°-180°	4800.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1053	1053	1053	1053	1053	
5°	1215	1053	922	1053	1215	122
15°	1517	1008	722	1008	1517	434
25°	1867	922	610	922	1867	853
35°	1499	802	522	802	1499	917
45°	706	633	434	633	706	565
55°	436	446	354	446	436	392
65°	267	275	274	275	267	265
75°	132	133	169	133	132	142
85°	30	26	42	26	30	34
90°	11	0	11	0	11	9
95°	116	16	116	16	116	164
105°	651	56	651	56	651	647
115°	725	99	725	99	725	708
125°	571	138	571	138	571	517
135°	474	161	474	161	474	368
145°	374	188	374	188	374	238
155°	314	214	314	214	314	146
165°	275	234	275	234	275	79
175°	247	243	247	243	247	24
180°	244	244	244	244	244	



TEST NUMBER: P333216-935

CATALOG NUMBER: S125DIP-S850D590U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3
2.5°	1114.1	1112.7	1111.3	1108.4	1110.5	1104.5	1101.6	1096.6	1090.5	1088.4	1085.9
5°	1215.1	1217.4	1219.6	1210.2	1211.2	1204.9	1190.6	1179.0	1169.6	1157.5	1149.0
7.5°	1336.8	1331.5	1331.0	1325.0	1314.5	1306.1	1291.1	1272.0	1253.4	1232.3	1214.9
10°	1397.6	1398.0	1394.0	1386.8	1375.7	1367.6	1348.0	1329.1	1306.4	1279.5	1260.3
12.5°	1443.4	1445.2	1440.1	1430.5	1425.0	1407.0	1391.5	1369.2	1342.1	1320.7	1291.4
15°	1517.4	1512.4	1508.9	1496.8	1487.5	1468.7	1444.1	1420.8	1391.3	1364.0	1336.8
17.5°	1588.7	1592.7	1586.0	1574.9	1545.8	1523.9	1490.9	1459.1	1422.4	1385.8	1353.2
20°	1652.4	1656.0	1645.7	1626.5	1591.6	1569.7	1526.3	1485.2	1442.7	1395.8	1360.0
22.5°	1731.8	1729.0	1715.1	1685.8	1655.6	1615.1	1568.1	1518.1	1464.9	1411.9	1364.3
25°	1867.0	1848.2	1839.7	1803.5	1763.8	1704.3	1639.9	1566.6	1500.4	1430.2	1369.4
27.5°	1941.9	1936.0	1926.6	1901.3	1859.5	1796.0	1720.0	1630.6	1537.3	1448.7	1369.2
30°	1926.9	1927.8	1928.7	1920.6	1893.9	1846.0	1770.5	1674.3	1563.4	1463.7	1371.7
32.5°	1793.9	1810.2	1825.7	1844.1	1851.6	1842.5	1795.1	1708.3	1594.2	1480.9	1370.2
35°	1498.6	1503.6	1554.0	1604.1	1672.1	1724.8	1760.1	1721.7	1625.6	1495.5	1368.5
37.5°	1168.5	1192.7	1227.6	1284.2	1382.2	1470.1	1583.0	1635.0	1604.0	1500.2	1365.4
40°	996.1	1018.5	1041.2	1098.9	1181.6	1288.1	1416.3	1525.9	1551.3	1485.2	1354.6
42.5°	863.1	880.7	906.0	949.4	1018.6	1112.8	1235.4	1378.5	1466.6	1441.6	1332.1
45°	706.4	717.6	737.3	771.6	821.7	895.5	1003.7	1160.2	1296.5	1341.7	1278.7
47.5°	604.6	604.5	619.8	643.6	679.8	742.4	822.4	945.0	1090.7	1198.4	1193.4
50°	548.1	545.9	557.9	578.5	607.1	648.7	725.1	823.0	963.0	1085.0	1119.0
52.5°	499.5	499.7	507.1	522.4	546.3	581.9	638.9	727.2	846.8	972.1	1036.0
55°	435.5	433.7	442.1	452.5	469.8	493.1	534.3	601.8	698.8	822.2	905.3
57.5°	376.8	381.7	385.1	392.3	406.7	422.3	457.0	506.5	583.5	689.4	777.3
60°	342.4	347.4	350.1	357.2	368.9	382.3	409.1	449.4	514.1	605.4	692.5
62.5°	311.7	315.6	316.4	322.9	332.3	345.4	366.5	400.3	451.5	531.3	616.7
65°	267.3	267.3	269.1	275.9	280.3	292.0	308.1	332.6	373.8	435.9	508.8
67.5°	224.6	226.8	226.3	229.3	233.4	242.4	253.9	274.2	304.7	350.1	408.4
70°	196.7	198.5	198.0	200.3	204.7	210.6	220.0	239.2	261.1	300.0	350.1
72.5°	171.7	172.4	171.3	174.2	176.8	181.9	192.4	202.7	223.2	256.0	297.1
75°	131.5	132.3	133.2	135.0	137.7	140.3	145.8	156.0	169.4	194.1	220.4
77.5°	98.5	96.9	99.0	98.8	100.2	102.3	107.0	112.4	123.5	139.1	159.5
80°	74.2	74.6	74.6	75.1	77.3	78.7	82.7	86.7	95.2	106.9	121.1
82.5°	54.2	55.4	54.7	55.4	57.3	58.3	60.5	63.8	68.8	77.9	88.3
85°	29.5	27.3	28.2	29.1	29.1	29.5	31.3	32.6	35.3	38.9	42.9
87.5°	10.8	11.5	11.8	11.8	12.1	12.0	13.3	13.2	14.2	15.2	16.4
90°	11.3	11.3	10.8	10.8	10.8	9.8	9.3	8.9	8.4	7.8	6.9
92.5°	31.3	32.1	32.8	34.0	40.3	47.5	63.2	87.0	128.2	158.3	160.9
95°	115.5	123.3	127.2	142.0	176.8	218.1	278.4	353.1	425.9	435.1	355.1
97.5°	279.0	285.2	299.5	327.0	357.3	414.7	473.6	525.9	538.8	464.7	317.1
100°	383.1	391.0	409.1	444.4	478.4	529.4	580.1	604.1	566.3	443.5	282.9
102.5°	499.4	505.3	525.0	550.2	586.4	621.0	645.2	630.4	549.7	406.1	256.9
105°	650.7	656.7	666.5	682.7	698.4	703.8	682.2	614.9	497.1	356.1	231.8
107.5°	731.1	735.0	738.3	738.4	730.4	704.8	649.3	559.5	443.2	321.6	221.2
110°	757.9	757.9	754.4	745.0	723.0	681.2	612.0	518.7	412.6	305.5	218.1



TEST NUMBER: P333216-935

CATALOG NUMBER: S125DIP-S850D590U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	754.7	751.1	742.6	726.6	694.3	645.1	575.1	486.5	389.8	296.1	218.1
115°	725.0	718.5	704.8	681.2	642.9	589.4	522.1	445.9	364.9	285.9	219.6
117.5°	672.8	668.8	655.2	630.9	592.5	543.4	485.4	419.8	350.1	280.9	222.7
120°	638.9	635.1	621.8	598.2	561.9	518.7	464.6	405.7	341.8	278.4	225.9
122.5°	609.1	605.5	592.3	570.7	538.3	497.8	449.7	395.1	334.8	276.6	228.7
125°	571.2	566.3	555.5	535.4	507.8	472.5	429.7	379.6	325.1	274.1	233.3
127.5°	538.8	536.6	526.4	508.6	483.7	450.6	410.7	363.9	316.3	272.9	238.5
130°	521.1	518.1	508.3	492.1	467.5	435.7	397.4	354.1	310.4	272.1	241.7
132.5°	503.4	500.1	491.0	474.8	450.3	419.6	384.8	344.3	305.7	272.1	245.2
135°	474.4	471.5	462.6	446.4	424.8	396.8	365.4	331.5	300.1	272.1	249.9
137.5°	443.5	440.2	432.1	417.3	398.0	374.3	348.1	320.7	295.1	272.7	254.4
140°	421.9	419.4	412.1	399.3	381.2	360.5	337.9	314.8	292.7	273.1	256.4
142.5°	401.8	399.8	392.8	382.0	366.6	348.7	329.2	309.7	290.8	273.5	257.5
145°	374.3	372.3	366.9	358.5	346.7	333.5	318.2	303.1	287.8	273.1	258.8
147.5°	350.9	350.0	346.8	340.2	330.8	320.8	309.1	296.8	284.7	271.8	259.3
150°	337.9	337.4	335.4	329.6	322.2	313.3	304.0	293.2	282.4	270.6	259.3
152.5°	327.7	327.2	325.2	320.6	314.4	307.5	298.9	289.3	279.7	269.1	258.9
155°	313.8	313.3	311.9	308.4	303.5	298.1	291.3	283.4	275.0	266.2	257.9
157.5°	301.4	301.5	300.1	297.3	293.5	289.3	284.0	277.5	270.7	263.2	256.6
160°	293.2	293.7	292.7	290.2	286.8	283.4	278.4	273.5	267.2	261.3	255.4
162.5°	285.8	285.9	285.7	283.6	280.9	277.8	273.8	269.2	264.1	258.9	254.3
165°	275.0	275.0	275.0	274.1	272.1	269.7	266.7	263.2	259.3	255.4	252.4
167.5°	265.2	265.3	265.7	264.8	263.8	262.1	259.8	257.5	254.7	251.9	249.7
170°	259.3	259.8	259.8	259.3	258.3	257.4	255.9	254.4	251.9	249.9	248.5
172.5°	253.8	254.3	255.1	254.3	254.0	253.4	252.4	250.9	249.2	247.6	246.9
175°	247.0	247.5	248.5	248.1	248.1	248.1	247.0	247.0	245.6	245.0	245.0
177.5°	243.6	243.6	244.8	244.4	244.8	244.8	244.8	244.4	244.0	243.6	243.6
180°	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6



TEST NUMBER: P333216-935

CATALOG NUMBER: S125DIP-S850D590U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3
2.5°	1083.7	1081.2	1078.3	1073.3	1067.3	1064.0	1059.0	1055.8	1049.4	1044.0	1038.3
5°	1138.7	1127.0	1116.4	1102.5	1087.3	1077.5	1065.8	1052.8	1039.5	1025.6	1010.4
7.5°	1195.7	1175.1	1152.7	1128.7	1105.2	1083.6	1062.9	1042.6	1023.6	1000.7	981.4
10°	1233.9	1208.0	1180.3	1147.6	1115.9	1088.2	1060.1	1035.4	1010.4	983.6	959.8
12.5°	1272.2	1237.7	1198.5	1162.7	1124.5	1091.1	1057.9	1026.5	995.1	965.4	937.7
15°	1299.2	1268.8	1232.6	1181.6	1138.7	1092.7	1048.9	1008.1	970.2	937.1	902.2
17.5°	1317.0	1277.8	1239.0	1190.1	1133.8	1082.3	1032.7	986.1	943.2	901.3	867.7
20°	1320.3	1280.0	1239.3	1191.5	1133.8	1074.8	1025.2	969.2	923.3	879.9	838.7
22.5°	1319.1	1273.6	1229.2	1180.0	1123.8	1069.4	1009.4	952.4	902.5	859.8	816.9
25°	1309.1	1260.3	1204.9	1155.3	1099.8	1042.2	981.4	922.3	871.3	822.6	780.2
27.5°	1300.6	1237.4	1174.7	1116.8	1063.2	1010.4	952.2	891.7	835.3	785.8	745.8
30°	1290.3	1221.0	1150.3	1089.9	1035.0	983.6	928.6	869.6	810.5	762.2	719.4
32.5°	1281.0	1200.2	1125.7	1060.0	1001.7	951.7	901.0	844.9	787.0	738.0	695.0
35°	1263.0	1169.6	1084.2	1010.0	947.8	896.4	853.9	801.6	748.4	701.0	659.9
37.5°	1240.2	1129.3	1037.7	959.8	891.7	837.6	798.1	757.9	706.8	661.2	624.0
40°	1222.3	1100.7	1003.7	924.1	853.5	797.1	760.5	722.5	680.0	637.6	598.2
42.5°	1199.8	1075.0	969.4	883.7	813.7	758.9	720.4	688.1	650.7	611.1	574.5
45°	1158.4	1028.3	913.9	821.7	751.1	697.0	657.2	633.1	604.9	567.3	536.5
47.5°	1097.5	972.2	853.9	758.8	685.9	635.8	598.5	575.3	555.4	527.5	499.6
50°	1043.4	930.4	810.5	716.2	643.3	592.8	558.4	537.4	520.4	498.9	475.3
52.5°	983.0	877.8	768.0	674.8	602.6	552.8	519.1	500.6	486.5	471.1	447.7
55°	887.0	797.6	695.7	607.1	540.5	491.8	462.3	446.2	434.5	422.9	408.6
57.5°	781.2	711.3	621.0	540.1	478.7	434.4	406.8	391.2	382.2	376.2	367.7
60°	706.8	647.0	569.1	495.3	435.5	396.1	369.3	357.2	349.7	344.7	338.5
62.5°	637.8	588.7	516.5	449.2	396.8	359.6	335.7	324.0	316.7	314.3	309.1
65°	536.1	498.1	438.6	382.7	338.0	306.3	286.1	274.9	270.4	267.8	268.3
67.5°	435.8	412.7	364.9	317.3	281.5	254.9	238.8	230.2	228.0	224.5	224.4
70°	374.6	357.2	317.0	275.4	243.7	223.1	208.8	199.8	197.6	195.8	195.4
72.5°	320.6	305.4	270.4	237.1	208.6	190.5	178.7	173.4	169.7	168.7	168.6
75°	241.0	232.5	204.7	178.4	158.7	146.2	138.2	133.2	130.5	130.1	130.5
77.5°	171.3	163.9	146.3	127.6	115.2	105.7	98.9	97.2	94.2	94.3	93.8
80°	128.7	123.8	112.7	97.9	87.6	79.6	76.0	72.8	72.0	70.6	72.0
82.5°	93.3	88.1	80.5	71.1	62.6	57.8	54.2	53.2	52.7	52.0	52.3
85°	46.1	46.5	42.0	34.9	31.3	28.6	26.3	26.3	25.9	25.5	25.9
87.5°	17.0	16.1	14.6	13.3	11.3	10.1	9.5	9.7	8.8	8.6	9.2
90°	6.4	5.4	4.9	4.0	2.9	2.0	0.9	0.5	0.9	2.0	2.9
92.5°	112.1	67.1	40.3	25.9	17.5	11.4	7.2	6.0	7.2	11.4	17.5
95°	219.6	111.5	59.0	36.9	26.0	20.7	16.7	16.2	16.7	20.7	26.0
97.5°	175.2	96.1	61.3	45.4	35.6	30.2	27.5	26.9	27.5	30.2	35.6
100°	159.1	95.3	66.8	52.1	42.7	37.4	35.4	34.4	35.4	37.4	42.7
102.5°	152.5	98.8	73.4	59.2	50.6	44.8	43.2	42.6	43.2	44.8	50.6
105°	149.8	106.1	84.5	70.7	62.9	57.9	55.5	55.5	55.5	57.9	62.9
107.5°	154.3	116.9	96.0	83.6	75.4	71.4	69.1	68.1	69.1	71.4	75.4
110°	158.6	124.8	104.6	91.9	84.5	80.1	78.1	77.1	78.1	80.1	84.5





TEST NUMBER: P333216-935

CATALOG NUMBER: S125DIP-S850D590U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	164.1	132.2	112.9	100.5	93.2	88.7	87.1	86.2	87.1	88.7	93.2
115°	172.4	143.9	125.7	113.5	106.1	101.7	100.2	99.2	100.2	101.7	106.1
117.5°	181.8	155.9	138.7	126.8	118.5	114.1	112.4	111.0	112.4	114.1	118.5
120°	188.1	164.5	147.3	135.1	126.7	122.3	120.4	118.8	120.4	122.3	126.7
122.5°	195.2	172.8	155.6	143.4	134.1	129.8	128.2	127.1	128.2	129.8	134.1
125°	204.8	183.7	167.5	154.7	145.3	140.9	138.5	137.5	138.5	140.9	145.3
127.5°	213.6	194.2	178.6	165.8	155.9	150.3	147.1	145.7	147.1	150.3	155.9
130°	219.6	200.9	185.6	172.9	162.6	156.2	152.2	150.8	152.2	156.2	162.6
132.5°	224.6	207.2	191.9	179.2	168.5	161.3	156.6	154.7	156.6	161.3	168.5
135°	231.8	215.6	200.4	187.1	176.8	168.9	163.1	161.1	163.1	168.9	176.8
137.5°	237.1	221.6	207.8	194.1	184.0	176.2	170.7	169.2	170.7	176.2	184.0
140°	240.6	225.9	211.7	198.5	189.1	181.2	175.3	173.8	175.3	181.2	189.1
142.5°	242.6	228.7	215.2	202.8	193.8	186.0	180.5	179.3	180.5	186.0	193.8
145°	245.6	233.3	220.5	209.2	200.4	193.5	188.6	187.6	188.6	193.5	200.4
147.5°	247.4	236.3	225.1	215.1	207.4	201.0	196.8	196.2	196.8	201.0	207.4
150°	248.5	238.2	227.4	219.0	212.2	205.8	202.3	201.4	202.3	205.8	212.2
152.5°	249.3	240.1	230.1	222.6	216.1	210.5	207.4	206.9	207.4	210.5	216.1
155°	249.9	242.1	233.8	226.9	222.0	217.1	214.1	214.1	214.1	217.1	222.0
157.5°	250.5	243.8	236.6	231.4	227.1	222.9	220.5	220.6	220.5	222.9	227.1
160°	250.5	244.6	238.2	233.8	229.9	226.4	224.5	225.0	224.5	226.4	229.9
162.5°	250.1	245.4	239.8	236.2	233.0	230.0	228.0	228.5	228.0	230.0	233.0
165°	249.5	245.6	241.7	238.7	236.7	234.3	232.8	233.8	232.8	234.3	236.7
167.5°	248.3	245.6	242.3	240.5	239.1	237.7	236.9	237.3	236.9	237.7	239.1
170°	247.5	245.6	243.1	241.7	240.6	239.7	239.2	239.7	239.2	239.7	240.6
172.5°	246.8	245.2	243.1	242.5	241.9	240.8	240.4	241.3	240.4	240.8	241.9
175°	245.6	244.6	243.1	243.1	243.1	242.6	242.1	243.1	242.1	242.6	243.1
177.5°	244.4	244.0	243.2	243.2	243.6	243.2	243.2	244.0	243.2	243.2	243.6
180°	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6



TEST NUMBER: P333216-935

CATALOG NUMBER: S125DIP-S850D590U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3
2.5°	1035.1	1031.1	1027.9	1020.8	1016.8	1011.5	1007.2	1011.8	1006.9	1009.0	1005.7
5°	1002.8	990.3	981.4	968.4	957.2	946.9	939.4	938.0	934.4	932.6	927.2
7.5°	964.0	948.3	933.0	916.0	901.6	887.1	877.8	870.1	865.0	858.3	853.8
10°	941.1	920.1	902.2	881.7	863.8	848.1	835.6	829.3	823.5	815.0	811.9
12.5°	912.8	891.1	869.3	847.3	830.2	812.7	801.9	792.5	788.5	778.9	777.9
15°	879.0	846.4	824.8	802.5	778.8	764.5	755.5	745.3	740.8	734.1	729.2
17.5°	838.5	809.4	782.6	759.4	739.1	727.0	715.9	708.9	701.2	696.8	688.8
20°	809.3	781.5	754.7	730.0	714.5	700.6	691.6	684.9	676.9	674.7	666.6
22.5°	784.5	754.0	728.2	707.6	690.4	674.9	665.1	660.6	655.0	648.2	646.5
25°	744.4	712.6	690.8	670.2	655.0	640.7	634.0	628.2	622.8	617.9	616.0
27.5°	709.7	681.3	655.3	636.7	623.5	610.4	604.5	597.4	593.6	589.6	584.8
30°	685.4	656.3	633.5	615.6	601.3	589.7	583.4	578.5	575.0	571.4	568.7
32.5°	660.3	633.4	611.3	593.8	579.5	570.8	565.2	561.7	557.8	553.5	550.1
35°	627.2	597.7	576.3	561.1	549.9	543.2	536.9	533.8	529.3	529.3	525.7
37.5°	590.0	564.5	545.5	531.7	521.7	515.7	508.9	506.7	503.9	502.0	500.8
40°	567.8	544.1	526.2	512.4	501.6	496.7	491.4	487.8	485.9	483.7	482.8
42.5°	544.9	522.3	505.1	492.3	483.0	478.8	473.8	471.3	467.7	464.8	464.3
45°	510.1	488.2	472.6	462.3	454.3	449.4	446.2	440.8	439.0	435.5	435.0
47.5°	477.1	456.1	440.7	432.3	425.2	421.2	416.3	411.0	408.9	407.1	406.9
50°	452.5	433.3	418.9	410.9	404.2	398.4	393.4	389.9	388.5	388.5	389.4
52.5°	427.4	411.0	398.9	389.1	382.7	376.5	372.0	369.8	367.7	369.9	371.5
55°	390.7	374.2	365.2	355.9	349.7	342.4	340.3	339.3	338.0	341.6	343.4
57.5°	352.0	340.4	329.8	320.6	315.0	310.8	307.8	307.2	309.7	311.4	317.3
60°	327.3	313.8	304.4	297.3	290.6	287.9	287.1	286.1	287.9	292.8	300.4
62.5°	300.1	289.2	279.1	273.7	268.8	264.3	264.2	264.7	268.3	273.9	281.5
65°	260.2	250.8	244.1	237.8	233.8	231.2	232.0	233.8	237.8	245.5	253.9
67.5°	219.7	213.3	207.2	202.2	198.3	198.3	199.2	201.9	206.6	215.4	223.2
70°	193.6	186.4	181.5	179.3	176.2	174.4	177.0	181.5	185.5	193.6	200.3
72.5°	167.5	161.4	157.6	156.0	154.7	153.3	154.1	158.9	164.5	172.5	180.3
75°	128.7	126.5	123.8	122.1	120.7	121.6	122.5	127.0	131.5	139.9	148.9
77.5°	93.9	91.6	90.1	89.6	88.9	89.3	91.9	95.1	99.5	105.7	112.4
80°	71.1	70.2	69.3	68.9	68.9	69.3	72.8	75.1	79.1	85.0	90.3
82.5°	51.7	51.2	51.1	51.0	51.3	51.4	53.6	56.5	59.8	64.2	68.9
85°	27.3	26.3	27.7	28.2	27.3	28.6	29.5	31.3	32.6	34.9	37.1
87.5°	9.7	10.7	10.4	10.9	11.0	12.0	11.7	13.2	14.0	14.8	14.6
90°	4.0	4.9	5.4	6.4	6.9	7.8	8.4	8.9	9.3	9.8	10.8
92.5°	25.9	40.3	67.1	112.1	160.9	158.3	128.2	87.0	63.2	47.5	40.3
95°	36.9	59.0	111.5	219.6	355.1	435.1	425.9	353.1	278.4	218.1	176.8
97.5°	45.4	61.3	96.1	175.2	317.1	464.7	538.8	525.9	473.6	414.7	357.3
100°	52.1	66.8	95.3	159.1	282.9	443.5	566.3	604.1	580.1	529.4	478.4
102.5°	59.2	73.4	98.8	152.5	256.9	406.1	549.7	630.4	645.2	621.0	586.4
105°	70.7	84.5	106.1	149.8	231.8	356.1	497.1	614.9	682.2	703.8	698.4
107.5°	83.6	96.0	116.9	154.3	221.2	321.6	443.2	559.5	649.3	704.8	730.4
110°	91.9	104.6	124.8	158.6	218.1	305.5	412.6	518.7	612.0	681.2	723.0



TEST NUMBER: P333216-935

CATALOG NUMBER: S125DIP-S850D590U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	100.5	112.9	132.2	164.1	218.1	296.1	389.8	486.5	575.1	645.1	694.3
115°	113.5	125.7	143.9	172.4	219.6	285.9	364.9	445.9	522.1	589.4	642.9
117.5°	126.8	138.7	155.9	181.8	222.7	280.9	350.1	419.8	485.4	543.4	592.5
120°	135.1	147.3	164.5	188.1	225.9	278.4	341.8	405.7	464.6	518.7	561.9
122.5°	143.4	155.6	172.8	195.2	228.7	276.6	334.8	395.1	449.7	497.8	538.3
125°	154.7	167.5	183.7	204.8	233.3	274.1	325.1	379.6	429.7	472.5	507.8
127.5°	165.8	178.6	194.2	213.6	238.5	272.9	316.3	363.9	410.7	450.6	483.7
130°	172.9	185.6	200.9	219.6	241.7	272.1	310.4	354.1	397.4	435.7	467.5
132.5°	179.2	191.9	207.2	224.6	245.2	272.1	305.7	344.3	384.8	419.6	450.3
135°	187.1	200.4	215.6	231.8	249.9	272.1	300.1	331.5	365.4	396.8	424.8
137.5°	194.1	207.8	221.6	237.1	254.4	272.7	295.1	320.7	348.1	374.3	398.0
140°	198.5	211.7	225.9	240.6	256.4	273.1	292.7	314.8	337.9	360.5	381.2
142.5°	202.8	215.2	228.7	242.6	257.5	273.5	290.8	309.7	329.2	348.7	366.6
145°	209.2	220.5	233.3	245.6	258.8	273.1	287.8	303.1	318.2	333.5	346.7
147.5°	215.1	225.1	236.3	247.4	259.3	271.8	284.7	296.8	309.1	320.8	330.8
150°	219.0	227.4	238.2	248.5	259.3	270.6	282.4	293.2	304.0	313.3	322.2
152.5°	222.6	230.1	240.1	249.3	258.9	269.1	279.7	289.3	298.9	307.5	314.4
155°	226.9	233.8	242.1	249.9	257.9	266.2	275.0	283.4	291.3	298.1	303.5
157.5°	231.4	236.6	243.8	250.5	256.6	263.2	270.7	277.5	284.0	289.3	293.5
160°	233.8	238.2	244.6	250.5	255.4	261.3	267.2	273.5	278.4	283.4	286.8
162.5°	236.2	239.8	245.4	250.1	254.3	258.9	264.1	269.2	273.8	277.8	280.9
165°	238.7	241.7	245.6	249.5	252.4	255.4	259.3	263.2	266.7	269.7	272.1
167.5°	240.5	242.3	245.6	248.3	249.7	251.9	254.7	257.5	259.8	262.1	263.8
170°	241.7	243.1	245.6	247.5	248.5	249.9	251.9	254.4	255.9	257.4	258.3
172.5°	242.5	243.1	245.2	246.8	246.9	247.6	249.2	250.9	252.4	253.4	254.0
175°	243.1	243.1	244.6	245.6	245.0	245.0	245.6	247.0	247.0	248.1	248.1
177.5°	243.2	243.2	244.0	244.4	243.6	243.6	244.0	244.4	244.8	244.8	244.8
180°	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6



TEST NUMBER: P333216-935

CATALOG NUMBER: S125DIP-S850D590U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3
2.5°	1003.6	1006.1	1003.9	1006.9	1003.9	1006.1	1003.6	1005.7	1009.0	1006.9	1011.8
5°	925.0	921.0	923.7	921.9	923.7	921.0	925.0	927.2	932.6	934.4	938.0
7.5°	852.4	848.5	844.2	842.1	844.2	848.5	852.4	853.8	858.3	865.0	870.1
10°	807.0	802.0	801.6	798.5	801.6	802.0	807.0	811.9	815.0	823.5	829.3
12.5°	773.7	769.1	764.1	762.8	764.1	769.1	773.7	777.9	778.9	788.5	792.5
15°	726.5	722.9	719.8	722.5	719.8	722.9	726.5	729.2	734.1	740.8	745.3
17.5°	687.3	684.3	683.7	680.4	683.7	684.3	687.3	688.8	696.8	701.2	708.9
20°	662.5	660.3	661.2	655.4	661.2	660.3	662.5	666.6	674.7	676.9	684.9
22.5°	642.9	638.5	638.0	636.8	638.0	638.5	642.9	646.5	648.2	655.0	660.6
25°	612.1	609.8	607.6	609.8	607.6	609.8	612.1	616.0	617.9	622.8	628.2
27.5°	585.1	582.5	581.9	582.1	581.9	582.5	585.1	584.8	589.6	593.6	597.4
30°	568.7	564.2	564.6	564.2	564.6	564.2	568.7	568.7	571.4	575.0	578.5
32.5°	550.8	547.8	547.2	546.3	547.2	547.8	550.8	550.1	553.5	557.8	561.7
35°	524.4	524.4	522.2	522.2	522.2	524.4	524.4	525.7	529.3	529.3	533.8
37.5°	499.6	499.2	497.8	498.1	497.8	499.2	499.6	500.8	502.0	503.9	506.7
40°	481.0	480.6	479.2	476.6	479.2	480.6	481.0	482.8	483.7	485.9	487.8
42.5°	463.1	461.7	461.1	460.1	461.1	461.7	463.1	464.3	464.8	467.7	471.3
45°	435.0	435.0	434.1	433.7	434.1	435.0	435.0	435.0	435.5	439.0	440.8
47.5°	407.7	408.5	410.2	409.9	410.2	408.5	407.7	406.9	407.1	408.9	411.0
50°	391.2	391.7	393.0	393.4	393.0	391.7	391.2	389.4	388.5	388.5	389.9
52.5°	373.0	375.6	377.2	376.9	377.2	375.6	373.0	371.5	369.9	367.7	369.8
55°	347.4	350.5	353.6	354.1	353.6	350.5	347.4	343.4	341.6	338.0	339.3
57.5°	322.1	326.5	329.8	330.8	329.8	326.5	322.1	317.3	311.4	309.7	307.2
60°	304.9	310.7	314.8	316.5	314.8	310.7	304.9	300.4	292.8	287.9	286.1
62.5°	288.4	295.0	299.0	299.4	299.0	295.0	288.4	281.5	273.9	268.3	264.7
65°	261.6	268.3	271.8	274.5	271.8	268.3	261.6	253.9	245.5	237.8	233.8
67.5°	232.6	239.3	243.2	245.4	243.2	239.3	232.6	223.2	215.4	206.6	201.9
70°	211.5	218.2	223.5	225.3	223.5	218.2	211.5	200.3	193.6	185.5	181.5
72.5°	190.7	196.7	201.0	203.1	201.0	196.7	190.7	180.3	172.5	164.5	158.9
75°	154.7	162.7	166.8	169.0	166.8	162.7	154.7	148.9	139.9	131.5	127.0
77.5°	119.2	126.7	129.1	130.2	129.1	126.7	119.2	112.4	105.7	99.5	95.1
80°	95.7	100.1	103.2	103.8	103.2	100.1	95.7	90.3	85.0	79.1	75.1
82.5°	73.5	77.2	78.3	79.4	78.3	77.2	73.5	68.9	64.2	59.8	56.5
85°	40.2	42.0	42.4	42.0	42.4	42.0	40.2	37.1	34.9	32.6	31.3
87.5°	15.4	15.1	15.2	15.8	15.2	15.1	15.4	14.6	14.8	14.0	13.2
90°	10.8	10.8	11.3	11.3	11.3	10.8	10.8	10.8	9.8	9.3	8.9
92.5°	34.0	32.8	32.1	31.3	32.1	32.8	34.0	40.3	47.5	63.2	87.0
95°	142.0	127.2	123.3	115.5	123.3	127.2	142.0	176.8	218.1	278.4	353.1
97.5°	327.0	299.5	285.2	279.0	285.2	299.5	327.0	357.3	414.7	473.6	525.9
100°	444.4	409.1	391.0	383.1	391.0	409.1	444.4	478.4	529.4	580.1	604.1
102.5°	550.2	525.0	505.3	499.4	505.3	525.0	550.2	586.4	621.0	645.2	630.4
105°	682.7	666.5	656.7	650.7	656.7	666.5	682.7	698.4	703.8	682.2	614.9
107.5°	738.4	738.3	735.0	731.1	735.0	738.3	738.4	730.4	704.8	649.3	559.5
110°	745.0	754.4	757.9	757.9	757.9	754.4	745.0	723.0	681.2	612.0	518.7



TEST NUMBER: P333216-935

CATALOG NUMBER: S125DIP-S850D590U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	726.6	742.6	751.1	754.7	751.1	742.6	726.6	694.3	645.1	575.1	486.5
115°	681.2	704.8	718.5	725.0	718.5	704.8	681.2	642.9	589.4	522.1	445.9
117.5°	630.9	655.2	668.8	672.8	668.8	655.2	630.9	592.5	543.4	485.4	419.8
120°	598.2	621.8	635.1	638.9	635.1	621.8	598.2	561.9	518.7	464.6	405.7
122.5°	570.7	592.3	605.5	609.1	605.5	592.3	570.7	538.3	497.8	449.7	395.1
125°	535.4	555.5	566.3	571.2	566.3	555.5	535.4	507.8	472.5	429.7	379.6
127.5°	508.6	526.4	536.6	538.8	536.6	526.4	508.6	483.7	450.6	410.7	363.9
130°	492.1	508.3	518.1	521.1	518.1	508.3	492.1	467.5	435.7	397.4	354.1
132.5°	474.8	491.0	500.1	503.4	500.1	491.0	474.8	450.3	419.6	384.8	344.3
135°	446.4	462.6	471.5	474.4	471.5	462.6	446.4	424.8	396.8	365.4	331.5
137.5°	417.3	432.1	440.2	443.5	440.2	432.1	417.3	398.0	374.3	348.1	320.7
140°	399.3	412.1	419.4	421.9	419.4	412.1	399.3	381.2	360.5	337.9	314.8
142.5°	382.0	392.8	399.8	401.8	399.8	392.8	382.0	366.6	348.7	329.2	309.7
145°	358.5	366.9	372.3	374.3	372.3	366.9	358.5	346.7	333.5	318.2	303.1
147.5°	340.2	346.8	350.0	350.9	350.0	346.8	340.2	330.8	320.8	309.1	296.8
150°	329.6	335.4	337.4	337.9	337.4	335.4	329.6	322.2	313.3	304.0	293.2
152.5°	320.6	325.2	327.2	327.7	327.2	325.2	320.6	314.4	307.5	298.9	289.3
155°	308.4	311.9	313.3	313.8	313.3	311.9	308.4	303.5	298.1	291.3	283.4
157.5°	297.3	300.1	301.5	301.4	301.5	300.1	297.3	293.5	289.3	284.0	277.5
160°	290.2	292.7	293.7	293.2	293.7	292.7	290.2	286.8	283.4	278.4	273.5
162.5°	283.6	285.7	285.9	285.8	285.9	285.7	283.6	280.9	277.8	273.8	269.2
165°	274.1	275.0	275.0	275.0	275.0	275.0	274.1	272.1	269.7	266.7	263.2
167.5°	264.8	265.7	265.3	265.2	265.3	265.7	264.8	263.8	262.1	259.8	257.5
170°	259.3	259.8	259.8	259.3	259.8	259.8	259.3	258.3	257.4	255.9	254.4
172.5°	254.3	255.1	254.3	253.8	254.3	255.1	254.3	254.0	253.4	252.4	250.9
175°	248.1	248.5	247.5	247.0	247.5	248.5	248.1	248.1	248.1	247.0	247.0
177.5°	244.4	244.8	243.6	243.6	243.6	244.8	244.4	244.8	244.8	244.8	244.4
180°	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6



TEST NUMBER: P333216-935

CATALOG NUMBER: S125DIP-S850D590U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3
2.5°	1007.2	1011.5	1016.8	1020.8	1027.9	1031.1	1035.1	1038.3	1044.0	1049.4	1055.8
5°	939.4	946.9	957.2	968.4	981.4	990.3	1002.8	1010.4	1025.6	1039.5	1052.8
7.5°	877.8	887.1	901.6	916.0	933.0	948.3	964.0	981.4	1000.7	1023.6	1042.6
10°	835.6	848.1	863.8	881.7	902.2	920.1	941.1	959.8	983.6	1010.4	1035.4
12.5°	801.9	812.7	830.2	847.3	869.3	891.1	912.8	937.7	965.4	995.1	1026.5
15°	755.5	764.5	778.8	802.5	824.8	846.4	879.0	902.2	937.1	970.2	1008.1
17.5°	715.9	727.0	739.1	759.4	782.6	809.4	838.5	867.7	901.3	943.2	986.1
20°	691.6	700.6	714.5	730.0	754.7	781.5	809.3	838.7	879.9	923.3	969.2
22.5°	665.1	674.9	690.4	707.6	728.2	754.0	784.5	816.9	859.8	902.5	952.4
25°	634.0	640.7	655.0	670.2	690.8	712.6	744.4	780.2	822.6	871.3	922.3
27.5°	604.5	610.4	623.5	636.7	655.3	681.3	709.7	745.8	785.8	835.3	891.7
30°	583.4	589.7	601.3	615.6	633.5	656.3	685.4	719.4	762.2	810.5	869.6
32.5°	565.2	570.8	579.5	593.8	611.3	633.4	660.3	695.0	738.0	787.0	844.9
35°	536.9	543.2	549.9	561.1	576.3	597.7	627.2	659.9	701.0	748.4	801.6
37.5°	508.9	515.7	521.7	531.7	545.5	564.5	590.0	624.0	661.2	706.8	757.9
40°	491.4	496.7	501.6	512.4	526.2	544.1	567.8	598.2	637.6	680.0	722.5
42.5°	473.8	478.8	483.0	492.3	505.1	522.3	544.9	574.5	611.1	650.7	688.1
45°	446.2	449.4	454.3	462.3	472.6	488.2	510.1	536.5	567.3	604.9	633.1
47.5°	416.3	421.2	425.2	432.3	440.7	456.1	477.1	499.6	527.5	555.4	575.3
50°	393.4	398.4	404.2	410.9	418.9	433.3	452.5	475.3	498.9	520.4	537.4
52.5°	372.0	376.5	382.7	389.1	398.9	411.0	427.4	447.7	471.1	486.5	500.6
55°	340.3	342.4	349.7	355.9	365.2	374.2	390.7	408.6	422.9	434.5	446.2
57.5°	307.8	310.8	315.0	320.6	329.8	340.4	352.0	367.7	376.2	382.2	391.2
60°	287.1	287.9	290.6	297.3	304.4	313.8	327.3	338.5	344.7	349.7	357.2
62.5°	264.2	264.3	268.8	273.7	279.1	289.2	300.1	309.1	314.3	316.7	324.0
65°	232.0	231.2	233.8	237.8	244.1	250.8	260.2	268.3	267.8	270.4	274.9
67.5°	199.2	198.3	198.3	202.2	207.2	213.3	219.7	224.4	224.5	228.0	230.2
70°	177.0	174.4	176.2	179.3	181.5	186.4	193.6	195.4	195.8	197.6	199.8
72.5°	154.1	153.3	154.7	156.0	157.6	161.4	167.5	168.6	168.7	169.7	173.4
75°	122.5	121.6	120.7	122.1	123.8	126.5	128.7	130.5	130.1	130.5	133.2
77.5°	91.9	89.3	88.9	89.6	90.1	91.6	93.9	93.8	94.3	94.2	97.2
80°	72.8	69.3	68.9	68.9	69.3	70.2	71.1	72.0	70.6	72.0	72.8
82.5°	53.6	51.4	51.3	51.0	51.1	51.2	51.7	52.3	52.0	52.7	53.2
85°	29.5	28.6	27.3	28.2	27.7	26.3	27.3	25.9	25.5	25.9	26.3
87.5°	11.7	12.0	11.0	10.9	10.4	10.7	9.7	9.2	8.6	8.8	9.7
90°	8.4	7.8	6.9	6.4	5.4	4.9	4.0	2.9	2.0	0.9	0.5
92.5°	128.2	158.3	160.9	112.1	67.1	40.3	25.9	17.5	11.4	7.2	6.0
95°	425.9	435.1	355.1	219.6	111.5	59.0	36.9	26.0	20.7	16.7	16.2
97.5°	538.8	464.7	317.1	175.2	96.1	61.3	45.4	35.6	30.2	27.5	26.9
100°	566.3	443.5	282.9	159.1	95.3	66.8	52.1	42.7	37.4	35.4	34.4
102.5°	549.7	406.1	256.9	152.5	98.8	73.4	59.2	50.6	44.8	43.2	42.6
105°	497.1	356.1	231.8	149.8	106.1	84.5	70.7	62.9	57.9	55.5	55.5
107.5°	443.2	321.6	221.2	154.3	116.9	96.0	83.6	75.4	71.4	69.1	68.1
110°	412.6	305.5	218.1	158.6	124.8	104.6	91.9	84.5	80.1	78.1	77.1



TEST NUMBER: P333216-935

CATALOG NUMBER: S125DIP-S850D590U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	389.8	296.1	218.1	164.1	132.2	112.9	100.5	93.2	88.7	87.1	86.2
115°	364.9	285.9	219.6	172.4	143.9	125.7	113.5	106.1	101.7	100.2	99.2
117.5°	350.1	280.9	222.7	181.8	155.9	138.7	126.8	118.5	114.1	112.4	111.0
120°	341.8	278.4	225.9	188.1	164.5	147.3	135.1	126.7	122.3	120.4	118.8
122.5°	334.8	276.6	228.7	195.2	172.8	155.6	143.4	134.1	129.8	128.2	127.1
125°	325.1	274.1	233.3	204.8	183.7	167.5	154.7	145.3	140.9	138.5	137.5
127.5°	316.3	272.9	238.5	213.6	194.2	178.6	165.8	155.9	150.3	147.1	145.7
130°	310.4	272.1	241.7	219.6	200.9	185.6	172.9	162.6	156.2	152.2	150.8
132.5°	305.7	272.1	245.2	224.6	207.2	191.9	179.2	168.5	161.3	156.6	154.7
135°	300.1	272.1	249.9	231.8	215.6	200.4	187.1	176.8	168.9	163.1	161.1
137.5°	295.1	272.7	254.4	237.1	221.6	207.8	194.1	184.0	176.2	170.7	169.2
140°	292.7	273.1	256.4	240.6	225.9	211.7	198.5	189.1	181.2	175.3	173.8
142.5°	290.8	273.5	257.5	242.6	228.7	215.2	202.8	193.8	186.0	180.5	179.3
145°	287.8	273.1	258.8	245.6	233.3	220.5	209.2	200.4	193.5	188.6	187.6
147.5°	284.7	271.8	259.3	247.4	236.3	225.1	215.1	207.4	201.0	196.8	196.2
150°	282.4	270.6	259.3	248.5	238.2	227.4	219.0	212.2	205.8	202.3	201.4
152.5°	279.7	269.1	258.9	249.3	240.1	230.1	222.6	216.1	210.5	207.4	206.9
155°	275.0	266.2	257.9	249.9	242.1	233.8	226.9	222.0	217.1	214.1	214.1
157.5°	270.7	263.2	256.6	250.5	243.8	236.6	231.4	227.1	222.9	220.5	220.6
160°	267.2	261.3	255.4	250.5	244.6	238.2	233.8	229.9	226.4	224.5	225.0
162.5°	264.1	258.9	254.3	250.1	245.4	239.8	236.2	233.0	230.0	228.0	228.5
165°	259.3	255.4	252.4	249.5	245.6	241.7	238.7	236.7	234.3	232.8	233.8
167.5°	254.7	251.9	249.7	248.3	245.6	242.3	240.5	239.1	237.7	236.9	237.3
170°	251.9	249.9	248.5	247.5	245.6	243.1	241.7	240.6	239.7	239.2	239.7
172.5°	249.2	247.6	246.9	246.8	245.2	243.1	242.5	241.9	240.8	240.4	241.3
175°	245.6	245.0	245.0	245.6	244.6	243.1	243.1	243.1	242.6	242.1	243.1
177.5°	244.0	243.6	243.6	244.4	244.0	243.2	243.2	243.6	243.2	243.2	244.0
180°	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6



TEST NUMBER: P333216-935

CATALOG NUMBER: S125DIP-S850D590U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3
2.5°	1059.0	1064.0	1067.3	1073.3	1078.3	1081.2	1083.7	1085.9	1088.4	1090.5	1096.6
5°	1065.8	1077.5	1087.3	1102.5	1116.4	1127.0	1138.7	1149.0	1157.5	1169.6	1179.0
7.5°	1062.9	1083.6	1105.2	1128.7	1152.7	1175.1	1195.7	1214.9	1232.3	1253.4	1272.0
10°	1060.1	1088.2	1115.9	1147.6	1180.3	1208.0	1233.9	1260.3	1279.5	1306.4	1329.1
12.5°	1057.9	1091.1	1124.5	1162.7	1198.5	1237.7	1272.2	1291.4	1320.7	1342.1	1369.2
15°	1048.9	1092.7	1138.7	1181.6	1232.6	1268.8	1299.2	1336.8	1364.0	1391.3	1420.8
17.5°	1032.7	1082.3	1133.8	1190.1	1239.0	1277.8	1317.0	1353.2	1385.8	1422.4	1459.1
20°	1025.2	1074.8	1133.8	1191.5	1239.3	1280.0	1320.3	1360.0	1395.8	1442.7	1485.2
22.5°	1009.4	1069.4	1123.8	1180.0	1229.2	1273.6	1319.1	1364.3	1411.9	1464.9	1518.1
25°	981.4	1042.2	1099.8	1155.3	1204.9	1260.3	1309.1	1369.4	1430.2	1500.4	1566.6
27.5°	952.2	1010.4	1063.2	1116.8	1174.7	1237.4	1300.6	1369.2	1448.7	1537.3	1630.6
30°	928.6	983.6	1035.0	1089.9	1150.3	1221.0	1290.3	1371.7	1463.7	1563.4	1674.3
32.5°	901.0	951.7	1001.7	1060.0	1125.7	1200.2	1281.0	1370.2	1480.9	1594.2	1708.3
35°	853.9	896.4	947.8	1010.0	1084.2	1169.6	1263.0	1368.5	1495.5	1625.6	1721.7
37.5°	798.1	837.6	891.7	959.8	1037.7	1129.3	1240.2	1365.4	1500.2	1604.0	1635.0
40°	760.5	797.1	853.5	924.1	1003.7	1100.7	1222.3	1354.6	1485.2	1551.3	1525.9
42.5°	720.4	758.9	813.7	883.7	969.4	1075.0	1199.8	1332.1	1441.6	1466.6	1378.5
45°	657.2	697.0	751.1	821.7	913.9	1028.3	1158.4	1278.7	1341.7	1296.5	1160.2
47.5°	598.5	635.8	685.9	758.8	853.9	972.2	1097.5	1193.4	1198.4	1090.7	945.0
50°	558.4	592.8	643.3	716.2	810.5	930.4	1043.4	1119.0	1085.0	963.0	823.0
52.5°	519.1	552.8	602.6	674.8	768.0	877.8	983.0	1036.0	972.1	846.8	727.2
55°	462.3	491.8	540.5	607.1	695.7	797.6	887.0	905.3	822.2	698.8	601.8
57.5°	406.8	434.4	478.7	540.1	621.0	711.3	781.2	777.3	689.4	583.5	506.5
60°	369.3	396.1	435.5	495.3	569.1	647.0	706.8	692.5	605.4	514.1	449.4
62.5°	335.7	359.6	396.8	449.2	516.5	588.7	637.8	616.7	531.3	451.5	400.3
65°	286.1	306.3	338.0	382.7	438.6	498.1	536.1	508.8	435.9	373.8	332.6
67.5°	238.8	254.9	281.5	317.3	364.9	412.7	435.8	408.4	350.1	304.7	274.2
70°	208.8	223.1	243.7	275.4	317.0	357.2	374.6	350.1	300.0	261.1	239.2
72.5°	178.7	190.5	208.6	237.1	270.4	305.4	320.6	297.1	256.0	223.2	202.7
75°	138.2	146.2	158.7	178.4	204.7	232.5	241.0	220.4	194.1	169.4	156.0
77.5°	98.9	105.7	115.2	127.6	146.3	163.9	171.3	159.5	139.1	123.5	112.4
80°	76.0	79.6	87.6	97.9	112.7	123.8	128.7	121.1	106.9	95.2	86.7
82.5°	54.2	57.8	62.6	71.1	80.5	88.1	93.3	88.3	77.9	68.8	63.8
85°	26.3	28.6	31.3	34.9	42.0	46.5	46.1	42.9	38.9	35.3	32.6
87.5°	9.5	10.1	11.3	13.3	14.6	16.1	17.0	16.4	15.2	14.2	13.2
90°	0.9	2.0	2.9	4.0	4.9	5.4	6.4	6.9	7.8	8.4	8.9
92.5°	7.2	11.4	17.5	25.9	40.3	67.1	112.1	160.9	158.3	128.2	87.0
95°	16.7	20.7	26.0	36.9	59.0	111.5	219.6	355.1	435.1	425.9	353.1
97.5°	27.5	30.2	35.6	45.4	61.3	96.1	175.2	317.1	464.7	538.8	525.9
100°	35.4	37.4	42.7	52.1	66.8	95.3	159.1	282.9	443.5	566.3	604.1
102.5°	43.2	44.8	50.6	59.2	73.4	98.8	152.5	256.9	406.1	549.7	630.4
105°	55.5	57.9	62.9	70.7	84.5	106.1	149.8	231.8	356.1	497.1	614.9
107.5°	69.1	71.4	75.4	83.6	96.0	116.9	154.3	221.2	321.6	443.2	559.5
110°	78.1	80.1	84.5	91.9	104.6	124.8	158.6	218.1	305.5	412.6	518.7





TEST NUMBER: P333216-935

CATALOG NUMBER: S125DIP-S850D590U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	87.1	88.7	93.2	100.5	112.9	132.2	164.1	218.1	296.1	389.8	486.5
115°	100.2	101.7	106.1	113.5	125.7	143.9	172.4	219.6	285.9	364.9	445.9
117.5°	112.4	114.1	118.5	126.8	138.7	155.9	181.8	222.7	280.9	350.1	419.8
120°	120.4	122.3	126.7	135.1	147.3	164.5	188.1	225.9	278.4	341.8	405.7
122.5°	128.2	129.8	134.1	143.4	155.6	172.8	195.2	228.7	276.6	334.8	395.1
125°	138.5	140.9	145.3	154.7	167.5	183.7	204.8	233.3	274.1	325.1	379.6
127.5°	147.1	150.3	155.9	165.8	178.6	194.2	213.6	238.5	272.9	316.3	363.9
130°	152.2	156.2	162.6	172.9	185.6	200.9	219.6	241.7	272.1	310.4	354.1
132.5°	156.6	161.3	168.5	179.2	191.9	207.2	224.6	245.2	272.1	305.7	344.3
135°	163.1	168.9	176.8	187.1	200.4	215.6	231.8	249.9	272.1	300.1	331.5
137.5°	170.7	176.2	184.0	194.1	207.8	221.6	237.1	254.4	272.7	295.1	320.7
140°	175.3	181.2	189.1	198.5	211.7	225.9	240.6	256.4	273.1	292.7	314.8
142.5°	180.5	186.0	193.8	202.8	215.2	228.7	242.6	257.5	273.5	290.8	309.7
145°	188.6	193.5	200.4	209.2	220.5	233.3	245.6	258.8	273.1	287.8	303.1
147.5°	196.8	201.0	207.4	215.1	225.1	236.3	247.4	259.3	271.8	284.7	296.8
150°	202.3	205.8	212.2	219.0	227.4	238.2	248.5	259.3	270.6	282.4	293.2
152.5°	207.4	210.5	216.1	222.6	230.1	240.1	249.3	258.9	269.1	279.7	289.3
155°	214.1	217.1	222.0	226.9	233.8	242.1	249.9	257.9	266.2	275.0	283.4
157.5°	220.5	222.9	227.1	231.4	236.6	243.8	250.5	256.6	263.2	270.7	277.5
160°	224.5	226.4	229.9	233.8	238.2	244.6	250.5	255.4	261.3	267.2	273.5
162.5°	228.0	230.0	233.0	236.2	239.8	245.4	250.1	254.3	258.9	264.1	269.2
165°	232.8	234.3	236.7	238.7	241.7	245.6	249.5	252.4	255.4	259.3	263.2
167.5°	236.9	237.7	239.1	240.5	242.3	245.6	248.3	249.7	251.9	254.7	257.5
170°	239.2	239.7	240.6	241.7	243.1	245.6	247.5	248.5	249.9	251.9	254.4
172.5°	240.4	240.8	241.9	242.5	243.1	245.2	246.8	246.9	247.6	249.2	250.9
175°	242.1	242.6	243.1	243.1	243.1	244.6	245.6	245.0	245.0	245.6	247.0
177.5°	243.2	243.2	243.6	243.2	243.2	244.0	244.4	243.6	243.6	244.0	244.4
180°	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6	243.6



TEST NUMBER: P333216-935

CATALOG NUMBER: S125DIP-S850D590U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3
2.5°	1101.6	1104.5	1110.5	1108.4	1111.3	1112.7	1114.1
5°	1190.6	1204.9	1211.2	1210.2	1219.6	1217.4	1215.1
7.5°	1291.1	1306.1	1314.5	1325.0	1331.0	1331.5	1336.8
10°	1348.0	1367.6	1375.7	1386.8	1394.0	1398.0	1397.6
12.5°	1391.5	1407.0	1425.0	1430.5	1440.1	1445.2	1443.4
15°	1444.1	1468.7	1487.5	1496.8	1508.9	1512.4	1517.4
17.5°	1490.9	1523.9	1545.8	1574.9	1586.0	1592.7	1588.7
20°	1526.3	1569.7	1591.6	1626.5	1645.7	1656.0	1652.4
22.5°	1568.1	1615.1	1655.6	1685.8	1715.1	1729.0	1731.8
25°	1639.9	1704.3	1763.8	1803.5	1839.7	1848.2	1867.0
27.5°	1720.0	1796.0	1859.5	1901.3	1926.6	1936.0	1941.9
30°	1770.5	1846.0	1893.9	1920.6	1928.7	1927.8	1926.9
32.5°	1795.1	1842.5	1851.6	1844.1	1825.7	1810.2	1793.9
35°	1760.1	1724.8	1672.1	1604.1	1554.0	1503.6	1498.6
37.5°	1583.0	1470.1	1382.2	1284.2	1227.6	1192.7	1168.5
40°	1416.3	1288.1	1181.6	1098.9	1041.2	1018.5	996.1
42.5°	1235.4	1112.8	1018.6	949.4	906.0	880.7	863.1
45°	1003.7	895.5	821.7	771.6	737.3	717.6	706.4
47.5°	822.4	742.4	679.8	643.6	619.8	604.5	604.6
50°	725.1	648.7	607.1	578.5	557.9	545.9	548.1
52.5°	638.9	581.9	546.3	522.4	507.1	499.7	499.5
55°	534.3	493.1	469.8	452.5	442.1	433.7	435.5
57.5°	457.0	422.3	406.7	392.3	385.1	381.7	376.8
60°	409.1	382.3	368.9	357.2	350.1	347.4	342.4
62.5°	366.5	345.4	332.3	322.9	316.4	315.6	311.7
65°	308.1	292.0	280.3	275.9	269.1	267.3	267.3
67.5°	253.9	242.4	233.4	229.3	226.3	226.8	224.6
70°	220.0	210.6	204.7	200.3	198.0	198.5	196.7
72.5°	192.4	181.9	176.8	174.2	171.3	172.4	171.7
75°	145.8	140.3	137.7	135.0	133.2	132.3	131.5
77.5°	107.0	102.3	100.2	98.8	99.0	96.9	98.5
80°	82.7	78.7	77.3	75.1	74.6	74.6	74.2
82.5°	60.5	58.3	57.3	55.4	54.7	55.4	54.2
85°	31.3	29.5	29.1	29.1	28.2	27.3	29.5
87.5°	13.3	12.0	12.1	11.8	11.8	11.5	10.8
90°	9.3	9.8	10.8	10.8	10.8	11.3	11.3
92.5°	63.2	47.5	40.3	34.0	32.8	32.1	31.3
95°	278.4	218.1	176.8	142.0	127.2	123.3	115.5
97.5°	473.6	414.7	357.3	327.0	299.5	285.2	279.0
100°	580.1	529.4	478.4	444.4	409.1	391.0	383.1
102.5°	645.2	621.0	586.4	550.2	525.0	505.3	499.4
105°	682.2	703.8	698.4	682.7	666.5	656.7	650.7
107.5°	649.3	704.8	730.4	738.4	738.3	735.0	731.1
110°	612.0	681.2	723.0	745.0	754.4	757.9	757.9



TEST NUMBER: P333216-935

CATALOG NUMBER: S125DIP-S850D590U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	575.1	645.1	694.3	726.6	742.6	751.1	754.7
115°	522.1	589.4	642.9	681.2	704.8	718.5	725.0
117.5°	485.4	543.4	592.5	630.9	655.2	668.8	672.8
120°	464.6	518.7	561.9	598.2	621.8	635.1	638.9
122.5°	449.7	497.8	538.3	570.7	592.3	605.5	609.1
125°	429.7	472.5	507.8	535.4	555.5	566.3	571.2
127.5°	410.7	450.6	483.7	508.6	526.4	536.6	538.8
130°	397.4	435.7	467.5	492.1	508.3	518.1	521.1
132.5°	384.8	419.6	450.3	474.8	491.0	500.1	503.4
135°	365.4	396.8	424.8	446.4	462.6	471.5	474.4
137.5°	348.1	374.3	398.0	417.3	432.1	440.2	443.5
140°	337.9	360.5	381.2	399.3	412.1	419.4	421.9
142.5°	329.2	348.7	366.6	382.0	392.8	399.8	401.8
145°	318.2	333.5	346.7	358.5	366.9	372.3	374.3
147.5°	309.1	320.8	330.8	340.2	346.8	350.0	350.9
150°	304.0	313.3	322.2	329.6	335.4	337.4	337.9
152.5°	298.9	307.5	314.4	320.6	325.2	327.2	327.7
155°	291.3	298.1	303.5	308.4	311.9	313.3	313.8
157.5°	284.0	289.3	293.5	297.3	300.1	301.5	301.4
160°	278.4	283.4	286.8	290.2	292.7	293.7	293.2
162.5°	273.8	277.8	280.9	283.6	285.7	285.9	285.8
165°	266.7	269.7	272.1	274.1	275.0	275.0	275.0
167.5°	259.8	262.1	263.8	264.8	265.7	265.3	265.2
170°	255.9	257.4	258.3	259.3	259.8	259.8	259.3
172.5°	252.4	253.4	254.0	254.3	255.1	254.3	253.8
175°	247.0	248.1	248.1	248.1	248.5	247.5	247.0
177.5°	244.8	244.8	244.8	244.4	244.8	243.6	243.6
180°	243.6	243.6	243.6	243.6	243.6	243.6	243.6

(END OF REPORT)