

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333175-830

Luminaire Tested: **S125DIP-S610D590U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333175-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S610D590U830-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4584.6 lumens
Efficiency: N/A
Efficacy: 139.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333175-830

CATALOG NUMBER: S125DIP-S610D590U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333175-830

CATALOG NUMBER: S125DIP-S610D590U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	90	86	90	87	83	80	74	71	69	62	60	58	51	49	48	43
2	89	82	76	70	82	76	70	66	65	60	57	54	51	49	45	42	41	36
3	81	72	64	59	75	67	60	55	57	52	48	48	44	41	39	37	35	31
4	74	64	56	50	68	59	52	47	51	45	41	43	39	35	35	32	30	26
5	68	57	48	42	63	53	45	40	45	40	35	38	34	31	32	29	26	23
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	25	23	20
7	58	46	38	32	54	43	36	30	37	31	27	31	27	24	26	23	20	18
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16
9	50	38	30	25	46	36	29	24	31	25	22	26	22	19	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	21	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5846	5846	5846
5°	5859	5803	5841
10°	5823	5762	5795
15°	5760	5693	5717
20°	5670	5597	5606
25°	5573	5481	5476
30°	5452	5357	5330
35°	5324	5222	5149
40°	5193	5078	5005
45°	5050	4945	4847
50°	4893	4786	4641
55°	4741	4604	4476
60°	4561	4421	4265
65°	4345	4202	4060
70°	4137	3950	3814
75°	3770	3646	3521
80°	3355	3303	3221
85°	2920	2971	2816



TEST NUMBER: P333175-830

CATALOG NUMBER: S125DIP-S610D590U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.3	1.9
10°-20°	241.1	5.3
20°-30°	356.0	7.8
30°-40°	415.4	9.1
40°-50°	417.2	9.1
50°-60°	366.2	8.0
60°-70°	272.9	6.0
70°-80°	156.0	3.4
80°-90°	46.9	1.0
90°-100°	26.4	0.6
100°-110°	162.5	3.5
110°-120°	294.7	6.4
120°-130°	378.2	8.2
130°-140°	406.7	8.9
140°-150°	381.8	8.3
150°-160°	308.8	6.7
160°-170°	199.7	4.4
170°-180°	68.9	1.5
0°-30°	682.4	14.9
0°-40°	1097.8	23.9
0°-60°	1881.2	41.0
0°-90°	2357.0	51.4
90°-120°	483.5	10.5
90°-150°	1650.2	36.0
90°-180°	2228.0	48.6
0°-180°	4584.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	905	905	905	905	905	
5°	904	902	895	901	901	86
15°	862	859	852	855	855	243
25°	782	778	769	770	768	360
35°	675	672	662	659	653	422
45°	553	550	541	533	531	426
55°	421	418	409	403	398	376
65°	284	282	275	269	266	282
75°	151	150	146	144	141	161
85°	39	40	40	39	38	44
90°	1	5	9	11	13	3
95°	31	28	9	11	11	39
105°	158	160	160	160	160	168
115°	297	299	300	298	295	294
125°	422	426	426	424	422	377
135°	526	529	529	527	524	406
145°	610	611	611	612	609	382
155°	672	669	670	671	667	310
165°	709	706	707	709	706	200
175°	726	722	723	727	722	69
180°	726	726	726	726	726	



TEST NUMBER: P333175-830

CATALOG NUMBER: S125DIP-S610D590U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	905.2	905.2	905.2	905.2	905.2	905.2	905.2	905.2	905.2	905.2	905.2
2.5°	907.5	907.1	906.7	906.3	906.0	905.1	903.9	902.6	901.4	900.0	901.4
5°	903.8	903.4	903.1	902.8	902.5	901.5	899.9	898.3	896.7	895.1	896.6
7.5°	895.4	895.1	894.8	894.5	894.2	893.2	891.4	889.7	887.9	886.2	887.5
10°	888.0	887.7	887.4	887.0	886.7	885.7	883.9	882.2	880.4	878.7	880.0
12.5°	878.8	878.3	877.7	877.1	876.6	875.4	873.8	872.2	870.5	868.9	870.0
15°	861.5	861.0	860.5	860.1	859.6	858.5	856.8	855.0	853.2	851.5	852.2
17.5°	841.6	840.9	840.2	839.5	838.8	837.5	835.8	833.9	832.1	830.3	831.2
20°	825.0	824.6	824.3	824.1	823.7	822.6	820.5	818.4	816.3	814.3	815.4
22.5°	808.3	807.8	807.2	806.6	806.1	804.8	802.9	801.0	799.0	797.0	797.8
25°	782.0	781.2	780.4	779.7	778.8	777.4	775.3	773.3	771.2	769.1	769.5
27.5°	751.2	750.7	750.3	749.8	749.3	748.0	745.8	743.8	741.6	739.5	739.5
30°	731.1	730.7	730.2	729.7	729.2	727.8	725.5	723.0	720.7	718.3	717.9
32.5°	709.4	708.7	707.9	707.2	706.4	705.0	702.9	700.8	698.6	696.5	696.0
35°	675.3	674.7	674.0	673.4	672.8	671.4	669.1	666.8	664.7	662.4	661.7
37.5°	639.9	639.1	638.4	637.5	636.8	635.3	633.2	631.1	629.0	626.9	625.8
40°	615.9	615.1	614.3	613.5	612.7	611.1	609.0	606.7	604.5	602.3	600.9
42.5°	590.1	589.5	588.7	588.1	587.4	586.0	583.7	581.5	579.3	577.0	575.8
45°	552.9	552.2	551.6	550.9	550.4	549.0	547.1	545.3	543.3	541.4	539.5
47.5°	512.7	512.7	512.8	512.8	512.8	511.7	509.4	507.2	504.9	502.6	500.7
50°	487.0	486.4	486.0	485.5	485.0	483.9	481.9	480.0	478.2	476.3	474.2
52.5°	460.6	460.2	460.0	459.6	459.2	458.0	456.0	453.9	451.9	449.9	448.1
55°	421.1	420.6	420.1	419.6	419.1	417.8	415.6	413.4	411.1	408.9	407.5
57.5°	379.4	379.2	378.9	378.6	378.4	377.3	375.4	373.5	371.6	369.9	368.0
60°	353.1	352.4	351.8	351.1	350.5	349.3	347.6	345.8	344.0	342.3	340.7
62.5°	325.6	325.1	324.5	324.0	323.5	322.5	321.0	319.5	318.0	316.5	314.8
65°	284.3	284.0	283.7	283.3	283.0	282.0	280.2	278.5	276.7	275.0	273.5
67.5°	244.3	243.6	243.0	242.3	241.7	240.7	239.4	238.1	236.8	235.4	234.2
70°	219.1	218.4	217.5	216.8	215.9	214.8	213.4	212.0	210.6	209.2	208.1
72.5°	191.6	191.1	190.6	190.0	189.5	188.7	187.8	186.9	186.0	185.0	184.0
75°	151.1	150.8	150.4	150.1	149.9	149.3	148.5	147.7	146.8	146.1	145.6
77.5°	113.8	113.6	113.5	113.3	113.2	112.9	112.4	112.1	111.6	111.1	110.8
80°	90.2	90.2	90.2	90.2	90.2	90.1	89.7	89.4	89.2	88.8	88.6
82.5°	69.7	69.4	69.1	68.8	68.6	68.4	68.3	68.3	68.2	68.1	67.9
85°	39.4	39.6	39.7	39.9	40.1	40.1	40.1	40.1	40.1	40.1	40.0
87.5°	15.6	15.7	15.9	16.1	16.3	16.5	16.5	16.5	16.6	16.6	16.8
90°	0.6	1.5	2.5	3.4	4.3	5.3	6.1	7.0	7.7	8.6	9.2
92.5°	8.3	7.6	7.0	6.3	5.6	5.7	6.4	7.2	7.8	8.6	9.2
95°	30.6	30.3	30.0	29.6	29.2	26.8	22.2	17.7	13.1	8.6	9.2
97.5°	64.0	64.7	65.3	65.9	66.5	62.4	53.4	44.4	35.4	26.5	23.1
100°	89.8	90.2	90.5	90.9	91.2	91.6	92.2	92.7	93.1	93.6	75.8
102.5°	116.0	116.5	117.0	117.4	117.8	118.2	118.5	118.9	119.1	119.4	116.0
105°	158.1	158.5	159.1	159.6	160.0	160.2	160.2	160.2	160.2	160.2	160.2
107.5°	201.8	201.8	201.8	201.8	201.8	201.9	202.1	202.4	202.6	202.8	202.8
110°	230.2	230.2	230.2	230.2	230.2	230.3	230.5	230.7	231.0	231.2	230.9



TEST NUMBER: P333175-830

CATALOG NUMBER: S125DIP-S610D590U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	256.8	257.1	257.4	257.7	258.0	258.2	258.4	258.4	258.6	258.7	258.4
115°	296.8	297.5	298.0	298.6	299.3	299.6	299.7	299.8	299.9	300.1	299.6
117.5°	338.3	338.2	338.2	338.2	338.2	338.4	338.8	339.3	339.7	340.2	339.6
120°	364.1	363.9	363.8	363.7	363.5	363.7	364.1	364.4	364.8	365.1	364.9
122.5°	386.8	387.3	387.8	388.2	388.7	389.0	389.2	389.4	389.5	389.6	389.5
125°	422.2	423.0	423.8	424.6	425.5	425.9	425.9	425.9	425.9	425.9	425.5
127.5°	455.8	456.4	457.0	457.6	458.2	458.5	458.4	458.4	458.3	458.2	457.9
130°	476.5	477.0	477.7	478.2	478.8	479.2	479.3	479.5	479.6	479.7	479.3
132.5°	497.1	497.8	498.5	499.2	499.8	500.1	499.8	499.5	499.3	499.1	499.0
135°	526.5	527.2	527.9	528.6	529.3	529.6	529.3	529.0	528.9	528.6	528.4
137.5°	553.5	554.1	554.7	555.3	555.9	556.2	555.9	555.7	555.5	555.3	555.3
140°	571.1	571.4	571.6	571.8	572.0	572.1	572.0	571.8	571.7	571.7	571.8
142.5°	587.0	587.2	587.3	587.5	587.6	587.8	588.0	588.1	588.2	588.4	588.4
145°	610.4	610.6	610.9	611.1	611.3	611.4	611.4	611.4	611.4	611.4	611.5
147.5°	630.7	630.7	630.7	630.7	630.6	630.7	630.7	630.9	631.0	631.2	631.4
150°	643.7	643.5	643.2	643.0	642.7	642.7	643.0	643.2	643.5	643.7	643.9
152.5°	656.2	655.6	655.2	654.6	654.0	653.9	654.1	654.4	654.6	654.9	655.2
155°	672.2	671.5	670.8	670.1	669.3	669.1	669.3	669.6	669.8	670.1	670.4
157.5°	684.6	684.1	683.7	683.2	682.9	682.7	682.7	682.7	682.7	682.8	683.2
160°	693.1	692.5	691.7	691.0	690.3	690.0	690.1	690.2	690.3	690.5	691.0
162.5°	700.0	699.4	698.6	697.9	697.2	696.9	697.0	697.1	697.2	697.4	698.0
165°	709.3	708.6	707.8	707.2	706.4	706.2	706.2	706.3	706.5	706.6	707.3
167.5°	716.1	715.5	714.7	714.0	713.2	712.9	713.0	713.1	713.2	713.4	714.3
170°	720.1	719.3	718.4	717.6	716.7	716.3	716.4	716.6	716.7	716.8	717.7
172.5°	722.6	721.8	721.0	720.1	719.3	719.0	719.2	719.4	719.6	719.8	720.7
175°	725.5	724.7	724.0	723.3	722.6	722.3	722.4	722.6	722.6	722.7	723.7
177.5°	726.7	726.1	725.6	725.0	724.4	724.2	724.2	724.3	724.4	724.5	725.3
180°	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5



TEST NUMBER: P333175-830

CATALOG NUMBER: S125DIP-S610D590U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	905.2	905.2	905.2	905.2	905.2	905.2	905.2	905.2
2.5°	902.6	903.9	905.1	905.7	905.6	905.4	905.3	905.2
5°	898.1	899.5	900.9	901.5	901.4	901.3	901.1	900.9
7.5°	888.9	890.3	891.7	892.4	892.2	892.0	891.9	891.7
10°	881.3	882.5	883.8	884.4	884.2	884.0	883.8	883.7
12.5°	871.0	872.0	873.0	873.5	873.5	873.5	873.5	873.4
15°	853.1	853.8	854.7	855.1	855.1	855.1	855.1	855.1
17.5°	832.3	833.2	834.2	834.3	833.5	832.7	832.0	831.1
20°	816.4	817.6	818.7	818.9	818.0	817.3	816.4	815.7
22.5°	798.5	799.3	800.0	800.1	799.6	799.0	798.4	798.0
25°	769.8	770.1	770.4	770.3	769.9	769.4	768.9	768.5
27.5°	739.6	739.7	739.7	739.5	739.0	738.6	738.1	737.6
30°	717.7	717.4	717.0	716.6	716.1	715.7	715.2	714.7
32.5°	695.4	694.7	694.2	693.5	692.7	691.8	690.9	690.0
35°	660.8	660.1	659.2	658.2	657.0	655.6	654.4	653.1
37.5°	624.5	623.4	622.2	621.2	620.5	619.8	619.1	618.3
40°	599.4	597.9	596.5	595.6	595.1	594.7	594.2	593.7
42.5°	574.5	573.2	571.8	570.8	570.0	569.4	568.6	567.9
45°	537.5	535.6	533.8	532.5	532.1	531.6	531.1	530.7
47.5°	498.7	496.7	494.8	493.3	492.2	491.1	489.9	488.8
50°	472.1	470.0	468.0	466.4	465.2	464.1	463.0	461.9
52.5°	446.2	444.4	442.6	441.1	439.9	438.6	437.3	436.1
55°	406.0	404.6	403.2	401.9	400.8	399.6	398.6	397.5
57.5°	366.1	364.3	362.4	361.2	360.6	360.0	359.4	358.8
60°	339.1	337.5	335.9	334.6	333.5	332.3	331.2	330.2
62.5°	313.1	311.4	309.6	308.4	307.6	306.6	305.8	304.9
65°	272.1	270.7	269.3	268.2	267.6	266.9	266.4	265.7
67.5°	233.1	231.9	230.6	229.8	229.4	229.0	228.7	228.3
70°	207.2	206.2	205.3	204.5	203.9	203.2	202.6	202.0
72.5°	182.9	181.8	180.7	179.8	179.2	178.6	178.0	177.3
75°	145.2	144.7	144.2	143.6	143.0	142.3	141.8	141.1
77.5°	110.6	110.3	110.0	109.6	109.1	108.8	108.3	107.8
80°	88.5	88.3	88.1	87.9	87.6	87.3	87.0	86.6
82.5°	67.6	67.3	67.0	66.8	66.8	66.7	66.6	66.6
85°	39.8	39.6	39.5	39.2	38.9	38.5	38.3	38.0
87.5°	16.9	17.0	17.1	17.1	16.9	16.7	16.5	16.3
90°	9.8	10.4	11.0	11.5	11.9	12.2	12.5	12.9
92.5°	9.8	10.4	11.0	11.4	11.5	11.7	11.9	12.1
95°	9.8	10.4	11.0	11.3	11.3	11.3	11.3	11.3
97.5°	19.7	16.3	13.0	11.3	11.3	11.3	11.3	11.3
100°	58.0	40.2	22.3	13.2	12.7	12.3	11.8	11.3
102.5°	112.6	109.2	105.9	100.2	92.0	83.9	75.8	67.7
105°	160.2	160.2	160.2	160.2	160.0	159.9	159.9	159.7
107.5°	202.9	202.9	202.9	202.7	202.5	202.1	201.7	201.3
110°	230.5	230.2	229.8	229.7	229.8	229.9	230.1	230.2



TEST NUMBER: P333175-830

CATALOG NUMBER: S125DIP-S610D590U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	257.9	257.4	256.9	256.7	256.5	256.3	256.2	256.0
115°	299.1	298.6	298.1	297.6	296.8	296.1	295.4	294.7
117.5°	338.9	338.3	337.7	337.2	337.0	336.6	336.3	336.0
120°	364.7	364.4	364.2	363.7	363.2	362.6	361.9	361.4
122.5°	389.2	389.0	388.7	388.2	387.6	386.8	386.2	385.5
125°	425.0	424.4	424.0	423.6	423.2	422.8	422.5	422.2
127.5°	457.6	457.4	457.1	456.6	455.6	454.8	453.9	453.0
130°	479.0	478.6	478.2	477.8	477.2	476.5	476.0	475.4
132.5°	498.9	498.8	498.8	498.4	497.9	497.2	496.6	496.1
135°	528.1	527.9	527.6	527.2	526.5	525.8	525.0	524.3
137.5°	555.3	555.4	555.4	555.2	554.6	553.9	553.4	552.7
140°	572.1	572.3	572.6	572.3	571.7	570.9	570.2	569.5
142.5°	588.5	588.5	588.6	588.2	587.6	586.8	586.1	585.4
145°	611.7	611.8	611.9	611.6	610.9	610.2	609.4	608.7
147.5°	631.5	631.7	631.8	631.4	630.6	629.7	628.9	628.0
150°	644.1	644.4	644.6	644.3	643.4	642.3	641.4	640.5
152.5°	655.3	655.6	655.8	655.5	654.7	653.8	652.9	652.1
155°	670.8	671.1	671.5	671.2	670.2	669.3	668.4	667.3
157.5°	683.5	683.9	684.3	684.0	683.1	682.0	681.1	680.1
160°	691.4	691.9	692.4	692.1	691.2	690.2	689.3	688.3
162.5°	698.7	699.4	700.0	699.8	698.8	697.8	696.7	695.6
165°	708.0	708.8	709.5	709.4	708.4	707.5	706.5	705.5
167.5°	715.1	716.0	716.8	716.7	715.7	714.5	713.5	712.4
170°	718.8	719.7	720.7	720.6	719.5	718.4	717.4	716.3
172.5°	721.5	722.5	723.3	723.2	722.1	721.0	719.9	718.9
175°	724.6	725.6	726.6	726.5	725.5	724.3	723.3	722.2
177.5°	725.9	726.6	727.3	727.2	726.4	725.7	724.9	724.2
180°	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5

(END OF REPORT)