

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333233-830

Luminaire Tested: **S125DIP-S850D1035U830-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333233-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S850D1035U830-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6630.5 lumens
Efficiency: N/A
Efficacy: 127.5 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333233-830

CATALOG NUMBER: S125DIP-S850D1035U830-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333233-830

CATALOG NUMBER: S125DIP-S850D1035U830-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	68	68	68	55	55	55	49
1	98	94	90	86	90	86	83	80	73	71	68	61	59	57	49	48	47	42
2	89	82	76	71	82	76	71	66	64	60	57	53	51	48	44	42	40	35
3	81	72	65	59	75	67	61	55	57	52	48	47	44	41	39	36	34	30
4	75	64	56	50	69	59	52	47	50	45	41	42	38	35	35	32	30	26
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26	23
6	63	51	43	37	58	48	40	35	41	35	31	34	30	27	28	25	23	20
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20	18
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7447	7447	7447	7447
5°	8624	7472	6543	7472
10°	10033	7433	5732	7433
15°	11106	7379	5288	7379
20°	12432	7292	4931	7292
25°	14564	7195	4757	7195
30°	15731	7099	4606	7099
35°	12934	6918	4507	6918
40°	9193	6668	4398	6668
45°	7063	6330	4337	6330
50°	6028	5910	4326	5910
55°	5368	5499	4365	5499
60°	4841	5052	4476	5052
65°	4473	4600	4592	4600
70°	4067	4132	4658	4132
75°	3591	3638	4616	3638
80°	3020	2964	4225	2964
85°	2393	2134	3409	2134



TEST NUMBER: P333233-830

CATALOG NUMBER: S125DIP-S850D1035U830-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.0	1.7
10°-20°	330.5	5.0
20°-30°	536.7	8.1
30°-40°	654.6	9.9
40°-50°	595.5	9.0
50°-60°	474.4	7.2
60°-70°	330.4	5.0
70°-80°	176.2	2.7
80°-90°	47.1	0.7
90°-100°	81.0	1.2
100°-110°	239.1	3.6
110°-120°	405.1	6.1
120°-130°	533.1	8.0
130°-140°	597.3	9.0
140°-150°	585.5	8.8
150°-160°	491.7	7.4
160°-170°	326.9	4.9
170°-180°	114.4	1.7
0°-30°	978.2	14.8
0°-40°	1632.8	24.6
0°-60°	2702.7	40.8
0°-90°	3256.4	49.1
90°-120°	725.2	10.9
90°-150°	2441.1	36.8
90°-180°	3374.0	50.9
0°-180°	6630.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1153	1153	1153	1153	1153	
5°	1330	1152	1009	1152	1330	134
15°	1661	1104	791	1104	1661	476
25°	2044	1010	668	1010	2044	934
35°	1640	878	572	878	1640	1004
45°	773	693	475	693	773	619
55°	477	488	388	488	477	429
65°	293	301	300	301	293	290
75°	144	146	185	146	144	155
85°	32	29	46	29	32	38
90°	23	1	23	1	23	14
95°	81	61	81	61	81	82
105°	233	214	233	214	233	247
115°	409	406	409	406	409	405
125°	596	592	596	592	596	532
135°	772	770	772	770	772	596
145°	936	933	936	933	936	584
155°	1067	1067	1067	1067	1067	491
165°	1157	1160	1157	1160	1157	326
175°	1202	1206	1202	1206	1202	114
180°	1209	1209	1209	1209	1209	



TEST NUMBER: P333233-830

CATALOG NUMBER: S125DIP-S850D1035U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1
2.5°	1219.7	1218.0	1216.5	1213.3	1215.7	1209.1	1205.9	1200.4	1193.8	1191.5	1188.7
5°	1330.2	1332.7	1335.1	1324.8	1325.9	1319.0	1303.3	1290.6	1280.3	1267.2	1257.8
7.5°	1463.4	1457.5	1457.1	1450.5	1439.0	1429.8	1413.3	1392.4	1372.2	1349.1	1329.9
10°	1529.9	1530.4	1526.0	1518.2	1506.0	1497.1	1475.6	1455.0	1430.1	1400.7	1379.7
12.5°	1580.1	1582.1	1576.5	1565.9	1560.0	1540.2	1523.3	1498.9	1469.2	1445.8	1413.7
15°	1661.1	1655.7	1651.8	1638.6	1628.3	1607.8	1580.8	1555.4	1523.1	1493.2	1463.4
17.5°	1739.2	1743.5	1736.2	1724.1	1692.2	1668.2	1632.1	1597.2	1557.1	1517.0	1481.4
20°	1808.9	1812.8	1801.6	1780.6	1742.4	1718.3	1670.8	1625.9	1579.3	1528.0	1488.8
22.5°	1895.8	1892.7	1877.5	1845.5	1812.4	1768.1	1716.7	1661.9	1603.6	1545.6	1493.6
25°	2043.8	2023.3	2013.9	1974.3	1930.8	1865.7	1795.2	1715.0	1642.5	1565.7	1499.1
27.5°	2125.8	2119.4	2109.0	2081.4	2035.6	1966.0	1882.9	1785.1	1682.9	1585.9	1498.8
30°	2109.4	2110.4	2111.4	2102.5	2073.2	2020.8	1938.2	1832.9	1711.5	1602.3	1501.6
32.5°	1963.8	1981.6	1998.6	2018.7	2026.9	2016.9	1965.1	1870.1	1745.2	1621.2	1500.0
35°	1640.5	1646.0	1701.2	1756.1	1830.4	1888.2	1926.8	1884.8	1779.5	1637.1	1498.1
37.5°	1279.1	1305.6	1343.9	1405.8	1513.2	1609.3	1733.0	1789.8	1755.9	1642.3	1494.7
40°	1090.4	1114.9	1139.8	1203.0	1293.5	1410.0	1550.5	1670.4	1698.3	1625.9	1482.9
42.5°	944.8	964.1	991.8	1039.3	1115.0	1218.1	1352.4	1509.1	1605.5	1578.1	1458.3
45°	773.3	785.5	807.1	844.7	899.6	980.3	1098.7	1270.1	1419.3	1468.8	1399.8
47.5°	661.9	661.8	678.5	704.6	744.1	812.8	900.3	1034.5	1194.0	1311.9	1306.5
50°	600.0	597.6	610.8	633.3	664.6	710.1	793.8	901.0	1054.2	1187.8	1225.0
52.5°	546.8	547.1	555.2	571.8	598.0	637.0	699.5	796.1	927.0	1064.1	1134.2
55°	476.7	474.8	484.0	495.3	514.3	539.8	584.8	658.7	765.0	900.0	991.1
57.5°	412.5	417.8	421.6	429.4	445.3	462.3	500.3	554.5	638.8	754.7	850.9
60°	374.8	380.3	383.2	391.1	403.8	418.5	447.8	491.9	562.8	662.7	758.1
62.5°	341.2	345.4	346.4	353.5	363.8	378.1	401.2	438.2	494.3	581.6	675.1
65°	292.7	292.7	294.6	302.0	306.9	319.6	337.2	364.1	409.2	477.2	556.9
67.5°	245.9	248.3	247.7	251.0	255.5	265.3	278.0	300.2	333.6	383.2	447.0
70°	215.4	217.3	216.8	219.2	224.1	230.5	240.8	261.8	285.8	328.4	383.2
72.5°	187.9	188.7	187.5	190.7	193.6	199.2	210.7	221.9	244.3	280.2	325.3
75°	143.9	144.9	145.8	147.8	150.7	153.6	159.6	170.8	185.5	212.4	241.3
77.5°	107.8	106.0	108.4	108.1	109.7	112.0	117.2	123.1	135.2	152.2	174.6
80°	81.2	81.7	81.7	82.2	84.6	86.1	90.6	94.9	104.2	117.0	132.6
82.5°	59.3	60.6	59.9	60.7	62.8	63.8	66.3	69.8	75.3	85.3	96.6
85°	32.3	29.9	30.8	31.9	31.9	32.3	34.2	35.7	38.6	42.6	46.9
87.5°	13.9	14.6	14.8	14.7	15.0	14.8	16.2	15.9	17.0	17.9	19.1
90°	22.6	22.0	21.3	20.7	20.1	19.2	18.2	17.2	16.1	15.1	13.6
92.5°	44.4	43.9	43.5	43.1	42.6	41.7	40.2	38.9	37.5	36.1	34.3
95°	81.0	80.5	80.1	79.6	79.3	78.3	76.8	75.4	73.9	72.5	70.4
97.5°	122.7	122.4	122.2	122.0	121.7	120.9	119.5	118.1	116.8	115.4	112.4
100°	154.3	153.9	153.4	153.1	152.7	151.5	149.6	147.7	145.8	143.9	141.3
102.5°	186.0	185.4	184.7	184.2	183.6	182.3	180.2	178.1	176.2	174.1	172.7
105°	233.4	232.7	232.1	231.5	230.8	229.9	228.7	227.4	226.1	224.9	223.7
107.5°	281.9	282.0	282.0	282.0	282.1	281.8	281.2	280.5	279.9	279.3	278.3
110°	318.0	318.3	318.5	318.7	318.9	318.7	318.0	317.4	316.8	316.1	315.6



TEST NUMBER: P333233-830

CATALOG NUMBER: S125DIP-S850D1035U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	353.5	353.8	354.2	354.6	355.0	355.0	354.7	354.4	354.1	353.8	353.0
115°	409.3	409.5	409.7	409.9	410.2	410.4	410.6	410.8	411.0	411.2	410.8
117.5°	463.9	464.8	465.6	466.4	467.2	467.6	467.4	467.2	467.1	466.9	466.6
120°	501.5	502.4	503.2	504.1	504.9	505.3	505.3	505.3	505.3	505.3	505.1
122.5°	539.2	539.9	540.5	541.2	541.9	542.2	542.4	542.6	542.8	542.9	542.4
125°	595.7	595.9	596.1	596.3	596.4	596.8	597.2	597.7	598.0	598.5	598.2
127.5°	649.9	650.3	650.6	651.1	651.5	651.9	652.1	652.2	652.4	652.7	652.4
130°	686.0	686.4	686.8	687.2	687.7	688.0	688.2	688.3	688.6	688.8	688.3
132.5°	719.8	720.5	721.0	721.6	722.2	722.6	722.8	723.0	723.2	723.4	723.5
135°	772.5	773.4	774.2	775.1	775.9	776.3	776.3	776.3	776.3	776.3	776.1
137.5°	824.2	825.2	826.2	827.3	828.3	828.7	828.4	828.2	827.9	827.6	827.3
140°	857.2	858.3	859.3	860.4	861.4	861.8	861.3	860.9	860.4	860.1	859.4
142.5°	888.8	889.9	891.0	892.0	893.1	893.4	893.2	893.0	892.7	892.4	891.6
145°	936.3	936.9	937.5	938.2	938.8	939.1	939.1	939.1	939.1	939.1	938.5
147.5°	976.8	978.2	979.6	981.0	982.4	982.9	982.4	981.8	981.4	980.9	980.3
150°	1006.8	1007.3	1007.7	1008.1	1008.5	1008.7	1008.7	1008.7	1008.7	1008.7	1007.9
152.5°	1031.7	1032.5	1033.2	1034.0	1034.7	1034.8	1034.3	1033.9	1033.3	1032.8	1032.5
155°	1067.1	1068.1	1069.1	1070.3	1071.3	1071.4	1070.5	1069.7	1068.8	1068.0	1067.8
157.5°	1096.6	1098.0	1099.4	1100.8	1102.1	1102.4	1101.5	1100.7	1099.9	1099.1	1098.9
160°	1116.9	1118.0	1119.1	1120.1	1121.2	1121.2	1120.4	1119.6	1118.7	1117.9	1117.7
162.5°	1134.3	1135.5	1136.7	1137.9	1139.2	1139.3	1138.2	1137.2	1136.2	1135.2	1135.2
165°	1157.4	1158.7	1159.9	1161.2	1162.4	1162.6	1161.8	1160.9	1160.2	1159.3	1159.0
167.5°	1175.8	1177.1	1178.5	1179.8	1181.0	1181.1	1179.8	1178.6	1177.3	1176.0	1176.0
170°	1185.6	1187.1	1188.5	1190.1	1191.5	1191.6	1190.3	1189.1	1187.9	1186.6	1186.6
172.5°	1193.9	1195.2	1196.6	1197.8	1199.1	1199.1	1197.9	1196.7	1195.3	1194.1	1194.1
175°	1201.6	1203.1	1204.6	1206.1	1207.5	1207.6	1206.4	1205.1	1203.8	1202.6	1202.6
177.5°	1206.2	1207.3	1208.5	1209.7	1210.9	1210.9	1209.9	1208.9	1208.0	1206.9	1207.1
180°	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2



TEST NUMBER: P333233-830

CATALOG NUMBER: S125DIP-S850D1035U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1
2.5°	1186.4	1183.6	1180.4	1175.0	1168.4	1164.8	1159.3	1155.8	1148.8	1142.9	1136.6
5°	1246.5	1233.8	1222.1	1206.9	1190.2	1179.5	1166.8	1152.5	1137.9	1122.8	1106.1
7.5°	1308.9	1286.4	1261.9	1235.6	1209.8	1186.2	1163.6	1141.3	1120.6	1095.5	1074.3
10°	1350.8	1322.4	1292.0	1256.3	1221.6	1191.3	1160.5	1133.5	1106.1	1076.8	1050.7
12.5°	1392.7	1354.9	1312.0	1272.8	1231.0	1194.4	1158.1	1123.7	1089.3	1056.8	1026.5
15°	1422.3	1388.9	1349.3	1293.5	1246.5	1196.2	1148.2	1103.6	1062.1	1025.9	987.7
17.5°	1441.7	1398.8	1356.3	1302.8	1241.1	1184.8	1130.5	1079.5	1032.6	986.7	949.9
20°	1445.3	1401.2	1356.7	1304.3	1241.1	1176.6	1122.3	1061.0	1010.7	963.2	918.1
22.5°	1444.1	1394.2	1345.7	1291.8	1230.2	1170.7	1105.0	1042.6	988.0	941.2	894.3
25°	1433.0	1379.7	1319.0	1264.7	1204.0	1140.9	1074.3	1009.7	953.9	900.5	854.0
27.5°	1423.8	1354.6	1285.9	1222.6	1163.9	1106.1	1042.4	976.2	914.4	860.3	816.4
30°	1412.5	1336.6	1259.2	1193.2	1133.0	1076.8	1016.5	952.0	887.3	834.4	787.5
32.5°	1402.3	1313.9	1232.3	1160.4	1096.6	1041.9	986.4	924.9	861.5	807.9	760.8
35°	1382.6	1280.3	1186.8	1105.6	1037.6	981.3	934.8	877.5	819.3	767.4	722.4
37.5°	1357.6	1236.2	1136.0	1050.7	976.2	916.9	873.6	829.6	773.7	723.8	683.1
40°	1338.0	1204.9	1098.7	1011.6	934.3	872.6	832.5	790.9	744.4	698.0	654.9
42.5°	1313.4	1176.8	1061.2	967.4	890.8	830.8	788.6	753.3	712.3	668.9	629.0
45°	1268.1	1125.7	1000.4	899.6	822.2	763.0	719.4	693.1	662.2	621.0	587.3
47.5°	1201.5	1064.3	934.7	830.7	750.8	696.0	655.2	629.8	608.0	577.5	546.9
50°	1142.3	1018.5	887.3	784.0	704.3	648.9	611.3	588.2	569.7	546.2	520.3
52.5°	1076.1	960.9	840.7	738.7	659.7	605.1	568.3	548.0	532.5	515.7	490.1
55°	971.0	873.2	761.6	664.6	591.7	538.4	506.1	488.4	475.7	463.0	447.3
57.5°	855.2	778.6	679.8	591.3	524.1	475.5	445.4	428.2	418.4	411.8	402.6
60°	773.7	708.2	623.0	542.2	476.7	433.7	404.3	391.1	382.8	377.3	370.5
62.5°	698.2	644.4	565.4	491.7	434.4	393.7	367.5	354.7	346.7	344.0	338.4
65°	586.8	545.3	480.1	419.0	370.0	335.3	313.2	301.0	296.1	293.1	293.7
67.5°	477.1	451.8	399.4	347.3	308.2	279.1	261.5	252.0	249.6	245.7	245.6
70°	410.1	391.1	347.0	301.5	266.7	244.2	228.6	218.8	216.3	214.3	213.9
72.5°	351.0	334.3	296.1	259.6	228.4	208.6	195.7	189.8	185.8	184.6	184.5
75°	263.8	254.5	224.1	195.3	173.7	160.0	151.3	145.8	142.9	142.4	142.9
77.5°	187.6	179.5	160.1	139.7	126.1	115.7	108.3	106.4	103.1	103.2	102.6
80°	140.9	135.5	123.4	107.2	96.0	87.1	83.2	79.7	78.8	77.3	78.8
82.5°	102.2	96.4	88.1	77.9	68.5	63.2	59.3	58.2	57.7	56.9	57.3
85°	50.4	50.9	46.0	38.2	34.2	31.3	28.8	28.8	28.4	27.9	28.4
87.5°	19.7	18.6	16.7	15.3	12.9	11.4	10.7	10.7	9.9	9.9	10.6
90°	12.2	10.7	9.2	7.6	5.9	4.2	2.6	0.9	2.6	4.2	5.9
92.5°	32.5	30.7	28.9	27.4	26.3	25.1	23.9	22.8	23.9	25.1	26.3
95°	68.2	66.2	64.1	62.9	62.4	62.0	61.5	61.2	61.5	62.0	62.4
97.5°	109.6	106.7	103.9	102.3	102.2	102.0	101.8	101.6	101.8	102.0	102.2
100°	138.6	135.8	133.1	131.8	131.8	131.8	131.8	131.8	131.8	131.8	131.8
102.5°	171.4	169.9	168.5	167.5	166.6	165.8	164.9	164.1	164.9	165.8	166.6
105°	222.3	221.1	219.9	218.8	217.7	216.6	215.6	214.5	215.6	216.6	217.7
107.5°	277.4	276.4	275.4	274.5	273.4	272.3	271.3	270.2	271.3	272.3	273.4
110°	314.9	314.2	313.7	312.8	311.8	310.8	309.7	308.7	309.7	310.8	311.8



TEST NUMBER: P333233-830

CATALOG NUMBER: S125DIP-S850D1035U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	352.2	351.5	350.6	350.0	349.4	348.8	348.4	347.8	348.4	348.8	349.4
115°	410.4	409.9	409.5	408.9	408.1	407.3	406.4	405.6	406.4	407.3	408.1
117.5°	466.2	465.8	465.4	465.1	464.7	464.3	463.9	463.5	463.9	464.3	464.7
120°	504.9	504.6	504.4	503.9	502.8	501.7	500.7	499.6	500.7	501.7	502.8
122.5°	541.9	541.3	540.7	540.4	540.0	539.6	539.2	538.9	539.2	539.6	540.0
125°	598.0	597.9	597.7	596.9	595.7	594.4	593.1	591.9	593.1	594.4	595.7
127.5°	652.1	652.0	651.7	651.2	650.4	649.8	649.0	648.4	649.0	649.8	650.4
130°	688.0	687.6	687.1	686.4	685.3	684.3	683.2	682.2	683.2	684.3	685.3
132.5°	723.6	723.7	723.8	722.9	721.2	719.5	717.8	716.0	717.8	719.5	721.2
135°	775.9	775.7	775.5	774.8	773.5	772.2	771.0	769.8	771.0	772.2	773.5
137.5°	826.8	826.3	825.9	825.0	823.8	822.6	821.3	820.2	821.3	822.6	823.8
140°	858.8	858.2	857.5	856.7	855.6	854.6	853.6	852.5	853.6	854.6	855.6
142.5°	890.9	890.0	889.3	888.4	887.5	886.6	885.8	884.9	885.8	886.6	887.5
145°	937.8	937.3	936.6	935.9	935.0	934.2	933.4	932.6	933.4	934.2	935.0
147.5°	979.9	979.4	978.9	978.4	978.0	977.5	977.0	976.6	977.0	977.5	978.0
150°	1007.1	1006.3	1005.4	1005.1	1005.3	1005.5	1005.7	1005.9	1005.7	1005.5	1005.3
152.5°	1032.2	1031.8	1031.5	1031.1	1030.9	1030.6	1030.3	1030.0	1030.3	1030.6	1030.9
155°	1067.6	1067.4	1067.1	1067.1	1067.1	1067.1	1067.1	1067.1	1067.1	1067.1	1067.1
157.5°	1098.6	1098.4	1098.3	1098.3	1098.8	1099.3	1099.8	1100.2	1099.8	1099.3	1098.8
160°	1117.5	1117.3	1117.1	1117.3	1117.9	1118.5	1119.2	1119.7	1119.2	1118.5	1117.9
162.5°	1135.1	1135.1	1135.0	1135.3	1135.7	1136.1	1136.6	1137.1	1136.6	1136.1	1135.7
165°	1158.9	1158.7	1158.5	1158.6	1159.0	1159.4	1159.8	1160.3	1159.8	1159.4	1159.0
167.5°	1176.0	1176.0	1176.0	1176.5	1177.3	1178.2	1178.9	1179.8	1178.9	1178.2	1177.3
170°	1186.6	1186.6	1186.6	1187.0	1187.9	1188.6	1189.5	1190.3	1189.5	1188.6	1187.9
172.5°	1194.1	1194.1	1194.1	1194.6	1195.3	1196.2	1197.0	1197.9	1197.0	1196.2	1195.3
175°	1202.6	1202.6	1202.6	1203.0	1203.8	1204.7	1205.5	1206.4	1205.5	1204.7	1203.8
177.5°	1207.2	1207.4	1207.6	1208.0	1208.6	1209.4	1210.0	1210.7	1210.0	1209.4	1208.6
180°	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2



TEST NUMBER: P333233-830

CATALOG NUMBER: S125DIP-S850D1035U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1
2.5°	1133.1	1128.8	1125.3	1117.5	1113.1	1107.3	1102.6	1107.7	1102.2	1104.6	1101.0
5°	1097.8	1084.1	1074.3	1060.1	1047.8	1036.6	1028.3	1026.8	1022.8	1021.0	1015.0
7.5°	1055.3	1038.1	1021.3	1002.8	987.0	971.1	960.9	952.5	947.0	939.6	934.6
10°	1030.2	1007.2	987.7	965.2	945.6	928.4	914.7	907.9	901.5	892.2	888.8
12.5°	999.3	975.5	951.6	927.6	908.8	889.7	877.9	867.5	863.2	852.6	851.6
15°	962.2	926.5	903.0	878.5	852.5	836.9	827.1	815.9	811.0	803.6	798.2
17.5°	917.9	886.1	856.7	831.3	809.1	795.9	783.7	776.0	767.6	762.8	754.0
20°	885.9	855.5	826.1	799.2	782.1	766.9	757.1	749.8	741.0	738.6	729.7
22.5°	858.8	825.4	797.2	774.6	755.8	738.8	728.1	723.2	717.1	709.5	707.8
25°	814.9	780.1	756.2	733.7	717.0	701.3	694.0	687.7	681.7	676.4	674.4
27.5°	776.9	745.8	717.4	697.0	682.6	668.3	661.8	654.0	649.8	645.5	640.2
30°	750.3	718.5	693.5	673.9	658.3	645.5	638.7	633.3	629.4	625.5	622.5
32.5°	722.8	693.4	669.2	650.1	634.4	624.8	618.7	614.9	610.6	605.9	602.2
35°	686.6	654.3	630.8	614.3	602.0	594.7	587.8	584.4	579.5	579.5	575.5
37.5°	645.8	617.9	597.2	582.0	571.1	564.5	557.0	554.7	551.6	549.5	548.2
40°	621.6	595.6	576.1	560.9	549.1	543.8	537.9	534.0	532.0	529.5	528.6
42.5°	596.5	571.7	553.0	538.9	528.8	524.1	518.7	515.9	512.0	508.8	508.2
45°	558.5	534.4	517.4	506.1	497.3	491.9	488.4	482.6	480.6	476.7	476.2
47.5°	522.3	499.3	482.5	473.3	465.5	461.1	455.7	449.9	447.6	445.6	445.4
50°	495.3	474.3	458.5	449.8	442.4	436.1	430.6	426.8	425.3	425.3	426.3
52.5°	467.9	450.0	436.7	425.9	419.0	412.2	407.2	404.8	402.6	404.9	406.7
55°	427.7	409.6	399.8	389.6	382.8	374.8	372.5	371.5	370.0	373.9	375.9
57.5°	385.3	372.6	361.1	350.9	344.8	340.3	337.0	336.3	339.0	340.9	347.3
60°	358.3	343.6	333.3	325.5	318.1	315.2	314.2	313.2	315.2	320.6	328.9
62.5°	328.5	316.6	305.5	299.6	294.3	289.4	289.2	289.7	293.7	299.8	308.1
65°	284.8	274.6	267.2	260.3	256.0	253.1	254.0	256.0	260.3	268.7	278.0
67.5°	240.5	233.5	226.9	221.3	217.1	217.1	218.1	221.0	226.2	235.8	244.3
70°	211.9	204.1	198.7	196.2	192.8	190.9	193.8	198.7	203.1	211.9	219.2
72.5°	183.3	176.7	172.5	170.8	169.4	167.8	168.7	174.0	180.0	188.8	197.4
75°	140.9	138.5	135.5	133.7	132.1	133.1	134.1	139.0	143.9	153.2	163.0
77.5°	102.8	100.3	98.6	98.1	97.3	97.7	100.6	104.2	109.0	115.7	123.1
80°	77.9	76.8	75.9	75.4	75.4	75.9	79.7	82.2	86.6	93.0	98.9
82.5°	56.6	56.1	55.9	55.8	56.2	56.3	58.6	61.8	65.5	70.3	75.4
85°	29.9	28.8	30.3	30.8	29.9	31.3	32.3	34.2	35.7	38.2	40.6
87.5°	11.3	12.4	12.3	13.0	13.3	14.3	14.1	15.9	17.0	17.9	17.7
90°	7.6	9.2	10.7	12.2	13.6	15.1	16.1	17.2	18.2	19.2	20.1
92.5°	27.4	28.9	30.7	32.5	34.3	36.1	37.5	38.9	40.2	41.7	42.6
95°	62.9	64.1	66.2	68.2	70.4	72.5	73.9	75.4	76.8	78.3	79.3
97.5°	102.3	103.9	106.7	109.6	112.4	115.4	116.8	118.1	119.5	120.9	121.7
100°	131.8	133.1	135.8	138.6	141.3	143.9	145.8	147.7	149.6	151.5	152.7
102.5°	167.5	168.5	169.9	171.4	172.7	174.1	176.2	178.1	180.2	182.3	183.6
105°	218.8	219.9	221.1	222.3	223.7	224.9	226.1	227.4	228.7	229.9	230.8
107.5°	274.5	275.4	276.4	277.4	278.3	279.3	279.9	280.5	281.2	281.8	282.1
110°	312.8	313.7	314.2	314.9	315.6	316.1	316.8	317.4	318.0	318.7	318.9



TEST NUMBER: P333233-830

CATALOG NUMBER: S125DIP-S850D1035U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	350.0	350.6	351.5	352.2	353.0	353.8	354.1	354.4	354.7	355.0	355.0
115°	408.9	409.5	409.9	410.4	410.8	411.2	411.0	410.8	410.6	410.4	410.2
117.5°	465.1	465.4	465.8	466.2	466.6	466.9	467.1	467.2	467.4	467.6	467.2
120°	503.9	504.4	504.6	504.9	505.1	505.3	505.3	505.3	505.3	505.3	504.9
122.5°	540.4	540.7	541.3	541.9	542.4	542.9	542.8	542.6	542.4	542.2	541.9
125°	596.9	597.7	597.9	598.0	598.2	598.5	598.0	597.7	597.2	596.8	596.4
127.5°	651.2	651.7	652.0	652.1	652.4	652.7	652.4	652.2	652.1	651.9	651.5
130°	686.4	687.1	687.6	688.0	688.3	688.8	688.6	688.3	688.2	688.0	687.7
132.5°	722.9	723.8	723.7	723.6	723.5	723.4	723.2	723.0	722.8	722.6	722.2
135°	774.8	775.5	775.7	775.9	776.1	776.3	776.3	776.3	776.3	776.3	775.9
137.5°	825.0	825.9	826.3	826.8	827.3	827.6	827.9	828.2	828.4	828.7	828.3
140°	856.7	857.5	858.2	858.8	859.4	860.1	860.4	860.9	861.3	861.8	861.4
142.5°	888.4	889.3	890.0	890.9	891.6	892.4	892.7	893.0	893.2	893.4	893.1
145°	935.9	936.6	937.3	937.8	938.5	939.1	939.1	939.1	939.1	939.1	938.8
147.5°	978.4	978.9	979.4	979.9	980.3	980.9	981.4	981.8	982.4	982.9	982.4
150°	1005.1	1005.4	1006.3	1007.1	1007.9	1008.7	1008.7	1008.7	1008.7	1008.7	1008.5
152.5°	1031.1	1031.5	1031.8	1032.2	1032.5	1032.8	1033.3	1033.9	1034.3	1034.8	1034.7
155°	1067.1	1067.1	1067.4	1067.6	1067.8	1068.0	1068.8	1069.7	1070.5	1071.4	1071.3
157.5°	1098.3	1098.3	1098.4	1098.6	1098.9	1099.1	1099.9	1100.7	1101.5	1102.4	1102.1
160°	1117.3	1117.1	1117.3	1117.5	1117.7	1117.9	1118.7	1119.6	1120.4	1121.2	1121.2
162.5°	1135.3	1135.0	1135.1	1135.1	1135.2	1135.2	1136.2	1137.2	1138.2	1139.3	1139.2
165°	1158.6	1158.5	1158.7	1158.9	1159.0	1159.3	1160.2	1160.9	1161.8	1162.6	1162.4
167.5°	1176.5	1176.0	1176.0	1176.0	1176.0	1176.0	1177.3	1178.6	1179.8	1181.1	1181.0
170°	1187.0	1186.6	1186.6	1186.6	1186.6	1186.6	1187.9	1189.1	1190.3	1191.6	1191.5
172.5°	1194.6	1194.1	1194.1	1194.1	1194.1	1194.1	1195.3	1196.7	1197.9	1199.1	1199.1
175°	1203.0	1202.6	1202.6	1202.6	1202.6	1202.6	1203.8	1205.1	1206.4	1207.6	1207.5
177.5°	1208.0	1207.6	1207.4	1207.2	1207.1	1206.9	1208.0	1208.9	1209.9	1210.9	1210.9
180°	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2



TEST NUMBER: P333233-830

CATALOG NUMBER: S125DIP-S850D1035U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1
2.5°	1098.6	1101.4	1099.0	1102.2	1099.0	1101.4	1098.6	1101.0	1104.6	1102.2	1107.7
5°	1012.6	1008.2	1011.2	1009.2	1011.2	1008.2	1012.6	1015.0	1021.0	1022.8	1026.8
7.5°	933.1	928.9	924.2	921.9	924.2	928.9	933.1	934.6	939.6	947.0	952.5
10°	883.4	878.0	877.5	874.1	877.5	878.0	883.4	888.8	892.2	901.5	907.9
12.5°	847.0	842.0	836.4	835.0	836.4	842.0	847.0	851.6	852.6	863.2	867.5
15°	795.3	791.4	788.0	790.9	788.0	791.4	795.3	798.2	803.6	811.0	815.9
17.5°	752.3	749.1	748.5	744.9	748.5	749.1	752.3	754.0	762.8	767.6	776.0
20°	725.3	722.8	723.9	717.5	723.9	722.8	725.3	729.7	738.6	741.0	749.8
22.5°	703.8	699.0	698.4	697.1	698.4	699.0	703.8	707.8	709.5	717.1	723.2
25°	670.1	667.6	665.2	667.6	665.2	667.6	670.1	674.4	676.4	681.7	687.7
27.5°	640.6	637.6	637.0	637.3	637.0	637.6	640.6	640.2	645.5	649.8	654.0
30°	622.5	617.6	618.1	617.6	618.1	617.6	622.5	622.5	625.5	629.4	633.3
32.5°	602.9	599.6	599.0	598.0	599.0	599.6	602.9	602.2	605.9	610.6	614.9
35°	574.1	574.1	571.7	571.7	571.7	574.1	574.1	575.5	579.5	579.5	584.4
37.5°	547.0	546.5	545.0	545.3	545.0	546.5	547.0	548.2	549.5	551.6	554.7
40°	526.6	526.1	524.6	521.7	524.6	526.1	526.6	528.6	529.5	532.0	534.0
42.5°	507.0	505.4	504.7	503.7	504.7	505.4	507.0	508.2	508.8	512.0	515.9
45°	476.2	476.2	475.2	474.8	475.2	476.2	476.2	476.2	476.7	480.6	482.6
47.5°	446.3	447.1	449.0	448.7	449.0	447.1	446.3	445.4	445.6	447.6	449.9
50°	428.2	428.8	430.2	430.6	430.2	428.8	428.2	426.3	425.3	425.3	426.8
52.5°	408.3	411.1	412.9	412.6	412.9	411.1	408.3	406.7	404.9	402.6	404.8
55°	380.3	383.7	387.1	387.7	387.1	383.7	380.3	375.9	373.9	370.0	371.5
57.5°	352.6	357.4	361.0	362.1	361.0	357.4	352.6	347.3	340.9	339.0	336.3
60°	333.8	340.2	344.6	346.5	344.6	340.2	333.8	328.9	320.6	315.2	313.2
62.5°	315.8	322.9	327.3	327.7	327.3	322.9	315.8	308.1	299.8	293.7	289.7
65°	286.3	293.7	297.6	300.5	297.6	293.7	286.3	278.0	268.7	260.3	256.0
67.5°	254.6	261.9	266.3	268.6	266.3	261.9	254.6	244.3	235.8	226.2	221.0
70°	231.5	238.8	244.7	246.7	244.7	238.8	231.5	219.2	211.9	203.1	198.7
72.5°	208.8	215.4	220.1	222.3	220.1	215.4	208.8	197.4	188.8	180.0	174.0
75°	169.4	178.1	182.6	185.0	182.6	178.1	169.4	163.0	153.2	143.9	139.0
77.5°	130.5	138.6	141.3	142.5	141.3	138.6	130.5	123.1	115.7	109.0	104.2
80°	104.7	109.6	113.0	113.6	113.0	109.6	104.7	98.9	93.0	86.6	82.2
82.5°	80.5	84.5	85.7	86.9	85.7	84.5	80.5	75.4	70.3	65.5	61.8
85°	44.0	46.0	46.5	46.0	46.5	46.0	44.0	40.6	38.2	35.7	34.2
87.5°	18.7	18.4	18.5	19.4	18.5	18.4	18.7	17.7	17.9	17.0	15.9
90°	20.7	21.3	22.0	22.6	22.0	21.3	20.7	20.1	19.2	18.2	17.2
92.5°	43.1	43.5	43.9	44.4	43.9	43.5	43.1	42.6	41.7	40.2	38.9
95°	79.6	80.1	80.5	81.0	80.5	80.1	79.6	79.3	78.3	76.8	75.4
97.5°	122.0	122.2	122.4	122.7	122.4	122.2	122.0	121.7	120.9	119.5	118.1
100°	153.1	153.4	153.9	154.3	153.9	153.4	153.1	152.7	151.5	149.6	147.7
102.5°	184.2	184.7	185.4	186.0	185.4	184.7	184.2	183.6	182.3	180.2	178.1
105°	231.5	232.1	232.7	233.4	232.7	232.1	231.5	230.8	229.9	228.7	227.4
107.5°	282.0	282.0	282.0	281.9	282.0	282.0	282.0	282.1	281.8	281.2	280.5
110°	318.7	318.5	318.3	318.0	318.3	318.5	318.7	318.9	318.7	318.0	317.4



TEST NUMBER: P333233-830

CATALOG NUMBER: S125DIP-S850D1035U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	354.6	354.2	353.8	353.5	353.8	354.2	354.6	355.0	355.0	354.7	354.4
115°	409.9	409.7	409.5	409.3	409.5	409.7	409.9	410.2	410.4	410.6	410.8
117.5°	466.4	465.6	464.8	463.9	464.8	465.6	466.4	467.2	467.6	467.4	467.2
120°	504.1	503.2	502.4	501.5	502.4	503.2	504.1	504.9	505.3	505.3	505.3
122.5°	541.2	540.5	539.9	539.2	539.9	540.5	541.2	541.9	542.2	542.4	542.6
125°	596.3	596.1	595.9	595.7	595.9	596.1	596.3	596.4	596.8	597.2	597.7
127.5°	651.1	650.6	650.3	649.9	650.3	650.6	651.1	651.5	651.9	652.1	652.2
130°	687.2	686.8	686.4	686.0	686.4	686.8	687.2	687.7	688.0	688.2	688.3
132.5°	721.6	721.0	720.5	719.8	720.5	721.0	721.6	722.2	722.6	722.8	723.0
135°	775.1	774.2	773.4	772.5	773.4	774.2	775.1	775.9	776.3	776.3	776.3
137.5°	827.3	826.2	825.2	824.2	825.2	826.2	827.3	828.3	828.7	828.4	828.2
140°	860.4	859.3	858.3	857.2	858.3	859.3	860.4	861.4	861.8	861.3	860.9
142.5°	892.0	891.0	889.9	888.8	889.9	891.0	892.0	893.1	893.4	893.2	893.0
145°	938.2	937.5	936.9	936.3	936.9	937.5	938.2	938.8	939.1	939.1	939.1
147.5°	981.0	979.6	978.2	976.8	978.2	979.6	981.0	982.4	982.9	982.4	981.8
150°	1008.1	1007.7	1007.3	1006.8	1007.3	1007.7	1008.1	1008.5	1008.7	1008.7	1008.7
152.5°	1034.0	1033.2	1032.5	1031.7	1032.5	1033.2	1034.0	1034.7	1034.8	1034.3	1033.9
155°	1070.3	1069.1	1068.1	1067.1	1068.1	1069.1	1070.3	1071.3	1071.4	1070.5	1069.7
157.5°	1100.8	1099.4	1098.0	1096.6	1098.0	1099.4	1100.8	1102.1	1102.4	1101.5	1100.7
160°	1120.1	1119.1	1118.0	1116.9	1118.0	1119.1	1120.1	1121.2	1121.2	1120.4	1119.6
162.5°	1137.9	1136.7	1135.5	1134.3	1135.5	1136.7	1137.9	1139.2	1139.3	1138.2	1137.2
165°	1161.2	1159.9	1158.7	1157.4	1158.7	1159.9	1161.2	1162.4	1162.6	1161.8	1160.9
167.5°	1179.8	1178.5	1177.1	1175.8	1177.1	1178.5	1179.8	1181.0	1181.1	1179.8	1178.6
170°	1190.1	1188.5	1187.1	1185.6	1187.1	1188.5	1190.1	1191.5	1191.6	1190.3	1189.1
172.5°	1197.8	1196.6	1195.2	1193.9	1195.2	1196.6	1197.8	1199.1	1199.1	1197.9	1196.7
175°	1206.1	1204.6	1203.1	1201.6	1203.1	1204.6	1206.1	1207.5	1207.6	1206.4	1205.1
177.5°	1209.7	1208.5	1207.3	1206.2	1207.3	1208.5	1209.7	1210.9	1210.9	1209.9	1208.9
180°	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2



TEST NUMBER: P333233-830

CATALOG NUMBER: S125DIP-S850D1035U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1
2.5°	1102.6	1107.3	1113.1	1117.5	1125.3	1128.8	1133.1	1136.6	1142.9	1148.8	1155.8
5°	1028.3	1036.6	1047.8	1060.1	1074.3	1084.1	1097.8	1106.1	1122.8	1137.9	1152.5
7.5°	960.9	971.1	987.0	1002.8	1021.3	1038.1	1055.3	1074.3	1095.5	1120.6	1141.3
10°	914.7	928.4	945.6	965.2	987.7	1007.2	1030.2	1050.7	1076.8	1106.1	1133.5
12.5°	877.9	889.7	908.8	927.6	951.6	975.5	999.3	1026.5	1056.8	1089.3	1123.7
15°	827.1	836.9	852.5	878.5	903.0	926.5	962.2	987.7	1025.9	1062.1	1103.6
17.5°	783.7	795.9	809.1	831.3	856.7	886.1	917.9	949.9	986.7	1032.6	1079.5
20°	757.1	766.9	782.1	799.2	826.1	855.5	885.9	918.1	963.2	1010.7	1061.0
22.5°	728.1	738.8	755.8	774.6	797.2	825.4	858.8	894.3	941.2	988.0	1042.6
25°	694.0	701.3	717.0	733.7	756.2	780.1	814.9	854.0	900.5	953.9	1009.7
27.5°	661.8	668.3	682.6	697.0	717.4	745.8	776.9	816.4	860.3	914.4	976.2
30°	638.7	645.5	658.3	673.9	693.5	718.5	750.3	787.5	834.4	887.3	952.0
32.5°	618.7	624.8	634.4	650.1	669.2	693.4	722.8	760.8	807.9	861.5	924.9
35°	587.8	594.7	602.0	614.3	630.8	654.3	686.6	722.4	767.4	819.3	877.5
37.5°	557.0	564.5	571.1	582.0	597.2	617.9	645.8	683.1	723.8	773.7	829.6
40°	537.9	543.8	549.1	560.9	576.1	595.6	621.6	654.9	698.0	744.4	790.9
42.5°	518.7	524.1	528.8	538.9	553.0	571.7	596.5	629.0	668.9	712.3	753.3
45°	488.4	491.9	497.3	506.1	517.4	534.4	558.5	587.3	621.0	662.2	693.1
47.5°	455.7	461.1	465.5	473.3	482.5	499.3	522.3	546.9	577.5	608.0	629.8
50°	430.6	436.1	442.4	449.8	458.5	474.3	495.3	520.3	546.2	569.7	588.2
52.5°	407.2	412.2	419.0	425.9	436.7	450.0	467.9	490.1	515.7	532.5	548.0
55°	372.5	374.8	382.8	389.6	399.8	409.6	427.7	447.3	463.0	475.7	488.4
57.5°	337.0	340.3	344.8	350.9	361.1	372.6	385.3	402.6	411.8	418.4	428.2
60°	314.2	315.2	318.1	325.5	333.3	343.6	358.3	370.5	377.3	382.8	391.1
62.5°	289.2	289.4	294.3	299.6	305.5	316.6	328.5	338.4	344.0	346.7	354.7
65°	254.0	253.1	256.0	260.3	267.2	274.6	284.8	293.7	293.1	296.1	301.0
67.5°	218.1	217.1	217.1	221.3	226.9	233.5	240.5	245.6	245.7	249.6	252.0
70°	193.8	190.9	192.8	196.2	198.7	204.1	211.9	213.9	214.3	216.3	218.8
72.5°	168.7	167.8	169.4	170.8	172.5	176.7	183.3	184.5	184.6	185.8	189.8
75°	134.1	133.1	132.1	133.7	135.5	138.5	140.9	142.9	142.4	142.9	145.8
77.5°	100.6	97.7	97.3	98.1	98.6	100.3	102.8	102.6	103.2	103.1	106.4
80°	79.7	75.9	75.4	75.4	75.9	76.8	77.9	78.8	77.3	78.8	79.7
82.5°	58.6	56.3	56.2	55.8	55.9	56.1	56.6	57.3	56.9	57.7	58.2
85°	32.3	31.3	29.9	30.8	30.3	28.8	29.9	28.4	27.9	28.4	28.8
87.5°	14.1	14.3	13.3	13.0	12.3	12.4	11.3	10.6	9.9	9.9	10.7
90°	16.1	15.1	13.6	12.2	10.7	9.2	7.6	5.9	4.2	2.6	0.9
92.5°	37.5	36.1	34.3	32.5	30.7	28.9	27.4	26.3	25.1	23.9	22.8
95°	73.9	72.5	70.4	68.2	66.2	64.1	62.9	62.4	62.0	61.5	61.2
97.5°	116.8	115.4	112.4	109.6	106.7	103.9	102.3	102.2	102.0	101.8	101.6
100°	145.8	143.9	141.3	138.6	135.8	133.1	131.8	131.8	131.8	131.8	131.8
102.5°	176.2	174.1	172.7	171.4	169.9	168.5	167.5	166.6	165.8	164.9	164.1
105°	226.1	224.9	223.7	222.3	221.1	219.9	218.8	217.7	216.6	215.6	214.5
107.5°	279.9	279.3	278.3	277.4	276.4	275.4	274.5	273.4	272.3	271.3	270.2
110°	316.8	316.1	315.6	314.9	314.2	313.7	312.8	311.8	310.8	309.7	308.7



TEST NUMBER: P333233-830

CATALOG NUMBER: S125DIP-S850D1035U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	354.1	353.8	353.0	352.2	351.5	350.6	350.0	349.4	348.8	348.4	347.8
115°	411.0	411.2	410.8	410.4	409.9	409.5	408.9	408.1	407.3	406.4	405.6
117.5°	467.1	466.9	466.6	466.2	465.8	465.4	465.1	464.7	464.3	463.9	463.5
120°	505.3	505.3	505.1	504.9	504.6	504.4	503.9	502.8	501.7	500.7	499.6
122.5°	542.8	542.9	542.4	541.9	541.3	540.7	540.4	540.0	539.6	539.2	538.9
125°	598.0	598.5	598.2	598.0	597.9	597.7	596.9	595.7	594.4	593.1	591.9
127.5°	652.4	652.7	652.4	652.1	652.0	651.7	651.2	650.4	649.8	649.0	648.4
130°	688.6	688.8	688.3	688.0	687.6	687.1	686.4	685.3	684.3	683.2	682.2
132.5°	723.2	723.4	723.5	723.6	723.7	723.8	722.9	721.2	719.5	717.8	716.0
135°	776.3	776.3	776.1	775.9	775.7	775.5	774.8	773.5	772.2	771.0	769.8
137.5°	827.9	827.6	827.3	826.8	826.3	825.9	825.0	823.8	822.6	821.3	820.2
140°	860.4	860.1	859.4	858.8	858.2	857.5	856.7	855.6	854.6	853.6	852.5
142.5°	892.7	892.4	891.6	890.9	890.0	889.3	888.4	887.5	886.6	885.8	884.9
145°	939.1	939.1	938.5	937.8	937.3	936.6	935.9	935.0	934.2	933.4	932.6
147.5°	981.4	980.9	980.3	979.9	979.4	978.9	978.4	978.0	977.5	977.0	976.6
150°	1008.7	1008.7	1007.9	1007.1	1006.3	1005.4	1005.1	1005.3	1005.5	1005.7	1005.9
152.5°	1033.3	1032.8	1032.5	1032.2	1031.8	1031.5	1031.1	1030.9	1030.6	1030.3	1030.0
155°	1068.8	1068.0	1067.8	1067.6	1067.4	1067.1	1067.1	1067.1	1067.1	1067.1	1067.1
157.5°	1099.9	1099.1	1098.9	1098.6	1098.4	1098.3	1098.3	1098.8	1099.3	1099.8	1100.2
160°	1118.7	1117.9	1117.7	1117.5	1117.3	1117.1	1117.3	1117.9	1118.5	1119.2	1119.7
162.5°	1136.2	1135.2	1135.2	1135.1	1135.1	1135.0	1135.3	1135.7	1136.1	1136.6	1137.1
165°	1160.2	1159.3	1159.0	1158.9	1158.7	1158.5	1158.6	1159.0	1159.4	1159.8	1160.3
167.5°	1177.3	1176.0	1176.0	1176.0	1176.0	1176.0	1176.5	1177.3	1178.2	1178.9	1179.8
170°	1187.9	1186.6	1186.6	1186.6	1186.6	1186.6	1187.0	1187.9	1188.6	1189.5	1190.3
172.5°	1195.3	1194.1	1194.1	1194.1	1194.1	1194.1	1194.6	1195.3	1196.2	1197.0	1197.9
175°	1203.8	1202.6	1202.6	1202.6	1202.6	1202.6	1203.0	1203.8	1204.7	1205.5	1206.4
177.5°	1208.0	1206.9	1207.1	1207.2	1207.4	1207.6	1208.0	1208.6	1209.4	1210.0	1210.7
180°	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2



TEST NUMBER: P333233-830

CATALOG NUMBER: S125DIP-S850D1035U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1
2.5°	1159.3	1164.8	1168.4	1175.0	1180.4	1183.6	1186.4	1188.7	1191.5	1193.8	1200.4
5°	1166.8	1179.5	1190.2	1206.9	1222.1	1233.8	1246.5	1257.8	1267.2	1280.3	1290.6
7.5°	1163.6	1186.2	1209.8	1235.6	1261.9	1286.4	1308.9	1329.9	1349.1	1372.2	1392.4
10°	1160.5	1191.3	1221.6	1256.3	1292.0	1322.4	1350.8	1379.7	1400.7	1430.1	1455.0
12.5°	1158.1	1194.4	1231.0	1272.8	1312.0	1354.9	1392.7	1413.7	1445.8	1469.2	1498.9
15°	1148.2	1196.2	1246.5	1293.5	1349.3	1388.9	1422.3	1463.4	1493.2	1523.1	1555.4
17.5°	1130.5	1184.8	1241.1	1302.8	1356.3	1398.8	1441.7	1481.4	1517.0	1557.1	1597.2
20°	1122.3	1176.6	1241.1	1304.3	1356.7	1401.2	1445.3	1488.8	1528.0	1579.3	1625.9
22.5°	1105.0	1170.7	1230.2	1291.8	1345.7	1394.2	1444.1	1493.6	1545.6	1603.6	1661.9
25°	1074.3	1140.9	1204.0	1264.7	1319.0	1379.7	1433.0	1499.1	1565.7	1642.5	1715.0
27.5°	1042.4	1106.1	1163.9	1222.6	1285.9	1354.6	1423.8	1498.8	1585.9	1682.9	1785.1
30°	1016.5	1076.8	1133.0	1193.2	1259.2	1336.6	1412.5	1501.6	1602.3	1711.5	1832.9
32.5°	986.4	1041.9	1096.6	1160.4	1232.3	1313.9	1402.3	1500.0	1621.2	1745.2	1870.1
35°	934.8	981.3	1037.6	1105.6	1186.8	1280.3	1382.6	1498.1	1637.1	1779.5	1884.8
37.5°	873.6	916.9	976.2	1050.7	1136.0	1236.2	1357.6	1494.7	1642.3	1755.9	1789.8
40°	832.5	872.6	934.3	1011.6	1098.7	1204.9	1338.0	1482.9	1625.9	1698.3	1670.4
42.5°	788.6	830.8	890.8	967.4	1061.2	1176.8	1313.4	1458.3	1578.1	1605.5	1509.1
45°	719.4	763.0	822.2	899.6	1000.4	1125.7	1268.1	1399.8	1468.8	1419.3	1270.1
47.5°	655.2	696.0	750.8	830.7	934.7	1064.3	1201.5	1306.5	1311.9	1194.0	1034.5
50°	611.3	648.9	704.3	784.0	887.3	1018.5	1142.3	1225.0	1187.8	1054.2	901.0
52.5°	568.3	605.1	659.7	738.7	840.7	960.9	1076.1	1134.2	1064.1	927.0	796.1
55°	506.1	538.4	591.7	664.6	761.6	873.2	971.0	991.1	900.0	765.0	658.7
57.5°	445.4	475.5	524.1	591.3	679.8	778.6	855.2	850.9	754.7	638.8	554.5
60°	404.3	433.7	476.7	542.2	623.0	708.2	773.7	758.1	662.7	562.8	491.9
62.5°	367.5	393.7	434.4	491.7	565.4	644.4	698.2	675.1	581.6	494.3	438.2
65°	313.2	335.3	370.0	419.0	480.1	545.3	586.8	556.9	477.2	409.2	364.1
67.5°	261.5	279.1	308.2	347.3	399.4	451.8	477.1	447.0	383.2	333.6	300.2
70°	228.6	244.2	266.7	301.5	347.0	391.1	410.1	383.2	328.4	285.8	261.8
72.5°	195.7	208.6	228.4	259.6	296.1	334.3	351.0	325.3	280.2	244.3	221.9
75°	151.3	160.0	173.7	195.3	224.1	254.5	263.8	241.3	212.4	185.5	170.8
77.5°	108.3	115.7	126.1	139.7	160.1	179.5	187.6	174.6	152.2	135.2	123.1
80°	83.2	87.1	96.0	107.2	123.4	135.5	140.9	132.6	117.0	104.2	94.9
82.5°	59.3	63.2	68.5	77.9	88.1	96.4	102.2	96.6	85.3	75.3	69.8
85°	28.8	31.3	34.2	38.2	46.0	50.9	50.4	46.9	42.6	38.6	35.7
87.5°	10.7	11.4	12.9	15.3	16.7	18.6	19.7	19.1	17.9	17.0	15.9
90°	2.6	4.2	5.9	7.6	9.2	10.7	12.2	13.6	15.1	16.1	17.2
92.5°	23.9	25.1	26.3	27.4	28.9	30.7	32.5	34.3	36.1	37.5	38.9
95°	61.5	62.0	62.4	62.9	64.1	66.2	68.2	70.4	72.5	73.9	75.4
97.5°	101.8	102.0	102.2	102.3	103.9	106.7	109.6	112.4	115.4	116.8	118.1
100°	131.8	131.8	131.8	131.8	133.1	135.8	138.6	141.3	143.9	145.8	147.7
102.5°	164.9	165.8	166.6	167.5	168.5	169.9	171.4	172.7	174.1	176.2	178.1
105°	215.6	216.6	217.7	218.8	219.9	221.1	222.3	223.7	224.9	226.1	227.4
107.5°	271.3	272.3	273.4	274.5	275.4	276.4	277.4	278.3	279.3	279.9	280.5
110°	309.7	310.8	311.8	312.8	313.7	314.2	314.9	315.6	316.1	316.8	317.4



TEST NUMBER: P333233-830

CATALOG NUMBER: S125DIP-S850D1035U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	348.4	348.8	349.4	350.0	350.6	351.5	352.2	353.0	353.8	354.1	354.4
115°	406.4	407.3	408.1	408.9	409.5	409.9	410.4	410.8	411.2	411.0	410.8
117.5°	463.9	464.3	464.7	465.1	465.4	465.8	466.2	466.6	466.9	467.1	467.2
120°	500.7	501.7	502.8	503.9	504.4	504.6	504.9	505.1	505.3	505.3	505.3
122.5°	539.2	539.6	540.0	540.4	540.7	541.3	541.9	542.4	542.9	542.8	542.6
125°	593.1	594.4	595.7	596.9	597.7	597.9	598.0	598.2	598.5	598.0	597.7
127.5°	649.0	649.8	650.4	651.2	651.7	652.0	652.1	652.4	652.7	652.4	652.2
130°	683.2	684.3	685.3	686.4	687.1	687.6	688.0	688.3	688.8	688.6	688.3
132.5°	717.8	719.5	721.2	722.9	723.8	723.7	723.6	723.5	723.4	723.2	723.0
135°	771.0	772.2	773.5	774.8	775.5	775.7	775.9	776.1	776.3	776.3	776.3
137.5°	821.3	822.6	823.8	825.0	825.9	826.3	826.8	827.3	827.6	827.9	828.2
140°	853.6	854.6	855.6	856.7	857.5	858.2	858.8	859.4	860.1	860.4	860.9
142.5°	885.8	886.6	887.5	888.4	889.3	890.0	890.9	891.6	892.4	892.7	893.0
145°	933.4	934.2	935.0	935.9	936.6	937.3	937.8	938.5	939.1	939.1	939.1
147.5°	977.0	977.5	978.0	978.4	978.9	979.4	979.9	980.3	980.9	981.4	981.8
150°	1005.7	1005.5	1005.3	1005.1	1005.4	1006.3	1007.1	1007.9	1008.7	1008.7	1008.7
152.5°	1030.3	1030.6	1030.9	1031.1	1031.5	1031.8	1032.2	1032.5	1032.8	1033.3	1033.9
155°	1067.1	1067.1	1067.1	1067.1	1067.1	1067.4	1067.6	1067.8	1068.0	1068.8	1069.7
157.5°	1099.8	1099.3	1098.8	1098.3	1098.3	1098.4	1098.6	1098.9	1099.1	1099.9	1100.7
160°	1119.2	1118.5	1117.9	1117.3	1117.1	1117.3	1117.5	1117.7	1117.9	1118.7	1119.6
162.5°	1136.6	1136.1	1135.7	1135.3	1135.0	1135.1	1135.1	1135.2	1135.2	1136.2	1137.2
165°	1159.8	1159.4	1159.0	1158.6	1158.5	1158.7	1158.9	1159.0	1159.3	1160.2	1160.9
167.5°	1178.9	1178.2	1177.3	1176.5	1176.0	1176.0	1176.0	1176.0	1176.0	1177.3	1178.6
170°	1189.5	1188.6	1187.9	1187.0	1186.6	1186.6	1186.6	1186.6	1186.6	1187.9	1189.1
172.5°	1197.0	1196.2	1195.3	1194.6	1194.1	1194.1	1194.1	1194.1	1194.1	1195.3	1196.7
175°	1205.5	1204.7	1203.8	1203.0	1202.6	1202.6	1202.6	1202.6	1202.6	1203.8	1205.1
177.5°	1210.0	1209.4	1208.6	1208.0	1207.6	1207.4	1207.2	1207.1	1206.9	1208.0	1208.9
180°	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2



TEST NUMBER: P333233-830

CATALOG NUMBER: S125DIP-S850D1035U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1
2.5°	1205.9	1209.1	1215.7	1213.3	1216.5	1218.0	1219.7
5°	1303.3	1319.0	1325.9	1324.8	1335.1	1332.7	1330.2
7.5°	1413.3	1429.8	1439.0	1450.5	1457.1	1457.5	1463.4
10°	1475.6	1497.1	1506.0	1518.2	1526.0	1530.4	1529.9
12.5°	1523.3	1540.2	1560.0	1565.9	1576.5	1582.1	1580.1
15°	1580.8	1607.8	1628.3	1638.6	1651.8	1655.7	1661.1
17.5°	1632.1	1668.2	1692.2	1724.1	1736.2	1743.5	1739.2
20°	1670.8	1718.3	1742.4	1780.6	1801.6	1812.8	1808.9
22.5°	1716.7	1768.1	1812.4	1845.5	1877.5	1892.7	1895.8
25°	1795.2	1865.7	1930.8	1974.3	2013.9	2023.3	2043.8
27.5°	1882.9	1966.0	2035.6	2081.4	2109.0	2119.4	2125.8
30°	1938.2	2020.8	2073.2	2102.5	2111.4	2110.4	2109.4
32.5°	1965.1	2016.9	2026.9	2018.7	1998.6	1981.6	1963.8
35°	1926.8	1888.2	1830.4	1756.1	1701.2	1646.0	1640.5
37.5°	1733.0	1609.3	1513.2	1405.8	1343.9	1305.6	1279.1
40°	1550.5	1410.0	1293.5	1203.0	1139.8	1114.9	1090.4
42.5°	1352.4	1218.1	1115.0	1039.3	991.8	964.1	944.8
45°	1098.7	980.3	899.6	844.7	807.1	785.5	773.3
47.5°	900.3	812.8	744.1	704.6	678.5	661.8	661.9
50°	793.8	710.1	664.6	633.3	610.8	597.6	600.0
52.5°	699.5	637.0	598.0	571.8	555.2	547.1	546.8
55°	584.8	539.8	514.3	495.3	484.0	474.8	476.7
57.5°	500.3	462.3	445.3	429.4	421.6	417.8	412.5
60°	447.8	418.5	403.8	391.1	383.2	380.3	374.8
62.5°	401.2	378.1	363.8	353.5	346.4	345.4	341.2
65°	337.2	319.6	306.9	302.0	294.6	292.7	292.7
67.5°	278.0	265.3	255.5	251.0	247.7	248.3	245.9
70°	240.8	230.5	224.1	219.2	216.8	217.3	215.4
72.5°	210.7	199.2	193.6	190.7	187.5	188.7	187.9
75°	159.6	153.6	150.7	147.8	145.8	144.9	143.9
77.5°	117.2	112.0	109.7	108.1	108.4	106.0	107.8
80°	90.6	86.1	84.6	82.2	81.7	81.7	81.2
82.5°	66.3	63.8	62.8	60.7	59.9	60.6	59.3
85°	34.2	32.3	31.9	31.9	30.8	29.9	32.3
87.5°	16.2	14.8	15.0	14.7	14.8	14.6	13.9
90°	18.2	19.2	20.1	20.7	21.3	22.0	22.6
92.5°	40.2	41.7	42.6	43.1	43.5	43.9	44.4
95°	76.8	78.3	79.3	79.6	80.1	80.5	81.0
97.5°	119.5	120.9	121.7	122.0	122.2	122.4	122.7
100°	149.6	151.5	152.7	153.1	153.4	153.9	154.3
102.5°	180.2	182.3	183.6	184.2	184.7	185.4	186.0
105°	228.7	229.9	230.8	231.5	232.1	232.7	233.4
107.5°	281.2	281.8	282.1	282.0	282.0	282.0	281.9
110°	318.0	318.7	318.9	318.7	318.5	318.3	318.0



TEST NUMBER: P333233-830

CATALOG NUMBER: S125DIP-S850D1035U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	354.7	355.0	355.0	354.6	354.2	353.8	353.5
115°	410.6	410.4	410.2	409.9	409.7	409.5	409.3
117.5°	467.4	467.6	467.2	466.4	465.6	464.8	463.9
120°	505.3	505.3	504.9	504.1	503.2	502.4	501.5
122.5°	542.4	542.2	541.9	541.2	540.5	539.9	539.2
125°	597.2	596.8	596.4	596.3	596.1	595.9	595.7
127.5°	652.1	651.9	651.5	651.1	650.6	650.3	649.9
130°	688.2	688.0	687.7	687.2	686.8	686.4	686.0
132.5°	722.8	722.6	722.2	721.6	721.0	720.5	719.8
135°	776.3	776.3	775.9	775.1	774.2	773.4	772.5
137.5°	828.4	828.7	828.3	827.3	826.2	825.2	824.2
140°	861.3	861.8	861.4	860.4	859.3	858.3	857.2
142.5°	893.2	893.4	893.1	892.0	891.0	889.9	888.8
145°	939.1	939.1	938.8	938.2	937.5	936.9	936.3
147.5°	982.4	982.9	982.4	981.0	979.6	978.2	976.8
150°	1008.7	1008.7	1008.5	1008.1	1007.7	1007.3	1006.8
152.5°	1034.3	1034.8	1034.7	1034.0	1033.2	1032.5	1031.7
155°	1070.5	1071.4	1071.3	1070.3	1069.1	1068.1	1067.1
157.5°	1101.5	1102.4	1102.1	1100.8	1099.4	1098.0	1096.6
160°	1120.4	1121.2	1121.2	1120.1	1119.1	1118.0	1116.9
162.5°	1138.2	1139.3	1139.2	1137.9	1136.7	1135.5	1134.3
165°	1161.8	1162.6	1162.4	1161.2	1159.9	1158.7	1157.4
167.5°	1179.8	1181.1	1181.0	1179.8	1178.5	1177.1	1175.8
170°	1190.3	1191.6	1191.5	1190.1	1188.5	1187.1	1185.6
172.5°	1197.9	1199.1	1199.1	1197.8	1196.6	1195.2	1193.9
175°	1206.4	1207.6	1207.5	1206.1	1204.6	1203.1	1201.6
177.5°	1209.9	1210.9	1210.9	1209.7	1208.5	1207.3	1206.2
180°	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2

(END OF REPORT)