

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333239-830

Luminaire Tested: **S125DIP-S850D1035U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333239-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S850D1035U830-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6596.5 lumens  
Efficiency: N/A  
Efficacy: 126.9 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 52  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333239-830

CATALOG NUMBER: S125DIP-S850D1035U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333239-830

CATALOG NUMBER: S125DIP-S850D1035U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	97	93	89	86	90	86	83	80	72	70	68	60	58	57	49	47	46	41
2	89	81	75	70	81	75	70	65	63	59	56	53	50	47	43	41	39	34
3	81	71	64	58	74	66	60	54	56	51	47	47	43	40	38	35	33	29
4	74	63	55	49	68	58	52	46	50	44	40	41	37	34	34	31	29	25
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	22
6	63	50	42	37	57	47	40	34	40	34	30	34	29	26	28	24	22	19
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	19	17
8	54	41	34	28	49	38	32	27	33	27	24	28	24	20	23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7991	7991	7991
5°	8009	7933	7983
10°	7960	7877	7922
15°	7874	7782	7815
20°	7750	7649	7663
25°	7617	7492	7485
30°	7454	7322	7285
35°	7278	7139	7039
40°	7098	6940	6842
45°	6902	6760	6625
50°	6688	6540	6344
55°	6481	6293	6117
60°	6234	6044	5829
65°	5938	5744	5550
70°	5655	5399	5214
75°	5153	4983	4811
80°	4590	4515	4407
85°	3987	4068	3838



TEST NUMBER: P333239-830

CATALOG NUMBER: S125DIP-S850D1035U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	116.7	1.8
10°-20°	329.6	5.0
20°-30°	486.6	7.4
30°-40°	567.8	8.6
40°-50°	570.3	8.6
50°-60°	500.6	7.6
60°-70°	373.0	5.7
70°-80°	213.3	3.2
80°-90°	64.7	1.0
90°-100°	81.0	1.2
100°-110°	239.1	3.6
110°-120°	405.1	6.1
120°-130°	533.1	8.1
130°-140°	597.3	9.1
140°-150°	585.5	8.9
150°-160°	491.7	7.5
160°-170°	326.9	5.0
170°-180°	114.4	1.7
0°-30°	932.8	14.1
0°-40°	1500.6	22.7
0°-60°	2571.4	39.0
0°-90°	3222.4	48.8
90°-120°	725.2	11.0
90°-150°	2441.1	37.0
90°-180°	3374.0	51.1
0°-180°	6596.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1237	1237	1237	1237	1237	
5°	1235	1233	1224	1232	1231	117
15°	1178	1174	1164	1169	1169	332
25°	1069	1064	1051	1053	1050	492
35°	923	919	906	900	893	577
45°	756	751	740	729	725	582
55°	576	572	559	550	543	514
65°	389	386	376	367	363	386
75°	206	204	200	197	193	220
85°	54	55	55	54	52	60
90°	1	8	15	20	23	6
95°	61	64	72	79	81	65
105°	214	219	225	230	233	229
115°	406	409	411	410	409	401
125°	592	597	598	597	596	530
135°	770	775	776	776	772	593
145°	933	936	939	939	936	583
155°	1067	1067	1068	1071	1067	491
165°	1160	1159	1159	1162	1157	327
175°	1206	1203	1203	1208	1202	115
180°	1209	1209	1209	1209	1209	



TEST NUMBER: P333239-830

CATALOG NUMBER: S125DIP-S850D1035U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3
2.5°	1240.5	1239.9	1239.4	1238.9	1238.3	1237.2	1235.5	1233.8	1232.0	1230.3	1232.0
5°	1235.4	1234.9	1234.4	1234.1	1233.6	1232.3	1230.1	1227.9	1225.8	1223.6	1225.6
7.5°	1224.0	1223.6	1223.1	1222.7	1222.3	1220.9	1218.4	1216.1	1213.7	1211.3	1213.1
10°	1213.8	1213.4	1213.0	1212.5	1212.1	1210.7	1208.2	1205.9	1203.5	1201.1	1202.9
12.5°	1201.3	1200.5	1199.8	1198.9	1198.2	1196.7	1194.5	1192.2	1190.0	1187.8	1189.2
15°	1177.6	1177.0	1176.3	1175.6	1175.0	1173.5	1171.1	1168.7	1166.3	1163.9	1165.0
17.5°	1150.4	1149.4	1148.5	1147.5	1146.6	1144.8	1142.4	1139.9	1137.4	1134.9	1136.2
20°	1127.7	1127.3	1126.8	1126.3	1126.0	1124.3	1121.4	1118.6	1115.8	1113.0	1114.6
22.5°	1104.9	1104.2	1103.4	1102.6	1101.8	1100.1	1097.5	1094.8	1092.1	1089.5	1090.5
25°	1068.9	1067.9	1066.8	1065.6	1064.6	1062.6	1059.8	1057.0	1054.1	1051.3	1051.8
27.5°	1026.8	1026.2	1025.6	1024.9	1024.3	1022.5	1019.5	1016.6	1013.7	1010.8	1010.9
30°	999.5	998.8	998.2	997.5	996.8	994.9	991.6	988.4	985.1	981.8	981.4
32.5°	969.7	968.7	967.7	966.7	965.7	963.7	960.8	957.9	955.0	952.1	951.3
35°	923.1	922.2	921.3	920.5	919.6	917.7	914.6	911.5	908.5	905.5	904.4
37.5°	874.8	873.6	872.5	871.5	870.3	868.4	865.5	862.6	859.8	857.0	855.3
40°	841.9	840.7	839.7	838.6	837.4	835.5	832.4	829.3	826.3	823.2	821.3
42.5°	806.6	805.7	804.7	803.9	803.0	801.0	798.0	794.8	791.8	788.8	787.0
45°	755.7	754.8	753.9	753.1	752.2	750.5	747.9	745.3	742.6	740.1	737.4
47.5°	700.9	701.0	701.0	701.0	701.1	699.6	696.4	693.2	690.1	687.0	684.3
50°	665.6	665.0	664.3	663.6	663.1	661.4	658.8	656.2	653.6	650.9	648.1
52.5°	629.6	629.1	628.7	628.2	627.7	626.0	623.3	620.5	617.7	614.9	612.5
55°	575.6	575.0	574.3	573.6	573.0	571.1	568.1	565.1	561.9	558.9	556.9
57.5°	518.6	518.3	517.9	517.6	517.3	515.8	513.2	510.7	508.0	505.5	502.9
60°	482.6	481.7	480.9	479.9	479.1	477.5	475.0	472.7	470.3	467.9	465.7
62.5°	445.0	444.3	443.7	442.9	442.2	440.8	438.8	436.8	434.7	432.6	430.4
65°	388.6	388.1	387.8	387.3	386.9	385.5	383.0	380.7	378.2	375.9	373.9
67.5°	334.0	333.1	332.2	331.2	330.4	328.9	327.3	325.5	323.7	321.9	320.2
70°	299.5	298.4	297.4	296.2	295.2	293.7	291.7	289.7	287.8	285.9	284.6
72.5°	261.9	261.2	260.4	259.8	259.0	258.0	256.7	255.4	254.2	253.0	251.5
75°	206.5	206.1	205.7	205.3	204.8	204.1	202.9	201.9	200.8	199.7	199.1
77.5°	155.4	155.2	155.1	155.0	154.8	154.4	153.7	153.2	152.5	151.9	151.6
80°	123.4	123.4	123.4	123.4	123.4	123.1	122.7	122.2	121.8	121.4	121.2
82.5°	95.1	94.8	94.4	94.1	93.8	93.5	93.4	93.4	93.3	93.2	92.8
85°	53.8	54.1	54.3	54.5	54.7	54.9	54.9	54.9	54.9	54.9	54.6
87.5°	21.3	21.7	22.0	22.3	22.7	22.9	23.0	23.1	23.3	23.4	23.6
90°	0.9	2.6	4.2	5.9	7.6	9.2	10.7	12.2	13.6	15.1	16.1
92.5°	22.8	23.9	25.1	26.3	27.4	28.9	30.7	32.5	34.3	36.1	37.5
95°	61.2	61.5	62.0	62.4	62.9	64.1	66.2	68.2	70.4	72.5	73.9
97.5°	101.6	101.8	102.0	102.2	102.3	103.9	106.7	109.6	112.4	115.4	116.8
100°	131.8	131.8	131.8	131.8	131.8	133.1	135.8	138.6	141.3	143.9	145.8
102.5°	164.1	164.9	165.8	166.6	167.5	168.5	169.9	171.4	172.7	174.1	176.2
105°	214.5	215.6	216.6	217.7	218.8	219.9	221.1	222.3	223.7	224.9	226.1
107.5°	270.2	271.3	272.3	273.4	274.5	275.4	276.4	277.4	278.3	279.3	279.9
110°	308.7	309.7	310.8	311.8	312.8	313.7	314.2	314.9	315.6	316.1	316.8



TEST NUMBER: P333239-830

CATALOG NUMBER: S125DIP-S850D1035U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	347.8	348.4	348.8	349.4	350.0	350.6	351.5	352.2	353.0	353.8	354.1
115°	405.6	406.4	407.3	408.1	408.9	409.5	409.9	410.4	410.8	411.2	411.0
117.5°	463.5	463.9	464.3	464.7	465.1	465.4	465.8	466.2	466.6	466.9	467.1
120°	499.6	500.7	501.7	502.8	503.9	504.4	504.6	504.9	505.1	505.3	505.3
122.5°	538.9	539.2	539.6	540.0	540.4	540.7	541.3	541.9	542.4	542.9	542.8
125°	591.9	593.1	594.4	595.7	596.9	597.7	597.9	598.0	598.2	598.5	598.0
127.5°	648.4	649.0	649.8	650.4	651.2	651.7	652.0	652.1	652.4	652.7	652.4
130°	682.2	683.2	684.3	685.3	686.4	687.1	687.6	688.0	688.3	688.8	688.6
132.5°	716.0	717.8	719.5	721.2	722.9	723.8	723.7	723.6	723.5	723.4	723.2
135°	769.8	771.0	772.2	773.5	774.8	775.5	775.7	775.9	776.1	776.3	776.3
137.5°	820.2	821.3	822.6	823.8	825.0	825.9	826.3	826.8	827.3	827.6	827.9
140°	852.5	853.6	854.6	855.6	856.7	857.5	858.2	858.8	859.4	860.1	860.4
142.5°	884.9	885.8	886.6	887.5	888.4	889.3	890.0	890.9	891.6	892.4	892.7
145°	932.6	933.4	934.2	935.0	935.9	936.6	937.3	937.8	938.5	939.1	939.1
147.5°	976.6	977.0	977.5	978.0	978.4	978.9	979.4	979.9	980.3	980.9	981.4
150°	1005.9	1005.7	1005.5	1005.3	1005.1	1005.4	1006.3	1007.1	1007.9	1008.7	1008.7
152.5°	1030.0	1030.3	1030.6	1030.9	1031.1	1031.5	1031.8	1032.2	1032.5	1032.8	1033.3
155°	1067.1	1067.1	1067.1	1067.1	1067.1	1067.1	1067.4	1067.6	1067.8	1068.0	1068.8
157.5°	1100.2	1099.8	1099.3	1098.8	1098.3	1098.3	1098.4	1098.6	1098.9	1099.1	1099.9
160°	1119.7	1119.2	1118.5	1117.9	1117.3	1117.1	1117.3	1117.5	1117.7	1117.9	1118.7
162.5°	1137.1	1136.6	1136.1	1135.7	1135.3	1135.0	1135.1	1135.1	1135.2	1135.2	1136.2
165°	1160.3	1159.8	1159.4	1159.0	1158.6	1158.5	1158.7	1158.9	1159.0	1159.3	1160.2
167.5°	1179.8	1178.9	1178.2	1177.3	1176.5	1176.0	1176.0	1176.0	1176.0	1176.0	1177.3
170°	1190.3	1189.5	1188.6	1187.9	1187.0	1186.6	1186.6	1186.6	1186.6	1186.6	1187.9
172.5°	1197.9	1197.0	1196.2	1195.3	1194.6	1194.1	1194.1	1194.1	1194.1	1194.1	1195.3
175°	1206.4	1205.5	1204.7	1203.8	1203.0	1202.6	1202.6	1202.6	1202.6	1202.6	1203.8
177.5°	1210.7	1210.0	1209.4	1208.6	1208.0	1207.6	1207.4	1207.2	1207.1	1206.9	1208.0
180°	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2



TEST NUMBER: P333239-830

CATALOG NUMBER: S125DIP-S850D1035U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3
2.5°	1233.8	1235.5	1237.2	1238.0	1237.8	1237.7	1237.5	1237.3
5°	1227.6	1229.5	1231.4	1232.3	1232.1	1231.9	1231.6	1231.4
7.5°	1215.1	1217.0	1218.9	1219.7	1219.6	1219.4	1219.1	1218.9
10°	1204.6	1206.4	1208.1	1208.8	1208.6	1208.3	1208.2	1208.0
12.5°	1190.5	1191.9	1193.4	1194.0	1194.0	1193.9	1193.9	1193.8
15°	1166.1	1167.2	1168.3	1168.8	1168.8	1168.8	1168.8	1168.8
17.5°	1137.6	1139.0	1140.3	1140.5	1139.3	1138.3	1137.2	1136.1
20°	1116.1	1117.6	1119.1	1119.3	1118.2	1117.1	1116.1	1114.9
22.5°	1091.5	1092.5	1093.5	1093.6	1092.9	1092.1	1091.4	1090.7
25°	1052.2	1052.6	1053.1	1052.9	1052.3	1051.7	1051.0	1050.4
27.5°	1011.0	1011.1	1011.2	1010.9	1010.2	1009.6	1008.9	1008.2
30°	981.0	980.5	980.1	979.6	978.9	978.3	977.6	976.9
32.5°	950.5	949.7	949.0	947.9	946.8	945.6	944.4	943.3
35°	903.3	902.2	901.2	899.8	898.0	896.3	894.5	892.8
37.5°	853.7	852.1	850.5	849.1	848.2	847.2	846.2	845.2
40°	819.4	817.4	815.4	814.1	813.4	812.8	812.2	811.5
42.5°	785.2	783.4	781.7	780.2	779.3	778.3	777.2	776.3
45°	734.8	732.2	729.6	727.9	727.4	726.7	726.0	725.4
47.5°	681.6	679.0	676.4	674.3	672.8	671.3	669.7	668.2
50°	645.3	642.4	639.6	637.4	635.9	634.4	632.9	631.4
52.5°	610.0	607.5	605.0	602.9	601.2	599.6	597.9	596.2
55°	555.1	553.1	551.1	549.4	547.8	546.3	544.8	543.3
57.5°	500.5	497.9	495.4	493.7	492.9	492.1	491.3	490.4
60°	463.5	461.4	459.2	457.3	455.8	454.3	452.8	451.3
62.5°	428.0	425.7	423.3	421.5	420.4	419.1	418.0	416.8
65°	372.0	370.0	368.1	366.6	365.8	365.0	364.0	363.2
67.5°	318.6	316.9	315.3	314.1	313.7	313.1	312.5	312.1
70°	283.2	281.9	280.6	279.6	278.6	277.8	276.9	276.1
72.5°	250.0	248.5	247.0	245.8	245.0	244.1	243.3	242.3
75°	198.4	197.7	197.1	196.3	195.5	194.5	193.7	192.8
77.5°	151.2	150.7	150.3	149.9	149.2	148.6	148.1	147.4
80°	120.9	120.7	120.6	120.2	119.8	119.3	118.9	118.5
82.5°	92.4	92.0	91.6	91.4	91.3	91.2	91.1	91.0
85°	54.4	54.2	53.9	53.6	53.2	52.8	52.3	51.8
87.5°	23.8	24.0	24.2	24.2	23.9	23.8	23.6	23.3
90°	17.2	18.2	19.2	20.1	20.7	21.3	22.0	22.6
92.5°	38.9	40.2	41.7	42.6	43.1	43.5	43.9	44.4
95°	75.4	76.8	78.3	79.3	79.6	80.1	80.5	81.0
97.5°	118.1	119.5	120.9	121.7	122.0	122.2	122.4	122.7
100°	147.7	149.6	151.5	152.7	153.1	153.4	153.9	154.3
102.5°	178.1	180.2	182.3	183.6	184.2	184.7	185.4	186.0
105°	227.4	228.7	229.9	230.8	231.5	232.1	232.7	233.4
107.5°	280.5	281.2	281.8	282.1	282.0	282.0	282.0	281.9
110°	317.4	318.0	318.7	318.9	318.7	318.5	318.3	318.0





TEST NUMBER: P333239-830

CATALOG NUMBER: S125DIP-S850D1035U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	354.4	354.7	355.0	355.0	354.6	354.2	353.8	353.5
115°	410.8	410.6	410.4	410.2	409.9	409.7	409.5	409.3
117.5°	467.2	467.4	467.6	467.2	466.4	465.6	464.8	463.9
120°	505.3	505.3	505.3	504.9	504.1	503.2	502.4	501.5
122.5°	542.6	542.4	542.2	541.9	541.2	540.5	539.9	539.2
125°	597.7	597.2	596.8	596.4	596.3	596.1	595.9	595.7
127.5°	652.2	652.1	651.9	651.5	651.1	650.6	650.3	649.9
130°	688.3	688.2	688.0	687.7	687.2	686.8	686.4	686.0
132.5°	723.0	722.8	722.6	722.2	721.6	721.0	720.5	719.8
135°	776.3	776.3	776.3	775.9	775.1	774.2	773.4	772.5
137.5°	828.2	828.4	828.7	828.3	827.3	826.2	825.2	824.2
140°	860.9	861.3	861.8	861.4	860.4	859.3	858.3	857.2
142.5°	893.0	893.2	893.4	893.1	892.0	891.0	889.9	888.8
145°	939.1	939.1	939.1	938.8	938.2	937.5	936.9	936.3
147.5°	981.8	982.4	982.9	982.4	981.0	979.6	978.2	976.8
150°	1008.7	1008.7	1008.7	1008.5	1008.1	1007.7	1007.3	1006.8
152.5°	1033.9	1034.3	1034.8	1034.7	1034.0	1033.2	1032.5	1031.7
155°	1069.7	1070.5	1071.4	1071.3	1070.3	1069.1	1068.1	1067.1
157.5°	1100.7	1101.5	1102.4	1102.1	1100.8	1099.4	1098.0	1096.6
160°	1119.6	1120.4	1121.2	1121.2	1120.1	1119.1	1118.0	1116.9
162.5°	1137.2	1138.2	1139.3	1139.2	1137.9	1136.7	1135.5	1134.3
165°	1160.9	1161.8	1162.6	1162.4	1161.2	1159.9	1158.7	1157.4
167.5°	1178.6	1179.8	1181.1	1181.0	1179.8	1178.5	1177.1	1175.8
170°	1189.1	1190.3	1191.6	1191.5	1190.1	1188.5	1187.1	1185.6
172.5°	1196.7	1197.9	1199.1	1199.1	1197.8	1196.6	1195.2	1193.9
175°	1205.1	1206.4	1207.6	1207.5	1206.1	1204.6	1203.1	1201.6
177.5°	1208.9	1209.9	1210.9	1210.9	1209.7	1208.5	1207.3	1206.2
180°	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2

(END OF REPORT)