

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333589-935

Luminaire Tested: **S125RDIP-S1090D590U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333589-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1090D590U935-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5672.0 lumens
Efficiency: N/A
Efficacy: 116.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333589-935

CATALOG NUMBER: S125RDIP-S1090D590U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333589-935

CATALOG NUMBER: S125RDIP-S1090D590U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69	64
1	101	97	93	90	95	91	88	85	80	78	76	71	69	67	62	60	59	55
2	92	85	79	74	87	80	75	70	71	67	63	62	59	56	54	52	50	46
3	84	75	68	62	79	71	64	59	63	58	53	55	51	48	49	45	43	39
4	77	67	59	52	73	63	56	50	56	50	46	50	45	41	44	40	37	34
5	71	60	51	45	67	56	49	43	50	44	40	45	40	36	39	36	33	30
6	66	54	45	39	62	51	43	38	45	39	35	40	36	32	36	32	29	26
7	61	49	40	35	57	46	39	33	41	35	31	37	32	28	33	29	26	23
8	57	44	36	31	53	42	35	30	38	32	28	34	29	25	30	26	23	21
9	53	40	33	28	50	38	32	27	35	29	25	31	26	23	28	24	21	19
10	49	37	30	25	47	35	29	24	32	26	22	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9939	9939	9939
5°	9962	9848	9909
10°	9886	9757	9757
15°	9768	9559	9482
20°	9619	9283	9171
25°	9443	9012	8813
30°	9223	8694	8416
35°	8999	8367	7972
40°	8790	8025	7535
45°	8535	7644	7059
50°	8280	7229	6563
55°	7983	6831	6033
60°	7687	6350	5465
65°	7335	5790	4814
70°	6936	5093	4147
75°	6381	4292	3451
80°	5620	3373	2894
85°	4735	2757	2586



TEST NUMBER: P333589-935

CATALOG NUMBER: S125RDIP-S1090D590U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.7	2.6
10°-20°	404.4	7.1
20°-30°	586.4	10.3
30°-40°	668.3	11.8
40°-50°	651.5	11.5
50°-60°	548.4	9.7
60°-70°	384.4	6.8
70°-80°	197.6	3.5
80°-90°	51.3	0.9
90°-100°	24.1	0.4
100°-110°	148.4	2.6
110°-120°	269.2	4.7
120°-130°	345.5	6.1
130°-140°	371.6	6.6
140°-150°	348.8	6.1
150°-160°	282.1	5.0
160°-170°	182.5	3.2
170°-180°	62.9	1.1
0°-30°	1135.5	20.0
0°-40°	1803.9	31.8
0°-60°	3003.7	53.0
0°-90°	3637.0	64.1
90°-120°	441.7	7.8
90°-150°	1507.5	26.6
90°-180°	2035.0	35.9
0°-180°	5672.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1539	1539	1539	1539	1539	
5°	1537	1532	1519	1530	1528	146
15°	1461	1453	1430	1428	1418	412
25°	1325	1306	1265	1250	1237	609
35°	1141	1112	1061	1028	1011	714
45°	934	899	837	792	773	721
55°	709	670	607	556	536	634
65°	480	439	379	334	315	475
75°	256	220	172	147	138	271
85°	64	44	37	36	35	72
90°	0	4	8	10	12	4
95°	28	26	8	10	10	36
105°	144	146	146	146	146	153
115°	271	274	274	272	269	269
125°	386	389	389	387	386	344
135°	481	484	483	482	479	371
145°	558	558	558	559	556	349
155°	614	611	612	613	610	283
165°	648	645	646	648	644	183
175°	663	660	660	664	660	63
180°	663	663	663	663	663	



TEST NUMBER: P333589-935

CATALOG NUMBER: S125RDIP-S1090D590U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1539.0	1539.0	1539.0	1539.0	1539.0	1539.0	1539.0	1539.0	1539.0	1539.0	1539.0
2.5°	1541.7	1541.1	1540.5	1539.8	1539.2	1537.9	1535.9	1533.8	1531.7	1529.7	1531.7
5°	1536.6	1535.6	1534.6	1533.5	1532.5	1530.5	1527.7	1524.8	1522.0	1519.1	1521.7
7.5°	1521.5	1520.5	1519.5	1518.5	1517.5	1515.4	1511.9	1508.6	1505.1	1501.8	1503.6
10°	1507.5	1506.8	1506.0	1505.2	1504.4	1502.3	1498.7	1495.0	1491.4	1487.8	1488.6
12.5°	1491.7	1490.7	1489.8	1488.8	1487.8	1484.9	1480.1	1475.2	1470.3	1465.4	1466.0
15°	1461.0	1459.5	1457.9	1456.4	1454.8	1451.4	1446.0	1440.5	1435.1	1429.7	1429.4
17.5°	1426.4	1424.0	1421.7	1419.3	1416.9	1412.3	1405.5	1398.7	1391.8	1385.0	1383.7
20°	1399.5	1396.9	1394.3	1391.7	1389.1	1383.7	1375.4	1367.2	1358.9	1350.7	1349.4
22.5°	1369.7	1367.1	1364.5	1361.9	1359.3	1353.8	1345.1	1336.4	1327.7	1319.0	1316.5
25°	1325.1	1321.2	1317.3	1313.5	1309.6	1302.9	1293.3	1283.8	1274.2	1264.6	1261.3
27.5°	1273.9	1269.2	1264.5	1259.8	1255.1	1247.7	1237.4	1227.2	1216.9	1206.7	1202.0
30°	1236.7	1231.8	1226.9	1222.0	1217.1	1209.2	1198.3	1187.5	1176.6	1165.8	1159.9
32.5°	1200.4	1194.7	1189.0	1183.3	1177.5	1169.2	1158.0	1147.0	1135.9	1124.9	1118.4
35°	1141.4	1135.2	1129.0	1122.8	1116.6	1107.7	1096.1	1084.4	1072.8	1061.2	1053.7
37.5°	1083.5	1076.0	1068.4	1060.9	1053.3	1043.6	1031.6	1019.6	1007.6	995.7	986.6
40°	1042.6	1034.8	1027.1	1019.3	1011.6	1001.5	989.1	976.7	964.3	951.9	942.1
42.5°	999.8	991.9	984.0	975.9	968.0	957.6	944.8	932.0	919.2	906.4	897.0
45°	934.5	927.0	919.5	912.1	904.6	893.7	879.5	865.3	851.1	836.9	826.6
47.5°	866.9	858.9	851.0	843.2	835.3	824.1	809.9	795.5	781.2	766.9	756.2
50°	824.1	815.5	807.0	798.5	790.0	778.3	763.6	748.9	734.2	719.5	708.6
52.5°	777.6	768.9	760.1	751.4	742.7	731.3	717.5	703.5	689.7	675.8	664.1
55°	709.0	700.8	692.5	684.2	676.0	664.6	650.1	635.7	621.2	606.7	595.1
57.5°	639.7	630.9	622.1	613.2	604.4	593.1	579.1	565.2	551.2	537.3	525.9
60°	595.1	586.1	577.0	568.0	559.0	547.4	533.5	519.5	505.6	491.6	480.3
62.5°	547.7	539.1	530.5	521.8	513.2	501.8	487.7	473.5	459.3	445.1	434.6
65°	480.0	471.2	462.4	453.7	444.9	433.7	420.0	406.3	392.6	378.9	368.6
67.5°	412.8	404.1	395.3	386.5	377.7	366.8	353.6	340.5	327.4	314.3	304.9
70°	367.3	358.5	349.7	341.0	332.2	321.3	308.4	295.5	282.6	269.7	261.7
72.5°	322.7	314.1	305.5	297.0	288.3	278.0	266.0	253.8	241.8	229.7	222.3
75°	255.7	248.0	240.2	232.5	224.7	215.4	204.6	193.7	182.9	172.0	166.3
77.5°	189.2	183.0	176.8	170.7	164.5	157.0	148.4	139.7	131.0	122.3	118.3
80°	151.1	144.9	138.7	132.5	126.3	119.6	112.4	105.1	97.9	90.7	88.3
82.5°	113.9	108.3	102.7	97.2	91.6	86.4	81.4	76.4	71.5	66.5	65.4
85°	63.9	59.2	54.6	49.9	45.3	42.4	41.1	39.8	38.5	37.2	36.9
87.5°	21.5	20.2	18.9	17.7	16.4	15.8	15.7	15.7	15.6	15.5	15.7
90°	0.5	1.4	2.2	3.1	4.0	4.8	5.6	6.4	7.1	7.8	8.4
92.5°	7.6	7.0	6.4	5.8	5.1	5.2	5.9	6.5	7.1	7.8	8.4
95°	28.0	27.6	27.4	27.0	26.7	24.5	20.3	16.2	12.0	7.8	8.4
97.5°	58.5	59.1	59.7	60.2	60.8	57.0	48.8	40.6	32.4	24.2	21.1
100°	82.1	82.4	82.7	83.0	83.3	83.7	84.2	84.6	85.1	85.5	69.2
102.5°	106.0	106.4	106.9	107.3	107.6	108.0	108.2	108.6	108.8	109.1	106.0
105°	144.4	144.8	145.3	145.8	146.2	146.4	146.4	146.4	146.4	146.4	146.4
107.5°	184.3	184.3	184.3	184.3	184.3	184.4	184.6	184.9	185.1	185.3	185.3
110°	210.3	210.3	210.3	210.3	210.3	210.3	210.6	210.8	211.0	211.2	210.9



TEST NUMBER: P333589-935

CATALOG NUMBER: S125RDIP-S1090D590U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	234.6	234.9	235.1	235.4	235.7	235.8	236.0	236.1	236.3	236.3	236.0
115°	271.1	271.7	272.2	272.8	273.4	273.7	273.8	273.9	274.0	274.1	273.7
117.5°	309.0	308.9	308.9	308.9	308.9	309.1	309.5	310.0	310.3	310.7	310.2
120°	332.6	332.4	332.3	332.3	332.1	332.3	332.6	332.9	333.2	333.6	333.3
122.5°	353.4	353.8	354.2	354.6	355.1	355.3	355.5	355.7	355.8	355.9	355.8
125°	385.6	386.4	387.1	387.9	388.7	389.1	389.1	389.1	389.1	389.1	388.7
127.5°	416.4	416.9	417.5	418.0	418.5	418.8	418.7	418.7	418.6	418.5	418.3
130°	435.2	435.8	436.4	436.9	437.4	437.7	437.8	438.0	438.1	438.2	437.8
132.5°	454.1	454.7	455.4	456.0	456.6	456.8	456.6	456.3	456.1	455.9	455.8
135°	481.0	481.6	482.2	482.8	483.5	483.8	483.5	483.3	483.1	482.8	482.7
137.5°	505.6	506.2	506.7	507.3	507.8	508.1	507.8	507.6	507.5	507.2	507.3
140°	521.7	521.9	522.1	522.4	522.5	522.6	522.5	522.4	522.3	522.2	522.4
142.5°	536.2	536.4	536.5	536.7	536.7	536.9	537.1	537.2	537.4	537.5	537.5
145°	557.6	557.8	558.0	558.2	558.4	558.5	558.5	558.5	558.5	558.5	558.6
147.5°	576.2	576.2	576.1	576.1	576.0	576.1	576.2	576.4	576.4	576.6	576.8
150°	588.0	587.8	587.5	587.4	587.1	587.1	587.4	587.5	587.8	588.0	588.2
152.5°	599.4	598.9	598.5	598.0	597.4	597.4	597.5	597.8	598.0	598.2	598.5
155°	614.1	613.4	612.8	612.1	611.4	611.2	611.4	611.7	611.8	612.1	612.4
157.5°	625.3	624.9	624.6	624.1	623.8	623.6	623.6	623.6	623.6	623.7	624.1
160°	633.2	632.6	631.9	631.2	630.6	630.3	630.4	630.5	630.6	630.8	631.2
162.5°	639.5	638.9	638.2	637.5	636.9	636.6	636.7	636.8	636.9	637.1	637.7
165°	647.9	647.3	646.6	646.0	645.3	645.1	645.1	645.2	645.4	645.5	646.1
167.5°	654.2	653.6	652.9	652.2	651.5	651.3	651.3	651.4	651.5	651.7	652.5
170°	657.8	657.0	656.3	655.5	654.7	654.4	654.4	654.6	654.7	654.8	655.7
172.5°	660.1	659.4	658.6	657.8	657.0	656.8	656.9	657.2	657.4	657.5	658.3
175°	662.7	662.0	661.3	660.7	660.0	659.8	659.9	660.0	660.1	660.2	661.1
177.5°	663.8	663.3	662.8	662.3	661.8	661.5	661.6	661.7	661.8	661.9	662.5
180°	662.7	662.7	662.7	662.7	662.7	662.7	662.7	662.7	662.7	662.7	662.7



TEST NUMBER: P333589-935

CATALOG NUMBER: S125RDIP-S1090D590U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1539.0	1539.0	1539.0	1539.0	1539.0	1539.0	1539.0	1539.0
2.5°	1533.8	1535.9	1537.9	1538.8	1538.6	1538.4	1538.2	1538.0
5°	1524.3	1526.9	1529.5	1530.5	1530.0	1529.5	1529.0	1528.4
7.5°	1505.4	1507.2	1509.0	1509.6	1509.0	1508.5	1507.9	1507.3
10°	1489.4	1490.1	1490.9	1490.9	1490.1	1489.4	1488.6	1487.8
12.5°	1466.6	1467.1	1467.7	1467.4	1466.2	1465.1	1463.9	1462.7
15°	1429.2	1428.9	1428.7	1427.4	1425.0	1422.7	1420.4	1418.1
17.5°	1382.4	1381.1	1379.8	1378.3	1376.3	1374.4	1372.5	1370.6
20°	1348.1	1346.8	1345.5	1343.7	1341.4	1339.0	1336.7	1334.4
22.5°	1314.0	1311.4	1308.9	1306.7	1304.8	1302.9	1300.9	1299.0
25°	1257.9	1254.6	1251.2	1248.1	1245.3	1242.4	1239.6	1236.7
27.5°	1197.3	1192.7	1187.9	1184.2	1181.5	1178.7	1176.0	1173.3
30°	1153.9	1148.0	1142.0	1137.9	1135.6	1133.2	1130.9	1128.6
32.5°	1111.8	1105.2	1098.6	1093.9	1091.0	1088.0	1085.0	1082.1
35°	1046.2	1038.7	1031.2	1025.7	1022.1	1018.5	1014.9	1011.2
37.5°	977.7	968.7	959.7	953.5	949.9	946.4	942.9	939.4
40°	932.3	922.5	912.7	906.2	903.1	900.0	896.9	893.8
42.5°	887.6	878.1	868.7	861.8	857.2	852.7	848.2	843.6
45°	816.2	805.9	795.6	788.4	784.5	780.7	776.8	772.9
47.5°	745.6	734.9	724.4	716.9	712.6	708.3	704.0	699.7
50°	697.8	686.9	676.1	668.7	664.9	661.0	657.1	653.2
52.5°	652.5	640.8	629.0	621.3	617.4	613.5	609.7	605.8
55°	583.5	571.9	560.3	552.3	548.2	544.1	539.9	535.8
57.5°	514.5	503.2	491.8	484.2	480.6	476.9	473.2	469.6
60°	468.9	457.5	446.2	438.6	434.7	430.8	427.0	423.1
62.5°	424.1	413.5	403.0	395.8	391.9	388.1	384.2	380.3
65°	358.3	347.9	337.6	330.5	326.6	322.7	318.8	315.0
67.5°	295.4	285.9	276.5	270.2	267.1	264.0	260.9	257.8
70°	253.7	245.6	237.6	232.0	228.9	225.8	222.7	219.6
72.5°	214.9	207.5	200.1	195.4	193.3	191.2	189.2	187.1
75°	160.7	155.0	149.3	145.5	143.7	141.9	140.1	138.3
77.5°	114.3	110.4	106.3	103.7	102.4	101.0	99.7	98.3
80°	86.0	83.7	81.4	79.9	79.4	78.9	78.4	77.8
82.5°	64.3	63.2	62.2	61.5	61.1	60.8	60.5	60.2
85°	36.7	36.4	36.2	35.9	35.6	35.4	35.1	34.9
87.5°	15.8	15.8	15.9	15.9	15.8	15.7	15.5	15.4
90°	9.0	9.5	10.1	10.5	10.8	11.1	11.5	11.8
92.5°	9.0	9.5	10.1	10.4	10.5	10.7	10.8	11.0
95°	9.0	9.5	10.1	10.3	10.3	10.3	10.3	10.3
97.5°	18.0	14.9	11.9	10.3	10.3	10.3	10.3	10.3
100°	53.0	36.7	20.4	12.1	11.6	11.2	10.8	10.3
102.5°	102.9	99.8	96.8	91.5	84.0	76.6	69.2	61.8
105°	146.4	146.4	146.4	146.4	146.2	146.1	146.0	145.9
107.5°	185.4	185.4	185.4	185.2	184.9	184.6	184.3	183.9
110°	210.6	210.3	209.9	209.8	209.9	210.0	210.2	210.3



TEST NUMBER: P333589-935

CATALOG NUMBER: S125RDIP-S1090D590U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	235.6	235.1	234.7	234.5	234.3	234.1	234.0	233.8
115°	273.2	272.8	272.3	271.8	271.1	270.5	269.8	269.2
117.5°	309.6	309.0	308.5	308.1	307.8	307.5	307.2	306.9
120°	333.1	332.9	332.7	332.3	331.7	331.2	330.6	330.1
122.5°	355.5	355.3	355.1	354.6	354.0	353.4	352.8	352.1
125°	388.2	387.7	387.3	386.9	386.6	386.2	386.0	385.6
127.5°	418.0	417.8	417.6	417.1	416.2	415.4	414.7	413.8
130°	437.6	437.2	436.9	436.4	435.9	435.3	434.8	434.3
132.5°	455.7	455.6	455.6	455.3	454.8	454.2	453.7	453.1
135°	482.4	482.2	482.0	481.6	481.0	480.3	479.6	479.0
137.5°	507.3	507.4	507.4	507.1	506.6	506.0	505.5	504.9
140°	522.6	522.8	523.1	522.8	522.2	521.5	520.9	520.2
142.5°	537.6	537.6	537.7	537.4	536.7	536.1	535.4	534.8
145°	558.8	558.9	559.0	558.7	558.0	557.4	556.7	556.0
147.5°	576.9	577.0	577.1	576.8	576.0	575.2	574.5	573.7
150°	588.4	588.7	588.8	588.6	587.7	586.8	585.9	585.0
152.5°	598.7	598.9	599.1	598.8	598.1	597.3	596.4	595.6
155°	612.8	613.0	613.4	613.1	612.3	611.4	610.5	609.6
157.5°	624.4	624.7	625.1	624.8	624.0	623.0	622.2	621.3
160°	631.6	632.1	632.5	632.2	631.4	630.5	629.6	628.8
162.5°	638.3	638.9	639.5	639.3	638.3	637.4	636.5	635.4
165°	646.8	647.5	648.1	648.0	647.1	646.3	645.4	644.5
167.5°	653.2	654.0	654.8	654.7	653.8	652.7	651.8	650.7
170°	656.6	657.5	658.3	658.2	657.3	656.3	655.3	654.4
172.5°	659.1	660.0	660.7	660.6	659.6	658.7	657.6	656.7
175°	661.9	662.8	663.7	663.7	662.7	661.7	660.7	659.7
177.5°	663.1	663.7	664.3	664.3	663.6	662.9	662.2	661.5
180°	662.7	662.7	662.7	662.7	662.7	662.7	662.7	662.7

(END OF REPORT)