

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333240-830

Luminaire Tested: **S125DIP-S850D1035U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333240-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S850D1035U830-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6722.1 lumens
Efficiency: N/A
Efficacy: 129.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333240-830

CATALOG NUMBER: S125DIP-S850D1035U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333240-830

CATALOG NUMBER: S125DIP-S850D1035U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48				48
1	97	93	89	85	89	86	82	79	72	70	67	59	58	56	48	47	46				40	
2	89	81	75	70	81	75	69	65	63	59	56	52	49	47	42	40	38				34	
3	81	71	64	58	74	66	59	54	56	51	47	46	43	40	37	35	33				28	
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	30	28				24	
5	68	56	48	42	62	52	45	39	44	39	34	37	33	29	30	27	24				21	
6	62	50	42	36	57	47	39	34	40	34	30	33	29	26	27	24	22				19	
7	58	45	37	32	53	42	35	30	36	30	26	30	26	23	25	22	19				16	
8	54	41	33	28	49	38	31	27	33	27	23	28	23	20	23	20	17				15	
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15				13	
10	47	34	27	22	43	32	26	21	28	22	19	23	19	16	19	16	14				12	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7991	7991	7991
5°	8009	7933	7983
10°	7960	7877	7922
15°	7874	7782	7815
20°	7750	7649	7663
25°	7617	7492	7485
30°	7454	7322	7285
35°	7278	7139	7039
40°	7098	6940	6842
45°	6902	6760	6625
50°	6688	6540	6344
55°	6481	6293	6117
60°	6234	6044	5829
65°	5938	5744	5550
70°	5655	5399	5214
75°	5153	4983	4811
80°	4590	4515	4407
85°	3987	4068	3838



TEST NUMBER: P333240-830

CATALOG NUMBER: S125DIP-S850D1035U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.7	1.7
10°-20°	329.6	4.9
20°-30°	486.6	7.2
30°-40°	567.8	8.4
40°-50°	570.3	8.5
50°-60°	500.6	7.4
60°-70°	373.0	5.5
70°-80°	213.3	3.2
80°-90°	64.7	1.0
90°-100°	338.3	5.0
100°-110°	727.2	10.8
110°-120°	682.5	10.2
120°-130°	553.1	8.2
130°-140°	443.9	6.6
140°-150°	334.9	5.0
150°-160°	235.8	3.5
160°-170°	139.0	2.1
170°-180°	45.2	0.7
0°-30°	932.8	13.9
0°-40°	1500.6	22.3
0°-60°	2571.4	38.3
0°-90°	3222.3	47.9
90°-120°	1747.9	26.0
90°-150°	3079.8	45.8
90°-180°	3500.0	52.1
0°-180°	6722.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1237	1237	1237	1237	1237	
5°	1235	1233	1224	1232	1231	117
15°	1178	1174	1164	1169	1169	332
25°	1069	1064	1051	1053	1050	492
35°	923	919	906	900	893	577
45°	756	751	740	729	725	582
55°	576	572	559	550	543	514
65°	389	386	376	367	363	386
75°	206	204	200	197	193	220
85°	54	55	55	54	52	60
90°	1	8	15	20	22	5
95°	31	92	834	378	221	33
105°	106	149	682	1343	1247	112
115°	190	229	548	1180	1389	187
125°	263	309	525	939	1094	234
135°	309	371	521	787	909	240
145°	359	412	523	652	717	225
155°	410	441	510	576	601	189
165°	448	460	489	519	527	126
175°	466	466	470	475	473	44
180°	467	467	467	467	467	



TEST NUMBER: P333240-830

CATALOG NUMBER: S125DIP-S850D1035U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3
2.5°	1240.5	1239.9	1239.4	1238.9	1238.3	1237.2	1235.5	1233.8	1232.0	1230.3	1232.0
5°	1235.4	1234.9	1234.4	1234.1	1233.6	1232.3	1230.1	1227.9	1225.8	1223.6	1225.6
7.5°	1224.0	1223.6	1223.1	1222.7	1222.3	1220.9	1218.4	1216.1	1213.7	1211.3	1213.1
10°	1213.8	1213.4	1213.0	1212.5	1212.1	1210.7	1208.2	1205.9	1203.5	1201.1	1202.9
12.5°	1201.3	1200.5	1199.8	1198.9	1198.2	1196.7	1194.5	1192.2	1190.0	1187.8	1189.2
15°	1177.6	1177.0	1176.3	1175.6	1175.0	1173.5	1171.1	1168.7	1166.3	1163.9	1165.0
17.5°	1150.4	1149.4	1148.5	1147.5	1146.6	1144.8	1142.4	1139.9	1137.4	1134.9	1136.2
20°	1127.7	1127.3	1126.8	1126.3	1126.0	1124.3	1121.4	1118.6	1115.8	1113.0	1114.6
22.5°	1104.9	1104.2	1103.4	1102.6	1101.8	1100.1	1097.5	1094.8	1092.1	1089.5	1090.5
25°	1068.9	1067.9	1066.8	1065.6	1064.6	1062.6	1059.8	1057.0	1054.1	1051.3	1051.8
27.5°	1026.8	1026.2	1025.6	1024.9	1024.3	1022.5	1019.5	1016.6	1013.7	1010.8	1010.9
30°	999.5	998.8	998.2	997.5	996.8	994.9	991.6	988.4	985.1	981.8	981.4
32.5°	969.7	968.7	967.7	966.7	965.7	963.7	960.8	957.9	955.0	952.1	951.3
35°	923.1	922.2	921.3	920.5	919.6	917.7	914.6	911.5	908.5	905.5	904.4
37.5°	874.8	873.6	872.5	871.5	870.3	868.4	865.5	862.6	859.8	857.0	855.3
40°	841.9	840.7	839.7	838.6	837.4	835.5	832.4	829.3	826.3	823.2	821.3
42.5°	806.6	805.7	804.7	803.9	803.0	801.0	798.0	794.8	791.8	788.8	787.0
45°	755.7	754.8	753.9	753.1	752.2	750.5	747.9	745.3	742.6	740.1	737.4
47.5°	700.9	701.0	701.0	701.0	701.1	699.6	696.4	693.2	690.1	687.0	684.3
50°	665.6	665.0	664.3	663.6	663.1	661.4	658.8	656.2	653.6	650.9	648.1
52.5°	629.6	629.1	628.7	628.2	627.7	626.0	623.3	620.5	617.7	614.9	612.5
55°	575.6	575.0	574.3	573.6	573.0	571.1	568.1	565.1	561.9	558.9	556.9
57.5°	518.6	518.3	517.9	517.6	517.3	515.8	513.2	510.7	508.0	505.5	502.9
60°	482.6	481.7	480.9	479.9	479.1	477.5	475.0	472.7	470.3	467.9	465.7
62.5°	445.0	444.3	443.7	442.9	442.2	440.8	438.8	436.8	434.7	432.6	430.4
65°	388.6	388.1	387.8	387.3	386.9	385.5	383.0	380.7	378.2	375.9	373.9
67.5°	334.0	333.1	332.2	331.2	330.4	328.9	327.3	325.5	323.7	321.9	320.2
70°	299.5	298.4	297.4	296.2	295.2	293.7	291.7	289.7	287.8	285.9	284.6
72.5°	261.9	261.2	260.4	259.8	259.0	258.0	256.7	255.4	254.2	253.0	251.5
75°	206.5	206.1	205.7	205.3	204.8	204.1	202.9	201.9	200.8	199.7	199.1
77.5°	155.4	155.2	155.1	155.0	154.8	154.4	153.7	153.2	152.5	151.9	151.6
80°	123.4	123.4	123.4	123.4	123.4	123.1	122.7	122.2	121.8	121.4	121.2
82.5°	95.1	94.8	94.4	94.1	93.8	93.5	93.4	93.4	93.3	93.2	92.8
85°	53.8	54.1	54.3	54.5	54.7	54.9	54.9	54.9	54.9	54.9	54.6
87.5°	21.3	21.5	21.9	22.2	22.6	22.9	23.0	23.2	23.2	23.4	23.6
90°	0.9	1.9	3.8	5.7	7.5	9.4	10.4	12.3	13.2	15.1	16.0
92.5°	11.5	13.9	21.9	33.5	49.7	77.2	128.6	214.7	308.2	303.3	245.5
95°	31.0	32.0	39.5	49.9	70.6	112.9	213.6	420.6	680.3	833.7	815.8
97.5°	51.6	52.7	58.0	68.3	86.9	117.4	184.1	335.7	607.5	890.3	1032.2
100°	65.9	67.8	71.5	81.8	99.7	128.0	182.6	304.8	542.0	849.6	1084.9
102.5°	81.7	82.8	85.8	96.9	113.3	140.7	189.4	292.1	492.3	778.2	1053.3
105°	106.3	106.3	111.0	120.5	135.5	161.8	203.2	287.0	444.1	682.1	952.3
107.5°	130.4	132.3	136.8	144.5	160.1	183.9	223.9	295.7	423.8	616.1	849.0
110°	147.7	149.6	153.4	161.8	176.0	200.4	239.0	303.9	417.7	585.2	790.3



TEST NUMBER: P333240-830

CATALOG NUMBER: S125DIP-S850D1035U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	165.0	166.9	169.9	178.4	192.5	216.2	253.3	314.4	417.7	567.2	746.7
115°	190.1	191.9	194.7	203.2	217.4	240.9	275.7	330.3	420.6	547.6	699.1
117.5°	212.6	215.5	218.5	227.0	243.0	265.7	298.7	348.4	426.8	538.0	670.7
120°	227.7	230.5	234.3	242.8	258.7	282.3	315.2	360.3	432.8	533.5	654.9
122.5°	243.6	245.5	248.5	257.0	274.6	298.1	331.0	373.9	438.1	529.7	641.3
125°	263.4	265.3	270.0	278.5	296.4	320.8	351.9	392.4	447.0	525.0	622.9
127.5°	279.1	281.9	287.9	298.7	317.6	342.1	372.0	409.3	456.9	522.7	606.0
130°	288.9	291.7	299.3	311.4	331.2	355.6	384.8	420.6	463.0	521.2	594.7
132.5°	296.4	299.9	309.0	322.7	343.3	367.7	396.9	430.4	469.7	521.2	585.6
135°	308.6	312.4	323.7	338.7	358.4	383.9	413.0	444.1	478.9	521.2	574.9
137.5°	324.0	326.9	337.4	352.5	371.8	398.0	424.5	454.3	487.4	522.4	565.3
140°	333.1	335.9	347.2	362.2	380.1	405.6	432.8	461.1	491.2	523.1	560.8
142.5°	343.7	345.7	356.2	371.3	388.4	412.3	438.1	464.8	493.4	523.9	557.0
145°	359.4	361.3	370.7	383.9	400.9	422.4	447.0	470.4	495.9	523.1	551.4
147.5°	376.0	377.1	385.2	397.5	412.1	431.1	452.6	473.8	496.8	520.7	545.5
150°	385.8	387.7	394.3	406.5	419.6	435.6	456.4	476.1	496.8	518.4	541.0
152.5°	396.3	397.5	403.3	414.0	426.4	440.9	460.1	477.6	496.1	515.5	535.7
155°	410.2	410.2	415.8	425.3	434.7	447.9	463.8	478.9	494.0	510.0	526.9
157.5°	422.6	422.4	427.0	435.1	443.4	453.4	467.0	479.8	491.5	504.4	518.6
160°	430.9	430.0	433.8	440.4	447.9	456.4	468.5	479.8	489.3	500.6	511.9
162.5°	437.7	436.8	440.5	446.4	452.4	459.4	470.0	479.1	487.0	496.1	505.9
165°	447.9	446.0	448.8	453.6	457.3	463.0	470.4	478.0	483.6	489.3	496.8
167.5°	454.7	453.7	455.4	458.1	460.7	464.2	470.4	475.7	478.3	482.7	488.0
170°	459.2	458.3	459.2	461.1	463.0	465.7	470.4	474.2	476.1	478.9	482.7
172.5°	462.2	460.5	461.5	463.3	464.4	465.7	469.7	472.7	473.1	474.4	477.4
175°	465.7	463.8	464.8	465.7	465.7	465.7	468.5	470.4	469.5	469.5	470.4
177.5°	467.4	465.9	465.9	466.7	465.9	465.9	467.4	468.2	466.7	466.7	467.4
180°	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7



TEST NUMBER: P333240-830

CATALOG NUMBER: S125DIP-S850D1035U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3	1237.3
2.5°	1233.8	1235.5	1237.2	1238.0	1237.8	1237.7	1237.5	1237.3
5°	1227.6	1229.5	1231.4	1232.3	1232.1	1231.9	1231.6	1231.4
7.5°	1215.1	1217.0	1218.9	1219.7	1219.6	1219.4	1219.1	1218.9
10°	1204.6	1206.4	1208.1	1208.8	1208.6	1208.3	1208.2	1208.0
12.5°	1190.5	1191.9	1193.4	1194.0	1194.0	1193.9	1193.9	1193.8
15°	1166.1	1167.2	1168.3	1168.8	1168.8	1168.8	1168.8	1168.8
17.5°	1137.6	1139.0	1140.3	1140.5	1139.3	1138.3	1137.2	1136.1
20°	1116.1	1117.6	1119.1	1119.3	1118.2	1117.1	1116.1	1114.9
22.5°	1091.5	1092.5	1093.5	1093.6	1092.9	1092.1	1091.4	1090.7
25°	1052.2	1052.6	1053.1	1052.9	1052.3	1051.7	1051.0	1050.4
27.5°	1011.0	1011.1	1011.2	1010.9	1010.2	1009.6	1008.9	1008.2
30°	981.0	980.5	980.1	979.6	978.9	978.3	977.6	976.9
32.5°	950.5	949.7	949.0	947.9	946.8	945.6	944.4	943.3
35°	903.3	902.2	901.2	899.8	898.0	896.3	894.5	892.8
37.5°	853.7	852.1	850.5	849.1	848.2	847.2	846.2	845.2
40°	819.4	817.4	815.4	814.1	813.4	812.8	812.2	811.5
42.5°	785.2	783.4	781.7	780.2	779.3	778.3	777.2	776.3
45°	734.8	732.2	729.6	727.9	727.4	726.7	726.0	725.4
47.5°	681.6	679.0	676.4	674.3	672.8	671.3	669.7	668.2
50°	645.3	642.4	639.6	637.4	635.9	634.4	632.9	631.4
52.5°	610.0	607.5	605.0	602.9	601.2	599.6	597.9	596.2
55°	555.1	553.1	551.1	549.4	547.8	546.3	544.8	543.3
57.5°	500.5	497.9	495.4	493.7	492.9	492.1	491.3	490.4
60°	463.5	461.4	459.2	457.3	455.8	454.3	452.8	451.3
62.5°	428.0	425.7	423.3	421.5	420.4	419.1	418.0	416.8
65°	372.0	370.0	368.1	366.6	365.8	365.0	364.0	363.2
67.5°	318.6	316.9	315.3	314.1	313.7	313.1	312.5	312.1
70°	283.2	281.9	280.6	279.6	278.6	277.8	276.9	276.1
72.5°	250.0	248.5	247.0	245.8	245.0	244.1	243.3	242.3
75°	198.4	197.7	197.1	196.3	195.5	194.5	193.7	192.8
77.5°	151.2	150.7	150.3	149.9	149.2	148.6	148.1	147.4
80°	120.9	120.7	120.6	120.2	119.8	119.3	118.9	118.5
82.5°	92.4	92.0	91.6	91.4	91.3	91.2	91.1	91.0
85°	54.4	54.2	53.9	53.6	53.2	52.8	52.3	51.8
87.5°	23.8	23.9	24.1	24.3	23.9	23.7	23.5	23.1
90°	17.0	17.9	18.9	20.7	20.7	20.7	21.7	21.7
92.5°	166.7	121.0	91.0	77.2	65.1	62.9	61.5	60.0
95°	676.6	533.5	417.7	338.7	271.9	243.7	236.2	221.1
97.5°	1007.6	907.2	794.5	684.6	626.5	573.7	546.5	534.4
100°	1157.3	1111.3	1014.3	916.4	851.5	783.8	748.9	734.0
102.5°	1207.8	1236.1	1189.7	1123.4	1054.0	1005.9	968.0	956.7
105°	1178.0	1306.9	1348.3	1337.9	1307.9	1276.9	1258.0	1246.7
107.5°	1071.9	1243.9	1350.2	1399.3	1414.6	1414.4	1408.2	1400.6
110°	993.6	1172.3	1305.0	1385.1	1427.4	1445.2	1451.8	1451.8



TEST NUMBER: P333240-830

CATALOG NUMBER: S125DIP-S850D1035U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	931.9	1101.6	1235.8	1330.1	1391.9	1422.7	1439.1	1445.8
115°	854.3	1000.2	1129.1	1231.6	1305.0	1350.2	1376.6	1388.8
117.5°	804.3	930.0	1041.0	1135.1	1208.5	1255.2	1281.3	1288.8
120°	777.2	890.1	993.6	1076.4	1146.0	1191.2	1216.6	1224.2
122.5°	756.9	861.5	953.7	1031.2	1093.3	1134.7	1160.2	1167.0
125°	727.4	823.3	905.1	972.9	1025.6	1064.1	1084.9	1094.3
127.5°	697.2	786.8	863.2	926.6	974.4	1008.4	1028.0	1032.2
130°	678.4	761.2	834.6	895.8	942.8	973.8	992.7	998.3
132.5°	659.6	737.1	803.7	862.6	909.6	940.8	958.0	964.4
135°	635.1	700.0	760.3	813.9	855.3	886.4	903.2	908.9
137.5°	614.4	666.9	717.0	762.5	799.6	827.8	843.5	849.6
140°	603.1	647.3	690.6	730.2	765.0	789.5	803.5	808.2
142.5°	593.3	630.7	668.1	702.3	731.9	752.5	765.9	769.9
145°	580.5	609.7	638.9	664.3	686.8	702.9	713.2	717.0
147.5°	568.5	592.2	614.6	633.8	651.7	664.5	670.5	672.2
150°	561.8	582.4	600.3	617.3	631.3	642.6	646.4	647.3
152.5°	554.2	572.6	589.0	602.2	614.1	623.1	626.8	627.7
155°	542.9	558.0	571.2	581.5	590.9	597.5	600.3	601.2
157.5°	531.6	544.0	554.2	562.3	569.7	575.0	577.7	577.5
160°	524.1	533.5	542.9	549.5	556.1	560.8	562.7	561.8
162.5°	515.9	524.4	532.3	538.2	543.3	547.2	547.6	547.4
165°	504.4	511.0	516.6	521.2	525.0	526.9	526.9	526.9
167.5°	493.4	497.8	502.1	505.5	507.4	509.1	508.3	508.1
170°	487.4	490.2	493.0	494.9	496.8	497.8	497.8	496.8
172.5°	480.6	483.4	485.5	486.6	487.0	488.7	487.2	486.3
175°	473.3	473.3	475.1	475.1	475.1	476.1	474.2	473.3
177.5°	468.2	468.9	468.9	468.9	468.2	468.9	466.7	466.7
180°	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7

(END OF REPORT)