

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333613-935

Luminaire Tested: **S125RDIP-S1270D365U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333613-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1270D365U935-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5460.5 lumens
Efficiency: N/A
Efficacy: 109.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333613-935

CATALOG NUMBER: S125RDIP-S1270D365U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333613-935

CATALOG NUMBER: S125RDIP-S1270D365U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	108	108	108	108	98	98	98	89	89	89	81	81	81	77
1	104	100	96	92	99	95	92	89	87	84	82	79	77	75	72	71	69	66
2	95	88	81	76	90	84	78	73	77	72	68	70	66	63	64	61	59	55
3	87	77	70	64	83	74	67	62	68	62	58	62	58	54	57	53	50	47
4	80	69	61	54	76	66	59	53	61	54	50	56	51	47	51	47	44	41
5	74	62	53	47	70	59	51	46	54	48	43	50	45	41	46	42	38	36
6	68	56	47	41	65	53	46	40	49	43	38	45	40	36	42	37	34	31
7	63	50	42	36	60	48	41	35	45	38	34	42	36	32	38	34	30	28
8	59	46	38	32	56	44	37	32	41	35	30	38	33	29	35	31	27	25
9	55	42	34	29	52	41	33	29	38	32	27	35	30	26	33	28	25	23
10	51	39	31	26	49	38	31	26	35	29	25	33	27	24	30	26	22	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11479	11479	11479
5°	11505	11374	11444
10°	11418	11269	11269
15°	11282	11040	10950
20°	11109	10721	10592
25°	10905	10408	10178
30°	10651	10041	9721
35°	10394	9663	9208
40°	10151	9269	8703
45°	9858	8828	8153
50°	9562	8349	7580
55°	9221	7891	6969
60°	8878	7334	6311
65°	8472	6687	5559
70°	8010	5880	4791
75°	7369	4956	3985
80°	6490	3894	3347
85°	5476	3186	2986



TEST NUMBER: P333613-935

CATALOG NUMBER: S125RDIP-S1270D365U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.1	3.1
10°-20°	467.1	8.6
20°-30°	677.3	12.4
30°-40°	771.9	14.1
40°-50°	752.4	13.8
50°-60°	633.3	11.6
60°-70°	444.0	8.1
70°-80°	228.2	4.2
80°-90°	58.5	1.1
90°-100°	14.9	0.3
100°-110°	92.0	1.7
110°-120°	166.8	3.1
120°-130°	214.0	3.9
130°-140°	230.2	4.2
140°-150°	216.1	4.0
150°-160°	174.8	3.2
160°-170°	113.0	2.1
170°-180°	39.0	0.7
0°-30°	1311.5	24.0
0°-40°	2083.3	38.2
0°-60°	3469.1	63.5
0°-90°	4199.7	76.9
90°-120°	273.7	5.0
90°-150°	934.0	17.1
90°-180°	1261.0	23.1
0°-180°	5460.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1777	1777	1777	1777	1777	
5°	1775	1769	1754	1767	1765	168
15°	1687	1678	1651	1649	1638	475
25°	1530	1509	1460	1443	1428	704
35°	1318	1284	1226	1188	1168	825
45°	1079	1038	967	915	893	832
55°	819	774	701	642	619	732
65°	554	507	438	386	364	549
75°	295	254	199	170	160	313
85°	74	51	43	42	40	83
90°	0	3	5	6	7	4
95°	17	16	5	6	6	22
105°	90	91	91	91	90	95
115°	168	169	170	169	167	166
125°	239	241	241	240	239	213
135°	298	300	299	298	297	230
145°	345	346	346	346	344	216
155°	380	379	379	380	378	175
165°	401	400	400	402	399	113
175°	410	409	409	411	409	39
180°	410	410	410	410	410	



TEST NUMBER: P333613-935

CATALOG NUMBER: S125RDIP-S1270D365U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1777.4	1777.4	1777.4	1777.4	1777.4	1777.4	1777.4	1777.4	1777.4	1777.4	1777.4
2.5°	1780.5	1779.9	1779.1	1778.4	1777.7	1776.2	1773.7	1771.3	1769.0	1766.6	1769.0
5°	1774.7	1773.5	1772.3	1771.1	1769.9	1767.6	1764.4	1761.1	1757.8	1754.5	1757.5
7.5°	1757.2	1756.1	1755.0	1753.8	1752.7	1750.2	1746.2	1742.2	1738.4	1734.4	1736.5
10°	1741.1	1740.2	1739.3	1738.4	1737.5	1735.0	1730.8	1726.6	1722.4	1718.3	1719.2
12.5°	1722.9	1721.7	1720.5	1719.4	1718.3	1714.9	1709.3	1703.7	1698.1	1692.5	1693.2
15°	1687.4	1685.6	1683.9	1682.0	1680.2	1676.2	1669.9	1663.7	1657.4	1651.1	1650.9
17.5°	1647.4	1644.7	1641.9	1639.2	1636.4	1631.1	1623.2	1615.3	1607.5	1599.6	1598.1
20°	1616.3	1613.3	1610.2	1607.3	1604.3	1598.0	1588.5	1579.0	1569.4	1559.9	1558.4
22.5°	1581.9	1578.9	1575.9	1573.0	1569.9	1563.5	1553.4	1543.4	1533.4	1523.4	1520.4
25°	1530.3	1525.9	1521.4	1516.9	1512.4	1504.7	1493.7	1482.6	1471.5	1460.5	1456.6
27.5°	1471.3	1465.9	1460.4	1455.0	1449.6	1441.0	1429.1	1417.3	1405.5	1393.7	1388.3
30°	1428.3	1422.6	1416.9	1411.4	1405.7	1396.5	1384.0	1371.5	1358.9	1346.4	1339.5
32.5°	1386.5	1379.8	1373.2	1366.6	1359.9	1350.2	1337.5	1324.7	1311.9	1299.2	1291.6
35°	1318.3	1311.0	1303.9	1296.8	1289.6	1279.3	1265.8	1252.5	1239.1	1225.6	1216.9
37.5°	1251.4	1242.7	1234.0	1225.3	1216.5	1205.2	1191.5	1177.6	1163.7	1149.9	1139.5
40°	1204.1	1195.2	1186.2	1177.2	1168.4	1156.7	1142.4	1128.1	1113.7	1099.4	1088.1
42.5°	1154.8	1145.6	1136.3	1127.1	1118.0	1106.0	1091.2	1076.4	1061.6	1046.8	1036.0
45°	1079.3	1070.7	1062.0	1053.3	1044.7	1032.2	1015.7	999.4	982.9	966.6	954.6
47.5°	1001.2	992.0	982.9	973.8	964.7	951.8	935.3	918.8	902.2	885.7	873.4
50°	951.7	941.9	932.0	922.2	912.4	899.0	881.9	865.0	847.9	831.0	818.4
52.5°	898.0	887.9	877.9	867.8	857.7	844.6	828.6	812.6	796.5	780.5	767.0
55°	818.9	809.3	799.8	790.2	780.7	767.6	750.9	734.2	717.5	700.8	687.3
57.5°	738.8	728.7	718.4	708.3	698.0	684.9	668.8	652.6	636.5	620.4	607.3
60°	687.3	676.8	666.4	656.0	645.6	632.2	616.1	600.0	583.9	567.8	554.7
62.5°	632.6	622.6	612.6	602.6	592.7	579.5	563.2	546.8	530.5	514.1	502.0
65°	554.4	544.2	534.2	524.0	513.8	500.8	485.1	469.2	453.4	437.6	425.7
67.5°	476.8	466.7	456.5	446.4	436.3	423.6	408.5	393.3	378.2	363.0	352.1
70°	424.2	414.1	403.9	393.7	383.7	371.1	356.2	341.3	326.3	311.4	302.2
72.5°	372.6	362.7	352.8	342.9	333.0	321.1	307.1	293.2	279.2	265.3	256.8
75°	295.3	286.4	277.4	268.5	259.5	248.8	236.3	223.8	211.2	198.6	192.1
77.5°	218.5	211.4	204.2	197.1	189.9	181.3	171.3	161.3	151.3	141.2	136.6
80°	174.5	167.4	160.2	153.0	145.9	138.1	129.8	121.4	113.0	104.7	102.0
82.5°	131.6	125.1	118.6	112.2	105.8	99.7	93.9	88.3	82.5	76.8	75.5
85°	73.9	68.4	63.1	57.7	52.3	48.9	47.4	46.0	44.4	43.0	42.6
87.5°	24.8	23.2	21.6	20.1	18.5	17.7	17.5	17.4	17.2	17.0	17.1
90°	0.3	0.9	1.4	1.9	2.5	3.0	3.4	4.0	4.4	4.9	5.2
92.5°	4.6	4.3	4.0	3.5	3.2	3.2	3.6	4.0	4.5	4.9	5.2
95°	17.3	17.1	17.0	16.7	16.5	15.2	12.6	10.0	7.4	4.9	5.2
97.5°	36.2	36.6	36.9	37.3	37.7	35.3	30.2	25.1	20.1	15.0	13.1
100°	50.8	51.1	51.2	51.4	51.7	51.8	52.2	52.4	52.7	53.0	42.9
102.5°	65.7	66.0	66.2	66.5	66.7	66.9	67.1	67.2	67.4	67.6	65.7
105°	89.5	89.7	90.1	90.3	90.6	90.7	90.7	90.7	90.7	90.7	90.7
107.5°	114.2	114.2	114.2	114.2	114.2	114.3	114.4	114.5	114.7	114.8	114.8
110°	130.3	130.3	130.3	130.3	130.3	130.4	130.4	130.6	130.7	130.9	130.7



TEST NUMBER: P333613-935

CATALOG NUMBER: S125RDIP-S1270D365U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	145.3	145.5	145.7	145.9	146.0	146.1	146.2	146.3	146.4	146.5	146.2
115°	168.0	168.3	168.7	169.0	169.4	169.5	169.6	169.7	169.8	169.8	169.5
117.5°	191.4	191.4	191.4	191.4	191.4	191.5	191.7	192.0	192.3	192.5	192.2
120°	206.0	206.0	206.0	205.9	205.8	205.9	206.0	206.2	206.5	206.6	206.6
122.5°	219.0	219.2	219.5	219.7	220.0	220.2	220.2	220.3	220.4	220.5	220.4
125°	238.9	239.4	239.9	240.3	240.8	241.1	241.1	241.1	241.1	241.1	240.7
127.5°	258.0	258.3	258.6	259.0	259.3	259.5	259.4	259.4	259.3	259.3	259.2
130°	269.7	270.0	270.4	270.7	271.0	271.2	271.3	271.3	271.4	271.5	271.3
132.5°	281.4	281.7	282.1	282.5	282.9	283.0	282.9	282.8	282.6	282.4	282.4
135°	298.0	298.3	298.8	299.2	299.5	299.7	299.5	299.5	299.3	299.2	299.0
137.5°	313.2	313.6	313.9	314.3	314.6	314.8	314.6	314.5	314.4	314.3	314.3
140°	323.2	323.4	323.5	323.6	323.7	323.8	323.7	323.6	323.6	323.6	323.6
142.5°	332.3	332.3	332.4	332.4	332.5	332.6	332.8	332.9	332.9	333.0	333.0
145°	345.4	345.6	345.7	345.9	345.9	346.0	346.0	346.0	346.0	346.0	346.1
147.5°	357.0	357.0	357.0	356.9	356.9	356.9	357.0	357.1	357.1	357.2	357.3
150°	364.3	364.2	364.0	363.9	363.8	363.8	363.9	364.0	364.2	364.3	364.5
152.5°	371.3	371.1	370.7	370.5	370.1	370.1	370.2	370.4	370.5	370.7	370.7
155°	380.5	380.0	379.6	379.2	378.8	378.7	378.8	378.9	379.1	379.2	379.4
157.5°	387.4	387.2	386.9	386.7	386.5	386.3	386.3	386.4	386.4	386.4	386.6
160°	392.3	391.9	391.5	391.1	390.7	390.5	390.5	390.6	390.7	390.8	391.1
162.5°	396.2	395.8	395.4	394.9	394.6	394.4	394.5	394.5	394.6	394.7	395.0
165°	401.4	401.1	400.6	400.2	399.8	399.7	399.7	399.8	399.8	399.9	400.3
167.5°	405.4	404.9	404.5	404.1	403.6	403.5	403.6	403.6	403.7	403.7	404.2
170°	407.5	407.1	406.6	406.1	405.6	405.4	405.5	405.5	405.6	405.7	406.2
172.5°	409.0	408.5	408.0	407.6	407.1	406.9	407.0	407.2	407.3	407.4	407.9
175°	410.5	410.2	409.7	409.3	409.0	408.8	408.8	408.9	409.0	409.1	409.6
177.5°	411.3	411.0	410.6	410.4	410.0	409.8	409.9	410.0	410.0	410.1	410.4
180°	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5



TEST NUMBER: P333613-935

CATALOG NUMBER: S125RDIP-S1270D365U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1777.4	1777.4	1777.4	1777.4	1777.4	1777.4	1777.4	1777.4
2.5°	1771.3	1773.7	1776.2	1777.2	1777.0	1776.8	1776.5	1776.2
5°	1760.5	1763.5	1766.4	1767.6	1767.0	1766.4	1765.8	1765.2
7.5°	1738.5	1740.7	1742.8	1743.4	1742.8	1742.1	1741.5	1740.9
10°	1720.0	1721.0	1721.8	1721.8	1721.0	1720.0	1719.2	1718.3
12.5°	1693.8	1694.4	1695.1	1694.8	1693.4	1692.0	1690.7	1689.3
15°	1650.5	1650.3	1649.9	1648.5	1645.8	1643.1	1640.4	1637.7
17.5°	1596.6	1595.1	1593.6	1591.8	1589.6	1587.3	1585.2	1582.9
20°	1556.9	1555.4	1553.9	1551.8	1549.1	1546.4	1543.8	1541.1
22.5°	1517.5	1514.6	1511.7	1509.1	1506.9	1504.7	1502.4	1500.3
25°	1452.8	1448.9	1445.0	1441.4	1438.1	1434.9	1431.6	1428.3
27.5°	1382.9	1377.4	1372.0	1367.7	1364.5	1361.3	1358.1	1355.0
30°	1332.7	1325.9	1319.0	1314.2	1311.6	1308.8	1306.1	1303.5
32.5°	1284.0	1276.4	1268.9	1263.3	1260.0	1256.5	1253.2	1249.7
35°	1208.3	1199.6	1191.0	1184.6	1180.4	1176.2	1172.1	1167.9
37.5°	1129.1	1118.8	1108.4	1101.1	1097.1	1093.0	1089.0	1084.9
40°	1076.8	1065.4	1054.1	1046.6	1043.0	1039.5	1035.9	1032.3
42.5°	1025.1	1014.3	1003.4	995.3	990.1	984.8	979.6	974.3
45°	942.6	930.7	918.8	910.6	906.1	901.6	897.2	892.7
47.5°	861.2	848.9	836.5	827.9	822.9	818.0	813.0	808.1
50°	805.9	793.3	780.8	772.3	767.8	763.4	758.9	754.4
52.5°	753.5	740.0	726.5	717.6	713.1	708.6	704.1	699.6
55°	673.9	660.5	647.0	637.9	633.2	628.4	623.6	618.9
57.5°	594.2	581.1	567.9	559.3	555.0	550.8	546.6	542.3
60°	541.6	528.5	515.3	506.5	502.0	497.6	493.1	488.6
62.5°	489.8	477.6	465.5	457.1	452.6	448.2	443.7	439.2
65°	413.8	401.8	389.9	381.7	377.2	372.7	368.2	363.8
67.5°	341.1	330.2	319.3	312.0	308.5	304.9	301.4	297.7
70°	292.9	283.7	274.5	268.0	264.4	260.9	257.3	253.7
72.5°	248.2	239.7	231.1	225.7	223.3	220.9	218.5	216.1
75°	185.5	179.0	172.5	168.1	166.0	163.9	161.9	159.7
77.5°	132.0	127.4	122.9	119.8	118.2	116.7	115.1	113.6
80°	99.4	96.7	93.9	92.3	91.7	91.1	90.6	90.0
82.5°	74.3	73.0	71.8	70.9	70.6	70.3	69.9	69.6
85°	42.4	42.1	41.8	41.5	41.2	40.9	40.6	40.3
87.5°	17.2	17.3	17.4	17.3	17.0	16.9	16.7	16.5
90°	5.5	5.9	6.2	6.5	6.7	6.9	7.1	7.3
92.5°	5.5	5.9	6.2	6.5	6.5	6.6	6.7	6.8
95°	5.5	5.9	6.2	6.4	6.4	6.4	6.4	6.4
97.5°	11.2	9.2	7.3	6.4	6.4	6.4	6.4	6.4
100°	32.8	22.7	12.7	7.5	7.2	7.0	6.6	6.4
102.5°	63.7	61.8	59.9	56.7	52.1	47.5	42.9	38.3
105°	90.7	90.7	90.7	90.7	90.6	90.5	90.5	90.4
107.5°	114.9	114.9	114.9	114.8	114.6	114.3	114.2	113.9
110°	130.4	130.3	130.1	130.0	130.1	130.1	130.2	130.3



TEST NUMBER: P333613-935

CATALOG NUMBER: S125RDIP-S1270D365U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	145.9	145.7	145.4	145.3	145.2	145.1	145.0	144.9
115°	169.3	169.0	168.8	168.4	168.0	167.6	167.2	166.8
117.5°	191.8	191.5	191.1	190.9	190.7	190.5	190.4	190.2
120°	206.4	206.2	206.1	205.9	205.5	205.2	204.8	204.5
122.5°	220.2	220.2	220.0	219.7	219.3	219.0	218.5	218.2
125°	240.5	240.2	240.0	239.7	239.5	239.4	239.1	238.9
127.5°	259.0	258.8	258.7	258.4	257.9	257.4	256.9	256.4
130°	271.0	270.9	270.7	270.4	270.1	269.8	269.4	269.1
132.5°	282.3	282.3	282.2	282.1	281.7	281.4	281.0	280.8
135°	298.9	298.8	298.6	298.3	298.0	297.6	297.1	296.7
137.5°	314.4	314.4	314.4	314.2	313.8	313.5	313.1	312.8
140°	323.8	323.9	324.1	323.9	323.6	323.1	322.7	322.3
142.5°	333.0	333.1	333.1	332.9	332.5	332.1	331.7	331.3
145°	346.2	346.2	346.3	346.1	345.8	345.3	344.9	344.5
147.5°	357.4	357.5	357.6	357.4	356.9	356.4	355.9	355.4
150°	364.5	364.7	364.8	364.6	364.1	363.6	363.0	362.5
152.5°	370.9	371.0	371.2	371.0	370.5	370.1	369.5	369.0
155°	379.6	379.8	380.0	379.9	379.4	378.8	378.2	377.7
157.5°	386.8	387.0	387.3	387.1	386.6	386.0	385.5	385.0
160°	391.3	391.6	391.8	391.8	391.2	390.6	390.1	389.6
162.5°	395.5	395.8	396.2	396.1	395.5	394.9	394.3	393.7
165°	400.7	401.1	401.6	401.5	401.0	400.4	399.8	399.3
167.5°	404.8	405.2	405.7	405.6	405.0	404.4	403.8	403.2
170°	406.7	407.3	407.9	407.9	407.3	406.7	406.0	405.4
172.5°	408.4	408.9	409.3	409.3	408.7	408.0	407.4	406.8
175°	410.1	410.7	411.2	411.2	410.5	409.9	409.3	408.7
177.5°	410.9	411.2	411.6	411.6	411.1	410.7	410.3	409.8
180°	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5

(END OF REPORT)