

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333205-830

Luminaire Tested: **S125DIP-S850D365U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333205-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S850D365U830-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4634.9 lumens
Efficiency: N/A
Efficacy: 132.4 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 35
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333205-830

CATALOG NUMBER: S125DIP-S850D365U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333205-830

CATALOG NUMBER: S125DIP-S850D365U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	84	84	84	75	75	75	70
1	103	98	94	91	97	93	90	87	84	81	79	75	73	71	67	65	64	60
2	94	86	80	75	88	82	76	72	74	69	66	66	63	60	59	56	54	51
3	86	76	69	63	81	72	66	60	65	60	55	59	54	51	52	49	46	43
4	79	68	59	53	74	64	57	51	58	52	48	52	48	44	47	43	40	37
5	72	60	52	46	68	58	50	44	52	46	41	47	42	38	42	38	35	32
6	67	54	46	40	63	52	44	39	47	41	36	43	38	34	39	34	31	28
7	62	49	41	35	58	47	40	34	43	37	32	39	34	30	35	31	28	25
8	57	45	37	31	54	43	36	30	39	33	28	36	30	27	32	28	25	23
9	54	41	33	28	51	39	32	27	36	30	26	33	28	24	30	26	22	20
10	50	38	30	25	47	36	29	25	33	27	23	30	25	22	28	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7447	7447	7447	7447
5°	8624	7472	6543	7472
10°	10033	7433	5732	7433
15°	11106	7379	5288	7379
20°	12432	7292	4931	7292
25°	14564	7195	4757	7195
30°	15731	7099	4606	7099
35°	12934	6918	4507	6918
40°	9193	6668	4398	6668
45°	7063	6330	4337	6330
50°	6028	5910	4326	5910
55°	5368	5499	4365	5499
60°	4841	5052	4476	5052
65°	4473	4600	4592	4600
70°	4067	4132	4658	4132
75°	3591	3638	4616	3638
80°	3020	2964	4225	2964
85°	2393	2134	3409	2134



TEST NUMBER: P333205-830

CATALOG NUMBER: S125DIP-S850D365U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.0	2.4
10°-20°	330.5	7.1
20°-30°	536.7	11.6
30°-40°	654.6	14.1
40°-50°	595.5	12.8
50°-60°	474.4	10.2
60°-70°	330.4	7.1
70°-80°	176.2	3.8
80°-90°	45.4	1.0
90°-100°	16.3	0.4
100°-110°	100.7	2.2
110°-120°	182.6	3.9
120°-130°	234.3	5.1
130°-140°	252.0	5.4
140°-150°	236.5	5.1
150°-160°	191.3	4.1
160°-170°	123.8	2.7
170°-180°	42.7	0.9
0°-30°	978.2	21.1
0°-40°	1632.8	35.2
0°-60°	2702.7	58.3
0°-90°	3254.7	70.2
90°-120°	299.6	6.5
90°-150°	1022.4	22.1
90°-180°	1380.0	29.8
0°-180°	4634.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1153	1153	1153	1153	1153	
5°	1330	1152	1009	1152	1330	134
15°	1661	1104	791	1104	1661	476
25°	2044	1010	668	1010	2044	934
35°	1640	878	572	878	1640	1004
45°	773	693	475	693	773	619
55°	477	488	388	488	477	429
65°	293	301	300	301	293	290
75°	144	146	185	146	144	155
85°	32	29	46	29	32	37
90°	8	0	8	0	8	5
95°	7	19	7	19	7	6
105°	99	98	99	98	99	89
115°	183	184	183	184	183	181
125°	262	262	262	262	262	233
135°	325	326	325	326	325	251
145°	377	378	377	378	377	236
155°	414	416	414	416	414	191
165°	437	439	437	439	437	123
175°	447	449	447	449	447	43
180°	449	449	449	449	449	



TEST NUMBER: P333205-830

CATALOG NUMBER: S125DIP-S850D365U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1
2.5°	1219.7	1218.0	1216.5	1213.3	1215.7	1209.1	1205.9	1200.4	1193.8	1191.5	1188.7
5°	1330.2	1332.7	1335.1	1324.8	1325.9	1319.0	1303.3	1290.6	1280.3	1267.2	1257.8
7.5°	1463.4	1457.5	1457.1	1450.5	1439.0	1429.8	1413.3	1392.4	1372.2	1349.1	1329.9
10°	1529.9	1530.4	1526.0	1518.2	1506.0	1497.1	1475.6	1455.0	1430.1	1400.7	1379.7
12.5°	1580.1	1582.1	1576.5	1565.9	1560.0	1540.2	1523.3	1498.9	1469.2	1445.8	1413.7
15°	1661.1	1655.7	1651.8	1638.6	1628.3	1607.8	1580.8	1555.4	1523.1	1493.2	1463.4
17.5°	1739.2	1743.5	1736.2	1724.1	1692.2	1668.2	1632.1	1597.2	1557.1	1517.0	1481.4
20°	1808.9	1812.8	1801.6	1780.6	1742.4	1718.3	1670.8	1625.9	1579.3	1528.0	1488.8
22.5°	1895.8	1892.7	1877.5	1845.5	1812.4	1768.1	1716.7	1661.9	1603.6	1545.6	1493.6
25°	2043.8	2023.3	2013.9	1974.3	1930.8	1865.7	1795.2	1715.0	1642.5	1565.7	1499.1
27.5°	2125.8	2119.4	2109.0	2081.4	2035.6	1966.0	1882.9	1785.1	1682.9	1585.9	1498.8
30°	2109.4	2110.4	2111.4	2102.5	2073.2	2020.8	1938.2	1832.9	1711.5	1602.3	1501.6
32.5°	1963.8	1981.6	1998.6	2018.7	2026.9	2016.9	1965.1	1870.1	1745.2	1621.2	1500.0
35°	1640.5	1646.0	1701.2	1756.1	1830.4	1888.2	1926.8	1884.8	1779.5	1637.1	1498.1
37.5°	1279.1	1305.6	1343.9	1405.8	1513.2	1609.3	1733.0	1789.8	1755.9	1642.3	1494.7
40°	1090.4	1114.9	1139.8	1203.0	1293.5	1410.0	1550.5	1670.4	1698.3	1625.9	1482.9
42.5°	944.8	964.1	991.8	1039.3	1115.0	1218.1	1352.4	1509.1	1605.5	1578.1	1458.3
45°	773.3	785.5	807.1	844.7	899.6	980.3	1098.7	1270.1	1419.3	1468.8	1399.8
47.5°	661.9	661.8	678.5	704.6	744.1	812.8	900.3	1034.5	1194.0	1311.9	1306.5
50°	600.0	597.6	610.8	633.3	664.6	710.1	793.8	901.0	1054.2	1187.8	1225.0
52.5°	546.8	547.1	555.2	571.8	598.0	637.0	699.5	796.1	927.0	1064.1	1134.2
55°	476.7	474.8	484.0	495.3	514.3	539.8	584.8	658.7	765.0	900.0	991.1
57.5°	412.5	417.8	421.6	429.4	445.3	462.3	500.3	554.5	638.8	754.7	850.9
60°	374.8	380.3	383.2	391.1	403.8	418.5	447.8	491.9	562.8	662.7	758.1
62.5°	341.2	345.4	346.4	353.5	363.8	378.1	401.2	438.2	494.3	581.6	675.1
65°	292.7	292.7	294.6	302.0	306.9	319.6	337.2	364.1	409.2	477.2	556.9
67.5°	245.9	248.3	247.7	251.0	255.5	265.3	278.0	300.2	333.6	383.2	447.0
70°	215.4	217.3	216.8	219.2	224.1	230.5	240.8	261.8	285.8	328.4	383.2
72.5°	187.9	188.7	187.5	190.7	193.6	199.2	210.7	221.9	244.3	280.2	325.3
75°	143.9	144.9	145.8	147.8	150.7	153.6	159.6	170.8	185.5	212.4	241.3
77.5°	107.8	106.0	108.4	108.1	109.7	112.0	117.2	123.1	135.2	152.2	174.6
80°	81.2	81.7	81.7	82.2	84.6	86.1	90.6	94.9	104.2	117.0	132.6
82.5°	59.3	60.6	59.9	60.7	62.8	63.8	66.3	69.8	75.3	85.3	96.6
85°	32.3	29.9	30.8	31.9	31.9	32.3	34.2	35.7	38.6	42.6	46.9
87.5°	11.0	11.8	12.1	12.1	12.3	12.3	13.9	13.8	14.8	15.9	17.4
90°	8.0	7.7	7.5	7.4	7.1	6.8	6.4	6.0	5.7	5.4	4.8
92.5°	7.4	7.4	7.3	7.2	7.1	6.8	6.4	6.0	5.7	5.4	4.9
95°	7.0	7.0	7.0	7.0	7.0	6.8	6.4	6.0	5.7	5.4	8.1
97.5°	7.0	7.0	7.0	7.0	7.0	8.0	10.1	12.3	14.3	16.4	22.0
100°	7.0	7.3	7.6	7.9	8.2	13.9	24.9	35.9	46.9	58.0	57.7
102.5°	41.9	46.9	52.0	57.0	62.0	65.6	67.7	69.7	71.9	74.0	73.8
105°	99.0	99.1	99.1	99.2	99.2	99.2	99.2	99.2	99.2	99.2	99.2
107.5°	124.7	125.0	125.2	125.5	125.6	125.7	125.7	125.7	125.6	125.6	125.5
110°	142.6	142.5	142.4	142.4	142.3	142.4	142.6	142.8	143.1	143.3	143.1



TEST NUMBER: P333205-830

CATALOG NUMBER: S125DIP-S850D365U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	158.6	158.7	158.8	158.9	159.0	159.2	159.5	159.8	160.0	160.3	160.2
115°	182.6	183.0	183.5	183.9	184.4	184.7	185.0	185.3	185.6	185.9	185.9
117.5°	208.2	208.4	208.6	208.8	209.0	209.2	209.6	210.0	210.4	210.8	210.5
120°	223.9	224.2	224.6	225.0	225.4	225.6	225.7	225.9	226.1	226.2	226.0
122.5°	238.8	239.2	239.7	240.1	240.5	240.8	241.0	241.1	241.3	241.4	241.3
125°	261.6	261.7	262.0	262.2	262.4	262.7	263.0	263.3	263.5	263.9	263.9
127.5°	280.7	281.3	281.7	282.3	282.9	283.2	283.3	283.5	283.7	283.9	283.9
130°	294.5	294.9	295.3	295.7	296.0	296.3	296.5	296.7	297.0	297.2	297.1
132.5°	307.4	307.6	308.0	308.4	308.8	309.0	309.1	309.1	309.2	309.2	309.3
135°	324.8	325.3	325.7	326.2	326.6	326.9	327.1	327.3	327.3	327.5	327.6
137.5°	342.4	342.8	343.2	343.6	343.9	344.1	344.1	344.1	344.0	344.0	344.1
140°	352.8	353.3	353.7	354.2	354.6	354.8	354.6	354.5	354.3	354.2	354.2
142.5°	362.7	363.2	363.5	364.0	364.5	364.7	364.7	364.6	364.6	364.6	364.5
145°	377.1	377.6	378.1	378.5	378.9	379.1	379.0	379.0	378.9	378.8	378.8
147.5°	389.1	389.6	390.1	390.7	391.2	391.4	391.3	391.2	391.2	391.1	391.0
150°	396.8	397.4	398.0	398.6	399.2	399.4	399.3	399.1	399.0	398.8	398.7
152.5°	404.0	404.5	405.1	405.6	406.1	406.3	406.1	406.0	405.9	405.8	405.6
155°	413.5	414.1	414.6	415.3	415.8	416.0	415.8	415.6	415.4	415.1	415.0
157.5°	421.4	422.0	422.5	423.2	423.8	424.0	423.7	423.5	423.2	423.0	423.0
160°	426.5	427.1	427.6	428.2	428.9	429.0	428.7	428.4	428.1	427.8	427.7
162.5°	431.0	431.7	432.3	432.9	433.6	433.8	433.3	432.9	432.4	432.1	432.0
165°	437.2	437.7	438.3	438.9	439.5	439.6	439.1	438.7	438.2	437.8	437.7
167.5°	441.4	442.1	442.7	443.4	444.0	444.1	443.6	443.1	442.5	442.0	442.0
170°	443.7	444.4	445.2	445.8	446.5	446.5	445.9	445.3	444.7	444.1	444.0
172.5°	445.4	446.0	446.7	447.4	448.1	448.1	447.6	447.0	446.5	446.0	445.8
175°	447.4	448.1	448.7	449.4	450.2	450.2	449.6	448.9	448.4	447.8	447.7
177.5°	448.7	449.1	449.6	450.1	450.5	450.5	450.2	449.8	449.3	448.9	448.8
180°	449.4	449.4	449.4	449.4	449.4	449.4	449.4	449.4	449.4	449.4	449.4



TEST NUMBER: P333205-830

CATALOG NUMBER: S125DIP-S850D365U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1
2.5°	1186.4	1183.6	1180.4	1175.0	1168.4	1164.8	1159.3	1155.8	1148.8	1142.9	1136.6
5°	1246.5	1233.8	1222.1	1206.9	1190.2	1179.5	1166.8	1152.5	1137.9	1122.8	1106.1
7.5°	1308.9	1286.4	1261.9	1235.6	1209.8	1186.2	1163.6	1141.3	1120.6	1095.5	1074.3
10°	1350.8	1322.4	1292.0	1256.3	1221.6	1191.3	1160.5	1133.5	1106.1	1076.8	1050.7
12.5°	1392.7	1354.9	1312.0	1272.8	1231.0	1194.4	1158.1	1123.7	1089.3	1056.8	1026.5
15°	1422.3	1388.9	1349.3	1293.5	1246.5	1196.2	1148.2	1103.6	1062.1	1025.9	987.7
17.5°	1441.7	1398.8	1356.3	1302.8	1241.1	1184.8	1130.5	1079.5	1032.6	986.7	949.9
20°	1445.3	1401.2	1356.7	1304.3	1241.1	1176.6	1122.3	1061.0	1010.7	963.2	918.1
22.5°	1444.1	1394.2	1345.7	1291.8	1230.2	1170.7	1105.0	1042.6	988.0	941.2	894.3
25°	1433.0	1379.7	1319.0	1264.7	1204.0	1140.9	1074.3	1009.7	953.9	900.5	854.0
27.5°	1423.8	1354.6	1285.9	1222.6	1163.9	1106.1	1042.4	976.2	914.4	860.3	816.4
30°	1412.5	1336.6	1259.2	1193.2	1133.0	1076.8	1016.5	952.0	887.3	834.4	787.5
32.5°	1402.3	1313.9	1232.3	1160.4	1096.6	1041.9	986.4	924.9	861.5	807.9	760.8
35°	1382.6	1280.3	1186.8	1105.6	1037.6	981.3	934.8	877.5	819.3	767.4	722.4
37.5°	1357.6	1236.2	1136.0	1050.7	976.2	916.9	873.6	829.6	773.7	723.8	683.1
40°	1338.0	1204.9	1098.7	1011.6	934.3	872.6	832.5	790.9	744.4	698.0	654.9
42.5°	1313.4	1176.8	1061.2	967.4	890.8	830.8	788.6	753.3	712.3	668.9	629.0
45°	1268.1	1125.7	1000.4	899.6	822.2	763.0	719.4	693.1	662.2	621.0	587.3
47.5°	1201.5	1064.3	934.7	830.7	750.8	696.0	655.2	629.8	608.0	577.5	546.9
50°	1142.3	1018.5	887.3	784.0	704.3	648.9	611.3	588.2	569.7	546.2	520.3
52.5°	1076.1	960.9	840.7	738.7	659.7	605.1	568.3	548.0	532.5	515.7	490.1
55°	971.0	873.2	761.6	664.6	591.7	538.4	506.1	488.4	475.7	463.0	447.3
57.5°	855.2	778.6	679.8	591.3	524.1	475.5	445.4	428.2	418.4	411.8	402.6
60°	773.7	708.2	623.0	542.2	476.7	433.7	404.3	391.1	382.8	377.3	370.5
62.5°	698.2	644.4	565.4	491.7	434.4	393.7	367.5	354.7	346.7	344.0	338.4
65°	586.8	545.3	480.1	419.0	370.0	335.3	313.2	301.0	296.1	293.1	293.7
67.5°	477.1	451.8	399.4	347.3	308.2	279.1	261.5	252.0	249.6	245.7	245.6
70°	410.1	391.1	347.0	301.5	266.7	244.2	228.6	218.8	216.3	214.3	213.9
72.5°	351.0	334.3	296.1	259.6	228.4	208.6	195.7	189.8	185.8	184.6	184.5
75°	263.8	254.5	224.1	195.3	173.7	160.0	151.3	145.8	142.9	142.4	142.9
77.5°	187.6	179.5	160.1	139.7	126.1	115.7	108.3	106.4	103.1	103.2	102.6
80°	140.9	135.5	123.4	107.2	96.0	87.1	83.2	79.7	78.8	77.3	78.8
82.5°	102.2	96.4	88.1	77.9	68.5	63.2	59.3	58.2	57.7	56.9	57.3
85°	50.4	50.9	46.0	38.2	34.2	31.3	28.8	28.8	28.4	27.9	28.4
87.5°	18.1	17.2	15.6	14.2	12.2	10.8	10.4	10.7	9.6	9.3	9.8
90°	4.3	3.8	3.3	2.7	2.1	1.5	0.9	0.4	0.9	1.5	2.1
92.5°	4.4	4.0	3.5	3.5	3.9	4.3	4.7	5.1	4.7	4.3	3.9
95°	10.9	13.8	16.6	18.1	18.3	18.6	18.8	18.9	18.8	18.6	18.3
97.5°	27.5	33.1	38.6	41.3	40.8	40.4	40.1	39.7	40.1	40.4	40.8
100°	57.4	57.1	56.7	56.6	56.3	56.1	55.9	55.6	55.9	56.1	56.3
102.5°	73.6	73.4	73.2	73.0	72.8	72.5	72.2	71.9	72.2	72.5	72.8
105°	99.2	99.2	99.2	99.2	98.9	98.6	98.2	97.9	98.2	98.6	98.9
107.5°	125.4	125.3	125.1	125.0	125.0	125.0	125.0	125.0	125.0	125.0	125.0
110°	143.0	142.8	142.7	142.6	142.6	142.6	142.6	142.6	142.6	142.6	142.6



TEST NUMBER: P333205-830

CATALOG NUMBER: S125DIP-S850D365U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	160.1	160.0	159.9	159.9	159.7	159.5	159.3	159.1	159.3	159.5	159.7
115°	185.8	185.7	185.6	185.4	185.0	184.6	184.3	183.9	184.3	184.6	185.0
117.5°	210.2	209.9	209.6	209.5	209.5	209.5	209.5	209.5	209.5	209.5	209.5
120°	225.7	225.6	225.4	225.3	225.4	225.5	225.5	225.6	225.5	225.5	225.4
122.5°	241.2	241.1	241.0	240.8	240.5	240.3	240.0	239.7	240.0	240.3	240.5
125°	263.9	263.9	263.9	263.6	263.1	262.6	262.0	261.6	262.0	262.6	263.1
127.5°	284.0	284.0	284.1	283.9	283.5	283.1	282.8	282.4	282.8	283.1	283.5
130°	297.0	297.0	296.9	296.7	296.3	296.0	295.6	295.2	295.6	296.0	296.3
132.5°	309.5	309.7	309.8	309.7	309.2	308.9	308.4	308.0	308.4	308.9	309.2
135°	327.8	327.9	328.1	327.9	327.5	327.1	326.6	326.2	326.6	327.1	327.5
137.5°	344.3	344.4	344.6	344.4	344.0	343.7	343.3	342.9	343.3	343.7	344.0
140°	354.3	354.4	354.5	354.4	354.3	354.1	354.0	353.8	354.0	354.1	354.3
142.5°	364.4	364.3	364.1	364.0	363.9	363.9	363.8	363.7	363.8	363.9	363.9
145°	378.8	378.8	378.8	378.7	378.6	378.4	378.3	378.1	378.3	378.4	378.6
147.5°	390.9	390.8	390.7	390.7	390.7	390.8	390.8	390.8	390.8	390.8	390.7
150°	398.5	398.3	398.2	398.2	398.3	398.5	398.7	398.8	398.7	398.5	398.3
152.5°	405.5	405.3	405.1	405.2	405.6	405.9	406.2	406.5	406.2	405.9	405.6
155°	414.8	414.7	414.5	414.7	415.1	415.6	416.0	416.5	416.0	415.6	415.1
157.5°	423.0	422.9	422.9	423.1	423.3	423.6	423.9	424.1	423.9	423.6	423.3
160°	427.6	427.5	427.5	427.7	428.1	428.6	429.0	429.4	429.0	428.6	428.1
162.5°	431.9	431.9	431.8	432.0	432.3	432.8	433.3	433.8	433.3	432.8	432.3
165°	437.6	437.5	437.5	437.7	438.1	438.6	439.0	439.4	439.0	438.6	438.1
167.5°	441.9	441.8	441.7	441.9	442.3	442.8	443.3	443.7	443.3	442.8	442.3
170°	443.9	443.9	443.8	444.0	444.6	445.1	445.6	446.1	445.6	445.1	444.6
172.5°	445.7	445.5	445.4	445.6	446.2	446.7	447.2	447.7	447.2	446.7	446.2
175°	447.6	447.5	447.5	447.7	448.1	448.6	449.0	449.4	449.0	448.6	448.1
177.5°	448.8	448.7	448.7	448.8	449.2	449.5	449.9	450.3	449.9	449.5	449.2
180°	449.4	449.4	449.4	449.4	449.4	449.4	449.4	449.4	449.4	449.4	449.4



TEST NUMBER: P333205-830

CATALOG NUMBER: S125DIP-S850D365U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1
2.5°	1133.1	1128.8	1125.3	1117.5	1113.1	1107.3	1102.6	1107.7	1102.2	1104.6	1101.0
5°	1097.8	1084.1	1074.3	1060.1	1047.8	1036.6	1028.3	1026.8	1022.8	1021.0	1015.0
7.5°	1055.3	1038.1	1021.3	1002.8	987.0	971.1	960.9	952.5	947.0	939.6	934.6
10°	1030.2	1007.2	987.7	965.2	945.6	928.4	914.7	907.9	901.5	892.2	888.8
12.5°	999.3	975.5	951.6	927.6	908.8	889.7	877.9	867.5	863.2	852.6	851.6
15°	962.2	926.5	903.0	878.5	852.5	836.9	827.1	815.9	811.0	803.6	798.2
17.5°	917.9	886.1	856.7	831.3	809.1	795.9	783.7	776.0	767.6	762.8	754.0
20°	885.9	855.5	826.1	799.2	782.1	766.9	757.1	749.8	741.0	738.6	729.7
22.5°	858.8	825.4	797.2	774.6	755.8	738.8	728.1	723.2	717.1	709.5	707.8
25°	814.9	780.1	756.2	733.7	717.0	701.3	694.0	687.7	681.7	676.4	674.4
27.5°	776.9	745.8	717.4	697.0	682.6	668.3	661.8	654.0	649.8	645.5	640.2
30°	750.3	718.5	693.5	673.9	658.3	645.5	638.7	633.3	629.4	625.5	622.5
32.5°	722.8	693.4	669.2	650.1	634.4	624.8	618.7	614.9	610.6	605.9	602.2
35°	686.6	654.3	630.8	614.3	602.0	594.7	587.8	584.4	579.5	579.5	575.5
37.5°	645.8	617.9	597.2	582.0	571.1	564.5	557.0	554.7	551.6	549.5	548.2
40°	621.6	595.6	576.1	560.9	549.1	543.8	537.9	534.0	532.0	529.5	528.6
42.5°	596.5	571.7	553.0	538.9	528.8	524.1	518.7	515.9	512.0	508.8	508.2
45°	558.5	534.4	517.4	506.1	497.3	491.9	488.4	482.6	480.6	476.7	476.2
47.5°	522.3	499.3	482.5	473.3	465.5	461.1	455.7	449.9	447.6	445.6	445.4
50°	495.3	474.3	458.5	449.8	442.4	436.1	430.6	426.8	425.3	425.3	426.3
52.5°	467.9	450.0	436.7	425.9	419.0	412.2	407.2	404.8	402.6	404.9	406.7
55°	427.7	409.6	399.8	389.6	382.8	374.8	372.5	371.5	370.0	373.9	375.9
57.5°	385.3	372.6	361.1	350.9	344.8	340.3	337.0	336.3	339.0	340.9	347.3
60°	358.3	343.6	333.3	325.5	318.1	315.2	314.2	313.2	315.2	320.6	328.9
62.5°	328.5	316.6	305.5	299.6	294.3	289.4	289.2	289.7	293.7	299.8	308.1
65°	284.8	274.6	267.2	260.3	256.0	253.1	254.0	256.0	260.3	268.7	278.0
67.5°	240.5	233.5	226.9	221.3	217.1	217.1	218.1	221.0	226.2	235.8	244.3
70°	211.9	204.1	198.7	196.2	192.8	190.9	193.8	198.7	203.1	211.9	219.2
72.5°	183.3	176.7	172.5	170.8	169.4	167.8	168.7	174.0	180.0	188.8	197.4
75°	140.9	138.5	135.5	133.7	132.1	133.1	134.1	139.0	143.9	153.2	163.0
77.5°	102.8	100.3	98.6	98.1	97.3	97.7	100.6	104.2	109.0	115.7	123.1
80°	77.9	76.8	75.9	75.4	75.4	75.9	79.7	82.2	86.6	93.0	98.9
82.5°	56.6	56.1	55.9	55.8	56.2	56.3	58.6	61.8	65.5	70.3	75.4
85°	29.9	28.8	30.3	30.8	29.9	31.3	32.3	34.2	35.7	38.2	40.6
87.5°	10.4	11.2	10.9	11.4	11.5	12.4	12.1	13.8	14.6	15.5	15.1
90°	2.7	3.3	3.8	4.3	4.8	5.4	5.7	6.0	6.4	6.8	7.1
92.5°	3.5	3.5	4.0	4.4	4.9	5.4	5.7	6.0	6.4	6.8	7.1
95°	18.1	16.6	13.8	10.9	8.1	5.4	5.7	6.0	6.4	6.8	7.0
97.5°	41.3	38.6	33.1	27.5	22.0	16.4	14.3	12.3	10.1	8.0	7.0
100°	56.6	56.7	57.1	57.4	57.7	58.0	46.9	35.9	24.9	13.9	8.2
102.5°	73.0	73.2	73.4	73.6	73.8	74.0	71.9	69.7	67.7	65.6	62.0
105°	99.2	99.2	99.2	99.2	99.2	99.2	99.2	99.2	99.2	99.2	99.2
107.5°	125.0	125.1	125.3	125.4	125.5	125.6	125.6	125.7	125.7	125.7	125.6
110°	142.6	142.7	142.8	143.0	143.1	143.3	143.1	142.8	142.6	142.4	142.3



TEST NUMBER: P333205-830

CATALOG NUMBER: S125DIP-S850D365U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	159.9	159.9	160.0	160.1	160.2	160.3	160.0	159.8	159.5	159.2	159.0
115°	185.4	185.6	185.7	185.8	185.9	185.9	185.6	185.3	185.0	184.7	184.4
117.5°	209.5	209.6	209.9	210.2	210.5	210.8	210.4	210.0	209.6	209.2	209.0
120°	225.3	225.4	225.6	225.7	226.0	226.2	226.1	225.9	225.7	225.6	225.4
122.5°	240.8	241.0	241.1	241.2	241.3	241.4	241.3	241.1	241.0	240.8	240.5
125°	263.6	263.9	263.9	263.9	263.9	263.9	263.5	263.3	263.0	262.7	262.4
127.5°	283.9	284.1	284.0	284.0	283.9	283.9	283.7	283.5	283.3	283.2	282.9
130°	296.7	296.9	297.0	297.0	297.1	297.2	297.0	296.7	296.5	296.3	296.0
132.5°	309.7	309.8	309.7	309.5	309.3	309.2	309.2	309.1	309.1	309.0	308.8
135°	327.9	328.1	327.9	327.8	327.6	327.5	327.3	327.3	327.1	326.9	326.6
137.5°	344.4	344.6	344.4	344.3	344.1	344.0	344.0	344.1	344.1	344.1	343.9
140°	354.4	354.5	354.4	354.3	354.2	354.2	354.3	354.5	354.6	354.8	354.6
142.5°	364.0	364.1	364.3	364.4	364.5	364.6	364.6	364.6	364.7	364.7	364.5
145°	378.7	378.8	378.8	378.8	378.8	378.8	378.9	379.0	379.0	379.1	378.9
147.5°	390.7	390.7	390.8	390.9	391.0	391.1	391.2	391.2	391.3	391.4	391.2
150°	398.2	398.2	398.3	398.5	398.7	398.8	399.0	399.1	399.3	399.4	399.2
152.5°	405.2	405.1	405.3	405.5	405.6	405.8	405.9	406.0	406.1	406.3	406.1
155°	414.7	414.5	414.7	414.8	415.0	415.1	415.4	415.6	415.8	416.0	415.8
157.5°	423.1	422.9	422.9	423.0	423.0	423.0	423.2	423.5	423.7	424.0	423.8
160°	427.7	427.5	427.5	427.6	427.7	427.8	428.1	428.4	428.7	429.0	428.9
162.5°	432.0	431.8	431.9	431.9	432.0	432.1	432.4	432.9	433.3	433.8	433.6
165°	437.7	437.5	437.5	437.6	437.7	437.8	438.2	438.7	439.1	439.6	439.5
167.5°	441.9	441.7	441.8	441.9	442.0	442.0	442.5	443.1	443.6	444.1	444.0
170°	444.0	443.8	443.9	443.9	444.0	444.1	444.7	445.3	445.9	446.5	446.5
172.5°	445.6	445.4	445.5	445.7	445.8	446.0	446.5	447.0	447.6	448.1	448.1
175°	447.7	447.5	447.5	447.6	447.7	447.8	448.4	448.9	449.6	450.2	450.2
177.5°	448.8	448.7	448.7	448.8	448.8	448.9	449.3	449.8	450.2	450.5	450.5
180°	449.4	449.4	449.4	449.4	449.4	449.4	449.4	449.4	449.4	449.4	449.4



TEST NUMBER: P333205-830

CATALOG NUMBER: S125DIP-S850D365U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1
2.5°	1098.6	1101.4	1099.0	1102.2	1099.0	1101.4	1098.6	1101.0	1104.6	1102.2	1107.7
5°	1012.6	1008.2	1011.2	1009.2	1011.2	1008.2	1012.6	1015.0	1021.0	1022.8	1026.8
7.5°	933.1	928.9	924.2	921.9	924.2	928.9	933.1	934.6	939.6	947.0	952.5
10°	883.4	878.0	877.5	874.1	877.5	878.0	883.4	888.8	892.2	901.5	907.9
12.5°	847.0	842.0	836.4	835.0	836.4	842.0	847.0	851.6	852.6	863.2	867.5
15°	795.3	791.4	788.0	790.9	788.0	791.4	795.3	798.2	803.6	811.0	815.9
17.5°	752.3	749.1	748.5	744.9	748.5	749.1	752.3	754.0	762.8	767.6	776.0
20°	725.3	722.8	723.9	717.5	723.9	722.8	725.3	729.7	738.6	741.0	749.8
22.5°	703.8	699.0	698.4	697.1	698.4	699.0	703.8	707.8	709.5	717.1	723.2
25°	670.1	667.6	665.2	667.6	665.2	667.6	670.1	674.4	676.4	681.7	687.7
27.5°	640.6	637.6	637.0	637.3	637.0	637.6	640.6	640.2	645.5	649.8	654.0
30°	622.5	617.6	618.1	617.6	618.1	617.6	622.5	622.5	625.5	629.4	633.3
32.5°	602.9	599.6	599.0	598.0	599.0	599.6	602.9	602.2	605.9	610.6	614.9
35°	574.1	574.1	571.7	571.7	571.7	574.1	574.1	575.5	579.5	579.5	584.4
37.5°	547.0	546.5	545.0	545.3	545.0	546.5	547.0	548.2	549.5	551.6	554.7
40°	526.6	526.1	524.6	521.7	524.6	526.1	526.6	528.6	529.5	532.0	534.0
42.5°	507.0	505.4	504.7	503.7	504.7	505.4	507.0	508.2	508.8	512.0	515.9
45°	476.2	476.2	475.2	474.8	475.2	476.2	476.2	476.2	476.7	480.6	482.6
47.5°	446.3	447.1	449.0	448.7	449.0	447.1	446.3	445.4	445.6	447.6	449.9
50°	428.2	428.8	430.2	430.6	430.2	428.8	428.2	426.3	425.3	425.3	426.8
52.5°	408.3	411.1	412.9	412.6	412.9	411.1	408.3	406.7	404.9	402.6	404.8
55°	380.3	383.7	387.1	387.7	387.1	383.7	380.3	375.9	373.9	370.0	371.5
57.5°	352.6	357.4	361.0	362.1	361.0	357.4	352.6	347.3	340.9	339.0	336.3
60°	333.8	340.2	344.6	346.5	344.6	340.2	333.8	328.9	320.6	315.2	313.2
62.5°	315.8	322.9	327.3	327.7	327.3	322.9	315.8	308.1	299.8	293.7	289.7
65°	286.3	293.7	297.6	300.5	297.6	293.7	286.3	278.0	268.7	260.3	256.0
67.5°	254.6	261.9	266.3	268.6	266.3	261.9	254.6	244.3	235.8	226.2	221.0
70°	231.5	238.8	244.7	246.7	244.7	238.8	231.5	219.2	211.9	203.1	198.7
72.5°	208.8	215.4	220.1	222.3	220.1	215.4	208.8	197.4	188.8	180.0	174.0
75°	169.4	178.1	182.6	185.0	182.6	178.1	169.4	163.0	153.2	143.9	139.0
77.5°	130.5	138.6	141.3	142.5	141.3	138.6	130.5	123.1	115.7	109.0	104.2
80°	104.7	109.6	113.0	113.6	113.0	109.6	104.7	98.9	93.0	86.6	82.2
82.5°	80.5	84.5	85.7	86.9	85.7	84.5	80.5	75.4	70.3	65.5	61.8
85°	44.0	46.0	46.5	46.0	46.5	46.0	44.0	40.6	38.2	35.7	34.2
87.5°	15.9	15.6	15.6	16.5	15.6	15.6	15.9	15.1	15.5	14.6	13.8
90°	7.4	7.5	7.7	8.0	7.7	7.5	7.4	7.1	6.8	6.4	6.0
92.5°	7.2	7.3	7.4	7.4	7.4	7.3	7.2	7.1	6.8	6.4	6.0
95°	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	6.8	6.4	6.0
97.5°	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	8.0	10.1	12.3
100°	7.9	7.6	7.3	7.0	7.3	7.6	7.9	8.2	13.9	24.9	35.9
102.5°	57.0	52.0	46.9	41.9	46.9	52.0	57.0	62.0	65.6	67.7	69.7
105°	99.2	99.1	99.1	99.0	99.1	99.1	99.2	99.2	99.2	99.2	99.2
107.5°	125.5	125.2	125.0	124.7	125.0	125.2	125.5	125.6	125.7	125.7	125.7
110°	142.4	142.4	142.5	142.6	142.5	142.4	142.4	142.3	142.4	142.6	142.8



TEST NUMBER: P333205-830

CATALOG NUMBER: S125DIP-S850D365U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	158.9	158.8	158.7	158.6	158.7	158.8	158.9	159.0	159.2	159.5	159.8
115°	183.9	183.5	183.0	182.6	183.0	183.5	183.9	184.4	184.7	185.0	185.3
117.5°	208.8	208.6	208.4	208.2	208.4	208.6	208.8	209.0	209.2	209.6	210.0
120°	225.0	224.6	224.2	223.9	224.2	224.6	225.0	225.4	225.6	225.7	225.9
122.5°	240.1	239.7	239.2	238.8	239.2	239.7	240.1	240.5	240.8	241.0	241.1
125°	262.2	262.0	261.7	261.6	261.7	262.0	262.2	262.4	262.7	263.0	263.3
127.5°	282.3	281.7	281.3	280.7	281.3	281.7	282.3	282.9	283.2	283.3	283.5
130°	295.7	295.3	294.9	294.5	294.9	295.3	295.7	296.0	296.3	296.5	296.7
132.5°	308.4	308.0	307.6	307.4	307.6	308.0	308.4	308.8	309.0	309.1	309.1
135°	326.2	325.7	325.3	324.8	325.3	325.7	326.2	326.6	326.9	327.1	327.3
137.5°	343.6	343.2	342.8	342.4	342.8	343.2	343.6	343.9	344.1	344.1	344.1
140°	354.2	353.7	353.3	352.8	353.3	353.7	354.2	354.6	354.8	354.6	354.5
142.5°	364.0	363.5	363.2	362.7	363.2	363.5	364.0	364.5	364.7	364.7	364.6
145°	378.5	378.1	377.6	377.1	377.6	378.1	378.5	378.9	379.1	379.0	379.0
147.5°	390.7	390.1	389.6	389.1	389.6	390.1	390.7	391.2	391.4	391.3	391.2
150°	398.6	398.0	397.4	396.8	397.4	398.0	398.6	399.2	399.4	399.3	399.1
152.5°	405.6	405.1	404.5	404.0	404.5	405.1	405.6	406.1	406.3	406.1	406.0
155°	415.3	414.6	414.1	413.5	414.1	414.6	415.3	415.8	416.0	415.8	415.6
157.5°	423.2	422.5	422.0	421.4	422.0	422.5	423.2	423.8	424.0	423.7	423.5
160°	428.2	427.6	427.1	426.5	427.1	427.6	428.2	428.9	429.0	428.7	428.4
162.5°	432.9	432.3	431.7	431.0	431.7	432.3	432.9	433.6	433.8	433.3	432.9
165°	438.9	438.3	437.7	437.2	437.7	438.3	438.9	439.5	439.6	439.1	438.7
167.5°	443.4	442.7	442.1	441.4	442.1	442.7	443.4	444.0	444.1	443.6	443.1
170°	445.8	445.2	444.4	443.7	444.4	445.2	445.8	446.5	446.5	445.9	445.3
172.5°	447.4	446.7	446.0	445.4	446.0	446.7	447.4	448.1	448.1	447.6	447.0
175°	449.4	448.7	448.1	447.4	448.1	448.7	449.4	450.2	450.2	449.6	448.9
177.5°	450.1	449.6	449.1	448.7	449.1	449.6	450.1	450.5	450.5	450.2	449.8
180°	449.4	449.4	449.4	449.4	449.4	449.4	449.4	449.4	449.4	449.4	449.4



TEST NUMBER: P333205-830

CATALOG NUMBER: S125DIP-S850D365U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1
2.5°	1102.6	1107.3	1113.1	1117.5	1125.3	1128.8	1133.1	1136.6	1142.9	1148.8	1155.8
5°	1028.3	1036.6	1047.8	1060.1	1074.3	1084.1	1097.8	1106.1	1122.8	1137.9	1152.5
7.5°	960.9	971.1	987.0	1002.8	1021.3	1038.1	1055.3	1074.3	1095.5	1120.6	1141.3
10°	914.7	928.4	945.6	965.2	987.7	1007.2	1030.2	1050.7	1076.8	1106.1	1133.5
12.5°	877.9	889.7	908.8	927.6	951.6	975.5	999.3	1026.5	1056.8	1089.3	1123.7
15°	827.1	836.9	852.5	878.5	903.0	926.5	962.2	987.7	1025.9	1062.1	1103.6
17.5°	783.7	795.9	809.1	831.3	856.7	886.1	917.9	949.9	986.7	1032.6	1079.5
20°	757.1	766.9	782.1	799.2	826.1	855.5	885.9	918.1	963.2	1010.7	1061.0
22.5°	728.1	738.8	755.8	774.6	797.2	825.4	858.8	894.3	941.2	988.0	1042.6
25°	694.0	701.3	717.0	733.7	756.2	780.1	814.9	854.0	900.5	953.9	1009.7
27.5°	661.8	668.3	682.6	697.0	717.4	745.8	776.9	816.4	860.3	914.4	976.2
30°	638.7	645.5	658.3	673.9	693.5	718.5	750.3	787.5	834.4	887.3	952.0
32.5°	618.7	624.8	634.4	650.1	669.2	693.4	722.8	760.8	807.9	861.5	924.9
35°	587.8	594.7	602.0	614.3	630.8	654.3	686.6	722.4	767.4	819.3	877.5
37.5°	557.0	564.5	571.1	582.0	597.2	617.9	645.8	683.1	723.8	773.7	829.6
40°	537.9	543.8	549.1	560.9	576.1	595.6	621.6	654.9	698.0	744.4	790.9
42.5°	518.7	524.1	528.8	538.9	553.0	571.7	596.5	629.0	668.9	712.3	753.3
45°	488.4	491.9	497.3	506.1	517.4	534.4	558.5	587.3	621.0	662.2	693.1
47.5°	455.7	461.1	465.5	473.3	482.5	499.3	522.3	546.9	577.5	608.0	629.8
50°	430.6	436.1	442.4	449.8	458.5	474.3	495.3	520.3	546.2	569.7	588.2
52.5°	407.2	412.2	419.0	425.9	436.7	450.0	467.9	490.1	515.7	532.5	548.0
55°	372.5	374.8	382.8	389.6	399.8	409.6	427.7	447.3	463.0	475.7	488.4
57.5°	337.0	340.3	344.8	350.9	361.1	372.6	385.3	402.6	411.8	418.4	428.2
60°	314.2	315.2	318.1	325.5	333.3	343.6	358.3	370.5	377.3	382.8	391.1
62.5°	289.2	289.4	294.3	299.6	305.5	316.6	328.5	338.4	344.0	346.7	354.7
65°	254.0	253.1	256.0	260.3	267.2	274.6	284.8	293.7	293.1	296.1	301.0
67.5°	218.1	217.1	217.1	221.3	226.9	233.5	240.5	245.6	245.7	249.6	252.0
70°	193.8	190.9	192.8	196.2	198.7	204.1	211.9	213.9	214.3	216.3	218.8
72.5°	168.7	167.8	169.4	170.8	172.5	176.7	183.3	184.5	184.6	185.8	189.8
75°	134.1	133.1	132.1	133.7	135.5	138.5	140.9	142.9	142.4	142.9	145.8
77.5°	100.6	97.7	97.3	98.1	98.6	100.3	102.8	102.6	103.2	103.1	106.4
80°	79.7	75.9	75.4	75.4	75.9	76.8	77.9	78.8	77.3	78.8	79.7
82.5°	58.6	56.3	56.2	55.8	55.9	56.1	56.6	57.3	56.9	57.7	58.2
85°	32.3	31.3	29.9	30.8	30.3	28.8	29.9	28.4	27.9	28.4	28.8
87.5°	12.1	12.4	11.5	11.4	10.9	11.2	10.4	9.8	9.3	9.6	10.7
90°	5.7	5.4	4.8	4.3	3.8	3.3	2.7	2.1	1.5	0.9	0.4
92.5°	5.7	5.4	4.9	4.4	4.0	3.5	3.5	3.9	4.3	4.7	5.1
95°	5.7	5.4	8.1	10.9	13.8	16.6	18.1	18.3	18.6	18.8	18.9
97.5°	14.3	16.4	22.0	27.5	33.1	38.6	41.3	40.8	40.4	40.1	39.7
100°	46.9	58.0	57.7	57.4	57.1	56.7	56.6	56.3	56.1	55.9	55.6
102.5°	71.9	74.0	73.8	73.6	73.4	73.2	73.0	72.8	72.5	72.2	71.9
105°	99.2	99.2	99.2	99.2	99.2	99.2	99.2	98.9	98.6	98.2	97.9
107.5°	125.6	125.6	125.5	125.4	125.3	125.1	125.0	125.0	125.0	125.0	125.0
110°	143.1	143.3	143.1	143.0	142.8	142.7	142.6	142.6	142.6	142.6	142.6



TEST NUMBER: P333205-830

CATALOG NUMBER: S125DIP-S850D365U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	160.0	160.3	160.2	160.1	160.0	159.9	159.9	159.7	159.5	159.3	159.1
115°	185.6	185.9	185.9	185.8	185.7	185.6	185.4	185.0	184.6	184.3	183.9
117.5°	210.4	210.8	210.5	210.2	209.9	209.6	209.5	209.5	209.5	209.5	209.5
120°	226.1	226.2	226.0	225.7	225.6	225.4	225.3	225.4	225.5	225.5	225.6
122.5°	241.3	241.4	241.3	241.2	241.1	241.0	240.8	240.5	240.3	240.0	239.7
125°	263.5	263.9	263.9	263.9	263.9	263.9	263.6	263.1	262.6	262.0	261.6
127.5°	283.7	283.9	283.9	284.0	284.0	284.1	283.9	283.5	283.1	282.8	282.4
130°	297.0	297.2	297.1	297.0	297.0	296.9	296.7	296.3	296.0	295.6	295.2
132.5°	309.2	309.2	309.3	309.5	309.7	309.8	309.7	309.2	308.9	308.4	308.0
135°	327.3	327.5	327.6	327.8	327.9	328.1	327.9	327.5	327.1	326.6	326.2
137.5°	344.0	344.0	344.1	344.3	344.4	344.6	344.4	344.0	343.7	343.3	342.9
140°	354.3	354.2	354.2	354.3	354.4	354.5	354.4	354.3	354.1	354.0	353.8
142.5°	364.6	364.6	364.5	364.4	364.3	364.1	364.0	363.9	363.9	363.8	363.7
145°	378.9	378.8	378.8	378.8	378.8	378.8	378.7	378.6	378.4	378.3	378.1
147.5°	391.2	391.1	391.0	390.9	390.8	390.7	390.7	390.7	390.8	390.8	390.8
150°	399.0	398.8	398.7	398.5	398.3	398.2	398.2	398.3	398.5	398.7	398.8
152.5°	405.9	405.8	405.6	405.5	405.3	405.1	405.2	405.6	405.9	406.2	406.5
155°	415.4	415.1	415.0	414.8	414.7	414.5	414.7	415.1	415.6	416.0	416.5
157.5°	423.2	423.0	423.0	423.0	422.9	422.9	423.1	423.3	423.6	423.9	424.1
160°	428.1	427.8	427.7	427.6	427.5	427.5	427.7	428.1	428.6	429.0	429.4
162.5°	432.4	432.1	432.0	431.9	431.9	431.8	432.0	432.3	432.8	433.3	433.8
165°	438.2	437.8	437.7	437.6	437.5	437.5	437.7	438.1	438.6	439.0	439.4
167.5°	442.5	442.0	442.0	441.9	441.8	441.7	441.9	442.3	442.8	443.3	443.7
170°	444.7	444.1	444.0	443.9	443.9	443.8	444.0	444.6	445.1	445.6	446.1
172.5°	446.5	446.0	445.8	445.7	445.5	445.4	445.6	446.2	446.7	447.2	447.7
175°	448.4	447.8	447.7	447.6	447.5	447.5	447.7	448.1	448.6	449.0	449.4
177.5°	449.3	448.9	448.8	448.8	448.7	448.7	448.8	449.2	449.5	449.9	450.3
180°	449.4	449.4	449.4	449.4	449.4	449.4	449.4	449.4	449.4	449.4	449.4



TEST NUMBER: P333205-830

CATALOG NUMBER: S125DIP-S850D365U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1
2.5°	1159.3	1164.8	1168.4	1175.0	1180.4	1183.6	1186.4	1188.7	1191.5	1193.8	1200.4
5°	1166.8	1179.5	1190.2	1206.9	1222.1	1233.8	1246.5	1257.8	1267.2	1280.3	1290.6
7.5°	1163.6	1186.2	1209.8	1235.6	1261.9	1286.4	1308.9	1329.9	1349.1	1372.2	1392.4
10°	1160.5	1191.3	1221.6	1256.3	1292.0	1322.4	1350.8	1379.7	1400.7	1430.1	1455.0
12.5°	1158.1	1194.4	1231.0	1272.8	1312.0	1354.9	1392.7	1413.7	1445.8	1469.2	1498.9
15°	1148.2	1196.2	1246.5	1293.5	1349.3	1388.9	1422.3	1463.4	1493.2	1523.1	1555.4
17.5°	1130.5	1184.8	1241.1	1302.8	1356.3	1398.8	1441.7	1481.4	1517.0	1557.1	1597.2
20°	1122.3	1176.6	1241.1	1304.3	1356.7	1401.2	1445.3	1488.8	1528.0	1579.3	1625.9
22.5°	1105.0	1170.7	1230.2	1291.8	1345.7	1394.2	1444.1	1493.6	1545.6	1603.6	1661.9
25°	1074.3	1140.9	1204.0	1264.7	1319.0	1379.7	1433.0	1499.1	1565.7	1642.5	1715.0
27.5°	1042.4	1106.1	1163.9	1222.6	1285.9	1354.6	1423.8	1498.8	1585.9	1682.9	1785.1
30°	1016.5	1076.8	1133.0	1193.2	1259.2	1336.6	1412.5	1501.6	1602.3	1711.5	1832.9
32.5°	986.4	1041.9	1096.6	1160.4	1232.3	1313.9	1402.3	1500.0	1621.2	1745.2	1870.1
35°	934.8	981.3	1037.6	1105.6	1186.8	1280.3	1382.6	1498.1	1637.1	1779.5	1884.8
37.5°	873.6	916.9	976.2	1050.7	1136.0	1236.2	1357.6	1494.7	1642.3	1755.9	1789.8
40°	832.5	872.6	934.3	1011.6	1098.7	1204.9	1338.0	1482.9	1625.9	1698.3	1670.4
42.5°	788.6	830.8	890.8	967.4	1061.2	1176.8	1313.4	1458.3	1578.1	1605.5	1509.1
45°	719.4	763.0	822.2	899.6	1000.4	1125.7	1268.1	1399.8	1468.8	1419.3	1270.1
47.5°	655.2	696.0	750.8	830.7	934.7	1064.3	1201.5	1306.5	1311.9	1194.0	1034.5
50°	611.3	648.9	704.3	784.0	887.3	1018.5	1142.3	1225.0	1187.8	1054.2	901.0
52.5°	568.3	605.1	659.7	738.7	840.7	960.9	1076.1	1134.2	1064.1	927.0	796.1
55°	506.1	538.4	591.7	664.6	761.6	873.2	971.0	991.1	900.0	765.0	658.7
57.5°	445.4	475.5	524.1	591.3	679.8	778.6	855.2	850.9	754.7	638.8	554.5
60°	404.3	433.7	476.7	542.2	623.0	708.2	773.7	758.1	662.7	562.8	491.9
62.5°	367.5	393.7	434.4	491.7	565.4	644.4	698.2	675.1	581.6	494.3	438.2
65°	313.2	335.3	370.0	419.0	480.1	545.3	586.8	556.9	477.2	409.2	364.1
67.5°	261.5	279.1	308.2	347.3	399.4	451.8	477.1	447.0	383.2	333.6	300.2
70°	228.6	244.2	266.7	301.5	347.0	391.1	410.1	383.2	328.4	285.8	261.8
72.5°	195.7	208.6	228.4	259.6	296.1	334.3	351.0	325.3	280.2	244.3	221.9
75°	151.3	160.0	173.7	195.3	224.1	254.5	263.8	241.3	212.4	185.5	170.8
77.5°	108.3	115.7	126.1	139.7	160.1	179.5	187.6	174.6	152.2	135.2	123.1
80°	83.2	87.1	96.0	107.2	123.4	135.5	140.9	132.6	117.0	104.2	94.9
82.5°	59.3	63.2	68.5	77.9	88.1	96.4	102.2	96.6	85.3	75.3	69.8
85°	28.8	31.3	34.2	38.2	46.0	50.9	50.4	46.9	42.6	38.6	35.7
87.5°	10.4	10.8	12.2	14.2	15.6	17.2	18.1	17.4	15.9	14.8	13.8
90°	0.9	1.5	2.1	2.7	3.3	3.8	4.3	4.8	5.4	5.7	6.0
92.5°	4.7	4.3	3.9	3.5	3.5	4.0	4.4	4.9	5.4	5.7	6.0
95°	18.8	18.6	18.3	18.1	16.6	13.8	10.9	8.1	5.4	5.7	6.0
97.5°	40.1	40.4	40.8	41.3	38.6	33.1	27.5	22.0	16.4	14.3	12.3
100°	55.9	56.1	56.3	56.6	56.7	57.1	57.4	57.7	58.0	46.9	35.9
102.5°	72.2	72.5	72.8	73.0	73.2	73.4	73.6	73.8	74.0	71.9	69.7
105°	98.2	98.6	98.9	99.2	99.2	99.2	99.2	99.2	99.2	99.2	99.2
107.5°	125.0	125.0	125.0	125.0	125.1	125.3	125.4	125.5	125.6	125.6	125.7
110°	142.6	142.6	142.6	142.6	142.7	142.8	143.0	143.1	143.3	143.1	142.8



TEST NUMBER: P333205-830

CATALOG NUMBER: S125DIP-S850D365U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	159.3	159.5	159.7	159.9	159.9	160.0	160.1	160.2	160.3	160.0	159.8
115°	184.3	184.6	185.0	185.4	185.6	185.7	185.8	185.9	185.9	185.6	185.3
117.5°	209.5	209.5	209.5	209.5	209.6	209.9	210.2	210.5	210.8	210.4	210.0
120°	225.5	225.5	225.4	225.3	225.4	225.6	225.7	226.0	226.2	226.1	225.9
122.5°	240.0	240.3	240.5	240.8	241.0	241.1	241.2	241.3	241.4	241.3	241.1
125°	262.0	262.6	263.1	263.6	263.9	263.9	263.9	263.9	263.9	263.5	263.3
127.5°	282.8	283.1	283.5	283.9	284.1	284.0	284.0	283.9	283.9	283.7	283.5
130°	295.6	296.0	296.3	296.7	296.9	297.0	297.0	297.1	297.2	297.0	296.7
132.5°	308.4	308.9	309.2	309.7	309.8	309.7	309.5	309.3	309.2	309.2	309.1
135°	326.6	327.1	327.5	327.9	328.1	327.9	327.8	327.6	327.5	327.3	327.3
137.5°	343.3	343.7	344.0	344.4	344.6	344.4	344.3	344.1	344.0	344.0	344.1
140°	354.0	354.1	354.3	354.4	354.5	354.4	354.3	354.2	354.2	354.3	354.5
142.5°	363.8	363.9	363.9	364.0	364.1	364.3	364.4	364.5	364.6	364.6	364.6
145°	378.3	378.4	378.6	378.7	378.8	378.8	378.8	378.8	378.8	378.9	379.0
147.5°	390.8	390.8	390.7	390.7	390.7	390.8	390.9	391.0	391.1	391.2	391.2
150°	398.7	398.5	398.3	398.2	398.2	398.3	398.5	398.7	398.8	399.0	399.1
152.5°	406.2	405.9	405.6	405.2	405.1	405.3	405.5	405.6	405.8	405.9	406.0
155°	416.0	415.6	415.1	414.7	414.5	414.7	414.8	415.0	415.1	415.4	415.6
157.5°	423.9	423.6	423.3	423.1	422.9	422.9	423.0	423.0	423.0	423.2	423.5
160°	429.0	428.6	428.1	427.7	427.5	427.5	427.6	427.7	427.8	428.1	428.4
162.5°	433.3	432.8	432.3	432.0	431.8	431.9	431.9	432.0	432.1	432.4	432.9
165°	439.0	438.6	438.1	437.7	437.5	437.5	437.6	437.7	437.8	438.2	438.7
167.5°	443.3	442.8	442.3	441.9	441.7	441.8	441.9	442.0	442.0	442.5	443.1
170°	445.6	445.1	444.6	444.0	443.8	443.9	443.9	444.0	444.1	444.7	445.3
172.5°	447.2	446.7	446.2	445.6	445.4	445.5	445.7	445.8	446.0	446.5	447.0
175°	449.0	448.6	448.1	447.7	447.5	447.5	447.6	447.7	447.8	448.4	448.9
177.5°	449.9	449.5	449.2	448.8	448.7	448.7	448.8	448.8	448.9	449.3	449.8
180°	449.4	449.4	449.4	449.4	449.4	449.4	449.4	449.4	449.4	449.4	449.4



TEST NUMBER: P333205-830

CATALOG NUMBER: S125DIP-S850D365U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1
2.5°	1205.9	1209.1	1215.7	1213.3	1216.5	1218.0	1219.7
5°	1303.3	1319.0	1325.9	1324.8	1335.1	1332.7	1330.2
7.5°	1413.3	1429.8	1439.0	1450.5	1457.1	1457.5	1463.4
10°	1475.6	1497.1	1506.0	1518.2	1526.0	1530.4	1529.9
12.5°	1523.3	1540.2	1560.0	1565.9	1576.5	1582.1	1580.1
15°	1580.8	1607.8	1628.3	1638.6	1651.8	1655.7	1661.1
17.5°	1632.1	1668.2	1692.2	1724.1	1736.2	1743.5	1739.2
20°	1670.8	1718.3	1742.4	1780.6	1801.6	1812.8	1808.9
22.5°	1716.7	1768.1	1812.4	1845.5	1877.5	1892.7	1895.8
25°	1795.2	1865.7	1930.8	1974.3	2013.9	2023.3	2043.8
27.5°	1882.9	1966.0	2035.6	2081.4	2109.0	2119.4	2125.8
30°	1938.2	2020.8	2073.2	2102.5	2111.4	2110.4	2109.4
32.5°	1965.1	2016.9	2026.9	2018.7	1998.6	1981.6	1963.8
35°	1926.8	1888.2	1830.4	1756.1	1701.2	1646.0	1640.5
37.5°	1733.0	1609.3	1513.2	1405.8	1343.9	1305.6	1279.1
40°	1550.5	1410.0	1293.5	1203.0	1139.8	1114.9	1090.4
42.5°	1352.4	1218.1	1115.0	1039.3	991.8	964.1	944.8
45°	1098.7	980.3	899.6	844.7	807.1	785.5	773.3
47.5°	900.3	812.8	744.1	704.6	678.5	661.8	661.9
50°	793.8	710.1	664.6	633.3	610.8	597.6	600.0
52.5°	699.5	637.0	598.0	571.8	555.2	547.1	546.8
55°	584.8	539.8	514.3	495.3	484.0	474.8	476.7
57.5°	500.3	462.3	445.3	429.4	421.6	417.8	412.5
60°	447.8	418.5	403.8	391.1	383.2	380.3	374.8
62.5°	401.2	378.1	363.8	353.5	346.4	345.4	341.2
65°	337.2	319.6	306.9	302.0	294.6	292.7	292.7
67.5°	278.0	265.3	255.5	251.0	247.7	248.3	245.9
70°	240.8	230.5	224.1	219.2	216.8	217.3	215.4
72.5°	210.7	199.2	193.6	190.7	187.5	188.7	187.9
75°	159.6	153.6	150.7	147.8	145.8	144.9	143.9
77.5°	117.2	112.0	109.7	108.1	108.4	106.0	107.8
80°	90.6	86.1	84.6	82.2	81.7	81.7	81.2
82.5°	66.3	63.8	62.8	60.7	59.9	60.6	59.3
85°	34.2	32.3	31.9	31.9	30.8	29.9	32.3
87.5°	13.9	12.3	12.3	12.1	12.1	11.8	11.0
90°	6.4	6.8	7.1	7.4	7.5	7.7	8.0
92.5°	6.4	6.8	7.1	7.2	7.3	7.4	7.4
95°	6.4	6.8	7.0	7.0	7.0	7.0	7.0
97.5°	10.1	8.0	7.0	7.0	7.0	7.0	7.0
100°	24.9	13.9	8.2	7.9	7.6	7.3	7.0
102.5°	67.7	65.6	62.0	57.0	52.0	46.9	41.9
105°	99.2	99.2	99.2	99.2	99.1	99.1	99.0
107.5°	125.7	125.7	125.6	125.5	125.2	125.0	124.7
110°	142.6	142.4	142.3	142.4	142.4	142.5	142.6



TEST NUMBER: P333205-830

CATALOG NUMBER: S125DIP-S850D365U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	159.5	159.2	159.0	158.9	158.8	158.7	158.6
115°	185.0	184.7	184.4	183.9	183.5	183.0	182.6
117.5°	209.6	209.2	209.0	208.8	208.6	208.4	208.2
120°	225.7	225.6	225.4	225.0	224.6	224.2	223.9
122.5°	241.0	240.8	240.5	240.1	239.7	239.2	238.8
125°	263.0	262.7	262.4	262.2	262.0	261.7	261.6
127.5°	283.3	283.2	282.9	282.3	281.7	281.3	280.7
130°	296.5	296.3	296.0	295.7	295.3	294.9	294.5
132.5°	309.1	309.0	308.8	308.4	308.0	307.6	307.4
135°	327.1	326.9	326.6	326.2	325.7	325.3	324.8
137.5°	344.1	344.1	343.9	343.6	343.2	342.8	342.4
140°	354.6	354.8	354.6	354.2	353.7	353.3	352.8
142.5°	364.7	364.7	364.5	364.0	363.5	363.2	362.7
145°	379.0	379.1	378.9	378.5	378.1	377.6	377.1
147.5°	391.3	391.4	391.2	390.7	390.1	389.6	389.1
150°	399.3	399.4	399.2	398.6	398.0	397.4	396.8
152.5°	406.1	406.3	406.1	405.6	405.1	404.5	404.0
155°	415.8	416.0	415.8	415.3	414.6	414.1	413.5
157.5°	423.7	424.0	423.8	423.2	422.5	422.0	421.4
160°	428.7	429.0	428.9	428.2	427.6	427.1	426.5
162.5°	433.3	433.8	433.6	432.9	432.3	431.7	431.0
165°	439.1	439.6	439.5	438.9	438.3	437.7	437.2
167.5°	443.6	444.1	444.0	443.4	442.7	442.1	441.4
170°	445.9	446.5	446.5	445.8	445.2	444.4	443.7
172.5°	447.6	448.1	448.1	447.4	446.7	446.0	445.4
175°	449.6	450.2	450.2	449.4	448.7	448.1	447.4
177.5°	450.2	450.5	450.5	450.1	449.6	449.1	448.7
180°	449.4	449.4	449.4	449.4	449.4	449.4	449.4

(END OF REPORT)